





Single-Level Terminal Blocks

- Screw connection terminal
- UL E179129 (For copper wire only. One conductor in terminal only.)
- VDE (IEC 60947-7-1)
- CE (EN 60947-7-1)



Dimensions: mm [in]



See our website: www.AutomationDirect.com for complete engineering drawings

¹UL Usage Group: B, C for 300V or D for 600V

Ordering Information

Colors	Part Number	Qty	Price	Part Number	Qty	Price	Part Number	Qty	Price
Gray	KN-T12GRY	100	Retired	KN-T10GRY	100	Retired	KN-T8GRY	100	Retired
	KN-T12GRY-25	25		KN-T10GRY-25	25	Retired	KN-T8GRY-25	25	Retired
Blue	KN-T12BLU	100	Retired	KN-T10BLU	100	Retired	KN-T8BLU	100	Retired
	KN-T12BLU-25	25		KN-T10BLU-25	25	Retired	KN-T8BLU-25	25	Retired
Brown	KN-T12BRN	100	Retired	KN-T10BRN	100	Retired	KN-T8BRN	100	Retired
	KN-T12BRN-25	25		KN-T10BRN-25	25	Retired	KN-T8BRN-25	25	Retired
Black	KN-T12BLK	100	Retired	KN-T10BLK	100	Retired	KN-T8BLK	100	Retired
	KN-T12BLK-25	25		KN-T10BLK-25	25	Retired	KN-T8BLK-25	25	Retired
Green	KN-T12GRN	100	Retired	KN-T10GRN	100	Retired	KN-T8GRN	100	Retired
	KN-T12GRN-25	25		KN-T10GRN-25	25	Retired	KN-T8GRN-25	25	Retired
Orange	KN-T12ORG	100	Retired	KN-T10ORG	100	Retired	KN-T8ORG	100	Retired
	KN-T12ORG-25	25		KN-T10ORG-25	25	Retired	KN-T8ORG-25	25	Retired
Red	KN-T12RED	100	Retired	KN-T10RED	100	Retired	KN-T8RED	100	Retired
	KN-T12RED-25	25		KN-T10RED-25	25	Retired	KN-T8RED-25	25	Retired
Yellow	KN-T12YEL	100	Retired	KN-T10YEL	100	Retired	KN-T8YEL	100	Retired
	KN-T12YEL-25	25		KN-T10YEL-25	25	Retired	KN-T8YEL-25	25	Retired
White	KN-T12WHT	100	Retired	KN-T10WHT	100	Retired	KN-T8WHT	100	Retired
	KN-T12WHT-25	25		KN-T10WHT-25	25	Retired	KN-T8WHT-25	25	Retired

Technical Specifications

Model	KN-T12			KN-T10			KN-T8		
Width	5mm [0.20 in]			6mm [0.24 in]			8mm [0.31 in]		
Stripping Length	10mm [0.39 in]			10mm [0.39 in]			12mm [0.47 in]		
Tightening Torque	0.4 N·m [3.5 lb·in]			0.5 N·m [4.4 lb·in]			0.8 N·m [7.1 lb·in]		
Density	200/m [60 pcs/ft]			166/m [50 pcs/ft]			125/m [38 pcs/ft]		
UL/CSA Approval	600V	20A	26-12 AWG	300V	30A	26-10 AWG	300V	50A	26-8 AWG
VDE Approval	750V	24A	2.5 mm²	750V	32A	4mm²	630V	41A	6mm²
CE Conformity	750V	24A	2.5 mm²	750V	32A	4mm²	630V	41A	6mm²
SCCR Rating	100kA			100kA			100kA		
Operating Temperature	Ambient air temperature: -67 to 185°F [-55 to 85°C], Relative humidity: 50% max at 104°F [40°C] and 90% max at 68°F [20°C]								
Material	Current Bar: Copper Alloy / Housing: Polyamide 66 / Screw: Zinc Plated Steel								
DIN Rail Width	35mm								

Accessories


End Covers (International colors)	Gray	KN-ECT6GRY	100/pkg	KN-ECT6GRY	100/pkg	KN-ECT6GRY	100/pkg
		KN-ECT6GRY-25	25/pkg	KN-ECT6GRY-25	25/pkg	KN-ECT6GRY-25	25/pkg
	Blue	KN-ECT6BLU	10/pkg	KN-ECT6BLU	10/pkg	KN-ECT6BLU	10/pkg
	Brown	KN-ECT6BRN		KN-ECT6BRN		KN-ECT6BRN	
	Black	KN-ECT6BLK		KN-ECT6BLK		KN-ECT6BLK	
	Green	KN-ECT6GRN		KN-ECT6GRN		KN-ECT6GRN	
	Orange	KN-ECT6ORG		KN-ECT6ORG		KN-ECT6ORG	
	Red	KN-ECT6RED		KN-ECT6RED		KN-ECT6RED	
	Yellow	KN-ECT6YEL		KN-ECT6YEL		KN-ECT6YEL	
White	KN-ECT6WHT	KN-ECT6WHT	KN-ECT6WHT				
Separators (International colors)	Gray	KN-ST1GRY	25/pkg	KN-ST1GRY	25/pkg	KN-ST1GRY	25/pkg
	Blue	KN-ST1BLU	10/pkg	KN-ST1BLU	10/pkg	KN-ST1BLU	10/pkg
	Brown	KN-ST1BRN		KN-ST1BRN		KN-ST1BRN	
	Black	KN-ST1BLK		KN-ST1BLK		KN-ST1BLK	
	Green	KN-ST1GRN		KN-ST1GRN		KN-ST1GRN	
	Orange	KN-ST1ORG		KN-ST1ORG		KN-ST1ORG	
	Red	KN-ST1RED		KN-ST1RED		KN-ST1RED	
	Yellow	KN-ST1YEL		KN-ST1YEL		KN-ST1YEL	
White	KN-ST1WHT	KN-ST1WHT	KN-ST1WHT				
Jumpers	2-pole	KN-2J12	25/pkg	KN-2J10	25/pkg	KN-2J8	25/pkg
	3-pole	KN-3J12	20/pkg	KN-3J10	20/pkg	KN-3J8	20/pkg
	4-pole	KN-4J12	15/pkg	KN-4J10	15/pkg	KN-4J8	15/pkg
	10-pole	KN-10J12	5/pkg	KN-10J10	5/pkg	KN-10J8	5/pkg
Comb-type jumper / 2-pole		KN-2JCC12	25/pkg	KN-2JCC10	25/pkg	KN-2JCC8	25/pkg
Top Cover / Blank		KN-TC-1	25/pkg	KN-TC-1	25/pkg	KN-TC-1	25/pkg
Top Cover / Symbol		KN-TC-1S	25/pkg	KN-TC-1S	25/pkg	KN-TC-1S	25/pkg
Marking Tags		KN-L5 Series		KN-L5 Series		KN-L5 / KN-L6P5 Series	



Single-Level Terminal Blocks

- Screw connection terminal
- UL E179129
(For copper wire only. One conductor in terminal only.)
- VDE (IEC 60947-7-1)
- CE (EN 60947-7-1)

Dimensions: mm [in]



See our website: www.AutomationDirect.com
for complete engineering drawings

¹UL Usage Group: B, C for 300V or D for 600V



Ordering Information

Colors	Part Number	Qty.	Price	Part Number	Qty.	Price	Part Number	Qty.	Price
Gray	KN-T6GRY	100	Retired	KN-T4GRY	50		KN-T2GRY	40	
	KN-T6GRY-25	25		KN-T4GRY-25	25		KN-T2GRY-10	10	
Blue	KN-T6BLU	100	Retired	KN-T4BLU	50		KN-T2BLU	40	
	KN-T6BLU-25	25		KN-T4BLU-25	25		KN-T2BLU-10	10	
Brown	KN-T6BRN	100	Retired						
	KN-T6BRN-25	25							
Black	KN-T6BLK	100	Retired						
	KN-T6BLK-25	25							
Green	KN-T6GRN	100	Retired						
	KN-T6GRN-25	25							
Orange	KN-T6ORG	100	Retired						
	KN-T6ORG-25	25							
Red	KN-T6RED	100	Retired						
	KN-T6RED-25	25							
Yellow	KN-T6YEL	100	Retired						
	KN-T6YEL-25	25							
White	KN-T6WHT	100	Retired						
	KN-T6WHT-25	25							

Dimensions: mm [in]

KN-T4

KN-T2



Technical Specifications




Model	KN-T6			KN-T4			KN-T2		
Width	10mm [0.39 in]			12mm [0.47 in]			16mm [0.63 in]		
Stripping Length	12mm [0.47 in]			16mm [0.63 in]			18mm [0.71 in]		
Tightening Torque	1.2 N·m [10.6 lb·in]			1.2 N·m [10.6 lb·in]			2.5 N·m [22.1 lb·in]		
Density	100/m [33 pcs/ft]			83/m [25 pcs/ft]			62/m [19 pcs/ft]		
UL/CSA Approval	1300V	65A	16-6 AWG	600V	80A	12-4 AWG	600V	115A	10-2 AWG
VDE Approval	630V	57A	10mm²	750V	76A	16mm²	750V	125A	35mm²
CE Conformity	630V	57A	10mm²	750V	76A	16mm²	750V	125A	35mm²
SCCR Rating	100kA			100kA			100kA		
Operating Temperature	Ambient air temperature: -67 to 185°F [-55 to 85°C], Relative humidity: 50% max at 104°F [40°C] and 90% max at 68°F [20°C]								
Material	Current Bar: Copper Alloy / Housing: Polyamide 66 / Screws: Zinc Plated Steel								
DIN Rail Width	35mm								

Accessories

End Covers (International colors)	Gray	KN-ECT6GRY	100/pkg		KN-ECT4GRY	25/pkg		Note: KN-T2 is totally enclosed, no end cover required	
		KN-ECT6GRY-25	25/pkg						
	Blue	KN-ECT6BLU			KN-ECT4BLU	10/pkg			
	Brown	KN-ECT6BRN							
	Black	KN-ECT6BLK							
	Green	KN-ECT6GRN							
	Orange	KN-ECT6ORG							
	Red	KN-ECT6RED							
	Yellow	KN-ECT6YEL							
Separators (International colors)	White	KN-ECT6WHT							
	Gray	KN-ST1GRY	25/pkg		KN-ST2GRY	25/pkg		KN-ST3GRY	10/pkg
	Blue	KN-ST1BLU			KN-ST2BLU	10/pkg		KN-ST3BLU	10/pkg
	Brown	KN-ST1BRN							
	Black	KN-ST1BLK							
	Green	KN-ST1GRN							
	Orange	KN-ST1ORG							
	Red	KN-ST1RED							
	Yellow	KN-ST1YEL							
Jumpers	White	KN-ST1WHT							
	2-pole	KN-2J6	25/pkg		KN-2J4	25/pkg		KN-2J2	25/pkg
	3-pole	KN-3J6	20/pkg		KN-3J4	20/pkg		KN-3J2	20/pkg
	4-pole	KN-4J6	15/pkg		KN-4J4	15/pkg		KN-4J2	15/pkg
	10-pole	KN-10J6	5/pkg		KN-10J4	5/pkg		KN-10J2	5/pkg
Comb-type jumper / 2-pole		KN-2JCC6	25/pkg						
Top Cover / Blank		KN-TC-1	25/pkg		KN-TC-2	25/pkg		KN-TC-2	25/pkg
Top Cover / Symbol		KN-TC-1S	25/pkg		KN-TC-2S	25/pkg		KN-TC-2S	25/pkg
Marking Tags		KN-L5/ KN-L6P5 Series			KN-L5/ KN-L6P5 Series			KN-L5/ KN-L6P5 Series	






Single-Level Terminal Blocks



Dimensions: mm [in]

- Screw connection terminal
- UL E179129
(For copper wire only.
One conductor in
terminal only.)
- CE (EN 60947-7-1)



See our website: www.AutomationDirect.com for complete engineering drawings

Ordering Information

Colors	Part Number	Qty	Price	Part Number	Qty	Price	Part Number	Qty	Price
Gray	KN-T1/0GRY	25		KN-T2/0GRY	10		KN-T12SP4	100	
	KN-T1/0GRY-10	10		—	—	—	KN-T12SP4-25	25	
Blue	KN-T1/0BLU	25		KN-T2/0BLU	10		—	—	—
	KN-T1/0BLU-10	10		—	—	—	—	—	—

Technical Specifications

Technical Specifications									
Model	KN-T1/0			KN-T2/0			KN-T12SP4		
Width	20mm [0.79 in]			22mm [0.87 in]			5mm [0.20 in]		
Stripping Length	20mm [0.79 in]			20mm [0.79 in]			10mm [0.39 in]		
Tightening Torque	6.0 N·m [53.1 lb·in]			6.0 N·m [53.1 lb·in]			0.5 N·m [4.4 lb·in]		
Density	50/m [15 pcs/ft]			45/m [13 pcs/ft]			200/m [60 pcs/ft]		
UL/CSA Approval	600V	150A	6-1/0 AWG	600V	175A	6-2/0 AWG	600V	20A	26-12 AWG
CE Conformity	1000V	150A	50mm²	750V	192A	70mm²	750V	24A	2.5 mm²
SCCR Rating	100kA			100kA			100kA per Table SB4.1, 2009, UL 508A.		
Operating Temperature	Ambient air temperature: -67 to 185°F [-55 to 85°C], Relative humidity: 50% max at 104°F [40°C] and 90% max at 68°F [20°C]								
Material	Current Bar: Copper Alloy / Housing: Polyamide 66 / Screws: Zinc Plated Steel								
DIN Rail Width	35mm								

Accessories

End Covers	Gray	—	—	—	—	—	—	KN-ECT12SP4	25/pkg	
Jumpers	2-pole	KN-2J1/0	5/pkg		—	—	—	KN-2JM12	25/pkg	
	3-pole	KN-3J1/0	5/pkg		—	—	—	KN-3JM12	20/pkg	
	4-pole	KN-4J1/0	5/pkg		—	—	—	KN-4JM12	15/pkg	
	10-pole	—	—	—	—	—	—	KN-10JM12	5/pkg	
Marking Tags	No tags available			KN-L5 Series KN-L6P5 Series			KN-L5 Series			



100kA Terminal Block

Short-Circuit Current

Rating Data

Short-Circuit Current Rating Data										
Part Number	Suitable Copper Conductor Range (AWG)		Fuse Class Maximum Amperage						SCCR Rating	Volts Max
	Line	Load	Class J	Class T	Class RK1	Class RK5	Class G	Class CC		
KN-T12 ²	26-12	26-12	20	20	—	—	20	20	100 kA	600
KN-T10 ²	26-10	26-10	30	30	—	—	30	30	100 kA	600
KN-T8 ²	26-8	26-8	50	50	30	—	45	30	100 kA	600
KN-T6 ²	16-6	16-6	80	80	60	30	60	30	100 kA	600
KN-T4 ²	12-4	12-4	80	80	60	30	60	30	100 kA	600
KN-T2 ²	12-2	12-2	125	125	100	30	60	30	100 kA	600
KN-T1/0 ³	6-1/0	6-1/0	150	150	100	30	60	30	100 kA	600
KN-T2/0 ³	6-2/0	6-2/0	225	225	100	60	60	30	100 kA	600
KN-D12 ^{1 2}	26-12	26-12	20	20	—	—	20	20	100 kA	600
KN-D10 ^{1 2}	26-10	26-10	30	30	—	—	30	30	100 kA	600
KN-TL14 ²	24-12	24-12	30	30	—	—	30	30	100 kA	600
KN-TG12 ²	24-12	24-12	30	30	—	—	30	30	100 kA	600
KN-M12 ²	26-12	26-12	30	30	—	—	30	30	100 kA	600
KN-M10 ²	14-12	14-12	30	30	—	—	30	30	100 kA	600

Note: ¹ KN-D12 and KN-D10 have optional short circuit rating evaluated for use with copper conductors only. Must be protected by the max ampere and Class of overcurrent protective device noted above.

² The terminal block short-circuit rating for KN-D12 and KN-D10 were determined based on testing in a minimum size enclosure measuring 4x4x6 inches. The suitability of smaller enclosures shall be determined in the end-use investigation.

³ The terminal block short-circuit rating for KN-T1/0 and KN-T2/0 were determined based on testing in a minimum size enclosure measuring 12x12x6 inches. The suitability of smaller enclosures shall be determined in the end-use investigation.



KONNECT-IT Accessories

Multi-Pole Jumper Bars

Multi-pole jumper bars provide terminal block connection flexibility. Screw-down connection jumpers feature all-metal construction and can be installed quickly just by tightening the screws. Screwless comb-style jumpers are also available. See next page for the larger J1/0 jumper installation instructions.

KN-10J12



KN-2JM12



KN-2JCC8



Multi-Pole Jumper Bars Ordering Information

Type	Part Number	Price	Qty	Number of Poles	Rating		Tightening Torque	Dimensions - mm [in]			Fig.	Works With
					(V)	(A)		Height	Length	Width		
Screw-down connection	KN-2J12		25	2	750	24	0.4–0.6 Nm [3.5–5.3 lb-in]	15.8 [0.62]	10.1 [0.40]	4.4 [0.17]	1	KN-T12xx KN-D12xx KN-D12X KN-D12DR1 KN-D12LEDxx
	KN-3J12		20	3	750	24			15.3 [0.60]			
	KN-4J12		15	4	750	24			20.4 [0.80]			
	KN-10J12		5	10	750	24			51.1 [2.01]			
	KN-2J10		25	2	750	32	0.6–0.8 Nm [5.3–7.1 lb-in]	15.5 [0.61]	10.8 [0.43]	6.0 [0.24]	1	KN-T10xx KN-D10xx KN-D10X KN-D10DR1 KN-D10LEDxx
	KN-3J10		20	3	750	32			17.0 [0.67]			
	KN-4J10		15	4	750	32			23.0 [0.91]			
	KN-10J10		5	10	750	32			59.0 [2.32]			
	KN-2J8		25	2	630	41	0.6–0.8 Nm [5.3–7.1 lb-in]	15.5 [0.61]	14.3 [0.56]	6.0 [0.24]	1	KN-T8xx
	KN-3J8		20	3	630	41			22.3 [0.88]			
	KN-4J8		15	4	630	41			30.3 [1.19]			
	KN-10J8		5	10	630	41			78.3 [3.08]			
	KN-2J6		25	2	630	57	0.6–0.8 Nm [5.3–7.1 lb-in]	15.5 [0.61]	18.0 [0.71]	6.0 [0.24]	1	KN-T6xx
	KN-3J6		20	3	630	57			28.0 [1.10]			
	KN-4J6		15	4	630	57			38.0 [1.50]			
	KN-10J6		5	10	630	57			98.0 [3.86]			
	KN-2J4		25	2	750	76	0.6–0.8 Nm [5.3–7.1 lb-in]	23.0 [0.91]	21.0 [0.83]	6.0 [0.24]	1	KN-T4xx
	KN-3J4		20	3	750	76			33.0 [1.30]			
	KN-4J4		15	4	750	76			45.0 [1.77]			
	KN-10J4		5	10	750	76			117.0 [4.61]			
	KN-2J2		25	2	750	125	1.2–1.4 Nm [10.6–12.4 lb-in]	21.0 [0.83]	29.0 [1.14]	8.0 [0.31]	1	KN-T2xx
	KN-3J2		20	3	750	125			45.0 [1.77]			
	KN-4J2		15	4	750	125			61.0 [2.40]			
	KN-10J2		5	10	750	125			157.0 [6.18]			
	KN-2J1/0		5	2	1000	150	2.5–3.5 Nm [22.1–31.0 lb-in]	22.3 [0.88]	36.0 [1.42]	12.0 [0.47]	2	KN-T1/0xx
	KN-3J1/0		5	3	1000	150			56.0 [2.20]			
	KN-4J1/0		5	4	1000	150			76.0 [2.99]			
	KN-2JTL12		25	2	440	24	0.4–0.6 Nm [3.5–5.3 lb-in]	15.5 [0.61]	11.0 [0.43]	4.4 [0.17]	1	KN-DG12 KN-TG12 KN-TL14 KN-TL14S KN-TL14SLN KN-TL14SLP
	KN-3JTL12		20	3	440	24			17.0 [0.67]			
	KN-4JTL12		15	4	440	24			23.0 [0.91]			
	KN-10JTL12		5	10	440	24			59.0 [2.32]			
Push-in Connection	KN-2JM10		25	2	750	32	–	23.2 [0.91]	9.5 [0.37]	2.7 [0.11]	3	KN-M10xx KN-KBD10
	KN-3JM10		20	3	750	32			15.5 [0.61]			
	KN-4JM10		15	4	750	32			21.5 [0.85]			
	KN-10JM10		5	10	750	32			57.5 [2.26]			
	KN-2JM12		25	2	750	24	–	21.7 [0.85]	8.0 [0.31]	2.3 [0.09]	3	KN-M12xx KN-T12SP4
	KN-3JM12		20	3	750	24			13.0 [0.51]			
	KN-4JM12		15	4	750	24			18.0 [0.71]			
	KN-10JM12		5	10	750	24			48.0 [1.89]			
Screwless Comb-style	KN-2JCC12		25	2	750	24	–	23.7 [0.93]	8.0 [0.31]	2.8 [0.11]	4	KN-T12xx
	KN-2JCC10		25		750	32	–	24.7 [0.97]	9.5 [0.37]			KN-T10xx
	KN-2JCC8		25		630	41	–	25.6 [1.01]	13.5 [0.53]			KN-T8xx
	KN-2JCC6		25		630	57	–	26.7 [1.05]	16.0 [0.63]			KN-T6xx

Figure 1




Figure 2




Figure 3





Figure 4



Please visit our website
www.AutomationDirect.com
for complete engineering drawings.

Screwless Comb-Style jumpers are designed to be connected under the conductor clamp.







KONNECT-IT® Accessories

End Brackets

End brackets prevent terminal blocks and other DIN rail mount components and devices from moving laterally on the rail. They are constructed from polyamide 66 and available in configurations for 35mm and 15mm DIN rails.

Dimensions mm [in]



End Brackets Ordering Information

Gray End Brackets	KN-EB3	100/pkg		KN-EB4	100/pkg		KN-EB5	100/pkg		KN-EB7	50/pkg	
	KN-EB3-10	10/pkg		KN-EB4-10	10/pkg		KN-EB5-10	10/pkg		KN-EB7-10	10/pkg	

Technical Specifications

Description	Screw-type end bracket	Screwless end bracket	Screwless end bracket	Screw-type end bracket
Bracket Width	8 mm [0.31 in]	8 mm [0.31 in]	8 mm [0.31 in]	10 mm [0.39 in]
DIN Rail Width	35 mm	35 mm	15 mm	35 mm
Material	Housing: Polyamide 66 / Clamping Connector: Zinc Plated Steel			


End Bracket Accessories

Label Holder	—	—	—	KN-MA-1	25/pkg	—	—	—	KN-MA-2	50/pkg	
	—	—	—	KN-MA-1-10	10/pkg	—	—	—	KN-MA-2-10	10/pkg	
Marking Tags	KN-L5 Series or KN-L6P5 Series										

End Covers

End covers are used to cover the open side of sectional DIN rail mount terminal blocks. They should be used at the end of an assembly of identical terminal blocks or whenever there is a change in the physical size of the terminal block.

Material: Polyamide 66



End Covers Ordering Information

Part Number	Color	Dimensions H x L x W mm [in]	Works With	Qty	Price	Part Number	Color	Dimensions H x L x W mm [in]	Works With	Qty	Price
KN-ECT6GRY	gray	34.0x42.7x1.3 [1.34x1.68x0.05]	KN-T12 KN-T10 KN-T8 KN-T6	100		KN-ECDORG	orange	48.2x63.2x1.3 [1.90x2.49x0.05]	KN-D10 KN-D12	10	
KN-ECT6GRY-25	gray			25		KN-ECDRED	red				
KN-ECT6BLU	blue					KN-ECDYEL	yellow				
KN-ECT6BLK	black					KN-ECTL	gray	54.7x87.1x1.3 [2.15x3.43x0.05]	KN-TL14	10	
KN-ECT6BRN	brown					KN-ECTLS	gray	54.7x72.8x1.2 [2.15x2.87x0.05]	KN-TL14S	10	
KN-ECT6GRN	green			10		KN-ECDG12	gray	48.0x71.4x1.2 [1.89x2.81x0.05]	KN-DG12	10	
KN-ECT6ORG	orange					KN-ECTG12	gray	62.5x87.5x1.2 [2.46x3.44x0.05]	KN-TG12	10	
KN-ECT6RED	red					KN-ECMGY	gray	28.1x27.0x3.0 [1.11x1.06x0.12]	KN-M12 KN-M10	100	
KN-ECT6WHT	white					KN-ECMGY-10	gray			10	
KN-ECT6YEL	yellow					KN-ECMBLU	blue				
KN-ECT4GRY	gray	45.7x52.8x1.2 [1.80x2.08x0.05]	KN-T4	25		KN-ECMGRN	green/ yellow	28.1x27.0x3.0 [1.11x1.06x0.12]	KN-MG12 KN-MG10	10	
KN-ECT4BLU	blue			10		KN-ECG12SP4	green/ yellow	39.7x57.1x1.2 [1.56x2.25x0.05]	KN-G12SP4	10	
KN-ECDGRY	gray	48.2x63.2x1.3 [1.90x2.49x0.05]	KN-D10 KN-D12	25		KN-ECT12SP4	gray	39.7x57.1x1.2 [1.56x2.25x0.05]	KN-T12SP4	25	
KN-ECDBLU	blue			10		KN-ECF10	gray	27.3x59.6x1.2 [1.07x2.35x0.05]	KN-F10	25	
KN-ECDBLK	black					KN-ECKBD	gray	37.1x53.5x1.2 [1.46x2.11x0.05]	KN-KDB10	10	
KN-ECDGRN	green										



KONNECT-IT® Accessories

Separators

Separators are used to segment banks of terminal blocks. Allows you to maintain a single row of terminal blocks, but have separate power source clusters.

Separators Ordering Information								
Part Number	Color	Works With	Dimensions - mm [in]			Qty	Price	
			Height	Length	Thickness			
KN-ST1GRY	Gray	KN-T12 KN-T10 KN-T8 KN-T6	39.0 [1.54]	42.5 [1.67]	1.2 [0.05]	25		
KN-ST1BLU	Blue					10		
KN-ST1BLK	Black							
KN-ST1BRN	Brown							
KN-ST1GRN	Green							
KN-ST1ORG	Orange							
KN-ST1RED	Red							
KN-ST1WHT	White							
KN-ST1YEL	Yellow							
KN-ST2GRY	Gray	KN-T4	52.5 [2.07]	50.5 [1.99]	1.5 [0.06]	25		
KN-ST2BLU	Blue					10		
KN-ST3GRY	Gray	KN-T2	62.6 [2.46]	53.1 [2.09]	1.5 [0.06]			
KN-ST3BLU	Blue							

KN-ST1GRY



Top Covers and Label Holders

Top Covers and Label Holders Ordering Information							
Part Number	Description	Works With	Dimensions - mm [in]			Qty	Price
			Height	Length	Width		
KN-TC-1	Top cover for Konnect-It terminal block, blank, white	KN-T12 KN-T10 KN-T8 KN-T6	6.8 [0.27]	29.0 [1.14]	5.8 [0.23]	25	
KN-TC-1S	Top cover for Konnect-It terminal block, printed electric symbol, white					25	
KN-TC-2	Top cover for Konnect-It terminal block, blank, white	KN-T4 KN-T2	7.3 [0.29]	35.8 [1.41]	9.0 [0.35]	25	
KN-TC-2S	Top cover for Konnect-It terminal block, printed electric symbol, white					25	
KN-MA-1	Label holder for terminal block group. Label media not included. Adhesive label: Apply on top.	KN-EB4	46.2 [1.82]	46.0 [1.81]	11.4 [0.45]	25	
KN-MA-1-10	Max label dimensions: 7 x 44 mm (0.28 x 1.73 in).					10	
KN-MA-2	Label holder for terminal block group. Label media not included. Adhesive label: Apply on top.	KN-EB7	37.5 [1.48]	46.2 [1.82]	9.5 [0.37]	50	
KN-MA-2-10	Max label dimensions: 7 x 44 mm (0.28 x 1.73 in).					10	
KN-MA-3	Top mounting marking tag adapter for terminal block. Holds up to (4) L5x5 tags	KN-T4 KN-T2	9.3 [0.36]	36.0 [1.42]	9.0 [0.35]	25	
KN-MA-4	Top mounting marking tag adapter for terminal block. Holds up to (4) L5x5 tags	KN-T12 KN-T10 KN-T8 KN-T6	9.0 [0.35]	29.0 [1.14]	5.7 [0.22]	25	
KN-MA-5	Label holder for terminal block group. Label media included.	Attaches to any 35mm DIN rail	46.4 [1.83]	44.5 [1.75]	10.0 [0.39]	50	
KN-MA-5-25	Max label dimensions: 10 x 38mm (0.39 x 1.50 in). Thickness 0.30 mm (0.01 in)					25	

KN-MA-1



KN-MA-2



KN-MA-5



KN-TC-1 / KN-TC-2



KN-TC-1S / KN-TC-2S



KN-MA-3



KN-MA-4






KONNECT-IT® Accessories

Marking Tags 5 x 5mm

Use with any KONNECT-IT series terminal blocks.



5 x 5mm Marking Tags Ordering Information

250 Pieces per Package						500 Pieces per Package					
Part Number	Imprint	Price	Part Number	Imprint	Price	Part Number	Imprint	Price	Part Number	Imprint	Price
<u>KN-L5-BLANK-250</u>	Blank		<u>KN-L5-A-250</u>	A		<u>KN-L5-BLANK</u>	Blank		<u>KN-L5-A</u>	A	
<u>KN-L5-0-250</u>	0		<u>KN-L5-B-250</u>	B		<u>KN-L5-0</u>	0		<u>KN-L5-B</u>	B	
<u>KN-L5-1-250</u>	1		<u>KN-L5-C-250</u>	C		<u>KN-L5-1</u>	1		<u>KN-L5-C</u>	C	
<u>KN-L5-2-250</u>	2		<u>KN-L5-D-250</u>	D		<u>KN-L5-2</u>	2		<u>KN-L5-D</u>	D	
<u>KN-L5-3-250</u>	3		<u>KN-L5-E-250</u>	E		<u>KN-L5-3</u>	3		<u>KN-L5-E</u>	E	
<u>KN-L5-4-250</u>	4		<u>KN-L5-F-250</u>	F		<u>KN-L5-4</u>	4		<u>KN-L5-F</u>	F	
<u>KN-L5-5-250</u>	5		<u>KN-L5-G-250</u>	G		<u>KN-L5-5</u>	5		<u>KN-L5-G</u>	G	
<u>KN-L5-6-250</u>	6		<u>KN-L5-H-250</u>	H		<u>KN-L5-6</u>	6		<u>KN-L5-H</u>	H	
<u>KN-L5-7-250</u>	7		<u>KN-L5-I-250</u>	I		<u>KN-L5-7</u>	7		<u>KN-L5-I</u>	I	
<u>KN-L5-8-250</u>	8		<u>KN-L5-J-250</u>	J		<u>KN-L5-8</u>	8		<u>KN-L5-J</u>	J	
<u>KN-L5-9-250</u>	9		<u>KN-L5-K-250</u>	K		<u>KN-L5-9</u>	9		<u>KN-L5-K</u>	K	
<u>KN-L5-10-250</u>	10		<u>KN-L5-L-250</u>	L		<u>KN-L5-10</u>	10		<u>KN-L5-L</u>	L	
<u>KN-L5-1-10-250</u>	1-10		<u>KN-L5-M-250</u>	M		<u>KN-L5-1-10</u>	1-10		<u>KN-L5-M</u>	M	
<u>KN-L5-11-20-250</u>	11-20		<u>KN-L5-N-250</u>	N		<u>KN-L5-11-20</u>	11-20		<u>KN-L5-N</u>	N	
<u>KN-L5-21-30-250</u>	21-30		<u>KN-L5-O-250</u>	O		<u>KN-L5-21-30</u>	21-30		<u>KN-L5-O</u>	O	
<u>KN-L5-31-40-250</u>	31-40		<u>KN-L5-P-250</u>	P		<u>KN-L5-31-40</u>	31-40		<u>KN-L5-P</u>	P	
<u>KN-L5-41-50-250</u>	41-50		<u>KN-L5-Q-250</u>	Q		<u>KN-L5-41-50</u>	41-50		<u>KN-L5-Q</u>	Q	
<u>KN-L5-1-50-250</u>	1-50		<u>KN-L5-R-250</u>	R		<u>KN-L5-1-50</u>	1-50		<u>KN-L5-R</u>	R	
<u>KN-L5-51-100-250</u>	51-100		<u>KN-L5-S-250</u>	S		<u>KN-L5-51-100</u>	51-100		<u>KN-L5-S</u>	S	
<u>KN-L5-101-150-250</u>	101-150		<u>KN-L5-T-250</u>	T		<u>KN-L5-101-150</u>	101-150		<u>KN-L5-T</u>	T	
<u>KN-L5-151-200-250</u>	151-200		<u>KN-L5-U-250</u>	U		<u>KN-L5-151-200</u>	151-200		<u>KN-L5-U</u>	U	
<u>KN-L5-201-250-250</u>	201-250		<u>KN-L5-V-250</u>	V		<u>KN-L5-201-250</u>	201-250		<u>KN-L5-V</u>	V	
<u>KN-L5-251-300-250</u>	251-300		<u>KN-L5-W-250</u>	W		<u>KN-L5-251-300</u>	251-300		<u>KN-L5-W</u>	W	
<u>KN-L5-301-350-250</u>	301-350		<u>KN-L5-X-250</u>	X		<u>KN-L5-301-350</u>	301-350		<u>KN-L5-X</u>	X	
<u>KN-L5-351-400-250</u>	351-400		<u>KN-L5-Y-250</u>	Y		<u>KN-L5-351-400</u>	351-400		<u>KN-L5-Y</u>	Y	
<u>KN-L5-401-450-250</u>	401-450		<u>KN-L5-Z-250</u>	Z		<u>KN-L5-401-450</u>	401-450		<u>KN-L5-Z</u>	Z	
<u>KN-L5-451-500-250</u>	451-500		<u>KN-L5-POS-250</u>	+		<u>KN-L5-451-500</u>	451-500		<u>KN-L5-POS</u>	+	
<u>KN-L5-L1-250</u>	L1		<u>KN-L5-NEG-250</u>	-		<u>KN-L5-L1</u>	L1		<u>KN-L5-NEG</u>	-	
<u>KN-L5-L2-250</u>	L2		<u>KN-L5-GND-250</u>	GND		<u>KN-L5-L2</u>	L2		<u>KN-L5-GND</u>	GND	
<u>KN-L5-L3-250</u>	L3					<u>KN-L5-L3</u>	L3				



KONNECT-IT Accessories


Marking Tags 6 x 11.5 mm

Use with Konnect-It series terminal blocks
6.5mm or wider.



Marking Tags 5 x 10mm, 6 x 10mm, 10 x 10mm

Use with Konnect-It series terminal blocks
5 x 10mm, 6 x 10mm, and 10 x 10mm.



Marking Tags 6 x 11.5mm			
Part Number	Description	Qty	Price
<u>KN-L6P5-BLNK</u>	Blank	500	
<u>KN-L6P5-BLNK-250</u>	Blank	250	
<u>KN-L6P5-BLNK-300</u>	Blank	300	
<u>KN-L6P5-1-10</u>	Numbered 1-10	500	
<u>KN-L6P5-1-10-250</u>	Numbered 1-10	250	
<u>KN-L6P5-1-10-300</u>	Numbered 1-10	300	
<u>KN-L6P5-11-20</u>	Numbered 11-20	500	
<u>KN-L6P5-11-20-250</u>	Numbered 11-20	250	
<u>KN-L6P5-11-20-300</u>	Numbered 11-20	300	
<u>KN-L6P5-21-30</u>	Numbered 21-30	500	
<u>KN-L6P5-21-30-250</u>	Numbered 21-30	250	
<u>KN-L6P5-21-30-300</u>	Numbered 21-30	300	
<u>KN-L6P5-31-40</u>	Numbered 31-40	500	
<u>KN-L6P5-31-40-250</u>	Numbered 31-40	250	
<u>KN-L6P5-31-40-300</u>	Numbered 31-40	300	
<u>KN-L6P5-41-50</u>	Numbered 41-50	500	
<u>KN-L6P5-41-50-250</u>	Numbered 41-50	250	
<u>KN-L6P5-41-50-300</u>	Numbered 41-50	300	
<u>KN-L6P5-51-60</u>	Numbered 51-60	500	
<u>KN-L6P5-51-60-250</u>	Numbered 51-60	250	
<u>KN-L6P5-51-60-300</u>	Numbered 51-60	300	
<u>KN-L6P5-61-70</u>	Numbered 61-70	500	
<u>KN-L6P5-61-70-250</u>	Numbered 61-70	250	
<u>KN-L6P5-61-70-300</u>	Numbered 61-70	300	
<u>KN-L6P5-71-80</u>	Numbered 71-80	500	
<u>KN-L6P5-71-80-250</u>	Numbered 71-80	250	
<u>KN-L6P5-71-80-300</u>	Numbered 71-80	300	
<u>KN-L6P5-81-90</u>	Numbered 81-90	500	
<u>KN-L6P5-81-90-250</u>	Numbered 81-90	250	
<u>KN-L6P5-91-100</u>	Numbered 91-100	500	
<u>KN-L6P5-91-100-250</u>	Numbered 91-100	250	

Marking Tags			
Part Number*	Description	Qty	Price
<u>KN-L5X-BLNK</u>	Blank marking tag, 5 x 10mm, use with any Konnect-It terminal block series	440	
<u>KN-L5X-BLNK-220</u>	Blank marking tag, 5 x 10mm, use with any Konnect-It terminal block series	220	
<u>KN-L6X-BLNK</u>	Blank marking tag, 6 x 10mm, use with any Konnect-It terminal block 6mm or wider	360	
<u>KN-L6X-BLNK-180</u>	Blank marking tag, 6 x 10mm, use with any Konnect-It terminal block 6mm or wider	180	
<u>KN-L10X-BLNK</u>	Blank marking tag, 10 x 10mm, use with any Konnect-It terminal block 10mm or wider	200	
<u>KN-L10X-BLNK-100</u>	Blank marking tag, 10 x 10mm, use with any Konnect-It terminal block 10mm or wider	100	

*Does not fit any KN-T1/0xx or [KN-G1/0](#) series block