

Connection Cables Sensor and Signal





M8 A-coded Cable to Pigtail

Features

- Industry-standard axial and 90-degree M8 screw-lock connectors with open leads
- Cables listed can be used with patch cables
- 1.5m [4.9ft], 2m [6.5ft], 5m [16.4ft], 7m [23ft], and 10m [32.8ft] cable lengths
- PVC (polyvinyl chloride) jacketed cable for general use and chemical washdown applications, ex. food & beverage industry
- PUR (polyurethane) jacketed cable for applications with exposure to oil and dynamic applications requiring more flexibility
- PP (polypropylene) wire insulation for low temperature applications



Dimensions



M8 A-coded Cable to Pigtail									
Part Number	Price	Number of Wires	Connector	Cable Jacket/ Wire Insulation Material	Jacket Color	Dimensions			
						A	B	C	L
						mm			m [ft]
CD08-0A-020-A1		3	Axial female	PVC/PVC	Gray	32	10	—	2
CD08-0A-020-C1			90-degree female			25	10	20	[6.5]
CD08-0A-050-A1			Axial female		Black	32	10	—	5
CD08-0A-050-C1			90-degree female			25	10	20	[16.4]
CD08-0C-050-A1-A			Axial female	PUR/PP	Black	32	10	—	5
CD08-0C-050-C1-A			90-degree female	PUR/PP		25	10	20	[16.4]
CD08-0A-070-A1			Axial female	PVC/PVC	Gray	32	10	—	7
CD08-0A-070-C1			90-degree female			25	10	20	[23]
7000-08001-0200200			Axial male	PUR/PVC	Yellow	39	10	—	2
7000-08001-0300200			Axial male	PUR/PP		39	10	—	[6.5]
7000-08021-0300200			90-degree male	PUR/PP		25	10	26	5
7000-08001-0300500			Axial male	PUR/PP		39	10	—	[16.4]
7000-08021-0300500			90-degree male	PUR/PP		25	10	26	10
7000-08001-0301000			Axial male	PUR/PP		39	10	—	[32.8]
7000-08021-0301000			90-degree male	PUR/PP		25	10	26	2
7000-08001-2100200			Axial male	PVC/PVC	Gray	39	10	—	[6.5]
7000-08021-2100200			90-degree male			25	10	26	5
7000-08001-2100500			Axial male			39	10	—	[16.4]
7000-08021-2100500			90-degree male			25	10	26	10
7000-08001-2101000			Axial male		Yellow	32	10	—	2
7000-08021-2101000			90-degree male			25	10	20	[6.5]
7000-08041-0300200			Axial female	PUR/PP		32	10	—	5
7000-08081-0300200			90-degree female	PUR/PP		25	10	20	[16.4]

Continued on next page.


See our website: www.AutomationDirect.com for complete engineering drawings.

Connection Cables Sensor and Signal


M8 A-coded Cable to Pigtail (continued)

M8 A-coded Cable to Pigtail									
Part Number	Price	Number of Wires	Connector	Cable Jacket/Wire Insulation Material	Jacket Color	Dimensions			
						A	B	C	L
						mm			m [ft]
7000-08041-0300700		3	Axial female	PUR/PP	Yellow	32	10	—	7
7000-08081-0300700			90-degree female	PUR/PP		25	10	20	[22.9]
7000-08041-2100500			Axial female	PVC/PVC	Gray	32	10	—	5
7000-08081-2100500			90-degree female			25	10	20	[16.4]
7000-08061-0310200		4	Axial female	PUR/PP	Yellow	32	10	—	2
7000-08101-0310200			90-degree female	PUR/PP		25	10	20	[6.5]
7000-08061-0310500			Axial female	PUR/PP		32	10	—	5
7000-08101-0310500			90-degree female	PUR/PP		25	10	20	[16.4]
7000-08061-0311000			Axial female	PUR/PP		32	10	—	10
7000-08101-0311000			90-degree female	PUR/PP		25	10	20	[32.8]
CD08-0G-020-A1			Axial female	PVC/PVC	Black	32	10	—	2
CD08-0W-020-C1			90-degree female			25	10	20	[6.5]
CD08-0G-050-A1			Axial female			32	10	—	5
CD08-0W-050-C1			90-degree female			25	10	20	[16.4]
CD08-0G-100-A1			Axial female		Gray	32	10	—	10
CD08-0W-100-C1			90-degree female			25	10	20	[32.8]
7000-08061-2110200			Axial female			32	10	—	2
7000-08101-2110200			90-degree female			25	10	20	[6.5]
7000-08061-2110500			Axial female		Gray	32	10	—	5
7000-08101-2110500			90-degree female			25	10	20	[16.4]
7000-08061-2111000		5	Axial female	PUR/PP	Black	34	10	—	1.5
7000-08951-6950150			90-degree female			28	10	21	[4.9]
7000-08941-6950500			Axial female			34	10	—	5
7000-08951-6950500			90-degree female			28	10	21	[16.4]
7000-08941-6951000			Axial female			34	10	—	10
7000-08951-6951000			90-degree female			28	10	21	[32.8]

Dimensions



Axial female



90-degree female


See our website: www.AutomationDirect.com for complete engineering drawings.

Connection Cables Sensor and Signal


Specifications					
Model	CD08 Series		7000 Series		
Type	3-Wire, 3-Pole	4-Wire, 4-Pole	3-Wire, 3-Pole	4-Wire, 4-Pole	5-Wire, 5-Pole
Max Voltage	50 VAC / 60 VDC				30 VAC/VDC
Max Voltage - UL Rating	N/A		30 VAC/VDC		
Max Current Per Contact	4A				3A
Protection Degree	IP65 / IP66K / IP67				IP67
Nut Material	Male threads are nickel-plated brass Female threads are nickel-plated die-cast zinc				
Cable Jacket/Wire Insulation Material	PUR-PVC/PVC, PVC/PVC, PUR/PVC, or PUR/PP				PUR/PP
Contacts Material	Copper Alloy				
Tightening Torque	≤ 0.4 N·m [≤ 0.34 ft-lb]				
Conductors Cross Section	0.25mm ² [24 AWG]				
Outer Cable Diameter Ø For PUR/PVC or PVC/PVC or PUR-PVC/PVC	3-Wire 4.5mm [0.18in] / 4-Wire 4.8mm [0.19in]				
Outer Cable Diameter Ø For PUR/PP	3-Wire 4.1mm [0.16in] / 4-Wire 4.5mm [0.18in]				5-Wire 4.7mm [0.19in]
Temperature Range - Stationary Use	PUR-PVC/PVC, PVC/PVC and PUR/PVC -30 to +80 °C [-22 to +176 °F]; PUR/PP -40 to +80 °C [-40 to +176 °F]				
Temperature Range - Flexible Use	PUR-PVC/PVC, PVC/PVC and PUR/PVC -5 to +80 °C [+23 to +176 °F]; PUR/PP -25 to +80 °C [-13 to +176 °F]				
Min Bend Radius	Stationary use: 5 x cable diameter Flexible use: 10 x cable diameter				
Approvals*	CE, cCSAus		cULus, CE, UKCA, cCSAus		cURus

*To obtain the most current agency approval information, see the Agency Compliance & Certifications Checklist section on the specific part number's web page.

Contact Diagrams



Wiring Diagrams



Field-Wireable Connectors - Sensor and Signal

M8 A-coded Insulation Displacement Connector (IDC)

Features

- IDC (insulation displacement connection) allows quick termination without stripping conductors
- Various cable gauges and diameters accepted
- IP67 rated once properly assembled


7000-08331-0000000

M8 A-coded Insulation Displacement Connector (IDC)

Part Number	Price	Number of Wires, Pins	Connection Type	Conductor Size	Outside Cable Ø	Drawing Link
7000-08325-0000000		3-Wire, 3-Pin	Axial male with male threads	24–20 AWG [0.25–0.5mm ²]	2.5–5.0mm [0.098–0.19in]	PDF
7000-08331-0000000			Axial female with female threads	26–22 AWG [0.14–0.34mm ²]	2.5–5.1 mm [0.098–0.20in]	PDF
7000-08371-0000000						PDF
7000-08351-0000000		4-Wire, 4-Pin	Axial male with male threads			PDF
7000-08391-0000000		4-Wire, 4-Pin	Axial female with female threads			PDF

Specifications

Coding	A-coded		
Model	08325	08331, 08371	08351, 08391
Max Voltage	48 VAC / 60 VDC	32 VAC/VDC	
Max Current per Contact	4A		
Temperature Range	-25 to +80 °C [-13 to +176 °F]	-25 to +85 °C [-13 to +185 °F]	
Protection Degree	IP65 IP67	IP67	
Housing Material	Nylon	Polyamide (PA)	
Locking Material	Zinc die-cast	Zinc die-cast, nickel-plated	
Weight	0.02 lbs	0.01 lbs	0.03 lbs
Approvals*	CE, UR	cURus	

* To obtain the most current agency approval information, see the Agency Compliance & Certifications Checklist section on the specific part number's web page.

Pin Assignments

LEGEND
■ MALE PIN ON CONNECTOR
○ FEMALE PIN ON CONNECTOR
(FIELD CONNECTION TERMINAL

