

NEMA 4, 4X, and 12 Stainless Steel Two-Door Floor-Mount with 3-Point Handle



Applications

Designed to house electrical and electronic controls, components and instruments in wet corrosive environments. Typical applications for these enclosures include dairies, breweries, waste water, coastal, food processing and/or activities that may require hose down. Enclosures are designed for outdoor applications.



Construction

- Bodies, doors and floor stand feet are fabricated from 12/10-gauge 304 or 316L stainless steel
- Continuously-welded seams ground smooth
- Body stiffeners added for extra strength
- Rolled lip around three sides of door and along top of enclosure's opening excludes liquids and contaminants from entering
- 3-point 316L SS padlocking handles
- Heavy gauge continuous hinges are provided to secure doors
- Pull hinge pin to remove doors
- Removable print pocket is provided
- Standard 12 in [305 mm] floor kits are welded to bottom of enclosure
- Heavy-duty removable lifting eyes
- Collar studs for mounting optional subpanels
- Easily Removable center post permits easy panel installations
- Doors sealed with poured-in-place gasket
- Grounding provisions provided
- Uses WAL3_SS series handles

Finish

- Exterior: smooth-grained finish

Listings

- UL 508, 4, 4X, and 12 [UL Files E64791]
- NEMA/EEMAC 4, 4X, and 12



Note: For current listings, please see www.automationdirect.com

Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

NEMA 4, 4X, and 12 Stainless Steel Two-Door Floor-Mount Enclosures with 3-Point Handle


304 Stainless Steel	Price	316L Stainless Steel	Price	Enclosure SizeHxWxD (not incl. 12 [305] legs)	Painted Steel Subpanel	Galvanized Subpanel
SSN4D6248123PT	Retired	SSN4D6248123PTA	Retired	62.12 x 48.12 x 13.29 [1578 x 1222 x 338]	NPDD6048	NPDD6048G
SSN4D6248183PT	Retired	SSN4D6248183PTA	Retired	62.12 x 48.12 x 19.29 [1578 x 1222 x 490]	NPDD6048	NPDD6048G
SSN4D6260123PT	Retired	SSN4D6260123PTA	Retired	62.12 x 60.12 x 13.29 [1578 x 1527 x 338]	NPDD6060	NPDD6060G
SSN4D7460123PT	Retired	SSN4D7460123PTA	Retired	74.12 x 60.12 x 13.29 [1883 x 1527 x 338]	NPDD7260	NPDD7260G
SSN4D7472123PT	Retired	SSN4D7472123PTA	Retired	74.12 x 72.12 x 13.29 [1883 x 1832 x 338]	NPDD7272	—
SSN4D7472243PT	Retired	SSN4D7472243PTA	Retired	74.12 x 72.12 x 25.29 [1883 x 1832 x 642]	NPDD7272	—

Notes: Subpanels must be ordered separately.
Dimensions in inches [millimeters].
Letters in table correspond to letters on dimensional drawings.

NEMA 4, 4X, and 12 Stainless Steel Two-Door Floor-Mount with 3-Point Handle



Dimensions



Enclosure Subpanels



Subpanels for Two-Door Floor-Mount Enclosures

- Subpanels are fabricated from 10-gauge carbon steel
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- Subpanels are used in NEMA 12 double-door floor-mount enclosures and some double-door wall-mount enclosures



Shipping Schedule				
Same day	1 - 5 days	1 - 7 days	1 - 15 days	1 - 20 days
Color indicates shipping lead time in business days.				

Subpanels for Two-door Floor-Mount Enclosures					
Painted Steel	Price	Galvanized	Price	Nominal Enclosure Size HxW*	Subpanel Size AxB
NPDD4242	—	NPDD4242G	Retired	42 x 42	39.00 x 39.00 [991 x 991]
NPDD4260	Retired	NPDD4260G	Retired	42 x 60	38.00 x 56.00 [965 x 1422]
NPDD4842	—	NPDD4842G	Retired	48 x 42	45.00 x 39.00 [1143 x 991]
NPDD4848	—	NPDD4848G	Retired	48 x 48	44.00 x 44.00 [1118 x 1118]
NPDD5442	—	NPDD5442G	Retired	54 x 42	50.00 x 38.00 [1270 x 965]
NPDD6048	—	NPDD6048G	Retired	60 x 48	44.00 x 56.00 [1118 x 1422]
NPDD6060	—	NPDD6060G	Retired	60 x 60	56.00 x 56.00 [1422 x 1422]
NPDD7260	—	NPDD7260G	Retired	72 x 60	56.00 x 68.00 [1422 x 1727]
NPDD7272	—	—	—	72 x 72	68.00 x 68.00 [1727 x 1727]

Notes: Dimensions in inches [millimeters].
 Letters in table correspond to letters on dimensional drawing.
 *Some floor-mount enclosures may be up to 2 in [51 mm] taller than height listed in this table.
 Disconnect enclosures will be up to 2 in [51 mm] wider than width dimensions listed in this table.

Dimensions

