

# NEMA 4, 4X, and 12 Stainless Steel Two-Door Floor-Mount



## Applications

These two-door enclosures provide industry-leading protection for systems incorporating large components or complex configurations in highly corrosive environments. It is typically used in the following areas: food processing plants, pharmaceutical manufacturing facilities, petrochemical plants, pulp and paper processing, and waste water treatment facilities.



## Construction

- Bodies and doors fabricated from 12-gauge 304 stainless steel
- Continuously-welded seams ground smooth
- X-type body stiffeners are included for extra strength
- Rolled lip around three sides of door and along top of enclosure opening excludes liquids and contaminants from entering
- Quick and easy-to-operate stainless steel door clamps around three sides of doors are provided
- Heavy gauge stainless steel continuous hinges are provided
- Pull hinge pin to remove doors
- Hasp and staple are provided for padlocking
- Print pocket is provided
- Standard 12 in [305 mm] floor kits are welded to bottom of enclosure
- Heavy-duty removable lifting eyes
- Doors are sealed with poured-in-place polyurethane gasket
- Grounding provisions provided
- Easily Removable center post permits easy panel installations
- Collar studs for mounting optional subpanels
- Uses WAN4XRA clamp

## Finish

- Enclosures have a smooth-grained finish on all exterior surfaces

## Listings

- UL 508, 4, 4X, and 12 [UL file E64791]
- Meets NEMA/EEMAC 4, 4X, and 12 requirements



Note: For current listings, please see [www.automationdirect.com](http://www.automationdirect.com)

## Shipping Schedule

Same day	1 - 5 days	1 - 7 days	1 - 15 days	1 - 20 days
----------	------------	------------	-------------	-------------

Color indicates shipping lead time in business days.

## NEMA 4, 4X, and 12 Stainless Steel Two-Door Floor-Mount Enclosures



Part Number	Price	Enclosure SizeHxWxD (not incl. 12 [305] legs)	Painted Steel Subpanel	Galvanized Subpanel
<b>SSN4D624812</b>	Retired	62.12 x 48.12 x 13.23 [1578 x 1222 x 336]	<b>NPDD6048</b>	<b>NPDD6048G</b>
<b>SSN4D626012</b>	Retired	62.12 x 60.12 x 13.23 [1578 x 1527 x 336]	<b>NPDD6060</b>	<b>NPDD6060G</b>
<b>SSN4D746012</b>	Retired	74.12 x 60.12 x 13.23 [1883 x 1527 x 336]	<b>NPDD7260</b>	<b>NPDD7260G</b>
<b>SSN4D747212</b>	Retired	74.12 x 72.12 x 13.23 [1883 x 1832 x 336]	<b>NPDD7272</b>	—
<b>SSN4D747224</b>	Retired	74.12 x 72.12 x 25.23 [1883 x 1832 x 641]	<b>NPDD7272</b>	—

Notes: Subpanels must be ordered separately.  
Dimensions in inches [millimeters].  
Letters in table correspond to letters on dimensional drawings.

# NEMA 4, 4X, and 12 Stainless Steel Two-Door Floor-Mount



## Dimensions



# Enclosure Subpanels



## Subpanels for Two-Door Floor-Mount Enclosures

- Subpanels are fabricated from 10-gauge carbon steel
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- Subpanels are used in NEMA 12 double-door floor-mount enclosures and some double-door wall-mount enclosures



Shipping Schedule				
Same day	1 - 5 days	1 - 7 days	1 - 15 days	1 - 20 days
Color indicates shipping lead time in business days.				

Subpanels for Two-door Floor-Mount Enclosures					
Painted Steel	Price	Galvanized	Price	Nominal Enclosure Size HxW*	Subpanel Size AxB
<a href="#">NPDD4242</a>	—	<a href="#">NPDD4242G</a>	Retired	42 x 42	39.00 x 39.00 [991 x 991]
<a href="#">NPDD4260</a>	Retired	<a href="#">NPDD4260G</a>	Retired	42 x 60	38.00 x 56.00 [965 x 1422]
<a href="#">NPDD4842</a>	—	<a href="#">NPDD4842G</a>	Retired	48 x 42	45.00 x 39.00 [1143 x 991]
<a href="#">NPDD4848</a>	—	<a href="#">NPDD4848G</a>	Retired	48 x 48	44.00 x 44.00 [1118 x 1118]
<a href="#">NPDD5442</a>	—	<a href="#">NPDD5442G</a>	Retired	54 x 42	50.00 x 38.00 [1270 x 965]
<a href="#">NPDD6048</a>	—	<a href="#">NPDD6048G</a>	Retired	60 x 48	44.00 x 56.00 [1118 x 1422]
<a href="#">NPDD6060</a>	—	<a href="#">NPDD6060G</a>	Retired	60 x 60	56.00 x 56.00 [1422 x 1422]
<a href="#">NPDD7260</a>	—	<a href="#">NPDD7260G</a>	Retired	72 x 60	56.00 x 68.00 [1422 x 1727]
<a href="#">NPDD7272</a>	—	—	—	72 x 72	68.00 x 68.00 [1727 x 1727]

Notes: Dimensions in inches [millimeters].  
 Letters in table correspond to letters on dimensional drawing.  
 \*Some floor-mount enclosures may be up to 2 in [51 mm] taller than height listed in this table.  
 Disconnect enclosures will be up to 2 in [51 mm] wider than width dimensions listed in this table.

## Dimensions

