

# PEW Series Inductive Proximity Sensors



## M8 (8mm) stainless steel - DC

- Low cost/high performance
- Metal sensing face for extreme environments
- LED status indicators are visible at a wide angle.
- Sensing face withstands up to 1450 psi.
- M12 quick-disconnect models
- 2 M8 stainless steel lock nuts included
- Purchase cable separately
- Lifetime warranty




**PEW Series DC Inductive Prox Selection Chart**

Part Number	Price	Sensing Range	Mounting	Output State	Logic	Connection	Wiring	Dimensions
PEW-AN-1H	\$48.50	2 mm (0.08 in)	Flush	N.O.	NPN	M12 (12mm) quick-disconnect	Diagram 1	Figure 1


## Wiring diagrams

**Diagram 1**

**NPN Output**




**M12 connector**



## Dimensions

mm[inches]

**Figure 1**



# PEW Series Inductive Proximity Sensors

PEW-AN-1H Specifications	
<b>Mounting Type</b>	<b>Flush</b>
<b>Nominal Sensing Distance</b>	2 mm (0.08 in) $\pm$ 10%
<b>Operating Distance</b>	0 to 1.6 mm (0.06 in)
<b>Material Correction Factors</b>	See the <a href="#">Material influence table</a>
<b>Output Type</b>	NPN, N.O. only
<b>Operating Voltage</b>	10 to 36 VDC
<b>No-load Supply Current</b>	< 20 mA
<b>Operating (Load) Current</b>	100 mA
<b>Off-state (Leakage) Current</b>	< 0.1 mA
<b>Voltage Drop</b>	< 2.5 V
<b>Switching Frequency</b>	100Hz
<b>Differential Travel (% of nominal Distance)</b>	1 to 15% of Sr
<b>Repeat Accuracy</b>	NA
<b>Ripple</b>	NA
<b>Reverse Polarity Protection</b>	Yes
<b>Short-Circuit Protection</b>	Yes (non-latching)
<b>Operating Temperature</b>	-25 to 70°C (-13 to 158°F)
<b>Protection Degree (DIN 40050)</b>	IEC IP67/68
<b>Indication/Switch Status</b>	4 Yellow
<b>Housing Material</b>	316L stainless steel
<b>Sensing Face Material</b>	316L stainless steel
<b>Shock/Vibration</b>	See <a href="#">Proximity Sensor Terminology</a>
<b>Tightening Torque</b>	3.5 Nm (2.58 lb-ft)
<b>Weight</b>	20g (0.71 oz)
<b>Connection</b>	M12 plug with gold-plated pins
<b>Agency Approvals</b>	cULus file E328811, CE, RoHS

# Accessories for 8mm Sensors

## Axial Mounting Bracket

Mounting bracket, axial, zinc-plated steel. For use with 8mm sensors. Has two mounting holes (use 3 mm screws) and allows the rotation of an optical axis for axial sensors. Hexagonal nuts not included.

Accessories for 8mm Sensors				
Part Number	Price	Description	Drawing Link	Weight [lb]
<b><u>ST08A</u></b>	\$2.00	Micro Detectors mounting bracket, axial, zinc plated steel. For use with 8mm sensors.	<a href="#">PDF</a>	0.04



**ST08A**

## Right-angle Mounting Bracket

Mounting bracket, right-angle, zinc-plated steel. For use with 8mm sensors. Has two mounting holes (use 3mm screws) and allows the rotation of an optical axis for right-beam-angle-adaptor sensors. Hexagonal nuts not included.

Accessories for 8mm Sensors				
Part Number	Price	Description	Drawing Link	Weight [lb]
<b><u>ST08C</u></b>	\$2.00	Micro Detectors mounting bracket, right-angle, zinc plated steel. For use with 8mm sensors.	<a href="#">PDF</a>	0.04



**ST08C**

# Accessories for 8mm Sensors

## Right-angle Mounting Bracket

Mounting bracket, right-angle, plastic. For use with 8mm sensors.

Accessories for 8mm Sensors				
Part Number	Price	Description	Drawing Link	Weight [lb]
<a href="#"><u>OPT2101</u></a>	\$7.25	Wenglor mounting bracket, right-angle, plastic. For use with 8mm sensors.	<a href="#"><u>PDF</u></a>	0.02



OPT2101

## Right-angle Swivel Mounting Systems

Mounting bracket, right-angle swivel, 360 degree vertical and horizontal adjustment. For use with 8mm sensors. Available in all stainless steel or with an aluminum head and stainless steel mounting plate.

Accessories for 8mm Sensors						
Part Number	Price	Description	Mounting Head	Mounting Plate	Drawing Link	Weight [lb]
<a href="#"><u>OPT2112</u></a>	\$10.50	Wenglor mounting bracket, right-angle swivel, 360 degree vertical and horizontal adjustment, aluminum, 12mm rod mount. For use with 8mm sensors.	Aluminum	304 Stainless Steel	<a href="#"><u>PDF</u></a>	0.14
<a href="#"><u>OPT2113</u></a>	\$18.50	Wenglor mounting bracket, right-angle swivel, 360 degree vertical and horizontal adjustment, 304 stainless steel, 12mm rod mount. For use with 8mm sensors.	304 Stainless Steel	304 Stainless Steel	<a href="#"><u>PDF</u></a>	0.26



OPT2112 & OPT2113

Note: 304 Stainless steel mounting rods sold separately: OPT2109 (200mm length), OPT2110 (300mm length), and OPT2111 (500mm length).

# Mounting Rods and Brackets

## Mounting Rods

304 Stainless steel rods for mounting swivel brackets OPT2112 - OPT2127. Available in three lengths: 200mm, 300mm, and 500mm. 12mm diameter.

Mounting Rods for OPT2112-2127 Swivel Mounting Brackets				
Part Number	Price	Description	Drawing Link	Weight lb (g)
<a href="#"><u>OPT2109</u></a>	\$11.50	Wenglor mounting rod, 12mm diameter, 200mm length, 304 stainless steel.	<a href="#"><u>PDF</u></a>	0.41 (185.97)
<a href="#"><u>OPT2110</u></a>	\$14.50	Wenglor mounting rod, 12mm diameter, 300mm length, 304 stainless steel.	<a href="#"><u>PDF</u></a>	0.60 (272.16)
<a href="#"><u>OPT2111</u></a>	\$18.50	Wenglor mounting rod, 12mm diameter, 500mm length, 304 stainless steel.	<a href="#"><u>PDF</u></a>	0.98 (444.52)



## Right-angle Mounting Bracket

Mounting bracket, right-angle, nickel-plated brass. For use with 12mm mounting rods OPT2109, OPT2110 & OPT2111.

Right-angle Mounting Brackets for 12mm Sensors				
Part Number	Price	Description	Drawing Link	Weight lb (g)
<a href="#"><u>OPT2108</u></a>	\$14.50	Wenglor mounting bracket, right-angle, nickel plated brass. For use with 12mm mounting rods OPT2109, OPT2110 & OPT2111.	<a href="#"><u>PDF</u></a>	0.07 (31.8)

