



Precision Ground Linear Shafts

1060 Steel and 440C Stainless Steel



Features

- C1060 steel
- RC60-65 Hardness
- 10RMS Surface Finish
- Tolerance: Class L
 $\pm 1/32"$ length tolerance
 $+ 0.0000" / - 0.0005"$ diameter tolerance



Linear Shafts - 1060 Steel				
Part Number	A	ØB	Price	Weight (lb)
<u>LPCS08-12</u>	12.0	0.50		0.71
<u>LPCS08-24</u>	24.0	0.50		2.41
<u>LPCS08-36</u>	36.0	0.50		3.41
<u>LPCS12-12</u>	12.0	0.75		1.52
<u>LPCS12-24</u>	24.0	0.75		4.03
<u>LPCS12-36</u>	36.0	0.75		5.84
<u>LPCS16-12</u>	12.0	1.0		2.71
<u>LPCS16-24</u>	24.0	1.0		6.41
<u>LPCS16-36</u>	36.0	1.0		9.41

Note: All measurements in inches



Features



- 440C Stainless steel
- RC50-55 Hardness
- 10RMS Surface Finish
- Tolerance: Class L
 $\pm 1/32"$ length tolerance
 $+ 0.0000" / - 0.0005"$ diameter tolerance



Linear Shafts - 440C Stainless Steel				
Part Number	A	ØB	Price	Weight (lb)
<u>LPSS08-12</u>	12.0	0.50		0.71
<u>LPSS08-24</u>	24.0	0.50		2.41
<u>LPSS08-36</u>	36.0	0.50		3.41
<u>LPSS12-12</u>	12.0	0.75		1.52
<u>LPSS12-24</u>	24.0	0.75		4.03
<u>LPSS12-36</u>	36.0	0.75		5.84
<u>LPSS16-12</u>	12.0	1.0		2.71
<u>LPSS16-24</u>	24.0	1.0		6.41
<u>LPSS16-36</u>	36.0	1.0		9.41

Note: All measurements in inches

Dimensions



See our website www.AutomationDirect.com for complete Engineering drawings.