

Tools – Hand Taps

Metric Thread Hand Taps

High-speed steel metric hand taps.




231100 shown

| High-Speed Steel Metric Hand Taps | | | | | | | | | | | |
|-----------------------------------|--------|---------|-------|-------------|----------------|-------------|----------|---------|-------|-------------|----------------|
| Coarse Thread | Part # | Pcs/Pkg | Price | Thread Size | Use With | Fine Thread | Part # | Pcs/Pkg | Price | Thread Size | Use With |
| | 231030 | 1 | <--> | M3x0.5 | 214025, 215025 | | 235041-1 | 1 | <--> | M4x0.5 | 214035, 215035 |
| | 231040 | 1 | <--> | M4x0.7 | 214033, 215033 | | 235050-1 | 1 | <--> | M5x0.5 | 214045, 215045 |
| | 231050 | 1 | <--> | M5x0.8 | 214042, 215042 | | 235081-1 | 1 | <--> | M8x1 | 214070, 215070 |
| | 231060 | 1 | <--> | M6x1 | 214050, 215050 | | 235122-1 | 1 | <--> | M12x1 | 214110, 215110 |
| | 231080 | 1 | <--> | M8x1.25 | 214068, 215068 | | 235181-1 | 1 | <--> | M18x1 | 17.0 mm |
| | 231100 | 1 | <--> | M10x1.5 | 214085, 215085 | | 235301-1 | 1 | <--> | M30x1.5 | 28.5 mm |
| | 231120 | 1 | <--> | M12x1.75 | 214102, 215102 | | | | | | |

NPT Thread Hand Taps

High-speed steel National Pipe Taper hand taps.

| High-Speed Steel NPT Hand Taps | | | | |
|--------------------------------|---------|-------|-------------|-------------------------|
| Part # | Pcs/Pkg | Price | Thread Size | Use With |
| 231116NPT | 1 | <--> | 1/16-27 NPT | 214813, 250813T, 215813 |
| 231018NPT | 1 | <--> | 1/8-27 NPT | 214819, 250819T, 215819 |
| 231014NPT | 1 | <--> | 1/4-18 NPT | 214825, 250825T, 215825 |
| 231038NPT | 1 | <--> | 3/8-18 NPT | 37/64" |
| 231012NPT | 1 | <--> | 1/2-14 NPT | 23/32" |




23108NPT shown

Conduit Thread Hand Taps

High-speed steel DIN 40430 conduit thread hand taps.

| High-Speed Steel Conduit Thread Hand Taps | | | | |
|---|---------|-------|-------------|----------|
| Part # | Pcs/Pkg | Price | Thread Size | Use With |
| 264009 | 1 | <--> | PG-9 | 14.0 mm |
| 264011 | 1 | <--> | PG-11 | 17.25 mm |
| 264016 | 1 | <--> | PG-16 | 21.25 mm |
| 264021 | 1 | <--> | PG-21 | 26.75 mm |
| 264029 | 1 | <--> | PG-29 | 35.5 mm |



264029 shown

Tools – Hand Tap Wrenches

Hand Tap Wrenches



241103 shown



241010 shown

| Hand Tap Wrenches | | | | | |
|-------------------|---------|-------|--|---|-------------------------------|
| Part # | Pcs/Pkg | Price | Description | Construction Material | Use With |
| 241010 | 1 | <---> | Sliding T-handle ratcheting tap wrench | Chrome plated steel | M3 to M10, 1/8" to 3/8" taps |
| 241020 | 1 | <---> | Sliding T-handle ratcheting tap wrench | Chrome plated steel | M5 to M12, 7/32" to 1/2" taps |
| 241103 | 1 | <---> | Two-jaw chuck tap wrench | Die cast zinc housing, steel handles, hardened chuck jaws | M5 to M20, 1/4" to 3/4" taps |
| 241112 | 1 | <---> | Two-jaw chuck tap wrench | Die cast zinc housing, steel handles, hardened chuck jaws | M1 to M12, 1/8" to 1/2" taps |

Tools – Countersinks

High-speed steel type C taper and deburring countersinks have cutting geometry that enables up to 30% faster chatter-free cutting.



102719 shown



102153 shown

| RUKO Countersinks | | | | | |
|-------------------|-------|---|-----------------|------------------|---------------------|
| Part # | Price | Countersink Diameter | | Total Length (L) | Shank Diameter (d2) |
| | | Nominal (d1) | d3 | | |
| 102714 | <---> | 10.4 mm (0.409") | 2.5 mm (0.098") | 50.0 mm (1.969") | 6.0 mm (0.236") |
| 102716 | <---> | 12.4 mm (0.488") | 2.8 mm (0.110") | 56.0 mm (2.205") | 8.0 mm (0.315") |
| 102719 | <---> | 16.5 mm (0.650") | 3.2 mm (0.126") | 60.0 mm (2.362") | 10.0 mm (0.394") |
| 102721 | <---> | 20.5 mm (0.807") | 3.5 mm (0.138") | 63.0 mm (2.480") | 10.0 mm (0.394") |
| 102723 | <---> | 25.0 mm (0.984") | 3.8 mm (0.150") | 67.0 mm (2.638") | 10.0 mm (0.394") |
| 102153 | <---> | 5-piece Countersink kit - Includes : 102714, 102716, 102719, 102721, 102723 | | | |

