

LED Modules

LED/sensor modules provide simple and logical termination for 3-wire sensors or other devices. These modules offer visual LED indication of device input status for quick troubleshooting. The LED/sensor modules are available in 120V AC or 24V AC/DC in 8 or 16-point versions, and offer extra termination points for daisy-chaining multiple modules.

Modules mount on 35 mm DIN rail part #DN-R35S1 (see Accessories below).



ZL-CM08L24




ZL-CM08L120




ZL-CM16L24

Specifications									
LED Modules	Part #	Pcs/Pkg	Price/Pkg	Part #	Pcs/Pkg	Price/Pkg	Part #	Pcs/Pkg	Price/Pkg
		ZL-CM08L24	1	<--->	ZL-CM08L120	1	<--->	ZL-CM16L24	1
Description	8 point I/O connector module with 8 LEDs, 24V, 20 pin IDC			8 point I/O connector module with 8 LEDs, 120V, 20 pin IDC			16 point I/O connector module with 16 LEDs, 24V, 24 pin IDC		
Approvals	UL/CUL/CE								
Operation Voltage	5-26VDC			48-120VAC			5-26VDC		
Max Voltage	30VDC			120VAC			30VDC		
Max Current per Channel				500mA					
Current Nominal per Channel	8-18mA			15-18mA			8-18mA		
Maximum Current (per Circuit)				1A					
Maximum Current (per Module)	8A			8A			16A		
Voltage Rating	0-30 VAC/DC			0-120VAC			0-30 VAC/DC		
Peak Voltage	70V			200VAC			70V		
Indicator Circuit Current				2mA					
# of Terminals per Device Common	10			10			18		
Terminal Block Contacts	Copper alloy, tin-lead plating								
Wire Range (Rated Cross Section)	14-22 AWG (0.2-2.5mm ²)								
Wire Strip Length	0.32 (8mm)								
Operating Temperature Range	0°C to +50°C			0°C to +40°C			0°C to +50°C		
Dimensions (L x W x H)	2.99"(76mm)x2.99"(76mm)x3.66"(93mm)			2.99"(76mm)x2.99"(76mm)x3.66"(93mm)			4.37"(111mm)x2.99"(76mm)x3.66"(93mm)		


Accessories									
	Part #	Pcs/Pkg	Price/Pkg	Part #	Pcs/Pkg	Price/Pkg	Part #	Pcs/Pkg	Price/Pkg
DIN Rail	DN-R35S1	10	<--->	DN-R35S1	10	<--->	DN-R35S1	10	<--->
Angled Support Bracket	DN-ASB1	50	<--->	DN-ASB1	50	<--->	DN-ASB1	50	<--->
End Bracket	DN-EB35	50	<--->	DN-EB35	50	<--->	DN-EB35	50	<--->
Slotted Screwdriver	DN-SS1	1	<--->	DN-SS1	1	<--->	DN-SS1	1	<--->



ZL-CM08L24
ZL-CM08L120



ZL-CM16L24



Note: See wiring details on our Web site at:
<http://www.automationdirect.com/static/manuals/ziplinks/ziplinks.html>

- PLC Overview
- DL05/06 PLC
- DL105 PLC
- DL205 PLC
- DL305 PLC
- DL405 PLC
- Field I/O
- Software
- C-more HMIs
- Other HMI
- AC Drives
- Motors
- Steppers/Servos
- Motor Controls
- Proximity Sensors
- Photo Sensors
- Limit Switches
- Encoders
- Current Sensors
- Pushbuttons/Lights
- Process
- Relays/Timers
- Comm.
- TB's & Wiring
- Power
- Circuit Protection
- Enclosures
- Appendix
- Part Index

LED Modules

LED/sensor modules provide simple and logical termination for 3-wire sensors or other devices. These modules offer visual LED indication of device input status for quick troubleshooting. The LED/sensor modules are available in 120V AC or 24V AC/DC in 8 or 16-point versions, and offer extra termination points for daisy-chaining multiple modules.

Modules mount on 35 mm DIN rail part #DN-R35S1 (see Accessories below).



ZL-CM16L120




ZL-CM32L524


Specifications						
LED Modules	Part #	Pcs/Pkg	Price/Pkg	Part #	Pcs/Pkg	Price/Pkg
		ZL-CM16L120	1	<--->	ZL-CM32L524	1
Description	16-point I/O connector module with 16 LEDs, 120VAC, 24 pin IDC			32-point I/O connector module with 32 LEDs, 5 - 28VDC, 40 pin IDC		
Approvals	UL/CUL/CE					
Operation Voltage	48 - 120VAC			5-26VDC		
Max Voltage	120VAC			30VDC		
Max Current per Channel	500mA					
Current Nominal per Channel	15-18mA			8-18mA		
Terminal Block Contacts	Copper alloy, tin - lead plating					
Wire Range (Rated Cross Section)	14 - 22 AWG (0.2 - 2.5mm ²)					
Wire Strip Length	0.32" (8mm)					
Voltage Rating	0 - 120VAC			0 - 30 VAC/DC		
Maximum Peak Voltage	200VAC			70V		
Maximum Current (per Circuit)	1A					
Maximum Current (per Module)	16A			32A		
Indicator Circuit Current (Nominal)	2mA			1mA		
No. of Terminals per Device Common	10			36		
Operating Temperature Range	0°C to +40°C			0°C to +50°C		
Dimensions (L x W x H)	4.37"(111mm)x2.99"(76mm)x2.58"(93mm)			8.50"(216mm)x2.99"(76mm)x3.66"(93mm)		

Accessories						
	Part #	Pcs/Pkg	Price/Pkg	Part #	Pcs/Pkg	Price/Pkg
DIN Rail	DN-R35S1	10	<--->	DN-R35S1	10	<--->
Angled Support Bracket	DN-ASB1	50	<--->	DN-ASB1	50	<--->
End Bracket	DN-EB35	50	<--->	DN-EB35	50	<--->
Slotted Screwdriver	DN-SS1	1	<--->	DN-SS1	1	<--->

ZL-CM16L120



ZL-CM32L524



Note: See wiring details on our Web site at:
<http://www.automationdirect.com/static/manuals/ziplinks/ziplinks.html>

Connection Cables

ZIPLink Connection Cables				
Part Number	Description	Insulation Rating	Conductor Size	Price
Standard DL205 8 Channel				
ZL-2CBL1	DL205-8 ZIPLink cable, 1.6 ft. (0.5M)	300V 80°C	#24 AWG	<--->
ZL-2CBL1-1	DL205-8 ZIPLink cable, 3.3 ft. (1.0M)	300V 80°C	#24 AWG	<--->
ZL-2CBL1-2	DL205-8 ZIPLink cable, 6.5 ft. (2.0M)	300V 80°C	#24 AWG	<--->
Standard DL205 16 Channel				
ZL-2CBL2	DL205-16 ZIPLink cable, 1.6 ft. (0.5M)	300V 80°C	#24 AWG	<--->
ZL-2CBL2-1	DL205-16 ZIPLink cable, 3.3 ft. (1.0M)	300V 80°C	#24 AWG	<--->
ZL-2CBL2-2	DL205-16 ZIPLink cable, 6.5 ft. (2.0M)	300V 80°C	#24 AWG	<--->
LED/Sensor DL205 16 Channel				
ZL-2CBL2L	DL205-16, ZIPLink LED/sensor module cable, 1.6 ft. (0.5M)	300V 80°C	#24 AWG	<--->
ZL-2CBL2L-1	DL205-16, ZIPLink LED/sensor module cable, 3.3 ft. (1.0M)	300V 80°C	#24 AWG	<--->
ZL-2CBL2L-2	DL205-16, ZIPLink LED/sensor module cable, 6.5 ft. (2.0M)	300V 80°C	#24 AWG	<--->
Standard DL305 16 Channel				
ZL-3CBL2	DL305-16 ZIPLink cable, 1.6 ft. (0.5M)	300V 80°C	#24 AWG	<--->
ZL-3CBL2-1	DL305-16 ZIPLink cable, 3.3 ft. (1.0M)	300V 80°C	#24 AWG	<--->
ZL-3CBL2-2	DL305-16 ZIPLink cable, 6.5 ft. (2.0M)	300V 80°C	#24 AWG	<--->
LED/Sensor DL305 16 Channel				
ZL-3CBL2L	DL305-16, ZIPLink LED/sensor module cable, 1.6 ft. (0.5M)	300V 80°C	#24 AWG	<--->
ZL-3CBL2L-1	DL305-16, ZIPLink LED/sensor module cable, 3.3 ft. (1.0M)	300V 80°C	#24 AWG	<--->
ZL-3CBL2L-2	DL305-16, ZIPLink LED/sensor module cable, 6.5 ft. (2.0M)	300V 80°C	#24 AWG	<--->
Fuse/Relay DL305 8 Channel				
ZL-3CBL1FR8	DL305-8, ZIPLink fuse/relay module cable, 1.6 ft. (0.5M)	300V 80°C	#24 AWG	<--->
ZL-3CBL1FR8-1	DL305-8, ZIPLink fuse/relay module cable, 3.3 ft. (1.0M)	300V 80°C	#24 AWG	<--->
ZL-3CBL1FR8-2	DL305-8, ZIPLink fuse/relay module cable, 6.5 ft. (2.0M)	300V 80°C	#24 AWG	<--->
Fuse/Relay DL305 16 Channel				
ZL-3CBL2FR16	DL305-16, ZIPLink fuse/relay module cable, 1.6 ft. (0.5M)	300V 80°C	#24 AWG	<--->
ZL-3CBL2FR16-1	DL305-16, ZIPLink fuse/relay module cable, 3.3 ft. (1.0M)	300V 80°C	#24 AWG	<--->
ZL-3CBL2FR16-2	DL305-16, ZIPLink fuse/relay module cable, 6.5 ft. (2.0M)	300V 80°C	#24 AWG	<--->
Standard DL305 16 Channel				
ZL-3CBL3	DL305-16 ZIPLink cable, 1.6 ft. (0.5M)	300V 80°C	#24 AWG	<--->
ZL-3CBL3-1	DL305-16 ZIPLink cable, 3.3 ft. (1.0M)	300V 80°C	#24 AWG	<--->
ZL-3CBL3-2	DL305-16 ZIPLink cable, 6.5 ft. (2.0M)	300V 80°C	#24 AWG	<--->
Fuse/Relay DL305 16 Channel				
ZL-3CBL3FRD16	DL305-16, ZIPLink fuse/relay module cable, 1.6 ft. (0.5M)	300V 80°C	#24 AWG	<--->
ZL-3CBL3FRD16-1	DL305-16, ZIPLink fuse/relay module cable, 3.3 ft. (1.0M)	300V 80°C	#24 AWG	<--->
ZL-3CBL3FRD16-2	DL305-16, ZIPLink fuse/relay module cable, 6.5 ft. (2.0M)	300V 80°C	#24 AWG	<--->
Standard DL405 16 Channel				
ZL-4CBL2	DL405-16 ZIPLink cable, 1.6 ft. (0.5M)	300V 80°C	#24 AWG	<--->
ZL-4CBL2-1	DL405-16 ZIPLink cable, 3.3 ft. (1.0M)	300V 80°C	#24 AWG	<--->
ZL-4CBL2-2	DL405-16 ZIPLink cable, 6.5 ft. (2.0M)	300V 80°C	#24 AWG	<--->
Standard DL205 or DL405 32 Channel				
ZL-4CBL4	DL205 or DL405-32 ZIPLink cable, 1.6 ft. (0.5M)	300V 80°C	#24 AWG	<--->
ZL-4CBL4-1	DL205 or DL405-32 ZIPLink cable, 3.3 ft. (1.0M)	300V 80°C	#24 AWG	<--->
ZL-4CBL4-2	DL205 or DL405-32 ZIPLink cable, 6.5 ft. (2.0M)	300V 80°C	#24 AWG	<--->

ZL-2CBL1xx



ZL-2CBL2xx



ZL-3CBL2xx



ZL-3CBL3xx



ZL-4CBL2xx



ZL-4CBL4xx



PLC Overview

DL05/06 PLC

DL105 PLC

DL205 PLC

DL305 PLC

DL405 PLC

Field I/O

Software

C-more HMIs

Other HMI

AC Drives

Motors

Steppers/Servos

Motor Controls

Proximity Sensors

Photo Sensors

Limit Switches

Encoders

Current Sensors

Pushbuttons/Lights

Process

Relays/Timers

Comm.

TB's & Wiring

Power

Circuit Protection

Enclosures

Appendix

Part Index

Connection Cables (cont.)

ZiLink Connection Cables				
Part Number	Description	Insulation Rating	Conductor Size	Price
Communication Adapter				
ZL-DN15TB-CBL	15 pin shielded cable for DN-15TB module 6.5 ft (2M)	300V 80°C	#28 AWG	<--->
ZL-DN25TB-CBL	25 pin shielded cable for DN-25TB module 6.5 ft (2M)	300V 80°C	#28 AWG	<--->
Ready to Wire w/Pigtail End				
ZL-2CBL2-2P	DL-205-16 Ready-to-wire 20 conductor cable, 2A max/conductor 6.5 ft (2M)	300V 80°C	#24 AWG	<--->
ZL-3CBL3-2P	DL-305-16 Ready-to-wire 24 conductor cable, 2A max/conductor 6.5 ft (2M)	300V 80°C	#24 AWG	<--->
Standard DL05/06				
ZL-CBL056	Ziplink cable for DL05 and 06 16 point I/O modules to Ziplink feedthrough modules (0.5M)	300V 80°C	#24 AWG	<--->
ZL-CBL056L	Ziplink cable for DL05 and 06 16 point I/O LED modules (0.5M)	300V 80°C	#24 AWG	<--->
ZL-CBL056FR	Ziplink cable for DL05 and 06 16 point I/O fuse/relay modules (0.5M)	300V 80°C	#24 AWG	<--->
Standard				
ZL-DB9-CBL	Cable with 9-pin Dsub connectors on both ends, black. male/female, (2M)	300V 80°C	#28 AWG	<--->
ZL-DB15-CBL	Cable with 15-pin Dsub connectors on both ends, black. male/female, (2M)	300V 80°C	#28 AWG	<--->
ZL-DB25-CBL	Cable with 25-pin Dsub connectors on both ends, black. male/female, (2M)	300V 80°C	#28AWG	<--->
ZL-RJ12-CBL	Reverse-wired cable with two RJ12 connectors, black. (2M)	300V 80°C	#28 AWG	<--->

Note: Use ZL-DN15TB-CBL cable only for Communication Module DN-15TB; Super VGA cables will not function correctly.

ZL-2CBL2-2P*



* Can be used with any brand PLC.

ZL-CBL056L



ZL-DN15TB-CBL



ZL-DN25TB-CBL

