


OPT Series Color Sensors Cable

Plastic Fiber Optic Cable

OPT2075 Diffuse Reflex Mode


\$43.00

- Compatible with the OPT2022 6-channel sensor
- Designed for installation in tight spaces
- IP68



OPT2075 Specifications	
Optical Fiber Core Ø	0.5 mm
Sensing Distance with OPT series	10mm
Fiber Length (L)	1m
Fiber Bending Radius	15mm
Spot Diameter	0.5 to 2 mm
Temperature Range	-40 to 85°C [-40 to 185°F]
Fiber Materials	PMMA
Sleeve Materials	PE (black)
Head Materials	Stainless steel
Jacket Diameter	1.3 mm
Fiber Distribution	Coaxial arrangement
Opening Angle	55°
Light Emission	Straight

Dimensions mm [inches]



See our website: www.AutomationDirect.com for complete Engineering drawings.

OPT Series Color Sensors Cable


Glass Fiber Optic Cable

OPT2087 Through-Beam Mode

\$110.00

Dimensions mm [inches]

OPT2087 Specifications	
Optical Fiber Core Ø	3mm
Sensing Distance with OPT series	600mm
Fiber Length (L)	1m
Fiber Bending Radius	50mm
Free Cut	No
Head Size	M18
Temperature Range	0 to 60°C [32 to 140°F]
Fiber Materials	Glass
Sleeve Materials	Brass (CuZn) nickel-plated
Head Materials	Anodized aluminum
Fiber Diameter	3mm
Fiber Distribution	Statistical mixture
Opening Angle	30°



See our website: www.AutomationDirect.com for complete Engineering drawings.

OPT Series Color Sensors Cable

Glass Fiber Optic Cable


OPT2088 Diffuse (Reflex) Mode

\$118.00

OPT2088 Specifications	
Optical Fiber Core Ø	3mm
Sensing Distance with OPT series	100mm
Fiber Length (L)	1m
Fiber Bending Radius	50mm
Free Cut	No
Head Size	M30
Temperature Range	0 to 60°C [32 to 140°F]
Fiber Materials	Glass
Sleeve Materials	Brass (CuZn) nickel-plated
Head Materials	Anodized aluminum
Fiber Diameter	3mm
Fiber Distribution	Statistical mixture



Dimensions mm [inches]




OPT2089 Diffuse (Reflex) Mode

\$105.00

OPT2089 Specifications	
Optical Fiber Core Ø	1.6 mm
Sensing Distance with OPT series	18mm
Fiber Length (L)	1m
Fiber Bending Radius	50mm
Free Cut	No
Head Size	M18
Temperature Range	0 to 60°C [32 to 140°F]
Fiber Materials	Glass
Sleeve Materials	Brass (CuZn) nickel-plated
Head Materials	Anodized aluminum
Fiber Diameter	1.6 mm
Fiber Distribution	Statistical mixture



Dimensions mm [inches]



See our website: www.AutomationDirect.com for complete Engineering drawings.