

OPT Series Transit Time Photoelectric Sensors

Rectangular Plastic Distance Sensors



- Diffuse and Retro-reflective (Transit time) laser distance measurement sensors
- Analog and switching outputs available
- Measured value independent of material, color, and brightness
- Class 1 and 2 lasers available (safety label included with Class 2 lasers)
- M12 and M8 quick-disconnect and pigtail versions; purchase cable separately
- Mounting hardware included

OPT2010, OPT2015, OPT2019

OPT Series Photoelectric Sensors Selection Chart

Part Number	Price	Working Range m [ft]	Laser Class	Function	Measurement Rate	Resolution	Output State	Connection	Wiring Diagram	Dims [mm]	Drawing Link
Diffuse (Transit Time)											
OPT2010	\$306.00	0 - 3 [0 - 9.84]	1	Switching	1kHz	Hysteresis < 15mm	Complementary (N.O./N.C.) PNP	5-pin M12 quick-disconnect	1	50 x 50 x 20	PDF
OPT2011	\$384.00	0.05 - 3.05 [0.16 - 10.01]		Measuring / Switching	500/s [2ms]	1mm [0.04 in]	Analog 4-20 mA or 0-10 VDC	4-pin M12 quick-disconnect	2		PDF
OPT2012	\$407.00	0.2 - 6.2 [0.66 - 20.34]			1-100/s [10ms]	1-12 mm [0.04 - 0.47 in]		Switching PNP/NPN (N.O./N.C.)	8-pin M12 quick-disconnect	3	PDF
OPT2013	\$701.00	0.1 - 10.1 [0.33 - 33.14]	2	1-100/s [10ms]	1-12 mm [0.04 - 0.47 in]		Switching PNP/NPN (N.O./N.C.)		4-pin M12 quick-disconnect	4	PDF
OPT2014	\$423.00								3	PDF	
OPT2016	\$317.00	0 - 1 [0 - 3.28]	1	Switching	1kHz	Hysteresis < 20mm	Complementary (N.O./N.C.) PNP	4-pin M8 quick-disconnect	5	22 x 32 x 12	PDF
OPT2017	\$317.00							4-pin M12 quick-disconnect, 200mm [7.87 in] cable			PDF
OPT2018	\$317.00							4-pin M8 quick-disconnect, 200mm [7.87 in] cable			PDF
OPT2019	\$317.00							Pigtail, 2m [6.5 ft] cable			PDF
OPT2170	\$259.00							0 - 3 [0 - 9.84]	1		Switching
OPT2171	\$259.00	2 mutually independent switching NPN	6	PDF							
OPT2172	\$207.00	0 - 1 [0 - 3.28]	1	Measuring/ Switching	1-100/s [10ms]	Hysteresis < 20mm	2 mutually independent switching PNP	4-pin M8 quick-disconnect	7	22 x 32 x 12	PDF
OPT2173	\$207.00							4-pin M8 quick-disconnect, 200mm [7.87 in] cable			PDF
OPT2174	\$207.00							4-pin M8 quick-disconnect, 200mm [7.87 in] cable			PDF
Retro-Reflective (Transit Time)											
OPT2015*	\$807.00	0.2 - 100.2 [0.66 - 328.74]	1	Measuring/ Switching	1-100/s [10ms]	4-20 mm [0.16 - 0.79 in]	Analog 4-20 mA or 0-10 VDC Switching PNP/NPN (N.O./N.C.)	8-pin M12 quick-disconnect	4	55 x 81 x 30	PDF

*Requires purchase of [OPT2030](#) reflector (see Accessories). <50m sensing distance requires 1 reflector. 50-100m sensing distance requires 4 reflectors.

OPT Series Transit Time Photoelectric Sensors

Wiring Diagrams

Diagram 1




Diagram 2




Diagram 3




Diagram 4




Diagram 5




Diagram 6





Diagram 7




Legend

+	Supply Voltage +	PT	Platinum measuring resistor
-	Supply Voltage 0 V	nc	not connected
-	Supply Voltage (AC Voltage)	U	Test Input
A	Switching Output (NO)	Ū	Test Input inverted
A̅	Switching Output (NC)	W	Trigger Input
V	Contamination/Error Output (NO)	W-	Ground for the Trigger Input
V̅	Contamination/Error Output (NC)	O	Analog Output
E	Input (analog or digital)	O-	Ground for the Analog Output
T	Teach Input	BZ	Block Discharge
Z	Time Delay (activation)	AWV	Valve Output
S	Shielding	a	Valve Control Output +
RxD	Interface Receive Path	b	Valve Control Output 0 V
TxD	Interface Send Path	SY	Synchronization
RDY	Ready	SY-	Ground for the Synchronization
GND	Ground	E+	Receiver-Line
CL	Clock	S+	Emitter-Line
E/A	Output/Input programmable	⊕	Grounding
	IO-Link	SnR	Switching Distance Reduction
PoE	Power over Ethernet	Rx+/-	Ethernet Receive Path
IN	Safety Input	Tx+/-	Ethernet Send Path
OSSD	Safety Output	B _{us}	Interfaces-Bus A(+)/B(-)
Signal	Signal Output	La	Emitted Light disengageable
BL_D +/-	Ethernet Gigabit bidirect. data line (A-D)	Mag	Magnet activation
EN ₀	Encoder 0-pulse 0-0̅ (TTL)	RES	Input confirmation
		EDM	Contactors Monitoring


EN _A	Encoder A/Ā (TTL)
EN _B	Encoder B/B̅ (TTL)
EN _A	Encoder A
EN _B	Encoder B
A _{MIN}	Digital output MIN
A _{MAX}	Digital output MAX
A _{OK}	Digital output OK
SY _{IN}	Synchronization In
SY _{OUT}	Synchronization OUT
O _L T	Brightness output
M	Maintenance
rsv	reserved
Wire Colors according to IEC 60757	
BK	Black
BN	Brown
RD	Red
OG	Orange
YE	Yellow
GN	Green
BU	Blue
VT	Violet
GY	Grey
WH	White
PK	Pink
GNYE	Green/Yellow

Connectors


4-Pin M8 connector




4-Pin M12 connector



5-Pin M12 connector



8-Pin M12 connector



Switching Element Function

	Through-Beam and Reflective Models	Diffuse Models
Light-on	N.C.	N.O.
Dark-on	N.O.	N.C.

Note: Class 2 power source required

OPT Series Transit Time Photoelectric Sensors Specifications

OPT Series Transit Time Photoelectric Sensors Specifications										
Part Number	OPT2016	OPT2017	OPT2018	OPT2019	OPT2010	OPT2011	OPT2012	OPT2013	OPT2014	OPT2015
Type	Diffuse (Transit time)									*Retro-Reflective
Sensing distance – m [in]	1 [39.37]			3 [118.11]	3.05 [120.08]	6.2 [244.09]	10.1 [397.64]	100.2 [3944.90]		
Light spot diameter (at maximum range)	< 15mm			9mm		< 12mm	< 20mm		80mm @ 40m < 200mm @ 100m	
Laser class (EN 60825-1)	Class 1 Red Laser			Class 1 Red Laser			Class 2 Red Laser		Class 1 Red Laser	
Emission	680nm			660nm						
Sensitivity	Adjustable via Potentiometer			Adjustable via Teach						
Output type	PNP N.O./N.C.				Programmable: Analog 4-20 mA / 0-10 VDC, N.O./N.C. PNP/NPN					
Current output max load	N/A				500Ω					
Operating voltage	10-30 VDC				18-30 VDC					
No load supply current	< 30mA			< 50mA	< 70mA	< 100mA				
Operating (load) current	100mA			200mA	100mA	200mA				
Voltage drop	< 2.5 V (switching outputs)									
Measurement rate	N/A				500/s	1-100/s				
Switching frequency	1000Hz				250Hz	50Hz				
Linearity	< 2.5%			NA			0.2 %		0.05%	
Short-circuit protection	Yes									
Operating temperature	-40 to 50°C [-40 to 122°F]			-40 to 60°C [-40 to 140°F]	-40 to 50°C [-40 to 122°F]	-25 to 60°C [-13 to 140°F]				
Protection degree (DIN 40050)	IP67			IP68						
LED indicators - switching status	Yellow				Screen Display					
LED indicators - power	Green				Screen Display					
Housing material	Polycarbonate									
Lens material	PMMA (Polymethyl methacrylate)									
Shock/vibration	Tested according to EN 60068-2-6 / EN 60068-2-27									
Tightening torque	0.5 N·m (mounting screws)									
Weight (cable/connector)	8g [0.28 oz]	22g [0.78 oz]	16g [0.56 oz]	48g [1.69 oz]	37g [1.31 oz]	43g [1.52 oz]	81g [2.86 oz]	82g [2.89 oz]	80g [2.82 oz]	82g [2.89 oz]
Connectors	4-pin M8	4-pin M12	4-pin M8	Pigtail	5-pin M12	4-pin M12	8-pin M12	4-pin M12	8-pin M12	
Agency approvals	CE, cULUS, E189727, RoHs									

*Requires purchase of OPT2030 reflector (see Accessories). <50m sensing distance requires 1 reflector. 50-100m sensing distance requires 4 reflectors. To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

IMPORTANT NOTE

The Laser Classification Systems for the standards IEC (EN) 60825-1 defines the following safety classes:

Class 1

This class is eye-safe under all operating conditions.

Class 2

These are visible lasers. This class is safe for accidental viewing under all operating conditions. However, it may not be safe for a person who deliberately stares into the laser beam for longer than 0.25 seconds, by overcoming their natural aversion response to the very bright light.

OPT Series Transit Time Photoelectric Sensors Specifications

OPT2170 - OPT2174 sensors guarantee reliable switching performance: Whether there is a glossy object in the background or a reflective surface or even reflectors in the working area these high-performance distance sensors continue to perform. Black surfaces are reliably detected even in extremely inclined positions depending on the surface characteristics and the distance from an angle of up to 89°. The sensors do not interact with each other if they are located in very close proximity to each other or even directly opposite each other.

The Laser Classification Systems for the standards IEC (EN) 60825-1 defines the following safety classes: Class 1. This class is eye-safe under all operating conditions.

OPT Series Transit Time Photoelectric Sensors Specifications					
Part Number	OPT2170	OPT2171	OPT2172	OPT2173	OPT2174
Type	Diffuse (Transit time)				
Sensing distance – m [ft]	3 [9.84]		1 [3.28]		
Light spot diameter (at maximum range)	9mm		15mm		
Laser class (EN 60825-1)	Class 1 Red Laser				
Wavelength	660nm		680nm		
Sensitivity	Adjustable via Teach				
Output type	PNP N.O.	NPN N.O.	PNP N.O.		
Current output max load	200mA		100mA		
Operating voltage	10-30 VDC				
Current consumption	< 40mA		< 30mA		
# Switching outputs	2				
Voltage drop	< 2.5 V (switching outputs)				
Response time	1ms				
Switching frequency	500Hz				
Short-circuit protection	Yes				
Operating temperature	-40 to 60°C [-40 to 140°F]		-40 to 50°C [-40 to 122°F]		
Protection degree (DIN 40050)	IP68		IP67		
LED indicators - switching status	Yellow				
LED indicators - power	Green				
Housing material	Polycarbonate				
Lens material	PMMA (Polymethyl methacrylate)				
Shock/vibration	Tested according to EN 60068-2-6 / EN 60068-2-27				
Tightening torque	0.5 N·m (mounting screws)				
Weight (cable/connector)	8g [0.28 oz]	22g [0.78 oz]	16g [0.56 oz]	48g [1.69 oz]	82g [2.89 oz]
Connectors	5-pin M12		4-pin M12	4-pin M12 pigtail	4-pin M8 pigtail
IO Link	IO-Link v1.1				
Agency approvals	CE, cULUS, E189727, RoHs				

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

Connectors


4-Pin M8 connector



4-Pin M12 connector




5-Pin M12 connector




OPT Series Transit Time Photoelectric Sensors

Characteristic Curves

OPT2010



**OPT2016, OPT2017
OPT2018, OPT2019**



Sr = Switching Distance

dSr = Switching Distance Change

— black 6 % remission

— blue 18 % remission

— Brushed aluminum

X	Distance to target [mm]
Y	Minimum distance between object and background [mm]

Typical curves based on Kodak white (90% remission)

Accessories for OPT Series 32x12mm Photoelectric Sensors

Right-Angle Mounting Brackets

Mounting bracket, right angle, vertical adjustment. For use with OPT series 32x12mm photoelectric sensors.

Mounting Brackets for OPT 32x12mm Sensors						
Part Number	Price	Description	Qty	Drawing Link	Weight lb [g]	
OPT2033	\$7.00	Wenglor mounting bracket, right-angle, vertical adjustment, nickel plated steel. For use with OPT series 32x12mm photoelectric sensors.	1	PDF	0.04 [16]	



[OPT2033](#)

Right-angle Swivel Mounting Systems

Mounting bracket, right-angle swivel, 360 degree vertical and horizontal adjustment, aluminum, 12mm rod mount. For use with OPT series 32x12mm photoelectric sensors.

Accessories for 32x12mm Sensors						
Part Number	Price	Description	Mounting Head	Mounting Plate	Drawing Link	Weight lb [g]
OPT2120	\$11.50	Wenglor mounting bracket, right-angle swivel, 360 degree vertical and horizontal adjustment, aluminum, 12mm rod mount. For use with OPT series 32x12mm photoelectric sensors.	Aluminum	304 Stainless Steel	PDF	0.14 [63.50]
OPT2121	\$21.00	Wenglor mounting bracket, right-angle swivel, 360 degree vertical and horizontal adjustment, 304 stainless steel, 12mm rod mount. For use with OPT series 32x12mm photoelectric sensors.	304 Stainless Steel	304 Stainless Steel	PDF	0.27 [122.46]



[OPT2121](#)



[OPT2120](#)

Note: 304 Stainless steel mounting rods sold separately: [OPT2109](#) (200mm length), [OPT2110](#) (300mm length), and [OPT2111](#) (500mm length).

Accessories for OPT2012 - OPT2015 Photoelectric Sensors

Right-angle Mounting Brackets

Mounting bracket, right angle, steel and nickel plated. For use with [OPT2012](#)-[OPT2015](#) photoelectric sensors.

Accessories for OPT2012-OPT2015 Photoelectric Sensors				
Part Number	Price	Description	Drawing Link	Weight lb (g)
OPT2032	\$7.00	Wenglor mounting bracket, right-angle, nickel plated brass. For use with OPT2012 - OPT2015 photoelectric sensors.	PDF	0.36 [163.29]



[OPT2032](#)

Right-angle Swivel Mounting Systems

Mounting bracket, right-angle swivel, 360 degree vertical and horizontal adjustment, 12mm rod mount. For use with [OPT2012](#)-[OPT2015](#) photoelectric sensors. Available in all stainless steel or with an aluminum head with a stainless steel mounting plate.

Accessories for OPT2012-OPT2015 Photoelectric Sensors						
Part Number	Price	Description	Mounting Head	Mounting Plate	Drawing Link	Weight lb [g]
OPT2126	\$11.50	Wenglor mounting bracket, right-angle swivel, 360 degree vertical and horizontal adjustment, aluminum, 12mm rod mount. For use with OPT2012 - OPT2015 photoelectric sensors.	Aluminum	304 Stainless Steel	PDF	0.23 [104.32]
OPT2127	\$21.00	Wenglor mounting bracket, right-angle swivel, 360 degree vertical and horizontal adjustment, 304 stainless steel, 12mm rod mount. For use with OPT2012 - OPT2015 photoelectric sensors.	304 Stainless Steel	304 Stainless Steel	PDF	0.36 [163.29]



[OPT2126](#)

[OPT2127](#)

Note: 304 Stainless steel mounting rods sold separately: [OPT2109](#) (200mm length), [OPT2110](#) (300mm length), and [OPT2111](#) (500mm length).

Mounting Rods and Brackets

Mounting Rods

304 Stainless steel rods for mounting swivel brackets [OPT2112](#) - [OPT2127](#). Available in three lengths: 200mm, 300mm, and 500mm. 12mm diameter.

Mounting Rods for OPT2112-2127 Swivel Mounting Brackets				
Part Number	Price	Description	Drawing Link	Weight lb (g)
OPT2109	\$13.00	Wenglor mounting rod, 12mm diameter, 200mm length, 304 stainless steel.	PDF	0.41 [185.97]
OPT2110	\$16.00	Wenglor mounting rod, 12mm diameter, 300mm length, 304 stainless steel.	PDF	0.60 [272.16]
OPT2111	\$21.00	Wenglor mounting rod, 12mm diameter, 500mm length, 304 stainless steel.	PDF	0.98 [444.52]



Right-angle Mounting Bracket

Mounting bracket, right-angle, nickel-plated brass. For use with 12mm mounting rods [OPT2109](#), [OPT2110](#) & [OPT2111](#).

Right-angle Mounting Brackets for 12mm Sensors				
Part Number	Price	Description	Drawing Link	Weight lb [g]
OPT2108	\$16.00	Wenglor mounting bracket, right-angle, nickel plated brass. For use with 12mm mounting rods OPT2109 , OPT2110 & OPT2111 .	PDF	0.07 [31.8]



Reflectors


Reflectors for Photoelectric Laser Sensors

Reflectors for OPT Series Photoelectric Sensors				
Part Number	Price	Description	Drawing Link	Weight lb [g]
OPT2030	\$14.00	Reflector, square, 100 x 100mm. For use with photoelectric laser sensors.	PDF	0.20 [90.71]
OPT2167	\$13.50	Wenglor reflector, rectangular, 61 x 51.5mm. For use with OPT2137 & OPT2138.	PDF	0.03 [13.60]

Note: [OPT2015](#) requires purchase of [OPT2030](#) reflector. <50m sensing distance requires 1 reflector. 50–100 m sensing distance requires 4 reflectors.



[OPT2167](#)



[OPT2030](#)