

# NEMA 4, 12, and 13 Extra-Large Wall-Mount Pushbutton



## Applications

Designed to offer protection for oil-tight pushbuttons, switches, and pilot lights from dust, water, dirt and oil.

## Construction

- 16 gauge carbon steel.
- Continuously-welded seams.
- Captivated cover screws thread into sealed wells.
- 4-way pushbutton holes accept all brands of oil-tight pushbuttons, switches and pilot lights.
- Hole diameter is 1.20in [30.5 mm] or 0.87in [22.5 mm].
- Poured-in-place oil- and water-resistant gasket.
- Provisions for subpanel.
- Ground stud on door and body.
- Bolt-on continuous hinge with stainless steel hinge pin.
- Welded mounting provision top and bottom of back.

## Finish

- ANSI 61 gray powder coated inside and out.
- Optional subpanels powder coated white

## Listings

- NEMA Type 4, 12, and 13
- cULus Listed Type 4 and 12 [File E69392]
- IEC 60529 IP66



Shipping Schedule	
Same day	1 - 15 days
Color indicates shipping lead time in business days.	



NEMA 4, 12, and 13 Extra-Large Wall-Mount Pushbutton							
22mm	30mm	Price	Size HxWxD	Holes	Drawing Link	Optional Subpanel	Price
<b>SCE-4SPBHI</b>	<b>SCE-4SPBH</b>	\$107.00	8.38 x 8.31 x 6.20 [213 x 211 x 157]	4	PDF	<b>SCE-8P8</b>	\$5.00
<b>SCE-6PBHI</b>	<b>SCE-6PBH</b>	\$123.00	10.38 x 8.31 x 6.20 [264 x 211 x 157]	6	PDF	<b>SCE-10P8</b>	\$6.00
<b>SCE-9PBHI</b>	<b>SCE-9PBH</b>	\$143.00	10.38 x 10.31 x 6.20 [264 x 262 x 157]	9	PDF	<b>SCE-10P10</b>	\$7.00
<b>SCE-12PBHI</b>	<b>SCE-12PBH</b>	\$162.00	12.38 x 10.31 x 6.20 [314 x 262 x 157]	12	PDF	<b>SCE-12P10</b>	\$8.00
<b>SCE-16PBHI</b>	<b>SCE-16PBH</b>	\$185.00	12.38 x 12.31 x 6.20 [314 x 313 x 157]	16	PDF	<b>SCE-12P12</b>	\$9.00

*Note: Dimensions in inches [millimeters]*


# NEMA 4, 12, and 13 Extra-Large Wall-Mount Pushbutton




## Dimensions




4S




6



9



12



16