

# Dold UG6970 Series Safety Relay 2 with Independent Selectable Function



Designed to protect people and machines in applications with various safety devices.

• 2 independent, separately adjustable safety functions: (power off before selecting the desired function):

- E-Stop
- Safety gate
- Two-hand control
- Safety mat / Safety edge
- Exclusive XOR contacts
- Light curtain

• Only one device, two safety functions at the same time

- Acc. to EN 50156-1 for furnaces
- Line fault detection on Pushbutton:
- Manual restart or automatic restart
- With or without cross fault monitoring
- 2-channel
- Forcibly guided output contacts
- Output: 2 N.O. contacts per safety function
- 1 semiconductor output per safety function
- LED indicator for operation, safety function 1, 2 and failure
- Pluggable terminal blocks for easy exchange of devices
- Width: 22.5 mm
- Two PNP sensor inputs only


Safety Data – Values per EN ISO 13849-1	
Category	4
Performance level	PLe
MTTF <sub>d</sub>	134.5 years
DC <sub>avg</sub>	99%
Safety Data – Values per IEC/EN 62061 / IEC/EN 61508	
SIL CL	3
SIL	3
HFT (Hardware Failure Tolerance)	1
DC <sub>avg</sub>	99%
SFF	99.6%
PFH <sub>D</sub>	3.89E-10 h <sup>-1</sup>

According to:


- Performance Level (PL) e and category 4 to EN ISO 13849-1: 2008
- SIL Claimed Level (SIL CL) 3 to IEC/EN 62061
- Safety Integrity Level (SIL) 3 to IEC/EN 61508 and IEC/EN 61511

Safety Relays Selection Chart				
Part Number	Price	Marking Type	Voltage	Outputs
UG6970-04PS-61-24	\$240.00	Safety relay module	24VDC	4 N.O. positive guided safety contact(s); 2 N.O. monitoring contact(s)


## Function Diagram



## Block Diagram



## Dimensions mm(in)



SEE OUR WEBSITE: [WWW.AUTOMATIONDIRECT.COM](http://WWW.AUTOMATIONDIRECT.COM) FOR COMPLETE ENGINEERING DRAWINGS.


# Dold UG6970 Series Safety Relay 2 with Independent Selectable Function

Dold UG6970 Series Safety Relay 2 with Independent Selectable Function Specification Table	
<b>General Specifications</b>	
<b>Temperature</b>	Storage: -25°C to 85°C (-13°F to 185°F) Operating: -15°C to 55°C (5°F to 131°F)
<b>Altitude</b>	<2,000 meters
<b>Vibration Resistance</b>	Amplitude: 0.35mm, Frequency: 10 to 55 Hz (IEC/EN 60-068-2-6)
<b>Degree of Protection</b>	Per IEC/EN 60 529. Housing: IP40; Terminals IP20
<b>Housing</b>	UL 94V-0 Thermoplastic; DIN mount 35 mm x 7.5 mm
<b>Weight</b>	275g (9.7 oz.)
<b>Terminal Designation per EN 60 000 Wire Connections</b>	1x4 mm <sup>2</sup> solid or 1 x 2.5 mm <sup>2</sup> stranded ferruled (isolated) or 2 x 1.5 mm <sup>2</sup> stranded ferruled (isolated) DIN 46 228-1/-2/-3/-4 or 2 x 2.5 mm <sup>2</sup> solid DIN 46 228-1/-2/-3/-4
<b>Wire Fixing</b>	Terminal screws M3.5 box terminals with wire protection.
<b>Wire Connection</b>	60degC/75degC Copper conductors only; AWG20-12 Sol/Str Torque 0.5NM
<b>Input Specifications</b>	
<b>Nominal Voltage</b>	24VDC
<b>Voltage Range</b>	At 10% residual ripple: DC: 0.8 to 1.1 U <sub>N</sub>
<b>Maximum Consumption</b>	DC approx. 3.2W
<b>Nominal Frequency</b>	Not applicable
<b>Minimum Off-time</b>	250 ms
<b>Control Voltage on S11 At U<sub>N</sub></b>	20VDC
<b>Control Current Typ. Over S12, S22</b>	8 mA at U <sub>N</sub>
<b>Min. Voltage on S12, S22 (relay activated)</b>	10VDC
<b>Short Circuit Protection</b>	Internal with PTC (Positive Temperature Coefficient resistor)
<b>Overvoltage Protection</b>	Internal VDR (Voltage Dependent Resistor)
<b>Output Specifications</b>	
<b>Electrical Contact Life</b>	AC 15 at 5A, 230VAC: > 1.5x10 <sup>6</sup> switching cycles
<b>Mechanical Life</b>	> 10x10 <sup>6</sup> switching cycles
<b>Contact Type</b>	Independent N.O. positive-guided safety contacts (2 per safety function)
<b>Operate Delay</b>	Manual start: 30 ms; automatic start: 350 ms.
<b>Release Delay</b>	E-Stop (1) (6), Safety gate (2) (7), Exclusive or contacts (5): Start up at U : < 65 ms Release delay at U and disconnecting the supply: < 40 ms Release delay at U and disconnecting S12,S22: < 60 ms  Two-hand control (3) Start up at U : < 110 ms Release delay at U and disconnecting the supply: < 40 ms Release delay at U and disconnecting S12,S22: < 60 ms simultaneity demand: max. 0,5 s  Safety mat (4) Start up at U : < 85 ms Release delay at U and disconnecting the supply: < 40 ms Release delay at U and disconnecting S12,S22: < 60 ms  Light curtains (8) Start up at U : < 35 ms Release delay at U and disconnecting the supply: < 40 ms Release delay at U and disconnecting S12,S22: < 25 ms
<b>Nominal Output Voltage</b>	AC: 24VDC; See continuous current limit curve in installation manual.
<b>Thermal Current (I<sub>th</sub>)</b>	Max. 8A. See quadratic total current limit curve in installation manual.
<b>Short Circuit Strength</b>	Max. fuse rating: 6A gL (IEC/EN 60 947-5-1); Line circuit breaker: B 6A
<b>Switching Capacity (IEC/EN 60 947-5-1)</b>	AC 15: N.O. contacts: 3A/230V DC 13: N.O. contacts: 2A/DC24V
<b>Switching Frequency</b>	Safety function 1: Max. 1800 switching cycles/hr Safety function 1: Max. 360 switching cycles/hr
<b>Agency Approvals and Standards</b>	CSA, cULus file E107778, CE, RoHS, TUV


To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page at [www.automationdirect.com](http://www.automationdirect.com)

# Dold UG6970 Series Safety Relay 2 with Independent Selectable Function

## Application Examples



Operating mode:3 Fkt1=AUTO ; Fkt2=MANUAL




Operating mode: 5 (MANUAL with common button)


**Note:** See page tESC-221 for Safety Function example drawings.

# Dold UG6970 Series Safety Relay 2 with Independent Selectable Function


## Safety Functions




Fct.: E-stop (1),  
with cross fault detection  
SIL 3, PL e, Cat. 4




Fct.: Safety gate (2),  
with cross fault detection  
SIL 3, PL e, Cat. 4




Fct.: Two-hand control (3),  
with cross fault detection  
SIL 3, PL e, Cat. 4  
Type III C to EN 574




Fct.: Safety mat / Safety edge (4),  
with cross fault detection  
SIL 3, PL e, Cat. 4




Fct.: Exclusive XOR contacts (5),  
with cross fault detection  
SIL 3, PL e, Cat. 4



Fct.: E-Stop (6),  
without cross fault detection  
SIL 3, PL e, Cat. 4<sup>1)</sup>




Fct.: Safety gate (7),  
without cross fault detection  
SIL 3, PL e, Cat. 4<sup>1)</sup>



Fct.: Light curtain (8),  
without cross fault detection  
SIL 3, PL e, Cat. 4<sup>2)</sup>

<sup>1)</sup>To achieve the stated safety classification the wiring has to be done with crossfault monitoring.  
<sup>2)</sup>To achieve the stated safety classification light curtains with selftest (type 4) according to IEC/EN 61496-1 have to be used.




\*UG6970: The safety function 2 is connected as well as safety function 1, but  
S11' = S31, S12' = S32, S21 = S41, S22 = S42 and ST1 = ST2

# Dold UG6970 Series Safety Relay 2 with Independent Selectable Function

## Connection Terminals

Terminal designation	Signal designation
A1 +	DC 24 V
A2	0 V
13, 14, 23, 24, 43, 44, 53, 54	Forcibly guided NO contacts for release circuit
38, 68	Semiconductor monitoring output
GND	Reference potential for Semiconductor monitoring output
S11, S21, S31, S41	control output
S12, S22, S32, S42, ST1, ST2, RES	control input

## Characteristic Curves




— device free-standing  
max. current at 55°C over  
4 contact path =  $5A \triangleq 4 \times 5^2 A^2 = 100A^2$

- - - device mounted without distance heated by  
devices with same load,  
max. current at 55°C over  
4 contact path =  $1A \triangleq 4 \times 1^2 A^2 = 4A^2$

$$\sum I^2 = I_1^2 + I_2^2 + I_3^2 + I_4^2$$

$I_1, I_2, I_3$  - current in contact paths

Quadratic total current limit curve output contacts



$$\sum I = I_{38} + I_{68}$$

z.B. :  $\sum I = 35mA + 15mA = 50mA$

$I_{38}$  - current semiconductor output 38

$I_{68}$  - current semiconductor output 68

Quadratic total current limit curve semiconductor monitoring outputs

## Function Setting

Fkt. 1/Fkt. 2	Safety Function	
1	E-Stop	cross fault detection
2	Safety Gate	
3	Two-hand Control	
4	Safety mat / safety edge	
5	Exclusive XOR contacts	
6	E-stop	without cross fault deflection
7	Safety gate	
8	Light curtain	

# Safety Products



***Warning: Safety products sold by AutomationDirect are Safety components only. The purchaser/installer is solely responsible for the application of these components and ensuring all necessary steps have been taken to assure each application and use meets all performance and applicable safety requirements and/or local, national and/or international safety codes as required by the application. AutomationDirect cannot certify that our products, used solely or in conjunction with other AutomationDirect or other vendors' products, will assure safety for any application. Any person using or applying any products sold by AutomationDirect is responsible for learning the safety requirements for their individual application and applying them, and therefore assumes all risks, and accepts full and complete responsibility, for the selection and suitability of the product for their respective application. AutomationDirect does not provide design or consulting services, and cannot advise whether any specific application or use of our products would ensure compliance with the safety requirements for any application.***