




Adhesive Mounts

Self-Adhesive Clips

Sapiselco's Adhesive Cord Clips offer a quick and convenient way to route and manage cables without the need for tools or additional fasteners. These clips are made from Nylon 6.6 and feature a square base with a reliable self-adhesive backing. Their hook-shaped head allows for easy installation and removal of one or more cables ensuring cable insulation remains undamaged while providing an organized and flexible cable management solution. They are recommended for application on smooth, grease-free surfaces.



GAN.3MT.401



Features

- UL 94 V-2 rated Nylon 6.6
- Rounded edges to avoid cable damage
- Min Install Temp: 50°F [10°C]

Cable Clip Mounts						
Part Number	Pcs/Bag	Price	Color	Fits	Size	Operating Temperature
GAN.3MT.401	100	\$13.50	Black	0.20in maximum cable diameter	0.75 x 0.39in [19 x 10mm]	-15 to 50°C [5 to 122°F]
GAN.3MT.402	100	\$17.50	Black	0.39in maximum cable diameter	1.02 x 0.51in [26 x 13mm]	-15 to 60°C [5 to 140°F]
GAN.3MT.403	100	\$21.50	Black	0.59in maximum cable diameter	1.02 x 0.71in [26 x 18mm]	-15 to 60°C [5 to 140°F]

Self-Adhesive Bi-Directional Mounts

Sapiselco's BAS series single and double square base with self-adhesive offers a convenient and secure mounting solution for cable ties. These bases, made from Nylon 6.6 feature a screw mounting hole and a self-adhesive backing for quick application onto smooth, clean surfaces. Available in both single and double square configurations, each base includes bi-directional openings to accommodate cable ties (up to 4.5mm wide), providing a flexible and efficient method for organizing and securing cable bundles in various applications.




BAS.3MT.507



BAS.3MT.510

Features

- UL 94 V2 rated Nylon 6.6
- 2-way cable tie openings
- Rounded edges to avoid cable damage
- Operating Temp: 5 to 122°F [-15 to 50°C]
- Min Install Temp: 50°F [10°C]



Square Bi-directional Nylon Square Bases								
Part Number	Pcs/Bag	Price	Color	Dual Adhesive	Fits	Dimensions		Fastener Hole Diameter
						A	B	
BAS.2MT.507	100	\$7.50	Natural	Yes	0.16in maximum width cable ties	18.8 mm [0.74 in]	4.4 mm [0.17 in]	0.19in [4.5mm]
BAS.3MT.507	100	\$7.50	Black					
BAS.2MT.508	100	\$10.00	Natural	Yes	0.18in maximum width cable ties	26.5 mm [1.04 in]	5.9 mm [0.23 in]	0.19in [4.5mm]
BAS.3MT.508	100	\$10.00	Black					


Double Square Bi-directional Nylon Square Bases								
Part Number	Pcs/Bag	Price	Color	Dual Adhesive	Fits	Dimensions		Fastener Hole Diameter
						A	B	
BAS.2MT.510	100	\$23.00	Natural	Yes	0.18in maximum width cable ties	18.8 mm [0.74 in]	4.4 mm [0.17 in]	0.19in [4.5mm]
BAS.3MT.510	100	\$23.00	Black					
BAS.2MT.511	100	\$21.50	Natural	Yes	0.16in maximum width cable ties	26.5 mm [1.04 in]	5.9 mm [0.23 in]	0.19in [4.5mm]
BAS.3MT.511	100	\$21.50	Black					



Cable Tie Tools

Cable Tie Cutting Tool

The special angle of this cutter's tips enables clean cuts of the ties to sizes between 2.5 and 12.5 mm in width, maintaining the wired electric cables intact. The cutter can also be used for cutting cables.

	
<u>PIN.009</u>	\$16.00

Collar Fastening Metal Plier

This tool makes it easier to tighten and cut collars. Use with Double-headed Cable Ties. Leaves a short length of tail close to the head. For use with up to 9mm wide cable ties.

	
<u>PIN.005</u>	\$14.50

Cable Tie Gun Installation Tool

For use with cable ties up to 5mm wide. This tool helps to adjust the preload and cut the tie. Tightening torque of 2.5 kg to 12kg.

	
<u>PIN.003</u>	\$21.00



Cable Ties Family Overview

General Purpose Nylon Cable Ties



SapiSelco general purpose Nylon 6.6 cable ties are slotted and held in place by the resistance of the elastic tooth against the rack. These cable ties are resistant to solvents and reagents, oil, gasoline, and hydrocarbons when used at low temperatures, in low concentrations, and for short periods of time. Assortment Kit available.



These ties are low-cost, releasable, and reusable cable ties, suitable for lightweight loads. The double-locking head enables securing two cable bundles with one tie. The body is completely rounded to eliminate all sharp edges guaranteeing reliable performance every time.

These ties are low-cost, releasable, and reusable cable ties, suitable for lightweight loads.

Colored Nylon Cable Ties



SapiSelco colored Nylon 6.6 cable ties are useful in applications that require distinct identifiers. These ties are colored with inorganic dyes and are resistant to solvents and reagents, oil, gasoline, and hydrocarbons when used at low temperatures, in low concentrations, and for short periods of time. Assortment Kit available.

Specialty Cable Ties



Nylon Releasable Tab



Screw Mount



Low Temp



Nylon Lashing Cable Tie



Identification Ties



Double-headed [Collars]

Stainless Steel Tooth Ties



SapiSelco stainless steel tooth ties are forged from nylon and hardened stainless steel with added Molybdenum. This ensures extremely high mechanical strength and optimal resistance to corrosion. A single central raised section makes this tie particularly flexible, while guaranteeing maximum strength at the same time.

UV Resistant Cable Ties



Exposure to sun and ultraviolet rays causes deterioration in nylon. SapiSelco specialty Nylon UV Resistant cable ties can resist and endure the harsh conditions of outdoor applications for up to 10 years. These ties can withstand temperatures up to 125°C [257°F].

Tools and Accessories



Cable Tie Cutting Tool



Collar Fastening Metal Plier

Metal Detector Readable Cable Ties



These ties are fabricated with a special composite of 6.6 polyamide and metal powder and are sensitive to electromagnetic fields. They are recommended in the food, pharmaceutical and chemical industry. They are useful in applications where, for safety reasons, it is necessary for a metal detector to be able to detect even very small fragments of these ties that may be mixed in with products.



Cable Tie Gun Installation Tool



Bi-directional Nylon Square Bases