

# AM Series Analog Inductive Proximity Sensors



## M12 (12 mm) metal – analog output

- Voltage or current analog output
- 4 models available
- Metal housing
- Axial cable or M12 quick-disconnect models
- IP67 rated
- Purchase cable separately (for quick-disconnect model)
- Lifetime warranty




**AM Series M12 Analog Inductive Prox Selection Chart**

Part Number	Price	Sensing Range	Housing	Output	Connection	Dimensions
AM9-05-1A	\$89.00	0 to 6 mm (0-0.24 in)	Shielded	0 - 5 VDC or 1-5 mA	2 m (6.5) axial cable	Figure 1
AM9-05-1H	\$89.00				M12 (12 mm) connector	Figure 2
AM9-10-1A	\$89.00	0 to 6 mm (0-0.24 in)		0-10 VDC or 4-20 mA	2 m (6.5) axial cable	Figure 1
AM9-10-1H	\$89.00				M12 (12 mm) connector	Figure 2

### Specifications

Mounting Type	AM9-05-1*	AM9-10-1*
		Shielded
Nominal Sensing Distance	0 to 6 mm (0-0.24 in)	0 to 6 mm (0-0.24 in)
Operating Distance	NA	
Material Correction Factors	See the <a href="#">Material influence table</a>	
Output Type	0-5 VDC or 1-5 mA	0-10 VDC or 4-20 mA
Current Output Max. Load / Power Supply	1 kΩ / 10 VDC; 5 kΩ / 30 VDC	0.5 kΩ / 15 VDC; 1 kΩ / 30 VDC
Voltage Output Min. Load	500 Ω	1 kΩ
Operating Voltage	10 -30 VDC	15 -30 VDC
No-load Supply Current	≤10 mA	≤12 mA
Operating (Load) Current	1 kΩ	0.5 kΩ
Off-state (Leakage) Current	NA	
Voltage Drop	≤2.0 V	
Switching Frequency	NA	
Differential Travel (# of Nominal Distance)	NA	
Repeat Accuracy	±0.01 mm	
Ripple	≤20%	
Response Time	1 ms	
Time Delay Before Availability (tv)	≤50 ms	
Reverse Polarity Protection	Yes	
Short-Circuit Protection	Yes (switch auto-resets after overload is removed)	
Operating Temperature	-25° to +70° C (-13° to 158° F)	
Protection Degree (DIN 40050)	IEC IP67	
Indication/Switch Status	NA	
Housing Material	Chrome-plated brass	
Sensing Face Material	Polybutylene Terephthalate (PBT)	
Shock / Vibration	See <a href="#">Proximity Sensor Terminology</a>	
Tightening Torque	10 Nm (7.37 lb-ft)	
Weight (cable/M8 connector)	95 g (3.35 oz.) / 33 g (1.16 oz.)	
Connection	2 m (6.5) axial cable or M12 (12 mm) connector	
Agency Approvals	UL file E328811	

### Wiring diagram



### Connector


M12 connector




### Dimensions

mm [inches]

**Figure 1**



**Figure 2**



# Accessories for 12mm Sensors

## Axial Mounting Bracket

Mounting bracket, axial, zinc-plated steel. For use with 12mm sensors. Has two mounting holes (use 3mm screws) and allows the rotation of an optical axis for right-angle adapter sensors. Hexagonal nuts not included.


Accessories for 12mm Sensors			
Part Number	Price	Description	Weight (lb)
ST12A	\$2.00	Mounting bracket, axial, zinc-plated steel. For use with 12mm sensors. 1/pk.	0.03
ST12A7W	\$6.00	Mounting bracket, axial, 316L stainless steel. For use with 12mm sensors. 1/pk.	0.03



ST12A

### Dimensions

mm [inches]



## Right-angle Mounting Bracket

Mounting bracket, right-angle, zinc-plated steel or 316L stainless steel. For use with 12mm sensors. Has two mounting holes (use 3mm screws) and allows the rotation of an optical axis for axial sensors. Hexagonal screws not included.


Accessories for 12mm Sensors			
Part Number	Price	Description	Weight (lb)
ST12C	\$2.00	Mounting bracket, right angle, zinc-plated steel. For use with 12mm sensors. 1/pk.	0.03
ST12C7W	\$6.00	Mounting bracket, right angle, 316L stainless steel. For use with 12mm sensors. 1/pk.	0.03



ST12C

### Dimensions

mm [inches]



See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings

# Accessories for 12mm Sensors

## Right-angle Mounting Brackets

Mounting bracket, right-angle, fixed insertion stop adjustment, plastic. For use with 12mm sensors. Available with or without fixed insertion stop.


Accessories for 12mm Sensors					
Part Number	Price	Description	Weight [lb]		
<b>OPT2102</b>	\$6.00	Mounting bracket, right-angle, fixed insertion stop adjustment, plastic. For use with 12mm sensors.	0.05		
<b>OPT2103</b>	\$6.00	Mounting bracket, right-angle, plastic. For use with 12mm sensors.	0.05		



**OPT2102, OPT2103**

## Dimensions

mm [inches]



## Right-angle Swivel Mounting Systems

Mounting bracket, right-angle swivel, 360 degree vertical and horizontal adjustment, 12mm rod mount. For use with 12mm sensors. Available in all stainless steel or with an aluminum head and stainless steel mounting plate.

Accessories for 12mm Sensors					
Part Number	Price	Description	Mounting Head	Mounting Plate	Weight [lb]
<b>OPT2114</b>	\$9.00	Mounting bracket, right-angle swivel, 360 vertical and horizontal adjustment, aluminum, 12mm rod mount. For use with 12mm sensors.	Aluminum	Stainless Steel	0.14
<b>OPT2115</b>	\$16.00	Mounting bracket, right-angle swivel, 360 vertical and horizontal adjustment, 304 stainless steel, 12mm rod mount. For use with 12mm sensors.	304 Stainless Steel	304 Stainless Steel	0.27


**Note: 304 Stainless steel mounting rods sold separately: OPT2109 (200mm length), OPT2110 (300mm length), and OPT2111 (500mm length).**



**OPT2114, OPT2115**

## Dimensions

mm [inches]



See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings

# Mounting Rods

## Mounting Rods

304 Stainless steel rods for mounting swivel brackets OPT2112 - OPT2127. Available in three lengths: 200mm, 300mm, and 500mm. 12mm diameter.


Mounting Rods for OPT2112-2127 Swivel Mounting Brackets			
Part Number	Price	Description	Weight [lb]
<b>OPT2109</b>	\$10.00	Mounting rod, 12mm diameter, 200mm length, 304 stainless steel.	0.41
<b>OPT2110</b>	\$12.00	Mounting rod, 12mm diameter, 300mm length, 304 stainless steel.	0.60
<b>OPT2111</b>	\$16.00	Mounting rod, 12mm diameter, 500mm length, 304 stainless steel.	0.98



**OPT2109, OPT2110, OPT2111**

## Dimensions


mm [inches]



## Right-angle Mounting Bracket

Mounting bracket, right-angle, nickel-plated brass. For use with 12mm mounting rods OPT2109, OPT2110 & OPT2111.


Accessories for 12mm Sensors			
Part Number	Price	Description	Weight [lb]
<b>OPT2108</b>	\$12.00	Mounting bracket, right-angle, nickel-plated brass. For use with 12mm mounting rods OPT2109, OPT2110 & OPT2111.	0.07



**OPT2108**

## Dimensions

mm [inches]



See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings