

# DW Series 20mm x 32mm Stainless Steel Proximity Sensors

## Miniature 20mm x 32mm stainless steel – DC



- Eight models available
- Miniature 20mm x 32mm proximity sensor
- Complete overload protection
- IP68/IP69K-rated
- Stainless steel construction
- One-piece for harsh duty applications
- LED status indicator
- Lifetime warranty
- IO-Link models available



**DW Series 20mm x 32mm Inductive Prox Selection Chart**

Part Number	Price	Size	Sensing Range	Housing	Output State	Logic	Connection	Wiring	Dimensions
<b>Extended Distance</b>									
<b>DW-AD-701-C23</b>	\$79.00	20mm x 32mm x 8mm	7mm (0.276 in)	Shielded	NO	NPN	2m (6.5 ft) axial cable	Diagram 1	Figure 1
<b>DW-AD-703-C23*</b>	\$79.00					PNP		Diagram 2	Figure 1
<b>DW-AV-701-C23-276</b>	\$79.00					NPN	M8 with 0.2 m cable	Diagram 3	Figure 2
<b>DW-AV-703-C23-276*</b>	\$79.00					PNP		Diagram 4	Figure 2
<b>DW-AD-702-C23</b>	\$79.00				NC	2m (6.5 ft) axial cable	NPN	Diagram 1	Figure 1
<b>DW-AD-704-C23</b>	\$79.00						PNP	Diagram 2	Figure 1
<b>DW-AV-702-C23-276</b>	\$79.00					M8 with 0.2 m cable	NPN	Diagram 3	Figure 2
<b>DW-AV-704-C23-276</b>	\$79.00						PNP	Diagram 4	Figure 2

\* IO-Link model


# DW Series 20mm x 32mm Stainless Steel Proximity Sensors

DW Series 20mm x 32 mm Specifications	
	<b>DW-Ax-70x-C23</b>
<b>Mounting Type</b>	Shielded
<b>Nominal Sensing Distance</b>	7mm (0.276 in)
<b>Operating Distance</b>	-
<b>Material Correction Factors</b>	See the <a href="#">Material influence table</a>
<b>Output Type</b>	NPN or PNP, N.O., N.C.
<b>Operating Voltage</b>	10 to 30 VDC
<b>No-load Supply Current</b>	≤ 10mA
<b>Operating (Load) Current</b>	≤ 200mA
<b>Off-state (Leakage) Current</b>	≤ 0.1 mA
<b>Voltage Drop</b>	≤ 2 V
<b>Switching Frequency</b>	≤ 180 Hz
<b>Differential Travel (% of Nominal Distance)</b>	≤ 10%
<b>Repeat Accuracy</b>	0.3 mm
<b>Ripple</b>	≤ 20%
<b>Time Delay Before Availability (tv)</b>	≤ 20ms
<b>Reverse Polarity Protection</b>	Yes
<b>Short-Circuit Protection</b>	Yes
<b>Operating Temperature</b>	-25 to 85°C (-13 to 185°F)
<b>Protection Degree (DIN 40050)</b>	IP 68 & IP69K
<b>Indication/Switch Status</b>	Yellow LED (LED on continuously - secured operating zone)
<b>Housing Material</b>	Stainless steel V4A
<b>Sensing Face Material</b>	Stainless steel V4A
<b>Shock/Vibration</b>	IEC 60947-5-2/7.4
<b>Tightening Torque</b>	--
<b>Weight</b>	47g (1.66 oz) with cable, 25g (0.88 oz) without cable
<b>Connection</b>	2m cable (PVC [polyvinyl chloride] 3 x 0.14mm <sup>2</sup> ≈ 26 AWG) or 0.2 m cable (PVC [polyvinyl chloride]) with M8 connection
<b>Minimum Mounting Distance (center to center)</b>	60.0 mm (2.36 in)
<b>IO-Link</b>	PNP NO version only
<b>Agency Approvals</b>	CE, cULus E239373


Note: To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

## Wiring diagrams

**Diagram 1**




**Diagram 2**




**Connectors**



**Diagram 3**



**Diagram 4**



# DW Series 20mm x 32mm Stainless Steel Proximity Sensors

## Dimensions

mm [inches]

Figure 1





Figure 2



See our website [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings.