



# Specialty Head Cable Ties

## Screw Mount Cable Tie

Sapiselco's OCH screw mount cable tie provides a specialized and highly secure mounting solution, particularly for applications requiring fixed-point attachment to panels or structures. This tie integrates a standard self-locking cable tie with a pre-formed screw hole opening at the head. This unique design allows the tie to be easily secured onto a screw, rivet, stud, or pre-existing button-style fastener, providing a robust and permanent mounting point for cable bundles. Manufactured from durable Nylon 6.6, the OCH series ensures reliable bundling and a secure attachment, making this tie ideal for applications in automotive, electronics, and appliance manufacturing where cables need to be precisely routed and anchored.

### Features

- UL 94: V-2 rated Nylon 6.6
- Suitable for indoor applications
- Rounded edges to avoid cable damage
- Operating temperature: -5 to 85°C [23 to 185°F]

### Agency Approvals

- CE



Screw Mount Cable Tie															
Part Number	Pcs/Bag	Price	Color	Length		Width		Mounting Head Hole Ø		Min. Bundle Ø		Max. Bundle Ø		Tensile Strength	
				mm	in	mm	in	mm	in	mm	in	mm	in	kg	lb
<b>OCH.2.2123</b>	100	\$3.50	Natural	200	7.87	4.5	0.18	5	0.20	3	0.12	51	2.01	22	48.51

## Identification Cable Ties

Sapiselco's identification cable ties offer a practical and efficient solution for organizing and clearly labeling cable bundles and components. These ties integrate a standard self-locking cable tie with an integrated flag or tag area at the head, providing a convenient surface for writing, printing, or attaching labels. Made from durable Nylon 6.6, they ensure reliable bundling while simultaneously offering a clear method for quick visual identification of wires, networks, or equipment. This feature is particularly valuable in complex installations, electrical panels, or data centers where precise and easy identification is crucial for maintenance, troubleshooting, and overall system management.

### Features

- UL 94: V-2 rated Nylon 6.6
- Suitable for indoor applications
- Rounded edges to avoid cable damage
- Operating temperature: -15 to 60°C [5 to 140°F]

### Agency Approvals

- CE




Identification Cable Ties															
Part Number	Pcs/Bag	Price	Color	Tag Size		Length		Width		Min. Bundle Ø		Max. Bundle Ø		Tensile Strength	
				mm	in	mm	in	mm	in	mm	in	mm	in	kg	lb
<b>SEL.2.202T</b>	100	\$4.25	Natural	8 x 25	0.31 x 0.98	100	3.94	2.5	0.1	10	0.39	25	0.98	9	19.85
<b>SEL.2.223T</b>	100	\$7.25	Natural	35 x 13	1.38 x 0.51	200	7.87	4.8	0.19	16	0.62	50	1.97	22	48.51



# Cable Tie Tools

## Cable Tie Cutting Tool

The special angle of this cutter's tips enables clean cuts of the ties to sizes between 2.5 and 12.5 mm in width, maintaining the wired electric cables intact. The cutter can also be used for cutting cables.

	
<b><u>PIN.009</u></b>	\$16.00

## Collar Fastening Metal Plier

This tool makes it easier to tighten and cut collars. Use with Double-headed Cable Ties. Leaves a short length of tail close to the head. For use with up to 9mm wide cable ties.

	
<b><u>PIN.005</u></b>	\$14.50

## Cable Tie Gun Installation Tool

For use with cable ties up to 5mm wide. This tool helps to adjust the preload and cut the tie. Tightening torque of 2.5 kg to 12kg.

	
<b><u>PIN.003</u></b>	\$21.00



# Cable Ties Family Overview

## General Purpose Nylon Cable Ties



SapiSelco general purpose Nylon 6.6 cable ties are slotted and held in place by the resistance of the elastic tooth against the rack. These cable ties are resistant to solvents and reagents, oil, gasoline, and hydrocarbons when used at low temperatures, in low concentrations, and for short periods of time. Assortment Kit available.



These ties are low-cost, releasable, and reusable cable ties, suitable for lightweight loads. The double-locking head enables securing two cable bundles with one tie. The body is completely rounded to eliminate all sharp edges guaranteeing reliable performance every time.

## Colored Nylon Cable Ties



SapiSelco colored Nylon 6.6 cable ties are useful in applications that require distinct identifiers. These ties are colored with inorganic dyes and are resistant to solvents and reagents, oil, gasoline, and hydrocarbons when used at low temperatures, in low concentrations, and for short periods of time. Assortment Kit available.

## Stainless Steel Tooth Ties



SapiSelco stainless steel tooth ties are forged from nylon and hardened stainless steel with added Molybdenum. This ensures extremely high mechanical strength and optimal resistance to corrosion. A single central raised section makes this tie particularly flexible, while guaranteeing maximum strength at the same time.

## UV Resistant Cable Ties



Exposure to sun and ultraviolet rays causes deterioration in nylon. SapiSelco specialty Nylon UV Resistant cable ties can resist and endure the harsh conditions of outdoor applications for up to 10 years. These ties can withstand temperatures up to 125°C [257°F].

## Metal Detector Readable Cable Ties



These ties are fabricated with a special composite of 6.6 polyamide and metal powder and are sensitive to electromagnetic fields. They are recommended in the food, pharmaceutical and chemical industry. They are useful in applications where, for safety reasons, it is necessary for a metal detector to be able to detect even very small fragments of these ties that may be mixed in with products.

## Specialty Cable Ties



Nylon Releasable Tab



Screw Mount



Low Temp



Nylon Lashing Cable Tie



Identification Ties



Double-headed [Collars]

## Tools and Accessories



Cable Tie Cutting Tool



Collar Fastening Metal Plier



Cable Tie Gun Installation Tool



Bi-directional Nylon Square Bases