



Nail / Screw Mounts

Nail Gun Mount

Sapiselco's SSC series nail gun mount provides a fast and efficient method for securing cable ties directly to various surfaces using a nail gun. Made from nylon, this mount features a central hole and an opening to accept a cable tie up to 9 mm wide. This system streamlines installation by integrating the mounting process with cable bundling, making it ideal for high-volume applications in construction and industrial applications.

Compatible with 6 to 8d and 10 to 11 gauge nails

Features

- UL 94: HB rated Nylon 6.6
- Suitable for indoor applications
- Rounded edges to avoid cable damage



SSC.3.2101



Nail Gun Mount						
Part Number	Pcs/ Bag	Price	Color	Fits	Size [Diameter x Height]	Fastener Hole Diameter
SSC.3.2101	100	\$10.75	Black	0.35in maximum width cable ties	1.08 x 0.47in [27.43 x 11.93mm]	0.118in [3.0mm]

Bi-directional Nylon Square Bases

Sapiselco's BAS series single square base (without adhesive) offers a secure mounting solution for cable ties. These bases, made from Nylon 6.6 feature a screw mounting hole for installing onto various surfaces. Available in a single square configuration, each mount includes bi-directional openings to accommodate cable ties (up to 4.5mm wide), providing a flexible and efficient method for organizing and securing cable bundles in various applications.



BAS.3.406


Features

- UL 94: V2 rated Nylon 6.6
- Suitable for indoor applications
- Rounded edges to avoid cable damage
- 5 to 140°F [-15 to 60°C]

Agency Approvals

- CE

Bi-directional Nylon Square Bases								
Part Number	Pcs/ Bag	Price	Color	Dual Adhesive	Fits	Dimensions		Fastener Hole Diameter
						A	B	
BAS.2.406	100	\$3.25	Natural	No	0.18in maximum width cable ties	26.5 mm [1.04 in]	5.9 mm [0.23 in]	4.75mm [0.187in]
BAS.3.406	100	\$3.25	Black					





Nail / Screw Mounts

Screw Anchor Mount

Sapiselco's screw anchor mount offers a method for anchoring cable bundles directly to surfaces using a screw. This mount features a clearance hole for the screw fastener and a single opening designed to accept a cable tie, allowing for robust and secure cable bundling. Made from Nylon 6.6, this system mount offers a stable and precise mounting point for cable management in various applications where a permanent, screw-in attachment is preferred.



Features

- UL 94 V-2 Nylon 6.6
- Operating Temperature: -15 to 65°C [5 to 149°F]

Agency Approvals

- CE

Screw Anchor Mount						
Part Number	Pcs/ Bag	Price	Color	Fits	Size	Hole Diameter
SUP.3.405	100	\$22.50	Black	0.20in maximum width cable ties	0.76 x 0.39 x 0.24in	0.150 in [3.8 mm]
*Screws not included, use #6 or M3.5 screws						

Saddle Mount

Sapiselco's SUP series saddle-type mounts provide a sturdy and elevated anchoring point for cable ties. Made from durable Nylon 6.6, these mounts feature a body with a central through-hole for screw or plug fastening (not included) and an opening to secure a cable tie (up to 13mm wide). The design insulates the cables from the mounting surface by providing spacing, making them ideal for organizing and insulating cable bundles and wires.



SUP.3.401



SUP.3.2508

Features

- UL 94 V-2 rated Nylon 6.6
- Halogen-free
- Rounded edges to avoid damage

Agency Approvals

- CE

Saddle Mounts							
Part Number	Pcs/ Bag	Price	Color	Fits	Size	Hole Diameter	Operating Temperature
SUP.3.401	100	\$3.50	Black	0.35in maximum width cable ties	1.18 x 0.59 x 0.47in	0.197in [5.0mm]	5 to 149°F [-15 to 65°C]
SUP.3.2508	50	\$8.50	Black	0.49in maximum width cable ties	1.73 x 0.75 x 0.63in	0.256 in [6.5mm]	5 to 122°F [-15 to 50°C]





Cable Tie Tools

Cable Tie Cutting Tool

The special angle of this cutter's tips enables clean cuts of the ties to sizes between 2.5 and 12.5 mm in width, maintaining the wired electric cables intact. The cutter can also be used for cutting cables.

	
<u>PIN.009</u>	\$16.00

Collar Fastening Metal Plier

This tool makes it easier to tighten and cut collars. Use with Double-headed Cable Ties. Leaves a short length of tail close to the head. For use with up to 9mm wide cable ties.

	
<u>PIN.005</u>	\$14.50

Cable Tie Gun Installation Tool

For use with cable ties up to 5mm wide. This tool helps to adjust the preload and cut the tie. Tightening torque of 2.5 kg to 12kg.

	
<u>PIN.003</u>	\$21.00



Cable Ties Family Overview

General Purpose Nylon Cable Ties



SapiSelco general purpose Nylon 6.6 cable ties are slotted and held in place by the resistance of the elastic tooth against the rack. These cable ties are resistant to solvents and reagents, oil, gasoline, and hydrocarbons when used at low temperatures, in low concentrations, and for short periods of time. Assortment Kit available.



These ties are low-cost, releasable, and reusable cable ties, suitable for lightweight loads. The double-locking head enables securing two cable bundles with one tie. The body is completely rounded to eliminate all sharp edges guaranteeing reliable performance every time.

Colored Nylon Cable Ties



SapiSelco colored Nylon 6.6 cable ties are useful in applications that require distinct identifiers. These ties are colored with inorganic dyes and are resistant to solvents and reagents, oil, gasoline, and hydrocarbons when used at low temperatures, in low concentrations, and for short periods of time. Assortment Kit available.

Stainless Steel Tooth Ties



SapiSelco stainless steel tooth ties are forged from nylon and hardened stainless steel with added Molybdenum. This ensures extremely high mechanical strength and optimal resistance to corrosion. A single central raised section makes this tie particularly flexible, while guaranteeing maximum strength at the same time.

UV Resistant Cable Ties



Exposure to sun and ultraviolet rays causes deterioration in nylon. SapiSelco specialty Nylon UV Resistant cable ties can resist and endure the harsh conditions of outdoor applications for up to 10 years. These ties can withstand temperatures up to 125°C [257°F].

Metal Detector Readable Cable Ties



These ties are fabricated with a special composite of 6.6 polyamide and metal powder and are sensitive to electromagnetic fields. They are recommended in the food, pharmaceutical and chemical industry. They are useful in applications where, for safety reasons, it is necessary for a metal detector to be able to detect even very small fragments of these ties that may be mixed in with products.

Specialty Cable Ties



Nylon Releasable Tab



Screw Mount



Low Temp



Nylon Lashing Cable Tie



Identification Ties



Double-headed [Collars]

Tools and Accessories



Cable Tie Cutting Tool



Collar Fastening Metal Plier



Cable Tie Gun Installation Tool



Bi-directional Nylon Square Bases