



# Specialty Head Cable Ties

## Releasable Cable Ties

Sapiselco's CLT series "Click" cable ties are a versatile and often reusable solution, distinguished by their unique beaded design and releasable mechanism. The "Click" design allows for easy opening and re-bundling of cables, making them ideal for temporary installations, prototyping, or situations where modifications are frequent.

Intended for lightweight loads, the double-locking head enables securing two cable bundles with one tie. The body is completely rounded to eliminate all sharp edges. This reusability not only offers convenience but also contributes to cost savings and waste reduction, making the CLT series a practical choice for various applications where reusability and flexibility are needed.



## Features

- Low-Density Polyethylene (LDPE) material
- Rounded edges to avoid cable damage
- Operating temperature: -50 to 60°C [-58 to 140°F]

## Agency Approvals

- CE



Releasable Cable Ties													
Part Number	Pcs/ Bag	Price	Color	Length		Width		Min. Bundle Ø		Max. Bundle Ø		Tensile Strength	
				mm	in	mm	in	mm	in	mm	in	kg	lb
<a href="#">CLT.10.2110R</a>	100	\$3.00	Red	118	4.65	3.5	0.13	3	0.12	26	1.02	7	15.44
<a href="#">CLT.10.2116R</a>	100	\$7.50	Red	238	9.37	3.8	0.16	4	0.15	61	2.4	13.5	29.77
<a href="#">CLT.10.2129R</a>	100	\$10.00	Red	318	12.52	4.4	0.17	5	0.20	83	3.26	15.5	34.18
<a href="#">CLT.10.2149R</a>	100	\$22.00	Red	496	19.53	5.6	0.22	40	1.57	140	5.51	27.5	60.64
<a href="#">CLT.10.2157</a>	100	\$36.00	Red	643	25.31	5.6	0.22	80	3.14	180	7.08	27.5	

## Winged Push-In Panel Cable Ties

Sapiselco's panel push cable ties are designed for efficient and secure fastening of cable bundles directly to panels, chassis, or other surfaces with pre-drilled holes. These ties integrate a self-locking cable tie with a winged push-mount fastener at the head, allowing for quick, tool-free installation into a compatible hole. Made from durable Nylon 6.6, they provide a reliable, integrated solution for routing and securing wiring, eliminating the need for separate mounting clips or screws. This design is ideal for applications where cables need to be neatly routed and anchored directly to a surface, offering a clean aesthetic and reducing installation time.



## Features

- UL 94: V-2 rated Nylon 6.6
- Operating temperature: -40 to 85°C [-58 to 140°F]
- Minimum installation temperature: -10°C [14°F]

## Agency Approvals

- CE


Winged Push-In Panel Cable Ties															
Part Number	Pcs/ Bag	Price	Color	Length		Width		Min. Bundle Ø		Max. Bundle Ø		Tensile Strength		Panel Hole Diameter	Panel Thickness
				mm	in	mm	in	mm	in	mm	in	kg	lb		
<a href="#">SCA.3.202</a>	100	\$2.75	Black	100	3.94	2.50	0.1	2.0	0.10	24.0	0.94	9	19.85	0.177in to 0.189in [4.5 to 4.8mm]	0.024in to 0.094in [0.6 to 2.4mm]
<a href="#">SCA.3.210</a>	100	\$3.75	Black	140	5.51	3.50	0.14	4.0	0.16	30.0	1.18	15	33.08	0.236in to 0.256in [6.0 to 6.5mm]	0.024in to 0.087in [0.6 to 2.2mm]



# Cable Tie Tools

## Cable Tie Cutting Tool

The special angle of this cutter's tips enables clean cuts of the ties to sizes between 2.5 and 12.5 mm in width, maintaining the wired electric cables intact. The cutter can also be used for cutting cables.

	
<b><u>PIN.009</u></b>	\$16.00

## Collar Fastening Metal Plier

This tool makes it easier to tighten and cut collars. Use with Double-headed Cable Ties. Leaves a short length of tail close to the head. For use with up to 9mm wide cable ties.

	
<b><u>PIN.005</u></b>	\$14.50

## Cable Tie Gun Installation Tool

For use with cable ties up to 5mm wide. This tool helps to adjust the preload and cut the tie. Tightening torque of 2.5 kg to 12kg.

	
<b><u>PIN.003</u></b>	\$21.00



# Cable Ties Family Overview

## General Purpose Nylon Cable Ties



SapiSelco general purpose Nylon 6.6 cable ties are slotted and held in place by the resistance of the elastic tooth against the rack. These cable ties are resistant to solvents and reagents, oil, gasoline, and hydrocarbons when used at low temperatures, in low concentrations, and for short periods of time. Assortment Kit available.



These ties are low-cost, releasable, and reusable cable ties, suitable for lightweight loads.

The double-locking head enables securing two cable bundles with one tie. The body is completely rounded to eliminate all sharp edges guaranteeing reliable performance every time.

## Colored Nylon Cable Ties



SapiSelco colored Nylon 6.6 cable ties are useful in applications that require distinct identifiers. These ties are colored with inorganic dyes and are resistant to solvents and reagents, oil, gasoline, and hydrocarbons when used at low temperatures, in low concentrations, and for short periods of time. Assortment Kit available.

## Stainless Steel Tooth Ties



SapiSelco stainless steel tooth ties are forged from nylon and hardened stainless steel with added Molybdenum. This ensures extremely high mechanical strength and optimal resistance to corrosion. A single central raised section makes this tie particularly flexible, while guaranteeing maximum strength at the same time.

## UV Resistant Cable Ties



Exposure to sun and ultraviolet rays causes deterioration in nylon. SapiSelco specialty Nylon UV Resistant cable ties can resist and endure the harsh conditions of outdoor applications for up to 10 years. These ties can withstand temperatures up to 125°C [257°F].

## Metal Detector Readable Cable Ties



These ties are fabricated with a special composite of 6.6 polyamide and metal powder and are sensitive to electromagnetic fields. They are recommended in the food, pharmaceutical and chemical industry. They are useful in applications where, for safety reasons, it is necessary for a metal detector to be able to detect even very small fragments of these ties that may be mixed in with products.

## Specialty Cable Ties



**Nylon Releasable Tab**



**Screw Mount**



**Low Temp**



**Nylon Lashing Cable Tie**



**Identification Ties**



**Double-headed [Collars]**

## Tools and Accessories



**Cable Tie Cutting Tool**



**Collar Fastening Metal Plier**



**Cable Tie Gun Installation Tool**



**Bi-directional Nylon Square Bases**