

CT Series Capacitive Proximity Sensors



CT1-00-2H



CT2-AP-1A



CT2-CP-2H

M30 (30mm) Plastic – DC

Pushbutton Models

- N.O./N.C. selectable
- Pushbutton teach
- LED status indicators
- IP65/IP67 rated
- M12 quick-disconnect; purchase cable separately
- Mounting accessories available



Potentiometer Models

- N.O. or N.C. units available
- Potentiometer sensitivity adjustment
- LED status indicators
- IP65/IP67/IP69K rated
- 2m (6.5 ft) cable or M12 quick-disconnect; purchase cable separately
- Mounting accessories available

CT Series Capacitive Proximity Selection Chart

| Part Number | Price | Sensing Distance | Mounting | Output State | Logic | Connection | Wiring | Dimensions |
|---|---------|------------------|-----------|--------------|---------|-----------------------------|-----------|------------|
| Pushbutton select and teach | | | | | | | | |
| CT1-00-2H | \$92.00 | 40 mm [1.58 in] | Non-flush | N.O./N.C. | NPN/PNP | M12 [12mm] quick-disconnect | Diagram 2 | Figure 1 |
| Potentiometer sensitivity adjustment | | | | | | | | |
| CT2-AP-1A | \$69.00 | 15mm [0.59 in] | Flush | N.O. | PNP | 2m [6.5 ft] cable | Diagram 1 | Figure 2 |
| CT2-AP-1H | \$69.00 | 15mm [0.59 in] | Flush | N.O. | PNP | M12 micro DC connector | Diagram 2 | Figure 3 |
| CT2-CP-1A | \$69.00 | 15mm [0.59 in] | Flush | N.C. | PNP | 2m [6.5 ft] cable | Diagram 1 | Figure 2 |
| CT2-CP-1H | \$69.00 | 15mm [0.59 in] | Flush | N.C. | PNP | M12 micro DC connector | Diagram 2 | Figure 3 |
| CT2-AN-2A | \$69.00 | 25mm [0.98 in] | Non-flush | N.O. | NPN | 2m [6.5 ft] cable | Diagram 1 | Figure 2 |
| CT2-AN-2H | \$69.00 | 25mm [0.98 in] | Non-flush | N.O. | NPN | M12 micro DC connector | Diagram 2 | Figure 3 |
| CT2-AP-2A | \$69.00 | 25mm [0.98 in] | Non-flush | N.O. | PNP | 2m [6.5 ft] cable | Diagram 1 | Figure 2 |
| CT2-AP-2H | \$69.00 | 25mm [0.98 in] | Non-flush | N.O. | PNP | M12 micro DC connector | Diagram 2 | Figure 3 |
| CT2-CN-2A | \$69.00 | 25mm [0.98 in] | Non-flush | N.C. | NPN | 2m [6.5 ft] cable | Diagram 1 | Figure 2 |
| CT2-CN-2H | \$69.00 | 25mm [0.98 in] | Non-flush | N.C. | NPN | M12 micro DC connector | Diagram 2 | Figure 3 |
| CT2-CP-2A | \$69.00 | 25mm [0.98 in] | Non-flush | N.C. | PNP | 2m [6.5 ft] cable | Diagram 1 | Figure 2 |
| CT2-CP-2H | \$69.00 | 25mm [0.98 in] | Non-flush | N.C. | PNP | M12 micro DC connector | Diagram 2 | Figure 3 |

CT Series Capacitive Proximity Sensors

| CT Series Capacitive Proximity Specifications | | | |
|---|---|---------------------|----------------|
| Model | CT1-00-2H | CT2-xx-xx | CT2-xx-xx |
| Mounting Type | Non-flush | Flush | Non-flush |
| Nominal Sensing Distance | 40mm [1.58 in] | 15mm [0.59 in] | 25mm [0.98 in] |
| Sensitivity | Push to teach | Potentiometer | |
| Operating Distance | NA | | |
| Material Correction Factors | NA | | |
| Output Type | NPN/PNP; N.O./N.C. | | |
| Operating Voltage | 10 to 36VDC | 10 to 30VDC | |
| No-load Supply Current | < 20mA | < 22mA | |
| Operating (Load) Current | 200mA | | |
| Off-state (Leakage) Current | NA | | |
| Voltage Drop | < 2.5 VDC | | |
| Switching Frequency | 10Hz | 40Hz | |
| Differential Travel (% of Nominal Distance) | NA | | |
| Repeat Accuracy | NA | | |
| Ripple | NA | | |
| Time Delay Before Availability (tv) | NA | | |
| Reverse Polarity Protection | Yes | | |
| Short-circuit Protection | Yes, pulsed | | |
| Operating Temperature | -25 to 80°C [-13 to 176°F] Sensing face: -25 to 110°C [-13 to 230°F] | | |
| Protection Degree (DIN 40050) | IEC IP65/IP67 | IEC IP65/IP67/IP69K | |
| Indication/Switch Status | Yellow [output energized] | | |
| Housing Material | Polybutylene terephthalate [PBT] | | |
| Sensing Face Material | Polybutylene terephthalate [PBT] | | |
| Shock/Vibration | DIN EN 60947-5-2 | | |
| Tightening Torque | 8.0 N•m [5.9 lb•ft] | | |
| Weight | 117g [4.13 oz] | 96.7 g [3.41 oz] | |
| Connectors | M12 connector, 2 lock nuts included | | |
| Agency Approvals | cULus file E328811, CE | | |

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

CT Series Capacitive Proximity Sensors

Wiring Diagrams

Diagram 1
NPN Cable







Diagram 2
NPN Output




Connector
M12 connector



PNP Cable




PNP Output




Mounting

*NOTE: If the required clear space is not observed for non-flush units, the sensor is predamped. This may lead to permanent switching.
Non-flush sensors may be installed flush in non-conductive materials and have to be installed in non-flush in conductive materials.*


Flush




Non-flush



Flush



Non-flush



CT Series Capacitive Proximity Sensors

Dimensions

mm [inches]

Figure 1






Figure 2



1 = LED YELLOW SWITCHING STATUS
2 = POTENTIOMETER SENSING RANGE

Figure 3



1 = LED YELLOW SWITCHING STATUS
2 = POTENTIOMETER SENSING RANGE

See our website: www.AutomationDirect.com for complete engineering drawings

Capacitive Proximity Sensors - Accessories



| Capacitive Proximity Sensors Accessory Chart | | | | |
|--|---------|---|---|------------|
| Part Number | Price | Description | Material | Dimensions |
| Mounting Adapter | | | | |
| CR1-ADPTR | \$5.00 | Adapter for CR1 series capacitive sensors | Housing: Polybutylene Terephthalate (PBT) Included Screws: M3 x 6 Steel (0.5 N•m [0.37 lb•ft]) | Figure 1 |
| Mounting Wells | | | | |
| MWT-01 | \$57.00 | 30mm [1.18 in] sensor mounting well | PTFE - Polytetrafluoroethylene (Teflon®) Temp: -25 to 246°C [-13 to 474.8°F] Max. pressure: 100 PSI [6.9 bar] | Figure 2 |
| MWK-01 | \$47.00 | 18mm [0.71 in] sensor mounting well | | Figure 3 |

Dimensions

mm [inches]

Figure 1




Figure 2





Figure 3



See our website: www.AutomationDirect.com for complete engineering drawings

Accessories for 30mm Sensors


Axial Mounting Bracket

Mounting bracket, axial, zinc-plated steel. For use with 30mm sensors. Has two mounting holes (use 5mm screws) and allows the rotation of an optical axis for right-beam-angle-adaptor sensors. Hexagonal nuts not included.

| Accessories for 30mm Sensors | | | |
|------------------------------|--------|--|---------------|
| Part Number | Price | Description | Weight lb [g] |
| ST30A | \$2.50 | Micro Detectors mounting bracket, axial, zinc plated steel. For use with 30mm sensors. | 0.18 [81.7] |

Dimensions

mm [inches]



ST30A



Right-angle Mounting Bracket

Mounting bracket, right-angle, zinc-plated steel. For use with 30mm sensors. Has two mounting holes (use 5mm screws) and allows the rotation of an optical axis for axial sensors. Hexagonal nuts not included.

| Accessories for 30mm Sensors | | | |
|------------------------------|--------|--|---------------|
| Part Number | Price | Description | Weight lb [g] |
| ST30C | \$2.50 | Micro Detectors mounting bracket, right-angle, zinc plated steel. For use with 30mm sensors. | 0.18 [81.7] |

Dimensions

mm [inches]



ST30C

Accessories for 30mm Sensors


Right-angle Mounting Bracket

Mounting bracket, right-angle, 304 stainless steel. For use with 30mm sensors.

| Accessories for FW Series Sensors | | | |
|-----------------------------------|--------|---|----------------|
| Part Number | Price | Description | Weight lb [g] |
| ST30C6W | \$6.00 | AutomationDirect mounting bracket, right-angle, 304 stainless steel. For use with 30mm sensors. | 0.15 (68.0) |

Dimensions

mm [inches]



ST30C6W

Right-angle Swivel Mounting Systems

Mounting bracket, right-angle swivel, 360 degree vertical and horizontal adjustment, 12mm rod mount. For use with 30mm sensors. Available in all 304 stainless steel or with an aluminum head with a 304 stainless steel mounting plate.

| Accessories for 30mm Sensors | | | | | | |
|------------------------------|---------|--|---------------------|---------------------|---------------------|----------------|
| Part Number | Price | Description | Mounting Head | Mounting Plate | Drawing Link | Weight lb [g] |
| OPT2118 | \$12.50 | Wenglor mounting bracket, right-angle swivel, 360 degree vertical and horizontal adjustment, aluminum, 12mm rod mount. For use with 30mm sensors. | Aluminum | 304 Stainless steel | PDF | 0.18 (81.7) |
| OPT2119 | \$22.50 | Wenglor mounting bracket, right-angle swivel, 360 degree vertical and horizontal adjustment, 304 stainless steel, 12mm rod mount. For use with 30mm sensors. | 304 Stainless Steel | 304 Stainless steel | PDF | 0.18 (81.7) |

Note: 304 Stainless steel mounting rods sold separately: [OPT2109](#) (200mm [7.87 in] length), [OPT2110](#) (300mm [11.81 in] length), and [OPT2111](#) (500mm [19.69 in] length).



OPT2118, OPT2119

Mounting Rods and Brackets

Mounting Rods

304 Stainless steel rods for mounting swivel brackets [OPT2112](#) - [OPT2127](#). Available in three lengths: 200mm, 300mm, and 500mm. 12mm diameter.

| Mounting Rods for OPT2112-2127 Swivel Mounting Brackets | | | | |
|---|---------|---|---------------------|------------------|
| Part Number | Price | Description | Drawing Link | Weight lb (g) |
| OPT2109 | \$14.00 | Wenglor mounting rod, 12mm diameter, 200mm length, 304 stainless steel. | PDF | 0.41 [185.97] |
| OPT2110 | \$17.50 | Wenglor mounting rod, 12mm diameter, 300mm length, 304 stainless steel. | PDF | 0.60 [272.16] |
| OPT2111 | \$22.50 | Wenglor mounting rod, 12mm diameter, 500mm length, 304 stainless steel. | PDF | 0.98 [444.52] |



Right-angle Mounting Bracket

Mounting bracket, right-angle, nickel-plated brass. For use with 12mm mounting rods [OPT2109](#), [OPT2110](#) & [OPT2111](#).

| Right-angle Mounting Brackets for 12mm Sensors | | | | |
|--|---------|---|---------------------|----------------|
| Part Number | Price | Description | Drawing Link | Weight lb [g] |
| OPT2108 | \$17.50 | Wenglor mounting bracket, right-angle, nickel-plated brass. For use with 12mm mounting rods OPT2109 , OPT2110 & OPT2111 . | PDF | 0.07 [31.8] |

