



SCHMERSAL Illuminated 30mm IP65 Plastic Pushbuttons

[EDL.VBL](#)[EDL.VGB](#)[EDL.VGN](#)[EDL.VRT](#)[EDL.VWS](#)

Illuminated 30mm IP65 Plastic Pushbuttons*					
Part Number	<u>EDL.VBL</u>	<u>EDL.VGB</u>	<u>EDL.VGN</u>	<u>EDL.VRT</u>	<u>EDL.VWS</u>
Price	\$26.50	\$26.50	\$26.50	\$26.50	\$26.50
Color	Blue	Yellow	Green	Red	White
Drawing Link	PDF	PDF	PDF	PDF	PDF
Description	Momentary action illuminated IP65 pushbuttons with flush mount				
Mounting diameter	30.5 mm [1.20 in]				
Actuating stroke	4 to 5 mm				
Dome material	Glass				
Front ring material	Aluminum				
Front panel thickness	1 to 6 mm				
Weight	30g [1.06 oz]				
Mounting screws tightening torque	0.6 N·m [0.44 lb·ft]				
Ambient temperature	-25 to +75°C [-13 to +167°F]				
Shock resistance	< 50g				
Vibration resistance	5g				
Ingress protection rating	IP65				
Standards **	IEC 60947-5-1; IEC 60947-1; UL File E57648				

*Operator only. Purchase contact and light blocks separately.

**To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.


SCHMERSAL

Contact Blocks and Light Terminal Blocks Overview

Features

- A self-cleaning contact bridge system, known as Elan four-way system, which is particularly suitable for low voltage applications and has a lower switching capacity of 5VDC/3.2 mA (max. 400VAC/8A). It is designed in the form of a bent twin contact bridge, with parallel and also diagonal operation.
- Block mounting via snap-on stainless steel springs.
- Complete terminal designations visible at a glance in compliance with IEC 60 947-1 (VDE 0660, Part 100) with a complete function and sequence number (refer also to product ranges). The function number identifies the N.C. and N.O. contact. The sequence number specifies the number and the order of the contacts on the complete switching device.
- N.C. contacts with positive opening in compliance with IEC 60 947-5-1 (VDE 0660 Part 200).
- Galvanically isolated contact circuits in 2-pole blocks.
- High resistance to shock and vibrations.



Technical Specifications			
	Contact Blocks	Light Blocks (ELE)	Light Blocks (ELDE)
General description	Contact element	Light terminal block w/Ba9S base	Light terminal block w/LED
Enclosure material	Plastic, glass fiber reinforced	Plastic, glass fiber reinforced	Plastic, glass fiber reinforced
Contact material	Fine-silver, phosphor bronze or brass carrier	–	–
Utilization category	AC-15: 250 V / 8 A DC-13: 24 V / 5 A	–	–
Suitability for low voltages	≥ 5VDC / 3.2 mA	–	–
Rated insulation voltage U_i	400V	440V	440V
Rated impulse withstand voltage U_{imp}	4kV	–	–
Thermal test current I_{the}	10A	–	–
Max. fuse rating	10A gG D-fuse slow blow	10A gG T-slow blow	10A gG T-slow blow
Wire size	0.5 mm ² to 2.5 mm ² (20 - 14 AWG)		
Tightening torque wire connection	Maximum 1 N·m (0.74 lb·ft)		
NEMA contact rating	A300 / P300	–	–
Switching frequency	1200 s/h	–	–
Switching capacity	5VDC / 3.2 mA (max 400VAC / 8A)	–	–
Mechanical life	10,000,000 operation	–	–
Resistance to shock	110 g/4ms to 30 g/18ms no bouncing	–	–
Resistance to vibration	> 20 g/10ms to 200Hz	–	–
Ambient temperature	-25 to +80°C [-13 to +176°F]		
Ingress protection rating	IP20 terminals / IP40 switching compartment	IP20 terminals	IP20 terminals
Standards	IEC 60947-5-1; IEC 60947-1; UL File E57648		

NEMA Contact Rating Designation

	Thermal Current	Voltage	Volt amperes
A300	10	300 AC	N/A
P300	5	300 DC	138



SCHMERSAL Contact Blocks



EF03.2



EF10.1



EF103.2



EF220.2



EF303.2



EFM

Contact Blocks								
Part Number	Price	Qty.	Drawing Link	Contacts	Mounting Position	Travel Diagram (mm)	Wiring Diagram	Application
EF10.1*	\$10.00	1	PDF	1 N.C.	1			Standard
EF10.2*	\$10.00	1	PDF		2			
EF10.3*	\$10.00	1	PDF		3			
EF03.1	\$10.00	1	PDF	1 N.O.	1			
EF03.2	\$10.00	1	PDF		2			
EF03.3	\$10.00	1	PDF		3			
EF110.1*	\$15.50	1	PDF	2 N.C.	1			
EF110.2*	\$16.00	1	PDF		2			
EF110.3*	\$16.00	1	PDF		3			
EF033.1	\$16.00	1	PDF	2 N.O.	1			
EF033.2	\$16.00	1	PDF		2			
EF033.3	\$16.00	1	PDF		3			
EF103.1*	\$12.50	1	PDF	1 N.C. / 1 N.O.	1			
EF103.2*	\$12.50	1	PDF		2			
EF103.3*	\$12.50	1	PDF		3			
EF220.1**	\$16.00	1	PDF	2 N.C.	1			Emergency Stop
EF220.2**	\$16.00	1	PDF		2			
EF220.3**	\$16.00	1	PDF		3			
EF303.1**	\$12.50	1	PDF	1 N.C. / 1 N.O.	1			
EF303.2**	\$12.50	1	PDF		2			
EF303.3**	\$12.50	1	PDF		3			

*Not suitable for Emergency Stop devices

**Not suitable for maintained selector switches NWS/NWT

Travel Diagram Legend

= contact closed

= contact open

Numbers indicate distance in mm

Mounting Flange			
Part Number	Price	Description	Drawing Link
EFM	\$5.50	Schmersal mounting flange, replacement. For use with E and N series pushbuttons.	PDF



SCHMERSAL Light Terminal Blocks



ELDE.Nxx230



ELDE.Nxx24



ELE



ELE230

Light Terminal Blocks

Part Number	Color	Price	Drawing Link	Voltage	Wattage	Diagram	Function
ELDE.NBL230	Blue	\$50.00	PDF	115-230 VAC	4		Integrated LED
ELDE.NBL24		\$27.00	PDF	24 VAC/VDC	0.4		
ELDE.NGB230	Yellow	\$50.00	PDF	115-230 VAC	4		
ELDE.NGB24		\$27.00	PDF	24 VAC/VDC	0.4		
ELDE.NGN230	Green	\$50.00	PDF	115-230 VAC	4		
ELDE.NGN24		\$27.00	PDF	24 VAC/VDC	0.4		
ELDE.NRT230	Red	\$50.00	PDF	115-230 VAC	4		
ELDE.NRT24		\$27.00	PDF	24 VAC/VDC	0.4		
ELDE.NWS230	White	\$50.00	PDF	115-230 VAC	4		
ELDE.NWS24		\$27.00	PDF	24 VAC/VDC	0.4		
ELE	–	\$11.50	PDF	24 VAC/VDC	1		Ba9S Lamp holder
ELE230	–	\$31.00	PDF	115-230 VAC	1		

Ba9S Bulbs for ELE and ELE230 Light Terminal Blocks

Part Number	Color	Price	Qty	Lamp Voltage	Current Consumption	Power Consumption	Lamp Durability
APX510-24R	Red	\$18.50	2	24V AC/DC	12mA AC 11mA DC	0.8 W	30,000h
APX510-24G	Green	\$18.50					
APX510-24Y	Yellow	\$18.50					
APX510-24S	Blue	\$68.00					
APX510-24O	Orange	\$18.50					

[APX510-24R](#)

Replacement LED Lamps for ELE and ELE230 Light Terminal Blocks

Part Number	Color	Price	Qty	Lamp Voltage	Current Consumption	Power Consumption	Lamp Durability
ECX1911-2	Red	\$19.00	2	24V AC/DC	14mA	0.6 W	100,000h
ECX1912-2	Green	\$24.00			13mA		
ECX1913-2	Yellow	\$19.00			13.3 mA		
ECX1914-2	Blue	\$26.00			13mA		
ECX1915-2	White	\$31.00			19mA		

[ECX1915-2](#)

NOTE: ELE230 has transformer to step down to 24V


Mounting Flange

Part Number	Price	Description	Drawing Link
ELM	\$5.50	Schmersal mounting flange, replacement. For use with E and N series illuminated pushbuttons.	PDF

[ELM](#)

SCHMERSAL Modular Design Flexibility

Non-Illuminated Devices



Illuminated Devices

