



Nnectors Screwless Feed-Through **Terminal Blocks**

Feed-through terminal blocks provide the means to connect two wires together, and are available in sizes suitable for up to 8AWG wire. These terminal blocks are 35mm DIN rail mountable.



DN-Q12-A (Euro Q2.5/35)



DN-Q10B-A (Euro Q4/35)




(Euro Q6/35)

				Orderin	g Informa	itioi	n				
		Part Number	Qty	Price	Part Numbe	r	Qty	Price	Part Number	Qty	Price
Gray Terminal	Block	DN-Q12-A	50	\$46.00	DN-Q10-A	١	50	\$45.00	DN-Q8-A	50	\$70.00
Blue Terminal	Block	DN-Q12B-A	50	\$48.00	DN-Q10B-	<u>A</u>	50	\$48.00	DN-Q8B-A	50	\$76.00
Description		Screwless feed	-through terr	minal blocks	Screwless fee	ed-thro	ough term	inal blocks	Screwless feed	-through teri	ninal blocks
				Technica	Specifica	atio	ns				
Stripping Leng	gth	12:	nm [0.47 in]		1	5mm	[0.59 in]		18	3mm [0.71]	
Density		200	m [60 pcs/ft]	16	66/m [50 pcs/ft]		125	/m [38 pcs/ft	
UL Approval*		600V	20A	24-12 AWG	600V	3	30A	24-10 AWG	600V	45A	22-8 AWG
VDE Approval		630V	24A	2.5 mm ²	630V	3	32A	4mm²	630V	41A	6mm²
Operating Ten	nperature	Ambient air t	emperature:	-20 to 105°C	[-4 to 221°F] / Re	elative	humidity:	50% max at	40°C [104°F]; 90°	% max at 20	°C [68°F]
SCCR Rating		,	0kA per Tab	le SB4.1, 2009	, UL 508A, Maxir	mum s	short circu	it current ratin	g for unmarked co	mponents	
CE Conformity	у				CE (EN 60	0947-1	1 / EN 609	47-7-1)			
Agency File #						UL E1	179129				
				Ac	cessories						
End Covers		DN-QEC12	50	\$23.50	DN-QEC1	0	50	\$23.50	DN-QEC8	50	\$28.00
Ena Covers		DN-QEC12MI	10	\$6.00	DN-QEC10N	<u>NN</u>	10	\$6.00	DN-QEC8MN	10	\$6.50
	2-pole	DN-2J2Y	100	\$47.50	DN-2J4Y		100	\$50.50	DN-2J6Y	100	\$66.00
		DN-2J2YMN	25	\$14.50	DN-2J4YM		25	\$16.00	DN-2J6YMN		\$16.50
Jumpers	3-pole	DN-3J2Y	100	\$68.00	<u>DN-3J4Y</u>		100	\$81.00	<u>DN-3J6Y</u>	100	\$92.00
		DN-3J2YMN	25	\$20.00	DN-3J4YM		25	\$24.00	DN-3J6YMN		\$26.00
	Multi-pole	<u>DN-24J2Y</u>	5	\$31.00	<u>DN-24J4Y</u>		5	\$32.50	<u>DN-12J6Y</u>	10	\$39.00
Jumper Cuttin	<u> </u>	DN-J2CUT	1	\$87.00	DN-J4CU		11	\$87.00		-	
35mm	7.5 mm	DN-R35S1	10	\$39.00	DN-R35S1		10	\$39.00	<u>DN-R35S1</u>	10	\$39.00
DIN Rail	high	DN-R35S1-2	2	\$11.00	DN-R35S1-		2	\$11.00	DN-R35S1-2		\$11.00
		DN-EB35	50	\$74.00	DN-EB35		50	\$74.00	DN-EB35	50	\$74.00
		DN-EB35MN	20 50	\$34.50 \$52.50	DN-EB35M		20 50	\$34.50 \$52.50	DN EB35MN	50	\$34.50 \$52.50
End Brackets		DN-EB35-A DN-EB35-A-1		\$13.00	DN-EB35-A-		10	\$13.00	DN-EB35-A DN-EB35-A-1		\$13.00
		DN-EB35-A-1	50	\$47.00	DN-EB35-A-		50	\$47.00	DN-EB35-A-1	50	\$47.00
		DN-QEB35-1		\$12.50	DN-QEB35-		10	\$12.50	DN-QEB35-1		\$12.50
Angled Suppo	ort Bracket	DN-ASB1	50	\$107.00	DN-ASB1		50	\$107.00	DN-ASB1	50	\$107.00
Marking Tags		DN-QL Series	500		DN-QL Series		500		DN-QL Series	500	various
*Copper wire only				1						300	1

Note: For more information on accessories, see the DINnectors Accessories section of this chapter.

Dimensions



Screwless Terminal Blocks Overview

Why go screwless?

Screwless clamping technology offers several benefits:


- Speed: On average, screwless connections can be made in half the time of screw type connections, cutting installation labor costs in half.
- Ease: No need for twisting and turning screws, so screwless terminal blocks are much easier on the installer's hands and arms. Also, wiring from the top of the terminal blocks allow installers to accurately and reliably see the wire fully inserted into the spring clamp.
- Safety: Never have a problem with faulty connections from loose screws again! Meets the same UL, and IEC standards as screwtype terminal blocks.
- Maintenance-free: The screwless spring clamp conforms to the wire with constant tension, making it maintenance-free.

Are there any trade-offs of going screwless versus screw-type?

Unless you need to clamp multiple wires to the same connection point, the answer is no. If you do, then there may be a slight trade-off in requiring more panel space than with screw terminal blocks. Unlike screw terminal blocks, screwless terminal block spring-clamps are designed to clamp a single wire, only. This is why multiple versions exist like the "one-to-two" or "two-to-two." These versions allow multiple wires to be connected together via multiple spring clamps.

How does it work?

Well, it's pretty simple: Push, Insert, Release. Just push your screwdriver into the spring clamp (a rectangular shaped hole) to open the spring clamp; insert the stripped wire into the clamp a circular shaped hole), and pull out your screwdriver to release the clamp against the wire. That's it. The connection is made.




How do the jumpers work?



Properly align jumper bar with terminal block center jumper slots.





Yes = Good, acceptable jumper No = Bad, damaged jumper

www.automationdirect.com

Terminal Blocks

Jumpers

Multi-pole jumper bars for DINnector terminal blocks




DN-12JL14B-A

	Multi-pole Jumper Bars								
			Number	Rati	ing	Tightening	Insulation	For Use With	
Part Number	Qty	Price	of Poles	(V)	(A)	Torque	Color	Terminal Block Series	
Screw-down Connecti	on								
<u>DN-2J6</u>	100	\$84.00	2	600	65		-		
<u>DN-3J6</u>	100	\$145.00	3	600	65	0.5 Nm [4.4 Lb-ln]	-	DN-T6	
<u>DN-4J6</u>	100	\$186.00	4	600	65		_	<u>DIN-10</u>	
<u>DN-55J6</u>	1	\$29.00	55	600	65		-		
<u>DN-24J8</u>	5	\$45.00	24	600	50	0.6 Nm [5.3 lb-in]	Green	<u>DN-T8</u>	
Push-in Connection									
DN-2J2Y	100	\$47.50	2	600	25		Orange	DN-T12-A	
DN-2J2YMN	25	\$14.50	2	600	25		Orange	DN-EMX	
DN-3J2Y	100	\$68.00	3	600	25		Orange	<u>DN-Q12-A</u> DN-QD12-A	
DN-3J2YMN	25	\$20.00	3	600	25		Orange	DN-QEMX	
<u>DN-24J2Y</u>	5	\$31.00	24	600	25		Orange	DN-QKBD12-A	
DN-2J4Y	100	\$50.50	2	600	25		Yellow		
DN-2J4YMN	25	\$16.00	2	600	25		Yellow	DN-T10-A	
<u>DN-3J4Y</u>	100	\$81.00	3	600	25		Yellow	<u>DN-D10-A</u> DN-M10-A	
<u>DN-3J4YMN</u>	25	\$24.00	3	600	25		Yellow	DN-Q10-A	
<u>DN-24J4Y</u>	5	\$32.50	24	600	25		Yellow		
<u>DN-2JL14-A</u>	100	\$74.00	2	300	20		Red		
DN-2JL14-AMN	25	\$16.50	2	300	20		Red		
DN-2JL14B-A	100	\$74.00	2	300	20		Blue		
DN-2JL14B-AMN	25	\$16.50	2	300	20	_	Blue		
<u>DN-3JL14-A</u>	100	\$109.00	3	300	20		Red	DN-TL-A	
DN-3JL14-AMN	25	\$25.50	3	300	20		Red	DIN-1L-A	
DN-3JL14B-A	100	\$109.00	3	300	20		Blue		
DN-3JL14B-AMN	25	\$25.50	3	300	20		Blue		
DN-12JL14-A	10	\$29.00	12	300	20		Red		
DN-12JL14B-A	10	\$29.00	12	300	20		Blue		
DN-12JFE	10	\$66.00	12	300	25		Blue	DN-FE4	
DN-2J6Y	100	\$66.00	2	600	30		Green	DN-Q8-A	
DN-2J6YMN	25	\$16.50	2	600	30		Green		
DN-3J6Y	100	\$92.00	3	600	30		Green	DN-Q8-A	
DN-3J6YMN	25	\$26.00	3	600	30		Green		
<u>DN-12J6Y</u>	10	\$39.00	12	600	30		Green	<u>DN-Q8-A</u>	


Dimensions

mm [inches]


DN-24J8




DN-xJ2Y / DN-xJ2YMN




DN-xJ4Y / DN-xJ4YMN




DN-xJL14 / DN-xJL14x-AMN, DN-xJ14x-A



DN-12JFE




DN-xJ6Y / DN-xJ6YMN



Modifying a DN-24J8 jumper bar to the required number of poles

- 1) Place the insulating part into the jumper bar and insert screws, based on number of poles required. (For instance, in the following example, 5 poles are required). Click into place.
- 2) Using a cutting tool, cut the insulating part at the edge of the jumper bar (see below).
- 3) Hold the metal jumper bar and insulating jumper with two hands, placing fingers to the left and right of the pole you wish to cut, repeatedly flexing up and down (1 or 2 times should be sufficient) until the jumper bar and insulating jumper break in two
- 4) Remove the small remaining piece of jumper (see below). This is important to ensure appropriate insulation distance in the case of contiguously applied jumpers in sequence. This step also facilitates the placement of a separator terminal if the bridge is positioned as the last terminal of a group.
- 5) The jumpers now are ready to be screwed onto <u>DN-T8</u> series terminal blocks.



Jumper Cutting Tools

Jumper cutting tools maintain protective covering.

Jumper Cutting Tools							
Part Number	Description	Qty	Price				
DN-J2CUT	DINnector jumper cutting tool, for use with DN-2J2Y, DN-3J2Y and DN-24J2Y jumpers.	1	\$87.00				
DN-J4CUT	DINnector jumper cutting tool, for use with DN-2J4Y, DN-3J4Y and DN-24J4Y jumpers.	1	\$87.00				
DN-J6CUT	DINnector jumper cutting tool, for use with DN-12J6Y jumpers.	1	\$130.00				
DN-JL14CUT	DINnector jumper cutting tool, for use with DN-12JL14-A and DN-12JL14B-A jumpers.	1	\$123.00				
DN-JXCUT	DINnector jumper cutting tool, for use with DN-J2DIE, DN-J4DIE, DN-J6DIE, DN-JL14DIE and DN-JFEDIE dies.	1	\$84.00				
DN-JFECUT	DINnector jumper cutting tool, for use with DN-12JFE jumpers.	1	\$101.00				
<u>DN-JKIT</u>	DIN <i>nector</i> cutting tool kit for DN series jumpers. Includes (1) DN-JXCUT cutting tool, (5) dies (DN-J2DIE, DN-J4DIE, DN-J6DIE, DN-JL14DIE, and DN-JFEDIE).	1	\$344.00				
DN-TOOL2	DIN <i>nector</i> tool kit, for use with DN series terminal blocks, includes (1) spring opening tool for DN-Q series screwless terminal blocks and (1) jumper removal tool for J2, J4, J6, and JL14 jumpers.	1	\$12.50				

Replacement Dies						
Part Number	Description	Price				
DN-J2DIE	DINnector die set, replacement. Package of 2. For use with jumper cutting tools DN-J2CUT or DN-JXCUT.	\$130.00				
DN-J4DIE	DINnector die set, replacement. Package of 2. For use with jumper cutting tools DN-J4CUT or DN-JXCUT.	\$130.00				
DN-JFEDIE	DINnector die set, replacement. Package of 2. For use with jumper cutting tools DN-JFECUT or DN-JXCUT.	\$101.00				
DN-J6DIE	DINnector die set, replacement. Package of 2. For use with jumper cutting tools DN-J6CUT or DN-JXCUT.	\$130.00				
DN-JL14DIE	DINnector die set, replacement. Package of 2. For use with jumper cutting tools DN-JL14CUT or DN-JXCUT.	\$130.00				



DN-J2CUT



DN-J4CUT



DN-JKIT




DN-TOOL2

www.automationdirect.com

Terminal Plugs



DN-xxPLUG / DN-xxPLUGMN



	Accessories – Terminal Plugs								
Plugs* Part Number	Qty	Price	Plugs* Part Number	Qty	Price	Number of Poles	Length mm [in]		
DN-2PLUG	200	\$127.00	<u>DN-2PLUGMN</u>	10	\$8.00	2	10.2 [0.40]		
DN-3PLUG	200	\$195.00	<u>DN-3PLUGMN</u>	10	\$12.50	3	15.2 [0.60]		
DN-4PLUG	100	\$130.00	<u>DN-4PLUGMN</u>	10	\$16.00	4	20.3 [0.80]		
<u>DN-5PLUG</u>	100	\$150.00	<u>DN-5PLUGMN</u>	10	\$20.00	5	25.4 [1.00]		
<u>DN-6PLUG</u>	100	\$194.00	<u>DN-6PLUGMN</u>	10	\$20.00	6	30.5 [1.20]		
DN-7PLUG	50	\$101.00	<u>DN-7PLUGMN</u>	5	\$16.00	7	35.6 [1.40]		
DN-8PLUG	50	\$129.00	<u>DN-8PLUGMN</u>	5	\$16.00	8	40.6 [1.60]		
DN-9PLUG	50	\$141.00	<u>DN-9PLUGMN</u>	5	\$16.50	9	45.7 [1.80]		
DN-10PLUG	50	\$150.00	<u>DN-10PLUGMN</u>	5	\$18.50	10	50.8 [2.00]		
DN-11PLUG	50	\$177.00	<u>DN-11PLUGMN</u>	5	\$21.50	11	55.9 [2.20]		
DN-12PLUG	50	\$194.00	DN-12PLUGMN	5	\$22.00	12	61.0 [2.40]		
Terminal Plugs I	Ratings								
Voltage/Curre	ent			300V, 1	2A				
Wire Gauge			1	4–22 AWG,	CU only				
Torque		Tightening Torque: 0.51 N⋅m [4.5 lb⋅in]							
Usage Temperature		Ambient air temperature: -20 to 105°C [-4 to 221°F] Relative humidity: 50% max at 40°C [104°F]; 90% max at 20°C [68°F]							
Agency Appro	ovals			UL file #: E1	79129				

Note: To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

^{*} DN-xxPLUGs fit all DN-EMXxx & DN-QEMXxx plug-in terminal blocks

	DN-DIS-BLADE DN-DIS-BMN				
	19.2 mm [0.77 in]	5.0 mm [0.20 in]			
26.9 mm [1.08 in]					


Disconnect Blade


Disconnect Blade							
Part Number	Description	Qty	Price				
DN-DIS-BLADE	Terminal block disconnect blade for DN-FE2,	50	\$39.50				
<u>DN-DIS-BMN</u>	DN-FE4, DN-DIS2 and DN-DIS4	10	\$10.50				


End Brackets



End Brackets						
Part Number	Description	Price				
DN-EB15	DINnector snap-on end bracket, 7mm wide. Package of 100. For use with 15mm DIN rail.	\$119.00				
DN-EB15MN	DINnector snap-on end bracket, 7mm wide. Package of 20. For use with 15mm DIN rail.	\$28.00				
DN-EB35	DINnector screw-down end bracket, 9mm wide. Package of 50. For use with 35mm DIN rail.	\$74.00				
DN-EB35MN	DINnector screw-down end bracket, 9mm wide. Package of 20. For use with 35mm DIN rail.	\$34.50				
DN-EB35-A	DINnector screw-down end bracket, 6mm wide. Package of 50. For use with 35mm DIN rail.	\$52.50				
DN-EB35-A-10	DINnector screw-down end bracket, 6mm wide. Package of 10. For use with 35mm DIN rail.	\$13.00				
DN-QEB35	DINnector snap-on end bracket, 6mm wide. Package of 50. For use with 35mm DIN rail.	\$47.00				
DN-QEB35-10	DINnector snap-on end bracket, 6mm wide. Package of 10. For use with 35mm DIN rail.	\$12.50				









For more information on accessories, see the "DINnectors Accessories" section of this section.

www.automationdirect.com

End Covers

Certain end covers can be used with multiple terminal block parts to cover and insulate the open side, or to put more space between adjacent blocks.

DIN <i>nector</i> 's End Covers					
Part Number	Description	Price			
DN-EC1210	DINnector terminal block end cover, gray. Package of 100. For use with DN-T12 or DN-T10 series terminal blocks.	\$47.50			
DN-EC1210MN	DINnector terminal block end cover, gray. Package of 25. For use with DN-T12 or DN-T10 series terminal blocks.	\$16.00			
DN-EC86	DINnector terminal block end cover, gray. Package of 100. For use with DN-T8 or DN-T6 series terminal blocks.	\$51.50			
DN-EC86MN	DINnector terminal block end cover, gray. Package of 25. For use with DN-T8 or DN-T6 series terminal blocks.	\$16.00			
DN-EC4	DINnector terminal block end cover, gray. Package of 50. For use with DN-T4 series terminal blocks.	\$32.50			
DN-EC4MN	DINnector terminal block end cover, gray. Package of 10. For use with DN-T4 series terminal blocks.	\$6.50			
DN-EC1/0	DINnector terminal block end cover, gray. Package of 50. For use with DN-T1/0 series terminal blocks.	\$37.00			
DN-EC1/0MN	DINnector terminal block end cover, gray. Package of 10. For use with DN-T1/0 series terminal blocks.	\$9.00			
DN-DEC10	DINnector terminal block end cover, gray. Package of 50. For use with DN-D10-A series terminal blocks.	\$34.50			
DN-DEC10MN	DINnector terminal block end cover, gray. Package of 10. For use with DN-D10-A series terminal blocks.	\$6.50			
DN-EC14	DINnector terminal block end cover, gray. Package of 25. For use with DN-TL14 series terminal blocks.	\$20.00			
DN-EC14S	DINnector terminal block end cover, gray. Package of 25. For use with DN-TL14S series terminal blocks.	\$16.50			
DN-ECM10	DINnector terminal block end cover, gray. Package of 100. For use with DN-M10-A series terminal blocks.	\$47.50			
DN-ECM10MN	DINnector terminal block end cover, gray. Package of 25. For use with DN-M10-A series terminal blocks.	\$16.00			
<u>DN-ECKBD</u>	DINnector terminal block end cover, gray. Package of 100. For use with DN-KBD12 series terminal blocks.	\$47.50			
<u>DN-ECKBDMN</u>	DINnector terminal block end cover, gray. Package of 10. For use with DN-KBD12 series terminal blocks.	\$6.50			
DN-EMXM1EC1	DINnector terminal block end cover, gray. Package of 25. For use with DN-EMXM1 series terminal block leftside.	\$16.50			
DN-EMXM1EC2	DINnector terminal block end cover, gray. Package of 25. For use with DN-EMXM1 series terminal block rightside.	\$16.50			
DN-EMXDVEC1	DINnector terminal block end cover, gray. Package of 25. For use with DN-EMXDV series terminal block leftside.	\$16.50			
DN-EMXDVEC2	DINnector terminal block end cover, gray. Package of 25. For use with DN-EMXDV series terminal block rightside.	\$16.50			
DN-FESEP	DINnector terminal block end cover, gray. Package of 50. For use with DN-FE and DN-DIS series terminal blocks.	\$29.00			
DN-FESEP-10	DINnector terminal block end cover, gray. Package of 10. For use with DN-FE and DN-DIS series terminal blocks.	\$6.00			
DN-QEC12	DINnector terminal block end cover, gray. Package of 50. For use with DN-Q12-A or DN-QG12 series terminal blocks.	\$23.50			
DN-QEC12MN	DINnector terminal block end cover, gray. Package of 10. For use with DN-Q12-A or DN-QG12 series terminal blocks.	\$6.00			
DN-QEC10	DINnector terminal block end cover, gray. Package of 50. For use with DN-Q10-A or DN-QG10 series terminal blocks.	\$23.50			
DN-QEC10MN	DINnector terminal block end cover, gray. Package of 10. For use with DN-Q10-A or DN-QG10 series terminal blocks.	\$6.00			
DN-QEC8	DINnector terminal block end cover, gray. Package of 50. For use with DN-Q8-A or DN-QG8 series terminal blocks.	\$28.00			
DN-QEC8MN	DINnector terminal block end cover, gray. Package of 10. For use with DN-Q8-A or DN-QG8 series terminal blocks.	\$6.50			
DN-QEC12-1-2	DINnector terminal block end cover, gray. Package of 25. For use with DN-Q12-1-2-A series terminal blocks.	\$16.50			
DN-QEC12-2-2	DINnector terminal block end cover, gray. Package of 25. For use with DN-Q12-2-2-A series terminal blocks.	\$18.00			
DN-QDEC12	DINnector terminal block end cover, gray. Package of 25. For use with DN-QD12 series terminal blocks.	\$18.00			

Spacers

Spacers are used to put more space between adjacent blocks.

DIN <i>nector</i> s Spacers								
Part Number	Description	Qty	Price					
DN-S1210	Spacer for DN-T12-A and DN-T10-A series		\$56.00					
DN-S1210MN	terminal blocks	25	\$17.50					
DN-S86	Spacer for <u>DN-T8</u> and <u>DN-T6</u> series terminal blocks		\$67.00					
DN-S86MN			\$15.50					
DN-EMXM1SPA1	Spacer for <u>DN-EMXM1</u> and <u>DN-QEMXM1</u> single-level plug-in terminal blocks		\$14.50					
DN-EMXDVSPA1	Spacer for <u>DN-EMXDV</u> and <u>DN-QEMXDV</u> double-level plug-in terminal blocks		\$16.00					
DN-FESPA	Spacer for DN-FE sockets and DN-DIS		\$29.00					
DN-FESPA-10	disconnects	10	\$6.00					

Top Covers


DIN <i>nector</i> s Top Covers								
Part Number	Description	For Use With	Qty	Price				
DN-C12	Top cover, clear, printed	DN T10 A	100	\$68.00				
DN-C12MN	electrical symbol.	<u>DN-T12-A</u>	25	\$15.50				
DN-C10	Top cover, clear, printed	DN T40 A	100	\$68.00				
DN-C10MN	electrical symbol.	<u>DN-T10-A</u>	25	\$15.50				
DN-C86	Top cover, clear, printed	DN-T8	100	\$68.00				
DN-C86MN	electrical symbol.	DN-T6	25	\$15.50				
DN-DC10	Top cover, clear, printed	DN-D10	100	\$66.00				
DN-DC10MN	electrical symbol.	טו ט-אוט	25	\$15.50				
DN-MC10	Top cover, clear, printed	DN-M10	100	\$70.00				
DN-MC10MN	electrical symbol.	טו אויט ווייט	25	\$15.50				


tTBL-68


www.automationdirect.com Terminal Blocks


DIN	DIN <i>nector</i> End Covers and Spacers Dimensions							
Part N	umber	Length mm[in]	Height mm [in]	Thickness mm [in]				
DN-EC1210	DN-EC1210MN	44 [1.73]	35 [1.38]					
DN-S1210	DN-S1210MN	55 [2.17]	44 [1.73]					
<u>DN-EC86</u>	DN-EC86MN	50 [1.97]	43 [1.69]					
DN-S86	DN-S86MN	55 [2.17]	49 [1.93]					
DN-EC4	DN-EC4MN	56 [2.21]	48 [1.89]					
DN-EC1/0	DN-EC1/0MN	62 [2.44]	60 [2.36]	1.5 [0.06]				
DN-DEC10	DN-DEC10MN	72 [2.80]	49 [1.93]					
DN-EC14	-	78 [3.08]	78 [3.08] 55 [2.17]					
DN-EC14S	_	55 [2.17]	55 [2.17] 50 [1.97]					
DN-ECM10	DN-ECM10MN	32 [1.26]	27 [1.06]					
DN-ECKBD	DN-ECKBDMN	52 [2.05]	34.5 [1.36]					
DN-EMXM1EC1	DN-EMXM1EC2							
DN-EMXDVEC1	DN-EMXDVEC2							
DN-EMXDVSPA1	DN-EMXM1SPA1		as shown on next page	•				
DN-FESPA	DN-FESPA-10							
DN-FESEP	DN-FESEP-10							
DN-QEC12	DN-QEC12MN	50 [1.97]	23 [0.9]					
DN-QEC10	DN-QEC10MN	57.4 [2.26]	33.6 [1.32]					
DN-QEC8	DN-QEC8MN	63 [2.48]	38.5 [1.52]	1 5 10 001				
DN-QEC12-1-2	-	68.5 [2.70]	28.5 [1.12]	1.5 [0.06]				
DN-QEC12-2-2	-	87.5 [3.44]	28.5 [1.12]					
DN-QDEC12	-	98 [3.86]	37 [1.46]					


 $\frac{\text{DN-EC1210}}{\text{DN-EC1/0}} \, (\text{MN}) \, \frac{\text{DN-EC36}}{\text{DN-ECKBD}} \, (\text{MN}), \, \frac{\text{DN-EC4}}{\text{DN-S1210}} \, (\text{MN}), \\ \frac{\text{DN-S86}}{\text{DN-S86}} \, (\text{MN})$






















Dimensional Drawings















55.0 mm [0.04 in] [0.04 in] [0.05 in] [0.05 in]

DN-FESEP.

DN-FESEP-10



DN-FESPA, DN-FESPA-10

Marking Tags Cross Reference Charts - Screwless

DIN <i>nector</i> Marking Tags Cross Reference - Screwless					
Block Type	DN-QL	DN-LA	DN-LT	DN-EMLBL	
DN-Q12	Х	_	_	-	
DN-Q10	Х	_	-	_	
DN-Q8	Х	_	-	_	
DN-QD12	Х	_	-	_	
DN-Q12-1-2	Х	-	-	_	
DN-Q12-1-2L	Х	_	-	_	
DN-Q12-1-2D	Х	_	_	_	
DN-QKBD	Х	_	_	_	
DN-Q12-2-2	Χ	_	_	_	
DN-Q12-2-2L	Х	_	-	_	
DN-Q12-2-2D	Х	_	-	_	
DN-QEMXM1	-	Х	X	Х	
DN-QEMXDV	_	Х	X	X	
DN-QG12	Х	_	_	_	
DN-QG10	Х	_	-	_	
DN-QG8	Х	_	-	_	
DN-QG12-1-2	Х	-	_	_	
DN-QG12-2-2	Х	_	_	_	

www.automationdirect.com Terminal Blocks tTBL-72

Marking Tags


Marking Tags DN-L Series				
Part Number	Marking Sequence	Qty	Price	
DN-L50	1-50	500	\$61.50	
DN-L100	51-100	500	\$61.50	
DN-L150	101-150	500	\$61.50	
DN-L200	151-200	500	\$61.50	
DN-L250	201-250	500	\$61.50	
DN-L300	251-300	500	\$61.50	
DN-L350	301-350	500	\$61.50	
DN-L400	351-400	500	\$61.50	
DN-L450	401-450	500	\$61.50	
DN-LB	Blank	500	\$42.00	
DN-LS	L1, L2, L3, L, N, GND, +, -, COM,COM*	500	\$61.50	

Marking Tags DN-LA Series					
Part Number	Marking Sequence	Qty	Price		
DN-LA100	1-100	500	\$61.50		
DN-LA200	101-200	500	\$61.50		
DN-LA300	201-300	500	\$61.50		
DN-LA400	301-400	500	\$61.50		
DN-LAB	Blank Tags	500	\$61.50		
DN-LAS	L1, L2, L3, L, N, GND, +, -, COM,COM*	500	\$61.50		

Marking Tags DN-LAT Series					
Part Number	Marking Sequence	Qty	Price		
DN-LAT100-A	1-100	500	\$54.00		
DN-LAT200-A	101-200	500	\$54.00		
DN-LAT300-A	201-300	500	\$54.00		
DN-LAT400-A	301-400	500	\$54.00		
DN-LAT500-A	401-500	500	\$54.00		
DN-LAT600-A	501-600	500	\$54.00		
DN-LATB-A	Blank Tags	500	\$39.00		
<u>DN-LATS-A</u>	L1, L2, L3, L, N, +,-, COM,COM*	500	\$54.00		


Marking Tags DN-QL Series					
Part Number	Marking Sequence	Qty	Price		
DN-QL100	1-100	500	\$47.00		
DN-QL200	101-200	500	\$47.00		
DN-QL300	201-300	500	\$47.00		
DN-QL400	301.400	500	\$47.00		
DN-QL500	401-500	500	\$47.00		
DN-QLB	Blank Tags	500	\$39.50		
DN-QLS	L1, L2, L3, L, N, +,-, COM,COM*	500	\$54.00		

Dimensions



- The marking sequence of 50 tags (i.e. 101-150) is printed 10 times in each package of 500
- The DN-L tags fit all DINnectors 6mm wide and wider
- There will be a gap between tags on blocks wider than 6mm.
- Material: Thermoplastic with heat embossed black print.

Dimensions




- The marking sequence of 100 tags (i.e. 1-100) is printed five times in each package of 500.
- The DN-LA tags fit all DINnectors 5mm wide and wider. There will be a gap between tags on blocks wider than 5mm.
- Material: Thermoplastic with heat embossed black print.

Dimensions



- The marking sequence of 500 tags (i.e. 1-100) is printed five times in each package of 500.
- Material: Thermoplastic with heat embossed black print.

Dimensions



- The marking sequence of 500 (i.e. 1-100) is printed five times in each package of 500.
- Material: Thermoplastic with heat embossed black print.

Marking Tags continued


	Marking Tags DN-LT Se	ries	
Part Number	Marking Sequence	Qty	Price
DN-LT15	1-5	100	\$11.00
<u>DN-LT60</u>	6-0	100	\$11.00
<u>DN-LT1</u>	1	100	\$11.00
DN-LT2	2	100	\$11.00
DN-LT3	3	100	\$11.00
DN-LT4	4	100	\$11.00
DN-LT5	5	100	\$11.00
DN-LT6	6	100	\$11.00
DN-LT7	7	100	\$11.00
DN-LT8	8	100	\$11.00
DN-LT9	9	100	\$11.00
DN-LT0	0	100	\$11.00
DN-LTBLNK	Unprinted	100	\$11.00
DN-LTA	A	100	\$11.00
DN-LTB	В	100	\$11.00
DN-LTC	С	100	\$11.00
<u>DN-LTD</u>	D	100	\$11.00
DN-LTE	E	100	\$11.00
DN-LTF	F	100	\$11.00
DN-LTG	G	100	\$11.00
DN-LTH	Н	100	\$11.00
DN-LTI	1	100	\$11.00
DN-LTJ	J	100	\$11.00
DN-LTK	K	100	\$11.00
<u>DN-LTL</u>	L	100	\$11.00
<u>DN-LTM</u>	M	100	\$11.00
<u>DN-LTN</u>	N	100	\$11.00
_	-	-	-
<u>DN-LTP</u>	Р	100	\$11.00
<u>DN-LTQ</u>	Q	100	\$11.00
<u>DN-LTR</u>	R	100	\$11.00
<u>DN-LTS</u>	S	100	\$11.00
DN-LTT	T	100	\$11.00
DN-LTU	U	100	\$11.00
DN-LTV	V	100	\$11.00
DN-LTW	W	100	\$11.00
DN-LTX	X	100	\$11.00
DN-LTY	Y	100	\$11.00
DN-LTZ	Z	100	\$11.00
DN-LTGND	(a)	100	\$11.00
DN-LTPOS	+	100	\$11.00
DN-LTNEG	-	100	\$11.00
DN-LTAC	~	100	\$11.00
DN-LTDC	=	100	\$11.00



- These marking tags allow the flexibility of creating custom marking sequences on site.
- The DN-M series supports a maximum of three digits (tags), while other DINnectors support up to four digits (tags).
- Material: Thermoplastic with heat embossed black print.

DN-MTA marking tag adapter

DN-MTA dimensions



Part Number	Description		Price
DN-MTA	Marking tag adapter holds up to six DN-LT tags	50	\$16.00

Note: <u>DN-MTA</u> adapter does not fit <u>DN-T12-A</u> terminal blocks.

www.automationdirect.com

Terminal Marking Accessories








DN-EMLBL3

Part Number	Description	For Use With	Qty	Price
DN-EMLBL1	Blank labels	DN-EMPEG1 pin protectors for DN-xEMXxx plug-in terminal blocks	100	\$10.00
DN-EMLBL2	Labels printed 1 – 12		100	\$14.50
DN-EMLBL3	Labels printed 13 – 24		100	\$14.50

Marking Pen – for terminal and wire marking tags

- Permanent
- Smudge-proof
- Waterproof
- Weatherproof
- Lightfast (won't fade)
- Dries in seconds (excellent for left-handed users)
- Dry-safe (pen can be left uncapped for days without drying out)
- Low odor ink





Marking pen

Wire Marking Accessories



DN-WM-x wire tag holders

Part Number	Description	For Use With	Qty	Price
DN-WMTAG1	Wire tag – blank	all DN-WM-x wire tag holders	525	\$66.00
<u>DN-WM-1</u>	Wire tag holder, clear, 12mm length, 0.051–0.118 in diameter; for 22–16 AWG wire	DN-WMTAG1	200	\$14.00
DN-WM-2	Wire tag holder, clear, 12mm length, 0.098–0.196 in diameter; for 16-11 AWG wire		200	\$14.00
DN-WM-3	Wire tag holder, clear, 12mm length, 0.157–0.393 in diameter; for 13–5 AWG wire		100	\$9.00
DN-WM-4	Wire tag holder, clear, 12mm length, 0.314–0.629 in diameter; for 5AWG wire		100	\$8.50

www.automationdirect.com Terminal Blocks tTBL-75