

NEMA 4, 12 and 13 Single-Door Wall Mount with 3-Point Handle (Ultimate Series)



Application

Designed to house and protect electrical and electronic components from harsh, dirty environments. For use in installations where dust, dirt, oil, water or other contaminants are present. Streamlined styling, 3-point latching with heavy-duty handle, and an attractive, durable finish complement any high-tech electronic equipment.



- Doors are interchangeable and easily removable [open to 90° to remove door]
- 3-point keylocking/padlocking combo handle
- Mounting holes in rear of enclosure

Finish

- ANSI 61 gray light-textured [N41212xxxxC] inside and outside over phosphatized surfaces
- Painted steel subpanels are white polyester powder over phosphatized surfaces
- Galvanized and stainless subpanels are a conductive finish [unpainted]

Construction

- Bodies and doors fabricated from 14 gauge steel
- Plasma welded seams
- Polyurethane poured in place gasket
- Collar studs provided for mounting optional subpanels
- Grounding provisions provided
- Concealed hinges
- Increased tub openings to accommodate larger size [optional] subpanels
- Optional subpanels must be ordered separately
- Swing-out panel kits WAJCDFK and WANADFK will not work with these enclosures

Listings

- UL 508, Types 4, 12, and 13 [UL file E64791]
- CSA Certified, Types 4, 12, and 13 [CSA file LL66078]
- Meets NEMA/EEMAC Types 4, 12 and 13 requirements
- Wall mounting brackets required to maintain UL/CSA external mounting requirements.



Enclosure Shipping Schedule		
Same day	1 - 7 days	1 -10 days

Color indicates shipping lead time in business days.

FOR CURRENT LISTINGS, PLEASE SEE WWW.AUTOMATIONDIRECT.COM

NEMA 4, 12 and 13 Single-Door Wall Mount with 3-Point Handle (Ultimate Series)						
ANSI 61 Gray Light-Textured	Price	Enclosure Size HxWxD	C	Painted Steel Subpanel	Stainless Steel Subpanel	Galvanized Subpanel
N4122416063PTC	\$304.00	24x16x6 [610x406x152]	12 [305]	NP2416C	NP2416SSC	NP2416CG
N4122416083PTC	\$311.00	24x16x8 [610x406x203]	12 [305]	NP2416C	NP2416SSC	NP2416CG
N4122420063PTC	\$325.00	24x20x6 [610x508x152]	12 [305]	NP2420C	NP2420SSC	NP2420CG
N4122420083PTC	\$333.00	24x20x8 [610x508x203]	12 [305]	NP2420C	NP2420SSC	NP2420CG
N4122420123PTC	\$371.00	24x20x12 [610x508x305]	12 [305]	NP2420C	NP2420SSC	NP2420CG
N4122424063PTC	\$346.00	24x24x6 [610x610x152]	12 [305]	NP2424C	NP2424SSC	NP2424CG
N4122424083PTC	\$354.00	24x24x8 [610x610x203]	12 [305]	NP2424C	NP2424SSC	NP2424CG
N4122424123PTC	\$387.00	24x24x12 [610x610x305]	12 [305]	NP2424C	NP2424SSC	NP2424CG
N4122424163PTC	\$429.00	24x24x16 [610x610x406]	12 [305]	NP2424C	NP2424SSC	NP2424CG
N4122424203PTC	\$462.00	24x24x20 [610x610x508]	12 [305]	NP2424C	NP2424SSC	NP2424CG
N4122430083PTC	\$387.00	24x30x8 [610x762x203]	12 [305]	NP3024C	NP3024SSC	NP3024CG
N4123020083PTC	\$370.00	30x20x8 [762x508x203]	15 [381]	NP3020C	-	NP3020CG

Note: Subpanels must be ordered separately. Dimensions in inches [millimeters]; letters in table correspond to letters on dimensional drawings.

NEMA 4, 12 and 13 Single-Door Wall Mount with 3-Point Handle (Ultimate Series)




Enclosure Shipping Schedule		
Same day	1 - 7 days	1 - 10 days
Color indicates shipping lead time in business days.		

NEMA 4, 12 and 13 Single-Door Wall Mount with 3-Point Handle (Ultimate Series) – [cont.]						
ANSI 61 Gray Light-Textured	Price	Enclosure Size HxWxD	C	Painted Steel Subpanel	Stainless Steel Subpanel	Galvanized Subpanel
N4123024083PTC	\$387.00	30x24x8 [762x610x203]	15 [381]	NP3024C	NP3024SSC	NP3024CG
N4123024123PTC	\$423.00	30x24x12 [762x610x305]	15 [381]	NP3024C	NP3024SSC	NP3024CG
N4123024203PTC	\$508.00	30x24x20 [762x610x508]	15 [381]	NP3024C	NP3024SSC	NP3024CG
N4123030083PTC	\$425.00	30x30x8 [762x762x203]	15 [381]	NP3030C	NP3030SSC	NP3030CG
N4123030123PTC	\$465.00	30x30x12 [762x762x305]	15 [381]	NP3030C	NP3030SSC	NP3030CG
N4123624083PTC	\$419.00	36x24x8 [914x610x203]	18 [457]	NP3624C	NP3624SSC	NP3624CG
N4123624123PTC	\$471.00	36x24x12 [914x610x305]	18 [457]	NP3624C	NP3624SSC	NP3624CG
N4123630083PTC	\$463.00	36x30x8 [914x762x203]	18 [457]	NP3630C	NP3630SSC	NP3630CG
N4123630123PTC	\$508.00	36x30x12 [914x762x305]	18 [457]	NP3630C	NP3630SSC	NP3630CG
N4123630163PTC	\$566.00	36x30x16 [914x762x406]	18 [457]	NP3630C	NP3630SSC	NP3630CG
N4123630203PTC	\$612.00	36x30x20 [914x762x508]	18 [457]	NP3630C	NP3630SSC	NP3630CG
N4123636083PTC	\$508.00	36x36x8 [914x914x203]	18 [457]	NP3636C	NP3636SSC	NP3636CG
N4123636123PTC	\$556.00	36x36x12 [914x914x305]	18 [457]	NP3636C	NP3636SSC	NP3636CG
N4124024123PTC	\$526.00	40x24x12 [1016x610x305]	20 [508]	NP4024C	–	NP4024CG
N4124236123PTC	\$605.00	42x36x12 [1066x914x305]	21 [533]	NP4236C	NP4236SSC	NP4236CG
N4124824123PTC	\$546.00	48x24x12 [1219x610x305]	24 [610]	NP4824C	–	NP4824CG
N4124836123PTC	\$653.00	48x36x12 [1219x914x305]	24 [610]	NP4836C	NP4836SSC	NP4836CG
N4124836163PTC	\$710.00	48x36x16 [1219x914x406]	24 [610]	NP4836C	NP4836SSC	NP4836CG
N4126036123PTC	\$750.00	60x36x12 [1524x914x305]	30 [762]	NP6036C	NP6036SSC	NP6036CG

Note: Subpanels must be ordered separately. Dimensions in inches [millimeters]; letters in table correspond to letters on dimensional drawings.

Dimensions
in [mm]



- NOTES:**
- 1. TWO HINGES PROVIDED WHEN H<36".
 - THREE HINGES PROVIDED WHEN H=36" OR GREATER.
 - FOUR HINGES PROVIDED WHEN H=48" OR GREATER.

See our website: www.AutomationDirect.com for complete engineering drawings.

Enclosure Subpanels




Subpanels for Ultimate Series Wall Mount Enclosures

- 12 gauge steel
- Subpanels with dimensions 30" x 30" and larger are flanged on all sides. Smaller subpanels are flanged on two sides
- Painted steel subpanels are white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)



Dimensions in [mm]



Panels listed fit all styles of N412 Ultimate Series wall mount enclosures, including slope top and disconnect enclosures.

NOTE: NPxxxxC subpanels will not fit in older NEMA 4/12 enclosures (purchased prior to 3-23-05) that do not have a C suffix. For example: Subpanel NP1212C will not fit enclosures N412121206 or N412121206SS.

Enclosure Shipping Schedule	
Same day	1 - 7 days
Color indicates shipping lead time in business days.	

Subpanels for Ultimate Series Wall Mount Enclosures							
Painted Steel	Price	Galvanized	Price	304 Stainless Steel	Price	Nominal Enclosure Size HxW*	Subpanel Size AxB
NP1212C	\$16.00	NP1212CG	\$16.00	—		12 x 12	10.20 x 10.20 [259 x 259]
NP1612C	\$19.50	NP1612CG	\$19.50	NP1612SSC	\$101.00	16 x 12	14.20 x 10.20 [361 x 259]
NP1616C	\$26.50	NP1616CG	\$26.50	NP1616SSC	\$70.00	16 x 16	14.20 x 14.20 [361 x 361]
NP2016C	\$26.50	NP2016CG	\$26.50	NP2016SSC	\$70.00	16 x 20 20 x 16	18.20 x 14.20 [462 x 361]
NP2020C	\$33.00	NP2020CG	\$33.00	NP2020SSC	\$93.00	20 x 20	18.20 x 18.20 [462 x 462]
NP2416C	\$37.00	NP2416CG	\$37.00	NP2416SSC	\$105.00	24 x 16	22.20 x 14.20 [564 x 361]
NP2420C	\$45.00	NP2420CG	\$45.00	NP2420SSC	\$119.00	24 x 20	22.20 x 18.20 [564 x 462]
NP2424C	\$47.50	NP2424CG	\$47.50	NP2424SSC	\$128.00	24 x 24	22.20 x 22.20 [564 x 564]
NP3020C	\$60.00	NP3020CG	\$60.00	—		30 x 20	28.20 x 18.20 [716 x 462]
NP3024C	\$57.00	NP3024CG	\$57.00	NP3024SSC	\$155.00	30 x 24	28.20 x 22.20 [716 x 564]
NP3030C	\$97.00	NP3030CG	\$97.00	NP3030SSC	\$276.00	30 x 30	28.20 x 28.20 [716 x 716]
NP3624C	\$75.00	NP3624CG	\$75.00	NP3624SSC	\$213.00	36 x 24	34.20 x 22.20 [869 x 564]
NP3630C	\$99.00	NP3630CG	\$99.00	NP3630SSC	\$263.00	36 x 30	34.20 x 28.20 [869 x 716]
NP3636C	\$117.00	NP3636CG	\$117.00	NP3636SSC	\$318.00	36 x 36	34.20 x 34.20 [869 x 869]
NP4024C	\$99.00	NP4024CG	\$99.00	—		40 x 24	38.20 x 22.20 [970 x 564]
NP4230C	\$126.00	—		—		42 x 32	40.20 x 28.20 [1021 x 716]
NP4236C	\$148.00	NP4236CG	\$148.00	NP4236SSC	\$411.00	42 x 36	40.20 x 34.20 [1021 x 869]
NP4824C	\$107.00	NP4824CG	\$107.00	—		48 x 24	46.20 x 22.20 [1173 x 564]
NP4836C	\$168.00	NP4836CG	\$168.00	NP4836SSC	\$446.00	48 x 36	46.20 x 34.20 [1173 x 869]
NP6036C	\$188.00	NP6036CG	\$188.00	NP6036SSC	\$535.00	60 x 36	58.20 x 34.20 [1478 x 869]

Notes: Dimensions in inches [millimeters].
 Letters in table correspond to letters on dimensional drawing.
 *Disconnect enclosures will be up to 2 inches [51mm] wider than width dimensions in this table.

Enclosure Accessories - Miscellaneous



Vapor Capsule

Carrying Handle



Carrying Handle	Price	Description	Wt.
HW-CARRYINGHANDLE	\$17.50	Non-metallic black handle, for use on Hubbell-Wiegmann non-metallic enclosures.	2 oz.



Vapor Capsule	Price	Description	Wt.
HW-C12	\$15.00	Non-toxic vapor emitted from the capsule passivates the metal surfaces on the interior of the enclosure against atmospheric corrosion for up to one year by reducing the electro-chemical activity of the metal surfaces. Installs easily with a self-adhesive strip.	1 oz.

Strip Gasket



Enclosure Shipping Schedule	
Same day	1 - 14 days
Color indicates shipping lead time in business days.	

Strip Gasket	Price	Description	Wt.
WGAS51634	\$16.00	Hubbell-Wiegmann strip gasket, replacement, self-adhesive, microcell urethane foam, 5/16 inch thick x 3/4 inch wide x 10 ft long roll. For gasket replacement on Hubbell-Wiegmann wall-mount NEMA 12, 4 & 4X enclosures.	7oz.
WGAS3834	\$16.00	Hubbell-Wiegmann strip gasket, replacement, self-adhesive, closed cell sponge rubber, 3/8 inch thick x 3/4 inch wide x 10 ft long roll. For gasket replacement on Hubbell-Wiegmann floor-mount and freestanding NEMA 12, 4 & 4X enclosures.	7oz.




Locking Protective Cover



Dimensions

in [mm]



Features

- Packaged multi-purpose protective cover
- Locking door
- Weather and UV resistant (UL 94-HB)
- IP 20 Protection Class
- Includes mounting screws

Locking Protective Cover	Description	Price
086110-00	Stego multi-purpose protective cover with locking door, weather and UV resistant (UL 94-HB), IP20 protection class. Includes mounting screws and keys.	\$37.00

See our website: www.AutomationDirect.com for complete engineering drawings.