

AD Series Class 8 Solid State Relays



AD-SSR810-AC-28Z
shown

The Class 8 solid state relays offer energy efficient current switching in a slim housing ideal for space-saving applications.

Switching types include Zero Cross for resistive AC loads where the output energizes/de-energizes when control voltage nears zero, and Random for AC loads where the output switches instantaneously with the actual voltage.

All Class 8 solid state relays use an SCR, which is suited for AC load applications, as the switching device .

Features

- Internal heat sink
- Finger-safe terminals
- DIN and panel mounting
- Optically coupled circuit

Class 8 Solid State Relay Selection Guide

Part Number	Price	Configuration	Input Voltage	Load Voltage	Switching Device	Contact Rating
AD-SSR810-AC-28Z	\$25.50	SPST-NO	90 to 280 VAC	24 to 280 VAC	SCR	10A
AD-SSR810-AC-28R	\$27.75		3 to 32 VDC			
AD-SSR810-DC-28Z	\$20.25	SPST-NC	3 to 32 VDC			
AD-SSR810-DC-28R	\$20.50					
AD-SSR810-DC-28RN	\$21.75					
AD-SSR810-AC-48Z	\$25.50	SPST-NO	90 to 280 VAC	48 to 480 VAC		
AD-SSR810-AC-48R	\$32.00		3 to 32 VDC			
AD-SSR810-DC-48Z	\$20.75		90 to 280 VAC	48 to 600 VAC		
AD-SSR810-DC-48R	\$22.75		3 to 32 VDC			
AD-SSR810-AC-60Z	\$32.25					
AD-SSR810-AC-60R	\$33.00					
AD-SSR810-DC-60Z	\$24.50					
AD-SSR810-DC-60R	\$24.50					


AD Series Class 8 Solid State Relays

Specifications														
Part Number	AD-SSR810-AC-28Z	AD-SSR810-AC-28R	AD-SSR810-DC-28Z	AD-SSR810-DC-28R	AD-SSR810-DC-28RN	AD-SSR810-AC-48Z	AD-SSR810-AC-48R	AD-SSR810-DC-48Z	AD-SSR810-DC-48R	AD-SSR810-AC-60Z	AD-SSR810-AC-60R	AD-SSR810-DC-60Z	AD-SSR810-DC-60R	
Input Characteristics														
Control Voltage Range	90 to 280 VAC		3 to 32 VDC			90 to 280 VAC		3 to 32 VDC		90 to 280 VAC		3 to 32 VDC		
Typical Input Current	12mA		16mA			12mA		16mA		12mA		16mA		
Must Release Voltage	10VAC		1VDC			10VAC		1VDC		10VAC		1VDC		
Reverse Polarity Protection	-		Yes			-		Yes		-		Yes		
Switching Type	Zero Cross	Random	Zero Cross	Random	Random	Zero Cross	Random	Zero Cross	Random	Zero Cross	Random	Zero Cross	Random	
Input Indicator	Green LED status lamp													
Output Characteristics														
Load Voltage Range	24 to 280 VAC					48 to 480 VAC				48 to 600 VAC				
Rated Load Current	10A													
Maximum Off-State Voltage dv/dt	500V/μs				200V/μs		350V/μs				200V/μs			
Minimum Load Current	50mA													
Non-Repetitive Surge Current (1 Cycle)	500A													
Maximum Off State Leakage current (RMS)	10mA													
Typical On-State Voltage Drop (RMS)	1.25 VAC													
Maximum I²T for Fusing (A²Sec)	1250					850				600				
RMS Overload Current/Sec	24A													
Contact Configuration	SPST N.O.				SPST N.C.		SPST N.O.							
Maximum Turn-On Time	8.3 ms													
Maximum Turn-Off Time	8.3 ms													
General Characteristics														
Dielectric Strength (Terminal to Chassis)	2500VAC													
Thermal Resistance (Junction to Case)	0.66°C/W (33.19°F/W)													
Internal Heat Sink	4°C/W (39.2°F/W)													
Operating Temperature Range	-30°C to 80°C (-22°F to 176°F)													
Storage Temperature Range	-40°C to 100°C (-40°F to 212°F)													
Weight	127g (4.1 oz)													
Terminal Torque	7.1 lb-in (0.8 N-m) max													
Terminal Wire Capacity	14AWG (2.5 mm ²) max													
Agency Approvals and Standards	UL file # E222847, CE, CSA, RoHS													
Environmental Protection	IP20													


AD Series Class 8 Solid State Relays Dimensions & Derating Charts

Dimensions


inches [mm]



Wiring Diagram



Derating Chart



* Indicates current cut-off.

Note: A minimum spacing of 17.5 mm (0.7 in) between adjacent AD Series Class 8 relays is required in order to achieve the maximum ratings. A 0mm spacing will result in a 50% reduction in the de-rating.

AD Series Class 8 Solid State Relays for Hazardous Locations

The Class 8 Hazardous Location series is similar to the Class 8 series with the added feature of being approved for hazardous locations (Class 1, Div. 2, Groups A, B, C, D).

Switching types include DC switching for DC loads and Zero Cross switching for resistive AC loads where the output energizes/de-energizes when the control voltage nears zero.

Switching devices include MOSFET for DC loads and SCR for AC loads.

Features

- For use in hazardous locations (Class I, Div 2, Groups A, B, C, D)
- Internal Heat Sink
- Finger-safe terminals
- DIN and panel mounting
- Optically coupled circuit



AD-HSSR808-DC-15 shown

Class 8 Hermetically-sealed Solid State Relay Selection Guide						
Part Number	Price	Switching Device	Input Voltage	Load Voltage	Configuration	Contact Rating
AD-HSSR815-DC-05	\$56.75	MOSFET	3.5 to 32 VDC	3 to 50 VDC	SPST N.O.	15A
AD-HSSR808-DC-15	\$55.25			3 to 150 VDC		8A
AD-HSSR810-AC-28	\$56.00	SCR	90 to 280 VAC	24 to 280 VAC		10A
AD-HSSR810-DC-28	\$54.50		3 to 32 VDC			
AD-HSSR810-AC-48	\$56.75		90 to 280 VAC	48 to 480 VAC		
AD-HSSR810-DC-48	\$55.25		3 to 32 VDC			
AD-HSSR810-AC-60	\$58.58		90 to 280 VAC	48 to 600 VAC		
AD-HSSR810-DC-60	\$56.75		3 to 32 VDC			


AD Series Class 8 Solid State Relays for Hazardous Locations

Specifications								
Part Number	AD-HSSR815-DC-05	AD-HSSR808-DC-15	AD-HSSR810-AC-28	AD-HSSR810-DC-28	AD-HSSR810-AC-48	AD-HSSR810-DC-48	AD-HSSR810-AC-60	AD-HSSR810-DC-60
Input Characteristics								
Control Voltage Range	3.5 to 32 VDC	90 to 280 VAC	3 to 32 VDC	90 to 280 VAC	3 to 32 VDC	90 to 280 VAC	3 to 32 VDC	90 to 280 VAC
Typical Input Current	12mA	12mA	16mA	12mA	16mA	12mA	16mA	16mA
Must Release Voltage	1VDC	10VAC	1VDC	10VAC	1VDC	10VAC	10VAC	1VDC
Reverse Polarity Protection	Yes	—	Yes	—	Yes	—	—	Yes
Nominal Input Impedance	Current Limiter	16 to 25 k Ω	Current Limiter	16 to 25 k Ω	Current Limiter	16 to 25 k Ω	Current Limiter	Current Limiter
Switching Type	DC		Zero Cross					
Input Indicator	Green LED status lamp							
Output Characteristics								
Load Voltage Range	3 to 50 VDC	3 to 150 VDC	24 to 280 VAC	48 to 480 VAC	48 to 600 VAC			
Rated Load Current	15A	8A	10A					
Maximum Off-State Voltage dv/dt	—	—	500 V/ μ s	350 V/ μ s	500 V/ μ s			
Minimum Load Current	20mA		50mA					
Non-Repetitive Surge Current (1 Cycle)	50A	35A	500A					
Maximum Off State Leakage current (RMS)	0.25 mA		10mA					
Typical On-State Voltage Drop (RMS)	N/A		1.25 VAC					
Maximum I²T for Fusing (A²Sec)	—	—	1250	850	600			
RMS Overload Current/Sec	24A	17A	24A					
Maximum Turn-On Time	5ms		8.3 ms					
Maximum Turn-Off Time	5ms		8.3 ms					
General Characteristics								
Dielectric Strength Terminals to Chassis	2500 V rms							
Thermal Resistance Junction to Case	1.4°C/W (34.52°F/W)	0.5°C/W (32.9°F/W)	0.66°C/W (33.19°F/W)					
Internal Heat Sink	4.0°C/W (39.2°F/W)							
Operating Temperature Range	-30 to 80°C (-22 to 176°F) (derating applies)							
Storage Temperature Range	-40 to 100°C (-40 to 212°F)							
Weight	127.1 g (4.1 oz)							
Terminal Torque	7.1 in-lb (0.8 N-m) maximum							
Terminal Wire Capacity	14AWG (2.5mm ²) max							
Agency Approvals and Standards	UL file # E344125, CE, RoHS							
Environmental Protections	IP20 (Class I, Div. 2 Groups A, B, C, D)							


AD Series Class 8 Solid State Relays for Hazardous Locations Dimensions and Derating Charts

Dimensions


inches [mm]



Wiring Diagram



Derating Chart



Note: A minimum spacing of 17.5 mm (0.7 in) between adjacent AD Series Class 8 relays is required in order to achieve the maximum ratings. A 0mm spacing will result in a 50% reduction in the de-rating.