



# STEGO INC. STEGOJET Compact Fans



019250-00



Range of Rotation

## Applications

The STEGOJET is a compact, powerful built-in fan. It is designed for precise cooling of heat sources and for maximum rotation range with an air output in almost any direction. The dual clip system (two clips at a 90° angle) allows four different positions on a DIN rail, while the hinge in the housing can be moved at a 40° angle. Additionally, the airflow at the air outlet can be directed at a 45° angle and the air duct can be turned 360°.

## Features

- Prevents heat pockets
- Wide voltage range
- Compact design
- Quick connection
- Panel or DIN rail mounting




| StegoJet Fan Specifications          |  |
|--------------------------------------|--|
| <b>Axial Fan, Ball Bearing</b>       | Service life 40,000h at 140°F (60°C) and 90% RH  |
| <b>Power Consumption</b>             | 4W   |
| <b>Connection</b>                    | 2-pole dual cage clamp for solid wire – 14AWG (2.5 mm <sup>2</sup> )<br>stranded wire (with wire end ferrule) – 16AWG (1.5 mm <sup>2</sup> ) |
| <b>Housing</b>                       | Plastic, UL 94V-0, black   |
| <b>Mounting</b>                      | Clip for 35mm DIN rail, EN 60715 or<br>M5 screws and washers (not included) – torque 2 N·m max.  |
| <b>Mounting Position</b>             | Variable   |
| <b>Operating/Storage Temperature</b> | +14° to +140°F (-10° to +60°C) /<br>-22° to +158°F (-30° to 70°C)  |
| <b>Operating/Storage Humidity</b>    | Max. 90% RH (non-condensing)   |
| <b>Protection Class</b>              | II (double insulated)  |
| <b>Protection Type</b>               | IP20   |
| <b>Approvals</b>                     | CE, UL Recognized File No. E234324, RoHS compliant   |

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page at [www.AutomationDirect.com](http://www.AutomationDirect.com)


| Part Number | Price   | Description       | Operating Voltage                                  | Air Flow, Free Blowing               | Weight (approx.) |
|-------------|---------|-------------------|--|--------------------------------------|------------------|
| 019250-00   | \$78.00 | DIN rail mounting | 100-240V AC, 50/60 Hz<br>(min. 90VAC, max. 265VAC) | 16.2 cfm<br>(27.6 m <sup>3</sup> /h) | 7oz<br>(198g)    |
| 019250-01   | \$78.00 | Panel mounting    |  |                                      |                  |

## Dimensions: Inches [mm]

### DIN rail mounting



### Panel mounting



Please see our website [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings.