

# Stride Unmanaged Industrial Ethernet Switches

Unmanaged Switches offer:

- Reliable connectivity
- Industrially hardened
- Simple installation

For detailed specifications on all models, see following pages



|  |                                    | SE Series         | SE2 Series DIN Rail | SE2 Series IP65   |
|--|------------------------------------|-------------------|---------------------|-------------------|
| <b>Price</b>                           |                                    |                   |                     |                   |
|  |                                    | starting at \$103 | starting at \$75    | starting at \$299 |
| <b>Broadcast Storm Protection</b>      |                                    |                   |                     |                   |
|  |                                    | —                 | ✓                   | —                 |
| <b>Industrial Temperature Ranges</b>   |                                    |                   |                     |                   |
|  | <i>Standard Temp</i>               | -10 to +60°C      | -10 to +60°C        | —                 |
|  | <i>Wide Temp</i>                   | -40 to +85°C      | -40 to +75°C        | -40 to +75°C      |
| <b>Port Connectivity</b>               |                                    |                   |                     |                   |
|  | <i>Port Count</i>                  | 2 to 9            | 2 to 18             | 5, 8              |
|  | <i>RJ45 Port Speed</i>             | up to 100 Mbps    | up to 1000 Mbps     | —                 |
|  | <i>M12 Port Speed</i>              | —                 | —                   | up to 100 Mbps    |
|  | <i>Fiber Optic Ports</i>           | ✓                 | ✓                   | —                 |
|  | <i>PoE+ Ports</i>                  | —                 | ✓                   | —                 |
|  | <i>SFP Ports</i>                   | —                 | ✓                   | —                 |
| <b>Mounting</b>                        |                                    |                   |                     |                   |
|  | <i>DIN Rail Mount</i>              | ✓                 | ✓                   | —                 |
|  | <i>Panel Mount</i>                 | ✓                 | ✓                   | ✓                 |
| <b>Input Power</b>                     |                                    |                   |                     |                   |
|  | <i>Redundant Power Inputs</i>      | ✓                 | ✓                   | ✓                 |
|  | <i>Reverse Polarity Protection</i> | ✓                 | ✓                   | ✓                 |
|  | <i>Power LED</i>                   | ✓                 | ✓                   | ✓                 |
| <b>Agency Approvals</b>                |                                    |                   |                     |                   |
|  | <i>UL508 or UL61010</i>            | ✓                 | ✓                   | ✓                 |
|  | <i>Haz Loc-Class 1 Div 2</i>       | ✓                 | ✓                   | —                 |
|  | <i>IECEX</i>                       | ✓                 | —                   | —                 |
|  | <i>ATEX Zone 2</i>                 | ✓                 | —                   | —                 |
|  | <i>CE</i>                          | ✓                 | ✓                   | ✓                 |
|  | <i>EN50155 &amp; EN50121</i>       | —                 | —                   | ✓                 |
| <b>Warranty</b>                        |                                    |                   |                     |                   |
|  |                                    | 2 years           | 5 years             | 5 years           |
| <b>Activity, Link &amp; Speed LEDs</b> |                                    |                   |                     |                   |
|  |                                    | ✓                 | ✓                   | ✓                 |