

# Stride<sup>®</sup> Unmanaged Industrial Ethernet Switches

## Unmanaged Switches offer:

- Reliable connectivity
- Industrially hardened
- Simple installation

For detailed specifications on all models, see following pages



		SE Series	SE2 Series DIN Rail	SE2 Series IP65
<b>Price</b>				
		starting at \$103	starting at \$75	starting at \$299
<b>Broadcast Storm Protection</b>				
		—	✓	—
<b>Industrial Temperature Ranges</b>				
	<i>Standard Temp</i>	-10 to +60°C	-10 to +60°C	—
	<i>Wide Temp</i>	-40 to +85°C	-40 to +75°C	-40 to +75°C
<b>Port Connectivity</b>				
	<i>Port Count</i>	2 to 9	2 to 18	5, 8
	<i>RJ45 Port Speed</i>	up to 100 Mbps	up to 1000 Mbps	—
	<i>M12 Port Speed</i>	—	—	up to 100 Mbps
	<i>Fiber Optic Ports</i>	✓	✓	—
	<i>PoE+ Ports</i>	—	✓	—
	<i>SFP Ports</i>	—	✓	—
<b>Mounting</b>				
	<i>DIN Rail Mount</i>	✓	✓	—
	<i>Panel Mount</i>	✓	✓	✓
<b>Input Power</b>				
	<i>Redundant Power Inputs</i>	✓	✓	✓
	<i>Reverse Polarity Protection</i>	✓	✓	✓
	<i>Power LED</i>	✓	✓	✓
<b>Agency Approvals</b>				
	<i>UL508 or UL61010</i>	✓	✓	✓
	<i>Haz Loc—Class 1 Div 2</i>	✓	✓	—
	<i>IECEX</i>	✓	—	—
	<i>ATEX Zone 2</i>	✓	—	—
	<i>CE</i>	✓	✓	✓
	<i>EN50155 &amp; EN50121</i>	—	—	✓
<b>Warranty</b>				
		2 years	5 years	5 years
<b>Activity, Link &amp; Speed LEDs</b>				
		✓	✓	✓