

NEMA 4, 12, and 13 Extra-Deep Wall-Mount Pushbutton



Applications

Designed to offer protection for oil-tight pushbuttons, switches, and pilot lights from dust, water, dirt and oil.

Construction

- 16 gauge carbon steel.
- Continuously-welded seams.
- Captivated cover screws thread into sealed wells.
- 4-way pushbutton holes accept all brands of oil-tight pushbuttons, switches and pilot lights
- Hole diameter is 1.20in [30.5 mm] or 0.87in [22.5 mm].
- Poured-in-place oil- and water-resistant gasket.
- Welded mounting provision top and bottom of back.

Finish

- ANSI 61 gray powder coated inside and out.

Listings

- NEMA Type 4, 12 and 13
- cULus Listed Type 4 and 12 [File E69392]
- IEC 60529 IP66



Shipping Schedule	
Same day	1 - 15 days
Color indicates shipping lead time in business days.	

NEMA 4, 12, and 13 Extra-Deep Wall-Mount Pushbutton					
22mm	30mm	Price	Size HxWxD	Holes	Drawing Link
SCE-1PBXI	SCE-1PBX	\$60.00	4.31 x 4.31 x 4.91 [109 x 109 x 125]	1	PDF
SCE-2PBXI	SCE-2PBX	\$69.00	6.31 x 4.31 x 4.91 [160 x 109 x 125]	2	PDF
SCE-3PBXI	SCE-3PBX	\$78.00	8.31 x 4.31 x 4.91 [211 x 109 x 125]	3	PDF
SCE-4PBXI	SCE-4PBX	\$86.00	10.31 x 4.31 x 4.91 [262 x 109 x 125]	4	PDF
SCE-4SPBXI	SCE-4SPBX	\$87.00	7.56 x 6.56 x 4.91 [192 x 167 x 125]	4	PDF
SCE-6PBXI	SCE-6PBX	\$101.00	9.81 x 6.56 x 4.91 [249 x 167 x 125]	6	PDF
SCE-6PBXVLI	SCE-6PBXVL	\$101.00	15.06 x 4.31 x 4.91 [383 x 109 x 125]	6	PDF
SCE-9PBXI	SCE-9PBX	\$114.00	9.81 x 8.81 x 4.91 [249 x 224 x 125]	9	PDF
SCE-10PBXI	SCE-10PBX	\$124.00	14.31 x 6.56 x 4.91 [363 x 167 x 125]	10	PDF
SCE-12PBXI	SCE-12PBX	\$131.00	12.06 x 8.81 x 4.91 [306 x 224 x 125]	12	PDF

Note: Dimensions in inches (millimeters)

NEMA 4, 12, and 13 Extra-Deep Wall-Mount Pushbutton



Your Enclosure Source®

Dimensions

