

NEMA 4, 4X, 12, and 13 30mm Stainless Steel Wall-Mount Pushbutton



Applications

Designed to house standard pushbuttons, switches and pilot lights in wet and hosed down areas and in corrosive atmospheres.

Construction

- 16 gauge stainless steel Type 304 and 316/316L.
- Continuously welded seams.
- Captivated cover screws thread into sealed wells.
- 4-way pushbutton holes accept all brands of oil-tight pushbuttons, switches and pilot lights. Hole diameter is 1.20in [30.5 mm].
- Fully-removable cover.
- Poured-in-place oil- and water-resistant gasket.
- Welded mounting provision top and bottom of back.

Finish

- #4 brushed finish on all exterior surfaces.

Listings

- NEMA Type 4, 4X, 12, and 13
- cULus Listed Type 4, 4X, and 12 [File E69392]
- IEC 60529 IP66



Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

30mm NEMA 4, 4X, 12, and 13 Stainless Steel Wall-Mount Pushbutton						
304 Stainless Steel	Price	316L Stainless Steel	Price	Size HxWxD	Holes	Drawing Link
SCE-1PBSS	\$112.00	SCE-1PBSS6	\$135.00	3.81 x 3.56 x 2.91 [97 x 90 x 74]	1	PDF
SCE-1PBXSS	\$140.00	SCE-1PBXSS6	\$168.00	4.31 x 4.31 x 4.91 [109 x 109 x 125]	1	PDF
SCE-2PBSS	\$141.00	SCE-2PBSS6	\$169.00	6.06 x 3.56 x 2.91 [154 x 90 x 74]	2	PDF
SCE-2PBXSS	\$175.00	SCE-2PBXSS6	\$210.00	6.31 x 4.31 x 4.91 [160 x 109 x 125]	2	PDF
SCE-3PBSS	\$153.00	SCE-3PBSS6	\$184.00	8.31 x 3.56 x 2.91 [211 x 90 x 74]	3	PDF
SCE-3PBXSS	\$186.00	–	–	8.31 x 4.31 x 4.91 [211 x 109 x 125]	3	PDF
SCE-4PBSS	\$174.00	SCE-4PBSS6	\$208.00	10.56 x 3.56 x 2.91 [268 x 90 x 74]	4	PDF
SCE-4PBXSS	\$193.00	SCE-4PBXSS6	\$232.00	10.31 x 4.31 x 4.91 [262 x 109 x 125]	4	PDF
SCE-4SPBSS	\$191.00	SCE-4SPBSS6	\$229.00	7.56 x 6.56 x 3.16 [192 x 167 x 80]	4	PDF
SCE-6PBSS	\$228.00	SCE-6PBSS6	\$274.00	9.81 x 6.56 x 3.16 [249 x 167 x 80]	6	PDF
SCE-9PBSS	\$258.00	SCE-9PBSS6	\$309.00	9.81 x 8.81 x 3.16 [249 x 224 x 80]	9	PDF
SCE-12PBSS	\$294.00	SCE-12PBSS6	\$353.00	12.06 x 8.81 x 3.16 [306 x 224 x 80]	12	PDF

Note: Dimensions in inches [millimeters]