

# wiha Measuring Tools

Tools that work for you

## Calipers


Wiha calipers are high-precision measuring instruments designed for professionals who need reliable, accurate, and durable tools. Made primarily from non-metallic, non-magnetic, fiberglass-reinforced materials, they're lightweight, corrosion-resistant, and ideal for environments where traditional steel calipers may not be suitable. These calipers are ideal for use in industrial, technical, and precision assembly settings.

## Features

- Digital, dial, and vernier options
- Measuring range: 0–6 in (152 mm)
- Outside, inside, depth, and step dimension measurement
- Imperial and metric options available
- Bi-directional thumb roller with friction stop
- Excellent chemical and temperature resistance
- Lightweight construction



**WT41101**



**WT41103**



**WT41104**

Calipers							
Part Number	Product Image	Display Type	Accuracy	Measurement Type	Measurement Reading	Additional Features	Price
<a href="#">WT41101</a>		Digital	0.0005in and 0.01 mm	Imperial Metric	depth inside outside step	Bi-directional thumb roller with friction stop, pushbutton for inch to metric conversion, switches on automatically when opened, switches off after 5 minutes of non-use	\$111.00
<a href="#">WT41103</a>		Vernier	1/64in and 0.1 mm	Imperial Metric	depth inside outside step	Bi-directional thumb roller with friction stop, non-magnetic, non-corroding	\$35.00
<a href="#">WT41104</a>		Dial	0.001in	Imperial	depth inside outside step	Bi-directional thumb roller with friction stop, bezel rotation allows for quick realignment to zero	\$47.00