

wiha Multi-bit Screwdrivers

Tools that work for you




SoftFinish Multi-bit Screwdrivers

Wiha SoftFinish Multi-bit screwdrivers include various double-ended bits stored in the driver shaft for easy access. They feature ergonomic cushion grip handles for comfort and control, dual durometer construction for long-lasting durability, parallel flats to prevent table-top roll-off. 6inOne, 11inOne and a conduit reamer with 6inOne multi-bit drivers are available. See table below for bits included.

Features

- SoftFinish® cushion grip handle for comfort and control
- Handle direct molded to blade for permanent bond
- Handle sized proportionate to blade for consistent mechanical advantage
- Dual durometer construction for long-lasting durability
- Interchangeable blade receiver for multi-tool adaptivity
- Wiha premium quality tool steel for strength and durability
- Parallel flats for roll-off prevention



Multi-bit Screwdrivers											
Part Number	Number of Pieces	Part Image	Type	Bit Size	Overall Length	Handle Type	Set Includes	Price			
<u>WT77890</u>	4		⊕ Phillips	#1	8.3in (211mm)	SoftFinish cushion grip handle	(1) SoftFinish cushion grip handle, (1) reversible shaft with 2 nutdriver profiles (1/4in, 5/16in), (1) Phillips double-ended bit (#1, #2), (1) slotted double-ended bit (3/16in, 1/4in)	\$14.00			
				⊖ Slotted					3/16 in		
			⊖ Slotted						1/4 in		
				<u>WT77891</u>					8		⊕ Phillips
⊖ Slotted	3/16 in										
	⊕ Torx	T20									
⊕ Torx		T25									
	⊖ Square	#1									
⊖ Square		#2									
	<u>WT77892</u>	5			⊕ Phillips	#1	8.3in (211mm)	SoftFinish cushion grip handle			(1) SoftFinish cushion grip handle, (1) interchangeable conduit reamer (1/2in, 3/4in, 1in), (1) reversible shaft with 2 nutdriver profiles (1/4in, 5/16in), (1) Phillips double-ended bit (#1, #2), (1) slotted double-ended bit (3/16in, 1/4in)
⊖ Slotted						3/16 in					
				⊖ Slotted	1/4 in						
⊕ Conduit Reamer					1/2 in						
				⊕ Conduit Reamer	3/4 in						
	⊕ Conduit Reamer	1 in									

