

# Wire - Type TFFN

## Applications

Type TFFN conductors are primarily used as fixture wire as defined by the National Electrical Code (NEC) at temperatures not to exceed 90°C in dry locations. All conductors are permitted for new construction or rewiring for 600-volt applications. Rated gasoline and oil-resistant II.

TFFN wire is sold in 500 foot spools; certain sizes are also available in 2500 foot reels.



## Conductors

Stranded, uncoated copper conductors per ASTM-B174

## Insulation

Color-coded Polyvinyl Chloride (PVC), heat and moisture-resistant, flame-retardant compound


## Jacket

A tough, polyamide, Nylon outer covering

## Ratings

- UL Standards UL-62, UL-66, UL-758 and UL-1063
- AWM Spec 1310, 1312, 1316, 1318, 1321 Canadian Standard Association C22.2 No. 127
- NFPA 70: National Electrical Code (NEC) ARRA 2009; Section 1605 "Buy American" Compliant
- RoHS

## Type TFFN Wire



*Please Note: Our prices on wire are closely tied to the market price for copper. This allows us to offer the best savings possible if conditions are favorable; however, it also means that our prices may increase if market conditions warrant.*

### Type TFFN Wire Specifications

Size (AWG or kcmil)	Number of Strands	Cross-sectional Area (mm <sup>2</sup> ) (According to NEC)	Insulation Thickness (inches)		Overall Outside Diameter		Allowable Ampacities*	Approx. Weight (lbs) 500'/2500'	Standard Packaging spool/reel
			PVC	Nylon	(inches)	(mm)			
18	16	3.548	0.015	0.004	0.088	2.24	6	4 / 20	500' or 2500'
16	26	4.645	0.015	0.004	0.101	2.57	8	5.5 / 27.5	

*\*Note: Allowable ampacity shown above is per the National Electric Code. The above data is approximate and subject to normal manufacturing tolerances.*

### Type TFFN Wire

Part Number	Insulation Color	Gauge	Description	Spool/Reel Length	Approx. Weight	Price				
<b>TFFN18BK</b>	Black	18AWG	Type TFFN wire, bare copper, 16 strands, 600 Volts	500'	4 lbs	\$33.00				
<b>TFFN18WH</b>	White					\$33.00				
<b>TFFN18RD</b>	Red					\$33.00				
<b>TFFN18BL</b>	Blue					\$33.00				
<b>TFFN18GN</b>	Green					\$33.00				
<b>TFFN18YL</b>	Yellow					\$33.00				
<b>TFFN18OR</b>	Orange					\$33.00				
<b>TFFN18BN</b>	Brown					\$33.00				
<b>TFFN18PL</b>	Purple					\$33.00				
<b>TFFN18GY</b>	Gray					\$33.00				
<b>TFFN18BW</b>	Blue with White spiral stripe					\$38.00				
<b>TFFN16BK</b>	Black					16AWG	Type TFFN wire, bare copper, 26 strands, 600 Volts	500'	5.5 lbs	\$45.00
<b>TFFN16WH</b>	White									\$45.00
<b>TFFN16RD</b>	Red	\$45.00								
<b>TFFN16BL</b>	Blue	\$45.00								
<b>TFFN16GN</b>	Green	\$45.00								
<b>TFFN16YL</b>	Yellow	\$45.00								
<b>TFFN16OR</b>	Orange	\$45.00								
<b>TFFN16BN</b>	Brown	\$45.00								
<b>TFFN16GY</b>	Gray	\$45.00								
<b>TFFN16BW</b>	Blue with White spiral stripe	\$50.00								

# Wire - Type TFFN

Type TFFN Wire						
Part Number	Color	Gauge	Description	Spool/Reel Length	Approx. Weight	Price
<b>TFFN18BK25</b>	Black	18AWG	Type TFFN wire, bare copper, 16 strands, 600 Volts	2500'	20 lbs	\$156.00
<b>TFFN18WH25</b>	White					\$156.00
<b>TFFN18RD25</b>	Red					\$156.00
<b>TFFN18BL25</b>	Blue					\$156.00
<b>TFFN18GN25</b>	Green					\$156.00
<b>TFFN18YL25</b>	Yellow					\$156.00
<b>TFFN18OR25</b>	Orange					\$156.00
<b>TFFN18BN25</b>	Brown					\$156.00
<b>TFFN18PL25</b>	Purple					\$156.00
<b>TFFN18GY25</b>	Gray					\$156.00
<b>TFFN18BW25</b>	Blue with White spiral stripe					\$181.00
<b>TFFN16BK25</b>	Black	16AWG	Type TFFN wire, bare copper, 26 strands, 600 Volts	2500'	27.5 lbs	\$218.00
<b>TFFN16WH25</b>	White					\$218.00
<b>TFFN16RD25</b>	Red					\$218.00
<b>TFFN16BL25</b>	Blue					\$218.00
<b>TFFN16GN25</b>	Green					\$218.00
<b>TFFN16YL25</b>	Yellow					\$218.00
<b>TFFN16OR25</b>	Orange					\$218.00
<b>TFFN16BN25</b>	Brown					\$218.00
<b>TFFN16PL25</b>	Purple					\$218.00
<b>TFFN16GY25</b>	Gray					\$218.00
<b>TFFN16BW25</b>	Blue with White spiral stripe					\$243.00

## Gauge Conversion Table

<b>American Wire Gauge Conversion Chart*</b>			
This cross reference shows equivalent nominal values. Actual cross sections may vary.			
AWG	mm <sup>2</sup>	AWG	mm <sup>2</sup>
30	0.05	6	16
28	0.08	4	25
26	0.14	2	35
24	0.25	1	50
22	0.34	1/0	55
21	0.38	2/0	70
20	0.50	3/0	95
18	0.75	4/0	120
17	1.00	300MCM	150
16	1.50	350MCM	185
14	2.50	500MCM	240
12	4	600MCM	300
10	6	750MCM	400
8	10	1000MCM	500

**\*Note: Table shows commercially used equivalent values.**