

IDEM Solenoid Interlock Safety Switch Selection Guide

KLP-201002



KLM-202002



KL3-SS-205002



KL1-P-221302



Series	KLP	KLM	KL3-SS	KL1-P
Prices start at	\$171.00	\$185.00	\$341.00	\$165.00
Description	Solenoid locking, tongue (key) interlock operated, 1800N holding force, power to unlock, 90° adjustable head	Solenoid locking, tongue (key) interlock operated, 2000N holding force, power to unlock, 90° adjustable head	Solenoid locking, tongue (key) interlock operated, 2000N holding force, power to unlock, 90° adjustable head	Solenoid locking, tongue (key) interlock operated, 1400N holding force, power to unlock, 180° adjustable head
Construction Material	46mm wide polyester plastic body, 40mm wide 316 stainless steel head	46mm wide die-cast aluminum body, 40mm wide die-cast aluminum head	48mm wide 316 stainless steel body, 40mm wide 316 stainless steel head	63mm wide polyester plastic body, 52mm wide 316 stainless steel head
Degree of Protection (IEC529)	IEC IP67		IEC IP67, IEC IP69K	IEC IP67
Mechanical Service Life	2.5M operations at 100mA load			
Conduit Opening	1 conduit opening, 1/2 in female NPT	3 conduit openings, 1/2 in female NPT		1 conduit opening, 1/2 in female NPT
Agency Approvals	cULus E258676, CE			

KL1-SS-220002



KLTM-450002



KLT-SS-451002



Series	KL1-SS	KLTM	KLT-SS
Prices start at	\$309.00	\$185.00	\$327.00
Description	Solenoid locking, tongue (key) interlock operated, 1600N holding force, power to unlock, 180° adjustable head	Solenoid locking, tongue (key) interlock operated, 2000N holding force, power to unlock, 180° adjustable head	Solenoid locking, tongue (key) interlock operated, 2000N holding force, power to unlock, 180° adjustable head
Construction Material	63mm wide 316 stainless steel body, 52mm wide 316 stainless steel head	105mm wide die-cast aluminum body, 95mm wide 316 stainless steel head	105mm wide 316 stainless steel body, 95mm wide 316 stainless steel head
Degree of Protection (IEC529)	IEC IP67, IEC IP69K	IEC IP67	IEC IP69K
Mechanical Service Life	2.5M operations at 100mA load		
Conduit Opening	1 conduit opening, 1/2 in female NPT	3 conduit openings, 1/2 in female NPT	
Agency Approvals	cULus E258676, CE		

IDEM Interlock Safety Switch Selection Guide

Inch-1/Inch-3 Series



MK1-SS Series



HC-1/HC-3 Series



HC-SS Series



Series	Inch-1 Inch-3	MK1-SS	HC-1 HC-3	HC-SS
Prices start at	\$30.00	\$91.00	\$32.00	\$92.00
Description	Safety switch, tongue (Key) Interlock operated, 90 degree adjustable Head		Safety switch, Compact Hinge Interlock	
Construction Material	25mm wide plastic body with metal head	30mm wide stainless steel 316	25mm wide plastic body with 316 stainless steel head	30mm wide stainless steel 316
Degree of Protection (IEC529)	IP67	IP69K	IP67	IP69K
Mechanical Service Life	2.5 x 10 ⁶ operations at 100mA load			
Conduit Opening	M16 & M12 QD	1/2 in NPT M20 & M12 QD	M16 & M12 QD	1/2 in NPT M20 & M12 QD
Agency Approvals	cULus E258676, CE			

IDIS-190051



IDIS-192002



**KM-203002
KM-203002-SS**



KM-SS-204002



Series	IDIS-1	IDIS-2	KM	KM-SS
Prices start at	\$26.00	\$25.00	\$62.00	\$121.00
Description	Safety switch, tongue (key) interlock operated, 90 degree adjustable head	Safety switch, lever hinge interlock operated, 90 degree adjustable head	Safety switch, tongue (key) interlock operated, 90 degree adjustable head	
Construction Material	31.5 mm wide, plastic body and head		40 mm wide, die-cast aluminum body and head or die-cast aluminum body and 316 stainless steel head	41.6 mm wide, 316 stainless body and head
Degree of Protection (IEC529)	IEC IP67			IEC IP67, IEC IP69K
Mechanical Service Life	2.5 x 10 ⁶ operations at 100 mA load			
Conduit Opening	One conduit opening, 1/2 in. female NPT			
Agency Approvals	cULus E258676, CE			

IDEM Interlock Safety Switch Selection Guide

KP-200002
KP-200002-SS



K-SS-208002



K-15-207002



K-15-207002-SS



Series	KP	K-SS	K-15	K-15-SS
Prices start at	\$40.00	\$116.00	\$40.00	\$61.00
Description	Safety switch, tongue (key) interlock operated, 180 degree adjustable head		Safety switch, tongue (key) interlock operated, 180 degree adjustable head	
Construction Material	58 mm wide, plastic body and head or plastic body and 316 stainless head	58 mm wide, 316 stainless body and head	54 mm wide, plastic body and head	54 mm wide, plastic body and 316 stainless head
Degree of Protection (IEC529)	IEC IP67	IEC IP67, IEC IP69K	IEC IP67	
Mechanical Service Life	2.5 x 10 ⁶ operations at 100 mA load			
Conduit Opening	Three conduit openings, 1/2 in. female NPT			
Agency Approvals	cULus E258676, CE			

GLM-143067-AS



GLS-142053



GLS-SS-144020-AS



Series	GLM	GLS	GLS-SS
Prices start at	\$115.00	\$125.00	\$263.00
Description	Safety switch, cable-pull interlock operated, with reset. Protection up to 50 meters (164 ft)	Safety switch, cable-pull interlock operated, with reset. Protection up to 80 meters (262 ft)	Safety switch, cable-pull interlock operated, with reset. Protection up to 100 meters (328 ft)
Construction Material	57 mm wide, die-cast aluminum body	63 mm wide, die-cast aluminum body	65 mm wide, 316 stainless steel body
Degree of Protection (IEC529)	IEC IP67		IEC IP67, IP69K
Mechanical Service Life	1.5 x 10 ⁶ operations at 100 mA load		
Conduit Opening	Three conduit openings, 1/2 in. female NPT		
Agency Approvals	cULus E258676, CE		

Comepi Safety Switches Selection Guide



Series	SP2 Series	SDM Series
Prices start at	\$15.00	\$19.00
Description	30 mm safety limit switch with keys or shaft lever	50 mm safety limit switch with keys, shaft lever or pull wire
Material of Construction	Plastic casing, double insulated	ZAMAK (zinc alloy) casing
Degree of Protection (IEC529)	IEC IP65	IEC IP66
Maximum Switching Frequency	Contact blocks: 1 cycle per second (all)	Contact blocks: 1 cycle per second (all)
Mechanical Service Life	1,000,000 operations interlock and limit switches	1,000,000 operations. interlock and limit switches 25,000 operations for pull wire
Contact Configuration	X11 - Slow action break before make, positive opening, 1 N.O. + 1 N.C. W02 - Simultaneous, slow action, positive opening, 2 N.C.	X11 - Slow action break before make, positive opening, 1 N.O. + 1 N.C. W02 - Simultaneous, slow action, positive opening, 2 N.C.
Conduit Opening	One cable hole, 1/2" NPT adapter	Three cable holes, 1/2" NPT
Connection	2x2.5mm ² (AWG14) to 2x0.5mm ² (AWG 18)	2x2.5mm ² (AWG14) to 2x0.5mm ² (AWG 18)
Agency Approvals	CE, UL file E189258, CSA 176294, RoHS	CE, UL file E189258, CSA 176294, RoHS



Series	SBM Series	SCM Series
Prices start at	\$25.50	\$26.00
Description	40 mm safety limit switch with keys or pull wire	60 mm safety limit switches with keys or pull wire
Material of Construction	Aluminum casing	Aluminum casing
Degree of Protection (IEC529)	IEC IP66	IEC IP66
Maximum Switching Frequency	Contact blocks: 1 cycle per second (all)	Contact blocks: 1 cycle per second (all)
Mechanical Service Life	1,000,000 operations. interlock and limit switches 25,000 operations for pull wire	1,000,000 operations interlock and limit switches 25,000 operations for pull wire
Contact Configuration	X11 - Slow action break before make, positive opening, 1 N.O. + 1 N.C. W02 - Simultaneous, slow action, positive opening, 2 N.C. X12 - Slow action break before make, positive opening, 1 N.O. + 2 N.C. W03 - Simultaneous, slow action, positive opening 3 N.C.	X11 - Slow action break before make, positive opening, 1 N.O. + 1 N.C. W02 - Simultaneous, slow action, positive opening, 2 N.C. X12 - Slow action break before make, positive opening, 1 N.O. + 2 N.C. W03 - Simultaneous, slow action, positive opening 3 N.C.
Conduit Opening	One cable hole, 1/2" NPT	Three cable holes, 1/2" NPT
Connection	2x2.5mm ² (AWG14) to 2x0.5mm ² (AWG 18)	2x2.5mm ² (AWG14) to 2x0.5mm ² (AWG 18)
Agency Approvals	CE, UL file E189258, CSA 176294, RoHS	CE, UL file E189258, CSA 176294, RoHS

Safety Limit Switches Selection Guide



Series	HLM Series	HLM-SS Series	LSPS Series
Prices start at	\$59.50	\$121.00	\$20.50
Description	Die-cast metal body safety limit switch	Stainless steel body safety limit switch	Plastic body safety limit switch
Material of Construction	Die-cast zinc aluminum casing	Stainless steel 316 casing	Plastic casing
Degree of Protection (IEC529)	IEC IP67	IEC IP67/IP69	IEC IP67
Maximum Switching Frequency	6,000 operations/day	6,000 operations/day	6,000 operations/day
Mechanical Service Life	2,500,000 cycles	2,500,000 cycles	2,500,000 cycles
Contact Configuration	Each model available with: 2 N.C. / 2 N.O. slow action break before make contacts, or 1 N.O. / 1 N.C. snap action contacts	Each model available with: 2 N.C. / 2 N.O. slow action break before make contacts, or 1 N.O. / 1 N.C. snap action contacts	Each model available with: 2 N.C. / 2 N.O. slow action break before make contacts, or 1 N.O. / 1 N.C. snap action contacts
Conduit Opening	One cable hole	One cable hole	One cable hole
Connection	1/2 inch female NPT conduit	1/2 inch female NPT conduit	1/2 inch female NPT conduit
Agency Approvals	CE, UL (file E258676)	CE, UL (file E258676)	CE, UL (file E258676)



Series	LSMM Series	LSPM Series	AP2 Series
Prices start at	\$37.50	\$28.50	\$13.00
Description	Panel mount die-cast metal body safety limit switch	Panel mount plastic body safety limit switch	30 mm limit switches with pull button reset
Material of Construction	Die-cast zinc aluminum casing	Plastic casing	Plastic casing, double insulated
Degree of Protection (IEC529)	IEC IP67	IEC IP67	IEC IP65
Maximum Switching Frequency	6,000 operations/day	6,000 operations/day	Contact blocks: 1 cycle per second (all)
Mechanical Service Life	2,500,000 cycles	2,500,000 cycles	1,000,000 operations interlock and limit switches
Contact Configuration	Each model available with: 2 N.C. / 1 N.O. slow action break before make contacts, or 1 N.O. / 1 N.C. snap action contacts	Each model available with: 2 N.C. / 1 N.O. slow action break before make contacts, or 1 N.O. / 1 N.C. snap action contacts	X11 - Slow action break before make, positive opening, 1 N.O. + 1 N.C. W02 - Simultaneous, slow action, positive opening, 2 N.C.
Conduit Opening	One cable hole	One cable hole	One cable hole, 1/2" NPT adapter
Connection	Pigtail; 2m / 6.5 ft cable length	Pigtail; 2m / 6.5 ft cable length	2x2.5mm ² (AWG14) to 2x0.5mm ² (AWG 18)
Agency Approvals	CE, UL (file E258676)	CE, UL (file E258676)	CE, UL file E189258, CSA 176294, RoHS

Safety Products



Warning: Safety products sold by AutomationDirect are Safety components only. The purchaser/installer is solely responsible for the application of these components and ensuring all necessary steps have been taken to assure each application and use meets all performance and applicable safety requirements and/or local, national and/or international safety codes as required by the application. AutomationDirect cannot certify that our products, used solely or in conjunction with other AutomationDirect or other vendors' products, will assure safety for any application. Any person using or applying any products sold by AutomationDirect is responsible for learning the safety requirements for their individual application and applying them, and therefore assumes all risks, and accepts full and complete responsibility, for the selection and suitability of the product for their respective application. AutomationDirect does not provide design or consulting services, and cannot advise whether any specific application or use of our products would ensure compliance with the safety requirements for any application.