



# Specialty Head Cable Ties

## Nylon Lashing Cable Tie

Sapiselco's ASO series lashing cable ties are engineered for heavy-duty bundling applications that demand exceptional strength and a secure, non-slip grip. Unlike traditional self-locking ties, these ties feature a robust buckle head design that allows the strap to be threaded through and tensioned, locked into place with a separate locking mechanism. This design typically provides superior tensile strength and resistance to vibration or accidental release. Made from high-quality Nylon 6.6, the ASO series is ideal for securing large or heavy bundles in demanding industrial, automotive, or construction environments where maximum holding power and reliability are paramount.

### Features

- UL 94: V-2 rated Nylon 6.6
- Suitable for indoor applications
- Rounded edges to avoid cable damage
- Operating temperature: -40 to 85°C [-40 to 185°F]
- Minimum installation temperature -10°C [14°F]

### Agency Approvals

- CE



Nylon Lashing Cable Tie													
Part Number	Pcs/ Bag	Price	Color	Length		Width		Min. Bundle Ø		Max. Bundle Ø		Tensile Strength	
				mm	in	mm	in	mm	in	mm	in	kg	lb
<b>ASO.3.251</b>	50	\$15.50	Black	500	19.69	12.5	0.49	10	0.39	140	5.51	98	216.09

## Double-headed Cable Ties [Collars]

Sapiselco's COL series double head cable ties offer a unique and efficient solution for organizing and separating two distinct bundles of cables or wires with a single fastening point. These innovative ties feature two independent locking heads on a single strap, allowing users to secure two separate bundles simultaneously or to create a robust double-loop fastening for a single, critical bundle. Made from durable Nylon 6.6, the COL series provides reliable tensile strength and secure locking for both bundles. This design is particularly useful in applications where segregation of different cable types (e.g., power and data) is required, or where a highly secure, redundant fastening is desired, optimizing space and improving organization.

### Features

- UL 94: HB rated Nylon 6.6
- UV resistant
- Suitable for outdoor applications
- Rounded edges to avoid cable damage
- Operating temperature: -40 to 85°C [-40 to 185°F]

### Agency Approvals

- IEC 62275
- CE




Black Double-headed Cable Ties													
Part Number	Pcs/Bag	Price	Color	Length		Width		Min. Bundle Ø		Max. Bundle Ø		Tensile Strength	
				mm	in	mm	in	mm	in	mm	in	kg	lb
<b>COL.3.321</b>	100	\$15.50	Black	265	10.43	9	0.35	15	0.59	63	2.48	40	88.20
<b>COL.3.322</b>		\$22.00		360	14.17			25	0.98	93	3.66		



# Cable Tie Tools

## Cable Tie Cutting Tool

The special angle of this cutter's tips enables clean cuts of the ties to sizes between 2.5 and 12.5 mm in width, maintaining the wired electric cables intact. The cutter can also be used for cutting cables.

	
<b><u>PIN.009</u></b>	\$16.00

## Collar Fastening Metal Plier

This tool makes it easier to tighten and cut collars. Use with Double-headed Cable Ties. Leaves a short length of tail close to the head. For use with up to 9mm wide cable ties.

	
<b><u>PIN.005</u></b>	\$14.50

## Cable Tie Gun Installation Tool

For use with cable ties up to 5mm wide. This tool helps to adjust the preload and cut the tie. Tightening torque of 2.5 kg to 12kg.

	
<b><u>PIN.003</u></b>	\$21.00



# Cable Ties Family Overview

## General Purpose Nylon Cable Ties



SapiSelco general purpose Nylon 6.6 cable ties are slotted and held in place by the resistance of the elastic tooth against the rack. These cable ties are resistant to solvents and reagents, oil, gasoline, and hydrocarbons when used at low temperatures, in low concentrations, and for short periods of time. Assortment Kit available.



These ties are low-cost, releasable, and reusable cable ties, suitable for lightweight loads. The double-locking head enables securing two cable bundles with one tie. The body is completely rounded to eliminate all sharp edges guaranteeing reliable performance every time.

## Colored Nylon Cable Ties



SapiSelco colored Nylon 6.6 cable ties are useful in applications that require distinct identifiers. These ties are colored with inorganic dyes and are resistant to solvents and reagents, oil, gasoline, and hydrocarbons when used at low temperatures, in low concentrations, and for short periods of time. Assortment Kit available.

## Stainless Steel Tooth Ties



SapiSelco stainless steel tooth ties are forged from nylon and hardened stainless steel with added Molybdenum. This ensures extremely high mechanical strength and optimal resistance to corrosion. A single central raised section makes this tie particularly flexible, while guaranteeing maximum strength at the same time.

## UV Resistant Cable Ties



Exposure to sun and ultraviolet rays causes deterioration in nylon. SapiSelco specialty Nylon UV Resistant cable ties can resist and endure the harsh conditions of outdoor applications for up to 10 years. These ties can withstand temperatures up to 125°C [257°F].

## Metal Detector Readable Cable Ties



These ties are fabricated with a special composite of 6.6 polyamide and metal powder and are sensitive to electromagnetic fields. They are recommended in the food, pharmaceutical and chemical industry. They are useful in applications where, for safety reasons, it is necessary for a metal detector to be able to detect even very small fragments of these ties that may be mixed in with products.

## Specialty Cable Ties



**Nylon Releasable Tab**



**Screw Mount**



**Low Temp**



**Nylon Lashing Cable Tie**



**Identification Ties**



**Double-headed [Collars]**

## Tools and Accessories



**Cable Tie Cutting Tool**



**Collar Fastening Metal Plier**



**Cable Tie Gun Installation Tool**



**Bi-directional Nylon Square Bases**