



Cable Ties Family Overview

General Purpose Nylon Cable Ties



SapiSelco general purpose Nylon 6.6 cable ties are slotted and held in place by the resistance of the elastic tooth against the rack. These cable ties are resistant to solvents and reagents, oil, gasoline, and hydrocarbons when used at low temperatures, in low concentrations, and for short periods of time. Assortment Kit available.



These ties are low-cost, releasable, and reusable cable ties, suitable for lightweight loads.

The double-locking head enables securing two cable bundles with one tie. The body is completely rounded to eliminate all sharp edges guaranteeing reliable performance every time.

Colored Nylon Cable Ties



SapiSelco colored Nylon 6.6 cable ties are useful in applications that require distinct identifiers. These ties are colored with inorganic dyes and are resistant to solvents and reagents, oil, gasoline, and hydrocarbons when used at low temperatures, in low concentrations, and for short periods of time. Assortment Kit available.

Specialty Cable Ties

Stainless Steel Tooth Ties



SapiSelco stainless steel tooth ties are forged from nylon and hardened stainless steel with added Molybdenum. This ensures extremely high mechanical strength and optimal resistance to corrosion. A single central raised section makes this tie particularly flexible, while guaranteeing maximum strength at the same time.

UV Resistant Cable Ties



Exposure to sun and ultraviolet rays causes deterioration in nylon. SapiSelco specialty Nylon UV Resistant cable ties can resist and endure the harsh conditions of outdoor applications for up to 10 years. These ties can withstand temperatures up to 125°C [257°F].

Metal Detector Readable Cable Ties



These ties are fabricated with a special composite of 6.6 polyamide and metal powder and are sensitive to electromagnetic fields. They are recommended in the food, pharmaceutical and chemical industry. They are useful in applications where, for safety reasons, it is necessary for a metal detector to be able to detect even very small fragments of these ties that may be mixed in with products.



Nylon Releasable Tab



Screw Mount



Low Temp



Nylon Lashing Cable Tie



Identification Ties



Double-headed [Collars]

Tools and Accessories



Cable Tie Cutting Tool



Collar Fastening Metal Plier



Cable Tie Gun Installation Tool



Bi-directional Nylon Square Bases



General Purpose Nylon Cable Ties

Overview

These general purpose Nylon 6.6 cable ties are slotted and held in place by the resistance of the elastic tooth against the rack. The tail of the strap is pulled through the head to form a noose that can only be tightened.

Used to fix and seal. The work load is calculated using a safety coefficient of no less than 2. A preload of no higher than 10% of the work load should be applied.

These cable ties are resistant to solvents and reagents, oil, gasoline, and hydrocarbons when used at low temperatures, in low concentrations, and for short periods of time.



Features

- UL 94: V2 self-extinguishing nylon
- Halogen-free
- Not resistant to mineral acids and oxidizing agents
- Designed for indoor applications
- Rounded edges to avoid cable damage
- Operating temperature:
-40 to +85°C [-40 to +185°F]

Agency Approvals

- UL Listed File E160935
- CE

General Purpose Nylon Cable Ties																
Part Number	Pcs/ Bag	Price	Part Number	Pcs/ Bag	Price	Color	Length		Width		Min. Bundle Ø		Max. Bundle Ø		Tensile Strength	
							mm	in	mm	in	mm	in	mm	in	Kg	lb
SEL.2.202	100	\$1.25:	SEL.2.302	1000	\$4.50	Natural	100	3.94	2.5	0.10	2	0.08	24	0.94	11	24.25
SEL.3.202	100	\$1.25:	SEL.3.302	1000	\$5.00	Black	100	3.94	2.5	0.10	2	0.08	24	0.94	11	24.25
SEL.2.204	100	\$1.25	SEL.2.304	1000	\$11.50	Natural	160	6.30	2.5	0.10	2	0.08	42	1.65	11	24.25
SEL.3.204	100	\$1.25	SEL.3.304	1000	\$11.50	Black	160	6.30	2.5	0.10	2	0.08	42	1.65	11	24.25
SEL.2.205	100	\$1.25	SEL.2.305	1000	\$12.00	Natural	200	7.87	2.5	0.10	2	0.08	55	2.17	11	24.25
SEL.3.205	100	\$1.25	–	–	–	Black	200	7.87	2.5	0.10	2	0.08	55	2.17	11	24.25
SEL.2.210	100	\$1.25	SEL.2.310	1000	\$10.50:	Natural	140	5.51	3.5	0.14	3	0.12	36	1.42	20	44.09
SEL.3.210	100	\$1.25	SEL.3.310	1000	\$11.50	Black	140	5.51	3.5	0.14	3	0.12	36	1.42	20	44.09
SEL.2.211	100	\$1.50	SEL.2.311	1000	\$15.50	Natural	200	7.87	3.5	0.14	3	0.12	55	2.17	20	44.09
SEL.3.211	100	\$1.75	–	–	–	Black	200	7.87	3.5	0.14	3	0.12	55	2.17	20	44.09
SEL.2.212	100	\$2.25	–	–	–	Natural	280	11.02	3.5	0.14	3	0.12	80	3.15	20	44.09
SEL.3.212	100	\$2.25	–	–	–	Black	280	11.02	3.5	0.14	3	0.12	80	3.15	20	44.09
SEL.2.214	100	\$4.25	–	–	–	Natural	360	14.17	3.5	0.14	5	0.20	103	4.06	20	44.09
SEL.3.214	100	\$3.75	–	–	–	Black	360	14.17	3.5	0.14	5	0.20	103	4.06	20	44.09

Continued on next page



General Purpose Nylon Cable Ties

Continued from previous page

General Purpose Nylon Cable Ties																
Part Number	Pcs/ Bag	Price	Part Number	Pcs/ Bag	Price	Color	Length		Width		Min. Bundle Ø		Max. Bundle Ø		Tensile Strength	
							mm	in	mm	in	mm	in	mm	in	Kg	lb
SEL.2.221	100	\$1.75	SEL.2.321	1000	\$19.00	Natural	160	6.30	4.5	0.18	3	0.12	38	1.50	28	61.73
SEL.3.221	100	\$1.75	–	–	–	Black	160	6.30	4.5	0.18	3	0.12	38	1.50	28	61.73
SEL.2.222	100	\$2.00	SEL.2.322	1000	\$19.00	Natural	180	7.09	4.5	0.18	3	0.12	45	1.77	28	61.73
SEL.3.222	100	\$2.00	–	–	–	Black	180	7.09	4.5	0.18	3	0.12	45	1.77	28	61.73
SEL.2.425	100	\$3.00	–	–	–	Natural	280	11.02	4.5	0.18	5	0.20	76	2.99	28	61.73
SEL.3.425	100	\$3.00	–	–	–	Black	280	11.02	4.5	0.18	5	0.20	76	2.99	28	61.73
SEL.2.426	100	\$3.75	–	–	–	Natural	360	14.17	4.5	0.18	5	0.20	101	3.98	28	61.73
SEL.3.426	100	\$4.00	–	–	–	Black	360	14.17	4.5	0.18	5	0.20	101	3.98	28	61.73
SEL.2.434	100	\$7.25	–	–	–	Natural	360	14.17	7.5	0.30	5	0.20	101	3.98	65	143.30
SEL.3.434	100	\$7.50	–	–	–	Black	360	14.17	7.5	0.30	5	0.20	101	3.98	65	143.30
SEL.2.143	100	\$26.50	–	–	–	Natural	780	30.71	9	0.35	20	0.79	235	9.25	80	176.37
SEL.3.143	100	\$28.00	–	–	–	Black	780	30.71	9	0.35	20	0.79	235	9.25	80	176.37
SEL.2.154	100	\$32.50	–	–	–	Natural	920	36.22	9	0.35	40	1.57	280	11.02	80	176.37
SEL.3.154	100	\$34.00	–	–	–	Black	920	36.22	9	0.35	40	1.57	280	11.02	80	176.37

Cable Tie Assortment Kit

Bucket Mix – Designed for professionals and do-it-yourselfers in mind. Packaged in a practical reusable bucket shaped plastic container, these cable ties are available in convenient 1,200 or 800 pieces, in black and natural. The products are packaged in bags of 100 pieces. This enables the cable ties to preserve their physical characteristics until the time of use, ensuring optimal performance for every application.

Cable Tie Assortment Kit		
Part Number	Price	Description
BUCK.001	\$23.50	SapiSelco cable tie assortment kit, black and natural. Package of 1200. Includes (300) 3.93in cable ties, (300) 7.09in cable ties, (300) 7.87in cable ties and (300) 9.84in cable ties.
BUCK.002	\$17.00	SapiSelco cable tie assortment kit, black and natural. Package of 800. Includes (200) 3.93in cable ties, (200) 5.51in cable ties, (200) 7.09in cable ties and (200) 7.87in cable ties.



[BUCK.001](#)



[BUCK.002](#)



General Purpose Colored Nylon Cable Ties

Overview

These general purpose colored Nylon 6.6 cable ties are slotted and held in place by the resistance of the elastic tooth against the rack. The tail of the strap is pulled through the head to form a noose that can only be tightened.

Used to fix and seal. The work load is calculated using a safety coefficient of no less than 2. A preload of no higher than 10% of the work load should be applied.

These cable ties are resistant to solvents and reagents, oil, gasoline, and hydrocarbons when used at low temperatures, in low concentrations, and for short periods of time.

Features

- UL 94: V2 self-extinguishing nylon
- Halogen-free
- Designed for indoor applications
- Rounded edges to avoid cable damage
- Operating temperature: -40 to +85°C [-40 to +185°F]

Agency Approvals

- CE

General Purpose Colored Nylon Cable Ties													
Part Number	Pcs/Bag	Price	Color	Length		Width		Min. Bundle Ø		Max. Bundle Ø		Tensile Strength	
				mm	in	mm	in	mm	in	mm	in	Kg	lb
SEL.10.202	100	\$1.25	Red	100	3.94	2.5	0.10	2	0.08	24	0.94	11	24.25
SEL.11.202	100	\$1.25	Blue	100	3.94	2.5	0.10	2	0.08	24	0.94	11	24.25
SEL.12.202	100	\$1.25	Green	100	3.94	2.5	0.10	2	0.08	24	0.94	11	24.25
SEL.14.202	100	\$1.25	Yellow	100	3.94	2.5	0.10	2	0.08	24	0.94	11	24.25
SEL.21.202	100	\$1.25	Gray	100	3.94	2.5	0.10	2	0.08	24	0.94	11	24.25
SEL.10.210	100	\$1.75	Red	140	5.51	3.5	0.14	3	0.12	36	1.42	20	44.09
SEL.11.210	100	\$1.75	Blue	140	5.51	3.5	0.14	3	0.12	36	1.42	20	44.09
SEL.12.210	100	\$1.75	Green	140	5.51	3.5	0.14	3	0.12	36	1.42	20	44.09
SEL.14.210	100	\$1.75	Yellow	140	5.51	3.5	0.14	3	0.12	36	1.42	20	44.09
SEL.21.210	100	\$1.75	Gray	140	5.51	3.5	0.14	3	0.12	36	1.42	20	44.09
SEL.10.223	100	\$2.50	Red	200	7.87	4.5	0.18	3	0.12	51	2.01	28	61.73
SEL.11.223	100	\$2.50	Blue	200	7.87	4.5	0.18	3	0.12	51	2.01	28	61.73
SEL.12.223	100	\$2.50	Green	200	7.87	4.5	0.18	3	0.12	51	2.01	28	61.73
SEL.14.223	100	\$2.50	Yellow	200	7.87	4.5	0.18	3	0.12	51	2.01	28	61.73
SEL.21.223	100	\$2.50	Gray	200	7.87	4.5	0.18	3	0.12	51	2.01	28	61.73
SEL.10.425	100	\$3.75	Red	280	11.02	4.5	0.18	5	0.20	76	2.99	28	61.73
SEL.11.425	100	\$3.75	Blue	280	11.02	4.5	0.18	5	0.20	76	2.99	28	61.73
SEL.12.425	100	\$3.75	Green	280	11.02	4.5	0.18	5	0.20	76	2.99	28	61.73
SEL.14.425	100	\$3.75	Yellow	280	11.02	4.5	0.18	5	0.20	76	2.99	28	61.73
SEL.21.425	100	\$3.75	Gray	280	11.02	4.5	0.18	5	0.20	76	2.99	28	61.73



Cable Tie Assortment Kit

Bucket Mix – Designed for professionals and do-it-yourselfers in mind. Packaged in a practical reusable bucket shaped plastic container, these cable ties are available in a convenient 800-piece assortment including the colors red, blue, green, and yellow. The products are packaged in bags of 100 pieces. This enables the cable ties to preserve their physical characteristics until the time of use, ensuring optimal performance for every application.

Cable Tie Assortment Kit		
Part Number	Price	Description
BUCK.003	\$18.50	SapiSelco cable tie assortment kit, red, blue, green and yellow. Package of 800. Includes (400) 5.51in cable ties and (400) 7.87in cable ties.



BUCK.003



Nylon Cable Ties with Stainless Steel Tooth

Overview

The increased size of the hardened stainless steel tooth [with added Molybdenum] ensures extremely high mechanical strength and optimal resistance to corrosion. The classic rack has been replaced by a single central raised section, making the MET tie particularly flexible, while guaranteeing maximum strength at the same time. The special design of the MET cable tie enables smoother insertion of the steel tooth, reducing the required insertion force.



Features

- UL 94: V2 self-extinguishing nylon
- Designed for indoor applications
- Rounded edges to avoid cable damage
- Operating temperature:
-40 to +85°C [-40 to +185°F]

Agency Approvals

- UL Listed File E160935
- CE

Nylon Cable Ties with Stainless Steel Tooth

Part Number	Pcs/ Bag	Price	Part Number	Pcs/ Bag	Price	Color	Length		Width		Min. Bundle Ø		Max. Bundle Ø		Tensile Strength	
							mm	in	mm	in	mm	in	mm	in	Kg	lb
MET.2.2102R	100	\$2.00	MET.2.2302R	1000	\$19.50	Natural	100	3.94	2.5	0.10	2	0.08	24	0.94	18	39.68
MET.3.2102R	100	\$2.00	MET.3.2302R	1000	\$19.50	Black	100	3.94	2.5	0.10	2	0.08	24	0.94	18	39.68
MET.2.2105R	100	\$4.75	MET.2.2305R	1000	\$52.00	Natural	200	7.87	2.5	0.10	2	0.08	55	2.17	18	39.68
MET.3.2105R	100	\$4.75	MET.3.2305R	1000	\$52.00	Black	200	7.87	2.5	0.10	2	0.08	55	2.17	18	39.68
MET.2.2110R	100	\$2.75	MET.2.2310R	1000	\$27.00	Natural	140	5.51	3.5	0.14	3	0.12	36	1.42	28	61.73
MET.3.2110R	100	\$2.75	MET.3.2310R	1000	\$27.50	Black	140	5.51	3.5	0.14	3	0.12	36	1.42	28	61.73
MET.2.2111R	100	\$4.75	MET.2.2311R	1000	\$47.00	Natural	200	7.87	3.5	0.14	3	0.12	55	2.17	28	61.73
MET.3.2111R	100	\$4.75	MET.3.2311R	1000	\$49.50	Black	200	7.87	3.5	0.14	3	0.12	55	2.17	28	61.73
MET.2.2112R	100	\$5.50	MET.2.2312R	1000	\$58.00	Natural	280	11.02	3.5	0.14	3	0.12	80	3.15	28	61.73
MET.3.2112R	100	\$5.75	MET.3.2312R	1000	\$58.00	Black	280	11.02	3.5	0.14	3	0.12	80	3.15	28	61.73
MET.2.2123R	100	\$5.25	MET.2.2323R	1000	\$53.00	Natural	186	7.32	4.5	0.18	3	0.12	51	2.01	40	88.18
MET.3.2123R	100	\$5.25	MET.3.2323R	1000	\$53.00	Black	186	7.32	4.5	0.18	3	0.12	51	2.01	40	88.18
MET.2.2140R	100	\$7.50	MET.2.2340R	1000	\$76.00	Natural	290	11.42	4.5	0.18	3	0.12	80	3.15	40	88.18
MET.3.2140R	100	\$7.75	MET.3.2340R	1000	\$77.00	Black	290	11.42	4.5	0.18	3	0.12	80	3.15	40	88.18
MET.2.2126R	100	\$9.25	MET.2.2326R	1000	\$91.00	Natural	360	14.17	4.5	0.18	3	0.12	103	4.06	40	88.18
MET.3.2126R	100	\$9.25	MET.3.2326R	1000	\$91.00	Black	360	14.17	4.5	0.18	3	0.12	103	4.06	40	88.18
MET.2.2548R	50	\$7.25	MET.2.2748R	500	\$71.00	Natural	340	13.39	7	0.28	6	0.24	90	3.54	70	154.32
MET.3.2548R	50	\$7.25	MET.3.2748R	500	\$69.00	Black	340	13.39	7	0.28	6	0.24	90	3.54	70	154.32
MET.2.2534R	50	\$9.75	MET.2.2734R	500	\$95.00	Natural	360	14.17	7.5	0.30	6	0.24	101	3.98	80	176.37
MET.3.2534R	50	\$9.25	MET.3.2734R	500	\$88.00	Black	360	14.17	7.5	0.30	6	0.24	101	3.98	80	176.37



Specialty Cable Ties

Nylon UV Resistant Cable Ties

Exposure to sun and ultraviolet rays causes deterioration in nylon. Our specialty Nylon UV Resistant cable ties can resist and endure the harsh conditions of outdoor applications for up to 10 years.



Features

- UL 94: V2 self-extinguishing nylon
- Designed for outdoor applications
- Rounded edges to avoid cable damage
- Operating temperature:
-40 to +125°C [-40 to +257°F]

Agency Approvals

- CE

Black Nylon UV Resistant Cable Ties												
Part Number	Pcs/ Bag	Price	Length		Width		Min. Bundle Ø		Max. Bundle Ø		Tensile Strength	
			mm	in	mm	in	mm	in	mm	in	Kg	lb
<u>SEL.UVV2.210</u>	100	\$2.00	140	5.51	3.5	0.14	3	0.12	36	1.42	20	44.09
<u>SEL.UVV2.223</u>	100	\$3.25	200	7.87	4.5	0.18	3	0.12	51	2.01	28	61.73
<u>SEL.UVV2.425</u>	100	\$5.00	280	11.02	4.5	0.18	5	0.20	76	2.99	28	61.73
<u>SEL.UVV2.426</u>	100	\$7.25	360	14.17	4.5	0.18	5	0.20	101	3.98	28	61.73
<u>SEL.UVV2.434</u>	100	\$13.00	360	14.17	7.5	0.30	5	0.20	101	3.98	65	143.30

Metal Detector Readable Nylon Cable Ties

These ties are produced with a special 6.6 polyamide with metal powder additive and are sensitive to electromagnetic fields. They are recommended in the food, pharmaceutical and chemical industry. They are useful in applications where, for safety reasons, it is necessary for a metal detector to be able to detect even very small fragments of these ties that may be mixed in with products.



Features

- UL 94: V2 self-extinguishing nylon
- Designed for indoor applications
- Rounded edges to avoid cable damage
- Operating temperature:
-40 to +85°C [-40 to +185°F]

Agency Approvals

- CE

Blue Metal Detector Readable Nylon Cable Ties												
Part Number	Pcs/ Bag	Price	Length		Width		Min. Bundle Ø		Max. Bundle Ø		Tensile Strength	
			mm	in	mm	in	mm	in	mm	in	Kg	lb
<u>DET.11.2102</u>	100	\$3.00	100	3.94	2.5	0.10	2	0.08	24	0.94	10	22.05
<u>DET.11.2110</u>	100	\$5.00	140	5.51	3.5	0.14	3	0.12	36	1.42	18	39.68
<u>DET.11.2123</u>	100	\$9.75	200	7.87	4.5	0.18	3	0.12	51	2.01	25	55.12
<u>DET.11.2124</u>	100	\$12.00	250	9.84	4.5	0.18	5	0.20	68	2.68	25	55.12
<u>DET.11.2140</u>	100	\$14.00	280	11.02	4.5	0.18	5	0.20	76	2.99	25	55.12
<u>DET.11.2127</u>	100	\$20.00	380	14.96	4.5	0.18	5	0.20	110	4.33	25	55.12
<u>DET.11.2134</u>	100	\$35.00	360	14.17	7.5	0.30	5	0.20	101	3.98	60	132.28



Specialty Cable Ties

Nylon Releasable Tab Cable Ties Features

These ties have a tongue for temporary cabling/fixing applications, enabling the tie to be reused.

- UL 94: V2 self-extinguishing nylon
- Suitable for indoor applications
- Rounded edges to avoid cable damage
- Operating temperature: -15 to +75°C [+5 to +167°F]



Agency Approvals

- CE

Nylon Releasable Tab Cable Ties

Part Number	Pcs/Bag	Price	Color	Length		Width		Min. Bundle Ø		Max. Bundle Ø		Tensile Strength	
				mm	in	mm	in	mm	in	mm	in	Kg	lb
RIA.2.232	100	\$6.00	Natural	200	7.87	7.5	0.30	10	0.39	50	1.97	36	79.37
RIA.3.232	100	\$6.00	Black	200	7.87	7.5	0.30	10	0.39	50	1.97	36	79.37
RIA.2.231	100	\$6.25	Natural	250	9.84	7.5	0.30	10	0.39	65	2.56	36	79.37
RIA.3.231	100	\$6.75	Black	250	9.84	7.5	0.30	10	0.39	65	2.56	36	79.37
RIA.2.233	100	\$7.00	Natural	280	11.02	7.5	0.30	10	0.39	76	2.99	36	79.37
RIA.3.233	100	\$7.75	Black	280	11.02	7.5	0.30	10	0.39	76	2.99	36	79.37
RIA.2.234	100	\$8.75	Natural	360	14.17	7.5	0.30	10	0.39	100	3.94	36	79.37
RIA.3.234	100	\$8.75	Black	360	14.17	7.5	0.30	10	0.39	100	3.94	36	79.37

Nylon Lashing Cable Tie

This nylon PA 6.6 wiring cable tie has a link above the head for inserting the left over tail which, after installation, does not need to be cut, thereby making installation faster. It can be buttonhole inserted through the teeth in the insert of the cable tie.

Features

- UL 94: V2 self-extinguishing nylon
- Suitable for indoor applications
- Rounded edges to avoid cable damage
- Operating temperature: -15 to +85°C [+5 to +185°F]



Agency Approvals

- CE

Nylon Lashing Cable Tie

Part Number	Pcs/Bag	Price	Color	Length		Width		Min. Bundle Ø		Max. Bundle Ø		Tensile Strength	
				mm	in	mm	in	mm	in	mm	in	Kg	lb
ASO.3.251	50	\$14.00	Black	500	19.69	12.5	0.49	10	0.39	140	5.51	130	286.60

Screw Mount Cable Tie

The eyelet tie is designed to tie cable bundles onto even sharp-edged supports, by rivets or screws [not included] inserted through the eyelet.

Features

- UL 94: V2 self-extinguishing nylon
- Suitable for indoor applications
- Rounded edges to avoid cable damage
- Operating temperature: -5 to +85°C [+23 to +185°F]



Agency Approvals

- CE

Screw Mount Cable Tie

Part Number	Pcs/Bag	Price	Color	Length		Width		Mounting Head Hole		Min. Bundle Ø		Max. Bundle Ø		Tensile Strength	
				mm	in	mm	in	mm	in	mm	in	mm	in	Kg	lb
OCH.2.2123	100	\$3.25	Natural	200	7.87	4.5	0.18	5	0.20	3	0.12	51	2.01	≥ 22	≥ 48.50



Specialty Cable Ties

Nylon Identification Cable Ties

Nylon cable ties with built-in identification tag.

Features

- UL 94: V2 self-extinguishing nylon
- Suitable for indoor applications
- Rounded edges to avoid cable damage
- Operating temperature: -15 to +75°C [+5 to +167°F]

Agency Approvals

- CE



SEL.2.202T

SEL.2.223T

Nylon Identification Cable Ties															
Part Number	Pcs/Bag	Price	Color	Tag Size		Length		Width		Min. Bundle Ø		Max. Bundle Ø		Tensile Strength	
				mm	in	mm	in	mm	in	mm	in	mm	in	Kg	lb
<u>SEL.2.202T</u>	100	\$3.75	Natural	8 x 25	0.31 x 0.98	100	3.94	2.5	0.10	10	0.39	25	0.98	11	24.25
<u>SEL.2.223T</u>	100	\$6.50	Natural	35 x 13	1.38 x 0.51	200	7.87	4.8	0.19	16	0.62	50	1.97	28	61.73

Double-headed Cable Ties [Collars]

Double-headed locking cable ties offer more secure fastening. Made from a softer thermoplastic, these ties are more flexible than standard cable ties. Because these ties are difficult to fasten by hand, we recommend utilizing [PIN.005](#) collar fastening plier.



Features

- UL 94: HB self-extinguishing nylon
- Suitable for outdoor applications
- Rounded edges to avoid cable damage
- Operating temperature: -40 to +125°C [-40 to +257°F]

Agency Approvals

- CE

Black Double-headed Cable Ties													
Part Number	Pcs/Bag	Price	Length		Width		Min. Bundle Ø		Max. Bundle Ø		Tensile Strength		
			mm	in	mm	in	mm	in	mm	in	Kg	lb	
<u>COL.3.321</u>	100	\$14.00	265	10.43	9	0.35	15	0.59	63	2.48	40	88.18	
<u>COL.3.322</u>	100	\$20.00	360	14.17	9	0.35	25	0.98	93	3.66	40	88.18	



Specialty Cable Ties

Low Temperature Cable Ties

Made of black UV-stabilized nylon. These cable ties are resistant to low temperatures and suitable for outdoor applications.

Features

- UL 94: HB self-extinguishing nylon
- Suitable for outdoor applications
- Rounded edges to avoid cable damage
- Operating temperature: -50 to +85°C [-58 to +185°F]

Agency Approvals

- CE



Low Temperature Cable Ties												
Part Number	Pcs/ Bag	Price	Length		Width		Min. Bundle Ø		Max. Bundle Ø		Tensile Strength	
			mm	in	mm	in	mm	in	mm	in	Kg	lb
SEL.ICE.210R	100	\$1.75	140	5.51	3.5	0.14	2.5	0.10	36	1.41	15.29	33.72
SEL.ICE.223R	100	\$3.25	200	7.87	4.5	0.18	3	0.12	51	2	22.43	49.45
SEL.ICE.425R	100	\$4.75	280	11.02	4.5	0.18	5	0.20	75	2.99	22.43	49.45
SEL.ICE.426R	100	\$6.75	360	14.17	4.5	0.18	5	0.20	101	3.97	22.43	49.45
SEL.ICE.434R	100	\$11.50	360	14.17	7.36	0.29	5	0.20	101	3.97	46.90	103.41

CLICK TIE Cable Ties

These cable ties are low-cost, releasable, and reusable cable ties, suitable for lightweight loads. The double-locking head enables securing two cable bundles with one tie. The body is completely rounded to eliminate all sharp edges guaranteeing reliable performance every time.

Features

- UL 94: HB self-extinguishing nylon
- Suitable for outdoor applications
- Rounded edges to avoid cable damage
- Operating temperature: -50 to +85°C [-58 to +185°F]

Agency Approvals

- CE



CLICK TIE Cable Ties												
Part Number	Pcs/ Bag	Price	Length		Width		Min. Bundle Ø		Max. Bundle Ø		Tensile Strength	
			mm	in	mm	in	mm	in	mm	in	Kg	lb
CLT.10.2110R	100	\$2.75	118.11	4.65	3.30	0.13	3	0.12	26	1.02	7.13	15.73
CLT.10.2116R	100	\$6.75	237.99	9.37	4.06	0.16	4	0.15	61	2.4	13.76	30.34
CLT.10.2129R	100	\$9.00	318.23	12.52	4.31	0.17	5	0.20	83	3.26	15.80	34.84
CLT.10.2149R	100	\$20.00	496.02	19.53	5.58	0.22	40	1.57	140	5.51	28.04	61.82
CLT.10.2157	100	\$32.50	642.87	25.31	5.58	0.22	80	3.14	180	7.08	28.04	61.82






Tools and Accessories

Cable Tie Cutting Tool

The special angle of this cutter's tips enables clean cuts of the ties to sizes between 2.5 and 12.5 mm in width, maintaining the wired electric cables intact. The cutter can also be used for cutting cables.



Collar Fastening Metal Plier

This tool makes it easier to tighten and cut collars. Use with Double-headed Cable Ties. Leaves a short length of tail close to the head. For use with up to 9mm wide cable ties.



Cable Tie Gun Installation Tool

For use with cable ties up to 5mm wide. This tool helps to adjust the preload and cut the tie. Tightening torque of 2.5 kg to 12kg.



Bi-directional Nylon Square Bases



BAS.xMT.507



BAS.x.406

Note: Screw/mount not included

Bi-directional Nylon Square Bases						
Part Number	Pcs/Bag	Price	Color	Dual Adhesive	Dimensions	
					A	B
<u>BAS.2MT.507</u>	100	\$6.75	Natural	Yes	18.8 mm [0.74 in]	4.4 mm [0.17 in]
<u>BAS.3MT.507</u>	100	\$6.75	Black	Yes		
<u>BAS.2MT.508</u>	100	\$9.25	Natural	Yes	26.5 mm [1.04 in]	5.9 mm [0.23 in]
<u>BAS.3MT.508</u>	100	\$9.25	Black	Yes		
<u>BAS.2.406</u>	100	\$3.00	Natural	No		
<u>BAS.3.406</u>	100	\$3.00	Black	No		

