



Panel / Hole Mounts

Push Button Panel Mount

Sapiselco's push button mount offers a simple and effective method for securing cable ties to panels or surfaces with pre-drilled holes. Made of Nylon 6.6, this mount features a button-shaped base for press-fit installation into the back of the panel and a central guide to accept a cable tie (up to 4.5mm wide). This design allows for quick, hand-applied attachment, providing a secure anchor point for cable bundles in various applications.

The support can be applied by hand.

Features

- UL 94 V2 rated Nylon 6.6
- Halogen-free
- Rounded edges to avoid cable damage

Agency Approvals

- CE



SUB.3.2301

Push Button Panel Mount						
Part Number	Pcs/ Bag	Price	Color	Fits	Panel Hole Diameter	Maximum Panel Thickness
<u>SUB.3.2301</u>	1000	\$20.50	Black	0.18in maximum width cable ties	0.256 inches [6.5mm]	0.118 in [3mm]

Masonry Push Mounts

Sapiselco's ALE series masonry push mount is designed to provide a secure and efficient mounting point for cable ties. Made from durable Nylon 6.6, these mounts are typically pushed or inserted into pre-drilled holes in masonry surfaces. Once in place, they act as a stable anchor for a cable tie, allowing wires and cables to be neatly bundled and fixed to the desired location, streamlining cable management in various applications.

Features

- UL 94 HB rated Nylon 6.6
- Halogen-free
- Rounded edges to avoid cable damage

Agency Approvals

- CE



ALE.3.401

Masonry Push Mounts							
Part Number	Pcs/ Bag	Price	Color	Size	Fits	Minimum Hole Depth	Hole Diameter
<u>ALE.3.401</u>	100	\$5.75	Black	0.39 x 1.69in	0.35in maximum width cable ties	1.57in [40mm]	0.315 to 0.327in [8.0 to 8.3mm]
<u>ALE.3.402</u>	100	\$4.75	Black	0.31 x 1.42in	0.35in maximum width cable ties	1.30in [33mm]	0.236 to 0.248in [6.0 to 6.3mm]



Panel / Hole Mounts

Push-in panel mount

Sapiselco's SLE series fir tree mount is designed for quick, manual installation of cable ties onto surfaces with pre-drilled holes. This mount consists of a winged, fir tree press-fit body that easily inserts into a hole, along with a slotted head that accepts a cable tie up to 5mm wide. Made from Nylon 6.6, the SLE series mount provides a simple yet secure method for anchoring cable bundles, making them ideal for applications requiring efficient hand applications and reliable cable routing.



SLE.3.2101



Features

- Nylon 6.6
- Halogen-free
- Rounded edges to avoid cable damage

Agency Approvals

- CE

Push-in Panel Mounts							
Part Number	Pcs/ Bag	Price	Color	Fits	Size	Panel Hole Diameter	Panel Thickness
SLE.3.2101	100	\$23.50	Black	0.20in maximum width cable ties	0.31 x 0.79in	0.252 to 0.280in [6.4 to 7.1mm]	0.030 to 0.315in [0.75 to 8.0mm]

Winged Push Barbed Saddle Mount

Sapiselco's winged push barbed saddle mount offers a versatile and easily installed solution for securing cable bundles. This Nylon 6.6 mount allows for the application of cable ties and is designed for hand installation into a panel through-hole. This accessory offers a quick and straightforward method to anchor and route cables, contributing to organized and secure installations.



SUP.3.2707



Features

- UL 94 V2 rated Nylon 6.6
- Halogen-free
- Rounded edges to avoid cable damage
- Operating Temperature: -40 to 85°C [-40 to 185°F]

Agency Approvals

- CE

Winged Push Barbed Saddle Mounts							
Part Number	Pcs/ Bag	Price	Color	Fits	Size	Panel Hole Diameter	Panel Thickness
SUP.3.2707	500	\$12.00	Black	0.49in maximum width cable ties	1.50 x 1.77in	0.354 to 0.433in [9.0 to 11.0mm]	0.118 to 0.315in [3.0 to 8.0mm]



Cable Tie Tools

Cable Tie Cutting Tool

The special angle of this cutter's tips enables clean cuts of the ties to sizes between 2.5 and 12.5 mm in width, maintaining the wired electric cables intact. The cutter can also be used for cutting cables.

	
<u>PIN.009</u>	\$16.00

Collar Fastening Metal Plier

This tool makes it easier to tighten and cut collars. Use with Double-headed Cable Ties. Leaves a short length of tail close to the head. For use with up to 9mm wide cable ties.

	
<u>PIN.005</u>	\$14.50

Cable Tie Gun Installation Tool

For use with cable ties up to 5mm wide. This tool helps to adjust the preload and cut the tie. Tightening torque of 2.5 kg to 12kg.

	
<u>PIN.003</u>	\$21.00



Cable Ties Family Overview

General Purpose Nylon Cable Ties



SapiSelco general purpose Nylon 6.6 cable ties are slotted and held in place by the resistance of the elastic tooth against the rack. These cable ties are resistant to solvents and reagents, oil, gasoline, and hydrocarbons when used at low temperatures, in low concentrations, and for short periods of time. Assortment Kit available.

CLICKTIE®



These ties are low-cost, releasable, and reusable cable ties, suitable for lightweight loads. The double-locking head enables securing two cable bundles with one tie. The body is completely rounded to eliminate all sharp edges guaranteeing reliable performance every time.

These ties are low-cost, releasable, and reusable cable ties, suitable for lightweight loads.

Colored Nylon Cable Ties



SapiSelco colored Nylon 6.6 cable ties are useful in applications that require distinct identifiers. These ties are colored with inorganic dyes and are resistant to solvents and reagents, oil, gasoline, and hydrocarbons when used at low temperatures, in low concentrations, and for short periods of time. Assortment Kit available.

Stainless Steel Tooth Ties



SapiSelco stainless steel tooth ties are forged from nylon and hardened stainless steel with added Molybdenum. This ensures extremely high mechanical strength and optimal resistance to corrosion. A single central raised section makes this tie particularly flexible, while guaranteeing maximum strength at the same time.

UV Resistant Cable Ties



Exposure to sun and ultraviolet rays causes deterioration in nylon. SapiSelco specialty Nylon UV Resistant cable ties can resist and endure the harsh conditions of outdoor applications for up to 10 years. These ties can withstand temperatures up to 125°C [257°F].

Metal Detector Readable Cable Ties



These ties are fabricated with a special composite of 6.6 polyamide and metal powder and are sensitive to electromagnetic fields. They are recommended in the food, pharmaceutical and chemical industry. They are useful in applications where, for safety reasons, it is necessary for a metal detector to be able to detect even very small fragments of these ties that may be mixed in with products.

Specialty Cable Ties



Nylon Releasable Tab



Screw Mount



Low Temp



Nylon Lashing Cable Tie



Identification Ties



Double-headed [Collars]

Tools and Accessories



Cable Tie Cutting Tool



Collar Fastening Metal Plier



Cable Tie Gun Installation Tool



Bi-directional Nylon Square Bases