



Nylon Cable Ties with Stainless Steel Tooth

The increased size of the hardened stainless steel tooth (with added Molybdenum) ensures extremely high mechanical strength and optimal resistance to corrosion. The classic rack has been replaced by a single central raised section, making the MET tie particularly flexible, while guaranteeing maximum strength at the same time. The special design of the MET cable tie enables smoother insertion of the steel tooth, reducing the required insertion force.



- UL 94: V2 self-extinguishing nylon
- Designed for extreme applications
- Rounded edges to avoid cable damage
- Operating temperature:
-40° to +85°C [-40° to +185°F]
- UL Listed File E160935



Nylon Cable Ties with Stainless Steel Tooth																
Part Number	Pcs/ Bag	Price	Part Number	Pcs/ Bag	Price	Color	Length		Width		Min. Bundle Ø		Max. Bundle Ø		Tensile Strength	
							mm	in	mm	in	mm	in	mm	in	Kg	lb
MET.2.2102R	100	\$1.50	MET.2.2302R	1000	\$15.50	Natural	100	3.94	2.5	0.10	2	0.08	24	0.94	18	39.68
MET.3.2102R	100	\$1.50	MET.3.2302R	1000	\$16.00	Black	100	3.94	2.5	0.10	2	0.08	24	0.94	18	39.68
MET.2.2105R	100	\$4.00	MET.2.2305R	1000	\$41.50	Natural	200	7.87	2.5	0.10	2	0.08	55	2.17	18	39.68
MET.3.2105R	100	\$4.00	MET.3.2305R	1000	\$41.50	Black	200	7.87	2.5	0.10	2	0.08	55	2.17	18	39.68
MET.2.2110R	100	\$2.00	MET.2.2310R	1000	\$22.50	Natural	140	5.51	3.5	0.14	3	0.12	36	1.42	28	61.73
MET.3.2110R	100	\$2.50	MET.3.2310R	1000	\$23.00	Black	140	5.51	3.5	0.14	3	0.12	36	1.42	28	61.73
MET.2.2111R	100	\$4.00	MET.2.2311R	1000	\$38.50	Natural	200	7.87	3.5	0.14	3	0.12	55	2.17	28	61.73
MET.3.2111R	100	\$4.00	MET.3.2311R	1000	\$40.50	Black	200	7.87	3.5	0.14	3	0.12	55	2.17	28	61.73
MET.2.2112R	100	\$4.50	MET.2.2312R	1000	\$48.00	Natural	280	11.02	3.5	0.14	3	0.12	80	3.15	28	61.73
MET.3.2112R	100	\$4.50	MET.3.2312R	1000	\$48.00	Black	280	11.02	3.5	0.14	3	0.12	80	3.15	28	61.73
MET.2.2123R	100	\$4.50	MET.2.2323R	1000	\$43.00	Natural	186	7.32	4.5	0.18	3	0.12	51	2.01	40	88.18
MET.3.2123R	100	\$4.50	MET.3.2323R	1000	\$43.50	Black	186	7.32	4.5	0.18	3	0.12	51	2.01	40	88.18
MET.2.2140R	100	\$6.25	MET.2.2340R	1000	\$61.00	Natural	290	11.42	4.5	0.18	3	0.12	80	3.15	40	88.18
MET.3.2140R	100	\$6.25	MET.3.2340R	1000	\$62.00	Black	290	11.42	4.5	0.18	3	0.12	80	3.15	40	88.18
MET.2.2126R	100	\$7.25	MET.2.2326R	1000	\$73.00	Natural	360	14.17	4.5	0.18	3	0.12	103	4.06	40	88.18
MET.3.2126R	100	\$7.75	MET.3.2326R	10000	\$73.00	Black	360	14.17	4.5	0.18	3	0.12	103	4.06	40	88.18
MET.2.2548R	50	\$6.25	MET.2.2748R	500	\$58.00	Natural	340	13.39	7	0.28	6	0.24	90	3.54	70	154.32
MET.3.2548R	50	\$6.25	MET.3.2748R	500	\$60.00	Black	340	13.39	7	0.28	6	0.24	90	3.54	70	154.32
MET.2.2534R	50	\$7.75	MET.2.2734R	500	\$77.00	Natural	360	14.17	7.5	0.30	6	0.24	101	3.98	80	176.37
MET.3.2534R	50	\$7.75	MET.3.2734R	500	\$76.00	Black	360	14.17	7.5	0.30	6	0.24	101	3.98	80	176.37



Tools and Accessories

Cable Tie Cutting Tool

The special angle of this cutter's tips enables clean cuts of the ties to sizes between 2.5 and 12.5 mm in width, maintaining the wired electric cables intact. The cutter can also be used for cutting cables.



Collar Fastening Metal Plier

This tool makes it easier to tighten and cut collars. Use with Double-headed Cable Ties. Leaves a short length of tail close to the head. For use with up to 9mm wide cable ties.



Cable Tie Gun Installation Tool

For use with cable ties up to 5mm wide. This tool helps to adjust the preload and cut the tie. Tightening torque of 2.5 kg to 12kg.



Bi-directional Nylon Square Bases






BAS.xMT.507



BAS.x.406

Note: Screw/mount not included

Bi-directional Nylon Square Bases						
Part Number	Pcs/ Bag	Price	Color	Dual Adhesive	Dimensions	
					A	B
BAS.2MT.507	100	\$5.50	natural	Yes	18.8 mm [0.74 in]	4.4 mm [0.17 in]
BAS.3MT.507	100	\$5.50	black	Yes		
BAS.2MT.508	100	\$7.50	natural	Yes	26.5 mm [1.04 in]	5.9 mm [0.23 in]
BAS.3MT.508	100	\$7.50	black	Yes		
BAS.2.406	100	\$2.50	natural	No		
BAS.3.406	100	\$2.50	black	No		





Cable Ties Family Overview

Standard Nylon Cable Ties



SapiSelco standard Nylon 6.6 cable ties are slotted and held in place by the resistance of the elastic tooth against the rack. These cable ties are resistant to solvents and reagents, oil, gasoline, and hydrocarbons when used at low temperatures, in low concentrations, and for short periods of time.

Colored Nylon Cable Ties



SapiSelco colored Nylon 6.6 cable ties are useful in applications that require distinct identifiers. These ties are colored with inorganic dyes and are resistant to solvents and reagents, oil, gasoline, and hydrocarbons when used at low temperatures, in low concentrations, and for short periods of time.

Stainless Steel Tooth Ties




SapiSelco stainless steel tooth ties are forged from nylon and hardened stainless steel with added Molybdenum. This ensures extremely high mechanical strength and optimal resistance to corrosion. A single central raised section makes this tie particularly flexible, while guaranteeing maximum strength at the same time.

UV Resistant Cable Ties



Exposure to sun and ultraviolet rays causes deterioration in nylon. SapiSelco specialty Nylon UV Resistant cable ties can resist and endure the harsh conditions of outdoor applications for up to 10 years. These ties can withstand temperatures up to 125°C [257°F].

Metal Detector Readable Cable Ties



These ties are fabricated with a special composite of 6.6 polyamide and metal powder and are sensitive to electromagnetic fields. They are recommended in the food, pharmaceutical and chemical industry. They are useful in applications where, for safety reasons, it is necessary for a metal detector to be able to detect even very small fragments of these ties that may be mixed in with products.

Specialty Cable Ties



Re-Openable Push Button



Screw Mount



Button Hole



Marker Ties



Double-headed (Collars)

Tools and Accessories



Cable Tie Cutting Tool



Collar Fastening Metal Plier



Cable Tie Gun Installation Tool



Bi-directional Nylon Square Bases