

Stride SE2 Series Unmanaged Industrial Ethernet Switches

SE2 Series IP65 Rated



Features

- Rugged IP65 rating
- Tight M12 connections
- Wide temp range
- Panel mount
- 12, 24, 48 VDC and 18-30 VAC redundant input
- Complies with EN50155 and EN50121 industrial standards
- 5-year warranty



RoHS Compliant

Stride SE2 Series IP65 Rated Models

Part Number	Price	M12, IP65 10/100 ports	Input power (max.)	Operating Temp	Agency Approvals
SE2-SW5U-N65-T	\$299.00	5	4.6 W	-40 to +75°C (-40 to +167°F)	UL/cUL 61010-1, UL/cUL 6010-2-201 CE, EN50155, EN50121
SE2-SW8U-N65-T	\$399.00	8			

Stride SE2 Series Unmanaged Industrial Ethernet Switches

SE2 Series IP65 Rated

General Specifications	
Operating Mode	Store and forward wire speed switching, non-blocking
Devices Supported	All IEEE 802.3 compliant devices are supported
MAC Addresses	2K
Packet Buffer	1Mbit
Packet Forwarding Rate	1.2 Mpps
Latency	< 10 μ s
Storage Temperature Range	-40 to +85 °C (-40 to +185 °F)
Humidity (non-condensing)	5 to 95% RH
Pollution Degree	2
Vibration and Shock	IEC60068-2-6, -27, -32
Freefall	IEC60068-2-32
Safety	EN60950-1
EMI Emissions	FCC CFR47 Part 15, EN55022/CISPR22, Class A
EMS	IEC61000-4-2 (ESD): \pm 6kV (contact), \pm 8kV (air) IEC61000-4-3 (RS): 20V/m (80MHz ~ 2 GHz) IEC61000-4-4 (EFT): Power Port \pm 2kV; Data Port: \pm 2kV IEC61000-4-5 (Surge): Power Port: \pm 1kV/DM, \pm 2kV/CM IEC61000-4-6 (CS): 10V (150 kHz ~ 80 MHz) IEC61000-4-8 (Power frequency magnetic field): .50 Hz 100A/m IEC61000-4-9 (Pulsed magnetic field): 300A/m IEC61000-4-29 (Voltage short interruptions): 10ms 100%
RoHS and WEEE	RoHS (Pb free) and WEEE compliant
Packaging and Protection	Metal case, IP65
Agency Approvals	UL/cUL 61010-1 UL/cUL 61010-2-201, (UL file #E157382), CE, EN50155, EN50121

Power Details	
Power Input	Redundant Input M12 connector
Input Voltage	Class 2 Power Supply: 12-48 VDC, 18-30VAC 50/60 Hz
Power Input Ports	M12, male, A-coding, 4-pin
Reverse Power Protection	Yes

M12 Ports	
10/100BaseT ports	M12, female, D-coding, 4-pin
Ethernet Compliance	IEEE 802.3i, 802.3u, 802.3x
Auto-Crossover	Yes, allows you to use straight-through or crossover wired cables
Auto-Sensing Operation	Yes, full and half duplex
Auto-Negotiating Speed	Yes
Flow Control	Automatic
Cable Requirements	Twisted pair (Cat5 or better) (shielded recommended)
Max. Cable Distance	100 meters
<i>*Note-M12 caps (ZP-JBH-CAP) need to be used on open (disconnect) ports.</i>	



Front Panel LEDs		
LED	State	Description
Power 1 LED	On	Power 1 connected and operational
	Off	Power 1 no voltage
Power 2 LED	On	Power 2 connected and operational
	Off	Power 2 no voltage
Ethernet Port Connection Status LED	On	Ethernet port connected
	Blinking	Ethernet port active
	Off	Ethernet port no connection

Stride SE2 Series Unmanaged Industrial Ethernet Switches

SE2 Series IP65 Rated

Dimensions

mm [Inches]



See our website: www.AutomationDirect.com for complete engineering drawings.

Stride Unmanaged Industrial Ethernet Switches

Unmanaged Switches offer:

- Reliable connectivity
- Industrially hardened
- Simple installation



For detailed specifications on all models, see following pages



		SE Series	SE2 Series DIN Rail	SE2 Series IP65
Price				
		starting at \$103	starting at \$75	starting at \$299
Broadcast Storm Protection				
		—	✓	—
Industrial Temperature Ranges				
	<i>Standard Temp</i>	-10 to +60°C	-10 to +60°C	—
	<i>Wide Temp</i>	-40 to +85°C	-40 to +75°C	-40 to +75°C
Port Connectivity				
	<i>Port Count</i>	2 to 9	2 to 16	5, 8
	<i>RJ45 Port Speed</i>	up to 100 Mbps	up to 1000 Mbps	—
	<i>M12 Port Speed</i>	—	—	up to 100 Mbps
	<i>Fiber Optic Ports</i>	✓	✓	—
	<i>PoE+ Ports</i>	—	✓	—
	<i>SFP Ports</i>	—	✓	—
Mounting				
	<i>DIN Rail Mount</i>	✓	✓	—
	<i>Panel Mount</i>	✓	✓	✓
Input Power				
	<i>Redundant Power Inputs</i>	✓	✓	✓
	<i>Reverse Polarity Protection</i>	✓	✓	✓
	<i>Power LED</i>	✓	✓	✓
Agency Approvals				
	<i>UL508 or UL61010</i>	✓	✓	✓
	<i>Haz Loc-Class 1 Div 2</i>	✓	✓	—
	<i>IECEX</i>	✓	—	—
	<i>ATEX Zone 2</i>	✓	—	—
	<i>CE</i>	✓	✓	✓
	<i>EN50155 & EN50121</i>	—	—	✓
Warranty				
		2 years	5 years	5 years
Activity, Link & Speed LEDs				
		✓	✓	✓