

Stride Unmanaged Industrial Ethernet Switches

Unmanaged Switches offer:

- Reliable connectivity
- Industrially hardened
- Simple installation

For detailed specifications on all models, see following pages



| | | SE Series | SE2 Series DIN Rail | SE2 Series IP65 |
|--|------------------------------------|-------------------|---------------------|-------------------|
| Price | | | | |
| | | starting at \$103 | starting at \$75 | starting at \$299 |
| Broadcast Storm Protection | | | | |
| | | — | ✓ | — |
| Industrial Temperature Ranges | | | | |
| | <i>Standard Temp</i> | -10 to +60°C | -10 to +60°C | — |
| | <i>Wide Temp</i> | -40 to +85°C | -40 to +75°C | -40 to +75°C |
| Port Connectivity | | | | |
| | <i>Port Count</i> | 2 to 9 | 2 to 16 | 5, 8 |
| | <i>RJ45 Port Speed</i> | up to 100 Mbps | up to 1000 Mbps | — |
| | <i>M12 Port Speed</i> | — | — | up to 100 Mbps |
| | <i>Fiber Optic Ports</i> | ✓ | ✓ | — |
| | <i>PoE+ Ports</i> | — | ✓ | — |
| | <i>SFP Ports</i> | — | ✓ | — |
| Mounting | | | | |
| | <i>DIN Rail Mount</i> | ✓ | ✓ | — |
| | <i>Panel Mount</i> | ✓ | ✓ | ✓ |
| Input Power | | | | |
| | <i>Redundant Power Inputs</i> | ✓ | ✓ | ✓ |
| | <i>Reverse Polarity Protection</i> | ✓ | ✓ | ✓ |
| | <i>Power LED</i> | ✓ | ✓ | ✓ |
| Agency Approvals | | | | |
| | <i>UL508 or UL61010</i> | ✓ | ✓ | ✓ |
| | <i>Haz Loc-Class 1 Div 2</i> | ✓ | ✓ | — |
| | <i>IECEX</i> | ✓ | — | — |
| | <i>ATEX Zone 2</i> | ✓ | — | — |
| | <i>CE</i> | ✓ | ✓ | ✓ |
| | <i>EN50155 & EN50121</i> | — | — | ✓ |
| Warranty | | | | |
| | | 2 years | 5 years | 5 years |
| Activity, Link & Speed LEDs | | | | |
| | | ✓ | ✓ | ✓ |