


# Bryant® Wire Management Products

## Cord Grips Family Overview

### Strain Relief Grips



*Liquidtight and dust-tight fittings available*

*Endless weave for easy installation*

Strain Relief Grips are used to connect cable enclosures and industrial equipment. These grips prevent cable pullout at the point of termination due to tension, vibration, flexure or motion. Used in conjunction with bus drop support grips and safety springs, they are an integral part of an overall support and strain relief system. These grips are suitable for indoor or outdoor use where subject to moisture, splash or washdown. Examples are crane hoist and pendant drop stations, hand tools, pumps, and processing equipment.


### Deluxe Cord Strain Relief Grips

- Endless weave for easy installation
- Indoor and outdoor applications
- Provides arc-of-bend control
- Stainless steel mesh
- Corrosion resistant
- Liquid-tight and dust-tight
- Range 0.187" – 1.687"

### Dust-tight Strain Relief Grips

- Dust-tight
- Galvanized steel mesh
- For indoor applications only
- deal for use in bus drop systems, motor connections, panel boards, and internal wiring of machines
- Range 0.32" – 1.70"

### Support Grips



*Extra large reinforced eye*

*Strand equalizers maintain equal loading*

Support Grips are applied to the vertical or horizontal runs of cable or service lines to support dead weight and reduce potential damage due to breakage or stress. These grips are designed to be used indoors for cable support where flexible cable connects electrical equipment to bus duct. Applications also include support for air hoses and water hoses.

### Standard Duty Support Grips

- Single U eye closed mesh fits over cable end
- Indoor and outdoor applications
- Split mesh is used when cable end is inaccessible
- Strand equalizers reinforce gripping strength and position; distributes load equally
- Range 0.54" – 1.74"

### Bus Drop Support Grips

- Light duty
- Strand equalizers position wires for equal loading
- Single variable weave
- Indoor use only
- Range 0.24" – 1.25"

**BRYANT®**

# Standard Duty Support Grips - Closed Mesh



## Features

- Closed grips with U eye
- Single weave variable mesh
- Tin-coated bronze grips are non-magnetic minimizing hysteresis and resultant heat build-up which can lead to cable degradation and reduced life
- Uniform gripping power
- Endless weave
- Strand equalizers position wires for equal loading

## Applications

- Commercial towers
- Elevator shafts
- Buildings
- Utility poles - telephone and power
- Construction
- Factories

## Agency Approvals


- CSA Certified File LR701228



# BRYANT®

| Bryant® Single Eye, Closed Mesh Support Grips |                                  |  |                        |                         |               |         |
|---|----------------------------------|--|------------------------|-------------------------|---------------|---------|
| Part Number                                   | Cable Diameter Range Inches (cm) | Approximate Breaking Strength Pounds (Newtons) | Eye Length Inches (cm) | Mesh Length Inches (cm) | Weight (lbs.) | Price   |
| SPC050U                                       | 0.50-0.62 (1.27-1.57)            | 530 (2,357)                                    | 7.0 (17.78)            | 10.0 (25.40)            | 0.1           | \$15.50 |
| SPC062U                                       | 0.63-0.74 (1.60-1.88)            | 790 (3,514)                                    | 8.0 (20.32)            | 10.0 (25.40)            | 0.2           | \$17.00 |
| SPC075U                                       | 0.75-0.99 (1.90-2.51)            | 1,020 (4,537)                                  | 8.0 (20.32)            | 13.0 (33.02)            | 0.2           | \$19.50 |
| SPC100U                                       | 1.00-1.24 (2.54-3.15)            | 1,610 (7,161)                                  | 9.0 (22.86)            | 14.0 (35.56)            | 0.3           | \$21.50 |
| SPC125U                                       | 1.25-1.49 (3.17-3.78)            | 1,610 (7,161)                                  | 10.0 (25.40)           | 15.0 (38.10)            | 0.4           | \$23.00 |
| SPC150U                                       | 1.50-1.74 (3.81-4.42)            | 1,610 (7,161)                                  | 12.0 (30.48)           | 17.0 (43.18)            | 0.4           | \$25.50 |

E = Eye Length  
M = Mesh Length



**CAUTION:** Never use grip to approximate breaking strength. Refer to technical data page for safety and working load factors. Banding is necessary to guard against accidental release of grip and provide maximum reliability.

# Bus Drop Support Grips

Company Information

Terminal Blocks

Power Distribution Blocks

Wiring Accessories

ZIPLink Connection System

Multi-wire Connectors

Sensor Cables and Connectors

M12 Junction Blocks

Panel Interface Connectors

Wiring Duct

Cable Ties

Wire

Flexible Cords

Bulk Multi-conductor Cables

Wire Management Products

Power Supplies

DC Converters

Transformers and Filters

Circuit Protection

Tools

Test Equipment

Enclosures

Enclosure Climate Control

Safety: Electrical Components

Safety: Protective Wear

Terms and Conditions

## Features

- Single variable weave
- Galvanized steel for additional holding power in abrasive environments
- Strand equalizers position wires for equal loading
- Light-duty support
- Indoor only, permanent support
- Easily installed
- Single eye

## Applications


- All factory equipment
- Cable drops for electrical connections

## Agency Approvals

- UL Listed File E167220
- CSA Certified File LR701228




# BRYANT®



**BDS56U**

E = Eye Length  
M = Mesh Length




**S80**

| Bryant® Single Eye, Closed Mesh Bus Drop Support Grips |                                  |  |                        |                         |               |         |
|--|----------------------------------|--|------------------------|-------------------------|---------------|---------|
| Part Number  | Cable Diameter Range Inches (cm) | Approximate Breaking Strength Pounds (Newtons) | Eye Length Inches (cm) | Mesh Length Inches (cm) | Weight (lbs.) | Price   |
| <b>BDS24U</b>  | 0.24-0.32 (0.61-0.81)            | 350 (1,557)                                    | 3.0 (7.62)             | 3.50 (8.89)             | 0.1           | \$7.00  |
| <b>BDS32U</b>  | 0.32-0.43 (0.81-1.09)            | 450 (2,002)                                    | 4.0 (10.16)            | 4.00 (10.16)            | 0.1           | \$7.00  |
| <b>BDS43U</b>  | 0.43-0.56 (1.09-1.42)            | 550 (2,446)                                    | 6.0 (15.24)            | 4.75 (12.06)            | 0.1           | \$8.50  |
| <b>BDS56U</b>  | 0.56-0.73 (1.42-1.85)            | 1,000 (4,448)                                  | 7.0 (17.78)            | 6.00 (15.24)            | 0.1           | \$9.50  |
| <b>BDS73U</b>  | 0.73-0.85 (1.85-2.16)            | 1,400 (6,227)                                  | 7.0 (17.78)            | 6.75 (17.14)            | 0.1           | \$10.00 |
| <b>BDS85U</b>  | 0.85-1.00 (2.16-2.54)            | 1,400 (6,227)                                  | 8.0 (20.32)            | 8.00 (20.32)            | 0.1           | \$10.50 |
| <b>BDS100U</b>   | 1.00-1.25 (2.54-3.17)            | 1,500 (6,672)                                  | 9.0 (22.86)            | 9.50 (24.13)            | 0.2           | \$11.00 |

| Bus Drop Safety Springs |                      |  |                    |                                      |               |        |
|-------------------------|----------------------|--|--------------------|--------------------------------------|---------------|--------|
| Part Number             | Diameter Inches (cm) | Approximate Breaking Strength Pounds (Newtons) | Length Inches (cm) | Maximum Deflection                   | Weight (lbs.) | Price  |
| <b>S40</b>              | 0.75 (1.90)          | 500 (2,224)                                    | 8.25 (20.95)       | 2¾ in. at 40 lbs. (6.67 cm at 178 N) | 0.2           | \$4.00 |
| <b>S80</b>              | 1.00 (2.54)          | 850 (3,781)                                    | 8.25 (20.95)       | 3⅞ in. at 80 lbs. (7.94 cm at 356 N) | 0.4           | \$6.00 |



**CAUTION:** Never use grip to approximate breaking strength. Refer to technical data page for safety and working load factors. Banding is necessary to guard against accidental release of grip and provide maximum reliability.

# Technical Data

## Working Load Factors for Wire Mesh Grips

There are many variables associated with the use of wire mesh cable grips. Working load is an estimation of several factors including tension, cable diameter, number of cables gripped, gripping surface and more. Safety factors associated in the product's use must be considered together with the effects of abrasion, corrosion, prior use and abuse and other variables specific to the application.

The appropriate breaking strength of a Bryant® cable grip

represents an average calculation based on data established from actual testing performed in our engineering laboratories. Under normal usage conditions, the recommended factor of safety is 5 for pulling grips and 10 for support grips.

Any warranty as to quality, performance of fitness-for-use of the grips is always premised on the condition that the published strengths apply only to new, unused grips, and that such products are properly stored, handled, used, maintained and inspected by the user at a frequency appropriate for the use and condition of the grip.

## Example

| Grip Style | Part Number | Approximate Breaking Strength | Safety Factor | Max. Recommended Load |
|------------|-------------|-------------------------------|---------------|-----------------------|
| Pulling    | PA075       | 4000 lbs.                     | 5             | 800 lbs.              |
| Support    | SPC150U     | 1610 lbs.                     | 10            | 161 lbs.              |

**Note:** The maximum recommended working load is the greatest tension to be exerted on a grip for any application, with a margin of safety to protect against unforeseen and unusual circumstances.

## Wire Mesh Grip Materials

| Material                       | Features                                      | Product Group       |
|--------------------------------|---|---------------------|
| Galvanized steel wire          | High strength                                 | Pulling grips       |
|                                | Not subject to continuous outside environment | Bus drop grips      |
|                                |   | Strain relief grips |
| Tin-Coated bronze wire         | Corrosion-resistant for normal outside areas  | Support grips       |
|                                | Non-magnetic                                  |                     |
|                                | Moderate strength                             |                     |
| Stainless steel wire (302/304) | Corrosion resistant                           | Strain relief grips |

## Applicable Code Requirements:

Bryant Economy Cable Grips meet the following requirements

|             |  |
|-------------|--|
| NEC® 300.19 | Support of conductors in vertical raceways     |
| NEC® 350    | Liquidtight flexible metal conduit termination |
| NEC® 400.14 | Flexible cord and cable protection             |
| NEC® 400.10 | Strain relief at joints and terminals          |

## Operating Temperatures

| Material                   | Temperature Range                 |
|----------------------------|-----------------------------------|
| Aluminum                   | -40°F to +300°F (-40°C to +149°C) |
| Aluminum Deluxe Cord Grips | -30°F to +240°F (-34°C to +115°C) |

## Flammability (Non-metallic deluxe cord Grips will not support combustion)

| Component | Rating   |
|-----------|----------|
| Mesh Grip | UL 94HB  |
| Fitting   | UL 94V-2 |

## Hazardous Locations

| Product Categories  |
|---|
| The product categories listed on the right are suitable Deluxe cord grip, aluminum fitting for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 |
| Dust-tight strain relief grips  |

## Wet Locations


| Product Categories   |
|--|
| The products noted to the right are suitable for use in wet locations when a listed sealing ring is used between box and fitting |
| Deluxe cord grip, aluminum fitting   |

# Multiple Cable/Grip Selection Chart

## Multiple Cable Selection Charts for Cables and Wires of Unequal Diameters

How to choose the correct grip size:

1. Find the grip circumference range by measuring the circumference of the bundle of different diameter cables to be gripped (see illustration).
2. Divide the bundle circumference by 3.14 to determine the diameter.
3. Choose a grip offering a range of cable diameters the same as the cable diameter.



## Selection Chart for Determining Grip Size for Multiple Equal Diameter Cables Held in a Single Grip

- ❶ Under "Number of Cables in One Grip", find the diameter range of your cables in vertical column. Read Grip Size and Grip Diameter Range to the left.
- ❷ If your diameter is the maximum of the range shown, stay with the same size grip.
- ❸ Example: 3 cables, each with 0.89" (2.26 cm) diameter, select a 1.50" - 1.74" (3.81 cm - 4.42 cm) range or 150 Grip Size.

|                     |                            | Number of Cables in One Grip |                          |                          |                          |                          |                          |                          |                          |
|---------------------|----------------------------|------------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|
|                     | Grip Size                  | Grip Dia. Range Inches (cm)  | 2                        | 3                        | 4                        | 5                        | 6 / 7                    | 8                        | 9                        |
| Pulling and Support | 50                         | 0.50-0.61<br>(1.27-1.55)     | 0.30-0.38<br>(0.76-0.97) | 0.25-0.31<br>(0.63-0.79) | 0.22-0.27<br>(0.56-0.69) | 0.19-0.24<br>(0.48-0.61) | 0.17-0.22<br>(0.43-0.56) | 0.15-0.19<br>(0.38-0.48) | 0.14-0.18<br>(0.36-0.46) |
|                     | 62                         | 0.62-0.74<br>(1.57-1.88)     | 0.38-0.44<br>(0.97-1.12) | 0.31-0.36<br>(0.79-0.91) | 0.27-0.31<br>(0.69-0.79) | 0.24-0.29<br>(0.61-0.74) | 0.22-0.26<br>(0.56-0.66) | 0.19-0.23<br>(0.48-0.58) | 0.18-0.21<br>(0.46-0.53) |
|                     | 75                         | 0.75-0.99<br>(1.90-2.51)     | 0.44-0.59<br>(1.12-1.50) | 0.36-0.49<br>(0.91-1.24) | 0.31-0.42<br>(0.79-1.07) | 0.29-0.38<br>(0.74-0.97) | 0.26-0.34<br>(0.66-0.86) | 0.23-0.31<br>(0.58-0.79) | 0.21-0.28<br>(0.53-0.71) |
|                     | 100                        | 1.00-1.24<br>(2.54-3.15)     | 0.59-0.75<br>(1.50-1.90) | 0.49-0.63<br>(1.24-1.60) | 0.42-0.54<br>(1.07-1.37) | 0.38-0.48<br>(0.97-1.22) | 0.34-0.43<br>(0.86-1.09) | 0.31-0.39<br>(0.79-0.99) | 0.28-0.35<br>(0.71-0.89) |
|                     | 125                        | 1.25-1.49<br>(3.17-3.78)     | 0.75-0.90<br>(1.90-2.29) | 0.63-0.76<br>(1.60-1.93) | 0.54-0.65<br>(1.37-1.65) | 0.48-0.58<br>(1.22-1.47) | 0.43-0.52<br>(1.09-1.32) | 0.39-0.46<br>(0.99-1.17) | 0.35-0.42<br>(0.89-1.07) |
|                     | 150                        | 1.50-1.74<br>(3.81-4.42)     | 0.90-1.07<br>(2.29-2.72) | 0.76-0.89<br>(1.93-2.26) | 0.65-0.77<br>(1.65-1.96) | 0.58-0.67<br>(1.47-1.70) | 0.52-0.60<br>(1.32-1.52) | 0.46-0.54<br>(1.17-1.37) | 0.42-0.49<br>(1.07-1.24) |
|                     | 175                        | 1.75-1.99<br>(4.44-5.05)     | 1.07-1.22<br>(2.72-3.10) | 0.89-1.02<br>(2.26-2.59) | 0.77-0.88<br>(1.96-2.24) | 0.67-0.77<br>(1.70-1.96) | 0.60-0.69<br>(1.52-1.75) | 0.54-0.62<br>(1.37-1.57) | 0.49-0.56<br>(1.24-1.42) |
|                     | 200                        | 2.00-2.49<br>(5.08-6.32)     | 1.22-1.53<br>(3.10-3.89) | 1.02-1.28<br>(2.59-3.25) | 0.88-1.10<br>(2.24-2.79) | 0.77-0.96<br>(1.96-2.44) | 0.69-0.86<br>(1.75-2.18) | 0.62-0.77<br>(1.57-1.96) | 0.56-0.71<br>(1.42-1.80) |
|                     | 250                        | 2.50-2.99<br>(6.35-7.59)     | 1.53-1.83<br>(3.89-4.65) | 1.28-1.53<br>(3.25-3.89) | 1.10-1.32<br>(2.79-3.35) | 0.96-1.16<br>(2.44-2.95) | 0.86-1.03<br>(2.18-2.62) | 0.77-0.93<br>(1.96-2.36) | 0.71-0.85<br>(1.80-2.16) |
|                     | 300                        | 3.00-3.49<br>(7.62-8.86)     | 1.83-2.14<br>(4.65-5.44) | 1.53-1.79<br>(3.89-4.55) | 1.32-1.54<br>(3.35-3.91) | 1.16-1.35<br>(2.95-3.43) | 1.03-1.20<br>(2.62-3.05) | 0.93-1.08<br>(2.36-2.74) | 0.85-0.99<br>(2.16-2.51) |
|                     | 350                        | 3.50-3.99<br>(8.89-10.13)    | 2.14-2.44<br>(5.44-6.20) | 1.79-2.05<br>(4.55-5.21) | 1.54-1.76<br>(3.91-4.47) | 1.35-1.54<br>(3.43-3.91) | 1.20-1.37<br>(3.05-3.48) | 1.08-1.24<br>(2.74-3.15) | 0.99-1.13<br>(2.51-2.87) |
|                     | 400                        | 4.00-4.49<br>(10.16-11.40)   | 2.44-2.75<br>(6.20-6.98) | 2.05-2.30<br>(5.21-5.84) | 1.76-1.98<br>(4.47-5.03) | 1.54-1.74<br>(3.91-4.42) | 1.37-1.55<br>(3.48-3.94) | 1.24-1.39<br>(3.15-3.53) | 1.13-1.27<br>(2.87-3.23) |
| 450                 | 4.50-4.99<br>(11.43-12.67) | 2.75-3.06<br>(6.98-7.77)     | 2.30-2.56<br>(5.84-6.50) | 1.98-2.20<br>(5.03-5.59) | 1.74-1.93<br>(4.42-4.90) | 1.55-1.72<br>(3.94-4.37) | 1.39-1.55<br>(3.53-3.94) | 1.27-1.41<br>(3.23-3.58) |                          |