




Synchronous Drive Components

Taper-Lock®* Style Bushings



TAPER 0.75 INCHES PER 12 INCHES ON DIAMETER

| Taper-Lock® Bushings | | | | | | | | | | | | | |
|----------------------|---------|-------------|--------|-------------------------|----------------|---------------------------|-------------|-------------------------|-------|-----------------|-----------------|------------|-----------|
| Part Number | Price | Weight (lb) | Series | Torque Capacity (lb-in) | Bore Size (in) | | Keyway (in) | Nominal Dimensions (in) | | | Mounting Screws | | Material* |
| | | | | | Nominal | Max. with Shallow Keyseat | | A | B | D (Bolt Circle) | # | Size | |
| TL-1108-0500 | \$11.00 | 0.4 | 1108 | 1300 | 0.500 | | 1/8 | 1.511 | 0.875 | 1.453 | 2 | 1/4 x 1/2 | S |
| TL-1108-0625 | \$11.00 | 0.3 | 1108 | 1300 | 0.625 | | 3/16 | 1.511 | 0.875 | 1.453 | 2 | 1/4 x 1/2 | S |
| TL-1108-0750 | \$11.00 | 0.3 | 1108 | 1300 | 0.750 | | 3/16 | 1.511 | 0.875 | 1.453 | 2 | 1/4 x 1/2 | S |
| TL-1108-0875 | \$11.00 | 0.3 | 1108 | 1300 | 0.875 | | 3/16 | 1.511 | 0.875 | 1.453 | 2 | 1/4 x 1/2 | S |
| TL-1108-1000 | \$11.00 | 0.2 | 1108 | 1300 | 1.00 | | 1/4 | 1.511 | 0.875 | 1.453 | 2 | 1/4 x 1/2 | S |
| TL-1210-0625 | \$12.00 | 0.6 | 1210 | 3600 | 0.625 | | 3/16 | 1.875 | 1.0 | 1.750 | 2 | 3/8 x 5/8 | S |
| TL-1210-0750 | \$12.00 | 0.5 | 1210 | 3600 | 0.750 | | 3/16 | 1.875 | 1.0 | 1.750 | 2 | 3/8 x 5/8 | S |
| TL-1210-0875 | \$12.00 | 0.6 | 1210 | 3600 | 0.875 | | 3/16 | 1.875 | 1.0 | 1.750 | 2 | 3/8 x 5/8 | S |
| TL-1210-1000 | \$12.00 | 0.4 | 1210 | 3600 | 1.000 | 1.25 | 1/4 | 1.875 | 1.0 | 1.750 | 2 | 3/8 x 5/8 | S |
| TL-1210-1125 | \$12.00 | 0.4 | 1210 | 3600 | 1.125 | | 1/4 | 1.875 | 1.0 | 1.750 | 2 | 3/8 x 5/8 | S |
| TL-1610-0625 | \$13.00 | 0.9 | 1610 | 4300 | 0.625 | | 3/16 | 2.250 | 1.0 | 2.125 | 2 | 3/8 x 5/8 | S |
| TL-1610-0750 | \$13.00 | 0.9 | 1610 | 4300 | 0.750 | | 3/16 | 2.250 | 1.0 | 2.125 | 2 | 3/8 x 5/8 | S |
| TL-1610-0875 | \$13.00 | 0.9 | 1610 | 4300 | 0.875 | | 3/16 | 2.250 | 1.0 | 2.125 | 2 | 3/8 x 5/8 | S |
| TL-1610-1000 | \$13.00 | 0.8 | 1610 | 4300 | 1.000 | | 1/4 | 2.250 | 1.0 | 2.125 | 2 | 3/8 x 5/8 | S |
| TL-1610-1125 | \$13.00 | 0.8 | 1610 | 4300 | 1.125 | | 1/4 | 2.250 | 1.0 | 2.125 | 2 | 3/8 x 5/8 | S |
| TL-1610-1250 | \$13.00 | 0.7 | 1610 | 4300 | 1.250 | | 1/4 | 2.250 | 1.0 | 2.125 | 2 | 3/8 x 5/8 | S |
| TL-1610-1375 | \$13.00 | 0.6 | 1610 | 4300 | 1.375 | | 5/16 | 2.250 | 1.0 | 2.125 | 2 | 3/8 x 5/8 | S |
| TL-2012-0750 | \$18.50 | 1.8 | 2012 | 7150 | 0.750 | | 3/16 | 2.750 | 1.250 | 2.625 | 2 | 7/16 x 7/8 | S |
| TL-2012-0875 | \$18.50 | 1.7 | 2012 | 7150 | 0.875 | | 3/16 | 2.750 | 1.250 | 2.625 | 2 | 7/16 x 7/8 | S |
| TL-2012-1000 | \$18.50 | 1.6 | 2012 | 7150 | 1.000 | 2 | 1/4 | 2.750 | 1.250 | 2.625 | 2 | 7/16 x 7/8 | S |
| TL-2012-1125 | \$18.50 | 1.5 | 2012 | 7150 | 1.125 | | 1/4 | 2.750 | 1.250 | 2.625 | 2 | 7/16 x 7/8 | S |
| TL-2012-1250 | \$18.50 | 1.5 | 2012 | 7150 | 1.250 | | 1/4 | 2.750 | 1.250 | 2.625 | 2 | 7/16 x 7/8 | S |
| TL-2012-1375 | \$18.50 | 1.4 | 2012 | 7150 | 1.375 | | 5/16 | 2.750 | 1.250 | 2.625 | 2 | 7/16 x 7/8 | S |
| TL-2517-0875 | \$31.00 | 3.8 | 2517 | 11600 | 0.875 | | 3/16 | 3.375 | 1.750 | 3.250 | 2 | 1/2 x 1 | S |
| TL-2517-1000 | \$31.00 | 3.7 | 2517 | 11600 | 1.000 | | 1/4 | 3.375 | 1.750 | 3.250 | 2 | 1/2 x 1 | S |
| TL-2517-1125 | \$31.00 | 3.5 | 2517 | 11600 | 1.125 | 2.5 | 1/4 | 3.375 | 1.750 | 3.250 | 2 | 1/2 x 1 | S |
| TL-2517-1250 | \$31.00 | 3.4 | 2517 | 11600 | 1.250 | | 1/4 | 3.375 | 1.750 | 3.250 | 2 | 1/2 x 1 | S |
| TL-2517-1375 | \$31.00 | 3.3 | 2517 | 11600 | 1.375 | | 5/16 | 3.375 | 1.750 | 3.250 | 2 | 1/2 x 1 | S |

*Taper-Lock® is a registered trademark of Reliance Electric.

* S = Steel

Note: Stock bore sizes shown. Bushings may be re-bored up the maximum size listed. Maximum bores may require a shallow keyway and rectangular key



Synchronous Drive Components

Product Overview



Timing Pulleys



Bushings




Timing Belts

Timing pulleys, bushings, and belts allow you to change speed and torque while connecting mechanically rotating components.

- Select pulley sizes in order to accomplish the speed or torque change that you need.
- Bushings allow you to connect the same pulleys to different sized shafts, or vice versa.
- Synchronous drive belts and pulleys utilize teeth to prevent slippage and unwanted speed variations.

Note: For pulley speeds in excess of 6,000 RPM, pulleys should be dynamically balanced.



Drive Component Selection

1. Determine required torque (ft·lbs) and rpm of driven shaft.
2. Determine design horsepower:

$$DHP = \frac{T \cdot N \cdot sf}{5,252}$$

Where: T = torque (ft·lb)
 N = rpm
 sf = service factor per table

| Service Factors | | | |
|-------------------|--------------|-----------------|------------|
| Machine Type | <8hr per day | 8-16 hr per day | Continuous |
| Smooth Running | 1.0 | 1.2 | 1.4 |
| Light Shock Loads | 1.3 | 1.5 | 1.7 |
| Heavy Shock Loads | 1.7 | 1.9 | 2.1 |


3. Determine Pitch (MXL XL or L) and belt width required by reading Design Horsepower Chart.
4. Select driver and driven pulleys to match desired speed or torque change.
5. Determine belt length per belt length calculation.

Note: AutomationDirect provides an online configuration tool to assist with pulley and belt sizing.
 See: www.automationdirect.com/selectors/beltandpulley




Synchronous Drive Components

Design Horsepower Chart



Drive Component Selection Continued



Belt Length Calculations

$$L = 2C + 1.57 (D + d) + \frac{(D-d)^2}{4C}$$

Where:

- L = Length of belt at pitch line (in inches)
- C = Center distance (in inches)
- D = Pitch diameter (in inches) of large sprocket
- d = Pitch diameter (in inches) of small sprocket