



Tamperproof Thermostats

Applications

Normally Closed (N.C.)

Normally Closed tamperproof (pre-set) thermostats have a red module and contacts that open when the air temperature rises above the setpoint. Uses may include regulating heaters or switching signal devices when temperature has fallen below the setpoint value.

Normally Open (N.O.)

Normally Open tamperproof (pre-set) thermostats have a blue module and contacts that close when the air temperature rises above the setpoint. Uses may include regulating cooling devices (heat exchangers, filter fans, vortex coolers, etc) or switching signal devices when temperature exceeds the setpoint value.

Features

- Compact design
- Fixed set points
- Color coded modules
- DIN rail mounting



011600-00



011610-02



011630-00

Tamperproof Thermostats Specifications	
Sensor Element	Thermostatic bimetal
Contact Type	Snap-action Contact
Contact Resistance	<20 mΩ
Service Life	>100,000 cycles
Max. Switching Capacity	10A resistive / 2A inductive @ 120VAC 5A resistive / 1.6 A inductive @ 240VAC DC 30W (24-72 VDC)
Max. Inrush Current	AC 16A for 10 sec.
Minimum Load	20 mA (all voltages)
Housing	Plastic, UL 94V-0, light gray
Mounting	Clip for 35mm DIN rail, EN 60715
Mounting Position	Vertical
Operating Temperature	-40 to 176°F [-40 to 80°C]
Storage Temperature	-49 to 176°F [-45 to 80°C]
Protection Type	IP20
Approvals	CE, VDE, EAC, UL Recognized File No. E164102, RoHS 2 compliant

Note: Tolerance is plus or minus (±) the specified number.



Tamperproof Thermostats

Tamperproof Thermostats							
Type	Part Number	Price	Contact	Switch-off	Switch-on	Connection	Weight
Single Thermostats	011600-00	\$12.00	N.C.	59 ± 9°F [15 ± 5°C]	41 ± 9°F [5 ± 5°C]	2-pole terminal, 0.8 Nm max. clamping torque 14 AWG [2.5 mm ²] Nm max. solid wire or stranded wire with wire end terminal	0.05 lb [23 g]
	011600-01	\$12.00	N.C.	77 ± 9°F [25 ± 5°C]	59 ± 9°F [15 ± 5°C]		
	011610-00	\$12.00	N.O.	104 ± 12.6°F [40 ± 7°C]	122 ± 11°F [50 ± 6°C]		
	011610-02	\$12.00	N.O.	77 ± 12.6°F [25 ± 7°C]	95 ± 11°F [35 ± 6°C]		
Dual Thermostats	011630-00	\$22.50	N.C.	59 ± 9°F [15 ± 5°C]	41 ± 9°F [5 ± 5°C]	4-pole terminal, 0.8 Nm max. clamping torque 14 AWG [2.5 mm ²] max. solid wire or stranded wire with wire end terminal	0.08 lb [40 g]
			N.O.	104 ± 12.6°F [40 ± 7°C]	122 ± 11°F [50 ± 6°C]		
	011630-02	\$22.50	N.C.	59 ± 9°F [15 ± 5°C]	41 ± 9°F [5 ± 5°C]		
			N.O.	77 ± 12.6°F [25 ± 7°C]	95 ± 11°F [35 ± 6°C]		
	011640-00	\$22.50	N.O.	104 ± 12.6°F [40 ± 7°C]	122 ± 11°F [50 ± 6°C]		
			N.O.	122 ± 12.6°F [50 ± 7°C]	140 ± 11°F [60 ± 6°C]		


Note: Tolerance is plus or minus (±) the specified number.

Tamperproof Thermostats

Dimensions


Single Thermostats

Inches [mm]




Dual Thermostats

Inches [mm]




Wiring Diagrams

Single Thermostats - All Models



Dual Thermostats - NC/NO Models



Please see our website www.AutomationDirect.com for complete engineering drawings.