



WERMA
SIGNALTECHNIK

Audible Signal Devices

Bracket-mount Signal Horns

Features

- Bracket mounting
- Continuous tone
- 148mm diameter

570 Series Signal Horns Specifications		
Part Number	57005255	57005267
Price	\$124.00	\$104.00
Drawing Link	PDF	PDF
Description	Signal Horn	
Voltage	24VDC	115VAC
Current Consumption	350mA	200mA
Tone Frequency	150Hz	100Hz (supply frequency)
Maximum Volume	108dB @ 1m	
Tone Type	Continuous	
Life Duration	> 250h	
Operating Temperature	-20 to 60°C [-4 to 140°F]	
Protection	IP55	
Weight	880g [31.04 oz]	860g [30.34 oz]
Housing Material	ABS/PC	
Connection	Screwable con max. 2.5 mm ² single wire, 18-14 AWG	
Agency Approvals	CE, RoHS	

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page at www.AutomationDirect.com




WERMA
 SIGNALTECHNIK

Audible Signal Devices

Bracket-mount Signal Horns

Features

- Corrosion-resistant aluminum housing, salt water proof
- Bracket mounting
- Continuous tone
- 132mm diameter



571 Series Signal Horns Specifications		
Part Number	57105255	57105267
Price	\$386.00	\$352.00
Drawing Link	PDF	PDF
Description	Signal Horn	
Voltage	24VDC	115VAC
Current Consumption	350mA	200mA
Tone Frequency	150Hz	100Hz (supply frequency)
Maximum Volume	108dB @ 1m	
Tone Type	Continuous	
Life Duration	> 250h	
Operating Temperature	-20 to 60°C [-4 to 140°F]	
Protection	IP55	
Weight	880g [31.04 oz]	860g [30.34 oz]
Housing Material	Aluminum	
Connection	Screwable con max. 2.5 mm ² single wire, 18-14 AWG	
Agency Approvals	CE, RoHS	

Features

- Modern electro-mechanical design
- Bracket mounting
- Continuous tone
- 178mm diameter



573 Series Signal Horns Specifications		
Part Number	57300055	57300067
Price	\$167.00	\$133.00
Drawing Link	PDF	PDF
Description	Signal Horn	
Voltage	24VDC	115VAC
Current Consumption	350mA	200mA
Tone Frequency	150Hz	100Hz (supply frequency)
Maximum Volume	105dB @ 1m	
Tone Type	Continuous	
Life Duration	> 250h	
Operating Temperature	-30°C to 50°C [-22° to 122°F]	
Protection	IP65	
Weight	1200g [42.33 oz]	1150g [40.57 oz]
Housing Material	Polycarbonate/ABS-blend	
Connection	Screwable con max. 2.5 mm ² single wire, 18-14 AWG	
Agency Approvals	CE, RoHS	

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page at www.AutomationDirect.com