

# KS 71 Pre-assembled Stacklights



64924001 and 64924002

## KombiSIGN 71 Pre-assembled Stacklights Features

- Available in common voltages of 24V AC/DC and 115VAC
- IP65
- LED Permanent Optical Elements
- 70mm diameter/base mount models
- Polycarbonate lens material
- Polyamide glass fiber-reinforced terminal element with cage clamp.








KS 71 Pre-assembled Stacklights									
Part Number	Price	Drawing Link	Voltage	Colors	Current	Starting Current	Operating Temp	Life Duration	Weight g [oz]
<a href="#">64924001</a>	\$226.00	<a href="#">PDF</a>	115VAC	Green, yellow, red	max. 20mA	-	-20 to 50°C [-4 to 122°F]	Up to 100,000h	249 [8.78]
<a href="#">64924002</a>	\$178.00	<a href="#">PDF</a>	24V AC/DC		max. 25mA	max. 500mA			
<a href="#">64924003</a>	\$168.00	<a href="#">PDF</a>	115VAC	Green, red	max. 20mA	-			191 [6.74]
<a href="#">64924004</a>	\$145.00	<a href="#">PDF</a>	24V AC/DC		max. 25mA	max. 500mA			



64924003 and 64924004

Components for KS 71 Pre-assembled Stacklights				
<b>Image</b>				
<b>Part Number</b>	97584001	97584085	97584086	96000002
<b>Price</b>	\$18.50	\$14.00	\$15.50	\$16.50
<b>Drawing Link</b>	<a href="#">PDF</a>	<a href="#">PDF</a>	<a href="#">PDF</a>	<a href="#">PDF</a>
<b>General Description</b>	Contact box with side cable exit, with mounting material	Bracket for 1-sided mounting, including rubber seals	Bracket for 2-sided mounting, including rubber seals	Bracket for surface mounting with cable gland

# KS 71 Brackets & Contact Boxes Specifications

Brackets & Contact Boxes Technical Specifications						
Part Number	Price	Description	Drawing Link	Temp. Range	Material	Weight g [oz]
 <a href="#"><u>97584001</u></a>	\$18.50	Contact box with side cable exit, with mounting material	<a href="#"><u>PDF</u></a>	-30 to 60°C [-22 to 140°F]	Polyamide	71 [2.50]
 <a href="#"><u>97584004</u></a>	\$50.00	Contact box with magnetic base and side cable exit	<a href="#"><u>PDF</u></a>	-30 to 60°C [-22 to 140°F]	Polyamide	316 [11.15]
 <a href="#"><u>97584085</u></a>	\$14.00	Bracket for 1-sided mounting, including rubber seals	<a href="#"><u>PDF</u></a>	-20 to 60°C [-4 to 140°F]	Polyamide	78 [2.75]
 <a href="#"><u>97584086</u></a>	\$15.50	Bracket for 2-sided mounting, including rubber seals	<a href="#"><u>PDF</u></a>	-20 to 60°C [-4 to 140°F]	Polyamide	76 [2.68]
 <a href="#"><u>96000001</u></a>	\$16.50	Bracket for base mounting with cable gland	<a href="#"><u>PDF</u></a>	-20 to 50°C [-4 to 122°F]	Polyamide	57 [2.01]
 <a href="#"><u>96000002</u></a>	\$16.50	Bracket for surface mounting with cable gland	<a href="#"><u>PDF</u></a>	-20 to 50°C [-4 to 122°F]	Polyamide	40 [1.41]
 <a href="#"><u>96000014</u></a>	\$20.00	Bracket for base mounting with concealed cable entry, including rubber seals	<a href="#"><u>PDF</u></a>	-20 to 50°C [-4 to 122°F]	Polyamide	80 [2.82]

# Foldaway Base for KS 71 and KS 50

- The signal tower can be folded away while still connected
- Minimizes packaging costs and optimizes machine transportation
- Simple mounting and cable entry – for up to 14 mm diameter cables
- Vertical alignment of signal towers even on sloping surfaces
- Positioning in 7.5° steps, markings for 30, 45, 60, or 90 degrees

Foldaway Base for KS 71 and KS 50				
Part Number	Price	Drawing Link	Technical Specifications	
<a href="#"><u>96000030</u></a>	\$55.00	<a href="#"><u>PDF</u></a>	Material	Polyamide Glass Fiber-Reinforced
			Cable Diameter	Max. 14mm [0.55 in]
			Assembly	Includes rubber seals
			Fixing	Vertical or horizontal positioning
			Weight	165g [5.82 oz]

