## What is a Programmable Controller?

# What are programmable controllers and how do they work?

Programmable controllers are often defined as miniature industrial computers that contain hardware and software used to perform control functions. A controller consists of two basic sections: the central processing unit (CPU) and the input/ output interface system. The CPU, which controls all system activity, can further be broken down into the processor and memory system. The input/output system is physically connected to field devices (e.g., switches, sensors, etc.) and provides the interface between the CPU and the information providers (inputs) and controllable devices (outputs).

To operate, the CPU "reads" input data from connected field devices through the use of its input interfaces, and then "executes" or performs the control program that has been stored in its memory system. Programs are typically created in ladder logic, a language that closely resembles a relay-based wiring schematic, and are entered into the CPU's memory prior to operation. Finally, based on the program, the PLC "writes" or updates output devices via the output interfaces. This process, also known as scanning, typically continues in the same sequence without interruption, and changes only when a change is made to the control program.

### **Discrete applications**

Programmable controllers are often used to control machines or processes that are sequential in nature, using "discrete" inputs and outputs that have defined states. For example, if a limit switch detects the presence of an object, it provides an "ON" signal to the PLC; if no object is detected, it provides an "OFF" signal. The machine or device typically performs actions based on time or events in a pre-defined order. The expected sequence is typically interrupted only when an abnormal condition occurs.

## Process control applications

Programmable controllers can also control continuous processes that use analog I/O. For example, a temperature sensor may provide a variable signal, such as 0-10 volts, based on the measurement of an actual temperature. The controller program monitors the sensed values continuously and operates devices that may also be analog in nature. This could include setting the position of a valve between 0-100% open, or controlling the speed of a motor. Continuous applications are so called because they typically have no defined start or end once they are initiated; they maintain a process in a "steady" operating state.



### Today's controllers

Initially, devices that exhibited the attributes discussed here were known as Programmable Logic Controllers (PLCs). This tended to emphasize that the main functionality of these systems was LOGIC operations. As technology has advanced, so have programming languages and communications capabilities, along with many other important features. These developments seemed to demand the definition of a new class of controller, the Programmable Automation Controller (PAC), which combines features of traditional PLCs with those of personal computers.

In the past, size was typically used to categorize controllers, and was often an indication of the features and types of applications it would accommodate. Small, non-modular PLCs (also known as fixed I/O PLCs) generally have less memory and accommodate a small number of inputs and outputs in fixed configurations. Modular PLCs have bases or racks that allow installation of multiple I/O modules, and will accommodate more complex applications. With the emergence of PACs, functionality is the determining factor in categorizing controllers.

## Which programmable controller is right for you?

Choosing the most effective controller for your application depends on a number of factors. To begin the selection process, a drawing of the machine or process is a good start. This can help identify field devices and physical requirements for hardware locations. From the drawing, you can determine how many analog and/ or discrete devices you will have.

Once the field device requirements and hardware locations are defined, you can review controllers that will meet your requirements. See the Controller Selection Worksheet in this section that will help you work through the considerations for determining the type of controller you will need, regardless of which manufacturers you are evaluating.

Prices as of April 15, 2015. Check Web site for most current prices.

This hybrid arose not only to solve

complex applications with the speed and

processing power of a PC-based system,

but to do it on a platform capable of

withstanding the environmental pound-

ing that PLCs have been subjected to for

Ideally, a PAC encompasses the following

many years.

features:

PLC Feel

PC Power

monitoring.

Modular footprint

Industrial reliability

Large memory and

 High-level data handling and enterprise connectivity

 Extensive communications capability, multiple protocols and

PACs are most often used for advanced machine control, process

control, data acquisition and equipment

Although each PAC vendor uses their own development environment (IDE) and programming language, PAC networking

This class of controller provides more

memory capacity and processing power

which allows for better data processing

capabilities, and connectivity to enterprise

Additionally, PACs offer the benefit

of easy integration for multi-domain

systems comprising Human Machine

Interface (HMI), discrete control and

business systems from the plant floor.

is typically based on IP and Ethernet.

fast processing

field networks

• Wide array of I/O modules

and system configurations





Control Syster CLICK PLC

Do-More PLCs Overview

Do-More H2 PLC

Do-More T1H PLC

DirectLOGIC PLCs Overview

DirectLOGIC DL05/06

DirectLOGIC DL105

DirectLOGIC DL205

DirectLOGIC DL305

DirectLOGIC DL405

Productivity Controller Overview

Productivity 3000

Universal Field I/O

C-More HMI

C-More Micro HMI ewMarq ndustrial Marquees

Other HMI

Communications Appendix Book 1

Terms and Conditions

# PLC vs. PAC vs. PC-based Control

The most common control systems today are the Programmable Logic Controller (PLC), PC-based control, and the most recent addition, the Programmable Automation Controller (PAC). While they each share a few attributes with the others, their differences lie mainly in form factor and functionality.

#### Programmable Logic Controller

The Farlex Dictionary defines a PLC as follows: "A programmable microprocessor-based device that is used in discrete manufacturing to control assembly lines and machinery on the shop floor as well as many other types of mechanical, electrical and electronic equipment in a plant. Typically RISC based and programmed in a specific-purpose programming language, a PLC is designed for realtime use in rugged, industrial environments. Connected to sensors and actuators, PLCs are categorized by the number and type of I/O ports they provide and by their I/O scan rate."



PLCs excel at sequential logic and basic analog control. Their modularity and ruggedness make them suitable for a wide variety of automation applications.

### PC-based Control

With Personal Computer technology booming in the 1980s and 1990s, there was a natural progression to consider using the processing power in these units to solve more complicated applications that extended well beyond the realm of digital and analog I/O manipulation. These more advanced capabilites could be performed far more efficiently by hardware and software native to the commercial personal computer. Examples of these requirements include:

- The need for a Human Machine Interface (HMI) as well as control
- Advanced data manipulation and advanced math functions

- Data exchange with business applications (spreadsheets, ERP systems)
- One or more third-party PC cards, such as those for motion control or vision systems
- Communication with serial or networked field devices
- · Storage or access to large amounts of data
- Large number of PID loops (64 or more)
- Open architecture for C/C++ or VisualBasic systems
- Online productivity tools to analyze and improve performance of the process



In a PC-based control system, a standard operating system such as Windows NT supports HMI and control software running on a PC platform, either a readily available commerical model or an industrially hardened unit. PC architecture allows the system to seamlessly support a variety of third-party I/O, specialty motion and vision systems, and field networks.

#### Programmable Automation Controller

A programmable automation controller is a compact controller that combines the features and capabilities of a PC-based control system with that of a typical programmable logic controller (PLC).



process control.



### Considerations for Choosing a Controller Use the worksheet on the following pages as a checklist of the things to consider when determining

Use the worksheet on the following pages as a checklist of the things to consider when determining programmable controller requirements. It lists the most important areas to consider when choosing a system, and provides space for recording determinations of your system needs.

Consideration	Information	to Record	Why this is important
1. Proposed System	New system	Existing system	Determine whether your system is new or existing: Will your system be installed from scratch or are there existing products already installed? The rest of your system will need to be compatible with new components. Why this is important: Certain controller products may not be compatible with others. Making sure your existing products are compatible with any new products you are researching will save
2. Environmental Issues	Codes/environmental issues to consider	No codes or environmental issues to con- sider	you time and money. Check appropriate entry. Consider any environmental issues that will affect your application (temperature, dust, vibration, codes specific to your facility, etc.). Why this is important: Certain environments may affect the opera- tion of a controller. For example, typical controllers have an oper- ating temperature of 0-55 degrees Celsius (32-130 degrees F). If your application will include any extreme environmental condi- tions, or you have specific codes at your facility that must be met, you will need to either research products that meet those speci- fications or design the installation to meet requirements. Check appropriate entry.
3. Discrete Devices	Total inputs: AC DC	Total outputs: AC DC	Determine how many discrete devices your system will have. Which types (AC, DC, etc.) are needed? <i>Why this is important:</i> The number and type of devices your system will include is directly linked to the amount of I/O that will be necessary for your system. You will need to choose a controller that supports your I/O count requirements and has modules that support your signal types. Enter quantities and type based on corre- sponding field devices.
4. Analog Devices	Total inputs: Voltage Current Thermo RTD	Total outputs: Voltage Current	Determine how many analog devices your system will have. Which types (voltage, current, temperature, etc.) are needed? Why this is important: The number and type of devices your system will include is directly linked to the amount of I/O that will be necessary for your system. You will need to choose a controller that supports your I/O count requirements and has modules that support your signal types. Enter quantities and type based on corre- sponding field devices.
5. Specialty Modules or Features (application- specific)	High speed cou         Positioning         Servo/stepper         BASIC program         Real-time clock         Others (list)	uming	Determine whether your system will require any specialty features: Will your application require high-speed counting or positioning? What about a real-time clock or other specialty feature? Why this is important: Specialty functions are not necessarily available in a controller CPU or in standard I/O modules. Understanding the special functions your system may perform will help you determine whether or not you will need to purchase addi- tional specialty modules. Check all features required.

Table continued on the following page

ontrol Syste

## **Considerations for Choosing a Controller**

**Consideration Information to Record** Why this is important CLICK PLC Determine the type of CPU you will need: How much memory will your o-More Hardware requirements: LCs Overview system require? How many devices will your system have (determines data memory)? How large is your program, and what types of instructions will Do-More H2 PLC K program memory your program include (determines program memory)? How fast a scan time required do you need? Do-More T1H (estimated) PLC Why this is important: Data memory refers to the amount of memory needed for dynamic data manipulation and storage in the system. For irectLOGIC example, counter and timer instructions typically use data memory to store PLCs Overviev K data memory required setpoints, current values, and other internal flags. If the application requires (estimated) DirectLOGIC DL05/06 historical data retention, such as measured device values over a long period of time, the size of the data tables required may determine the CPU model Fast scan time required? DirectLOGIC DL105 you choose. Program memory is the amount of memory needed to store the sequence of program instructions that have been selected to perform the 6. CPU Required application. Each type of instruction requires a specific amount of program DirectLOGIC DL205 Battery backup required? memory, typically defined in a programming manual. Applications that are basically sequential in nature can rely on the I/O device rule of thumb DirectLOGIC DL305 Software/special function to estimate program memory (five words of memory for each I/O device); requirements: complex applications will be more difficult to judge. DirectLOGIC DL405 If scan time is important in your application, consider the CPU processor speed as well as instruction execution speed. Some CPUs are faster at PID Productivity boolean logic but slower with data handling instructions. Controller Overview If special functions such as PID are required, the CPU you select may make Floating Point Math those functions easier to perform. Productivity 8000 For program memory required, follow this rule of thumb: 5 words of Others (see Programming section program memory for each discrete device and 25 words for each analog Jniversal Field I/O device. Check or calculate all requirements that apply. below) Determine where your I/O will be located: Will your system require only local I/O, or both local and remote I/O locations? C-More HMI Why this is important: If subsystems will be needed at long distances from **Remote Locations** the CPU, you will need a controller that supports remote I/O. You will C-More Micro HMI Local ... also have to determine if the remote distances and speeds supported will Specific remote I/O proto-7. I/O Locations only be adequate for your application. Serial and Ethernet-based I/O hardcol required? Which one? ware are two typical choices available for most systems. This I/O may also ndustrial Marquees be referred to as distributed I/O, and may require a particular protocol, such as Modbus. Other HM Enter number of physical locations needed, and if/what specific protocol may be required. Ethernet Determine your communication requirements: Will your system Appendix Book 1 be communicating to other networks, systems or field devices? PLC to PLC Why this is important: Communication ports (other than the program-Modbus RTU Ferms and Conditions 8. Communications ming port) are not always included with a controller. Knowing your system ASCII (interface to serial devices) communication requirements will help you choose a CPU that supports your communication requirements, or additional communication modules Other if necessary. Check any/all communications functions required. Determine your programming requirements: Does your application require **PID** loops only traditional programming instructions, or are special instructions necessary? number of loops Floating needed Why this is important: Certain controllers may not support every type of point math 9. Programming instruction. You will need to choose a model that supports all instructions that **Subroutines** you may need for a specific application. For example, built-in PID functions Drum are much easier to use than writing your own code to perform closed-loop sequencer Direct interrupts process control. Typical instructions such as timers, counters, etc. are available in most controllers; note any other special instructions required here. Others (list) Check any/all programming functions required.



## Programmable Controller Summary

Those making the buying decisions for Programmable Controller applications can have very different needs. We offer a selection of controller families that can fit a variety of applications. Regardless if you are a newcomer to programmable controllers or if you

#### CLICK: Our best value PLC Easy for new user



The CLICK PLC is becoming one of the industry's favorite control systems in the 142 I/O or less category.



#### Basic PLCs: 8 DC In / 6 DC Out (sinking) 8 DC In / 6 DC Out (sourcing) 8 DC In / 6 Relay Out 8 AC In / 6 Relay Out

#### Analog PLCs:

- 4 DC In / 4 DC Out (sinking), 2 Analog In, 2 Analog Out
- (current/voltage selectable) 4 DC In / 4 DC Out (sourcing),
- 2 Analog In, 2 Analog Out (current/voltage selectable)

Do-more is a micro-modular PLC that leverages our most

flexible I/O systems to create an incredibly powerful PLC

are a seasoned veteran; whether you need simple discrete control or if you need to calculate complex algorithms lightning fast, we have a controller family that is perfect for you.

- Built-in communication ports (two in Basic PLC units, three in Standard and Analog PLC units)
- Optional battery backup (Standard and Analog PLCs units only)
- Real time clock/calendar 8 DC In / 6 DC Out (sourcing) (Standard and Analog PLCs units only)
  - Removable terminal blocks for easy wiring
  - Stackable discrete and analog I/O option
  - modules (DIN-rail or panel mountable)
- Program AND documentation stored in PLC unit (current/voltage selectable)
  - Decimal memory addressing
  - 21 easy-to-use instructions
  - 8,000 steps of program memory

#### Do-more H2 and T1H Series CPUs: Spend Less, Do More! **)>mo**ne

#### ast CPU CPU w/ built-in Ethernet

H2 works with most DL205 I/O modules T1H works with mos Terminator I/O

Advanced discrete

Process control

Expandability

FREE Software



- Practical counting/pulse Ethernet-connected expansion I/O
- High-performance processors

Cost effective hardware

board

Documentation can be stored on

Built-in communications include USB programming, serial, and (optional) Ethernet

- at a fraction of the cost of comparable controllers. FREE programming software
  - (with built-in simulator) Powerful control over program

Standard PLCs:

8 DC In / 6 Relay Out

• 8 AC In / 6 Relay Out

• 4 DC In / 4 Relay Out.

2 Analog In, 2 Analog Out

8 DC In / 6 DC Out (sinking)

- execution • Enhanced troubleshooting tools
- FREE online training with coupon
- Starter kits available





displays

Web Server

**FREE Software** 



The Productivity controllers shatter the price per feature paradiam in every category, with prices that can't be beat and a two-year warranty on all modules.



**Productivity**<sub>3000</sub>

#### Auto discovery of hardware, including remote I/O bases (P3000 only) and GS drives when connected to the Ethernet remote I/O network

- Tag name database programming
- Task management
- Advanced "fill-in-the-blank" instructions
- Seamless corporate database connectivity
- · Run-time editing and project transfer
- Project file, tag database and ladder documentation stored in the CPU
- FREE Productivity Suite software

Advanced discrete Basic process control Expandability Ethernet **FREE Software** 

100-word program limitation \$395 for unlimited program sizes

1 (14.3) eCS-6

### DirectLOGIC: Long-running PLCs

DirectLOGIC PLCs (nano fixed I/O to modular units) are industry workhorses, time-tested in some of the toughest industrial settings.

All platforms use the same DirectSOFT programming software, so your investment is protected.



- Six PLC platforms to choose from in the DirectLOGIC family:
  - DL05 stand-alone brick with one option slot (30 I/O max)
  - DL06 stand-alone brick with 4 option slots (100 I/O max)
  - DL105 stand-alone brick with high amp relays (18 I/O max)
  - DL205 powerful modular PLC with the most available option modules (up to 16,384 I/O max)
  - DL305 time tested, legacy control platform (up to 368 I/O max)
  - DL405 time tested, legacy control platform (up to 16.384 I/O max)



# **Application Briefs**

# DL06 PLC puts heaters to the test

Pyromatics Automation Systems of Crystal Lake, II. was contracted by a customer to develop a Life Cycle Test Station for its electric heating elements.

This test station needed a user-friendly graphical interface to give operators the ability to select multiple ramp/soak parameters, output voltages, temperature sensor types, amperage ratings and total cycle counts on tests for the cast-in electric heater platens. The system also needed to record temperature, volts, and current draw throughout the test for use in quality reports. Also, a failure of the heater required a safe shutdown of the test while alerting the quality department of the alarm condition.

Pyromatics selected the cost-effective DirectLOGIC® DL06 PLC as the heart of the system because of its ability to control up to eight PID loops and the multiple expansion slots available for thermocouple cards and analog input modules. It also controls two heaters, two chillers and an array of panel indicators, buttons, switches and relays.

A C-more 10-inch TFT touch-screen operator interface was used to provide operators with the necessary interface to operate and monitor the tests.



The completed system allows users to quickly connect the heater to be tested, enter test parameters, and run the test. Trend charts on the C-more panel track test parameters and quickly identify potential issues such as sudden drops in current or temperature.

Alarm reporting and history are also automatically recorded, allowing the operator to determine causes of failure. Data from the test can be easily uploaded to a USB thumb drive from the C-more panel. The data can then be imported into the user's choice of word processor or spreadsheet.

www.automationdirect.com

## Semi cab sheeting production improved

ITS, a design build firm in Columbus, Ohio specializes in industrial automation. The company was contacted by a division of International Harvester responsible for the manufacturing of semi cabs. International Harvester uses automated machines to place aluminum rivets on sheeting that is attached to the frame of the semi cabs. The original CNC machines were becoming antiquated and needed to be upgraded.



ITS chose a DL205 PLC as the new controller for the machines, along with discrete I/O and an H2-CTRIO high-speed counter module that drives a dual axis servo. An H2-ECOM Ethernet Communications card links the machines back to an office for data acquisition. ITS also added a 15-inch touch screen for diagnostics.

In the new system, an operator stamps sheets of aluminum to welded framework with a handful of hand rivets and then places the product onto a dual axis servo table. After the operator selects one of five different parts programs, the machine will navigate the panel under the head assembly, which is responsible for the drilling and riveting, with a tolerance of 1/10 of a millimeter. The panel is drilled and a rivet is installed and squeezed to approximately 1200 PSI, producing a rivet consistency within .003 in. After completion of the panel (between 64 and 138 rivet locations), the machine will return to its home position and await the next product.

The solution increased productivity by approximately 30% and provides an easy way to run and maintain the machines.

### Cost-effective I/O simplifies hydroelectric plant controls upgrade

Lockhart Power Company owns and operates a hydroelectric plant located on the Broad River in upstate South Carolina.



The plant includes an 8-gate dam feeding a canal that channels the water flow to the powerhouse. The powerhouse contains five turbine generators with a combined power capacity of over 17 MW. The dam and turbine control system receives data from power, flow, and level sensing devices to perform monitoring and control of the dam, generators, and associated equipment.

Lockhart Power contracted North Fork Electric in Crumpler, NC, to lend their expertise to a renovation of the conrtol system.

The system consists of seven DirectLOGIC DL205 micro-modular PLCs with built in PID functionality. Each of the five systems for generator control includes discrete and analog I/O, and an Ethernet communications module. The remaining two PLCs are configured in a master/slave arrangement and control the dam gates, located upriver from the powerhouse, via radio modems. Operator interfaces include two 6-inch color touch screen panels and a Windows NT-based PC running the LookoutDirect SCADA/HMI software package.

In the automatic mode, the PLC can start, stop, and operate the generator, and control startup and synchronization of the turbine. Changing the generator gate position varies the flow of water to the turbine.

The dam control system controls the eight canal gates located at the dam, which regulate the flow of water downstream to the turbines.

**Control Systems Overview** 

Book 1 (14.3) eCS-7 S. Automatio



CLICK PLC

Do-More PLCs Overview

Do-More H2 PLC

Do-More T1H PLC

DirectLOGIC PLCs Overview

DirectLOGIC DL05/06

DirectLOGIC DL105

DirectLOGIC DL205

DirectLOGIC DL305 DirectLOGIC DL405

Productivity Controller Overview

<sup>2</sup>roductivity 3000

Jniversal Field I/O

Software C-More

C-More Micro HMI

/iewMarq

Communications Appendix Book 1

Terms and Conditions

# **Programmable Controller Selection Guide**

Sele	ction Criteria		I/O Capa	icity			sic hine itrol	Pro Con		High-Speed and Motion	CPU Communications						5	
Controller Family	Series / CPU	Built-In I/O		Local 1/0 (with Expansion)	Total Possible I/O	Digital I/O & Simple Logic Requirements	Stage Programming (State Machine Control)	Analog I/O, Simple Math and data manipulation	16 PID loops, Complex Math for- mulas &/or Array Manipulation	High-speed I/O modules with Motion Control	Built-In Ethernet & USB	Built-In Local I/O Expansion Ports	Built-In Remote I/O	Built-In RS-232 Serial port	Built-In RS-422 Multi-drop port	Built-In RS-485 Multi-drop port	Modbus TCP Ethernet Protocol	EtherNet/IP
	Serie	AC, DC, Relay I/O	Analog In & Out	Loc (with E)	Total P	Digital I/C Logic Rec	Stage Pro (State Mach	Analog I/0, and data m	16 PID loops, Co mulas &/or Arra	High-speed I/( Motion	Built-In Eth	Built-In Local 1/0	Built-In R	Built-In RS-2	Built-In RS-422	Built-In RS-485	Modbus TCP E	Fther
LC	Basic CPU	8 In/6 Out		142	142	~		~						~				
CLICK PLC	Standard CPU	8 In/6 Out		142	142	~		~						~		~		
C	Analog CPU	4 In/4 Out	2 In/2 Out	140	140	~		~						~		~		
	H2-DM1			256	65,536	~	~	~	~	~				~				
Do-more	H2-DM1E			256	65,536	~	~	~	~	<b>~</b>	~		✔6	~			2	
Do-n	T1H-DM1			256	65,536	~	~	~	~	~				~				
	T1H-DM1E			256	65,536	~	~	~	~	~	~		✔6	~			~	
Ā	P2-550 CPU			240	240	~		~	~	~	~		•7	~		~	~	~
Productivity	P3-550 CPU			3520	59,840	~		~	~	~	~	~	~	~		~	~	~
Ŀ	P3-530 CPU			3520	3520	~		~	~	~	~	~		~		~	~	

3 DeviceNet & ProfiBus Slave modules for the DL205 series are installed in place of the CPU in the CPU slot

High Speed inputs available on DC input models / Pulse output available on DC output models

5 RS-485 for Modbus protocol only

6 The Ethernet ports on the H2-DM1E and T1H-DM1E allow expansion beyond the local base.

⑦ GS Drives only

 $\ensuremath{\textcircled{O}}$  Scan times may vary during Run-Time Transfers



Prices as of April 15, 2015. Check Web site for most current prices.

# **Programmable Controller Selection Guide**

Automation Direct

Company nformation

Control System Overview

CLICK PLC

	Ports	otoc	ols						ations Modu					Pro	gramı	nabili	ty					Do-More PLCs Overvi	
Modbus RTU Slave	Modbus RTU Master	K-Sequence Slave	DirectNet Slave	DirectNet Master	ASCII Out	ASCII IN	Ethernet (10/100 Mb)	Serial RS-232 & RS-485	Basic Coprocessor	Ethernet or Serial Remote I/O	DeviceNet/Profibus Slaves	Total Memory	Battery Backed Memory Clock / Calendar	Stage Programming	Run Mode Edits (Outputs pause during transfer)	Run-Time Transfer (Scan updates during transfer)	Built-in High Speed Counter & Pulse Output	Floating point Math	Freeform Expressions in Math	Drum Sequencer	Email Instruction	Sub-Divided Program Tasks	Do-More H2 PLC Do-More T1F PLC DirectLOGIC DLCS/O6 DirectLOGIC DL05/06 DirectLOGIC DL05/06 DirectLOGIC DL05
~	~				~	~												~	~	~		~	DirectLOGIC DL305
~	~				~	~						8k steps	~					•	~	~		~	DL305
~	~				~	~							~					~	~	~		~	DL405
~	~	~			~	~	~	~		~		262kb	~	~	~	~		~	~	~	~	~	Productivity Controller Overview
~	~	~			~	~	~	~		~		262kb	~	>	~	~		>	~	~	~	~	Productivity 3000
>	~	~			~	~	~	~		~		262kb	~	~	~	~		~	~	~	~	~	Universal Field I/O Software
~	~	~			~	~	~	~		~		262kb	~	~	~	~		~	~	~	~	~	C-More HMI
<b>`</b>	~				~	~		~				50Mb	~			✔2		~	~	~	~	~	C-More Micro HMI ViewMarq Industrial
	~				~	~		~		~		50Mb	~			✔2		~	~	~	~	~	Marquees Other HMI
~	~				~	~		~				25Mb	>			✔2		>	~	~	~	~	Communicati Appendix Book 1

Terms and Conditions



# **Programmable Controller Selection Guide**

Selection Criteria				I/O Caj	pacity			sic hine itrol		cess itrol	High-Speed and Motion	d CPU Commun			muni	icatior	າຣ		
Controller Family	Series / CPU		0/1 ml Him		Local 1/0 (with Expansion)	Total Possible I/O	Digital I/O & Simple Logic Requirements	Stage Programming (State Machine Control)	Analog I/O, Simple Math and data manipulation	16 PID loops, Complex Math for- mulas &/or Array Manipulation	High-speed I/O modules with Motion Control	Built-In Ethernet & USB	Built-In Local I/O Expansion Ports	Built-In Remote I/O	Built-In RS-232 Serial port	Built-In RS-422 Multi-drop port	Built-In RS-485 Multi-drop port	Modbus TCP Ethernet Protocol	
Contro			AC, DC, Relay I/O	Analog In & Out	L (with	Total F	Digital Logic F	Stage P (State Ma	Analog I/C and data	16 PID loops, ( mulas &/or Arr	High-speed Motic	Built-In E	Built-In Local I	Built-In	Built-In RS	Built-In RS-42	Built-In RS-48	Modbus TCP	
	DL05	All CPUs	8 In/6 Out		30	30	~	~	~		~				~				
	DL06	All CPUs	20 In/ 16 Out		100	100	~	~	~		~				~	~	~		
	DL105	All CPUs	10 In/ 8 Out		n/a	18	~	~							~				
		D2-230			256	256	~	~							~				
<u>ں</u>	05	D2-240			256	896	~	~			~				~				
DirectLOGIC	DL205	D2-250-1			768	16,384*	~	~	~		<ul> <li>✓</li> </ul>			~	~	~			
lirect		D2-260			1280	16,384*	~	~	~		<ul> <li>✓</li> </ul>			~	~	~	✔5		
		D3-330			176	176	~						~						
	DL305	D3-340			184	184	~						~		<				
	DL	D3-350			368	368	~	~	~				~	~	~	~			
		D4-430			640	1664	~	~					~		~				
	DL405	D4-440			640	2688	~	~					~		~	~			
	DL4	D4-450			2048	16,384*	~	~	~		~		~	~	~	~			

\* 16384 (fully expanded H4-EBC slave bases, using V-memory & bit of word instructions)

 $\ensuremath{\textcircled{O}}$  Scan times may vary during Run-Time Transfers

- 3 DeviceNet & ProfiBus Slave modules for the DL205 series are installed in place of the CPU in the CPU slot
- $\textcircled{\sc 0}$  High Speed inputs available on DC input models / Pulse output available on DC output models
- ⑤ RS-485 for Modbus protocol only
- 6 The Ethernet ports on the H2-DM1E and T1H-DM1E allow expansion beyond the local base.

Prices as of April 15, 2015. Check Web site for most current prices.

# **Programmable Controller Selection Guide**

Automation Direct



Control System Overview

	Pc	orts &	Prot	ocol	ls						ations Modu					Pro	gram	mabil	ity					Do-More PLCs Overvie
	Modbus RTU Slave	Modbus RTU Master	K-Sequence Slave	DirectNet Slave	DirectNet Master	ASCII Out	ASCII IN	Ethernet (10/100 Mb)	Serial RS-232 & RS-485	Basic Coprocessor	Ethernet or Serial Remote I/O	DeviceNet/Profibus Slaves	Total Memory	Battery Backed Memory Clock / Calendar	Stage Programming	Run Mode Edits (Outputs pause during transfer)	Run-Time Transfer (Scan updates during transfer)	Built-in High Speed Counter & Pulse Output	Floating point Math	Freeform Expressions in Math	Drum Sequencer	Email Instruction	Sub-Divided Program Tasks	Do-More H2 PLC Do-More T1F PLC DirectLOGIC PLCs Overvin DirectLOGIC DL05/06 DirectLOGIC DL105
	~	~	~	~	~	~		~	~	~		~	6.0k		~	~		✔④		~	~	~		DL205 DirectLOGIC DL305
	~	~	~	~	~	~	~	~	~	~		~	14.8k	~	~	~		✔④	~	~	~	~		DirectLOGIC DL405
			~										2.4k		~	~		✔④			~			Productivity Controller Overview
			~				İ					✔3	2.4k		~	~								Productivity 3000
			~	~				~	~	~	~	✔3	3.8k	~	~	~								Universal
	<b>~</b>	~	~	~	~	~		~	~	~	~	✔3	14.8k	~	~	~			~	~	~	~		Field I/O
	<b>~</b>	~	~	~	~	~	~	~	~	~	~	✔3	30.4k	~	~	~			~	~	~	~		Software
				~	~								3.8k											C-More HMI
	~			~									3.9k											C-More Micro HMI
	<b>~</b>	~	~	~	~	~			~				14.8k	~	~	~			~		~			ViewMarq
			~	~				~	~	~	~		6.5k	~	~	~								Industrial Marquees
			~	~				V	~	~	~		22.5k	~	~	~					~			Other HMI
	~	~	~	~	~	~		~	~	~	~		30.8k	~	~	~			~	~	~	~		Communicati
_																								Appendix

Appendix Book 1

Terms and Conditions

### Get The Training You Need, When And Where You Need It

### INTERCONNECTING AUTOMATION

### Doug Bell and InterConnecting Automation, Inc.

Interested in a PLC training course focused entirely on AUTOMATIONDIRECT's products, taught by someone who has used most of our products in real-world applications? Would it be extra convenient if the training was held in a city near you? We thought so! Doug's offering includes:

- Basic PLC training course (three days) covering basic PLC theory of operation including CPU, bases, discrete I/O, analog I/O, and communications
- Advanced PLC training course (three days) covering advanced programming and debugging, with remote I/O, networking, modems and more
- PID training course (two days) covering PID loop setup, tuning and troubleshooting, as well as shortcuts and tools the experts use

Go online to:

www.interconnectingautomation.com for a complete schedule.

### Training sets

### Available on DVD and in Spanish

Want to learn how to program our PLCs in the comfort of your own office? Doug Bell has created two hands-on training kits, one based on his world-famous basic PLC training class, the other focusing on PLC analog principles. The basic PLC training kit includes two videotapes or one DVD, a pre-wired trainer containing a DL05 PLC, and the DL05 User Manual.

The analog training kit includes two videotapes or one DVD, a pre-wired trainer with potentiometers and meters, a DL05 analog input/output module, I/O cable and 24 VDC power supply. Each kit can be ordered directly from ICA.

(*Direct*SOFT programming software must be purchased separately.)

### **Online training**

If you can't travel and can't justify a training kit, how about inexpensive online training? Check out Doug's online training videos for PLCs and HMI.

Interconnecting Automation 1-414-425-8348 www.interconnectingautomation.com



### "Introduction to PLC Logic and Principles" video or DVD and training kit

Get the most important lessons from the three-day basic PLC seminar in a step-by-step two-video or DVD set.

### "PLC analog I/O" training video or DVD and hardware

Learn the ins and outs of using analog I/O with PLCs in this step-by-step training set.

Check the Appendix for complete descriptions of the training kits and course contents.





### Online training at www.interconnectingautomation.com

View the complete list of videos in each "library" as well as watch sample videos; when ready to purchase, register and pay for your selected libraries on a monthly basis. Get unlimited access anytime during the 30 days; videos can be viewed as many times as needed. Most libraries range from \$29.95 - \$39.95 per month. Typical libraries include:

- Introduction to PLC Principles (for the novice non-user with limited controls knowledge)
- Do-More series PLC Training (includes Introduction to PLCs library)
- Productivity2000 series PLC Training (includes Introduction to PLCs library)
- CLICK series PLC Training (includes Introduction to PLCs library)
- Productivity3000 series Controller Training

Libraries will be added on a continuing basis.

