

UL 489 or UL 1077?

What are your Circuit Protection Requirements?

An understanding of circuit types and circuit protection products is critical to ensure their proper application.
See NEC Sections 100, 430 and 409 for definitions.

The proper sizing of an overcurrent protection device is the responsibility of the customer and should be determined using the application standards of the NEC (National Electric Code), CEC (Canadian Electrical Code) or other applicable standards. Per fine print note of 2008 NEC Section 100 "A current in excess of rating may be accommodated by certain equipment and conductors for a given set of conditions. Therefore, the rules for overcurrent protection are specific for particular situations."

UL 489

Branch Protection



UL 1077

Supplementary Protection



What You Need to Know and Look For In Specifications

Certifications – Standards – Acceptance

UL 489 Branch Protection

- UL 489 Listed or Recognized
- CSA C22.2 No. 5
- International ratings available depending on breaker type

UL 1077 Supplementary Protection

- UL Recognized under UL 1077
- CSA 22.2 No. 285
- IEC 60947-2 or IEC 898

Function

- Opens automatically on Overload and Short Circuit when properly applied within its ratings
- Protects wire and cable against Overload and Short Circuit

- Opens automatically on Overload and Short Circuit
- Provides additional equipment protection where branch circuit protection is already provided or not required
- Not suitable for the protection of branch circuit conductors

Applications

- Branch circuit protection in control panels, panelboards, switchboards and motor control centers
- Motor overload and motor short circuit protection (UL 489 Recognized motor circuit protectors) for control panels and motor control centers

- Used within appliances or other electrical equipment such as control circuits, control power transformers, relays, PLC I/O points and lighting circuits
- Ideal replacement for fuses that are applied as supplementary protection

Features

- Bolted down or DIN rail mounted
- External handle mechanisms available
- Field mounted accessories
- Stand alone branch circuit protection
- Various levels of protection (curve type)
- High voltage and interruption levels (up to 100 kAIC @ 480V)

- DIN rail mounted
- Field mounted accessories
- Various levels of protection (curve type)
- 10 kAIC @ 240 VAC
- 10 kAIC @ 277 VAC and 5 kAIC @ 480VAC
- 10 kAIC @ 48VDC


kAIC = thousands of Amps interrupt capacity

Summary

A Supplementary Protector can't be used for Branch Circuit Protection.

Understanding the difference between Branch Circuit Protection and Supplementary Protection helps to ensure their proper use.

UL 1077 Supplementary Protectors and UL 489 Circuit Breakers Application Guidelines



Example of UL 489 and UL 1077 Application

UL489 circuit breakers

Used for branch circuit protection, internal/external receptacles, external motors and HACR equipment (heating, air conditioning and refrigeration).

UL1077 supplementary protectors

Used for overcurrent protection within appliances or electrical equipment, where branch circuit protection is already provided or not required.

Note: UL489 devices can be used in place of UL1077; UL1077 devices cannot be used in place of UL489.

Fuji Molded Case Circuit Breakers Overview

Overview

Fuji Molded Case Circuit Breakers are more compact (especially 100A, 125A, 250A frames) than any breakers on the market, so they take up less space in control panels.

This product group maintains conformity to all Worldwide standards.

Agency Approvals

- UL listed, MCCB, File: E90584
- UL listed, Accessories, File E93289
- CE marked
- CCC marked
- TUV certified

Standards

- UL 489
- CSA C22.2 No.5
- IEC 60947-2
- EN 60947-2
- GB 14048.2
- JIS C8201-2-1, 2 (ANN.1, 2)



Fuji Electric Molded Case Circuit Breakers Technical Specifications

Circuit Breaker Type	Ampere Rating at 40°C	No. Poles	Volts		Type of Trip*	UL 489 Interrupting Ratings (rms Symmetrical Amperes) (kA)			
			AC	DC		Volts AC (50/60 Hz)			Volts DC
						240	480	600	250**
BW125JAGU	15-125	3	600	250	N.I.T.U	50	30	10	10
BW250JAGU	125-250	3	600	250	N.I.T.U	50	30	10	10
BW400SAGU	250-400	3	480	250	N.I.T.U	50	35	–	10
BW630RAGU	500-600	3	480	250	N.I.T.U	100	50	–	10
BW800RAGU	700-800	3	480	250	N.I.T.U	100	50	–	10

Operating Range: -10 to 50°C [14 to 122°F]

*Note: N.I.T.U denotes non-interchangeable trip unit.

**Note: For DC or 1-phase AC applications, use the two outside poles of the 3-pole circuit breaker

Fuji Molded Case Circuit Breakers

125A Frame



BW125JAGU-3P125SB

Fuji BW125A series MCCBs are 125 amp frame, 3-pole, non-adjustable magnetic trip, molded case circuit breakers (MCCB). The BW125 series is suitable for reverse feed applications. Included with each

MCCB are Line and Load-side lug terminals, terminal covers and mounting hardware. Accessories are not pre-installed and are sold separately.

BW125-Frame Series Three-Pole Molded Case Circuit Breakers

Part Number	Price	Frequency	Rated Interrupting Capacity (kA)						
			Rated Current	UL489 CAN/CSA C22.2 No. 5		IEC60947-2, JIS C 8201-2-1 Icu/Ics		GB14048.2 Icu/Ics	
			Ampere Rating	Voltage	Interrupt Capacity	Voltage	Interrupt Capacity	Voltage	Interrupt Capacity
BW125JAGU-3P015SB	\$296.00	50/60 Hz	15	600V/Y AC 480V/i AC 480V/Y AC 240V AC 250V DC	10 kA 30 kA 30 kA 50 kA 10 kA	500V AC 440V AC 400V AC 380V AC 240V AC 250V DC	15/8 kA 30/15 kA 30/15 kA 30/15 kA 50/25 kA 15/8 kA	400V AC 230V AC	30/15 kA 50/25 kA
BW125JAGU-3P020SB	\$296.00		20						
BW125JAGU-3P030SB	\$296.00		30						
BW125JAGU-3P040SB	\$296.00		40						
BW125JAGU-3P050SB	\$296.00		50						
BW125JAGU-3P060SB	\$296.00		60						
BW125JAGU-3P070SB	\$296.00		70						
BW125JAGU-3P075SB	\$296.00		75						
BW125JAGU-3P080SB	\$296.00		80						
BW125JAGU-3P090SB	\$296.00		90						
BW125JAGU-3P100SB	\$296.00		100						
BW125JAGU-3P125SB	\$296.00		125						

Note: SCCR = UL489 interrupting capacity

BW125-Frame Accessory Selection Guide

Part Number	Price	Description
BW9W1SG0	\$40.00	Field installable auxiliary contact switch, use with BW125 and BW250 series MCCBs. SPDT. 20AWG lead wires, 19.69" long, left side mount only
BW9FRG0	\$81.00	Field installable DC shunt trip, use with BW125 and BW250 series MCCBs; 24 VDC/AC, 20 AWG lead wires 19.69" long, left and right side mount
BW9FAG0	\$81.00	Field installable AC shunt trip, use with BW125 and BW250 series MCCBs; 100-120 VAC, 20 AWG lead wires 19.69" long, left and right side mount
BW9RGAR	\$81.00	Field installable DC undervoltage release, use with BW125 and BW250 series MCCBs; 24 VDC, 20AWG lead wires, 19.69" long, left side mount only
BW9RGAT	\$81.00	Field installable AC undervoltage release, use with BW125 and BW250 series MCCBs; 110-130 VAC, 20AWG lead wires, 19.69" long, left side mount only
BW9SL0CA-3	\$82.00	Replacement lugs for BW125-frame MCCBs, package of 3
BW9V0CA	\$72.00	NEMA 12 rotary handle for BW125-Frame. Position indicating; lock-off feature. Shaft length: 0.39"
BW9VSG0	\$17.50	NEMA 12 rotary handle shaft for BW9V0CA and BW9V0GA, BW125 and BW250 Frames. Steel shaft length: 6.06" (154 mm)
BW9VSG0-24	\$47.50	NEMA 12 rotary handle shaft for BW9V0CA and BW9V0GA, BW125 and BW250 Frames. Steel shaft length: 24" (610 mm)
BW9F0CA-15A	\$386.00	NEMA 12 flexible shaft handle for BW125-Frame. Flange mounted. Lockable. Flex cable shaft length: 4.92' (1.5m)
BW9F0CA-20A	\$401.00	NEMA 12 flexible shaft handle for BW125-Frame. Flange mounted. Lockable. Flex cable shaft length: 6.56' (2m)
BW9Q1CA	\$19.50	Lockout attachment, use to lock out BW125 and BW250 series MCCBs. Lock not included.

Note: Short-type terminal covers (gray-white) are supplied as standard.



BW9V0CA



BW9F0CA-15A



BW9FAG0



BW9RGAR




BW9Q1CA


Fuji Molded Case Circuit Breakers

125A Frame Characteristic Curves


BW125 Rated Current 15A




BW125 (rated current 15A)



BW125 Rated Current 20A




BW125 (rated current 20A)




Fuji Molded Case Circuit Breakers

125A Frame Characteristic Curves


BW125 Rated Current 30A




BW125 (Rated current: 30A)



BW125 Rated Current 40A




BW125 (Rated current: 40A)



Fuji Molded Case Circuit Breakers

125A Frame Characteristic Curves


BW125 Current Range 50 - 125A



Note: Instantaneous tripping = $10 \times (\text{rated current}) \pm 20\%$
 I_n = rated current



BW125 (Rated current: 50 - 125A)



Fuji Molded Case Circuit Breakers

250A Frame



Fuji BW250A series MCCBs are 250 amp frame, 3-pole, non-adjustable magnetic trip, molded case circuit breakers (MCCB). The BW250 series is suitable for reverse feed applications.

Included with each MCCB are Line and Load-side lug terminals, terminal covers and mounting hardware. Accessories are not pre-installed and are sold separately.

BW250JAGU-3P125SB

BW250-Frame Series Three-Pole Molded Case Circuit Breakers

Part Number	Price	Frequency	Rated Interrupting Capacity (kA)						
			Rated Current	UL489 CAN/CSA C22.2 No. 5		IEC60947-2, JIS C 8201-2-1 Icu/Ics		GB14048.2 Icu/Ics	
			Ampere Rating	Voltage	Interrupt Capacity	Voltage	Interrupt Capacity	Voltage	Interrupt Capacity
BW250JAGU-3P125SB	\$664.00	50/60 Hz	125	600V/Y AC 480V/Delta AC 480V/Y AC 240V AC 250V DC	10 kA 30 kA 30 kA 50 kA 10 kA	500V AC 440V AC 400V AC 380V AC 240V AC 250V DC	18/9 kA 30/15 kA 30/15 kA 30/15 kA 50/25 kA 20/10 kA	400V AC 230V AC	30/15 kA 50/25 kA
BW250JAGU-3P150SB	\$664.00		150						
BW250JAGU-3P160SB	\$664.00		160						
BW250JAGU-3P175SB	\$664.00		175						
BW250JAGU-3P200SB	\$664.00		200						
BW250JAGU-3P225SB	\$664.00		225						
BW250JAGU-3P250SB	\$664.00		250						

Note: SCCR = UL489 interrupting capacity

BW250-Frame Accessory Selection Guide

Part Number	Price	Description
BW9W1SG0	\$40.00	Field installable auxiliary contact switch, use with BW125 and BW250 series MCCBs. SPDT. 20AWG lead wires, 19.69" long, left side mount only
BW9FRG0	\$81.00	Field installable DC shunt trip, use with BW125 and BW250 series MCCBs; 24 VDC/AC, 20 AWG lead wires 19.69" long, left and right side mount
BW9FAG0	\$81.00	Field installable AC shunt trip, use with BW125 and BW250 series MCCBs; 100-120 VAC, 20 AWG lead wires 19.69" long, left and right side mount
BW9RGAR	\$81.00	Field installable DC undervoltage release, use with BW125and BW250 series MCCBs; 24 VDC, 20AWG lead wires, 19.69" long, left side mount only
BW9RGAT	\$81.00	Field installable AC undervoltage release, use with BW125and BW250 series MCCBs; 110-130 VAC, 20AWG lead wires, 19.69" long, left side mount only
BW9SL0GA-3	\$92.00	Replacement lugs for BW250-frame MCCBs up to 175A, package of 3
BW9SL1GA-3	\$102.00	Replacement lugs for BW250-frame MCCBs 175A to 250A, package of 3
BW9V0GA	\$72.00	NEMA 12 rotary handle for BW250-Frame. Position indicating; lock-off feature. Shaft length: 0.39"
BW9VSG0	\$17.50	NEMA 12 rotary handle shaft for BW9V0CA and BW9V0GA, BW125 and BW250 Frames. Steel shaft length: 6.06" (154 mm)
BW9VSG0-24	\$47.50	NEMA 12 rotary handle shaft for BW9V0CA and BW9V0GA, BW125 and BW250 Frames. Steel shaft length: 24" (610 mm)
BW9F0GA-15A	\$401.00	NEMA 12 flexible shaft handle for BW250-Frame. Flange mounted. Lockable. Flex cable shaft length: 4.92' (1.5m)
BW9F0GA-20A	\$421.00	NEMA 12 flexible shaft handle for BW250-Frame. Flange mounted. Lockable. Flex cable shaft length: 6.56' (2m)
BW9Q1CA	\$19.50	Lockout attachment, use to lock out BW125 and BW250 series MCCBs. Lock not included.


Note: Short-type terminal covers (gray-white) are supplied as standard.



BW9V0GA



BW9F0GA-15A



BW9FRG0




BW9RGAR



BW9Q1CA

Fuji Molded Case Circuit Breakers –250A Frame Characteristic Curves


BW250 Current Range 125 - 250A



Note: Instantaneous tripping = $10 \times (\text{rated current}) \pm 20\%$
I_n = rated current



BW250 (Current Range: 125 - 250A)



Fuji Molded Case Circuit Breakers

400A Frame



Fuji BW400A series MCCBs are 400 amp frame, 3-pole, non-adjustable magnetic trip, molded case circuit breakers (MCCB). The BW400 series is suitable for reverse feed applications. Included

with each MCCB are Line and Load-side lug terminals and mounting hardware. Accessories are not pre-installed and are sold separately.

BW400SAGU-3P250SB

BW400-Frame Series Three-Pole Molded Case Circuit Breakers

Part Number	Price	Frequency	Rated Interrupting Capacity (kA)						
			Rated Current	UL489 CAN/CSA C22.2 No. 5		IEC60947-2, JIS C 8201-2-1 Icu/Ics		GB14048.2 Icu/Ics	
			Ampere Rating	Voltage	Interrupt Capacity	Voltage	Interrupt Capacity	Voltage	Interrupt Capacity
BW400SAGU-3P250SB	\$1,219.00	50/60 Hz	250	480V/Delta AC 480V/Y AC 240V AC 250V DC	35 kA 35 kA 50 kA 10 kA	690V AC	10/5 kA	400V AC 230V AC	36/18 kA 85/43 kA
BW400SAGU-3P300SB	\$1,219.00		300			500V AC	20/10 kA		
BW400SAGU-3P350SB	\$1,223.00		350			440V AC	36/18 kA		
BW400SAGU-3P400SB	\$1,219.00		400			400V AC	36/18 kA		

Note: SCCR = UL489 interrupting capacity

BW400-Frame Accessory Selection Guide

Part Number	Price	Description
BW9W1SHA	\$36.00	Field installable auxiliary contact switch, use with BW400, BW630 and BW800 series MCCBs. SPDT. 20AWG lead wires, 19.69" long, left side mount only
BW9FHA-R	\$81.00	Field installable DC shunt trip, use with BW400, BW630 and BW800 series MCCBs; 24 VDC/AC, 20 AWG lead wires 19.69" long, left and right side mount
BW9FHA-A	\$81.00	Field installable AC shunt trip, use with BW400, BW630 and BW800 series MCCBs; 100-120 VAC, 20 AWG lead wires 19.69" long, left and right side mount
BW9RHA-R	\$78.00	Field installable DC undervoltage release, for BW400, BW630 and BW800 series MCCBs; 24-48 VDC, 20AWG lead wires, 19.69" long, left side mount only
BW9RHA-1	\$81.00	Field installable AC undervoltage release, for BW400, BW630 and BW800 series MCCBs; 120-130 VAC, 20AWG lead wires, 19.69" long, left side mount only
BW9BTHA-L3W*	\$81.00	Terminal cover for BW400-frame MCCBs, line and load side, package of 2
BW9V0HA	\$110.00	NEMA 12 rotary handle for BW400-Frame. Position indicating; lock-off feature. Shaft length: 0.39"
BZ-VS2	\$14.00	NEMA 12 rotary handle shaft for BW9V0HA and BW9V0JA, BW400, BW630 and BW800 Frames. Steel shaft length: 3.48" (88 mm)
BZ-VS2-24	\$47.50	NEMA 12 rotary handle shaft for BW9V0HA and BW9V0JA, BW400, BW630 and BW800 Frames. Steel shaft length: 24" (610 mm)
BW9F0HA-15A**	\$584.00	NEMA 12 flexible shaft handle for BW400-Frame. Flange mounted. Lockable. Flex cable shaft length: 4.92' (1.5m)
BW9F0HA-20A**	\$601.00	NEMA 12 flexible shaft handle for BW400-Frame. Flange mounted. Lockable. Flex cable shaft length: 6.56' (2m)
BW9QNHA	\$47.50	Lockout attachment, use to lock out BW400, BW630 and BW800 series MCCBs. Lock not included.

*Terminal covers are not supplied as standard.

**Terminal covers for line side and load side included with Flange Disconnects. 2/pk

Note: Terminals are factory-installed only. No replacement terminals available.



BW9V0HA



BW9F0HA-15A



BW9FHA-R



BW9RHA-R




BW9QNHA

Fuji Molded Case Circuit Breakers

400A Frame Characteristic Curves


BW400 Current Range 250 - 400A



Note: Instantaneous tripping = $10 \times (\text{rated current}) \pm 20\%$
 I_n = rated current



BW400 (Current Range: 250 - 400A)



Fuji Molded Case Circuit Breakers – 630A



Fuji BW630A series MCCBs are 630 amp frame, 3-pole, non-adjustable magnetic trip, molded case circuit breakers (MCCB). The BW630 series is suitable for reverse feed applications. Included

with each MCCB are Line and Load-side lug terminals and mounting hardware. Accessories are not pre-installed and are sold separately.

BW630RAGU-3P500SB

BW630-Frame Series Three Pole Molded Case Circuit Breakers									
Part Number	Price	Frequency	Rated Interrupting Capacity (kA)						
			Rated Current	UL489 CAN/CSA C22.2 No. 5		IEC60947-2, JIS C 8201-2-1		GB14048.2	
			Ampere Rating	Voltage	Interrupt Capacity	Voltage	Interrupt Capacity	Voltage	Interrupt Capacity
BW630RAGU-3P500SB	\$1,807.00	50/60 Hz	500	480V/Delta AC 480V/Y AC 240V AC 250V DC	50 kA 50 kA 100 kA 10 kA	690V AC 500V AC 440V AC 400V AC 380V AC 240V AC 250V DC	15/8 kA 36/18 kA 50/25 kA 50/25 kA 50/25 kA 100/50 kA 40/20 kA	400V AC 230V AC	50/25 kA 100/50 kA
BW630RAGU-3P600SB	\$1,807.00		600						


Note: SCCR = UL489 interrupting capacity

BW630-Frame Accessory Selection Guide		
Part Number	Price	Description
BW9W1SHA	\$36.00	Field installable auxiliary contact switch, use with BW400, BW630 and BW800 series MCCBs. SPDT. 20AWG lead wires, 19.69" long, left side mount only
BW9FHA-R	\$81.00	Field installable DC shunt trip, use with BW400, BW630 and BW800 series MCCBs; 24 VDC/AC, 20 AWG lead wires 19.69" long, left and right side mount
BW9FHA-A	\$81.00	Field installable AC shunt trip, use with BW400, BW630 and BW800 series MCCBs; 100-240 VAC/100-220 VDC, 20 AWG lead wires 19.69" long, left and right side mount
BW9RHA-R	\$78.00	Field installable DC undervoltage release, for BW400, BW630 and BW800 series MCCBs; 24-48 VDC, 20AWG lead wires, 19.69" long, left side mount only
BW9RHA-1	\$81.00	Field installable AC undervoltage release, for BW400, BW630 and BW800 series MCCBs; 120-130 VAC, 20AWG lead wires, 19.69" long, left side mount only
BW9BTJA-L3W*	\$84.00	Terminal cover for BW400-frame MCCBs, line and load side, package of 2
BW9V0JA	\$130.00	NEMA 12 rotary handle for BW630-Frame. Position indicating; lock-off feature. Shaft length: 0.39"
BZ-VS2	\$14.00	NEMA 12 rotary handle shaft for BW9V0HA and BW9V0JA, BW400, BW630 and BW800 Frames. Steel shaft length: 3.48" (88 mm)
BZ-VS2-24	\$47.50	NEMA 12 rotary handle shaft for BW9V0HA and BW9V0JA, BW400, BW630 and BW800 Frames. Steel shaft length: 24" (610 mm)
BW9F0JA-15A**	\$631.00	NEMA 12 flexible shaft handle for BW630 and BW800 frames. Flange mounted. Lockable. Flex cable shaft length: 4.92' (1.5m)
BW9F0JA-20A**	\$648.00	NEMA 12 flexible shaft handle for BW630 and BW800 frames. Flange mounted. Lockable. Flex cable shaft length: 6.56' (2m)
BW9QNHA	\$47.50	Lockout attachment, use to lock out BW400, BW630 and BW800 series MCCBs. Lock not included.


*Terminal covers are not supplied as standard.

**Terminal covers for line side and load side included with Flange Disconnects. 2/pk

Note: Terminals are factory-installed only. No replacement terminals available.



BW9V0JA



BW9F0JA-15A



BW9FHA-R



BW9RHA-R



BW9QNHA



Fuji Molded Case Circuit Breakers

630A Frame Characteristic Curves

BW630 Current Range 500 - 600A



BW630 (Current Range: 500 - 600A)



Fuji Molded Case Circuit Breakers

800A Frame



Fuji BW800A series MCCBs are 800 amp frame, 3-pole, non-adjustable magnetic trip, molded case circuit breakers (MCCB). The BW800 series is suitable for reverse feed applications.

Included with each MCCB are Line and Load-side lug terminals and mounting hardware. Accessories are not pre-installed and are sold separately.

BW800RAGU-3P700SB

BW800-Frame Series Three-Pole Molded Case Circuit Breakers

Part Number	Price	Frequency	Rated Interrupting Capacity (kA)						
			Rated Current	UL489 CAN/CSA C22.2 No. 5		IEC60947-2, JIS C 8201-2-1 Icu/Ics		GB14048.2 Icu/Ics	
			Ampere Rating	Voltage	Interrupt Capacity	Voltage	Interrupt Capacity	Voltage	Interrupt Capacity
<u>BW800RAGU-3P700SB</u>	\$2,485.00	50/60 Hz	700	480V/Delta AC 480V/Y AC 240V AC 250V DC	50 kA 50 kA 100 kA 10 kA	690V AC 500V AC 440V AC 400V AC 380V AC 240V AC 250V DC	15/8 kA 36/18 kA 50/25 kA 50/25 kA 50/25 kA 100/50 kA 40/20 kA	400V AC 230V AC	50/25 kA 100/50 kA
<u>BW800RAGU-3P800SB</u>	\$2,485.00		800						

Note: SCCR = UL489 interrupting capacity


BW800-Frame Accessory Selection Guide

Part Number	Price	Description
<u>BW9W1SHA</u>	\$36.00	Field installable auxiliary contact switch, use with BW400, BW630 and BW800 series MCCBs. SPDT. 20AWG lead wires, 19.69" long, left side mount only
<u>BW9FHA-R</u>	\$81.00	Field installable DC shunt trip, use with BW400, BW630 and BW800 series MCCBs; 24 VDC/AC, 20 AWG lead wires 19.69" long, left and right side mount
<u>BW9FHA-A</u>	\$81.00	Field installable AC shunt trip, use with BW400, BW630 and BW800 series MCCBs; 100-120 VAC, 20 AWG lead wires 19.69" long, left and right side mount
<u>BW9RHA-R</u>	\$78.00	Field installable DC undervoltage release, for BW400, BW630 and BW800 series MCCBs; 24-48 VDC, 20AWG lead wires, 19.69" long, left side mount only
<u>BW9RHA-1</u>	\$81.00	Field installable AC undervoltage release, for BW400, BW630 and BW800 series MCCBs; 120-130 VAC, 20AWG lead wires, 19.69" long, left side mount only
<u>BW9BTJA-L3W*</u>	\$84.00	Terminal cover for BW400-frame MCCBs, line and load side, package of 2
<u>BW9V0JA</u>	\$130.00	NEMA 12 rotary handle for BW800-Frame. Position indicating; lock-off feature. Shaft length: 0.39"
<u>BZ-VS2</u>	\$14.00	NEMA 12 rotary handle shaft for BW9V0HA and BW9V0JA, BW400, BW630 and BW800 Frames. Steel shaft length: 3.48" (88 mm)
<u>BZ-VS2-24</u>	\$47.50	NEMA 12 rotary handle shaft for BW9V0HA and BW9V0JA, BW400, BW630 and BW800 Frames. Steel shaft length: 24" (610 mm)
<u>BW9F0JA-15A**</u>	\$631.00	NEMA 12 flexible shaft handle for BW630 and BW800 frames. Flange mounted. Lockable. Flex cable shaft length: 4.92' (1.5m)
<u>BW9F0JA-20A**</u>	\$648.00	NEMA 12 flexible shaft handle for BW630 and BW800 frames. Flange mounted. Lockable. Flex cable shaft length: 6.56' (2m)
<u>BW9QNHA</u>	\$47.50	Lockout attachment, use to lock out BW400, BW630 and BW800 series MCCBs. Lock not included.


*Terminal covers are not supplied as standard.

**Terminal covers for line side and load side included with Flange Disconnects. 2/pk

Note: Terminals are factory-installed only. No replacement terminals available.



BW9V0JA



BW9F0JA-15A



BW9FHA-R



BW9RHA-R




BW9QNHA


Fuji Molded Case Circuit Breakers

800A Frame Characteristic Curves

BW800 Current Range 700 - 800A



BW800 (Current Range: 700 - 800A)




Fuji Molded Case Circuit Breakers

Dimensions


Dimensions

mm [inches]

15 to 125A
BW125A Frame



125 to 250A
BW250A Frame





Fuji Molded Case Circuit Breakers

Dimensions


Dimensions

mm [inches]

250A to 350A BW400 Frame





PANEL DRILLING FOR MOUNTING MCCB



RATED CURRENT 250, 300, 350A

400A BW400 Frame



PANEL DRILLING FOR MOUNTING MCCB


Fuji Molded Case Circuit Breakers

Dimensions

Dimensions

mm [inches]

**500A to 600A
BW630 Frame**




Fuji Molded Case Circuit Breakers

Dimensions


Dimensions

mm [inches]

700A BW800 Frame




RATED CURRENT 700A




PANEL DRILLING FOR MOUNTING MCCB

800A BW800 Frame



RATED CURRENT 800A



PANEL DRILLING FOR MOUNTING MCCB

Fuji Molded Case Circuit Breakers

Products And Accessory Compatibility

Match the Accessories with Fuji Molded Case Circuit Breakers						
Part Number	Description	BW125JAGU	BW250JAGU	BW400SAGU	BW630RAGU	BW800RAGU
BW9W1SG0	Auxiliary Switch (Mounting Left and right side)	X	X			
BW9W1SHA	Auxiliary Switch (Mounting Left side ONLY)			X	X	X
BW9FRG0	Shunt Trip 24 VAC/VDC (Mounting both Left and Right sides)	X	X			
BW9FHA-R	Shunt Trip 24-48 VAC/VDC (Mounting Left side ONLY)			X	X	X
BW9FAG0	Shunt Trip 100-120 VAC, 100-110 VDC (Mounting both Left and Right sides)	X	X			
BW9FHA-A	Shunt Trip 100-280 VAC, 100-220 VDC (Mounting Left side ONLY)			X	X	X
BW9RGAR	UnderVoltage Release 24VDC (Left side ONLY)	X	X			
BW9RHA-R	UnderVoltage Release 24 VAC/VDC (Left side ONLY)			X	X	X
BW9RGAT	UnderVoltage Release 110-130 VAC (Left side ONLY)	X	X			
BW9RHA-1	UnderVoltage Release 120-130 VAC, 125VDC (Left side ONLY)			X	X	X
BW9SL0CA-3	Replacement Lugs Kit for 125 Amp frame	X				
BW9SL0GA-3	Replacement Lugs Kit for 250 Amp frame up to 175A		X			
BW9SL1GA-3	Replacement Lugs Kit for 250 Amp frame 200A to 250A		X			
BW9V0CA	Rotary Handle	X				
BW9V0GA	Rotary Handle		X			
BW9VSG0	Optional Shaft for BW9V0CA and BW9V0GA , 6.063"	X	X			
BW9VSG0-24	Optional Shaft for BW9V0CA and BW9V0GA , 24"	X	X			
BW9V0HA	Rotary Handle,			X		
BW9V0JA	Rotary Handle,				X	X
BZ-VS2	Optional Shaft for BW9V0HA and BW9V0JA , 3.48"			X	X	X
BZ-VS2-24	Optional Shaft for BW9V0HA and BW9V0JA , H = 24"			X	X	X
BW9F0CA-15A	Flange Handle (flex shaft), NEMA 12, 59" (1.5m) cable, 125 Amp frame	X				
BW9F0CA-20A	Flange Handle (flex shaft), NEMA 12, 78.7" (2.0m) cable, 125 Amp frame	X				
BW9F0GA-15A	Flange Handle (flex shaft), NEMA 12, 59" (1.5m) cable, 250 Amp frame		X			
BW9F0GA-20A	Flange Handle (flex shaft), NEMA 12, 78.7" (2.0m) cable, 250 Amp frame		X			
BW9F0HA-15A	Flange Handle (flex shaft), NEMA 12, 59" (1.5m) cable, 400 Amp frame			X		
BW9F0HA-20A	Flange Handle (flex shaft), NEMA 12, 78.7" (2.0m) cable, 400 Amp frame			X		
BW9F0JA-15A	Nema 12 flexible shaft handle for 630A or 800A frame. 59.06" (1.5m) cable				X	X
BW9F0JA-20A	Nema 12 flexible shaft handle for 630A or 800A frame. 78.74" (2m) cable				X	X
BW9BTJA-L3W	Terminal Cover for the 400A frame			X		
BW9BTJA-L3W	Terminal Cover for the 630A AND 800A frame				X	X
BW9Q1CA	Lockout Attachment 125A and 250A frames	X	X			
BW9QNHA	Lockout Attachment 400A, 630A and 800A frames			X	X	X

Internal Accessory Combinations for BW Series



MCCB	BW125 BW250	BW400 BW630 BW800
Pole	3	3
Auxiliary switch		
SPDT		
Shunt trip		
Undervoltage trip		
Auxiliary Switch + Shunt Trip		
Undervoltage + Auxiliary Switch		

Fuji Molded Case Circuit Breakers

Field-mountable Accessories



Defeatable Rotary Handle Operating Mechanisms


BW9V0CA shown

Rotary Operating Handles for Fuji MCCBs – Selection Guide									
Breaker Type	V-type Handle	Price	V-type Handle	With the optional shaft (x = 6.102 (155))		With the optional shaft (x = 24.567 (624))		Mounting Screw	V-type Handle Mass lb. (kg)
			H: inch(mm)	Max. Mounting Depth H: inch(mm)	Range in which the hinge with H can be installed	Max. Mounting Depth H: inch(mm)	Range in which the hinge with H can be installed		
BW125	BW9V0CA	\$72.00	4.134±0.078 (105±2)	9.843±0.078 (250±2)	5.512 to 9.843 (140 to 250)	28.307±0.078 (719±2)	28.307 - 5.591 (124 - 719)	M4 x 3.35 (85)	1.48 (0.67)
BW250	BW9V0GA	\$72.00							

Notes: • Handle is an operating mechanism only; not for sealing enclosure door.

• Not available for side mounting

• For BW250 Series only: When mounting a terminal cover, cut away part of it because it hides the mounting screws for the breaker.





Remove the shaded parts in the figure.

125A, 250A Frame V type handle



• BW9V0CA, BW9V0GA (BW9VSG0, BW9VSG0-24: optional shafts)

Dimensions


mm [inches]




Optional shafts
BW9VSG0
X = 6.102 (155)
BW9VSG0-24
X = 24.567 (624)




Note: Align the center of the hole cut in the panel with the center of the breaker handle.



Installation caution area



Use caution that any item mounted in shaded area can move freely.



BW9VSG0-24 optional shaft Breaker and Shaft Assembly

Fuji Molded Case Circuit Breakers

Field-mountable Accessories



Rotary Operating Handles for Fuji MCCBs – Selection Guide

Breaker Type	V-type Handle	Price	V-type Handle	With the optional shaft (x= 3.504 (89))		With the optional shaft (x= 24 (609.6))		Mounting Screw	V-type Handle Mass lb. (kg)
			H: inch(mm)	Max. Mounting Depth H: inch(mm)	Range in which the hinge with H can be installed	Max. Mounting Depth H: inch(mm)	Range in which the hinge with H can be installed		
BW400	BW9V0HA	\$110.00	7.48±0.078 (190±2)	9.843±0.078 (250±2)	7.95 to 9.843 (202to 250)	30.35±0.078 (771±2)	7.95 - 30.35 (202 - 771)	M4 x 3.35 (85)	1.48 (0.67)
BW630 BW800	BW9V0JA	\$130.00							

Notes:


- Handle is an operating mechanism only; not for sealing enclosure door.
- Not available for side mounting

Dimensions

mm [inches]

400A, 630A, 800A Frame V type handle


- BW9V0HA, BW9V0JA (BZ-VS2, BZ-VS2-24: optional shafts)



Fuji Molded Case Circuit Breakers

Field-mountable Accessories

Defeatable Flexible Handle Operating Mechanisms



BW9F0JA-20A shown

Flex Shaft Handles for Fuji MCCBs – Selection Guide			
Breaker Type	Handle Type	Price	Description
BW125	BW9F0CA-15A	\$386.00	Nema 12 flexible shaft handle for 125A frame. 59.06" (1.5m)cable
	BW9F0CA-20A	\$401.00	Nema 12 flexible shaft handle for 125A frame. 78.74" (2m) cable
BW250	BW9F0GA-15A	\$401.00	Nema 12 flexible shaft handle for 250A frame. 59.06" (1.5m)cable
	BW9F0GA-20A	\$421.00	Nema 12 flexible shaft handle for 250A frame. 78.74" (2m) cable
BW400*	BW9F0HA-15A	\$584.00	Nema 12 flexible shaft handle for 400A frame. 59.06" (1.5m)cable
	BW9F0HA-20A	\$601.00	Nema 12 flexible shaft handle for 400A frame. 78.74" (2m) cable
BW630*& BW800*	BW9F0JA-15A	\$631.00	Nema 12 flexible shaft handle for 630A or 800A frame. 59.06" (1.5m)cable
	BW9F0JA-20A	\$648.00	Nema 12 flexible shaft handle for 630A or 800A frame. 78.74" (2m) cable

*Terminal covers for line side and load side included with Flange Disconnects. 2/pk

Flex Handle Specifications				
Operating instructions	<ul style="list-style-type: none"> • Operating handle facing up, Breaker is in ON position. • Operating handle facing down, Breaker is in OFF position or is reset. • Panel door cannot be opened when in ON, OFF or Trip position. In order to open the door, the handle must be turned toward reset position. • Release screw is standard. If you want to open a panel door in ON position, please turn the release screw using flat head screwdriver. 			
Frame Size	125A frame	250A frame	400A frame	630A/800 frame
Mechanical Endurance (cycles)	10,000	8,000	6,000	6,000
Ambient Temperature	14 to 140F (- 10 to 40°C)			
Relative Humidity	less than 95% RH			
Protection	NEMA Type12 IP54 (IEC60529)			
Conforming Standards	NFPA 79(2007), ANSI(Lockout), OSHA(1910.147, Lockout/tagout), UL489(cUL)			
Environment	No excessive dust, smoke, corrosive gases, flammable gases, steam or salt.			

BW9F0CA




Fuji Molded Case Circuit Breakers

Field-mountable Accessories


Dimensions

mm [inches]

BW9F0HA




BW9F0JA



Fuji Molded Case Circuit Breakers Accessories



Auxiliary Contacts



BW9W1SHA shown

The auxiliary contacts are accessory contacts for the indication of circuit breaker open-closed or tripped.


Auxiliary Contacts for Fuji MCCBs – Selection Guide

Breaker Type	Part Number	Price	Description
BW125 BW250	BW9W1SG0	\$40.00	Auxiliary switch for for 125A and 250A frame. Mounting left and right side
BW400 BW630 BW800	BW9W1SHA	\$36.00	Auxiliary switch for for 400A, 630A and 800A frame. Mounting left side ONLY

Ratings of Auxiliary Switches


Standard Type								
Breaker Type	Rated Thermal Current (A)	Make/Break Current (A)						Minimum Load Current
		AC			DC			
		Voltage (V)	Res. Load	Ind. Load	Voltage (V)	Res. Load	Ind. Load	
BW125, BW250, BW400 BW630, BW800	5	24	5	5	24	4	3	5V DC 160 mA
		48	5	5	48	2.5	1	30V DC 30 mA
		125	5	3	125	0.4	0.4	
		250	3	2	250	0.2	0.2	

Operation of auxiliary switches



Shunt Trips

Shunt Trip is for remote tripping (opening) of circuit breaker.



BW9FRG0 shown

Shunt Trips for Fuji MCCBs – Selection Guide

Part Number	Price	Description
BW9FRG0	\$81.00	Field installable 24 VAC/VDC shunt trip for BW125 and BW250 series MCCB. Left and right side mounting. Lead wires 20AWG, 19.69" long.
BW9FHA-R	\$81.00	Field installable 24/48 VAC/VDC shunt trip for BW400, BW630 and BW800 series MCCB. Left side mounting only. Lead wires 20AWG, 19.69" long.
BW9FAG0	\$81.00	Field installable 100/120 VAC, 100-110 VDC shunt trip for BW125 and BW250 series MCCB. Left and right side mounting. Lead wires 20AWG, 19.69" long.
BW9FHA-A	\$81.00	Field installable 100/240 VAC, 100-220 VDC shunt trip for BW400, BW630 and BW800 series MCCB. Left side mounting only. Lead wires 20AWG, 19.69" long.

Ratings of Shunt Trips

Breaker Type	AC		DC		Time Rating of Coil (with 1 N.O. contact to prevent coil burnout)	Operating Time (ms)
	Voltage (V)	VA	Voltage (V)	W		
BW125, BW250	24	50	24	50	Continuous	13-21
	100-120	50	100-110	50		
BW400, BW630, BW800	24-48	2	24-48	2	Continuous	8-20
	100-240	3	100-220	3		

Note: Allowable operating voltage AC voltage: 85% to 110% of coil rated voltage
DC voltage: 75% to 125% of coil rated voltage

Fuji Molded Case Circuit Breakers Accessories



Undervoltage Releases

Undervoltage Release will trip the circuit breaker when the connected voltage drops to less than 70% of undervoltage release voltage rating. It will allow the circuit breaker to close (ON) when voltage is approximately 85% of rated voltage.

Undervoltage Releases for Fuji MCCBs – Selection Guide			
Breaker Type	Part Number	Price	Description
BW125, BW250	BW9RGAR	\$81.00	Undervoltage Release 24V DC (Left side ONLY)
BW125, BW250	BW9RGAT	\$81.00	Undervoltage Release 110 to 130 VAC VAC/VDC (Left side ONLY)
BW400, BW630, BW800	BW9RHA-R	\$78.00	Undervoltage Release 24 VAC/VDC (Left side ONLY)
BW400, BW630, BW800	BW9RHA-1	\$81.00	Undervoltage Release 120 to 130 VAC 125 VDC (Left side ONLY)



BW9RGAR shown

Ratings of Undervoltage Trip				
Breaker Type	AC		DC	
	Voltage (V)	VA	Voltage (V)	W
BW125*1 BW250*1	–	–	24	5
	110 - 130	5	–	–
BW400*2 BW630*2 BW800*2	24	2	24	2
	120 - 130	3	125	3

Note: Allowable operating voltage: AC voltage: 85% to 110% of coil rated voltage
DC voltage: 75% to 125% of coil rated voltage.

*1 Reset-allowed type: When the breaker handle is in the OFF or RESET state, tripping does not occur, even if the undervoltage trip coil is not energized.

Turning ON with the undervoltage trip coil not energized causes normal tripping.

*2 Reset-prohibited type: When the undervoltage trip coil is not energized, reset operation cannot reset the tripped breaker to the OFF state.



BW9SL0GA-3 shown

Replacement Lugs

Replacement Lug Kits for Fuji MCCBs – Selection Guide		
Part Number	Price	Description
BW9SL0CA-3	\$82.00	Replacement lug kit for BW125 series MCCB. 75°C. Cu only Package of 3
BW9SL0GA-3	\$92.00	Replacement lug kit for BW250 series up to 175A MCCB. 75°C. Cu only Package of 3
BW9SL1GA-3	\$102.00	Replacement lug kit for BW250 MCCB series 200A to 250A. 75°C. Cu only Package of 3

Note: Terminals are factory-installed only for BW400, BW630 and BW800 series. No replacement terminals available.

Fuji Molded Case Circuit Breakers Accessories



Terminal Covers

Terminal covers act as guards to shield the operator from touching live terminations. They fit either the line or load side.




BW9BTJA-L3W shown

Terminal Covers for Fuji MCCBs – Selection Guide						
Breaker Type	Part Number	Price	Description	Dimensions inch (mm)		
				A	B	C
BW400	BW9BTJA-L3W	\$81.00	Gray-white Long type terminal cover for Fuji MCCBs. For line side and load side. 2/pk	6.772 (172)	4.331 (110)	3.858 (98)
BW630, BW800	BW9BTJA-L3W	\$84.00	Gray-white Long type terminal cover for Fuji MCCBs. For line side and load side. 2/pk	8.268 (210)	6.102 (155)	3.858 (98)

Note: Gray-white short type terminal covers are provided with breakers as standard for 125 and 250 Amp frames.

Dimensions of Terminal Covers: inch (mm)



Lockout Attachment

Lockout Attachments for Fuji MCCBs – Selection Guide			
Breaker Type	Part Number	Price	Description
BW125 BW250	BW9Q1CA	\$19.50	Use to lock out BW125 and BW 250 series MCCBs. Lock not included
BW400, BW630, BW800	BW9QNHA	\$47.50	Use to lock out BW400, BW600 and BW800 MCCBs. Lock not included.



BW9Q1CA shown

Fuji Molded Case Circuit Breakers

Wire Range Specifications



Wiring


- When connecting the wires, follow NEC (National Electric Code, USA) or CEC (Canadian Electrical code Part 1, Canada) instructions.
- Use copper wire rated for 75°C (167°F) for connecting. UL or CSA approved wire is recommended.
- Tighten the wire connections adequately, as a very large electromagnetic force will be generated when short circuit current is generated.
- Perform additional tightening of the terminal screws periodically.

Allowable Wire Specifications for Lug Terminals

Wire Size AWG or MCM (mm ²)	Number of Wire Strands
14 to 2 (2.1 to 33.6)	7
1 to 4/0 (42.4 to 107.2)	19
250 to 500 (127 to 250)	37




- Adhere to the allowable number of strands of wire indicated in the table on the left.
- Two wires cannot be connected together to a single connecting hole of lug terminal except BW400SAGU-3P400SB.
- Follow the number of strands of wire indicated on the table. (Wire size and number of wire strands not listed on table can not be connected)
- Do not solder the end of the wire.




Rated current
15A to 350A



Rated current
400A
3/0 AWG x 2
19 strands each



Rated current
500A to 700A



Rated current
800A
300 MCM x 3
37 strands each

Allowable Wire Sizes and Tightening Torque

Type	Rated Current (A)	Wire Size (AWG or MCM [mm ²])	Tightening Torque
			Lug Terminal*
BW125	15	14 AWG [2.1 mm ²]	51 lb•in [5.8 N•m]
	20	12 AWG [3.3 mm ²]	
	30	10 AWG [5.3 mm ²]	
	40	8 AWG [8.4 mm ²]	
	50	8 AWG [8.4 mm ²]	
	60	6 AWG [13.3 mm ²]	
	70	4 AWG [21.1 mm ²]	
	75	4 AWG [21.1 mm ²]	
	80	4 AWG [21.1 mm ²]	
	90	3 AWG [26.7 mm ²]	
	100	3 AWG [26.7 mm ²]	
BW250	125	1 AWG [42.4 mm ²]	204 lb•in [23 N•m]
	150	1/0 AWG [53.5 mm ²]	
	175	2/0 AWG [67.4 mm ²]	
	200	3/0 AWG [85.0 mm ²]	
	225	4/0 AWG [107.2 mm ²]	
	250	250 MCM [127 mm ²]	
BW400	250	250 MCM [127mm ²]	385 lb•in [43.5 N•m]
	300	350 MCM [177mm ²]	
	350	500 MCM [253mm ²]	
	400	3/0 AWGx2 [85.0 mm ² x2]	282 lb•in [31.9 N•m]
BW630	500	250 MCMx2	275 lb•in [31.07 N•m]
	600	350 MCMx2	
BW800	700	500 MCMx2	275 lb•in [31.07 N•m]
	800	300 MCMx3	

*Lug terminals are supplied as standard.

Note: Terminals are factory-installed only for BW400, BW630 and BW800 series.

No replacement terminals available.

Gladiator MCCB (Molded Case Circuit Breakers)



Gladiator MCCBs thermal-magnetic circuit breakers are designed to protect low voltage electrical systems from damage caused by overloads and short circuits.

Wide Range of Applications

- Branch and feeder circuits
- Industrial control panels
- Industrial machines
- Power distribution

High Performance

- Ultimate breaking capacity (kA rms)
- Max 65kA@480VAC and 50kA@600V
- DC ratings
- Reverse feed capable
- HACR (Heating, Air Conditioning and Refrigeration) rated

Simplified Product Range

- Seven frame sizes
- Three trip unit types
- Ampere range: 15A to 1200A
- Poles: 2P, 3P

Variety of Trip Units

- AA: Adjustable thermal & magnetic unit
- FF: Fixed thermal & magnetic unit
- ES: Electronic self-powered

STANDARDS

- World class with UL489
 - UL489
 - CSA C22.2 No. 5
- IEC60947-2
- Class 1E for Nuclear power plant
 - EQ : Environment Qualification
 - SQ : Seismic Qualification

Seven Frame Sizes Up To 1200A

GCB100 Series 15-100 A
GCB150 Series 125-150 A
GCB250 Series 175-250 A
GCB400 Series 300-400 A
GCB600 Series 500-600 A
GCB800 Series 800 A
GCB1200 Series 1200 A

Wide Range of Accessories


- Electrical auxiliaries (AUX, ALX, ALM, UVT, SHT)
- Extended rotary handle
- Flange handle with flexible cable and linkage
- Locking devices
- LUG for CU/AL cable with UL486



UL file E503708 MCCB
UL file E509077 Accessories


FF

Fixed Thermal: 15A to 600A
Fixed Magnetic: 400A to 6000A



AA


Adjustable Thermal: 100A to 600A
Adjustable Magnetic: 500A to 6000A



Gladiator MCCB Part Number Nomenclature

Gladiator MCCB

GCB 1200 S - 3 FF 75 LL



Gladiator MCCB Accessories

GCBX 1 - AUX - LT - BK

Series	Frame Size	Type	Product Description/Ratings	
GCBX	1: 100 2: 150-250 3: 400-600 4: 150-800 5: 800-1200	ALX – Alarm/Auxiliary	LT (left), RT (right), or Blank (either side)	
		AUX – Auxiliary	LT (left), RT (right), or Blank (either side)	
		ALM – Alarm Contact	LT (left), RT (right), or Blank (either side)	
		SHT – Shunt Trip	24VDC / 110VAC	
		UVT – Trip	24VDC / 110VAC	
		EHR – Exterior Handle Rotary	NEMA Rating: N12, N3R4, N1, N4X	Color: GY – Gray BK – Black
		SFT – Shaft	Length (12, 16, 24 in)	
		FHC – Flange Handle Cable	NEMA Rating (N12, N3R4, N1, N4X)	M – With operating mechanism
		CBL – Cable	Length (36, 60, or 72 in)	
		LCK – Locking Device	PL – Removable Padlocking	
		PBR – Insulating Phase Barrier	STD – Standard	

Gladiator MCCB GCB100 (15-100 A)

2-Pole or 3-Pole



GCB100S-2FF15LL

- HACR rated
- SWD (lighting circuits) switch duty rating (applied only to 15 and 20A / 347VAC or less)
- HID high intensity discharge lighting rating (15-50A / 480VAC or less)
- 40°C [104°F]
- Reverse feed capable
- Includes line and loadside lugs

Gladiator MCCB GCB100 2-Pole (15-100 A) Selection Guide

Part Number	Price	Frequency	Ampere Rating	Voltage (AC)	Interrupt Capacity (kA)	Voltage (DC)	Interrupt Capacity (kA)	Dimensional Drawing		
GCB100S-2FF15LL	\$194.00	50/60 Hz	15	120/240	65	250 (2P)	25	PDF		
GCB100S-2FF20LL	\$194.00		20					PDF		
GCB100S-2FF25LL	\$194.00		25					PDF		
GCB100S-2FF30LL	\$194.00		30					PDF		
GCB100S-2FF40LL	\$194.00		40	240	65			PDF		
GCB100S-2FF50LL	\$194.00		50	480	35			PDF		
GCB100S-2FF60LL	\$194.00		60	600Y/347	18			PDF		
GCB100S-2FF70LL	\$194.00		70					PDF		
GCB100S-2FF80LL	\$194.00		80					PDF		
GCB100S-2FF90LL	\$194.00		90					PDF		
GCB100S-2FF100LL	\$194.00		100					PDF		

Gladiator MCCB GCB100 3-Pole (15-100 A) Selection Guide

Part Number	Price	Frequency	Ampere Rating	Voltage (AC)	Interrupt Capacity (kA)	Voltage (DC)	Interrupt Capacity (kA)	Dimensional Drawing		
GCB100S-3FF15LL	\$232.00	50/60 Hz	15	120/240	65	250 (2P) 500 (3P)	25 35	PDF		
GCB100S-3FF20LL	\$232.00		20					PDF		
GCB100S-3FF25LL	\$232.00		25					PDF		
GCB100S-3FF30LL	\$232.00		30					PDF		
GCB100S-3FF40LL	\$232.00		40	240	65			PDF		
GCB100S-3FF50LL	\$232.00		50	480	35			PDF		
GCB100S-3FF60LL	\$232.00		60	600Y/347	18			PDF		
GCB100S-3FF70LL	\$232.00		70					PDF		
GCB100S-3FF80LL	\$232.00		80					PDF		
GCB100S-3FF90LL	\$232.00		90					PDF		
GCB100S-3FF100LL	\$232.00		100					PDF		

Gladiator MCCB GCB100 (15-100 A)

2-Pole or 3-Pole

Gladiator MCCB GCB100 (15-100 A) Specifications			
Maximum Rated Current		100A	100A
Number of Poles		2	3
Breaker Type		S	S
UL489/CSA C22.2		GCB100	GCB100
Interrupting capacity (kA rms) AC (50/60HZ) UL, CSA	120/240 V	65	65
	240VAC	65	65
	480VAC	35	35
	600VAC	–	–
	600Y/347 VAC	18	18
UL489 DC		GCB100	GCB100
Interrupting Capacity (kA) DC UL, CSA	250V DC-2P	25	25
	500V DC-3P	–	35
	600V DC-3P	–	–
IEC 60947-2		GCB100	GCB100
Ultimate Breaking Capacity, (kA rms) AC 50/60Hz, Icu	220/240V	65	65
	380/415V	35	35
	480/500V	–	–
Service Breaking Capacity, Ics (%Icu)		100%	100%
Insulation Voltage, Ui		750VAC	750VAC
Impulse Withstand Voltage, Uimp		8KVAC	8KVAC
Rated Short-Time Withstand Current (Icw)		–	–
Utilization Category		A	A
TRIP UNITS F : Fixed A : Adjustable T : Thermal E : Electronics	Amperes	15-100 A	15-100 A
	ATU	–	–
	FTU	✓	✓
	ETS	–	–
Trip Unit Mounted		✓	✓
Mechanical Lugs		✓	✓
Terminal Shields		–	–
Interphase Barriers		✓	✓
Shunt Trip		✓	✓
Undervoltage Trip		✓	✓
Auxiliary Switch		✓	✓
Alarm Switch		✓	✓
Flange Cable Handle		✓	✓
NEMA-Door-Mounted Operating Mechanisms		✓	✓
Handle Padlock Attachment		✓	✓
Weight (lb [kg])		1.64 [0.74]	2.33 [1.06]

Gladiator MCCB GCB100 (15-100 A)

2-Pole or 3-Pole – Accessories

Gladiator MCCB GCB100 (15-100 A) Accessories			
Part Number	Price	Description	Dimensional Drawing
<u>GCBX1-ALX-LT</u>	\$14.50	Gladiator field installable alarm/auxiliary contact, left side mount, (2) SPDT contact(s), 3A @ 250VAC/0.2A @ 250VDC, 20in 24AWG lead wires, Auxiliary contact indicates if the MCCB is closed or open/tripped. Alarm contact indicates if the MCCB is tripped.	NA
<u>GCBX1-ALX-RT</u>	\$14.50	Gladiator field installable alarm/auxiliary contact, right side mount, (2) SPDT contact(s), 3A @ 250VAC/0.2A @ 250VDC, 20in 24AWG lead wires, Auxiliary contact indicates if the MCCB is closed or open/tripped. Alarm contact indicates if the MCCB is tripped.	NA
<u>GCBX1-AUX-LT</u>	\$14.50	Gladiator field installable auxiliary contact, left side mount, (1) SPDT contact(s), 3A @ 250VAC/0.2A @ 250VDC, 20in 24AWG lead wires, Auxiliary contact indicates if the MCCB is closed or open/tripped.	NA
<u>GCBX1-AUX-RT</u>	\$14.50	Gladiator field installable auxiliary contact, right side mount, (1) SPDT contact(s), 3A @ 250VAC/0.2A @ 250VDC, 20in 24AWG lead wires, Auxiliary contact indicates if the MCCB is closed or open/tripped.	NA
<u>GCBX1-LCK-PL</u>	\$26.00	Gladiator lockout attachment, 5-8mm (3/16-5/16in) diameter. For locking in the OFF position only. Accepts up to 3 locks.	<u>PDF</u>
<u>GCBX1-SHT-110VAC</u>	\$29.50	Gladiator field installable shunt trip, right side mount, 110-130 VAC/VDC coil voltage, screw terminals.	NA
<u>GCBX1-SHT-24VDC</u>	\$26.00	Gladiator field installable shunt trip, right side mount, 24 VAC/VDC coil voltage, screw terminals.	NA
<u>GCBX1-UVT-110VAC</u>	\$29.50	Gladiator field installable undervoltage trip, right side mount, 110-130 VAC/VDC sensing range, screw terminals.	NA
<u>GCBX1-UVT-24VDC</u>	\$26.00	Gladiator field installable undervoltage trip, right side mount, 24 VAC/VDC sensing range, screw terminals.	NA



Gladiator MCCB GCB100 (15-100 A) Flange Handles and Cables			
Part Number	Price	Description	Dimensional Drawing
<u>GCBX1-FHC-N3R4-M</u>	\$283.00	Gladiator flange handle, lever, gray/chrome, external front mount, 2-position, lockable in OFF only, defeatable, NEMA 3/3R/4. Operating mechanism included.	<u>PDF</u>
<u>GCBX1-FHC-N4X-M</u>	\$306.00	Gladiator flange handle, lever, chrome, external front mount, 2-position, lockable in OFF only, defeatable, NEMA 3/4/4X. Operating mechanism included.	<u>PDF</u>
<u>GCBX2-CBL-36</u>	\$69.00	Gladiator cable assembly, 36in [0.91 m]	<u>PDF</u>
<u>GCBX2-CBL-60</u>	\$81.00	Gladiator cable assembly, 60in [1.52 m]	<u>PDF</u>



Gladiator MCCB GCB100 (15-100 A) Rotary Handles and Shafts			
Part Number	Price	Description	Dimensional Drawing
<u>GCBX1-EHR-N12-GY</u>	\$69.00	Gladiator rotary handle, pistol, gray, external front mount, 2-position, lockable in ON-OFF, defeatable, NEMA 1/12. Operating mechanism included.	<u>PDF</u>
<u>GCBX1-EHR-N3R4-BK</u>	\$76.00	Gladiator rotary handle, pistol, black, external front mount, 2-position, lockable in ON-OFF, defeatable, NEMA 3/3R/4. Operating mechanism included.	<u>PDF</u>
<u>GCBX1-EHR-N4X-BK</u>	\$87.00	Gladiator rotary handle, pistol, black, external front mount, 2-position, lockable in ON-OFF, defeatable, NEMA 3/4/4X. Operating mechanism included.	<u>PDF</u>
<u>GCBX1-SFT-12</u>	\$12.50	Gladiator shaft, 12in [0.30 m] length.	<u>PDF</u>
<u>GCBX1-SFT-16</u>	\$14.00	Gladiator shaft, 16in [0.41 m] length.	<u>PDF</u>
<u>GCBX1-SFT-24</u>	\$21.50	Gladiator shaft, 24in [0.61 m] length.	<u>PDF</u>

[GCBX1-EHR-N12-GY](#)



Gladiator MCCB GCB150 (125-150 A) 3-Pole



GCB150S-3FF125LL

- HACR rated
- 40°C [104°F]
- Reverse feed capable
- Includes line and loadside lugs

Gladiator MCCB GCB150 3-Pole (125-150 A) Selection Guide								
Part Number	Price	Frequency	Ampere Rating	Voltage (AC)	Interrupt Capacity (kA)	Voltage (DC)	Interrupt Capacity (kA)	Dimensional Drawing
GCB150S-3FF125LL	\$331.00	50/60 Hz	125	240	65	250 (2P) 600 (3P)	35	PDF
GCB150S-3FF150LL	\$331.00		150	480 600	35 18			PDF
GCB150H-3FF125LL	\$367.00		125	240	100	600 (3P)	50	PDF
GCB150H-3FF150LL	\$367.00		150	480 600	65 35			PDF

Gladiator MCCB GCB150 (125-150 A)

3-Pole


Gladiator MCCB GCB150 (125-150 A) Specifications			
Maximum Rated Current		150A	150A
Number of Poles		3	3
Breaker Type		S	H
UL489/CSA C22.2		GCB150	GCB150
Interrupting capacity (kA rms) AC (50/60HZ) UL, CSA	120/240 V	–	–
	240VAC	65	100
	480VAC	35	65
	600VAC	18	35
	600Y/347 VAC	–	–
UL489 DC		GCB150	GCB150
Interrupting Capacity (kA) DC UL, CSA	250V DC-2P	35	35
	500V DC-3P	–	–
	600V DC-3P	35	50
IEC 60947-2		GCB150	GCB150
Ultimate Breaking Capacity, (kA rms) AC 50/60Hz, Icu	220/240V	65	65
	380/415V	35	35
	480/500V	18	18
Service Breaking Capacity, Ics (%Icu)		100%	100%
Insulation Voltage, Ui		750VAC	750VAC
Impulse Withstand Voltage, Uimp		8KVAC	8KVAC
Rated Short-Time Withstand Current (Icw)		–	–
Utilization Category		A	A
TRIP UNITS F : Fixed A : Adjustable T : Thermal E : Electronics	Amperes	125-150 A	125-150 A
	ATU	–	–
	FTU	✓	✓
	ETS	–	–
Trip Unit Mounted		✓	✓
Mechanical Lugs		✓	✓
Terminal Shields		–	–
Interphase Barriers		✓	✓
Shunt Trip		✓	✓
Undervoltage Trip		✓	✓
Auxiliary Switch		✓	✓
Alarm Switch		✓	✓
Flange Cable Handle		✓	✓
NEMA-Door-Mounted Operating Mechanisms		✓	✓
Handle Padlock Attachment		✓	✓
Weight (lb [kg])		3.44 [1.56]	3.95 [1.79]

Gladiator MCCB GCB150 (125-150 A)


3-Pole – Accessories

Gladiator MCCB GCB150 3-Pole (125-150 A) Accessories			
Part Number	Price	Description	Dimensional Drawing
<u>GCBX2-LCK-PL</u>	\$40.50	Gladiator lockout attachment, 5-8mm (3/16-5/16in) diameter. For locking in the OFF position only. Accepts up to 3 locks.	<u>PDF</u>
<u>GCBX2-PBR-STD</u>	\$8.25	Gladiator phase barrier, package of 2.	<u>PDF</u>
<u>GCBX4-ALM</u>	\$14.50	Gladiator field installable alarm contact, left or right side mount, (1) SPDT contact(s), 3A @ 250VAC/0.2A @ 250VDC, 20in 26AWG lead wires, Alarm contacts indicate when the MCCB is tripped.	NA
<u>GCBX4-AUX</u>	\$14.50	Gladiator field installable auxiliary contact, left or right side mount, (1) SPDT contact(s), 3A @ 250VAC/0.2A @ 250VDC, screw terminals, Auxiliary contact indicates if the MCCB is closed or open/tripped.	NA
<u>GCBX4-SHT-110VAC</u>	\$37.00	Gladiator field installable shunt trip, left side mount, 110-130 VAC/VDC coil voltage, screw terminals.	NA
<u>GCBX4-SHT-24VDC</u>	\$37.00	Gladiator field installable shunt trip, left side mount, 24 VAC/VDC coil voltage, screw terminals.	NA
<u>GCBX4-UVT-110VAC</u>	\$48.50	Gladiator field installable undervoltage trip, left side mount, 110-130 VAC/VDC sensing range, screw terminals.	NA
<u>GCBX4-UVT-24VDC</u>	\$45.00	Gladiator field installable undervoltage trip, left side mount, 24 VAC/VDC sensing range, screw terminals.	NA

Gladiator MCCB GCB150 3-Pole (125-150 A) Flange Handles and Cables			
Part Number	Price	Description	Dimensional Drawing
<u>GCBX2-FHC-N3R4-M</u>	\$211.00	Gladiator flange handle, lever, gray/chrome, external front mount, 2-position, lockable in OFF only, defeatable, NEMA 3/3R/4. Operating mechanism included.	<u>PDF</u>
<u>GCBX2-FHC-N4X-M</u>	\$229.00	Gladiator flange handle, lever, chrome, external front mount, 2-position, lockable in OFF only, defeatable, NEMA 3/4/4X. Operating mechanism included.	<u>PDF</u>
<u>GCBX2-CBL-36</u>	\$69.00	Gladiator cable assembly, 36in [0.91 m]	<u>PDF</u>
<u>GCBX2-CBL-60</u>	\$81.00	Gladiator cable assembly, 60in [1.52 m]	<u>PDF</u>

[GCBX2-FHC-N3R4-M](#)

Gladiator MCCB GCB150 3-Pole (125-150 A) Rotary Handles and Shafts			
Part Number	Price	Description	Dimensional Drawing
<u>GCBX2-EHR-N12-GY</u>	\$79.00	Gladiator rotary handle, pistol, gray, external front mount, 2-position, lockable in ON-OFF, defeatable, NEMA 1/12. Operating mechanism included.	<u>PDF</u>
<u>GCBX2-EHR-N3R4-BK</u>	\$91.00	Gladiator rotary handle, pistol, black, external front mount, 2-position, lockable in ON-OFF, defeatable, NEMA 3/3R/4. Operating mechanism included.	<u>PDF</u>
<u>GCBX2-EHR-N4X-BK</u>	\$107.00	Gladiator rotary handle, pistol, black, external front mount, 2-position, lockable in ON-OFF, defeatable, NEMA 3/4/4X. Operating mechanism included.	<u>PDF</u>
<u>GCBX4-SFT-12</u>	\$20.00	Gladiator shaft, 12in [0.30 m] length.	<u>PDF</u>
<u>GCBX4-SFT-16</u>	\$22.00	Gladiator shaft, 16in [0.41 m] length.	<u>PDF</u>
<u>GCBX4-SFT-24</u>	\$33.00	Gladiator shaft, 24in [0.61 m] length.	<u>PDF</u>

[GCBX2-CBL-36](#)[GCBX4-SHT-24VDC](#)[GCBX4-UVT-24VDC](#)[GCBX4-AUX](#)[GCBX2-EHR-N12-GY](#)[GCBX4-ALM](#)[GCBX2-PBR-STD](#)[GCBX2-LCK-PL](#)[GCBX4-SFT-12](#)

Gladiator MCCB GCB250 (175-250 A) 3-Pole



GCB250S-3FF175LL



GCB250H-3FF175LL

- HACR rated
- 40°C [104°F]
- Reverse feed capable
- Includes line and loadside lugs

Gladiator MCCB GCB250 3-Pole (175-250 A) Selection Guide

Part Number	Price	Frequency	Ampere Rating	Voltage (AC)	Interrupt Capacity (kA)	Voltage (DC)	Interrupt Capacity (kA)	Dimensional Drawing
GCB250S-3FF175LL	\$444.00	50/60 Hz	175	240 480 600	65 35 18	250 (2P) 600 (3P)	35 35	PDF
GCB250S-3FF200LL	\$444.00		200					PDF
GCB250S-3FF225LL	\$444.00		225					PDF
GCB250S-3FF250LL	\$444.00		250					PDF
GCB250H-3FF175LL	\$500.00		175	240 480 600	100 65 35	250 (2P) 600 (3P)	50 50	PDF
GCB250H-3FF200LL	\$500.00		200					PDF
GCB250H-3FF225LL	\$500.00		225					PDF
GCB250H-3FF250LL	\$353.00		250					PDF
GCB250S-3AA200LL	\$531.00		200	240 480 600	65 35 18	250 (2P) 600 (3P)	35 35	PDF
GCB250S-3AA250LL	\$531.00		250					PDF

Gladiator MCCB GCB250 (175-250 A)

3-Pole


Gladiator MCCB GCB250 3-Pole (175-250 A) Specifications			
Maximum Rated Current		250A	250A
Number of Poles		3	3
Breaker Type		S	H
UL489/CSA C22.2		GCB250	GCB250
Interrupting capacity (kA rms) AC (50/60HZ) UL, CSA	120/240 V	–	–
	240VAC	65	100
	480VAC	35	65
	600VAC	18	35
	600Y/347 VAC	–	–
UL489 DC		GCB250	GCB250
Interrupting Capacity (kA) DC UL, CSA	250V DC-2P	35	50
	500V DC-3P	–	–
	600V DC-3P	35	50
IEC 60947-2		GCB250	GCB250
Ultimate Breaking Capacity, (kA rms) AC 50/60Hz, Icu	220/240V	65	100
	380/415V	35	65
	480/500V	18	35
Service Breaking Capacity, Ics (%Icu)		100%	100%
Insulation Voltage, Ui		750VAC	750VAC
Impulse Withstand Voltage, Uimp		8KVAC	8KVAC
Rated Short-Time Withstand Current (Icw)		–	–
Utilization Category		A	A
TRIP UNITS F : Fixed A : Adjustable T : Thermal E : Electronics	Amperes	175-250 A	175-250 A
	ATU	✓	–
	FTU	✓	✓
	ETS	–	–
Trip Unit Mounted		✓	✓
Mechanical Lugs		✓	✓
Terminal Shields		–	–
Interphase Barriers		✓	✓
Shunt Trip		✓	✓
Undervoltage Trip		✓	✓
Auxiliary Switch		✓	✓
Alarm Switch		✓	✓
Flange Cable Handle		✓	✓
NEMA-Door-Mounted Operating Mechanisms		✓	✓
Handle Padlock Attachment		✓	✓
Weight (lb [kg])		4.49 [2.04]	4.49 [2.04]

Gladiator MCCB GCB250 (175-250 A)

3-Pole – Accessories

Gladiator MCCB GCB250 3-Pole (175-250 A) Accessories			
Part Number	Price	Description	Dimensional Drawing
<u>GCBX2-LCK-PL</u>	\$40.50	Gladiator lockout attachment, 5-8mm (3/16-5/16in) diameter. For locking in the OFF position only. Accepts up to 3 locks.	<u>PDF</u>
<u>GCBX2-PBR-STD</u>	\$8.25	Gladiator phase barrier, package of 2.	<u>PDF</u>
<u>GCBX4-ALM</u>	\$14.50	Gladiator field installable alarm contact, left or right side mount, (1) SPDT contact(s), 3A @ 250VAC/0.2A @ 250VDC, 20in 26AWG lead wires, Alarm contacts indicate when the MCCB is tripped.	NA
<u>GCBX4-AUX</u>	\$14.50	Gladiator field installable auxiliary contact, left or right side mount, (1) SPDT contact(s), 3A @ 250VAC/0.2A @ 250VDC, screw terminals, Auxiliary contact indicates if the MCCB is closed or open/tripped.	NA
<u>GCBX4-SHT-110VAC</u>	\$37.00	Gladiator field installable shunt trip, left side mount, 110-130 VAC/VDC coil voltage, screw terminals.	NA
<u>GCBX4-SHT-24VDC</u>	\$37.00	Gladiator field installable shunt trip, left side mount, 24 VAC/VDC coil voltage, screw terminals.	NA
<u>GCBX4-UVT-110VAC</u>	\$48.50	Gladiator field installable undervoltage trip, left side mount, 110-130 VAC/VDC sensing range, screw terminals.	NA
<u>GCBX4-UVT-24VDC</u>	\$45.00	Gladiator field installable undervoltage trip, left side mount, 24 VAC/VDC sensing range, screw terminals.	NA

Gladiator MCCB GCB250 3-Pole (175-250 A) Flange Handles and Cables			
Part Number	Price	Description	Dimensional Drawing
<u>GCBX2-FHC-N3R4-M</u>	\$211.00	Gladiator flange handle, lever, gray/chrome, external front mount, 2-position, lockable in OFF only, defeatable, NEMA 3/3R/4. Operating mechanism included.	<u>PDF</u>
<u>GCBX2-FHC-N4X-M</u>	\$229.00	Gladiator flange handle, lever, chrome, external front mount, 2-position, lockable in OFF only, defeatable, NEMA 3/4/4X. Operating mechanism included.	<u>PDF</u>
<u>GCBX2-CBL-36</u>	\$69.00	Gladiator cable assembly, 36in [0.91 m]	<u>PDF</u>
<u>GCBX2-CBL-60</u>	\$81.00	Gladiator cable assembly, 60in [1.52 m]	<u>PDF</u>

[GCBX2-FHC-N3R4-M](#)[GCBX2-CBL-36](#)

Gladiator MCCB GCB250 3-Pole (175-250 A) Rotary Handles and Shafts			
Part Number	Price	Description	Dimensional Drawing
<u>GCBX2-EHR-N12-GY</u>	\$79.00	Gladiator rotary handle, pistol, gray, external front mount, 2-position, lockable in ON-OFF, defeatable, NEMA 1/12. Operating mechanism included.	<u>PDF</u>
<u>GCBX2-EHR-N3R4-BK</u>	\$91.00	Gladiator rotary handle, pistol, black, external front mount, 2-position, lockable in ON-OFF, defeatable, NEMA 3/3R/4. Operating mechanism included.	<u>PDF</u>
<u>GCBX2-EHR-N4X-BK</u>	\$107.00	Gladiator rotary handle, pistol, black, external front mount, 2-position, lockable in ON-OFF, defeatable, NEMA 3/4/4X. Operating mechanism included.	<u>PDF</u>
<u>GCBX4-SFT-12</u>	\$20.00	Gladiator shaft, 12in [0.30 m] length.	<u>PDF</u>
<u>GCBX4-SFT-16</u>	\$22.00	Gladiator shaft, 16in [0.41 m] length.	<u>PDF</u>
<u>GCBX4-SFT-24</u>	\$33.00	Gladiator shaft, 24in [0.61 m] length.	<u>PDF</u>

[GCBX4-SFT-12](#)[GCBX2-EHR-N12-GY](#)[GCBX4-UVT-24VDC](#)[GCBX4-SHT-24VDC](#)[GCBX4-AUX](#)[GCBX2-PBR-STD](#)[GCBX4-ALM](#)[GCBX2-LCK-PL](#)

Gladiator MCCB GCB400 (300-400 A) 3-Pole



GCB400S-3FF300LL



GCB400H-3FF300LL

- HACR rated
- 40°C [104°F]
- Reverse feed capable
- Includes line and loadside lugs

Gladiator MCCB GCB400 3-Pole (300-400 A) Selection Guide

Part Number	Price	Frequency	Ampere Rating	Voltage (AC)	Interrupt Capacity (kA)	Voltage (DC)	Interrupt Capacity (kA)	Dimensional Drawing
<u>GCB400S-3FF300LL</u>	\$858.00	50/60 Hz	300	240 480 600	65 35 18	250 600	35 35	<u>PDF</u>
<u>GCB400S-3FF350LL</u>	\$858.00		350					<u>PDF</u>
<u>GCB400S-3FF400LL</u>	\$858.00		400					<u>PDF</u>
<u>GCB400H-3FF300LL</u>	\$962.00		300	240 480 600	100 65 35	250 600	50 50	<u>PDF</u>
<u>GCB400H-3FF350LL</u>	\$962.00		350					<u>PDF</u>
<u>GCB400H-3FF400LL</u>	\$962.00		400					<u>PDF</u>
<u>GCB400H-3AA300LL</u>	\$1,222.00		300					<u>PDF</u>
<u>GCB400H-3AA400LL</u>	\$1,222.00		400					<u>PDF</u>

Gladiator MCCB GCB400 (300-400 A)

3-Pole

Gladiator MCCB GCB400 3-Pole (300-400 A) Specifications			
Maximum Rated Current		400	400
Number of Poles		3	3
Breaker Type		S	H
UL489/CSA C22.2		GCB400	GCB400
Interrupting capacity (kA rms) AC (50/60HZ) UL, CSA	120/240 V	–	–
	240VAC	65	100
	480VAC	35	65
	600VAC	18	35
	600Y/347 VAC	–	–
UL489 DC		GCB400	GCB400
Interrupting Capacity (kA) DC UL, CSA	250V DC-2P	35	50
	500V DC-3P	–	–
	600V DC-3P	35	50
IEC 60947-2		GCB400	GCB400
Ultimate Breaking Capacity, (kA rms) AC 50/60Hz, Icu	220/240V	65	100
	380/415V	35	65
	480/500V	18	35
Service Breaking Capacity, Ics (%Icu)		100%	100%
Insulation Voltage, Ui		750VAC	750VAC
Impulse Withstand Voltage, Uimp		8KVAC	8KVAC
Rated Short-Time Withstand Current (Icw)		–	–
Utilization Category		A	A
TRIP UNITS F : Fixed A : Adjustable T : Thermal E : Electronics	Amperes	300/350/400 A	300/350/400 A
	ATU	–	✓
	FTU	✓	✓
	ETS	–	–
Trip Unit Mounted		✓	✓
Mechanical Lugs		✓	✓
Terminal Shields		✓	✓
Interphase Barriers		✓	✓
Shunt Trip		✓	✓
Undervoltage Trip		✓	✓
Auxiliary Switch		✓	✓
Alarm Switch		✓	✓
Flange Cable Handle		✓	✓
NEMA-Door-Mounted Operating Mechanisms		✓	✓
Handle Padlock Attachment		✓	✓
Weight (lb [kg])		13.89 [6.30]	13.89 [6.30]

Gladiator MCCB GCB400 (300-400 A)

3-Pole – Accessories

Gladiator MCCB GCB400 3-Pole (300-400 A) Accessories			
Part Number	Price	Description	Dimensional Drawing
<u>GCBX3-LCK-PL</u>	\$48.50	Gladiator lockout attachment, 5-8mm (3/16-5/16in) diameter. For locking in the OFF position only. Accepts up to 3 locks.	<u>PDF</u>
<u>GCBX3-PBR-STD</u>	\$16.00	Gladiator phase barrier, package of 2.	<u>PDF</u>
<u>GCBX4-ALM</u>	\$14.50	Gladiator field installable alarm contact, left or right side mount, (1) SPDT contact(s), 3A @ 250VAC/0.2A @ 250VDC, 20in 26AWG lead wires, Alarm contacts indicate when the MCCB is tripped.	NA
<u>GCBX4-AUX</u>	\$14.50	Gladiator field installable auxiliary contact, left or right side mount, (1) SPDT contact(s), 3A @ 250VAC/0.2A @ 250VDC, screw terminals, Auxiliary contact indicates if the MCCB is closed or open/tripped.	NA
<u>GCBX4-SHT-110VAC</u>	\$37.00	Gladiator field installable shunt trip, left side mount, 110-130 VAC/VDC coil voltage, screw terminals.	NA
<u>GCBX4-SHT-24VDC</u>	\$37.00	Gladiator field installable shunt trip, left side mount, 24 VAC/VDC coil voltage, screw terminals.	NA
<u>GCBX4-UVT-110VAC</u>	\$48.50	Gladiator field installable undervoltage trip, left side mount, 110-130 VAC/VDC sensing range, screw terminals.	NA
<u>GCBX4-UVT-24VDC</u>	\$45.00	Gladiator field installable undervoltage trip, left side mount, 24 VAC/VDC sensing range, screw terminals.	NA

Gladiator MCCB GCB400 3-Pole (300-400 A) Flange Handles and Cables			
Part Number	Price	Description	Dimensional Drawing
<u>GCBX3-FHC-N3R4-M</u>	\$211.00	Gladiator flange handle, lever, gray/chrome, external front mount, 2-position, lockable in OFF only, defeatable, NEMA 3/3R/4. Operating mechanism included.	<u>PDF</u>
<u>GCBX3-FHC-N4X-M</u>	\$177.00	Gladiator flange handle, lever, chrome, external front mount, 2-position, lockable in OFF only, defeatable, NEMA 3/4/4X. Operating mechanism included.	<u>PDF</u>
<u>GCBX3-CBL-36</u>	\$81.00	Gladiator cable assembly, 36in [0.91 m]	<u>PDF</u>
<u>GCBX3-CBL-60</u>	\$96.00	Gladiator cable assembly, 60in [1.52 m]	<u>PDF</u>

[GCBX3-FHC-N3R4-M](#)[GCBX3-CBL-36](#)

Gladiator MCCB GCB400 3-Pole (300-400A) Rotary Handles and Shafts			
Part Number	Price	Description	Dimensional Drawing
<u>GCBX3-EHR-N12-GY</u>	\$95.00	Gladiator rotary handle, pistol, gray, external front mount, 2-position, lockable in ON-OFF, defeatable, NEMA 1/12. Operating mechanism included.	<u>PDF</u>
<u>GCBX3-EHR-N3R4-BK</u>	\$110.00	Gladiator rotary handle, pistol, black, external front mount, 2-position, lockable in ON-OFF, defeatable, NEMA 3/3R/4. Operating mechanism included.	<u>PDF</u>
<u>GCBX3-EHR-N4X-BK</u>	\$125.00	Gladiator rotary handle, pistol, black, external front mount, 2-position, lockable in ON-OFF, defeatable, NEMA 3/4/4X. Operating mechanism included.	<u>PDF</u>
<u>GCBX4-SFT-12</u>	\$20.00	Gladiator shaft, 12in [0.30 m] length.	<u>PDF</u>
<u>GCBX4-SFT-16</u>	\$22.00	Gladiator shaft, 16in [0.41 m] length.	<u>PDF</u>
<u>GCBX4-SFT-24</u>	\$33.00	Gladiator shaft, 24in [0.61 m] length.	<u>PDF</u>

[GCBX4-SFT-12](#)[GCBX3-EHR-N12-GY](#)[GCBX4-AUX](#)[GCBX4-SHT-24VDC](#)[GCBX4-UVT-24VDC](#)[GCBX4-ALM](#)[GCBX3-PBR-STD](#)[GCBX3-LCK-PL](#)

Gladiator MCCB GCB600 (500-600 A) 3-Pole



GCB600S-3FF500LL



GCB600H-3FF500LL

- HACR rated
- 40°C [104°F]
- Reverse feed capable
- Includes line and loadside lugs

Gladiator MCCB GCB600 3-Pole (500-600 A) Selection Guide

Part Number	Price	Frequency	Ampere Rating	Voltage (AC)	Interrupt Capacity (kA)	Voltage (DC)	Interrupt Capacity (kA)	Dimensional Drawing
GCB600S-3FF500LL	\$1,422.00	50/60 Hz	500	240	65	250 (2P) 600 (3P)	35	PDF
GCB600S-3FF600LL	\$1,422.00		600	480 600	35 18			PDF
GCB600H-3FF500LL	\$1,661.00		500	240 480 600	100 65 35	250 (2P) 600 (3P)	50 50	PDF
GCB600H-3FF600LL	\$1,661.00		600					PDF
GCB600H-3AA500LL	\$2,296.00		500					PDF
GCB600H-3AA600LL	\$2,296.00		600					PDF

Gladiator MCCB GCB600 (500-600 A)

3-Pole


Gladiator MCCB GCB600 3-Pole (500-600 A) Specifications			
Maximum Rated Current		600	600
Number of Poles		3	3
Breaker Type		S	H
UL489/CSA C22.2		GCB600	GCB600
Interrupting capacity (kA rms) AC (50/60HZ) UL, CSA	120/240 V	–	–
	240VAC	65	100
	480VAC	35	65
	600VAC	18	35
	600Y/347 VAC	–	–
UL489 DC		GCB600	GCB600
Interrupting Capacity (kA) DC UL, CSA	250V DC-2P	35	50
	500V DC-3P	–	–
	600V DC-3P	35	50
IEC 60947-2		GCB600	GCB600
Ultimate Breaking Capacity, (kA rms) AC 50/60Hz, Icu	220/240V	65	100
	380/415V	35	65
	480/500V	18	35
Service Breaking Capacity, Ics (%Icu)		100%	100%
Insulation Voltage, Ui		750VAC	750VAC
Impulse Withstand Voltage, Uimp		8KVAC	8KVAC
Rated Short-Time Withstand Current (Icw)		–	–
Utilization Category		A	A
TRIP UNITS F : Fixed A : Adjustable T : Thermal E : Electronics	Amperes	500/600 A	500/600 A
	ATU	–	✓
	FTU	✓	✓
	ETS	–	–
Trip Unit Mounted		✓	✓
Mechanical Lugs		✓	✓
Terminal Shields		✓	✓
Interphase Barriers		✓	✓
Shunt Trip		✓	✓
Undervoltage Trip		✓	✓
Auxiliary Switch		✓	✓
Alarm Switch		✓	✓
Flange Cable Handle		✓	✓
Directly-Mounted Rotary Operating Handle		✓	✓
NEMA-Door-Mounted Operating Mechanisms		✓	✓
Handle Padlock Attachment		✓	✓
Weight (lb [kg])		15.79 [7.16]	15.79 [7.16]

Gladiator MCCB GCB600 (500-600 A)


3-Pole – Accessories

Gladiator MCCB GCB600 3-Pole (500-600 A) Accessories			
Part Number	Price	Description	Dimensional Drawing
<u>GCBX3-LCK-PL</u>	\$48.50	Gladiator lockout attachment, 5-8mm (3/16-5/16in) diameter. For locking in the OFF position only. Accepts up to 3 locks.	<u>PDF</u>
<u>GCBX3-PBR-STD</u>	\$16.00	Gladiator phase barrier, package of 2.	<u>PDF</u>
<u>GCBX4-ALM</u>	\$14.50	Gladiator field installable alarm contact, left or right side mount, (1) SPDT contact(s), 3A @ 250VAC/0.2A @ 250VDC, 20in 26AWG lead wires, Alarm contacts indicate when the MCCB is tripped.	NA
<u>GCBX4-AUX</u>	\$14.50	Gladiator field installable auxiliary contact, left or right side mount, (1) SPDT contact(s), 3A @ 250VAC/0.2A @ 250VDC, screw terminals, Auxiliary contact indicates if the MCCB is closed or open/tripped.	NA
<u>GCBX4-SHT-110VAC</u>	\$37.00	Gladiator field installable shunt trip, left side mount, 110-130 VAC/VDC coil voltage, screw terminals.	NA
<u>GCBX4-SHT-24VDC</u>	\$37.00	Gladiator field installable shunt trip, left side mount, 24 VAC/VDC coil voltage, screw terminals.	NA
<u>GCBX4-UVT-110VAC</u>	\$48.50	Gladiator field installable undervoltage trip, left side mount, 110-130 VAC/VDC sensing range, screw terminals.	NA
<u>GCBX4-UVT-24VDC</u>	\$45.00	Gladiator field installable undervoltage trip, left side mount, 24 VAC/VDC sensing range, screw terminals.	NA

Gladiator MCCB GCB600 3-Pole (500-600 A) Flange Handles and Cables			
Part Number	Price	Description	Dimensional Drawing
<u>GCBX3-FHC-N3R4-M</u>	\$211.00	Gladiator flange handle, lever, gray/chrome, external front mount, 2-position, lockable in OFF only, defeatable, NEMA 3/3R/4. Operating mechanism included.	<u>PDF</u>
<u>GCBX3-FHC-N4X-M</u>	\$177.00	Gladiator flange handle, lever, chrome, external front mount, 2-position, lockable in OFF only, defeatable, NEMA 3/4/4X. Operating mechanism included.	<u>PDF</u>
<u>GCBX3-CBL-36</u>	\$81.00	Gladiator cable assembly, 36in [0.91 m]	<u>PDF</u>
<u>GCBX3-CBL-60</u>	\$96.00	Gladiator cable assembly, 60in [1.52 m]	<u>PDF</u>

[GCBX3-FHC-N3R4-M](#)[GCBX3-CBL-36](#)[GCBX4-SFT-12](#)

Gladiator MCCB GCB600 3-Pole (500-600 A) Rotary Handles and Shafts			
Part Number	Price	Description	Dimensional Drawing
<u>GCBX3-EHR-N12-GY</u>	\$95.00	Gladiator rotary handle, pistol, gray, external front mount, 2-position, lockable in ON-OFF, defeatable, NEMA 1/12. Operating mechanism included.	<u>PDF</u>
<u>GCBX3-EHR-N3R4-BK</u>	\$110.00	Gladiator rotary handle, pistol, black, external front mount, 2-position, lockable in ON-OFF, defeatable, NEMA 3/3R/4. Operating mechanism included.	<u>PDF</u>
<u>GCBX3-EHR-N4X-BK</u>	\$125.00	Gladiator rotary handle, pistol, black, external front mount, 2-position, lockable in ON-OFF, defeatable, NEMA 3/4/4X. Operating mechanism included.	<u>PDF</u>
<u>GCBX4-SFT-12</u>	\$20.00	Gladiator shaft, 12in [0.30 m] length.	<u>PDF</u>
<u>GCBX4-SFT-16</u>	\$22.00	Gladiator shaft, 16in [0.41 m] length.	<u>PDF</u>
<u>GCBX4-SFT-24</u>	\$33.00	Gladiator shaft, 24in [0.61 m] length.	<u>PDF</u>

[GCBX3-EHR-N12-GY](#)[GCBX4-SHT-24VDC](#)[GCBX4-UVT-24VDC](#)[GCBX4-AUX](#)[GCBX3-PBR-STD](#)[GCBX3-LCK-PL](#)[GCBX4-ALM](#)

Gladiator MCCB GCB800 (800A) 3-Pole



[GCB800S-3ES800LL](#)



[GCB800H-3ES800LL](#)

- HACR rated
- 40°C [104°F]
- Self-powered electronic trip unit
- Reverse feed capable
- Includes line and loadside lugs

Gladiator MCCB GCB800 3-Pole (800A) Selection Guide								
Part Number	Price	Frequency	Ampere Rating	Voltage (AC)	Interrupt Capacity (kA)	Voltage (DC)	Interrupt Capacity (kA)	Dimensional Drawing
<u>GCB800S-3ES800LL</u>	\$1,935.00	50/60 Hz	800	240 480 600	65 35 18	—	—	<u>PDF</u>
<u>GCB800H-3ES800LL</u>	\$2,322.00		800	240 480 600	100 65 35	—	—	<u>PDF</u>

Gladiator MCCB GCB800 (800A)

3-Pole


Gladiator MCCB GCB800 3-Pole (800A) Specifications			
Maximum Rated Current		800A	800A
Number of Poles		3	3
Breaker Type		S	H
UL489/CSA C22.2		GCB800	GCB800
Interrupting capacity (kA rms) AC (50/60HZ) UL, CSA	120/240 V	–	–
	240VAC	65	100
	480VAC	35	65
	600VAC	18	35
	600Y/347 VAC	–	–
UL489 DC		GCB800	GCB800
Interrupting Capacity (kA) DC UL, CSA	250V DC-2P	–	–
	500V DC-3P	–	–
	600V DC-3P	–	–
IEC 60947-2		GCB800	GCB800
Ultimate Breaking Capacity, (kA rms) AC 50/60Hz, Icu	220/240V	65	100
	380/415V	35	65
	480/500V	18	35
Service Breaking Capacity, Ics (%Icu)		100%	100%
Insulation Voltage, Ui		1000VAC	1000VAC
Impulse Withstand Voltage, Uimp		8KVAC	8KVAC
Rated Short-Time Withstand Current (Icw)		18kA	–
Utilization Category		B	A
TRIP UNITS F : Fixed A : Adjustable T : Thermal E : Electronics	Amperes	800 A	800 A
	ATU	–	–
	FTU	–	–
	ETS	✓	✓
Trip Unit Mounted		✓	✓
Mechanical Lugs		✓	✓
Terminal Shields		✓	✓
Interphase Barriers		✓	✓
Shunt Trip		✓	✓
Undervoltage Trip		✓	✓
Auxiliary Switch		✓	✓
Alarm Switch		✓	✓
Flange Cable Handle		✓	✓
NEMA-Door-Mounted Operating Mechanisms		✓	✓
Handle Padlock Attachment		✓	✓
Weight (lb [kg])		31.35 [14.22]	31.35 [14.22]

Gladiator MCCB GCB800 (800A)


3-Pole – Accessories

Gladiator MCCB GCB800 3-Pole (800A) Accessories			
Part Number	Price	Description	Dimensional Drawing
<u>GCBX5-ALM</u>	\$14.50	Gladiator field installable alarm contact, right side mount, (1) SPDT contact(s), 3A @ 250VAC/0.2A @ 250VDC, 20in 26AWG lead wires, Alarm contacts indicate when the MCCB is tripped.	NA
<u>GCBX5-AUX</u>	\$14.50	Gladiator field installable auxiliary contact, right side mount, (1) SPDT contact(s), 3A @ 250VAC/0.2A @ 250VDC, screw terminals, Auxiliary contact indicates if the MCCB is closed or open/tripped.	NA
<u>GCBX5-LCK-PL</u>	\$56.00	Gladiator lockout attachment, 5-8mm (3/16-5/16in) diameter. For use with Gladiator 800A and 1200A frame MCCBs. Accepts up to 3 locks.	<u>PDF</u>
<u>GCBX5-PBR-STD</u>	\$34.00	Gladiator phase barrier, package of 2.	<u>PDF</u>
<u>GCBX5-SHT-110VAC</u>	\$69.00	Gladiator field installable shunt trip, right side mount, 110-130 VAC/VDC coil voltage, screw terminals.	NA
<u>GCBX5-SHT-24VDC</u>	\$69.00	Gladiator field installable shunt trip, right side mount, 24 VAC/VDC coil voltage, screw terminals.	NA
<u>GCBX5-UVT-110VAC</u>	\$82.00	Gladiator field installable undervoltage trip, right side mount, 110-130 VAC/VDC sensing range, screw terminals.	NA
<u>GCBX5-UVT-24VDC</u>	\$76.00	Gladiator field installable undervoltage trip, right side mount, 24 VAC/VDC sensing range, screw terminals.	NA

Gladiator MCCB GCB800 3-Pole (800A) Flange Handles and Cables			
Part Number	Price	Description	Dimensional Drawing
<u>GCBX5-FHC-N3R4-M</u>	\$459.00	Gladiator flange handle, lever, gray/chrome, external front mount, 2-position, lockable in OFF only, defeatable, NEMA 3/3R/4. Operating mechanism included.	<u>PDF</u>
<u>GCBX5-FHC-N4X-M</u>	\$485.00	Gladiator flange handle, lever, chrome, external front mount, 2-position, lockable in OFF only, defeatable, NEMA 3/4/4X. Operating mechanism included.	<u>PDF</u>
<u>GCBX5-CBL-60</u>	\$102.00	Gladiator cable assembly, 60in [1.52 m]	<u>PDF</u>



Gladiator MCCB GCB800 3-Pole (800 A) Rotary Handles and Shafts			
Part Number	Price	Description	Dimensional Drawing
<u>GCBX5-EHR-N12-GY</u>	\$209.00	Gladiator rotary handle, tee, gray, external front mount, 2-position, lockable in ON-OFF, defeatable, NEMA 1/12. Operating mechanism included.	<u>PDF</u>
<u>GCBX5-EHR-N3R4-BK</u>	\$225.00	Gladiator rotary handle, tee, black, external front mount, 2-position, lockable in ON-OFF, defeatable, NEMA 3/3R/4. Operating mechanism included.	<u>PDF</u>
<u>GCBX5-EHR-N4X-BK</u>	\$247.00	Gladiator rotary handle, tee, black, external front mount, 2-position, lockable in ON-OFF, defeatable, NEMA 3/4/4X. Operating mechanism included.	<u>PDF</u>
<u>GCBX5-SFT-12</u>	\$33.00	Gladiator shaft, 12in [0.30 m] length.	<u>PDF</u>
<u>GCBX5-SFT-16</u>	\$35.00	Gladiator shaft, 16in [0.41 m] length.	<u>PDF</u>
<u>GCBX5-SFT-24</u>	\$52.00	Gladiator shaft, 24in [0.61 m] length.	<u>PDF</u>



Trip Unit Replacement Battery

Gladiator Trip Unit Replacement Battery			
Part Number	Price	Description	Drawing
<u>GCBX5-BATT</u>	\$22.00	Gladiator trip unit replacement battery, for use with GCB800 and GCB1200 molded case circuit breakers.	NA



Gladiator MCCB GCB1200 (1200A) 3-Pole



GCB1200S-3ES1200LL



GCB1200H-3ES1200LL

- HACR rated
- 40°C [104°F]
- Self-powered electronic trip unit
- Reverse feed capable
- Includes line and loadside lugs

Gladiator MCCB GCB1200 3-Pole (1200A) Selection Guide								
Part Number	Price	Frequency	Ampere Rating	Voltage (AC)	Interrupt Capacity (kA)	Voltage (DC)	Interrupt Capacity (kA)	Dimensional Drawing
<u>GCB1200S-3ES1200LL</u>	\$2,875.00	50/60 Hz	1200	240	50	—	—	PDF
				480	35			
				600	18			
<u>GCB1200H-3ES1200LL</u>	\$3,448.00		1200	240	100	—	—	PDF
				480	65			
				600	25			

Gladiator MCCB GCB1200 (1200A)

3-Pole

Gladiator MCCB GCB1200 3-Pole (1200A) Specifications				
Maximum Rated Current		1200A		
Number of Poles		3		3
Breaker Type		S		H
UL489/CSA C22.2		GCB1200		
Interrupting capacity (kA rms) AC(50/60HZ) UL, CSA	120/240 V	–		–
	240VAC	50		100
	480VAC	35		65
	600VAC	18		25
	600Y/347 VAC	–		–
UL489 DC		GCB1200		
Interrupting Capacity (kA) DC UL, CSA	250V DC-2P	–		–
	500V DC-3P	–		–
	600V DC-3P	–		–
IEC 60947-2		GCB1200		
Ultimate Breaking Capacity, (kA rms) AC 50/60Hz, Icu	220/240V	50		100
	380/415V	35		65
	480/500V	25		35
Service Breaking Capacity, Ics (%Icu)		100%		100%
Insulation Voltage, Ui		1000VAC		1000VAC
Impulse Withstand Voltage, Uimp		8KVAC		8KVAC
Rated Short-Time Withstand Current (Icw)		25KA		–
Utilization Category		B		A
TRIP UNITS F : Fixed A : Adjustable T : Thermal E : Electronics	Amperes	1200A		1200A
	ATU	–		–
	FTU	–		–
	ETS	✓		✓
Trip Unit Mounted		✓		✓
Mechanical Lugs		✓		✓
Terminal Shields		✓		✓
Interphase Barriers		✓		✓
Shunt Trip		✓		✓
Undervoltage Trip		✓		✓
Auxiliary Switch		✓		✓
Alarm Switch		✓		✓
Flange Cable Handle		✓		✓
NEMA-Door-Mounted Operating Mechanisms		✓		✓
Handle Padlock Attachment		✓		✓
Weight (lb [kg])		40.28 [18.27]		40.28 [18.27]

Gladiator MCCB GCB1200 (1200A)


3-Pole – Accessories

Gladiator MCCB GCB1200 3-Pole (1200A) Accessories			
Part Number	Price	Description	Dimensional Drawing
<u>GCBX5-ALM</u>	\$14.50	Gladiator field installable alarm contact, right side mount, (1) SPDT contact(s), 3A @ 250VAC/0.2A @ 250VDC, 20in 26AWG lead wires, Alarm contacts indicate when the MCCB is tripped.	NA
<u>GCBX5-AUX</u>	\$14.50	Gladiator field installable auxiliary contact, right side mount, (1) SPDT contact(s), 3A @ 250VAC/0.2A @ 250VDC, screw terminals, Auxiliary contact indicates if the MCCB is closed or open/tripped.	NA
<u>GCBX5-LCK-PL</u>	\$56.00	Gladiator lockout attachment, 5-8mm (3/16-5/16in) diameter. For locking in the OFF position only. Accepts up to 3 locks.	<u>PDF</u>
<u>GCBX5-PBR-STD</u>	\$34.00	Gladiator phase barrier, package of 2.	<u>PDF</u>
<u>GCBX5-SHT-110VAC</u>	\$69.00	Gladiator field installable shunt trip, right side mount, 110-130 VAC/VDC coil voltage, screw terminals.	NA
<u>GCBX5-SHT-24VDC</u>	\$69.00	Gladiator field installable shunt trip, right side mount, 24 VAC/VDC coil voltage, screw terminals.	NA
<u>GCBX5-UVT-110VAC</u>	\$82.00	Gladiator field installable undervoltage trip, right side mount, 110-130 VAC/VDC sensing range, screw terminals.	NA
<u>GCBX5-UVT-24VDC</u>	\$76.00	Gladiator field installable undervoltage trip, right side mount, 24 VAC/VDC sensing range, screw terminals.	NA

Gladiator MCCB GCB1200 3-Pole (1200A) Flange Handles and Cables			
Part Number	Price	Description	Dimensional Drawing
<u>GCBX5-FHC-N3R4-M</u>	\$459.00	Gladiator flange handle, lever, gray/chrome, external front mount, 2-position, lockable in OFF only, defeatable, NEMA 3/3R/4. Operating mechanism included.	<u>PDF</u>
<u>GCBX5-FHC-N4X-M</u>	\$485.00	Gladiator flange handle, lever, chrome, external front mount, 2-position, lockable in OFF only, defeatable, NEMA 3/4/4X. Operating mechanism included.	<u>PDF</u>
<u>GCBX5-CBL-60</u>	\$102.00	Gladiator cable assembly, 60in [1.52 m]	<u>PDF</u>

[GCBX5-ALM](#)[GCBX5-SHT-24VDC](#)[GCBX5-UVT-24VDC](#)

Gladiator MCCB GCB1200 3-Pole (1200A) Rotary Handles and Shafts			
Part Number	Price	Description	Dimensional Drawing
<u>GCBX5-EHR-N12-GY</u>	\$209.00	Gladiator rotary handle, tee, gray, external front mount, 2-position, lockable in ON-OFF, defeatable, NEMA 1/12. Operating mechanism included.	<u>PDF</u>
<u>GCBX5-EHR-N3R4-BK</u>	\$225.00	Gladiator rotary handle, tee, black, external front mount, 2-position, lockable in ON-OFF, defeatable, NEMA 3/3R/4. Operating mechanism included.	<u>PDF</u>
<u>GCBX5-EHR-N4X-BK</u>	\$247.00	Gladiator rotary handle, tee, black, external front mount, 2-position, lockable in ON-OFF, defeatable, NEMA 3/4/4X. Operating mechanism included.	<u>PDF</u>
<u>GCBX5-SFT-12</u>	\$33.00	Gladiator shaft, 12in [0.30 m] length.	<u>PDF</u>
<u>GCBX5-SFT-16</u>	\$35.00	Gladiator shaft, 16in [0.41 m] length.	<u>PDF</u>
<u>GCBX5-SFT-24</u>	\$52.00	Gladiator shaft, 24in [0.61 m] length.	<u>PDF</u>

[GCBX5-EHR-N12-GY](#)[GCBX5-PBR-STD](#)[GCBX5-CBL-60](#)[GCBX5-LCK-PL](#)[GCBX5-FHC-N3R4-M](#)

Trip Unit Replacement Battery

Gladiator Trip Unit Replacement Battery			
Part Number	Price	Description	Drawing
<u>GCBX5-BATT</u>	\$22.00	Gladiator trip unit replacement battery, for use with GCB800 and GCB1200 molded case circuit breakers.	NA

[GCBX5-BATT](#)[GCBX5-SFT-12](#)

Gladiator MCCB Derating Tables (80% Rating)

Gladiator MCCB GCB100 (15-100 A)								
Temperature	50°F [10°C]	68°F [20°C]	77°F [25°C]	86°F [30°C]	104°F [40°C]	122°F [50°C]	140°F [60°C]	158°F [70°C]
Rating (A)	Modification of Current (A)							
15	13.1	12.7	12.5	12.4	12.0	11.2	10.3	9.5
20	17.4	17.0	16.7	16.5	16.0	14.9	13.8	12.6
25	21.8	21.2	20.9	20.6	20.0	18.6	17.2	15.8
30	26.2	25.4	25.1	24.7	24.0	22.3	20.6	19.0
35	30.5	29.7	29.3	28.8	28.0	26.0	24.1	22.1
40	34.9	33.9	33.4	33.0	32.0	29.8	27.5	25.3
45	39.2	38.2	37.6	37.1	36.0	33.5	31.0	28.4
50	43.6	42.4	41.8	41.2	40.0	37.2	34.4	31.6
60	52.3	50.9	50.2	49.4	48.0	44.6	41.3	37.9
70	61.0	59.4	58.5	57.7	56.0	52.1	48.2	44.2
80	69.8	67.8	66.9	65.9	64.0	59.5	55.0	50.6
90	78.5	76.3	75.2	74.2	72.0	67.0	61.9	56.9
100	87.2	84.8	83.6	82.4	80.0	74.4	68.8	63.2

Gladiator MCCB GCB150 (40-150 A)								
Temperature	50°F [10°C]	68°F [20°C]	77°F [25°C]	86°F [30°C]	104°F [40°C]	122°F [50°C]	140°F [60°C]	158°F [70°C]
Rating (A)	Modification of Current (A)							
40	36.8	35.2	34.4	33.6	32.0	30.1	28.2	26.2
50	46.0	44.0	43.0	42.0	40.0	37.6	35.2	32.8
60	55.2	52.8	51.6	50.4	48.0	45.1	42.2	39.4
70	64.4	61.6	60.2	58.8	56.0	52.6	49.3	45.9
80	73.6	70.4	68.8	67.2	64.0	60.2	56.3	52.5
90	82.8	79.2	77.4	75.6	72.0	67.7	63.4	59.0
100	92.0	88.0	86.0	84.0	80.0	75.2	70.4	65.6
110	101.2	96.8	94.6	92.4	88.0	82.7	77.4	72.2
125	115.0	110.0	107.5	105.0	100.0	94.0	88.0	82.0
150	138.0	132.0	129.0	126.0	120.0	112.8	105.6	98.4

Gladiator MCCB GCB250 (150-250 A)								
Temperature	50°F [10°C]	68°F [20°C]	77°F [25°C]	86°F [30°C]	104°F [40°C]	122°F [50°C]	140°F [60°C]	158°F [70°C]
Rating (A)	Modification of Current (A)							
150	138.0	132.0	129.0	126.0	120.0	106.8	93.6	80.4
160	147.2	140.8	137.6	134.4	128.0	113.9	99.8	85.8
175	161.0	154.0	150.5	147.0	140.0	124.6	109.2	93.8
200	184.0	176.0	172.0	168.0	160.0	142.4	124.8	107.2
225	207.0	198.0	193.5	189.0	180.0	160.2	140.4	120.6
250	230.0	220.0	215.0	210.0	200.0	178.0	156.0	134.0


Gladiator MCCB GCB400 (250-400 A)								
Temperature	50°F [10°C]	68°F [20°C]	77°F [25°C]	86°F [30°C]	104°F [40°C]	122°F [50°C]	140°F [60°C]	158°F [70°C]
Rating (A)	Modification of Current (A)							
250	218.0	212.0	209.0	206.0	200.0	172.0	144.0	116.0
300	261.6	254.4	250.8	247.2	240.0	206.4	172.8	139.2
350	305.2	296.8	292.6	288.4	280.0	240.8	201.6	162.4
400	348.8	339.2	334.4	329.6	320.0	275.2	230.4	185.6

Gladiator MCCB GCB600 (500-600 A)								
Temperature	50°F [10°C]	68°F [20°C]	77°F [25°C]	86°F [30°C]	104°F [40°C]	122°F [50°C]	140°F [60°C]	158°F [70°C]
Rating (A)	Modification of Current (A)							
500	436.0	424.0	418.0	412.0	400.0	344.0	288.0	232.0
600	523.2	508.8	501.6	494.4	480.0	412.8	345.6	278.4

Circuit Diagrams For DC Applications


250VDC, 2P in Series

Suitable for use on ungrounded systems, or grounded systems that have one end of load(A) connected to grounded terminal, opposite poles in series connection.



A. Grounded System


Suitable for use on ungrounded systems only



B. Ungrounded System


500VDC or 600VDC, 3P in Series

Suitable for use on ungrounded systems, or grounded systems that have one end of load(A) connected to grounded terminal, opposite poles in series connection.



A. Grounded System

Suitable for use on ungrounded systems only



B. Ungrounded System

Ambient Air Temperature Considerations


Operation	-20 to 70°C [-4 to 158°F]
Storage	-40 to 70°C [-40 to 158°F]

NOTE: MCCB can be used without derating up to -20°C [-4°F]. However, if the ambient temperature exceeds 40°C [104°F], then the rated current must be derated.

NOTE: GCB800 and GCB1200 models have an electronic trip unit, so derating is not necessary.

Gladiator MCCB Mechanical Lugs



Gladiator MCCB circuit breakers come standard with mechanical line and load side lugs. All lugs are UL/cUL Listed Certified for their proper application and marked for use with aluminum and copper (Al/Cu) or copper only (Cu) conductors. Lugs suitable for copper and aluminum conductors are made of tin-plated aluminum. Mechanical lugs are sold factory-installed only. Lugs are rated for 60/75°C [140/167°F] wire.



- Lug type (catalog number)
- Cable size
- Standard mark

Mechanical Lug Kits For GCB100 Circuit Breakers

Lug Type	Terminal Body Material	Wire Type	Breaker Amp Range (A)	Wire (AWG)	Torque (N•m [lb•in])
100TE-L	Aluminum	Cu	15	14-10	3.6 [31.9]
			20		
			25		
			30		
100TE	Aluminum	Cu	40	8	4.5 [39.8]
		Cu	50	14-10	3.6 [31.9]
			60		
			70		
			80		
		Cu/Al	90	6-3	5.4 [47.8]
			100		
		Al		2-1	6.3 [55.8]
		Al		1/0	6.3 [55.8]



Mechanical Lug Kits For GCB150 Circuit Breakers

Lug Type	Terminal Body Material	Wire Type	Breaker Amp Range (A)	Wire (AWG)	Torque (N•m [lb•in])
150TS	Aluminum	Cu	1.6-15	14	4.1 [36.2]
			20-30	12-10	5.4 [47.8]
			40-175	8-2/0	15.1 [133.6]
		Al	50-70	6-3	5.4 [47.8]
			90-150	2-3/0	15.7 [138.6]



Mechanical Lug Kits For GCB250 Circuit Breakers

Lug Type	Terminal Body Material	Wire Type	Breaker Amp Range (A)	Wire (AWG)	Torque (N • m [lb • in])
250TS	Aluminum	Cu	150-175	1/0-2/0	32 [283.2]
		Cu/Al Cu/Al	150-175	3/0-4/0	
			200-225		
		Cu/Al	200-225	250-300 kcmil	44 [389.4]
			250 (Cu)		
		Al	250	350 kcmil	




Mechanical Lug Kits For GCB400 Circuit Breakers

Lug Type	Terminal Body Material	Wire Type	Breaker Amp Range (A)	Wire (AWG)	Torque (N•m [lb•in])
400TS	Aluminum	Cu/Al	250	1/0 AWG - 300kcmil	40.5 [358.5]
			300	350-600 kcmil	
		Al	350	700-750 kcmil	54 [478]
			400		



Mechanical Lug Kits For GCB600 Circuit Breakers


Lug Type	Terminal Body Material	Wire Type	Breaker Amp Range (A)	Wire (AWG)	Torque (N•m [lb•in])
600TS	Aluminum	Cu	500	2/0 - 350kcmil	40.5 [358.5]
			600	3/0 - 500kcmil	
		Al*			40.5 [358.5]



* Compact wire only (400-500 kcmil)

Mechanical Lug Kits For GCB800 Circuit Breakers


Lug Type	Terminal Body Material	Wire Type	Breaker Amp Range (A)	Wire (AWG)	Torque (N•m [lb•in])
800TS	Aluminum	Cu	400	3/0 - 300kcmil	45 [398.3]
			600		
		Al*	630	3/0 - 400kcmil	45 [398.3]
			800		



* Compact wire only (350-400 kcmil)

Mechanical Lug Kits For GCB1200 Circuit Breakers


Lug Type	Terminal Body Material	Wire Type	Breaker Amp Range (A)	Wire (AWG)	Torque (N•m [lb•in])
1200TS	Aluminum	Cu	800	3/0 - 350kcmil	45 [398.3]
			1000		
		Al*	1200	3/0 - 500kcmil	45 [398.3]







* Compact wire only (400-500 kcmil)

Gladiator MCCB Internal Accessories

Field-installable accessories provide flexibility for installation at the point of use. Auxiliary switches, alarm switches, shunt trip, and undervoltage release accessories are easy to install, reliable, and common to all Gladiator molded case circuit breakers. The internal accessories comply with requirements of Underwriters Laboratories® Inc. UL 489 Standards.



- Auxiliary Switch (AX)
- Alarm Switch (AL)
- Undervoltage trip (UVT) or Shunt Trip (SHT)


Gladiator MCCB Internal Accessories				
Frame	Internal Accessories Locations	Type	Left (R)	Right (T)
GCB100	<p>* 2P : Right only</p>  <ul style="list-style-type: none"> • AX or AL or AX+AL • UVT or SHT or AX or AL or AX+AL 	AX	1*	1*
		AL	1*	1*
		AX+AL	1*	1*
		SHT	–	1*
		UVT	–	1*
GCB150 GCB250	 <ul style="list-style-type: none"> • AX • AX • AL • UVT or SHT 	AX	1	1
		AL	1	–
		SHT	1*	–
		UVT	1*	–
GCB400 GCB600	 <ul style="list-style-type: none"> • AX • AL • UVT or SHT 	AX	3	–
		AL	–	1
		SHT	1*	–
		UVT	1*	–
GCB800 GCB1200	 <ul style="list-style-type: none"> • AX • AL • UVT or SHT 	AX	–	3
		AL	–	1
		SHT	–	1*
		UVT	–	1*

* Only one part can be installed in a designated place.


Gladiator MCCB Internal Accessories

Electrical accessories are fitted with numbered terminal blocks for wires. Auxiliary circuit wiring exits fixed mounted devices through a knock-out in the front cover. The internal accessories comply with requirements of Underwriters Laboratories® Inc.


UL 489 Standards




GCB100



GCB150 / 250



GCB400 / 600



GCB800 / 1200



GCBX1-AUX-LT



GCBX4-AUX



GCBX4-ALM



GCBX5-ALM

Auxiliary Switch (AX) and Alarm Switch (AL)

Auxiliary switches provide remote information of the circuit breaker status and can be used for indications, electrical locking, relays, etc. Includes both an Auxiliary switch (AX) and an Alarm Switch (AL). See definitions of each below.

Auxiliary Switch (AX)

Indicates the position of the circuit breaker contacts (Open/Closed Auxiliary switch is for applications requiring remote "ON" and "OFF" indication). Each switch contains two contacts having a common connection. One is open and the other closed when the circuit breaker is open, and vice-versa.






Gladiator MCCB Auxiliary Switch AX Connections

AX	Frame	Wire Size	On	Off / Trip
	GCB100	24 AWG (0.2 mm ²)		
	GCB150 GCB250 GCB400 GCB600	20 AWG (0.52 mm ²)		
	GCB800 GCB1200	19-16 AWG (0.65 - 1.31 mm ²)		

Gladiator MCCB Internal Accessories

Alarm Switch (AL)

Alarm switches indicate that the circuit breaker has tripped due to an overload, short circuit, shunt trip, undervoltage trip, or the “push-to-trip” button. They are particularly useful in automated plants where operators must be signaled about changes in the electrical distribution system. This switch features a closed contact when the circuit breaker is tripped automatically. In other words, this switch does not function when the breaker is operated manually. Its contact is open when the circuit breaker is reset.

Gladiator MCCB Alarm Switch (AL) Connections				
AL	Frame	Wire Size	On / Off	Trip
	GCB100	24 AWG (0.2 mm ²) 75°C [167°F]		
	GCB150 GCB250 GCB400 GCB600	26 AWG (0.13 mm ²) 75°C [167°F]		
	GCB800 GCB1200	19-16 AWG (0.65 - 1.31 mm ²) 90°C [194°F]		

UL Technical Specs				
Part Number	UL Max. Voltage	Frequency (Hz)	UL Max Current (DC)	UL Max Current (AC)
GCBX1-AUX-LT	250V	60	0.2 A	3A (resistive load) / 2A (inductive load)
GCBX1-AUX-RT				
GCBX1-ALX-LT				
GCBX1-ALX-RT				
GCBX4-AUX				
GCBX4-ALM				
GCBX5-AUX				
GCBX5-ALM				

Trip Unit Replacement Battery

Gladiator Trip Unit Replacement Battery			
Part Number	Price	Description	Drawing
GCBX5-BATT	\$22.00	Gladiator trip unit replacement battery, for use with GCB800 and GCB1200 molded case circuit breakers.	NA



[GCBX5-BATT](#)

Gladiator Trip Unit Replacement Battery	
Nominal Capacity (at 1mA, 20°C [68°F], 2.0 V cut-off)	1.2 Ah
Nominal Voltage	3.6 V
Maximum Recommended Continuous Current	30mA
Maximum Pulse Current Capability	60mA
Operating Temperature Range	-55 to +85°C [-67 to 185°F]
Lithium Metal Content	Approx. 0.3 g
Weight	9g [0.32 oz]
Volume	4.3 cm ³

Note: Maximum Pulse Capability reading over 3.0 V at 60mA: 0.1 sec every 2 min at 20°C [68°F], 10uA/cm² base current with fresh batteries. The pulse capability can be different depending on the cell status and environment. For maximum pulse coverage, capacitor support is recommended.

Gladiator MCCB Internal Accessories

Shunt Trip (SHT) and Undervoltage Trip (UVT) Switches

A voltage release can be used to trip the circuit breaker via a control signal.

Shunt Trip (SHT)

The shunt trip opens the mechanism in response to an externally applied voltage signal. The releases include coil clearing contacts that automatically clear the signal circuit when the mechanism has tripped.

Gladiator MCCB GCB100 SHT Technical Specifications				
Control Voltage U_e		Power Consumption		
		AC (VA)	DC (W)	mA
Voltage	AC/DC 12V	0.35	0.36	30
	AC/DC 24V	0.64	0.65	27
	AC/DC 48V	1.09	1.1	23
	AC/DC 60V	1.2	1.22	20
	AC/DC 100-130V	0.73	0.75	5.8
	AC/DC 200-250V	1.21	1.35	5.4
	AC 380-450V	1.67	—	3.8
	AC 440-500V	1.68	—	3.5
Maximum Opening Time		50ms maximum		
Terminal Screw Tightening Torque		7.12 lb•in [0.8 N•m]		
Operating Voltage Range		AC : 0.7-1.1 (rated voltage), DC : 0.8-1.1 (rated voltage)		
Frequency		45Hz - 65 Hz (AC only)		
Wire Size		20 AWG (0.52 mm ²)		



Gladiator MCCB GCB150/250/400/600 SHT Technical Specifications				
Control Voltage U_e		Power Consumption		
		AC (VA)	DC (W)	mA
Voltage	DC 12V	—	0.36	30
	AC/DC 24V	0.58	0.58	24
	AC/DC 48V	1.22	1.23	25
	AC/DC 100-130V	1.36	1.37	10.5
	AC 220-240 V	1.8	1.88	7.5
	DC 250V	—	—	—
	AC 380-500 V	1.15	—	2.3
Maximum Opening Time		50ms maximum		
Terminal Screw Tightening Torque		7.12 lb•in [0.8 N•m]		
Operating Voltage Range		AC : 0.7-1.1 (rated voltage), DC : 0.8-1.1 (rated voltage)		
Frequency		45Hz - 65 Hz (AC only)		
Wire Size		20 AWG (0.52 mm ²)		



Gladiator MCCB GCB800/1200 SHT Technical Specifications				
Control Voltage U_e		Operating Voltage Range	Power Consumption (VA or W)	
			Inrush	Steady-State
Voltage	DC 24-30 V	0.6 - 1.1 V_n	200	5
	AC 48V DC 48-60 V	0.6 - 1.1 V_n		
	AC/DC 100-130 V	0.56 - 1.1 V_n		
	AC/DC 200-250 V	0.56 - 1.1 V_n		
	AC 380-480V	0.56 - 1.1 V_n		
Maximum Opening Time		40ms maximum		
Frequency		45Hz - 65 Hz (AC only)		
Wire Size		16 AWG (1.31mm ²) – 14 AWG (2.08mm ²)		



Gladiator MCCB Internal Accessories

Undervoltage Trip (UVT)

The undervoltage release automatically opens a circuit breaker when voltage drops to a value less than the line voltage. The operation is instantaneous, and after tripping, the circuit breaker cannot be re-closed again until the voltage returns to a recover value of line voltage. Continuously energized, the undervoltage release must be operating before the circuit breaker can be closed.

Gladiator MCCB GCB100 UVT Technical Specifications

Control Voltage U_e		Power Consumption		
		AC (VA)	DC (W)	mA
Voltage	AC/DC 24V	0.64	0.65	27
	AC/DC 48V	1.09	1.1	23
	AC/DC 100-110 V	0.73	0.75	5.8
	AC/DC 200-220 V	1.21	1.35	5.4
	AC 380-440 V	1.67	—	3.8
	AC 440-480 V	1.68	—	3.5
Maximum Opening Time		50ms maximum		
Terminal Screw Tightening Torque		7.12 lb•in [0.8 N•m]		
Operating Voltage Range	Trip	0.2 - 0.7 (rated voltage)		
	Reset/Closing	≥ 0.85 (rated voltage)		
Frequency		45Hz - 65 Hz (AC only)		
Wire Size		20 AWG (0.52 mm ²)		



Gladiator MCCB GCB150/250/400/600 UVT Technical Specifications

Control Voltage U_e		Power Consumption		
		AC (VA)	DC (W)	mA
Voltage	AC/DC 24V	0.64	0.65	27
	AC/DC 48V	1.09	1.1	23
	AC/DC 110-130 V	0.73	0.75	5.8
	AC 220-240 V DC 250V	1.21	1.35	5.4
	AC 380-440 V	1.67	—	3.8
	AC 440-480 V	1.68	—	3.5
Maximum Opening Time		50ms maximum		
Terminal Screw Tightening Torque		7.12 lb•in [0.8 N•m]		
Operating Voltage Range	Trip	0.35 - 0.7 (rated voltage)		
	Reset/Closing	≥ 0.85 (rated voltage)		
Frequency		45Hz - 65 Hz (AC only)		
Wire Size		20 AWG (0.52 mm ²)		



Gladiator MCCB GCB800/1200 UVT Technical Specifications

Control Voltage U_e		Power Consumption (VA or W)		
		Inrush	Steady-State	Maximum Opening Time
Voltage	DC 24-30 V	200	5	50ms
	AC 48V DC 48-60 V			
	AC/DC 100-130 V			
	AC/DC 200-250 V			
	AC 380-480 V			
Operating Voltage Range	Trip	0.44-0.6 (rated voltage)		
	Reset/Closing	0.65-0.85 (rated voltage)		
Frequency		45Hz - 65 Hz (AC only)		
Wire Size		16 AWG (1.31 mm ²) - 14 AWG (2.08 mm ²)		




Gladiator MCCB Locking Systems Overview

Padlocking Device

A padlocking device is available for GCB100 to GCB1200 circuit breakers. The locking device is designed to be easily attached to the circuit breaker. This device allows the handle to be locked in the "OFF" position. A maximum of three (3) padlocks with shackle diameters of 0.19 to 0.31 in (5 to 8mm) may be used. Padlocks are not included.


Gladiator MCCB Padlocking Device Technical Specifications		
Description	Use With	Function
<u>GCBX1-LCK-PL</u>	GCB100	Lock in "OFF" position
<u>GCBX2-LCK-PL</u>	GCB150/250	
<u>GCBX3-LCK-PL</u>	GCB400/600	
<u>GCBX5-LCK-PL</u>	GCB800/1200	




Insulation Barrier

These barriers are insulated between the phases for an increased insulation level. The barriers can be easily installed, even on breakers that are already mounted, by inserting them into the corresponding slots. They are incompatible with the insulating terminal covers. It is possible to mount the phase separating partitions between two side-by-side circuit breakers.

Gladiator MCCB Insulation Barrier Technical Specifications		
Description	Use With	Poles
<u>GCBX2-PBR-STD</u>	GCB150/250	3P
<u>GCBX3-PBR-STD</u>	GCB400/600	3P
<u>GCBX5-PBR-STD</u>	GCB800/1200	3P



Standard Type



Standard Type GCBX5-PBR-STD

Gladiator MCCB Door-Mounted Rotary Handles

NEMA Door-Mounted Rotary Handles

The extended rotary operating handle consists of the following:

- A mounting plate that provides a rotary actuator for a standard toggle circuit breaker
- Handle assemblies available for NEMA Type 1, 12, 3, 3R, 4, 4X
- Available in standard or long (12-24 in) handle assemblies

The door mounted operating handle makes it possible to operate circuit breakers installed in enclosure from the front.

- Indication of three positions: I (ON), Tripped and O (OFF): NEMA Type 1, 12
- Provides ON (I) and OFF (O) indication : NEMA Type 3, 3R, 4, 4X
- The circuit breaker may be locked in either the ON or OFF position

Models

- Standard with dark gray handle (NEMA Type 1, 12)
- Outdoor with black handle (NEMA Type 3, 3R, 4, 4X)
- Field-installable (secured by screws)

GCB100	GCB150/250	GCB400/600	GCB800/1200
GCBX1-EHR-N12-GY	GCBX2-EHR-N12-GY	GCBX3-EHR-N12-GY	GCBX5-EHR-N12-GY
GCBX1-EHR-N3R4-BK	GCBX2-EHR-N3R4-BK	GCBX3-EHR-N3R4-BK	GCBX5-EHR-N3R4-BK
GCBX1-EHR-N4X-BK	GCBX2-EHR-N4X-BK	GCBX3-EHR-N4X-BK	GCBX5-EHR-N4X-BK


The shaft length is the distance between the back of the circuit breaker and door:

- Minimum mounting depth is 5.51 in [140mm] in GCB100
- Minimum shaft length is 12 in. [305mm] with long shaft
- Minimum shaft length is 24 in. [600mm] with long shaft
- Extended shaft length must be adjusted

Note: Rotary handles (EHR) include external operating handle and internal operating mechanism. Shafts (SFT) are sold separately.

Standards

- The door-mounted rotary operating handle is UL Listed under file E509077
- Degree of protection NEMA Type 1, 12, 3, 3R, 4, 4X




Door-Mounted Rotary Operating Handle

[GCBX2-EHR-N12-GY](#)
[GCBX2-EHR-N3R4-BK](#)
[GCBX2-EHR-N4X-BK](#)

[GCBX3-EHR-N12-GY](#)
[GCBX3-EHR-N3R4-BK](#)
[GCBX3-EHR-N4X-BK](#)

[GCBX5-EHR-N12-GY](#)
[GCBX5-EHR-N3R4-BK](#)
[GCBX5-EHR-N4X-BK](#)



Door-Mounted Rotary Operating Handle

[GCBX1-EHR-N12-GY](#)
[GCBX1-EHR-N3R4-BK](#)
[GCBX1-EHR-N4X-BK](#)

Gladiator MCCB Flange Handles With Sliding Operating Mechanism

Flange Handle With Sliding Operating Mechanism

Flange handle with sliding operating mechanism is for use with a cable assembly.

The cable operator maintains:

- Suitability for isolation
- Indication of two positions: O (OFF) and I (ON)
- The circuit breaker can be locked in the off position by one to three padlocks
- Door can be locked closed due to interlocking features of the handle operator

Handle is mounted on flange of enclosure using specified mounting dimensions while circuit breaker and operating mechanism are mounted to inside of enclosure using screws.

- Handles are available in NEMA Type 1, 12, 3, 3R, 4 and NEMA Type 4, 4x
- All circuit breaker operating mechanisms are suitable for right-hand flange mounting on the job

Models

- Standard with painted handle (NEMA Type 1, 12, 3, 3R, 4)
- Outdoor with nickel-plated handle (NEMA Type 4, 4X)
- Field installable (secured by screws)

GCB100	GCB150/250	GCB400/600	GCB800/1200
-	GCBX2-FHC-N3R4-M GCBX2-FHC-N4X-M	GCBX3-FHC-N3R4-M GCBX3-FHC-N4X-M	-

Standard type handle (NEMA Type 1, 12, 3, 3R, 4) with sliding mechanism and without cable


Outdoor type handle (NEMA Type 4, 4X) with sliding mechanism and without cable

- Cable lengths available in 36in to 60in

Note: Flange handles (FHC) include external operating handle and internal operating mechanism. Cables (CBL) are sold separately.


Standards

- Flange cable operating handle is UL Listed under file E509077
- Degree of protection NEMA Type 1, 12, 3, 3R, 4, 4X



Flange Handle With Sliding Operating Mechanism

[GCBX2-FHC-N3R4-M](#)
[GCBX2-FHC-N4X-M](#)



Flange Handle With Sliding Operating Mechanism

[GCBX3-FHC-N3R4-M](#)
[GCBX3-FHC-N4X-M](#)

Gladiator MCCB Flange Handles With Flange-Mounted Cable Operating Mechanism

Flange-Mounted Cable Operating Mechanism

Flange-mounted handle cable operating mechanism is for use with FH or COM Type handle operators especially designed for tall, deep enclosures where placement flexibility is required.

The cable operator maintains:

- Suitability for isolation
- Indication of two positions: O (OFF) and I (ON)
- The circuit breaker may be locked in the off position by one to three padlocks
- Door can be locked closed due to interlocking features of the handle operator

Handle is mounted on flange of enclosure using specified mounting dimensions while circuit breaker and operating mechanism are mounted to inside of enclosure using screws.

- Handles are available in COM and FHU NEMA Type 1,12, 3, 3R, 4 and FHX NEMA Type 4, 4x
- All circuit breaker operating mechanisms are suitable for right-hand flange mounting on the job.

Models

- Standard with painted handle (NEMA Type 1,12, 3, 3R, 4): FHU
- Outdoor with nickel-plated handle (NEMA Type 4, 4X): FHX
- Field installable (secured by screws)


GCB100	GCB150/250	GCB400/600	GCB800/1200
GCBX1-FHC-N3R4-M GCBX1-FHC-N4X-M	GCBX1-FHC-N3R4-M GCBX1-FHC-N4X-M	GCBX5-FHC-N3R4-M GCBX5-FHC-N4X-M	GCBX5-FHC-N3R4-M GCBX5-FHC-N4X-M

Cable Length (in [m])	GCB100/150/250	GCB400/600	GCB800/1200
36 [0.91]	GCBX2-CBL-36	GCBX3-CBL-36	—
60 [1.52]	GCBX2-CBL-60	GCBX3-CBL-60	GCBX5-CBL-60

Note: Flange handles (FHC) include external operating handle and internal operating mechanism. Cables (CBL) are sold separately.


Standards

- Flange cable operating handle is UL Listed under file E509077
- NEMA Type 1, 12, 3, 3R, 4, 4X



**Flange Handle
With Cable Operating Mechanism**

[GCBX1-FHC-N3R4-M](#)
[GCBX1-FHC-N4X-M](#)



**Handle With Cable
and Cable Operating Mechanism**

[GCBX5-FHC-N3R4-M](#)
[GCBX5-FHC-N4X-M](#)

Cable




[GCBX2-CBL-36](#)
[GCBX2-CBL-60](#)
[GCBX3-CBL-36](#)
[GCBX3-CBL-60](#)
[GCBX5-CBL-60](#)

Gladiator MCCB Characteristic Curves

GCB100 (FTU – Fixed Trip Units)

All time/current characteristic curve data is based on 40°C ambient cold start.




Rating	FTU	
	2P/3P	Mag Trip (80% - 130%) (A)
15	✓ / ✓	400
20	✓ / ✓	
25	✓ / ✓	
30	✓ / ✓	
35	✓ / ✓	
40	✓ / ✓	800
45	✓ / ✓	
50	✓ / ✓	
60	✓ / ✓	
70	✓ / ✓	
80	✓ / ✓	1000
90	✓ / ✓	
100	✓ / ✓	

Gladiator MCCB Characteristic Curves

GCB150 (FTU – Fixed Trip Units)

All time/current characteristic curve data is based on 40°C ambient cold start.




Rating	FTU	
	2P/3P	Mag Trip (80% - 130%) (A)
40	✓ / ✓	500
50	✓ / ✓	
60	✓ / ✓	800
70	✓ / ✓	
80	✓ / ✓	1000
90	✓ / ✓	
100	✓ / ✓	1250
125	✓ / ✓	1500
150	✓ / ✓	

Gladiator MCCB Characteristic Curves

GCB250 (FTU – Fixed Trip Units)

All time/current characteristic curve data is based on 40°C ambient cold start.




Rating	FTU	
	2P/3P	Mag Trip (80% - 130%) (A)
150	✓ / ✓	1500
175	✓ / ✓	1750
200	✓ / ✓	2000
225	✓ / ✓	2250
250	✓ / ✓	2500

Gladiator MCCB Characteristic Curves

GCB250 (ATU – Adjustable Trip Units)

All time/current characteristic curve data is based on 40°C ambient cold start.




Rating	ATU		
	2P/3P	Rating Range (A) ($0.8-1 \times I_n$)	Mag Trip (80% - 130%) (A) ($5-10 \times I_n$)
160	✓ / ✓	128-160	800-1600
200	✓ / ✓	160 - 200	1000-2000
250	✓ / ✓	200 - 250	1250-2500

Gladiator MCCB Characteristic Curves

GCB400 (FTU – Fixed Trip Units)

All time/current characteristic curve data is based on 40°C ambient cold start.




Rating	FTU	
	2P/3P	Mag Trip (80% - 130%) (A)
250	✓ / ✓	2500
300	✓ / ✓	3000
350	✓ / ✓	3500
400	✓ / ✓	4000

Gladiator MCCB Characteristic Curves

GCB400 (ATU – Adjustable Trip Units)

All time/current characteristic curve data is based on 40°C ambient cold start.




Rating	ATU		
	2P/3P	Rating Range (A) ($0.8-1 \times I_n$)	Mag Trip (80% - 130%) (A) ($5-10 \times I_n$)
300	✓ / ✓	240-300	1500-3000
400	✓ / ✓	320-400	2000-4000

Gladiator MCCB Characteristic Curves

GCB600 (FTU – Fixed Trip Units)

All time/current characteristic curve data is based on 40°C ambient cold start.




Rating	FTU	
	2P/3P	Mag Trip (80% - 130%) (A)
500	✓ / ✓	5000
600	✓ / ✓	6000

Gladiator MCCB Characteristic Curves

GCB600 (ATU – Adjustable Trip Units)

All time/current characteristic curve data is based on 40°C ambient cold start.





Rating	ATU		
	2P/3P	Rating Range (A) ($0.8 - 1 \times I_n$)	Mag Trip (80% - 130%) (A) ($5 - 10 \times I_n$)
500	✓ / ✓	400-500	2500-5000
600	✓ / ✓	480-600	3000-6000

Gladiator MCCB Characteristic Curves


GCB800/1200

Long-Time Delay (800-1200 A)

Long-time pickup $0.4-1 \times I_r$ and delay 0.5-20 s



①, ②, ③ – Long-time setting



Notes :

1. There is a thermal-imaging effect that can act to shorten the long-time delay. The thermal imaging effect comes into play if a current above the long-time delay pickup value exists for a time and then is cleared by the tripping of a downstream device or the circuit breaker itself. A subsequent overload will cause the circuit breaker to trip in a shorter time than normal. The amount of time delay reduction is inverse to the amount of time that has elapsed since the previous overload.



2. Total clearing times shown include the response times of the trip unit, the circuit breaker opening, and the extinction of the current.

Gladiator MCCB Characteristic Curves


GCB800/1200

Short-Time Delay (800-1200 A)

Short-time pickup $1.5-10 \times I_r$ and delay $0.1-0.4$ s



④, ⑤ – Short-time setting





Gladiator MCCB Characteristic Curves


GCB800/1200

Instantaneous and Ground Fault (800-1200 A)

Instantaneous pickup $2-15 \times I_n$ and Ground Fault pickup $0.2-1 \times I_n$ and delay $0.1-0.4$ s



⑥, ⑦, ⑧ - Instantaneous and Ground fault setting



3P Series Molded Case Circuit Breakers

Overview

Overview

Designed to provide branch and feeder circuit protection in industrial control panels, this line of Molded Case Circuit Breakers supplies protection against overload in conductors and short circuit in connected equipment such as motors. They are UL listed for installation in UL 508 control panels. Their small size, in relation to standard circuit breakers or other comparable devices, saves panel space. Four frame sizes and all standard accessories are available.

Features

- UL489 listed performance for branch circuit overcurrent protection and disconnecting means
- Patented contact conductor designs featuring high-speed "blow-open" action, providing superior performance when high level fault currents produce extra-ordinary electromechanical forces
- Advanced arc extinguishing technology
- Toggle handle provides three positions (on/off/tripped) along with visual indicators
- Manufactured in ISO 9000 certified facilities
- HACR (heating, air conditioning and refrigeration) rated
- G-Frame and F-Frame breakers are suitable for reverse feed
- K-Frame and L-Frame breakers include 3-pole adjustable magnetic trip.

Listings

- UL 489 MCCB, File: E7819
- Field-installed accessories: UL file E64983
- CSA 22.2 No.5, File: 43556
- IEC 157-1
- NEMA Standards Pub. No. AB1-1993



Manufactured by Eaton Corporation

Note: These parts available for sale to North American locations only.


Molded Case Circuit Breakers Technical Specifications

Circuit Breaker Type	Ampere Rating at 40°C	No. Poles	Volts		Type of Trip*	Federal Specification W-C-375b	UL 489 Interrupting Ratings (rms Symmetrical Amperes) (kA)			
			AC	DC			Volts AC (50/60 Hz)			Volts DC
							240	480	600	250**
G-Frame	15 -100	3	480	250	N.I.T.U	13b	65	22	–	10
F-Frame	60 - 225	3	600	250	N.I.T.U	22a	65	35	18	10
K-Frame	250 - 400	3	600	250	I.T.U	23a	65	35	25	10
L-Frame	400 - 600	3	600	250	I.T.U	23a	65	35	25	22

*Note: N.I.T.U denotes non-interchangeable trip unit. I.T.U denotes interchangeable trip unit.

**Note: For DC or 1-phase AC applications, use the two outside poles of the 3-pole circuit breaker

Molded Case Circuit Breakers Part Numbering System



3P Series Molded Case Circuit Breakers

15-100 Amp G-Frame



G3P-040



GHMVD12B



F0S03C



3TA100G6K



GDIN

G-Frame circuit breakers are available as a single unit, or with accessories pre-installed only. Accessories are not field installable on this frame size. G-Frame breakers are suitable for reverse feed use. All breakers include base mounting hardware for panel mount applications.

G-Frame Series Three Pole Molded Case Circuit Breakers

Part Number	Price	Description	Pre-Installed Accessories*	Ampere Rating	Voltage	Interrupt Capacity
G3P-015	\$428.00	Molded case circuit breaker with non-adjustable thermal magnetic trip; line and load lug terminals included.	None	15	240VAC 480VAC	65kA 22kA 10kA
G3P-015-AUX	\$509.00		With auxiliary contact, SPDT			
G3P-020	\$428.00	Molded case circuit breaker with non-adjustable thermal magnetic trip; line and load lug terminals included.	None	20		
G3P-020-AUX	\$509.00		With auxiliary contact, SPDT			
G3P-025	\$428.00	Molded case circuit breaker with non-adjustable thermal magnetic trip; line and load lug terminals included.	None	25		
G3P-030	\$428.00		None			
G3P-030-AUX	\$509.00	Molded case circuit breaker with non-adjustable thermal magnetic trip; line and load lug terminals included.	With auxiliary contact, SPDT	30		
G3P-030-STAC	\$509.00		With 120 VAC shunt trip			
G3P-030-STDC	\$509.00		With 24 VDC shunt trip			
G3P-030-UVAC	\$509.00		With 120 VAC undervoltage release			
G3P-040	\$428.00	Molded case circuit breaker with non-adjustable thermal magnetic trip; line and load lug terminals included.	None	40		
G3P-050	\$428.00		None	50		
G3P-060	\$428.00		None			
G3P-060-AUX	\$509.00	Molded case circuit breaker with non-adjustable thermal magnetic trip; line and load lug terminals included.	With auxiliary contact, SPDT	60		
G3P-060-STAC	\$509.00		With 120 VAC shunt trip			
G3P-060-STDC	\$509.00		With 24 VDC shunt trip			
G3P-060-UVAC	\$509.00		With 120 VAC undervoltage release			
G3P-070	\$428.00	Molded case circuit breaker with non-adjustable thermal magnetic trip; line and load lug terminals included.	None	70		
G3P-080	\$428.00		None	80		
G3P-090	\$428.00		None	90		
G3P-100	\$428.00	Molded case circuit breaker with non-adjustable thermal magnetic trip; line and load lug terminals included.	None	100		
G3P-100-AUX	\$509.00		With auxiliary contact, SPDT			
G3P-100-STAC	\$509.00		With 120 VAC shunt trip			
G3P-100-STDC	\$509.00		With 24 VDC shunt trip			
G3P-100-UVAC	\$509.00		With 120 VAC undervoltage release			

*Note: Available accessories are pre-installed on G-Frame and F-Frame Molded Case Circuit Breakers. They are not field installable or interchangeable. G-frame terminals are factory-installed only. No replacement terminals available.

** For DC or 1-phase AC applications, use the two outside poles of the 3-pole circuit breaker

G-Frame Accessory Selection Guide

Part Number	Price	Description
GHMVD06B	\$110.00	NEMA 1/12 rotary handle for G-Frame. Position indicating; lock-off feature. Shaft length: 6"
GHMVD12B	\$123.00	NEMA 1/12 rotary handle for G-Frame. Position indicating; lock-off feature. Shaft length: 12"
F0S03C	\$473.00	NEMA 1/12 flex shaft cable operator for G-Frame. Flange mounted. Lockable. Cable length: 3'
F0S06C	\$529.00	NEMA 1/12 flex shaft cable operator for G-Frame. Flange mounted. Lockable. Cable length: 6'
3TA100G6K	\$87.00	Multi-wire connector to allow 6 wires to be connected to the G-frame. UL for copper only. 14-6AWG. Package of 3
GDIN	\$15.00	DIN rail clip adapter to allow mounting of G-Frame unit on 35mm DIN rail. Pkg of 1 includes mounting hardware.

G-Frame Electrical Ratings

	Volts	Frequency	Amperes	Contact Arrangement
G-Frame Auxiliary Switch	240 VAC	50/60 Hz	6	1a/1b - SPDT
G-Frame Shunt Trip	120 VAC	50/60 Hz	1.1	
	24 VDC	DC	5.7	
G-Frame Undervoltage Release Mechanism	120 VAC	50/60 Hz	0.05	
	Dropout Voltage		Pickup Voltage	
	Min	Max	Max	
	38.5 VAC	77.0 VAC	93.5 VAC	


AWG Wire Range Specifications

Circuit Breaker	Ampere Rating	Wire Type	AWG Wire Range	Metric Wire Range mm ²
G-Frame	15 - 20	Cu/Al	14 - 10	2.5 - 4
	25 - 100		10 - 1/0	4 - 50

3P Series Molded Case Circuit Breakers

15-100 Amp G-Frame

Type G3P 15-100 Amperes 3 Pole



3P Series Molded Case Circuit Breakers

60-225 Amp F-Frame



F3P-200




FHMVD12B



F1S03C



3TA150F6K



3TA225FD

F-Frame circuit breakers are available as a single unit, or with accessories pre-installed only. Accessories are not field installable on this frame size.

This frame size is suitable for reverse feed use. All breakers include base mounting hardware for panel mount applications.

F-Frame Series Three Pole Molded Case Circuit Breakers

Part Number	Price	Description	Pre-Installed Accessories*	Ampere Rating	Voltage	Interrupt Capacity
F3P-060	\$943.00	Molded case circuit breaker with non-adjustable thermal magnetic trip; line and load lug terminals included.	None	60	240VAC 480VAC 600VAC 250VDC**	65kA 35kA 18kA 10kA
F3P-070	\$1,012.00		None	70		
F3P-080	\$1,012.00		None	80		
F3P-090	\$953.00		None	90		
F3P-100	\$1,012.00		None	100		
F3P-125	\$1,012.00		None	125		
F3P-150	\$1,012.00	Molded case circuit breaker with non-adjustable thermal magnetic trip; line and load lug terminals included.	None	150		
F3P-150-AUX	\$1,110.00		Auxiliary contact, SPDT			
F3P-150-STAC	\$1,110.00		120 VAC shunt trip			
F3P-150-STDC	\$1,110.00		24 VDC shunt trip			
F3P-150-UVAC	\$1,110.00		120 VAC undervoltage release			
F3P-175	\$1,012.00	Molded case circuit breaker with non-adjustable thermal magnetic trip; line and load lug terminals included.	None	175		
F3P-200	\$1,012.00	Molded case circuit breaker with non-adjustable thermal magnetic trip; line and load lug terminals included.	None	200		
F3P-200-AUX	\$1,110.00		Auxiliary contact, SPDT			
F3P-200-STAC	\$1,110.00		120 VAC shunt trip			
F3P-200-STDC	\$1,110.00		24 VDC shunt trip			
F3P-200-UVAC	\$1,110.00		120 VAC undervoltage release			
F3P-225	\$1,012.00	Molded case circuit breaker with non-adjustable thermal magnetic trip; line and load lug terminals included.	None	225		

*Note: Available accessories are pre-installed on G-Frame and F-Frame Molded Case Circuit Breakers. They are not field installable or interchangeable.

**Note: For DC or 1-phase AC applications, use the two outside poles of the 3-pole circuit breaker

F-Frame Accessory Selection Guide

Part Number	Price	Description
FHMVD12B	\$123.00	NEMA 1/12 rotary handle for F-frame. Position indicating. Lock-off feature. Shaft length: 12"
HM1R12X	\$173.00	NEMA 4/4X rotary handle for F-frame. Position indicating. Lock-off feature. Shaft length: 12"
HM1R24X	\$194.00	NEMA 4/4X rotary handle for F-frame. Position indicating. Lock-off feature. Shaft length: 24"
F1S03C	\$529.00	NEMA 1/12 flex shaft cable operator for F-frame. Flange mountable. Lockable. Cable length: 3'
F1S06C	\$573.00	NEMA 1/12 flex shaft cable operator for F-frame. Flange mountable. Lockable. Cable length: 6'
3TA150F6K	\$87.00	Multi-wire connector to allow 6 wires to be connected to the F-frame. UL for copper only. 14-6 AWG. Package of 3
3TA225FD	\$129.00	Replacement lug kit for F-frame. Package of 3

F-Frame Electrical Ratings ^{1,2}

	Max Volts	Frequency	Max Amperes	Dielectric Withstand Voltage	Notes
F-Frame Auxiliary Switch	125 VAC ³	50/60 Hz	1	2500	1. Endurance: 5000 electrical operations plus 4000 mechanical operations. 2. Pigtail wire size: 18 AWG (0.82 mm ²) 3. Minimum switching circuit capabilities of 100 micro-amperes and 15 VDC minimum. 4. Non-inductive load
	600 VAC	50/60 Hz	6		
	125 VDC	DC	0.50 ⁴		
	250 VDC	DC	0.25 ⁴		

F-Frame Shunt Trip	Supply Voltage	Min Operating Voltage	VA
	120 VAC	36 VAC	570
	24 VDC	9 VDC	400


F-Frame Undervoltage Release Mechanism	Supply Voltage	Dropout Voltage		Pickup Voltage	VA
		Min	Max	Maximum	
	120 VAC	44.5 VAC	77.0 VAC	93.5 VAC	1.5

AWG Wire Range Specifications

Circuit Breaker	Ampere Rating	Wire Type	AWG Wire Range	Metric Wire Range mm ²
F-Frame	60 - 100	Cu/Al	14 - 1/0	2.5 - 50
	125 - 225		4 - 4/0	25 - 95


3P Series Molded Case Circuit Breakers

70 Amp F-Frame




3P Series Molded Case Circuit Breakers

80 Amp F-Frame




3P Series Molded Case Circuit Breakers

90 Amp F-Frame




3P Series Molded Case Circuit Breakers

100 Amp F-Frame




3P Series Molded Case Circuit Breakers

125 Amp F-Frame




3P Series Molded Case Circuit Breakers

150 Amp F-Frame



3P Series Molded Case Circuit Breakers

175-225 Amp F-Frame



3P Series Molded Case Circuit Breakers

250-400 Amp K-Frame

K-Frame circuit breakers are available as individual components or in a kit. Breaker frame includes 3-pole adjustable magnetic trip. Available

accessories are field installable on this frame size. All breakers include base mounting hardware for panel mount applications.

K-Frame Series Three Pole Molded Case Circuit Breakers						
Part Number	Price	Description	Kits	Ampere Rating	Voltage	Interrupt Capacity
K3P-250	\$1,832.00	Molded case circuit breaker with adjustable thermal magnetic trip; line and load lug terminals included.	MCCB only	250	240VAC 480VAC 600VAC 250VDC	65kA 35kA 25kA 10kA*
K3P-250-AUX	\$2,110.00		Kit includes K3P-250 and A1X3PK			
K3P-250-STAC	\$2,068.00		Kit includes K3P-250 and SNT3P11K			
K3P-250-STDC	\$2,068.00		Kit includes K3P-250 and SNT3P04K			
K3P-250-UVAC	\$2,068.00		Kit includes K3P-250 and UVH3LP08K			
K3P-250-UVDC	\$2,068.00		Kit includes K3P-250 and UVH3LP21K			
K3P-300	\$1,832.00	Molded case circuit breaker with adjustable thermal magnetic trip; line and load lug terminals included.	MCCB only	300		
K3P-300-AUX	\$2,110.00		Kit includes K3P-300 and A1X3PK			
K3P-300-STAC	\$2,068.00		Kit includes K3P-300 and SNT3P11K			
K3P-300-STDC	\$2,068.00		Kit includes K3P-300 and SNT3P04K			
K3P-300-UVAC	\$2,068.00		Kit includes K3P-300 and UVH3LP08K			
K3P-300-UVDC	\$2,068.00		Kit includes K3P-300 and UVH3LP21K			
K3P-350	\$1,832.00	Molded case circuit breaker with adjustable thermal magnetic trip; line and load lug terminals included.	MCCB only	350		
K3P-350-AUX	\$2,110.00		Kit includes K3P-350 and A1X3PK			
K3P-350-STAC	\$2,068.00		Kit includes K3P-350 and SNT3P11K			
K3P-350-STDC	\$2,068.00		Kit includes K3P-350 and SNT3P04K			
K3P-350-UVAC	\$2,068.00		Kit includes K3P-350 and UVH3LP08K			
K3P-350-UVDC	\$2,068.00		Kit includes K3P-350 and UVH3LP21K			
K3P-400	\$1,832.00	Molded case circuit breaker with adjustable thermal magnetic trip; line and load lug terminals included.	MCCB only	400		
K3P-400-AUX	\$2,110.00		Kit includes K3P-400 and A1X3PK			
K3P-400-STAC	\$2,068.00		Kit includes K3P-400 and SNT3P11K			
K3P-400-STDC	\$2,068.00		Kit includes K3P-400 and SNT3P04K			
K3P-400-UVAC	\$2,068.00		Kit includes K3P-400 and UVH3LP08K			
K3P-400-UVDC	\$2,068.00		Kit includes K3P-400 and UVH3LP21K			

*Note: For DC or 1-phase AC applications, use the two outside poles of the 3-pole circuit breaker

K-Frame Accessory Selection Guide		
Part Number	Price	Description
KHMVD12B	\$175.00	NEMA 1/12 rotary handle for K-Frame. Position indicating. Lock-off feature. Shaft length: 12"
HM3R12X	\$212.00	NEMA 4/4X rotary handle for K-Frame. Position indicating. Lock-off feature. Shaft length: 12"
HM3R24X	\$237.00	NEMA 4/4X rotary handle for K-Frame. Position indicating. Lock-off feature. Shaft length: 24"
F3S03C	\$631.00	NEMA 1/12 flexible shaft cable operator for K-Frame. Flange Mounted. Lockable. Cable length: 3'
F3S06C	\$662.00	NEMA 1/12 flexible shaft cable operator for K-Frame. Flange Mounted. Lockable. Cable length: 6'
A1X3PK	\$310.00	Field installable auxiliary contact for K-Frame MCCB, SPDT, 18" pigtail leads
SNT3P11K	\$481.00	Field installable 110 - 240 VAC / 110 - 125 VDC shunt trip for K-Frame, 18" pigtail leads
SNT3P04K	\$481.00	Field installable 12/24 VDC / VAC shunt trip for K-Frame, 18" pigtail leads
3TA401K	\$135.00	Replacement lug kit for K-Frame. Package of 3
UVH3LP08K	\$481.00	Field installable 110 - 127 VAC undervoltage release for K-Frame, 18" pigtail leads
UVH3LP21K	\$481.00	Field installable 24 VDC undervoltage release for K-Frame, 18" pigtail leads

Note: See 3P Series Molded Case Circuit Breakers Accessories catalog pages for accessory electrical specifications.

AWG Wire Range Specifications				
Circuit Breaker	Ampere Rating	Wire Type	AWG Wire Range	Metric Wire Range mm ²
K-Frame	250 - 350	Cu/Al	250 - 500 (1)	120 - 240
	400		3/0 - 250 (2)	95 - 120




[K3P-400](#)



[KHMVD12B](#)




[F3S03C](#)




[A1X3PK](#)



[SNT3P04K](#)




[3TA401K](#)



[UVH3LP08K](#)

3P Series Molded Case Circuit Breakers

250-400 Amp K-Frame



3P Series Molded Case Circuit Breakers

400-600 Amp L-Frame

L-Frame circuit breakers are available as individual components or in a kit. Breaker frame includes 3-pole adjustable magnetic trip. Available accessories are field installable

on this frame size.

All breakers include base mounting hardware for panel mount applications.

L-Frame Series Three Pole Molded Case Circuit Breakers

Part Number	Price	Description	Kits	Ampere Rating	Voltage	Interrupt Capacity
L3P-400	\$2,519.00	Molded case circuit breaker with adjustable thermal magnetic trip; line and load lug terminals included.	MCCB only	400	240VAC 480VAC 600VAC 250VDC	65kA 35kA 25kA 22kA*
L3P-400-AUX	\$2,864.00		Kit includes L3P-400 and A1X4PK			
L3P-400-STAC	\$2,813.00		Kit includes L3P-400 and SNT4RP11K			
L3P-400-STDC	\$2,813.00		Kit includes L3P-400 and SNT4RP03K			
L3P-400-UVAC	\$2,813.00		Kit includes L3P-400 and UVH4LP08K			
L3P-400-UVDC	\$2,813.00		Kit includes L3P-400 and UVH4LP21K			
L3P-500	\$2,519.00	Molded case circuit breaker with adjustable thermal magnetic trip; line and load lug terminals included.	MCCB only	500		
L3P-500-AUX	\$2,864.00		Kit includes L3P-500 and A1X4PK			
L3P-500-STAC	\$2,813.00		Kit includes L3P-500 and SNT4RP11K			
L3P-500-STDC	\$2,813.00		Kit includes L3P-500 and SNT4RP03K			
L3P-500-UVAC	\$2,813.00		Kit includes L3P-500 and UVH4LP08K			
L3P-500-UVDC	\$2,813.00		Kit includes L3P-500 and UVH4LP21K			
L3P-600	\$2,519.00	Molded case circuit breaker with adjustable thermal magnetic trip; line and load lug terminals included.	MCCB only	600		
L3P-600-AUX	\$2,864.00		Kit includes L3P-600 and A1X4PK			
L3P-600-STAC	\$2,813.00		Kit includes L3P-600 and SNT4RP11K			
L3P-600-STDC	\$2,813.00		Kit includes L3P-600 and SNT4RP03K			
L3P-600-UVAC	\$2,813.00		Kit includes L3P-600 and UVH4LP08K			
L3P-600-UVDC	\$2,813.00		Kit includes L3P-600 and UVH4LP21K			

*Note: For DC or 1-phase AC applications, use the two outside poles of the 3-pole circuit breaker

L-Frame Accessory Selection Guide

Part Number	Price	Description
LHMVD12B	\$202.00	NEMA 1/12 rotary handle for L-Frame. Position indicating. Lock-off feature. Shaft length: 12"
HM4R12X	\$276.00	NEMA 4/4X rotary handle for L-Frame. Position indicating. Lock-off feature. Shaft length: 12"
HM4R24X	\$292.00	NEMA 4/4X rotary handle for L-Frame. Position indicating. Lock-off feature. Shaft length: 24"
F4S04C	\$721.00	NEMA 1/12 flex shaft cable operator for L-Frame. Flange mounted. Lockable. Cable length: 4'
F4S06C	\$829.00	NEMA 1/12 flex shaft cable operator for L-Frame. Flange mounted. Lockable. Cable length: 6'
A1X4PK	\$318.00	Field installable auxiliary contact for L-Frame MCCB, SPDT, 18" pigtail leads
SNT4RP11K	\$550.00	Field installable 110 - 240 VAC shunt trip for L-Frame, 18" pigtail leads
SNT4RP03K	\$550.00	Field installable 12/24 VDC / VAC shunt trip for L-Frame, 18" pigtail leads
3TA603LDK	\$166.00	Replacement lug kit for L-Frame. Rated 600A. Package of 3
UVH4LP08K	\$513.00	Field installable 110 - 127 VAC undervoltage release for L-Frame, 18" pigtail leads
UVH4LP21K	\$550.00	Field installable 24 VDC undervoltage release for L-Frame, 18" pigtail leads

Note: See 3P Series Molded Case Circuit Breakers Accessories catalog pages for accessory electrical specifications.

AWG Wire Range Specifications

Circuit Breaker	Ampere Rating	Wire Type	AWG Wire Range	Metric Wire Range mm ²
L-Frame	400	Cu/Al	3/0 - 350 (2)	95 - 150
	500		3/0 - 350 (2)	95 - 150
	600		400 - 500 (2)	185 - 240




[L3P-600](#)



[LHMVD12B](#)




[F4S04C](#)




[A1X4PK](#)



[SNT4RP03K](#)




[3TA603LDK](#)



[UVH4LP08K](#)

3P Series Molded Case Circuit Breakers

400-600 Amp L-Frame




3P Series Molded Case Circuit Breakers

Dimensions


Dimensions

mm [inches]

15 - 100 Amp G-Frame



60 - 225 Amp F-Frame




3P Series Molded Case Circuit Breakers

Dimensions


Dimensions

mm [inches]

250 - 400 Amp K-Frame



400 - 600 Amp L-Frame




3P Series Molded Case Circuit Breakers

Accessories


Field Mountable Accessories



GHMVD12B



HM1R12X



F0S03C

Rotary Handles

A rotary handle is available for each frame size of molded case circuit breaker.

The C-Series rotary handle (HM) is available for F, K, & L frame molded case breakers. These robust and durable handles include the following features:

- Suitable for use with NEMA 4/4X enclosures
- Handle, shaft, and mechanism made from all metal parts
- Large handle easily accommodates gloves
- Heavy Duty Metal locking hasp
- Door interlock and defeater
- Standard ON/OFF/Trip markings and a 45-degree rotation
- UL 489, CSA

The Universal rotary series handles (HMV) is available for G, F, K, & L frame molded case breakers. These handles include the following features:

- Suitable for use with NEMA 1/12 enclosures
- Composite Nylon handle with metal shaft, and mechanism
- Large handle easily accommodates gloves
- Access Handle Lock-Off by pressing arrow on handle insert
- Door interlock and defeater
- Global ON/OFF markings (I/ON, O/OFF) and TRIP indication on handle plus 90-degree rotation
- UL 489, IEC 947-1/-2, CSA

Rotary Handle Accessory Selection Guide

Part Number	Price	Description
GHMVD06B	\$110.00	NEMA 1/12 black rotary handle for G-Frame MCCB. Shaft length: 6in [152.4 mm]
GHMVD12B	\$123.00	NEMA 1/12 black rotary handle for G-Frame MCCB. Shaft length: 12in [304.8 mm]
FHMVD12B	\$123.00	NEMA 1/12 black rotary handle for F-Frame MCCB. Shaft length: 12in [304.8 mm]
HM1R12X	\$173.00	NEMA 4/4X black rotary handle for F-Frame MCCB. Shaft length: 12in [304.8 mm]
HM1R24X	\$194.00	NEMA 4/4X black rotary handle for F-Frame MCCB. Shaft length: 24in [609.6 mm]
KHMVD12B	\$175.00	NEMA 1/12 black rotary handle for K-Frame MCCB. Shaft length: 12in [304.8 mm]
HM3R12X	\$212.00	NEMA 4/4X black rotary handle for K-Frame MCCB. Shaft length: 12in [304.8 mm]
HM3R24X	\$237.00	NEMA 4/4X black rotary handle for K-Frame MCCB. Shaft length: 24in [609.6 mm]
LHMVD12B	\$202.00	NEMA 1/12 black rotary handle for L-Frame MCCB. Shaft length: 12in [304.8 mm]
HM4R12X	\$276.00	NEMA 4/4X black rotary handle for L-Frame MCCB. Shaft length: 12in [304.8 mm]
HM4R24X	\$292.00	NEMA 4/4X black rotary handle for L-Frame MCCB. Shaft length: 24in [609.6 mm]

Flex Shaft™ Flexible Handle

Meeting crucial time limits for shutdown procedures is easier with an externally mounted handle. The flexible handle makes it possible to operate the circuit breaker externally and can be used in enclosures of varying depths and heights. It can be used with NEMA 1, NEMA 3R and NEMA 12 enclosures, and it accepts up to three padlock shackles. Each item includes a painted steel handle, breaker operating mechanism, and cable.

Note: A minimum bending radius of four inches is necessary for proper operation.

Flex Shaft™ Flexible Handle Accessory Selection Guide

Part Number	Price	Description
F0S03C	\$473.00	NEMA 1/12 flex shaft cable operator for G-Frame MCCB. Cable length: 3ft [0.91 m]
F0S06C	\$529.00	NEMA 1/12 flex shaft cable operator for G-Frame MCCB. Cable length: 6ft [1.83 m]
F1S03C	\$529.00	NEMA 1/12 flex shaft cable operator for F-Frame MCCB. Cable length: 3ft [0.91 m]
F1S06C	\$573.00	NEMA 1/12 flex shaft cable operator for F-Frame MCCB. Cable length: 6ft [1.83 m]
F3S03C	\$631.00	NEMA 1/12 flex shaft cable operator for K-Frame MCCB. Cable length: 3ft [0.91 m]
F3S06C	\$662.00	NEMA 1/12 flex shaft cable operator for K-Frame MCCB. Cable length: 6ft [1.83 m]
F4S04C	\$721.00	NEMA 1/12 flex shaft cable operator for L-Frame MCCB. Cable length: 4ft [1.22 m]
F4S06C	\$829.00	NEMA 1/12 flex shaft cable operator for L-Frame MCCB. Cable length: 6ft [1.83 m]

3P Series Molded Case Circuit Breakers

Accessories

**F0S03HP**

High Performance Flex Shaft™ Flange Handles

These two-position flange handles feature external front mounting. Models are available for NEMA 1/3R/12 and 4/4X enclosures and for G-frame, F-frame, K-frame or L-frame model MCCBs. All models are lockable in the OFF position and are defeatable. The Flex Shaft handle will accept up to three padlock shackles, each with a maximum diameter of 0.375 in [9.5 mm]. Each item includes a high-strength nylon handle, breaker operating mechanism, and cable.

Flange Handle Accessory Selection Guide


Part Number	Price	Description
<u>F0S03HP</u>	\$309.00	3ft [0.91 m] cable length, NEMA 1/3R/12. For use with G-frame model MCCBs.
<u>F0S06HP</u>	\$352.00	6ft [1.83 m] cable length, NEMA 1/3R/12. For use with G-frame model MCCBs.
<u>F1S03HP</u>	\$352.00	3ft [0.91 m] cable length, NEMA 1/3R/12. For use with F-frame model MCCBs.
<u>F1S06HP</u>	\$379.00	6ft [1.83 m] cable length, NEMA 1/3R/12. For use with F-frame model MCCBs.
<u>F3S03HP</u>	\$429.00	3ft [0.91 m] cable length, NEMA 1/3R/12. For use with K-frame model MCCBs.
<u>F3S06HP</u>	\$450.00	6ft [1.83 m] cable length, NEMA 1/3R/12. For use with K-frame model MCCBs.
<u>F4S04HP</u>	\$504.00	4ft [1.22 m] cable length, NEMA 1/3R/12. For use with L-frame model MCCBs.
<u>F4S06HP</u>	\$580.00	6ft [1.83 m] cable length, NEMA 1/3R/12. For use with L-frame model MCCBs.
<u>F0S03HPX</u>	\$340.00	3ft [0.91 m] cable length, NEMA 4/4X. For use with G-frame model MCCBs.
<u>F0S06HPX</u>	\$387.00	6ft [1.83 m] cable length, NEMA 4/4X. For use with G-frame model MCCBs.
<u>F1S03HPX</u>	\$387.00	3ft [0.91 m] cable length, NEMA 4/4X. For use with F-frame model MCCBs.
<u>F1S06HPX</u>	\$418.00	6ft [1.83 m] cable length, NEMA 4/4X. For use with F-frame model MCCBs.
<u>F3S03HPX</u>	\$473.00	3ft [0.91 m] cable length, NEMA 4/4X. For use with K-frame model MCCBs.
<u>F3S06HPX</u>	\$496.00	6ft [1.83 m] cable length, NEMA 4/4X. For use with K-frame model MCCBs.
<u>F4S04HPX</u>	\$543.00	4ft [1.22 m] cable length, NEMA 4/4X. For use with L-frame model MCCBs.
<u>F4S06HPX</u>	\$625.00	6ft [1.83 m] cable length, NEMA 4/4X. For use with L-frame model MCCBs.

Note: A minimum bending radius of four inches is necessary for proper operation.

3P Series Molded Case Circuit Breakers

Accessories

Field Mountable Accessories



A1X3PK

Auxiliary Contact

The auxiliary contact provides circuit breaker contact status information by monitoring the position of the molded cross bar which contains the moving contact arms. The auxiliary switch is used for remote indication and interlock system verification, and consists of one SPDT switch housed in a plug-in module. Each SPDT switch has one 'a' and one 'b' contact. When the circuit breaker contacts are open, the 'a' contact is open and the 'b' contact is closed.

Note: Field installable auxiliary contacts are not available for the G and F frame breakers.

For G and F frame auxiliary contacts, order breakers with -AUX as part of the part number. Please see G and F-frame sections for available selections.

Auxiliary Contact Accessory Selection Guide

Part Number	Price	Description
A1X3PK	\$310.00	Field installable auxiliary contact for K-Frame MCCB, SPDT, 18" pigtail leads
A1X4PK	\$318.00	Field installable auxiliary contact for L-Frame MCCB, SPDT, 18" pigtail leads


K-Frame Electrical Ratings ^{1,2}

	Max Volts	Frequency	Max Amperes	Dielectric Withstand Voltage	Notes
K-Frame Auxiliary Switch	600	50/60 Hz	6	2500	1. Endurance: 5000 electrical operations plus 1000 mechanical operations. 2. Pigtail wire size: 18 AWG (0.82 mm ²) 3. Non-inductive load
	125	DC	0.50 ³		
	250	DC	0.25 ³		

L-Frame Electrical Ratings ^{1,2}

	Max Volts	Frequency	Max Amperes	Dielectric Withstand Voltage	Notes
L-Frame Auxiliary Switch	600	50/60 Hz	6	2500	1. Endurance: 5000 electrical operations plus 1000 mechanical operations. 2. Pigtail wire size: 18 AWG (0.82 mm ²) 3. Non-inductive load
	125	DC	0.50 ³		
	250	DC	0.25 ³		

Undervoltage Release



UVH3LP21K

This product monitors a voltage (typically a line voltage) and trips the circuit breaker when the voltage falls to between 70% and 35% of the solenoid coil rating. It consists of a continuous rated solenoid, with a plunger and tripping lever mounted in a plug-in module.

Note: The undervoltage release is a pre-installed accessory on G-Frame and F-Frame breakers.

Undervoltage Release Accessory Selection Guide

Part Number	Price	Description
UVH3LP08K	\$481.00	Field installable 110 - 127 VAC undervoltage release for K-Frame MCCB
UVH4LP08K	\$513.00	Field installable 110 - 127 VAC undervoltage release for L-Frame MCCB
UVH3LP21K	\$481.00	Field installable 24 VDC undervoltage release for K-Frame MCCB
UVH4LP21K	\$550.00	Field installable 24 VDC undervoltage release for L-Frame MCCB

K-Frame Undervoltage Release Mechanism	Supply Voltage	Dropout Voltage		Pickup Voltage	VA	Notes
		Min	Max	Max		
	24 VDC	8.4	16.8	20.4	3.1	1. Endurance: 5000 electrical operations plus 1000 mechanical operations. 2. 50/60 Hz
	110 VAC ²				1.8	
	120 VAC ²	44.5	77.0	93.5	2.1	
	127 VAC ²				2.4	

L-Frame Undervoltage Release Mechanism	Supply Voltage	Dropout Voltage		Pickup Voltage	VA	Notes
		Min	Max	Max		
	24 VDC	8.4	16.8	20.4	3.1	1. Endurance: 5000 electrical operations plus 1000 mechanical operations. 2. 50/60 Hz
	110 VAC ²				1.8	
	120 VAC ²	44.5	77.0	93.5	2.1	
	127 VAC ²				2.4	

3P Series Molded Case Circuit Breakers

Accessories

Field Mountable Accessories

Shunt Trip

The Shunt Trip provides remote controlled tripping of the circuit breaker. Consisting of an intermittent rated solenoid with a tripping plunger and a cutoff switch assembled to a plug-in module, shunt trip coils are designed to be applied at specific AC or DC voltages.



SNT3P04K

Shunt Trip Accessory Selection Guide

Part Number	Price	Description
SNT3P11K	\$481.00	Field installable 110/240 VAC / 110/125 VDC shunt trip for K-Frame MCCB.
SNT4RP11K	\$550.00	Field installable 110/240 VAC shunt trip for L-Frame MCCB
SNT3P04K	\$481.00	Field installable 12/24 VAC/DC shunt trip for K-Frame MCCB
SNT4RP03K	\$550.00	Field installable 12/24 VAC/DC shunt trip for L-Frame MCCB

K-Frame Shunt Trip	Supply Voltage	Min Operating Voltage	VA	Supply Voltage	Min Operating Voltage	VA	Notes
	VAC 50/60 Hz			VDC			1. Endurance: 5000 electrical operations plus 1000 mechanical operations. 2. Approx. unlatching time: 6 ms Approx. total circuit breaker contact opening time: 8 ms
	12	9	45	12	8.4	35	
	24		200	24		170	
	110	60	100	110	77	110	
	120		120	120	77	130	
	127		140	125	77	140	
	208		420	—	—	—	
	220		470	—	—	—	
	240		550	—	—	—	

L-Frame Shunt Trip	Supply Voltage	Min Operating Voltage	VA	Supply Voltage	Min Operating Voltage	VA	Notes
	VAC 50/60 Hz			VDC			<div>1. Endurance: 5000 electrical operations plus 1000 mechanical operations.</div> <div>2. Approx. unlatching time: 6 ms</div> <div>Approx. total circuit breaker contact opening time: 18 ms</div>
	12	9	45	12	9	35	
	24		200	24		170	
	110	60	100	—	—	—	
	120		120	—	—	—	
	127		140	—	—	—	
	208		420	—	—	—	
	220		470	—	—	—	
	240		550	—	—	—	

3P Series Molded Case Circuit Breakers

Accessories


Field Mountable Accessories

Six-wire Connector

This is a field installable multi-wire connector which allows six wires to be connected to the load side (OFF) end terminals. It is used to distribute the load from the circuit breaker to multiple devices without the use of separate distribution terminal blocks. UL listed for copper only as used on the load side (OFF) end. Includes mounting hardware, insulators and tin-plated aluminum connectors.

Six-wire Connector Accessory Selection Guide

Part Number	Price	Description
<u>3TA100G6K</u>	\$87.00	For G-Frame MCCBs. Pkg. of 3. Wire size: 14 - 6 AWG, copper
<u>3TA150F6K</u>	\$87.00	For F-Frame MCCBs. Pkg. of 3. Wire size: 14 - 6 AWG, copper



[3TA100G6K](#)

Multi-Wire Box Type Wiring Lug

These multi-wire lugs allow for cost and space savings within a panel and allow for improved short-circuit ratings by eliminating the need for power distribution blocks. Designed for load-side mounting. Choose for G-frame, F-frame, or K-frame model MCCBs. Mounting hardware and insulators included. Package of 3.

Multi-Wire Box Type Wiring Lug Selection Guide

Part Number	Price	Description
<u>3TA100G3K</u>	\$72.00	100A, 3 openings, #14-2 AWG copper only. For use with G-frame model MCCBs.
<u>3TA150F3K</u>	\$80.00	225A, 3 openings, #14-2 AWG copper only. For use with F-frame model MCCBs.
<u>3TA400K3K</u>	\$161.00	400A, 3 openings, #14-2/0 AWG copper only. For use with K-frame model MCCBs.
<u>3TA400K6K</u>	\$161.00	400A, 6 openings, #14-3 AWG copper only. For use with K-frame model MCCBs.



[3TA100G3K](#)


Replacement Lug Kit

Line and load terminals provide wire connecting capabilities for specific ranges of continuous current ratings and wire types. Replacement lugs will accept wire types Cu/Al as standard.

Replacement Lug Kit Accessory Selection Guide

Part Number	Price	Description
<u>3TA225FD</u>	\$129.00	Replacement lug kit for F-Frame MCCB. Wire range (1) #4-4/0 (25-95 mm²). Package of (3) terminals.
<u>3TA401K</u>	\$135.00	Replacement lug kit for K-Frame MCCB. Wire range (2) 2/0-250 kcmil or (1) 2/0-500 kcmil (70-240 mm²). 3-pole kit (one terminal per pole and one terminal cover).
<u>3TA603LDK</u>	\$166.00	Replacement lug kit for L-Frame MCCB. 3-pole kit (one terminal per pole and one terminal cover). Wire range 400-500 AWG (185-240 mm²), 2 conductors.

Note: G-frame terminals are factory-installed only. No replacement terminals available.



[3TA401K](#)

Din Rail Mounting Clip

Din Rail Mount Clip Accessory Selection Guide

Part Number	Price	Description
<u>GDIN</u>	\$15.00	Clip for mounting G-Frame to 35 mm Din rail. Mounting hardware included. Pkg of 1



[GDIN](#)

3P Series Molded Case Circuit Breakers

Accessories

Field Mountable Accessories

NEMA 12 Safety Door Hardware

Type C361 door interlocking safety handle kits are designed for use with AutomationDirect 3P series MCCBs and flexible handle when mounted in an SDN12, or equivalent, enclosure. These handles secure the SDN12 enclosure, protecting against unauthorized entry while the MCCB is in the ON position. Use them on enclosures with right-side flanges only and material thickness from 16 gauge through 3/16 in. All mounting hardware is included for enclosures up to 40in [101.6 cm] tall. The addition of the C361KR roller kit is necessary for enclosures taller than 40in [101.6 cm] that require a 3-point latch. See SDN12 Enclosures section for enclosure specifications.

Safety Door Hardware Selection Guide		
Part Number	Price	Description
<u>C361KJ4</u>	\$360.00	Handle length: 4in [10.16 cm]. Mounting hardware included for enclosures up to 40in [101.6 cm] tall. For taller enclosures that require a 3-point latch, the C361KR (purchase separately) will also be needed.
<u>C361KJ6</u>	\$378.00	Handle length: 6in [15.24 cm]. Mounting hardware included for enclosures up to 40in [101.6 cm] tall. For taller enclosures that require a 3-point latch, the C361KR (purchase separately) will also be needed.
<u>C361KR</u>	\$77.00	Door interlocking safety roller kit for use with the C361KJ4 and C361KJ6 safety handle kits when the SDN12 series enclosure is taller than 40in [101.6 cm] and 3-point latching is required. Kit includes roller and all hardware.

Note: The 1/4" x 1/2" standard mill rectangular locking bar is not supplied with these kits. The bar is supplied with the enclosures.



Safety Handle shown on enclosure

Eaton Quality at AutomationDirect Prices

1, 2 and
3-pole
models

EAT•N



Third party Certification and marking

- UL recognized under UL 1077 Category QVNU2, File E177451
- CSA 22.2, No. 235 File 204453
- CE File LVD 2006/95/EC
- IEC 60898
- IEC 60947-2




Full line of field installable accessories

- Auxiliary switch
- Alarm/Auxiliary Switch
- Shunt trip
- Padlock provision
- Busbar systems

Trip curves

- B [3-5 I_n]
- C [5-10 I_n]
- D [10-20 I_n]



FAZ Series Supplementary Protectors

FAZ Supplementary Protectors are UL 1077 recognized for applications where branch circuit protection is not required or is already provided. They are thermal magnetic and protect against short circuit (see ratings chart) and overload conditions.

These DIN-rail mounted supplementary protectors come in one, two and three pole configurations and are available in three trip curves.

The B curve magnetic trip point is 3 to 5 times the rated current and is typically used for computers and electronic loads with very low current loads.

The C curve magnetic trip point is 5 to 10 times the rated current and is typically used for small transformers, pilot devices, etc.

The D curve magnetic trip point is 10 to 20 times the rated current and is typically used for transformers or with very high inductive loads.

Shunt trips are available for remotely tripping the protector with an external voltage from a control system or alarm device.

A padlocking feature is also available for preventing unauthorized operation. Maintenance personnel can safely work on protected equipment without electrical safety concerns.





Overview

The Eaton FAZ supplementary protectors are used to provide overcurrent protection where branch protection (for example, UL 489 MCCB) is already provided or not required. The units can be installed as a component within, or as a part of an appliance or a piece of electrical equipment. Supplementary protectors are ideal replacements for fuses that are applied as a supplementary protector, i.e. in addition to branch protection (if required). They are 35mm DIN-rail mountable, utilizing spring clips. These are standard protectors, recognized by UL and CSA under UL 1077 and CSA 22.2. They are CE marked in accordance with Low Voltage Directive (LVD) (73/23/EEC).



Product Specification

The FAZ supplementary protector is a dual-rated product for both AC and DC supplies, in accordance with UL 1077 and CSA 22.2 standards and is marked with CE in accordance with the Low Voltage Directive. With this dual standard product, you can include it in your design, knowing that in most cases wherever your equipment is used, the product will conform to the local UL, CSA or IEC (International) requirements.

The supplementary protector is designed to be applied in conjunction with a branch circuit protector (if branch protection is required) and can be a replacement for similarly applied fuses. Its advantage over fuses is that it is resettable and the device's status is easily and clearly identified by the position of the handle and the flag indicator.

In addition, you can select a device that provides maximum reliability and accuracy to fit various applications due to the availability of a wide range of current ratings from 0.5 to 63 amperes in three overcurrent characteristic curves, B, C and D.

Features and Benefits

- Dual rated for AC or DC Applications
- Box terminals accept #18 to #4 wire (1 to 25mm²) for one wire connection or #18 to #8 for two wire connection.
- Thermal magnetic overcurrent protection: three levels, categorized by B, C and D curves in direct relation to continuous rating of the device
- **B curve magnetic trip point:** 3 to 5 times the rated current, typically used for computers and electronic loads with very low inrush currents (PLC wiring).
- **C curve magnetic trip point:** 5 to 10 times the rated current, typically used for small transformers, pilot devices, etc.
- **D curve magnetic trip point:** 10 to 20 times the rated current, typically used for transformers or devices with very high inductive loads.
- Trip Free Design: Protector cannot be defeated by holding the handle in the "ON" position.
- Module width of only 17.7 mm per pole
- Color coded status indicator window – Red = ON or Green = OFF
- P20 finger protection
- 35mm DIN-rail mountable, utilizing spring clip
- Captive screws cannot be lost
- Suitable for reverse feed applications

Listings

- UL recognized under UL 1077 Category QVNU2 File E177451
- CSA 22.2, No. 235 File 204453

- CE File LVD 2006/95/EC
- IEC/EN 60898

- IEC/EN 60947-2

Applications

FAZ Supplementary protectors are recognized per UL 1077 and certified per CSA C22.2 No. 235 as a Supplementary Protector and can be fully utilized per the NEC and CEC Codes in that capacity. For international purposes, the entire FAZ family is CE marked and in full conformity with the applicable IEC standards for miniature circuit breakers, EN/IEC 60898 and IEC/EN 60947-2.

Outside North America, they can be used in both residential and industrial applications as feeder and branch circuit


protective devices. In North America, most European Miniature Circuit Breakers are only UL recognized and CSA certified as "Supplementary Protectors", meaning they cannot be utilized as feeder or branch circuit protective devices per the local electrical codes (2008 NEC 240.10 and CEC Part 1 C22.1). This commonly restricts their use to applications where "closer" protection is desired than that offered by a branch circuit protection device.

Eaton FAZ Supplementary Protectors are

ideal for providing protection in many applications, including:

- Control power transformers (D curve)
- Relays
- Contactor coils
- PLC I/O points
- Lighting circuits
- Power supplies
- Computers
- Electronic equipment
- Control circuits

Supplementary Protectors Sample Applications



Supplementary protectors are not to be used in feeder circuits or motor circuits. Use them only in applications where branch protection is already provided or is not required.

EATON FAZ Supplementary Protectors Selection Guide



Single-Pole

Note: Eaton product part numbers will contain a [.] instead of [P] and a [/] instead of a [-].
Example: FAZ-C0P5-1-SP = FAZ-C0.5/1-SP

FAZ - Single-Pole Selection Guide						
Ampere Rating	B Curve Part Number	Price	C Curve Part Number	Price	D Curve Part Number	Price
0.5	—	—	FAZ-C0P5-1-SP		FAZ-D0P5-1-SP	
1	FAZ-B1-1-SP	\$20.00	FAZ-C1-1-SP	\$20.00	FAZ-D1-1-SP	\$20.00
2	FAZ-B2-1-SP		FAZ-C2-1-SP		FAZ-D2-1-SP	
3	FAZ-B3-1-SP		FAZ-C3-1-SP		FAZ-D3-1-SP	
4	FAZ-B4-1-SP		FAZ-C4-1-SP		FAZ-D4-1-SP	
5	FAZ-B5-1-SP		FAZ-C5-1-SP		FAZ-D5-1-SP	
6	FAZ-B6-1-SP		FAZ-C6-1-SP		FAZ-D6-1-SP	
7	FAZ-B7-1-SP		FAZ-C7-1-SP		FAZ-D7-1-SP	
8	FAZ-B8-1-SP		FAZ-C8-1-SP		FAZ-D8-1-SP	
10	FAZ-B10-1-SP		FAZ-C10-1-SP		FAZ-D10-1-SP	
13	FAZ-B13-1-SP		FAZ-C13-1-SP		FAZ-D13-1-SP	
15	FAZ-B15-1-SP		FAZ-C15-1-SP		FAZ-D15-1-SP	
16	FAZ-B16-1-SP		FAZ-C16-1-SP		FAZ-D16-1-SP	
20	FAZ-B20-1-SP		FAZ-C20-1-SP		FAZ-D20-1-SP	
25	FAZ-B25-1-SP		FAZ-C25-1-SP		FAZ-D25-1-SP	
30	FAZ-B30-1-SP		FAZ-C30-1-SP		FAZ-D30-1-SP	
32	FAZ-B32-1-SP		FAZ-C32-1-SP		FAZ-D32-1-SP	
40	FAZ-B40-1-SP		FAZ-C40-1-SP		FAZ-D40-1-SP	
50	FAZ-B50-1-SP		FAZ-C50-1-SP		—	—
63	FAZ-B63-1-SP		FAZ-C63-1-SP		—	—



Two-Pole

Note: Eaton parts available for sale to North America locations only.

FAZ - Two-Pole Selection Guide						
Ampere Rating	B Curve Part Number	Price	C Curve Part Number	Price	D Curve Part Number	Price
0.5	—	—	FAZ-C0P5-2		FAZ-D0P5-2	
1	FAZ-B1-2	\$39.00	FAZ-C1-2	\$39.00	FAZ-D1-2	\$39.00
2	FAZ-B2-2		FAZ-C2-2		FAZ-D2-2	
3	FAZ-B3-2		FAZ-C3-2		FAZ-D3-2	
4	FAZ-B4-2		FAZ-C4-2		FAZ-D4-2	
5	FAZ-B5-2		FAZ-C5-2		FAZ-D5-2	
6	FAZ-B6-2		FAZ-C6-2		FAZ-D6-2	
7	FAZ-B7-2		FAZ-C7-2		FAZ-D7-2	
8	FAZ-B8-2		FAZ-C8-2		FAZ-D8-2	
10	FAZ-B10-2		FAZ-C10-2		FAZ-D10-2	
13	FAZ-B13-2		FAZ-C13-2		FAZ-D13-2	
15	FAZ-B15-2		FAZ-C15-2		FAZ-D15-2	
16	FAZ-B16-2		FAZ-C16-2		FAZ-D16-2	
20	FAZ-B20-2		FAZ-C20-2		FAZ-D20-2	
25	FAZ-B25-2		FAZ-C25-2		FAZ-D25-2	
30	FAZ-B30-2		FAZ-C30-2		FAZ-D30-2	
32	FAZ-B32-2		FAZ-C32-2		FAZ-D32-2	
40	FAZ-B40-2		FAZ-C40-2		FAZ-D40-2	
50	FAZ-B50-2		FAZ-C50-2		—	—
63	FAZ-B63-2		FAZ-C63-2		—	—

EAT•N FAZ Supplementary Protectors Selection Guide

FAZ - Three-Pole Selection Guide					
Ampere Rating	B Curve Part Number	Price	C Curve Part Number	Price	D Curve Part Number
0.5	—	—	FAZ-C0P5-3		FAZ-D0P5-3
1	FAZ-B1-3	\$53.00	FAZ-C1-3	\$53.00	FAZ-D1-3
2	FAZ-B2-3		FAZ-C2-3		FAZ-D2-3
3	FAZ-B3-3		FAZ-C3-3		FAZ-D3-3
4	FAZ-B4-3		FAZ-C4-3		FAZ-D4-3
5	FAZ-B5-3		FAZ-C5-3		FAZ-D5-3
6	FAZ-B6-3		FAZ-C6-3		FAZ-D6-3
7	FAZ-B7-3		FAZ-C7-3		FAZ-D7-3
8	FAZ-B8-3		FAZ-C8-3		FAZ-D8-3
10	FAZ-B10-3		FAZ-C10-3		FAZ-D10-3
13	FAZ-B13-3		FAZ-C13-3		FAZ-D13-3
15	FAZ-B15-3		FAZ-C15-3		FAZ-D15-3
16	FAZ-B16-3		FAZ-C16-3		FAZ-D16-3
20	FAZ-B20-3		FAZ-C20-3		FAZ-D20-3
25	FAZ-B25-3		FAZ-C25-3		FAZ-D25-3
30	FAZ-B30-3		FAZ-C30-3		FAZ-D30-3
32	FAZ-B32-3		FAZ-C32-3		FAZ-D32-3
40	FAZ-B40-3		FAZ-C40-3		FAZ-D40-3
50	FAZ-B50-3		FAZ-C50-3		—
63	FAZ-B63-3		FAZ-C63-3		—



Three-Pole

Note: Eaton product part numbers will contain a [.] instead of [P] and a [/] instead of a [-].
Example: FAZ-C0P5-3 = FAZ-C0.5/3

FAZ Series Technical Specifications

UL 1077 Supplementary Protectors – UL/CSA

		B Curve	C Curve	D Curve
Short Circuit Trip Response		3 - 5 I_n	5 - 10 I_n	10 - 20 I_n
Current Range		1 - 63 A	0.5 - 63 A	0.5 - 40 A
Maximum Voltage Ratings UL / CSA	1 pole	277VAC, 48VDC		
	2 pole / 3 pole	480Y / 277VAC*		
	2 poles in series	96VDC Max		
Thermal Tripping Characteristics	1 pole	1.35 I_n @ 40°C		
	Multi-pole	1.45 I_n @ 40°C		
Interrupting Ratings (@ maximum voltage)	1 pole	10kA (5kA for 40 - 63 A)		5kA
		10kA @ 48VDC		
	2 pole	10kA (5kA for 40 - 63 A)		5kA
	3 pole			
	2 poles in series	10kA @ 96VDC		
Agency Approvals		File E177451, UL 1077, File 204453 CSA 22.2 No. 235, CE		

Note: To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

IEC/EN 60947-2 Miniature Circuit Breaker

		B Curve	C Curve	D Curve
Short Circuit Trip Response		3 - 5 I_n	5 - 10 I_n	10 - 20 I_n
Current Range		1 - 63 A	0.5 - 63 A	0.5 - 63 A
Maximum Voltage Ratings - IEC/EN 60947-2	1 pole	240VAC, 48VDC		
	2 pole / 3 pole	240/415 VAC		
	2 poles in series	96VDC		
Thermal Tripping Characteristics	1 pole	> 1 hour @ 1.05 I_n		
	Multi-pole	< 1 hour @ 1.3 I_n		
Interrupt Ratings (At Max Voltage)		15kA		
Operational Switching Capacity		7.5 kA		
Max. Back-up Fuse		125A gL/gG		
Rated impulse withstand - U_{imp}		4000VAC		
Rated insulation voltage - U_i		440VAC		

General Specifications

Selectivity Class	3		
Lifespan	>10,000 (1 operation = ON/OFF)		
Operating Temperature	-40 to +167°F (-40 to +75°C)		
Storage Temperature	-40 to +185°F (-40 to +85°C)		
Shock (IEC68-2-22)	10g - 120ms		
Housing Material	Nylon		
Weight	1 pole	0.28 lb (127g)	
	2 pole	0.54 lb (245g)	
	3 pole	0.84 lb (381g)	

Mechanical Specifications

Terminal Protection	Finger and back-of-hand proof to IEC 536		
Mounting Width Per Pole	17.5 mm		
Mounting	IEC/EN 60715 top-hat rail, DIN rail		
Degree of Protection	IP20		
Terminals Top and Bottom	Twin-purpose terminals		
Supply Connection	Line or load side		
Mounting Position	Without limitation		

Wire Size and Torque Setting

Ampere Rating	Conductor Size		Tightening Torque
0.5 - 63	1 wire	0.75 to 25mm ²	21.2 lb·in (2.4 N·m)
	2 wires	0.75 to 10mm ²	

*A circuit breaker with a 480Y/277 VAC rating can be applied in a solidly grounded circuit where the nominal voltage of any conductor to ground does not exceed the lower value of the circuit breaker's rating (e.g., 277VAC) and the nominal voltage between any two conductors does not exceed its higher value (480VAC). These ratings typically can be found on protective devices such as molded-case circuit breakers and self-protected "Type F" combination motor controllers.

EAT•N FAZ Series Technical Data


Corrected values of the rated current dependent on the ambient temperature

Influence of the Ambient Temperature on the Thermal Tripping Behavior																	
Rated Current (Amps)	Ambient Temperature °C																
	-40	-30	-20	-10	0	10	20	30	35	40	45	50	55	60	65	70	75
0.50	0.64	0.62	0.60	0.58	0.56	0.54	0.52	0.50	0.49	0.48	0.47	0.46	0.45	0.44	0.43	0.42	0.41
1.00	1.30	1.20	1.20	1.20	1.10	1.10	1.00	1.00	0.99	0.97	0.95	0.93	0.90	0.89	0.87	0.85	0.83
2.00	2.60	2.50	2.40	2.30	2.20	2.20	2.10	2.00	2.00	1.90	1.90	1.90	1.80	1.80	1.70	1.70	1.70
3.00	3.80	3.70	3.60	3.50	3.40	3.30	3.10	3.00	3.00	2.90	2.80	2.80	2.70	2.70	2.60	2.50	2.50
4.00	5.10	5.00	4.80	4.70	4.50	4.30	4.20	4.00	3.90	3.90	3.80	3.70	3.60	3.50	3.50	3.40	3.30
5.00	6.40	6.20	6.00	5.80	5.60	5.40	5.20	5.00	4.90	4.80	4.70	4.60	4.50	4.40	4.30	4.20	4.10
6.00	7.70	7.50	7.20	7.00	6.70	6.50	6.30	6.00	5.90	5.80	5.70	5.60	5.40	5.30	5.20	5.10	5.00
7.00	9.00	8.70	8.40	8.20	7.80	7.60	7.40	7.00	6.90	6.80	6.70	6.50	6.30	6.20	6.10	6.00	5.80
8.00	10.20	9.90	9.60	9.30	9.00	8.70	8.40	8.00	7.90	7.70	7.60	7.40	7.20	7.10	6.90	6.80	6.60
10.00	13.00	12.00	12.00	12.00	11.00	11.00	10.00	10.00	9.90	9.70	9.50	9.30	9.00	8.90	8.70	8.50	8.30
13.00	17.00	16.00	16.00	15.00	15.00	14.00	14.00	13.00	13.00	13.00	12.00	12.00	12.00	12.00	11.00	11.00	11.00
15.00	19.00	19.00	18.00	17.00	17.00	16.00	16.00	15.00	15.00	15.00	14.00	14.00	14.00	13.00	13.00	13.00	12.00
16.00	20.00	20.00	19.00	19.00	18.00	17.00	17.00	16.00	16.00	15.00	15.00	15.00	14.00	14.00	14.00	14.00	13.00
20.00	26.00	25.00	24.00	23.00	22.00	22.00	21.00	20.00	20.00	19.00	19.00	19.00	18.00	18.00	17.00	17.00	17.00
25.00	32.00	31.00	30.00	29.00	28.00	27.00	26.00	25.00	25.00	24.00	24.00	23.00	23.00	22.00	22.00	21.00	21.00
32.00	41.00	40.00	38.00	37.00	36.00	35.00	33.00	32.00	32.00	31.00	30.00	30.00	29.00	28.00	28.00	27.00	26.00
40.00	51.00	50.00	48.00	47.00	45.00	43.00	42.00	40.00	39.00	39.00	38.00	37.00	36.00	35.00	35.00	34.00	33.00
50.00	64.00	62.00	60.00	58.00	56.00	54.00	52.00	50.00	49.00	48.00	47.00	46.00	45.00	44.00	43.00	42.00	41.00
63.00	81.00	78.00	76.00	73.00	71.00	68.00	66.00	63.00	62.00	61.00	60.00	58.00	57.00	56.00	55.00	53.00	52.00

Influence of the mains system frequency on the tripping behavior IMA of the instantaneous release

Influence of the Mains Frequency							
Mains Frequency f (Hz)	16 2/3	50	60	100	200	300	400
$I_{MA}(f) / I_{MA}(50\text{Hz})$ [%]	91	100	101	106	115	134	141

Load Carrying Capacity of Adjoining Supplementary Protectors




EAT•N FAZ Series Technical Data

Characteristic Curves


- The X axis shows the prospective short-circuit current levels.
- The Y axis indicates the actual let-through values at those prospective fault ratings for each FAZ device plotted.

As can be interpreted from the bend in the plotted curves, each device acts to limit the damaging let-through energy (and current) at those values of short-circuit current.


Let-through energy I^2t
Characteristic B and C




Let-through current I
Characteristic B and C



Let-through energy I^2t
Characteristic D




Let-through current I
Characteristic D



EAT•N FAZ Series Technical Data


Time-current characteristic

Type B, C and D



FAZ Supplementary Protector Dimensions

in [mm]




Please see our website www.AutomationDirect.com for complete engineering drawings. Dimensions are approximate. Not for construction purposes.


EATON FAZ Series Accessories

Field Mountable Accessories

- Auxiliary switch
- Alarm switch
- Shunt trip
- No tools required for mounting



FAZ-XHIN11-SP
Auxiliary Contact



FAZ-XAM002
Alarm/Aux Contact



FAZ-XAA-C12-110V
FAZ-XAA-C110-415V
Shunt Trip


FAZ Series Auxiliary Contacts and Shunt Trip Release

Part Number	Description	Contacts	Module Width	Module Weight	Price
FAZ-XHIN11-SP	1 NO / 1 NC Installs on left side of FAZ or shunt trip Maximum one per FAZ (1077) device Switches when FAZ is tripped electrically or manually	(1) DPST	0.35 in [8.9 mm]	0.15 lb [68g]	\$37.50
FAZ-XAM002	Small selector screw changes mode Two form C (one set changeover) contacts Installs on left side of FAZ or shunt trip Auxiliary contacts switch when FAZ is tripped electrically or manually Trip indicating contact switches only when FAZ is tripped electrically	(2) Form C Contacts SPDT			
Part Number	Description	Trip Voltage	Module Width	Module Weight	Price
FAZ-XAA-C110-415V	Allows remote trip of FAZ Installs on left side of FAZ	110 – 415 VAC 110 – 230 VDC	0.69 in [17.5 mm]	0.28 lb [127g]	\$66.00
FAZ-XAA-C12-110V		12 – 110 VAC 12 – 60 VDC			

Auxiliary Contacts and Voltage Trips Technical Specifications

Part Number	Circuit Diagram	Electrical Characteristics	Mechanical Characteristics	Wire Size (Solid and Stranded)		Tightening Torque	
				mm ²	AWG	N·m	lb·in
FAZ-XHIN11-SP		Rated for general use 2A at 230/240 VAC 0.5 A at 110/120 VDC rated frequency 50/60 Hz	FAZ mounting, IP40 protection, IEC 536 protection against electric shock, lift terminals	0.5 - 2.5	18 - 14	0.8 - 1.0	7.1 - 9.0
FAZ-XAM002	See FAZ-XAM002 diagrams on dimensions page	1 SPDT auxiliary contact and 1 SPDT alarm contact that can be configured and used as an auxiliary contact, rated for general use, 2A at 230/240 VAC, 0.5 A at 110/120 VDC, rated frequency 50/60 Hz	FAZ mounting, IP40 protection, IEC 536 protection against electric shock, lift terminals				
FAZ-XAA-C110-415V		110 - 415 VAC, 110 - 230 VDC operating range, max inrush current 2.1 A (AC) / 1A (DC), rated frequency 50/60 Hz	IEC/EN 30715 top-hat rail or DIN rail mounting, IP40 protection, IEC 536 protection against electric shock, twin-purpose terminals	1 - 2.5	18 - 12	2.4	21.2
FAZ-XAA-C12-110V		12 - 110 VAC, 12 - 60 VDC operating range, maximum inrush current 15A (AC) / 21A (DC), rated frequency 50/60 Hz					


Allowable Combinations of Accessories



EAT•N FAZ Series Accessories

Protective Accessories

FAZ Series Protective Accessories			
Part Number	Description	Quantity	Price
ZIS-SPE-1TE-3	Lockout attachment for Eaton FAZ series supplementary protectors and FAZ mini circuit breakers, suitable to prevent unauthorized activation of a de-energized circuit, accepts lock shackles up to 9/32 in. (7.1 mm) in diameter	3 per pack	\$46.00
BBIP-5	Busbar protection shroud, covers up to 5 unused terminals (break off unused pieces to size), for use with Eaton BBUL series busbar.	10 per pack	\$74.00
BBIP-5-5		5 per pack	\$44.50




ZIS-SPE-1TE-3
Lockout Attachment

Busbar System

Without auxiliary contacts

BBUL Series Busbars for use with FAZ Series Supplementary Protectors				
	Description	Rated Operational Current	Qty	Price
BBUL25-1P-1M57-SP	Busbar, 1 pole, 57-position, 480VAC	100A, fed from end	1	\$62.00
BBUL25-2P-2M56-SP	Busbar, 2 pole, 56-position, 480VAC		1	\$114.00
BBUL25-3P-3M57-SP	Busbar, 3 pole, 57-position, 480VAC		1	\$173.00





Busbar Accessories			
	Description	Qty	Price
BBUL-EC-1	Busbar end cover for use with 1-pole Eaton BBUL series busbar.	10	\$16.50
BBUL-EC-1-2		2	\$6.75
BBUL-EC-3	Busbar cover end for use with 2-pole and 3-pole Eaton BBUL series busbar.	10	\$25.50
BBUL-EC-3-2		2	\$6.75
BBUL-TEPA-35-1	Busbar terminal lug, connects wiring to busbar system, for use with 1-pole Eaton BBUL series busbar, accepts 10AWG to 1/0 AWG copper wire, 115A, 1000V AC/DC.	1	\$20.00
BBUL-TEPA-35-3		3	\$55.00
BBUL-TEP-35-1	Busbar terminal lug, connects wiring to busbar system, for use with 2-pole and 3-pole Eaton BBUL series busbar, accepts 10AWG to 1/0 AWG copper wire, 115A, 1000V AC/DC.	1	\$20.00
BBUL-TEP-35-3		3	\$55.00



FAZ Series Accessories

Accessories Dimensions

in [mm]

**FAZ-XAM002****FAZ-XHIN11-SP****FAZ-XAA-C-xxx**


FAZ Series Miniature Circuit Breakers

Connection Diagrams


Single Pole



Two-Pole




Three-Pole




Busbar Connection Diagrams


Three-Pole Busbar



Two-Pole Busbar




Single Pole Busbar

Please see our website www.AutomationDirect.com for complete engineering drawings.


EATON FAZ Series Accessories

Accessories Dimensions


in [mm]




BBUL25-1P-1M57-SP




BBUL25-2P-2M56-SP




BBUL25-3P-3M57-SP




BBUL-TEP-35-1




BBUL-TEPA-35-1





BBUL-EC-1



BBUL-EC-3



BBIP-5



Please see our website www.AutomationDirect.com for complete engineering drawings.

EAT•N FAZ-NA Miniature Circuit Breakers



Overview

Eaton FAZ-NA and FAZ-NA-L miniature circuit breakers offer optimum and efficient protection for branch and control circuits up to 63 amps. The FAZ-NA and FAZ-NA-L series is available with B, C or D trip characteristics in accordance with UL 489. These circuit breakers are current limiting, which means they interrupt fault currents within one half cycle of the fault. The FAZ-NA and FAZ-NA-L series units are DIN-rail mountable and can be used in feeder and branch circuit applications.

Listings

- UL Listed under UL 489
Category DIVQ File E235139
Busbar Accessory
Category NMTR2.E257181
Category DIHS E257181
Category NMTR E307559
- CSA 22.2, No. 5 File 204453
- CE LVD 2014/35/EU
- CE RoHS 2011/65/EU
- IEC/EN 60947-2

Features and Benefits

- Dual rated for AC or DC applications
- Complete range of UL 489 listed DIN rail mounted miniature circuit breakers up to 63 amp current rating
- Single-pole, two-pole and three-pole models
- Current limiting design provides fast short circuit interruption that reduces the let-through energy, which can damage the circuit
- Suitable for reverse feed applications Suitable for branch circuit device protection
- Thermal-magnetic overcurrent protection – three levels of short circuit protection, categorized by B, C and D curves
 - B-curve magnetic trip point: 3 to 5 times the rated current, typically used for resistive loads such as conductors or heaters.
 - C-curve magnetic trip point: 5 to 10 times the rated current, typically used for small transformers, pilot devices, etc.
 - D-curve magnetic trip point: 10 to 20 times the rated current, typically used for transformers or very high inductive loads.
- Trip-free design – breaker cannot be defeated by holding the handle in the “ON” position Captive screws cannot be lost
- SWD (switching duty) rated circuit breaker – suitable for switching fluorescent lighting loads (In m 20A)
- Fulfills UL 489, CSA C22.2 No.5 and also IEC 60947-2 Standard
- Can also be used in applications for which UL 1077 or CSA C22.2 No.235 are also allowed
- Field installable shunt trip and auxiliary switch subsequent mounting Module width of only 17.7 mm [0.70 in] (per pole) Contact position indicator (red / green)
- 35mm DIN-rail mountable, utilizing spring clip

Applications

Feeder and Branch Circuit Protection

- PLC I/O points
- Motor control circuits
- Control instrumentation
- Power supplies
- Relays
- Convenience receptacle circuits (internal / external)
- Load circuits leaving the equipment (external)
- HACR Equipment (Heating Air Conditioning, Refrigeration)
- Computers
- UPS
- Power conditioners



EAT•N FAZ-NA Miniature Circuit Breakers

Tripping Characteristics

Eaton FAZ-NA and FAZ-NA-L miniature circuit breakers are available with "B" or "C" or "D" tripping characteristics.

Type B trip curve: 3 to 5 times I_n

B-curve devices are suitable for resistive loads such as conductors or heaters.


Type C trip curve: 5 to 10 times I_n

C-curve devices are suitable for applications where medium levels of inrush current are expected. Applications include small transformers, lighting, pilot devices, control circuits and coils. C-curve devices provide a medium magnetic trip point.

Type D trip curve: 10 to 20 times I_n


D-curve devices are suitable for applications where high levels of inrush current are expected. The high magnetic trip point prevents nuisance tripping in high inductive applications such as motors, transformers and power supplies.

Eaton FAZ-NA and FAZ-NA-L devices are current limiting, which means they interrupt fault currents within one half cycle of the fault. Current limiting devices offer superior protection by reducing peak let-through current and energy.



Labeling

The front of each Eaton FAZ-NA and FAZ-NA-L miniature circuit breaker is labeled for positive identification.



EAT•N FAZ-NA Series Selection Guide



Single-Pole

FAZ-NA – Single-Pole 480/277 VAC Selection Guide						
Ampere Rating	B-Curve Part Number	Price	C-Curve Part Number	Price	D-Curve Part Number	Price
0.5	—		FAZ-C0P5-1-NA-SP	\$34.00	FAZ-D0P5-1-NA-SP	\$37.50
1	FAZ-B1-1-NA-SP	\$31.00	FAZ-C1-1-NA-SP	\$34.00	FAZ-D1-1-NA-SP	\$37.50
1.5	FAZ-B1P5-1-NA-SP	\$31.00	FAZ-C1P5-1-NA-SP	\$34.00	FAZ-D1P5-1-NA-SP	\$37.50
2	FAZ-B2-1-NA-SP	\$85.00	FAZ-C2-1-NA-SP	\$34.00	FAZ-D2-1-NA-SP	\$37.50
3	FAZ-B3-1-NA-SP	\$31.00	FAZ-C3-1-NA-SP	\$34.00	FAZ-D3-1-NA-SP	\$37.50
4	FAZ-B4-1-NA-SP	\$31.00	FAZ-C4-1-NA-SP	\$34.00	FAZ-D4-1-NA-SP	\$37.50
5	FAZ-B5-1-NA-SP	\$31.00	FAZ-C5-1-NA-SP	\$34.00	FAZ-D5-1-NA-SP	\$37.50
6	FAZ-B6-1-NA-SP	\$31.00	FAZ-C6-1-NA-SP	\$34.00	FAZ-D6-1-NA-SP	\$34.00
7	FAZ-B7-1-NA-SP	\$31.00	FAZ-C7-1-NA-SP	\$34.00	FAZ-D7-1-NA-SP	\$34.00
8	FAZ-B8-1-NA-SP	\$31.00	FAZ-C8-1-NA-SP	\$34.00	FAZ-D8-1-NA-SP	\$34.00
10	FAZ-B10-1-NA-SP	\$31.00	FAZ-C10-1-NA-SP	\$34.00	FAZ-D10-1-NA-SP	\$34.00
13	FAZ-B13-1-NA-SP	\$31.00	FAZ-C13-1-NA-SP	\$34.00	FAZ-D13-1-NA-SP	\$34.00
15	FAZ-B15-1-NA-SP	\$31.00	FAZ-C15-1-NA-SP	\$34.00	FAZ-D15-1-NA-SP	\$34.00
16	FAZ-B16-1-NA-SP	\$31.00	FAZ-C16-1-NA-SP	\$34.00	FAZ-D16-1-NA-SP	\$34.00
20	FAZ-B20-1-NA-SP	\$31.00	FAZ-C20-1-NA-SP	\$34.00	FAZ-D20-1-NA-SP	\$34.00
25	FAZ-B25-1-NA-SP	\$31.00	FAZ-C25-1-NA-SP	\$30.50	FAZ-D25-1-NA-SP	\$34.00
30	FAZ-B30-1-NA-SP	\$31.00	FAZ-C30-1-NA-SP	\$34.00	FAZ-D30-1-NA-SP	\$37.50
32	FAZ-B32-1-NA-SP	\$31.00	FAZ-C32-1-NA-SP	\$34.00	FAZ-D32-1-NA-SP	\$37.50



Two-Pole

FAZ-NA – Two-Pole 480/277 VAC Selection Guide						
Ampere Rating	B-Curve Part Number	Price	C-Curve Part Number	Price	D-Curve Part Number	Price
0.5	—		FAZ-C0P5-2-NA	\$70.00	FAZ-D0P5-2-NA	\$73.00
1	FAZ-B1-2-NA	\$71.00	FAZ-C1-2-NA	\$73.00	FAZ-D1-2-NA	\$73.00
1.5	FAZ-B1P5-2-NA	\$71.00	FAZ-C1P5-2-NA	\$73.00	FAZ-D1P5-2-NA	\$73.00
2	FAZ-B2-2-NA	\$30.50	FAZ-C2-2-NA	\$73.00	FAZ-D2-2-NA	\$73.00
3	FAZ-B3-2-NA	\$71.00	FAZ-C3-2-NA	\$73.00	FAZ-D3-2-NA	\$73.00
4	FAZ-B4-2-NA	\$71.00	FAZ-C4-2-NA	\$73.00	FAZ-D4-2-NA	\$73.00
5	FAZ-B5-2-NA	\$71.00	FAZ-C5-2-NA	\$73.00	FAZ-D5-2-NA	\$73.00
6	FAZ-B6-2-NA	\$66.00	FAZ-C6-2-NA	\$67.00	FAZ-D6-2-NA	\$67.00
7	FAZ-B7-2-NA	\$66.00	FAZ-C7-2-NA	\$67.00	FAZ-D7-2-NA	\$67.00
8	FAZ-B8-2-NA	\$66.00	FAZ-C8-2-NA	\$67.00	FAZ-D8-2-NA	\$67.00
10	FAZ-B10-2-NA	\$66.00	FAZ-C10-2-NA	\$70.00	FAZ-D10-2-NA	\$67.00
13	FAZ-B13-2-NA	\$66.00	FAZ-C13-2-NA	\$67.00	FAZ-D13-2-NA	\$67.00
15	FAZ-B15-2-NA	\$66.00	FAZ-C15-2-NA	\$67.00	FAZ-D15-2-NA	\$67.00
16	FAZ-B16-2-NA	\$66.00	FAZ-C16-2-NA	\$67.00	FAZ-D16-2-NA	\$67.00
20	FAZ-B20-2-NA	\$66.00	FAZ-C20-2-NA	\$67.00	FAZ-D20-2-NA	\$67.00
25	FAZ-B25-2-NA	\$66.00	FAZ-C25-2-NA	\$67.00	FAZ-D25-2-NA	\$67.00
30	FAZ-B30-2-NA	\$66.00	FAZ-C30-2-NA	\$67.00	FAZ-D30-2-NA	\$67.00
32	FAZ-B32-2-NA	\$71.00	FAZ-C32-2-NA	\$73.00	FAZ-D32-2-NA	\$73.00

Note: Eaton product part numbers will contain a [.] instead of [P] and a [/] instead of a [-]. Example: FAZ-C0P5-3-NA = FAZ-C0.5/3-NA

Note: Eaton parts available for sale to North America locations only.

EATON FAZ-NA Series Selection Guide



Three-Pole

FAZ-NA – Three-Pole 480/277 VAC Selection Guide						
Ampere Rating	B-Curve Part Number	Price	C-Curve Part Number	Price	D-Curve Part Number	Price
0.5	—		FAZ-C0P5-3-NA	\$114.00	FAZ-D0P5-3-NA	\$114.00
1	FAZ-B1-3-NA	\$105.00	FAZ-C1-3-NA	\$104.00	FAZ-D1-3-NA	\$114.00
1.5	FAZ-B1P5-3-NA	\$105.00	FAZ-C1P5-3-NA	\$104.00	FAZ-D1P5-3-NA	\$114.00
2	FAZ-B2-3-NA	\$181.00	FAZ-C2-3-NA	\$104.00	FAZ-D2-3-NA	\$114.00
3	FAZ-B3-3-NA	\$105.00	FAZ-C3-3-NA	\$110.00	FAZ-D3-3-NA	\$114.00
4	FAZ-B4-3-NA	\$105.00	FAZ-C4-3-NA	\$110.00	FAZ-D4-3-NA	\$114.00
5	FAZ-B5-3-NA	\$105.00	FAZ-C5-3-NA	\$110.00	FAZ-D5-3-NA	\$114.00
6	FAZ-B6-3-NA	\$101.00	FAZ-C6-3-NA	\$104.00	FAZ-D6-3-NA	\$104.00
7	FAZ-B7-3-NA	\$101.00	FAZ-C7-3-NA	\$104.00	FAZ-D7-3-NA	\$104.00
8	FAZ-B8-3-NA	\$101.00	FAZ-C8-3-NA	\$104.00	FAZ-D8-3-NA	\$104.00
10	FAZ-B10-3-NA	\$101.00	FAZ-C10-3-NA	\$104.00	FAZ-D10-3-NA	\$104.00
13	FAZ-B13-3-NA	\$101.00	FAZ-C13-3-NA	\$104.00	FAZ-D13-3-NA	\$104.00
15	FAZ-B15-3-NA	\$101.00	FAZ-C15-3-NA	\$104.00	FAZ-D15-3-NA	\$104.00
16	FAZ-B16-3-NA	\$101.00	FAZ-C16-3-NA	\$104.00	FAZ-D16-3-NA	\$104.00
20	FAZ-B20-3-NA	\$65.00	FAZ-C20-3-NA	\$104.00	FAZ-D20-3-NA	\$104.00
25	FAZ-B25-3-NA	\$101.00	FAZ-C25-3-NA	\$104.00	FAZ-D25-3-NA	\$104.00
30	FAZ-B30-3-NA	\$101.00	FAZ-C30-3-NA	\$104.00	FAZ-D30-3-NA	\$104.00
32	FAZ-B32-3-NA	\$101.00	FAZ-C32-3-NA	\$114.00	FAZ-D32-3-NA	\$114.00



Single-Pole

FAZ-NA and FAZ-NA-L Single-Pole 240VAC Selection Guide						
Ampere Rating	B-Curve Part Number	Price	C-Curve Part Number	Price	D-Curve Part Number	Price
0.5	—		FAZ-C0P5-1-NA-L-SP	\$24.50	FAZ-D0P5-1-NA-L-SP	\$24.50
1	FAZ-B1-1-NA-L-SP	\$24.50	FAZ-C1-1-NA-L-SP	\$24.50	FAZ-D1-1-NA-L-SP	\$24.50
1.5	FAZ-B1P5-1-NA-L-SP	\$24.50	FAZ-C1P5-1-NA-L-SP	\$24.50	FAZ-D1P5-1-NA-L-SP	\$24.50
2	FAZ-B2-1-NA-L-SP	\$23.50	FAZ-C2-1-NA-L-SP	\$24.50	FAZ-D2-1-NA-L-SP	\$24.50
3	FAZ-B3-1-NA-L-SP	\$24.50	FAZ-C3-1-NA-L-SP	\$24.50	FAZ-D3-1-NA-L-SP	\$24.50
4	FAZ-B4-1-NA-L-SP	\$24.50	FAZ-C4-1-NA-L-SP	\$24.50	FAZ-D4-1-NA-L-SP	\$24.50
5	FAZ-B5-1-NA-L-SP	\$24.50	FAZ-C5-1-NA-L-SP	\$24.50	FAZ-D5-1-NA-L-SP	\$24.50
6	FAZ-B6-1-NA-L-SP	\$24.50	FAZ-C6-1-NA-L-SP	\$24.50	FAZ-D6-1-NA-L-SP	\$24.50
7	FAZ-B7-1-NA-L-SP	\$24.50	FAZ-C7-1-NA-L-SP	\$24.50	FAZ-D7-1-NA-L-SP	\$24.50
8	FAZ-B8-1-NA-L-SP	\$24.50	FAZ-C8-1-NA-L-SP	\$24.50	FAZ-D8-1-NA-L-SP	\$24.50
10	FAZ-B10-1-NA-L-SP	\$24.50	FAZ-C10-1-NA-L-SP	\$24.50	FAZ-D10-1-NA-L-SP	\$24.50
13	FAZ-B13-1-NA-L-SP	\$24.50	FAZ-C13-1-NA-L-SP	\$24.50	FAZ-D13-1-NA-L-SP	\$24.50
15	FAZ-B15-1-NA-L-SP	\$24.50	FAZ-C15-1-NA-L-SP	\$24.50	FAZ-D15-1-NA-L-SP	\$24.50
16	FAZ-B16-1-NA-L-SP	\$24.50	FAZ-C16-1-NA-L-SP	\$24.50	FAZ-D16-1-NA-L-SP	\$24.50
20	FAZ-B20-1-NA-L-SP	\$24.50	FAZ-C20-1-NA-L-SP	\$24.50	FAZ-D20-1-NA-L-SP	\$24.50
25	FAZ-B25-1-NA-L-SP	\$24.50	FAZ-C25-1-NA-L-SP	\$24.50	FAZ-D25-1-NA-L-SP	\$24.50
30	FAZ-B30-1-NA-L-SP	\$24.50	FAZ-C30-1-NA-L-SP	\$24.50	FAZ-D30-1-NA-L-SP	\$24.50
32	FAZ-B32-1-NA-L-SP	\$24.50	FAZ-C32-1-NA-L-SP	\$24.50	FAZ-D32-1-NA-L-SP	\$24.50
35	FAZ-B35-1-NA-SP	\$36.00	FAZ-C35-1-NA-SP	\$37.50	FAZ-D35-1-NA-SP	\$37.50
40	FAZ-B40-1-NA-SP	\$36.00	FAZ-C40-1-NA-SP	\$37.50	FAZ-D40-1-NA-SP	\$37.50
50	FAZ-B50-1-NA-SP	\$36.00	FAZ-C50-1-NA-SP	\$36.00	—	
63	FAZ-B63-1-NA-SP	\$36.00	FAZ-C63-1-NA-SP	\$36.00	—	

Note: Eaton product part numbers will contain a [.] instead of [P] and a [/] instead of a [-]. Example: FAZ-C0P5-3-NA = FAZ-C0.5/3-NA

Note: Eaton parts available for sale to North America locations only.

EATON FAZ-NA Series Selection Guide



Two-Pole

FAZ-NA and FAZ-NA-L Two-Pole 240VAC Selection Guide						
Ampere Rating	B-Curve Part Number	Price	C-Curve Part Number	Price	D-Curve Part Number	Price
0.5	—		FAZ-C0P5-2-NA-L	\$50.00	FAZ-D0P5-2-NA-L	\$50.00
1	FAZ-B1-2-NA-L	\$50.00	FAZ-C1-2-NA-L	\$50.00	FAZ-D1-2-NA-L	\$50.00
1.5	FAZ-B1P5-2-NA-L	\$50.00	FAZ-C1P5-2-NA-L	\$50.00	FAZ-D1P5-2-NA-L	\$50.00
2	FAZ-B2-2-NA-L	\$30.50	FAZ-C2-2-NA-L	\$50.00	FAZ-D2-2-NA-L	\$50.00
3	FAZ-B3-2-NA-L	\$50.00	FAZ-C3-2-NA-L	\$50.00	FAZ-D3-2-NA-L	\$50.00
4	FAZ-B4-2-NA-L	\$50.00	FAZ-C4-2-NA-L	\$50.00	FAZ-D4-2-NA-L	\$50.00
5	FAZ-B5-2-NA-L	\$50.00	FAZ-C5-2-NA-L	\$50.00	FAZ-D5-2-NA-L	\$50.00
6	FAZ-B6-2-NA-L	\$50.00	FAZ-C6-2-NA-L	\$50.00	FAZ-D6-2-NA-L	\$50.00
7	FAZ-B7-2-NA-L	\$50.00	FAZ-C7-2-NA-L	\$50.00	FAZ-D7-2-NA-L	\$50.00
8	FAZ-B8-2-NA-L	\$50.00	FAZ-C8-2-NA-L	\$50.00	FAZ-D8-2-NA-L	\$50.00
10	FAZ-B10-2-NA-L	\$50.00	FAZ-C10-2-NA-L	\$50.00	FAZ-D10-2-NA-L	\$50.00
13	FAZ-B13-2-NA-L	\$50.00	FAZ-C13-2-NA-L	\$50.00	FAZ-D13-2-NA-L	\$50.00
15	FAZ-B15-2-NA-L	\$50.00	FAZ-C15-2-NA-L	\$50.00	FAZ-D15-2-NA-L	\$50.00
16	FAZ-B16-2-NA-L	\$50.00	FAZ-C16-2-NA-L	\$50.00	FAZ-D16-2-NA-L	\$50.00
20	FAZ-B20-2-NA-L	\$50.00	FAZ-C20-2-NA-L	\$50.00	FAZ-D20-2-NA-L	\$50.00
25	FAZ-B25-2-NA-L	\$50.00	FAZ-C25-2-NA-L	\$50.00	FAZ-D25-2-NA-L	\$50.00
30	FAZ-B30-2-NA-L	\$50.00	FAZ-C30-2-NA-L	\$50.00	FAZ-D30-2-NA-L	\$50.00
32	FAZ-B32-2-NA-L	\$50.00	FAZ-C32-2-NA-L	\$50.00	FAZ-D32-2-NA-L	\$50.00
35	FAZ-B35-2-NA	\$71.00	FAZ-C35-2-NA	\$73.00	FAZ-D35-2-NA	\$73.00
40	FAZ-B40-2-NA	\$71.00	FAZ-C40-2-NA	\$73.00	FAZ-D40-2-NA	\$73.00
50	FAZ-B50-2-NA	\$71.00	FAZ-C50-2-NA	\$71.00	—	—
63	FAZ-B63-2-NA	\$71.00	FAZ-C63-2-NA	\$71.00	—	—



Three-Pole

FAZ-NA and FAZ-NA-L Three-Pole 240VAC Selection Guide						
Ampere Rating	B-Curve Part Number	Price	C-Curve Part Number	Price	D-Curve Part Number	Price
0.5	—		FAZ-C0P5-3-NA-L	\$72.00	FAZ-D0P5-3-NA-L	\$72.00
1	FAZ-B1-3-NA-L	\$72.00	FAZ-C1-3-NA-L	\$72.00	FAZ-D1-3-NA-L	\$72.00
1.5	FAZ-B1P5-3-NA-L	\$72.00	FAZ-C1P5-3-NA-L	\$72.00	FAZ-D1P5-3-NA-L	\$72.00
2	FAZ-B2-3-NA-L	\$72.00	FAZ-C2-3-NA-L	\$72.00	FAZ-D2-3-NA-L	\$72.00
3	FAZ-B3-3-NA-L	\$72.00	FAZ-C3-3-NA-L	\$72.00	FAZ-D3-3-NA-L	\$72.00
4	FAZ-B4-3-NA-L	\$72.00	FAZ-C4-3-NA-L	\$72.00	FAZ-D4-3-NA-L	\$72.00
5	FAZ-B5-3-NA-L	\$72.00	FAZ-C5-3-NA-L	\$72.00	FAZ-D5-3-NA-L	\$72.00
6	FAZ-B6-3-NA-L	\$72.00	FAZ-C6-3-NA-L	\$72.00	FAZ-D6-3-NA-L	\$72.00
7	FAZ-B7-3-NA-L	\$72.00	FAZ-C7-3-NA-L	\$72.00	FAZ-D7-3-NA-L	\$72.00
8	FAZ-B8-3-NA-L	\$72.00	FAZ-C8-3-NA-L	\$72.00	FAZ-D8-3-NA-L	\$72.00
10	FAZ-B10-3-NA-L	\$72.00	FAZ-C10-3-NA-L	\$72.00	FAZ-D10-3-NA-L	\$72.00
13	FAZ-B13-3-NA-L	\$72.00	FAZ-C13-3-NA-L	\$72.00	FAZ-D13-3-NA-L	\$72.00
15	FAZ-B15-3-NA-L	\$72.00	FAZ-C15-3-NA-L	\$72.00	FAZ-D15-3-NA-L	\$72.00
16	FAZ-B16-3-NA-L	\$72.00	FAZ-C16-3-NA-L	\$72.00	FAZ-D16-3-NA-L	\$72.00
20	FAZ-B20-3-NA-L	\$87.00	FAZ-C20-3-NA-L	\$72.00	FAZ-D20-3-NA-L	\$72.00
25	FAZ-B25-3-NA-L	\$72.00	FAZ-C25-3-NA-L	\$72.00	FAZ-D25-3-NA-L	\$72.00
30	FAZ-B30-3-NA-L	\$72.00	FAZ-C30-3-NA-L	\$72.00	FAZ-D30-3-NA-L	\$72.00
32	FAZ-B32-3-NA-L	\$72.00	FAZ-C32-3-NA-L	\$72.00	FAZ-D32-3-NA-L	\$72.00
35	FAZ-B35-3-NA	\$110.00	FAZ-C35-3-NA	\$114.00	FAZ-D35-3-NA	\$114.00
40	FAZ-B40-3-NA	\$110.00	FAZ-C40-3-NA	\$114.00	FAZ-D40-3-NA	\$114.00
50	FAZ-B50-3-NA	\$110.00	FAZ-C50-3-NA	\$110.00	—	
63	FAZ-B63-3-NA	\$110.00	FAZ-C63-3-NA	\$110.00	—	

Note: Eaton product part numbers will contain a [.] instead of [P] and a [/] instead of a [-]. Example: FAZ-C0P5-3-NA = FAZ-C0.5/3-NA

Note: Eaton parts available for sale to North America locations only.



FAZ-NA Series

Technical Specifications

FAZ-NA and FAZ-NA-L Miniature Circuit Breakers – UL/CSA				
		B-Curve	C-Curve	D-Curve
Short Circuit Trip Response		3-5 x I _n	5-10 x I _n	10-20 x I _n
Current Range		1-63 A	0.5-63 A	0.5-40 A
Maximum Voltage Ratings UL / CSA	0.5-32 A	277/480Y VAC (FAZ-NA), 240VAC (FAZ-NA-L)		
	35-63 A	240VAC		
	Per pole	48VDC		
	2 poles in series	96VDC Max		
Thermal Tripping Characteristics	Single pole	40°C [104°F]		
	Multi-pole			
Interrupting Ratings (@ maximum voltage)	1 pole	10kA Note: 14 kAIC at select amperages B and C curves (15-25 A) D curve (13-20 A)		
	2 pole			
	3 pole			
Rated Frequency		50/60 Hz		
Agency Approvals		UL File #E235139, CSA #204453		

Notes: Line voltage connection suitable for reverse feed

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

FAZ-NA and FAZ-NA-L Miniature Circuit Breaker - IEC				
		<i>B-Curve</i>	<i>C-Curve</i>	<i>D-Curve</i>
<i>Short Circuit Trip Response</i>		3-5 x I _n	5-10 x I _n	10-20 x I _n
<i>Current Range</i>		1-63 A	0.5-63 A	0.5-40 A
<i>Maximum Voltage Ratings - IEC/EN 60947-2</i>	<i>1 pole</i>	240/415 VAC		
	<i>2 pole / 3 pole</i>			
	<i>2 poles in series</i>			
<i>Thermal Tripping Characteristics</i>	<i>Single pole</i>	30°C [86°F]		
	<i>Multi-pole</i>			
<i>Interrupt Ratings (At Max Voltage)</i>		15kA		
<i>Rated Frequency</i>		50/60 Hz		

General Specifications

Lifespan / Endurance		20,000 (1 operation = ON/OFF)		
Operating Temperature		UL 489, CSA C22.2 No.5 = 40°C IEC 60947-2 = 30°C		
Shock (UL 489)		10g 20-25 ms		
Housing Material		Nylon		
Mounting Position		Vertical		
Weight	1 pole	0.3 lb (136g)		
	2 pole	0.6 lb (272g)		
	3 pole	0.9 lb (408g)		

Wire Size

Ampere Rating		Conductor Size	
0.5 - 63	One wire	18 to 6 AWG (0.75 to 13 mm ²)	
	Two wires	18 to 10 AWG (0.75 to 5 mm ²)	

Note: Eaton does not recommend the use of wire ferrules or crimping terminals. The wire gauges are specified above and in the installation instructions included with each circuit breaker.

Tightening Torque

Conductor Size	Tightening Torque
18-12 AWG	21 lb·in (2.4 N·m)
10-8 AWG	25 lb·in (2.8 N·m)
6AWG	36 lb·in (4.1 N·m)


EAT•N FAZ-NA Series Technical Data

Let-Through Energy


- The X axis shows the prospective short-circuit current levels.
- The Y axis indicates the actual let-through values at those prospective fault ratings for each FAZ-NA device plotted.

As can be interpreted from the bend in the plotted curves, each device acts to limit the damaging let-through energy at those values of short-circuit current.


Characteristic C (0.5-20A), 277V




Characteristic C (25-40A), 240V



Characteristic D (0.5-20A), 277V



Characteristic D (25-40A), 240V




EAT•N FAZ-NA Series Technical Data


Let-Through Energy

- The X axis shows the prospective short-circuit current levels.
 - The Y axis indicates the actual let-through values at those prospective fault ratings for each FAZ-NA device plotted.
- As can be interpreted from the bend in the plotted curves, each device acts to limit the damaging let-through energy at those values of short-circuit current.*


Characteristic B (1–32 A), 277 V




Characteristic B (35–63 A), 240 V



Characteristic C (35–63 A), 240 V



Characteristic D (35–63 A), 240 V



EAT•N FAZ-NA Series Technical Data


FAZ-NA Miniature Circuit Breakers Dimensions



FAZ-NA Series Technical Data

Influence of Ambient Temperature T on Load Carrying Capacity

Device Market Current Rating I_n (A) at 40°C	I_n (A) at Higher Ambient Temperature							
	15°C	20°C	25°C	30°C	40°C	50°C	55°C	60°C
0.5	0.6	0.5	0.5	0.5	0.5	0.5	0.5	0.5
1.0	1.1	1.1	1.1	1.0	1.0	1.0	0.9	0.9
1.5	1.7	1.6	1.6	1.6	1.5	1.4	1.4	1.4
2.0	2.2	2.2	2.1	2.1	2.0	1.9	1.9	1.8
3.0	3.3	3.2	3.2	3.1	3.0	2.9	2.9	2.8
4.0	4.4	4.3	4.2	4.2	4.0	3.8	3.8	3.7
5.0	5.5	5.4	5.3	5.2	5.0	4.8	4.7	4.6
6.0	6.6	6.5	6.4	6.2	6.0	5.8	5.6	5.5
7.0	7.7	7.6	7.4	7.3	7.0	6.7	6.6	6.4
8.0	8.8	8.6	8.5	8.3	8.0	7.7	7.5	7.4
10.0	11.0	10.8	10.6	10.4	10.0	9.6	9.4	9.2
13.0	14.3	14.0	13.8	13.5	13.0	12.5	12.5	12.0
15.0	16.5	16.2	15.9	15.6	15.0	14.4	14.1	13.8
16.0	17.6	17.3	17.0	16.6	16.0	15.4	15.0	14.7
20.0	22.0	21.6	21.2	20.8	20.0	19.2	18.8	18.4
25.0	27.5	27.0	26.5	26.0	25.0	24.0	23.3	23.0
30.0	33.0	32.4	31.8	31.2	30.0	28.8	28.2	27.6
32.0	35.2	34.6	33.9	33.3	32.0	30.7	30.1	29.4
35.0	38.5	37.8	37.1	36.4	35.0	33.6	32.9	32.2
40.0	44.0	43.2	42.4	41.6	40.0	38.4	37.6	36.8
50.0	55.0	54.0	53.0	52.0	50.0	48.0	47.0	46.0
63.0	69.3	68.0	66.8	65.5	63.0	60.5	59.2	58.0



I_L = Maximum Load
 T = Ambient Temperature
 I_N = Rated Current in Amps
 K_T = Load Factor

Maximum load I_L at ambient temperature T :
 $I_L(T) = I_n K_T(T)$

EAT•N FAZ-NA Series Accessories

Field Mountable Accessories

- Auxiliary switch
- Alarm switch
- Shunt trip
- No tools required for mounting



Z-NHK
Alarm/Aux Contact





Z-IHK-NA
Auxiliary Contact

		Z-NHK*	Z-IHK-NA
Price		\$37.50	\$30.00
Electrical Data			
Contact function		2 Form C (one set changeover) (SPDT)	1 NO + 1 NC (DPST)
Rated voltage		230VAC / 110V AC/DC	600VAC / 230VAC / 120VAC
Frequency		50/60 Hz	
Rated current		2A / 0.5 A	1.2 A / 2A / 6A
Rated thermal current I_{th} 60947-5-1		2A / 250VAC	6A / 250VAC
60947-5-1 Rated operational current I_e	Utilization category AC13	3A / 250VAC	
	Utilization category AC15	2A / 250VAC	
	Utilization category DC12	0.5 A / 110VDC	0.5 A / 110VDC 0.25 A / 220VDC
Rated insulation voltage U_i		250VAC	
Minimal operational voltage per Contact U_{min}		5VDC	
Minimum operational current I_{min}		10mA DC	10 mAAC/DC
Rated peak withstand voltage U_{imp} (1.2/50μ)		2.5 kV	4kV
Conditional short-circuit current I_k w/ backup fuse 6A		1kA	1kA
Mechanical Data			
Tripping indicator "electrical tripping"		Blue/white	—
Frame size		45mm	
Mounting		Onto FAZ-NA	
Degree of protection, built-in		IP40	
Terminal protection		Finger and hand touch safe according to BGV A3, OVE-EN 6	
Terminals		Lift terminals	
Terminal capacity		20-18 AWG (0.75 - 2.5 mm ²)	20-14 AWG (0.5 - 2.5 mm ²)
Terminal screws		M3 (Posidrive Z0 - Phillips)	
Fastening torque of terminal screws		7 lb-in (0.79 N·m)	Max. 10.6 lb-in (1.2 N·m)

*Voltage of the FAZ-NA circuit breaker is limited to 300V with contact installed.

Allowable Combinations of Accessories




EAT•N FAZ-NA Series Accessories

Shunt Trip Release

- Remote release for subsequent mounting onto FAZ-NA
- Additional installation of standard auxiliary switch is possible
- Position indicator red-green



FAZ-XAA-NA Series



Circuit Diagram

	FAZ-XAA-NA12-110V	FAZ-XAA-NA110-415V
Price	\$55.00	\$55.00
Electrical Data		
Can be mounted onto	FAZ-NA	
Operational voltage range	12-110 VAC 12-60 VDC	110-415 VAC 110-230 VDC
Maximum inrush current	15A	2.1 A
Frequency	50/60 Hz	
Mechanical Data		
Frame size	45mm	
Height	4.13 in (105mm)	
Width	0.69 in (17.5 mm)	
Weight	0.28 lb (127g)	
Mounting	Quick fastening with two lock-in positions on EN 50022	
Degree of protection, built-in	IP40	
Terminal protection	Finger and hand touch safe according to BGV A3, OVE-EN 6	
Terminals	Open mouthed/lift	
Terminal capacity, one and two wires	18-10 AWG (0.8 - 5.3 mm²)	
Agency Approval	UL File # E257181, CSA 204453	

Note: To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.


Lockout Attachment

Lockout Attachment				
Part Number	Description	Weight	Qty	Price
ZIS-SPE-1TE-3	Lockout attachment for Eaton FAZ-NA series supplementary protectors and FAZ-NA mini circuit breakers, suitable to prevent unauthorized activation of a de-energized circuit, accepts lock shackles up to 9/32 in. (7.1 mm) in diameter	0.10 lb (45g)	3	\$46.00



ZIS-SPE-1TE-3
Lockout Attachment

ZIS-SPE-1TE-3 Installation



EAT•N FAZ-NA Series Accessories


Busbar System

(Without auxiliary contacts)

Busbar System for FAZ-NA Series Miniature Circuit Breakers

Part Number	Price	Description
<u>ZSVUL16-1P-1TE6SP</u>	\$15.50	Busbar for connecting up to six (6) 1-pole FAZ-NA series circuit breakers
<u>ZSVUL16-1P-1TE12SP</u>	\$28.00	Busbar for connecting up to twelve (12) 1-pole FAZ-NA series circuit breakers
<u>ZSVUL16-1P-1TE18SP</u>	\$43.00	Busbar for connecting up to eighteen (18) 1-pole FAZ-NA series circuit breakers
<u>ZSVUL16-2P-2TE6SP</u>	\$17.50	Busbar for connecting up to three (3) 2-pole FAZ-NA series circuit breakers
<u>ZSVUL16-2P-2TE12SP</u>	\$35.00	Busbar for connecting up to six (6) 2-pole FAZ-NA series circuit breakers
<u>ZSVUL16-2P-2TE18SP</u>	\$52.00	Busbar for connecting up to nine (9) 2-pole FAZ-NA series circuit breakers
<u>ZSVUL16-3P-3TE6SP</u>	\$19.00	Busbar for connecting up to two (2) 3-pole FAZ-NA series circuit breakers
<u>ZSVUL16-3P-3TE12SP</u>	\$36.00	Busbar for connecting up to four (4) 3-pole FAZ-NA series circuit breakers
<u>ZSVUL16-3P-3TE18SP</u>	\$55.00	Busbar for connecting up to six (6) 3-pole FAZ-NA series circuit breakers

Note: FAZ-NA Busbar is not for use with FAZ supplementary protectors.






ZSVUL16-xP-xTExSP


Busbar Specifications

Description	UL489		IEC/EN60947-2
Operating Voltage	480VAC	96VDC	240/415 VAC
Frequency	50/60 Hz	n/a	50/60 Hz
Rated Impulse Withstand Uimp	n/a		9.5 kV
Max Current - Ie Fed From End	80A @ 40°C		80A @ 30°C
Cross Section	n/a		16 mm ²
Agency Approval	UL File #E257181		

Busbar Connection Diagrams



Note: Do not cut



FAZ-NA Series

EAT•N FAZ-NA Series Accessories

Busbar Accessories

Busbar Accessories for FAZ-NA Series Miniature Circuit Breakers

Part Number	Price	Description
<u>ZVBS-UL</u>	\$39.00	Busbar Shroud - covers for unused bus bar terminals, (10) 3-terminal covers per package
<u>ZVBS-UL-5</u>	\$22.00	Busbar Shroud - covers for unused bus bar terminals, (5) 3-terminal covers per package
<u>ZEK35-UL</u>	\$59.00	Wiring Lug, 2 - 14 AWG (35mm), 3 lugs per package
<u>ZEK35-UL-1</u>	\$20.00	Wiring Lug, 2 - 14 AWG (35mm), 1 lug per package





[ZVBS-UL](#)



[ZEK35-UL](#)

ZEK35-UL – Specifications

Description	UL489		IEC/EN60947-2
Operating Voltage	480VAC	96VDC	240/415 VAC
Frequency	50/60 Hz	n/a	50/60 Hz
Rated impulse withstand - U_{imp}	n/a		9.5 kV
Max Current - I_e	80A @ 40°C		80A @ 30°C
	#2 - 14 AWG		2.5 - 35 mm ²
	0.56 in		14mm
Agency Approval	UL File # E307559		

Note: To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.



ZEK35-UL – Tightening Torque

Tested According To	Cable Size	Tightening Torque
UL 486A	#14 AWG	M 20 lb·in (2.3 N·m)
UL 486B	#8 - 12 AWG	M 25 lb·in (2.8 N·m)
UL 486E	#6 - 1 AWG	35 lb·in (4 N·m)



FAZ-NA Series Accessories

Accessories Dimensions


in [mm]







ZNHK



ZIHK-NA



FAZ-XAA-NA-xxx


ZIHK-NA
Diagram

FAZ-NA Series Miniature Circuit Breakers Connection Diagrams


Single Pole



Two-Pole




Three-Pole




FAZ-NA Series Accessories

Accessories Dimensions *in [mm]*




FAZ-NA Busbar Length – in [mm]


Part Number	A	B
ZSVUL16-xP-xTE6SP	3.90 [99.0]	3.46 [88.0]
ZSVUL16-xP-xTE12SP	8.06 [204.6]	7.62 [193.6]
ZSVUL16-xP-xTE18SP	12.21 [310.2]	11.78 [299.2]



ZVBS-UL



ZEK35-UL



Please see our website www.AutomationDirect.com for complete engineering drawings. Dimensions are approximate. Not for construction purposes.

socomec

Innovative Power Solutions

Disconnect Switches



Compact UL 98 Non-Fusible Switches 30 - 100 Amp Range

- Touch safe
- DIN-rail or back-plate mounted
- Direct or external operation handle
- Double breaking per pole



UL 98 Non-Fusible Heavy Duty Switches 100 - 600 Amp Range

- Fully visible disconnection
- High thermal and dynamic withstand
- High electrical and mechanical endurance



UL 508 Non-Fusible Switches 16 - 100 Amp Range

- Compact and modular
- Direct or external operation
- DIN-rail or base mount
- Suitable as motor disconnect




UL 508 Enclosed Non-Fusible Switches 30 - 60 Amp Range

- 1 removable ground terminal
- Ability to add 1 power pole and 1 auxiliary contact
- NEMA/UL type 1, 3R, 12, 4, 4X
- Suitable as motor disconnect



UL 98 Manual Multipolar Load Switches 100 - 250 Amp Range

- Ideal for photovoltaic applications
- 600VDC per UL 98 / CSA
- 1000VDC per UL98B
- Up to 1000VDC per UL IEC 60947-3 characteristics



UL 489 Compact Fusible Disconnect Switches 30 Amp Rating

- Front operation
- Touch safe covers
- Voltage sensing terminals
- Up to 200kA SCCR



- #### UL 98 Fusible Disconnect Switches 30 - 600 Amp Range
- Front and side operation
 - Touch safe covers
 - Up to 200kA SCCR
 - Double break contact



To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page at www.AutomationDirect.com

Disconnect Switches

Introduction

UL®/CSA® Standards for Disconnect Switches

UL 98 – Enclosed and Deadfront Switches (CSA C22.2 No. 4)

These requirements cover enclosed or deadfront switches, with or without provision for fuses, at 600V or less. These products are used as disconnecting means without restrictions; they are heavy-duty products requiring 2 inches (50mm) minimum of creepage distance between phases, which gives maximum safety for users and installation. The short-circuit withstand of these products goes up to 200kA.

UL 489 – Molded Case Switches (CSA C22.22 No. 5)

These requirements cover molded case circuit breakers, molded case switches and fused molded case switches, rated at 600V or less and 6000A or less.

NFPA® 79 Electrical Standard for Industrial Machinery

The following types of machines are identified as industrial machinery:

- Metalworking machine tools, including machines that cut or form metal
- Plastics machinery
- Wood machinery, including woodworking, laminating and sawmill machines
- Assembly machines
- Material handling machines, including industrial robots and transfer machines
- Inspection and testing machines, including coordinate measuring and in-process gauging machines



UL® Standards for Electrical Machinery

UL 508 – Industrial Control Equipment (CSA C22.2 No. 14)

These requirements cover manual, magnetic and solidstate starters and controllers, overload relays, pushbuttons, selector switches and control lights. These products are smaller, requiring only a creepage distance between phases of 0.50 inch (12.7 mm). Their use as a disconnecting means is limited to local disconnection of motors. These products can be used as a disconnect means only when they have been additionally tested "suitable as motor disconnect." This additional testing ensures that the switch has a proper closing capacity on a short circuit.

UL 508 devices **cannot** be used as main disconnect of an electrical panel, e.g., at the entrance of control panels. A manual motor controller marked "suitable as motor disconnect" shall be installed only on the load side of the branch circuit protective device [UL 508A 30.3.3 and NEC 430.109 (6)].

Typical Control Panel



Meeting the requirements of UL508A and NFPA79

The disconnect shall be operable independent of the door position.

The disconnect must be operable, by qualified persons, independent of the door position without the use of accessory tools or devices.

Note: NFPA 79; Paragraph 5.3.3.1 (5).

An operating mechanism for the disconnecting means shall be operable independent of the door position without the use of accessory tools or devices.






Note: UL 508A; Paragraph 66.6.3 c.

Non-Fusible Disconnect Switches



Selection Guide

- Which application?
- Which function?
- Which operation handle?
- Which type of breaking?

Machine Control			Power Distribution	
UL 98 Compact Non-Fusible Disconnect Switches	UL 508 Non-Fusible Disconnect Switches*	UL 508 Non-Fusible Enclosed Disconnect Switches	UL 98 Non-Fusible Disconnect Switches	UL 98B DC Non-Fusible Disconnect Switches
				
22013003 22013006 22003010	22003000 , 22003001 22003002 , 22003003 22003004 , 22003006 22003008	22143503 22243503 22243506	27003011 , 27004011 27003021 , 27004021 27003041 , 27003060	27DC3011 27DC4011 27DC3021 27DC4021

Applications					
Main switchboard		✓	✓	✓	✓
Distribution panel		✓	✓	✓	✓
Emergency disconnect		✓	✓	✓	✓
Local safety disconnect (padlockable)		✓	✓	✓	✓
Photovoltaic disconnect					✓
Enclosed switches		✓	✓	✓	✓
Functions					
3/4 pole non-fusible disconnect switch		✓	✓	✓	✓
Characteristics					
Operation	Manual (rotating)	✓	✓	✓	✓
Direct operation handle	Front	✓	✓	✓	✓
External operation handle	Front	✓	✓	✓	✓
	Right side	✓	✓		
Indication of breaking	Positive break indication	✓	✓	✓	✓
Switch body	Modular	✓	✓		


* Note: These part numbers are direct replacements for previous part numbers with a "-UL" suffix. They have identical technical specs, form, fit and function. There is no change in agency approvals, the UL mark, listing, or File numbers E173959 and E201138.

Non-Fusible Disconnect Switches


Assembly of Accessories



Non-fusible 16 - 100A Disconnect Switches Accessories



Non-fusible 100 - 600A Disconnect Switches Accessories




SIRCO M UL 98

Compact Non-Fusible Disconnect Switches




To assemble a switch, please select:

Direct Operation



External Operation



UL 98 Compact Non-Fusible Disconnect Switches				
Part Number*	Description	Amp Rating	Voltage Rating	Price
22013003	Non-fusible rotary 3-pole disconnect switch, M3 frame size	30	600VAC	\$66.00
22013006		60	600VAC	\$77.00
22003010		100	600VAC	\$90.00

* These part numbers are direct replacements for previous part numbers with a "-UL" suffix. They have identical technical specs, form, fit and function. There is no change in agency approvals, the UL mark, listing, or File numbers E173959 and E201138.

Handles – Defeatable and Lockable						
Part Number	Description	Switch Body Rating (A)	Handle Color	Handle Type	NEMA/UL Type	Price
22995032	Mounts directly on switch, no shaft required*	30 - 100	Blue	M01	–	\$4.75
147D1111	External front and right side handles, shaft required	16 - 100	Black/Blue	S00	4, 4X	\$23.50
147E1111			Red/Yellow			\$23.50
14831111		16 - 100	Black/Blue	S0	1, 3R, 12	\$24.50
14841111			Red/Yellow			\$25.50
148D1111			Black/Blue		4, 4X	\$41.00
148E1111			Red/Yellow			\$41.00
140F2111			Black/Blue	S01	1, 3R, 12	\$38.50
140G2111			Red/Yellow			\$38.50
140D2111			Black/Blue		4, 4X	\$56.00
140E2111			Red/Yellow			\$56.00



* Not defeatable

Shafts for External Handles					
Part Number	Switch Body Rating (A)	Handle Type	Length (in)	Length (mm)	Price
14070515	16 - 100	S00, S0	5.9	150	\$6.00
14070520			7.9	200	\$7.00
14070532			12.6	320	\$7.75
14040520		S01	7.9	200	\$12.00
14040532			12.6	320	\$15.00
14040540			15.7	400	\$24.00



SIRCO M UL 98

Compact Non-Fusible Disconnect Switches




Shaft Guide for External Handle

Part Number	Description	Handle Type	Price
14190000	This accessory makes alignment connections between the shaft and handle easier. Allows up to 15mm misalignment tolerance. Required for a shaft length over 300mm. Included with longer shafts.	S00, S0	\$2.75
14290000		S01, S1, S2, S3	\$7.50

[14190000](#)

Additional Poles

Part Number*	Description	Switch Body Rating (A)	No. of Poles	Use	Price
22011003	Fourth pole module switched 600VAC 100kA SCCR	30	1	Adding one additional pole transforms a non-fusible disconnect switch from 3 poles to 4 poles	\$20.00
22011006	Fourth pole module switched 600VAC 65kA SCCR	60	1		\$23.00
22001010	Fourth pole module switched 600VAC 100kA SCCR	100	1		\$28.50
22005011	Solid neutral pole module unswitched 600VAC	30 - 100	1	Transforms the 3-pole switch into a 3-pole + solid neutral	\$24.00
22009011	Grounding pole module unswitched 600VAC	30 - 100	1	Adds 1 ground module pole to the switch-disconnector	\$24.00

[22011003](#)

4th Pole Configurations

* These part numbers are direct replacements for previous part numbers with a "-UL" suffix. They have identical technical specs, form, fit and function. There is no change in agency approvals, the UL mark, listing, or File numbers E173959 and E201138.

Terminal Shrouds


Part Number	Description	Switch Body Rating (A)	No. of Poles	Price
22941011	Terminal shroud line/load mount, 2 per pack, offers additional protection against direct contact with the terminals.	30 - 100	1	\$5.00
22943016		30 - 100	3	\$8.75

[22941011](#)

Auxiliary Contacts

Part Number*	Description	Switch Body Rating (A)	Contacts	Price
22990001	Auxiliary contact block module, 10A @ 240VAC, can be mounted on left or right side of switch, maximum 4 auxiliary contacts can be used (requires 2 modules)	16 - 100	1 NO / 1 NC	\$18.50
22990011		16 - 100	2 NO	\$20.50

* These part numbers are direct replacements for previous part numbers with a "-UL" suffix. They have identical technical specs, form, fit and function. There is no change in agency approvals, the UL mark, listing, or File numbers E173959 and E201138.

[22990001](#)

Auxiliary Contact Configurations

SIRCO M UL 98

Compact Non-Fusible Disconnect Switches



Technical Characteristics

Characteristics According to UL 98 / CSA 22.2#4			
DIN rail panel	22013003	22013006	22003010
General use rating (A)	30	60	100
Short-circuit rating at 480VAC (kA) ¹	100	100	100
Short-circuit rating at 600VAC (kA) ¹	100	100	25
Type of fuse	J	J	J
Max fuse rating (A)	30	60	100
Max. motor hp / FLA 3-phase motor max.			
220-240 VAC	10 / 28	20 / 54	20 / 54
440-480 VAC	20 / 27	40 / 52	50 / 65
600VAC	25 / 27	50 / 52	50 / 52
Max. motor hp / FLA 1-phase motor max.			
120VAC	2 / 24	3 / 34	5 / 56
240VAC	5 / 28	10 / 50	10 / 50
Wire type/temperature	Cu / 75°C (167°F)		
Product weight – lb (kg)	1.3 (0.6)		
Wire range			
Solid (AWG)	#12-10	#12-10	#12-10
Torque – lb·in (N·m)	35.4 (4)	35.4 (4)	35.4 (4)
Stranded (AWG)	#10-1	#10-1	#10-1
Torque – lb·in (N·m)	35.4 (4)	35.4 (4)	35.4 (4)
Stranded (AWG)	1/0	1/0	1/0
Torque – lb·in (N·m)	39.8 (4.5)	39.8 (4.5)	39.8 (4.5)
Stranded (AWG)	2/0	2/0	2/0
Torque – lb·in (N·m)	44.3 (5)	44.3 (5)	44.3 (5)
Mechanical characteristics			
Endurance (number of operating cycles)	10,000	10,000	10,000
Operating torque (lb·in / N·m)	12.4 / 1.4	12.4 / 1.4	12.4 / 1.4
Environmental - switch body			
Operating temperature ²	-20°C to 70°C (-4°F to +158°F)		
Flammability rating	UL 94-V0		
Mounting	35mm DIN rail or panel mount		
Auxiliary contacts			
Electrical characteristics	A300	A300	A300
Agency approvals			
UL file # E201138 (UL 98), CSA file # 112964 (C22.2 NO. 14)			

¹ Short-circuit rating achieved when used with corresponding fuse type and max fuse rating.

² At temperatures above 40°C, the current rating of the switch has to be de-rated 1% per °C over 40°C. Example: At 60°C a 100A switch is rated 80A.

Note: These part numbers are direct replacements for previous part numbers with a "-UL" suffix. They have identical technical specs, form, fit and function. There is no change in agency approvals, the UL mark, listing, or File numbers E173959 and E201138.

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

SIRCO M UL 98

Compact Non-Fusible Disconnect Switches



Technical Characteristics (Continued)

Characteristics According to IEC 60647-3			
	<u>22013003</u>	<u>22013006</u>	<u>22003010</u>
Thermal current I_{th} at 40°C (A)	30	60	100
Rated insulation voltage U_i (V)	800	800	800
Rated impulse withstand voltage U_{imp} (kV)	8	8	8
Rated operational currents I_e			
400VAC / AC-22A utilization category (A)¹	32	63	100
400VAC / AC-23A utilization category (A)¹	32	63	100
690VAC / AC-22A utilization category (A)¹	32	63	80
690VAC / AC-23A utilization category (A)¹	32	63	63
Operational power in AC-23 (kW)^{2/3}			
@ 400VAC without prebreak AC in AC-23	15	30	45
@ 500VAC without prebreak AC in AC-23	15	30	45
@ 690VAC without prebreak AC in AC-23	18.5	30	45
Overload capacity (U_e 415VAC)			
Rated short-circuit making capacity I_{cm} (kA peak)⁴	12	12	12
Connection			
Min. connection section (mm²)	2.5	2.5	10
Max. connection section (mm²)	70	70	70

¹Category with index A = frequent operation.

²A/B: Category with index A = frequent operation - Category with index B = infrequent operation.

³The power value is given for information only, the current values vary from one manufacturer to another.

⁴For a rated operating voltage U_e = 400VAC

Note: These part numbers are direct replacements for previous part numbers with a "-UL" suffix. They have identical technical specs, form, fit and function. There is no change in agency approvals, the UL mark, listing, or File numbers E173959 and E201138.



SIRCO M UL 98

Compact Non-Fusible Disconnect Switches




Dimensions [inches/mm]

Direct operation with handle




1. Location for: 1 switched fourth pole module (1 per device max), or 1 unswitched neutral pole module, or 1 auxillary contact module
 2. Position for auxillary contact module
- NOTE: MAX OF 2 ADDITIONAL BLOCK MODULES

External front operation



External side operation



Dimensions

Switch Body Rating (A) / Frame Size	Units	Overall Dimensions				Terminal Shrouds AC	Switch Body				Switch Mounting		Connection
		D min	D Max	E min	E max		F	F1	G	J	M	N	
100 / M3	in	1.18	7.87	3.94	14.65	7.44	3.07	1.02	4.91	0.51	1.02	5.17	1.02
	mm	30	201	100	372	189	78	26	124.6	13	26	131.4	26

Please see our website www.AutomationDirect.com for complete engineering drawings.

SIRCO UL 98 Non-Fusible Disconnect Switches



To assemble a switch, please select:

Direct Operation

External Operation



+



OR



+



+



Switch Body

Direct Handle

Switch Body

Shaft

External Handle

UL 98 Non-Fusible Disconnect Switches

Part Number	Description	Amp Rating	# of Poles	Price
27003011	Non-fusible 600VAC rotary disconnect switch, 200kA	100	3	\$194.00
27004011			4	\$227.00
27003021		200	3	\$301.00
27004021			4	\$332.00
27003041		400	3	\$721.00
27003060		600	3	\$1,247.00

Handles – Defeatable and Lockable

Part Number	Description	Switch Body Rating (A)	Handle Color	Handle Type	NEMA/UL Type	Price
26995052	Mounts directly on switch, no shaft required*	100-400	Black	—	—	\$20.00
37996012		600	Black	—	—	\$40.00
142F2111	External front handles, shaft required	100-400	Black/Blue	S2	1, 3R, 12	\$54.00
142G2111			Red/Yellow			\$54.00
142D2111			Black/Blue		4, 4X	\$75.00
142E2111			Red/Yellow			\$75.00
143D3111		600	Black/Bue	S3		\$89.00
143E3111			Red/Yellow		\$89.00	
143F3111			Black/Blue		1, 3R, 12	\$70.00
143G3111			Red/Yellow			\$70.00
142D2911			External heavy duty front handles, shaft required**		100-400	Black/Blue
142E2911	Red/Yellow	\$94.00				
143D3911	600	Black/Blue		S3	\$123.00	
143E3911		Red/Yellow			\$123.00	

* Not defeatable.

** Heavy duty handles have larger metal hasp to accommodate multiple locking devices.



Shafts for External Handles

Part Number	Switch Body Rating (A)	Handle Type	Length (in)	Length (mm)	Price
14001020	100-400	S1, S2	7.9	200	\$14.00
14001032			12.6	320	\$15.00
14001040			15.7	400	\$16.50
14011520	600	S3	7.9	200	\$17.50
14011532			12.6	320	\$23.50
14011540			15.7	400	\$26.50



SIRCO UL 98 Non-Fusible Disconnect Switches



Shaft Guide for External Handle

Part Number	Description	Fits Handle Type	Price
<u>14290000</u>	This accessory makes alignment connections between the shaft and handle easier. Allows up to 15mm misalignment tolerance. Required for a shaft length over 300mm. Included with longer shafts	S01, S1, S2, S3	\$7.50

[14290000](#)

Auxiliary Contacts

Part Number	Description	Switch Body Rating (A)	Type	Contacts	Price
<u>27990021</u>	Auxiliary Contact Block: 1 Form C, 10A @ 125 VAC	100-600	C Type standard level	1 NO / 1 NC	\$15.00
<u>27990022</u>	Auxiliary Contact Block: 1 Form C, 10A @ 125 VAC, 2/pk			1 NO / 1 NC	\$20.00
<u>27990121</u>	Auxiliary Contact Block: 1 Form C, 1A @ 125 VAC, low impedance		C Type low impedance	1 NO / 1 NC	\$17.00
<u>27990122</u>	Auxiliary Contact Block: 1 Form C, 1A @ 125 VAC, low impedance, 2/pk			1 NO / 1 NC	\$27.50

[27990021](#)

Terminal Screens

Part Number	Description	Switch Body Rating (A)	No. of Poles	Position	Price
<u>27983021</u>	Terminal screens provide line or load protection against direct contact with terminals or connection parts.	100-250	3	Line	\$23.50
<u>27988021</u>				Load	\$23.50
<u>27984021</u>			4	Line or load	\$27.50
<u>27983041</u>		400	3	Line	\$35.00
<u>27988041</u>				Load	\$35.00
<u>27983060*</u>		600		Load	\$78.00

[27983021](#)

* Load side screen, the line side is included with the switch.

Terminal Lugs

Part Number	Description	Switch Body Rating (A)	Wire Range	Lugs per kit	No cables per lug	Price
<u>39542020</u>	Terminal lug kits allow for the connection of bare copper cables on to the terminals (no spade lugs). Cable type Cu/Al.	100-250	#6 - 300MCM	2	1	\$20.00
<u>39543020</u>				3		\$29.50
<u>39544020</u>				4		\$38.50
<u>39543040</u>		400	#4 - 600MCM	3	2	\$76.00
<u>39543041</u>			2x (#6 - 350MCM)			\$103.00
<u>39543060</u>		600	2x (#2 - 600MCM)			\$155.00

[39542020](#)

SIRCO UL 98 Non-Fusible Disconnect Switches



Technical Characteristics

Characteristics According to UL 98 / CSA 22.2#4				
	<u>27003011</u> <u>27004011</u>	<u>27003021</u> <u>27004021</u>	<u>27003041</u>	<u>27003060</u>
General use rating (A)	100	200	400	600
Short-circuit rating at 600VAC (kA)	200	200	200	200
Type of fuse	J	J	J	J
Max fuse rating (A)	100	200	400	600
Max. motor hp / FLA 3-phase motor max.				
220-240 VAC	30 / 80	75 / 192	125 / 312	200 / 480
440-480 VAC	75 / 96	150 / 180	250 / 302	400 / 477
600VAC	100 / 99	200 / 192	350 / 336	350 / 336
Max. motor hp / FLA 1-phase motor max.				
240VAC	10 / 50	10 / 50	–	–
Max. motor hp / DC FLA motor max.				
120VDC ¹	10 / 76	15 / 112	20 / 148	20 / 148
250VDC ²	15 / 55	15 / 55	50 / 173	50 / 173
Wire type/temperature	Cu / 75°C (167°F)			
Product weight – lb (kg)				
3-pole	4.2 (1.91)	4.2 (1.91)	10.0 (4.6)	18.1 (8.2)
4-pole	5.0 (2.3)	5.0 (2.3)	12.3 (5.6)	23.9 (10.9)
Wire range				
Stranded (AWG)	#6-300MCM	#6-300MCM	#4-600MM	(2) #2-600MCM
Torque – lb·in (N·m)	275 (31)	275 (31)	550 (62)	375 (42.4)
Stranded (AWG)	–	–	(2) 1/0-250MCM	–
Torque – lb·in (N·m)	–	–	550 (62)	–
Stranded (AWG)	–	–	(2) #6-2	–
Torque – lb·in (N·m)	–	–	200 (22.6)	–
Stranded (AWG)	–	–	(2) #1-350MCM	–
Torque – lb·in (N·m)	–	–	375 (42.4)	–
Environmental – switch body				
Operating temperature ³	-20°C to 70°C (-4°F to +158°F)			
Flammability rating	UL 94-V0			
Mechanical characteristics				
Endurance (number of operating cycles)	10,000	8,000	6,000	6,000
Operating torque (lb·in / N·m)	88.5 / 10	88.5 / 10	128.3 / 14.5	327.5 / 37
Mounting	Panel mount			
Auxiliary contacts				
Electrical characteristics	A300	A300	A300	A600
Approvals				
UL file # E201138 (UL 98), CSA file # 112964 (C22.2 NO. 4)				

¹ 2 pole in series² 3 pole in series³ Temperatures above 40°C, the current rating of the switch has to be de-rated 1% per °C over 40°C. Example, at 60°C a 100A switch is rated 80A

Note: Short-circuit rating achieved when used with corresponding fuse type and max fuse rating.

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

SIRCO UL 98 Non-Fusible Disconnect Switches



Technical Characteristics

Characteristics According to IEC 60647-3				
	<u>27003011</u> <u>27004011</u>	<u>27003021</u> <u>27004021</u>	<u>27003041</u>	<u>27003060</u>
Thermal current I_{th} at 40°C (A)	100	200	400	600
Rated insulation voltage U_i (V)	1000	1000	1000	1000
Rated impulse withstand voltage U_{imp} (kV)	12	12	12	12
Rated operational currents I_e				
400VAC / AC-22A utilization category (A) ¹	100	200	400	630
400VAC / AC-23A utilization category (A) ¹	100	200	400	630
690VAC / AC-22A utilization category (A) ¹	100	200	400	500
Connection				
Min. Cu cable cross section (mm ²)	35	70	185	2 x 150
Min. Cu busbar (mm ²)	–	–	–	2 x 30 x 5
690VAC / AC-23A utilization category (A) ¹	100	200	315	200
Operational power in AC-23 (kW)^{2/3}				
@ 400VAC without prebreak AC in AC-23	51	100	220	355
@ 500VAC without prebreak AC in AC-23	63	140	280	450
@ 690VAC without prebreak AC in AC-23	90	185	185	185
Overload capacity (U_e 415VAC)				
Rated short-circuit making capacity I_{cm} (kA peak) ⁴	17.6	32	48	48

¹Category with index A = frequent operation.

²A/B: Category with index A = frequent operation - Category with index B = infrequent operation.

³The power value is given for information only, the current values vary from one manufacturer to another.


⁴For a rated operating voltage U_e = 400VAC

SIRCO UL 98 Non-Fusible Disconnect Switches




Dimensions [inches/mm]

27003011, 27004011, 27003021, 27004021, 27003041



Mounting Orientation




Note: The switch will operate correctly when rotated clockwise 90 degrees.
The switch will not operate correctly when rotated counterclockwise 90 degrees.

Dimensions

Switch Body Rating (A)	Unit	Overall Dims	Terminal Shrouds			Switch Body					Switch Mounting					Connection							
		C	AC	AD	F 3p	F 4p	H	J1 3p	J1 4p	K	M 3p	M 4p	N	R1	R2	T	U	V	W	Y	Z	AA	CA
100	in	3.72	3.05	10.1	7.09	9.06	4.22	2.17	4.13	1.8	6.3	8.27	5.31	0.35	0.27	1.97	0.98	1.18	0.43	0.14	1.35	6.3	0.6
	mm	94.6	77.5	256	180	230	107	55	105	45.6	160	210	135	9	7	50	25	30	11	3.5	34.4	160	15
200	in	3.72	3.05	10.1	7.09	9.06	4.22	2.17	4.13	1.8	6.3	8.27	5.31	0.35	0.27	1.97	0.98	1.18	0.43	0.14	1.35	6.3	0.6
	mm	94.6	77.5	256	180	230	107	55	105	45.6	160	210	135	9	7	50	25	30	11	3.5	34.4	160	15
400	in	4.92	4.15	16	9.05	–	6.53	2.95	–	2.65	8.26	–	7.67	0.35	0.27	2.56	1.77	1.97	0.43	0.2	2.08	10.2	0.8
	mm	128	115	406	230	–	166	75	–	67.5	210	–	195	9	7	65	45	50	13	5	53	260	20

27003060



Dimensions


Switch Body Rating (A)	Unit	Terminal Shrouds	Switch Body					Switch Mounting				Connection	
		AC	F 3p	F 4p	H	J1 3p	J1 4p	M 3p	M 4p	N	N1	AA	Z
600	in	18.12	11	—	5.5	5	—	10.03	—	6.88	2.34	12.6	1.85
	mm	460	280	—	140	127.5	—	255	—	175	59.5	320	47

Please see our website www.AutomationDirect.com for complete engineering drawings.

SIRCO M UL 508 Non-Fusible Disconnect Switches



To assemble a switch, please select:



UL 508 Non-Fusible Disconnect Switches				
Part Number*	Description	Switch Body Rating (A)	# of Poles	Price
22003000	Non-fusible UL 508 disconnect rotary 600VAC disconnect switch	16	3	\$25.00
22003001		20	3	\$26.50
22003002		25	3	\$29.00
22003003		32	3	\$30.00
22003004		40	3	\$30.50
22003006		63	3	\$40.50
22003008		80	3	\$45.00
22003009		100	3	\$58.00

* These part numbers are direct replacements for previous part numbers with a "-UL" suffix. They have identical technical specs, form, fit and function. There is no change in agency approvals, the UL mark, listing, or File number E173959.

Handles – Defeatable and Lockable						
Part Number	Description	Switch Body Rating (A)	Handle Color	Handle Type	NEMA/ UL Type	Price
22995012	Direct operation handle, shaft not required*	16 - 100	Blue	M00	–	\$3.00
14731111	Front and right side handles I - O, shaft required		Black/Blue	S00	1, 3R, 12	\$14.50
14741111			Red/Yellow			\$14.50
147D1111			Black/Blue	4, 4X	\$23.50	
147E1111			Red/Yellow		\$23.50	
14831111			Black/Blue	S0	1, 3R, 12	\$24.50
14841111			Red/Yellow			\$25.50
148D1111			Black/Blue		4, 4X	\$41.00
148E1111			Red/Yellow			\$41.00
140F2111			Black/Blue	S01	1, 3R, 12	\$38.50
140G2111			Red/Yellow			\$38.50
140D2111			Black/Blue		4, 4X	\$56.00
140E2111			Red/Yellow			\$56.00

* Not defeatable



Shafts for External Handles						
Part Number	Description	Switch Body Rating (A)	Handle Type	Length		Price
				in	mm	
14070515	For 3/4-pole switches: shafts are for external front and side handle	16 - 100	S00, S0	5.9	150	\$6.00
14070520				7.9	200	\$7.00
14070532				12.6	320	\$7.75
14040520	For 3/4-pole switches: shafts are for external front and side handle.		S01	7.9	200	\$12.00
14040532				12.6	320	\$15.00
14040540				15.7	400	\$24.00



SIRCO M UL 508 Non-Fusible Disconnect Switches




Shaft Guide for External Handle

Part Number	Description	Fits Handle Type	Price
14190000	This accessory makes alignment connections between the shaft and handle easier. Allows up to 15mm misalignment tolerance. Required for a shaft length over 300mm. Included with longer shafts.	S0, S00	\$2.75
14290000		S01, S1, S2, S3	\$7.50

[14190000](#)

Additional Poles

Part Number*	Description	Switch Body Rating (A)	No. of Poles	Use	Price
22001000	Module switched 4th pole	16	1	Transforms a 3-pole switch into a 4-pole	\$14.50
22001001		20			\$15.50
22001002		25			\$15.50
22001003		32			\$17.00
22001004		40			\$18.50



4th Pole Configurations

* These part numbers are direct replacements for previous part numbers with a "-UL" suffix. They have identical technical specs, form, fit and function. There is no change in agency approvals, the UL mark, listing, or File number E173959.

Terminal Shrouds

Part Number	Description	Switch Body Rating (A)	No. of Poles	Price
22941005	Terminal shroud line/load mount, 2 per pack, offers additional protection against direct contact with the terminals.	16-40	1	\$3.00
22943005			3	\$4.75
22941009		63-100	1	\$3.50
22943009			3	\$6.00


[22941005](#)

Auxiliary Contacts

Part Number*	Description	Switch Body Rating (A)	Contacts	Price
22990001	Auxiliary contact block module, 10A @ 240VAC, can be mounted on left or right side of switch, maximum 4 auxiliary contacts can be used (requires 2 modules).	16 - 100	1 NO / 1 NC	\$18.50
22990011		16 - 100	2 NO	\$20.50

[22990001](#)

* These part numbers are direct replacements for previous part numbers with a "-UL" suffix. They have identical technical specs, form, fit and function. There is no change in agency approvals, the UL mark, listing, or File number E173959.



Auxiliary Contact Configurations

Conversion Kit

Part Number	Description	Switch Body Rating (A)	Price
22096009	Front mount transfer switch (2/4 pole) conversion kit. Open center transition (I-O-II).	16 - 100	\$27.50
22696009	Front mount multi-pole (6/8 pole) conversion kit.	16 - 100	\$24.50

[22096009](#)

Door Mounting Kit

Part Number	Description	Switch Body Rating (A)	No. of Poles	Price
22993409	This kit enables direct mounting of the switch on the panel door or on the right or left side of the panel. For use with S0 and S00 handles only.	16-100	3/4	\$6.00

[22993409](#)

SIRCO M UL 508 Non-Fusible Disconnect Switches



Technical Characteristics

Characteristics According to UL 508 / CSA 22.2#4								
	22003000	22003001	22003002	22003003	22003004	22003006	22003008	22003009
General use rating (A)	16	20	25	32	40	63	80	100
Short-circuit rating at 600VAC (kA) ¹	65	65	65	65	10 / 65	50 / 65	50 / 65	50 / 65
Type of fuse	J	J	J	J	J	J	J	J
Max fuse rating (A)	30	30	30	30	60 / 30	100 / 60	100 / 60	100 / 60
Max. motor hp / FLA 3-phase motor max.								
208VAC	3 / 10.6	5 / 16.7	7.5 / 24.2	7.5 / 24.2	7.5 / 24.2	15 / 46.2	15 / 46.2	15 / 46.2
220-240 VAC	5 / 15.2	5 / 15.2	7.5 / 22	7.5 / 22	7.5 / 22	20 / 54	20 / 54	20 / 54
440-480 VAC	10 / 14	10 / 14	15 / 21	20 / 27	20 / 27	40 / 52	40 / 52	40 / 52
600VAC	10 / 11	15 / 17	20 / 22	25 / 27	25 / 27	40 / 41	40 / 41	40 / 41
Wire type / temperature	Cu / 167°F (75°C)							
Product weight – lb (kg)	0.5 (0.2)					0.7 (0.32)		
Wire range								
Solid (AWG) - 1 wire	#14-10	#14-10	#14-10	#14-10	#14-10	#14-10	#14-10	#14-10
Torque - lb·in (N·m)	26.5 (3)	26.5 (3)	26.5 (3)	26.5 (3)	26.5 (3)	39.8 (4.5)	39.8 (4.5)	
Solid (AWG) - 2 wire	(2) #12	(2) #12	(2) #12	(2) #12	(2) #12	(2) #12	(2) #12	(2) #12
Torque - lb·in (N·m)	26.5 (3)	26.5 (3)	26.5 (3)	26.5 (3)	26.5 (3)	39.8 (4.5)	39.8 (4.5)	
Stranded (AWG) - 1 wire	#14-4	#14-4	#14-4	#14-4	#14-4	#14-1	#14-1	#14-1
Torque - lb·in (N·m)	26.5 (3)	26.5 (3)	26.5 (3)	26.5 (3)	26.5 (3)	39.8 (4.5)	39.8 (4.5)	
Stranded (AWG) - 2 wire	(2) #14-12	(2) #14-12	(2) #14-12	(2) #14-12	(2) #14-12	(2) #10-6	(2) #10-6	(2) #10-6
Torque - lb·in (N·m)	26.5 (3)	26.5 (3)	26.5 (3)	26.5 (3)	26.5 (3)	39.8 (4.5)	39.8 (4.5)	
Environmental – switch body								
Operating temperature ²	-20°C to 70°C (-4°F to +158°F)							
Flammability rating	UL 94-V0							
Mechanical characteristics								
Endurance (# of operating cycles)	10,000	10,000	10,000	10,000	10,000	10,000	10,000	10,000
Operating torque (lb·in / N·m)	7 / 0.8	7 / 0.8	7 / 0.8	7 / 0.8	7 / 0.8	8.9 / 1	8.9 / 1	8.9 / 1
Mounting	DIN rail or panel mount							
Auxiliary contacts								
Electrical characteristics	A300	A300	A300	A300	A300	A300	A300	A300
Agency approvals								
UL file # E173959 (UL 508, C22.2 NO. 14) Manual motor controller "suitable as motor disconnect" CE2011/65/EU								

¹ Short-circuit rating achieved when used with corresponding fuse type and max fuse rating.

² At temperatures above 40°C, the current rating of the switch has to be de-rated 1% per °C over 40°C. Example: At 60°C a 100A switch is rated 80A.

Note: These part numbers are direct replacements for previous part numbers with a "-UL" suffix. They have identical technical specs, form, fit and function. There is no change in agency approvals, the UL mark, listing, or File number E173959.

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

SIRCO M UL 508 Non-Fusible Disconnect Switches



Technical Characteristics

Characteristics According to IEC 60647-3									
	22003000	22003001	22003002	22003003	22003004	22003006	22003008	22003009	
General use rating (A)									
Thermal current I _{th} at 40°C (A)	16	20	25	32	40	63	80	100	
Rated insulation voltage U _i (V)	800	800	800	800	800	800	800	800	
Rated impulse withstand voltage U _{imp} (kV)	8	8	8	8	8	8	8	8	
Rated operational currents I_e									
415VAC AC-23A / AC-23B utilization category (A/B) ¹	16 / 16	20 / 20	25 / 25	32 / 32	40 / 40	63 / 63	80 / 80	80 / 80	
500VAC AC-22A / AC-22B utilization category (A/B) ¹	16 / 16	20 / 20	25 / 25	32 / 32	40 / 40	63 / 63	80 / 80	-	
500VAC AC-23A / AC-23B utilization category (A/B) ¹	16 / 16	20 / 20	25 / 25	25 / 25	25 / 25	63 / 63	63 / 63	-	
690VAC AC-21A / AC-21B utilization category (A/B) ¹	16 / 16	20 / 20	25 / 25	32 / 32	40 / 40	63 / 63	80 / 80	100 / 100	
690VAC AC-22A / AC-22B utilization category (A/B) ¹	16 / 16	20 / 20	25 / 25	32 / 32	32 / 40	40 / 63	63 / 80	-	
690VAC AC-23A / AC-23B utilization category (A/B) ¹	16 / 16	20 / 20	25 / 25	25 / 25	25 / 25	40 / 40	40 / 40	-	
Operational power in AC-23 (kW)									
@ 400VAC without prebreak AC in AC-23 ^{1/2}	7.5	9	11	15	18.5	30	37	-	
@ 500VAC without prebreak AC in AC-23 ^{1/2}	7.5	9	11	15	15	30	37	-	
@ 690VAC without prebreak AC in AC-23 ^{1/2}	7.5	11	15	18.5	18.5	30	37	-	
Fuse protected short-circuit withstand (kA rms prospective)									
Prospective short-circuit current (kA rms) ³	50	50	50	50	50	50	50	25	
Associated fuse rating (A) ³	16	20	25	32	40	63	80	100	
Overload capacity (U_e 415VAC)									
Rated short-time withstand current 0.3 s. I _{cw} (kA rms) ³	2.5	2.5	2.5	2.5	2.5	3	3	1.5	
Rated short-circuit making capacity I _{cm} (kA peak) ³	6	6	6	6	6	9	9	2.1	
Connection									
Minimum Cu cable cross section (mm ²)	1.5	1.5	1.5	1.5	1.5	2.5	2.5	2.5	
Maximum Cu cable cross section (mm ²)	16	16	16	16	16	35	35	35	
Tightening torque min/max (N·m)	2 / 2.2	2 / 2.2	2 / 2.2	2 / 2.2	2 / 2.2	3.5 / 3.85	3.5 / 3.85	3.5 / 3.85	

¹A/B: Category with index A = frequent operation - Category with index B = infrequent operation.

²The power value is given for information only, the current values vary from one manufacturer to another.

³For a rated operating voltage U_e = 400VAC

Note: These part numbers are direct replacements for previous part numbers with a "-UL" suffix. They have identical technical specs, form, fit and function. There is no change in agency approvals, the UL mark, listing, or File number E173959.


SIRCO M UL 508 Non-Fusible Disconnect Switches




Dimensions

Inches [mm]


Switch with direct handle



Switch with external handle side operation



Switch with external handle front operation



Dimensions

Switch Body Rating (A)	Units	Overall Dimensions				Terminal Shrouds AC	Switch Body				Switch Mounting		Connection
		D min	D max	E min	E max		F	F1	G	J	M	N	
16 - 40	in	1.18	9.25	3.94	14.64	4.33	1.77	0.59	2.67	0.59	1.18	2.95	0.59
	mm	30	235	100	372	110	45	15	68	15	30	75	15
63 - 100	in	1.18	9.25	3.94	14.64	4.33	2.06	0.69	2.99	0.69	1.38	3.35	0.69
	mm	30	235	100	372	110	52.5	17.5	76	17.5	35	85	17.5

Please see our website www.AutomationDirect.com for complete engineering drawings.

SIRCO M UL 508 Enclosed Non-Fusible Disconnect Switches



Our enclosed UL 508 switches allow for the safe control and disconnection of any motor application.

General characteristics


- Gray enclosure with red handle
- Equipped with a 3-pole SIRCO M
- 1 removable ground terminal
- Possibility of adding 1 power pole and 1 auxiliary contact
- Operating temperature -4° to +158°F (-20° to +70°C)
- Polycarbonate plastic
- Flammability rating UL94-5VA
- NEMA/UL Type 1, 3R, 4, 4X, 12

UL 508 Enclosed Non-Fusible Disconnect Switches						Accessories*		
Part Number	Enclosure Rating (A)	No. of Poles	Enclosure Size	Weight lb (kg)	Price	Switched 4th Pole Module	Auxiliary Contacts	Terminal Shrouds (Line & Load)
22143503	30	3	1	1.25 (0.56)	\$119.00	1P 22001003 \$17.00	1 NO / 1 NC 22990001 \$18.50	1P 22941005 \$3.00
22243503			2	1.60 (0.72)	\$138.00			3P 22943005 \$4.75
22243506	60	3	2	1.80 (0.82)	\$164.00	—		1P 22941009 \$3.50
								3P 22943009 \$6.00

Note: 2294100x fits 4th pole module only.

* These part numbers are direct replacements for previous part numbers with a "-UL" suffix. They have identical technical specs, form, fit and function. There is no change in agency approvals, the UL mark, listing, or File number E173959.

Configuration of the Auxiliary Contacts



1. M Type auxiliary contacts
2. Additional 4th pole



See switch body drawings for dimensions

Dimensions

Inches [mm]

Size 1

Size 2



Please see our website www.AutomationDirect.com for complete engineering drawings.

SIRCO M UL 508 Enclosed Non-Fusible Disconnect Switches



Technical Characteristics

Characteristics According to UL 508 / CSA 22.2#4			
	22143503	22243503	22243506
General use rating (A)	30A	30A	60A
Max volts (VAC)	600VAC		
Short circuit rating at 600VAC (kA)	65kA	65kA	50kA
Type of fuse	J		
Max fuse rating (A)	30	100	100
Max. motor 3-ph HP			
240VAC	7.5	7.5	20
480VAC	20	20	40
600VAC	25	25	40
Wire type/temperature	Cu / 75°C (167°F)		
Product weight – lb (kg)	1.5 lb (0.68 kg)	1.9 lb (0.86 kg)	2.1 lb (0.95 kg)
Wire range			
Solid (AWG) - 1 wire	#14-10	#14-10	#14-10
Torque - lb·in (N·m)	26.5 (3)	26.5 (3)	38.9 (4.5)
Solid (AWG) - 2 wire	(2) #12	(2) #12	(2) #12
Torque - lb·in (N·m)	26.5 (3)	26.5 (3)	38.9 (4.5)
Stranded (AWG) - 1 wire	#14-4	#14-4	#14-1
Torque - lb·in (N·m)	26.5 (3)	26.5 (3)	38.9 (4.5)
Stranded (AWG) - 2 wire	(2) #14-12	(2) #14-12	(2) #10-6
Torque - lb·in (N·m)	26.5 (3)	26.5 (3)	38.9 (4.5)
Environmental			
Operating temperature ¹	-20°C to 70°C (-4°F to +158°F)		
Flammability rating	UL94-5VA		
Enclosure Material	Polycarbonate		
Enclosure NEMA/UL type	1, 3R, 12, 4, 4X		
Mounting	Wall		
Auxiliary contacts	A300		
Agency approvals			
UL file # E173959 (UL 508, C22.2 NO. 14) Manual motor controller "suitable as motor disconnect" CE 2011/65/EU, 2014/35/EU LVD and 2014/30/EU EMC			

¹Temperatures above 40°C, the current rating of the switch has to be de-rated 1% per °C over 40°C. Example, at 60°C a 100A switch is rated 80A

Note: Short-circuit rating achieved when used with corresponding fuse type and max fuse rating.

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

SIRCO UL 98B DC Non-Fusible Disconnect Switches



To assemble a switch, please select:

Direct Operation

External Operation



OR



Switch Body

Direct Handle

Switch Body

Shaft

External Handle

UL 98B Non-Fusible Disconnect Switches

Part Number	Description	Switch Body Rating (A)	Voltage Rating	# of Poles	Price
27DC3011	Non-fusible UL 98B rotary disconnect switch	100	600VDC	3	Retired
27DC4011			1000VDC	4	\$408.00
27DC3021		250	600VDC	3	Retired
27DC4021			1000VDC	4	\$493.00

Handles – Defeatable and Lockable

Part Number	Description	Switch Body Rating (A)	Handle Color	Handle Type	NEMA/UL Type	Price
26995052	Mounts directly on switch, no shaft required*	100-400	Black	–	–	\$20.00
142F2111	External front handles, shaft required	100-400	Black/Blue	S2	1, 3R, 12	\$54.00
142G2111			Red/Yellow			\$54.00
142D2111			Black/Blue		4, 4X	\$75.00
142E2111			Red/Yellow			\$75.00
142D2911	External heavy duty front handles, shaft required**	100-400	Black/Blue	S2	4, 4X	\$94.00
142E2911			Red/Yellow			\$94.00


* Not defeatable

** Heavy duty handles have larger metal hasp to accommodate multiple locking devices.



Shafts for External Handles

Part Number	Switch Body Rating (A)	Handle Type	Length (in)	Length (mm)	Price
14001020	100-400	S1, S2	7.9	200	\$14.00
14001032			12.6	320	\$15.00
14001040			15.7	400	\$16.50



SIRCO UL 98B DC Non-Fusible Disconnect Switches

Shaft Guide for External Handle

Part Number	Description	Fits Handle Type	Price
<u>14290000</u>	This accessory makes alignment connections between the shaft and handle easier. Allows up to 15mm misalignment tolerance. Required for a shaft length over 300mm. Included with longer shafts.	S01, S1, S2, S3	\$7.50

[14290000](#)

Auxiliary Contacts

Part Number	Description	Switch Body Rating (A)	Type	Contacts	Price
<u>27990021</u>	Auxiliary contact block: 1 Form C, 10A @ 125VAC	100-600	C Type standard level	1 NO / 1 NC	\$15.00
<u>27990022</u>	Auxiliary contact block: 1 Form C, 10A @ 125VAC, 2/pk			1 NO / 1 NC	\$20.00
<u>27990121</u>	Auxiliary contact block: 1 Form C, 1A @ 125VAC, low impedance		C Type low impedance	1 NO / 1 NC	\$17.00
<u>27990122</u>	Auxiliary contact block: 1 Form C, 1A @ 125VAC, low impedance, 2/PK			1 NO / 1 NC	\$27.50

[27990021](#)

Terminal Screens

Part Number	Description	Switch Body Rating (A)	No. of Poles	Position	Price
<u>27983021</u>	Terminal screens provide line or load protection against direct contact with terminals or connection parts.	100-250	3	Line	\$23.50
<u>27988021</u>				Load	\$23.50
<u>27984021</u>			4	Line or load	\$27.50

[27983021](#)

Terminal Lugs

Part Number	Description	Switch Body Rating (A)	Wire Range	Lugs per kit	No cables per lug	Price
<u>39542020</u>	Terminal lug kits allow for the connection of bare copper cables on to the terminals (no spade lugs). Cable type Cu/Al.	100-250	#6 - 300MCM	2	1	\$20.00

[39542020](#)

SIRCO UL 98B DC

Non-Fusible Disconnect Switches



Technical Characteristics

Characteristics According to UL 98 / CSA 22.2#4 and UL 98B		
	<u>27DC3011, 27DC4011</u>	<u>27DC3021, 27DC4021</u>
General use rating (A)	100	250
600VDC / 3P in series (A)	100	250
1000VDC / 4P in series (A)	100	250
Short-circuit capacity at 600VDC		
Prospective short-circuit current (kA rms) ¹	20	20
Type of fuse	Mersen A70P100	Mersen A70P100
Associated fuse rating (A)	200	200
Short-circuit capacity at 1000VDC (any breaker)		
Prospective short-circuit current (kA rms) ¹	10	10
Wire type/temperature	Cu/Al / 75°C (167°F)	
Product weight – lb (kg)		
3-pole	4.2 (1.91)	
4-pole	5.0 (2.3)	
Wire range		
Stranded (AWG)	#6-300MCM	#6-300MCM
Torque - lb-in (N·m)	275 (31)	275 (31)
Environmental – switch body		
Operating temperature ¹	-20°C to 70°C (-4°F to +158°F)	
Flammability rating	UL 94-V0	
Mechanical characteristics		
Endurance (number of operating cycles)	10,000	10,000
Operating torque (lb-in / N·m)	88.5 / 10	88.5 / 10
Mounting	Panel mount	
Auxiliary contact		
Electrical characteristics	A300	A300
Agency approvals		
UL file # E201138 (UL 98), E346418 (UL 98B) CSA file # 112964 (22.2 No. 4)		

¹ Temperatures above 40°C, the current rating of the switch has to be de-rated 1% per °C over 40°C. Example, at 60°C a 100A switch is rated 80A

Note: Short-circuit rating achieved when used with corresponding fuse type and max fuse rating.


To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

Characteristics According to IEC 60647-3		
	<u>27DC3011</u> <u>27DC4011</u>	<u>27DC3021</u> <u>27DC4021</u>
Thermal current I_{th} at 40°C (A)	160	250
Rated insulation voltage U_i (V)	1,200	1,200
Rated impulse withstand voltage U_{imp} (kV)	12	12
Rated operational currents I_e, DC-22B		
750VDC / 3P in series (A)	160	250
1000VDC / 4P in series (A)	160	250

SIRCO UL 98B DC Non-Fusible Disconnect Switches




Dimensions [inches/mm]



Dimensions																							
Switch Body Rating (A)	Unit	Overall Dims	Terminal Shrouds		Switch Body						Switch Mounting					Connection							
		C	AC	AD	F 3p	F 4p	H	J1 3p	J1 4p	K	M 3p	M 4p	N	R1	R2	T	U	V	W	Y	Z	AA	CA
	100-250	in	3.72	10.1	3.05	7.09	9.06	4.22	2.17	4.13	1.8	6.3	8.27	5.31	0.35	0.27	1.97	0.98	1.18	0.43	0.14	1.35	6.3
	mm	94.6	256	77.5	180	230	107	55	105	45.6	160	210	135	9	7	50	25	30	11	3.5	34.4	160	15

Mounting Orientation



Note: The switch will operate correctly when rotated clockwise 90 degrees.
The switch will not operate correctly when rotated counterclockwise 90 degrees.

Please see our website www.AutomationDirect.com for complete engineering drawings.

FUSERBLOC UL 489


Compact Fusible Disconnect Switches



To assemble a switch, please select:

Direct Operation

External Operation



OR



Switch Body

Direct Handle

Switch Body

Shaft

External Handle

UL 489 Compact Fusible Disconnect Switches

Part Number	Description	Frame Size	Fuse Type	Price
37103003	Compact UL 489 fusible front operated switch, 30A, 600VAC, 3-pole	1	Class CC	\$134.00
37104003	Compact UL 489 fusible front operated switch, 30A, 600VAC, 3-pole with switched neutral			\$173.00
37105003	Compact UL 489 fusible front operated switch, 30A, 600VAC, 3-pole with unswitched neutral			\$165.00
37103004	Compact UL 489 fusible front operated switch, 30A, 600VAC, 3-pole	2	Class J	\$134.00
37104004	Compact UL 489 fusible front operated switch, 30A, 600VAC, 3-pole with switched neutral			\$173.00
37105004	Compact UL 489 fusible front operated switch, 30A, 600VAC, 3-pole with unswitched neutral			\$166.00

Handles

Part Number	Description	Switch Body Rating (A)	Handle Color	Handle Type	NEMA/UL Type	Test	Price
37294012	Direct handle for class CC disconnect switches*	30	Black	—	—	—	\$24.00
37294014	Direct handle for class J disconnect switches*	30	Black	—	—	—	\$24.00
14930111	Front operation handle for compact UL 489 fusible disconnect switches, defeatable and lockable	30	Black/Blue	S0	1, 3R, 12	I - O	\$24.50
14940111		30	Red/Yellow	S0		I - O	\$24.50
149D0111		30	Black/Blue	S0	4, 4X	I - O	\$30.00
149E0111		30	Red/Yellow	S0		I - O	\$30.00
141F2111		30	Black/Blue	S1	1, 3R, 12	I - O	\$37.50
141G2111		30	Red/Yellow	S1		I - O	\$37.50
141D2111		30	Black/Blue	S1	4, 4X	I - O	\$47.00
141E2111		30	Red/Yellow	S1		I - O	\$47.00
141D2115		30	Black/Blue	S1		I - O - Test	\$51.00
141E2115		30	Red/Yellow	S1		I - O - Test	\$51.00
141D2911	External heavy duty front handles, shaft required**	30	Black/Blue	S1	4, 4X	I - O	\$55.00
141E2911		30	Red/Yellow	S1		I - O	\$55.00

* Defeatable

** Heavy duty handles have larger metal hasp to accommodate multiple locking devices.



Direct Handle
[37294012](#)




S0 Handle
[149D0111](#)



S1 Handle
[141F2111](#)

Shafts for External Handles

Part Number	Switch Body Rating (A)	Handle Type	Length		Price
			in	mm	
14050620	30	S0	7.9	200	\$12.00
14050632			12.6	320	\$15.00
14050640			15.7	400	\$15.00
14010520		S1	7.9	200	\$11.00
14010532			12.6	320	\$12.50
14010540			15.7	400	\$15.00



FUSERBLOC UL 489

Compact Fusible Disconnect Switches



Shaft Guide for External Handle

Part Number	Description	Fits Handle Type	Price
<u>14290000</u>	This accessory makes alignment connections between the shaft and handle easier. Allows up to 15mm misalignment tolerance. Required for a shaft length longer than 300mm. Included with longer shafts.	S01, S1, S2, S3	\$7.50
<u>14190000</u>		S00, S0	\$2.75

[14290000](#)


Auxiliary Contacts

Part Number	Description	Switch Body Rating (A)	Contacts	Price
<u>39990701</u>	Front mount auxiliary contacts can be configured to be operated on standard and TEST position switches. Each slot can accommodate up to 2 interlocked auxiliary contacts. 3A @ 240VAC. For 30 to 200A/J, maximum of 4 auxiliary contacts.	30 - 600	1 NO	\$10.00
<u>39990702</u>			1 NC	\$10.00

[39990701](#)


Contact Holder for Additional Auxiliary Contacts

Part Number	Description	Switch Body Rating (A)	Fuse Types	Price
<u>39990710</u>	Additional auxiliary contact holder, side mount. For use with Class CC and J FUSERBLOC compact 30A fused switch bodies. Holds a maximum of 4 (2 wide x 2 high).	30	Class CC / J	\$16.00

[39990710](#)

NFPA 79 "Through the Door" Kit

Part Number	Description	Switch Body Rating (A)	Frame Size	Price
<u>37294532</u>	Allows retrofit of installations for 30A ratings. Meets both UL 508A and NFPA 79 requirements. Order an S1-type external handle separately.	30	1, 2	\$52.00

[37294532](#)

FUSERBLOC UL 489

Compact Fusible Disconnect Switches



Technical Characteristics

Characteristics According to UL 489 / CSA 22.2#5		
	<u>37103003, 37104003</u> <u>37105003</u>	<u>37103004, 37104004</u> <u>37105004</u>
General use rating (A)	30	30
Short circuit rating at 600VAC (kA)	100	100
Type of fuse	CC	J
Maximum fuse rating (A)	30	30
Operational power (hp) / current max operation 3-phase (A)		
220-240 VAC	7.5 / 22	7.5 / 22
440-480 VAC	15 / 21	15 / 21
600VAC	20 / 22	20 / 22
125VDC ¹	3 / 25	3 / 25
250VDC ²	5 / 20	5 / 20
Product weight – lb (kg)	1.3 (0.6)	1.4 (0.6)
Environmental – switch body		
Operating temperature ³	-20°C to 70°C (-4°F to +158°F)	
Flammability rating	UL 94-V0	
Mechanical endurance		
Endurance (number of operating cycles)	10,000	10,000
Operating torque – lb·in (N·m)	3.5 (0.4)	3.5 (0.4)
Mounting	35mm DIN rail or panel mount	
Connection		
Min. connection cross-section (AWG) ²	#14	#14
Max. connection cross-section (AWG) ²	#10	#10
Torque – lb·in (N·m)	27 (3)	27 (3)
Agency Approvals		
UL file # E255272 (UL 489, C22.2 No.5) Accessories UL file # 201138, CSA 112964		

¹ 2 poles in series² 3 poles in series³ Temperatures above 40°C, the current rating of the switch has to be derated 1% per °C over 40°C. Example, at 60°C a 100A switch is rated 80A

Note: Short-circuit rating achieved when used with corresponding fuse type and max fuse rating.

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.


FUSERBLOC UL 489

Compact Fusible Disconnect Switches




Dimensions [inches/mm]

Class CC



Class J



Dimensions										
Switch Body Rating (A)	Unit	Switch Body					Switch Mounting		Connection	
		F	H	H1	J	J1	N	N1	AA	Z
30 Class CC	in	3.78	3.28	5.19	1.47	0.59	3.13	1	4.56	1.12
	mm	96	83.5	132	37.5	15	79.5	25.5	116	28.5
30 Class J	in	4.13	3.89	–	1.47	0.59	3.30	1	4.56	1.12
	mm	105	99	–	37.5	15	84	25.5	116	28.5

Please see our website www.AutomationDirect.com for complete engineering drawings.


FUSERBLOC UL 489

Compact Fusible Disconnect Switches



39990710 Contact Holder for Additional Auxiliary Contacts

Dimensions in inches [mm]




Please see our website www.AutomationDirect.com for complete engineering drawings.

FUSERBLOC UL 98 Fusible Disconnect Switches

To assemble a switch, please select:

Direct Operation




Switch Body

Direct Handle

OR

External Operation



Switch Body

Shaft

External Handle

UL 98 Fusible Disconnect Switches

Part Number	Description	Switch Body Rating (A)	Frame Size	Number of Poles	Price
38612004	Front or side operated UL 98 Class J fusible switch, 600VAC, 250VDC	30	4	2	\$127.00
38613004				3	\$161.00
38616004				4	\$191.00
38612005		60	4	2	\$163.00
38613005				3	\$201.00
38616005				4	\$252.00
38612010		100	5	2	\$219.00
38613010				3	\$273.00
38616010				4	\$348.00
38612020		200	6	2	\$598.00
38613020				3	\$736.00
38616020				4	\$932.00
38513038		400	7	3	\$1,012.00
38503060		600	8	3	\$1,764.00

Front Operation Handles

Part Number	Description	Switch Body Rating (A)	Fits Frame	Handle Color	Handle Type	NEMA/ UL Type	Test	Price		
36297910	Direct mount handle	30-400	4 - 7	Black	—	—	—	\$31.00		
38596011		600	8	Black	—	—	—	\$55.00		
141F2111	Front operation handle for UL 98 fusible disconnect switches	30-60	4	Black/Blue	S1	1, 3R, 12	I - O	\$37.50		
141G2111				Red/Yellow				\$37.50		
141D2111				Black/Blue	S1	4, 4X	I - O	\$47.00		
141E2111				Red/Yellow				\$47.00		
141D2115				Black/Blue	S1		I - O - Test	\$51.00		
141E2115				Red/Yellow				\$51.00		
142D2115				100-200	5, 6	Black/Blue	S2	4, 4X	I - O - Test	\$94.00
142E2115						Red/Yellow				\$94.00
142F2111		100-400	5, 6, 7	Black/Blue	S2	1, 3R, 12	I - O	\$54.00		
142G2111				Red/Yellow				\$54.00		
142D2111				Black/Blue		4, 4X	I - O	\$75.00		
142E2111				Red/Yellow				\$75.00		
143F3111		600	8	Black/Blue	S3	1, 3R, 12	I - O	\$70.00		
143G3111				Red/Yellow				\$70.00		
143D3111				Black/Blue		4, 4X	I - O	\$89.00		
143E3111				Red/Yellow				\$89.00		
141D2911	Heavy duty front operation handle for UL 98 fusible disconnect switches	30-60	4	Black/Blue	S1	4, 4X	I - O	\$55.00		
141E2911				Red/Yellow				\$55.00		
142D2911		100-400	5, 6, 7	Black/Blue	S2	4, 4X	I - O	\$94.00		
142E2911				Red/Yellow				\$94.00		
143D3911		600	8	Black/Blue	S3	4, 4X	I - O	\$123.00		
143E3911				Red/Yellow				\$123.00		



Direct Handle
[36297910](#)



S1 Handle
[142F2111](#)



S2 Handle
[142G2111](#)



S3 Handle
[143D3111](#)

FUSERBLOC UL 98 Fusible Disconnect Switches





Right Side Operation Handles (No door interlocking)								
Part Number	Description	Switch Body Rating (A)	Fits Frame	Handle Color	Handle Type	NEMA/UL Type	Test	Price
141H6111	Side operation handle for UL 98 fusible disconnect switches	30-60	4	Black/Blue	S1	4, 4X	I - O	\$47.50
141I6111				Red/Yellow				\$47.50
142H6111		100-400	5, 6, 7	Black/Blue	S2			\$70.00
142I6111				Red/Yellow				\$70.00
141H6911	Heavy duty side operation handle for UL 98 fusible disconnect switches*	30-60	4	Black/Blue	S1			\$95.00
141I6911				Red/Yellow				\$95.00
142H6911		100-400	5, 6, 7	Black/Blue	S2			\$118.00
142I6911				Red/Yellow				\$118.00

[141H6111](#)

* Heavy duty handles have larger metal hasp to accommodate multiple locking devices.

Shafts for External Handles					
Part Number	Switch Body Rating (A)	Handle Type	Length		Price
			in	mm	
14001020	30-400	S1, S2	7.9	200	\$14.00
14001032			12.6	320	\$15.00
14001040			15.7	400	\$16.50
14001220	600	S3	7.9	200	\$17.50
14001232			12.6	320	\$21.00
14001240			15.7	400	\$24.00

[14001020](#)[14001220](#)

Shaft Guide for External Handle			
Part Number	Description	Fits Handle Type	Price
14290000	This accessory makes alignment connections between the shaft and handle easier. Allows up to 15mm misalignment tolerance. Required for a shaft length longer than 300mm. Included with longer shafts.	S1, S2, S3	\$7.50

[14290000](#)

Auxiliary Contacts				
Part Number	Description	Body Switch Rating (A)	Contacts	Price
39990701	Front mount auxiliary contacts can be configured to be operated on standard and TEST position switches. Each slot can accommodate up to 2 interlocked auxiliary contacts. 3A @ 240VAC.	30 - 600	1 NO	\$10.00
39990702			1 NC	\$10.00
	For 30 to 200A/J, maximum of 4 auxiliary contacts			
3999U041	Side operated auxiliary contacts for frame sizes 3 to 8 UL 98 fusible disconnect switches, position OFF and ON signalled by 1 to 4 NO + NC auxiliary contacts. 10A @ 600 VAC/DC. 2/pk	30-200	1 NO	\$34.00
3999U042		30-200	1NO / 1NC	\$66.00


[39990701](#)[3999U041](#)

FUSERBLOC UL 98 Fusible Disconnect Switches



Terminal Shrouds

Part Number	Description	Switch Body Rating (A)	Pcs/pk	Price
38982020	Line or load protection against direct contact with terminals or connection parts, 1 pole	200	2	\$20.50
38983020		200	3	\$29.50
38984020		200	4	\$38.00
38983040		400	3	\$37.50
38983080		600	3	\$66.00

[38982020](#)

Terminal Lugs

Part Number	Switch Body Rating (A)	Wire Range	Wires per lug	Lugs per Kit	Price
39542020	200	#6 - 300MCM	1	2	\$20.00
39543020				3	\$29.50
39544020				4	\$38.50
39543040	400	#2 - 600MCM	1	3	\$76.00
39543041		2 x (#6 - 350MCM)	2	3	\$103.00
39543060	600	2 x (#2 - 600MCM)	2	3	\$155.00

[39542020](#)

Note: Accept either copper or aluminum wires

NFPA 79 Accessories

Flange Handles

Part Number	Description	Switch Body Rating (A)	Handle Color	Handle Type	NEMA/UL Type	Price
37299002	Flange handle, meets UL 508A and NFPA 79 requirements. The handle will operate the switch by cable.	30-200	Gray	Standard	1, 3, 3R, 4, 12	\$144.00
37299003		30-200	—	Chrome plated	1, 3, 3R, 4, 4X, 12	\$387.00

Requires flange handle, cable operator and cable.

[37299002](#)[37299003](#)

Cable Operator

Part Number	Description	Switch Body Rating (A)	Price
37299903	Cable flange mechanism links to flange handle and side-operated switches. Must also order flange handle.	30-200	\$149.00


Cables

Part Number	Cable Length (feet)	Cable Length (m)	Price
37299992	3	1	\$174.00
37299993	5	1.5	\$202.00

[37299992](#)[37299903](#)

NFPA 79 "Through the Door" Kit

Part Number	Description	Min Enclosure Depth	Switch Body Rating (A)	Fits Frame Size	Price
37297540	Meets both UL 508A and NFPA 79 requirements. Order an S-type external handle separately (not S0).	11.14 in (238mm)	30-200	3, 4, 5, 6	\$65.00
37297544		11.81 in (300mm)	400	7	\$94.00
37297552		14.96 in (380mm)	600	8	\$197.00

[37297544](#)

FUSERBLOC UL 98 Fusible Disconnect Switches



Blown Fuse Monitors

These fuse monitors detect fuse opening using a bistable (latching) relay and a signaling LED. They can be mounted on a 35mm DIN rail, a back plate, next to the disconnect switch or on the door, or can be mounted directly on the side of Fuserbloc (3861xxx) series switches.


Blown Fuse Monitors for UL 98 Fusible Disconnect Switches						
Part Number	Model	# of LEDs	Auxiliary Contacts	Operating Voltage	Weight lb (kg)	Price
38991120	FMD10	1	1 NO / 1 NC	120 - 260 VAC	0.35 (0.16)	Retired
38991380				380 - 690 VAC		Retired
38993120	FMD30	3	3A @ 230VAC/30VDC	120 - 260 VAC		\$199.00
38993380				380 - 690 VAC		\$219.00

[38991120](#)[38993120](#)

Fuse Monitors Accessories			
Part Number	Description	Mounting	Price
38199120	Blown fuse monitor connection hardware	Standard	\$35.00
38299120	Blown fuse monitor door mounting and connection hardware	Door mounted	\$66.00

[38199120](#)[38299120](#)

Dimensions [inches/mm]



Please see our website www.AutomationDirect.com for complete engineering drawings.

FUSERBLOC UL 98 Fusible Disconnect Switches



Technical Characteristics

Characteristics According to UL 98 / CSA 22.2 #4						
	<u>38612004</u> <u>38613004</u> <u>38616004</u>	<u>38612005</u> <u>38613005</u> <u>38616005</u>	<u>38612010</u> <u>38613010</u> <u>38616010</u>	<u>38612020</u> <u>38613020</u> <u>38616020</u>	<u>38513038</u>	<u>38503060</u>
General Use Rating (A)	30	60	100	200	400	600
Short circuit rating at 600VAC (kA)	200	100	200	200	200	200
Type of fuse	J	J	J	J	J	J
Max. fuse rating (A)	30	60	100	200	400	600
Operational Power (hp) / Current Max Operation 3-Phase (A)						
220-240 VAC	7.5 / 22	15 / 42	30 / 80	60 / 154	125 / 312	200 / 480
440-480 VAC	15 / 21	30 / 40	60 / 77	125 / 156	250 / 302	500 / 590
600VAC	20 / 22	50 / 52	75 / 77	150 / 144	350 / 336	500 / 475
125VDC ¹	3 / 25	5 / 40	7.5 / 58	15 / 112	20 / 148	–
250VDC ²	5 / 20	10 / 38	20 / 72	40 / 140	50 / 173	–
Mechanical Endurance						
Endurance (number of operating cycles)	10,000	10,000	10,000	8,000	6,000	5,000
Operating torque (lb·in / N·m)	4.1	8.7	9.7	10.2	17	66.2
Wire Type / Temperature	Cu / 75°C (167°F)			Cu/Al / 75°C (167°F)		
Product Weight – lb (kg)						
2-pole	3.0 (1.3)	3.1 (1.4)	4.07 (1.8)	5.7 (2.6)	–	–
3-pole	3.8 (1.7)	4.1 (1.8)	5.3 (2.4)	7.8 (3.5)	16.6 (7.6)	44.2 (20.1)
4-pole	4.7 (2.1)	4.8 (2.2)	6.49 (2.9)	10.8 (4.9)	–	–
Wire Range						
Solid (AWG)	#14-10	#14-10	#10-8	–	–	–
Torque – lb·in (N·m)	44.2 (5)	44.2 (5)	35.4 (4)	–	–	–
Solid (AWG)	(2) #10	(2) #10	–	–	–	–
Torque – lb·in (N·m)	44.2 (5)	44.2 (5)	–	–	–	–
Stranded (AWG)	#14-6	#14-6	#10-2 ⁴	#6-300MCM	#4-600MCM	(2) #2-600MCM
Torque – lb·in (N·m)	44.2 (5)	44.2 (5)	35.4 (4)	275 (31)	550 (62)	375 (42.4)
Stranded (AWG)	(2) #12-6	(2) #12-6	#1-2/0 ⁴	–	(2) 1/0-250MCM	–
Torque – lb·in (N·m)	44.2 (5)	44.2 (5)	44.2 (5)	–	550 (62)	–
Environmental – Switch Body						
Operating temperature ³	-20°C to 70°C (-4°F to +158°F)					
Flammability rating	UL 94-V0					
Mounting	35mm DIN rail or panel mount		Panel mount			
Agency Approvals						
UL file # E201138 (UL 98), CSA file # 112964 (C22.2 No. 4)						

¹ 2 poles in series² 3 poles in series³ Temperatures above 40°C, the current rating of the switch has to be de-rated 1% per °C over 40°C. Example: At 60°C a 100A switch is rated 80A.⁴ Stranded or compact stranded Cu


To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

FUSERBLOC UL 98 Fusible Disconnect Switches




Dimensions [inches/mm]

30A to 60A - Frame Size 4



Note: For 2-pole decrease overall width by 36mm [1.42 in]. For 4-pole, increase overall width by 36mm [1.42 in].

100A - Frame Size 5




Please see our website www.AutomationDirect.com for complete engineering drawings.

FUSERBLOC UL 98 Fusible Disconnect Switches




Dimensions [inches/mm]

200A - Frame Size 6



Note: For 2-pole decrease overall width by 36mm [1.42 in]. For 4-pole, increase overall width by 36mm [1.42 in].

400A - Frame Size 7




Please see our website www.AutomationDirect.com for complete engineering drawings.

FUSERBLOC UL 98 Fusible Disconnect Switches



Dimensions [inches/mm]

600A - Frame Size 8



Please see our website www.AutomationDirect.com for complete engineering drawings.

Accessories Dimensions


Handles

[inches/mm]

Direct Handle for UL 98 Compact Non-Fusible Disconnect Switches

22995032

Handle Dimensions



External Handles for UL 98 Compact Non-Fusible Disconnect Switches

S00 Type

Handle Dimensions	Direction of Operation	Door Drilling

S0 Type

Handle Dimensions	Direction of Operation	Door Drilling

S01 Type

Handle Dimensions	Direction of Operation	Door Drilling

Please see our website www.AutomationDirect.com for complete engineering drawings.

Accessories Dimensions

Handles

[inches/mm]



Direct Handles for UL 98 Non-Fusible Disconnect Switches	
26995052	37996012
Handle Dimensions	Handle Dimensions

External Handles for UL 98 Non-Fusible Disconnect Switches		
S2 Type		
Handle Dimensions	Direction of Operation	Door Drilling
S3 Type		
Handle Dimensions	Direction of Operation	Door Drilling

Please see our website www.AutomationDirect.com for complete engineering drawings.

Accessories Dimensions


Handles

[inches/mm]

Direct Handle for UL 508 Non-Fusible Disconnect Switches

22995012

Handle Dimensions



External Handles for UL 508 Non-Fusible Disconnect Switches

S00 Type

Handle Dimensions	Direction of Operation	Door Drilling

S0 Type

Handle Dimensions	Direction of Operation	Door Drilling

S01 Type



Handle Dimensions	Direction of Operation	Door Drilling

Please see our website www.AutomationDirect.com for complete engineering drawings.

Accessories Dimensions

Handles

[inches/mm]





Please see our website www.AutomationDirect.com for complete engineering drawings.

Accessories Dimensions

Handles

[inches/mm]

Direct Handles for UL 489 Compact Fusible Disconnect Switches

26995052	37996012
Handle Dimensions	Handle Dimensions
	

External Handles for UL 489 Compact Fusible Disconnect Switches

S0 Type			
Handle Dimensions	Direction of Operation	Door Drilling	
<p>$\phi 3.07$ [$\phi 78.0$] 3.46 [88.0] 1.46 [37.0]</p>	<p>90° 0</p>	<p>4X $\phi 0.27$ [$\phi 7.0$] $\phi 1.22$ [$\phi 31.0$] 0.53 [13.5] 1.10 [28.0] 1.57 [40.0] 0.12 [3.0] $\phi 0.89$ [$\phi 22.5$]</p>	
S1 Type			
Handle Dimensions	Direction of Operation	Door Drilling	
<p>$\phi 3.07$ [$\phi 78.0$] 2.76 [70.0] 1.73 [44.0]</p>	<p>90° 0 65° TEST TEST POSITION INCLUDED ON CERTAIN MODELS ONLY AS INDICATED IN THE SELECTION TABLES</p>	<p>$\phi 0.27$ [$\phi 7.0$] $\phi 1.46$ [$\phi 37.0$] 1.57 [40.0] 1.10 [28.0]</p>	



Note: Test position included on certain models only as indicated in the selection tables.

Please see our website www.AutomationDirect.com for complete engineering drawings.

Accessories Dimensions

Handles

[inches/mm]

Direct Handles for UL 98 Fusible Disconnect Switches	
36297910	38596011
Handle Dimensions	Handle Dimensions
	

External Handles for UL 98 Fusible Disconnect Switches

S1 Type			
Handle Dimensions	Direction of Operation		Door Drilling
<p>Ø3.07 [Ø78.0] 2.76 [70.0] 1.73 [44.0]</p>	<p>90° 0 65° TEST EST POSITION INCLUDED ON CERTAIN MODELS ONLY AS INDICATED IN THE SELECTION TABLES</p>	<p>90° 0</p>	<p>Ø0.27 [Ø7.0] Ø1.46 [Ø37.0] 1.57 [40.0] 1.10 [28.0]</p>
S2 Type			
Handle Dimensions	Direction of Operation		Door Drilling
<p>Ø3.07 [Ø78.0] 4.92 [125.0] 1.77 [45.0]</p>	<p>90° 0 65° TEST EST POSITION INCLUDED ON CERTAIN MODELS ONLY AS INDICATED IN THE SELECTION TABLES</p>	<p>90° 0</p>	<p>4X Ø0.27 [Ø7.0] Ø1.46 [Ø37.0] 1.57 [40.0] 1.10 [28.0]</p>
S3 Type			
Handle Dimensions	Direction of Operation		Door Drilling
<p>Ø3.07 [Ø78.0] 8.27 [210.0] 2.36 [60.0]</p>	<p>90° 0 65° TEST EST POSITION INCLUDED ON CERTAIN MODELS ONLY AS INDICATED IN THE SELECTION TABLES</p>	<p>90° 0</p>	<p>4X Ø0.27 [Ø7.0] Ø1.46 [Ø37.0] 1.57 [40.0] 1.10 [28.0]</p>





Note: Test position included on certain models only as indicated in the selection tables.

Please see our website www.AutomationDirect.com for complete engineering drawings.

Accessories Dimensions


Shafts for Non-Fusible Disconnect Switches

[inches/mm]

Shafts for Non-Fusible Disconnect Switches					
Shafts for S00, S0 Handle Type	Part Number	Switch Body Rating (A)	Length		
			in	mm	
	14070515	16 - 100	5.9	150	
	14070520		7.9	200	
	14070532		12.6	320	
Shafts for S01 Handle Type	Part Number	Switch Body Rating (A)	Length		
			in	mm	
	14040520	16 - 100	7.9	200	
	14040532		12.6	320	
	14040540		15.7	400	
Shafts for S1, S2 Handle Type	Part Number	Switch Body Rating (A)	Length		
			in	mm	
	14001020	100 - 400	7.9	200	
	14001032		12.6	320	
	14001040		15.7	400	
Shafts for S3 Handle Type	Part Number	Switch Body Rating (A)	Length		
			in	mm	
	14011520	600	7.9	200	
	14011532		12.6	320	
	14011540		15.7	400	

Please see our website www.AutomationDirect.com for complete engineering drawings.

Shaft Length Minimum Dimensions						
Use standard lengths: 7.9 in / 200mm – 12.6 in / 320mm – 15.7 in / 400mm						
Switch Body Rating (A)	Dimension X		Handle Type	Length		Part Number
	in	mm		in	mm	
100 - 400	5.31 - 10.43	135 - 265	S2	7.9	200	14001020
100 - 400	5.31 - 15.16	135 - 385	S2	12.6	320	14001032
100 - 400	5.31 - 18.31	135 - 465	S2	15.7	400	14001040
600	8.70 - 13.50	221 - 343	S3	7.9	200	14011520
600	8.70 - 18.23	221 - 463	S3	12.6	320	14011532
600	8.70 - 21.38	221 - 543	S3	15.7	400	14011540



Accessories Dimensions


Shafts for Fusible Disconnect Switches

[inches/mm]

Shafts for Fusible Disconnect Switches									
Shafts for S0 Handle Type	Part Number	Body Switch Rating	Length		Shafts for S2 Handle Type	Part Number	Body Switch Rating	Length	
			in	mm				in	mm
	14050620	30A	7.9	200		14001020	30A to 400A	7.9	200
	14050632		12.6	320		14001032	30A to 200A	12.6	320
	14050640		15.7	400		14001040	30A to 400A	15.7	400
Shafts for S1 Handle Type	Part Number	Switch Body Rating	Length		Shafts for S3 Handle Type	Part Number	Switch Body Rating	Length	
			in	mm				in	mm
	14010520	30A	7.9	200		14001220	600A	7.9	200
	14010532		12.6	320		14001232		12.6	320
	14010540		15.7	400		14001240		15.7	400

Please see our website www.AutomationDirect.com for complete engineering drawings.

Shaft Length Minimum Dimensions						
Use standard lengths: - 7.9 in / 200mm - 12.6 in / 320mm - 15.7 in / 400mm						
Switch Body Rating (A)	Dimension X		Handle Type	Length		Part Number
	in	mm		in	mm	
30	4.02 - 9.65	102 - 245	S0	7.9	200	14050620
30	4.02 - 14.37	102 - 365	S0	12.6	320	14050632
30	4.02 - 17.52	102 - 445	S0	15.7	400	14050640
30	4.02 - 9.65	102 - 245	S1	7.9	200	14010520
30	4.02 - 14.37	102 - 365	S1	12.6	320	14010532
30	4.02 - 17.52	102 - 445	S1	15.7	400	14010540
30 - 100	5.3 - 9.06	135 - 230	S2	7.9	200	14001020
200	5.7 - 9.06	145 - 230	S2	7.9	200	14001020
400	7.87 - 10.24	200 - 260	S2	7.9	200	14001020
30 - 100	5.3 - 13.78	135 - 350	S1, S2	12.6	320	14001032
200	5.7 - 13.78	145 - 350	S2	12.6	320	14001032
400	7.87 - 14.96	200 - 380	S2	12.6	320	14001032
30 - 100	5.3 - 16.93	135 - 430	S1, S2	15.7	400	14001040
200	5.7 - 16.93	145 - 430	S2	15.7	400	14001040
400	7.87 - 18.1	200 - 460	S2	15.7	400	14001040
600 - 800	10.63 - 11.97	270 - 304	S3	7.9	200	14001220
600 - 800	10.63 - 16.69	270 - 424	S3	12.6	320	14001232
600 - 800	10.63 - 19.84	270 - 504	S3	15.7	400	14001240




Accessories Dimensions




Lugs


[inches/mm]




39542020, 39543020, 39544020



39543040



39543041


















39543060

Please see our website www.AutomationDirect.com for complete engineering drawings.

Accessories Dimensions

Auxiliary Contacts and Additional Poles

[inches/mm]

Please see our website www.AutomationDirect.com for complete engineering drawings.

Socomec Modular Fuse Holders For Class CC and Midget Class Fuses

Why choose fuses for electrical protection?

Guaranteed Performance



The use of fuses can greatly limit the short-circuit current and minimize its destructive effect on the equipment being protected. No device can compete with the exceptional speed of the fuse with regard to limitation of short-circuit and thermal stress. Several milliseconds are sufficient to completely eliminate a strong short-circuit current (up to 200kA).

Total Reliability

Fuses are totally sealed products, which guarantees long-term protection without any maintenance. Circuit breakers are complex devices that include moving parts. Their mechanisms can be affected by dust, humidity, and other external factors.

Maximum Safety

Fuses protect the user and the electrical system while avoiding any outward sign when managing a failure. The energy released during a short-circuit event is contained in the sealed fuse cartridge. There is no release of ionized gases and thus no effect on surrounding equipment in comparison to what happens when circuit breakers open on a short-circuit.



Socomec Modular Fuse Holders for Class CC Fuses



Features

- Up to 30A, 600VAC, 200kA RMS
- 1-, 2-, and 3-pole versions available
- Blown fuse indicating LED on select models
- Modular DIN 45mm cutout design
- IP20 finger safe / touch safe
- Sealed by a wire to prevent unwanted opening
- Very small footprint

Application examples

- Distribution boards
- Motor and control circuits
- Transformer protection
- Measuring devices and multimeter protection

Socomec Modular Fuse Holders for Class CC Selection Guide

Part Number	Price	Fuse Size (mm)	Box Qty.	Poles	Weight Per Individual Unit (kg [lb])	Drawing
57050001	\$96.00	10x38 mm	12	1	0.057 [0.126]	PDF
57050001-1PK	\$8.75		1			PDF
57050002	\$87.00		6	2	0.114 [0.251]	PDF
57050002-1PK	\$16.00		1			PDF
57050003	\$94.00		4	3	0.170 [0.375]	PDF
57050003-1PK	\$26.00		1			PDF
57050011	\$129.00		12	1 with LED	0.057 [0.126]	PDF
57050011-1PK	\$12.00		1			PDF
57050012	\$135.00		6	2 with LED	0.114 [0.251]	PDF
57050012-1PK	\$26.50		1			PDF
57050013	\$111.00		4	3 with LED	0.170 [0.375]	PDF
57050013-1PK	\$31.50		1			PDF

Agency Approvals

- UL file E307648, standard UL 4248-4
- CE compliant to RoHS Directive and Low Voltage directives
- CSA C22.2 No 4248-07 class 6225-01 File 265615



Socomec Modular Fuse Holders for Class CC Fuses

Socomec Modular Fuse Holders for Class CC Fuses Specifications			
Characteristics According to UL 4248-4			
Rated Operational Current		30A	
Fuse Type		CC	
Fuse Feature		Rejection ferrule	
Rated Operating Voltage		600V	
Dielectric Strength		2200V	
LED Working Voltage ¹		120-600 VAC / 12-24 VDC	
Rated Power Dissipation (watts per pole)		3	
Protection Degree		IP20	
Class CC Fuse Protected Short-Circuit Withstand			
Prospective Short-Circuit Current		200kA rms	
Connection			
1 Wire	Minimum Cu cable cross-section solid / stranded	0.75 mm ² / 18 AWG	
	Maximum Cu cable cross-section solid / stranded	10mm ² / 8 AWG	
2 Wires	Minimum Cu cable cross-section solid / stranded	0.75 mm ² / 18 AWG	
	Maximum Cu cable cross-section solid	10mm ² / 8 AWG	
	Maximum Cu cable cross-section stranded	10mm ² / 8 AWG	
Wire Strip		10mm [0.39 in]	
Maximum Tightening Torque		2.5 N•m / 22 lb•in	
Mounting		DIN rail 35mm DIN 46277/1-3 (EN50022)	
Mechanical Characteristics			
Weight	1P	0.057 kg [0.126 lb]	
	2P	0.114 kg [0.251 lb]	
	3P	0.170 kg [0.375 lb]	

1: For fuse holders with LED indicator

Socomec Modular Fuse Holders for Class CC Fuses Specifications		
Characteristics According to UL 4248-4		
Thermal Current		30A
Fuse Type		CC
Fuse Feature		Rejection ferrule
Rated Operating Voltage		600V
LED Working Voltage ¹		120-600 VAC / 12-24 VDC
Fuse Rating	At 400VAC	30A
	At 500VAC	30A
	At 690VAC	–
Fuse Protected Short-Circuit Withstand		
Prospective Short-Circuit Current (kA rms) ¹		200

1: For fuse holders with LED indicator

Note: Current de-rating factors when multiple holders are installed side by side:

- 1 to 3 – 1
- 4 to 6 – 0.8
- 7 to 9 – 0.7
- More than 10 – 0.6

Socomec Modular Fuse Holders for RM Midget/Ferrule Fuses

Socomec RM Midget/Ferrule Fuse Holder Selection Guide						
Part Number	Price	Basic Device	Fuse Size (mm)	Box Qty.	Poles	Drawing
57010011	\$136.00	30A	10x38	12	1 with LED	PDF
57010011-1PK	\$12.50			1		PDF
57010015	\$57.00			12	1	PDF
57010015-1PK	\$5.50			1		PDF
57010020	\$65.00			6	2	PDF
57010020-1PK	\$12.00			1		PDF
57010018	\$64.00			4	3	PDF
57010018-1PK	\$17.50			1		PDF

Socomec RM Midget/Ferrule Fuse Holder Specifications (Characteristics according to UL 4248-1 and CSA-C22.2 No. 4248-1)			
Thermal Current			30A
Fuse Type			Midget
Fuse Size			10x38 mm
Rated Operating Voltage			750V
Rated Fuse Dissipated Power (watts per pole)			3
Protection Degree			IP20
gG Fuse Protected Short-Circuit Withstand	Prospective Short-Circuit Current (kA rms) ¹	Rated voltage: 690VAC	100
		Rated voltage: 400/500VAC	120
Design Current Derating Coefficient Depending on Temperature		20°C [68°F]	1
		30°C [86°F]	0.95
		40°C [104°F]	0.90
		50°C [122°F]	0.80
		60°C [140°F]	0.70
		70°C [158°F]	0.60
Connection	Minimum Cu cable cross-section solid/stranded		0.75 mm ² / 18 AWG
	Maximum Cu cable cross-section solid		10mm ² / 8 AWG
	Maximum Cu cable cross-section stranded		10mm ² / 8 AWG
	Tightening torque		2.5 N•m / 22 lb•in
Weight		1 P	0.125 lb [0.057 kg] 0.0132 lb [0.06 kg]
		1 P	0.258 lb [0.117 kg]
		3 P	0.505 lb [0.229 kg]

1: Connection for RM32 1 P (1 module)

Note: Current de-rating factors when multiple holders are installed side by side:

1 to 3 – 1
4 to 6 – 0.8
7 to 9 – 0.7
More than 10 – 0.6

Features

- Blown fuse indicating LED on select models
- High breaking capacity
- High dielectric strength
- Touch safe
- IP2X protection
- DIN rail mounting
- Non-load disconnect
- Handle can be padlocked (padlock not supplied)
- Padlocking handle accessories must be purchased from Socomec

Application examples

- Industrial control panels
- Inverters
- Measuring devices
- Multifunction meter protection
- UPS
- Motor drives

Agency Approvals

- UL 4248-1,
- CSA-C22.2 No. 4248-1
- Guide IZLT
- File E307648
- IEC 60269-2-1
- CSA22.2 No 14 class 3211-37 File 265615



Get Your Fuses From Us!

AutomationDirect has teamed up with Edison Fuse, a subsidiary of Cooper Industries, the worldwide leader in circuit protection, to offer the Edison line of fuses and fuse holders. Cooper Industries is a \$4.1B corporation with seven electrical products divisions, including two fuse brands. The Edison Fuse products are industry-standard fuses that are designed using the highest quality materials and manufacturing methods. All Edison fuses can be directly cross referenced and used as replacements for other name-brand fuses such as Littelfuse, Mersen, Siemens, and many more. Our fuse manufacturer cross reference list is at the end of this section.

AutomationDirect carries a wide range of fuses in convenient package sizes. Just about every electrical system requires some sort of circuit protection, so while you're ordering your other components from us, don't forget the fuses!



Fuses



Fuse Holders

Fuse Blocks



Where to Use a Fuse

Fuses can be used for a variety of overcurrent and overload applications. They can be used to protect transformers, motors, DC power supplies, lighting circuits, contactors, relays and other industrial and commercial electrical equipment and conductors.


AutomationDirect now carries a vast assortment of fuse types. General purpose Midget Class fuses are typically used as supplemental protection for control loads. Where adherence to extensive current limiting codes is not required, the Class M Midget fuses are a great low-cost solution for both time-delay and fast-acting protection.

Current limiting fuses, frequently used in applications for motor branch circuit protection, are available in both time-delay and fast-acting models.

In addition, the current limiting line is recognized for NEC branch circuit protection and Type 2 coordinated applications for IEC or NEMA starters/contactors.

Small dimension fuses are perfect in size and ratings for protection in electronic applications.

And, we've not forgotten the accessories you need: fuse holders and fuse blocks are available in a variety of 1, 2, and 3-pole form factors.



Per 2005 NEC Article 430

10 Great Reasons to Use a Fuse...

Why use a fuse?

Fuses offer a safe and economical solution for overcurrent protection of both conductors and components. Fuses can help make your control systems meet the UL and NEC codes.

- 1 Safety**
Overcurrent protective devices that have tripped are often reset without first investigating the cause of the fault. Electromechanical devices may not have the reserve capacity to open safely when a second or third fault occurs. When a fuse opens it is replaced with a new fuse, so the protection level is not degraded by previous faults. Our current limiting fuses meet the UL and NEC codes.
- 2 Cost effective**
Fuses typically are the most cost effective means of providing overcurrent protection. This is especially true where high fault currents exist or where small components such as Control Transformers or DC power supplies need protection.
- 3 High interrupting rating**
With most low voltage current limiting fuses (< 600 volts) having a 200,000 amp interrupting rating, you are not paying a high premium for a high interrupting capacity. Our current limiting fuses meet the UL and NEC codes.
- 4 Reliability**
Fuses have no moving parts to wear out or become contaminated by dust or oil.
- 5 North American standards**
Tri-National Standards specify fuse performance and maximum allowable fuse I^p and I^2t let-thru values.
- 6 Component protection**
The high current limiting action of a fuse minimizes or eliminates component damage.
- 7 Extended protection**
Devices with low interrupting ratings are often rendered obsolete by service upgrades or increases in available fault current. Updated NEC and UL standards are causing the need for potentially expensive system upgrades to non-fused systems.
- 8 Selectivity**
Fuses can be easily coordinated to provide selectivity under both overload and short circuit conditions.
- 9 Minimal maintenance**
Fuses do not require periodic recalibration as do some electromechanical overcurrent protective devices.
- 10 Long life**
As a fuse ages, the speed of response will not slow down or change. A fuse's ability to provide protection will not be adversely affected by the passing of time.

...plus the best reason of all - our prices!

AutomationDirect has secured great pricing for our fuses, fuse holders and fuse blocks, and can pass those savings on to you. Many items are priced well below industry list prices, making fuse protection a beneficial and affordable option for almost every electrical device.

Fuse Construction and Operation

The typical fuse consists of an element which is surrounded by a filler and enclosed by the fuse body. The element is welded or soldered to the fuse contacts (blades or ferrules).

The element is a calibrated conductor. Its configuration, mass and the materials employed are selected to achieve the desired electrical and thermal characteristics. The element provides the current path through the fuse. It generates heat at a rate dependent on its resistance and the load current.


The heat generated by the element is absorbed by the filler and passed through the fuse body to the surrounding air.

The filler material, such as quartz sand, provides effective heat transfer and allows for the small element cross-section typical in modern fuses. The effective heat transfer allows the fuse to carry harmless overloads. The small element cross section melts quickly under short-circuit conditions. The filler also aids fuse performance by absorbing arc energy when the fuse clears

an overload or short circuit.

When a sustained overload occurs, the element will generate heat at a faster rate than the heat can be passed to the filler. If the overload persists, the element will reach its melting point and open. Increasing the applied current will heat the element faster and cause the fuse to open

low-level overloads for relatively long periods without damage. However, under high-current conditions, damage can occur quickly. Because of its inverse time current characteristic, a properly applied fuse can provide effective protection over a broad current range, from low-level overloads to high-level short circuits.



sooner. Thus, fuses have an inverse time current characteristic: that is, the greater the overcurrent, the less time required for the fuse to open the circuit.

This characteristic is desirable because it parallels the characteristics of conductors, motors, transformers, and other electrical apparatus. These components can carry

How to Talk Fuses

Commonly used terms

I²t (Ampere Squared seconds): A measure of the thermal energy associated with currentflow. I²t is equal to (IRMS)² x t, where t is the duration of current flow in seconds.

Clearing I²t: The total I²t passed by a fuse as the fuse clears a fault, with t being equal to the time elapsed from the initiation of the fault to the instant the fault has been cleared.

Melting I²t: The minimum I²t required to melt the fuse element.

Ampere Rating: The continuous current carrying capability of a fuse under defined laboratory conditions. The ampere rating is marked on each fuse.

Available Fault Current: The maximum short-circuit current that can flow in an unprotected circuit

Coordination: The use of overcurrent protective devices that will isolate only that portion of an electrical system that has been overloaded or faulted.

Current-Limiting Range: The available fault currents a fuse will clear in less than ½ cycle, thus limiting the actual magnitude of current flow.

Element: A calibrated conductor inside a fuse that melts when subjected to excessive current. The element is enclosed by the fuse body and may be surrounded by an arc-quenching medium such as silica sand. The element is sometimes referred to as a link.

Fast-Acting Fuse: This is a fuse with no intentional time-delay designed into the overload range. It is sometimes referred to as a "single-element fuse" or "non-delay fuse."

Fault Current: Short-circuit current that flows partially or entirely outside the intended normal load current path of a circuit component. Values may be from hundreds to many thousands of amperes.

Ferrule: The cylindrical brass, bronze or copper mounting terminals of fuses with amp ratings up to 60 amperes. The cylindrical terminals at each end of a fuse fit into fuse clips.

Current-limiting Fuse: A fuse that meets the following three conditions:

1. Interrupts all available overcurrents within its interrupt rating.
2. Within its current limiting range, limits the clearing time at rated voltage to an interval equal to, or less than, the first major or symmetrical current loop duration.
3. Limits peak let-through current to a value less than the available peak current.

Interrupting Rating: The maximum level of fault current that the fuse has been tested to safely interrupt.

Our Fuses at a Glance

Fuse



Fuse Holders



Fuse Block



Fuse Series	Class	Amperage Range	Description	Application
JDL	J	1A to 600A	Most popular current limiting dual element time delay fuses available. Small physical size and high performance characteristics makes the class J ideal for any space limited applications	All general purpose circuits with high inrush inductive loads including motor branch circuits and transformers. Also suited for lighting loads. Recommended for type 2 (no damage) protection of IEC style motors, starters, and contactors.
JHL			JHL Class J fuses combine the performance of high-speed semiconductor fuses and the convenience of Class J branch-circuit fuses in one small package. Ideal for AC and DC drives and controllers.	AC and DC drives, electronic motor controllers, power semiconductor devices that utilize diodes, GTOs, SCR's, or SSR's.
ECNR	RK5	1A to 600A	The dual element time delay characteristics of these fuses typically allows them to be sized closer to the running ampacity of inductive loads to reduce cost and improve over current protection.	Use in AC power distribution system mains, feeders, and branch circuits. Recommended for high inrush inductive loads, like motors and transformers, and non inductive loads like lighting, and heating loads.
ECSR		3A to 600A		
LENRK	RK1	10A to 600A	These dual element time delay fuses have up to 40% more current limitation and up to 350% more I ₂ t limitation under fault conditions than the ECNR and ECSR fuses, reducing the potential for damage.	Use in AC power distribution system mains, feeders, and branch circuits. Recommended for high inrush inductive loads, like motors and transformers, and non inductive loads like lighting, and heating loads.
LESRK		5A to 600A		
TJN	T	1A to 600A	These fuses are extremely fast-acting fuses in a compact, space-saving size.	These fuses are ideal as the main fuse protection for panel boards, load centers, meter stacks, and AC drives.
TJS				
HCLR	CC	0.5A to 30A	Fast acting characteristics with 200kA Interrupting Rating, and compact design are an excellent choice for inductive loads as well as resistive loads	Recommended for branch circuit protection, resistive heating loads, and lighting loads
HCTR	CC	0.25A to 30A	Time delay characteristics with 200kA Interrupting Rating, and compact design are an excellent choice for high inductive loads. Meets the requirements of the NEC® 430.72 and UL508	Recommended for Motor Branch protection, short circuit protection required by NEC® 430.52 and for Primary protection for control transformer loads.
EDCC	CC	0.5A to 30A	Low peak design was developed specifically for motor protection, Provides excellent current limiting capabilities up to 200KA 600VAC	Recommended for small horsepower motor circuits. Can provide Type 2 coordinated protection for IEC or NEMA starters/contactors
MCL	Midget	0.5A to 50A	Provides supplemental protection to end-use equipment with a 100KA interruption rating, 600VAC. Fast acting design responds quickly to both overloads and short-circuit protection	Recommended for control circuits, street lighting, HID lighting, and electronic equipment protection
MOL	Midget	0.5A to 30A	Provides supplemental protection to end-use equipment with a 10,000A interruption rating, economical laminated paper tube	Recommended to use as supplemental protection for non inductive control loads and lighting circuits
MEQ	Midget	0.25 to 30A	Provides supplemental protection to high inrush loads. has a 10,000A interruption rating, 500VAC. Fiber tube construction.	Recommended to use as supplemental protection for inductive control loads such as transformers and solenoids.
MEN	Midget	0.5A to 30A	Provides supplemental protection to high inrush loads. has a 10,000A interruption rating, fiber tube construction. Dual element allows harmless inductive surges to pass without opening.	Recommended to use as supplemental protection for inductive control loads such as transformers and solenoids, and other high inrush electronics circuits.
ABC	1 1/4" x 1/4" Ceramic	0.5A to 30A	Fast acting 1/4" x 1-1/4" ceramic tube construction. Small dimension electronic fuses.	Recommended as supplemental protection for electronic applications
AGC	1 1/4" x 1/4" Glass	0.5A to 30A	Fast acting 1/4" x 1-1/4" glass tube construction. Small dimension electronic fuses.	Recommended as supplemental protection for electronic applications
GMA	5mm x 20mm Glass	0.063A to 15A	Fast acting 5mm x 20mm glass tube construction. Small dimension electronics fuses.	Recommended as supplemental protection for electronic applications
GMC	5mm x 20mm Glass	0.5A to 10A	Medium Time Delay 5mm x 20mm glass tube construction. Small dimension electronics fuses.	Recommended as supplemental protection for electronic applications
MDA	1 1/4" x 1/4" Ceramic	0.5A to 20A	Time Delay 1/4" x 1-1/4" ceramic tube construction. Small dimension electronics fuses.	Recommended as supplemental protection for electronic applications
MDL	1 1/4" x 1/4" Glass	0.0625A to 20A	Time Delay 1/4" x 1-1/4" glass tube construction. Small dimension electronics fuses.	Recommended as supplemental protection for electronic applications
S500	5mm x 20mm Glass	0.032A to 10A	Fast acting 5mm x 20mm glass tube construction. Small dimension electronics fuses.	Recommended as supplemental protection for electronic applications
S506	5mm x 20mm Glass	0.25A to 6.3 A	Time Delay 5mm x 20mm glass tube construction. Small dimension electronics fuses.	Recommended as supplemental protection for electronic applications
LCU	L	601-1200 A	Fast acting current limiting for non-inductive applications.	Suited for protection of low interrupting circuit breakers and non-inductive loads.



Selection Guide

Line Overview

The Edison family of fuses, fuse blocks and fuse holders is divided into two classes:

1. Current Limiting: Class CC, Class J, Class L, Class RK, Class T
2. General Purpose: Class M Midget and Small Dimension

The fuse selection guide below is a general summary of the

specifications included for each fuse type. This selection guide does not include the many variables that can exist for specific situations such as local codes, unusual temperature, or other operating conditions. When selecting fuses, be sure to comply with any applicable PUBLIC SAFETY standards that apply to Overcurrent Protection Devices (OPD).

Edison Fuses Selection Guide and General Specifications												
Description	Current Limiting											
	Class J		Class RK5		Class RK1		Class T		Class L	Class CC		
Fuse Type	Fast-Acting	Time-Delay	Time-Delay				Extremely Fast-Acting		Fast-Acting	Fast-Acting	Time-Delay	
Part Number	JHL	JDL	ECNR	ECSR	LENRK	LESRK	TJN	TJS	LCU	HCLR	HCTR	EDCC
Voltage Rating	600VAC 450VDC	600VAC 300VDC*	250VAC 125 VDC* (1-200A) 250VDC* (201-600A)	600VAC 300VDC*	250VAC 125 VDC* (10-60A) 250VDC* (70-600A)	600VAC 300VDC*	300VAC 160 VDC (15-600A)	600VAC	600V	600VAC 300VDC (15-20A)	600VAC	600VAC 300VDC (0.5-2.25A) (20-30A)
Amp Rating	1 - 600		1 - 600	3 - 600	10 - 600	5 - 600	1 - 600		601 - 1200	0.5 - 30	0.25 - 30	0.5 - 30
Interrupting Rating	200,000 RMS Symmetrical Amps											
Current Limiting	Class J		Class RK5		Class RK1		Class T		Class L	Class CC		
Agency Approvals	UL Listed Class J Guide JDDZ File E162363 CSA Certified HRCI-J per C22.2, No. 248.8 File 700489 RoHS compliant	UL Listed Class J Guide JDDZ File E162363 CSA Certified HRCI-J per C22.2, No. 248.8 File 700489	UL Listed, Class RK, Guide JDDZ, File E162363 CSA Certified HRCI-R per C22.2, No. 248.12, File 700489 (LENRK CSA File 053787)				UL Listed, Class T, Guide JDDZ, File E162363 CSA Certified HRCI-T per C22.2, No. 248.12, File 53787, Class 1422-02 & 1422-82		UL Listed, Std. 248-10 CSA Certified, HRC-L C22.2 No. 248.10, Class 1422- 02, File 53787	UL Listed to 248.4, Class CC, Guide JDDZ, File E162363, CSA certified HRCI-MISC per C22.2 No. 248.4, File 700489		
Dimensions	See product specification pages.									ferrule (in): 13/32, length (in): 1-1/2		

* Self-certified DC ratings

Edison Fuses Selection Guide and General Specifications												
Description	General Purpose – Midget				General Purpose – Small Dimension Electronic							
Fuse Type	Fast-Acting		Time-Delay		Fast-Acting Ceramic	Fast-Acting Glass		Medium Time-Delay Glass	Time-Delay Ceramic	Time-Delay Glass	Fast-Acting Glass	Time-Delay Glass
Part Number	MCL	MOL	MEQ	MEN	ABC	AGC	GMA	GMC	MDA	MDL	S500	S506
Voltage Rating	600 VAC	250 VAC	500 VAC	250 VAC	250 VAC (0.5 to 30A) 125VDC: (0.5 to 30A)	250VAC: (0.1 to 10A) 32VAC: (15 to 30A)	250VAC (0.063 - 3A) 125VAC (4 - 15A)	250VAC (0.5 - 3A) 125VAC (4 - 10A)	250VAC 125VDC (20A)	250VAC: (0.0625 to 8A) 32VAC: (10 to 20A)	250VAC	250VAC
Amp Rating	0.5 to 50	0.5 to 30	0.25 to 30	0.5 to 30	0.5 to 30	0.10 to 30	0.063 to 15	0.5 to 10	0.5 to 20	0.0625 to 20	0.032 to 10	0.25 to 6.3
Interrupting Rating	100,000 RMS Amps	10,000 RMS Amps			See specifications table on product pages							
Current Limiting	N/A				N/A							
Agency Approvals	UL Listed to 248.14, File E162443 CSA Cert. C22.2 Part 59.2, LR 700489				UL Listed standard 248-14 UL Listed Guide and File nos. (ABC 0.25-20 A): (AGC 1/100-10 A) JDYX and E19180 UL Recognition Guide and File nos. (ABC 20-30A):(AGC 11-30) JDYX2 and E19180 CSA Certification Record No: 053787 C 000 and Class No: 1422 01 and 1422 30		Designed to UL/CSA 248-14 UL Listed, Guide JDYX, File E19180 63mA-6A UL Recognition, Guide JDYX2, File E19180, 7A-15A CSA Certified, File 053787 C_000, 63mA-6A Class 1422-01		UL Listed standard 248-14 UL Listed Card: MDA 2/10-20A , MDL 1/16-8A (Guide JDYX, File E19180 UL Recognized Card: MDA 25-30A MDL 9-30A (Guide JDYX2, File E19180) CSA Certification Card: MDA 2/10-15A (Class No. 1422-01)		UL Recognized Guide JDYX2, File E19180 Semko Approval VDE Approval BSI Approval IMQ Approval RoHS compliant	
					RoHS							
Dimensions	ferrule (in): 13/32 length (in): 1-1/2				1/4" x 1-1/4", (6.3mm x 32mm)		0.197" x 0.788" (5mm x 20mm)		1/4" x 1-1/4", (6.3mm x 32mm)		0.197" x 0.788" (5mm x 20mm)	

Cross Reference Guide



CROSS REFERENCE GUIDE By manufacturers type reference or series number. Ampere ratings must be added for ordering purposes.

FUSE TYPE		VOLT	EDISON	BRUSH/ DORMAN	BUSSMANN	MERSEN / GOULD	GEC/CEFCO	LITTELFUSE
UL CLASS CURRENT LIMITING FUSES (CSA CLASS)								
CC (HRCI-CC)	<i>Time-Delay</i>	600	EDCC	–	LP-CC	ATDR	–	CCMR
	<i>Time-Delay</i>	600	HCTR	–	FNQ-R	ATQR	–	KLDR
	<i>Fast-Acting</i>	600	HCLR	HCLR	KTK-R	ATMR	CTK-R	KLKR
RK1	<i>Time-Delay Dual Element</i>	250	LENRK	–	LPN-RK-SP	A2DR	–	LLNRK
		600	LESRK	–	LPS-RK-SP	A6DR	–	LLSRK
RK5	<i>Time-Delay Dual Element</i>	250	ECNR	–	FRN-R	TR	–	FLNR
		600	ECSR	–	FRS-R	TRS	–	FLSR
J	<i>Time-Delay Dual Element</i>	600	JDL	–	LPJ	AJT	–	JTD
	<i>High-Speed AC Drive</i>	600	JHL	–	DFJ	HSJ	–	–
T	<i>Extremely Fast-Acting</i>	300	TJN	–	JJN	A3T	–	JLLN
		600	TJS	–	JJS	A6T	–	JLLS
L	<i>Fast-Acting</i>	600	LCU	LCU	KTU	A4BY	CL, CLU	LDC
UL CLASS GENERAL PURPOSE FUSES								
Midget	<i>Fast-Acting</i>	600	MCL	MCL	KTK	ATM	CTK	KLK
		250	MOL	MOL	BAF/BAN	OTM	–	BLF
	<i>Time-Delay</i>	500	MEQ	MEQ	FNQ	ATQ	–	FLQ
		250	MEN	MEN	FNM	TRM	–	FLM
1/4"x1/4" Ceramic	<i>Fast-Acting</i>	250/125	ABC	ABC	ABC	GAB	–	314
1/4"x1/4"Glass		250/32	AGC	AGC	AGC	GGC	–	312
1/4"x1/4" Ceramic	<i>Time-Delay</i>	250	MDA	MDA	MDA	–	–	326
1/4"x1/4"Glass		250/32	MDL	MDL	MDL	GDL	–	313
5x20 mm Glass	<i>Fast-Acting</i>	250/125	GMA	GMA	GMA	GGM	–	235
	<i>Medium Time-Delay</i>	250/125	GMC	GMC	GMC	GSC	–	–
5x20 mm Glass	<i>Fast-Acting</i>	250	S500	BDB	GDB	GSB	–	217
	<i>Time-Delay</i>	250	S506	BDC	GDC	GDG	–	218
Fuse Puller								
Fuse Puller FP-2		–	old - 38072 new - FP-2	–	FP-2	–	–	–

Dual Element Time-Delay Class J Fuses



JDL5

JDL40

JDL150

EDISON JDL Class J fuses are among the most popular current limiting time-delay fuses available. Their small physical size and high performance characteristics make Class J fuses ideal for any space-limited application.

JDL Features

- Space saving dimensions compared to Class R
- Dual-Element construction provides superior time-delay to pass harmless motor or transformer surges
- High performance with fatigue-free cycling capabilities
- Extremely current limiting

Applications

- Recommended for Type 2 (no damage) protection of IEC style motor starters and contactors.
- Use to protect lower interrupting rated circuit breakers.
- All general purpose circuits with inductive (high inrush) loads, including motor and motor branch circuits, and transformer circuits. Also suitable for lighting loads.

Specifications

Voltage Rating: JDL - 600 VAC

Ampere Rating: 1–600 Amps

Interrupting Rating:
200,000 RMS Symmetrical Amps

Self-Certified Interrupting

Rating:

300,000 RMS Symmetrical Amps

Self-Certified DC Ratings:

Voltage Rating: JDL - 300 VDC

Interrupting Rating:

JDL - 20,000 Amperes DC

Current Limiting:

- Class J Fuse


Agency Approvals

- UL Listed, Class J, Guide JDDZ, File E162363
- CSA Certified HRCI-J per C22.2, No. 248.8

JDL Series Dual-element Time-delay Fuses					
Part Number	AMP Rating	Rated Voltage AC Max	Pcs/ Pkg	Package Weight	Price
JDL1	1	600V	10	1.00 lb.	\$273.00
JDL2	2				\$273.00
JDL3	3				\$280.00
JDL4	4				\$291.00
JDL5	5				\$270.00
JDL6	6				\$272.00
JDL8	8				\$284.00
JDL10	10				\$271.00
JDL12	12				\$269.00
JDL15	15				\$286.00
JDL17-5	17.5				\$296.00
JDL20	20				\$284.00
JDL25	25				\$287.00
JDL30	30				\$312.00
JDL35	35				\$491.00
JDL40	40		5	2.00 lb	\$481.00
JDL45	45				\$489.00
JDL50	50				\$478.00
JDL60	60				\$483.00
JDL70	70				\$451.00
JDL80	80		1	1.70 lb	\$451.00
JDL90	90				\$478.00
JDL100	100				\$452.00
JDL110	110				\$184.00
JDL125	125				\$181.00
JDL150	150			4.25 lb	\$184.00
JDL175	175				\$184.00
JDL200	200				\$184.00
JDL225	225				\$294.00
JDL250	250			1.70 lb	\$286.00
JDL300	300				\$340.00
JDL350	350				\$344.00
JDL400	400				\$312.00
JDL450	450			2.80 lb	\$508.00
JDL500	500				\$512.00
JDL600	600				\$489.00

CROSS REFERENCE				
VOLTS	EDISON	BUSSMANN	MERSEN GOLD	LITTELFUSE
600	JDL	LPJ	AJT	JTD

JDL Dimensions inches (mm)




JDL Series Dimensions - Inches [mm]										
Ampere Rating	Overall Length	Max. Dia.	Blade Length	Barrel Length	Blade Thickness	Blade Width	Mounting Hole Spacing			
Range	A	B	C	D	E	F	G	H	J	K
1-30	2.25 [57.15]	0.81 [20.6]	—	—	—	—	—	—	—	—
35-60	2.38 [60.5]	1.06 [26.92]	—	—	—	—	—	—	—	—
70-100	4.63 [117.5]	1.13 [28.6]	1 [25.4]	2.63 [66.7]	0.13 [3.2]	0.75 [19.1]	0.5 [12.7]	3.63 [92.1]	0.38 [9.5]	0.28 [7.1]
110-200	5.75 [146.1]	1.63 [41.3]	1.38 [34.9]	3 [76.2]	0.19 [4.8]	1.13 [28.6]	0.69 [17.5]	4.38 [111.1]	0.38 [9.5]	0.28 [7.1]
225-400	7.13 [181]	2.13 [54]	1.88 [47.8]	3.38 [85.8]	0.25 [6.35]	1.63 [41.3]	0.94 [23.8]	5.25 [133.4]	0.56 [14.3]	0.41 [10.3]
450-600	8 [203.2]	2.5 [63.5]	2.13 [54]	3.75 [95.3]	0.38 [9.5]	2 [50.8]	1 [25.4]	6 [152.4]	0.75 [19.1]	0.53 [13.5]

Dual Element Time-Delay Class J Fuses




AVERAGE TIME/CURRENT CURVE

Cat. No. JDL (Amp) 600V



PEAK LET-THROUGH CURRENT CURVES

Cat. No. JDL (Amp) 600V




Current-Limiting Effects

*Prop. S.C.C.	Let-Thru Current (Apparent RMS Symmetrical) JDL (600V) Fuse Ratings						
	15A	30A	60A	100A	200A	400A	600A
1,000	270	470	750	—	—	—	—±
3,000	370	670	1,130	1,640	2,360	—	—
5,000	450	800	1,420	1,910	2,760	4,400	—
10,000	550	1,000	1,730	2,450	3,520	5,540	8,000
15,000	625	1,220	1,890	2,850	4,000	6,420	9,000
20,000	700	1,330	2,120	3,090	4,400	7,000	10,000
25,000	750	1,440	2,250	3,400	5,000	7,500	11,100
30,000	800	1,530	2,370	3,650	5,140	8,000	11,800
35,000	820	1,600	2,580	3,780	5,430	8,330	12,500
40,000	900	1,640	2,670	4,000	5,640	9,000	13,270
50,000	925	1,760	2,790	4,470	6,000	9,380	13,820
60,000	1,000	1,850	3,000	4,670	6,420	10,000	15,000
80,000	1,160	2,000	3,220	5,000	7,400	11,270	16,000
100,000	1,220	2,150	3,520	5,360	7,950	12,180	17,270
150,000	1,400	2,460	4,000	6,170	9,000	14,360	19,270
200,000	1,560	2,640	4,450	7,000	10,000	15,820	20,600

*RMS Symmetrical Amperes Short-Circuit Current.

NOTEData derived from Current Limiting Curves.



Class J High-Speed Drive Fuses



1 – 60 A



70 – 600 A

EDISON JHL Class J fuses combine the performance of high-speed semiconductor fuses and the convenience of Class J branch-circuit fuses in one small package, allowing maximum protection for AC and DC drives* and controllers.

** Note: JHL fuses can be used with GS and DURApulse drives in non-UL applications. Fuse the drive according to NEC guidelines (NEC Article 430). For UL applications, GS and DURApulse drives require Class T fuses (refer to the drive's user manual for details).*

Applications

- AC and DC drives
- Electronic motor controllers
- Power semiconductor devices that utilize diodes, GTOs, SCR's, or SSR's

JHL Features

- Space saving Class J dimensions allow the use of readily available Class J fuse blocks, holders, and switches
- Allows the lowest I²t let-through energy of any branch-circuit overcurrent protective device
- Works with existing and new variable speed drives and electronic motor controllers
- Meets UL, CSA, and NEC requirements for branch circuit protection devices

Specifications

Voltage Rating: 600 VAC; 450 VDC

Ampere Rating: 1 – 600 Amps

Interrupting Rating:
200,000 RMS Symmetrical Amps;
100,000 DC Amps


Current Limiting: Class J Fuse

Agency Approvals


- UL, std 248-8, Class J, Guide JDDZ, File E162363
- CSA Certified, C22.2 # 248.8, Class 1422-02, File 700489
- RoHS compliant

CROSS REFERENCE

VOLTS	EDISON	COOPER / BUSSMANN	FERRAZ / MERSEN	LITTELFUSE
600	JHL	DFJ	HSJ	-

JHL Series Class J High-Speed Drive Fuses									
Part Number	AMP Rating	Rated Voltage (max)	Pcs/ Pkg	Pkg Weight (lb[kg])	Price	Part Number	Pcs/ Pkg	Pkg Weight (lb[kg])	Price
JHL1	1	600 VAC 450 VDC	10	1.0 [0.45]	\$251.00	JHL1-1	1	0.10 [0.05]	\$34.00
JHL2	2				\$271.00	JHL2-1			\$34.00
JHL3	3				\$251.00	JHL3-1			\$34.00
JHL4	4				\$284.00	JHL4-1			\$35.50
JHL5	5				\$271.00	JHL5-1			\$34.00
JHL6	6				\$271.00	JHL6-1			\$34.00
JHL8	8				\$287.00	JHL8-1			\$35.50
JHL10	10				\$271.00	JHL10-1			\$34.00
JHL12	12				\$287.00	JHL12-1			\$35.50
JHL15	15				\$273.00	JHL15-1			\$34.00
JHL17P5	17.5				\$279.00	JHL17P5-1			\$32.50
JHL20	20				\$273.00	JHL20-1			\$34.00
JHL25	25				\$273.00	JHL25-1			\$34.00
JHL30	30				\$273.00	JHL30-1			\$34.00
JHL35	35		1.5 [0.68]		JHL35-1	\$54.00			
JHL40	40				JHL40-1	\$54.00			
JHL45	45				JHL45-1	\$54.00			
JHL50	50				JHL50-1	\$54.00			
JHL60	60				JHL60-1	\$58.00			
JHL70	70			1	0.30 [0.14]	\$95.00		<div>JHL Dimensions</div> 	
JHL80	80					\$95.00			
JHL90	90		\$100.00						
JHL100	100		0.70 [0.32]		\$95.00				
JHL110	110				\$183.00				
JHL125	125		0.8 [0.36]		\$191.00				
JHL150	150				\$191.00				
JHL175	175				\$188.00				
JHL200	200		1.6 [0.73]		\$191.00				
JHL225	225				\$325.00				
JHL250	250				\$294.00				
JHL300	300		2.6 [1.18]		\$294.00				
JHL350	350				\$306.00				
JHL400	400				\$294.00				
JHL450	450				\$446.00				
JHL500	500				\$461.00				
JHL600	600				\$451.00				

JHL Dimensions



JHL Series Dimensions - Inches [mm]


Range	A	B	C	D	E	F	H	J	K
1-30	2.25 [57.2]	0.81 [20.6]	-	-	-	-	-	-	-
35-60	2.38 [60.5]	1.06 [26.9]	-	-	-	-	-	-	-
70-100	4.63 [117.6]	1.13 [28.7]	1.00 [25.4]	2.63 [66.8]	0.13 [3.3]	0.75 [19.1]	3.63 [92.2]	0.43 [10.9]	0.28 [7.1]
110-200	5.75 [146.1]	1.63 [41.4]	1.38 [35.1]	3.00 [76.2]	0.19 [4.8]	1.13 [28.7]	4.38 [111.3]	0.43 [10.9]	0.28 [7.1]
225-400	7.13 [181.1]	2.11 [53.6]	1.88 [47.8]	3.38 [85.9]	0.25 [6.4]	1.63 [41.4]	5.25 [133.4]	0.58 [14.7]	0.41 [10.4]
450-600	8.00 [203.2]	2.50 [63.5]	2.13 [54.1]	3.75 [95.3]	0.38 [9.7]	2.00 [50.8]	6.00 [152.4]	0.74 [18.8]	0.53 [13.5]

Class J High-Speed Drive Fuses

Time-Current Characteristic Curves



Time-Current Characteristic Curves – Average Melt – JHL Fuses




Class J High-Speed Drive Fuses

Current Limitation Curves



Current Limitation Curves – JHL Fuses



Dual Element Time-Delay Class RK5 Fuses



ECNR40



ECNR70



ECNR150



ECSR5



ECSR100



ECSR200

These fuses are recommended for AC power distribution system mains, feeders and branch circuits having inductive loads (motors, transformers) or non-inductive loads (lighting, heating) where the available short-circuit current does not exceed 200,000 RMS symmetrical amperes. These dual element, time-delay fuses have minimum industry standard time-delay of 10 seconds at 5 times the fuse rating (8 sec. minimum for 250V, 30A and less). The time-delay characteristics of these fuses typically allows them to be sized closer to the running ampacity of inductive loads to reduce cost and provide improved overcurrent protection. These fuses will override normal equipment current surges to reduce unnecessary fuse openings. They are the most popular fuses used in the industry and the most economical for most applications, especially motors and transformers. They have moderate current limitation.

ECNR/ECSR

Features

- True dual - element construction allows sizing of 125% FLA for motor backup protection
- Superior overload and cycling capabilities
- Current limiting; provides component short circuit protection

Applications

- Recommended for AC power distribution system mains, feeders, and branch circuits
- Protection of motors and motor branch circuits
- Protection of transformers and other inductive loads
- All general-purpose applications including lighting, heating and other non-inductive loads

ECNR/ECSR Specifications

Voltage Rating:

- ECNR: 250 VAC
- ECSR: 600 VAC

Ampere Rating:

- ECNR: 1–600 Amps
- ECSR: 3–600 Amps

Interrupting Rating:

- 200,000 RMS Symmetrical Amps

Self-Certified DC Ratings:

- Voltage Rating:
ECNR (1–200): 125 VDC
ECNR (201–600): 250 VDC
ECSR (3–600): 300 VDC
- Self-Certified Interrupting Rating:
ECNR/ECSR 20,000 Amperes DC

Current Limiting: RK5 Fuse

Agency Approvals

- UL Listed, Class RK5, Guide JDDZ, File E162363
- CSA Certified HRCI-R per C22.2, No. 248.12

CROSS REFERENCE

VOLTS	EDISON	BUSSMANN	MERSEN GOULD	LITTELFUSE
250	ECNR	FRN-R	TR	FLNR
600	ECSR	FRS-R	TRS	FLSR

Dual Element Time-Delay Class RK5 Fuses




ECNR Series 250V Dual-element Time-delay Fuses					
Part Number	AMP Rating	Rated Voltage AC Max	Pcs/Pkg	Package Weight	Price
ECNR1	1	250V	10	0.30 lb	\$131.00
ECNR2	2				\$127.00
ECNR3	3				\$122.00
ECNR5	5				\$119.00
ECNR8	8				\$122.00
ECNR10	10				\$119.00
ECNR15	15			0.50 lb	\$93.00
ECNR20	20				\$93.00
ECNR25	25				\$93.00
ECNR30	30				\$93.00
ECNR35	35		5	1.00 lb	\$151.00
ECNR40	40				\$151.00
ECNR45	45				\$151.00
ECNR50	50				\$151.00
ECNR60	60				\$151.00
ECNR70	70			1.50 lb	\$175.00
ECNR80	80				\$175.00
ECNR90	90				\$186.00
ECNR100	100				\$175.00
ECNR125	125		1	0.77 lb	\$88.00
ECNR150	150				\$88.00
ECNR175	175			1.10 lb	\$88.00
ECNR200	200				\$88.00
ECNR225	225			1.52 lb	\$115.00
ECNR250	250				\$115.00
ECNR300	300				\$115.00
ECNR350	350				\$118.00
ECNR400	400				\$112.00
ECNR450	450			3.00 lb	\$187.00
ECNR500	500				\$187.00
ECNR600	600				\$187.00

ECSR Series 600V Dual-element Time-delay Fuses					
Part Number	AMP Rating	Rated Voltage AC Max	Pcs/Pkg	Package Weight	Price
ECSR3	3	600V	10	1.7 lb	\$217.00
ECSR4	4				\$217.00
ECSR5	5				\$217.00
ECSR6	6				\$217.00
ECSR6-25	6.25				\$226.00
ECSR7	7				\$231.00
ECSR8	8				\$217.00
ECSR10	10				\$217.00
ECSR12	12				\$217.00
ECSR15	15				\$193.00
ECSR17-5	17.5		5	3.00 lb	\$193.00
ECSR20	20				\$193.00
ECSR25	25				\$193.00
ECSR30	30				\$193.00
ECSR35	35				\$338.00
ECSR40	40				\$338.00
ECSR45	45				\$338.00
ECSR50	50				\$338.00
ECSR60	60				\$338.00
ECSR70	70		1	50.54 lb	\$363.00
ECSR80	80				\$363.00
ECSR90	90			1.00 lb	\$142.00
ECSR100	100				\$142.00
ECSR110	110		1	1.22 lb	\$142.00
ECSR125	125				\$142.00
ECSR150	150			3.00 lb	\$219.00
ECSR175	175				\$219.00
ECSR200	200				\$219.00
ECSR225	225				\$219.00
ECSR250	250				\$219.00
ECSR300	300			5.00 lb	\$321.00
ECSR350	350				\$321.00
ECSR400	400				\$321.00
ECSR450	450				\$321.00
ECSR500	500				\$321.00
ECSR600	600				\$321.00

ECNR/ECSR Dimensions

Ferrule Design – 1 through 60 Amperes

Knife Blade – 70 through 600 Amperes





Dimensions inches (mm)							
Part Number	Amps	Overall Length A	Max Diameter B	Part Number	Amps	Overall Length A	Max Diameter B
ECNR 250V	1-30	2 (50.8)	0.56 (14.2)	ECSR 600V	3-30	5 (127)	0.81 (20.6)
	35-60	3 (76.2)	0.81 (20.6)		35-60	5.5 (139.7)	1.06 (26.9)
	70-100	5.88 (149.4)	1.06 (26.9)		70-100	7.88 (200.2)	1.11 (28.2)
	110-200	7.13 (181.1)	1.56 (39.6)		110-200	9.63 (244.6)	1.61 (40.9)
	225-400	8.63 (219.2)	2.06 (52.3)		225-400	11.63 (295.4)	2.34 (59.4)
	450-600	10.38 (263.7)	2.59 (65.8)		450-600	13.38 (339.9)	2.88 (73.2)

Dual Element Time-Delay Class RK5 Fuses





ECNR Curves

AVERAGE TIME/CURRENT CURVES
Cat No. ECNR (AMP) 250 VAC



ECSR Curves

AVERAGE TIME/CURRENT CURVES
Cat No. ECSR (AMP) 600 VAC




Dual Element Time-Delay Class RK5 Fuses




ECNR/ECSR Curves

PEAK LET-THROUGH CURRENT CURVES*

ECNR (250V)



ECSR (600V)



CURRENT LIMITATION TABLES

ECNR (250V)*

Available Fault Current RMS Amps	Apparent Effective Let-Thru Amperes					
	Fuse Ampere Ratings					
	30A	60A	100A	200A	400A	600A
5,000	1,050	2,070	2,820	4,300	5,000	5,000
10,000	1,310	2,570	3,630	5,400	8,700	10,000
15,000	1,490	2,920	4,140	6,200	9,900	15,000
20,000	1,630	3,200	4,500	6,800	10,700	16,100
25,000	1,720	3,420	4,800	7,200	11,400	17,200
30,000	1,840	3,630	5,100	7,700	12,100	18,300
35,000	1,920	3,810	5,400	8,100	12,600	19,200
40,000	2,000	3,980	5,600	8,500	13,100	19,900
50,000	2,140	4,200	6,000	9,100	14,000	21,400
60,000	2,260	4,500	6,400	9,600	14,900	22,600
80,000	2,450	4,900	7,000	10,600	16,000	24,600
100,000	2,620	5,200	7,500	11,400	17,100	26,200
150,000	2,920	5,800	8,300	13,000	19,200	29,200
200,000	3,140	6,200	8,900	14,300	20,800	31,700

ECSR (600V)*

Available Fault Current RMS Amps	Apparent Effective Let-Thru Amperes					
	Fuse Ampere Ratings					
	30A	60A	100A	200A	400A	600A
5,000	1,290	2,070	2,980	5,000	5,000	5,000
10,000	1,640	2,590	3,810	6,500	8,800	10,000
15,000	1,890	2,940	4,400	7,500	10,200	15,000
20,000	2,110	3,250	4,800	8,300	11,400	18,200
25,000	2,260	3,470	5,200	8,900	12,400	19,600
30,000	2,420	3,660	5,500	9,600	13,200	21,100
35,000	2,570	3,850	5,800	10,100	14,100	22,400
40,000	2,670	4,030	6,000	10,500	14,700	23,400
50,000	2,890	4,300	6,500	11,400	16,000	25,300
60,000	3,060	4,500	6,900	12,100	17,200	27,000
80,000	3,360	4,900	7,600	13,400	19,100	29,500
100,000	3,630	5,200	8,200	14,400	20,700	31,700
150,000	4,100	5,800	9,300	16,500	23,900	36,300
200,000	4,400	6,100	10,400	18,300	26,700	39,500

*"Apparent Let-Thru Amperes" values are read from "Peak Let-Through Current Curves" and the peak current value divided by 2.3 Asymmetry Factor.

Dual Element Time-Delay Class RK1 Fuses



LENRK/LESRK Features

- True dual - element spring - trigger construction allows sizing of 125% FLA for motor backup protection
- Superior overload and cycling capabilities
- Extremely current limiting; provides superior short circuit component protection

Applications


- Recommended for AC power distribution system mains, feeders, and branch circuits
- Protection of motors and motor branch circuits
- Type 2 protection for IEC components
- All general-purpose applications including lighting, heating and other non-inductive loads

LENRK/LESRK Dimensions

Dimensions inches (mm)			
Catalog Number	Amps	Overall Length	Max Diameter
		A	B
LENRK series 250V	10-30	2 (50.8)	0.56 (14.2)
	35-60	3 (76.2)	0.81 (20.6)
	70-100	5.88 (149.4)	1.10 (27.9)
	110-200	7.13 (181.1)	1.61 (40.9)
	225-400	8.63 (219.2)	2.36 (59.9)
LESRK series 600V	450-600	10.38 (263.7)	2.88 (73.2)
	5-30	5 (127)	0.81 (20.6)
	35-60	5.5 (139.7)	1.06 (26.9)
	70-100	7.88 (200.2)	1.11 (28.2)
	110-200	9.63 (244.6)	1.61 (40.9)
	225-400	11.63 (295.4)	2.36 (59.9)
	450-600	13.38 (339.9)	2.88 (73.2)

Ferrule Design - 5 through 60 Amperes

Knife Blade - 70 through 600 Amperes



CROSS REFERENCE

VOLTS	EDISON	BUSSMANN	MERSEN GOULD	LITTELFUSE
250	LENRK	LPN-RK-SP	A2DR	LLNRK
600	LESRK	LPS-RK-SP	A6DR*	LLSRK

*Not dual element 110-600 Amp

LENRK/LESRK series fuses have up to 40% more current limitation and up to 350% more Amps-Squared-Second (I²t) limitation under fault conditions than ECNR/ECSR series fuses, reducing the potential for damage. They also offer a better selection for electrical power system designers and superior short circuit protection for breakers having inadequate interrupting ratings. ECNR/ECSR and LENRK/LESRK fuse lines are physically interchangeable (and electrically interchangeable per U.L. equipment listing conditions). We recommend them as a practical, economical way to upgrade systems in many situations.

Specifications

Voltage Rating:

- LENRK: 250 VAC
- LESRK: 600 VAC

Ampere Rating:

- LENRK: 10-600A
- LESRK: 5-600A

Interrupting Rating:

- 200,000 RMS Symmetrical Amps

Self-Certified Interrupting Rating:

- 300,000 RMS Symmetrical Amps

Self-Certified DC Ratings:

- Voltage Rating:
LENRK (10-60A) 125 VDC
LENRK (70-600A) 250 VDC
LESRK 300 VDC
Interrupting Rating: LENRK/LESRK 20,000 Amperes DC

Current Limiting: RK1 Fuse

Agency Approvals:

- UL Listed, Class RK1, Guide JDDZ, File E162363
- CSA Certified HRCI-R per C22.2, No. 248.12

LENRK Series Dual-element Time-delay Fuses

Part Number	AMP Rating	Rated Voltage AC Max	Pcs/Pkg	Package Weight	Price
LENRK10	10	250V	10	0.50 lb	\$174.00
LENRK15	15				\$118.00
LENRK20	20				\$118.00
LENRK30	30				\$118.00
LENRK60	60			1.24 lb	\$234.00
LENRK100	100		5	1.90 lb	\$242.00
LENRK200	200		1	0.90 lb	\$118.00
LENRK300	300			2.00 lb	\$166.00
LENRK400	400				\$163.00
LENRK500	500			3.00 lb	\$279.00
LENRK600	600				\$264.00

LESRK Series Dual-element Time-delay Fuses





Part Number	AMP Rating	Rated Voltage AC Max	Pcs/Pkg	Package Weight	Price
LESRK5	5	600V	10	1.60 lb	\$314.00
LESRK10	10				\$314.00
LESRK15	15				\$295.00
LESRK20	20				\$295.00
LESRK25	25				\$295.00
LESRK30	30			3.05 lb	\$425.00
LESRK40	40				\$425.00
LESRK50	50			3.10 lb	\$425.00
LESRK60	60			5	\$425.00
LESRK100	100				\$458.00
LESRK200	200		1	1.10 lb	\$209.00
LESRK300	300			2.40 lb	\$321.00
LESRK400	400				\$321.00
LESRK500	500			3.40 lb	\$462.00
LESRK600	600				\$457.00

Dual Element Time-Delay Class RK1 Fuses



LENRK/LESRK

Average Time/
Current Curves




Dual Element Time-Delay Class RK1 Fuses




PEAK LET-THROUGH CURRENT CURVES*

LENRK (250V)



LESRK (600V)



*Curves test data obtained at 15% short-circuit power factor when possible.

CURRENT LIMITATION TABLES

LENRK (250V)* RMS & Peak Let-Thru Currents (kA)

Available Fault current	Apparent Effective Let-Thru Amperes (kA)											
	30		60		100		200		400		600	
RMS Amperes	I _{RMS}	I _p	I _{RMS}	I _p	I _{RMS}	I _p	I _{RMS}	I _p	I _{RMS}	I _p	I _{RMS}	I _p
1,000	1	1	1	2	1	2	1	2	1	2	1	2
2,000	1	2	1	3	2	4	2	5	2	5	2	5
3,000	1	2	1	3	2	4	3	6	3	7	3	7
5,000	1	2	2	4	2	5	3	7	5	12	5	12
10,000	1	3	2	4	2	6	4	9	7	15	9	21
15,000	1	3	2	5	3	6	4	10	7	17	10	23
20,000	1	3	2	6	3	7	5	11	8	19	11	25
25,000	1	3	3	6	3	7	5	12	9	20	12	27
30,000	2	3	3	6	3	8	5	12	9	21	13	29
35,000	2	4	3	7	4	8	6	13	10	22	13	30
40,000	2	4	3	7	4	9	6	13	10	23	13	31
50,000	2	4	3	7	4	9	6	14	10	24	14	33
60,000	2	4	3	8	4	10	7	15	11	26	15	35
70,000	2	4	3	8	4	10	7	16	12	27	16	36
80,000	2	5	4	8	5	11	7	16	12	28	17	38
90,000	2	5	4	9	5	11	7	17	13	29	17	39
100,000	2	5	4	9	5	11	8	18	13	30	17	40
150,000	2	6	4	10	5	13	8	19	16	36	20	46
200,000	3	6	5	11	6	14	9	21	18	42	22	50

LESRK (600V)* RMS & Peak Let-Thru Currents (kA)

Available Fault current	Apparent Effective Let-Thru Amperes (kA)											
	30		60		100		200		400		600	
RMS Amperes	I _{RMS}	I _p	I _{RMS}	I _p	I _{RMS}	I _p	I _{RMS}	I _p	I _{RMS}	I _p	I _{RMS}	I _p
1,000	1	1	1	2	1	2	1	2	1	2	1	2
2,000	1	2	1	3	2	4	2	4	2	4	2	4
3,000	1	2	1	3	2	4	3	6	3	7	3	7
5,000	1	2	2	4	2	5	3	7	5	12	5	12
10,000	1	3	2	5	3	6	4	9	7	16	9	21
15,000	1	3	2	5	3	7	5	11	8	18	10	24
20,000	1	3	3	6	3	7	5	12	8	19	11	26
25,000	2	4	3	6	3	8	5	12	9	21	12	28
30,000	2	4	3	6	4	8	6	13	10	22	13	30
35,000	2	4	3	7	4	9	6	14	10	23	13	31
40,000	2	4	3	7	4	9	6	14	10	24	14	32
50,000	2	5	3	8	4	10	7	15	11	26	15	35
60,000	2	5	3	8	4	10	7	16	12	28	16	37
70,000	2	5	4	8	5	11	7	17	13	29	17	39
80,000	2	5	4	9	5	11	8	18	13	30	17	40
90,000	2	5	4	9	5	12	8	18	13	31	18	42
100,000	2	6	4	9	5	12	8	19	14	32	19	44
150,000	3	6	5	11	6	14	9	21	16	36	22	50
200,000	3	7	5	12	7	15	10	23	17	40	23	54

**"Apparent Let-Thru Amperes" values are read from "Peak Let-Through Current Curves" and the peak current value divided by 2.3 Asymmetry Factor.

Extremely Fast-Acting Class T Fuses



EDISON TJN and TJS Class T fuses are extremely fast-acting fuses in a compact, space-saving size. These fuses are ideal as the main fuse protection for panel boards, load centers, meter stacks, and AC drives.

TJN/S Features

- Extremely current limiting
- No intentional time delay; opens quickly on overload
- Silver link construction provides superior component protection against fault currents
- Space saving dimensions

Applications

- Recommended for protection of non-inductive loads such as lighting and resistance-heating circuits
- Use to protect lower interrupting-rated circuit breakers when series rated with Class T fuses
- For motor protection, size at 300% FLC; provides short-circuit protection only
- Use for short-circuit protection of AC drives

Specifications

Voltage Rating:

TJN: 300 VAC

TJS: 600 VAC

Ampere Ratings:

1–600 Amps

Interrupting Rating:

200,000 RMS Symmetrical Amps

Self-Certified Voltage Ratings (DC)

(15–600): 160 VDC

TJS (15–400): 300 VDC

Self-Certified Interrupting

Ratings (DC):

TJN (15–600): 20,000 Amps DC

TJS (15–400): 10,000 Amps DC

Current Limiting: Class T Fuse

Agency Approvals

- UL Listed, Class T, Guide JDDZ, File E162363
- CSA Certified HRCI-T per C22.2, No. 248.12

T Series 300VAC Extremely Fast-Acting Fuses					
Part Number	AMP Rating	Rated Voltage	Pcs/ Pkg	Package Weight	Price
TJN1	1	300 VAC	10	0.12 lb	\$210.00
TJN1-1			1	0.02 lb	\$27.00
TJN3	3		10	0.12 lb	\$210.00
TJN3-1			1	0.02 lb	\$27.00
TJN6	6		10	0.12 lb	\$210.00
TJN6-1			1	0.02 lb	\$27.00
TJN10	10		10	0.12 lb	\$257.00
TJN10-1			1	0.02 lb	\$31.50
TJN15	15		10	0.12 lb	\$279.00
TJN15-1			1	0.02 lb	\$35.00
TJN20	20		10	0.12 lb	\$279.00
TJN20-1			1	0.02 lb	\$34.50
TJN25	25		10	0.12 lb	\$267.00
TJN25-1			1	0.02 lb	\$34.50
TJN30	30		10	0.12 lb	\$279.00
TJN30-1			1	0.02 lb	\$35.00
TJN35	35		10	0.23 lb	\$289.00
TJN35-1			1	0.03 lb	\$35.00
TJN40	40		10	0.23 lb	\$292.00
TJN40-1			1	0.03 lb	\$35.00
TJN45	45		10	0.23 lb	\$289.00
TJN45-1			1	0.03 lb	\$35.00
TJN50	50		10	0.23 lb	\$289.00
TJN50-1			1	0.03 lb	\$35.00
TJN60	60		10	0.23 lb	\$278.00
TJN60-1			1	0.03 lb	\$35.00
TJN70	70		5	0.36 lb	\$164.00
TJN70-1			1	0.11 lb	\$38.50
TJN80	80		5	0.36 lb	\$174.00
TJN80-1			1	0.11 lb	\$43.00
TJN90	90		5	0.36 lb	\$174.00
TJN90-1			1	0.11 lb	\$43.00
TJN100	100		5	0.36 lb	\$163.00
TJN100-1			1	0.11 lb	\$38.50
TJN110	110		1	0.14 lb	\$49.00
TJN125	125		1		\$49.00
TJN150	150		1		\$54.00
TJN175	175		1		\$54.00
TJN200	200		1	0.25 lb	\$54.00
TJN225	225		1		\$125.00
TJN250	250		1		\$125.00
TJN300	300		1		\$125.00
TJN350	350		1	0.44 lb	\$108.00
TJN400	400		1		\$98.00
TJN450	450		1		\$143.00
TJN500	500		1		\$159.00
TJN600	600		1		\$159.00

T Series 600VAC Extremely Fast-Acting Fuses					
Part Number	AMP Rating	Rated Voltage	Pcs /Pkg	Package Weight	Price
TJS1	1	600 VAC	10	0.33 lb	\$203.00
TJS1-1			1	0.02 lb	\$21.50
TJS3	3		10	0.33 lb	\$203.00
TJS3-1			1	0.02 lb	\$21.50
TJS6	6		10	0.33 lb	\$203.00
TJS6-1			1	0.02 lb	\$21.50
TJS10	10		10	0.33 lb	\$231.00
TJS10-1			1	0.02 lb	\$26.50
TJS15	15		10	0.33 lb	\$232.00
TJS15-1			1	0.02 lb	\$26.50
TJS20	20		10	0.33 lb	\$231.00
TJS20-1			1	0.02 lb	\$27.00
TJS25	25		10	0.33 lb	\$232.00
TJS25-1			1	0.02 lb	\$26.50
TJS30	30		10	0.33 lb	\$217.00
TJS30-1			1	0.02 lb	\$25.00
TJS35	35		10	0.82 lb	\$323.00
TJS35-1			1	0.03 lb	\$34.50
TJS40	40		10	0.82 lb	\$354.00
TJS40-1			1	0.03 lb	\$38.50
TJS45	45		10	0.82 lb	\$372.00
TJS45-1			1	0.03 lb	\$42.00
TJS50	50		10	0.82 lb	\$327.00
TJS50-1			1	0.03 lb	\$35.50
TJS60	60		10	0.82 lb	\$324.00
TJS60-1			1	0.03 lb	\$34.00
TJS70	70		5	0.51 lb	\$236.00
TJS70-1			1	0.11 lb	\$52.00
TJS80	80		5	0.51 lb	\$266.00
TJS80-1			1	0.11 lb	\$60.00
TJS90	90		5	0.51 lb	\$299.00
TJS90-1			1	0.11 lb	\$63.00
TJS100	100		5	0.51 lb	\$266.00
TJS100-1			1	0.11 lb	\$60.00
TJS110	110		1	0.19 lb	\$62.00
TJS125	125		1		\$62.00
TJS150	150		1		\$62.00
TJS175	175		1		\$65.00
TJS200	200		1	0.46 lb	\$65.00
TJS225	225		1		\$158.00
TJS250	250		1		\$158.00
TJS300	300		1		\$178.00
TJS350	350		1	0.85 lb	\$183.00
TJS400	400		1		\$188.00
TJS450	450		1		\$371.00
TJS500	500		1		\$382.00
TJS600	600		1		\$415.00

Extremely Fast-Acting Class T Fuses





300V TJN Fuses




600V TJS Fuses

CROSS REFERENCE				
VOLTS	EDISON	BUSSMANN	MERSEN GOLD	LITTELFUSE
300	TJN	JJN	A3T	JLLN
600	TJS	JJS	A6T	JLLS

TJN & TJS Fuse Dimensions

1A to 60A TJN
1A to 30A TJS

35A to 60A TJS



70A to 600A


Fuse Type	Current Rating	Overall Length	Maximum Diameter		Barrel Length	Blade Length	Blade Thickness	Blade Width	Mounting Hole Spacing		
	Range	A	B1	B2	C	D	E	F	G	H	J
	(A)	(in [mm])									
TJN (300 VAC)	1-30	0.88 [22.4]	0.41 [10.4]	n/a	n/a (no blades)						
	35-60		0.56 [14.2]								
	70-100	2.16 [54.9]	0.82 [20.8]		0.84 [21.3]	0.66 [16.8]	0.125 [3.18]	0.75 [19.1]	0.27 [6.86]	1.56 [39.6]	0.284 [7.21]
	110-200	2.44 [62.0]	1.06 [26.9]			0.80 [20.3]	0.19 [4.83]	0.88 [22.4]	0.34 [8.64]	1.69 [42.9]	0.344 [8.74]
	225-400	2.75 [69.9]	1.33 [33.8]			0.95 [24.1]	0.25 [6.35]	1.00 [25.4]	0.42 [10.7]	1.84 [46.7]	0.406 [10.3]
	450-600	3.06 [77.7]	1.60 [40.6]			1.08 [27.4]	0.31 [7.87]	1.25 [31.8]	0.48 [12.2]	2.03 [51.6]	0.484 [12.3]
TJS (600 VAC)	1-30	1.50 [38.1]	0.56 [14.2]	1.00 [25.4]	n/a (no blades)						
	35-60	1.56 [39.6]	0.81 [20.6]								
	70-100	2.95 [74.9]	0.82 [20.8]	n/a	1.64 [41.7]	0.66 [16.8]	0.125 [3.18]	0.75 [19.1]	0.27 [6.86]	2.36 [59.9]	0.281 [7.14]
	110-200	3.25 [82.6]	1.07 [27.2]		1.66 [42.2]	0.80 [20.3]	0.19 [4.83]	0.88 [22.4]	0.34 [8.64]	2.50 [63.5]	0.344 [8.74]
	225-400	3.63 [92.2]	1.60 [40.6]		1.73 [43.9]	0.95 [24.1]	0.25 [6.35]	1.00 [25.4]	0.42 [10.7]	2.72 [69.1]	0.406 [10.3]
	450-600	3.98 [101]	2.08 [52.8]		1.78 [45.2]	1.08 [27.4]	0.31 [7.87]	1.25 [31.8]	0.48 [12.2]	2.95 [74.9]	0.484 [12.3]

Extremely Fast-Acting Class T Fuses


TJN (300 VAC) Trip Curves



Current Limitation Curves




**TJS Time-Current Characteristic Curves
- Average Melt**




TJS (600 VAC) Trip Curves

Current Limitation Curves



**TJS Time-Current Characteristic Curves
- Average Melt**



Class L Fast-Acting Current Limiting Fuses



Edison LCU UL Class L fuses are particularly suited for protection of circuit breakers with lower interrupting ratings and non-inductive loads such as lighting and heating circuits. 99% pure silver links provide low watt loss and low operating temperature at normal current levels.

**LCU601****LCU1200**

Applications

- Circuit breakers
- Drive protection
- Meets UL, NEC and CSA requirements for branch and feeder protection

Class L Features

- Fast-acting, short circuit protection
- Allows low I²t let-through energy of any branch circuit overcurrent protective device
- High grade silica-sand filler accelerates response of fuse to short circuits by having a quenching effect upon the fuse arc.
- O-ring seals maximize pressure build-up during current limiting actions and ensure filler retention.
- Silver-plated micro-peened terminals provide high electrical conductivity, minimize heat generation, and keep fuses and switches cool.
- Selective coordination (blackout prevention)
- Glass melamine tube
- Silver-plated end bells
- No fuse reducers required.

Cross Reference

Edison	Bussmann	Mersen	Littelfuse
LCU	KTU	A4BY	LDC

Specifications

Voltage Rating: 600 VAC (or less)

Ampere Rating: 601-1200 Amps

Interrupting Rating:
200,000 RMS Symmetrical Amps;

Current Limiting: Class L Fuse

Mounting: Bolt mount

Note: Fuse blocks not sold by AutomationDirect.com

Agency Approvals


- UL Listed, Std. 248-10, E162363, JDDZ
- CSA Certified, HRC-L C22.2 No. 248.10, Class 1422-02, File 53787
- RoHS compliant, CE, Reach

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.


LCU Series Class L Fast-Acting Fuses

Part Number	AMP Rating	Rated Voltage (max)	Pcs/Pkg	Weight lb [kg]	Price
LCU601	601	600VAC	1	3.64 [1.65]	\$782.00
LCU650	650				\$932.00
LCU700	700				\$782.00
LCU800	800				\$738.00
LCU1000	1000			4.04 [1.82]	\$738.00
LCU1200	1200				\$738.00

Dimensions in [mm]



±.016 [±0.39] ON ALL DIMENSIONS NOT OTHERWISE MARKED




Dimensions

Amp	A	B	C
1000-1200	2-25/64	3/8	2

Please see our website www.AutomationDirect.com for complete engineering drawings. Dimensions are approximate. Not for construction purposes.

Class L Fast-Acting Fuses


Time-Current Characteristic Curves



Note: See website for interpolation method document to address the correct method in which to interpolate the fuse curve that does not appear on the chart (601, 650, 700).

Class L Fast-Acting Fuses

Current Limitation Curves



How to Use the Let-Through Charts

Using the example given, one can determine the pertinent let-through data for the LCU800 amp fuse. The Let-Through Chart pertaining to the 800A fuse is illustrated.

Determine the PEAK let-through CURRENT.

Step 1. Enter the chart on the Prospective Short-Circuit current scale at 100,000 amps and proceed vertically until the 800A fuse curve is intersected.

Step 2. Follow horizontally until the Instantaneous Peak Let-Through Current scale is intersected.

Step 3. Read the PEAK let-through CURRENT as 50,000A. (If a fuse had not been used, the peak current would have been 200,000A.)

UL Class L bolt-on fuses rated 601 to 1200A: Mounting

To mount UL Class L fuse, use stainless steel bolts of correct number, diameter and length, stainless steel spring washers on each side of the bolt and stainless steel nuts. The nuts shall be tightened to the torque recommended by ASTM Standards for the bolt size used. The bolts shall have the largest diameter that will fit the bolt holes and length to allow full nut thread engagement. Bolts shall be installed in each fuse mounting hole or slot.

HCLR Current Limiting Class CC Fuses



Features

- Branch circuit rated for 600 VAC
- Compact dimensions
- Fast-acting design responds quickly to both overload and short-circuit current

Applications

- Lighting
- Resistive heating loads

HCLR Specifications

Fast-Acting

Voltage Rating: HCLR:
600 VAC
300 VDC (15A and 20A fuses)

Ampere Rating: 0.5–30 Amps

Interrupting Rating:
200,000 RMS Symmetrical Amps

Current Limiting: Class CC Fuse



Agency Approvals


- UL Listed, Class CC, Guide JDDZ, File E162363
- CSA Certified HRCI-MISC per C22.2, No. 248.4
- CE Compliant

HCLR Current Limiting Class CC Fuses				
Part Number	AMP Rating	Pcs/Pkg	Package Weight	Price
HCLR-5	0.5	10	0.2 lb	\$150.00
HCLR-75	0.75			\$165.00
HCLR1	1			\$144.00
HCLR1-5	1.5			\$144.00
HCLR2	2			\$144.00
HCLR2-5	2.5			\$182.00
HCLR3	3			\$144.00
HCLR3-5	3.5			\$190.00
HCLR4	4			\$152.00
HCLR5	5			\$144.00
HCLR6	6			\$149.00
HCLR7	7			\$176.00
HCLR8	8			\$152.00
HCLR9	9			\$190.00
HCLR10	10			\$144.00
HCLR12	12			\$145.00
HCLR15	15			\$144.00
HCLR20	20			\$144.00
HCLR25	25			\$152.00
HCLR30	30			\$144.00

DIMENSIONS		
Amps	Ferrule (in)	Length (in)
0.5 - 30	13/32	1-1/2

CROSS REFERENCE			
EDISON	BUSSMANN	GOULD	LITTELFUSE
HCLR	KTK-R	ATMR	KLKR

Characteristic Curves



HCTR Current Limiting Class CC Fuses



Features

- Branch circuit rated for 600 VAC
- Compact dimensions
- Time-delay design allows closer sizing for inductive loads such as control transformers and solenoids

Applications

- Primary protection for our PH series of control power transformers. See our complete selection listed at the end of this catalog section.

HCTR Specifications

Time-Delay

Voltage Rating: HCTR - 600 VAC

Ampere Rating: 0.25 - 30 Amps

Interrupting Rating:
200,000 RMS Symmetrical Amps

Current Limiting: Class CC Fuse

Agency Approvals

- UL Listed, Class CC, Guide JDDZ, File E162363
- CSA Certified HRCI-MISC per C22.2, No. 248.4
- CE Compliant

HCTR Current Limiting Class CC Fuses

Part Number	AMP Rating	Pcs/Pkg	Package Weight	Price
HCTR-25	0.25	10	0.2 lb	\$195.00
HCTR-5	0.5			\$167.00
HCTR-75	0.75			\$211.00
HCTR1	1			\$167.00
HCTR1-25	1.25			\$211.00
HCTR1-5	1.5			\$169.00
HCTR2	2			\$169.00
HCTR2-5	2.5			\$187.00
HCTR3	3			\$167.00
HCTR3-5	3.5			\$211.00
HCTR4	4			\$182.00
HCTR5	5			\$169.00
HCTR6	6			\$187.00
HCTR7-5	7.5			\$203.00
HCTR8	8			\$187.00
HCTR10	10			\$182.00
HCTR15	15			\$172.00
HCTR20	20			\$180.00
HCTR25	25			\$180.00
HCTR30	30			\$180.00


DIMENSIONS

Amps	Ferrule (in)	Length (in)
0.25 - 30	13/32	1-1/2

CROSS REFERENCE

EDISON	BUSSMANN	GOULD	LITTELFUSE
HCTR	FNQ-R	ATQR	KLDR


Time-Current Characteristic Curves - Total Clearing



HCTR Current Limiting Class CC Fuses



Instantaneous Peak Let-Thru Current



EDCC Current Limiting Class CC Fuses



EDCC Current Limiting Class CC Fuses				
Part Number	AMP Rating	Pcs/Pkg	Package Weight	Price
EDCC-5	0.5	10	0.2 lb	\$160.00
EDCC1	1			\$156.00
EDCC1-5	1.5			\$172.00
EDCC2	2			\$156.00
EDCC2-5	2.5			\$160.00
EDCC3	3			\$156.00
EDCC3-5	3.5			\$156.00
EDCC4	4			\$156.00
EDCC5	5			\$156.00
EDCC5-6	5.6			\$166.00
EDCC6	6			\$166.00
EDCC7	7			\$166.00
EDCC8	8			\$166.00
EDCC9	9			\$166.00
EDCC10	10			\$156.00
EDCC12	12			\$166.00
EDCC15	15			\$156.00
EDCC20	20			\$157.00
EDCC25	25			\$166.00
EDCC30	30			\$156.00

Features

- Branch circuit rated for 600 VAC
- Time-delay for motor branch circuit protection
- Excellent current-limiting performance
- Upgrade for standard "midget" fuses

Applications

- Use for protection of small horsepower motor circuits or other circuits requiring small dimension, time-delay fuses
- Can provide Type "2" coordinated protection for IEC or NEMA starters/contactors
- For control transformer applications, refer to HCTR fuses



EDCC Specifications

Time-Delay

Voltage Rating: EDCC
600 VAC; 300 VDC (0.5–2.25A, 20–30A)

Ampere Rating: 0.5–30 Amps

Interrupting Rating:
200,000 RMS Symmetrical Amps
20,000 Amps DC

Current Limiting: Class CC Fuse

UL Listed DC Ratings (per 198L)

Agency Approvals

- UL Listed, Class CC, Guide JDDZ, File E162363
- CSA Certified HRCI-MISC per C22.2, No. 248.4
- CE Compliant

Current-Limiting Effects EDCC (600V) Fuse Rating						
Let-Thru Current (Apparent RMS Symmetrical) Versus Fuse Ratings						
Prospective Short-Circuit Current*	1.25A	2.8A	15A	20A	25A	30A
1000	100	135	240	305	380	435
3000	140	210	350	440	575	580
5000	165	255	420	570	690	710
10,000	210	340	540	700	870	1,000
20,000	260	435	680	870	1,090	1,305
30,000	290	525	800	1,030	1,300	1,520
40,000	315	610	870	1,150	1,390	1,700
50,000	340	650	915	1,215	1,520	1,820
60,000	350	735	1,050	1,300	1,650	1,980
80,000	390	785	1,130	1,500	1,780	2,180
100,000	420	830	1,210	1,600	2,000	2,400
200,000	525	1,100	1,600	2,000	2,520	3,050

Note: RMS Symmetrical Amperes


Short-circuit Current

$I_{peak} = I_{RMS} \times 2.3$

DIMENSIONS		
Amps	Ferrule (in)	Length (in)
0.5 - 30	13/32	1-1/2

CROSS REFERENCE			
EDISON	BUSSMANN	GOULD	LITTELFUSE
EDCC	LP-CC	ATDR	CCMR

Characteristic Curves



*RMS Symmetrical Amperes Short-Circuit Current.

NOTE: To calculate I_o (I_{peak}) multiply IRMS value x 2.3.

General Purpose Midget Class MCL Fuses



Features

- Provide supplemental protection to end-use equipment
- Compact dimensions
- High interrupting rating
- Fast-acting design responds quickly to both overloads and short-circuit current

Applications

- Control circuits, electronic equipment protection, street lighting holders, and HID lighting

MCL Specifications

Fast-Acting

Voltage Rating: MCL - 600 VAC

Ampere Rating: 0.5 - 50 Amps

Interrupting Rating: 100,000 RMS Amps

Agency Approvals


- (0.5 - 30) UL Listed, File E162443
- (0.5 - 30) CSA Certified C22.2, Part 59.2, LR700489
- CE Compliant

MCL General Purpose Midget Class Fuses

Part Number	AMP Rating	Pcs/Pkg	Package Weight	Price
MCL-5	0.5	10	0.2 lb	\$188.00
MCL1	1			\$168.00
MCL1-5	1.5			\$190.00
MCL2	2			\$175.00
MCL2-5	2.5			\$220.00
MCL3	3			\$168.00
MCL3-5	3.5			\$228.00
MCL4	4			\$180.00
MCL5	5			\$168.00
MCL6	6			\$164.00
MCL8	8			\$172.00
MCL10	10			\$168.00
MCL12	12			\$210.00
MCL15	15			\$168.00
MCL20	20			\$168.00
MCL25	25			\$175.00
MCL30	30			\$168.00
MCL35*	35			\$228.00
MCL40*	40			\$205.00
MCL50	50			\$232.00

*Note: Max continuous load 25A. Not UL.

Characteristic Curves



DIMENSIONS

Amps	Ferrule (in)	Length (in)
0.5 - 50	13/32	1-1/2

CROSS REFERENCE

EDISON	BUSSMANN	GOULD	LITTELFUSE
MCL	KTK	ATM	KLK

General Purpose Midget Class MOL Fuses



Features

- Provide supplemental protection to end-use equipment
- Compact dimensions
- Economical laminated paper tube design

Applications

- Supplemental protection for non-inductive control and lighting circuits

MOL Specifications

Fast-Acting

Voltage Rating: MOL:

0.5 to 15 Amps - 250 VAC

20 to 30 Amps - 125 VAC

Ampere Rating: 0.5 - 30 Amps

Interrupting Rating: 10,000 RMS Amps

Agency Approvals

- (0.5 - 30) UL Listed to 198G, File E162443
- (0.5 - 30) CSA Certified C22.2, Part 59.2, LR700489
- CE Compliant

MOL General Purpose Midget Class Fuses

Part Number	AMP Rating	Pcs/Pkg	Package Weight	Price
MOL-5	0.5	10	0.2 lb	\$56.00
MOL1	1			\$36.50
MOL1-5	1.5			\$56.00
MOL2	2			\$36.50
MOL2-5	2.5			\$56.00
MOL3	3			\$36.50
MOL4	4			\$46.50
MOL5	5			\$36.50
MOL6	6			\$36.50
MOL8	8			\$40.00
MOL10	10			\$29.00
MOL15	15			\$33.50
MOL20	20			\$44.50
MOL25	25			\$45.00
MOL30	30			\$41.50


DIMENSIONS

Amps	Ferrule (in)	Length (in)
0.5 - 30	13/32	1-1/2

CROSS REFERENCE

EDISON	BUSSMANN	GOULD	LITTELFUSE
MOL	BAF/BAN	OTM	BLF

Characteristic Curves



General Purpose Midget Class MEQ Fuses



Features

- Compact dimensions
- Fiber tube construction
- Time-delay allows harmless inductive surges to pass without needless fuse opening

Applications

- Supplemental protection of transformers, solenoids, and other high-inrush circuits
- For motor branch circuit applications, refer to EDCC fuses

MEQ Specifications

Time-Delay

Voltage Rating: MEQ - 500 VAC

Ampere Rating: 0.25 - 30 Amps

Interrupting Rating: 10,000 RMS Amps

Agency Approvals

- (0.25 - 30) UL Listed, File E162443
- (0.25 - 30) CSA Certified C22.2, Part 59.2, LR700489
- CE Compliant




MEQ General Purpose Midget Class Fuses				
Part Number	AMP Rating	Pcs/Pkg	Package Weight	Price
MEQ-25	0.25	10	0.2 lb	\$189.00
MEQ-5	0.5			\$184.00
MEQ1	1			\$171.00
MEQ1-5	1.5			\$184.00
MEQ2	2			\$171.00
MEQ2-5	2.5			\$184.00
MEQ3	3			\$171.00
MEQ3-5	3.5			\$198.00
MEQ4	4			\$171.00
MEQ4-5	4.5			\$214.00
MEQ5	5			\$171.00
MEQ6	6			\$171.00
MEQ7	7			\$184.00
MEQ8	8			\$171.00
MEQ10	10			\$171.00
MEQ12	12			\$179.00
MEQ15	15			\$171.00
MEQ20	20			\$171.00
MEQ25	25			\$171.00
MEQ30	30			\$171.00

DIMENSIONS		
Amps	Ferrule (in)	Length (in)
0.25 - 30	13/32	1-1/2

CROSS REFERENCE			
EDISON	BUSSMANN	GOULD	LITTELFUSE
MEQ	FNQ	ATQ	FLQ

Characteristic Curves



General Purpose Midget Class MEN Fuses



Features

- Compact dimensions
- Fiber tube construction
- Dual-element construction allows harmless inductive surges to pass without opening

Applications

- Supplemental protection of small motors, transformers, solenoids, and other high-inrush power electronic circuits
- For motor branch circuit applications, refer to EDCC fuses

MEN Specifications

Time-Delay

Voltage Rating: MEN - 250 VAC

Ampere Rating: 0.5 - 30 Amps

Interrupting Rating: 10,000 RMS Amps @ 125V

Agency Approvals

- UL Listed, File E162443
- CSA Certified C22.2, Part 59.2, LR700489
- CE Compliant

MEN General Purpose Midget Class Fuses

Part Number	AMP Rating	Pcs/Pkg	Package Weight	Price
MEN-5	0.5	10	0.2 lb	\$86.00
MEN-6	0.6			\$86.00
MEN1	1			\$82.00
MEN1-4	1.4			\$106.00
MEN1-5	1.5			\$110.00
MEN2	2			\$73.00
MEN2-5	2.5			\$84.00
MEN3	3			\$78.00
MEN3-5	3.5			\$81.00
MEN4	4			\$78.00
MEN5	5			\$73.00
MEN6	6			\$84.00
MEN7	7			\$81.00
MEN8	8			\$80.00
MEN10	10			\$73.00
MEN12	12			\$85.00
MEN15	15			\$80.00
MEN20	20			\$80.00
MEN25	25			\$90.00
MEN30	30			\$80.00


DIMENSIONS

Amps	Ferrule (in)	Length (in)
0.5 - 30	13/32	1-1/2

CROSS REFERENCE

EDISON	BUSSMANN	GOULD	LITTELFUSE
MEN	FNM	TRM	FLM

Characteristic Curves



Small Dimension Fast-Acting ABC Fuses



Features

- Compact dimensions 1/4" x 1-1/4", (6.3 mm x 32 mm)
- Ceramic tube construction
- Fast-acting
- Fit on our DN-F6 fuse terminal blocks sold in Wiring Solutions section of this catalog
- RoHS Compliant

Applications

- Supplemental protection for electronic applications

ABC Specifications

Voltage Rating: ABC - See table below

Ampere Rating: 0.5 - 30 Amps

Interrupting Rating: See table below

Environmental Data

- Shock: 0.5A - MIL-STD-202, Method 213, Test Condition I;
- 1A thru 30A - MIL-STD-202, Method 207, (HI Shock)
- Vibration: 0.5A thru 30A - MIL-STD-202, Method 204, Test Condition C (except 5g, 500 HZ)

Agency Approvals

- UL Listed product meets standard 248-14
- UL Listed Guide and File numbers (ABC 0.5-15A): JDYX and E19180
- UL Recognition Guide and File numbers (ABC 20-30A): JDYX2 and E19180
- CSA Certification Record No: 053787, Class No: 1422 01 and 1422 30
- RoHS

ABC Small Dimension Fast-Acting Fuses

Part Number	AMP Rating	Rated Voltage		AC Interrupting Rating*		DC Interrupting Rating*		Melting I2t**	Voltage Drop***	Pcs/Pkg	Package Weight (lb)	Price	
		AC Max	DC Max	250V	125V	125V	75V						
ABC-5	0.5	250V	125V	35A	10000A	10000A	-	0.19	0.51	5	0.045	\$11.00	
ABC-75	0.75							0.8	0.42			\$11.00	
ABC1	1							1.4	0.35			\$11.00	
ABC2	2			100A				4.2	0.35			\$11.00	
ABC3	3							19.5	0.25			\$11.00	
ABC4	4							29.1	0.25			\$11.00	
ABC5	5			200A				16.4	0.23			\$10.50	
ABC6	6							31.6	0.24			\$10.50	
ABC7	7							109.3	0.17			\$10.50	
ABC8	8							111.9	0.17			\$10.50	
ABC10	10							215.6	0.15			\$10.50	
ABC12	12							750A	129.6			0.11	\$10.50
ABC15	15			200.2					0.12			\$10.50	
ABC20	20			400A	550.8		0.13		\$15.50				
ABC25	25			200A	1000A		400A	1000A	839.3			0.12	\$15.50
ABC30	30						1429	0.14	\$15.50				

* Interrupting ratings were measured at 70% – 80% power factor on AC, and at a time constant described in UL 198L.

** Typical Melting I₂t (A²sec) – measured at listed interrupting rating and rated voltage (at 70% to 80% power factor on AC).

*** Typical Voltage Drop – measured at 25°C ± 3°C ambient temperature at rated current.

For mounting and wiring ABC fuses, see our DN-F6 Series fuse blocks in the Terminal Blocks and Wiring Solutions section.

CROSS REFERENCE


OLD EDISON	BUSSMANN	MERSEN GOULD	LITTELFUSE
BBC	ABC	GAB	314

Small Dimension Fast-Acting ABC Fuses




TIME CURRENT CURVE

CURRENT IN AMPERES



Dimensions

mm [in]



ABC Electrical Characteristics

Rated Current	% of Amp Rating	Opening Time
0.5 to 30 Amps	100	4 hours minimum
	135	60 minutes maximum
	200	120 seconds maximum

Small Dimension Fast-Acting AGC Fuses



Applications

- Supplemental protection for electronic applications

AGC Specifications

Voltage Rating: AGC - See table below

Ampere Rating: 0.10 - 30 Amps

Interrupting Rating: See table below

Environmental Data

- Shock: 0.1A thru 0.75A - MIL-STD-202, Method 213, Test Condition I;
- 1A thru 30A - MIL-STD-202, Method 207, (HI shock)
- Vibration: 0.1A thru 30A - MIL-STD-202, Method 204, Test condition A (except 5g, 500 HZ)

Features

- Compact dimensions 1/4" x 1-1/4", (6.3 mm x 32 mm)
- Glass tube construction, with nickel plated brass endcaps
- Fast-acting
- RoHS Compliant

Agency Approvals

- UL Listed product meets standard 248-14
- UL Listed Card: (0.1-10A): JDYX E19180
- UL Recognition Card: (15-30A): JDYX2 E19180
- CSA Certification 053787
(Class No. 1422 01 and 1422 30)
- RoHS

AGC Small Dimension Fast-Acting Fuses

Part Number	AMP Rating	Rated Voltage	AC Interrupting Rating*			Melting I2t**	Voltage Drop mv***	Pcs/Pkg	Package Weight (lb.)	Price
		AC Max	250V	125V	32V					
AGC-1	0.10	250V	35A	10000A	-	0.000787	6.00	5	0.035	\$14.50
AGC-125	0.125					0.00131	4.67			\$14.50
AGC-25	0.25					0.0148	0.89			\$8.25
AGC-5	0.5					0.269	0.59			\$5.50
AGC-75	0.75					0.815	0.37			\$5.50
AGC1	1					1.615	0.31			\$3.50
AGC1-5	1.5		100A			0.0149	0.27			\$3.50
AGC2	2					0.00509	0.28			\$3.50
AGC2-5	2.5					0.00879	0.31			\$3.50
AGC3	3					0.0167	0.025			\$3.50
AGC4	4		200A			0.0305	0.22			\$4.50
AGC5	5					0.045	0.23			\$5.50
AGC6	6					0.071	0.23			\$5.75
AGC7	7					0.105	0.23			\$5.75
AGC7-5	7.5					-	-			\$5.00
AGC8	8					0.152	0.19			\$5.00
AGC10	10					0.492	0.20			\$5.00
AGC15	15	32V	-	-	1000A	0.566	0.14			\$4.25
AGC20	20					1.438	0.12			\$4.25
AGC25	25					2.109	0.11			\$4.25
AGC30	30					3.807	0.12			\$4.25

*Note: Interrupting ratings were measured at 70% - 80% power factor on AC, and at a time constant described in UL 198L.

** Typical Melting I²t (A²Sec) - measured at listed interrupting rating and rated voltage (at 70% to 80% power factor on AC)

*** Typical Voltage Drop - measured at 25°C ± 3°C ambient temperature at rated current.


CROSS REFERENCE			
OLD EDISON	BUSSMANN	MERSEN GOULD	LITTELFUSE
BGC	AGC	GGC	312

For mounting and wiring AGC fuses, see our DN-F6 Series fuse blocks in the Terminal Blocks and Wiring Solutions section.

Small Dimension Fast-Acting AGC Fuses




TIME CURRENT CURVES



Dimensions

mm [in]



AGC Electrical Characteristics

Rated Current	% of Amp Rating	Opening Time
0.1 to 30 Amps	100	None
	135	60 minutes maximum
	200	120 seconds maximum

5x20mm Glass Fast-Acting GMA Fuses



Features

- Compact dimensions, 0.197" x 0.788" (5mm x 20mm)
- Glass tube construction with nickel-plated brass end caps
- Fast-acting, low breaking capacity
- RoHS Compliant

Applications

- Supplemental protection for electronic applications

GMA Specifications

Voltage Rating: GMA - See table below

Ampere Rating: 0.063 - 15 Amps

Interrupting Rating: See table below

Agency Approvals

- Designed to UL/CSA 248-14
- UL Listed, Guide JDYX, File E19180, 63 mA-6A
- UL Recognition, Guide JDYX2, File E19180, 7A-15A
- CSA Certified, Class 1422-01, File 053787, 63 mA-6A
- RoHS

GMA Series 5x20mm Glass, Fast-Acting Fuses

Part Number	AMP Rating	Rated Voltage	AC Interrupting Rating*		Typical Pre-Arc I2t AC**	Voltage Drop mv***	Pcs/Pkg	Package Weight (lb.)	Price
		AC Max	250V	125V					
GMA-063	0.063	250V	35A	10000A	0.00024	4700	5	0.1	\$12.00
GMA-1	0.10				0.0001	4300			\$11.00
GMA-25	0.25				0.018	2200			\$8.25
GMA-5	0.5				0.15	230			\$7.25
GMA1	1				0.48	300			\$7.25
GMA1-5	1.5		1.6		270	\$7.25			
GMA1-6	1.6		2.0		260	\$7.25			
GMA2	2		3.1		250	\$7.25			
GMA2-5	2.5		4.9		240	\$7.25			
GMA3	3		8.8		215	\$7.25			
GMA4	4	125V	-	200A	19	205			\$7.25
GMA5	5				29	200			\$7.25
GMA6	6				45	180			\$7.25
GMA7	7				150	110			\$7.50
GMA8	8				280	110			\$7.50
GMA10	10			280	110	\$7.50			
GMA15	15			950	100	\$7.50			

*Note: Interrupting ratings for 63 mA - 6A were measured at 70% - 80% power factor on AC; interrupting ratings for 7A - 15A were measured at 100% power factor on AC.

** Typical pre-arcing I_{2t} (A²Sec) - measured at listed interrupting rating and rated voltage (at 70% to 80% power factor on AC)


*** Typical Voltage Drop - measured at 20°C ambient temperature at rated current.

For mounting and wiring GMA fuses, see our DN-F10 Series fuse blocks in the Terminal Blocks and Wiring Solutions section.


CROSS REFERENCE

OLD EDISON	BUSSMANN	MERSEN GOULD	LITTELFUSE
BMA	GMA	GGM	235

5x20mm Glass Fast-Acting GMA Fuses



Dimensions (mm)



GMA Electrical Characteristics		
Rated Current	% of Amp Rating	Opening Time
63 mA to 10 Amps	100	None
	135	60 minutes maximum
	200	2 minutes maximum

5x20mm Glass Medium Time-Delay GMC Fuses



Features

- Compact dimensions, 0.197" x 0.788" (5 mm x 20 mm)
- Glass tube construction with nickel-plated brass end caps
- Medium time-delay, low breaking capacity
- RoHS

Applications

- Supplemental protection for electronic applications

GMC Specifications

Voltage Rating: GMC - See table below
Ampere Rating: 0.5 - 10 Amps

Interrupting Rating: See table below

Agency Approvals

- Designed to UL/CSA 248-14
- UL Listed, Guide JDYX, File E19180, 0.5A - 5A
- UL Recognition, Guide JDYX2, File E19180, 10A
- CSA Certified, Class 1422-01, File 053787, 0.5A - 5A
- RoHS

GMC Series 5x20mm Glass, Medium Time-Delay Fuses

Part Number	AMP Rating	Rated Voltage	AC Interrupting Rating*		Typical Pre-Arc I2t AC**	Voltage Drop mv***	Pcs/Pkg	Package Weight (lb.)	Price
		AC Max	250V	125V					
GMC-5	0.5	250V	35A	10000A	0.41	370	5	0.025	\$12.00
GMC1	1				1.8	250			\$12.00
GMC2	2		100A		8.9	130			\$12.00
GMC3	3				19	130			\$12.00
GMC4	4	125V	-		36	120			\$12.00
GMC5	5				58	120			\$12.00
GMC10	10				200A	300			110

*Note: Interrupting ratings for 63 mA - 6A were measured at 70% - 80% power factor on AC; interrupting ratings for 7A - 15 A were measured at 100% power factor on AC.

** Typical pre-arcing I_{2t} (A²Sec) - measured at listed interrupting rating and rated voltage.


*** Typical Voltage Drop - measured at 20°C ambient temperature at rated current.

For mounting and wiring GMC fuses, see our DN-F10 Series fuse blocks in the Terminal Blocks and Wiring Solutions section.

CROSS REFERENCE


OLD EDISON	BUSSMANN	MERSEN GOULD	LITTELFUSE
none	GMC	GSC	none

5x20mm Glass Medium Time-Delay GMC Fuses



Dimensions

(mm)



GMC Electrical Characteristics

Rated Current	% of Amp Rating	Opening Time
0.5A to 10 Amps	100	None
	135	60 minutes maximum
	200	2 minutes maximum

Small Dimension Time-Delay MDA Fuses



Features

- Compact dimensions 1/4" x 1-1/4", (6.3 mm x 32 mm)
- Ceramic tube construction with nickel-plated brass end caps
- Time-delay
- RoHS

Applications

- Supplemental protection for electronic applications

MDA Specifications

Voltage Rating: MDA - See table below

Ampere Rating: 0.5 - 20 Amps

Interrupting Rating: See table below

Environmental Data

- Shock: 0.5A : MIL-STD-202, Method 213, Test Condition I;
- 1A thru 20A: MIL-STD-202, Method 207, (HI shock)
- Vibration: 0.5A: MIL-STD-202, Method 201;
- 0.5A thru 20A: MIL-STD-202, Method 204, Test condition C (except 5g, 500 HZ)

Agency Approvals

- UL Listed product meets standard 248-14
- UL Listed Card: MDA 0.5-20A (Guide JDYX, File E19180)
- CSA Certification File 053787: MDA 0.5-15 (Class No. 1422-01)
- RoHS

MDA Small Dimension Time-Delay Fuses

Part Number	AMP Rating	Rated Voltage		AC Interrupting Rating*		DC Interrupting Rating	Melting I2t**	Voltage Drop mv***	Pcs/Pkg	Package Weight (lb.)	Price
		AC Max	DC Max	250V	125V	125V					
MDA-5	0.5	250V	—	35A	10000A	—	2.3	1.42	5	0.0425 lb	\$29.50
MDA1	1						11.1	1.03			\$29.50
MDA2	2			100A			64.0	0.623			\$29.50
MDA3	3						40.9	0.182			\$19.00
MDA4	4						134.0	0.162			\$19.00
MDA5	5			200A			345.9	0.145			\$19.00
MDA8	8						944.0	0.134			\$19.00
MDA10	10						1491.3	n/a			\$19.00
MDA12	12						113.8	0.114			\$19.00
MDA15	15						206.2	0.107			\$19.00
MDA20	20		125V	1500A			10000A	439.5			0.095

*Note: Interrupting ratings were measured at 70% - 80% power factor on AC, and at a time constant described in UL 198L.

** Typical Melting I₂t (A²Sec) - measured at listed interrupting rating and rated voltage (at 70% to 80% power factor on AC)


*** Typical Voltage Drop - measured at 25°C ± 3°C ambient temperature at rated current.

For mounting and wiring MDA fuses, see our DN-F6 Series fuse blocks in the Terminal Blocks and Wiring Solutions section.


CROSS REFERENCE

OLD EDISON	BUSSMANN	MERSEN GOULD	LITTELFUSE
BDA	MDA	None	326

Small Dimension Time-Delay MDA Fuses



Dimensions (mm/inches)



MDA Electrical Characteristics

Rated Current	% of Amp Rating	Opening Time
0.5 to 20 Amps	100	None
	135	60 minutes maximum
	200	120 seconds maximum

Small Dimension Time-Delay MDL Fuses



Features

- Compact dimensions 1/4" x 1-1/4", (6.3mm x 32mm)
- Glass tube construction with nickel-plated brass end caps
- Time-delay
- RoHS Compliant

Applications

- Supplemental protection for electronic applications

MDL Specifications

Voltage Rating: MDL - See table below

Ampere Rating: 0.0625 - 20 Amps

Interrupting Rating: See table below

Environmental Data

- Shock: 0.0625A MIL-STD-202, Method 213, Test Condition I;
- 1A thru 20A: MIL-STD-202, Method 207, (HI shock)

Vibration: 0.0625A: MIL-STD-202, Method 201;
0.25A thru 20A: MIL-STD-202, Method 204, Test condition C (except 5g, 500 HZ)

Agency Approvals

- UL Listed product meets standard 248-14
- UL Listed Card: MDL 0.0625-8A (Guide JDYX, File E19180)
- UL Recognized Card: MDL 9-20A (Guide JDYX2, File E19180)
- CSA Certification File 053787: MDA 0.25-15A (Class No. 1422-01)
- RoHS

MDL Small Dimension Time-Delay Fuses

Part Number	AMP Rating	Rated Voltage	AC Interrupting Rating*			Melting I2t**	Voltage Drop mv***	Pcs/Pkg	Package Weight (lb.)	Price
		AC Max	250V	125V	32V					
MDL-0625	0.0625	250V	35A	10000A	-	0.0046	2.79	5	0.1	\$29.00
MDL-25	0.25					0.447	0.965			\$17.50
MDL-5	0.5					1.656	1.27			\$14.50
MDL1	1					11.498	0.995			\$16.00
MDL1-5	1.5					22.7	0.721			\$12.50
MDL2	2		100A			62.3	0.644			\$12.50
MDL2-5	2.5					63.1	0.410			\$13.50
MDL3	3					67.5	0.345			\$12.50
MDL4	4					19.3	0.187			\$12.50
MDL5	5					32.0	0.160			\$12.50
MDL6	6		200A			37.4	0.155			\$12.50
MDL6-25	6.25					38.7	0.152			\$13.50
MDL7	7					42.7	0.140			\$13.50
MDL8	8					47.8	0.119			\$12.50
MDL10	10	32V		-	-	1000A	64.4	0.114	\$16.00	
MDL15	15		354.0				0.130	\$18.00		
MDL20	20		2914.0				0.530	\$16.50		

*Note: Interrupting ratings were measured at 70% - 80% power factor on AC, and at a time constant described in UL 198L.

** Typical Melting I2t (A2Sec) - measured at listed interrupting rating and rated voltage (at 70% to 80% power factor on AC)


*** Typical Voltage Drop - measured at 25°C ± 3°C ambient temperature at rated current.

For mounting and wiring MDL fuses, see our DN-F6 Series fuse blocks in the Terminal Blocks and Wiring Solutions section.


CROSS REFERENCE

OLD EDISON	BUSSMANN	MERSEN GOULD	LITTELFUSE
BDL	MDL	GDL	313

Small Dimension Time-Delay MDL Fuses



Dimensions (mm/inches)



MDL Electrical Characteristics

Rated Current	% of Amp Rating	Opening Time
0.0625 to 20 Amps	100	None
	135	60 minutes maximum
	200	120 seconds maximum
0.0625 to 3 Amps	200	5 seconds minimum
4 to 8 Amps	200	12 seconds minimum

5x20mm Fast-Acting S500 Series Fuses



Features

- Compact dimensions, 0.197" x 0.788" (5 mm x 20 mm)
- Glass tube construction with nickel-plated brass end caps
- Fast-acting, low breaking capacity
- Designed to IEC 60127-2 (32mA-6.3A)
- RoHS Compliant

Applications

- Supplemental protection for electronic applications

Agency Approvals

- UL Recognized Card: (0.5A-10A) Guide JDYX2, File E19180
- CSA Component Acceptance File 53787
- Semko Approval 160 mA-400 mA and 800 mA-10A
- VDE Approval 0.32A-10A
- BSI Approval 0.32A-10A
- IMQ Approval 0.32A-10A
- RoHS

S500 Specifications

Voltage Rating: See table below

Ampere Rating: 0.32 - 10 Amps

Interrupting Rating: See table below

S500 Series 5x20 mm Glass Fast-acting Fuses								
Part Number	AMP Rating	Rated Voltage	AC Interrupting Rating at Rated Voltage (50Hz)	Typical Melting I _{2t} AC*	Voltage Drop mv**	Pcs/Pkg	Package Weight (lb.)	Price
		AC Max						
S500-32-R	0.032	250V	35A	0.000047	3200	5	0.025	\$24.00
S500-5-R	0.5			0.18	220			\$14.50
S5001-R	1			0.60	200			\$14.50
S5001-6-R	1.6			1.6	190			\$14.50
S5002-R	2			4.2	150			\$14.50
S5003-15-R	3.15			13	130			\$14.50
S5004-R	4		40A	22	130			\$14.50
S5005-R	5		50A	42	120			\$14.50
S5006-3-R	6.3		63A	69	120			\$14.50
S5008-R	8		80A	—	—			\$15.50
S50010-R	10		100A	—	—			\$15.50

*Note: Typical Melting I_{2t} (A2Sec) - measured at listed interrupting rating and rated voltage.

** Typical Voltage Drop - measured at 20°C ambient temperature at rated current.


For mounting and wiring S500 fuses, see our DN-F10 Series fuse blocks in the Terminal Blocks and Wiring Solutions section.

CROSS REFERENCE			
OLD EDISON	BUSSMANN	MERSEN GOULD	LITTELFUSE
GDB/BDB	GDB	GSB	217

5x20 mm Fast-Acting S500 Series Fuses




TIME CURRENT CURVE
Time-Current Characteristic Curves—Average Melt



Dimensions

mm (inches)



S500 Electrical Characteristics							
IN	1.5 In min	2.1 In max	2.75 In min	2.75 In max	4 In min	4 In max	10 In max
0.32A to 6.3A	60min	30min	50ms	2sec	10ms	300ms	20ms

5x20 mm Time-Delay S506 Series Fuses



Features

- Compact dimensions, 0.197" x 0.788" (5 mm x 20 mm)
- Glass tube construction with nickel-plated brass end caps
- Time-delay, low breaking capacity
- Designed to IEC 60127-2 (32 mA-10A)
- RoHS Compliant

Applications

- Supplemental protection for electronic applications

Agency Approvals:

- UL Recognized Card: (0.25A-10A) Guide JDYX2, File E19180
- CSA Component Acceptance File 053787
- Semko Approval 0.25-10A
- VDE Approval 0.25-10A
- BSI Approval 0.25-10A
- IMQ Approval 0.25-10A
- MITI Approval, 0.25-10A
- RoHS

S506 Specifications

Voltage Rating: See table below

Ampere Rating: 0.25 - 6.3 Amps

Interrupting Rating: See table below

S506 Series 5x20 mm Glass Time-delay Fuses								
Part Number	AMP Rating	Rated Voltage	AC Interrupting Rating at Rated Voltage (50Hz)	Typical Melting I _{2t} AC*	Voltage Drop mv**	Pcs/Pkg	Package Weight (lb.)	Price
		AC Max						
S506-25-R	0.25	250V	35A	0.17	270	5/1	0.025	\$18.00
S506-5-R	0.5			0.67	140			\$16.50
S5061-R	1			2.7	80			\$16.50
S5061-6-R	1.6			9.7	70			\$16.50
S5062-R	2			15	68			\$16.50
S5062-5-R	2.5			25	68			\$16.50
S5063-15-R	3.15			51	66			\$16.50
S5064-R	4		40A	88	66			\$16.50
S5065-R	5		50A	150	66			\$16.50
S5066-3-R	6.3		63A	214	75			\$19.50

*Note: Typical Melting I_{2t} (A2Sec) - measured at 10 In and rated voltage.

** Typical Voltage Drop - measured at 20°C ambient temperature at rated current.



For mounting and wiring S506 fuses, see our DN-F10 Series fuse blocks in the Terminal Blocks and Wiring Solutions section.

CROSS REFERENCE			
OLD EDISON	BUSSMANN	MERSEN GOULD	LITTELFUSE
GDC/BDC	GDC	GDG	218

5x20 mm Time-Delay S506 Series Fuses




TIME CURRENT CURVE



Dimensions

mm (inches)



S506 Electrical Characteristics

<i>I_N</i>	<i>2.1 I_N max</i>	<i>2.75 I_N min</i>	<i>2.75 I_N max</i>	<i>4 I_N min</i>	<i>4 I_N max</i>	<i>10 I_N min</i>	<i>10 I_N max</i>
0.25A - 6.3A	2 min	600 ms	10 sec	150 ms	3 sec	20 ms	300 ms

Modular Ferrule Fuse Blocks for Class R Fuses



Description

RM Series for use with Class R fuses LENRK, LESRK, ECNR & ECSR

Mounting

35mm DIN rail or panel mount

Specifications

Materials:

Base – Thermoplastic

Terminals – Tin-plated copper brass

Covers – Thermoplastic

Screws – Zinc-plated steel

SCCR: 200kA

Flammability rating:

Blocks – UL 94V0, self-extinguishing

Covers – UL 94HB, self-extinguishing

Operating and storage temp range:

Blocks – -40° to 120°C [-40° to 248°F]

Covers – indicating -20° to 90°C [-4° to 194°F]

non-indicating -40° to 120°C [-40° to 248°F]

Wire:

Cu – 75°/90°C [167°/194°F]

Al – 75°C [167°F]

Ring or Fork terminal to fit a #10-32 screw

Agency Approvals

Fuse Blocks

- UL® Listed E14853 - IZLT
- CSA® Certified 47235-6225-01
- CE
- RoHS Compliant
- Conflict mineral free
- REACH Compliant

Covers

- Covers are included in the overall UL Listing/Recognition and CSA Certification
- IP20 finger-safe
- RoHS compliant
- REACH Compliant

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.



Clear IP20 finger-safe cover (sold separately)

Patented lockout / tagout

Modular dove-tail design for tool-less snap together assembly

DIN Rail or panel mount

Test probe holes

Screw terminal

Compact Footprint

Modular Ferrule Fuse Blocks for Class R Fuses


Type	Part Number	Pc/ pkg	Price	Volts	Amps	Poles	Wire Range		Torque lb-in [N·m]	Wt. lb [kg]	Covers (sold separately)		
							solid and stranded	fine stranded (Cu)			w/o Indication	w/ Indication ¹	Pc/ pkg
Screw	RM25030-1SR	1	\$18.00	250V AC/DC	30	1	18-10 AWG (Cu)	18-10 AWG	20 [2.3]	0.10 [0.04]	CVR-RH-25030 \$11.50	CVRI-RH-25030 \$15.00	1
	RM25030-2SR	1	\$29.00			2				0.15 [0.07]			
	RM25030-3SR	1	\$44.00			3				0.25 [0.12]			
Box Lug	RM25060-1CR	1	\$34.50		60	1	14-2 AWG (Cu) 8-2 AWG (Al)	3-2 AWG 6-4 AWG 8 AWG 14-10 AWG	50 [5.6] 45 [5.1] 40 [4.5] 35 [4.0]	0.15 [0.07]	CVR-RH-25060 \$14.00	CVRI-RH-25060 \$15.50	1
	RM25060-2CR	1	\$61.00			2				0.30 [0.14]			
	RM25060-3CR	1	\$82.00			3				0.45 [0.22]			
Screw	RM60030-1SR	1	\$38.50	600V AC/DC	30	1	18-10 AWG (Cu)	18-10 AWG	20 [2.3]	0.15 [0.07]	CVR-RH-60030 \$12.00	CVRI-RH-60030 \$15.00	1
	RM60030-2SR	1	\$59.00			2				0.30 [0.14]			
	RM60030-3SR	1	\$71.00			3				0.45 [0.22]			
Box Lug	RM60060-1CR	1	\$48.50		60	1	14-2 AWG (Cu) 8-2 AWG (Al)	3-2 AWG 6-4 AWG 8 AWG 14-10 AWG	50 [5.6] 45 [5.1] 40 [4.5] 35 [4.0]	0.25 [0.12]	CVR-RH-60060 \$14.00	CVRI-RH-60060 \$15.50	1
	RM60060-2CR	1	\$81.00			2				0.45 [0.22]			
	RM60060-3CR	1	\$146.00			3				0.70 [0.30]			

¹ Open fuse indication requires 90V minimum and closed circuit to operate.



Modular Ferrule Fuse Blocks for Class R Fuses Dimensions




in [mm]



RM25030



RM25060




Please see our website www.AutomationDirect.com for complete engineering drawings. Dimensions are approximate. Not for construction purposes.


Modular Ferrule Fuse Blocks for Class R Fuses

Dimensions

in [mm]



RM60030



RM60060

Please see our website www.AutomationDirect.com for complete engineering drawings. Dimensions are approximate. Not for construction purposes.

T300 & T600 Fuse Blocks for Class T Fuses



Description

For use with Class T fuses

T300 series: for use with 300V Class T fuses
(TJN)

T600 series: for use with 600V Class T fuses
(TJS)

- Terminal type:
 - SR = Screw type; clip with re-inforcing spring
 - CR = Box lug type; clip with reinforcing spring
 - C = Box lug type; clip with reinforcing spring standard on FB rated 100A; spring not required above 100A for bolt-on fuses

Specifications

Construction: Glass Polyester; Phenolic on 600V

UL Flammability: 94V-O

Ratings:


T300: 300 VAC; 30–600A

T600: 600 VAC; 30–600A

Short-circuit Current Rating:

200,000 RMS Symmetrical Amps

Edison Class T Fuse Blocks



Agency Approvals

- UL Listed, Guide IZLT, File E14853
- CSA, Class 6225-01, File 47235
- CE
- REACH
- RoHS

Class T Fuse Blocks

Class T Fuse Blocks									
Part Number	Volts	Amps	Poles	Terminal Type	Wire Range (AWG)	Fig #	Wt. (lb)	Pcs /Pkg	Price
T30030-2SR	300	0.5 to 30	2	screw	10–18 Cu (only)	1	0.3	1	\$41.00
T30030-3SR			3				0.4		\$40.50
T30060-2CR		31 to 60	2	box lug	2–14 Cu/Al		0.4		\$52.00
T30060-3CR			3			0.5	\$78.00		
T30100-1CR		61 to 100	1		1/0–8 Cu/Al	4	0.6		Retired
T30100-3CR			3				1.5		Retired
T30200-1C		101 to 200	1		250 kcmil – 6 Cu/Al	5a	1.0		Retired
T30600-1C		401 to 600	1		(2) 600 kcmil – 4/0 Cu/Al	7	2.4		Retired
T60030-1SR	600	0.5 to 30	1	screw	10–18 Cu (only)	2	0.2	1	\$30.00
T60030-2SR			2				0.3		\$54.00
T60030-3SR			3				0.5		\$47.50
T60060-1CR		31 to 60	1	box lug	2–14 Cu/Al	3	0.3		\$29.50
T60060-2CR			2				0.4		\$60.00
T60060-3CR			3				0.6		\$88.00
T60100-1C		61 to 100	1		2/0–14 Cu/Al	4	1.0		Retired
T60100-3C			3				1.5		Retired
T60400-1C		201 to 400	1		600 kcmil – 2/0 Cu/Al	6	1.3		Retired
T60600-1C		401 to 600	1		(2) 600 kcmil – 4/0 Cu/Al	7	2.6		Retired

T300 & T600 Fuse Blocks for Class T Fuses



Fuse Block Terminal Torque Specifications

Terminal Tightening Torque Specs – Class T Fuse Blocks							
Part Number	Amps	Volts	Poles	Terminal Type	Wire Range (AWG)	Wire Torque (lb-in)	Fuse Torque (lb-in)
Tx0030-xSR	30	300, 600	1,2,3	screw	10–18 Cu (only)	20	n/a
Tx0060-xCR	60	300, 600	1,2,3	box lug	2–3	50	n/a
					4–6	45	
					8	40	
					10–14	35	
T30100-xCR	100	300	1,3		1/0–8 Cu/Al	100	n/a
T60100-xC	100	600	1,3		2/0–3	50	70
					4–6	45	
					8	40	
					10–14	35	
Tx0200-1C	200	300, 600	1		250 kcmil – 6 Cu/Al	375	132
Tx0400-1C	400	300, 600	1		600 kcmil – 2/0 Cu/Al	500	192
Tx0600-1C	600	300, 600	1		(2) 600 kcmil – 4/0 Cu/Al	450	380

Fuse Block Dimensions

Fig.1: 300V; 0.5–60A




Figure 1: 300V 1/2A to 60A

Terminal Type	Dimensions (in [mm])		
	A	B	C
T30030-2SR T30060-2CR	2.41 [61.2]	–	1.03 [26.2]
T30030-3SR T30060-3CR	3.44 [87.4]	1.03 [26.2]	2.06 [52.3]

Fig.2: 600V; 0.5–30A




Figure 2:
600V 1/2A to 30A

Dimensions
= in [mm]

Fig.3: 600V; 31–60A




Figure 3:
600V 131A to 60A

Dimensions
= in [mm]

T300 & T600 Fuse Blocks for Class T Fuses



Fuse Block Dimensions

Fig.4: 300V, 600V; 61-100A




Fig.5a: 300V, 600V; 101-200A





Fig.5b: 300V; 101-200A



T300 & T600 Fuse Blocks for Class T Fuses



Fuse Block Dimensions

Fig.6: 300V, 600V; 201–400A






FIGURE 6:
300V, 600V
201A to 400A

Dimensions = in [mm]

Fuse Block	Dimension A
T30400-1C	1.84 [46.7]
T60400-1C	2.72 [69.1]

Fig.7: 300V, 600V; 401–600A



Dimensions = in [mm]

FIGURE 7: 300V, 600V 401A to 600A

Fuse Block	Dimensions (in [mm])	
	A	B
T30600-1C	5.75 [146]	2.03 [51.6]
T60600-1C	6.75 [171.4]	2.95 [74.9]

Modular Ferrule Fuse Blocks for Class J Fuses



Description

JM Series for use with Class J fuses JHL & JDL

Mounting

35mm DIN rail or panel mount

Specifications

Materials:

Base – Thermoplastic

Terminals – Tin-plated copper brass

Covers – Thermoplastic

Screws and pressure plates – Zinc-plated steel

SCCR: 200kA

Flammability rating:

Blocks – UL 94V0, self-extinguishing

Covers – UL 94HB, self-extinguishing

Operating and storage temp range:

Blocks – -40° to 120°C [-40° to 248°F]

Covers – indicating -20° to 90°C [-4° to 194°F]
non-indicating -40° to 120°C [-40° to 248°F]

Wire:

Cu – 75°/90°C [167°/194°F]

Al – 75°C [167°F]

Ring or Fork terminal to fit a #10-32 screw

Agency Approvals

Fuse Blocks


- UL® Listed E14853 - IZLT
- CSA® Certified 47235-6225-01
- CE
- RoHS Compliant
- Conflict mineral free
- REACH Compliant

Covers

- Covers are included in the overall UL Listing/Recognition and CSA Certification
- IP20 finger-safe
- RoHS compliant
- REACH Compliant



To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.




Modular Ferrule Fuse Blocks for Class J Fuses													
Type	Part Number	Pc/ pkg	Price	Volts	Amps	Poles	Wire Range		Torque lb-in [N·m]	Wt. lb [kg]	Covers (sold separately)		
							solid and stranded	fine stranded (Cu)			w/o Indication	w/ Indication ¹	Pc/ pkg
Box lug	JM60030-1CR	1	\$39.00	600V AC/DC	30	1	14-2 AWG (Cu) 8-2 AWG (Al)	3-2 AWG	50 [5.6]	0.15 [0.08]	CVR-J-60030 \$11.50	CVRI-J-60030 \$15.00	1
	JM60030-2CR	1	\$82.00			2		6-4 AWG	45 [5.1]	0.25 [0.12]			
	JM60030-3CR	1	\$119.00			3		8AWG	40 [4.5]	0.40 [0.18]			
Pressure Plate	JM60030-1PR	1	\$35.50			1	18-10 AWG (Cu)	14-10 AWG	35 [4.0]	0.40 [0.18]			
	JM60030-2PR	1	\$70.00			2		18-10 AWG	20 [2.3]	0.15 [0.08]			
	JM60030-3PR	1	\$107.00			3				0.25 [0.12]			
Box lug	JM60060-1CR	1	\$47.50		60	1	14-2 AWG (Cu) 8-2 AWG (Al)	3-2 AWG	50 [5.6]	0.20 [0.10]	CVR-J-60060 \$14.00	CVRI-J-60060 \$15.50	1
	JM60060-2CR	1	\$95.00			2		6-4 AWG	45 [5.1]	0.35 [0.16]			
	JM60060-3CR	1	\$143.00			3		8AWG	40 [4.5]	0.55 [0.26]			

¹ Open fuse indication requires 90V minimum and closed circuit to operate.


Modular Ferrule Fuse Blocks for Class J Fuses

Dimensions

in [mm]



JM60030



JM60060

Please see our website www.AutomationDirect.com for complete engineering drawings. Dimensions are approximate. Not for construction purposes.

Modular Fuse Holders for Class J Fuses



CH30J1



CH30J2I



CH30J3

Description

- Choice of LED indicator or non-indicating fuse holder
- Comes in standard 1-, 2- and 3-Pole ganged assemblies where all fuses are extracted simultaneously
- Meets requirements of IEC 60529 for IP-20 finger safe rating
- 35mm DIN rail and chassis (6-32 UNC Pan Head recommended) mounting features
- Fuseholder wire ports dual wire rated from 18 to 3 AWG

Specifications

Construction: Thermoplastic, with tin-plated copper clip
UL Flammability: 94V-0

Voltage Ratings: 600 Volts AC/DC (or less)

Ampere Ratings: 1 - 60 Amps

Interrupting Rating: 200,000 RMS Symmetrical Amps

Minimum Indicating Voltage (neon lamp): 90 Volts

Nominal Operating Current (neon lamp): 34 mA (460 VAC)

Agency Approvals


- Listed UL 512, Guide IZLT, File E14853
- CSA Certified per C22.2 Nos. 39 Class 6225-01, File LR47235
- CE compliance for the European Union Low Voltage Directive

CH Series Modular Fuse Holders for Class J Fuses

Amp Rating	Part Number	Amps	Type	Poles	Maximum Wire Size	Pcs/Pkg	Weight (lbs.)	Price
30A	CH30J1	0.5 to 30	Easy ID window	1	18 -1 AWG Single 18 -3 AWG Dual 75°C	6	2.8	\$285.00
	CH30J2		Easy ID window	2		3		\$397.00
	CH30J3		Easy ID window	3		2		\$392.00
	CH30J1I		Neon indicator	1		6		\$330.00
	CH30J2I		Neon indicator	2		3		\$452.00
	CH30J3I		Neon indicator	3		2		\$430.00
						6	3.4	\$380.00
60A	CH60J1	31 to 60	Easy ID window	1		3		\$445.00
	CH60J2		Easy ID window	2		2		\$451.00
	CH60J3		Easy ID window	3		6		\$425.00
	CH60J1I		Neon indicator	1		3		\$529.00
	CH60J2I		Neon indicator	2		2		\$484.00
	CH60J3I		Neon indicator	3				

Dimensions

Dimension	CH30J in (mm)	CH60J in (mm)
A	1.28 (32.5)	1.58 (40.0)
B	2.56 (65.0)	3.16 (80.0)
C	3.84 (97.5)	4.72 (120.0)
D	4.59 (116.6)	4.88 (124.0)
E	2.83 (71.8)	3.31 (84.1)
F	3.56 (90.4)	3.85 (97.9)
G	1.28 (32.5)	1.58 (40.0)
H	0.18 (4.44)	0.18 (4.44)



Modular Fuse Blocks for Class J Fuses



Description

For use with Edison JHL, JDL, Class J fuses

Specifications

Materials:

Base – thermoplastic

Box lug terminals – tin-plated aluminum

SCCR: 200kA

Flammability rating:

Blocks – UL 94V0, self-extinguishing

Covers – UL 94HB, self-extinguishing

Operating and storage temp range:

Blocks – -40° to 120°C [-40° to 248°F]

Covers – indicating -20° to 90°C [-4° to 194°F]
non-indicating -40° to 120°C [-40° to 248°F]

Wire:

Cu/Al – 75°/90°C [167°/194°F] (100-200 A)

Cu/Al – 75°C [167°F] only (400-600 A)*

Note: Higher temperature rated wire can be used with appropriate derating.

* 400A Class J double box lug rated for 75°/90°C Cu/Al.


Agency Approvals

- Blocks – UL – Listed cULus E14853 – IZLT & IZLT7
- CSA – Certified 47235 – 6225-01
- Covers – UL – Listed UL E58836 – JDVS
- CE, RoHS, Reach compliant

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.



Class J Fuse Blocks



Class J Fuse Block Covers

JM Series Modular Fuse Blocks										
Part Number (1 pc/pkg)	Volts	Amps	Poles	Wire Range		Torque lb-in [N·m]	Wt. lb [kg]	Covers**		
				solid and stranded***	fine stranded (Cu)			w/o Indication	w/ Indication	Pcs/ Pkg
JM60100-1CR-1 \$56.00	600	100	1	–	3-1 AWG	55 [6.2]	0.32 [0.14]	CVR-J-60100-M-1 \$15.00	CVRI-J-60100-M-1 \$28.00	1
JM60100-1CR-2 \$112.00			2	3-1/0 AWG; (2) Cu 6-4 AWG 6-4 AWG; (2) Cu 8AWG 8AWG; (2) Cu 14-10 AWG	6-4 AWG 8AWG	50 [5.6] 45 [5.1]	0.64 [0.28]	CVR-J-60100-M-2 \$31.00	CVRI-J-60100-M-2 \$54.00	2
JM60100-1CR-3 \$168.00			3	Cu 14-10 AWG; Al 12-10 AWG	–	40 [4.5] 35 [4.0]	0.96 [0.42]	CVR-J-60100-M-3 \$45.00	CVRI-J-60100-M-3 \$80.00	3
JM60200-1CR-1 \$229.00	600	200	1	1AWG - 250MCM 6-2 AWG; (2) Cu 6-2 AWG	1-3/0 AWG 6-2 AWG	375 [42] 275 [31]	0.82 [0.37]	CVR-J-60200-M-1 \$18.50	CVRI-J-60200-M-1 \$31.00	1
JM60200-1CR-2 \$454.00			2				1.64 [0.74]	CVR-J-60200-M-2 \$39.00	CVRI-J-60200-M-2 \$59.00	2
JM60200-1CR-3 \$687.00			3				2.46 [1.11]	CVR-J-60200-M-3 \$56.00	CVRI-J-60200-M-3 \$90.00	3
JM60400-1CR-1 \$442.00	600	400	1	600MCM 500MCM (2) Cu 4-3/0 AWG (2) Al 4-3/0 AWG	N/A	500 [57] 450 [51] 500 [57] 300 [34]	2.16 [0.98]	CVR-J-60400-M-1 \$34.00	CVRI-J-60400-M-1 \$48.50	1
JM60400-1CR-3 \$1,321.00			3				6.48 [2.94]	CVR-J-60400-M-3 \$100.00	CVRI-J-60400-M-3 \$141.00	3
JM60400-1MW22-1* \$475.00		600	1	(2) 1AWG - 350MCM	NA	375 [42]	2.58 [1.17]	CVR-J-60400-M-1 \$34.00	CVRI-J-60400-M-1 \$48.50	1
JM60400-1MW22-3* \$1,356.00			3	(2) 6-2 AWG		275 [51]	7.74 [3.51]	CVR-J-60400-M-3 \$100.00	CVRI-J-60400-M-3 \$141.00	3
JM60600-1CR-1* \$714.00	600	600	1	(2) 4AWG - 500MCM	N/A	450 [51]	3.92 [1.78]	CVR-J-60600-1 \$56.00	CVRI-J-60600-1 \$70.00	1
JM60600-1CR-3* \$2,134.00			3				11.76 [5.34]	CVR-J-60600-3 \$169.00	CVRI-J-60600-3 \$212.00	3

* Modular double box lug fuse block

** Covers sold separately. Blown fuse indication requires 90V minimum and closed circuit to operate.

*** Ratings are for copper and aluminum wire except where otherwise noted.

Double Box Lug Configurations

- Allows for ease of installation with smaller, more flexible wire
- Capable of achieving maximum current rating with parallel copper or aluminum wires
- Standard on all 600A blocks
- Optional on 400A blocks
- Compatible with IP20 finger-safe covers (for 400A double box lug configuration, optional cover provides IP20 finger-safe protection for dual 1AWG - 350MCM wires or one single 6AWG - 350MCM)





JM60400-1MW22

Fuse Blocks for Class J Fuses



Dimensions in [mm]




Please see our website www.AutomationDirect.com for complete engineering drawings. Dimensions are approximate. Not for construction purposes.

Fuse Blocks for Class J Fuses




Dimensions in [mm]


JM60400 Series



JM60600 Series



JM60400-1MW22-x



Please see our website www.AutomationDirect.com for complete engineering drawings. Dimensions are approximate. Not for construction purposes.

Modular Power Distribution Multi-Wire Fuse Blocks for Class J Fuses




Features

- Combination power distribution block and fuse block reduces wire connections and total panel components, using 50% less panel space and reducing installation time and labor by 33%.
- A 200kA withstand rating helps achieve a higher assembly short circuit current rating (SCCR) for compliance with NEC® sections 110.10, 409.110(4), 409.22, 440.4(B), 670.3(A)(4) and 670.5.
- Optional see-through cover enhances safety with IP20 finger-safe protection, lockout/tagout capability and open circuit indication.



Class J
Power Distribution Blocks



Covers for Class J
Power Distribution Blocks

Specifications

Materials:

Base – thermoplastic

Box lug terminals – tin-plated aluminum

SCCR: 200kA

Flammability rating:

Blocks – UL 94V0, self-extinguishing

Covers – UL 94HB, self-extinguishing

Operating and storage temp range:

Blocks – -40° to 120°C [-40° to 248°F]

Covers – indicating -20° to 90°C [-4° to 194°F]

non-indicating -40° to 120°C [-40° to 248°F]

Wire:

Cu/Al – 75°C [167°F]*

* Conductors with higher temperature rating may be used, but at their 75°C ampacity.

Agency Approvals

- Blocks - UL - UR recognized E14853 – IZLT2
- CSA - Certified 47235 – 6225-01
- Covers - UL - Listed UL E58836 – JDVS
- CE, RoHS, Reach Compliant

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

JM Series Modular Power Distribution Multi-Wire Fuse Blocks

Part Number (1 pc/pkg)	Volts	Amps	Poles	Lineside		Loadside		Wt. lb [kg]	Covers***		
				Wire range (AWG)	Torque N-m [lb-in]	Wire range (AWG)	Torque N-m [lb-in]		w/o Indication	w/ Indication	Pcs/ Pkg
JM60100-1MW14-1 \$69.00	100	100	1	(1) 14 - 1/0 Cu/Al	1-1/0; 5.6 [50] 6-4; 5.0 [45] 8; 4.5 [40] 14-10; 4.0 [35]	(4) 14-4 Cu, 8-4 Al	6-4; 4.0 [35] 8; 2.8 [25] 14-10; 2.3 [20]† (2) 14-10; 3.4 [30]†	0.32 [0.15]	CVR-J-60100-M-1 \$15.00	CVRI-J-60100-M-1 \$28.00	1
JM60100-1MW14-2 \$133.00			2						CVR-J-60100-M-2 \$31.00	CVRI-J-60100-M-2 \$54.00	2
JM60100-1MW14-3 \$205.00			3						CVR-J-60100-M-3 \$45.00	CVRI-J-60100-M-3 \$80.00	3
JM60200-1MW16-1 \$232.00	200	200	1	(1) 6 - 250MCM Cu/Al	1 - 250MCM; 42 [375] (2) 6-2; 31 [275]	(6) 14-4 Cu, 8-4 Al (12)** 14-10 Cu	6-4; 4.0 [35] 8; 2.8 [25] 14-10; 2.3 [20]† (2) 14-10; 3.4 [30]†	0.84 [0.39]	CVR-J-60200-M-1 \$18.50	CVRI-J-60200-M-1 \$31.00	1
JM60200-1MW16-2 \$445.00			2						CVR-J-60200-M-2 \$39.00	CVRI-J-60200-M-2 \$59.00	2
JM60200-1MW16-3 \$670.00			3						CVR-J-60200-M-3 \$56.00	CVRI-J-60200-M-3 \$90.00	3
JM60400-1MW16-1 \$412.00	400	400	1	(1) 4 - 600MCM Cu/Al	4 - 600MCM; 57 [500] 500MCM; 51 [450] (2) 4-3/0; 57 [500] Cu 34 [300] Al	(6) 14-2 Cu, 8-2 Al (12)** 14-8 Cu, 8 Al	3-2; 5.6 [50] 6-4; 5.0 [45] 8; 4.5 [40] (2) 8; 4.5 [40]†† 14-10; 4.0 [35]†† (2) 14-10; 4.5 [40]††	2.24 [1.02]	CVR-J-60400-M-1 \$34.00	CVRI-J-60400-M-1 \$48.50	1
JM60400-1MW16-3 \$1,182.00			3						CVR-J-60400-M-3 \$100.00	CVRI-J-60400-M-3 \$141.00	3
JM60400-1MW26-1* \$518.00			1	(2) 6 - 350MCM Cu/Al	(2) 1 - 350MCM; 42 [375] (2) 6-2; 31 [275]	(6) 14-2 Cu, 8-2 Al (12)** 14-8 Cu, 8 Al	3-2; 5.6 [50] 6-4; 5.0 [45] 8; 4.5 [40] (2) 8; 4.5 [40]†† 14-10; 4.0 [35]†† (2) 14-10; 4.5 [40]††	2.44 [1.1]	CVR-J-60400-M-1 \$34.00	CVRI-J-60400-M-1 \$48.50	1
JM60400-1MW26-3* \$1,479.00			3						CVR-J-60400-M-3 \$100.00	CVRI-J-60400-M-3 \$141.00	3

* Lineside dual box lug

** Dual wire rated lugs with same wire size

*** Covers sold separately. Blown fuse indication requires 90V minimum and closed circuit to operate.


† Copper conductor only.

†† Dual wire not for CSA installations

Power Distribution Blocks for Class J Fuses



Dimensions



Dimensions																Connections		
Block Size		A	B	C	D	E	F	G	H	I	J	K	L	M	øN	øO	Lineside (P)	Loadside (Q)
100A	in	2.0	4.0	6.0	5.5	5.5	2.8	2.2	6.0	2.8	0.9	2.0	0.4	1.1	0.4	0.5	1	4
	mm	51	102	153	139	139	72	55	152	72	22	51	10	29	9	13		
200A	in	2.6	5.3	8.0	6.8	6.8	3.8	3.0	7.3	3.8	1.4	2.6	0.3	1.3	0.4	0.7	1	6
	mm	67	134	203	172	172	97	75	186	97	35	34	8	32	9	19		
400A	in	3.5	7.0	10.6	8.0	8.0	4.8	4.1	8.7	4.8	2.0	3.5	0.3	1.6	0.4	0.7	2 (1)*	6
	mm	88	177	268	202	202	121	105	220	121	50	88	8	41	9	19		

*JM60400-1MW16-X

Please see our website www.AutomationDirect.com for complete engineering drawings. Dimensions are approximate. Not for construction purposes.

Modular Fuse Blocks for Class R Fuses



Description

For use with Edison ECNR, ECSR, LENRK, LESRK, Class R fuses

Specifications

Materials:

Base – thermoplastic

Box lug terminals – tin-plated aluminum

SCCR: 200kA sym RMS

Flammability rating:

Blocks – UL 94V0, self-extinguishing

Covers – UL 94HB, self-extinguishing

Operating and storage temp range:

Blocks – -40° to 120°C [-40° to 248°F]

Covers – indicating -20° to 90°C [-4° to 194°F]

– non-indicating -40° to 120°C [-40° to 248°F]

Wire:

Cu/Al – 75°/90°C [167°/194°F] (100-200 A)

Cu/Al – 75°C [167°F] only (400-600 A)

Note: Higher temperature rated wire can be used with appropriate derating.


Agency Approvals

- Blocks – UL – Listed cULus E14853 – IZLT & IZLT7
- CSA – Certified 47235 – 6225-01
- Covers – UL – Listed UL E58836 – JDVS
- CE, RoHS, Reach Compliant

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.



Class R Fuse Blocks



Class R Fuse Block Covers

RM Series Modular Fuse Blocks										
Part Number (1 pc/pkg)	Volts	Amps	Poles	Wire Range		Torque lb-in [N-m]	Wt. lb [kg]	Covers*		
				solid and stranded**	fine stranded(Cu)			w/o Indication	with Indication	Pcs/Pkg
RM25100-1CR-1 \$50.00	250	100	1	–	3-1 AWG	55 [6.2]	0.86 [0.39]	CVR-RH-25100-1 \$17.50	CVRI-RH-25100-1 \$29.50	1
RM25100-1CR-2 \$99.00			2	3-1/0 AWG; (2) Cu 6-4 AWG 6-4 AWG; (2) Cu 8AWG 8AWG; (2) Cu 14-10 AWG Cu 14-10 AWG; Al 12-10 AWG	6-4 AWG 8AWG –	50 [5.6] 45 [5.1] 40 [4.5]	1.72 [0.78]	CVR-RH-25100-2 \$36.50	CVRI-RH-25100-2 \$58.00	2
RM25100-1CR-3 \$150.00			3		–	35 [4.0]	2.58 [1.17]	CVR-RH-25100-3 \$54.00	CVRI-RH-25100-3 \$86.00	3
RM25200-1CR-1 \$166.00	250	200	1	1AWG - 250MCM 6-2 AWG; (2) Cu 6-2 AWG	1-3/0 AWG 6-2 AWG	375 [42] 275 [31]	0.88 [0.4]	CVR-RH-25200-1 \$25.50	CVRI-RH-25200-1 \$39.00	1
RM25200-1CR-2 \$326.00			2				1.76 [0.8]	CVR-RH-25200-2 \$51.00	CVRI-RH-25200-2 \$76.00	2
RM25200-1CR-3 \$496.00			3				2.64 [1.2]	CVR-RH-25200-3 \$73.00	CVRI-RH-25200-3 \$114.00	3
RM25400-1CR-1 \$571.00	250	400	1	600MCM 500MCM - 4AWG (2) Cu 4-3/0 AWG (2) Al 4-3/0 AWG	N/A	500 [57] 450 [51] 500 [57] 300 [34]	2.24 [1.02]	CVR-RH-25400-1 \$40.50	CVRI-RH-25400-1 \$55.00	1
RM25400-1CR-3 \$1,716.00			3				6.72 [3.06]	CVR-RH-25400-3 \$116.00	CVRI-RH-25400-3 \$168.00	3
RM25600-1CR-1 \$732.00			1				4.04 [1.83]	CVR-RH-25600-1 \$71.00	CVRI-RH-25600-1 \$86.00	1
RM25600-1CR-3 \$2,192.00	250	600	3	(2) 4AWG - 500 MCM	N/A	450 [51]	12.12 [5.49]	CVR-RH-25600-3 \$219.00	CVRI-RH-25600-3 \$266.00	3
RM60100-1CR-1 \$60.00	600	100	1	–	3-1 AWG	55 [6.2]	0.34 [0.16]	CVR-RH-60100-1 \$23.00	CVRI-RH-60100-1 \$36.50	1
RM60100-1CR-2 \$122.00			2	3-1/0 AWG; (2) Cu 6-4 AWG 6-4 AWG; (2) Cu 8AWG 8AWG; (2) Cu 14-10 AWG Cu 14-10 AWG; Al 12-10 AWG	6-4 AWG 8AWG –	50 [5.6] 45 [5.1] 40 [4.5]	0.68 [0.32]	CVR-RH-60100-2 \$44.00	CVRI-RH-60100-2 \$71.00	2
RM60100-1CR-3 \$181.00			3		–	35 [4.0]	1.02 [0.48]	CVR-RH-60100-3 \$62.00	CVRI-RH-60100-3 \$107.00	3
RM60200-1CR-1 \$158.00	600	200	1	1AWG - 250MCM 6-2 AWG; (2) Cu 6-2 AWG	1-3/0 AWG 6-2 AWG	375 [42] 275 [31]	0.92 [0.42]	CVR-RH-60200-1 \$29.50	CVRI-RH-60200-1 \$44.00	1
RM60200-1CR-2 \$312.00			2				1.84 [0.84]	CVR-RH-60200-2 \$56.00	CVRI-RH-60200-2 \$86.00	2
RM60200-1CR-3 \$469.00			3				5.52 [2.52]	CVR-RH-60200-3 \$85.00	CVRI-RH-60200-3 \$131.00	3
RM60400-1CR-1 \$466.00	600	400	1	600MCM 4AWG - 500MCM (2) Cu 4-3/0 AWG (2) Al 4-3/0 AWG	N/A	500 [57] 450 [51] 500 [57] 300 [34]	2.32 [1.05]	CVR-RH-60400-1 \$52.00	CVRI-RH-60400-1 \$70.00	1
RM60400-1CR-3 \$1,395.00			3				6.96 [3.15]	CVR-RH-60400-3 \$153.00	CVRI-RH-60400-3 \$211.00	3
RM60600-1CR-1 \$731.00			1				4.16 [1.88]	CVR-RH-60600-1 \$89.00	CVRI-RH-60600-1 \$108.00	1
RM60600-1CR-3 \$2,191.00	600	600	3	(2) 4AWG - 500MCM	N/A	450 [51]	12.48 [5.64]	CVR-RH-60600-3 \$272.00	CVRI-RH-60600-3 \$326.00	3

* Covers sold separately. Blown fuse indication requires 90V minimum and closed circuit to operate.

** Ratinas are for copper and aluminum wire except where otherwise noted.

Modular Fuse Holders for Class CC & Midget Class Fuses



Features

- EHCC Series: High SCCR rated, UL Listed CC holder with indicator option for 600VAC/DC
- EHM Series: UL Recognized midget holders
- Minimum 90VAC/DC required for illumination
- Rated for use with 75°C or 90°C wire, fine stranded wire, spade terminals and comb-bus bars. Use any higher temperature rated wire with appropriate derating.
- Complete range of UL Listed and high SCCR rated 1-phase and 3-phase finger-safe comb-bus bars and power feed lugs
- Polyester material is UL 94V0 rated, self extinguishing
- Multi-phase connections available for ganging up to 4 poles*
- Mounts on 35 mm DIN rail
- IP20 rated
- Spade terminals are accepted (Max width-10mm, Min ID of slot 4mm, Max ID of slot 5mm)
- Wire ferrules may not be used.

Application

- EHM: Edison MCL, MOL, MEQ, MEN, or midget fuses
- EHCC: Edison HCLR, HCTR, EDCC fuses, or class CC fuses

Agency Approvals

Standards Class CC

- UL File E300536
Guide IZLT Listed
- CSA File 47235, Class 6225-01
- CE Compliant
- RoHS, Reach

Standards Midget

- UL File E300536
IZLT2 Recognized
- CSA File 47235, Class 6225-30
- IEC 60269-2
- CE Compliant
- RoHS, Reach

Modular Fuse Holder Selection Table

Series Size	Max Voltage & Current	IEC	UL	Phase Configuration	Fuse Holder Without Indication	Box Qty.	Pkg. Wt. (lb.)	Price	Fuse Holder with NEON Indication	Product Weight (lb.)	Box Qty.	Price
EHM Midget Class	UL 600V/30A	•	•	1 pole	EHM1DU	1	0.12	\$17.50	EHM1DIU	0.12	1	\$23.50
					EHM1DU-12	12	1.42	\$180.00	EHM1DIU-12	1.42	12	\$239.00
	IEC 690V/32A	•	•	2 pole	EHM2DU	1	0.24	\$36.50	EHM2DIU	0.24	1	\$47.50
					EHM2DU-6	6	1.42	\$187.00	EHM2DIU-6	1.42	6	\$242.00
		•	•	3 pole	EHM3DU	1	0.36	\$55.00	EHM3DIU	0.36	1	\$76.00
					EHM3DU-4	4	1.42	\$188.00	EHM3DIU-4	1.42	4	\$249.00
EHCC Class CC	UL 600V/30A		••	1 pole	EHCC1DU	1	0.12	\$21.00	EHCC1DIU	0.12	1	\$26.50
					EHCC1DU-12	12	1.42	\$210.00	EHCC1DIU-12	1.42	12	\$273.00
			••	2 pole	EHCC2DU	1	0.24	\$42.50	EHCC2DIU	0.24	1	\$55.00
					EHCC2DU-6	6	1.42	\$214.00	EHCC2DIU-6	1.42	6	\$280.00
			••	3 pole	EHCC3DU	1	0.36	\$63.00	EHCC3DIU	0.36	1	\$83.00
					EHCC3DU-4	4	1.42	\$218.00	EHCC3DIU-4	1.42	4	\$282.00

* To add additional poles, see multi-pole connection kit JV-L in accessories. One JV-L kit is sufficient to gang up to 4 poles.

• UL Recognized, CSA

•• UL Listed, CSA

Modular Fuse Holders for Class CC & Midget Class Fuses



Modular Fuse Holder Specifications

Part Number w/o Indication	Part Number w/ Indication	Holder Size	Max Voltage & Current	Number of poles	Wire Range	Maximum Torque	Operating Temperature	SCCR Rating	Terminal Rating	Flammability Rating
EHM1DU	EHM1DIU	EHM Midget Class and 10x38	UL/CSA 600V/30A	1	18-4 AWG (0.8-21 mm ²)	30 lb-in (3.4 N•m) maximum	-20°C to +90°C -4°F to 194°F (indicating)	200kA rms sym	Solid, Stranded, Fine stranded, Spade lug, Comb-bus bar; Single and dual wire; 75°C and 90°C Cu wire	UL 94V0 self-extinguishing
EHM1DU-12	EHM1DIU-12			2						
EHM2DU	EHM2DIU			3						
EHM2DU-6	EHM2DIU-6		IEC 690V/32A	1						
EHM3DU	EHM3DIU			2						
EHM3DU-4	EHM3DIU-4	EHCC Class CC	UL/CSA 600V/30A	3			-20°C to +120°C -4°F to 248°F (non-indicating)			
EHCC1DU	EHCC1DIU			1						
EHCC1DU-12	EHCC1DIU-12			2						
EHCC2DU	EHCC2DIU			3						
EHCC2DU-6	EHCC2DIU-6			1						
EHCC3DU	EHCC3DIU			2						
EHCC3DU-4	EHCC3DIU-4			3						


CHCC and EHM Wire Range, Type and Torque

Wire Range	Conductor Type	Number of Conductors	Torque
18-14 AWG (0.8-2.0 mm ²)	Solid, Stranded	Single	20 lb-in (2.3 N•m)
18-16 AWG (0.8-1.3 mm ²)		Dual	25 lb-in (2.8 N•m)
14-10 AWG (2.0-5.2 mm ²)		Single	30 lb-in (3.4 N•m)
12-10 AWG (3.3-5.2 mm ²)	Stranded, Fine Stranded		
8-4 AWG (8.3-21.1 mm ²)	Spade Terminal		
18-14 AWG (0.8-2.0 mm ²)	Comb Bus		
N/A			

Fuse Holder Dimensions


mm [inches]

EHM Midget Class / EHCC Class CC




Fuse Blocks for Class R Fuses

Dimensions in [mm]



RM25100 Series




RM25200 Series

Please see our website www.AutomationDirect.com for complete engineering drawings. Dimensions are approximate. Not for construction purposes.


Fuse Blocks for Class R Fuses



Dimensions *in [mm]*



RM25400 Series





RM25600 Series

Please see our website www.AutomationDirect.com for complete engineering drawings. Dimensions are approximate. Not for construction purposes.

Fuse Blocks for Class R Fuses

Dimensions in [mm]




Please see our website www.AutomationDirect.com for complete engineering drawings. Dimensions are approximate. Not for construction purposes.


Fuse Blocks for Class R Fuses



Dimensions in [mm]



RM60400 Series



RM60600 Series

Please see our website www.AutomationDirect.com for complete engineering drawings. Dimensions are approximate. Not for construction purposes.

Modular Ferrule Fuse Blocks for Midget Class and CC Fuses



Description

- BCM Series for use with Class CC fuses EDCC, HCTR and HCLR
- BMM Series for use with Midget Class Midget fuses MCL, MEQ, MEN & MOL

Mounting

35mm DIN rail or panel mount

Specifications

Materials:

Base – Thermoplastic

Terminals – Tin-plated bimetallic copper

Covers – Thermoplastic

Screws and pressure plates – Zinc-plated steel

SCCR: 200kA

Flammability rating:

Blocks – UL 94V0, self-extinguishing

Covers – UL 94HB, self-extinguishing

Operating and storage temp range:

Blocks – -40° to 120°C [-40° to 248°F]

Covers – indicating -20° to 90°C [-4° to 194°F]

– non-indicating -40° to 120°C [-40° to 248°F]

Wire:

Cu – 75°/90°C [167°/194°F]

Ring or Fork terminal to fit a #10-32 screw

Agency Approvals


Fuse Blocks

- BCM – UL® Listed E14853 - IZLT
- BMM and BCCM UL Recognized E14853-IZLT2
- CSA® Certified 47235-6225-01
- CE
- RoHS Compliant
- Conflict mineral free
- REACH Compliant

Covers

- Covers are included in the overall UL Listing/Recognition and CSA Certification
- IP20 finger-safe
- RoHS compliant
- REACH Compliant

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.



Pressure Plate (with Quick Connect**) Modular Ferrule Fuse Blocks for Midget Class and CC Fuses													
Class	Part Number	Pc/pkg	Price	Volts	Amps	Poles	Wire Range ¹		Torque lb-in [N·m]	Wt. lb [kg]	Covers* (Sold Separately)		
							Solid and Stranded	Fine Stranded			w/o Indication	With Indication ³	Pc/pkg
Midget	BMM603-1PQ	15	\$152.00	600V AC/DC	30	1	18-10 AWG	18-10 AWG	20 [2.3]	0.05 [0.04]	CVR-CCM-QC \$31.50	CVRI-CCM-QC \$41.00	3
	BMM603-2PQ	5	\$86.00			2				0.15 [0.06]			
	BMM603-3PQ	5	\$110.00			3				0.20 [0.10]			
	BMM603-1PQ-1	1	\$11.00			1				0.05 [0.04]			
CC	BCM603-1PQ	15	\$209.00			1				0.05 [0.04]			
	BCM603-2PQ	5	\$107.00			2				0.15 [0.06]			
	BCM603-3PQ	5	\$134.00			3				0.20 [0.10]			
	BCM603-1PQ-1	1	\$15.00			1				0.05 [0.04]			
Combo	BCCMM603-3PQ ²	5	\$146.00			3				0.20 [0.10]			

¹ Ratings are for copper wire only.

² Combination modular fuse block for use with transformers. Accepts two (2) Class CC and one (1) Midget class fuse.

³ Open fuse indication requires 90V minimum and closed circuit to operate.

*Once installed, the cover cannot be removed.



**Quick connect terminal rated for 20A maximum.



Modular Ferrule Fuse Blocks for Midget Class and CC Fuses

Dimensions

in [mm]




Please see our website www.AutomationDirect.com for complete engineering drawings. Dimensions are approximate. Not for construction purposes.

Modular Ferrule Fuse Blocks for Midget Class and CC Fuses

Dimensions

in [mm]



Please see our website www.AutomationDirect.com for complete engineering drawings. Dimensions are approximate. Not for construction purposes.


Edison Comb-Bus Bars



Features

- Easily distribute power in single-phase or three-phase configurations
- Flexible cut-to length solutions without compromising on the product's finger-safe features
- 10kA (default) SCCR
- 100kA SCCR (Short Circuit Current Rating) when protected by a 200A Class J fuse
- Single-phase bus bars rated to 1000VDC/600VAC and 100A configuration
- Three-phase bus bars rated to 600VAC/DC and 100A configuration
- Power feed terminals for single-phase and three-phase service

Note: Not to be used with older style CH series fuse holders.



Agency Approvals/Standards

- UL508, File E195399
- CE
- RoHS
- Reach

Comb-Bus Bar Selection Table


Part Number	Wiring Configuration	Maximum Voltage	Maximum Current	Endcap	# of Pins/Connections	Product Weight (lbs.)	Box Qty.	Price
EB1P100M3	Single-phase	600VAC 1000VDC	100A	Ships w/2 Endcaps	3	1.84	1	\$14.50
EB1P100M6					6	3.90		\$21.50
EB1P100M9					9	5.38		\$27.00
EB1P100M12					12	7.94		\$34.00
EB1P100M15					15	10.00		\$40.50
EB1P100M57				Sold separately (EECAP1P)	57	15.52	1	\$123.00
EB3P100M6	Three-phase	600VAC/DC	100A	Ships w/2 Endcaps	6	1.84	1	\$48.50
EB3P100M9					9	3.07		\$61.00
EB3P100M12					12	4.28		\$76.00
EB3P100M15					15	5.54		\$101.00
EB3P100M57				Sold separately (EECAPMP)	57	44.67	1	\$344.00

Comb-Bus Bars



Typical Single-Phase Dimensional Data


mm [inches]



Single-Phase Comb-Bus Bar Dimensions

Part Number	A mm [inches]	B mm [inches]	C # of pins
EB1P100M3	35.6 [1.40]	60.4 [2.38]	3
EB1P100M6	88.9 [3.50]	113.0 [4.45]	6
EB1P100M9	142.4 [5.61]	157.1 [6.19]	9
EB1P100M12	195.8 [7.71]	211.8 [8.33]	12
EB1P100M15	249.2 [9.81]	271.7 [10.70]	15
EB1P100M57	996.8 [39.24]	1011.2 [39.81]	57


Typical Three-Phase Dimensional Data



Three-Phase Comb-Bus Bar Dimensions

Part Number	A mm [inches]	B inches [mm]	C # of Pins
EB3P100M6	88.9 [3.50]	103.7 [4.08]	6
EB3P100M9	142.4 [5.61]	158.4 [6.24]	9
EB3P100M12	195.8 [7.71]	213.3 [8.39]	12
EB3P100M15	249.2 [9.81]	265.0 [10.43]	15
EB3P100M57	996.8 [39.24]	1011.2 [39.81]	57


Comb-Bus Bar Installation and Accessories



Comb-Bus Bar Accessories


Part Number	Description	Product Weight (lbs)	Qty. Per Pack	Price
EECAP1P	Single-phase busbar endcap	0.02	50	\$76.00
EECAP1P-10			10	\$21.00
EECAPMP	Three-phase busbar endcap	0.22	50	\$92.00
EECAPMP-10			10	\$26.50
EPWR35MM	35mm² feeder terminal for three-phase busbar, wire range: 10-1/0 AWG CU, torque 50 lb-in, (115A, 1000VAC/DC)	0.68	10	\$168.00
EPWR35MM-1			1	\$25.00
EPWR50MM	50mm² direct feed terminal, wire range: 14-1 AWG CU, torque 35 lb-in, (115A, 1000VAC/DC)	0.61	10	\$203.00
EPWR50MM-1			1	\$29.50
EFSCVR	Spare contact safety protection covers	0.17	10	\$74.00
EFSCVR-2			2	\$22.00
EPWR1PLP	Single-phase low-profile feeder terminal, wire range: 10-1/0 AWG CU, torque 50 lb-in, (115A, 1000VAC/DC)	0.51	10	\$183.00
EPWR1PLP-1			1	\$27.50

DIN Rail Removal



Fuse Holder Accessories

Part Number	Description	Qty. Per Pack	Price
JV-L (Not Field Installable)	Multi-pole connection kit to connect multiple Class CC and Midget Class fuse holders together.	6 connectors 3 handle pins	\$15.00




JV-L


Comb-Bus Accessories

Dimensions

mm [inches]




EECAP1P
EECAP1P-10




EECAPMP
EECAPMP-10

EPWR1PLP
EPWR1PLP-1





EPWR50MM
EPWR50MM-1




Comb-Bus Accessories Dimensions

mm [inches]



Accessories


**FP-2****JV-L**

Accessories			
Part Number	Description	Pcs/Pkg	Price
FP-2	Fuse puller for fuse dia. 13/32" - 13/16". Fuse type: 0-60A, 250V; 0-30A, 600V	1	\$40.00
JV-L* (Not Field Installable)	Multi-pole connection kit to connect new design multiple Class CC and Midget Class fuse holders together. Kit consists of 6 connectors and 3 handle pins to connect up to 4 fuse holders.		\$15.00

Note: Will not work with retired design fuse holders shipped before November 1, 2009.

*Roll pin punch or installation tool is required to install handle pins (Tool not sold by AutomationDirect.com).

Handle Pin Dimensions
Diameter = 0.0625 in [1.58 mm]
Length = 0.632 in [16.07 mm]



Cross Reference Guide



CROSS REFERENCE GUIDE By manufacturers type reference or series number. Ampere ratings must be added for ordering purposes.

FUSE TYPE		VOLT	EDISON	BRUSH/ DORMAN	BUSSMANN	MERSEN / GOULD	GEC/CEFCO	LITTELFUSE
UL CLASS CURRENT LIMITING FUSES (CSA CLASS)								
CC (HRCI-CC)	Time-Delay	600	EDCC	–	LP-CC	ATDR	–	CCMR
	Time-Delay	600	HCTR	–	FNQ-R	ATQR	–	KLDR
	Fast-Acting	600	HCLR	HCLR	KTK-R	ATMR	CTK-R	KLKR
RK1	Time-Delay Dual Element	250	LENRK	–	LPN-RK-SP	A2DR	–	LLNRK
		600	LESRK	–	LPS-RK-SP	A6DR	–	LLSRK
RK5	Time-Delay Dual Element	250	ECNR	–	FRN-R	TR	–	FLNR
		600	ECSR	–	FRS-R	TRS	–	FLSR
J	Time-Delay Dual Element	600	JDL	–	LPJ	AJT	–	JTD
	High-Speed AC Drive	600	JHL	–	DFJ	HSJ	–	–
T	Extremely Fast-Acting	300	TJN	–	JJN	A3T	–	JLLN
		600	TJS	–	JJS	A6T	–	JLLS
UL CLASS GENERAL PURPOSE FUSES								
Midget	Fast-Acting	600	MCL	MCL	KTK	ATM	CTK	KLK
		250	MOL	MOL	BAF/BAN	OTM	–	BLF
	Time-Delay	500	MEQ	MEQ	FNQ	ATQ	–	FLQ
		250	MEN	MEN	FNM	TRM	–	FLM
1/4"x 1-1/4" Ceramic	Fast-Acting	250/125	ABC	ABC	ABC	GAB	–	314
1/4"x 1-1/4" Glass		250/32	AGC	AGC	AGC	GGC	–	312
1/4"x 1-1/4" Ceramic	Time-Delay	250	MDA	MDA	MDA	–	–	326
1/4"x 1-1/4" Glass		250/32	MDL	MDL	MDL	GDL	–	313
5x20 mm Glass	Fast-Acting	250/125	GMA	GMA	GMA	GGM	–	235
	Medium Time-Delay	250/125	GMC	GMC	GMC	GSC	–	–
5x20 mm Glass	Fast-Acting	250	S500	BDB	GDB	GSB	–	217
	Time-Delay	250	S506	BDC	GDC	GDG	–	218
Fuse Puller								
Fuse Puller FP-2			old - 38072 new - FP-2	–	FP-2	–	–	–



SIRCOVER UL 1008

Manual Transfer Switching Equipment

The solution for manufacturing, power distribution and domestic applications

Functions

The Socomec SIRCOVER family of switches are manual transfer switches rated UL 1008. These switches are extremely durable and are tested and approved for use in the most demanding applications, such as resistive load or total system applications.

Applications

- Normal power supply to generator transfer
- Bypass operations
- Changing motor phase for rotation control or equipment grounding

Advantages

Stable positions

SIRCOVERs have three stable, completely isolated positions that are not affected by voltage drops or mechanical vibrations. This safety feature eliminates the risk of short-circuiting between two unsynchronized power supplies, even during transient events.

Compact design

The SIRCOVER is based on back-to-back switching technology, providing a compact solution.

Reliability

The SIRCOVER has double breaking per pole achieved through its sliding bar contacts system.

The quick opening and rapid closure provides simultaneous disconnecting or making of all power contacts.




Agency approvals: UL file # E173959, CSA 112964, CE 2011/65/EU, 2014/35/EU LVD and 2014/30/EU EMC

Sircover M UL 1008 Manual Transfer Switching Equipment



To assemble a switch, please select:

Direct Operation




Switch Body

Direct Handle

OR

External Operation




Switch Body

Shaft

External Handle

UL 1008 Manual Transfer Switching Equipment

Part Number	Poles	Amp Rating	Max Operation Voltage (AC)	Price
41502012	2	100	240VAC	\$451.00
41503012	3		600VAC	\$527.00
41504012	4			\$674.00
41502026	2	260	240VAC	\$869.00
41503026	3		600VAC	\$1,063.00
41504026	4			\$1,411.00
41503042	3	400		\$1,243.00
41504042	4			\$1,696.00



[41503012](#)

Note: Not to be used as motor disconnect. MTS meets the requirements of NEC section 702.2.

Direct Handle

Part Number	Description	Switch Body Rating (A)	Handle Color	Handle Type	NEMA / UL Type	Price
41994012	B type handle for direct operation. Lockable in positions I and II.	100 - 400	Black	B3	—	\$42.50

Direct Handle



[41994012](#)

External Handles

Part Number	Switch Body Rating (A)	Handle Color	Handle Type	NEMA / UL Type	Lockable in 3 positions	Price
142D2113	100 - 200	Black / Blue	S2	4, 4X	No	\$76.00
142E2113		Red / Yellow				\$76.00
142F2113		Black / Blue		1, 3R, 12		\$70.00
142G2113		Red / Yellow				\$70.00
142D2813		Black / Blue		4, 4X	Yes	\$77.00
142E2813		Red / Yellow				\$77.00
142F2813		Black / Blue		1, 3R, 12		\$70.00
142G2813		Red / Yellow				\$70.00
143D3113	260 - 600	Black / Blue	S3	4, 4X	No	\$80.00
143E3113		Red / Yellow				\$80.00
143F3113		Black / Blue		1, 3R, 12		\$84.00
143G3113		Red / Yellow				\$84.00
143D3813		Black / Blue		4, 4X	Yes	\$80.00
143E3813		Red / Yellow				\$80.00
143F3813		Black / Blue		1, 3R, 12		\$80.00
143G3813		Red / Yellow				\$80.00



S2 Type

[142D2113](#)



S3 Type

[143D3113](#)

Sircover UL 1008

Manual Transfer


Switching Equipment



Shafts for External Handles

Part Number	Switch Body Rating (A)	Handle Type	Length (in / mm)	Price
14001020	30-400	S1, S2	7.9 / 200	\$14.00
14001032			12.6 / 320	\$15.00
14001040			15.7 / 400	\$16.50
14011520	600	S3	7.9 / 200	\$17.50
14011532			12.6 / 320	\$23.50
14011540			15.7 / 400	\$26.50

Shaft for External Handle



[14001020](#)

Bridging Bars

Part Number	Description	Switch Body Rating (A)	QTY	Price
41592021	Allows creation of a common point, above or below the switch, between positions I and II for line or load side connections.	100 - 200	2 bridging bars	\$101.00
41593021			3 bridging bars	\$134.00
41594021			4 bridging bars	\$169.00
41592041		260 - 400	2 bridging bars	\$106.00
41593041			3 bridging bars	\$158.00
41594041			4 bridging bars	\$230.00

Bridging Bars



[41593021](#)

Auxiliary Contacts

Part Number	Description	Switch Body Rating (A)	Contacts	Price
41590021	Auxiliary contact, side mount, 10A @ 125VAC/250VAC. Package of 2.	100 - 400	NO/NC on position I and II	\$17.00
41590022	Auxiliary contact, side mount, 1A @ 125VAC, low impedance. Package of 2.	100 - 400	Low level NO/NC on position I and II	\$26.50

Auxiliary contacts



[41590021](#)

Terminal Protection Screens

Part Number	Description	Switch Body Rating (A)	Number of poles	Price
41583021 *	Use for top or bottom protection against direct contact with terminals or connecting parts.	100 - 200	2/3 P	\$23.50
41584021 *		100 - 200	4 P	\$36.00
41583041		260 - 400	2/3 P	\$33.00
41584041		260 - 400	4 P	\$38.00

Terminal Protection Screens



[41583021](#)

* Note: Screen covers line AND load terminals

Terminal Lugs

Part Number	Description	Switch Body Rating (A)	Wires	Wires range	Lugs per kit	Wires per lug	Price
39542020	Kit of terminal lugs for connection of bare copper cables onto the terminals (without lugs).	200	Cu/Al	#6 - 300MCM	2	1	\$20.00
39542040		260-400		#4 - 600MCM	2		\$64.00
39543020		200		#6 - 300MCM	3		\$29.50
39543040		400		#2 - 600MCM	3		\$76.00
39544020		200		#6 - 300MCM	4		\$38.50
39544040		260-400		#4 - 600MCM	4		\$123.00



[39542040](#)

Sircover M UL 1008


Manual Transfer Switching Equipment

Technical Characteristics


Characteristics According to UL 1008			
	41502012 41503012 41504012	41502026 41503026 41504026	41503042 41504042
General Use Rating	100A	260A	400A
Operation Voltage 2 P / 3-4 P	240 / 600	240 / 600	240 / 600
Short-Circuit Rating With Any Breaker (kA) / Short-Circuit Capacity (ms)	10 / 25	14 / 50	14 / 50
Short-Circuit Rating at 600 VAC (kA)	100	65	65
Type of Fuse	J	J	J
Max. Fuse Rating (A)	200	600	600
Short-Circuit Rating With Specific Breaker (kA)			
Square D JJ reaker 250 A 2 Poles 240 VAC / 3-4 Poles 480 VAC	65	-	-
Schneider Electric NSX-F 160 A 3-4 Poles 480 VAC	35	-	-
Operational Power / Current Max Operational 1 ph			
240 VAC Total System (A)	100	260	400
240 VAC Resistive Load (A)	100	260	400
Operational Power / Current Max Operational 3 ph			
240 VAC Total System (A)	100	260	400
240 VAC Resistive Load (A)	100	260	400
480 VAC Total System (A)	100	260	400
480 VAC Resistive Load (A)	100	260	400
600 VAC Total System (A)	100	200	200
600 VAC Resistive Load (A)	100	260	400
Mechanical Endurance			
Endurance (Number of Operating Cycles)	6050	6050	4050
Operating Torque (lb·in [N·m])	88.5 [10]	88.5 [10]	128.3 [14.5]
Connection Terminals			
Min. Connection Section / AWG	#6	#4 / 2x1 / 0	#4 / 2x1 / 0
Max. Connection Section / AWG	300MCM	600MCM / 2 x 250MCM	600MCM / 2 x 250MCM
Agency Approvals			
UL file # E173959, CSA file # 112964, CE 2011/65/EU, 2014/35/EU LVD, and 2014/30/EU EMC			

Mounting orientation (100 to 400 A)



Ensure that the product is installed on a flat rigid surface



Recommended
orientation



OK



Sircover M UL 1008 Manual Transfer Switching Equipment

Dimensions


Inches [mm]




External Handles for UL 1008 Manual Transfer Switches

S2 Handle


Handle Dimensions



Direction of Operation




Door Drilling




S3 Handle


Handle Dimensions



Direction of Operation




Door Drilling



Shaft Length Minimum Dimensions

Switch Body Rating (A)	Dimension X		Handle Type	Length		Part Number
	in	mm		in	mm	
100 - 200	10-14.3	254-362	S2	7.9	200	14001020
	10-19	254-482		12.6	320	14001032
	10-22.1	254-562		15.7	400	14001040
260-400	20-23.4	508-594	S3	7.9	200	14011520
	20-28.1	508-714		12.6	320	14011532
	20-31.3	508-794		15.7	400	14011540




Please see our website www.AutomationDirect.com for complete engineering drawings.

Sircover M UL 1008 Manual Transfer Switching Equipment



Dimensions

Inches [mm]


Direct Handle




Bridging Bars




Terminal Lugs



39542040



39542020
39543020
39544020



39544040


Please see our website www.AutomationDirect.com for complete engineering drawings.

Sircover M UL 1008

Manual Transfer Switching Equipment



Dimensions (see table at bottom of page)



Dimensions Inches [mm]																							
Part Number	Body Rating	C	AC	AD	F 2p	F 3p	F 4p	J	K	M 2p	M 3p	M 4p	N	R1	R2	T	U	V	W	Y	Z	AA	CA
41502012	100A	6.42	6.93	10.43	9.61	9.61	11.57	1.38	3.84	6.30	6.30	8.27	7.68	0.18	0.14	1.97	0.98	1.18	0.43	0.14	1.55	6.30	0.56
41503012		[163]	[176]	[265]	[244]	[244]	[294]	[35]	[98]	[160]	[160]	[210]	[195]	[5]	[4]	[50]	[25]	[30]	[11]	[4]	[39]	[160]	[14]
41504012																							
41502026	260A	9.43	9.70	15.98	11.84	11.84	14.19	1.33	3.84	8.27	8.27	10.63	7.68	0.18	0.14	2.56	1.77	1.97	0.50	0.19	2.07	10.24	0.79
41503026		[240]	[246]	[406]	[301]	[301]	[360]	[34]	[98]	[210]	[210]	[270]	[195]	[5]	[4]	[65]	[45]	[50]	[13]	[5]	[53]	[260]	[20]
41504026																							
41503042	400A	9.43	9.70	15.98	—	11.84	14.19	1.33	3.84	—	8.27	10.63	7.68	0.18	0.14	2.56	1.77	1.97	0.50	0.19	2.07	10.24	0.79
41504042		[240]	[246]	[406]		[301]	[360]	[34]	[98]		[210]	[270]	[195]	[5]	[4]	[65]	[45]	[50]	[13]	[5]	[53]	[260]	[20]

Please see our website www.AutomationDirect.com for complete engineering drawings.



Miniature Circuit Breakers (UL 489)



Single-Pole



Two-Pole



Three-Pole

Overview

Gladiator miniature circuit breakers offer optimum and efficient protection for branch and control circuits up to 63 amps. The Gladiator series is available with B, C or D trip characteristics in accordance with UL 489. The Gladiator series units are DIN rail mountable and can be used in feeder and branch circuit applications.

Listings

- UL Listed under UL 489 Category DIVQ E503708
- Category DIHS E509077
- CE LVD 2014/35/EU
- IEC/EN 60947-2

Features and Benefits

- Dual rated for AC or DC applications
- Complete range of UL 489 listed DIN rail mounted miniature circuit breakers up to 63 amp current rating
- Single-pole, two-pole and three-pole models
- Suitable for reverse feed applications
- Suitable for branch circuit device protection
- Thermal-magnetic overcurrent protection – three levels of short circuit protection, categorized by B, C and D curves
- B-curve magnetic trip point: 3 to 5 times the rated current, typically used for resistive loads such as conductors or heaters.
- C-curve magnetic trip point: 5 to 10 times the rated current, typically used for small transformers, pilot devices, etc.
- D-curve magnetic trip point: 10 to 20 times the rated current, typically used for transformers or very high inductive loads.
- Trip-free design – breaker cannot be defeated by holding the handle in the "ON" position
- Captive screws cannot be lost
- Can also be used in applications for which UL 1077 or CSA C22.2 No.235 are also allowed
- Field installable shunt trip and auxiliary switches, side mountable
- Module width of only 18mm [0.71 in] (per pole)
- Contact position indicator (red / green)
- 35mm DIN rail mountable, utilizing spring clip

Full Line of Field Installable Accessories

- Auxiliary switch
- Alarm/auxiliary switch
- Shunt trip
- Padlock provision

Applications

- Feeder and Branch Circuit Protection
- PLC I/O points
- Motor control circuits
- Control instrumentation
- Power supplies
- Relays
- Convenience receptacle circuits (internal / external)
- Load circuits leaving the equipment (external)
- Computers
- UPS
- HACR Equipment (Heating Air Conditioning, Refrigeration)
- Power conditioners





Miniature Circuit Breakers

Tripping Characteristics

Gladiator miniature circuit breakers are available with "B" or "C" or "D" tripping characteristics.

Type B trip curve

(3 to 5 times I_n)

B-curve devices are suitable for resistive loads such as conductors or heaters.

Type C trip curve

(5 to 10 times I_n)

C-curve devices are suitable for applications where medium levels of inrush current are expected. Applications include small transformers, lighting, pilot devices, control circuits and coils. C-curve devices provide a medium magnetic trip point.



Type D trip curve

(10 to 20 times I_n)

D-curve devices are suitable for applications where high levels of inrush current are expected. The high magnetic trip point prevents nuisance tripping in high inductive applications such as motors, transformers and power supplies.

Labeling

The front of each Gladiator miniature circuit breaker is labeled for positive identification.





Miniature Supplementary Protectors (UL 1077)

Overview


Gladiator supplementary protectors are used to provide overcurrent protection where branch protection (for example, UL 489 MCCB) is already provided or not required. The units can be installed as a component within, or as a part of, an appliance or a piece of electrical equipment. Supplementary protectors are ideal replacements for fuses that are applied as a supplementary protector, i.e. in addition to branch protection (if required). They are 35mm DIN rail mountable, utilizing spring clips. These are standard protectors, recognized by UL and CSA under UL 1077 and CSA 22.2. They are CE marked in accordance with Low Voltage Directive (LVD) (73/23/EEC).

Product Specification

Gladiator Supplementary Protectors are a dual-rated product for both AC and DC supplies, in accordance with UL 1077 and CSA 22.2 standards and is marked with CE in accordance with the Low Voltage Directive. You can include this dual-standard product in your design and know that in most cases wherever your equipment is used, the product will conform to the local UL, CSA or IEC (International) requirements.

The supplementary protector is designed to be applied in conjunction with a branch circuit protector (if branch protection is required) and can be a replacement for similarly applied fuses. Its advantage over fuses is that it is resettable and the device's status is easily and clearly identified by the position of the handle and the flag indicator.

In addition, you can select a device that provides maximum reliability and accuracy to fit various applications due to the availability of a wide range of current ratings from 1 to 63 amperes in three overcurrent characteristic curves, B, C and D.



Single-Pole



Two-Pole



Three-Pole

Features and Benefits

- Dual rated for AC or DC applications
- Box terminals accept #14 to #4 wire
- Thermal magnetic overcurrent protection: three levels, categorized by B, C and D curves in direct relation to continuous rating of the device
 - **B-curve magnetic trip point:** 3 to 5 times the rated current, typically used for computers and electronic loads with very low inrush currents (PLC wiring).
 - **C-curve magnetic trip point:** 5 to 10 times the rated current, typically used for small transformers, pilot devices, etc.
 - **D-curve magnetic trip point:** 10 to 20 times the rated current, typically used for transformers or devices with very high inductive loads.
- Trip Free Design: Protector cannot be defeated by holding the handle in the "ON" position.
- Module width of only 18mm [0.71 in] per pole
- Color coded status indicator window (Red = ON or Green = OFF)
- IP20 finger protection
- 35mm DIN rail mountable, utilizing spring clip
- Captive screws cannot be lost
- Suitable for reverse feed applications

Listings

- UL recognized under UL 1077 Category QVNU2 File E508820
- CE File LVD
- IEC/EN 60947-2

Applications

Gladiator Supplementary Protectors are recognized per UL 1077 as a Supplementary Protector and can be fully utilized per the NEC and CEC Codes in that capacity. For international purposes, the entire Gladiator family is CE marked and in full conformity with the applicable IEC standards for miniature circuit breakers, EN/IEC 60898 and IEC/EN 60947-2.

Outside North America, they can be used in both residential and industrial applications as feeder and branch circuit protective devices. In North America, most European miniature circuit breakers are only UL recognized and CSA certified as "Supplementary Protectors," meaning they cannot be utilized as feeder or branch circuit protective devices per the local electrical codes (2008 NEC 240.10 and CEC Part 1 C22.1). This commonly restricts their use to applications where "closer" protection is desired than that offered by a branch circuit protection device.

Gladiator Supplementary Protectors are ideal for providing protection in many applications, including:

- Control power transformers (D curve)
- Relays
- Contactor coils
- PLC I/O points
- Lighting circuits
- Power supplies
- Computers
- Electronic equipment
- Control circuits



Miniature Circuit Breakers (UL 489)



Single-Pole

Gladiator UL 489 Single-Pole 277 VAC Selection Guide						
Ampere Rating	B-Curve Part Number	Price	C-Curve Part Number	Price	D-Curve Part Number	Price
1	GMCBU-1B-1	\$19.00	GMCBU-1C-1	\$19.00	GMCBU-1D-1	\$19.00
2	GMCBU-1B-2	\$19.00	GMCBU-1C-2	\$19.00	GMCBU-1D-2	\$19.00
3	GMCBU-1B-3	\$19.00	GMCBU-1C-3	\$19.00	GMCBU-1D-3	\$19.00
4	GMCBU-1B-4	\$19.00	GMCBU-1C-4	\$19.00	GMCBU-1D-4	\$19.00
5	GMCBU-1B-5	\$19.00	GMCBU-1C-5	\$19.00	GMCBU-1D-5	\$19.00
6	GMCBU-1B-6	\$19.00	GMCBU-1C-6	\$19.00	GMCBU-1D-6	\$19.00
8	GMCBU-1B-8	\$19.00	GMCBU-1C-8	\$19.00	GMCBU-1D-8	\$19.00
10	GMCBU-1B-10	\$19.00	GMCBU-1C-10	\$19.00	GMCBU-1D-10	\$19.00
15	GMCBU-1B-15	\$19.00	GMCBU-1C-15	\$19.00	GMCBU-1D-15	\$19.00
16	GMCBU-1B-16	\$19.00	GMCBU-1C-16	\$19.00	GMCBU-1D-16	\$19.00
20	GMCBU-1B-20	\$19.00	GMCBU-1C-20	\$19.00	GMCBU-1D-20	\$19.00
25	GMCBU-1B-25	\$19.00	GMCBU-1C-25	\$19.00	GMCBU-1D-25	\$19.00

Gladiator UL 489 Single-Pole 120/240 VAC Selection Guide						
Ampere Rating	B-Curve Part Number	Price	C-Curve Part Number	Price	D-Curve Part Number	Price
30	GMCBU-1B-30	\$19.00	GMCBU-1C-30	\$19.00	GMCBU-1D-30	\$19.00
32	GMCBU-1B-32	\$19.00	GMCBU-1C-32	\$19.00	GMCBU-1D-32	\$19.00
40	GMCBU-1B-40	\$19.00	GMCBU-1C-40	\$19.00	GMCBU-1D-40	\$19.00
50	GMCBU-1B-50	\$21.50	GMCBU-1C-50	\$21.50	GMCBU-1D-50	\$21.50
63	GMCBU-1B-63	\$21.50	GMCBU-1C-63	\$21.50	GMCBU-1D-63	\$21.50



Two-Pole

Gladiator UL 489 Two-Pole 480Y/277 VAC Selection Guide						
Ampere Rating	B-Curve Part Number	Price	C-Curve Part Number	Price	D-Curve Part Number	Price
1	GMCBU-2B-1	\$37.00	GMCBU-2C-1	\$37.00	GMCBU-2D-1	\$37.00
2	GMCBU-2B-2	\$37.00	GMCBU-2C-2	\$37.00	GMCBU-2D-2	\$37.00
3	GMCBU-2B-3	\$37.00	GMCBU-2C-3	\$37.00	GMCBU-2D-3	\$37.00
4	GMCBU-2B-4	\$37.00	GMCBU-2C-4	\$37.00	GMCBU-2D-4	\$37.00
5	GMCBU-2B-5	\$37.00	GMCBU-2C-5	\$37.00	GMCBU-2D-5	\$37.00
6	GMCBU-2B-6	\$37.00	GMCBU-2C-6	\$37.00	GMCBU-2D-6	\$37.00
8	GMCBU-2B-8	\$37.00	GMCBU-2C-8	\$37.00	GMCBU-2D-8	\$37.00
10	GMCBU-2B-10	\$37.00	GMCBU-2C-10	\$37.00	GMCBU-2D-10	\$37.00
15	GMCBU-2B-15	\$37.00	GMCBU-2C-15	\$37.00	GMCBU-2D-15	\$37.00
16	GMCBU-2B-16	\$37.00	GMCBU-2C-16	\$37.00	GMCBU-2D-16	\$37.00
20	GMCBU-2B-20	\$37.00	GMCBU-2C-20	\$37.00	GMCBU-2D-20	\$37.00
25	GMCBU-2B-25	\$37.00	GMCBU-2C-25	\$37.00	GMCBU-2D-25	\$37.00

Gladiator UL 489 Two-Pole 240VAC Selection Guide						
Ampere Rating	B-Curve Part Number	Price	C-Curve Part Number	Price	D-Curve Part Number	Price
30	GMCBU-2B-30	\$37.00	GMCBU-2C-30	\$37.00	GMCBU-2D-30	\$37.00
32	GMCBU-2B-32	\$37.00	GMCBU-2C-32	\$37.00	GMCBU-2D-32	\$37.00
40	GMCBU-2B-40	\$37.00	GMCBU-2C-40	\$37.00	GMCBU-2D-40	\$37.00
50	GMCBU-2B-50	\$42.50	GMCBU-2C-50	\$42.50	GMCBU-2D-50	\$42.50
63	GMCBU-2B-63	\$42.50	GMCBU-2C-63	\$42.50	GMCBU-2D-63	\$42.50

Miniature Circuit Breakers (UL 489)



Three-Pole

Gladiator UL 489 Three-Pole 480Y/277 VAC Selection Guide

Ampere Rating	B-Curve Part Number	Price	C-Curve Part Number	Price	D-Curve Part Number	Price
1	<u>GMCBU-3B-1</u>	\$56.00	<u>GMCBU-3C-1</u>	\$56.00	<u>GMCBU-3D-1</u>	\$56.00
2	<u>GMCBU-3B-2</u>	\$56.00	<u>GMCBU-3C-2</u>	\$56.00	<u>GMCBU-3D-2</u>	\$56.00
3	<u>GMCBU-3B-3</u>	\$56.00	<u>GMCBU-3C-3</u>	\$56.00	<u>GMCBU-3D-3</u>	\$56.00
4	<u>GMCBU-3B-4</u>	\$56.00	<u>GMCBU-3C-4</u>	\$56.00	<u>GMCBU-3D-4</u>	\$56.00
5	<u>GMCBU-3B-5</u>	\$56.00	<u>GMCBU-3C-5</u>	\$56.00	<u>GMCBU-3D-5</u>	\$56.00
6	<u>GMCBU-3B-6</u>	\$56.00	<u>GMCBU-3C-6</u>	\$56.00	<u>GMCBU-3D-6</u>	\$56.00
8	<u>GMCBU-3B-8</u>	\$56.00	<u>GMCBU-3C-8</u>	\$56.00	<u>GMCBU-3D-8</u>	\$56.00
10	<u>GMCBU-3B-10</u>	\$56.00	<u>GMCBU-3C-10</u>	\$56.00	<u>GMCBU-3D-10</u>	\$56.00
15	<u>GMCBU-3B-15</u>	\$56.00	<u>GMCBU-3C-15</u>	\$56.00	<u>GMCBU-3D-15</u>	\$56.00
16	<u>GMCBU-3B-16</u>	\$56.00	<u>GMCBU-3C-16</u>	\$56.00	<u>GMCBU-3D-16</u>	\$56.00
20	<u>GMCBU-3B-20</u>	\$56.00	<u>GMCBU-3C-20</u>	\$56.00	<u>GMCBU-3D-20</u>	\$56.00
25	<u>GMCBU-3B-25</u>	\$56.00	<u>GMCBU-3C-25</u>	\$56.00	<u>GMCBU-3D-25</u>	\$56.00

Gladiator UL 489 Three-Pole 240VAC Selection Guide

30	<u>GMCBU-3B-30</u>	\$56.00	<u>GMCBU-3C-30</u>	\$56.00	<u>GMCBU-3D-30</u>	\$56.00
32	<u>GMCBU-3B-32</u>	\$56.00	<u>GMCBU-3C-32</u>	\$56.00	<u>GMCBU-3D-32</u>	\$56.00
40	<u>GMCBU-3B-40</u>	\$56.00	<u>GMCBU-3C-40</u>	\$56.00	<u>GMCBU-3D-40</u>	\$56.00
50	<u>GMCBU-3B-50</u>	\$65.00	<u>GMCBU-3C-50</u>	\$65.00	<u>GMCBU-3D-50</u>	\$65.00
63	<u>GMCBU-3B-63</u>	\$65.00	<u>GMCBU-3C-63</u>	\$65.00	<u>GMCBU-3D-63</u>	\$65.00



Miniature Circuit Breakers (UL 489)

Technical Specifications

Gladiator Miniature Circuit Breakers – UL 489				
		B-Curve	C-Curve	D-Curve
Short Circuit Trip Response		3-5 x In	5-10 x In	10-20 x In
Current Rating		1, 2, 3, 4, 5, 6, 8, 10 ,15, 16, 20 ,25, 30, 32, 40, 50, 63A		
Maximum Voltage Ratings UL / CSA	1-63 A, AC	1P: 120/240V 2P:240V 3P: 240V		
	1-25 A, AC	1P: 277V 2P:480Y/277V 3P: 480Y/277V		
	1-63 A, DC	1P: 60V 2P:125V 3P: 125V		
Thermal Tripping Characteristics (Temperature)	Single-pole	104°F [40°C]		
	Multi-pole			
Interrupting Ratings (@ maximum voltage)	1-pole	AC: 10kA @ 120/240VAC, 10kA @ 277VAC (1~25A),10kA @ 120/240VAC (30~63A) DC: 10kA @ 60VDC		
	2-pole	AC: 10kA @ 240VAC, 480Y/277 VAC(1~25A), 10kA@240VAC (30~63A) DC: 10kA @ 125VDC		
	3-pole			
Rated Frequency		50/60 Hz		
Agency Approvals		UL, CB		

Notes: Line voltage connection suitable for reverse feed

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

Gladiator Miniature Circuit Breaker - IEC				
		B-Curve	C-Curve	D-Curve
Short Circuit Trip Response		3-5 x In	5-10 x In	10-20 x In
Current Rating		1, 2, 3, 4, 5, 6, 8, 10 ,15, 16, 20 ,25, 30, 32, 40, 50, 63A		
Maximum Voltage Ratings - IEC/EN 60947-2	1-pole	500VAC		
	2-pole / 3-pole			
	2 poles in series			
Thermal Tripping Characteristics (Temperature)	Single-pole	104°F [40°C]		
	Multi-pole			
Interrupt Ratings (At Max Voltage) Uimp		6kV		
Rated Frequency		50/60 Hz		

General Specifications		
Lifespan / Endurance		6,000 operations electrical
Operating Temperature		23°F to 104°F [-5°C to 40°C]
Housing Material		Engineering plastic
Mounting Position		On 35mm DIN rail (vertical)
Weight	1-pole	0.28 lb [130g]
	2-pole	0.58 lb [260g]
	3-pole	0.86 lb [390g]
Wire Size		
Conductor Size Copper Only, 149°F [65°C]		Lug type 14-4 AWG
Tightening Torque		
Tightening Torque		35 lb•in [3.9 N•m]



Series Technical Data (UL 489)

Temperature Derating (UL 489)

Temperature Derating for UL 489 Influence of Ambient Temperature T on Load Carrying Capacity (UL 489)												
Device Current Rating in Amps at 104°F [40°C]	In (A) at Higher Ambient Temperature											
	-40°F [-40°C]	-22°F [-30°C]	-4°F [-20°C]	14°F [-10°C]	32°F [0°C]	50°F [10°C]	68°F [20°C]	86°F [30°C]	104°F [40°C]	122°F [50°C]	140°F [60°C]	158°F [70°C]
1	1.5	1.4	1.3	1.3	1.2	1.2	1.1	1.1	1.0	0.9	0.8	0.8
2	3.0	2.8	2.7	2.6	2.4	2.3	2.2	2.1	2.0	1.8	1.7	1.5
3	4.4	4.2	4.0	3.8	3.6	3.5	3.3	3.2	3.0	2.8	2.5	2.3
4	5.9	5.6	5.4	5.1	4.9	4.6	4.4	4.2	4.0	3.7	3.4	3.1
5	7.4	7.0	6.7	6.4	6.1	5.8	5.5	5.3	5.0	4.6	4.2	3.9
6	8.9	8.4	8.0	7.7	7.3	6.9	6.6	6.3	6.0	5.5	5.0	4.6
8	11.8	11.3	10.7	10.2	9.7	9.3	8.8	8.4	8.0	7.3	6.7	6.2
10	14.8	14.1	13.4	12.8	12.2	11.6	11.0	10.5	10.0	9.2	8.4	7.7
15	22.2	21.1	20.1	19.1	18.2	17.4	16.5	15.8	15.0	13.8	12.6	11.6
16	23.6	22.5	21.4	20.4	19.4	18.5	17.6	16.8	16.0	14.7	13.5	12.3
20	29.5	28.1	26.8	25.5	24.3	23.2	22.1	21.0	20.0	18.3	16.8	15.4
25	36.9	35.2	33.5	31.9	30.4	28.9	27.6	26.3	25.0	22.9	21.0	19.3
30	44.3	42.2	40.2	38.3	36.5	34.7	33.1	31.5	30.0	27.5	25.2	23.1
32	47.3	45.0	42.9	40.8	38.9	37.0	35.3	33.6	32.0	29.3	26.9	24.7
40	59.1	56.3	53.6	51.1	48.6	46.3	44.1	42.0	40.0	36.7	33.6	30.8
50	73.9	70.4	67.0	63.8	60.8	57.9	55.1	52.5	50.0	45.9	42.0	38.6
63	93.1	88.6	84.4	80.4	76.6	72.9	69.5	66.2	63.0	57.8	53.0	48.6

Power Loss at I_n (UL 489)



Power Loss at I _n			
Characteristic B			
I _n [A]	1p P[W]	2p P[W]	3p P[W]
1	1.2	1.5	3.2
2	1.4	3.2	3.5
3	1.2	2.9	3.9
4	1.3	3.1	4.3
5	1.6	3.2	3.5
6	1.3	2.6	3.9
8	1.5	3.1	4.3
10	1.6	3.7	5.3
15	1.9	4.4	5.2
16	1.9	4.3	6.1
20	2.5	5.3	8.6
25	3.2	6.1	9.3
30	3.6	6.5	9.6
32	3.5	7.0	10.5
40	4.2	8.2	12.4
50	5.5	10.2	15.5
63	6.3	12.6	19.1

Power Loss at I _n			
Characteristic C			
I _n [A]	1p P[W]	2p P[W]	3p P[W]
1	1.1	1.8	3.2
2	1.3	2.2	4.2
3	1.1	2.1	3.7
4	1.2	2.8	4.0
5	1.5	3.0	3.7
6	1.2	2.3	3.5
8	1.4	3.1	4.2
10	1.5	2.8	4.3
15	1.8	3.3	4.8
16	1.8	3.6	5.4
20	2.7	4.8	8.2
25	3.1	5.9	9.1
30	3.3	6.4	9.5
32	3.7	7.1	10.7
40	4.0	7.9	12.3
50	4.8	9.7	15.1
63	6.1	12.1	18.5

Power Loss at I _n			
Characteristic D			
I _n [A]	1p P[W]	2p P[W]	3p P[W]
1	1.5	2.1	2.8
2	1.2	2.3	3.3
3	1.3	2.4	3.9
4	1.1	2.3	3.8
5	1.4	2.5	3.8
6	1.4	2.4	3.7
8	1.9	2.9	3.2
10	1.5	2.7	4.2
15	1.6	2.9	4.3
16	1.7	3.1	4.5
20	2.0	3.3	4.9
25	2.7	5.4	7.3
30	3.0	5.9	8.8
32	3.3	5.9	9.8
40	3.7	7.2	10.7
50	4.8	9.2	14.1
63	6.0	11.6	17.9


Miniature Circuit Breakers Accessories (UL 489)

Gladiator Miniature Circuit Breakers Accessories										
Part Number	Price	Description	For Use With	Rating	Control Voltage (U_e)	Operation Voltage	Trip Voltage	VA/Watt	Operating Time	Dimensions in [mm]
<u>GMCBU-AUX11</u>	\$16.50	Auxiliary contact	UL 489 models	6A @ 240VAC 3A @ 415VAC 1A @ 110VDC 2A @ 48VDC	-	-	-	-	-	0.35x4.13x2.60 [9x105x66]
<u>GMCBU-ALM11</u>	\$19.50	Alarm contact	UL 489 models							
<u>GMCBU-SH110-380VAC</u>	\$27.00	Shunt trip	UL 489 models	-	110-380 VAC 60-220 VDC	80-110% U_e	-	70	300ms	0.71x4.13x2.60 [18x105x66]
<u>GMCBU-UV110-120VAC</u>	\$34.00	Undervoltage trip	UL 489 models	-	110-120 VAC 220-240 VAC	-	35-70% U_e	1	2s	0.71x4.13x2.60 [18x105x66]
<u>GMCBU-UV220-240VAC</u>	\$34.00	Undervoltage trip	UL 489 models	-				3.5	2s	

[GMCBU-AUX11](#)[GMCBU-ALM11](#)[GMCBU-SH110-380VAC](#)
[GMCBU-UV110-120VAC](#)
[GMCBU-UV220-240VAC](#)

Gladiator Miniature Circuit Breakers Locking Device						
Part Number	Price	Description	For use with	Lock opening diameter	Weight	To operate
<u>GMCBU-LOCK</u>	\$7.75	Locking device	UL 489 and UL 1077 models	0.28 in [7.0]	Not less than 4.23 oz [120g]	Press button and insert into the handle

Note: Do not overpull by 10kg F.

[GMCBU-LOCK](#)



Press button and insert into handle





Miniature Circuit Breakers Accessories (UL 489)

Contact Diagrams

GMCBU-AUX11

	OFF	TRIP	ON
MCB 			
AUX 			


GMCBU-ALM11

	OFF	TRIP	ON
MCB 			
ALM 			

Connecting Accessories


Auxiliary contacts

Up to 0.71 in
[18mm]




Tripping devices

Up to 1.42 in
[36mm]



Both auxiliary contacts and tripping devices

Up to 2.13 in
[54mm]





Miniature Supplementary Protectors (UL 1077)



Single-Pole



Two-Pole



Three-Pole

Overview

Gladiator miniature supplemental protectors offer optimum and efficient protection for branch and control circuits up to 63 amps. The Gladiator series is available with B, C or D trip characteristics in accordance with UL 1077. The Gladiator series units are DIN rail mountable and can be used in feeder and branch circuit applications.

Listings

- UL Listed under UL 1077
Category DIHS E509077
Category NMTR E503708
- CE LVD 2014/35/EU
- IEC/EN 60947-2



Features and Benefits

- Dual rated for AC or DC applications
- Complete range of UL 1077 listed DIN rail mounted miniature supplemental protectors up to 63 amp current rating
- Single-pole, two-pole and three-pole models
- Suitable for reverse feed applications
- Thermal-magnetic overcurrent protection – three levels of short circuit protection, categorized by B, C and D curves
 - **B-curve magnetic trip point:**
3 to 5 times the rated current, typically used for resistive loads such as conductors or heaters.
 - **C-curve magnetic trip point:**
5 to 10 times the rated current, typically used for small transformers, pilot devices, etc.
 - **D-curve magnetic trip point:**
10 to 20 times the rated current, typically used for transformers or very high inductive loads.
- Trip-free design – breaker cannot be defeated by holding the handle in the “ON” position
- Captive screws cannot be lost
- Can also be used in applications for which UL 1077 or CSA C22.2 No.235 are also allowed
- Field installable shunt trip and auxiliary switches, side mountable
- Module width of only 18mm [0.71 in] (per pole)
- Contact position indicator (red / green)
- 35mm DIN rail mountable, utilizing spring clip

Applications

- Control power transformers (D curve)
- Relays
- Contactor coils
- PLC I/O points
- Lighting circuits
- Power supplies
- Computers
- Electronic equipment
- Control circuits

Gladiator
from AutomationDirect

Miniature Supplementary Protectors (UL 1077)

1-, 2- and
3-pole
models



Single-Pole



Two-Pole



Three-Pole

Third party certification and marking

- UL recognized under UL 1077 Category QVNU2, File E508820
- CE File LVD 2014/35/EU
- IEC 60947-2

Full line of field installable accessories

- Auxiliary switch
- Alarm/Auxiliary Switch
- Shunt trip
- Padlock provision

Trip curves

- B [3-5 I_n]
- C [5-10 I_n]
- D [10-20 I_n]



Gladiator Series Supplementary Protectors

Gladiator Series Supplementary Protectors are UL 1077 recognized for applications where branch circuit protection is not required or is already provided. They are thermal magnetic and protect against short circuit (see ratings chart) and overload conditions.

These DIN rail mounted supplementary protectors come in 1-, 2- or 3-pole configurations and are available in three trip curves.


The B-curve magnetic trip point is 3 to 5 times the rated current and is typically used for computers and electronic loads with very low current loads.

The C-curve magnetic trip point is 5 to 10 times the rated current and is typically used for small transformers, pilot devices, etc.

The D-curve magnetic trip point is 10 to 20 times the rated current and is typically used for transformers or with very high inductive loads.

Shunt trips are available for remotely tripping the protector with an external voltage from a control system or alarm device.

A padlocking feature is also available for preventing unauthorized operation. Maintenance personnel can safely work on protected equipment without electrical safety concerns.





Miniature Supplementary Protectors (UL 1077)



Single-Pole

Gladiator UL 1077 Single-Pole 277 VAC Selection Guide

Ampere Rating	B-Curve Part Number	Price	C-Curve Part Number	Price	D-Curve Part Number	Price
1	GMCB-1B-1	\$9.50	GMCB-1C-1	\$9.50	GMCB-1D-1	\$9.50
2	GMCB-1B-2	\$9.50	GMCB-1C-2	\$9.50	GMCB-1D-2	\$9.50
3	GMCB-1B-3	\$9.50	GMCB-1C-3	\$9.50	GMCB-1D-3	\$9.50
4	GMCB-1B-4	\$9.50	GMCB-1C-4	\$9.50	GMCB-1D-4	\$9.50
5	GMCB-1B-5	\$9.50	GMCB-1C-5	\$9.50	GMCB-1D-5	\$9.50
6	GMCB-1B-6	\$9.50	GMCB-1C-6	\$9.50	GMCB-1D-6	\$9.50
8	GMCB-1B-8	\$9.50	GMCB-1C-8	\$9.50	GMCB-1D-8	\$9.50
10	GMCB-1B-10	\$9.50	GMCB-1C-10	\$9.50	GMCB-1D-10	\$9.50
15	GMCB-1B-15	\$9.50	GMCB-1C-15	\$9.50	GMCB-1D-15	\$9.50
16	GMCB-1B-16	\$9.50	GMCB-1C-16	\$9.50	GMCB-1D-16	\$9.50
20	GMCB-1B-20	\$9.50	GMCB-1C-20	\$9.50	GMCB-1D-20	\$9.50
25	GMCB-1B-25	\$9.50	GMCB-1C-25	\$9.50	GMCB-1D-25	\$9.50
30	GMCB-1B-30	\$9.50	GMCB-1C-30	\$9.50	GMCB-1D-30	\$9.50
32	GMCB-1B-32	\$9.50	GMCB-1C-32	\$9.50	GMCB-1D-32	\$9.50
40	GMCB-1B-40	\$9.50	GMCB-1C-40	\$9.50	GMCB-1D-40	\$9.50
50	GMCB-1B-50	\$10.00	GMCB-1C-50	\$10.00	GMCB-1D-50	\$10.00
63	GMCB-1B-63	\$10.00	GMCB-1C-63	\$10.00	GMCB-1D-63	\$10.00



Two-Pole

Gladiator UL 1077 Two-Pole 480Y/277 VAC Selection Guide

Ampere Rating	B-Curve Part Number	Price	C-Curve Part Number	Price	D-Curve Part Number	Price
1	GMCB-2B-1	\$19.00	GMCB-2C-1	\$19.00	GMCB-2D-1	\$19.00
2	GMCB-2B-2	\$19.00	GMCB-2C-2	\$19.00	GMCB-2D-2	\$19.00
3	GMCB-2B-3	\$19.00	GMCB-2C-3	\$19.00	GMCB-2D-3	\$19.00
4	GMCB-2B-4	\$19.00	GMCB-2C-4	\$19.00	GMCB-2D-4	\$19.00
5	GMCB-2B-5	\$19.00	GMCB-2C-5	\$19.00	GMCB-2D-5	\$19.00
6	GMCB-2B-6	\$19.00	GMCB-2C-6	\$19.00	GMCB-2D-6	\$19.00
8	GMCB-2B-8	\$19.00	GMCB-2C-8	\$19.00	GMCB-2D-8	\$19.00
10	GMCB-2B-10	\$19.00	GMCB-2C-10	\$19.00	GMCB-2D-10	\$19.00
15	GMCB-2B-15	\$19.00	GMCB-2C-15	\$19.00	GMCB-2D-15	\$19.00
16	GMCB-2B-16	\$19.00	GMCB-2C-16	\$19.00	GMCB-2D-16	\$19.00
20	GMCB-2B-20	\$19.00	GMCB-2C-20	\$19.00	GMCB-2D-20	\$19.00
25	GMCB-2B-25	\$19.00	GMCB-2C-25	\$19.00	GMCB-2D-25	\$19.00
30	GMCB-2B-30	\$19.00	GMCB-2C-30	\$19.00	GMCB-2D-30	\$19.00
32	GMCB-2B-32	\$19.00	GMCB-2C-32	\$19.00	GMCB-2D-32	\$19.00
40	GMCB-2B-40	\$19.00	GMCB-2C-40	\$19.00	GMCB-2D-40	\$19.00
50	GMCB-2B-50	\$21.00	GMCB-2C-50	\$21.00	GMCB-2D-50	\$21.00
63	GMCB-2B-63	\$21.00	GMCB-2C-63	\$21.00	GMCB-2D-63	\$21.00



Miniature Supplementary Protectors (UL 1077)



Three-Pole

Gladiator UL 1077 Three-Pole 480Y/277 VAC Selection Guide

Ampere Rating	B-Curve Part Number	Price	C-Curve Part Number	Price	D-Curve Part Number	Price
1	<u>GMCB-3B-1</u>	\$28.50	<u>GMCB-3C-1</u>	\$28.50	<u>GMCB-3D-1</u>	\$28.50
2	<u>GMCB-3B-2</u>	\$28.50	<u>GMCB-3C-2</u>	\$28.50	<u>GMCB-3D-2</u>	\$28.50
3	<u>GMCB-3B-3</u>	\$28.50	<u>GMCB-3C-3</u>	\$28.50	<u>GMCB-3D-3</u>	\$28.50
4	<u>GMCB-3B-4</u>	\$28.50	<u>GMCB-3C-4</u>	\$28.50	<u>GMCB-3D-4</u>	\$28.50
5	<u>GMCB-3B-5</u>	\$28.50	<u>GMCB-3C-5</u>	\$28.50	<u>GMCB-3D-5</u>	\$28.50
6	<u>GMCB-3B-6</u>	\$28.50	<u>GMCB-3C-6</u>	\$28.50	<u>GMCB-3D-6</u>	\$28.50
8	<u>GMCB-3B-8</u>	\$28.50	<u>GMCB-3C-8</u>	\$28.50	<u>GMCB-3D-8</u>	\$28.50
10	<u>GMCB-3B-10</u>	\$28.50	<u>GMCB-3C-10</u>	\$28.50	<u>GMCB-3D-10</u>	\$28.50
15	<u>GMCB-3B-15</u>	\$28.50	<u>GMCB-3C-15</u>	\$28.50	<u>GMCB-3D-15</u>	\$28.50
16	<u>GMCB-3B-16</u>	\$28.50	<u>GMCB-3C-16</u>	\$28.50	<u>GMCB-3D-16</u>	\$28.50
20	<u>GMCB-3B-20</u>	\$28.50	<u>GMCB-3C-20</u>	\$28.50	<u>GMCB-3D-20</u>	\$28.50
25	<u>GMCB-3B-25</u>	\$28.50	<u>GMCB-3C-25</u>	\$28.50	<u>GMCB-3D-25</u>	\$28.50
30	<u>GMCB-3B-30</u>	\$28.50	<u>GMCB-3C-30</u>	\$28.50	<u>GMCB-3D-30</u>	\$28.50
32	<u>GMCB-3B-32</u>	\$28.50	<u>GMCB-3C-32</u>	\$28.50	<u>GMCB-3D-32</u>	\$28.50
40	<u>GMCB-3B-40</u>	\$28.50	<u>GMCB-3C-40</u>	\$28.50	<u>GMCB-3D-40</u>	\$28.50
50	<u>GMCB-3B-50</u>	\$30.50	<u>GMCB-3C-50</u>	\$30.50	<u>GMCB-3D-50</u>	\$30.50
63	<u>GMCB-3B-63</u>	\$30.50	<u>GMCB-3C-63</u>	\$30.50	<u>GMCB-3D-63</u>	\$30.50



Miniature Supplementary Protectors Technical Specifications (UL 1077)

Gladiator Miniature Supplementary Protectors – UL 1077				
		B-Curve	C-Curve	D-Curve
Short Circuit Trip Response		3-5 x In	5-10 x In	10-20 x In
Current Rating		1, 2, 3, 4, 5, 6, 8, 10 ,15, 16, 20 ,25, 30, 32, 40, 50, 63A		
Maximum Voltage Ratings UL / CSA	1-63 A, AC	1P: 120/240V 2P:240V 3P: 240V		
	1-63 A, AC	1P: 277V 2P:480Y/277V 3P: 480Y/277V		
	1-63 A, DC	1P: 60V 2P:125V 3P: 125V		
Thermal Tripping Characteristics (Temperature)	Single-pole	104°F [40°C]		
	Multi-pole			
Interrupting Ratings (@ maximum voltage)	1-pole	AC: 10kA @ 120/240 VAC, 6kA @ 277VAC DC: 10kA @ 60VDC		
	2-pole	AC: 10kA @ 120/240 VAC, 6kA @ 480Y/277VAC DC: 10kA @ 125VDC		
	3-pole			
Rated Frequency		50/60 Hz		
Agency Approvals		UL, CB, ABS		

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

Gladiator Miniature Supplementary Protectors - IEC				
		B-Curve	C-Curve	D-Curve
Short Circuit Trip Response		3-5 x In	5-10 x In	10-20 x In
Current Rating		1, 2, 3, 4, 5, 6, 8, 10 ,15, 16, 20 ,25, 30, 32, 40, 50, 63A		
Maximum Voltage Ratings - IEC 60898-1	1-pole	240/415 VAC		
	2-pole / 3-pole	415VAC		
	2 poles in series			
Thermal Tripping Characteristics (Temperature)	Single-pole	104°F [40°C]		
	Multi-pole			
Interrupt Ratings (At Max Voltage)		6kV		
Rated Frequency		50/60 Hz		

General Specifications

Lifespan / Endurance	6,000 operations electrical		
Operating Temperature	23°F to 104°F [-5°C to 40°C]		
Housing Material	Engineering plastic		
Mounting Position	On 35mm DIN rail (vertical)		
Weight	1 pole	0.26 lb [120g]	
	2 pole	0.53 lb [240g]	
	3 pole	0.79 lb [360g]	

Wire Size

Conductor Size Copper Only, 149°F [65°C]	Lug type 14-4 AWG
---	-------------------

Tightening Torque

Tightening Torque	17.5 lb•in [2 N•m]
--------------------------	--------------------

Gladiator[®] Series Technical Data (UL 1077)

from AutomationDirect

Temperature Derating (UL 1077)

Temperature Derating for UL 1077 Influence of Ambient Temperature T on Load Carrying Capacity (UL 1077)													
Device Current Rating in Amps at 77°F [25°C]	I_n (A) at Higher Ambient Temperature												
	-40°F [-40°C]	-22°F [-30°C]	-4°F [-20°C]	14°F [-10°C]	32°F [0°C]	50°F [10°C]	68°F [20°C]	77°F [25°C]	86°F [30°C]	104°F [40°C]	122°F [50°C]	140°F [60°C]	158°F [70°C]
1	1.4	1.3	1.2	1.2	1.1	1.1	1.0	1.0	1.0	0.9	0.8	0.7	0.7
2	2.7	2.6	2.5	2.4	2.3	2.2	2.1	2.0	1.9	1.8	1.6	1.5	1.4
3	4.1	3.9	3.7	3.6	3.4	3.2	3.1	3.0	2.9	2.6	2.4	2.2	2.0
4	5.5	5.2	5.0	4.7	4.5	4.3	4.1	4.0	3.8	3.5	3.2	3.0	2.7
5	6.9	6.5	6.2	5.9	5.7	5.4	5.1	5.0	4.8	4.4	4.0	3.7	3.4
6	8.2	7.8	7.5	7.1	6.8	6.5	6.2	6.0	5.8	5.3	4.8	4.4	4.1
8	11.0	10.5	10.0	9.5	9.0	8.6	8.2	8.0	7.7	7.0	6.5	5.9	5.4
10	13.7	13.1	12.5	11.9	11.3	10.8	10.3	10.0	9.6	8.8	8.1	7.4	6.8
15	20.6	19.6	18.7	17.8	17.0	16.1	15.4	15.0	14.4	13.2	12.1	11.1	10.2
16	22.0	20.9	19.9	19.0	18.1	17.2	16.4	16.0	15.4	14.1	12.9	11.8	10.9
20	27.5	26.2	24.9	23.7	22.6	21.5	20.5	20.0	19.2	17.6	16.1	14.8	13.6
25	34.3	32.7	31.1	29.7	28.3	26.9	25.6	25.0	24.0	22.0	20.2	18.5	17.0
30	41.2	39.2	37.4	35.6	33.9	32.3	30.8	30.0	28.8	26.4	24.2	22.2	20.4
32	44.0	41.9	39.9	38.0	36.2	34.4	32.8	32.0	30.7	28.2	25.8	23.7	21.7
40	54.9	52.3	49.8	47.5	45.2	43.1	41.0	40.0	38.4	35.2	32.3	29.6	27.2
50	68.7	65.4	62.3	59.3	56.5	53.8	51.3	50.0	48.0	44.0	40.4	37.0	33.9
63	86.5	82.4	78.5	74.8	71.2	67.8	64.6	63.0	60.5	55.5	50.9	46.6	42.8

Power Loss at I_n (UL 1077)



Power Loss at I_n			
Characteristic B			
I_n [A]	1p P[W]	2p P[W]	3p P[W]
1	1.6	2.2	4.2
2	1.5	2.9	4.4
3	1.3	2.7	4.2
4	1.3	2.9	4.6
5	1.5	3.5	4.3
6	1.9	2.9	4.3
8	1.5	3.1	4.5
10	1.7	3.5	5.5
15	1.9	3.5	6.2
16	2.1	3.4	6.3
20	3.1	4.3	8.6
25	3.1	5.6	10.1
30	3.3	6.6	10.2
32	3.4	6.8	11.5
40	4.2	8.6	13.2
50	5.3	11.1	15.5
63	6.2	12.9	19.6

Power Loss at I_n			
Characteristic C			
I_n [A]	1p P[W]	2p P[W]	3p P[W]
1	1.3	2.1	4.1
2	1.4	2.3	4.3
3	1.2	2.4	4.5
4	1.3	2.7	4.1
5	1.5	3.3	4.2
6	1.3	2.8	3.9
8	1.6	3.0	4.3
10	1.4	3.1	4.9
15	1.6	3.6	5.2
16	1.7	3.3	5.7
20	2.8	4.7	7.9
25	2.9	5.5	9.8
30	3.4	6.7	9.9
32	3.5	7.2	11.2
40	4.1	8.5	13.3
50	5.2	10.8	15.4
63	6.3	13.1	19.2

Power Loss at I_n			
Characteristic D			
I_n [A]	1p P[W]	2p P[W]	3p P[W]
1	1.3	2.5	2.9
2	1.5	2.4	3.1
3	1.3	2.1	3.5
4	1.4	2.4	3.9
5	1.4	2.8	3.7
6	1.4	2.4	3.8
8	1.2	2.7	3.8
10	1.5	2.8	4.1
15	1.4	2.7	4.2
16	1.5	3.1	4.5
20	2.1	3.5	4.7
25	2.4	5.2	7.1
30	2.8	5.6	8.5
32	3.1	5.9	9.5
40	4.1	7.9	11.5
50	5.0	9.8	14.7
63	6.1	12.3	18.5


Miniature Supplementary Protectors Accessories (UL 1077)

Gladiator Miniature Supplementary Protectors Accessories										
Part Number	Price	Description	For Use With	Rating	Control Voltage (U_e)	Operation Voltage	Trip Voltage	VA/Watt	Operating Time	Dimensions in [mm]
<u>GMCB-AUX11</u>	\$15.00	Auxiliary contact	UL 1077 models	6A @ 240VAC 3A @ 415VAC 1A @ 110VDC 2A @ 48VDC	-	-	-	-	-	0.35x3.19x2.60 [9x81x66]
<u>GMCB-ALM11</u>	\$16.50	Alarm contact	UL 1077 models							
<u>GMCB-SH110-380VAC</u>	\$24.00	Shunt trip	UL 1077 models	-	110-380 VAC 60-220 VDC	80-110% U_e	-	70	300ms	0.71x3.19x2.60 [18x81x66]

[GMCB-AUX11](#)[GMCB-ALM11](#)[GMCB-SH110-380VAC](#)

Gladiator Miniature Circuit Breakers Locking Device						
Part Number	Price	Description	For use with	Lock opening diameter	Weight	To operate
<u>GMCBU-LOCK</u>	\$7.75	Locking device	UL 489 and UL 1077 models	0.28 in [7.0]	Not less than 4.23 oz [120g]	Press button and insert into the handle

Note: Do not overpull by 10kg F.

[GMCBU-LOCK](#)



Press button and insert into handle





Miniature Supplementary Protectors Accessories (UL 1077)

Contact Diagrams

GMCB-AUX11

	OFF	TRIP	ON
MCB 			
AUX 			


GMCB-ALM11

	OFF	TRIP	ON
MCB 			
ALM 			

Connecting Accessories


Auxiliary contacts

Up to 0.71 in
[18mm]




Tripping devices

Up to 1.42 in
[36mm]



Both auxiliary contacts and tripping devices


Up to 2.13 in
[54mm]



1P : 120g





2P : 240g



3P : 360g

Supplementary Protectors

Supplementary Protectors Sample Applications



Supplementary protectors are not to be used in feeder circuits or motor circuits. Use them only in applications where branch protection is already provided or is not required.

Gladiator Cuttable Busbars

Gladiator busbars are the first cuttable UL489 rail and are available in a wide range of step spacings and cross-sections.

Whether you're feeding from the top, the bottom, centrally, or laterally, the Gladiator busbar system provides the flexibility you need to meet all requirements and any mounting situation.

Accessories such as feeder terminals and contact-protective, finger-safe end caps are also available.

These busbars are suitable for DC applications and for use in situations with a high degree of pollution.

Features

- For AC or DC applications
- One of the first cuttable UL489 busbars – no special tools required
- For GFCB/GFCBU series MCBs and protectors
- Can be used with fuse holders according to UL 512
- Can be used with 1-, 2-, or 3-phase systems
- Rated for 80/100 A
- Center feeding at 160/200 A
- Available accessories include feeder terminals, finger-safe push-on terminal covers, and end caps
- Completely closed
- Protection class: IP 20
- 2014/35/EU (Low Voltage Directive)
- 2011/65/EU Annex II 2015/863/EU

Gladiator
from AutomationDirect



UL file number E197592



GMCB-BB3P-57-100C



GMCB-BB1P-57-100C

UL508 Gladiator Busbars Selection Guide

Part Number	Price	Amps	Voltage (VAC/VDC)	Number of Pins	Cut to Length?	Connections	Endcaps	Drawing
GMCB-BB1P-57-100C	\$37.50	100	600	57	Yes	Up to 57 1-pole Gladiator GFCB series miniature circuit breakers without auxiliary components	2, included	PDF
GMCB-BB2P-56-100C	\$56.00	100	600	56	Yes	Up to 28 2-pole Gladiator GFCB series miniature circuit breakers without auxiliary components	2, included	PDF
GMCB-BB3P-57-100C	\$79.00	100	600	57	Yes	Up to 19 3-pole Gladiator GFCB series miniature circuit breakers without auxiliary components	2, included	PDF

UL508 Gladiator Busbars Technical Specifications

Voltage Ratings	Single Phase	2 and 3 phase
Max AC Voltage	600VAC	
Max DC Voltage	1000VDC	600VDC
Current Ratings	End Feed	Center Feed
Max Current, 25mm ² Cross Section	100A	200A*
Protection Class	IP20	IP20
KA Rating (J Fuse)	100KA	
25mm ² (3 Fuse)	200A	

* Two 115A feeder terminals required per phase.

UL489 Gladiator Busbars Selection Guide

Part Number	Price	Amps	Voltage (VAC/VDC)	Number of Pins	Cut to Length?	Connections	Endcaps	Drawing
GMCBU-BB1P-12-100C	\$22.50	100	1000	12	Yes	Up to 12 1-pole Gladiator GMCBU series miniature circuit breakers without auxiliary components	2, included	PDF
GMCBU-BB1P-57-100C	\$87.00	100	1000	57	Yes	Up to 57 1-pole Gladiator GMCBU series miniature circuit breakers without auxiliary components	2, included	PDF
GMCBU-BB2P-12-100C	\$27.50	100	1000	12	Yes	Up to 6 2-pole Gladiator GMCBU series miniature circuit breakers without auxiliary components	2, included	PDF
GMCBU-BB2P-56-100C	\$108.00	100	1000	56	Yes	Up to 28 2-pole Gladiator GMCBU series miniature circuit breakers without auxiliary components	2, included	PDF
GMCBU-BB3P-12-100C	\$31.50	100	1000	12	Yes	Up to 4 3-pole Gladiator GMCBU series miniature circuit breakers without auxiliary components	2, included	PDF
GMCBU-BB3P-57-100C	\$123.00	100	1000	57	Yes	Up to 19 3-pole Gladiator GMCBU series miniature circuit breakers without auxiliary components	2, included	PDF

UL489 Gladiator Busbars Technical Specifications

Voltage Ratings	Single Phase	2 and 3 phase
Max AC Voltage	1000VAC	600VAC
Max DC Voltage	1000VDC	600VDC
Current Ratings	End Feed	Center Feed
Max Current, 25mm ² Cross Section	100A	200A*
Protection Class	IP20	IP20
KA Rating (J Fuse)	140KA	
25mm ² (3 Fuse)	200A	

* Two 115A feeder terminals required per phase.

Gladiator Cuttable Busbars Accessories



Gladiator
from AutomationDirect

UL508 Gladiator Busbars Accessories Selection Guide



Part Number	Price	Description	For Use With	Drawing
<u>GMCB-BB1P-ECAP</u>	\$6.00	Gladiator end cap. Package of 10.	For use with Gladiator GMCB series 1-phase busbars.	<u>PDF</u>
<u>GMCB-BBM-ECAP</u>	\$7.25	Gladiator end cap. For use with Gladiator GMCB series 2-phase and 3-phase busbars. Package of 10.	For use with Gladiator GMCB series 2-phase and 3-phase busbars.	<u>PDF</u>
<u>GMCB-BBM-PTB</u>	\$54.00	Gladiator box type wiring lug, 115A, 1000 VAC/VDC, one opening, 1/0 to 10 AWG copper only. Package of 10.	For use with Gladiator GMCB series 2-phase and 3-phase UL1077 busbars.	<u>PDF</u>
<u>GMCB-BB1P-PTB</u>	\$48.00	Gladiator box type wiring lug, 115A, 1000 VAC/VDC, one opening, 1/0 to 10 AWG copper only. Package of 10.	For use with Gladiator GMCB series 1-phase UL1077 busbars.	<u>PDF</u>
<u>GMCB-BBM-BFT</u>	\$54.00	Gladiator direct feed wiring lug, 115A, 1000 VAC/VDC, one opening, 1 to 14 AWG copper only. Package of 10.	For use with Gladiator GMCB series UL1077 busbars.	<u>PDF</u>
<u>GMCB-BBM-TMC-5</u>	\$23.00	Gladiator safety cover. Package of 10. For use with up to five unused pins on Gladiator GMCB series busbars.	For use with up to five unused pins on Gladiator GMCB series busbars.	<u>PDF</u>

UL489 Gladiator Busbars Accessories Selection Guide

Part Number	Price	Description	For Use With	Drawing
<u>GMCBU-BBM-BFT</u>	\$53.00	Gladiator direct feed wiring lug, 115A, 1000 VAC/VDC, one opening, 1 to 14 AWG copper only. Package of 8.	For use with Gladiator GMCBU series UL489 busbars.	<u>PDF</u>
<u>GMCBU-BBM-ECAP</u>	\$9.00	Gladiator end cap. Package of 10.	For use with Gladiator GMCBU series busbars.	<u>PDF</u>
<u>GMCBU-BBM-PTB</u>	\$77.00	Gladiator box type wiring lug, 115A, 1000 VAC/VDC, one opening, 2 to 14 AWG copper only. Package of 10.	For use with Gladiator GMCBU series UL489 busbars.	<u>PDF</u>
<u>GMCBU-BBM-TMC-3</u>	\$13.00	Gladiator safety cover. Package of 10.	For use with up to three unused pins on Gladiator GMCBU series busbars.	<u>PDF</u>




Complete system of cuttable busbar with accessories for top and bottom feeding.



1-Phase Feeder Terminal

2- and 3-Phase Feeder Terminal

Merz ML Series Non-Fusible Disconnect Switches



DIN Rail



Front Door



Enclosed

Compact Switches


UL 508/UL 60947 manual motor controllers have been additionally rated for use as motor disconnects. They are also known as compact switches in Europe.

The term "compact switch" is a common one in the industry and describes a particular approach to the design of disconnect switches – specifically, ON/OFF switches arranged for switchboard installation.

In the majority of cases the switches are designed for snap-on DIN rail mounting, base mounting or front mounting in a door. The terminal screws are all accessible from one side. ML1 Compact Switches are available for applications from 16A to 40A. For more demanding applications loads, the ML2 to ML3 series accommodates loads from 63A up to 125A.

Technical details for units in these series are covered in the following pages.

Typical Control Panel



UL 98 or UL 489
Non-fusible disconnect switches

or

Fusible disconnect switches



UL 508
Non-Fusible Switches



Agency Approvals

UL Listed File, E195426

Standards: UL 508, UL 60947-1 and UL 60947-4-1

Cam Switches CSA only file 025483_0_000

CE: 2014/35/EU LVD

2014/30/EU EMC

2011/65/EU RoHs


Merz UL 508 Non-Fusible Disconnect Switches DIN Rail Mount

To assemble a switch, please select:



Switch Body

+



External Handle

OR




Switch Body

+



Shaft

+



External Handle

Merz UL 508 Non-Fusible Manual Motor Controller Switches - DIN Rail Mount

Part Number	Price	Description	Switch Body Rating (A)	Poles	Drawing Link
ML1-016-V-A01	\$21.50	Non-fusible UL 508 / UL 60947 600VAC manual motor controller	16	3	PDF
ML1-025-V-A01	\$23.50		25		PDF
ML1-032-V-A01	\$25.00		32		PDF
ML1-040-V-A01	\$27.00		40		PDF
ML2-063-V-A02	\$37.50		63		PDF
ML2-080-V-A02	\$42.00		80		PDF
ML3-125-V-A02	\$48.50		125		PDF

Merz UL 508 Non-Fusible Disconnect Switches

DIN Rail Mount - Accessories

Lockable Handles								
Part Number	Price	Description	Type	Color	Mounting	NEMA/UL Type	Use With	Drawing Link
H05R	\$12.50	Two-position, lockable in OFF only	Round	Red/yellow	External front mount	NEMA 4/4X	Merz ML1 switch bodies in DIN rail applications with hinged doors.	PDF
H05B	\$12.50	Two-position, lockable in OFF only	Round	Black/gray	External front mount	NEMA 4/4X	Merz ML1 switch bodies in DIN rail applications with hinged doors.	PDF
H06R	\$14.50	Two-position, lockable in OFF only	Round	Red/yellow	External front mount	NEMA 4/4X	Merz ML2 and ML3 switch bodies in DIN rail applications with hinged doors.	PDF
H06B	\$14.50	Two-position, lockable in OFF only	Round	Black/gray	External front mount	NEMA 4/4X	Merz ML2 and ML3 switch bodies in DIN rail applications with hinged doors.	PDF
H01R	\$12.50	Two-position, lockable in OFF only	Round	Red/yellow	External front mount	NEMA 4/4X	Merz ML1 switch bodies in DIN rail applications with non-hinged doors.	PDF
H01B	\$12.50	Two-position, lockable in OFF only	Round	Black/gray	External front mount	NEMA 4/4X	Merz ML1 switch bodies in DIN rail applications with non-hinged doors.	PDF
H02R	\$14.50	Two-position, lockable in OFF only	Round	Red/yellow	External front mount	NEMA 4/4X	Merz ML2 and ML3 switch bodies in DIN rail applications with non-hinged doors.	PDF
H02B	\$14.50	Two-position, lockable in OFF only	Round	Black/gray	External front mount	NEMA 4/4X	Merz ML2 and ML3 switch bodies in DIN rail applications with non-hinged doors.	PDF
H10B	\$7.25	Two-position, lockable in OFF only	Pistol	Black/gray	Direct mount	NEMA 1	Merz ML1 switch bodies in DIN rail applications. On-off faceplate included.	PDF
H10R	\$7.25	Two-position, lockable in OFF only	Pistol	Red/yellow	Direct mount	NEMA 1	Merz ML1 switch bodies in DIN rail applications. On-off faceplate included.	PDF
H11B	\$8.75	Two-position, lockable in OFF only	Pistol	Black/gray	Direct mount	NEMA 1	Merz ML2 switch bodies in DIN rail applications. On-off faceplate included.	PDF
H11R	\$8.75	Two-position, lockable in OFF only	Pistol	Red/yellow	Direct mount	NEMA 1	Merz ML2 switch bodies in DIN rail applications. On-off faceplate included.	PDF
H12B	\$12.00	Two-position, lockable in OFF only	Pistol	Black/gray	Direct mount	NEMA 1	Merz ML3 switch bodies in DIN rail applications. On-off faceplate included.	PDF
H12R	\$12.00	Two-position, lockable in OFF only	Pistol	Red/yellow	Direct mount	NEMA 1	Merz ML3 switch bodies in DIN rail applications. On-off faceplate included.	PDF

Adjustable Shafts for External Handles					
Part Number	Price	Description	Length (mm [in])	Use With	Drawing Link
AL-165	\$5.50	6x6 mm [0.24 x 0.24 in] shaft	178-238 [7.01-9.37]	Merz handles -H01R(B), -H02R(B), -H05R(B), -H06R(B)	PDF
AL-265	\$6.50	6x6 mm [0.24 x 0.24 in] shaft	278-338 [10.95-13.31]	Merz handles -H01R(B), -H02R(B), -H05R(B), -H06R(B)	PDF
AL-365	\$7.75	6x6 mm [0.24 x 0.24 in] shaft	378-438 [14.88-17.24]	Merz handles -H01R(B), -H02R(B), -H05R(B), -H06R(B)	PDF
ASB-AL265-365	\$11.00	Shaft support	—	Merz AL-265 and AL-365 shafts	NA

NOTE: Shaft supports are necessary for extension of AL-265 and AL-365.



[AL-165](#)

Merz UL 508 Non-Fusible Disconnect Switches

Accessories

Merz UL 508 Additional Pole Modules (For Use with Merz MLx Switch Bodies in DIN Rail Applications)

Part Number	Price	Description	Module Rating (A)	Use With	Drawing Link
<u>SK1-V</u>	\$8.25	Fourth pole module (load break capable)	40A	ML1 switch bodies	<u>PDF</u>
<u>SK2-V</u>	\$17.00	Fourth pole module (load break capable)	80A	ML2 switch bodies	<u>PDF</u>
<u>SK3-V</u>	\$20.50	Fourth pole module (load break capable)	125A	ML3 switch bodies	<u>PDF</u>
<u>PE1-V</u>	\$8.25	Ground pole module	40A	ML1 switch bodies	<u>PDF</u>
<u>PE2-V</u>	\$13.00	Ground pole module	80A	ML2 switch bodies	<u>PDF</u>
<u>PE3-V</u>	\$15.50	Ground pole module	125A	ML3 switch bodies	<u>PDF</u>
<u>N1-V</u>	\$7.25	Solid neutral pole module	40A	ML1 switch bodies	<u>PDF</u>
<u>N2-V</u>	\$13.00	Solid neutral pole module	80A	ML2 switch bodies	<u>PDF</u>
<u>N3-V</u>	\$15.50	Solid neutral pole module	125A	ML3 switch bodies	<u>PDF</u>


Merz UL 508 Auxiliary Contact

Part Number	Price	Description	Rating	Drawing Link
<u>AUX11-V</u>	\$10.50	1 NO / 1 NC auxiliary contacts, left or right side mount For use with Merz ML1, ML2 or ML3 DIN rail mount switch bodies -A01, -A02, -E01R, -E02R, E03R, -E04R, -E05R	10A @ 600VAC	<u>PDF</u>

Merz UL 508 Terminal

Part Number	Price	Description	Rating	Drawing Link
<u>2KL-V</u>	\$25.50	2-pole solid feed-through terminal, left or right side mount For use with Merz ML1, ML2 or ML3 DIN rail mount switch bodies -A01, -A02, -E01R, -E02R, E03R, -E04R, -E05R	10A @ 600VAC	<u>PDF</u>

Optional contact, auxiliary contact, and terminal 2-pole




Optional contact/terminal

Max. 2NV/SK

In total max 3 contacts

+max 1 PE terminal

+max 1 N terminal




Optional contact/auxiliary contact/terminal

Max. 2NV/SK/AUX11

In total max 3 contacts

+max 1 PE terminal

+max 1 N terminal



Optional contact/auxiliary contact/terminal 2-pole/terminal

Max. 2NV/SK/AUX11

In total max 3 contacts

+max 2 2KL terminal 2-pole

+max 1 PE terminal

+max 1 N terminal

Merz UL 508 Non-Fusible Disconnect Switches With External Handle, Front Door Mount



Switch Body With Front External Handle

Wire connections accessible from the rear

Merz UL 508 Non-Fusible Disconnect Switches - With External Handle, Front Mount

Part Number	Price	Description	Switch Body Rating (A)	Poles	Handle	Drawing Link
ML1-016-E-H03R	\$33.00	Non-fusible UL 508 / UL 60947 manual motor controller 600VAC "suitable as motor" disconnect switch	16	3	Red/yellow	PDF
ML1-016-E-H03B	\$33.00		16		Black/gray	PDF
ML1-025-E-H03R	\$36.50		25		Red/yellow	PDF
ML1-025-E-H03B	\$36.50		25		Black/gray	PDF
ML1-032-E-H03R	\$37.00		32		Red/yellow	PDF
ML1-032-E-H03B	\$37.00		32		Black/gray	PDF
ML1-040-E-H03R	\$38.50		40		Red/yellow	PDF
ML1-040-E-H03B	\$38.50		40		Black/gray	PDF
ML2-063-E-H04R	\$53.00		63		Red/yellow	PDF
ML2-063-E-H04B	\$53.00		63		Black/gray	PDF

NOTE: Hardware for 4-hole door mounting and lockable handle for use with NEMA 4/4X enclosures included

Merz UL 508 Auxiliary Contact

Part Number	Price	Description	Rating	Drawing Link
AUX11-E	\$10.50	Auxiliary contact, left or right side mount, 1 NO / 1 NC contacts For use with Merz ML1, ML2 or ML3 door mount switch bodies -H03R(B), -H04R(B)	10A @ 600VAC	PDF

Merz UL 508 Terminal

Part Number	Price	Description	Rating	Drawing Link
2KL-E	\$13.00	2-pole solid feed-through terminal, left or right side mount For use with Merz ML1, ML2 or ML3 door mount switch bodies -H03R(B), -H04R(B)	10A @ 600VAC	PDF

Merz UL 508 Non-Fusible Disconnect Switches With Enclosure



Switch Body With Enclosure

General characteristics

- Gray enclosure with red handle
- Equipped with a 3-pole Merz ML1, ML2 or ML3 disconnect
- 1 removable ground terminal
- Possibility of adding 1 power pole and 1 auxiliary contact
- Operating temperature max 45°C or 55°C [113°F or 131°F]
- Operating temperature min -5°C [23°F]
- Polycarbonate plastic enclosure
- NEMA/UL Type 1, 3R, 4, 4X

Merz UL 508 Non-Fusible Disconnect Switches - With Enclosure

Part Number	Price	Description	Enclosure Rating (A)	Poles	Enclosure Size (in [mm])	Weight (lb [kg])	Included With PE/ Neutral Terminal	Included With Auxiliary Contacts	Drawing Link
ML1-025-V-E01R	\$73.00	Non-fusible UL 508 / UL 60947 manual motor controller 600VAC "suitable as motor" disconnect switch	25	3	4.80 x 7.72 [122 x 120]	1.35 [0.61]	PE1-V	AUX11-V 1 NO / 1 NC	PDF
ML1-032-V-E01R	\$76.00		32		4.80 x 7.72 [122 x 120]	1.35 [0.61]	PE1-V		PDF
ML1-040-V-E02R	\$108.00		40		7.87 x 7.87 [200 x 200]	3.35 [1.52]	PE1-V		PDF
ML2-063-V-E03R	\$101.00		63		7.87 x 7.87 [200 x 200]	3.85 [1.75]	PE2-V		PDF
ML2-080-V-E03R	\$156.00		80		7.87 x 7.87 [200 x 200]	3.85 [1.75]	PE2-V		PDF
ML3-125-V-E03R	\$179.00		125		7.87 x 7.87 [200 x 200]	4.05 [1.84]	PE3-V		PDF
ML1-040-V-E04R	\$125.00		40		7.87 x 7.87 [200 x 200]	3.40 [1.54]	PE1-V + NV2-V*		PDF
ML2-063-V-E05R	\$112.00		63		7.87 x 7.87 [200 x 200]	4.05 [1.84]	PE2-V + NV2-V*		PDF

* Replacement NV2-V units are not sold by AutomationDirect.com.

Merz UL 508 Non-Fusible Disconnect Switches

Accessories

Terminal Shrouds

Part Number	Price	Description	Use With	Poles	Drawing Link
<u>HS1-ML1</u>	\$3.00	Terminal shroud, line or load side	Merz ML1 switch bodies	1	<u>PDF</u>
<u>HS3-ML1</u>	\$8.75	Terminal shroud, line or load side	Merz ML1 switch bodies	3	<u>PDF</u>
<u>HS1-ML2</u>	\$5.50	Terminal shroud, line or load side	Merz ML2 switch bodies	1	<u>PDF</u>
<u>HS3-ML2</u>	\$14.50	Terminal shroud, line or load side	Merz ML2 switch bodies	3	<u>PDF</u>
<u>HS1-ML3</u>	\$6.50	Terminal shroud, line or load side	Merz ML3 switch bodies	1	<u>PDF</u>
<u>HS3-ML3</u>	\$17.50	Terminal shroud, line or load side	Merz ML3 switch bodies	3	<u>PDF</u>

[HS1-ML1](#)

Replacement Mounting Screws

Part Number	Price	Description	Use With
<u>ML-SKT-1</u>	\$5.50	Cover mounting screws	Merz small size enclosed disconnects -E01R
<u>ML-SKT-2</u>	\$6.50	Cover mounting screws	Merz large size enclosed disconnects -E02R, -E03R, -E04R, -E05R
<u>ML-SKT-3</u>	\$5.50	Screw kit, mounting and hardware screws	Shafts AL-165, AL-265, AL-365 (Shaft support ASB-AL265-365 and terminal shrouds HS3-ML1, HS3-ML2, HS3-ML3 included)
<u>ML-SKT-4</u>	\$6.25	Handle mounting screws	Merz handles -H01R(B), -H02R(B), -H03R(B), -H04R(B), -H05R(B), -H06R(B), -H08R(B), -H09R(B), -H010R(B), -H011R(B), -H012R(B)

[ML-SKT-1](#)

Merz UL 508 Non-Fusible Disconnect Switches

Technical Characteristics

Characteristics According to UL 508, UL 60947-4-1

Type	ML1-016	ML1-025	ML1-032	ML1-040	ML2-063-	ML2-080	ML3-125
General use rating (A)	16	25	32	40	63	80	125
Short-circuit rating at 600VAC (kA)	5	5	5	5	5	5	5
Type of fuse	RK5	RK5	RK5	RK5	RK5	RK5	RK5
Max. fuse rating (A)	50	50	50	50	80	80	125

Max. Motor hp / Max. 3-Phase Motor FLA

Type		ML1-016	ML1-025	ML1-032	ML1-040	ML2-063	ML2-080	ML3-125
General purpose 600VAC 3-phase [A]		16	25	32	40	63	80	125
Motor 3-phase	240VAC (hp [FLA])	7.5 [22]	7.5 [22]	10 [28]	10 [28]	15 [42]	20 [54]	25 [68]
	480VAC (hp [FLA])	10 [14]	10 [14]	20 [27]	20 [27]	30 [40]	40 [52]	50 [65]
	600VAC (hp [FLA])	10 [11]	10 [11]	20 [22]	20 [22]	30 [32]	40 [41]	50 [52]
Motor 1-phase	120VAC (hp [FLA])	1 [16]	1 [16]	1.5 [20]	1.5 [20]	3 [34]	5 [56]	7.5 [80]
	240VAC 2-Pole (hp [FLA])	2 [12]	2 [12]	3 [17]	3 [17]	7.5 [40]	10 [50]	15 [68]

Wire Type / Temperature – Use Copper (Cu) Wire Only, 75°C [167°F] or Higher

Type	ML1	ML2	ML3	AUX11	2KL
Terminal cross section [AWG]	14-8	14-2	8-1/0	17-13	17-13
Single or multi-core [mm2]	2.5-16	2.5-35	6-70	1-4	1-4
Stranded with sleeve [mm2]	2.5-16	1.5-25	6-50	1-2.5	1-2.5
Stripping distance connector cable (mm [in])	10 [0.39]	13 [0.51]	16 [0.63]	10 [0.39]	10 [0.39]
Torque terminal screw (N•m [lb•ft])	1.2 [0.89]	2.5 [1.84]	3 [2.21]	0.6 [0.44]	0.6 [0.44]

Environmental – Switch Body

Type	ML1-016	ML1-025	ML1-032	ML1-040	ML2-063	ML2-080	ML3-125
Max. surrounding air temperature (Open type) (C [F])	60 [140]	60 [140]	60 [140]	60 [140]	70 [158]	70 [158]	75 [167]
Max. ambient temperature (Enclosed type) (C [F])	45 [113]	45 [113]	45 [113]	45 [113]	50 [122]	50 [122]	55 [131]
Mounting	Horizontal on DIN rail or front door panel						

Auxiliary contacts

Electrical characteristics	A600, thermal 10A @ 600VAC
----------------------------	----------------------------

Product Weight – lb (kg)

Type	ML1-016	ML1-025	ML1-032	ML1-040	ML2-063	ML2-080	ML3-125
Open switches	0.40 [0.18]	0.40 [0.18]	0.40 [0.18]	0.40 [0.18]	0.75 [0.34]	0.75 [0.34]	0.95 [0.43]

Agency Approvals

UL file #E195426 (Manual Motor Controllers)

Note: Short-circuit rating achieved when used with corresponding fuse type and max fuse rating.

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

Merz Non-UL Cam Changeover Switches

4 Hole Front Mount

[Z251-2.H08B](#)[W251-2.H08B](#)

Merz Non-UL Cam Changeover Switches - 4 Hole Front Mount

Part Number	Price	Description	Rating (A)	Poles	Drawing Link
<u>Z251-2.H08B</u>	\$31.00	Non-UL changeover switches	25	2	<u>PDF</u>
<u>Z251-3.H08B</u>	\$38.00		25	3	<u>PDF</u>
<u>Z451-2.H08B</u>	\$43.50		32	2	<u>PDF</u>
<u>Z451-3.H08B</u>	\$56.00		32	3	<u>PDF</u>
<u>Z656-3.H09B</u>	\$102.00		80	3	<u>PDF</u>
<u>W251-2.H08B</u>	\$34.00	Non-UL reversing switches	25	2	<u>PDF</u>
<u>W251-3.H08B</u>	\$39.00		25	3	<u>PDF</u>
<u>W451-2.H08B</u>	\$56.00		32	2	<u>PDF</u>
<u>W451-3.H08B</u>	\$59.00		32	3	<u>PDF</u>

NOTE: Hardware for 4-hole door mounting and black operating handle included.

Merz Non-UL Cam Changeover Switches

Technical Characteristics

Characteristics According to CSA 22.2 No. 14-05			
Type	251	451	656
General Purpose 600VAC, 3-Phase	25A	32A	80A
Motor 3-Phase	110/120 VAC	3hp	7.5 hp
	220/240 VAC	7.5 hp	7.5 hp
	440/480 VAC	15hp	20hp
	550/600 VAC	20hp	20hp
Motor 1-Phase 2-pole	110/120 VAC	1.5 hp	–
	220/240 VAC	3hp	3hp
	440/480 VAC	7.5 hp	10hp
	550/600 VAC	10hp	15hp
Short-Circuit Rating at 600VAC (kA)	5	5	5
Type of Fuse	RK5	RK5	RK5
Max. Fuse Rating (A)	60	60	60
Max. Surrounding Air Temperature (Open Type) (°C [°F])	40 [104]	40 [104]	40 [104]

Suitable for use on a circuit capable of delivering not more than 5kA rms symmetrical amperes, 600V maximum

Wire Type / Temperature – Use Copper (Cu) Wire Only, 75°C [167°F] or Higher			
Type	251	451	656
Terminal cross section [AWG]	14-8	14-6	14-4
Single or multi-core [mm ²]	1-6	1.5-10	1.5-25
Finely stranded with sleeve [mm ²]	1-4	1.5-6	1.5-16
Stripping distance connector cable (mm [in])	10 [0.39]	12 [0.47]	15 [0.59]
Terminal screw torque (N•m [lb•ft])	4.5 [40]	5.1 [45]	4.5 [40]

NOTE: Verify that all connections (including bridging link connections) are tightened to manufacturer's required torque before energization.

Agency Approvals

CSA file #025483_0_000

NOTE: The controllers are suitable for use on a circuit capable of delivering not more than 5000 rms symmetrical amperes at 600VAC max when protected by a 60A Class RK5 fuse.

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

Bryant Pin and Sleeve Mechanical Interlocks

BRY420MI9W**BRYAUX1****BRYRPLCFT****BRYMIRS30**

Bryant Pin and Sleeve Mechanical Interlocks are used with matching connectors to provide enhanced safety in a variety of situations. These heavy-duty disconnect switches are horsepower rated for motor load applications.

The interlock's switch cannot be turned ON until the plug is completely engaged, and the plug cannot be removed from the interlock until the switch has been turned to the OFF position.

These interlocks feature durable NEMA 4X and 12 enclosures, which have been designed to provide watertight and dust-tight protection in harsh environments.

A watertight conduit hub and grounding plate are included for use with metallic conduit.

Available accessories include break-after-main-break and break-before-main-break auxiliary contacts. Replacement switches, as well as replacement mounting feet, are also available.

Features


- Disconnect switches in 20A, 30A, 60A, and 100A ratings, multiple wiring configurations, and with a pre-wired IEC 60309 receptacle.
- Accepts all manufacturers' IEC 60309 plugs
- Rugged housing provides superior corrosion and impact resistance for use in the harshest of industrial environments
- Watertight hub and grounding plate included
- Handles are designed to satisfy OSHA lockout/tagout requirements
- Manual motor controller

Applications

- OEMs
- Food processing
- Industrial applications
- Pharmaceuticals
- Data centers
- Welders
- Conveyors
- Mobile equipment

Certifications


- CSA file 033196_C_00
- UL file # E70402
- Accessories E36355 displayed as Hubbell HBL Series



Identification of Voltage Ratings

Bryant's Pin & Sleeve line safeguards against improperly connecting devices of different amperage and voltage ratings. Conformance with IEC 60309-1 and IEC 60309-2 international standards results in a singly-rated, non-interchangeable configuration for each amperage/voltage type.

The voltage rating can be identified by the clock position of the female grounding sleeve relative to the housing keyway. With the keyway always positioned at 6 o'clock, the female grounding sleeve is located at a specific clock position for each voltage rating.















































The housing keyway is always located at the 6 o'clock position on all female devices and is clearly visible to the user.



IEC Pin & Sleeve device housings are color coded by voltage rating for easy identification.

Rated Voltage	Color
100V-130V	Yellow
125V/250V	Orange
200V-250V	Blue
277V	Grey
380V-480V	Red
500V and above	Black

Bryant Pin and Sleeve Mechanical Interlocks

Bryant Unfused Pin and Sleeve Mechanical Interlock Selection Guide									
Part Number	Price	Amps	Poles/Wires	Configuration		Voltage	Horsepower	Use with Mating Plug	Drawing
				Recep/Conn	Plug/Inlet				
BRY420MI9W	\$513.00	20	3P / 4W			240VAC 3Ø	5	BRY420P9W	PDF
BRY420MI7W	\$513.00					480VAC 3Ø	10	BRY420P7W	PDF
BRY330MI4W	\$518.00	30	2P / 3W			120VAC	2	BRY330P4W	PDF
BRY330MI6W	\$518.00					240VAC	³ (208-240 VAC)	BRY330P6W	PDF
BRY330MI7W	\$518.00					480VAC	7.5	BRY330P7W *	PDF
BRY430MI12W	\$588.00		3P / 4W			120/240 VAC	³ (208-240 VAC)	BRY430P12W *	PDF
BRY430MI9W	\$588.00					240V AC 3Ø	7.5	BRY430P9W	PDF
BRY430MI7W	\$578.00					480V AC 3Ø	15	BRY430P7W	PDF
BRY430MI5W	\$588.00					600V AC 3Ø	20	BRY430P5W	PDF
BRY530MI7W	\$650.00		4P / 5W			277/480 VAC 3ØY	15	BRY530P7W	PDF
BRY360MI6W	\$773.00	60	2P / 3W			240VAC	^{7.5} (208-240 VAC)	BRY360P6W	PDF
BRY460MI12W	\$879.00		3P / 4W			120/240 VAC	^{7.5} (208-240 VAC)	BRY460P12W *	PDF
BRY460MI9W	\$879.00					240V AC 3Ø	15	BRY460P9W	PDF
BRY460MI7W	\$879.00					480V AC 3Ø	30	BRY460P7W	PDF
BRY460MI5W	\$879.00					600V AC 3Ø	40	BRY460P5W	PDF
BRY560MI9W	\$879.00		4P / 5W			120/208 VAC 3ØY	15	BRY560P9W	PDF
BRY560MI7W	\$879.00					277/480 VAC 3ØY	30	BRY560P7W	PDF
BRY4100MI12W	\$994.00	100	3P / 4W			120VAC	15	BRY4100P12W *	PDF
BRY4100MI9W	\$994.00					240VAC 3Ø	²⁵ (208-240 VAC)	BRY4100P9W	PDF
BRY4100MI7W	\$994.00					480VAC 3Ø	50	BRY4100P7W	PDF
BRY4100MI5W	\$994.00					600V AC 3Ø	50	BRY4100P5W	PDF
BRY5100MI9W	\$994.00		4P / 5W			120/208 VAC 3ØY	20	BRY5100P9W	PDF

NOTE: Mating plugs sold separately.

* Not currently offered by AutomationDirect

Bryant Pin and Sleeve Mechanical Interlocks

Bryant Unfused Pin and Sleeve Mechanical Interlock Specifications			
Typical Specifications			
Electrical Type		3 Pole + Ground	
Rating		20, 30, 60, and 100A 480/600V AC, 3 Phase	
Configuration		IEC 60309-2, UL1686 C2, Clock position 7	
Enclosure Type		Indoor and Outdoor - 4X (Watertight, Washdown); Indoor - 12 (Dust-tight, Falling Dirt and Noncorrosive Liquids)	
Ingress Protection		IP67 Suitability	
Enclosure Material		Non-metallic, enclosure suitable for metallic conduit	
Certification / UL Listings		UL Listed, CSA Certified File 033196_C_00 UL file # E70402 and accessories E36355 displayed as Hubbell HBL Series Listings: UL Listed Standard ANSI/UL 60947-1, "Low-Voltage Switchgear and Controlgear - Part 1: General Rules," and ANSI/UL 60947-4-1, "Low-Voltage Switchgear and Controlgear - Part 4-1: Contactors and Motor-Starters - Electromechanical Contactors and Motor-Starters." CE	
Materials			
Base	PBT	Top	PBT
Handle	PBT	Conduit Hub	Zinc
Enclosure Gasket	Neoprene	Shaft	PBT
Shaft Seal	Neoprene	Ground Plate	Galvanized Steel
Enclosure Screws	Stainless Steel 300 Series	Enclosure Inserts	Brass
Hinge Pins	Nickel Plated Brass	Hinge Spring	Stainless Steel 300 Series
Performance			
Dielectric Voltage		Withstands 3000VAC Min.	
Max. Working Voltage		600V AC RMS	
Current Interrupting		Certified for current interrupting at full rated current and voltage	
Short Circuit Withstand Rating		Suitable for use on a circuit capable of delivering not more than 10,000 RMS symmetrical amperes at the voltage rating of the receptacle. 20A and 30A models: Suitable for use on a circuit capable of delivering not more than 65,000 RMS symmetrical amperes, 600V when protected by class "J" fuses rated 30A.	
Operations		Mechanical 10,000 cycles, electrical 6,000 cycles	
Mechanical			
Impact Resistance		In accordance with UL 746C	
Terminal Identification		In accordance with UL, CSA and international conventions	
Product Identification		Identification and ratings are part of the external label and molded into the receptacle mount	
Mounting		External adjustable feet	
Environmental			
Moisture Resistance		Indoor and Outdoor - 4X (Watertight, Washdown) Indoor - 12 (Dust-tight, Falling Dirt and Noncorrosive Liquids)	
Ingress Protection		IP69K Suitability	
Flammability		UL94-5VA and V-0 Classification	
Operating Temperature		Max. Continuous +75°C [167°F]; Min. Continuous -40°C [-40°F]	
UV Resistance		All materials are UV stabilized	


Note: This device provides ON/OFF switched control of a plug connected load and includes an interlocking feature to prevent the plug from being disconnected while the receptacle is energized. The switch cannot be turned "ON" until the plug is inserted properly, and the plug cannot be removed until the switch is turned "OFF."

Bryant Pin and Sleeve Mechanical Interlocks

Horsepower Ratings				
Amps	AC Voltage Rating	Horsepower	Mechanical Interlock	Mating Plug
20	3Ø 240VAC	5	BRY420MI9W	BRY420P9W
	3Ø 480VAC	10	BRY420MI7W	BRY420P7W
30	120VAC	2	BRY330MI4W	BRY330P4W
	240VAC	3 (208-240V AC)	BRY330MI6W	BRY330P6W
	480VAC	7.5	BRY330MI7W	BRY330P7W *
	120/240 VAC	3 (208-240V AC)	BRY430MI12W	BRY430P12W *
	3Ø 600VAC	20	BRY430MI5W	BRY430P5W
	3Ø 480VAC	15	BRY430MI7W	BRY430P7W
	3Ø 250VAC	7.5	BRY430MI9W	BRY430P9W
	3ØY 277/480 VAC	15	BRY530MI7W	BRY530P7W
60	240VAC	7.5 (208-240 VAC)	BRY360MI6W	BRY360P6W
	120/240 VAC	7.5 (208-240V AC)	BRY460MI12W	BRY460P12W *
	3Ø 600VAC	40	BRY460MI5W	BRY460P5W
	3Ø 480VAC	30	BRY460MI7W	BRY460P7W
	3Ø 250VAC	15	BRY460MI9W	BRY460P9W
	3ØY 277/480 VAC	30	BRY560MI7W	BRY560P7W
	3ØY 120/208 VAC	15	BRY560MI9W	BRY560P9W
100	120/240 VAC	15	BRY4100MI12W	BRY4100P12W *
	3Ø 600VAC	50	BRY4100MI5W	BRY4100P5W
	3Ø 480VAC	50	BRY4100MI7W	BRY4100P7W
	3Ø 250VAC	25 (208-240 VAC)	BRY4100MI9W	BRY4100P9W
	3ØY 120/208 VAC	20	BRY5100MI9W	BRY5100P9W

* Not currently offered by AutomationDirect

Ground Connections



Bryant Pin and Sleeve Mechanical Interlocks Accessories

Bryant Unfused Pin and Sleeve Mechanical Interlock Accessories Selection Guide

Part Number	Price	Description	Drawing
<u>BRYAUX1</u>	\$31.00	Field installable auxiliary contact, side mount, (1) N.O./ (1) N.C. contact, 10A @ 600 VAC/2.5A @ 600 VDC, screw terminal. For use with Bryant pin and sleeve mechanical interlocks 20-100A. Break after main break. Hubbell part number HBLAC1	<u>PDF</u>
<u>BRYAUX2</u>	\$31.00	Field installable auxiliary contact, side mount, (1) N.O. contact, 10A @ 600 VAC/2.5A @ 600 VDC, screw terminal. For use with Bryant pin and sleeve mechanical interlocks 20-100A. Break before main break. Hubbell part number HBLAC2. For VFD applications.	<u>PDF</u>
<u>BRYMIRS20</u>	\$64.00	Disconnect switch, replacement, 3-pole, 20A. For use with 20A Bryant pin and sleeve mechanical interlocks. Hubbell part number HBLDS3RS.	<u>PDF</u>
<u>BRYMIRS30</u>	\$145.00	Disconnect switch, replacement, 3-pole, 30A. For use with 30A Bryant pin and sleeve mechanical interlocks. Hubbell part number HBL30MIRS.	<u>PDF</u>
<u>BRYMIRS60100</u>	\$210.00	Disconnect switch, replacement, 3-pole, 100A. For use with 60 & 100A Bryant pin and sleeve mechanical interlocks. Hubbell part number HBLDS60100RS.	<u>PDF</u>
<u>BRYRPLCFT</u>	\$19.00	Mounting feet, replacement. Package of 10 feet and 10 screws. For use with Bryant pin and sleeve mechanical interlocks 20-100A. Hardware included.	<u>PDF</u>



[BRYAUX1](#)



[BRYAUX2](#)



[BRYRPLCFT](#)



[BRYMIRS20](#)



[BRYMIRS30](#)



[BRYMIRS60100](#)