

Overview

WAGO Pro2 compact switched-mode power supplies provide a wide range of uses. These power supplies can be mounted on a 35mm DIN rail and can be configured directly via buttons on the device's face, using the WAGO USB configuration cable to connect to the integrated communication interface, or using one of the WAGO Pro2 communication modules. In addition, the WAGO Interface Configuration software (free download) can be used to record and evaluate various output parameters.

The pluggable connection technology uses WAGO CAGE CLAMP® connectors, which allow pre-wiring for quicker installations as well as quicker and easier product replacement.

For configuration, data collection, and read-out of status information, the Pro2 Power Supply can be connected to a dedicated WAGO Pro2 communication module at any time, allowing selection of the desired protocol for coupling to the automation and control system.

The LED bar chart on the front reliably indicates the current output power, as well as overloads/load reserves. Furthermore, the LEDs indicate the selected operating mode and, when needed, warnings and errors.

Features

- Power supply with TopBoost, PowerBoost and configurable overload behavior
- Configurable digital signal input and output, optical status indication, function keys
- Communication interface for configuration and monitoring
- Suitable for both parallel and series operation
- Snap on communication modules (sold separately)
- Free WAGO configuration software (download only)
- 2-year warranty

Switching Power Supplies										
Part Number	Price	Output Voltage (V _{nom})	Output Current (I _{max})	Output Power (P _{max})	Weight grams [lb]	Drawing Link				
Single-Phase I	Single-Phase Input									
2787-2134	\$205.00		10A	120W	650 [1.43]	PDF				
<u>2787-2135</u>	\$343.00	IZ VDC	15A	180W	1000 [2.20]	<u>PDF</u>				
2787-2144	\$210.00		5A	120W	700 [1.54]	PDF				
2787-2146	\$294.00		10A	240W	1000 [2.20]	PDF				
<u>2787-2147</u>	\$425.00	24 VDC	20A	480W	1450 [3.19]	<u>PDF</u>				
2787-2448	\$668.00		40A	960W	1950 [4.29]	PDF				
2787-2154	\$322.00		2.5 A	120W	650 [1.43]	PDF				
<u>2787-2157</u>	\$520.00	40 VDC	10A	480W	1450 [3.19]	<u>PDF</u>				
Three-Phase II	ıput									
2787-2344	\$294.00		5A	120W	650 [1.43]	PDF				
2787-2346	\$405.00		10A	240W	1000 [2.20]	<u>PDF</u>				
2787-2347	\$544.00	24 VDC	20A	480W	1450 [3.19]	PDF				
2787-2348	\$781.00		40A	960W	1980 [4.29]	PDF				
2787-2357	\$567.00		10A	480W	1400 [3.08]	PDF				
2787-2358	\$878.00	48 VDC	20A	960W	1980 [4.29]	PDF				

		ס [ד.בט]
	PDF) [4 29]
2787-2348	PDF) [3.08]
1	PDF) [4.29]

	Switching Power Supplies Accessory					
Part Number	Price	Description				
<u>750-923</u>	\$45.00	WAGO cable, 8.2ft/2.5m cable length. For use with WAGO Pro2 power supplies.				











Input Specifications																		
Part Number	Nominal Input Voltage [V _{nom}]	Voltage Range	Frequency Range	Input Current [Typ. @ full load]	Inrush Current Limitation @+25°C	Max Power Dissipation	Efficiency [Typ.]	Circuit Breaker [Minimum]										
Single-Phase																		
<u>2787-2134</u>		90–264 VAC 130–373 VDC		≤ 1.3 A @ 110VAC 0.6 A @ 230VAC	≤ 9.6 A [after 1ms]	≤ 0.8 W [Standby] ≤ 1.6 W [No load] ≤ 10W [230 VAC; Nominal load]	93.8% @ 110VAC											
<u>2787-2135</u>		90–264 VAC 130–240 VDC		2.0 A @ 110VAC 0.88 A @ 230 VAC	≤ 11.4 A [after 1ms]	≤ 0.8 W [Standby] ≤ 2.3 W [No load] ≤ 14W [230 VAC; Nominal load]	95.3% @ 110VAC											
<u>2787-2144</u>	100-240 VAC			≤ 1A @ 240VAC ≤ 1.8 A @ 100VAC	≤ 9A [after 1ms]	≤ 1W [Standby] ≤ 2W [No load] ≤ 10W [230 VAC; Nominal load]	93% @ 110VAC 93.8% @ 230VAC											
<u>2787-2146</u>	146	90–264 VAC 130–373 VDC	E0 60 LI-	≤ 1.2 A @ 240VAC ≤ 2.7 A @ 100VAC	≤ 11A [after 1ms]	≤ 1W [Standby] ≤ 2.2 W [No load] ≤ 12W [230 VAC; Nominal load]	93.5% @ 110VAC 95.2% @ 230VAC	164										
<u>2787-2147</u>													50-60 Hz	≤ 2.2 A @ 240VAC ≤ 5.9 A @ 100VAC	≤ 12A [after 1ms]	≤ 1.3 W [Standby] ≤ 2.6 W [No load] ≤ 24W [230 VAC; Nominal load]	93.9% @ 110VAC 95.4% @ 230VAC	IOA
<u>2787-2448</u>	200-240 VAC	0 VAC 180–264 VAC 255–373 VDC 0 VAC 90–264 VAC 130–240 VDC		≤ 4.3 A @ 240VAC ≤ 5.1 A @ 200VAC	≤ 10A [after 1ms]	≤ 1.5 W [Standby]; ≤ 2.4 W [No load]; ≤ 40W [230 VAC; Nominal load]	96% @ 230VAC											
<u>2787-2154</u>	400.040.1/4.0			≤ 1.3 A @ 100VAC	11A [after 1ms]	≤ 0.8 W [Standby] ≤ 1.7 W [No load] ≤ 9W [230 VAC; Nominal load]	95.3% @ 110VAC											
<u>2787-2157</u>	100-240 VAC		130–240 VDC	130–240 VDC	130–240 VDC	130–240 VDC	130–240 VDC	130–240 VDC	130–240 VDC	130–240 VDC	130–240 VDC	130-240 VDC	130-240 VDC		5.9 A @ 100VAC 2.2 A @ 230VAC	≤ 12A [after 1ms]	≤ 1.3 W [Standby]; ≤ 2.6 W [No load]; ≤ 24W [230 VAC; Nominal load]	95.3% @ 110VAC
Three-Phase																		
<u>2787-2344</u>		240 550.140		0.4 A @ 400VAC	≤ 15A [after 1ms]	≤ 3W [Standby] ≤ 3W [No load] ≤ 18W [400 VAC; Nominal load]	92.5% @ 400VAC											
<u>2787-2346</u>		340–550 VAC		0.63 A @ 400VAC	1A [after 1ms]	≤ 3W [Standby] ≤ 3W [No load] ≤ 18W [400 VAC; Nominal load]	94.1% @ 400VAC											
<u>2787-2347</u>		340–550 VAC		≤ 0.8 A @ 400VAC	≤ 15A	\leq 3.6 W [Standby]	95.9% @ 400VAC	164										
<u>2787-2348</u>	400-500 VAC	480–780 VDC	50-60 HZ	≤ 1.7 A @ 400VAC	[after 1ms]	\leq 4.4 W [No load] \leq 21W [400 VAC; Nominal load]	96.3% @ 400VAC	IbA										
<u>2787-2357</u>		240 550 \/AC		0.8 A @ 400VAC	1A [after 1ms]	≤ 3.6 W [Standby] ≤ 4.4 W [No load] ≤ 21W [400 VAC; Nominal load]	95% @ 400VAC											
<u>2787-2358</u>		340–550 VAC		1.6 A @ 400VAC	1A [after 1ms]	≤ 3.6 W [Standby] ≤ 4.4 W [No load] ≤ 21W [400 VAC; Nominal load]	96% @ 400VAC											



Output Specifications									
Part Number	Output Voltage	Output Voltage Adj. Range	Output Current (Max.)	Power Boost (5s)	Top Boost (15ms)	Switch on Delay	Line Regulation	Load Regulation	MTBF (@ 25°C) [per IEC 61709]
Single-Phase	Single-Phase								
2787-2134	10.100	10 11 100	10A	15A	60A	< 2.2 sec	< 0.02 %	< 2.0 %	> 1,200,000 h
<u>2787-2135</u>	12 VDC	12-14 VDC	15A	22.5 A	90A	< 1.8 sec	< 0.02 %	< 2.5 %	> 1,200,000 h
2787-2144			5A	7.5 A	30A	< 2.2 sec	< 0.02 %	< 2.0 %	> 1,000,000 h
2787-2146	24 VDC	24–28 VDC	10A	15A	60A	< 1.8 sec	< 0.02 %	< 2.0 %	> 1,200,000 h
<u>2787-2147</u>	24 VDC		20A	30A	120A	< 1.5 sec	< 0.02 %	< 2.0 %	> 800,000 h
2787-2448			40A	60A	200A	< 1.5 sec	< 0.1 %	< 2.6 %	> 900,000 h
2787-2154	49.1/00	C 48–56 VDC	2.5 A	3.75 A	15A	< 2.2 sec	< 0.02 %	< 1.0 %	> 900,000 h
2787-2157	48 VDC		10A	15A	60A	< 1.5 sec	< 0.02 %	< 1.0 %	> 800,000 h
Three-Phase									
2787-2344			5A	7.5 A	30A	1.5 sec	< 0.05 %	< 2.0 %	1,400,000 h
2787-2346			10A	15A	60A	1.5 sec	< 2.0 %	< 2.5 %	> 1,000,000 h
2787-2347		24-20 VDC	20A	30A	120A	< 1.4 sec	< 0.02 %	< 2.0 %	> 800,000 h
2787-2348			40A	60A	200A	< 1.5 sec	< 0.01 %	< 0.01 %	> 800,000 h
2787-2357		48 56 VDC	10A	15A	60A	1.6 sec	< 0.02 %	< 1.0 %	900,000 h
2787-2358	40 VDC	40-30 VDC	20A	30A	100A	1.6 sec	< 0.04 %	< 2.0 %	800,000 h

General Specifications					
Temperature	Operating [ambient] -25 to 70°C [-13 to 158°F] Storage [non-operating] -40 to 85°C [-40 to 185°F]				
Humidity	5 to 96 % [no condensation permissible]				
Overload Behavior ¹	Constant Current [Factory Default], Constant Current with Latching Mode, Hiccup, Electronic Circuit Breaker, Latching Shutdown on Thermal Overload, Power Boost, Top Boost				
Status Indicators	Optical status indication [DC OK; load; warning and error states] Digital signal input and output [DI/DO]				
Overvoltage Protection	Yes				
Vibration	IEC 60068-2-6 [5 to 150Hz / 1g]				
Shock	IEC 60068-2-27 [15g / 11ms]				
Enclosure Rating	IP20				
Mounting	35mm DIN rail				
Connection	Cage Clamp®				
Housing Material	Metal (enclosed)				
Agency Approval	cULus File E255817, CE				

¹All functions are described in detail in the user manual.



	Additional Data								
Port Number	Solid Wire Size								
Part Number	Input	Output	Strip Length						
<u>2787-2134</u>									
2787-2135		0.08 - 2.5 mm ²	Input/Output						
2787-2144		[28 -12 AWG]	8-9mm [0.31 - 0.35 in]						
<u>2787-2146</u>									
<u>2787-2147</u>	0.08 - 2.5 mm² [28 -12 AWG]	0.50 - 10 mm²	Input 8-9mm [0.31 - 0.35 in]						
<u>2787-2448</u>		[20 -12 AWG]	Output 13-15mm [0.51 - 0.59 in]						
<u>2787-2154</u>		0.08 - 2.5 mm² [28 -12 AWG]	Input/Output 8-9mm [0.31 - 0.35 in]						
<u>2787-2157</u>		0.50 - 10 mm² [20 -12 AWG]	Input 8-9mm [0.31 - 0.35 in] Output 13-15mm [0.51 - 0.59 in]						
<u>2787-2344</u>		0.08 - 2.5 mm ²	Input/Output 8-9mm						
<u>2787-2346</u>		28 - 12 AVVGJ	[0.31 - 0.35 in]						
<u>2787-2347</u>									
<u>2787-2348</u>		0.50 - 10 mm²	Input 8-9mm [0.31 - 0.35 in]						
<u>2787-2357</u>		[20 -12 AWG]	Output 13-15mm [0.51 - 0.59 in]						
<u>2787-2358</u>									



Digital I/O Functions

Digital I/O Functions							
Section	Operation	Description					
	Power supply standby on/off	If this checkbox is selected, the product can be switched on and off via the digital input.					
Digital Input	Inversion DI	If this checkbox is selected, the digital input is inverted.					
	Function triggered by low/high transition	If this checkbox is selected, the digital input is activated in the event of an edge change from 0 to 1.					
	Function triggered by high/low transition	If this checkbox is selected, the digital input is activated in the event of an edge change from 1 to 0.					
	DC OK	If this checkbox is selected, the digital output is set if the DC output voltage is OK.					
	Load current warning level exceeded	If this checkbox is selected, the digital output is set if the overload warning threshold is exceeded.					
	Electronic circuit breaker tripped	If this checkbox is selected, the digital output is set if the electronic circuit breaker has tripped.					
Digital Output	Power supply switched off (Latched)	If this checkbox is selected, the digital output is set if latching shutdown occurs.					
	Digital output via process data/communication	If this checkbox is selected, the digital output can be controlled via the process data.					
	Digital output on	If this checkbox is selected, the digital output is switched on.					
	Inversion DO	If this checkbox is selected, the digital output is inverted.					
Warning	Overload limit active	If this checkbox is selected, warning is triggered if the overload warning threshold is exceeded.					
Thresholds (Software	Warning threshold	Here you can enter the value for current (unit: mA) at or above which a warning message is generated.					
Config.)	Operating hour counter warning limit	You can enter after how many operating hours (unit: h) after which a warning message is generated.					

Note: Digital I/O function checkboxes are available in the WAGO configuration software.

Operation via Buttons

Using the + and - buttons on the front of the product, you can make the following settings:

Operation via Buttons							
Button [+] Button [–] Function		Function					
Switch product on or off							
Hold down simultaneously for 3 seconds The product is switched on or off.							
Set output voltage							
Press once	-	The output voltage increases in steps.					
Press and hold	_	The output voltage increases continuously.					
-	Press once	The output voltage is reduced in steps.					
-	Press and hold	The output voltage is reduced continuously.					
Reset product for factory settings							
Hold down simultaneously for 10 seconds		The product is reset to the factory settings.					

During ongoing operation, you can set the output voltage and reset the product to factory settings. These settings can be saved and then remain available when the product is switched off and back on.



	Safety and Agency Approvals								
Specification	Standard	Docume	nt Number						
Harmonic Limits	Harmonic Current Limits	EN 61000-3-2, Class /	A for limited output power						
	Hazardous Locations	UL Standard 1212	01 [File No. E198726]						
	Industrial control equipment	UL 61010-2-201	[File No. E255817]						
Safety Standards	Electrical equipment of machines	IEC60204-1 [over	voltage category III]						
	Electronic equipment for power installation	IEC/EN 6247	7-1 / IEC62103						
	Safety, Transient surge voltage protection	VAR	ISTOR						
Safety Approvals	CB-Report per IEC 60950	IEC 60950-1, IEC 61010-1, IEC 61010-2-201							
Safety Class	Degree of electrical protection Class1	e of electrical protection Class1 Class I with GND connection							
CE	In conformance	with EMC directive 2014/30/EU and low voltage direction	rective 2014/35/EU						
RoHS Compliant		RoHS Directive [EU] 2015/863 Compliant [EN 50581]							
Electromagnetic Compatibility (EMC), Emissions	EMC, Emissions	EN55032, EN55011, EN61000-3-2 Class A, EN61000-3-3, EN61000-6-3							
	EMC, Immunity	EN 55024, EN 61000-6-2 [EN61000-4-2, 3, 4, 5, 6, 8, 11, 12]							
	Electrostatic Discharge [ESD]	IEC 61000-4-2 Level 4 Criteria A Air Discharge: 15kV; Contact Discharge: 8kV							
Electromagnetic	Radiated RF field immunity [80-1000 MHz]	IEC / EN 61000-4-3: 120W&240W: 80MHz-1GHz, 10V/M, 80% modulation [1kHz] 1.4GHz-2GHz, 3V/M, 80% modulation [1KHz] 2GHz-2.7GHz, 1V/M, 80% modulation [1KHz]	IEC / EN 61000-4-3: 480W: 80MHz-1GHz, 10V/ M, 80% modulation [1kHz] 1.4GHz-2GHz, 10V/M, 80% modulation [1KHz] 2GHz-2.7GHz, 10V/M, 80% modulation [1KHz]						
Compatibility (EMC),	Electrical fast transient / burst immunity	IEC / EN 61000-4-4	Level 4 Criteria A 4kV						
	Surge immunity	IEC / EN 61000-4-5 Level 4 Criteria A C	common Mode: 4kV Differential Mode: 2kV						
	Immunity to conducted RF disturbances [0.15 to 80 MHz]	IEC / EN 61000-4-6 Level 3 Criteria A 150kHz-80MHz, 10Vrms							
	Power frequency field immunity	IEC / EN 610	100-4-8 30 A / m						
	Voltage dips	IEC / EN 61000-4-11[70% UN Crit. B/40%/100% UN Crit. C]							
Pollution Degree		2	2						

To obtain the most current agency approval information, see the Agency Approval Compliance & Certifications Checklist section on the specific part number's web page.

Communication Modules Pro2 Series

Overview

WAGO Pro2 communication modules easily snap into place as an add-on to WAGO Pro2 power supplies. These modules are available for various communication protocols with their respective communication ports, allowing connectivity to PLCs for programming and monitoring. Connectivity to modules also provides accessibility to features and data from the power supplies.

Features

- Snaps on to a WAGO Pro2 Power Supply
- Modbus RTU, EtherNet/IP, Modbus TCP/IP UDP/IP or IO-Link v1.1
- 2-year warranty











<u>2789-9015</u>

2789-9023

2789-9052

2789-9080

Communication Modules										
Part Number	Price	Port Protocol	Number of Ports	Communication Port	Port Speed	Requires	Drawing Link			
<u>2789-9015</u> *	\$76.00	Modbus RTU	2	(2) RS-485 (RJ45)	4.8 to 115.2k baud	WAGO Pro2 power supply and terminating resistor <u>2789-9915</u>	<u>PDF</u>			
<u>2789-9023</u>	\$108.00	EtherNet/IP	2	(2) Ethernet 10/100Base-T (RJ45)	10/100 Mbps auto-detect	WAGO Pro2 power supply	<u>PDF</u>			
<u>2789-9052</u> *	\$108.00	Modbus TCP/IP UDP/IP	2	(2) Ethernet 10/100Base-T (RJ45)	10/100 Mbps auto-detect	WAGO Pro2 power supply	<u>PDF</u>			
<u>2789-9080</u>	\$76.00	IO-Link Class A Device	1	(1) 3-position removable terminal	230.4k baud IO-Link COM3	WAGO Pro2 power supply	PDF			

* Firmware on the Pro2 Power Supply must be version 01.04 or higher.

Terminating Resistor For Use With 2789-9015

Terminating Resistor								
Part Number	Price Resistance		Connection	Weight	For Use With	Drawing Link		
<u>2789-9915</u>	\$42.00	120Ω	RJ45	35g [1.23 oz]	<u>2789-9015</u>	PDF		



8-Pin RJ45



www.automationdirect.com

8-Pin RJ45 Pin Out						
Pin	Description					
4	Contact "A" (D+/D1)					
5	Contact "B" (D-/D0)					
8	Contact "GND"					

For the latest prices, please check AutomationDirect.com.



MAGE Communication Modules Pro2 Series

		Specifications			
Part Number	<u>2789-9015</u>	<u>2789-9023</u>	<u>2789-9052</u>	<u>2789-9080</u>	
Communication	Modbus RTU (RS-485)	EtherNet/IP - Protocols: HTTP(S), BootP, DHCP, SNTP, MQTT	Modbus (TCP, UDP) Ethernet Protocols: HTTP(S), BootP, DHCP, SNTP	IO-Link v1.1	
Nominal Input Voltage		5VDC (SELV)		24VDC (SELV; via IO-Link Master)	
Input Voltage Range	4.5 to 5.5 VDC (SELV)	_		18 to 30VDC (SELV; via IO-Link Master)	
Input Current	≤ 0.04 A	≤ 250mA	210mA	≤ 15mA	
Power Loss (max.)	0.22 W	—	1.1 W	_	
Operating Temperature	-25 to 70°C [-13 to 158°F]	-40 to 55°C [-	40 to 131°F]	-25 to 70°C [-13 to 158°F]	
Storage Temperature	-40 to 85°C [-40 to 185°F]	-40 to 85°C [-	40 to 185°F]	-40 to 85°C [-40 to 185°F]	
Relative Humidity		5 to 95% (no condensation)		5 to 96% (no condensation)	
LED Indicator	1 LED PWR (Green) 1 LED RxD (Yellow) 1 LED TxD (Yellow)	1 ERR LE 1 COM OK L 1 LED LNK/A 1 LED SPEEI	1 ERR LED (Red) 1 COM OK LED (Green) 1 LED LNK/ACTx (Green) 1 LED SPEEDx (Orange)		
Baud Rate	4.8 to 115.2 kBd	10/100 Mbps	auto-detect	230.4k baud	
Number of Devices (max.)	247	—	—	_	
Test Voltage	2 kVAC; 50Hz; 1 min	0.775 kVAC; 50Hz; 1 min	0.775 kVAC; 50Hz; 1 min	_	
Test Voltage (input/output/shield)	1 kVAC; 50Hz; 1 min	_	-	_	
Protection Class					
Degree of Protection		IP20 per E	N 60529		
Pollution Degree		2 (according to IE	EC/EN 60664-1)		
Connector	(2) RJ45	(2) Ethernet 10/100Base-T (RJ45)		Push-in CAGE CLAMP ® Solid /Fine conductor 0.08 to 2.5 mm² / 28 to12 AWG Strip length: 8 to 9 mm [0.31 to 0.35 in] Cable length max: 20m [65.61 ft] (IO-Link)	
Transmission Medium	Twisted pair, shielded copper cable	Ethernet: Twisted pair S-UTP; 100Ω; Cat. 5			
Mounting		Only vertical on a WAG	O Pro2 Power Supply		
Weight	35g [1.23 oz]	45g [1.58 oz]	45g [1.58 oz]	35g [1.23 oz]	
Agency Approval		CE, UL File E175199,	UL Haz File E198726		

To obtain the most current agency approval information, see the Agency Approval Compliance & Certifications Checklist section on the specific part number's web page.



Communication Modules Pro2 Series

Mounting/Removal



- Remove the cover for the communication interface from the WAGO Pro2 Power Supply you are using.
- Insert the bottom latches of the communication module into the bottom mounting slots of the WAGO Pro2 Power Supply [A].
- Slide the communication module toward the communication interface [B] until the top latches catch in the top mounting slots.
- Check that the communication module has correctly latched in position.



- Press in on the top locking tab of the communication module [C].
- Swing the device out to remove it from the WAGO Power Supply Pro2 [D].





Overview

The WAGO Eco2 series is a great combination of performance and value when enhanced features are not required. The push-in connection and WAGO levers make connection with the Eco2 series quick, easy, and tool-free, saving time on wiring the power supply units. With a reduced overall width, the Eco2 saves space. With a high efficiency over 88% and the associated reduction in heat generated, the metal housing models are sustainable and durable. The built-in DC OK relay contact indicates whether the output voltage is in the nominal range. WAGO's impressive Eco2 Power Supply is an economical, reliable, robust power supply in control cabinets for 24 VDC mechanical engineering applications.

Features

- Optical status indication
- Suitable for either parallel or series operation
- Push-in Cage $\mathsf{Clamp}\,^{\textcircled{B}}$ technology and tool-free lever operation
- Electrically isolated output voltage (SELV/PELV) per EN 61010/UL 61010
- Rated for UL Hazardous Locations
- 2-year warranty





2687-2142

<u>2687-2144</u>



Switching Power Supplies									
Part Number	Price	Output Voltage Range (Adjustable)	Nominal Input	Output (Adjustable)	Efficiency	MTBF (@ 25°C)	Circuit Breaker	Weight grams [oz]	Drawing Link
Single Phase Input									
<u>2687-2142</u>	\$68.00	22-29 VDC	100-240 VAC	24 VDC @ 1.25A/30W	88% @110 VAC			160 [5.64]	<u>PDF</u>
<u>2687-2143</u>	\$93.00	22-29 VDC	120/240 VAC	24 VDC @ 2.5A/60W	90.5% @115 VAC	> 1,000,000h	C Curve	250 [8.81]	<u>PDF</u>
<u>2687-2144</u>	\$118.00	23-28 VDC	100-240 VAC	24 VDC @ 5A/120W	90% @110 VAC	[per IEC 61709]	15A	620 [21.86]	<u>PDF</u>
<u>2687-2146</u>	\$198.00	23-28 VDC	100-240 VAC	24 VDC @ 10A/240W	93% @110 VAC			800 [28.21]	PDF

Wiring Diagrams







Switching Power Supplies Eco2 Series

General Specifications								
Part Number		2687-2142	<u> 2687-2143</u>	2687-2144	<u> 2687-2146</u>			
Voltage Range			90-26	4 VAC				
Frequency Range			47-6	3 Hz				
Input Current		≤ 0.3A @ 230 VAC ≤ 0.6A @ 100 VAC	≤ 0.5A @ 230 VAC ≤ 1.1A @100 VAC	≤ 0.8A @ 230 VAC ≤ 1.5A @ 100 VAC	≤ 1.1A @ 230 VAC ≤ 2.7A @100 VAC			
Inrush Current		≤ 10A [after 1ms]	≤ 20A [after 1ms]	≤ 20A [after 1ms]	≤ 25A [after 1ms]			
Mains Failure Hold-Up	Time	≥ 120ms (230 VAC) ≥ 15ms (110 VAC)	≥ 130ms (230 VAC) ≥ 3ms (110 VAC)	≥ 20ms (230 VAC)	≥ 25ms (230 VAC)			
Residual Ripple		≤ 30mV (peak-to-peak @ 230 VAC)	≤ 20mV (peak-to-peak @ 230 VAC)	≤ 75mV (pe	eak-to-peak)			
Overload Behavior		Constant power up to 125%; shutdown and automatic restart in the event of a short circuit	Constant power up to 130 %; shutdown and automatic restart in the event of a short circuit	Constant power up to 125%; shutdown and automatic restart in the event of a short circuit	Constant current up to 105 to 110%; shutdown and automatic restart in the event of a short circuit			
	Primary - Secondary		3510 VAC					
Isolation	Primary - Ground	_		2200 VAC				
	Secondary - Ground	_		DC, 0.5 kV				
	Secondary Signal	-	-	DC, 0.5 kV				
Short-circuit Protection	า	Yes						
Parallel Operation		Yes						
Status Indicators		1 x LED DC	OK (green)	Optical status indication (DC OK) Digital signal output (DO)				
Vibration (according to	IEC 60068-2-6)	5Hz ≤ f ≤ 8.4 Hz: 3.5 mm, 8.4 Hz ≤ f ≤ 150Hz: 1g						
Shock (according to IE	C 60068-2-27)	15g, 11ms, 3 shocks per axis (18 shocks in total)						
Temperature		Operating: -25 to 70°C [-13 to 158°F] Storage: -40 to 85°C [-40 to 185°F]						
Humidity		5 to 96% [no condensation permissible]						
Protection Rating		IP20						
Mounting		35mm DIN rail						
Housing Material		Plastic Metal						
Connection		Push-in Cage Clamp®						
Solid or Fine Conducto	or		0.2 to 4mm ²	/ 24-12AWG				
Ferrule Size			0.25 to 2	2.5 mm²				
Agency Approval			CE, UKCA, cULus File E255	817, UL Hazardous E198726				

To obtain the most current agency approval information, see the Agency Approval Compliance & Certifications Checklist section on the specific part number's web page.

For the latest prices, please check AutomationDirect.com.

1-800-633-0405



Switching Power Supplies 1-Phase CPS ECO Series



Overview

LUTZE ECO series power supplies were developed with technical innovations in mind. The Compact economy series power supplies are efficiently sized and offer up to 91% power conversion efficiency. Adjustable voltage outputs and DC Ok contacts are standard.

Features

- Compact footprint
- Aluminum housing
- 35mm DIN rail mount
- IP20
- 5 year warranty



Switching Power Supplies 1-Phase								
Part Number	Price	Output Voltage	Output Current	Output Power	Input Voltage	Power Boost	Dimensions (W x H x D)	Drawing Link
<u>CPSB1-120-24E</u>	\$97.00		5A	120W	120/240 VAC	140% for 5s	40 x 115 x 110mm [1.57 x 4.52 x 4.33 in]	<u>PDF</u>
<u>CPSB1-240-24E</u>	\$150.00	24VDC	10A	240W		135% for 30s	63 x 140 x 139mm [2.48 x 5.51 x 5.47 in]	PDF
<u>CPSB1-480-24E</u> *	\$275.00		20A	480W	200/240 VAC	140% for 5s	73 x 140 x 149mm [2.87 x 5.51 x 5.86 in]	<u>PDF</u>

* Requires an external fuse.

1-Phase Input Specifications						
Part Number	<u>CPSB1-120-24E</u>	<u>CPSB1-240-24E</u>	<u>CPSB1-480-24E</u>			
Operation Voltage Range	85–264 VAC 110–345 VDC	90–132 VAC 187–264 VAC 270–345 VDC	187–264 VAC 250–375 VDC			
Frequency Range	47-63Hz					
Rated Current	2.1 A @ 120VAC 1.2 A @ 240VAC	4A @ 120VAC 2A @ 240VAC	2.9 A @ 200VAC 2.5 A @ 240 VAC			
Inrush Current	\leq 30A / 0.72 A ² s	< 40A	\leq 29A / 0.61 A ² s			
Power Factor Correction	> 0.6	> 0.6	> 0.90 enabled			
Recommended Circuit Breaker	C-curve 6A	C-curve 10A	C-curve 6A or D-curve 4A			

1-Phase Output Specifications							
Part Number	<u>CPSB1-120-24E</u>	CPSB1-240-24E	<u>CPSB1-480-24E</u>				
Overload Limit In Constant Current Mode	-	-	50A				
Max. Output Current	7A, 5s	13.5 A, 30s	28A 5s @ Hiccup mode				
Power Dissipation	< 18W	< 35W	< 48W				
Setting Range	23-28 VDC	23-27.5 VDC	23-28 VDC				
Load Regulation	< 1%	< 1%	≤ 1%				
Ripple And Noise	60mV	< 100mV pp	≤ 50mV rms				
Hold-Up Time	> 20ms @ 120VAC 50ms @ 230VAC	> 60ms @ 120VAC 70ms @ 230VAC	≥ 50ms @ 230VAC				
Parallel / Redundant Mode		Yes via external decoupling diode					
Efficiency (Typical)	> 87% @ 120VAC > 87% @ 120VAC > 91% @ 24						
Short-Circuit	Hiccup mode						
MTBF	_	_	500,000 h @ 25°C ambient full load				



Switching Power Supplies 1-Phase CPS Ultra Series

CPS2B1-240-24

Overview

The Compact Ultra series power supplies are approximately 50% smaller than standard industrial power supplies. These power supplies provide maximum efficiency to 93% in housings even smaller than the ECO line.

Features

- Compact footprint
- Aluminum housing
- 35mm DIN rail mount
- IP20 rated
- Power Boost 150% for 5s
- 5 year warranty



Switching Power Supplies 1-Phase								
Part Number	Price	Output Voltage	Output Current	Output Power	Input Voltage	Power Boost	Dimensions (W x H x D)	Drawing Link
<u>CPS2B1-120-24</u>	\$155.00		5A	120W			35 x 103 x 126mm [1.37 x 4.05 x 4.96 in]	PDF
<u>CPS2B1-240-24</u>	\$210.00	24VDC	10A	240W	120/240 VAC	150% for 5s	40 x 115 x 133mm [1.57 x 4.52 x 5.23 in]	PDF
<u>CPS2B1-480-24</u>	\$335.00		20A	480W			56 x 140 x 139mm [2.20 x 5.51 x 5.57 in]	PDF

1-Phase Input Specifications						
Part Number	<u>CPS2B1-120-24</u> <u>CPS2B1-240-24</u> <u>CPS2B1-480-24</u>					
Operation Voltage Range	90–264 VAC 110–345 VDC					
Frequency Range	47-63Hz					
Rated Current	1.4 A @ 120VAC 0.7 A @ 240VAC	2.4 A @ 120VAC 1.2 A @ 240VAC	4.8 A @ 120VAC 2.4 A @ 240 VAC			
Inrush Current	\leq 32A / 0.49 A ² s	$\leq 32A / 0.49 A^2 s$ $\leq 34A / 0.66 A^2 s$ $\leq 23A / 0.56 A^2 s$				
Power Factor Correction	> 0.90 enabled					
Recommended Circuit Breaker	C-curve 4A	C-cur	ve 10A			

1-Phase Output Specifications							
Part Number	<u>CPS2B1-120-24</u> <u>CPS2B1-240-24</u> <u>CPS2B1-480-24</u>						
Overload Limit In Constant Current Mode	7.5 A	11A	21A				
Maximum Output Current	7.5 A 5s @ Hiccup mode	15A 5s @ Hiccup mode	30A 5s @ Hiccup mode 21A CC mode				
Power Dissipation	< 13.5 W	< 19W	< 36.5 W				
Setting Range	11.5-29 VDC	22-29 VDC	22-29 VDC				
Load Regulation	≤ 1%	≤ 1%	< 1.5%				
Ripple And Noise	60mV pp	≤ 260mV pp	< 150mV pp				
Hold-Up Time	≥ 20ms @ 120VAC ≥ 30ms @ 240VAC	≥ 20ms @ 240VAC	> 25ms @ 240VAC				
Parallel / Redundant Mode		Yes, via external decoupling diode					
Efficiency (Typical)	> 90% @ 240VAC	> 93% @ 240VAC	> 93% @ 240VAC				
Short-Circuit	Hiccup mode/ Current limit	Hiccup mode/ Current limit Constant current					
МТВҒ	500,000h @ 25°C ambient full load	600,000h @ 25°C ambient full load	600,000h @ 25°C ambient full load				

www.automationdirect.com

For the latest prices, please check AutomationDirect.com.

1-800-633-0405



Switching Power Supplies 1/2/3 Phase CPS Universal Series



Overview

The LUTZE Universal Compact power supply series provides high efficiency, compact size, and power boost while allowing maximum installation flexibility. These models can take 1-, 2-, or 3-phase inputs to help installations in any application.

Features

- Compact footprint
- Aluminum housing
- 35mm DIN rail mount
- IP20
- 5 year warranty



CPSB-123-240-24

Switching Power Supplies 1/2/3 Phase								
Part Number	Price	Output Voltage	Output Current	Output Power	Input Voltage	Power Boost	Dimensions (W x H x D)	Drawing Link
<u>CPSB-123-240-24</u> *	\$230.00	24//DC	10A	240W		150% for 5s	54 x 115 x 110mm [2.12 x 4.52 x 4.33 in]	<u>PDF</u>
<u>CPSB-123-480-24</u> *	\$355.00	Z4VDC	20A	480W	200-500 VAC	140% for 5s	73 x 140 x 125mm [2.87 x 5.51 x 4.92 in]	PDF

* Requires an external fuse.

1/2/3 Phase Input Specifications							
Part Number	<u>CPSB-123-240-24</u>	<u>CPSB-123-480-24</u>					
Operation Voltage Range	187–550 VAC 250–725 VDC						
Frequency Range	47-6	63Hz					
Rated Current	1-Phase/2-Phase 2.2 A @ 220VAC, 1.1 A @ 500VAC 3-Phase 1.5 A @ 220VAC, 0.8 A @ 500VAC	1-Phase/2-Phase 2.9 A @ 200VAC, 1.3 A @ 500VAC 3-Phase 1.8 A @ 200VAC, 0.8 A @ 500VAC					
Inrush Current	≤ 45A / 1.31 A²s	≤ 55A / 2.16 A²s					
Power Factor Correction	> 0.6 @ 230V, 0.5 @ 400V > 0.9						
Recommended Circuit Breaker	C-curve 6A c	or D-curve 4A					

1/2/3 Phase Output Specifications							
Part Number	<u>CPSB-123-240-24</u>	<u>CPSB-123-480-24</u>					
Maximum Output Current	15A, 6A	28A, 5s					
Power Dissipation	< 18W < 42W						
Setting Range	23-28 VDC 23-28 VDC						
Load Regulation	< 1%	< 1%					
Ripple And Noise	<100mV pp	<50mV pp					
Hold-Up Time	15ms @ 230VAC > 100ms @ 500VAC	> 50ms					
Parallel / Redundant Mode	Yes, via external	decoupling diode					
Efficiency (Typical)	> 93% @ 240VAC	> 92% @ 240VAC					
Short-Circuit	38A	50A					
MTBF	500,000h	500,000h					



Switching Power Supplies 3-Phase CPS Universal Series



Overview

LUTZE 3-phase Compact power supply series are reliable 24VDC and equipped with an efficiency rating of over 91%, resulting in low power loss and low heat dissipation. The integrated power boost function allows for higher peak loads to be energized for a short period of time. An advantage of the remote on/off function is the convenience to remotely switch the unit on and off, therefore significantly reducing energy consumption. Additionally, status indication via a status output relay allows for remote monitoring.

Features

- Aluminum housing
- 35mm DIN rail mount
- IP20 rated
- 5 year warranty
- Superior power output to size ratio



CPSB3-120-24

Switching Power Supplies 3-Phase										
Part Number	Price	Output Voltage	Output Current	Output Power	Input Voltage	Power Boost	Remote On/Off Function	Dimensions (W x H x D)	Drawing Link	
CPSB3-120-24	\$165.00		5A	120W	350-575 VAC		Yes	55 x 129 x 133mm [2.16 x 5.07 x 5.23 in]	PDF	
CPSB3-240-24	\$215.00	24VDC	10A	240W		150% for 5s			PDF	
<u>CPSB3-960-24</u> *	\$495.00	250	40A	960W	400-500 VAC	150 /0 101 55	No	80 x 127 x 137.5 mm [3.14 x 5 x 5.41 in]	PDF	

* Requires an external fuse.

3-Phase Input Specifications							
Part Number	<u>CPSB3-120-24</u>	<u>CPSB3-240-24</u>	<u>CPSB3-960-24</u>				
Operation Voltage Range	350–575 VAC 350–575 VAC 340–550 VAC 520–725 VDC						
Frequency Range		47-63Hz					
Rated Current	0.35 A @ 400VAC 0.3 A @ 500VAC	0.59 A @ 400VAC 0.50 A @ 500VAC	2.4 A @ 400VAC 2.1 A @ 500VAC				
Inrush Current	30A @ 400VAC 39A @ 500VAC	30A @ 400VAC 36A @ 400VAC 39A @ 500VAC 40A @ 500VAC					
Power Factor Correction	> 0.5	> 0.6	> 0.7				
Recommended Circuit Breaker	(3) B-curve 6A	(3) B-curve 6A	(3) C-curve10A				

3-Phase Output Specifications								
Part Number	<u>CPSB3-120-24</u>	<u>CPSB3-240-24</u>	<u>CPSB3-960-24</u>					
Maximum Output Current	7.5 A	15A	44A					
	6A (Hiccup 2s)	12A (Hiccup 2s)	60A (Hiccup, 5s)					
Power Dissipation	< 11.5 W, < 2.1 W (stand-by)	< 18W, < 2.0 W (stand-by)	< 78W					
Setting Range	22.5-29 VDC	22.5-29 VDC	23-28 VDC					
Load Regulation	max. 0.4% 350-550 VAC max. 2.9% parallel mode	max. 0.6% 350-550 VAC max. 3.1% parallel mode	<1%					
Ripple And Noise	< 30mV pp	< 40mV pp	< 150mV pp					
Hold-Up Time	> 23ms @ 400VAC > 43ms @ 500VAC	> 22ms @ 400VAC > 44ms @ 500VAC	> 15ms					
Parallel / Redundant Mode	Yes, via external (max 3	decoupling diode devices)	Yes, via external decoupling diode (max 2 devices)					
Efficiency (Typical)	91.3 % @ 400VAC 91.2 % @ 500VAC	93.1 % @ 400VAC 93.2 % @ 500VAC	> 92.5 % @ 400VAC					
Short-Circuit	Hiccup, C	Hiccup, Current Limit						
МТВҒ	184,000h @ 400VAC 162,000h @ 500VAC	184,000h @ 400VAC 162,000h @ 500VAC	500,000h					

www.automationdirect.com

Power Supplies +





Power Supplies - Switching CPS Series

General Specifications								
Series	ECO Series 1-Phase	Ultra Series 1-Phase	Universal Series - 1/2/3 Phase	3-Phase Series				
Overvoltage Protection		≤ 33VDC		<u>CPSB3-120-24</u> <32V <u>CPSB3-240-24</u> <32V <u>CPSB3-960-24</u> <33VDC				
Overtemperature Protection		`	Yes					
Status Indicators	DC ON LED (gr DC LOW LED (een): ≥ 21.6 V red): ≤ 21.6 V	<u>CPSB-123-240-24</u> DC ON LED (green): ≥ 21.6 V DC LOW LED (red): ≥ 21.6 V <u>CPSB-123-480-24</u> DC ON LED (green): ≥ 21.6 V DC LOW LED (red): I _{out} >1.11 _n	$\label{eq:cpsB3-120-24} \\ \hline CPSB3-240-24 \\ DC OK LED (green) \\ ON U_{out} > 95\% U_{set} \\ OFF U_{out} > 90\% U_{se} \\ \hline CPSB3-960-24 \\ DC ON LED (green) \approx 21.6 \ V \\ DC LOW LED (red) \approx 21.6 \ V \\ \hline \end{array}$				
Humidity		5 to 95%, n	on-condensing					
Vibration		IEC 6	0068-2-6					
Shock		IEC 60	068-2-27					
Protection Rating	IP20							
Mounting		35mm DIN	I rail (vertical)					
Housing Material		Aluminun	n (enclosed)					
Agency Approval		CE, UKCA, o	CULus E249179					

Additional Data									
Dort Number	Weight	Operating	Storage	Terminal	Solid W	ire Size*	Tightoning Torque		
Part Nulliber	kg [lb]	Temperature	Temperature	Туре	Output	Input	rigiliening lorque		
CPSB1-120-24E	0.45 [0.99]								
<u>CPSB1-240-24E</u>	0.75 [1.65]	-40 to 70°C [-40 to 158°F]	-40 to 80°C [-40 to 176°F]	Screw	0.20 – 2.5 mm ² IAWG 24-141	0.20 – 2.5 mm ²	0.5 – 0.6 N•m [4.42 – 5.30 lb•ft]		
<u>CPSB1-480-24E</u>	1 [2.20]	[40 10 100 1]			[/ (10 24 14]	[/ (10 24 14]	[4.42 0.00 10 1(]		
<u>CPS2B1-120-24</u>	0.45 [0.99]	-35 to 70°C [-31 to 158°F]	-40 to 80°C		0 20 – 2 5 mm ²	0 20 – 2 5 mm ²	0.5 – 0.6 N•m		
CPS2B1-240-24	0.75 [1.65]	-40 to 70°C	[-40 to 176°F]	Screw	[AWG 24-14]	[AWG 24-14]	[4.42 – 5.30 lb•ft]		
<u>CPS2B1-480-24</u>	1.1 [2.42]	[-40 to 158°F]							
<u>CPSB-123-240-24</u>	0.65 [1.43]	-40 to 70°C	-40 to 70°C	-40 to 70°C	-40 to 80°C	Corour	0.20 – 2.5 mm² [AWG 30-12]	0.20 – 2.5 mm² [AWG 30-12]	0.5 – 0.6 N•m
<u>CPSB-123-480-24</u>	1 [2.20]	[-40 to 158°F]	[-40 to 176°F]	Screw	0.20 – 2.5 mm² [AWG 24-14]	0.20 – 2.5 mm² [AWG 24-14]	[4.42 – 5.30 lb•ft]		
CPSB3-120-24	0.66 [1.45]	-25 to 70°C	-40 to 85°C	Duch in	0.20 – 2.5 mm ²	0.20 – 2.5 mm ²	-		
<u>CPSB3-240-24</u>	0.78 [1.71]	[-13 to 158°F]	[-40 to 185°F]	Fusit-in	0.20 – 2.5 mm ²	0.20 – 2.5 mm ²	-		
<u>CPSB3-960-24</u>	1.3 [2.86]	-40 to 70°C [-40 to 158°F]	-40 to 80°C [-40 to 176°F]	Screw	0.20 – 10mm² [AWG 24-14]	0.20 – 10mm² [AWG 24-14]	max. 62 N•m		

* For other types of wire please see the insert.

BLOCK Power Supplies - Switching Mini Series 12VDC 1-Phase



Overview

These all-round power supply units can be utilized for various applications in the area of solar, measurement and control technology, especially plant and mechanical engineering. They are robust and adaptable in a range of applications, yet feature a light and compact design, which provides an outstanding protection against transients and high-energy interference pulses at the power input. The output voltage can be set by using the rotary potentiometer on the front panel of the device.

Features

- Compact footprint
- Push-in terminals
- 35mm DIN rail mount
- IP20
- 2A and 4A models are NEC class 2.



Power Supplies - Switching Mini Series 1-Phase									
Part Number	Price	Output Voltage	Output Current	Output Power	Input Voltage	Dimensions [W x H x D]	Drawing Link		
<u>PM-0112-020-0</u>	\$85.00		2A	2A 24W		22.5 x 90 x 97.5 mm [0.89 x 3.54 x 3.84 in]	PDF		
<u>PM-0112-040-0</u>	\$85.00	12 VDC	4A	48W	100-240 VAC	45 x 90 x 97.5 mm [1.77 x 3.54 x 3.84 in]	PDF		
<u>PM-0112-070-0</u>	\$102.00		7A	84W		52 x 90 x 109.5 mm [2.05 x 3.54 x 4.31 in]	<u>PDF</u>		

Power Supplies - Switching Mini Series 1-Phase Input Specifications								
Part Number	<u>PM-0112-020-0</u> <u>PM-0112-040-0</u> <u>PM-0112-070-0</u>							
Operation Voltage Range		85-264 VAC 120-372 VDC*						
Frequency Range		47-63Hz						
Input Voltage Derating	-2.5 % / VAC < 95 VAC							
Rated Current	0.50 A @ 100VAC 0.29 A @ 240VAC	1.66 A @ 100VAC 0.90 A @ 240VAC						
Inrush Current		≤ 30A, NTC						
Power Up Delay	1.5 s @ 100VAC 1.5 s @ 100VAC 0.5 s @ 0.4 s @ 230VAC 0.7 s @ 230VAC 0.3 s @							
Mains Buffering (nominal load)	15ms @ 100VAC 15ms @ 100VAC 120ms @ 230VAC 80ms @ 230VAC							
Internal Fuse	2AT 4AT							
Recommended Circuit Breaker	C-curve 6A	C-curve 10A	C-curve 16A					

* DC input voltage requires an external fuse.

Power Supplies - Switching Mini Series 1-Phase Output Specifications								
Part Number	<u>PM-0112-020-0</u>	<u>PM-0112-070-0</u>						
Nominal Output Voltage		12 VDC +/- 1%						
Output Voltage Range		11.5-14.5 VDC						
Nominal Output Current	2A 2.1 A @ max. 40°C	7A 7.5 A @ max. 40°C						
Output Current Limitation Constant Current	typ. 2.2 - 2.4 A	typ. 4.4 - 4.8 A	typ. 7.7 - 8.0 A					
Class 2 Output	(EN 60	950-1)	_					
Power Loss (Stand-by / Nominal Load)	< 0.7 W / 5.3 W (230VAC)	< 1W / 8W (230VAC)	< 1W / 16.2 W (230VAC)					
Maximum Power Loss	5.7 W (100VAC / 12V / 2A)	9.1 W (100 VAC / 12V / 4A)	19.8 W (100 VAC / 12V / 7A)					
Efficiency	82% typ. 86% typ.							
Ripple and Noise	20mVss							
Reverse Feed Max. Resistance (Nominal Load)	25VDC max.							
Internal Surge Voltage Protection (OVP)		35VDC max						

www.automationdirect.com

BLOCK Power Supplies - Switching Mini Series 24VDC 1-Phase



PM-0124-020-0

Overview

These all-round power supply units can be utilized for various applications in the area of solar, measurement and control technology, especially plant and mechanical engineering. They are robust and adaptable in a range of applications, yet feature a light and compact design, which provides an outstanding protection against transients and high-energy interference pulses at the power input. The output voltage can be set by using the rotary potentiometer on the front panel of the device.

Features

- Compact footprint
- Push-in terminals
- 35mm DIN rail mount
- IP20
- 1A, 2A and 3.8A models are NEC class 2.



Power Supplies - Switching Mini Series 1-Phase									
Part Number	Price	Output Voltage	Output Current	Output Power	Input Voltage	Dimensions [W x H x D]	Drawing Link		
<u>PM-0124-010-0</u>	\$49.50		1A	24W		22.5 x 90 x 97.5mm [0.89 x 3.54 x 3.84 in]	PDF		
<u>PM-0124-020-0</u>	\$67.00	24 VDC	2A	48W	100-240 VAC	45 x 90 x 97.5mm [1.77 x 3.54 x 3.84 in]	PDF		
<u>PM-0124-038-0</u>	\$102.00		3.8A	91.2W		52 x 90 x 111 mm [2.05 x 3.54 x 4.37 in]	PDF		
<u>PM-0124-040-0</u>	\$93.00		4A	96W			PDF		

Power Supplies - Switching Mini Series 1-Phase Input Specifications								
Part Number	<u>PM-0124-010-0</u>	<u>PM-0124-020-0</u>	<u>PM-0124-038-0</u>	<u>PM-0124-040-0</u>				
Operation Voltage Range		85-264 VAC 120-372 VDC*						
Frequency Range		47-63Hz						
Input Voltage Derating		-2.5 % / VA	.C < 95VAC					
Rated Current	0.49 A @ 100VAC 0.28 A @ 240VAC	0.82 A @ 100VAC 0.48 A @ 240VAC	1.73 A @ 100VAC 0.95 A @ 240VAC	1.82 A @ 100VAC 0.98 A @ 240VAC				
Inrush Current		≤ 30A	, NTC					
Power Up Delay	2.3 s @ 100VAC 0.74 s @ 230VAC	0.5 s @ 100VAC 0.27 s @ 230VAC	0.5 s @ 100VAC 0.2 s @ 230VAC	0.24 s @ 100VAC 0.14 s @ 230VAC				
Mains Buffering (nominal load)	20ms @ 100VAC 15ms @ 100VAC 120ms @ 230VAC 80ms @ 230VAC			100VAC 230VAC				
Recommended Circuit Breaker	C-curve 6A		C-curve 10A					

* DC input voltage requires an external fuse.

Power Supplies - Switching Mini Series 1-Phase Output Specifications								
Part Number	<u>PM-0124-010-0</u>	<u>PM-0124-020-0</u>	<u>PM-0124-038-0</u>	<u>PM-0124-040-0</u>				
Nominal Output Voltage		24 VD0	C+/- 1%					
Output Voltage Range		23-28.	5 VDC					
Nominal Output Current	1A 1.2 A @ max. 40°C	4A 4.2 A @ max. 40°C						
Output Current Limitation Constant Current	typ. 1.25 - 1.4 A	typ. 2.25 - 2.4 A	typ. 3.8 - 3.2 A	typ. 4.4 A				
Class 2 Output	(EN 60	0950-1)	(EN 60950-1, UL1310)	-				
Power Loss (Stand-by / Nominal Load)	< 1W / 4W (230 VAC)	< 1W / 6W (230 VAC)	< 2.8 W / 14W (230 VAC)	< 1W / 12W (230 VAC)				
Maximum Power Loss	5W (100VAC / 24V / 1A)	7W (100VAC / 24V / 2A)	20W (100 VAC / 91W)	15W (100 VAC / 24V / 4A)				
Efficiency	86% typ.	89% typ.	87% typ.	89% typ.				
Ripple and Noise	20mVss							
Reverse Feed Max. Resistance (Nominal Load)	35VDC max.							
Internal Surge Voltage Protection (OVP)	39VDC max	37VDC max	40VD	IC max				

www.automationdirect.com

Power Supplies tPWR-18

For the latest prices, please check AutomationDirect.com.

1-800-633-0405 **BLOCK** Power Supplies - Switching Mini Series 1-Phase

Power	Supplies -	Switching N	lini Series 1	-Phase Gen	eral Specifi	cations		
Part Number	PM-0112-020-0	<u>PM-0112-040-0</u>	<u>PM-0112-070-0</u>	<u>PM-0124-010-0</u>	<u>PM-0124-020-0</u>	<u>PM-0124-038-0</u>	<u>PM-0124-040-0</u>	
Signaling			<u></u>					
Signaling "DC OK"	Gr	een LED ON, Uout>'	10V		Green LED OI	N, Uout>21.5 V		
Signal Contact "DC OK"	Active High,	Uout>10V max. 40m	nA @ 12VDC	Act	ive High, Uout>21.5	V max. 20mA @ 24V	DC	
Environmental								
Derating		-3% / K > 50°C						
Cooling Type				Natural air convectior	l			
<i>Current Rating at any Mounting Position</i>	1.4 A max	2.6 A max	4.2 A max	0.7 A max.	1.3 A max	2.4 A	max	
Humidity			5 t	o 96%, non-condens	ing			
Environment		For u	use in Pollution Degre	e 2 environment, no	corrosive gases perm	nitted		
Minimum Spacing			0mm sid	e, 50mm above, 50m	im below			
General Data								
Degree of Protection				IEC 60529, IP20				
Protection Class				EN 61140, Class II				
Housing Material				Plastic				
Safety Standards								
Safety			EN 61010-1, EN 61	010-2-201, EN 6155	8-2-16, EN 60335-1			
ЕМС				EN 61204-3				
Safety Extra-low Voltage (SELV/PELV)				EN 61140				
CE			С	onforms to 2014/30/E	EU			
Agency Approvals	UL-Note: Output UL-Note: Output UL 60 DNV GL classified Vibration class A	IL 508: E219022 liste disconnecting means during installation. 950-1: E213214 reco : Temperature class B A; EMC class A*, B; E	ed shall be provided gnized B; Humidity class B inclosure class A	DNV GL Vibrat	UL 508: E2 UL60950-1: E21 classified: Temperat ion class A; EMC cla	19022 listed 3214 recognized ure class B; Humidity ss A,B**; Enclosure c	r class B ⊧lass A	

* EMCA only in conjunction with the filter HFE 156-230/10. ** EMCB only in conjunction with the filter HFE 156-230/10 No ECMC for PM-0124-040-0.

	Additional Data									
Part Number	Weight	Operating	Storage	Storage Terminal		Wire Size*				
	g [oz]	Temperature	Temperature	Туре	Bare Wire	With Ferrule	Strip Length			
<u>PM-0112-020-0</u>	128 [4.52]									
<u>PM-0112-040-0</u>	210 [7.41]									
<u>PM-0112-070-0</u>	384 [13.55]									
<u>PM-0124-010-0</u>	128 [0.99]	-25 to 70°C [-13 to 158°F]	-25 to 85°C [-13 to 185°F]	Push-in	0.08 – 2.5 mm ² [AWG 28-12]	0.25 – 2.5 mm ² [AWG 24-12]	8 – 9mm [0.31 - 0.35 in]			
<u>PM-0124-020-0</u>	210 [7.41]	[[[]	[]				
<u>PM-0124-038-0</u>	200 [12 76]									
PM-0124-040-0	390 [13.76]									

* Use 75°C rated copper conductors only..

BLOCK PM-0624-100-0 Redundancy



Module

The <u>PM-0624-100-0</u> redundancy module used with two BLOCK matched power supplies creates redundancy to help prevent costly downtime due to power supply failure. The <u>PM-0624-100-0</u> decouples the outputs of the two connected power supplies so that in case of failure, one power supply cannot overload the other.

PM-0624-100-0 Redundancy Module								
Part Number Price Drawing Link Input Voltage Range Max Power per Input Output Voltage Range Output Voltage Range								
<u>PM-0624-100-0</u>	\$98.00	<u>PDF</u>	2 x 10-36 VDC	144W	10-36 VDC	10A	Push-in Terminals	

PN	PM-0624-100-0 General Specifications							
Redundancy Module Input Specifications								
Rated Input Voltage	24 VDC							
Input Voltage Range	10-36 VDC							
Rated Input Current	10A							
Redundancy Module Output Specifications								
Rated Output Voltage	24 VDC							
Rated Output Current	10A							
Output Voltage Range	10-36 VDC							
Power Boost	120A, 25ms / 40A, 4s / 30A, 16s							
Max. Voltage Drop Between Input and Output	750mV							
Max. Power Loss	7.5 W							
Max. Feedback Resistance	37VDC							
Efficiency	96%							
Parallel Connection Possible	Yes							
Signaling								
Signal Output	Relay contact							
Signal Display	2x Green LED							
Environment								
Climate Class According to EN 60721	3K3							
Ambient Temperature	-40 to 70°C [-40 to 158°F]							
Storage Temperature	-40 to 85°C [-40 to 185°F]							
Humidity	5 to 96%, non-condensing							
Cooling Type	Natural air convection							
Minimum Spacing	0mm side, 30mm above, 30mm below							
Environment	For use in Pollution Degree 2 environment, no corrosive gases permitted							
Protection Class According to EN 61140	III, without PE connection							
Safety Extra Low Voltage (SELV/PELV)	EN 60950 (SELV), EN 60204 (PELV)							
Housing Material	Plastic							

www.automationdirect.com

Power Supplies tPWR-20

1-800-633-0405 **BLOCK PM-0624-100-0 Redundancy Module**

Weight and Dimensions						
Width mm [inches]	Height mm [inches]	Depth mm [inches]	Weight kg [lbs]			
22 [0.87]	90 [3.54]	94 [3.70]	0.12 [0.26]			

Redundancy Module Function Diagram





Switching Power Supplies PSRP Series

Overview

AutomationDirect's RHINO PRO PSRP series switching power supplies are designed for industrial applications inside a control cabinet. The PSRP series offers a sleek and space-saving design with push connectors in a rugged housing.



PSRP-24-120

Features

- High efficiency
- Power Boost to start difficult loads with additional power reserve
- Hyper Boost for 20ms
- Compact, space-saving footprint
- Integral 35mm DIN rail mounting
- Integrated device protection
- Quickly connect with push-in spring clamp
- DC OK alarm contact for remote monitoring
- Internal isolating transformer with reinforced insulation



PSRP-24-480-3

Switching Power Supplies								
Part Number	Price	Output Voltage	Output Current	Output Power	Drawing Link			
Single-Phase								
<u>PSRP-12-120</u>	\$225.00	12-15 VDC	10A	120W	<u>PDF</u>			
PSRP-24-120	\$170.00		5A	120W	<u>PDF</u>			
<u>PSRP-24-240</u>	\$229.00	24-28 VDC	10A	240W	<u>PDF</u>			
<u>PSRP-24-480</u>	\$335.00		20A	480W	PDF			
Three-Phase								
<u>PSRP-24-120-3</u>	\$190.00		5A	120W	PDF			
<u>PSRP-24-240-3</u>	\$213.00	24.28 VDC	10A	240W	PDF			
<u>PSRP-24-480-3</u>	\$387.00	24-20 VDC	20A	480W	<u>PDF</u>			
PSRP-24-960-3	\$525.00		40A	960W	PDF			





			In	out Specificatio	ons			
Part Number	Nominal Voltage	Input Voltage Range	Nominal Frequency	Nominal Input Current	Max. Inrush Current (after 1ms)	Nominal Watts	Efficiency [Typ.]	Circuit Breaker
Single-Phase	Single-Phase							
<u>PSRP-12-120</u>	100-240 VAC 90 100-230 VDC			13A@100VAC/VDC	64	0.88 kW @ 230VAC	91.6% @ 115VAC 93.1% @ 230VAC	
<u>PSRP-24-120</u>		85-265 VAC 90-250 VDC	50/60 Hz	0.6 A @ 240VAC/VDC	ŬĂ	0.87 kW @ 230VAC	92.8% @ 115VAC 94.3% @ 230VAC	C4
<u>PSRP-24-240</u>		100-230 VDC		±6 %	2.6 A @ 100VAC/VDC 1.1 A @ 240VAC/VDC	7A	0.95 kW @ 230VAC	93.4% @ 115VAC 94.4% @ 230VAC
<u>PSRP-24-480</u>		90-265 VAC 90-250 VDC		5.3 A @ 100VAC/VDC 2.3 A @ 240VAC/VDC	26A	0.96 kW @ 230VAC	93.4% @ 115VAC 94.6% @ 230VAC	C6, B10
Three-Phase								
<u>PSRP-24-120-3</u>				0.45 A @ (3 x 360VAC) 0.30A @ (3 x 500VAC)	9.5 A (3 x 500VAC)	0.61 kW (3 x 400VAC)	92.5% @ 3 x 400VAC 91.8% @ 3 x 480VAC	
<u>PSRP-24-240-3</u>	(3) 360-500 VAC	(3) 324 - 572 VAC	50/60 Hz	0.75 A @ (3 x 360VAC) 0.55 A @ (3 x 500VAC)	9A (3 x 500VAC)	0.66 kW (3 x 500VAC)	93.7% @ 3 x 400VAC 93.2% @ 3 x 480VAC	C1
<u>PSRP-24-480-3</u>	(3) 200-200 VAC	(3) 187 - 330 VAC	±6 %	1.3 A @ (3 x 360VAC) 1.0 A @ (3 x 500VAC)	13A (3 x 500VAC)	0.65 kW (3 x 500VAC)	94.8% @ 3 x 400VAC 94.5% @ 3 x 480VAC	04
<u>PSRP-24-960-3</u>				2.3 A @ (3 x 360VAC) 1.6 A @ (3 x 500VAC)	14A (3 x 500VAC)	0.88 kW (3 x 500VAC)	93.7% @ 3 x 400VAC 93.5% @ 3 x 480VAC	

			Output Speci	lications			
Part Number	Output Voltage Adjustable Range	Output Current	Output Current Power Boost	Output Current Hyper Boost	Output Hold Up Time (Min.)	Parallel Usage/ Serial Usage (Max.)	MTBF (@ 40°C)
Single-Phase							
<u>PSRP-12-120</u>	12-15 VDC	10A @ 12VDC 8A @ 15VDC		350% for min. 20ms @ 60°C	30ms @ 100VAC 10A @ 12VDC	5/2	> 900,000h
<u>PSRP-24-120</u>		5A @ 24VDC 4.25 A @ 28VDC	150% for min.		30ms @ 100VAC 5A @ 24VDC		> 900,000h
<u>PSRP-24-240</u>	24-28 VDC	10A @ 24VDC 8.5 A @ 28VDC	variation	450% for min. 20ms @ 60°C	30ms @ 100VAC 10A @ 24VDC		> 800,000h
<u>PSRP-24-480</u>		20A @ 24VDC 17A @ 28VDc		200% for min. 20ms @ 60°C	30ms @ 100VAC 20A @ 24VDC		> 800,000h
Three-Phase							
<u>PSRP-24-120-3</u>		5A @ 24VDC 4.3A @ 28VDC	7.5 A @ 24VDC > 5s	30A/20ms	25ms (3 x 360VAC) 5A @ 24VDC		> 1,000,000h
<u>PSRP-24-240-3</u>	24.29.VDC	10A @ 24VDC 8.6 A at 28VDC	15A @ 24VDC > 5s	35A/20ms	45ms (3 x 500VAC) 10A @ 24VDC	2	> 1,000,000h
<u>PSRP-24-480-3</u>	24-20 VDC	20A @ 24VDC 17.2 A @ 28VDC	30A @ 24VDC > 5s	60A/20ms	40ms (3 x 500VAC)	3	> 900,000h
<u>PSRP-24-960-3</u>		40A @ 24VDC 34A @ 28VDC	60A @ 24VDC > 5s	100A/20ms	40ms (3 x 500VAC)		> 700,000h



				Genera	al Specific	ations			
Part Number		<u>PSRP-12-120</u>	<u>PSRP-24-120</u>	<u>PSRP-24-240</u>	<u>PSRP-24-480</u>	<u>PSRP-24-120-3</u>	<u>PSRP-24-240-3</u>	<u>PSRP-24-480-3</u>	<u>PSRP-24-960-3</u>
Tomporatura	Operating	-25 to 60°C [-13 to 140 °F]		-40 to 60°C [-40 to 140°F]			-40 to 70°C [-40 to 158 °F]		-40 to 60°C [-40 to 140°F]
remperature	Storage					-40 to 85°C [-40 to 185°F]			
Humidity					5 to 9	95%, no condensin	g		
Line Regulati	on		< 1	mV				10mV	
Load Regulat	ion	200mV	220mV	210mV	180mV	Parallel mode on: 1000mV Parallel mode off: 100mV			
Start-up Time	(typ)		< 400ms @ U _{In}	_{put} 100-230 VAC			< 400ms		< 600ms
Short Circuit	Protection					Yes			
Leakage Current		0.3	mA	0.78 mA	2mA	(3 x 360VAC / 50Hz) 0.22 mA (3 x 500VAC / 60Hz) 0.34 mA		(3 x 360VAC / 50Hz) 1.15 mA (3 x 500VAC / 60Hz) 1.77 mA	(3 x 360VAC / 50Hz) 1.7 mA (3 x 500VAC / 60Hz) 2.1 mA
Overload Pro	tection					Yes			
Overvoltage S	Shutdown		-	_			31	VDC max.	
Status Indicat	tors				LED (red): overl	ED (green): OK oad, overheating o	r short-circuit		
Ripple		< 50 mVrms	< 50 mVeff	< 50 mVrms	< 50 mVeff		<	20 mVrms	
Spikes		< 200 mVp-p	< 200 mVss	< 200 mVp-p	< 200 mVss			-	
Vibration		IEC 60068	-2-6; 5-17.8 Hz:	1.6mm 17.8 - 50	0 Hz: 2.3 g	IEC 60068-2-6	i; 5-17.8 Hz: 1.6mr	n 17.8 - 500Hz: 2g	IEC 60068-2-6 2-17.8 Hz: 7.84 mm 17.8-500 Hz: 5g
Shock			IEC 60068-2-2	27 [30g / 11ms]		IEC 60068-2-	27 [50g / 6ms]	IEC 60068-2-27 [30g / 6ms]	IEC 60068-2-27 50g sinusoidal 8ms
Protection Ra	ting					IP20			
Mounting					35mm E	IN rail (horizontal o	only)		
Housing Mate	erial				Alu	minum (enclosed)			
Connection					Push-in	spring clamp termi	nals		
Weight kg [lb]		0.66 [1.45]	0.66 [1.45]	0.85 [1.87]	1.26 [2.77]	0.65 [1.43]	0.78 [1.71]	1.25 [2.75]	2.70 [5.95]
Agency Appro	oval				UL 50	08 File E197592, C	E		

	Additional Data								
	Solid Wire Size*								
Part Number	Output	Input							
<u>PSRP-12-120</u>	1.5 - 4 mm² [16 - 12 AWG]								
PSRP-24-120	0.75 - 4 mm² [18 - 12 AWG]	$0.75 \ 1 \ mm^2 \ [19 \ 10 \ \Lambda M/C]$							
<u>PSRP-24-240</u>	1.5 - 10 mm² [16 - 8 AWG]	0.75 - 4 IIIII- [16 - 12 AWG]							
PSRP-24-480	4 - 10 mm² [12 - 8 AWG]								
PSRP-24-120-3	0.2 - 4 mm² [24 - 12 AWG]	0.2 - 10 mm2 [24 - 8 AWG]							
PSRP-24-240-3	0.2 - 10 mm² [24 - 8 AWG]	0.2 - 10 mm2 [24 - 8 AWG]							
PSRP-24-480-3	0.2 - 10 mm2 [24 - 8 AWG]	0.2 - 10 mm2 [24 - 8 AWG]							
PSRP-24-960-3	0.75 - 16 mm2 [18 - 6 AWG]	0.2 - 10 mm2 [24 - 8 AWG]							

* For other types of wire please see the insert.



Switching Power Supplies PSRT Series

Overview

AutomationDirect's RHINO TOUGH PSRT series of switching power supplies are designed for industrial applications outside of the control cabinet. These fieldmountable power supplies offer a compact footprint and allow machine mounting near the load.

Features

- High efficiency
- Compact size
- Integrated device protection
- Quick connection with 7/8" connectors
- Internal isolating transformer with reinforced insulation
- IP67 protection class safe to touch even at full load







Switching Power Supplies								
Part Number Price Output Voltage Output Current Output Power					Drawing Link			
PSRT-24-100	\$289.00		3.8 A	91.2 W	PDF			
PSRT-24-200	\$375.00	Z4VDC	8A	192W	PDF			

Input Specifications								
Part Number	Nominal Input Voltage	Input Voltage Range	Nominal Frequency Range	Max. Input Current	Max. Inrush Current (after 1ms)	Nominal Watts	Efficiency	Circuit Breaker
PSRT-24-100	120/240 VAC	90-265 VAC/VDC 50/60 H	50/60 Hz	1.1 A @ 100VAC 0.5 A @ 240VAC	8.9A @ 230VAC	0.95 kW @ 230VAC	91.4% @ 115VAC 92.1% @ 230VAC	C4
<u>PSRT-24-200</u>	100/230 VDC	90-265 VAC 90-372 VDC	±6 %	2.1 A @ 100 VAC 0.9 A @ 240 VAC	7A @ 230VAC	0.95 kW @ 230VAC	93.7% @ 115VAC 94.4% @ 230VAC	B or C

Output Specifications							
Part Number	Output Voltage	Output Hold-up Time (Min.)	Output Current (Continuous 24VDC)	Output Current (Power Boost)	Output Current (Short-Circuit)	MTBF (@ 40°C)	
<u>PSRT-24-100</u>	24VDC	80ms (230VAC) 3.8 A (24VDC)	3.8 A (+60 °C) 2.4 A (+70 °C)	N/A	4.4 A	> 1,000,000h	
PSRT-24-200	(SELV) ±2%	≥ 35ms (230VAC) 8A (24VDC)	8A (+60 °C) 4.8 A (+70 °C)	150% for 5s	9A	> 700,000h	



General Specifications						
Part Number		<u>PSRT-24-100</u>	<u>PSRT-24-200</u>			
T	Operating	-40 to 85°C [-40 to 185°F]				
Temperature	Storage	-40 to 85°C [-40 to 185°F]			
Humidity		4 to 1	00%			
Line Regulation		5n	١V			
Load Regulation		110	mV			
Short Circuit Protection		Ye	95			
Leakage Current		< 1mA @ 230	0VAC / 50 Hz			
Start-up Time		≤ 330ms @ 100VAC ≤ 330ms @ 230VAC	≤ 500 ms			
Short Circuit Protection		Yes				
Overload Protection		Yes				
Overvoltage Shutdown		N/A				
Status Indicators		LED (green): output voltage OK LED (red): overload, overheating or short-circuit No color - No input voltage				
Ripple (max.)		50 mVrms	< 30 mVeff/rms			
Spikes (max.)		130 mVp-p	300 mVss/pp			
Vibration		IEC 60068-2-6; 2-17.8Hz:	7.84 mm, 17.8-500 Hz: 5g			
Shock		IEC 60068-2-2	27 [50g / 8ms]			
Enclosure Rating		IP	67			
Mounting		Chassis				
Housing Material		Aluminum (e	ncapsulated)			
Connection		(1) 7/8in - 16 UN2 4-pin female (1) 7/8in - 16 UN2 3-pin male Diagram 1	(1) 7/8in - 16 UN2 3-pin male (1) 7/8in - 16 UN2 5-pin female Diagram 2			
Tightening Torque		1.5 N•m [13.27 lb-in]				
Weight kg [lb]		1.22 [2.68]	1.65 [3.63]			
Agency Approval		UL 508 File E197592, CE				

Wiring Diagrams





Achie▼e[™] Switching Power Supplies **PSA Series**

Overview

AutomationDirect's AchieVe PSA series of switching power supplies are designed with essential features needed for industrial applications without compromising quality and reliability at a lower cost. These models can operate in constant current mode making them suitable for inductive and capacitive loads.

Features

- Universal AC input voltage range
- · Built-in constant current circuit for reactive loads
- Quick installation by 35mm DIN rail mounting
- Adjustable output voltage via potentiometer
- · 2-year warranty





PSA-24-240

Switching Power Supplies PSA Series								
Part Number	Price	Nominal Output Voltage	Output Current	Output Power	Nominal Input Frequency	Housing Material	Drawing Link	
Single-Phase								
<u>PSA-12-75</u>	\$25.50		6.25 A	75W		Plastic	<u>PDF</u>	
<u>PSA-12-120</u>	\$32.00	12VDC	10A	120W	50/60 Hz	Aluminum	PDF	
<u>PSA-12-240</u>	\$59.00		20A	240W			PDF	
<u>PSA-24-75</u>	\$25.50		3.125 A	75W		Plastic	<u>PDF</u>	
<u>PSA-24-120</u>	\$29.50	241/00	5A	120W		Aluminum	<u>PDF</u>	
<u>PSA-24-240</u>	\$59.00	Z4VDC	10A	240W			<u>PDF</u>	
PSA-24-480	\$118.00		20A	480W			PDF	
PSA-48-120	\$32.00		2.5 A	120W			PDF	
PSA-48-240	\$59.00	48VDC	5A	240W			PDF	
<u>PSA-48-480</u>	\$118.00		10A	480W			PDF	



PSA-24-75



Achie▼e[™] Switching Power Supplies **PSA Series Specifications**

Input Specifications							
Part Number	Nominal Input Voltage	Input Voltage Range	Input Frequency Range	Max. Input Current	Max. Inrush Current (cold start)	Efficiency	Circuit Breaker (Min.)
<u>PSA-12-75</u>		85-264 VAC 120-375 VDC		1.4 A @ 115VAC 0.9 A @ 230VAC	50A @ 230VAC	87.5% @ 230VAC	
<u>PSA-12-120</u>		00.264.VAC		2.1 A @ 115VAC 1.3 A @ 230VAC	35A @ 230VAC	88% @ 115VAC 86% @ 230VAC	
<u>PSA-12-240</u>		90-264 VAC	- - 47-63 Hz	2.5 A @ 115VAC 1.3 A @ 230VAC	40A @ 230VAC	88% @ 115VAC 86.5% @ 230VAC	-
<u>PSA-24-75</u>		85-264 VAC 120-375 VDC		1.4 A @ 115VAC 0.9 A @ 230VAC	50A @ 230VAC	89% @ 230VAC	
<u>PSA-24-120</u>	400/040 \/AC			2.1 A @ 115VAC 1.3 A @ 230VAC	35A @ 230VAC	88% @ 115VAC 88.5% @ 230VAC	20A
<u>PSA-24-240</u>	100/240 VAC			2.5 A @ 115VAC 1.3 A @ 230VAC	40A @ 230VAC	88% @ 115VAC 90% @ 230VAC	B Curve
<u>PSA-24-480</u>		00.004.1/0.0		4.7 A @ 115VAC 2.4 A @ 230VAC	40A @ 230VAC	91.5% @ 115VAC 93% @ 230VAC	
<u>PSA-48-120</u>		90-264 VAC		2.1 A @ 115VAC 1.3 A @ 230VAC	35A @ 230VAC	88% @ 115VAC 9.5% @ 230VAC	
<u>PSA-48-240</u>				2.5 A @ 115VAC 1.3 A @ 230VAC	40A @ 230VAC	91.5% @ 115VAC 90.5% @ 230VAC	
<u>PSA-48-480</u>				4.7 A @ 115 VAC 2.4 A @ 230VAC	40A @ 230VAC	91.5% @ 115VAC 93.5% @ 230VAC	

Output Specifications								
Part Number	Factory Set Point Tolerance	Output Voltage Range	Rise Time @ 100% Load	Start-up Time @ 100% Load	Hold Up Time @ 100% Load	MTBF		
<u>PSA-12-75</u>	12VDC ± 2%		30ms @ nominal input	1200ms @ 115VAC 1000ms @ 230VAC	16ms @ 115VAC 60ms @ 230VAC			
<u>PSA-12-120</u>	12VDC ± 1%	10.8-13.2 VDC	30ms @ 115/230 VAC	500ms @ 115/230 VAC	10ms @ 115VAC 16ms @ 230VAC			
<u>PSA-12-240</u>	12VDC ± 1%		301113 @ 113/230 VAC	300m3 @ 110/230 VAO	20ms @ 115/230 VAC			
<u>PSA-24-75</u>	24VDC ± 2%		30ms @ nominal input	1200ms @ 115VAC 1000ms @ 230VAC	16ms @ 115VAC 60ms @ 230VAC			
<u>PSA-24-120</u>	24VDC ± 1%	21.6-26.4 VDC			10ms @ 115VAC 16ms @ 230VAC	> 700 000 b		
<u>PSA-24-240</u>	24VDC ± 1%				20ms @ 115/230 VAC	> 700,000 H		
<u>PSA-24-480</u>	24VDC ± 1%	24-28 VDC	20ma @ 115/220 \/AC	500ms @ 115/23 VAC	25ms @ 115/230 VAC			
<u>PSA-48-120</u>	48VDC ± 1%	42.2.52.8.VDC	SUIIS @ TIS/250 VAC		10ms @ 115VAC 16ms @ 230VAC			
<u>PSA-48-240</u>	48VDC ± 1%	40.2-02.0 VDC			20ms @ 115/230 VAC			
<u>PSA-48-480</u>	48VDC ± 1%	48-55 VDC		800ms @ 230VAC	25ms @ 115/230 VAC			

Specifications continued on the following page.



Achie√e[™] Switching Power Supplies **Specifications PSA Series**

General Specifications											
Part Number		PSA-12-75	PSA-12-120	PSA-12-240	PSA-24-75	PSA-24-120	PSA-24-240	PSA-24-480	PSA-48-120	PSA-48-240	PSA-48-480
T	Operating	-20 to 70°C [-4 to 158°F]	-30 to [-22 to	70°C 158°F]	-20 to 70°C [-4 to 158°F]		-30 to 70°C [-22 to 158°F]				
Temperature	Storage					-40 tc [-40 to	985°C 185°F]				
Humidity Non-Condens	ing	5 to 95% RH	20 to 9	10% RH	5 to 95% RH			20 to 9	0% RH		
Line Regulatio @ 100% Load	on	< .05% @ 85-264 VAC	± 0.8 115/2	5% @ 30 VAC	< .05% @ 85-264 VAC			±0.5 115/23	% @ 30 VAC		
Load Regulati @ 0-100% Loa	ion ad	<1%	±	1%	<1%			± 0	.5 %		
Start-up With Loads (maxim	Capacitive num)	5,000 µF	8,00	/0 μF	5,000 µF		8,000 µF			3,000 µF	
Short Circuit	Protection			Hiccu	up Mode, Non-L	atching (Auto-F	Recovery when	the fault is rem	oved)		
Leakage Curr	ent	< 1mA @ 240VAC	0.5 mA @ 240VAC	0.75 mA @ 240VAC	< 1mA @ 240VAC	0.5 mA @ 240VAC	0.75 mA @ 240VAC	1.5 mA @ 240VAC	0.5 mA @ 240VAC	0.75 mA @ 240VAC	1.5 mA @ 240VAC
Overload Prot	tection				Y	es					
No Power Loa Consumption	d	-	0.15 115/23	W @ 30 VAC	-	0.15 W @ 115/230 VAC	0.21 W @ 115/230 VAC	0.75 W @ 115/230 VAC	0.21 W @ 115/230 VAC	0.3 W @ 115/230 VAC	0.75 W @ 115/230 VAC
Overvoltage L	atch Mode	<18V SELV	17.4	SELV		< 33.6 V SELV < 34V SELV			<64.8 V SELV < 68V SELV		
Status Indicat	ors					LED (gree	n): DC OK				
Bingle		<120 mVpp @ -10 to 70°C	<120 @ 0 t	mVpp o 70°C	<120 mVpp @ -10 to 70°C		<150 mVpp @ 0 to 70°C			<200 mVpp @ 0 to 70°C	
Прріе		< 360 mVpp @ -10 to 30°C	< 360 @ -30	mVpp to 0°C	< 360 mVpp @ -10 to 30°C		< 450 mVpp @ -30 to 0°C			< 600 mVpp @ -30 to 0°C	
Vibration						IEC 60	068-2-6				
Shock						IEC 600	68-2-27				
Protection Ra	ting	IP20									
Mounting		35mm DIN rail									
Connection					Screw termin	nals (see additio	onal data on fol	lowing page)			
Weight kg [lb]	1	0.22 [0.49]	0.45 [99.20]	0.62 [1.136]	0.22 [0.49]	0.45 [99.20]	0.62 [1.136]	0.87 [1.91]	0.45 [99.20]	0.62 [1.136]	0.87 [1.91]
Agency Appro	oval				CE, cUL	us File: E19759	2, cURus File:	E131881			



Achie▼e[™] Switching Power Supplies **PSA Series**

Additional Data						
Part Number		Solid Wire Size				
	Input	Output	ADC Ferrule Part Number			
<u>PSA-12-75</u>	0.8 - 3.3 mm² [18 -12 AWG] 0.4 N•m [3.5 lb•in]	0.8 - 3.3 mm² [22 -12 AWG] 0.4 N•m [3.5 lb•in]	20AWG <u>V30AE000038</u> 18AWG <u>V30AE000041</u> 16AWG <u>V30AE000048</u> 14AWG <u>V30AE000052</u> 12AWG <u>V30AE000055</u>			
<u>PSA-12-120</u>	0.8 - 3.3 mm² [18 -12 AWG] 0.4 N•m [3.5 lb•in]	0.34 - 4 mm² [22 - 12 AWG] 0.4 N•m [3.5 lb•in]	18AWG <u>V30AE000041</u> 16AWG <u>V30AE000048</u> 14AWG <u>V30AE000052</u> 12AWG <u>V30AE000055</u>			
<u>PSA-12-240</u>	0.8 - 3.3 mm² [18 -12 AWG] 0.4 N•m [3.5 lb•in]	0.8 - 3.3 mm² [18 -12 AWG] 0.4 N•m [3.5 lb•in]	18AWG <u>V30AE000041</u> 16AWG <u>V30AE000048</u> 14AWG <u>V30AE000052</u> 12AWG <u>V30AE000055</u>			
<u>PSA-24-75</u>	0.8 - 3.3 mm² [18 -12 AWG] 0.4 N•m [3.5 lb•in]	0.8 - 3.3 mm² [20 -12 AWG] 0.4 N•m [3.5 lb•in]	20AWG <u>V30AE000038</u> 18AWG <u>V30AE000041</u> 16AWG <u>V30AE000048</u> 14AWG <u>V30AE000052</u> 12AWG <u>V30AE000055</u>			
<u>PSA-24-120</u>	0.8 - 3.3 mm² [18 -12 AWG] 0.4 N•m [3.5 lb•in]	0.34 - 4 mm² [22 - 12 AWG] 0.4 N•m [3.5 lb•in]	18AWG <u>V30AE000041</u> 16AWG <u>V30AE000048</u> 14AWG <u>V30AE000052</u> 12AWG <u>V30AE000055</u>			
<u>PSA-24-240</u>	0.8 - 3.3 mm² [18 -12 AWG] 0.4 N•m [3.5 lb•in]	0.8 - 3.3 mm² [18 -12 AWG] 0.4 N•m [3.5 lb•in]	18AWG <u>V30AE000041</u> 16AWG <u>V30AE000048</u> 14AWG <u>V30AE000052</u> 12AWG <u>V30AE000055</u>			
<u>PSA-24-480</u>	2.1 - 3.3 mm² [14 -12 AWG] 0.51 N•m [4.5 lb•in]	2.1 - 3.3 mm² [14 -12 AWG] 0.51 N•m [4.5 lb•in]	14AWG <u>V30AE000052</u> 12AWG <u>V30AE000055</u>			
<u>PSA-48-120</u>	0.8 - 3.3 mm² [18 -12 AWG] 0.4 N•m [3.5 lb•in]	0.34 - 4 mm² / 22 - 12 AWG 0.4 N•m [3.5 lb•in]	18AWG <u>V30AE000041</u> 16AWG <u>V30AE000048</u> 14AWG <u>V30AE000052</u> 12AWG <u>V30AE000055</u>			
<u>PSA-48-240</u>	0.8 - 3.3 mm² [18 -12 AWG] 0.4 N•m [3.5 lb•in]	0.8 - 3.3 mm² [18 -12 AWG] 0.4 N•m [3.5 lb•in]	18AWG <u>V30AE000041</u> 16AWG <u>V30AE000048</u> 14AWG <u>V30AE000052</u> 12AWG <u>V30AE000055</u>			
<u>PSA-48-480</u>	2.1 - 3.3 mm² [14 -12 AWG] 0.51 N•m [4.5 lb•in]	2.1 - 3.3 mm² [14 -12 AWG] 0.51 N•m [4.5 lb•in]	14AWG <u>V30AE000052</u> 12AWG <u>V30AE000055</u>			

For the latest prices, please check AutomationDirect.com.



RHINO PRO DC To DC Converters

Overview

The RHINO PRO DC to DC Converters, designed for harsh industrial environments, feature stringent protection ratings, such as:

- High EMC immunity against surge, burst, radiated, and conducted disturbances
- High shock and vibration resistance
- High thermal shock resistance

At 100% load, the current characteristics goes from constant voltage to constant current which makes the units also suitable for battery charger applications. With protection against over-temperature, overload, shortcircuit, reverse input, overvoltage and input undervoltage lock-out they are hard to destroy.

Features

- Input voltage ranges: 9 to 36 and 18 to 75 VDC
- Constant current output characteristic for battery load applications
- Wide operating temperature range: -40 to 75°C [-40 to 167°F]
- Under voltage lock-out, overtemperature & reverse input protection
- Easy chassis and wall mounting
- 3-year warranty





Part Number	Price	Drawing Link	Input Voltage Range	Input Current @ No Load	Output Voltage	Output Current Max	Output Power	Efficiency typ.
PSRP-12-DC24-150	\$215.00	PDF			12VDC	12,500 mA		86%
PSRP-15-DC24-150	\$215.00	PDF		400.4	15VDC	10,000 mA	150W	
PSRP-24-DC24-150	\$215.00	PDF	9-36 VDC (24.VDC Nom)	100mA (24VDC Nom)	24VDC	6,300 mA		87%
PSRP-28-DC24-150	\$215.00	PDF			28VDC	5,400 mA		
PSRP-48-DC24-150	\$217.00	PDF			48VDC	3,200 mA		86%
PSRP-12-DC48-150	\$217.00	PDF	18-75 VDC	65mA (48VDC Nom)	12VDC	12,500 mA		88%
PSRP-24-DC48-150	\$217.00	PDF	(48VDC Nom)		24VDC	6,300 mA		89%

Wiring



PINOUT						
PIN	Function	Recommended Wire				
1	+Vin	14-16 AWG				
2	+Vin	14-16 AWG				
3	-Vin	14-16 AWG				
4	-Vin	14-16 AWG				
5	Remote	14-24 AWG				
6	+Vout	14-16 AWG				
7	-Vout	14-16 AWG				
8	Trim	14-24 AWG				
9	Trim	14-24 AWG				



RHINO PRO DC To DC Converters

Input Specifications				
Surge Voltage (100 sec. max.)	24 VDC models: 50VDC 48 VDC models: 100VDC			
Start-Up Time	35 ms typ.			
Under Voltage Lockout	24 Vin models: 7.9 - 8.5 VDC 48 Vin models: 15.6 - 16.8 VDC			
Recommended Input Fuse	24 Vin models 30A (slow blow) 48 Vin models 15A (slow blow)			
ESD (Electrostatic Discharge)	Air: EN 61000-4-2, ±8 kV, perf. criteria A Contact: EN 61000-4-2, ±6 kV, perf. criteria A			
Radiated Emissions	EN 55032 class A (internal filter) FCC Part 15 class A (internal filter)			
Reverse Voltage Protection	Parallel diode (external input fuse required)			
Input Filter	Internal Pi-Type			

Note: All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.

Output Specifications				
Voltage Set Accuracy	±1% max			
Regulation	Input Variation (Vmin - Vmax) 0.2% max. - Load Variation (0 - 100%) 0.4% max.I			
Minimum Load	Not required			
Temperature Coefficient	±0.02 %/K			
Ripple and Noise (20MHz bandwidth)	12VDC and 15VDC models: 100 mVp-p max. 24VDC and 28VDC models: 200 mVp-p max. 48V DC models: 300 mVp-p max.			
Transient Response	200 µs typ. (25% Load Step)			
Overvoltage Protection	125 - 140% of Vout nom			
Output Current Limitation	105 - 120% of lout max.			
Short Circuit Protection	Continuous, Automatic recovery			
Capacitive Load	12VDC models: 40'000 μF max. 15VDC models: 26'000 μF max. 24VDC models: 10'000 μF max. 28VDC models: 7'600 μF max. 48VDC models: 2'600 μF max.			

Note: All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.

For the latest prices, please check AutomationDirect.com.



RHINO PRO DC To DC Converters

	General Specifications					
Output Voltage Adjustable Range	0% to +20% (By external trim resistor)					
Output Voltage Regulation*	Input variation - 0.2% max Load variation - 0.4% max					
Ripple/Noise (20MHz bandwidth)	12VDC and 15VDC models: 100 mVp-p max. 24VDC and 28VDC models: 200 mVp-p max. 48VDC models: 300 mVp-p max.					
Temperature: Operating Storage (non-operating)	-40 to 75°C [-40 to 167°F max] -55 to 125°C, [-67 to 257°F max]					
Derating	Above 50°C -> 2.0 %/K [24VDC nom.] Above 55°C -> 2.2 %/K [48VDC nom.]					
Relative Humidity	95% max. (non-condensing)					
Output Power Derating (natural convection)	Natural convection					
Temperature Coefficient	±0.02 %/K max.					
Switching Frequency	203 - 330 kHz (PWM)					
Isolation Voltage (1 min.) – Input/Output	3,000 VDC					
Safety Standards	EN 60950-1, EN 62368-1, IEC 60950-1,IEC 62368-1, UL 60950-1, UL 62368-1 - Railway Applications EN 50155					
Electromagnetic Compatibility (EMC)	EN 61000-4-3, 10 V/m, perf. criteria A					
Parallel Operation	N/A					
Pollution Degree	PD 2					
Environmental Air	No corrosive gases permitted					
Enclosure Rating	IP 55 [IEC 60529]					
Enclosure Material	Aluminum					
Mounting	Chassis mount					
Mounting Orientation	Vertical only					
Wiring	14-24 AWG [2.5-0.25 mm²]					
Weight [g]	300					
Connections	Screw terminal Recommended tightening torque 0.25 Nm [2.21 in-lb]					
Short Circuit Protection	Continuous, automatic recovery					
Agency Approvals	CE, cURus File E198298					

* Input variation Vin min to Vin max and load variation 0 to 100%

Note: All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.

To obtain the most current agency approval information, see the Agency Compliance & Certifications Checklist section on the specific part number's web page.

RHINO PRO DC To DC Converters

Output Voltage Adjustment

Output voltage set point adjustment allows the user to increase the output voltage set point of the module. This is accomplished by connecting an external resistor between pin 8 (Trim) and pin 9 (Trim). The external TRIM resistor needs to be at least 1/16 W of rated power.

Trim-Tables

PSRP-12-DC24-150, PSRP-24-DC48-150										
	1%	2%	3%	4%	5%	6%	7%	8%	9%	10%
Vout [V] R _u [kOhm]	12.12 222.64	12.24 105.09	12.36 66.35	12.48 47.06	12.60 33.51	12.72 27.83	12.84 22.34	12.96 18.23	13.08 18.23	13.20 12.48
	11%	12%	13%	14%	15%	16%	17%	18%	19%	20%
Vout [V] R _u [kOhm]	13.32 10.39	13.44 8.65	13.56 7.18	13.68 5.91	13.80 4.82	13.92 3.86	14.04 3.02	14.16 2.27	14.28 1.60	14.40 0.99

PSRP-15-DC24-150										
	1%	2%	3%	4%	5%	6%	7%	8%	9%	10%
Vout [V] R _u [kOhm]	15.15 238.62	15.30 113.62	15.45 71.95	15.60 51.12	15.75 38.62	15.90 30.29	16.05 24.33	16.20 19.87	16.35 16.40	16.50 13.62
	11%	12%	13%	14%	15%	16%	17%	18%	19%	20%
Vout [V] R _u [kOhm]	16.65 11.35	16.80 9.45	16.95 7.85	17.10 6.48	17.25 5.29	17.40 4.25	17.55 3.33	17.70 2.51	17.85 1.78	18.80 1.12

PSRP-24-DC24-150, PSRP-24-DC48-150										
	1%	2%	3%	4%	5%	6%	7%	8%	9%	10%
Vout [V] R _u [kOhm]	24.24 212.47	24.48 106.69	24.72 68.79	24.96 49.30	25.20 37.43	25.44 29.44	25.68 23.70	25.92 19.37	26.16 15.99	26.40 13.28
	11%	12%	13%	14%	15%	16%	17%	18%	19%	20%
Vout [V] R _u [kOhm]	26.64 11.06	26.88 9.20	27.12 7.63	27.36 6.28	27.6 5.11	27.84 4.08	28.08 3.18	28.32 2.37	28.56 1.65	28.80 1.00

PSRP-28-DC24-150										
	1%	2%	3%	4%	5%	6%	7%	8%	9%	10%
Vout [V] R _u [kOhm]	28.28 255.65	28.56 121.72	28.84 77.08	29.12 77.08	29.40 41.36	29.68 32.44	29.96 26.06	30.24 21.28	30.52 17.56	30.80 14.58
	11%	12%	13%	14%	15%	16%	17%	18%	19%	20%
Vout [V] R _u [kOhm]	31.08 12.14	31.36 10.11	31.64 8.40	31.92 6.93	32.20 5.65	32.48 4.53	32.76 3.55	33.04 2.67	33.32 1.89	33.60 1.10

PSRP-48-DC24-150										
	1%	2%	3%	4%	5%	6%	7%	8%	9%	10%
Vout [V] R _u [kOhm]	48.48 268.86	48.96 127.44	49.44 80.57	49.92 57.19	50.40 43.17	50.88 33.84	51.36 27.17	51.84 22.18	52.32 18.29	52.80 15.18
	11%	12%	13%	14%	15%	16%	17%	18%	19%	20%
Vout [V] R _u [kOhm]	53.28 12.64	53.76 10.52	54.24 8.73	54.72 7.20	55.20 5.87	55.68 4.70	56.16 3.67	56.64 2.76	57.12 1.94	57.60 1.21

Connection of trim-up resistor





DC to DC Converters 859 Series

Features

- Ultra-wide input voltage range
- Overload and short circuit protection
- Low ripple and noise
- I/O-isolation 1500 VDC
- Compact, slim plastic case
- Reliable snap-on 35mm DIN rail mount
- Wall-mount bracket included
- 2-year warranty



859-801



DC to DC Converters										
Part Number	Price	Input Voltage Range	Input Current Max. @ Vin, [lout = 0% / 100%]	Output Voltage	Output Current Max	Output Power	Weight grams [oz]	Drawing Link		
<u>859-801</u>	\$75.00	10-30 VDC	80mA / 0.15A @ 24 VDC	5 VDC	0.5A	2.5W	34.6 [1.22]	PDF		
<u>859-802</u>	\$75.00	10-30 VDC	80mA / 0.25A @ 24 VDC	10 VDC	0.5A	5W	41.1 [1.44]	PDF		
<u>859-805</u>	\$75.00	10-30 VDC	80mA / 0.29A @ 24 VDC	12 VDC	0.5A	6W	35 [1.23]	PDF		

DC to DC Converters Accessory								
Part Number	Price	Description	Drawing Link					
<u>859-525-5</u>	\$5.00	WAGO end cover, package of 5. For use with WAGO DC to DC converters.	<u>PDF</u>					



859-525-5



	General Specifications					
Startup Voltage / Undervoltage Shut-down	17.2 VDC / 15.7 VDC [PSP24-DC12-1: 8.4 VDC / 7.6 VDC]					
Efficiency (Typical)	<u>859-801</u> 70% <u>859-802</u> and <u>859-805</u> 85%					
Output Voltage	<u>859-801</u> - 5VDC <u>859-802</u> - 10VDC <u>859-805</u> - 12VDC					
Overvoltage Protection, Trigger Point	$\frac{859-801}{859-802} \le 6.5 \vee \\ \frac{859-802}{859-805} \le 24 \vee \\ \frac{859-805}{2} \le 42 \vee $					
Output Voltage Regulation*	$\frac{859-801}{859-802} \le 0.5\%$					
Ripple/Noise (20MHz bandwidth)	<u>859-801</u> ≤ 150mV <u>859-802</u> and <u>859-805</u> ≤ 20mV					
Temperature: Operating Storage (non-operating) Derating	-25 to 70°C max [-13 to 158°F max] -25 to 85°C max, [-13 to 185°F max] 1.5%/K above 50°C [122°F] for 25W models, 2%/K above 40°C [104°F] for 60W models					
Humidity (Non-condensing)	95 % relative humidity max.					
Temperature Coefficient	0.02%/K					
Switching Frequency	20kHz [nominal]					
Isolation Voltage (1 min.) – Input/Output	1500VDC					
Safety Standards						
Electromagnetic Compatibility (EMC)	Emissions: EN 61000-6-3; Immunity: EN 61000-6-2					
Parallel Operation	No parallel operation					
Safety Class	Degree of protection class 111					
Environmental Air	No corrosive gases permitted					
Enclosure Rating	IP20 [per EN 60529]					
Enclosure Material	Plastic FR2010-110C [UL 94V-0 rated]					
Mounting	DIN rails per EN 50022-35x15/7.5 [snap-on with self-locking spring]; bracket for wall/chassis mount included					
Mounting Orientation	Vertical only					
Wiring	28-14 AWG [0.08-2.5 mm²]					
Connections	Cage Clamp®, recommended tightening torque 0.5-0.7 Nm [4.5-6.2 in-lb]					
Short Circuit Protection	Current limited at 110% typical					
MTBF (IEC 61709 @ 25°C)	> 2.5 million hours					
Agency Approvals**	UL 508 File E175199, CE, RoHS					

* Input variation Vin min to Vin max and load variation 0 to 100% ** To obtain the most current agency approval information, see the Agency Approval Compliance & Certifications Checklist section on the specific part number's web page.

Note: All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.
1-800-633-0405



Overview

The 2000-5420-1399-0987 gives the user the ability to easily convert a signal to their PLC from PNP to NPN or vice-versa simply by moving a couple of wires and changing of the internal jumper

Features

- 35mm DIN rail mount
- 2- year warranty





2000-5420-1399-0987

PNP/NPN Converter								
Part Number	Price	Input Voltage Range	Input Current @ 24 VDC	Output Voltage	Output Current Max	Weight grams [oz]	Drawing Link	
<u>2000-5420-1399-0987</u>	\$52.00	19.2 - 28.8 VDC	7mA	24VDC	100mA	35 [1.23]	PDF	

Specifications						
Specification						
Maximum Output Current	100mA					
Minimum Load on Output	1mA					
Voltage Drop at Output	[24V, 100mA] 1.3 V					
Input Voltage Nominal	24VDC					
Input Voltage Range	19.2 - 28.8 VDC					
Input Current at 24VDC	7mA					
Operating Temperature	0 to 40°C [+32 to 104°F]					
Isolation Voltage	500Vrms [60s, R.H. ≤ 60%]					
Maximum Switching Frequency	500Hz					
Housing Material	Plastic					
Insulation Material	Polyamide [PA66]					
Mounting	35mm DIN					
LED	Green, illuminated when signal applied to input					
Agency Approval *	RoHS					

* To obtain the most current agency approval information, see the Agency Approval Compliance & Certifications Checklist section on the specific part number's web page.

Accessory						
Part Number	Price	Description	Drawing Link			
<u>2000-5491-5</u>	\$6.00	WAGO end cover, package of 5. For use with WAGO PNP/NPN converters.	<u>PDF</u>			



RHINO Panel Mount Power Supply PSS Series

Overview

AutomationDirect's RHINO PSS panel mount power supply is perfect for applications that require a basic DC voltage power supply. The low cost power supply offers high performance and reliability without all the additional features of higher cost full-featured power supplies. The <u>PSS0524-100</u> provides both a 24VDC and a 5VDC output. The rugged aluminum housing easily screw mounts in three different mounting orientations. This high-quality power supply includes overload, overvoltage and thermal protection, and is UL 60950 recognized, CE marked and RoHS compliant.

Features

- Dual 5 and 24VDC, 100 Watts
- Adjustable output voltage
- Rugged aluminum housing, screw mounts in three different orientations
- Output voltage status LED
- Robust fixed-screw terminal strips
- Overload, overvoltage and thermal protection
- UL 60950 recognized, CE marked and RoHS compliant
- 2-year warranty





Input Specifications									
Part Number	Price	Weight kg [lb]	Input Voltage	Input Frequency Range	Max. Input Current	Inrush Current Limitation I2t @ 77°F [+25°C] typ.	Leakage Current	Recommended Circuit Breaker	
<u>PSS0524-100</u>	\$54.00	0.52 [1.15]	85–264 VAC [DC input range 125–375 VDC]	47–63 Hz [0Hz @ DC Input]	< 2A Max @ 115VAC, < 1.1A Max @ 230VAC	< 50A @ 115VAC, 100A @ 230VAC	< 1mA	16A "B" Curve	

Output Specifications									
Part Number	Output Voltage (Vnom) / Adjustment Range	Output Power	Output Current	Ripple and Noise [20MHz]	Startup with Capacitive Loads	Start-Up Time	Hold-Up Time at Nominal Load (Typ.) (Mains Buffering) @ 25°C [77°F]	Rise Time	Efficiency [Typ @115VAC]
<u>PSS0524-100</u>	V1: 24VDC / 22:8–26.4 VDC V2: 5VDC / Fixed	100W	V1: 2.7 A V2: 7.0 A	V1: < 200 mVpp; V2: < 80 mVpp	4000µF	< 1000ms @ 100% load 25°C [77°F] and typical line input	> 15ms @ 115VAC, >80ms @ 230VAC with 100W load	V1: < 30ms, V2: < 20ms @ 100% load 25°C [77°F]	82%

RHINO Panel Mount Power Supply Specifications PSS Series

General Specifications						
Output Line Regulation	<0.5% typical @ 85–264 VAC input, 100% load					
Output Load Regulation	<1% typical @ 85–264 VAC input, 0-100% load					
Overload/Short Circuit Protection	>150% of total rated output power, hiccup mode, non-latching, auto-recovery)					
Overvoltage Protection	V1: <32.4 VDC max., V2: 6.75 VDC max.], hiccup mode, non-latching [auto recovery]					
Case Cover	Aluminium [Al1100]					
Signals	Green LED DC OK					
MTBF	>700,000 hrs.					
Noise	Sound pressure level [SPL] <40dBA					
Cooling	Convection					
Input/Output Terminal	7-Pin rated 300V/15A]					
Shock Test	30g half sine, 3 times per direction, 6 directions, per IEC60068-2-27					
Vibration	10 to 150Hz, 5g, 20 min. each axis per IEC60068-2-6					
Operating Temperature	-10 to 70°C* [14 to158°F]					
Storage Temperature	-25 to 85°C [-13 to 185°F]					
Humidity at +25 °C [77°F], no condensation	<95% RH non-condensing					

* Operating to 70°C [158°F] possible with a linear derating to half power from 50 to 70°C [122 to 158°F]

Safety and Agency Approvals						
EMC / Emissions	FCC Title 47, Class B/EN 55032;CISPR32, Class B					
Immunity	EN 61000-4-2,1995; EN 61000-4-3,1998; EN 61000-4-4,1995; IEC61000-4-5,1995; EN 61000-4-6,1996; EN 61000-4-8 or IEC61000-4-12 or IEEE C62.41; EN 61000-3-2,1994					
Voltage Dips	Conform to EN 61000-4-11					
Galvanic Isolation	Input to Output : 3 KVAC, Input to Ground : 1.5 KVAC, Output to Ground : 0.5 KVAC					
Approvals	UR/cUR recognized to UL60950-1 File no. E198298; CB test certificate and report to IEC60950-1, CE [EMC and Low Voltage directive]					
RoHS Compliant	Yes					

Additional Data								
	Wire Size	e / Torque						
Part Number	Input	Output	Terminal Block Type	Chassis Mounting Torque	Drawing Link			
<u>PSS0524-100</u>	0.82-2.08 mm² (AWG 18-14) / 1.3 Nm (11.3 in-lb)	0.82-2.08 mm² (AWG 18-14) / 1.3 Nm (11.3 in-lb)	Fixed screw terminals	0.4–0.8 N•m [3.5–7 lb•in]	PDF			

1-800-633-0405 RHINO Panel Mount Power Supplies PSS-S Series



Overview

AutomationDirect's RHINO PSS-S low profile, panel mount, power supplies accept a universal AC input and feature a highly efficient convection cooling construction that operates from -30°C to 70°C [-22 to 158°F].

Features

- Universal AC input voltage range 90–264 VAC
- Adjustable output voltage
- No load power consumption <0.3 W
- Low profile design
- Overload, overvoltage and thermal protection
- Output voltage status LED
- Rugged aluminum housing, screw mounts in three different orientations
- Wide operating temperature -30 to 70°C (-40°C cold start) [-22 to 158°F]
- 3-year warranty



Input Specifications											
Part Number	Price	Input Voltage Range	Input Frequency Range	Input Current	Max. Inrush Current (cold start)	Leakage Current	*Recommended Circuit Breaker				
<u>PSS12-035-S</u>	\$14.50			0.7 A typ. @ 115VAC, 0.42 A typ. @ 230VAC	45A typ. @ 230VAC		10A "B" Curve				
<u>PSS12-050-S</u>	\$16.50			0.95 A typ. @ 115VAC, 0.6 A typ. @ 230VAC	45A typ. @ 230VAC		16A "B" Curve				
<u>PSS12-100-S</u>	\$22.00	00 264 1/4 C	47 00 11	47 00 11	47 00.11	47 0011-	47 6211-	1.9 A typ. @ 115VAC, 1.2 A typ. @ 230VAC	55A typ. @ 230VAC	< 0.5 m A @ 240\/AC	20A "B" Curve
<u>PSS24-035-S</u>	\$14.50	90 - 264 VAC	47 - 03 HZ	0.7 A typ. @ 115VAC, 0.42 A typ. @ 230VAC	45A typ. @ 230VAC	< 0.5 IIIA @ 240VAC	10A "B" Curve				
<u>PSS24-050-S</u>	\$16.50		-	0.95 A typ. @ 115VAC, 0.6 A typ. @ 230VAC	45A typ. @ 230VAC	_	16A "B" Curve				
<u>PSS24-100-S</u>	\$22.00			1.9 A typ. @ 115VAC, 1.2 A typ. @ 230VAC	55A typ. @ 230VAC		20A "B" Curve				

*Note: Input circuit breaker is based on Input and Inrush current. Defined Inrush is based on cold start at 25°C.

	Output Specifications																		
Part Number	Output Voltage (Vnom) / Adjustment Range	Output Power	Output Current	Ripple and Noise (20MHz)	Startup with Capacitive Loads	Start-Up Time	Hold-Up Time	Rise Time	Efficiency										
<u>PSS12-035-S</u>		35W	3A	< 120 mVpp		1,000ms typ. @ 115VAC	16ms typ. @ 115 VAC, 70ms typ. @ 230 VAC		86.0% typ.										
<u>PSS12-050-S</u>	10.8–13.2 VDC	50W	4.2 A	@ 0 to 70°C 360 mVpp typ. @ -30 to 0°C	@ 0 to 70°C 360 mVpp typ. @ -30 to 0°C < 150 mVpp @ 0 to 70°C 450 mVpp	@ 0 to 70°C 360 mVpp typ.	@ 0 to 70°C 360 mVpp typ.	@ 0 to 70°C 360 mVpp typ.	@ 0 to 70°C 360 mVpp typ.	@ 0 to 70°C 360 mVpp typ.	@ 0 to 70°C 360 mVpp typ.	@ 0 to 70°C 360 mVpp typ.	@ 0 to 70°C	@ 0 to 70°C 360 mVpp typ.		500ms typ. @ 230VAC	12ms typ. @ 115 VAC, 60ms typ. @ 230 VAC		85.0% typ.
<u>PSS12-100-S</u>		100W	8.5 A			@ -30 to 0°C	500ms typ. @ 115VAC & 230VAC	9ms typ. @ 115 VAC, 42ms typ. @ 230 VAC	30ms typ. @ 115VAC &	87.5% typ.									
<u>PSS24-035-S</u>		35W	1.5 A	< 150 mVpp @ 0 to 70°C			1,000ms typ. @ 115VAC	16ms typ. @ 115 VAC, 70ms typ. @ 230 VAC	230VAC	88.5% typ.									
<u>PSS24-050-S</u>	21.6–26.4 VDC	50W	2.2 A				500ms typ. @ 230VAC	12ms typ. @ 115 VAC, 60ms typ. @ 230 VAC		88.0% typ.									
<u>PSS24-100-S</u>		100W	4.5 A	@ -30 to 0°C		500ms typ. @ 115VAC & 230VAC	9ms typ. @ 115 VAC, 42ms typ. @ 230 VAC		90.0% typ.										

1-800-633-0405 For the latest prices, RHINO Specifications PSS-S Series

General Specifications						
Output Line Regulation	± 0.5% (@ 115VAC & 230VAC input)					
Output Load Regulation	± 0.5% (@ 115VAC & 230VAC input)					
Overload/Short Circuit Protection	110-175% of rated load current, Hiccup Mode, Non-Latching (Auto-Recovery when the fault is removed)					
Overvoltage Protection	PSS12 - 13.2 V - 17.4 V, SELV Output, Latch Mode PSS24 - 26.4 V - 33.6 V, SELV Output, Latch Mode					
Case Chassis / Cover	Aluminum / SGCC (Galvanized Steel)					
Signals	Green LED (DC OK)					
MTBF	> 700,000 hrs as per Telcordia SR-332 I/P: 230 Vac, O/P: 100% Load, Ta: 25°C)					
Noise	Sound pressure level (SPL) < 25 dBA					
Cooling	Convection					
Terminal	M3.5 x 5 Pins (Rated 300V / 20A)					
Shock Test	Non-Operating IEC 60068-2-27, Half Sine Wave: 50G for a duration of 11ms, 3 shocks for each 3 directions Operating IEC 60068-2-27, Half Sine Wave: 10G for a duration of 11ms, 3 shock for each 3 directions.					
Vibration	Non-Operating IEC 60068-2-6, Random: 5Hz to 500Hz (2.09G); 20 min per axis for all X, Y, Z direction Operating IEC 60068-2-6, Sine Wave: 20Hz to 500Hz (5G); 10 min per cycle, 60 min for each axis (X, Y, Z)					
Operating Temperature	-30 to 70°C (-40°C Cold Start) [-22 to 158°F]					
Storage Temperature	-40 to 85°C [-40 to 185°F]					
Humidity	20 to 90% RH (Non-Condensing)					

Safety and Agency Approvals					
EMC / Emissions	EN 55032				
Immunity	EN 55035, IEC 61000-4-2, IEC 61000-4-3, IEC 61000-4-4, IEC 61000-4-5, IEC 61000-4-6, IEC 61000-4-8				
Voltage Dips	Conform to IEC 61000-4-11				
Galvanic Isolation	Input to output 4.0 KVAC, Input to Ground 2.0 KVAC, Output to Ground 1.25 KVAC				
Approvals	cURus File: E508040, UL 62368-1, CAN/CSA C22.2 No. 62368-1 CB scheme: IEC 62368-1, IEC 60335-1, IEC 61558-1/-2-16 CE: In conformance with EMC Directive 2014/30/EU and Low Voltage Directive 2014/35/EU				

To obtain the most current agency approval information, see the Agency Approval Compliance & Certifications Checklist section on the specific part number's web page.

Additional Data									
	Wire Size / Torque					Drawing			
Part Number	Input	Output	Terminal Block Type	Chassis Mounting Torque	Weight	Link			
<u>PSS12-035-S</u>		0.82-3.31 mm² [AWG 18-12] 0.78 N•m [6.94 lb•in]	M3.5 x 5 Pins (Rated 300V / 20A)		0.165 kg [0.363 lb]	<u>PDF</u>			
<u>PSS12-050-S</u>				0.39–0.69 N•m [3.47–6.08 lb•in]	0.176 kg [0.389 lb]	<u>PDF</u>			
<u>PSS12-100-S</u>	0.82-3.31 mm² [AWG 18-12]		M3.5 x 7 Pins (Rated 300V / 20A)		0.285 kg [0.628 lb]	<u>PDF</u>			
<u>PSS24-035-S</u>	0.78 N•m [6.94 lb•in]		M3.5 x 5 Pins (Rated 300V / 20A)		0.165 kg [0.363 lb]	<u>PDF</u>			
<u>PSS24-050-S</u>					0.176 kg [0.389 lb]	<u>PDF</u>			
<u>PSS24-100-S</u>			M3.5 x 7 Pins (Rated 300V / 20A)		0.285 kg [0.628 lb]	<u>PDF</u>			

1-800-633-0405 **RHINO DIN Rail Power Supplies PSB Series**

Single-Phase Input Overview

AutomationDirect's RHINO PSB series of DIN rail power supplies is perfect for applications that require a basic DC voltage power supply. These low-cost power supplies offer high performance and reliability without all the additional features of higher-cost full-featured power supplies. The following models in the RHINO PSB series are available with universal single-phase input and with output voltages of 24VDC or 48VDC from 60 to 480 Watts. They feature removable terminal blocks, high efficiencies, conformal coated circuit boards, and approval for Class 1, Division 2 hazardous locations. The rugged plastic and aluminum housings easily install with integral 35mm DIN rail mounting adapters. These high-quality power supplies include overload, overvoltage and thermal protection, and are UL 508 listed, UL 60950 recognized, CSA certified, CE marked and RoHS compliant.

PSB48-480S is perfect for Stepper Drives, like our STP-DRV-6575, STP-DRV-4850 or STP-DRV-80100

Features

- Universal input voltage, single-phase 120/240 VAC or 120-375 VDC
- 24VDC or 48VDC outputs, 60 to 480 Watts
- Adjustable output voltage
- Rugged plastic or aluminum housings with integral 35mm DIN rail mounting adapters
- Output voltage status LED
- NEC Class2 (Model PSB24-100-N & PSB24-060S-P only)
- Removable terminal blocks (except <u>PSB24-060S-P</u>, <u>PSB24-100-N</u>, PSB24-480S and PSB48-480S) with IP20 protection
- · Conformal coated circuit board for protection against demanding environments
- Overload, overvoltage and thermal protection
- UL 508 listed, UL 60950 recognized, CSA certified, approved for Class I (except PSB24-100-N), Division 2 hazardous locations CE marked and RoHS compliant
- 3-year warranty





	Input Specifications																		
Part Number	Price	Weight kb [lb]	Housing	Input Voltage	Input Frequency Range	Max. Input Current	Inrush Current Limitation I2t @ 77°F (+25°C) typ.	Leakage Current	Recommended Circuit Breaker	Hold-Up Time at Nominal Load (Typ.) (Mains Buffering) (100% load, 25°C)	Turn-on Time								
<u>PSB24-060S-P</u>	\$45.00	0.33 [0.73]	Plastic			<1.5 A @ 100VAC	<40A @ 115VAC, <80A @ 230VAC	<0.5mA @ 240VAC	16A "B" Curve	>20ms @ 115VAC >125ms @	<3 sec.								
<u>PSB24-060S</u>	\$54.00	0.37 [0.82]		85–264	85–264	85–264	85–264	85–264	85–264	85–264	85–264	85–264		<1.4 A @ 115VAC, <0.8 A @ 230VAC	<20A @ 115VAC, <35A @ 230VAC	<1mA @ 240VAC	8A "B" Curve	230VAC	
<u>PSB24-100-N</u>	\$81.00	0.60 [1.32]											85–264	85–264		<1.00A @ 115VAC, <0.53A @ 230 VAC	<30A @ 115VAC <60A @ 230VAC	<0.5mA @ 24VAC	13A "B" Curve
<u>PSB24-120S</u>	\$97.00	0.72 [1.59]		VAC [DC input range		<2.2 A @ 115VAC, <1.2 A @ 230VAC		<1mA@	10A <1mA @ "B" Curve	>20ms @ 115VAC >115ms @ 230VAC									
<u>PSB24-240S</u>	\$161.00	1.10 [2.43]		120–375 VDC]	47–63 Hz [0Hz @ DC	<2.5 A @ 115VAC, <1.3 A @ 230VAC		240VAC	8A "B" Curve	>20ms @ 115VAC									
<u>PSB24-480S</u>	\$248.00	1.37 [3.02]	Aluminum	Approved for	mpad	<5A @ 115VAC, <3A @ 230VAC		<3mA @ 240VAC	6A "B" Curve	& 230VAC									
<u>PSB48-120S</u>	\$97.00	0.72 [1.59]		100-240 VAC only		<2.2 A @ 115VAC, <1.1 A @ 230VAC	<35A @ 115VAC, <35A @ 230VAC	<1mA @	8A "B" Curve	>20ms @ 115VAC >50ms @ 230VAC	<1 sec.								
<u>PSB48-240S</u>	\$161.00	0.97 [2.14]				<2.5 A @ 115VAC, <1.3 A @ 230VAC		240VAČ	8A "B" Curve	>20ms @ 115VAC & 230VAC									
<u>PSB48-480S</u>	\$219.00	1.37 [3.02]				<5A @ 115VAC, <3A @ 230VAC		<3mA @ 240VAC	10A "B" Curve	>20ms @ 115VAC & 230VAC	<1.5 sec.								

www.automationdirect.com

RHINO DIN Rail Power Supplies PSB Series

	Output Specifications									
Part Number	Output Voltage (Vnom) / Adjustment Range	Output Power	Output Current	Ripple and Noise [20 MHz]	Startup with Capacitive Loads Max	Derating	Max. Power Dissipation Idling/Nominal Load Approx.	Efficiency [Typ @ 115VAC]	MTBF	
<u>PSB24-060S-P</u>	24VDC ±2%/22–28 VDC [maximum power ≤60W]	60W	2.5 A	<240mVpp @ 25°C	8,000µF	>50°C de-rate power by 2.5%/°C >70°C de-rate power by 4%/°C	8W	88%	>800,000 hrs.	
<u>PSB24-060S</u>	24VDC ±2%/24–28 VDC [maximum power ≤60W]					>50°C de-rate power by 2.5%/°C	7.4 W	90%	>1,000,000 hrs.	
<u>PSB24-100-N</u>	24VDC ±2%/22–24 VDC [maximum power ≤91.2W]	91.2 W	3.80A	<150mVpp @ 25°C	8,000µF	>50°C de-rate power by 2.5%/°C > 70°C de-rate power by 4%/°C	12.4 W	88%	>800,000	
<u>PSB24-120S</u>	24VDC ±2%/24–28 VDC [maximum power ≤120W]	120W	5A		10.000.uE	>50°C de-rate power by 2.5%/°C	14.8 W	89%		
<u>PSB24-240S</u>	24VDC ±2%/24–28 VDC [maximum power ≤240W]	240W	10A				26.5 W	90%		
<u>PSB24-480S</u>	24VDC ±2%/24–28 VDC [maximum power ≤480W]	480W	20A	<150mVpp @ 25°C	10,000μ1	>50°C de-rate power by 2.5%/°C >70°C de-rate power by 5%/°C	47W	91%	>500,000 hrs.	
<u>PSB48-120S</u>	48VDC ±1%/48–56 VDC [maximum power ≤120W]	120W	2.5 A	<200mVpp @ 25°C	6,500µF	>50°C de-rate power by	14.8 W	90%	>800,000 hrs.	
<u>PSB48-240S</u>	48VDC ±1%/48–56 VDC [maximum power ≤240W]	240W	5A	<200mVpp @ 85VAC to 265VAC		2.5%/°C	25W	90%		
<u>PSB48-480S</u>	48VDC ±1%/48–56 VDC [maximum power ≤480W]	480W	10A	<200 mVpp @ 85VAC to 264VAC	10,000µF	>50°C de-rate power by 2.5%/°C >70°C de-rate power by 5%/°C	46.5 W	91%	>500,000 hrs.	

General Specifications							
Output Line Regulation	<0.5% @ 85–264 VAC input, 100% load						
Output Load Bosylation	<1% @ 85–264 VAC input, 0-100% load						
	PSB24-100-N: < 1% at -25°C to +25°C < 2% at +25°C to +50°C <1% typ. @ 85–264 VAC input, 0-100% load						
Parallel Operation	PSB60-REM20S / PSB60-REM40S or with ORing Diode						
Case Cover	Aluminium or Plastic [Polycarbonate] for P Series						
Signals	Green LED DC OK						
Humidity at 25°C [77°F], no condensation	<95% RH [non-condensing]						
Shock (Non-Operating)	IEC 60068-2-27, 30G [300m/S ²] for a duration of 18ms, 1 time per direction, 2 times in total						
Vibration (Non-Operating)	IEC60068-2-6, 10Hz to 500Hz @ 30 m/S2 [3G peak]; 60 min per axis for all X, Y, Z direction						
Environmental Air	No corrosive gases permitted (PSB24-100-N) Conformal coating on PCBA to protect against chemical and dust pollutants						
Pollution Degree	2						
Climatic Class	3K3 according to EN 60721						

Series Certification and Standards						
Electrical Equipment of Machines	IEC60204-1 [over voltage category III]					
Electronic equipment for use in electrical power installations	EN62477-1 / IEC62103					
Safety Entry Low Voltage	PELV [EN60204], SELV [EN60950]					
Industrial Control Equipment	UL/cUL listed to UL508 and CSA C22.2 No. 107.1-01 File no. E197592 CSA to CSA C22.2 No. 107.1-01					
Hazardous Location	cCSAus to CSA C22.2 No. 213-M1987, ANSI / ISA 12.12.01:2007 Class I, Division 2, Group A,B,C,D T4, Ta = 25 to +80°C (<u>PSB24-060S-P, PSB24-060S, PSB24-120S, PSB24-240S, PSB48-120S, PSB48-240S</u>); 25 to +75°C (<u>PSB24-480S, PSB48-480S</u>) Vertical: > +50°C derating, File no. 249074					
Class 2 Power Supply	UR/cUR Class 2 power supply recognized to UL1310 and CSA C22.2 No. 223 File no. E198298 (PSB24-060S-P and PSB24-100-N only)					
CE	CE					

To obtain the most current agency approval information, see the Agency Approval Compliance & Certifications Checklist section on the specific part number's web page.

1-800-633-0405 **RHINO DIN Rail Power Supplies PSB Series**

Safety and Protection								
Transient surge voltage protection	V	aristor						
Overvoltage	PSB24-060S-P, PSB24-060S, PSB24-100-N, PSB24-120S, PSB24-240S, PSB24-480S: <32V, SELV Output, hiccup mode, non-latching [auto-recovery]	PSB48-120S, PSB48-240S, PSB48-480S: <57V, SELV Output, hiccup mode, non-latching [auto-recovery]						
Overload / Overcurrent	PSB24-060S-P, PSB24-060S, PSB24-100-N, PSB24-120S, PSB24-240S, PSB24-480S: >150% of rated load current, hiccup mode, non-latching [auto-recovery].							
	PSB24-060S-P: 110-150% of rated load current, hiccup mode, non-latching [auto-recovery].							
Isolation Voltage: Input/output (type test/routine test) Input/GND (type test/routine test) Output/GND (type test/routine test)	4 kVA 1.5 kVA 1.5 kVA	C / 3 kVAC C / 1.5 kVAC C / 500 VAC						
Protection Degree		IP20						
Safety Class	Class I with	GND connection						

	Additional Data										
	Wire Size / 1	Forque*									
Part Number	Input	Output	Terminal Block Type	Ambient Operating Temperature**	Storage Temperature	Drawing Link					
<u>PSB24-060S-P</u>	0.52–5.3 mm² [A\ 0.45 Nm [3.9	NG 20–10] / 96 lb-in]	Fixed screw terminals	-25 to 80°C [-13 to 176°F]	-25 to 80°C [-13 to 176°F]	<u>PDF</u>					
<u>PSB24-060S</u>	0.52–3.3 mm² [A\ 0.46 Nm [4.0	NG 20–12] /)5 lb-in]	Removable screw terminals			<u>PDF</u>					
<u>PSB24-100-N</u>	0.82–3.3 mm² [AWG 18–12] / 0.91 Nm [8.1 lb-in]	0.82–3.3 mm² [AWG 18–12] / 0.61 Nm [5.4 lb in]	Fixed screw terminals	-25 to 80°C		<u>PDF</u>					
<u>PSB24-120S</u>	0.52–3.3 mm² [A\ 0.46 Nm [4.0	NG 20–12] /)5 lb-in]	Removable screw	Cold start at -40°C [-40°F]		<u>PDF</u>					
<u>PSB24-240S</u>	1.3–2.1 mm² [AV 0.46 Nm [4.0	VG 16–14] /)5 lb-in]	terminals		-40 to 85°C [-40 to 185°F]	<u>PDF</u>					
<u>PSB24-480S</u>	0.82–5.3 mm² [AWG 18–10] / 0.45 Nm [3.96 lb-in]	3.3–5.3 mm² [AWG 12–10] / 0.45 Nm [3.96 lb-in]	Fixed screw terminals	-25 to 75°C [-13 to 176°F]		<u>PDF</u>					
<u>PSB48-120S</u> PSB48-240S	0.52–3.3 mm² [A\ 0.46 Nm [4.0	WG 20–12] /)5 lb in]	Removable screw terminals	-25 to 80°C [-13 to 176°F]		PDF PDF					
PSB48-480S	0.82–5.3 mm² [AWG 18–10] / 0.45 Nm [3.96 lb-in]	1.3–5.3 mm² [AWG 16–10] / 0.45 Nm [3.96 lb-in]	Fixed screw terminals	-25 to 75°C [-13 to 176°F]		PDF					

*Stripping length 7 mm [0.28 in] ** See output specifications for temperature derating

1-800-633-0405 **RHINO DIN Rail Power Supplies PSB Series**

Three-Phase Input Overview

AutomationDirect's RHINO PSB series of DIN rail threephase input power supplies is perfect for applications that require a basic DC voltage power supply. These low cost power supplies offer high performance and reliability without all the additional features of higher cost full-featured power supplies. The three-phase input eliminates the need for a separate step down transformer and the output of 24VDC is available from 60 to 960 Watts. The rugged aluminum housings easily install with integral 35mm DIN rail mounting adapters. These high-quality power supplies include overload, overvoltage and thermal protection, and are UL 508 listed, UL 60950 recognized, CSA certified, CE marked and RoHS compliant. Units are covered by a three year warranty.



PSB 3-Phase Series Input Specifications												
Part Number	Price	Weight kg [lb]	Housing	Input Voltage	Input Frequency Range	Max. Input Current	Inrush Current Limitation I2t @ 77°F [+25°C] typ.	Leakage Current	Recommended Circuit Breaker	Hold-Up Time at Nominal Load [Typ] (Mains Buffering)	Turn-on Time	
<u>PSB24-060S-3</u>	\$76.00	0.66				<0.3 A / Phase @ 400VAC and <0.25 A / Phase @ 500VAC	<30A @ 400VAC & 500VAC @ 25°C [With 3Ph AC source capability up to 3KVA] <55A @ 400VAC & 500VAC @ 25°C [With 3Ph AC source capability up to 18KVA]					
<u>PSB24-120S-3</u>	\$98.00	[1.46]						<0.5 A / Phase @ 400VAC and <0.4 A / Phase @ 500VAC	<30A @ 400VAC & 500VAC @ 25°C [With 3Ph AC source capability up to 3KVA] <60A @ 400VAC & 500VAC @ 25°C [With 3Ph AC source capability up to 18KVA]			>20ms @ 3 x 400VAC.
<u>PSB24-240S-3</u>	\$163.00	0.89 [1.96]	Aluminum	uminum UL/CSA approved to 500VAC	47–63 Hz	<0.75 A / Phase @ 400VAC and <0.65 A / Phase @ 500VAC	<40A @ 400VAC & 500VAC @ 25°C [With 3Ph AC source capability up to 3KVA] <60A @ 400VAC & 500VAC @ 25°C [With 3Ph AC source capability up to 18KVA]	<3.5 mA	3 x circuit breakers 16A "B" Curve	>40ms @ 3 x 500VAC	<1000ms @ 100% load [25°C] and typical line input	
<u>PSB24-480S-3</u>	\$232.00	1.35 [2.98]				<0.95 A / Phase @ 400VAC and <0.75 A / Phase @ 500VAC	<50A @ 400VAC & 500VAC @ 25°C [With 3Ph AC source capability up to 3KVA] <70A @ 400VAC & 500VAC @ 25°C [With 3Ph AC source capability up to 18KVA]					
<u>PSB24-960S-3</u>	\$343.00	2.6 [5.73]				1.7 A Max / Phase	<50A @ 500VAC @ 25°C	<3mA @ 575VAC		>20ms @ 3 x 400VAC & 3 x 500VAC		

RHINO DIN Rail Power Supplies PSB Series

	Output Specifications										
Part Number	Output Voltage (Vnom) / Adjustment Range	Output Power	Output Current	Ripple and Noise [20 MHz]	Startup with Capacitive Loads	Derating	Max Power Dissipation Idling / Nominal Load Approx.	Efficiency [Typ 3 @ 400VAC and 500VAC]	MTBF		
<u>PSB24-060S-3</u>	24–28 VDC [Max power ≤60W]	60W	2.5 A [60W Max]	<150mVpp at 320VAC to 600VAC input					9.8 W	86%	>500,000
<u>PSB24-120S-3</u>	24–28 VDC [Max power ≤120W]	120W	5A [120W Max]			>50°C de-rate power by 2.5%/°C	16.5 W	88%	hrs		
<u>PSB24-240S-3</u>	24–28 VDC [Max power ≤240W]	240W	10A [240W Max]		600VAC input	Max 10,000µF	>70°Ć de-rate power by 5%/°C	26.7 W	92%		
<u>PSB24-480S-3</u>	24–28 VDC [Max power ≤480W]	480W	20A [480W Max]				53W	91%	>300,000 hrs		
<u>PSB24-960S-3</u>	24–28 VDC [Max power ≤960W]	960W	40A [960W Max]	<240mVpp at 320VAC to 575VAC input		>50°C de-rate power by 2.5%/°C	94W	92%			

General Specifications						
Output Line Regulation	<0.5% typ. @ 320 to 600VAC input, 100% load					
Output Load Regulation	<1% typical with rated input, 0 to 100% load					
Parallel Operation	PSB60-REM20S* / PSB60-REM40S or with ORing Diode					
Case Cover	Aluminium [AI5052]					
Signals	Green LED DC OK					
Humidity at +25°C [77°F], no condensation	<95% RH [non-condensing]					
Shock	IEC 60068-2-27					
Vibration (Non-operating)	IEC 60068-2-6					
Pollution Degree	2					
Climatic Class	3K3 according to EN 60721					

* Does not apply to the PSB24-960S-3

Certification and Standards						
EMC / Emissions	FCC Title 47, Class B / EN55032, CISPR32, CISPR11, Class B					
Immunity	EN61000-4-2, 1995; EN61000-4-4, 1995; EN61000-4-5, 1995; IEC61000-4-12 or IEEE C62.41; EN61000-4-3, 1998; EN61000-4-8; EN61000-4-6, 1996					
Voltage Dips	EN61000-4-11					
Approvals	UL/cUL listed to UL508 and CSA C22.2 No. 107.1-01 File no. E197592, CSA to CSA C22.2 No. 107.1-01 File no. 249074, UR/cUR recognized to UL60950-1 and CSA C22.2 No. 60950-1 File no. E198298. CE (EMC and Low Voltage directive)					

To obtain the most current agency approval information, see the Agency Compliance & Certifications Checklist section on the specific part number's web page.

Safety and Protection							
Transient Surge Voltage Protection	Varistor						
Overload/Short Circuit Protection	> 150% of rated load current, auto recovery [hiccup mode]						
Overvoltage Protection	<32V, w10%, SELV output, non-latching [autorecovery]						
Isolation Voltage: Input/output Input/GND Output/GND	4 KVac 1.5 KVac 1.5 KVac						
Protection Degree	IP20						
Safety Class	Class I with GND connection						

1-800-633-0405 **RHINO DIN Rail Power Supplies PSB Series**

Additional Data						
Part Number	Wire Size / Torque*		Terminal Block Type	Ambient Operating	Storage	Drawing
	Input	Output		Temperature**	Temperature	Link
<u>PSB24-060S-3</u>	0.82–3.3 mm² [AWG 18–12] /	0.82–3.3 mm² [AWG 18–12] /				PDF
<u>PSB24-120S-3</u>	0.92 Nm [8.1 lb-in]	0.61 Nm [5.4 lb-in]				<u>PDF</u>
<u>PSB24-240S-3</u>	0.82–3.3 mm² [AWG 18–12] / 0.92 Nm [8.1 lb-in]	1.3–3.3 mm² [AWG 16–12] / 0.61 Nm (5.4 lb-in)	Fixed screw terminals	-25 to 80°C [-13 to 176°F]	-25 to 85°C	<u>PDF</u>
<u>PSB24-480S-3</u>	0.82–8.4 mm² [AWG 18–8] /	3.3–5.3 mm² [AWG 12–10] /				<u>PDF</u>
<u>PSB24-960S-3</u>	0.92 Nm [8.1 lb-in]	0.92 Nm [8.1 lb-in]		-25 to 65°C [-13 to 149°F]		<u>PDF</u>

*Stripping length 7 mm [0.28 in] or use suitable lug to crimp

** See output specifications for temperature derating

PSB24-060S-3 PSB24-120S-3

Wiring Connection				
Inj	out	Out	put	
L1	Line 1	+	Out +	
L2	Line 2	+	Out +	
L3	Line 3	-	Out -	
Ŧ	AC Ground	-	Out -	

PSB24-480S-3

Wiring Connection			
Inj	out	Out	tput
L1	Line 1	+	Out +
L2	Line 2	+	Out +
L3	Line 3	-	Out -
Ŧ	AC Ground	-	Out -

PSB24-240S-3

Wiring Connection			
Input Output			tput
L1	Line 1	+	Out +
L2	Line 2	+	Out +
L3	Line 3	-	Out -
Ŧ	AC Ground	-	Out -

PSB24-960S-3

Wiring Connection			
Inj	out	Out	put
L1	Line 1	+	Out +
L2	Line 2	+	Out +
L3	Line 3	-	Out -
Ŧ	AC Ground	-	Out -

Redundancy Module Overview

The RHINO PSB60-REM series redundancy modules are used with two RHINO PSB series power supplies in parallel to create redundancy to help prevent costly downtime due to power supply failure. The redundancy module decouples the outputs of the two connected power supplies so that in case of failure, one power supply cannot overload the other. The modules can handle power supply voltages from 22 to 60VDC and provides alarm relay contacts for remote monitoring.

Features

- Provides redundancy and parallel operation of two RHINO PSB power supplies
- Wide input and output range 22–60 VDC
- Input voltage OK LED and relay alarm indication
- · Corrosion resistant aluminum housing • Approved for use in Class I, Division 2 hazardous locations
- 3-year warranty





Redundancy Modules			
Part Number	PSB60-REM20S	PSB60-REM40S	
Price	\$45.00	\$55.00	
Weight kg [lb]	0.375 [0.83]	0.515 [1.14]	
Redundancy Module Input Specification	IS IS		
Nominal Input Voltage	24 / 4	48 VDC	
Voltage Range	22-6	50 VDC	
Nominal Current	20A max	40A max	
Input Voltage Alarm/Relay Contacts	24V system: both Vin1 & Vin2 >18 48V system: both Vin1 & Vin2 >36	V ± 5% or < 30V max. relay contacts V ± 5% or <60V max. relay contacts	
Input Voltage LED Operation	The LED will turn on when the Vin1 & Vin2 >18V± 5% (for 24V syst systems) or not more than 60V (for 48V systems), the relay contact tur	tems) or >36V \pm 5% (for 48V system) and not more than 30V (for 24V s will be closed. If Vin1 & Vin2 is under or over this range, the LED will n off	
Redundancy Module Output Specification	ns		
Nominal Output Voltage UN / Tolerance	Vin-0.6	65V [Typ]	
Nominal Current	20A max	40A max	
Derating above +50°C	>50°C [2.5% / K]		
Short Circuit / Over Load Limit	<25A	<50A	
Efficiency	>97% typical		
Note: The overload condition must be co than 50A (for 40A module)	ntrolled by the power supply units in parallel; The limit of input c	urrent should not be more than 25A (for 20A module) or not more	
Redundancy Module Certification / Stan	ndards		
Electrical Equipment of Machines	IEC60204-1 [over	voltage category III]	
Electrical Safety (IT equipment)	UR/cUR recognized to UL60950-1 File no. E198298, CB test certificate and report to IEC60950-1 and CE		
Industrial Control Equipment	UL/cUL recognized to UL508 and CS	A C22.2 No. 107.1-01File no. E197592	
Hazardous Location	cCSAus to CSA C22.2 No. 213-M1987, ANSI / ISA 12.12.01:2007 [Class I, Division 2, Group A,B,C,D T4, Ta = -40 to +80°C (> +50°C derating)], File no. 249074		
Electronic Equipment For Use in Electrical Power Installations	EN50178 / IEC62103		
Safety Entry Low Voltage	PELV [EN60204], SELV [EN60950]		
RoHS Compliant	Yes, RoHS direct	ive, WEEE directive	
Protection Against Electric Shock	DIN 57100-410		

Specifications (continued)		
Isolation Voltage: Input / PE Output / PE	1.5 KVAC / 1.5 KVAC 1.5 KVAC / 1.5 KVAC	
Degree of Protection	IP20	
Class of Protection	Class II with PE connection	
MTBF	>800,000 hrs. per BELL CORE STD or IEC61709	
Type of Housing	Aluminum [AL1100F]	
	Environmental Specifications	
Humidity at +25°C, no condensation	<95% RH	
Vibration	10Hz to 500Hz @ 30 m/S2 [3G peak]; displacement of 0.35 mm; 60 min per axis for all X, Y, Z direction. Refer to IEC 60068-2-6. Note: all figures quoted are amplitudes [peak values]	
Shock (in all directions)	IEC60068-2-27, 30G [300m/s2] for duration 18ms 1 Shock in 2 directions tested with fixture with EUT mounted on DIN rail in vertical and horizontal position	
Pollution Degree	2 according to EN50178	
Climatic Class	3K3 according to EN60721	

Additional Data						
Port Number	Wire Size / Torque*		Terminal Block Tuna	Ambient Operating	Storogo Tomporatura	Drawing
Part Number	Input	Output	тегіппа віоск туре	Temperature**	Sioraye temperature	Link
PSB60-REM20S	3 3–5 3 mm² [AWG 12–10] /	3 3–5 3 mm² [AWG 12–10] /		-25 to 80°C	-25 to 85°C	PDF
PSB60-REM40S	0.72 Nm [6.3 lb-in]	0.72 Nm [6.3 lb-in]	Fixed screw terminals	[-13 to 176°F]	[-13 to 185°F]	PDF

*Stripping length 7 mm [0.28 in] or use suitable lug to crimp

** See output specifications for temperature derating

PSB60-REM20S PSB60-REM40S

Wiring Connection			
Input		0	utput
Vin1	Line 1	Vout+	Output +
Vin2	Line 2	Vout+	Output +
Com	Common	OK	Alarm Relay
		ОК	Alarm Relay

Redundancy Module Wiring



Parallel Operation

When 2 power supplies are connected in parallel, they can share the load if the following steps are taken.

- Step 1: Measure the output voltages at no load from Vin1 to Com of power supply 1 and Vin2 to Com of power supply 2. If the voltages are not the same, follow Step 2. If they are the same, skip to Step 3.
- Step 2: Adjust the output voltages, with the help of the adjustment pot on the power supply front panel marked as ADJUST, to the same level. For example, if power supply 1 is measuring 24.15 VDC and power supply 2 is measuring 24.25 VDC, adjust the output voltage of one to be the same as the other.
- Step 3: Connect the power supply to the end system load and measure the output voltages from Vin1 to Com of power supply 1 and Vin2 to Com of power supply 2. Ensure that the output voltages are the same even after the 2 power supplies are connected to load. If not, adjust them with the adjustment pot available on the front panel. A tolerance of $w \pm 25$ mV would be acceptable.

Note:

- 1) If the output voltage of any power supply is higher, it will take the initial load and share the maximum load.
- 2) If the output voltages are the same, then an equal load current sharing between the 2 power supplies can be achieved.

Buffer Module

The RHINO PSB24-BFM20S buffer module is a cost effective alternative to battery-based backup systems. Utilizing electrolytic capacitors the buffer module is maintenance free and will maintain the output voltage of a 24VDC power supply system for 250 msec minimum with a 20A load and 5 sec minimum with a 1A load. A switch is provided to select the voltage level to start buffering. An inhibit input is available for remote shutdown as well as output signals for remote stand-by and buffering mode indication. The module is housed in a corrosion-resistant aluminum chassis with IP20 terminals and conformal coated circuit board for protection against demanding environments.

Features

- · Corrosion-resistant aluminum housing
- Long minimum buffering time of 250ms @ 24V/20A
- · Units can be connected in parallel to increase buffering time
- Less than 30 second charging time locations
- P20 wiring terminals
- Overvoltage / Overcurrent / Short Circuit protections

3-year warranty



Buffer Module		
Part Number	PSB24-BFM20S	
Price	\$142.00	
Drawing Link	PDF	
Weight kg [lb]	0.76 [1.68]	
Buffer Module Input Specifications		
Nominal Input Voltage	24VDC	
Voltage Range	22.8 to 28.8 VDC [35VDC Max]	
Input Current	Charging mode: < 0.6 A; Discharging mode: 20A Max	
Input Power	2.5 W average	
Maximum Signal Input (Inhibit)	35V / 10mA	
Max Inrush Current	< 20A	
Charging Time	< 30sec	
Buffer Module Output Specifications		
Nominal Output Voltage	24VDC typ. [depends on V _{in}]	
Adjustment Range Of The Voltage	22 to 28VDC Switch = "Fix 22V" - Buffering starts if terminal voltage falls below 22V Factory Setting, Switch = "V _{in} - 1V" - Buffering starts if terminal voltage is decreased by >1V	
Maximum Output Voltage	35VDC	
Output Current	20A max	
Buffering Time	250ms Min @ 24V / 20A Load, 5sec Min @ 24V / 1A Load [Refer to Fig.1]	
Maximum Signal Output	35V / 10mA	
Signals	Inhibit Signal [I] - "Low" = shuts down buffer module Ready Signal [R] - "High" = buffer module is fully charged or in standby mode Buffering Signal [B] - "High" = Buffer module is discharging or in buffering mode Supply Voltage (+Vs) - Common +Vs, 35V Max	
Noise and Ripple (20MHz)	<200mVpp @ 25°C [77°F] during buffering mode	
Parallel Connection	Yes [requires PSB60-REM redundancy module]	
Series Connection	No	
Protective Device	Transient voltage suppressor [TVS] for signals	



Figure 1



Mechanical Specifications		
Case Cover	Aluminum	
LED Indicators	Green LED Off - Unit is discharged or Vin <22VDC Green LED On - Unit is fully charged	
Cooling System	Convection	
Terminal	Input / Output - M3 x 2 pins [Rated 300V / 30A] Signal - M3 x 5 pins [Rated 300V / 30A]	
Wire	Input / Output - AWG 12–10 [0.08–0.10 in]; Torque: 0.72 Nm [6.3 lb-in] Signal - AWG 24–10 [0.02–0.10 in]; Torque: 0.72 Nm [6.3 lb-in]	
	Environmental Specifications	
Operating Temperature	-25 to 75°C [-13 to 167°F]	
Storage Temperature	-25 to 85°C [-13 to 185°F]	
ower De-rating >70°C [158°F] de-rate power by 5% / °C		
Operating Humidity <95% RH [Non-Condensing]		
Dperating Altitude 2,500 Meters		
Shock Test (Non-Operating)	IEC60068-2-27, 30G [300m/S ²] for a duration of 18ms	
Vibration (Non-Operating)	IEC60068-2-6, 10 Hz to 500 Hz @ 30m/S2 [3G peak]; 60 min per axis for all X, Y, Z direction	
Pollution Degree	2	
	Protection Specifications	
Overvoltage	32V ± 10%	
Overload / Overcurrent	30A Max	
Short Circuit	No damage	
Penetration Protection	> 3.5 mm [eg. screws, small parts]	
Reverse Polarity Protection	Yes	
Degree of Protection	IP20	
Protection Against Shock	Class I with GND connection	

For the latest prices, please check AutomationDirect.com.

1-800-633-0405 **RHINO Power Supply Accessories PSB Series**

Reliability Specifications		
MTBF (at V _{in} -1V Mode)	>2,800,000 hrs. as per Telcordia SR-332 at Standby Mode [Buffer Module in Ready State]	
Expected Capacitor Life	10 years [Standby mode @ 40°C]	
	Safety Standards / Directives	
Electronic Equipment in Power Installations	EN50718 / IEC62103	
Electrical Safety (Information Technology Equipment)	UR/cUR recognized to UL60950-1 and CSA C22.2 No. 60950-1 File no. E198298, CB scheme to IEC60950-1	
Industrial Control Equipment	UL/cUL listed to UL508 and CSA C22.2 No. 107.1-01 File no. E197592, CSA to CSA C22.2 No. 107.1-01; File No. 249074	
Hazardous Location	cCSAus to CSA C22.2 No. 213-M1987, ANSI / ISA 12.12.01:2007 [Class I, Division 2, Group A,B,C,D T4, Ta = -25°C to +75°C (> +70°C derating)], File No. 249074	
CE	in conformance with EMC Directive 2004/108/EC and Low Voltage Directive 2006/95/EC	
Materials and Parts	RoHS Directive 2011/65/EU Compliant	
Galvanic Isolation	Input & Output to Ground - 1.5 KVAC Signal to Ground - 1.5 KVAC	
	EMC Specifications	
EMC / Emissions	CISPR32, EN55032, EN55011	
Component Power Supply for General Use	EN61204-3	
Immunity	EN55024, EN61000-6-2	
Electrostatic Discharge	EN61000-4-2	
Radiated Field	EN61000-4-3	
Fast Transient / Burst	EN61000-4-4	
Surge	IEC61000-4-5	
Conducted	EN61000-4-6	
Power Frequency Magnetic Fields	EN61000-4-8	
Voltage Dips	EN61000-4-11	
Low Energy Pulse Test (Ring Wave)	EN61000-4-12	

Note: Product intended to be used as Apparatus with AC-DC Power Supply, EMC compliance to be verified in correspondence to the connected units.

PSB24-BFM20S

Wiring Connection							
In	put		Output				
+	DC+	R	Ready				
-	DC+	В	Buffering				
I	Inhibit	+Vs	+ Voltage Supply				
		Ŧ	Ground				

For the latest prices, please check AutomationDirect.com.

1-800-633-0405 **RHINO Power Supply Accessories PSB Series**

	Buffering, Ready, and Inhibit Signal
Buffering Output Signal (B)	"High" = <u>PSB24-BFM20S</u> is discharging or in Buffering Mode
Ready Output Signal (R)	"High" = <u>PSB24-BFM20S</u> is fully charged or in Standby Mode
Inhibit Input Signal (I)	"Low" = Shuts down Buffer Module
Signal Voltage	+VS: 10–35 VDC
Maximum Signal Current	10mA
Isolation (Signal to Power)	1.5 KVAC





Buffer Module Operations

Example



Buffer Module Wiring



Parallelling of buffer units



Decoupling of buffered branches





Power Supplies PSR Series

Overview

AutomationDirect's RHINO PSR Series DIN rail industrial power supply features high power density and high efficiency. The series offers overcurrent protection in constant current mode, making it suitable for charging applications. Conformal coating is applied on the printed circuit board assembly (PCBA) to protect against dust and pollutants often found in harsh industrial environments. The series electromagnetic radiated and conducted emissions are compliant with heavy industrial Class B Emission standard and Immunity standard, and complies with environmental protection standards RoHS Directive.

Features

Ultra-slim design

• IP20

• 35mm DIN-rail mount

- Universal AC input voltage range
- Built-in constant current circuit for charging applications
- Long life electrolytic capacitor
- Built-in DC OK relay and LED indicator
- Conformal coating on PCBAs to protect against common dust and pollutants





PSR-24-120

PSR-24-240-3

Input Specifications								
Part Number	Price	Input Voltage Range	Input Frequency Range	Nominal Input Current	Inrush Current Limitation (+25°C cold start)	Leakage Current	Efficiency (@100% load)	Recommended Circuit Breaker
Single Phase Input								
<u>PSR-24-120</u>	\$69.00			1.2 A typ. @ 115VAC 0.6 A typ. @ 230VAC		< 0.5 mA @	90.5% typ. @ 115VAC 93.5% typ. @ 230VAC	
<u>PSR-24-240</u>	\$92.00	90-264 VAC	47–63 Hz	2.5 A typ. @ 115VAC 1.3 A typ. @ 230VAC	40A @ 230VAC	240 VAC	92.5% typ. @ 115VAC 94.5% typ. @ 230VAC	20A B Curve
<u>PSR-24-480</u>	\$149.00			4.7 A typ. @ 115VAC 2.4 A typ. @ 230VAC		< 1.5 mA @ 240 VAC	91.5% typ. @ 115VAC 95% typ. @ 230VAC	
Three Phase Input								
<u>PSR-24-120-3</u>	\$91.00			< 0.50 A @ (3 x 400VAC) < 0.40 A @ (3 x 500VAC)	20A @ (3 x 400VAC),		87.5% @ (3 x 400 & 500VAC)	4A
<u>PSR-24-240-3</u>	\$137.00	220 575 \/AC	47 62 LI -	< 0.75 A @ (3 x 400VAC) < 0.65 A @ (3 x 500VAC)	25A @ (3 x 500VAC)	< 3.5 mA @	89.5% @ (3 x 400 & 500VAC)	B Curve
<u>PSR-24-480-3</u>	\$237.00	320-375 VAC	41-03 HZ	< 0.85 A @ (3 x 400VAC) < 0.73 A @ (3 x 500VAC)	35A @ (3 x 400VAC).	(3 x 500 VAC)	94% @ (3 x 400 & 500VAC)	10A B Curve or 4A C Curve
<u>PSR-24-960-3</u>	\$356.00			< 1.65 A @ (3 x 400VAC) < 1.35 A @ (3 x 500 VAC)	35A @ (3 x 500VAC)		94.5% @ (3 x 400 & 500VAC)	

	Output Specifications									
Part Number	Output Voltage / Adjustment Range	Output Power (Watts)	Output Current (Amps)	Ripple and Noise (20MHz)	Startup with Capacitive Loads (µF)	Start-Up Time	Hold-Up Time (@100% load)	Rise Time	MTBF (as per Telcordia SR-332. Ta: 25°C)	
<u>PSR-24-120</u>		120	5	< 100 mV/m @		300ms typ. @ 115 and 230VAC	35 ms typ. @ 115VAC & 230VAC			
<u>PSR-24-240</u>		240	10	0°C to +70°C < 300 mVpp @		300ms typ. @	30 ms typ. @ 115VAC & 230VAC	30 ms typ. @ 115 & 230VAC		
<u>PSR-24-480</u>		480	20	-30 C 10 0 C	10,000 Max.	25 ms typ. @ 115VAC & 230VAC		> 700,000h		
<u>PSR-24-120-3</u>	24-28 VDC	120	5	< 100 mVpp		500ms typ. @ nominal input (100% load)	20ms typ. @(3 x 400VAC) 40ms typ. @(3 x 500VAC)	50 ms typ.@ nominal input		
<u>PSR-24-240-3</u>		240	10			1000ma.tun @		(100%10au)		
<u>PSR-24-480-3</u>		480	20	< 150 mVpp		nominal input (100% load)	20ms tvp @	100 ms typ.@ nominal input (100% load)	> 600,000h	
<u>PSR-24-960-3</u>		960	40	< 200 mVpp	20,000 Max.	2000ms typ. @ nominal input (100% load)	(3 x 400 & 500VAC)	85 ms typ.@ nominal input (100% load)	> 500,000h	

www.automationdirect.com

Power Supplies

tPWR-56



Power Supplies PSR Series

	General Specifications		
Model	Single Phase	Three Phase	
Operating Temperature (-40°C [40°F] Cold Start)	Vertical: -30 to +70°C [-22 to 158°F]	PSR-24-120-3 and PSR-24-240-3 Vertical mounting: -25 to 70°C [13 to 158°F] Horizontal mounting: -25 to 60°C [13 to 140°F] PSR-24-480-3 and PSR-24-960-3 Vertical mounting: -25°C to 70°C [13 to 158°F] Horizontal mounting: -25°C to 55°C [13 to 131°F]	
Storage Temperature	-40 to 85°C [-40 to 185°F]	
Humidity	5 to 95% RH @ 25°	°C, no condensation	
Line Regulation	± 0.5% @ 115 & 230VAC	< 40mV (@ 3 x 320-575 VAC Input (100% load)	
Load Regulation	± 0.5%	@ 3 x 320-575 VAC Input (100% load) <u>PSR-24-120-3</u> <100mv, <u>PSR-24-240-3</u> < 150mv <u>PSR-24-480-3</u> < 200mv, <u>PSR-24-960-3</u> < 250mv	
Short Circuit Protection	Hiccup Mode, Non-Latching (Auto-F	Recovery when the fault is removed)	
Overvoltage Protection	< 34V, SELV Output, Latch Mode	< 35V, Hiccup Mode, Non-latching (Auto Recovery)	
Overload/Overcurrent	105 - 150% of rated load current, Auto-recovery Continuous current limit Mode*1 (Vo > 80%)	PSR-24-120-3 and PSR-24-240-3 105 - 150% of rated load current, Auto-recovery Continuous current limit Mode*1 (Vo > 80%) PSR-24-480-3 and PSR-24-960-3 110 - 150% of rated load current, Auto-recovery Continuous current limit Mode*1 (Vo > 80%)	
Status Indicators	Green LEI	D (DC OK)	
Cooling System	Conv	ection	
Vibration (operating)	IEC 60068-2-6, Sine Wave: 10-500 Hz; 4G peak; 60 min per axis for all X, Y, Z directions	IEC 60068-2-6, Sine Wave: 10-500 Hz; 3G peak; 60 min per axis for all X, Y, Z directions	
Shock (non-operating)	IEC 60068-2-27, Half Sine Wave: 50G fo	or duration of 11ms; 3 times per direction	
Protection Rating	IP	20	
Pollution Degree		2	
Mounting	35mm DIN rail (Vertical input terminal block on bottom) 35mm DIN rail (Vertical: input terminal block on bottom)		
Connection	Input & output terminal block DC OK relay contact	connector: Screw connection t: Push-in connection	
Housing Material	Metal	Aluminum	
Approvals	CE, cULus File E197592, c	URus: File E508040, UKCA	

*1 Constant current limit protection for inductive and capacitive load applications

	Additional Data								
Part Number		Wire Size / Torque		ADC Ferrule Part	Terminal Block Type	Weight	Drawing		
	Input	Output	DC OK	Number	(Screw Terminals)		LIIIK		
<u>PSR-24-120</u>	0.82-3.3 mm² [AWG 18-12] 0.51 N•m [4.5 in•lb]	0.82-3.3 mm² [AWG 18-12] 0.51 N•m [4.5 in•lb]	00040	20AWG <u>V30AE000038</u> 18AWG V30AE000041	Input: 3-pins (600V/30A) Output: 3-pins (600V/30A) DC OK: 2-pins (300V/6A)	0.50 kg [1.10 lb]	<u>PDF</u>		
<u>PSR-24-240</u>	0.82-3.3 mm² [AWG 18-12] 0.51 N•m [4.5 in•lb]	0.82-3.3 mm² [AWG 18-12] 0.51 N•m [4.5 in•lb]	0.32-1.3 mm ² [AWG 22-16]	16AWG V30AE000048 14AWG V30AE000052	AWG V30AE000048 IAWG V30AE000052 Input: 3-pins (600V/30A)	0.64 kg [1.41 lb]	<u>PDF</u>		
<u>PSR-24-480</u>	2.1 -3.3 mm² [AWG 14-12] 0.51 N•m [4.5 in•lb]	2.1 -3.3 mm² [AWG 14-12] 0.51 N•m [4.5 in•lb]	12AWG <u>V30AE000055</u>		DC OK: 2-pins (300V/6A)	0.88 kg [1.94 lb]	<u>PDF</u>		
<u>PSR-24-120-3</u>	0.82-5.3 mm² [AWG 18-10] 0.54 N•m [4.7 in•lb]	0.82-5.3 mm² [AWG 18-10] 0.54 N•m [4.7 in•lb]		20AWG <u>V30AE000038</u> 18AWG <u>V30AE000041</u> 16AWG <u>V30AE000048</u> 14AWG <u>V30AE000052</u> 12AWG <u>V30AE000055</u> 10AWG <u>V30AE000058</u> 10AWG <u>V30AE000058</u> 10AWG <u>V30AE000058</u>	20AWG <u>V30AE000038</u> 8AWG <u>V30AE000041</u> 6AWG <u>V30AE000048</u> 4AWG <u>V30AE000052</u> Input: 4-pins (600V/30A) Output: 4-pins (600V/30A) Signal: 2-pins (300V/12A)	0.54 kg [1.19 lb]	<u>PDF</u>		
<u>PSR-24-240-3</u>	0.82-5.3 mm² [AWG 18-10] 0.54 N•m [4.7 in•lb]	1.3-5.3 mm² [[] AWG 16-10] 0.54 N•m [4.7 in•lb]				0.84 kg [1.85 lb]	<u>PDF</u>		
<u>PSR-24-480-3</u>	0.82-5.3 mm² [AWG 18-10] 0.54 N•m [4.7 in•lb]	3.3-5.3 mm² [AWG 12-10] 0.54 N•m [4.7 in•lb]	0.52-1.3 mm ²		o.g po (00007, 1_1.)	1.20 kg [2.65 lb]	<u>PDF</u>		
<u>PSR-24-960-3</u>	0.82-5.3 mm² [AWG 18-10] 0.54 N•m [4.7 in•lb]	3.3-5.3 mm² [AWG 12-6]* 1.93 №m [17.1 in•lb]	[AWG 20-16]	20AWG V30AE000038 18AWG V30AE000041 16AWG V30AE000048 14AWG V30AE000052 12AWG V30AE000055 10AWG V30AE000055 10AWG V30AE000058 8AWG V30AE000060 6AWG V30AE000062	Input: 4-pins (600V/30A) Output: 4-pins (300V/65A) Signal: 2-pins (300V/12A)	2.26 kg [4.98 lb]	<u>PDF</u>		

*For AWG 12-10, ensure that all output terminals are connected.

RHINO[®] SELECT

Power Supplies With Integrated UPS PSFA Series

Overview

RHINO SELECT PSFA series open frame power supplies come with integrated DC UPS function. The PSFA models will switch to battery operation (batteries not included) without interruption to prevent end-product downtime for the customer in the event of power disruption or unexpected loss of AC input power. Consequently, the PSFA series can increase operational reliability of a critical operation. Convection cooling is applied for the single phase design with wide operating temperature range from -20°C to +70°C. Diagnostic monitoring signals for AC OK and Battery Low status will alert the user of any failure through TTL open collector. Metal chassis with case cover is available for different installation preferences.

Features

- Universal AC input voltage range
- Zero switch over time from loss of AC to battery operation
- Protection against reverse polarity battery connection
- Built-in diagnostic monitoring for AC OK and Battery Low status
- Overvoltage / Overcurrent / Over Temperature / Short circuit Protections
- Built-in over current and short circuit protection in buffering (battery discharging) mode operation
- 3-year warranty





Power Supply with Integrated UPS								
Part Number Price Output Maximum Drawin Voltage Output Power Link								
<u>PSFA12-060-U</u>	\$39.00	13.8 V	60W	PDF				
<u>PSFA24-060-U</u>	\$39.00	27.6 V	60W	PDF				



Power Supplies Specifications PSFA Series

Technical Specifications								
Creationtiana		PSFA12-	<u>060-U</u>	PSFA	124-060-U			
Specifications	Specifications		B+	V+	B+			
Input (AC)								
Input Voltage Range)		9	0-264 VAC				
Frequency				47-63 Hz				
Nominal Current			< 1.2 A @ 115	VAC, <0.8 A @ 230VAC				
Inrush Current Limit	ation l2t (+25 °C) typ		< 25A @	115VAC & 230VAC				
Leakage Current	IEC/EN 60950-1	< 0.5 mA / 1.0 n	nA @264VAC	TN/TT sys	stem / IT system			
	IEC/EN 62368-1	< 1.0 mA / 2.0 n	nA @264VAC	TN/TT sys	stem / IT system			
Recommend Circuit (Characteristic B)	Breaker			10A				
Output (DC)								
Nominal Output Volt Range	age / Adjustment	13.8 VDC / 13.52 - 14.00 V	13.6 VDC	27.6 VDC / 27.04 - 28.00 V	27.4 VDC			
Output Power				60W max				
Output Current	Normal Mode	3.5 A [0 - 4.3 A]	0.8 A [0 - 0.8 A]	1.4 A [0 - 2.15 A]	0.75 A [0-75 A]			
Output Current	Buffering Mode	-	0 - 4.3 A	-	0.215 A			
PARD (20MHz)	V+	< 100mVpp						
Start-up Time	V+	< 3,000ms @ 115VAC [100% load], <1,500ms @ 230VAC [100% load]						
Hold-up Time	V+		> 10ms @ 115Vac [100% load]					
Rise Time	V+	< 50ms @ nominal input						
Efficiency	Ť	> 85.0% @ 115VAC / > 86.0% @ 230VAC > 88.0% @ 115VAC / > 89.0% @ 230VAC						
Line Regulation	V+		< 0.5% [90-2	64VAC @ 100% load]				
Load Regulation	V+		< 1.0% [90-26	64VAC @ 0-100% load]				
Voltage Drop	Normal Mode	0.2 V typ.						
V+ and B+	Buffering Mode	0.4 V typ.						
General Data		[
Case Chassis / Cove	er	SECC						
Weight		0.25 kg [0.56 lb]						
MTBF		> 700,000 hrs. as per Telcordia SR-332, I/P: 115VAC & 230VAC, Ta: 25°C, O/P: 13.8V/4.3A for 13V model and 27.6V/2.15A for 27V model						
Noise		Sound Pressure Level [SPL] < 25dBA						
Cooling	T	Convection						
Input / Output	Input		Terminal block	3-Pin [Rated 300V/16A]				
Terminal	Output with Signal		Terminal block	6-Pin [Rated 300V/8A]				
Wire Size / Torque	Input	AWG 22-12	/ 7.0 lbf-in	AWG 24	-12 / 7.0 lbf-in			
	Output with Signal	AWG 22-16	/ 2.0 lbf-in	AWG 24	I-16/ 2.0 lbf-in			
Shock Test	Non-Operating	IEC 60068-2-27,	Half Sine Wave: 50G for a c	duration of 11ms; 3 times per d	irection, 9 times in total			
	Operating	IEC 60	068-2-27, Half Sine Wave:	10G for a duration of 11ms; 1 t	ime in X axis			
Vibration	Non-Operating	IEC 60068-	2-6, Random: 5-500Hz; 2.0	19Grms; 20 min per axis for all	X, Y, Z directions			
vibration	Operating	с	IEC 60068-2-6, Sine lisplacement of 0.35mm; 60	e Wave: 10-500Hz; 2G peak;) min per axis for all X, Y, Z dire	ections			

Continued on next page



Power Supplies Specifications PSFA Series

Technical Specifications (continued)							
One office times	PSFA12	2-060-U	PSFA24-060-U				
Specifications	V+	B+	V+	B+			
Safety / Environmental	·	` 	` 	•			
EMC / Emissions		CISPR 32, EN 55032, FCC	Title 47: Class B GB9254.1				
Immunity	EN 55024, IEC 61000-4-2,	IEC 61000-4-3, IEC 61000-4-4, IE	C 61000-4-5, IEC 61000-4-6, IEC	61000-4-8, IEC 61000-4-12			
Voltage Dips		Conform to IE	EC 61000-4-11				
Galvanic Isolation	Input to	Output : 3.0K VAC, Input to Grour	nd : 1.5KVac, Output to Ground : 0	.5K VAC			
RoHS Compliant		Y	es				
Operating Temperature		-20 to 70°C	[-4 to 158°F]				
Storage Temperature		-40 to 85°C	[-40 to 185°F]				
Humidity at +25 °C, no condensation		5 to 95% RH [Non-Condensing]					
Approvals	CE lin conf	SIQ Bauart: UL 62368-1 and CSA C22.2 N CB scheme: prmance with EMC Directive 2014/	EN 62368-1, lo. 62368-1; File No. E508040 IEC 62368-1 '30/EU and Low Voltage Directive	2014/35/EU1			

Battery Input / Output Characteristics					
Specifications		PSFA1	<u>2-060-U</u>	PSFA24	4-060-U
		V+4	B+	V+	B+
Nominal Battery Voltage (Battery not included with Power Supply)		12VDC SLA Sealed lead acid battery		24VDC SLA Sealed lead acid battery 2x12 VDC SLA Sealed lead acid battery	
Battery Voltage Range	Continuously Operating	11.0 - 13.8 VDC [nominal at 12V]		22.0 - 27.6 VDC [nominal at 24V]	
	Maximum Allowed Voltage	16VDC maximum		32VDC maximum	
	Battery Low Voltage ¹	11.5 VDC typ		22.5 VDC typ	
	Minimum Voltage ²	10.0 VDC +/- 0.5 VDC		18.0 VDC +/- 0.5 VDC	
Battery Capacity		3.2AH - 15AH		3.2AH – 7AH	
Charging Time ³		< 9hrs ± 1hr for	battery 12V/7AH	< 10hrs ± 1hr for	battery 24V/7AH
Buffering Time		Approx.1hr 30mins	for battery 12V/7AH	Approx.3hrs for	battery 24V/7AH
Recommended Extended Fuse for Battery		Automotive 20A / 80V, FK3 type from Littelfuse, or similar in the battery B+ path. The battery fuse protects the wires between thebattery and the unit.			ery B+ path. e unit.
Battery Charging (Normal Mo	de)	CC-CV mode [constant current-constant voltage]			
End-Of-Change Voltage		The unit always charges battery to a fixed voltage value.			

1. The voltage level of battery to enable "Battery Low" function.

2. Minimum battery voltage required for power supply to detect battery in order to begin charging. Battery must be connected to power supply, with the correct polarity, across B+ and B- terminals; and, with input and output loads disconnected.

3. Charging time depends on the state/condition of battery discharge; and will depend on the amount of buffering/discharging time, and load current that battery was discharged at.

4. V+ and V- terminals are for power supply voltage output.

Wiring Diagram



RHINO SELECT

Power Supplies With Integrated UPS PSS Series

Overview

The RHINO SELECT PSS*-U panel mount power supplies, with integrated DC UPS function, prevents end-product downtime for the customer in the event of failure/disruption or unexpected loss of input AC power. The power supply will switch to battery operation (batteries not included) without interruption to increase operational reliability. The TTL compatible monitoring signals for AC OK, DC OK and Battery Low will alert the user in the event of failure. This convection-cooled single-phase power supply has a wide operating temperature range from -20°C to + 70°C and is suitable for security system, access control, automatic doors, alarm system and other similar products. In addition to having overvoltage, overload, over temperature, deep battery discharge, and reverse battery polarity protections on the main output, there are also short circuit and overload protections when operating in the buffering (battery discharging) mode. The PSS*-U design meets worldwide safety approvals, certified to Class B radiated and conducted emission requirements.

Features

- LED indicators for DC OK (Green) and Battery Reverse
- Zero cut-over time from loss of AC, to battery operation
- Protection against reverse polarity battery connection
- Conforms to harmonic current IEC/EN 61000-3-2, Class A
 - High MTBF > 700,000 hrs. per Telcordia SR-332
 - Monitoring Signals for AC OK, DC OK and Battery Low indication
 - Overvoltage / Overcurrent / Over temperature / Short circuit protections
 - Built-in over current and short circuit protection in buffering (battery discharging) mode operation
 - Certified according to IEC/EN/UL 62368-1
 - 3-year warranty





Power Supply With Integrated UPS								
Part Number	Price	Maximum Output Power	Drawing Link					
<u>PSS12-155-U</u>	\$48.00	13.8 V	151W	<u>PDF</u>				
<u>PSS24-155-U</u>	\$48.00	27.6 V	151W	PDF				



Power Supplies With Integrated UPS Specifications PSS Series

Technical Specifications							
Specifications		<u>PSS12</u>	<u>-155-U</u>	PSS24	<u>4-155-U</u>		
		V+	B+	V+	B+		
Input (AC)							
Input Voltage Range			90-132 VAC, 180-264 V	AC [Selectable by Switch]			
Frequency			47-	63 Hz			
Nominal Current			< 2.5 A @ 115VAC	C, < 1.5 A @ 230VAC			
Inrush Current Limitatio (+25 °C) typ	on l2t		< 25A @ 115	VAC & 230VAC			
Leakage Current			< 0.5 mA	@ 264VAC			
Recommend Circuit Bre (Characteristic B)	eaker		1	10A			
Output (DC)							
Nominal Output Voltage Adjustment Range	e /	13.8 VDC / 12 - 14 VDC	13.3 VDC	27.6 VDC / 24 - 28 VDC	27.1 VDC		
Output Power			1511	V [max]			
Output Current	Normal Mode	905 A [0 - 11A]	1.5 A [0.5 - 1.5 A]	4.0 A [0 - 5.5 A]	1.5 A [0.5 -1.5 A]		
Curput Current	Buffering Mode	-	0 - 11A	-	0 - 5.5 A		
PARD ripple and noise (20MHz)	V+		< 150mVpp < 100mVpp	@ 0 to -20°C @ > 0 to 70°C			
Start-up Time	V+		< 1,000ms [115VAC @ 90%	6 load, 230VAC @ 100% load]			
Hold-up Time	V+		> 20ms [115VAC @ 90% load, 230VAC @ 100% load]				
Rise Time	V+		< 50ms [100VAC @ 90%	load, 200VAC @ 100% load]			
Efficiency		> 85.0% @ 115VAC /	> 86.0% @ 230VAC	> 88.0% @ 115VAC	/ > 89.0% @ 230VAC		
Line Regulation	V+		< 0.5% [90-132VAC @ 100%	load, 180-264VAC @ 100% load]			
Load Regulation	V+		< 1.0% [90-132VAC @ 0-90%	oad,180-264VAC @ 0-100% load]		
Voltage Drop Between	Normal Mode	0.5 V typ.					
V+ and B+	Buffering Mode	0.2 V typ.					
General Data							
Case Chassis / Cover		AL / SGCC					
Weight		0.60 kg [1.32 lb]					
MTBF		> 700,000 hrs. as per Telcordia SR-332, I/P: 115VAC, Ta: 25°C, O/P: 13.8 V/9.9 A for 13V model and 27.6 V / 4.95 A for 27V model					
Noise			Sound Pressure L	_evel [SPL] < 30dBA			
Cooling			Con	vection			
Input / Output Terminal		Terminal block M3.5 x 7-Pin [Rated 300V/15A]					
Wire Size / Torque			AWG 16-1	4 / 11.3 lbf-in			
Status Connector		4	00mm length, 4-pin JST: XHP-4 1 Statuses available: DC	Mating connector: B4B-XH-A(LF)(COK, Low Battery, AC OK	SN)		
Shock Test		IEC 60068-	2-27, 30G (300m/S²) for a duratic	on of 18ms,3 times per direction, 9	etimes in total		
Vibration			IEC 60068-2-6, 10Hz to 1 displacement of 0.35 mm; 20 m	I50Hz @ 50m/S² (5G peak); nin per axis for all X, Y, Z direction			

Continued on next page

1-800-633-0405



Power Supplies With Integrated UPS Specifications PSS Series

	Technical Specifications											
Specifications	<u>PSS12</u>	- <u>155-U</u>	<u>PSS24-155-U</u>									
Specifications	V+	B+	V+	B+								
Safety / Environmental												
EMC / Emissions	C	ISPR 22, CISPR 32, EN 55022, E	EN 55032, FCC Title 47: Class B	GB9254.1								
Immunity	EN 55024, IEC 61000-4-	2, IEC 61000-4-3, IEC 61000-4-4	4, IEC 61000-4-5, IEC 61000-4-6,	IEC 61000-4-8, IEC 61000-4-12								
Voltage Dips		Conform	to IEC 61000-4-11									
Galvanic Isolation	Input to Output : 3.0K VAC, Input to Ground : 1.5K VAC, Output to Ground : 0.5K VAC											
RoHS Compliant			Yes									
Operating Temperature		-20 to 70)°C [-4 to 158°F]									
Storage Temperature		-40 to 85	°C [-40 to 185°F]									
Humidity at +25 °C, no condensation		5 to 95% RI	H [Non-Condensing]									
Approvals	CE (In co	SIQ Bau UL 62368-1 and CSA C22 CB schei Informance with EMC Directive 20	uart: EN 62368-1 2.2 No. 62368-1; File No. E508040 me: IEC 62368-1, 014/30/EU and Low Voltage Direc	0 ctive 2014/35/EU)								

	Batt	ery Input / Outpu	t Characteristics	5		
Specifications		<u>PSS12</u>	2- <u>155-U</u>	<u>PSS24-155-U</u>		
Specifications		V + ⁴	V+4 B+		B+	
Nominal Battery Voltage (Battery not included with Power Supply)		12\ SLA Sealed le	/DC ad acid battery	24VDC SLA Sealed lead acid battery 2x12 VDC SLA Sealed lead acid battery		
	Continuously Operating	11.0 to 13.8 VDC	[nominal at 12V]	22.0 to 27.6 VDC [nominal at 24V]		
Battery Voltage Range	Maximum Allowed Voltage	16VD	C Max	32VDC Max		
	Battery Low Voltage 1	11.5 V	DC typ	22.5 VDC typ		
	Minimum Voltage ²	9.0 VDC +	-/- 0.5 VDC	18.0 VDC +/- 0.5 VDC		
Battery Capacity			3.3 AH/ 7AH	/ 12AH/ 15AH	/ 15AH	
Buffering Time		Approx. 1 hr 15 mins	for battery 12V/15AH	Approx. 2 hrs 30 mins	s for battery 24V/15AH	
Charging Time ³		2-10 hrs @ charging current of 1.5A				
Recommended Extended Fuse for Battery		Automotive	e 30A / 80V FK3 type from Lit battery fuse protects the wire	telfuse, or similar, in the battery B+ path. s between the battery and the unit.		
Battery Charging (Norma	I Mode)	CC-CV mode [constant current-constant voltage] at 0 to 1.5 A				
End-Of-Change Voltage			The unit always charges ba	ttery to a fixed voltage value.		

1. The voltage level of battery to enable "Battery Low" function.

2. Minimum battery voltage required for power supply to detect battery in order to begin charging. Battery must be connected to power supply, with the correct polarity, across B+ and B- terminals; and, with input and output loads disconnected.

3. Charging time depends on the state/condition of battery discharge; and will depend on the amount of buffering/discharging time, and load current that battery was discharged at.

4. V+ and V- terminals are for power supply voltage output.

Wiring Diagram



PRO

Power Supplies PSD Series

Versatile Switching Power Supplies with LED Display & Automatic Power Boost

AutomationDirect offers the RHINO PRO PSD DIN rail power supply series with LCD display. The LCD displays output current, output voltage, peak hold current, lifetime expectancy* and ambient temperature data. The high power density product is designed according to major industrial safety standards. The PSD series provides 150% Power Boost up to 7 seconds, including the Advanced Power Boost (APB) feature. With multiple loads connected in a system, a large inrush current could be drawn (demanded) due to one fault load. This will be detected by APB. The APB will trip the circuit breaker (with appropriate rating based on the system load) on the current path of the fault load due to high current. This prevents the system from shutting down while the other connected current paths continue to operate without interruption.

Features

- Universal AC input voltage range
- · Lifetime expectancy alarm* signal and monitoring
- Built-in active PFC** with up to 94% efficiency
- Power Boost of 150% up to 7 seconds
- LCD display of output current / voltage / peak current and temperature
- Advanced Power Boost (APB) protects system to ensure continuing operation when large inrush current detected due to faulty load on a multiple load connection
- DC OK Contact and LED indicator for DC OK/ Overload
- Conformal coating on PCBAs to protect against common dust and chemical pollutants

The lifetime expectancy function indicates an approximate period of life left for the power supply unit, based on deterioration of the electrolytic capacitor.

**Active Power Factor Correction (PFC) - Active wave shaping of the input current, filtering of the high frequency switching, feedback sensing of the source current for waveform control





PSD24-120-L



PSD24-240-L



PSD24-480-L

Industrial Power Supplies										
Part Number Price Output Voltage [V _{nom}] Output Current [Imax] Output Power [Pmax] Weight kg [Ib]										
PSD24-120-L	\$224.00		5.0 A	120W	0.75 [1.65]	PDF				
<u>PSD24-240-L</u>	\$311.00	24 VDC	10.0 A	240W	1.02 [2.25]	PDF				
PSD24-480-L	\$395.00		20.0 A	480W	1.45 [3.20]	PDF				

Input Specifications											
Part Number N	Nominal Input Inp Voltage Rai	Input Voltage Range	Input Frequency Bange	Input Current [Typ. @ full load]		Inrush Current Limitation [<2ms] @+25°C		Max Power Dissipation	Efficiency [Typ] @120VAC	Circuit Breaker (Minimum)	
		nungo	linnigo	120 VAC	230 VAC	120 VAC	230 VAC		Gillowio	[
<u>PSD24-120-L</u>		85-264VAC 88-275VDC		1.11 A	0.61 A	5.5 A	10.1 A	14W	90%	6A B- or 3A C-	
<u>PSD24-240-L</u>	100 - 240VAC 110-300VDC	85-276VAC	47-63 Hz	2.18 A	1.16 A	6.0 A	7.0 A	22.4 W	92%	6A B- or 4A C-	
PSD24-480-L		88-275VDC		4.24 A	2.29 A	9.0 A	7.0 A	46.0 W	93%	10A B- or 6A C-	

1-800-633-0405



RHINO Power Supplies PSD Series

	Output Specifications											
Part Number	Output Voltage	Output Voltage Adj. Range	Output Current [Max]	Power Boost [7s]	Output Overvoltage Protection	Startup with Capacitative Loads [Max.]	Startup Time @120VAC	Relay Output	MTBF [@ 25°C]			
<u>PSD24-120-L</u>			5.0 A	7.5 A		10,000µF	750ms		1,444,000 hrs			
<u>PSD24-240-L</u>	24VDC	24-28 VDC	10.0 A	15.0 A	28.8- 35.2 V	10,000µF	650ms	DC OK = contact closed [rated: 30	1,268,000 hrs			
<u>PSD24-480-L</u>			20.0 A	30.0 A		20,000µF	1000ms		751,000 hrs			

	General Specifications
Specification	Description
Temperature	Operating (ambient): -25 to + 70°C max [-13 to 158°F]. Above +60°C [140°F] load derating. Storage (non-operating): -40 to + 85°C max [-40 to 185°F]. Cooling: convection, no internal fan.
Humidity	5-95% [non-condensing] relative humidity maximum
Isolation	According to IEC/EN 60950, EN62477-1, EN60204, CSA
Mains Buffering at Nominal Load	See Product Insert
Output Line Regulation	120W=20mV, 240W & 480W = 10mV [100% load]
Output Load Regulation	100mV peak-to-peak typical [20MHz bandwidth]
Overload/Short Circuit Protection	Current limit: > 150% of rated load current, Constant current, Hiccup Mode [Auto-Recovery]
Overvoltage Protection	28.8 – 35.2V, SELV Output, Hiccup Mode, Non-Latching [Auto-Recovery]
Overtemperature Protection	Switch off at over-temperature, automatic restart
Status Indicators	2 color LEDs [green: DC Ok, Red: Overload]
Maximum Capacitative Load	120W & 240W=10,000uF, 480W=20,000uF
Noise (1 meter from power supply)	Sound Pressure Level [SPL] < 25dBA
Vibration	IEC 60068-2-6, sine wave: 10-500Hz; 3G peak; displacement of 0.35mm; 60 min per axis for all X, Y, Z directions
Shock	IEC 60068-2-27, half sine wave: 30G for a duration of 18ms; 3 times per direction, 6 times in total
Enclosure Rating	IP20
Enclosure Material	Aluminum and plastic
Mounting	Snap-on with self-locking spring for 35mm DIN rails
Connection	Screw terminals, See nsert for Wire size and Torque Ratings
Agency Approvals	UL/C-UL recognized to UL60950-1 and CSA C22.2 No. 60950-1; File No. E198298 , UL/C-UL listed to UL508 and CSA C22.2 No. 107.1-01; File No. E197592

Note: Unless otherwise stated all specifications are valid at nominal input voltage, full load and +25°C after warm up time.

1-800-633-0405

PRO

Power Supplies PSD Series

	General Spo	ecifications (Continued)					
Specification	Standard	Document Number					
Harmonic Limits	Harmonic Current Limits	EN 61000-3-2, Class A	A for limited output power				
	Information technology equipment	UL/C-UL recognized to UL60950-1 and CSA C22.2 No. 60950-1; File No. E198298					
	Industrial control equipment	UL508 and CSA C22.2 No. 107.1-01; File No. E197592					
Safety Standards	Electrical equipment of machines	IEC60204-1 (over	voltage category III)				
Safaty Approvals	Electronic equipment for power installation	IEC/EN 6247	7-1 / IEC62103				
	Safety, Transient surge voltage protection	VAR	ISTOR				
Safety Approvals	CB-Report per IEC 60950	IEC 60950-1, IEC 610	010-1, IEC 61010-2-201				
Safety Class	Degree of electrical protection Class1	Class I with C	GND connection				
CE	In conformance	e with EMC directive 2014/30/EU and low voltage	directive 2014/35/EU				
RoHS Compliant		RoHS Directive (EU) 2015/863 Compliant (EN 50581)					
Electromagnetic Compatibility (EMC), Emissions	EMC, Emissions	EN55032, EN55011, EN61000-3-2 Class A, EN61000-3-3, EN61000-6-3					
	EMC, Immunity	EN 55024, EN 61000-6-2 (EN61000-4-2, 3, 4, 5, 6, 8, 11, 12)					
	Electrostatic Discharge [ESD]	IEC 61000-4-2 Level 4 Criteria A Air D	vischarge: 15kV; Contact Discharge: 8kV				
Electromagnetic	Radiated RF field immunity [80-1000 MHz]	IEC / EN 61000-4-3: 120W&240W: 80MHz-1GHz, 10V/M, 80% modulation [1kHz] 1.4GHz-2GHz, 3V/M, 80% modulation [1KHz] 2GHz-2.7GHz, 1V/M, 80% modulation [1KHz]					
Compatibility (EMC),	Electrical fast transient / burst immunity	IEC / EN 61000-4-4	Level 4 Criteria A 4kV				
mmunity	Surge immunity	IEC / EN 61000-4-5 Level 4 Criteria A C	common Mode: 4kV Differential Mode: 2kV				
	Immunity to conducted RF disturbances [0.15 to 80 MHz]	IEC / EN 61000-4-6 Level 3 Criteria A 150kHz-80MHz, 10Vrms					
	Power frequency field immunity	IEC / EN 610	00-4-8 30 A / m				
	Voltage dips	IEC / EN 61000-4-11 [70% U	N Crit. B/40%/100% UN Crit. C]				
Pollution Degree		2					

Years Alarm Signal Circuit and Wiring



*The applied voltage should be 30VDC maximum with sink current of 10mA max.



Years Alarm Signal Status



- The years alarm signal is Low when the set value of alarm year has not been reached.
- The years alarm signal status will be changed from low to high when the set value of alarm year has been reached.

RHINO Power Supplies PSD Series

Engineering Data for RHINO PRO PSD Series Power Supplies

Output Load De-rating vs. Surrounding Air Temperature

Note:

Pro

- Power supply components may degrade, or be damaged, when the power supply is continuously used outside the shaded region.
- If the output capacity is not reduced when the surrounding air temperature exceeds its specification as defined under "Temperature" in the General Specifications table, the device will run into Over Temperature Protection. When activated, the output voltage will go into bouncing mode and will recover when the surrounding air temperature is lowered or the load is reduced as far as necessary to keep the device in working condition.
- In order for the device to function in the manner intended, it is also necessary to keep a safety distance as recommended in the safety instructions while the device is in operation.
- Depending on the surrounding air temperature and output load delivered by the power supply, the device can be very hot!

Power Derating Curve for PSD24-120-L and PSD24-240-L

PSD24-120-L, PSD24-240-L Derating							
Part Number	Vertical or Horizontal Orientation						
<u>PSD24-120-L</u>	> 60°C de-rate power by 2.5% / °C						
<u>PSD24-240-L</u>							



Power Derating Curve for PSD24-480-L

PSD24-480-L Derating					
Part Number	Vertical or Horizontal Orientation				
<u>PSD24-480-L</u>	> 60°C de-rate power by 2.5% / °C				



RHINO Power Supplies PSM Series

Versatile switching power supplies are DIN rail mountable

AutomationDirect offers the most practical industrial control power supplies available. The RHINO PSM series power supplies are industrial grade switching DC output supplies with a sturdy steel case to withstand harsh environments. Autoselect inputs for 115 VAC or 230 VAC and international agency approvals make the RHINO PSM series suitable for worldwide use. RHINO PSM power supplies are available in 12 or 24 VDC output, with adjustable output voltages, and feature low output ripple along with overload and overtemperature protection. The seven models offer power ratings from 78W to 600W, and up to 25A output current.

Features

- Industrial grade design
- Sturdy metal case to withstand harsh industrial environments
- Model PSM24-090S-N meets NEC Class 2
- Universal 100/230 VAC input voltage
- Adjustable output voltage
- Low output ripple
- Short-circuit, overvoltage and overtemperature protection
- Power Good signal
- Remote ON/OFF
- Optional wall mounting
- Specialty modules for redundancy, power backup and UPS
- Terminal connectors included
- 3-year warranty



Part Numbering System



Industrial Power Supplies											
Part Number	Price	Drawing Link	*Output Voltage [V _{nom}]	**Output Current [I _{max}]	***Output Power [P _{max}]						
<u>PSM12-078S</u>	\$198.00	PDF	12VDC	6.0 A	78W						
<u>PSM24-090S</u>	\$147.00	PDF	24VDC	3.75 A	90W						
<u>PSM24-090S-N</u>	\$203.00	PDF	24VDC	3.75 A	90W						
<u>PSM12-156S</u>	\$236.00	PDF	12VDC	12.0 A	156W						
<u>PSM24-180S</u>	\$229.00	PDF	24VDC	7.5 A	180W						
<u>PSM24-360S</u>	\$345.00	<u>PDF</u>	24VDC	15.0 A	360W						
<u>PSM24-600S</u>	\$513.00	PDF	24VDC	25.0 A	600W						

*12V models adjustable from 12 to14 VDC. 24V models adjustable from 24 - 28 VDC

**Maximum current at nominal output voltage

***Up to an operating temperature of +40°C

1-800-633-0405

Power Supplies Specifications PSM Series

	Input Specifications											
Part Number	Input Voltage Range	Operating Voltage min/	Input Frequency Range	Input Curre at ful	Input Current [Typical] at full load		rrent max @ +25°C	Holdup Time	Efficiency [Typ @	Circuit Breaker or Fuse		
		max		115 VAC	230 VAC	115 VAC	230 VAC		115VAC]	[slo-blow]		
<u>PSM12-078S</u>			47-63 Hz	2.0 A	1.0 A		<20 A	20 ms min. [full load 115/230 VAC]	81%	6.0 A to 16.0 A		
<u>PSM24-090S</u>	100 - 240 VAC Universal Input	NAC nput 85 - 264 VAC		2.1 A	1.0 A	<12 A			86%			
<u>PSM24-090S-N</u>	onivoroal input			2.1 A	1.0 A				85%			
<u>PSM12-156S</u>				2.5 A	1.4 A	-12 A			85%			
PSM24-180S	100 - 120 VAC/ 220 - 230 VAC Autoselect	85 - 132 VAC/		2.8 A	1.5 A	<13 A			87%			
PSM24-360S		Autoselect 187 - 264 VAC		5.0 A	2.5 A	<16 A	<25 A		85%	10.0 A to 16.0 A		
PSM24-600S				10.0 A	5.0 A	<25 A	<30 A		88%	16.0 A to 25.0 A		

	Output Specifications												
	Output	Output	Output	Output Output			Power - Good Signal		MTBF				
Part Number	Voltage	Voltage Adj. Range	Current (Max.)	Power (Max.)	Overvoltage Protection Threshold		Active Output Signal	Relay Output	(IEC 61709 @ 25°C)				
<u>PSM12-078S</u>	12VDC	12 - 14 VDC	6.5 A	78 watts	20V	9 - 11 V	11V ± 1V / 20mA max.						
<u>PSM24-090S</u>	241/00		3.75 A	90 watts	35V	10 00 1/	2014 - 214 /10 4	DC OK =					
<u>PSM24-090S-N</u>	24000	24 - 20 VDC	3.75 A	90 watts	35V	10 - 22 V	$22V \pm 2V / 1000A max$						
<u>PSM12-156S</u>	12VDC	12 - 14 VDC	13.0 A	156 watts	20V	9 - 11 V	11V ± 1V / 40mA max.	contact closed	350,000 hours				
<u>PSM24-180S</u>			7.5 A	180 watts	35V			1.0A)					
<u>PSM24-360S</u>	24VDC	24 - 28 VDC	15.0 A	360 watts	35V	18 - 22 V	22V ± 2V / 20mA max						
<u>PSM24-600S</u>			25.0 A	600 watts	35V								

General Specifications					
Specification	Description				
Temperature	Operating (ambient): -25 to 70°C max [-13 to 158°F]. Above +40°C [104°F] load derating Storage [non-operating]: -25 to 85°C max [-13 to 185°F]. Temperature drift: 0.02%/C. Cooling: convection, no internal fan				
Humidity	95% [non-condensing] relative humidity maximum				
Isolation	According to IEC/EN 60950, EN50178, EN61558-2-8, EN60204, CSA				
Output Regulation	Input variation: 0.5% maximum. Load variation [10 to 100%]: 0.5% maximum				
Output Voltage Ripple	100 mV peak-to-peak typical [20 MHz bandwidth], [200 mV peak to peak maximum at Imax]				
Output Protection	Current limit: 110% constant current, automatic recovery, thermal protection, output rating, Voltage limit: 140% Vout nom				
Over-temperature Protection	Switch off at over-temperature, automatic restart				
Status Indicator	Dual color LED [green: DC Ok; Red: DC Off]				
Remote ON/OFF	By external contact. DC On: -S contact open. DC Off: -S connected via 1 Kq to -Vout, (3VDC max across Vout [+] and Vout [-])				
Maximum Capacitive Load	Unlimited				
Vibration	IEC 60068-2-6: 3 axis, sine sweep, 10-55 Hz, 1g, 1 oct/min				
Shock	IEC 60068-2-27: 3 axis, 15g half sine, 11ms				
Enclosure Rating	IP20 [IEC 529]				
Enclosure Material	Aluminum [chassis] / zinc plated steel [cover]				
Mounting	Snap-on with self-locking spring for 35mm DIN rails per EN 50022-35x15/75, or wall mount with bracket				
Connection	Pluggable screw terminals [plugs included] 2 terminals per output [not available in 600 watt unit.]				
Agency Approvals	UL 508 Listed File E197592, UL 60950 Recognized File E198298; CSA C22.2-60950 File 229285; CE				

Note: Unless otherwise stated all specifications are valid at nominal input voltage, full load and +25°C after warmup time.

For the latest prices, please check AutomationDirect.com.

1-800-633-0405

Power Supplies Specifications PSM Series

General Specifications (continued)							
Specification	Standard	Document Number					
Harmonic Limits	Harmonic Current Limits	EN 61000-3-2, Class A for limited output power					
	Information technology equipment	IEC/EN60950; CSA 60950-1-03/UL 60950-1					
	Industrial control equipment	UL 508					
Cofety Clanderde	Electrical equipment of machines	EN 60204					
Safety Standards	Electronic equipment for power installation	EN 50178					
	Safety, transformers	EN 61558-2-8					
	Limited power source (model PSM24-090S-N)	EN 60950 sect. 2.5 and NEC Class 2					
Safety Approvals	CB-Report per IEC 60950	EN 50178, EN 60079-15 EN 61558-2-8, CSA					
Safety Class	Degree of electrical protection Class1	IEC 536					
	EMC, Emissions	EN 61204-3, EN61000-6-3					
Electromagnetic Compatibility (EMC), Emissions	Conducted RI suppression on input	EN 55011 class B, EN 55032 class B					
	Radiated RI suppression	EN 55011 class B, EN 55032 class B					
	EMC, Immunity	EN 61000-6-2, EN 61204-3					
	Electrostatic Discharge [ESD]	IEC / EN 61000-4-2 4 kV [contact discharge] / 8 kV [air discharge]					
	Radiated RF field immunity [80-1000 MHz]	IEC / EN 61000-4-3 10 V / m					
Electromagnetic Compatibility (EMC)	Electrical fast transient / burst immunity	IEC / EN 61000-4-4 2 kV					
Immunity	Surge immunity	IEC / EN 61000-4-5 1 kV / 2 kV					
	Immunity to conducted RF disturbances [0.15 to 80 MHz]	IEC / EN 61000-4-6 10 V					
	Power frequency field immunity	IEC / EN 61000-4-8 30 A / m					
	Voltage dips	IEC / EN 61000-4-11 [70% UN Crit. B/40%/100% UN Crit. C]					
Pollution Degree	2*						

*Note: Normally, only non-conductive pollution occurs. Temporary conductivity caused by condensation is to be expected.

Output Power Derating



Note: Unless otherwise stated, all specifications are valid at nominal input voltage, full load and +25°C after warmup time.

1-800-633-0405 For the late RHINO Connections PSM Series

PSM12-078S / PSM24-090S PSM24-REM360S PSM24-BCM360S

	Wiring Connections							
Pin	J1	J3	J4					
1	Earth	GND [-]	S+	Normal mode				
2	Neutral	Vout [+]	S-	Common				
3	Line	DC-OK Signal	—	Parallel mode				
4	_	DC-OK Relay contact 1	_	_				
5	_	DC-OK Relay contact 2	_	_				

PSM12-156S PSM24-180S PSM24-BFM600S

Wiring Connections								
Pin	J1	J2	J3	J4				
1	Earth	GND [-]	S+	Normal mode				
2	Neutral GND [-]		S-	Common				
3	Line	Vout [+]	—	Parallel mode				
4	— Vout [+]		—	—				
5	—	DC-OK Signal	—	—				
6	_	DC-OK Relay contact 1	_	_				
7	_	DC-OK Relay contact 2	_	_				

PSM24-360S

Wiring Connections								
Pin	J1	J2	J3	J4				
1	Earth	GND [-]	S+	Normal mode				
2	Neutral	GND [-]	S-	Common				
3	Line	Vout [+]	—	Parallel mode				
4	—	Vout [+]	—	—				
5	_	DC-OK Signal	_	—				
6	—	DC-OK Relay contact 1	_	—				
7	_	DC-OK Relay contact 2	_	_				

PSM24-600S

Wiring Connections							
Pin	J1 J2 J3 J4		J5				
1	Earth	GND [-]	S+	Normal mode	DC-OK Relay contact 1		
2	Neutral	GND [-]	S-	Common	DC-OK Relay contact 2		
3	Line	Vout [+]	_	Parallel mode	DC-OK Signal		
4	_	Vout [+])	_	—	—		

1-800-633-0405 For the latest prices, please check / RHINO <u>PSM24-REM360S</u> Redundancy Module

Using two PSM24 power supplies and a redundancy module, you can configure a redundant power system, featuring active current sharing, without any additional components. Even if one power supply fails or becomes disconnected, the second unit will supply full current to the load. The module has an alarm contact for monitoring of operations. The inputs are hot-swappable and can be loaded up to 15A each.



Redundancy Module							
Part Number	Price	Drawing Link	Input	Max Power per Input	Output Voltage Adjust	Output Power Max	
PSM24-REM360S (includes terminal plugs)	\$238.00	PDF	2 x 24VDC 2 x Control Input	2 x 360W	24VDC [24 - 27 VDC]	360W	

General Specifications					
Operating Temperature	-25 to 70°C max [-13 to 158°F], derating above 40°C [104°F]				
Electromagnetic Compatibility	In correspondence to connected units [no internal switching device]				
Redundancy OK Signal	Trigger threshold at 18 to 22VD				
Remote Link Wire 0.5m	Two cables included with PSM24-REM360S module				
Remote ON/OFF	By external contact: ON = J5.3 + J5.4 not shorted OFF = J5.3 + J5.4 shorted				
Alarm Contact Rating	30 VDC/1.0 A max				

Redundancy Module Function Diagram



Note: this redundancy module only works with the PSM series. Other series of power supplies are not compatible.

Redundancy Module Connector Positions



	Wiring Connections							
Pin	J1	J2	J3 Voltage control 1 for Input 1	J4 Voltage control 2 for Input 2	J5			
1	Input 1 -Vin	GND [-]	S+	S+	DC-OK Signal			
2	Input 1 +Vin	GND [-]	S-	S-	DC-OK Relay contact			
3	Input 2 -Vin	Vout [+]	_	_	Remote ON/OFF			
4	Input 2 +Vin	Vout [+]	_	_	Remote ON/OFF			
1-800-633-0405 RHINO PSM24-BFM600S Buffer Module



The buffer module will maintain the output voltage of a 24 VDC power supply after brownouts or voltage dips for up to 200ms at 25 amps. It is a cost effective alternative to a battery-based backup system. The operation modes are indicated by an LED on the front panel.

Storing the energy in a capacitor bank, this backup solution is completely maintenance free. Its storage capacity does not deteriorate over the lifetime of the unit.

Buffer Module						
Part Number	Price	Drawing Link	Input	Operating Voltage Range	Buffer Time	Output Power Max
PSM24-BFM600S (includes terminal plugs)	\$276.00	PDF	24VDC	22 to 28VDC	200 msec typical @ 25A max load 4.0 sec maximum @ 1.2A load	25.0 A [600W]

General Specifications				
Operating Temperature	-25 to 70°C max [-13 to 158°F], derating above 40°C [104°F]			
Electromagnetic Compatibility	In correspondence to connected units [no internal switching device]			
Buffer Voltage	Adjustable, >1 V below input voltage, min. 22 VDC			
Charging	0.6 A max/30s max			
Status Signals	Buffer Active, Buffer Ready [optocoupler output], dual-color LED for status indication			
Inhibit Input	Optocoupler input: supply between 5VDC and 28VDC to Inhibit			
Signal Output Ratings	10mA			

Buffer Module Function Diagram



Wiring Connections				
Pin	J1	J2		
1	+ Vin	Inhibit GND		
2	+ Vin	Inhibit +		
3	- Vin	Active GND		
4	- Vin	Active Signal		
5	FG	Ready GND		
6	_	Ready Signal		

Buffer Module Connector Positions



RHINO Power Supplies - Accessories PSM Series

A variety of accessories is available to complement the RHINO PSM power supplies. Choose panel mounting brackets and replacement plug kits from the table below, based on the size of the power supply. There is also a temperature sensor for the battery control module and replacement link cable for the redundancy and battery control modules.



Accessories				
Part Number	Price	Drawing Link	Description	
<u>PSM-PANEL1</u>	\$45.50	PDF	Panel mounting bracket. 1 bracket type A includes M4-screw [DIN 74-4fA] for 78W, 90W, 156W, 180W PSM power supplies	
PSM-PANEL2	\$39.50	PDF	Panel mounting bracket. 2 brackets type A include M4-screws [DIN 74-4fA] for 360W, 600W PSM power supplies	
<u>PSM-PK1</u>	\$8.50	N/A	Replacement plug kit for PSM series with 78W and 90W outputs	
<u>PSM-PK2</u>	\$12.50	N/A	Replacement plug kit for PSM series with 156W, 180W and 360W outputs	
<u>PSM-TS</u>	\$40.00	N/A	Temperature sensor for PSM24-BCM360S battery control module	
PSM-JC01	\$9.00	N/A	Replacement link cable for PSM series redundancy module PSM24-REM360S and battery control module PSM24-BCM360S	

Mounting

PSM power supplies are designed for mounting on a DIN rail. Please allow minimum free space of 80 mm (3.15") above and below, and 50 mm (1.97") on each side of the power supply for air convection. To attach unit onto the DIN rail, hook the top part of clip on DIN rail, then push down and inward until you hear the clipping sound. To remove, pull the latch of the clip using an insulated flathead screwdriver.

For wall or chassis mounting, use mounting brackets <u>PSM-PANEL1</u> (for 78W to 180W PSM style power supplies) or <u>PSM-PANEL2</u> (for 360W and 600W PSM power supplies). Remove the DIN clips and replace with the brackets. Use the countersink screws included with the wall mount kit to attach the brackets to the power supply. To attach the power supply to the DIN rail





To remove the power supply from DIN rail





PRO

Power Supplies PSN Series

Versatile Switching power supplies with Automatic Power Boost

AutomationDirect offers the RHINO PRO PSN power supply series which includes compliance with harmonic current IEC/EN 61000-3-2, class A, built-in DC OK contacts, and an LED for indicating DC OK and Overload conditions. In addition to having Power Boost of 150% up to 7 seconds, the PSN series features Advanced Power Boost (APB). With multiple loads connected in a system, a large inrush current could be drawn due to one fault load. This will be detected by APB. The APB will trip the circuit breaker (with appropriate rating based on the system load) on the current path of the fault load due to high current. This prevents the system from shutting down while the other connected current paths continue to operate without interruption.

Features

- Universal AC input voltage range (1 Phase Units)
- Built-in constant current circuit for charging applications (3 Phase Units)
- Built-in active PFC* with up to 96% efficiency
- Full power from -25 to +60°C @ 5,000m (16,400 ft.)
- Power Boost of 150% up to 7 seconds
- Advanced Power Boost (APB) protects the system and ensures continuing operation when a large inrush current is detected due to faulty load on a multiple load connection
- Built-in DC OK Contact and LED indicator for DC OK/Overload
- Conformal coating on PCBAs to protect against common dust and chemical pollutants
- * Active Power Factor Correction (PFC) Active wave shaping of the input current, filtering of the high frequency switching, feedback sensing of the source current for waveform control



PSN24-080

PSN24-120







PSN24-480



PSN24-960



PSN24-480-3



PSN24-960-3

	Industrial Power Supplies PSN Series					
Part Number	Price	Output Voltage [V _{nom}]	Output Current [I _{max}]	Output Power [P _{max}]	Weight kg [lb]	Drawing Links
PSN24-080	\$107.00		3.4 A	80W	0.50 [1.10]	PDF
<u>PSN24-120</u>	\$142.00		5.0 A	120W	0.63 [1.39]	PDF
<u>PSN24-240</u>	\$208.00		10.0 A	240W	0.94 [2.07]	PDF
<u>PSN24-480</u>	\$318.00	24VDC	20.0 A	480W	1.40 [3.09]	PDF
<u>PSN24-960</u>	\$485.00		40.0 A	960W	2.87 [6.33]	PDF
<u>PSN24-480-3</u>	\$321.00		20.0 A	480W	1.18 [2.60]	PDF
PSN24-960-3	\$509.00		40.0 A	960W	2.30 [5.07]	PDF



Power Supplies PSN Series

	Input Specifications									
Part Number	Nominal Input Voltage Range	Operating Voltage min/mox	Input Frequency Bange	Input ([Typ. @	Current full load]	Inrush Limit [<2ms) (Current tation @+25°C]	Max Power Dissipation	Efficiency [Typ]	Circuit Breaker [Minimum]
	nungo	mminiax	naiiye	120VAC	230VAC	120VAC	230VAC			
<u>PSN24-080</u>			/AC	0.76 A	0.44 A	7.0 A	13.0 A	9.5 W	91% @ 120VAC	
<u>PSN24-120</u>	100-240 VAC	85-276 VAC 88-375 VDC 47-63Hz 5-276 VAC		1.09 A	0.60 A	15.0 A	15.0 A	12.6 W	92% @ 120VAC	
<u>PSN24-240</u>	110-300 VDC			2.17 A	1.16 A	10.0 A	10.0 A	23.5 W	93% @ 120VAC	6A to 16A
<u>PSN24-480</u>			4.24 A	2.29 A	101	13A	46W	93% @ 120VAC		
<u>PSN24-960</u>	85-264 VAC			8.60 A	4.50 A	13A	17 A	70W	95% @ 120VAC	
PSN24-480-3				400VAC	480VAC	400VAC	480VAC	26 4 W	95% @ 480VAC	6A B-type
	3 x 400-500 VAC	3 x 320-575 VAC		0.78 A	0.67 A	10A	10A			3A C-type
<u>PSN24-960-3</u>				1.53 A	1.28 A	14.2 A	17A	48.4 W	96% @ 480VAC	6A

	Output Specifications								
Part Number	Output Voltage	Output Voltage Adj. Range	Output Current [Max]	Power Boost [7 seconds]	Output Overvoltage Protection	Startup with Capacitative Loads [Max]	Startup Time	Relay Output	MTBF [@ 25°C]
<u>PSN24-080</u>			3.4 A	5.0 A		8,000 µF	370ms @120VAC		2,164,300 hrs
<u>PSN24-120</u>			5.0 A	7.5 A		10.000E	750ms @ 120VAC		1,831,000 hrs
<u>PSN24-240</u>			10.0 A	10.0 A 15A 28.8-35.2 V	ι 10,000 με	650ms @120VAC	DC OK = contact	1,476,000 hrs	
<u>PSN24-480</u>	24VDC	24-28 VDC	20.0 A	30A		20,000 µF	1000ms @ 120VAC	closed [rated:30 VDC	778,800 hrs
<u>PSN24-960</u>			40.0 A	60A		40,000 µF	800ms @ 120VAC	1.0 A]	513,800 hrs
<u>PSN24-480-3</u>			20.0 A	30A	<32.1/	20,000 µF	500ms @ 480VAC		750,000 hrs
<u>PSN24-960-3</u>			40.0 A	60A	~32 V	40,000 µF	1000ms @ 480VAC		568,300 hrs



Power Supplies PSN Series

General Specifications						
Specification		Description				
Temperature	Operating [ambient]: -25 to 70°C max [-13 to 158°F]. Above +60°C[140°F] load derating Storage [non-operating]: -40 to 85°C max [-40 to 185°F]. Cooling: convection, no internal fan					
Humidity		5-95% [non-condensing] relative humidity maximum				
Isolation	According to IEC/EN 60950, EN62477-1, EN60204, CSA					
Mains Buffering at Nominal Load		See Product Insert				
Output Regulation	10mV [except 120W = 20mV] [100% load]					
Output Voltage Ripple	100mVp	p [except 80W/120W/240W 1-Ph :50mV]	[20 MHz bandwidth]			
Output Protection	1Ph models: > 150% of rated load current, Constant current, Hiccup Mode [Auto-Recovery]	480W 3Ph: 160-195% of rated load current, Constant current, Hiccup Mode [Auto-Recovery]	960W 3Ph: 150-200% of rated load current, Constant current, Hiccup Mode [Auto-Recovery]			
Overtemperature Protection		Switch off at over-temperature, automa	atic restart			
Status Indicators		Two color LEDs [green: DC Ok, Red:	Overload]			
Maximum Capacitative Load	1Ph 80W: 8,000uF, 1Ph 120W: 10,000	uF, 1Ph 240W: 10,000uF, 1Ph 480W: 20, 3Ph 960W: 40,000uF	000uF, 1Ph 960W: 40,000uF, 3Ph 480W: 20,000uF,			
Noise (1 meter from power supply)		Sound Pressure Level [SPL] < 25	5dBA			
Vibration	IEC 60068-2-6, Sine Wave: 10	0-500Hz; 3G peak; displacement of 0.35m	nm; 60 min per axis for all X, Y, Z directions			
Shock	IEC 60068-2-27, Half \$	Sine Wave: 30G for a duration of 18ms; 3	times per direction, 6 times in total			
Enclosure Rating		IP20				
Enclosure Material		Aluminum				
Mounting		Snap-on with self-locking spring for 35m	nm DIN rails			
Connection	Sc	rew terminals, See Insert for wire size an	d torque ratings			
Agency Approvals	UL/C-UL recog UL/C-UL recog UL/C-UL Sing	nized to UL60950-1 and CSA C22.2 No. nized to UL62368-1 and CSA C22.2 No. listed to UL508 and CSA C22.2 No. 107. gle-phase only: CSA C22.2 No. 107.1-01;	60950-1; File No. E198298, 62368-1; File No. E508040, 1-01; File No. E197592 File No. 249074			

Note: Unless otherwise stated all specifications are valid at nominal input voltage, full load and +25°C after warm up time.

	Standards/Directives				
Specification	Standard	Document Number			
Harmonic Limits	Harmonic Current Limits	EN 61000-3-2, Class A for limited output power			
	Information technology equipment	UL/C-UL recognized to UL60950-1 and CSA C22.2 No. 60950-1; File No. E198298, UL/C-UL recognized to UL62368-1 and CSA C22.2 No. 62368-1; File No. E508040			
Safety Standards	Industrial control equipment	UL/C-UL listed to UL508 and CSA C22.2 No. 107.1-01; File No. E197592 CSA to CSA C22.2 No. 107.1-01; File No. E249074, except 3 Phase input.			
	Electrical equipment of machines	IEC60204-1 [over voltage category III]			
	Electronic equipment for power installation	IEC/EN 62477-1 / IEC62103			
	Safety, Transient surge voltage protection	VARISTOR			
Safety Approvals	CB-Report per IEC 60950	IEC 60950-1, IEC 61558-1, IEC 61558-2-16, IEC 61010-1, IEC 61010-2-201			
Safety Class	Degree of electrical protection Class1 Class I with GND connection				
CE	In conformance v	vith EMC directive 2014/30/EU and low voltage directive 2014/35/EU			
RoHS Compliant		Yes			
Electromagnetic Compatibility (EMC), Emissions	EMC, Emissions	Generic Standards: EN 61000-6-3 CISPR 32, EN 55032, CISPR 11, EN 55011, FCC Title 47: Class B			
	EMC, Immunity	EN 55024, EN 61000-6-2			
	Electrostatic Discharge [ESD]	IEC 61000-4-2 Level 4 Criteria A Air Discharge: 15kV; Contact Discharge: 8kV			
	Radiated RF field immunity [80-1000 MHz]	IEC / EN 61000-4-3 80MHz-1GHz, 10V/M, 80% modulation [1kHz]; 1.4GHz-2GHz, 10V/M, 80% modulation [1kHz]; 2GHz-2.7GHz, 10V/M, 80% modulation [1kHz]			
Electromagnetic Compatibility	Electrical fast transient / burst immunity	IEC / EN 61000-4-4 Level 4 Criteria A 4kV			
(EMC), Immunity	Surge immunity	IEC / EN 61000-4-5 Level 4 Criteria A Common Mode: 4kV Differential Mode: 2kV			
	Immunity to conducted RF disturbances [0.15 to 80 MHz]	IEC / EN 61000-4-6 Level 3 Criteria A 150kHz-80MHz, 10Vrms			
	Power frequency field immunity	IEC / EN 61000-4-8 30 A / m			
	Voltage dips	IEC / EN 61000-4-11 [70% UN Crit. B/40%/100% UN Crit. C]			
Pollution Degree		2			

RHINC PRO **Power Supplies PSN Series**

Engineering Data for RHINO PRO PSN Series Power Supplies

Output Load De-rating VS Surrounding Air Temperature

- Note:
- Power supply components may degrade, or be damaged, when the power supply is continuously used outside the shaded region.
- If the output capacity is not reduced when the surrounding air temperature exceeds its specification as defined under "Temperature" in the General Specifications table, the device will run into Over Temperature Protection. When activated, the output voltage will go into bouncing mode and will recover when the surrounding air temperature is lowered or the load is reduced as far as necessary to keep the device in working condition.
- In order for the device to function in the manner intended, it is also necessary to keep a safety distance as recommended in the safety instructions while the device is in operation.
- Depending on the surrounding air temperature and output load delivered by the power supply, the device can be very hot!

Power Derating Curve for PSN24-080, PSN24-120, PSN24-240



PSN Series Derating for Mounting Position						
Part Number	Vertical Orientation	Horizontal Orientation				
<u>PSN24-080</u>						
<u>PSN24-120</u>	> 60°C de-rate power by 2.5% / °C	> 50°C de-rate power by 2.5% / °C				
<u>PSN24-240</u>						

PRO

Power Supplies PSN Series

Power Derating Curve for PSN24-480



RHINO P	RO PSN Series Derating	g for Mounting Position		
Part Number	Vertical Orientation	Horizontal Orientation		
PSN-480	> 60°C de-rate power by 2.5% / °C	> 40°C de-rate power by 1.67% / °C		

Power Derating Curve for PSN24-960



<90 VAC	

Derating for Mounting Position PSN Series					
Vertical Orientation		rientation	Horizontal Orientation		
Part Number	<90 VAC	90-264 VAC	<90 VAC	90-264 VAC	
<u>PSN24-960</u>	> 55°C de-rate power by 1.67% / °C	> 60°C de-rate power by 2.5% / °C	> 35°C de-rate power by 1.43% / °C	>40°C de-rate power by 1.67% / °C	

RHINO Power Supplies PSN Series

Power Derating Curve for PSN24-480-3



Derating for Mounting Position PSN Series					
Dout Number	Vertical Orientation		Horizontal Orientation		
Part Number	3-Phase	2-Phase	3-Phase	2-Phase	
PSN24-480-3	> 60°C de-rate power by 2.5% / °C		> 40°C de-rate power by 1.67% / °C	> 40°C de-rate power by 2.0% / °C	

Power Derating Curve for PSN24-960-3



V _{in}	Vertical Mounting	Horizontal Mounting
3-Phase		
2-Phase		

Derating for Mounting Position PSN Series					
Vertical Orientation			Horizontal Orientation		
	3-Phase	2-Phase	3-Phase	2-Phase	
PSN24-960-3	> 60°C de-rate power by 2.5% / °C	> 50°C de-rate power by 2.5% / °C	> 40°C de-rate power by 1.67% / °C	> 40°C de-rate power by 2% / °C	

2-Phase

1-800-633-0405 **RHINO 5,12 & 24 VDC Power Supplies PSP Series**





Slimline Power Supplies

RHINO PSP series power supplies are plastic housed ultracompact switching supplies available in 5V, 12V and 24V adjustable models. There are 13 models available with power ratings of 20W to 240W and up to 10A output current. They are DIN rail or panel-mountable and feature universal inputs, adjustable DC voltage outputs, power good signal and feature low output ripple along with short circuit, overvoltage and overload protection.

The RHINO PSP series of switching power supplies offer an excellent price/performance ratio. They provide tightly regulated output voltage for sensitive loads in industrial environments. The slim plastic case is lightweight and compact, and comes in both screw and spring clamp terminal versions. The constant-current, short-circuit protection limits the output current as the voltage is reduced, to safely protect the control components from direct shorts and device failures. Once a fault is corrected, the power supply automatically resumes supplying full-voltage power. (PSPxx-024x models have foldback current protection with auto-recovery.)

The RHINO PSP power supplies have a Power ON LED for easy visual indication of operation as well as a Power Good signal for feedback to your system controller.

With a UL 508C rating, the RHINO PSP series is the right choice for space limited applications.

Features

- Regulated switch mode type
- Ultra-compact plastic case
- Finger-safe terminals
- Reliable snap-on mounting on DIN rails
- Wall mounting bracket included
- Universal input 120/240VAC, 50/60Hz or 85-375 VDC (120 or 240VAC only for <u>PSP24-240S</u> input)
- Models with 5, 12 or 24 VDC output
- Output voltage adjustable
- Parallel operation up to five units (not <u>PSP24-240S</u>)
- Power good signal (some models)
- Low ripple and noise
- Overload and short-circuit protection
- UL/cUL 508 listed, UL/cUL 60950 recognized*
- Worldwide safety approvals
- 3-year warranty

* Note:<u>PSP24-240S</u> is not cUL listed. <u>PSP05-020S</u>, <u>PSP12-024S</u>, and <u>PSP24-240S</u> are not UL 60950 recognized.

For the latest prices, please check AutomationDirect.com.

RHINO 5,12 & 24 VDC Power Supplies PSP Series



PSP05-020S PSP12-024S PSP24-024S



PSP24-024C



PSP12-060S PSP24-060S



PSP12-060C PSP24-060C



PSP12-120C PSP24-120C



PSP24-120S PSP12-120S



<u>P3P24-2403</u>	
www.automationdirect	com

	Input Specifications						
Part Number	Input Voltage Range		Input Freq.	Input Curre at ful	Input Current [Typical] at full load		C-Curve Circuit Breaker or Slow-
			Range	115 VAC	230 VAC	115VAC]	blow Fuse
<u>PSP05-020S</u>		30% output derating below 93 VAC/ 130 VDC		0.35 A	0.2A	82%	
<u>PSP12-024S</u>						82%	
<u>PSP24-024S</u>		20% output derating below 93 VAC/ 130 VDC	0.35 A	0.25 4	0.0.4	85%	5.0 A
PSP24-024C				0.55 A	0.2 A	85%	
<u>PSP12-060S</u>	85-264 VAC				0.04	81%	
PSP12-060C	85-375 VDC			104		81%	
PSP24-060S	UL Approved for 100-240 VAC only	15% output derating below 93 VAC/ 130 VDC	15% output derating	40 VAC only 15% output derating	0.6 A	83%	
PSP24-060C					iting		83%
PSP12-120S	below 93 VAC/ 130 VDC				77%		
PSP12-120C				2.0.4	104	77%	
PSP24-120S				2.0 A	1.0 A	80%	
PSP24-120C						80%	
<u>PSP24-240S</u>	85-132/ 187-264 VAC	20% output derating below 93 VAC		4.7 A	2.0 A	82%	

Output Specifications										
Part Number	Price Di	Drawing	Output	Output Volt.	Output Current	Output Power	Hold-Up Time		MTBF IIEC 1709 @	
		LINK	voitage	Adjust. Kange	[Max]	[IVIAX]	115 VAC	230 VAC	25℃] Ŭ	
<u>PSP05-020S</u>	\$91.00	PDF	5.1 VDC	5-5.25 VDC	4.0 A	20W				
PSP12-024S	\$110.00	PDF	12 VDC	12-16 VDC	2.0 A	24W			2,681,000	
<u>PSP24-024S</u>	\$84.00	PDF		24.29.1/00	104	24\\/			hours	
<u>PSP24-024C</u>	\$89.00	PDF	24 VDC	24-20 VDC	1.0 A	2470				
<u>PSP12-060S</u>	\$143.00	PDF			4.0 A	48W @ 12VDC 60W @ 60VDC			2,947,000	
<u>PSP12-060C</u>	\$162.00	PDF	12 000	12-15 VDC						
<u>PSP24-060S</u>	\$128.00	PDF	24 VDC	24.1/DC 24.2	24-28 \/DC	254	6014	15 ms	125 ms	hours
<u>PSP24-060C</u>	\$129.00	PDF		24-20 VDU	2.5 A	0000				
<u>PSP12-120S</u>	\$230.00	PDF	12 100		0 0 4					
<u>PSP12-120C</u>	\$203.00	PDF	12 VDC	12-13 VDC 0.0 A	12-15 VDC 0.0 A	8.0 A			1,620,000	
<u>PSP24-120S</u>	\$201.00	PDF			5.0.0	12000			hours	
PSP24-120C	\$214.00	PDF	24 VDC	24-28 VDC	5.0 A					
<u>PSP24-240S</u>	\$270.00	PDF			10.0 A	240W			1,912,000 hours	



The unit can be mounted on a chassis or wall using the included mounting bracket.

Part numbering system



For the latest prices, please check AutomationDirect.com.

RHINO 5,12 & 24 VDC Power Supplies PSP Series

	General Specification	ns		
Temperature	Operating: -10 to 70°C [14 to 158°F], Derating at 93-132 VAC or 130-187 VDC: -1.10%/C above 40°C, Derating at 187-264 VAC or 265-375 VDC: -1.67%/C above 50°C, Derating at 85-93 VAC or 85-130 VDC: -1.30%/C above 30°C, Temperature Coefficient: 0.02%/C Storage: -25 to 85°C [-13 to 185°F]			
Humidity	95% [non-cor	ndensing] relative humidity max.		
Output Regulation	2.5% [1% for PS	P12-060x], 10 to 90% load variation		
Switching Frequency	55 - 18	80 kHz depending on load		
Safety Standards	IEC/EN 60950 [output SELV], UL	60950, UL 508, EN 50178, EN 60204, EN 61558-2-8		
Output Voltage Ripple	<50 mV peak-to-peak			
Output Protection	Current Limit at 120% typ., constant current, auto recovery [PSPxx-024x foldback, auto-recovery], Voltage Limit <40 VDC			
Power Good Signal*	Trigger Point 12VDC Models: >11 V 24VDC Models: >22 V	Output Signal [reference to -Vout] 11.0 V+/- 1.0 V @ 60 mA max. 22.0 V+/- 2.0 V @ 30 mA max.		
Electromagnetic Compatibility (EMC)	EN 61000-3-	2, EN 61000-6-2, EN 61000-6-3		
Enclosure Rating		IP 20		
Enclosure Material	Plastic FR	2010-110C [UL 94 V-O rated]		
Mounting	35mm DIN rails, snap on with	self-locking spring or wall mount adapter included		
Weight g[oz]	PSP05-020S, PSP12-024S, PSP24-024x: 40 (4.9), PSPxx-060x: 265 (9.4), PSPxx-120x: 440 (15.5), PSP24-240S: 50 (33.5)			
Connection	S models: Plug-in Screw Terminals, wire stripping length 7-8mm, C Models: Clamp Terminals, wire stripping length 6mm. For 28-12 AWG wire.			
Agency Approvals	UL/cUL 508 listed; Fi UL 60950 recognized; File No. E19829	le No. E197592 (<u>PSP24-240S</u> not cUL), /8 (except <u>PSP05-020S, PSP12-024S</u> and <u>PSP24-240S</u>).		

*Note: PSP05-020S, PSP12-024S and PSP24-024x models do not have Power Good output.

Note: All specifications are valid at nominal input voltage, full load and +25°C after warmup time, unless otherwise stated.

PSP05-020S, PSP12-024S, PSP24-024x

Input		0	Output
1	AC Ground	1	+Vout
2	Neutral	2	-Vout
3	Line		

PSPxx-120x

	Input		Output
1	AC Ground	1	+Vout
2	Neutral	2	+Vout
3	Line	3	-Vout
-	-	4	-Vout
-	-	5	Power Good

PSPxx-060x

	Input		Output
1	AC Ground	1	+Vout
2	Neutral	2	+Vout
3	Line	3	-Vout
-	-	4	-Vout
-	-	5	Power Good

PSP24-240S

	Input		Output
1	AC Ground	1	+Vout
2	Neutral	2	+Vout
3	Line	3	-Vout
-	-	4	-Vout
-	-	5	Power Good

1-800-633-0405 For the latest prices, please cheat RHINO <u>PSP24-REM240S</u> Redundancy Module

The PSP24-REM240S redundancy module used with two matched power supplies creates redundancy to help prevent costly downtime due to power supply failure. The PSP24-REM240S decouples the outputs of the two connected power supplies so that in case of failure, one power supply cannot overload the other.



PSP Redundancy Module							
Part Number	Price	Drawing Link	Input Voltage Range	Max Power per Input	Output Voltage	Output Current Max.	Connection
PSP24-REM240S	\$71.00	<u>PDF</u>	2 x 5 – 60 VDC	144W	V in - 0.9 VDC	8 A	Detachable screw terminal block

PSP24-REM240S General Specifications					
Temperature	Operating: -10 to 70°C max [14 to 158°F max], Storage: -25 to 85°C max, [-13 to 185°F max], Cooling: Natural air convection				
Parallel Operation (2) matched power supplies per module. Maximum power shall not exceed 200 watts per input.					
Electromagnetic Compatibility In correspondence with connected power supplies					
Enclosure Material	Gray plastic, FR2010-110C [UL94 V-0 rated]				
Mounting	Built-in snap-on connection for 35mm DIN rail or surface mount adapter included				
Indication	Green LED for Output ON				
Connections	Plug-in screw terminals, 0.5 to 0.7Nm [4.5 to 6.2lb-in] recommended tightening torque, wire stripping length 7-8mm				
Wire Size range 24 to 12 AWG [0.21 to 3.16 mm²]					
Agency Approvals	UL/cUL 508 listed; File No. E197592, CE				



	Input		Output
1	+Vin1	1	+Vout
2	+Vin2	2	+Vout
3	Common		

Redundancy Module Connector Positions



Recommendations for redundant PSP Series power supply applications:

- With no load connected, adjust the output voltage of both power supplies to the same value.
- Use separate input over-current protection for each power supply.
- When possible, connect the input power to each power supply to different phases or circuits.
- When available on the connected power supplies, use the DC-OK output and/or DC-ON LED on each power supply to monitor for failure. (<u>PSP05-020S</u>, <u>PSP12-024S</u> and PSP24-024x do not have DC-OK output).
- Connect all output leads together at a single distribution node using leads having the same length and cross section.

1-800-633-0405 For the latest price RHINO Power Supplies PSL Series

Low Cost NEC Class 2 Supplies*

The RHINO PSL series power supplies are plastic low-profile switching supplies available in 5, 12 and 24VDC output models. There are 9 models with power ratings from 7.5W to 91W. They have an integral DIN rail mounting adapter and feature universal 90VAC to 264VAC input voltage, DC-OK LED indication, and output current limitation. Some models feature adjustable DC output.

These are designed to fit in shallow depth control panels often used in the building automation industry. Screw terminals are provided for simple and speedy wiring terminations.

The RHINO PSL series is both UL508 listed for demanding industrial applications and UL60950-1 recognized for NEC Class 2* compliance in industrial, commercial, and residential applications.



Features

- Low-profile housing only 2.15 inches (55mm) deep (MCB form factor)
- 5, 12, 24VDC outputs
- (adjustable models available in 12 and 24VDC)
- Output power ratings from 7.5 to 91W
- Integral DIN rail mounting adapter
- Universal input voltage range 90-264 VAC, 125-375 VDC
- DC-OK LED indication
- UL508 Listed, File No. E198298
- UL60950-1 Recognized for NEC Class 2 compliance*
- Protection Class II Double Isolation

Note: * PSL-12-090 is not NEC Class 2



PSL-05-010, PSL-12-010, PSL-24-010



PSL-12-030, PSL-24-030





PSL-12-060, PSL-24-060

	Single-Phase Input																			
Part Number	Price	Drawing Link	Input Voltage Range	Input Frequency Range	Input Current Max [@ 115/230 VAC]	Inrush Current l2t @ 77°F [+25°C] typ [@ 115/230 VAC]	Efficiency [Typ @ 115VAC]	Recommended Backup Protection	Turn-on Time											
<u>PSL-05-010</u>	\$35.00	PDF					81%	8A B -or 4A C												
<u>PSL-12-010</u>	\$32.00	PDF			0.3 A / 0.2 A	<15A / <30A	85%	characteristic circuit breaker												
<u>PSL-12-030</u>	\$42.00	<u>PDF</u>			0.8 A / 0.6 A	<25A / 50A	86%	13A B -or 8A C characteristic circuit breaker	<3 sec											
<u>PSL-12-060</u>	\$57.00	PDF	400.040.1/0.0.1/		1.5 A / 1.0 A	<30A / 60A	85%	16A B -or 8A C												
<u>PSL-12-090</u>	\$73.00	PDF	Approved		1.5 A / 0.9 A	<40A / <80A	87%	characteristic circuit breaker	<1.5 sec											
<u>PSL-24-010</u>	\$35.00	<u>PDF</u>	90-264 VAC 125-375 VDC	90-264 VAC 125-375 VDC	90-264 VAC 125-375 VDC	90-264 VAC 125-375 VDC	90-264 VAC 125-375 VDC	90-264 VAC 125-375 VDC	90-264 VAC 125-375 VDC	90-264 VAC 125-375 VDC	90-264 VAC 125-375 VDC	90-264 VAC 125-375 VDC	90-264 VAC 125-375 VDC	90-264 VAC 125-375 VDC	90-264 VAC 125-375 VDC	0.3 A / 0.2 A	<15A/<30A	85%	16A B -or 8A C characteristic circuit breaker	
<u>PSL-24-030</u>	\$42.00	<u>PDF</u>			0.8 A / 0.6 A	<25A / <50A	88%	13A B -or 8A C characteristic circuit breaker	<3 sec											
PSL-24-060	\$57.00	PDF			1.5 A / 1.0 A	<30A / <60A	82%	16A B -or 8A C												
<u>PSL-24-090*</u>	\$73.00	<u>PDF</u>			2.2 A / 1.0 A	<30A / <60A	82%	characteristic circuit breaker	<1.5 sec											

*PSL-24-090 is UL Listed for 125-250 VDC input.

Single-Phase Output							
Part Number	Output Voltage	Output Voltage Range	Output Current [A]	Output Power [Max] [W]	Min. Hold-Up Time at Nominal Load [@115/230VAC]		
PSL-05-010	5VDC	N/A	1.5	7.5	10		
PSL-12-010		N/A	0.83	10	Toms / 30ms		
PSL-12-030	10\/DC		2.1	25	25ms / 30ms		
PSL-12-060	12VDC	11.5-14.5 VDC	4.5	54	16ms / 30ms		
PSL-12-090		12-14 VDC	6.0	72	18ms / 30ms		
PSL-24-010		N/A	0.42	10	10ms / 30ms		
PSL-24-030	24VDC	24.29.100	1.25	30	25ms / 30ms		
PSL-24-060		24-26 VDC	2.5	60	16ms / 30ms		
PSL-24-090		22-24 VDC	3.8	91.2	10ms / 30ms		

www.automationdirect.com

Power Supplies †

1-800-633-0405 For the latest price RHINO Power Supplies PSL Series

General Specifications					
Enclosure Material	Plastic [PC], closed				
Signals	Green LED DC OK				
MTBF	> 500,000 hrs. as per Telcordia				
Connection method	Screw connection				
Protection Class II	to IEC/EN 60536				
Leakage Current	<0.25mA @ 240VAC				
Startup with capacitive loads	Max. 3,000µF				
Line Regulation	< 1% typ. [@ 90-264Vac, 100% load]				
Load Regulation	< 2% typ. [@ 90-264Vac, 100% load]				
Residual ripple/ peak switching (20MHz) (at nominal values)	< 50mVpp / < 150mVpp				
Operating Temperature (Surrounding air temperature)	-25 to 71°C [-13 to 160°F] Derate above +55°C [2.5%/°C]				
Storage Temperature	-25 to 85°C [-13 to 185°F]				
Humidity at 25°C, no condensation	< 95% RH				
Vibration (operating)	IEC60068-2-6, Sine Wave: 10-500Hz @ 19.6m/S ² [2G peak]; 10 min per cycle, 60 min for all X, Y, Z directions				
Shock (operating)	IEC60068-2-27, Half Sine Wave: 4G for a duration of 22ms, 3 shocks for each 3 directions, 9 times in total				
Pollution degree	Pollution degree 2				
Altitude (operating)	2000m [6562ft] maximum				

Certification and Standards					
Safety entry low voltage SELV [EN60950]					
Electrical safety (of information technology equipment)	UL/C-UL recognized to UL60950-1 and CSA C22.2 No. 60950-1, CB scheme to IEC60950-1, Limited Power Source [LPS] <u>PSL-12-090</u> is not LPS				
Industrial control equipment	UL/C-UL listed to UL508 and CSA C22.2 No. 107.1-01; File No. E197592				
Class 2 Power Supply	UL/C-UL recognized to UL60950-1 and CSA C22.2 No. 60950-1; File No. E198298 PSL-12-090 is not a Class 2 power supply				
CE	In conformance with EMC directive 2014/30/EC and low voltage directive 2014/35/EC				
ITE	EN55032, EN61000-3-2, EN61000-3-3, EN55024				
RoHS	Yes				

Additional Data						
Part Number	Weight kg [lb]	Wire Size / Torque*				
PSL-05-010	0.06 [0.13]	26.120M/C / 0.9 N = [7.0 k =]				
PSL-12-010	0.06 [0.13]	26-12AWG / 0.8 N·m [7.0 lb-lh]				
PSL-12-030	0.14 [0.31]	24-12AWG / 0.45 N·m [4.0 lb-in]				
PSL-12-060	0.22 [0.49]	22-12AWG / 0.45 N·m [4.0 lb-in]				
PSL-12-090	0.35 [0.77]	20-12AWG / 0.45 N·m [4.0 lb-in]				
PSL-24-010	0.06 [0.13]	26-12AWG / 0.8 N·m [7.0 lb-in]				
PSL-24-030	0.14 [0.31]	24-12AWG / 0.45 N·m [4.0 lb-in]				
PSL-24-060	0.22 [0.49]	22-12AWG / 0.45 N·m [4.0 lb-in]				
PSL-24-090	0.35 [0.77]	2x24 AWG or 22-12AWG / 0.45N·m [4.0 lb-in]				

*Stripping length 7mm [0.28 in]

1-800-633-0405 For the latest prices RHINO Power Supplies PSC Series

NEC Class 2 Compliant Supplies

The RHINO PSC series power supplies are plastic low-profile housed switching supplies available in 5, 12 and 24 VDC adjustable output models. There are 8 models with power ratings from 12W to 90W. They have an integral DIN rail mounting adapter and feature universal 120/240 VAC input voltage, adjustable DC output, DC-OK LED indication, and output current limitation.

The RHINO PSC series of switching power supplies provide tightly regulated output voltage for sensitive loads in industrial, commercial and residential environments. The plastic housing is lightweight and low-profile, designed to fit in shallow depth control panels often used in the building automation industry. Screw terminals are provided for simple and speedy wiring terminations.

The RHINO PSC series is both UL508 listed for demanding industrial applications and UL1310 recognized for NEC Class 2 compliance in industrial, commercial and residential applications.



Features

- Low-profile housing only 2.15 inches (55mm) deep (MCB form factor)
- 5, 12, 24VDC adjustable outputs
- Output power ratings from 12 to 90W
- Integral DIN rail mounting adapter
- Universal input voltage range 120/240 VAC
- Tight output voltage regulation
- DC-OK LED indication
- UL508 Listed
- UL1310 Recognized for NEC Class 2 compliance
- CE compliant
- RoHS compliant



PSC-05-012, PSC-12-015, PSC-24-015









PSC-12-060, PSC-24-060

PSC-24-090

Input Specifications							
Part Number	Input Voltage Range	Input Frequency	Input Current [Ty	pical] at full load	Efficiency [Typ @ 115VAC]	C-Curve Circuit Breaker	
		Kange	115 VAC	230 VAC		or Slow-Dlow Fuse	
PSC-05-012			0.25A typ.	0.17A typ.	76%		
PSC-12-015			0.204 trm	0.204.hm	78%		
PSC-24-015	100-240VAC - Nominal 85 to 264VAC - Universal [output power derating 5% / V for operation below 90 VAC]	47-63 Hz	0.29A typ.	0.20A typ.	79%	6.0 A	
PSC-12-030			0.57A typ.	0.57A typ. 0.39A typ.	81%		
PSC-24-030					84%		
PSC-12-060			1.00A typ.	0.68A typ.	83%		
PSC-24-060			1.10A typ.	0.70A typ.	85%		
PSC-24-090			1.60A typ.	1.07A typ.	87%		

Output Specifications									
Part Number	Price	Drawing	Output	Output Volt. Adjust.	Max Output Current	Max Output Power	Hold-U	p Time	MTBF
		Link	Voltage	Range	[A]	[W]	115 VAC	230 VAC	[IEC 1709 @ 25°C]
<u>PSC-05-012</u>	\$67.00	PDF	5.0VDC	5.0 to 5.2VDC	2.4	12			
PSC-12-015	\$67.00	PDF	12.0VDC	12.0 to 16.0VDC	1.25	45			1,600,000 hours
PSC-24-015	\$65.00	PDF	24.0VDC	24.0 to 28.0VDC	0.63	10			
PSC-12-030	\$68.00	PDF	12.0VDC	12.0 to 16.0VDC	2.5	20	minimum	minimum	1 200 000 hours
PSC-24-030	\$86.00	PDF	24.0VDC	24.0 to 28.0VDC	1.25	30	10 ms	20 ms	1,500,000 nours
PSC-12-060	\$86.00	PDF	12.0VDC	12.0 to 16.0VDC	4.5	54			0.400.000 hours
PSC-24-060	\$103.00	PDF	24.0VDC		2.5	60			2,100,000 hours
PSC-24-090	\$127.00	PDF	24.0VDC	24.0 to 28.0VDC	3.75	90			1,300,000 hours

1-800-633-0405 For the latest prices RHINO Power Supplies PSC Series

General Specifications						
Temperature	Operating: -25 to 60°C [-13 to 140°F] max at nominal load, above +60°C [+140°F] 2.5% / °C derating up to +70°C [+185°F] Storage: -25 to 85°C [-13 to 185°F] max					
Humidity	95% [non-condensing]	relative humidity max.				
Output Regulation	19	6				
Protection Class II	to IEC/EN 60536					
Safety Standards	UL508, UL1310, Class 2 IEC/EN 60950-1, UL60950-1, EN50178 EN60204, EN61558-2-8					
Output Voltage Ripple	<100 mV peak-to-peak					
Output Protection	Current limitation at 100 - 150	0% typ. [automatic recovery]				
Electromagnetic Compatibility (EMC)	Emissions - EN61000-6-3 Conducted RI suppression on input - EN55032 class B Radiated RI suppression - EN55032 class B FCC Class B	Immunity - EN61000-6-2 EN61000-4-X				
Enclosure Rating	IP 20 [IEC	C 60529]				
Enclosure Material	Plastic FR2010-110C [UL 94V- 0 rated]					
Mounting	DIN rails as per EN50022-35x15/735 [snap-on with self-locking springs]					
Connection	Screw terminals with combi-type screw heads for wire size 24 to 12AWG [0.20 to 3.30mm ²]					
Agency Approvals	UL508 Listed, Fi UL1310 Class 2 Recogn	le No.E197592 ized, File No. E198298				

	Wiring	
Input/Output	Description	Wire size
AC Input	all models: L, N only [2 pin terminal]	24 -12AWG / 3.30mm ² max
DC Output	15 -30 Watt models: single + and - terminals	24 -12AWG / 3.30mm ² max
DC Output	60 - 90 Watt models: double + and - terminals	24 -12AWG / 3.30mm² max

Weight				
Part No.	Weight oz [g]			
<u>PSC-05-012</u>	3.53 [100]			
<u>PSC-12-015</u>	3.53 [100]			
PSC-24-015	3.53 [100]			
<u>PSC-12-030</u>	5.64 [160]			
<u>PSC-24-030</u>	5.64 160]			
<u>PSC-12-060</u>	8.11 [230]			
<u>PSC-24-060</u>	8.11 [230]			
<u>PSC-24-090</u>	12.0 [340]			

1-800-633-0405 **RHINO 12 VDC and 24 VDC Power Supplies PS** Series

Switching power supplies at linear supply prices

The PS Series power supplies give you consistent, reliable, switched DC power at linear power supply prices.

These power supplies use efficient switching technology to produce the most power in the smallest space, while generating a minimum amount of heat. The constant-current short circuit protection limits the output current as the voltage is reduced to safely protect your control components from direct shorts and device failures. Once the short is corrected, the PS Series power supplies automatically resume supplying fullvoltage power. Precisely regulated output power is suitable for battery charging applications. Extra-sturdy DIN rail mounts and removable plug connections make installation a breeze.

Meeting UL/cUL 60950, 508 and 1604* (Class I, Div. 2), our PS-D (DIN rail mounted) power supplies meet the standards required for practically any industrial control application.

Features

- 2A 24A at 24 VDC, 3.5A at 12 VDC
- Regulated switch mode type
- Low profile case
- Easy DIN rail mounting
- · Constant-current short circuit protection
- · Low ripple and noise
- Selectable input voltage (115/230 VAC)
- High EMC immunity
- EMI meets EN 55011-B and FCC Part 15, Level B
- · Constant current protection with auto-recovery:
- No current spikes to damage powered devices due to improper wiring or a powered device failure
- Worldwide safety approvals: UL/cUL 508, 60950 and 1604 Class I, Div. 2, CE

* [PS12-050D, PS24-050D and PS24-500D do not meet UL 1604 Class I Div 2]



Part numbering system



For the latest prices, please check AutomationDirect.com.

1-800-633-0405 **RHINO Power Supplies Specifications PS Series**



PS12-050D PS24-050D



PS12-075D PS24-075D



PS24-150D



PS24-300D



PS24-500D



General Specifications					
Temperature	e Operating [ambient]: -25 to 70°C [-13 to 158°F] max, Derating above 50°C 2%/C Storage [non-operating]: -25 to 85°C [-13 to 185°F] max, Temperature drift: 0.02%/C				
Humidity	95% [non-condensing] relative humidity max				
Switching Frequency	80 kHz typical [PWM]				
Isolation	According to IEC/EN 60950, UL 60950, UL 508				
Output Regulation	Input variation: ± 0.2% max Load variation: 50W, 75W, 150W models: ± 1% max 300W, 500W, 600W models: ± 0.3% max				
Output Voltage Ripple	<pre>vtput Voltage Ripple < 50 mV peak to peak [20 MHz bandwidth]</pre>				
Output Protection	Current limit: 110% maximum output rating. Voltage limit: 140% Vout nom				
Vibration	1gn 20 sweeps each axis				
Shock	15gn, 11mS each axis				
Enclosure Rating	IP 20				
Enclosure Material	Aluminum [chassis] / stainless steel [cover]				
Mounting	Snap-on with self-locking spring for 35mm DIN rails				
Connection	Removable screw terminals for 22-10AWG, wire stripping length 7-8mm				
Agency Approvals	UL/cUL 60950 recognized, File No. E198298, UL/cUL 508 listed File No. E197592, UL/cUL 1604 listed [Class I, Div 2, groups A,B,C, and D hazardous locations], File No. E197886, except PSxx-050D and <u>PS24-500D</u> , which are not UL/cUL1604 listed. CE				

Note: All specifications are valid at nominal input voltage, full load and +25°C after warm-up time, unless otherwise stated.

Input Specifications								
Part Number	Input Voltage Range	Input Frequency Range	Input Current [Typical]		Inrush Current [<2mS]		Efficiency [Typ @	C-Curve Circuit Breaker or
			115 VAC	230 VAC	115 VAC	230 VAC	115VAC]	Slow-blow Fuse
PS12-050D	93-264 VAC	47-63 Hz	1.2 A	0.7 A	- 1F A	< 30 A	84%	5.0 A
PS24-050D	93-264 VAC		1.2 A	0.7 A	< 15 A		85%	
PS12-075D			1.7 A	0.9 A	< 16.5 A	< 33 A	82%	
PS24-075D	93-132 VAC		1.7A	0.9 A			86%	
PS24-150D	[switch selectable]		3.0 A	1.7 A	< 25 A	< 70 A	87%	10.0 A
PS24-300D	[]		5.4 A	3.3 A	< 35 A		88%	45.0.4
PS24-500D	93-132 VAC		9.5 A	N/A	< 50 A	N/A	87%	15.0 A
<u>PS24-600D</u>	93-132 VAC 187-264 VAC [switch selectable]		10.5 A	6.4 A	< 70 A	< 80 A	88%	20.0 A

Output Specifications										
Part Number Price		Price Drawing	Output	t Output	Output Current	Output Power	Output Voltage	Hold-Up Time		MTBF
	11100	Link	Voltage	Range	[Max]	[Max]	Regulation*	115 VAC	230 VAC	@ 25°C]
<u>PS12-050D</u>	Retired	PDF	12VDC	12-14 VDC	3.5 A	50W				2,992,000
PS24-050D	Retired	PDF	24VDC	24-28 VDC	2.0 A	50W		25mS	30mS .	hours
<u>PS12-075D</u>	\$212.00	PDF	12VDC	12-14 VDC	6.0 A	75W	1%			1,800,000
<u>PS24-075D</u>	Retired	PDF			3.0 A	75W				hours
<u>PS24-150D</u>	Retired	<u>PDF</u>			6.0 A	150W				1,939,000 hours
<u>PS24-300D</u>	\$292.00	<u>PDF</u>	24VDC		12.0 A	300W				1,913,000 hours
<u>PS24-500D</u>	\$511.00	PDF			20.0 A	500W	0.3%	20mS	N/A	1,467,000 hours
<u>PS24-600D</u>	\$507.00	<u>PDF</u>			24.0 A	600W		15mS	25mS	1,434,000 hours

*Load variation (10-90%)

Notes: Output current characteristic suitable for battery charging applications. Not recommended for redundancy or parallel operation.





PSE15-110-S

Overview

The RHINO PSE-S series offers 10-, 20-, 25-, and 50-watt AC/DC power supplies with an extended input range of 90-277 VAC. The power supplies are suitable for industrial, household, and building technology applications and are in a compact encapsulated plastic case.

PSE-S Series



PSE15-150-S

Features

Encapsulated Power Supplies

- Wide input voltage range 90-277 VAC
- High efficiency up to 89%
- Compact chassis
- I/O-Isolation 4,000 VAC
- Plastic housing
- Wide operating temperature -40 to 70°C (-40°C cold start) [-40 to 158°F]
- Optional DIN rail mounting kit
- 3-year warranty



Encapsulated Power Supplies									
Part Number	Price	Output Power (max.)	Nominal Output Voltage	Nominal Input Voltage	Nominal Output Amperage	Efficiency @ 115VAC	Weight	Dimensions W x H x D mm [in]	Drawing Link
<u>PSE05-110-S</u>	\$22.50		5VDC		2A	81%			PDF
PSE12-110-S	\$22.50	1014	12VDC		0.8 A	85%	65g	55.1 x 43.2 x 22.9	PDF
<u>PSE15-110-S</u>	\$22.50	1000	15VDC	2 2	0.6 A	86%	[2.29 oz]	[2.17 x 1.70 x 0.90]	PDF
PSE24-110-S	\$21.50]	24VDC		0.4 A	86%			PDF
PSE05-125-S	\$31.00	20W	5VDC		3.9 A	84%			PDF
PSE12-125-S	\$31.00		12VDC	120/240	2.1 A	88%	100g	88.4 x 38.1 x 24.1	PDF
PSE15-125-S	\$31.00	25W	15VDC	VA0	1.6 A	88%	[3.52 oz]	[3.48 x 1.50 x 0.95]	PDF
PSE24-125-S	\$29.50		24VDC		1A	87%]		PDF
PSE12-150-S	\$42.00		12VDC		4.1 A	89%			PDF
PSE15-150-S	\$42.00	50W	15VDC		3.3 A	88%	180g	97 x 48.3 x 25.4	PDF
PSE24-150-S	\$42.00	1	24VDC		2.1 A	88%	[0.54 02]		PDF

Optional DIN Rail Mounting Brackets						
Part Number	Price	Description	Weight	Drawing Link		
<u>PSE-BRKT-10</u>	\$7.50	RHINO DIN rail mounting bracket, aluminum. For use with 10W PSE-S series encapsulated power supplies. Mounting hardware included.	34g [1.19 oz]	PDF		
<u>PSE-BRKT-25</u>	\$7.50	RHINO DIN rail mounting bracket, aluminum. For use with 20W-25W PSE-S series encapsulated power supplies. Mounting hardware included.	39g [1.37 oz]	<u>PDF</u>		
PSE-BRKT-50	\$7.50	RHINO DIN rail mounting bracket, aluminum. For use with 50W PSE-S series encapsulated power supplies. Mounting hardware included.	46g [1.62 oz]	PDF		





RHINO® VAUTOMATIONDIRECT®

Encapsulated Power Supplies PSE-S Series

Input Specifications

Input Specifications						
Part Number	Input Voltage	Input Current (Full Load And Vin)	Power Consumption (No Load And Vin)	Input Inrush Current	Recommended Input Fuse	
PSE05-110-S						
<u>PSE12-110-S</u>		140mA max @ 230VAC			1.6 A	
PSE15-110-S		250MA Max @ 115VAC				
PSE24-110-5 PSE05-125-S	100-277 VAC			60A @ 230VAC 30A @ 115VAC		
PSE12-125-S	(47-60 Hz)	320mA max @ 230\/AC	100mW max @ 230VAC		254	
PSE15-125-S	100-250 VDC	490mA max @ 115VAC	100mvv max @ 115VAC		(slow blow)	
<u>PSE24-125-S</u>						
<u>PSE12-150-S</u>		600mA may @ 2201/AC		004 @ 2201/40	25 4	
<u>PSE15-150-S</u>		1,000mA max @ 230VAC		45A @ 115VAC	(slow blow)	
PSE24-150-S		, O		<u> </u>		

Output Specifications

Output Specifications								
Part Number	Voltage Set Accuracy	Ripple And Noise (20MHz)	Capacitive Load (max.)	Temperature Coefficient	Start-up Time (max.)	Hold-up Time (min.)	Output Current Limitation	Overvoltage Protection
<u>PSE05-110-S</u>		60 mVp-p	3,500 µF	±0.02 %/K max.				105 - 145% of Vout nom.
<u>PSE12-110-S</u>		120 mVp-p	700µF		K max. 60ms @ 230VAC 60ms @ 115VAC	30ms @ 230VAC	140 - 235% of lout max.	
<u>PSE15-110-S</u>		150 mVp-p	390µF					
<u>PSE24-110-S</u>		240 mVp-p	180µF					
<u>PSE05-125-S</u>		120 mVp-p	2,000 µF			36ms @ 230VAC	140 - 280% of	
<u>PSE12-125-S</u>	±2% max.	150 mVp-p	680 µF					
<u>PSE15-125-S</u>		160 mVp-p	220 µF		130ms @		lout max.	
PSE24-125-S		240 mVp-p	220 µF	±0.05 %/K max.	230VAC			
PSE12-150-S		120 mVp-p	3,500 µF		115VAC		400 04504 6	
PSE15-150-S		150 mVp-p	3,000 µF			10ms @ 230VAC	130 - 215% of	
<u>PSE24-150-S</u>		240 mVp-p	2,200 µF				iout Illax.	

RHINO[®] VAUTOMATIONDIRECT[®]

Encapsulated Power Supplies PSE-S Series

General Specifications

General Specifications						
Models	10W	20/25W	50W			
Operating Temperature		-40 to 70°C [-40 to 158°F]				
Storage Temperature		-40 to 85°C [-40 to 185°F]				
Humidity		95% max. (non-condensing)				
Power Derating	High temperature: 2.5 %/ K above 50°C Low input voltage: 2%/ V below 100VAC	High temperature: 2.5 % /K above 50°C Low temperature: 2%/ V below -30°C Low input voltage: 2%/ V below 100VAC	High temperature: 2.5 % /K above 50°C Low input voltage: 2%/ V below 100VAC			
Cooling System		Natural convection (20LFM)				
Altitude During Operation		5,000 m max. (according to IEC 62368-1) 2,000 m max. (according to IEC 60335-1)				
Short Circuit Protection	Continuous, automatic recovery					
Switching Frequency	35 - 75 kHz (PWM, PFM)	50 - 68 kHz (PWM, PFM)	55 - 90 kHz (PWM, PFM)			
Protection Class		Reinforced insulation Class I & II				
Over Voltage Category		OVC II				
Working Voltage (rated)	254 VAC	311 VAC	342 VAC			
Isolation Test Voltage		Input to Output, 60s; 4,000 VAC				
Leakage Current		Touch current 250 µA max.				
MTBF	450,000 h (MIL-HDBK-217F, ground benign)	400,000 h (MIL-HDBK-217F, ground benign)	300,000 h (MIL-HDBK-217F, ground benign)			
Housing Material		Plastic resin (UL 94 V-0 rated)				
Potting Material		Silicone (UL 94 V-0 rated)				
Mounting Type		Chassis				
Connection Type	Screw terminal; torque	: 0.3 N•m (3 kgfcm)	Screw terminal; torque: 0.2 N•m (2 kgfcm)			
Shock		IEC 60068-2-27				
Vibration	IEC 60068-2-6 2g, 3 axis, 60 min, 10-500 Hz, 10 min/cycle					
Pollution Degree		PD 2				
Agency Approval		cURus File E198298 , CE, UKCA				

To obtain the most current agency approval information, see the Agency Approval Compliance & Certifications Checklist section on the specific part number's web page.

Wiring



Pinout				
Pin	Single			
1	AC IN (N)			
2	AC IN (L)			
3	-Vout			
4	NC			
5	+Vout			

NC: Not connected



Encapsulated Power Supplies PSE-S Series

EMC Specifications

	EM	C Specifications			
	Conducted Emissions	EN 55032 class B (internal filter)			
· · ·	Radiated Emissions	EN 550032 class B (internal filter)			
EIVII EMISSIONS	Harmonic Current Emissions	EN61000-3-2 class A			
	Voltage Fluctuations & Flicker	Input to output 4.0 KVAC, Input to Ground 2.0 KVAC, Output to Ground 1.25 KVAC			
		EN 61000-6-2 (Generic Industrial) EN 55024 (IT Equipment) EN 55035 (Multimedia)			
	Electrostatic Discharge	Air: EN 61000-4-2, ±8 kV, perf. criteria A			
		Contact: EN 61000-4-2, ±4 kV, perf. criteria A			
	RF Electromagnetic Field	EN 61000-4-3, 10 V/m, perf. criteria A			
	EFT (Burst) / Surge	EN 61000-4-4, ±2 kV, perf. criteria A L to L: EN 61000-4-5, ±1 kV, perf. criteria A			
	Conducted RF Disturbances	EN 61000-4-6, 10 Vrms, perf. criteria A			
	PF Magnetic Field	Continuous: EN 61000-4-8, 30 A/m, perf. criteria A			
EMS Immunity Voltage Dips &	Voltage Dips & Interruptions	230 VAC / 50 Hz: EN 61000-4-11 30%, 25 periods, perf. criteria A 60%, 10 periods, perf. criteria A >95%, 0.5 periods, perf. criteria A >95%, 250 periods, perf. criteria B 100%, 0.5 periods, perf. criteria A 100%, 1 period, perf. criteria B 115 VAC / 60 Hz: EN 61000-4-11 30%, 25 periods, perf. criteria A 60%, 10 periods, perf. criteria A >95%, 0.5 periods, perf. criteria A >95%, 0.5 periods, perf. criteria B 100%, 0.5 periods, perf. criteria B 100%, 0.5 periods, perf. criteria A >90%, 250 periods, perf. criteria A 100%, 1 period, perf. criteria A 100%, 250 periods, perf. criteria A 100%, 250 periods, perf. criteria A			

Safety Specifications

Safety Specifications			
	IT / Multimedia Equipment	EN 62368-1 IEC 62368-1 UL 62368-1	
Standards	Household	EN 60335-1 IEC 60335-1	
	Power Transformers	IEC 61558-1 IEC 61558-2-16	

RHINO Encapsulated Power Supplies PSE Series

The PSE series are AC/DC switch mode power supplies encapsulated in an ultra-compact, low-profile housing. They are ideal for space limited applications and are easily screw mounted to a panel or equipment chassis or can be DIN rail mounted using the optional DIN rail mounting kit. The PSE series features a universal input from 120/240 VAC and single or dual outputs from 15 Watts up to 60 Watts (above 30 Watt, single output only).

Features

- Ultra compact, low profile plastic case
- Single or dual output models
- Screw terminal blocks
- Chassis mount or 35mm DIN rail mount with optional adapter
- Universal input 120/240 VAC, 47-440 Hz (60 Watt, 47-63 Hz)
- Double insulated no external ground required
- UL508 listed, UL60950-1 recognized, CE marked
- Short circuit and overload protection
- DC on LED indicator3-year warranty
- Single Output Models 15 to 60 Watt Weight Drawing Efficiency **Output Power Max.** Part Number Price Output Link [lbs] [Typ @ 115VAC] 5VDC / 3000mA PSE05-115 \$67.00 PDF 0.3 74% 0.3 81% PSE12-115 \$66.00 PDF 12VDC / 1250mA 15W PSE15-115 \$66.00 0.3 15VDC / 1000mA 81% PDF PSE24-115 \$66.00 PDF 0.3 24VDC / 625mA 83% PSE05-130 \$98.00 PDF 0.5 5VDC / 6000mA 76% PSE12-130 \$98.00 PDF 0.5 12VDC / 2500mA 80% 30W \$98.00 0.5 15VDC / 2000mA 81% <u>PSE15-130</u> PDF PSE24-130 \$98.00 PDF 0.5 24VDC / 1250mA 81% PSE05-150 \$118.00 PDF 0.8 51W 5.1 VDC / 10,000mA 76% 81% PSE12-160 \$117.00 PDF 0.8 12VDC / 5000mA PSE15-160 \$117.00 0.8 60W 15VDC / 4000mA 82% PDF 83% PSE24-160 \$117.00 PDF 0.8 24VDC / 2500mA

Dual Output Models 15 to 30 Watt							
Part No.	Price	Drawing Link	Weight [lbs]	Output Power Max.	Output 1	Output 2	Efficiency [Typ @ 115VAC]
<u>PSE12-215</u>	\$69.00	PDF	0.3	15\\\	+12VDC / 650mA	-12VDC / 650mA	82%
<u>PSE15-215</u>	\$69.00	PDF	0.3	1500	+15VDC / 500mA	-15VDC / 500mA	82%
<u>PSE12-230</u>	\$101.00	PDF	0.5	2014/	+12VDC / 1300mA	-12VDC / 1300mA	81%
PSE15-230	\$101.00	PDF	0.5	3000	+15VDC / 1000mA	-15VDC / 1000mA	82%



WOHS CULUS CALUS CE

www.automationdirect.com

1-800-633-0405 **RHINO Encapsulated Power Supplies PSE Series**

Input Specifications				
	Nominal	120/240 VAC		
Input Voltage	AC range [universal input]	85 - 264 VAC		
	DC range	120 - 370 VDC [not for 60 Watt models]		
Input Frequency	47 - 440Hz [47 - 63H	z for 60 Watt models]		
Input Current at Full Load	15 Watt models	300mA / 190mA typ.		
	30 Watt models	550mA / 330mA typ.		
	51/60 Watt models [typical for all]	1050mA / 670mA typ.		
Input Current at No Load	15mA @ 115VAC & 2	20mA @ 230VAC typ.		
	15 Watt models	15A / 30A		
Inrush Current (< 2ms, cold start at	30 Watt models	20A / 40A		
115VAC / 250VAC)	60 Watt models	30A / 50A		
External Input Fuse Required	15 and 30 Watt models	1.5 A slow blow		
(recommended value)	51/60 Watt models	3.0 A slow blow		

Output Specifications						
Voltage Set Accuracy	v	w2%				
	Input variation		1% max.			
Regulation	Load variation	Single output models [10-100%]: 1% max. Dual output models balanced load [10-100%]: 2.5% max. Dual output models unbalanced load [20/100%]: 5.0% max.		% max. 0% max.		
Minimum Load	Single and dual output models	10% of rated max. current				
Ripple and Noise	5.0 VDC outputs	1.8% of Vout [mVpk-pk]				
(20MHz bandwidth)	All other outputs	1.3% of Vout [mVpk-pk]				
Overload Protection by Current Limit	105% min. of nominal current, fold back, automatic recovery [long term overload condition may cause damage to the power supply]					
May Canaditive Load [11]	Output	Model Series				
Max. Capacitive Load [µF]	Ծաւթա	PSE15	PSE30	PSE60		
	5.0 VDC; 5.1 VDC	3900	8000	8000		
Single Output Models	12 / 15 VDC	2200	3900	3900		
	24VDC	1000	1500	1500		
Dual Output Models	+/-12V; +/-15V	1500	1500	NA		

1-800-633-0405 **RHINO Encapsulated Power Supplies PSE Series**

	General Specifications					
	Standard/		Model S	Series		
	Approval	PSExx-x15	PSExx-x30	PSExx-150	PSExx-160	
Operating Temperature	IEC/EN60950-1	-25 to 71°C [-1	3 to 159.8°F]	-10 to 40°C [14 to 104°F]	-10 to 50°C [14 to 122°F]	
	UL508	-25 to 50°C [-1	13 to 122°F]	-10 to 40°C [14 to 104°F]		
Storage Temperature		-40 to 185°F [-40 to 85°C]				
Power Derating		3.75% per °C above +122°F [50°C] 2.5% per °C above +104°F [40°C] for PSE05-150				
Temperature Coefficient			0.02 %/°C			
Humidity (non-condensing)			95% rel. H max.			
Efficiency			78% typ.			
Switching Frequency			100kHz typ. [fixed]			
Isolation Voltage (60 sec.)		Input/Output		3,000VAC		
Isolation Resistance		Input/Output		100MΩ [@ 500VDC]		
Electromagnetic Compatibility (EMC), Emissions			EN 61000-6-3: 2007 EN61204-3: 2000, clas EN 55032, level B, FCC Part	rs A 15 level B		
	EN61000-6-2: 2005 EN61204-3: 2000, class A					
	Electro	ostatic discharge ESD	El	V61000-4-2 - 8kV / 4 kV, criteria	В	
	RF	field susceptibility		EN61000-4-3 - 10 V/m, criteria A		
Electromagnetic	Electrical fast transient / burst immunity input EN61000-4-4 - w2 kV, criteria B					
Compatibility (EMC),	Electrical fast transient / burst immunity output EN61000-4-4 - w2 kV, criteria B					
Immunity	Surge immunity line - neutral EN61000-4-5 - w			EN61000-4-5 - w1 kV, criteria B		
	Surge immunity output		E	N61000-4-5 - w0.5 kV, criteria E	3	
	Immunity to	conducted RF disturbances	EN61000-4-6 - 10 V, criteria B			
	Mains volt	s voltage dips and interruptions = Solution Sol			a B, a C, ia C	
Protection Class II			to IEC/EN 60536			
Safety Standards	Informatio	on technology equipment		IEC/EN 60950-1, UL 60950-1		
Agency Approvals	U	L and cUL for UL 508, Listed File	No. E197592; UL and cUL for l	JL 60950-1, Recognized File No	. E198298; CE	
RoHS Compliant		Yes				
Vibration			None			
Shock			None			
Reliability / Calculated		15 Watt Models	>280,000 hours			
MTBF (MIL-HDBK-217F, @		30 Watt Models		>250,000 hours		
		60 Watt Models		>125,000 hours		
Casing Material			Plastic resin + fiberglass [UL 9	4V-U rated]		
Torque Specifications	4~5 in-lb [0.45~0.56 Nm]					

Note: All specifications valid at nominal input voltage, full load and +25°C [+77°F] after warm-up time unless otherwise stated.

RHINO Encapsulated Power Supplies PSE Series

Derating Curves





PSE 15W models

Wiring Connection					
Pin	Single	Dual (12V, 15V)			
1	AC[N] - AC Neutral				
2	AC[L] - AC Line				
3	NC				
4	-Vout				
5	NC	Common			
6	+Vout				
7	1	٩C			

M3 x 0.5 mm screw size, Typ

Mounting Brackets

35mm DIN Rail Mounting Bracket				
Part Number	Price	Drawing Link	Weight (lbs)	Description
PSE-BRKT-1	\$13.00	PDF	0.2	DIN rail mounting bracket for 15W PSE models
PSE-BRKT-2	\$13.00	PDF	0.2	DIN rail mounting bracket for 30W-60W PSE models

Note: Kit contains interface plate, DIN rail clip and necessary screws.





PSE-BRKT-1

PSE-BRKT-2



Wiring Connection				
Pin	Single	Dual (12V, 15V)		
1	AC[N] - AC Neutral			
2	AC[L] - AC Line			
3	+Vout			
4	NC			
5	-Vout	Common		
6	NC			
7	NC	-Vout		
M2 v (

6 000

100

000

-0

M3 x 0.5 mm screw size, Typ

© ©

@

PSE 60W models

W	Wiring Connection			
Pin	Function			
1	AC[N] - AC Neutral			
2	AC[L] - AC Line			
3	NC			
4	+Vout			
5	NC			
6	-Vout			
7	NC			

#4 screw size, Typ

#4 361 CW 312C, 1

PRO

DIN Rail Power Supplies PSH Series

High Efficiency Power Supplies

AutomationDirect's RHINO PRO PSH series DIN rail power supplies offer best-in-class efficiency, temperature performance, and agency approvals for extreme conditions. With efficiencies of up to 94% and an operating temperature range of -25°C to 70°C, RHINO PRO PSH supplies will keep going when other supplies won't. There are 10 models, with output power from 80W to 480W and output voltages from 12 to 48 VDC. They feature universal 120/240 VAC input voltage, adjustable DC output, DC-OK LED indication, and output current limitation.

Well suited for harsh environments and hazardous locations, the rugged aluminum and stainless steel housings easily install with included 35mm DIN rail mounting adapters. The DIN rail clips can be moved to the side of the power supply for side mounting in flat panels. These high-quality power supplies are backed by a 5-year warranty, UL 508 and hazardous location listed, UL 60950 recognized, ATEX certified, CE marked and RoHS compliant.



DIN Rail Power Supplies Drawing Output Maximum Output Efficiency Part Number Price Link Voltage Power [Typ @ 115VAC] PSH-12-080 \$138.00 PDF 12V 90% PSH-24-080 \$129.00 PDF 24V 80W 91% 48V PSH-48-080 \$125.00 PDF 91% \$183.00 PSH-12-120 PDF 12V 91% 120W PSH-24-120 \$166.00 PDF 24V 92% PSH-48-120 \$182.00 PDF 48V 93% <u>PSH-24-240</u> \$218.00 PDF 24V 93% 240W \$231.00 PDF 48V 94% <u>PSH-48-240</u> \$327.00 24V PSH-24-480 PDF 93% 480W PSH-48-480 \$343.00 PDF 48V 94%

Features

- 12, 24 and 48 VDC models
- –40°C start-up on all models
- ATEX & UL Class 1, Div. 2
- Battery control module available
- Alternative side-mounting for flat panels
- Very high efficiency, up to 94%
- Back power immunity
- 150% peak current for 4 sec.
- Operating temperature range: -25 to +70°C max. [Full load to 60°C]
- Adjustable output voltage
- DC-OK indicator
- Short circuit and overload protection
- 5-year warranty



PSH-xx-080



PSH-xx-120



PSH-xx-240





RHINO PRO PSH-xx-080 Power Supplies

Technical Specifications				
Part Number		<u>PSH-12-080</u>	<u>PSH-24-080</u>	<u>PSH-48-080</u>
Input (AC)				
Nominal Inp	out Voltage	100–240VAC		
Nominal Inp	out Current	2–0.9 A		
Operational	Input Voltage Range	85–264VAC		
Input Voltag	ge Frequency Range	45–65Hz		
Inrush Curr	ent (115/230 VAC)	15/30A		
Standby Po	wer Consumption		0.9/1.45 W [115/230 VAC]	
Active Powe	er Factor Correction (PFC)		0.48/0.48 [115/230 VAC]	
Harmonic li	mits – acc. EN 61000-3-2		Class A	
Circuit Brea	ker Rating / Characteristic		6-16 A /B, C [IEC]; 20 A /B, C[USA]	
Output (DC)				
Max. Outpu	t Power		80W	
Output Volt	age	12V	24V	48V
Max. Output power" whic motors, sole	t Current / Max. Output Current 4s ("Boost ch facilitates the activation of stepper enoids, or actuators)	6.7 A / 10A	3.4 A / 5A	1.7 A / 2.5 A
Output Voltage Adjustment Range		11.8–15V	23.5–28V	47.5–56V
Typical Effic	ciency (@ 115/230 VAC)	90/88 %	91/89 %	91/89 %
Regulation Input Variat Load Variat	ion ion	0.1 % max. [10–90 %] 0.5 % max.		
Output Pow	er Derating - Temperature		2%/K above 60°C	
Output Pow	er Derating - Input Voltage		3%/V below 90VAC	
Hold-up tim	e		20/160ms min. [115/230 VAC]	
Start-up tim	e		2s max.	
Ripple and	Noise (20MHz bandwidth) (Note 1)	100mVp-p max.	100mVp-p max.	200mVp-p max.
Output Ove	rvoltage Protection (OVP) (Note 2)	16–19V	32–35V	56–60V
Power Back	(Immunity (Note 3)		< OVP level	
Operation Nominal Op Peak Power Constant Ci	veration • Operation urrent (CC)	100% of lout nominal 105–150% of lout nominal 155% of lout nominal		
Duty Cycle Threshold CC or Peak Normal Ope	(for peak and cc mode) (Note 4) Operation Timer eration / Off Period	> 105 % 4s max. [switch off] < 6s typ [automatic restart after switch off or peak and cc operation timer reset]		
Short Circu	it Protection	Switch	off after 4s delay, automatic restart (No	ote 4)
DC ОК	Threshold for Vout	ON: > 10.9 V typ. OFF :< 10.7 V typ.	ON: > 22.5 V typ. OFF:< 21.5 V typ.	ON: > 45V typ. OFF:< 43V typ.
Signal	DC ON	Relay contact close	ed, max. 1A, < 100mOhm, also indicate	ed by green LED
	DC OFF	Relay contact open, max 30V		

Notes:

1. Output voltage can be adjusted as indicated. However, output power has to be maintained at nominal value. This means the output nominal current has to be reduced in accordance with the increase of output voltage.

2. In case of an internal error, a second voltage regulation loop keeps the output voltage at a safe level, and the power supply turns off and restarts after 10 seconds. 3. When external voltage is supplied above set output voltage and below OVP threshold, the power supply will function normally without switch off or destruction, even if

external voltage is applied continuously.

4. In case of overload or short circuit, the unit switches the output voltage off after 4 seconds and tries to restart every 10 seconds.

Continued on following page.

RHINO PRO

RHINO PRO PSH-xx-080 Power Supplies

Technical Specification (continued)					
Part Number	<u>PSH-12-080</u> <u>PSH-24-080</u> <u>PSH-48-080</u>				
General Data					
Weight g [oz]	367 [12.95]				
Leakage Current (max.)	0.75 mA				
Network Configuration	TN-S, TN-C, TT, IT				
Enclosure Material (Chassis/Cover)	Aluminum / Stainless Steel				
Cooling		Convection cooling, no internal fan			
Over Temperature Protection		Switch off at over temperature			
Isolation Voltage	Input/Output 4250VDC Input/Chassis 1500VDC Output/Chassis 750VDC				
Creepage Clearance		Input/Output 8mm Input/Chassis 4mm Output/Chassis 1.5 mm			
Safety / Environmental	1				
Surrounding Ambient Temperature Range		-40 to 70°C [-40 to 158°F]			
Temperature Coefficient		0.02 %/K			
Humidity		5–95%, non-condensing			
Storage Temperature		-40 to 85°C [-40 to 185°F]			
Maximum Altitude		2000m			
Safety Standards	Information technology equipment IEC/EN 60950-1, UL 60950-1 CSA 22.2 No 60950-1-03, File No. E198298 Safety low voltage switchgear and controlgear UL 508, File No. E197592 Process Control Equipment Haz Loc, File No. E502478 ATEX I I 3 G Ex ec nC IIC T4 Gcw				
MTBF (acc. to IEC 61709 at 25°C)	> 1,950,000 hours				
Protection Class		Class I			
Degree of Protection		IP20			
Electromagnetic compatibility (EMC)					
Emissions	EN 61000-6-3, EN 61204-3				
Conducted RI Suppression On Input	EN 55032, EN 55011 class B,				
Radiated RI Suppression	EN 55032, EN 55011 class B,				
Immunity		EN 61000-6-2, EN 61204-3			
Railway Applications Signaling Apparatus		EN 50121-4			
Railway Applications Rolling Stock Apparatus		EN 50121-3-2			
Electrostatic Discharge (ESD)		IEC/EN 61000-4-24 kV/8 kV, criteria A			
Radiated RF Field Immunity		IEC/EN 61000-4-310 V/m, criteria A			
Electrical Fast Transient / Burst Immunity		IEC/EN 61000-4-42 kV, criteria B			
Surge Immunity		IEC/EN 61000-4-51 kV/2 kV, criteria B			
Immunity To Conducted RF Disturbances		IEC/EN 61000-4-610 V, criteria A			
Power Frequency Field Immunity		IEC/EN 61000-4-830 A/m, criteria A			
Mains Voltage Dips And Interruptions		IEC/EN 61000-4-11, criteria B/C			
Voltage Sag Immunity		SEMI F47230VAC, criteria B/C			
Environment					
Railway Applications Shock and Vibration		According EN 61373			
Vibration Acc. IEC 60068-2-6-3	3	axis, 2 g sine sweep, 10-55Hz, 11 oct/mi	IN		
SHOCK ACC. IEC 00008-2-2/					
Approvals	$C \in CB_{Scheme} CL_{SOB} CHULGOSO-1 $				



RHINO PRO PSH-xx-080 Power Supplies

Fig. 1



	Identification of Features (Fig.1)	
1	Input Terminal L	
2	Input Terminal N	
3	Input Terminal GND	
4	Output Voltage adjustment potentiometer	
5	DC ON LED	
6/7	DC OK Contact	
8	Output Connection Terminal +	
9	Output Connection Terminal –	

Fig. 2







		1
INP	JT	

Wiring Specifications (Fig. 3)			
Α	Wire Size, Output	18–10 AWG	
В	Wire Size, Input	18–10 AWG	
С	Strip Length	10mm [0.39 in]	
D	Tightening Torque	0.7 N·m [6.2 lb·in]	









RHINO PRO PSH-xx-120 Power Supplies

Technical Specifications				
Part Number		PSH-12-120	<u>PSH-24-120</u>	<u>PSH-48-120</u>
Input (AC)		·	· · · · · · · · · · · · · · · · · · ·	
Nominal Input Voltage		100–240 VAC		
Nominal Inp	out Current		1.5–0.78 A	
Operational	I Input Voltage Range		85–264VAC	
Input Voltag	ge Frequency Range	45–65Hz		
Inrush Curr	rent (115/230 VAC)		15/30A	
Standby Po	wer Consumption		2.2/2.2 W [115/230 VAC]	
Active Powe	er Factor Correction (PFC)		0.97/0.8 [115/230 VAC]	
Harmonic li	imits – acc. EN 61000-3-2		Class A, D	
Circuit Brea	aker Rating / Characteristic		6-16 A /B, C [IEC]; 20 A /B, C [USA]	
Output (DC)				
Max. Outpu	t Power		120W	
Output Volt	age	12V	24V	48V
Max. Outpu power" whi motors, sol	nt Current / Max. Output Current 4s ("Boost ich facilitates the activation of stepper lenoids, or actuators)	10A / 15A	5A / 7.5 A	2.5 A / 3.75 A
Output Volt	age Adjustment Range	11.8–15 V 23.5–28 V 47.5–56 V		47.5–56 V
Typical Efficiency (@ 115/230 VAC)		91/93 %	92/94 %	93/94 %
Regulation Input Variat Load Variat	Regulation 0.1 % max. Input Variation 0.1 % max. Load Variation [10–90 %] 0.5 % max.			
Output Pow	Dutput Power Derating - Temperature 2%/K above 60°C, refer to Fig. 5			
Output Power Derating - Input Voltage 3%/V below 90 VAC, refer to Fig.		3%/V below 90 VAC, refer to Fig. 4		
Hold-up tim	le		20ms min.	
Start-up tim	10		2s max.	
Ripple and	Noise (20MHz bandwidth) (Note 1)	100mVp-p max. 100mVp-p max. 200mVp-p max.		200mVp-p max.
Output Ove	rvoltage Protection (OVP) (Note 2)	16–19V	32–35V	56–60V
Power Back	k Immunity (Note 3)		< OVP level	
Operation Nominal Op Peak Power Constant C	peration r Operation urrent (CC)	100% of lout nominal 105–150% of lout nominal 155% of lout nominal		
Duty Cycle Threshold CC or Peak Normal Ope	(for peak and cc mode) (Note 4) Operation Timer eration / Off Period	> 105 % 4s max. [switch off] < 10s typ [automatic restart after switch off or peak and cc operation timer reset]		
Short Circu	it Protection	Switch off after 4s delay, automatic restart [Note 4]		
дс ок	Threshold for Vout	ON: > 10.9 V typ. OFF:< 10.7 V typ.	ON: > 22.5 V typ. OFF:< 21.5 V typ.	ON: > 45V typ. OFF:< 43V typ.
Signal	DC ON	Relay contact closed, max. 1A, < 100mOhm, also indicated by green LED		
	DC OFF	Relay contact open, max 30V		

Notes:

1. Output voltage can be adjusted as indicated. However, output power has to be maintained at nominal value. This means the output nominal current has to be reduced in accordance with the increase of output voltage.

2. In case of an internal error, a second voltage regulation loop keeps the output voltage at a safe level, and the power supply turns off and restarts after 10 seconds.

3. When external voltage is supplied above set output voltage and below OVP threshold, the power supply will function normally without switch off or destruction, even if external voltage is applied continuously.

4. In case of overload or short circuit, the unit switches the output voltage off after 4 seconds and tries to restart every 10 seconds. Continued on following page.

RHINO PRO

RHINO PRO PSH-xx-120 Power Supplies

Technical Specifications (continued)				
Part Number	<u>PSH-12-120</u> <u>PSH-24-120</u> <u>PSH-48-120</u>			
General Data				
Weight g [oz]	461 [16.26]			
Leakage Current (max.)	0.9 mA			
Network Configuration	TN-S, TN-C, TT, IT			
Enclosure Material (Chassis/Cover)	Aluminum / Stainless Steel			
Cooling	Convection cooling, no internal fan			
Over Temperature Protection	Switch off at over temperature			
Isolation Voltage	Input/Output 4250VDC Input/Chassis 1500VDC Output/Chassis 750VDC			
Creepage Clearance	Input/Output 8mm Input/Chassis 4mm Output/Chassis 1.5 mm			
Safety / Environmental				
Surrounding Ambient Temperature Range	-40 to 70°C [-40 to 158°F]			
Temperature Coefficient	0.02 %/K			
Humidity	5–95%, non-condensing			
Storage Temperature	-40 to 85°C [-40 to 185°F]			
Maximum Altitude	2000m			
Safety Standards Information technology equipment IEC/EN 60950-1, UL 60950-1 CSA 22.2 No 60950-1-03, File No. E198298 Safety Standards Safety low voltage switchgear and controlgear UL 508, File No. E197592 Process Control Equipment Haz Loc, File No. E502478 ATEX © II 3 G Ex ec nC IIC T4 Gcw				
MTBF (acc. to IEC 61709 at 25°C)	> 1,450,000 hrs			
Protection Class	Class I			
Degree of Protection	IP20			
Electromagnetic compatibility (EMC)				
Emissions	EN 61000-6-3, EN 61204-3			
Conducted RI Suppression On Input	EN 55032, EN 55011 class B,			
Radiated RI Suppression	EN 55032, EN 55011 class B,			
Immunity	EN 61000-6-2, EN 61204-3			
Railway Applications Signaling Apparatus	EN 50121-4			
Railway Applications Rolling Stock Apparatus	EN 50121-3-2			
Electrostatic Discharge (ESD)	IEC/EN 61000-4-24 kV/8 kV , criteria A			
Radiated RF Field immunity	IEC/EN 61000-4-310 V/m , criteria A			
Electrical Fast Transient / Burst Immunity	IEC/EN 61000-4-42 kV , criteria B			
Surge immunity	IEC/EN 61000-4-51 kV/2 kV , criteria B			
Remarking To Conducted RF Disturbances	IEC/EN 61000-4-610 V , criteria A			
Moine Voltage Dine And Interruptione	IEU/EN 61000-4-830 A/m , criteria A			
Voltago Sag Immunity				
Environment	rorrage sag immunity SEMI F47 230VAC, criteria B/C			
Environment Bailway Applications Shock and Vibration	According EN 61273			
Vibration Acc. IEC 60068-2.6.2	3 axis 2a sine sween 10 55Hz 11 oct/min			
Shock Acc. IEC 60068-2-0-3	3 axis, 2y sine sweep, 10-3312, 11 00011111			
Approvals	$\begin{array}{c c} & & & \\ \hline \\$			



RHINO PRO PSH-xx-120 Power Supplies

Fig. 1



Identification of Features (Fig.1)			
1	Input Terminal L		
2	Input Terminal N		
3	Input Terminal GND		
4	Output Voltage adjustment potentiometer		
5	DC ON LED		
6/7	DC OK Contact		
8	Output Connection Terminal +		
9	Output Connection Terminal –		

Fig. 3

Fig. 2







Wiring Specifications (Fig. 3)				
Α	Wire Size, Output	18–10AWG		
в	Wire Size, Input	18–10AWG		
С	Strip Length	10mm [0.39 in]		
D	Tightening Torque	0.7 N·m [6.2 lb·in]		









RHINO PRO PSH-xx-240 Power Supplies

Technical Specifications				
		<u>PSH-24-240</u>	<u>PSH-48-240</u>	
Input (AC)				
Nominal Inp	out Voltage	100–24	0 VAC	
Nominal Inp	out Current	2.89–1	I.27 A	
Operational	I Input Voltage Range	85–26	4VAC	
Input Voltag	ge Frequency Range	45–6	5Hz	
Inrush Curr	rent (115/230 VAC)	15/3	30A	
Standby Po	wer Consumption	2.3/2.3 W [115/230 VAC]		
Active Pow	er Factor Correction (PFC)	0.98/0.92 [11	5/230 VAC]	
Harmonic li	mits – acc. EN 61000-3-2	Class	A, D	
Circuit Brea	aker Rating / Characteristic	6-16 A /B, C [IEC];	20 A /B, C [USA]	
Output (DC)				
Max. Outpu	t Power	240	W	
Output Volt	age	24V	48V	
Max. Outpu power" whi motors, sol	t Current / Max. Output Current 4s ("Boost ch facilitates the activation of stepper enoids, or actuators)	10A / 15A	5A / 7.5 A	
Output Voltage Adjustment Range		23.5–28 V	47.5–56 V	
Typical Effi	ciency (@ 115/230VAC)	93/95 %	94/95 %	
Regulation Input Variation Load Variation		0.1 % max. [10–90 %] 0.5 % max.		
Output Power Derating - Temperature		2%/K above 60°C, refer to Fig. 5		
Output Power Derating - Input Voltage		3%/V below 90 VAC, refer to Fig. 4		
Hold-up time		20 ms min.		
Start-up tim	1e	2s max.		
Ripple and Noise (20MHz bandwidth) (Note 1)		100 mVp-p max.	200 mVp-p max.	
Output Ove	rvoltage Protection (OVP) (Note 2)	32–35V	56–60V	
Power Back Immunity (Note 3)		< OVP level		
Operation Nominal Operation Peak Power Operation Constant Current (CC)		100% of lout nominal 105–150% of lout nominal 155% of lout nominal		
Duty Cycle (for peak and cc mode) (Note 4) Threshold CC or Peak Operation Timer Normal Operation / Off Period		> 105 % 4s max. [switch off] < 10s typ [automatic restart after switch off or peak and cc operation timer reset]		
Short Circuit Protection		Switch off after 4s delay, automatic restart (Note 4)		
дс ок	Threshold for Vout	ON: > 22.5 V typ. OFF: < 21.5 V typ.	ON: > 45V typ. OFF: < 43V typ.	
Signal	DC ON	Relay contact closed, max. 1A, < 100mOhm, also indicated by green LED		
	DC OFF	Relay contact open, max 30V		

Notes:

1. Output voltage can be adjusted as indicated. However, output power has to be maintained at nominal value. This means the output nominal current has to be reduced in accordance with the increase of output voltage.

In case of an internal error, a second voltage regulation loop keeps the output voltage at a safe level, and the power supply turns off and restarts after 10 seconds.
When external voltage is supplied above set output voltage and below OVP threshold, the power supply will function normally without switch off or destruction, even if external voltage is applied continuously.

4. In case of overload or short circuit, the unit switches the output voltage off after 4 seconds and tries to restart every 10 seconds. Continued on following page.

RHINO PRO

RHINO PRO PSH-xx-240 Power Supplies

Technical Specifications (continued)				
	<u>PSH-24-240</u>	<u>PSH-48-240</u>		
General Data				
Weight g [oz]	643	[22.68]		
Leakage Current (max.)	1.2	2 mA		
Network Configuration	TN-S, TM	N-C, TT, IT		
Enclosure Material (Chassis/Cover)	Aluminum / S	Stainless Steel		
Cooling	Convection cooli	ing, no internal fan		
Over Temperature Protection	Switch off at o	ver temperature		
Isolation Voltage	Input/Output 4250VDC Input/Chassis 1500VDC Output/Chassis 750VDC			
Creepage Clearance	Input/Ou Input/Ch Output/Cha	ıtput 8mm assis 4mm assis 1.5 mm		
Safety / Environmental	1			
Surrounding Ambient Temperature Range	-40 to 70°C	[-40 to 158°F]		
Temperature Coefficient	0.02	2 %/K		
Humidity	5–95%, nor	n-condensing		
Storage Temperature	-40 to 85°C	[-40 to 185°F]		
Maximum Altitude	20	00m		
Safety Standards	Information technology equipment IEC/EN 60950-1, UL 60950-1 CSA 22.2 No 60950-1-03, File No. E198298 Safety low voltage switchgear and controlgear UL 508, File No. E197592 Process Control Equipment Haz Loc, File No. E502478 ATEX I 3 G Ex ec nC IIC T4 Gcw			
MTBF (acc. to IEC 61709 at 25°C)	> 1,300,000 hrs			
Protection Class	Class I			
egree of Protection IP20		220		
Electromagnetic compatibility (EMC)				
Emissions	EN 61000-6-3, EN 61204-3			
Conducted RI Suppression On Input	EN 55032, EN	I 55011 class B,		
Radiated RI Suppression	EN 55032, EN	I 55011 class B,		
Immunity	EN 61000-6-	2, EN 61204-3		
Railway Applications Signaling Apparatus	EN 50121-4			
Railway Applications Rolling Stock Apparatus	EN 50	121-3-2		
Electrostatic Discharge (ESD)	IEC/EN 61000-4-2	4 kV/8 kV , criteria A		
Radiated RF Field Immunity	IEC/EN 61000-4-310 V/m , criteria A			
Electrical Fast Transient / Burst Immunity	IEC/EN 61000-4-42 kV , criteria B			
Surge Immunity	IEC/EN 61000-4-51 kV/2 kV , criteria B			
Immunity To Conducted RF Disturbances				
Power Frequency Field Immunity	IEU/EN 61000-4-830 A/m , criteria A			
Mains Voltage Dips And Interruptions	IEC/EN 61000-4-11criteria B/C			
/ortage Sag immunity SEMI F4/ 230VAC, criteria B/C				
Environment				
Kallway Applications Snock and Vibration	According EN 61373			
VIDIALION ACC. IEC 00008-2-0-3	3 axis, 2g sine sweep, 10–55Hz, 11 oct/min			
SHOCK ACC. IEU 00008-2-21	STICK ACC. IEC 00008-2-2/ 3 axis, 25g half sine, 11ms			
Approvals	CECB c(1) us c Scheme UL508 UI			



RHINO PRO PSH-xx-240 Power Supplies

Fig. 1



	Identification of Features (Fig.1)	
1	Input Terminal L	
2	Input Terminal N	
3	Input Terminal GND	
4	Output Voltage adjustment potentiometer	
5	DC ON LED	
6/7	DC OK Contact	
8	Output Connection Terminal +	
9	Output Connection Terminal +	
10	Output Connection Terminal –	
11	Output Connection Terminal –	







Wiring Specifications (Fig. 3)			
4	Wire Size, Output	16–10AWG	
В	Wire Size, Input	18–10AWG	
С	Strip Length	10mm [0.39 in]	
D	Tightening Torque	0.7 N·m [6.2 lb·in]	







Power Supplies t

tPWR-108


RHINO PRO PSH-xx-480 Power Supplies

Technical Specifications					
Part Number		<u>PSH-24-480</u>	<u>PSH-48-480</u>		
Input (AC)					
Nominal In	put Voltage	100–24	NO VAC		
Nominal In	put Current	5.8–2	2.5 A		
Operationa	I Input Voltage Range	85–264VAC			
Input Volta	ge Frequency Range	45–6	5Hz		
Inrush Curr	rent (115/230 VAC)	15/3	30A		
Standby Po	ower Consumption	4.8/3.8 W [11	15/230 VAC]		
Active Pow	er Factor Correction (PFC)	0.99/0.97[11	5/230 VAC]		
Harmonic li	imits – acc. EN 61000-3-2	Class	A, D		
Circuit Brea	aker Rating / Characteristic	6-16 A /B, C[IEC];	20 A /B, C [USA]		
Output (DC)		1			
Max. Outpu	It Power	480	W		
Output Volt	tage	24V	48V		
Max. Output Current / Max. Output Current 4s ("Boost power" which facilitates the activation of stepper motors, solenoids, or actuators)		20A / 30A	10A / 15A		
Output Volt	tage Adjustment Range	23.5–28 V	47.5–56 V		
Typical Effi	ciency (@ 115/230 VAC)	93/95 %	94/95 %		
Regulation Load Variation		0.1 % max. [10–90 %] 0.5 % max.			
Output Power Derating - Temperature		2%/K above 60°	C, refer to Fig. 5		
Output Pow	ver Derating - Input Voltage	3%/V below 90 VA	AC, refer to Fig. 4		
Hold-up tim	ne	20ms min.			
Start-up tin	ne	2s n	lax.		
Ripple and	Noise (20MHz bandwidth) (Note 1)	100 mVp-p max.	200 mVp-p max.		
Output Ove	ervoltage Protection (OVP) (Note 2)	32–35V	56–60V		
Power Back	k Immunity (Note 3)	< 0VF	? level		
Operation Coperation Constant Current (CC)		100% of lout nominal 105–150% of lout nominal 155% of lout nominal			
Duty Cycle (for peak and cc mode) (Note 4) Threshold CC or Peak Operation Timer Normal Operation / Off Period		> 105 % 4s max. [switch off] < 10s typ [automatic restart after switch off or peak and cc operation timer reset]			
Short Circuit Protection		Switch off after 4s delay, automatic restart (Note 4)			
рс ок	Threshold for Vout	ON: > 22.5 V typ. OFF: < 21.5 V typ.	ON: > 45V typ. OFF: < 43V typ.		
Signal	DC ON	Relay contact closed, max. 1A, < 100mOhm, also indicated by green LED			
	DC OFF	Relay contact open, max 30V			

1. Output voltage can be adjusted as indicated. However, output power has to be maintained at nominal value. This means the output nominal current has to be reduced in accordance with the increase of output voltage.

In case of an internal error, a second voltage regulation loop keeps the output voltage at a safe level, and the power supply turns off and restarts after 10 seconds.
 When external voltage is supplied above set output voltage and below OVP threshold, the power supply will function normally without switch off or destruction, even if

external voltage is applied continuously.

4. In case of overload or short circuit, the unit switches the output voltage off after 4 seconds and tries to restart every 10 seconds. Continued on next page.



RHINO PRO PSH-xx-480 Power Supplies

Iecnnic	cal Specifications (continued)			
Part Number	<u>PSH-24-480</u>	<u>PSH-48-480</u>		
General Data				
Weight g [oz]	1018	3 [35.91]		
Leakage Current (max.)	2.3 mA			
Network Configuration	TN-S, T	N-C, TT, IT		
Enclosure Material (Chassis/Cover)	Aluminum /	Stainless Steel		
Cooling	Convection coo	ling, no internal fan		
Over Temperature Protection	Switch off at	over temperature		
Inclusion Voltage	Input/Out	put 4250VDC		
	Output/Ch	assis 750VDC		
Creepage Clearance	Input/C	utput 8mm nassis 4mm		
	Output/Ch	assis 1.5 mm		
Remote On/Off	The unit can be controlled by extern	al relay contact or open collector signal.		
Contact Rating	Open: 15V; leaka Close: 0.3 V; r	je current max 100μΑ nax drop at 15mΑ		
Safety / Environmental	· · · · · · · · · · · · · · · · · · ·			
Surrounding Ambient Temperature Range	-40 to 70°C	; [-40 to 158°F]		
Temperature Coefficient	0.0	12 %/K		
Humidity	5–95%, no	un-condensing		
Storage Temperature	-40 to 85°C [-40 to 185°F]			
Maximum Altitude	20	 D00m		
Safety Standards	Information technology equipment IEC/EN 60950-1, UL 60950-1 CSA 22.2 No 60950-1-03, File No. E198298 Safety low voltage switchgear and controlgear UL 508, File No. E197592 Process Control Equipment Haz Loc, File No. E502478 ATEX © II.3 G Ex ec. nC. IIC. T4 Gcw			
MTBF (acc. to IEC 61709 at 25°C)	> 1,000,000 hrs			
Protection Class	С	lass I		
Degree of Protection	IP20			
Electromagnetic compatibility (EMC)				
Emissions	EN 61000-6	-3, EN 61204-3		
Conducted RI Suppression On Input	EN 55032, E	N 55011 class B,		
Radiated RI Suppression	EN 55032, E	N 55011 class B,		
Immunity	EN 61000-6	-2, EN 61204-3		
Railway Applications Signaling Apparatus	EN	50121-4		
Railway Applications Rolling Stock Apparatus	EN 5	0121-3-2		
Electrostatic Discharge (ESD)	IEC/EN 61000-4-	2 4 kV/8 kV, criteria A		
Radiated RF Field Immunity	IEC/EN 61000-4	-3 10 V/m, criteria A		
Electrical Fast Transient / Burst Immunity	IEC/EN 61000-	4-4 2 kV, criteria B		
Surge Immunity	IEC/EN 61000-4-5 1 kV/2 kV, criteria B			
Immunity To Conducted RF Disturbances	IEC/EN 61000-4-6 10 V, criteria A			
Power Frequency Field Immunity	IEC/EN 61000-4-8 30 A/m, criteria A			
Mains Voltage Dips And Interruptions	IEC/EN 61000-4-11 criteria B/C			
Voltage Sag Immunity	SEMI F47 230VAC, criteria B/C			
invironment				
Railway Applications Shock and Vibration	According EN 61373			
Vibration Acc. IEC 60068-2-6-3	3 axis, 2g sine sweep, 10–55Hz, 11 oct/min			
Shock Acc. IEC 60068-2-27	3 axis, 25g half sine, 11ms			
Approvals	$C \in CB_{Scheme} \stackrel{\circ}{\underset{UL508}{\textcircled{\baselines}}} \stackrel{\circ}{\underset{UL508}{\textcircled{\baselines}}} \stackrel{\circ}{\underset{UL509}{\textcircled{\baselines}}} \stackrel{\circ}{\underset{UL509}{\hline{\baselines}}} }{\underset{UL509}{\hline{\baselines}}} }{\underset{UL509}{\hline{\baselines}}} }{\underset{UL509}{\hline{\baselines}}} }{\underset{UL509}{\b$			



RHINO PRO PSH-xx-480 Power Supplies

Fig. 1



Identif	ication of Features (Fig.1)
1	Input Terminal L
2	Input Terminal N
3	Input Terminal GND
4	Output Voltage adjustment potentiometer
5	DC ON LED
6/7	DC OK Contact
8–10	Remote On/Off
11	Output Connection Terminal –
12	Output Connection Terminal –
13	Output Connection Terminal +
14	Output Connection Terminal +

Fig. 2



Remote On/Off







G	• (F ● ●
E C SIGNALS	D B	

	Wiring Specificati	ons (Fig. 3)
4	Wire Size, Output	12–10AWG
В	Wire Size, Input	18–10AWG
С	Wire Size, Signal	30–16AWG
D	Strip Length, Input/Output	10mm [0.39 in]
E	Strip Length, Signal	5mm [0.20 in]
F	Tightening Torque, Input/Output	0.7 N·m [6.2 lb·in]
G	Tightening Torque, Signal	0.2 N·m [1.8 lb·in]







1-800-633-0405 For the latest prices RHINO Power Supplies PSX Series

Ruggedized Power Supplies

AutomationDirect's RHINO PSX series of ruggedized power supplies are Class I, Div. 2 hazardous location rated. There are 2 models available, with 12 and 24VDC output voltages. They feature universal 120/240 VAC input voltage, adjustable DC output, DC-OK LED indication, and output current limitation.

The rugged aluminum housings offer IP67 and NEMA 4X ratings for harsh outdoor environments. These high-quality power supplies are UL 508 listed, UL 60950 recognized, CE marked and RoHS compliant.



Features

- Ruggedized for harsh outdoor environments
- IP67 and NEMA 4X rated (dust, water, ice and oil resistant enclosure)
- Connection via waterproof I/O plug connectors
- Shock & vibration per IEC 60068
- Operating temperature range: -40°C to 85°C
- Universal input 85 to 264 VAC
- Output voltage adjustable
- DC-OK indicator
- Worldwide safety approvals
- Hazardous location Class I, Div 2
- 3-year warranty



Power Supplies							
Part Number Price Drawing Output Voltage Maximum Output Efficiency (Typ @ 115VAC)							
<u>PSX-12-100</u>	\$372.00	<u>PDF</u>	12V	96W	82		
<u>PSX-24-120</u>	\$346.00	PDF	24V	120W	82		

1-800-633-0405 For the latest prices RHINO Power Supplies PSX Series

Technical Specifications						
Part Number		<u>PSX-12-100</u>	<u>PSX-24-120</u>			
Input (AC/DC)						
Nominal Input	Voltage	100–24	IO VAC			
Nominal Input	Current (115/230VAC)	2.0 A / 1.0 A	2.4 A / 1.2 A			
Power Consun	mption (115/230VAC)	114W/112W typ.	140W/136W typ.			
Operational In	put Voltage Range	85–264 VAC, 85*–375 VDC [*se	e derating chart for <u>PSX-24-120]</u>			
Input Voltage I	Frequency Range	47–63 Hz				
Circuit Breake	r Rating / Characteristic	5.0 /	A/C			
Output (DC)						
Max. Output P	ower	96W	120W			
Output Voltage	9	12V	24V			
Max. Output C	urrent	8.0 A	5.0 A			
Output Voltage	e Adjustment Range	12.0–15.0 V	24.0–28.0 V			
Output Regulation		[10–90 % load variation] 2.5 % max.				
Output Power Derating - Temperature		2%/K above 60°C [140°F]				
Hold-up time		20 ms	s min.			
Ripple and No.	ise (20MHz bandwidth)	<50 mVp-p max.				
Output Overvo	oltage Protection (OVP)	<40V				
Short Circuit P	Protection	Current limitation at 110% typ., automatic restart				
Parallel Operat	tion	Only parallel redundancy is possible, with external decoupling diode. [See diagram on next page.]				
Indicator LED		DC-OK				
General Data						
Weight		1000g [35.3 oz]				
Network Configuration		TN-S, TT, IT				
Enclosure Material (Chassis/Cover)		Die-cast Aluminum				
Cooling		Convection cooling, no internal fan				
Power II	nput Connector:	ADC p/n PSX-CON1, Binder Circular Connector Series 693: 99-4222-14-04				
Connectors C	Dutput Connector:	ADC p/n PSX-CON2, Binder Circular Connector Series 693: 99-4217-160-07				
Wiring		Input: 3 x 18–14AWG (1 x Live, 1 x Neutral, 1 x Protective Earth Ground) Output: 7 x 18–16AWG (3 x +Vout, 3 x -Vout, 1 x Protective Earth Ground)				

Continued on next page

1-800-633-0405 RHINO Power Supplies PSX Series

Technical Specifications (continued)					
Part Number	<u>PSX-12-100</u> <u>PSX-24-120</u>				
Safety / Environmental					
Surrounding Ambient Temperature Range (Natural Air Convection Cooling)	-40 to 85°C [-40 to 185°F] [Observe derating] ATEX: -40 to 70°C [-40 to 158°F] [Observe derating]				
Humidity	Up to 100%, with condensation				
Storage Temperature	-40 to 85°C [-40 to 185°F]				
Maximum Altitude	3000m				
MTBF (acc. to IEC 61709 at 40°C)	> 900,000 hrs				
Protection Class	Class I				
Degree of Protection	IP67 (IEC 60529), NEMA 6P, UL50 4X Test to: Water intrusion, Dust, Icing, Oil exclusion, Salt spray, Gasket aging, Hosedown.				
Safety Standards	Information technology equipment IEC/EN 60950-1 Control equipment for hazardous location UL File No. E197886 (Class I, Division 2, group A, B, C & D, T4) Electrical equip. for potentially explosive atmospheres IEC/EN 60079-15 (Class I, Zone 2, EEx nA IIC T4) Industrial control equipment UL 508, File No. E197592 CSA (Tested to 61010), File No. 229285 Electrical equip. for measurement, control, laboratory IEC/EN 61010-1, C22.2 61010-1-12, UL 61010-1 3rd Electrical equipment for machines EN 60204-3 Electronic equipment for power installation EN 50178 Safety transformers EN 61558-2-8				
Environmental Compliance	Reach, RoHS directive 2011/65/EU				
Electromagnetic compatibility (EMC)					
Emissions	EN 61000-6-3				
Conducted RI Suppression On Input	EN 55032 class B				
Radiated RI Suppression	EN 55032 class B				
Harmonic Limits	EN 61000-3-2, class A				
Immunity	EN 61000-6-2				
Electrostatic Discharge (ESD)	IEC/EN 61000-4-2 8 kV/ 15 kV, perf criteria A				
Radiated RF Field Immunity	IEC/EN 61000-4-3 10 V/m, perf criteria A				
Electrical Fast Transient / Burst Immunity	Input: IEC/EN 61000-4-4 4 kV, perf criteria A Output: IEC/EN 61000-4-4 2 kV, perf criteria A				
Surge Immunity	Line–Neutral: IEC/EN 61000-4-5 4 kV, perf criteria A Line–Ground: IEC/EN 61000-4-5 2 kV, perf criteria A Neutral–Ground: IEC/EN 61000-4-5 4 kV, perf criteria A Output: IEC/EN 61000-4-5 0.5 kV, perf criteria A				
Immunity To Conducted RF Disturbances	IEC/EN 61000-4-6 10 V, perf criteria A				
Mains Voltage Dips And Interruptions	IEC/EN 61000-4-11 30%/10mS, criteria B; 60%/100mS, criteria C				
Environment					
Vibration Acc. IEC 60068-2-6-3	3 axis, 1g sine sweep, 10–55Hz, 1 oct/min				
Shock Acc. IEC 60068-2-27	3 axis, 15g half sine, 11ms				
Safety Approvals and Certifications	CE CB IP67 CE UI 508				

RHINO Power Supplies PSX Series



Connector Pinouts						
	Input					
1	Input Terminal L					
2	Input Terminal N					
3	Input Terminal PE (GND)					
Output						
1	Output Connection Terminal –					
2 Output Connection Terminal –						
3	3 Output Connection Terminal –					
4	Output Connection Terminal +					
5	Output Connection Terminal +					
6	6 Output Connection Terminal +					
7	Case Ground					



PSX-24-120 Output Power Derating (with DC Input Voltage)



Parallel Redundancy Wiring



Note:

1. The total current draw should not exceed the rated current of the power supply.

2. O-Ring diode current and voltage rating should be selected accordingly.



Accessories					
Part Number Price Description					
PSX-CON1	\$36.00	AC Input connector: Binder 3-pin female circular plug 99-4222-14-04			
PSX-CON2	\$36.00	DC Output connector: Binder 7-pin male circular plug 99-4225-160-07			

Note: The integrity of the seal cannot be guaranteed and warranty is void once the cover has been removed in the field!

To adjust the output voltage, the case cover must be removed. Carefully loosen and remove all six screws, then remove the cover. The output voltage of the unit can be adjusted by turning the potentiometer screw, using an insulated screwdriver. By turning the screw clockwise (cw) the output voltage will increase; by turning the screw counter-clockwise (ccw), the output voltage will decrease. The output voltage level should only be adjusted with the output connected to a load, (similar to the load used in the application). After adjusting the output voltage to the required value, the case must be carefully reassembled. Place the cover over the case and ensure that the rubber-sealing gasket is undamaged and is correctly positioned. Secure the lid with the six screws. Tighten the screws gradually, moving diagonally from one to another. The recommended tightening torque is 0.6 N·m [5.310 lb·in].

1-800-633-0405 **RHINO DIN Rail Power Supplies PSV Series**

Economical Power Supplies

Features

15–100W Models

- Ultra-compact size
- Up to 89% efficiency and built-in active PFC
- Universal AC input voltage
- Full power from -10°C to +55°C
- Low earth leakage current < 0.5 ma @ 264VAC
- Extreme low temperature cold start at -40°C
- NEC Class 2 / Limited Power Source (LPS) certified
- Plastic housing
- UL/cUL 508
- UL/cUL Recognized 60950-1
- CE
- Three year warranty



120–480W Models

- Universal AC input voltage
- Built-in constant current circuit for reactive loads
- Up to 89% efficiency
- Full power from -10°C to +50°C
- Compliance to SEMI F47 @ 200VAC voltage sag immunity
- Metal housing
- UL/cUL 508
- UL/cUL Recognized 60950-1
- CE
- 3-year warranty



DIN Rail Power Supplies						
Part Number	Price	Drawing Link	Output Voltage	Maximum Output Power [W]	Efficiency [Typ @ 115VAC]	
<u>PSV5-15S</u>	\$29.50	<u>PDF</u>	5V	15	79%	
<u>PSV5-25S</u>	\$45.00	<u>PDF</u>	5V	25	82%	
<u>PSV12-50S</u>	\$45.00	<u>PDF</u>	12V	48	88%	
<u>PSV24-30S</u>	\$29.50	<u>PDF</u>	24V	30	87.5%	
<u>PSV24-50S</u>	\$42.00	<u>PDF</u>	24V	50	89%	
<u>PSV24-100S</u>	\$55.00	<u>PDF</u>	24V	91.2	87%	
<u>PSV24-120S</u>	\$66.00	<u>PDF</u>	24V	120	85%	
<u>PSV24-240S</u>	\$96.00	<u>PDF</u>	24V	240	88%	
<u>PSV24-480S</u>	\$169.00	PDF	24V	480	85%	
<u>PSV48-120S</u>	\$66.00	PDF	48V	120	89%	

RHINO PSV5-15S Power Supply











READ INSTRUCTIONS BEFORE INSTALLING OR OPERATING THIS DEVICE. KEEP FOR FUTURE REFERENCE.

1. Safety instructions

- Switch main power off before connecting or disconnecting the device. Risk of explosion!
 To durantee sufficient convection cooling, place keep a distance of X40mm above and X2
- To guarantee sufficient convection cooling, please keep a distance of >40mm above and >20mm below the device as well as a lateral distance of >15mm to other cold source or heat source. Note that the enclosure of the device can become very hot depending on the ambient
- temperature and load of the power supply. Risk of burns!
- The main power must be turned off before connecting or disconnecting wires to the terminals!
- Do not introduce any objects into the unit!
- Dangerous voltage present for at least 5 minutes after disconnecting all sources of power.
- The power supplies are built-in units and must be installed in a cabinet or room (condensation free environment and indoor location) that is relatively free of conductive contaminants.
- The unit must be installed in an IP54 enclosure or cabinet in the final installation.

CAUTION: FOR USE IN A CONTROLLED ENVIRONMENT.

2. Device description (Fig. 1)

- Input terminal block connector
- (2) Output terminal block connector
- (3) DC voltage adjustment potentiometer
- (4) DC OK LED (green)
- (5) Universal mounting rail system

3. Mounting (Fig. 2)

The power supply unit can be mounted on 35mm DIN rails in accordance with EN60715. The device should be installed with input terminal block on the bottom.

Each device is delivered ready to install.

Snap on the DIN rail as shown in Fig. 2:

- 1. Tilt the unit slightly upwards and put it onto the DIN rail.
- Push downwards until stopped.
- Press against the bottom front side for locking.
- Shake the unit slightly to ensure that it is secured.

4. Dismounting (Fig. 3)

To uninstall, use a flat screwdriver to pull or slide down the latch as shown in Fig. 3. Then slide the PSU in the opposite direction, release the latch and pull out the PSU from the rail.

5. Connection

The terminal block connectors allow easy and fast wiring.

You can use flexible (stranded wire) or solid cables with cross sections:

	Electrical Connections and Wire Size						
	Stranded / Solid Torque						
	mm²	AWG	N∙m	lb∙in			
Input	0.32-3.3	22-12	0.51	4.5			
Output	0.52-3.3	20-12	0.51	4.5			

To secure reliable and shock proof connections, the stripping length should be 4-5mm (see Fig. 4 (1)). Please ensure that wires are fully inserted into the connecting terminals as shown in Fig. 4 (2).

In accordance to EN60950 / UL60950, flexible cables require ferrules.

Use appropriate copper cables that are designed to sustain operating temperature of at least 60°C/75°C for USA or at least 90°C for Canada.

5.1. Input connection (Fig. 1, Fig. 5)

Use L, N and GND connections of input terminal connector (see Fig. 1 (1)) to establish the 100-240 VAC connection. Typical connection methods are shown in Figure 5.

The unit is protected with an internal fuse (not replaceable) at L pin and it has been tested and approved on 20A (UL) and 16A (IEC) branch circuits without additional protection device. An external protection device is only required if the supplying branch has an ampacity greater than above. Thus, if an external protective device is necessary, or utilized, a minimum value of 10A B- or 6A C- characteristic breaker should be used.

The internal fuse must not be replaced by the user.

5.2. Output connection (Fig. 1 (2))

Use the "+" and "-" screw connections to establish the 5VDC connection. The output provides 5VDC. The output voltage can be adjusted from 5 to 5.5 VDC on the potentiometer. The green LED DC OK displays correct function of the output (Fig. 1 (4)). The device has a short circuit and overload protection and an overvoltage protection limited to 6.325-7.425 VDC.

5.3. Output characteristic curve

The device functions normal under operating line and load conditions. In the event of a short circuit or overload the output voltage and current collapses ($I_0 = 110-150\%$). The secondary voltage is reduced and bounces until short circuit or overload on the secondary side has been removed.

5.4. Thermal behavior (Fig. 6)

In the case of ambient temperatures:

- 1. At -10°C to -20°C [14°F to -4°F], the output capacity has to be reduced by 2% per degree Celsius increase in temperature.
- Above +55°C [131°F], the output capacity has to be reduced by 3.33% per degree Celsius increase in temperature.

If the output capacity is not reduced when $T_{Amb} > 55^{\circ}C$ [131°F], the device will engage thermal protection by switching off, i.e., the output voltage will go into latch-off mode until the component temperature cools down and the AC power is recycled.

FOR TECHNICAL ASSISTANCE CALL 770-844-4200

tPWR-117

RHINO PSV5-15S Power Supply

Technical Specifications				
Input (AC)				
Nominal input voltage / frequency	100-240 VAC / 50-60 Hz			
Voltage range	85-264 VAC			
Frequency	47-63 Hz			
Nominal current	< 0.5 A @ 115VAC, < 0.3 A @ 230VAC			
Inrush current limitation (+25°C, cold start)	< 35A @ 115VAC, < 65A @ 230VAC			
Mains buffering at nominal load (typ.)	20ms typ. @ 115VAC (100% load) 100ms typ. @ 230VAC (100% load)			
Turn-on time	< 3s @ 115VAC < 1.5 s @ 230VAC (100% load)			
Internal fuse	T 3 15 A / 250V (non-replaceable)			
Recommended backup protection	10A B- or 6A C- characteristic circuit breaker			
Leakage current	< 1mA @ 240VAC			
Output (DC)	·			
Nominal output voltage U _N / tolerance	5VDC ± 2 %			
Voltage adjustment range	5-5.5 VDC (maximum power \leq 15W)			
Nominal current	3A			
Derating	Refer to Fig. 6 -10°C to -20°C (2%/°C), > 55°C (3.33%/°C) in vertical orientation			
Startup with capacitive loads	Max. 3,000µF			
Max. power dissipation idling / nominal load approx.	0.3 W / 4 W			
Efficiency at 100% load	78.0% typ. @ 115VAC, 79.0% typ. @ 230VAC			
PARD (20MHz) at 100% load	< 75 mVpp			
General Data				
Type of housing	Plastic (PC), enclosed			
LED signals	Green LED DC OK			
MTBF	> 350,000 hrs. as per Telcordia			
Dimensions (L x W x H)	75mm x 21mm x 89.5 mm [2.95 in x 0.83 in x 3.52 in] (See www.AutomationDirect.com for complete engineering drawings.)			
Weight	0.11 kg [3.9 oz]			
Connection method	Screw connection			
Stripping length	4-5mm [U.16-U.20 In]			
Operating temperature (surrounding air temperature)	-20°C t0 +/0°C (-4°F t0 + 158°F) (Refer t0 FIG. 6)			
Storage temperature	-40°U TO +85°U [-40°F TO +185°F]			
Vibration	Operating: IEC60068-2-6, Sine Wave: 10Hz to 500Hz @ 19.6m/s ² ; displacement of 0.35 mm, 60min per axis for all X, Y, Z directions			
Shock	Non-Operating: IEC60068-2-6, Random: 5Hz to 500Hz (2.09 Grms); 20 min. per axis for all X, Y, Z directions Operating: IEC60068-2-27, Half Sine Wave: 10G for a duration of 11ms, shock for 1 direction (X axis) New Construct IEC60006-0-27, that Sine Wave: CoC for a duration of 11ms, shock for 1 direction (X axis)			
Pollution degree				
	2 2000m			
Certification and Standards	200011			
Safety entry low voltage	SELV (EN60950)			
Electrical safety (of information technology equipment)	UL/C-UL recognized to UL60950-1 and CSA C22.2 No. 60950-1 (File No. E198298), CB scheme to IEC60950-1, Limited Power Source (LPS)			
Industrial control equipment	UL/C-UL listed to UL508 and CSA C22.2 No.107.1-01 (File No. E197592)			
Class 2 power supply	UL/C-UL listed to UL508 and CSA C22.2 No.107.1-01 (File No. E197592)			
CE	In conformance with EMC directive 2014/30/EU and Low Voltage Directive 2014/35/EU			
Component power supply for general use	EN61204-3			
Immunity	EN55024, EN61000-6-1, EN61000-6-2 (EN61000-4-2, 3, 4, 5, 6, 8, 11)			
Emission	EN55032, EN55011, EN61000-3-3, EN61000-6-3, EN61000-6-4			
Ce	c US LISTED Ind. Cont. Eq.			
RoHS Compliant	Yes			
Safety and Protection				
Surge voltage protection against internal surge voltages	No			
Isolation voltage:	21/140			
Input / PE	SKVAC 3kVAC			
Output / PE	0.5 kVAC			
Protection degree	IP20			
Safety class	Class I with PE connection			

RHINO PSV5-25S Power Supply





d 3









READ INSTRUCTIONS BEFORE INSTALLING OR OPERATING THIS DEVICE. KEEP FOR FUTURE REFERENCE.

1. Safety instructions

- Switch main power off before connecting or disconnecting the device. Risk of explosion!
 To guarantee sufficient convection cooling, please keep a distance of >40mm above and >20mm below the device as well as a lateral distance of >15mm to other cold source. In case the adjacent
- device is a heat source, the lateral distance will be >25mm.
 Note that the enclosure of the device can become very hot depending on the ambient temperature and load of the away supply. Bick of hursel
- temperature and load of the power supply. Risk of burns! • The main power must be turned off before connecting or disconnecting wires to the terminals!
- Do not introduce any objects into the unit!
- Dangerous voltage present for at least 5 minutes after disconnecting all sources of power.
- The power supplies are built-in units and must be installed in a cabinet or room (condensation
- free environment and indoor location) that is relatively free of conductive contaminants.
- The unit must be installed in an IP54 enclosure or cabinet in the final installation.

CAUTION: FOR USE IN A CONTROLLED ENVIRONMENT.

- 2. Device description (Fig. 1)
 - (1) Input terminal block connector
 - (2) Output terminal block connector
 - (3) DC voltage adjustment potentiometer
 - (4) DC OK LED (green)
 - (5) Universal mounting rail system

3. Mounting (Fig. 2)

The power supply unit can be mounted on 35mm DIN rails in accordance with EN60715. The device should be installed with input terminal block on the bottom.

Each device is delivered ready to install.

- Snap on the DIN rail as shown in Fig. 2:
 - 1. Tilt the unit slightly upwards and put it onto the DIN rail.
 - Push downwards until stopped.
 - Press against the bottom front side for locking.
 - Shake the unit slightly to ensure that it is secured.

4. Dismounting (Fig. 3)

To uninstall, use a flat screwdriver to pull or slide down the latch as shown in Fig. 3. Then slide the PSU in the opposite direction, release the latch and pull out the PSU from the rail.

5. Connection

The terminal block connectors allow easy and fast wiring.

You can use flexible (stranded wire) or solid cables with cross sections:

Electrical Connections and Wire Size					
Stranded / Solid Torque					
	mm²	AWG	N∙m	lb∙in	
Input	0.32-3.3	22-12	0.51	4.5	
Output	0.82-3.3	18-12	0.51	4.5	

To secure reliable and shock proof connections, the stripping length should be 4-5mm (see Fig. 4 (1)). Please ensure that wires are fully inserted into the connecting terminals as shown in Fig. 4 (2).

In accordance to EN60950 / UL60950, flexible cables require ferrules.

Use appropriate copper cables that are designed to sustain operating temperature of at least $60^{\circ}C/75^{\circ}C$ for USA or at least $90^{\circ}C$ for Canada.

5.1. Input connection (Fig. 1, Fig. 5)

Use L, N and GND connections of input terminal connector (see Fig. 1 (1)) to establish the 100-240 VAC connection. Typical connection methods are shown in Figure 5.

The unit is protected with an internal fuse (not replaceable) at L pin and it has been tested and approved on 20A (UL) and 16A (IEC) branch circuits without additional protection device. An external protection device is only required if the supplying branch has an ampacity greater than above. Thus, if an external protective device is necessary, or utilized, a minimum value of 20A B- or 10A C- characteristic breaker should be used.

The internal fuse must not be replaced by the user.

5.2. Output connection (Fig. 1 (2))

Use the "+" and "-" screw connections to establish the 5VDC connection. The output provides 5VDC. The output voltage can be adjusted from 5 to 5.5 VDC on the potentiometer. The green LED DC OK displays correct function of the output (Fig. 1 (4)). The device has a short circuit and overload protection and an overvoltage protection limited to 6.325-7.425 VDC.

5.3. Output characteristic curve

The device functions normal under operating line and load conditions. In the event of a short circuit or overload the output voltage and current collapses (I₀ = 110-160%). The secondary voltage is reduced and bounces until short circuit or overload on the secondary side has been removed.

5.4. Thermal behavior (Fig. 6)

In the case of ambient temperatures:

- At -10°C to -20°C [14°F to -4°F], the output capacity has to be reduced by 2% per degree Celsius increase in temperature.
- Above +55°C [131°F], the output capacity has to be reduced by 3.33% per degree Celsius increase in temperature.

If the output capacity is not reduced when $T_{Amb} > 55^{\circ}C$ [131°F], the device will engage thermal protection by switching off, i.e., the output voltage will go into latch-off mode until the component temperature cools down and the AC power is recycled.

FOR TECHNICAL ASSISTANCE CALL 770-844-4200

Power Supplies tP

tPWR-119

RHINO PSV5-25S Power Supply

Technical Specifications				
Input (AC)				
Nominal input voltage / frequency	100-240 VAC / 50-60 Hz			
Voltage range	85-264 VAC			
Frequency	47-63 Hz			
Nominal current	< 0.8 A @ 115VAC. < 0.5 A @ 230VAC			
Inrush current limitation (+25°C, cold start)	< 35A @ 115VAC. < 60A @ 230VAC			
Mains buffering at nominal load (two.)	20ms typ. @ 115VAC (100% load)			
	100ms typ. @ 230VAC (100% load)			
Turn-on time	< 3s @ 115VAC, < 1.5 s @ 230VAC (100% load)			
Internal fuse	I 3.15 A / 250V (non-replaceable)			
Recommended backup protection	20A B- or 10A C- characteristic circuit breaker			
Leakage current	< 1ma @ 24UVAC			
Output (DC)				
Nominal output voltage U _N / tolerance	5VDC ± 2 %			
Voltage adjustment range	5-5.5 VDC (maximum power ≤ 25W)			
Nominal current	5A Defecto Fig. 6			
Derating	-10°C to -20°C (2%/°C), > 55°C (3.33%/°C) in vertical orientation			
Startup with capacitive loads	Max. 3,000µF			
Max. power dissipation idling / nominal load approx.	0.4 W / 8 W			
Efficiency at 100% load	79.0% typ. @ 115VAC, 80.0% typ. @ 230VAC			
PARD (20MHz) at 100% load	< 75 mVpp			
General Data				
Type of housing	Plastic (PC), enclosed			
LED signals	Green LED DC OK			
MTBF	> 350,000 hrs. as per Telcordia			
Dimensions (L x W x H)	75mm x 30mm x 89.5 mm [2.95 in x 1.18 in x 3.52 in] (See www.AutomationDirect.com for complete engineering drawings.)			
Weight	0.16 kg [5.6 oz]			
Connection method	Screw connection			
Stripping length	4-5mm [0.16-0.20 in]			
Operating temperature (surrounding air temperature)	-20°C to +70°C [-4°F to +158°F] (Refer to Fig. 6)			
Storage temperature	-40°C to +85°C [-40°F to +185°F]			
Humidity at +25°C, no condensation	5 to 95% RH			
Vibration	Operating: IEC60068-2-6, Sine Wave: 10Hz to 500Hz @ 19.6m/s ² ; displacement of 0.35 mm, 60min per axis for all X, Y, Z			
VIDIALION	Non-Operating: IEC60068-2-6, Random: 5Hz to 500Hz (2.09 Grms); 20 min. per axis for all X, Y, Z directions			
Shock	Operating: IEC60068-2-27, Half Sine Wave: 10G for a duration of 11ms, shock for 1 direction (X axis)			
	Non-Uperating: IEC60068-2-27, Halt Sine Wave: 50G for a duration of 11ms, 3 shocks for each 3 directions			
	2000m			
Certification and Standards	200011			
Safaty antry low voltage	SEL 1/ (EN60050)			
	UL/C-UL recognized to UL60950-1 and CSA C22.2 No. 60950-1 (File No. E198298), CB scheme to IEC60950-1,			
Electrical safety (of information technology equipment)	Limited Power Source (LPS)			
Industrial control equipment	UL/C-UL listed to UL508 and CSA C22.2 No.107.1-01 (File No. E197592)			
Class 2 power supply	UL/C-UL listed to UL508 and CSA C22.2 No.107.1-01 (File No. E197592)			
CE	In conformance with EMC directive 2014/30/EU and Low Voltage Directive 2014/35/EU			
Component power supply for general use	EN61204-3			
Immunity	ENSO24, ENG1000-6-1, ENG1000-6-2 (EN61000-4-2, 3, 4, 5, 6, 8, 11)			
Emission	EN55032, EN55011, EN61000-3-3, EN61000-6-3, EN61000-6-4			
	LISTED E198298			
	Ind. Cont. Eq.			
RoHS Compliant	Yes			
Safety and Protection				
Surge voltage protection against internal surge voltages	No			
Isolation voltage:	20//00			
Input / PE	3kVAC			
Output / PE	0.5 kVAC			
Protection degree	IP20			
Safety class	Class I with PE connection			

(3)

(2)

READ INSTRUCTIONS BEFORE INSTALLING OR OPERATING THIS DEVICE. **KEEP FOR FUTURE REFERENCE.**

1. Safety instructions

- Switch main power off before connecting or disconnecting the device. Risk of explosion!
- To guarantee sufficient convection cooling, please keep a distance of >40mm above and >20mm below the device as well as a lateral distance of >15mm to other cold source. In case the adjacent device is a heat source, the lateral distance will be >25mm.
 - Note that the enclosure of the device can become very hot depending on the ambient
- temperature and load of the power supply. Risk of burns!
- The main power must be turned off before connecting or disconnecting wires to the terminals!
- Do not introduce any objects into the unit!
- Dangerous voltage present for at least 5 minutes after disconnecting all sources of power. The power supplies are built-in units and must be installed in a cabinet or room (condensation
- free environment and indoor location) that is relatively free of conductive contaminants.
- The unit must be installed in an IP54 enclosure or cabinet in the final installation
- CAUTION: FOR USE IN A CONTROLLED ENVIRONMENT.

2. Device description (Fig. 1)

- (1) Input terminal block connector
- (2) Output terminal block connector
- (3) DC voltage adjustment potentiometer
- DC OK LED (green) (4)
- (5) Universal mounting rail system

3. Mounting (Fig. 2)

The power supply unit can be mounted on 35mm DIN rails in accordance with EN60715. The device should be installed with input terminal block on the bottom.

Each device is delivered ready to install.

- Snap on the DIN rail as shown in Fig. 2:
 - 1. Tilt the unit slightly upwards and put it onto the DIN rail.
 - 2. Push downwards until stopped.
 - 3. Press against the bottom front side for locking.
 - 4. Shake the unit slightly to ensure that it is secured

4. Dismounting (Fig. 3)

To uninstall, use a flat screwdriver to pull or slide down the latch as shown in Fig. 3. Then slide the PSU in the opposite direction, release the latch and pull out the PSU from the rail.

5. Connection

The terminal block connectors allow easy and fast wiring.

You can use flexible (stranded wire) or solid cables with cross sections:

Electrical Connections and Wire Size					
	Stranded / Solid Torque				
	mm²	AWG	N∙m	lb•in	
Input	0.52-3.3	20-12	0.51	4.5	
Output	0.52-3.3	20-12	0.51	4.5	

To secure reliable and shock proof connections, the stripping length should be 4-5mm (see Fig. 4 (1)). Please ensure that wires are fully inserted into the connecting terminals as shown in Fig. 4 (2).

In accordance to EN60950 / UL60950 and EN62368 / UL62368, flexible cables require ferrules.

Use appropriate copper cables that are designed to sustain operating temperature of at least 60°C/75°C for USA or at least 90°C for Canada.

5.1. Input connection (Fig. 1, Fig. 5)

Use L, N and GND connections of input terminal connector (see Fig. 1 (1)) to establish the 100-240 VAC connection. Typical connection methods are shown in Figure 5.

The unit is protected with an internal fuse (not replaceable) at L pin and it has been tested and approved on 20A (UL) and 16A (IEC) branch circuits without additional protection device. An external protection device is only required if the supplying branch has an ampacity greater than above. Thus, if an external protective device is necessary, or utilized, a minimum value of 20A B- or 13A C- characteristic breaker should be used.

The internal fuse must not be replaced by the user.

5.2. Output connection (Fig. 1 (2))

Use the "+" and "-" screw connections to establish the 12 VDC connection. The output provides 12 VDC. The output voltage can be adjusted from 12 to 15 VDC on the potentiometer. The green LED DC OK displays correct function of the output (Fig. 1 (4)). The device has a short circuit and overload protection and an overvoltage protection limited to 16-18.7 VDC.

5.3. Output characteristic curve

The device functions normal under operating line and load conditions. In the event of a short circuit or overload the output voltage and current collapses (I₀ = 110-150%). The secondary voltage is reduced and bounces until short circuit or overload on the secondary side has been removed.

5.4. Thermal behavior (Fig. 6)

In the case of ambient temperatures:

- 1. At -10°C to -20°C [14°F to -4°F], the output capacity has to be reduced by 2% per degree Celsius increase in temperature.
- 2. Above +55°C [131°F], the output capacity has to be reduced by 3.33% per degree Celsius increase in temperature.

If the output capacity is not reduced when T_{Amb} > 55°C [131°F], the device will engage thermal protection by switching off, i.e., the output voltage will go into latch-off mode until the component temperature cools down and the AC power is recycled.

FOR TECHNICAL ASSISTANCE CALL 770-844-4200



5 10 15 20 25 30 35 40 45 50 55 60 65 70

Surrounding Air Temperature (°C)

-4 5 14 23 32 41 50 59 68 77 86 95 104 113 122 131 140 149 158

Surrounding Air Temperature (°F)

Figure 1

Figure 2

Figure 3

Figure 4

30

20

10

Figure 6

-20 -15 -10 -5 0

←1 ↓2

♥③

• 2

₽①

4-5mm [0.16-0.20in]

1



RHINO PSV12-50S Power Supply

	Technical Specifications
Input (AC)	
Nominal input voltage / frequency	100-240 VAC / 50-60 Hz
Voltage range	85-264 VAC
Frequency	47-63 Hz
Nominal current	< 1.0 A @ 115VAC, < 0.6 A @ 230VAC
Inrush current limitation (+25°C, cold start)	< 35A @ 115VAC, < 60A @ 230VAC
Mains buffering at nominal load (typ.)	20ms typ. @ 115VAC (100% load)
	90115 typ. @ 230VAC (100% 10dd)
	< 35 @ 113VAC, < 1.3 5 @ 230VAC (100% 10du) T 3 15 A / 250V/ (non-replaceable)
Becommended backup protection	200 B- or 130 C- characteristic circuit breaker
Leakage current	
Nominal output voltage LL, / tolerance	12VDC + 2 %
Voltage adjustment range	12-15 VDC (maximum nower < 48W)
Nominal current	
Desition	Refer to Fig. 6
Derating	-10°C to -20°C (2%/°C), > 55°C (3.33%/°C) in vertical orientation
Startup with capacitive loads	Max. 3,000µF
Max. power dissipation idling / nominal load approx.	0.5 W / 7 W
Efficiency at 100% load	86.0% typ. @ 115VAC, 88.0% typ. @ 230VAC
PARD (20MHz) at 100% load	< 75 mVpp
Parallel operation	With ORing Diode
General Data	I
Type of housing	Plastic (PC), enclosed
LED signals	Green LED DC OK
MIBF	> 350,000 hrs. as per l'elcordia
Dimensions (L x W x H)	75mm x 30mm x 89.5 mm [2.95 in x 1.18 in x 3.52 in] (See www.AutomationDirect.com for complete engineering drawings.)
Weight	0.18 kg [6.3 oz]
Connection method	Screw connection
	4-5mm [U. 16-U.20 In]
Operating temperature (surrounding air temperature)	-20°C to +70°C [-4°F to +158°F] (Reter to Fig. 6)
Storage temperature	-40°C (0 +85°C [-40°F (0 +185°F]
Humidity at +25°C, no condensation	0 IU 95% KH Operating: IEC60068-2-6 Sine Wave: 10Hz to 500Hz @ 10 6m/c²: displacement of 0.35 mm, 60min per avis for all X.V. 7
Vibration	directions
	Non-Operating: IEC60068-2-6, Random: 5Hz to 500Hz (2.09 Grms); 20 min. per axis for all X, Y, Z directions
Shock	Non-Operating: IEC60068-2-27, Half Sine Wave: 50G for a duration of 11ms, 3 shocks for each 3 directions
Pollution degree	2
Altitude (operating)	2000m
Certification and Standards	
Safety entry low voltage	SELV (EN60950)
Electrical safety (of information technology equipment)	UL/C-UL recognized to UL60950-1 and CSA C22.2 No. 60950-1 (File No. E198298), CB scheme to IEC60950-1, UL/C-UL recognized to UL62368-1 and CSA C22.2 No. 62368-1 (File No. E508040), CB scheme to IEC62368-1, Limited Power Source (LPS)
Industrial control equipment	UL/C-UL listed to UL508 and CSA C22.2 No.107.1-01 (File No. E197592)
Class 2 power supply	UL/C-UL listed to UL508 and CSA C22.2 No.107.1-01 (File No. E197592)
CE	In conformance with EMC directive 2014/30/EU and Low Voltage Directive 2014/35/EU
Component power supply for general use	EN61204-3
Immunity	EN55024, EN61000-6-1, EN61000-6-2
Emission	(EN01000-4-2, 3, 4, 3, 0, 6, 11) EN55022 EN55011 EN61000 2.2 EN61000 6.2 EN61000 6.4
Emission	ENSSU32, ENSSU11, EN61000-3-3, EN61000-6-4
RoHS Compliant	Yes
Safety and Protection	
Surge voltage protection against internal surge voltages	No
Isolation voltage:	
Input / output	3KVAC
Output / PE	O.5 kVAC
Protection degree	IP20
Safety class	Class I with PE connection

1st Edition, Rev. C, 08/2019

For the latest prices, please check AutomationDirect.com. 1-800-633-0405 **RHINO PSV24-30S Power Supply**











Power Derating Curve for PSU in Vertical Mounting 110 100 90 80 Percentage of Max Load (%) 70 60 50 40 30 20 10 -20 -15 -10 -5 0 5 10 15 20 25 30 35 40 45 50 55 60 65 70 Surrounding Air Temperature (°C) -4 5 14 23 32 41 50 59 68 77 86 95 104 113 122 131 140 149 158 Surrounding Air Temperature (°F) Figure 6

READ INSTRUCTIONS BEFORE INSTALLING OR OPERATING THIS DEVICE. KEEP FOR FUTURE REFERENCE.

1. Safety instructions

- Switch main power off before connecting or disconnecting the device. Risk of explosion!
- To guarantee sufficient convection cooling, please keep a distance of >40mm above and >20mm below the device as well as a lateral distance of >10mm to other cold source. In case the adjacent device is a heat source, the lateral distance will be >25mm
- Note that the enclosure of the device can become very hot depending on the ambient temperature and load of the power supply. Risk of burns!
- The main power must be turned off before connecting or disconnecting wires to the terminals!
- Do not introduce any objects into the unit! .
- Dangerous voltage present for at least 5 minutes after disconnecting all sources of power.
- The power supplies are built-in units and must be installed in a cabinet or room (condensation
- free environment and indoor location) that is relatively free of conductive contaminants.
- The unit must be installed in an IP54 enclosure or cabinet in the final installation.

CAUTION: FOR USE IN A CONTROLLED ENVIRONMENT.

- 2. Device description (Fig. 1)
 - (1) Input terminal block connector
 - Output terminal block connector (2) (3) DC voltage adjustment potentiometer
 - (4)
 - DC OK LED (green) (5) Universal mounting rail system

3. Mounting (Fig. 2)

The power supply unit can be mounted on 35mm DIN rails in accordance with EN60715. The device should be installed with input terminal block on the bottom.

Each device is delivered ready to install.

- Snap on the DIN rail as shown in Fig. 2:
 - 1. Tilt the unit slightly upwards and put it onto the DIN rail.
 - 2. Push downwards until stopped.
 - 3. Press against the bottom front side for locking.
 - 4. Shake the unit slightly to ensure that it is secured.

4. Dismounting (Fig. 3)

To uninstall, use a flat screwdriver to pull or slide down the latch as shown in Fig. 3. Then slide the PSU in the opposite direction, release the latch and pull out the PSU from the rail.

5. Connection

The terminal block connectors allow easy and fast wiring.

You can use flexible (stranded wire) or solid cables with cross sections:

Electrical Connections and Wire Size				
	Stranded / Solid Torque			
	mm²	AWG	N·m	lb∙in
Input	0.32-3.3	22-12	0.51	4.5
Output	0.52-3.3	20-12	0.51	4.5

To secure reliable and shock proof connections, the stripping length should be 4-5mm (see Fig. 4 (1)). Please ensure that wires are fully inserted into the connecting terminals as shown in Fig. 4 (2).

In accordance to EN60950 / UL60950, flexible cables require ferrules.

Use appropriate copper cables that are designed to sustain operating temperature of at least 60°C/75°C for USA or at least 90°C for Canada.

5.1. Input connection (Fig. 1, Fig. 5)

Use L, N and GND connections of input terminal connector (see Fig. 1 (1)) to establish the 100-240 VAC connection. Typical connection methods are shown in Figure 5.

The unit is protected with an internal fuse (not replaceable) at L pin and it has been tested and approved on 20A (UL) and 16A (IEC) branch circuits without additional protection device. An external protection device is only required if the supplying branch has an ampacity greater than above. Thus, if an external protective device is necessary, or utilized, a minimum value of 13A B- or 8A C- characteristic breaker should be used.

The internal fuse must not be replaced by the user.

5.2. Output connection (Fig. 1 (2))

Use the "+" and "-" screw connections to establish the 24VDC connection. The output provides 24VDC. The output voltage can be adjusted from 24 to 28 VDC on the potentiometer. The green LED DC OK displays correct function of the output (Fig. 1 (4)). The device has a short circuit and overload protection and an overvoltage protection limited to 30-34.8 VDC.

5.3. Output characteristic curve

The device functions normal under operating line and load conditions. In the event of a short circuit or overload the output voltage and current collapses ($I_0 = 110-150\%$). The secondary voltage is reduced and bounces until short circuit or overload on the secondary side has been removed.

5.4. Thermal behavior (Fig. 6)

- In the case of ambient temperatures:
 - 1. At -10 $^\circ$ C to -20 $^\circ$ C [14 $^\circ$ F to -4 $^\circ$ F], the output capacity has to be reduced by 2% per degree Celsius increase in temperature
 - 2. Above +55°C [131°F], the output capacity has to be reduced by 3.33% per degree Celsius increase in temperature.

If the output capacity is not reduced when T_{Amb} > 55 $^{\circ}C$ [131 $^{\circ}F$], the device will engage thermal protection by switching off, i.e., the output voltage will go into latch-off mode until the component temperature cools down and the AC power is recycled.

RHINO PSV24-30S Power Supply

Technical Specifications			
Input (AC)			
Nominal input voltage / frequency	100-240 VAC / 50-60 Hz		
Voltage range	85-264 VAC		
Frequency	47-63 Hz		
Nominal current	< 0.8 A @ 115VAC, < 0.4 A @ 230VAC		
Inrush current limitation (+25°C, cold start)	< 35A @ 115VAC, < 60A @ 230VAC		
Mains buffering at nominal load (typ.)	20ms typ. @ 115VAC (100% load)		
Turn-on time	~ ?< @ 115\VAC. < 1 6 < @ 230\VAC. (100% load)		
Internal fuse	T 3 15 A / 250V (non-replaceable)		
Recommended backup protection	13A B- or 8A C- characteristic circuit breaker		
Leakage current	< 1mA @ 240VAC		
Output (DC)			
Nominal output voltage U _N / tolerance	24VDC ± 2 %		
Voltage adjustment range	24-28 VDC (maximum power ≤ 30W)		
Nominal current	1.25 A		
Derating	Refer to Fig. 6 -10°C to -20°C (2%/°C), > 55°C (3.33%/°C) in vertical orientation		
Startup with capacitive loads	Max. 3,000µF		
Max. power dissipation idling / nominal load approx.	0.5 W / 4.5 W		
Efficiency at 100% load	87.0% typ. @ 115VAC, 88.0% typ. @ 230VAC		
PARD (20MHz) at +25°C, 100% load	< 75 mVpp		
Parallel operation	PSB60-REM20S / PSB60-REM40S or with UKing Diode		
General Data			
	Plastic (PC), enclosed		
	S 250 000 bre as por Talcordia		
NIBF	> 300,000 IIIS. as per record and a second a		
	1/311111 X 2 111111 X 03.0 11111 [2.30 111 X 0.00 111 X 0.32 111] (000 mmm.dutorination.org/org/not/org/not/ing/org/norg/not/ing/org/not/ing/org/not/ing/org/norg/not/ing/org/		
Connection method	Screw connection		
Strinning length	4-5mm [0.16-0.20 in]		
Operating temperature (surrounding air temperature)	-20°C to +70°C [-4°F to +158°F] (Refer to Fig. 6)		
Storage temperature	-40°C to +85°C [-40°F to +185°F]		
Humidity at +25°C, no condensation	5 to 95% RH		
Vibration	Operating: IEC60068-2-6, Sine Wave: 10Hz to 500Hz @ 19.6m/s ² ; displacement of 0.35 mm, 60min per axis for all X, Y, Z directions Non-Operating: IEC60068-2-6, Random: 5Hz to 500Hz (2.09 Grms); 20 min. per axis for all X, Y, Z directions		
Shock	Operating: IEC60068-2-27, Half Sine Wave: 10G for a duration of 11ms, shock for 1 direction (X axis) Non-Operating: IEC60068-2-27, Half Sine Wave: 50G for a duration of 11ms, 3 shocks for each 3 directions		
Pollution degree	2		
Altitude (operating)	2000m		
Certification and Standards			
Safety entry low voltage	SELV (EN60950) UL/C-UL recognized to UL60950-1 and CSA C22.2 No. 60950-1 (File No. E198298), CB scheme to IEC60950-1,		
	Limited Power Source (LPS)		
	UL/U-UL IISTED TO ULOUG AIRU USA UZZZ INU. TUT. I-UT (FITE INU. E 197092)		
Class 2 power suppry	In conformance with FMC directive 2014/30/FLLand Low Voltage Directive 2014/35/FLL		
Component nower supply for dependings	FN61204-3		
	EN0100-6-2		
Immunity	(EN61000-4-2, 3, 4, 5, 6, 8, 11)		
Emission	EN55032, EN55011, EN61000-3-3, EN61000-6-3, EN61000-6-4		
C	C US LISTED Ind. Cont. Eq.		
RoHS Compliant	Yes		
Safety and Protection			
Surge voltage protection against internal surge voltages	No		
Isolation voltage:			
Input / output Input / PE	3KVAC 3KVAC		
Output / PE	0.5 KVAC		
Protection degree	IP20		
Safety class	Class I with PE connection		

1-800-633-0405 For the latest prices, please check AutomationDirect.com. RHINO PSV24-50S Power Supply



Figure 2







Power Derating Curve for PSU in Vertical Mounting 110 100 90 80 Percentage of Max Load (%) 70 60 50 40 30 20 10 -20 -15 -10 -5 0 5 10 15 20 25 30 35 40 45 50 55 60 65 70 Surrounding Air Temperature (°C) -4 5 14 23 32 41 50 59 68 77 86 95 104 113 122 131 140 149 158 Surrounding Air Temperature (°F) Figure 6

READ INSTRUCTIONS BEFORE INSTALLING OR OPERATING THIS DEVICE. KEEP FOR FUTURE REFERENCE.

1. Safety instructions

- Switch main power off before connecting or disconnecting the device. Risk of explosion!
- To guarantee sufficient convection cooling, please keep a distance of >40mm above and >20mm below the device as well as a lateral distance of >15mm to other cold source. In case the adjacent device is a heat source, the lateral distance will be >25mm.
- Note that the enclosure of the device can become very hot depending on the ambient temperature and load of the power supply. Risk of burns!
- The main power must be turned off before connecting or disconnecting wires to the terminals!
- Do not introduce any objects into the unit!
- Dangerous voltage present for at least 5 minutes after disconnecting all sources of power.
- The power supplies are built-in units and must be installed in a cabinet or room (condensation
- free environment and indoor location) that is relatively free of conductive contaminants. The unit must be installed in an IP54 enclosure or cabinet in the final installation.

CAUTION: FOR USE IN A CONTROLLED ENVIRONMENT.

2. Device description (Fig. 1)

- (1) Input terminal block connector
- (2) Output terminal block connector
- (3) DC voltage adjustment potentiometer
- (4) DC OK LED (green)
- (5) Universal mounting rail system

3. Mounting (Fig. 2)

The power supply unit can be mounted on 35mm DIN rails in accordance with EN60715. The device should be installed with input terminal block on the bottom.

Each device is delivered ready to install.

Snap on the DIN rail as shown in Fig. 2:

- 1. Tilt the unit slightly upwards and put it onto the DIN rail.
- Push downwards until stopped.
- Press against the bottom front side for locking.
- 4. Shake the unit slightly to ensure that it is secured.

4. Dismounting (Fig. 3)

To uninstall, use a flat screwdriver to pull or slide down the latch as shown in Fig. 3. Then slide the PSU in the opposite direction, release the latch and pull out the PSU from the rail.

5. Connection

The terminal block connectors allow easy and fast wiring.

You can use flexible (stranded wire) or solid cables with cross sections:

Electrical Connections and Wire Size					
Stranded / Solid Torque					
	mm²	AWG	N∙m	lb∙in	
Input	0.32-3.3	22-12	0.51	4.5	
Output	0.52-3.3	20-12	0.51	4.5	

To secure reliable and shock proof connections, the stripping length should be 4-5mm (see Fig. 4 (1)). Please ensure that wires are fully inserted into the connecting terminals as shown in Fig. 4 (2).

In accordance to EN60950 / UL60950, flexible cables require ferrules.

Use appropriate copper cables that are designed to sustain operating temperature of at least $60^{\circ}C/75^{\circ}C$ for USA or at least $90^{\circ}C$ for Canada.

5.1. Input connection (Fig. 1, Fig. 5)

Use L, N and GND connections of input terminal connector (see Fig. 1 (1)) to establish the 100-240 VAC connection. Typical connection methods are shown in Figure 5.

The unit is protected with an internal fuse (not replaceable) at L pin and it has been tested and approved on 20A (UL) and 16A (IEC) branch circuits without additional protection device. An external protection device is only required if the supplying branch has an ampacity greater than above. Thus, if an external protective device is necessary, or utilized, a minimum value of 20A B- or 13A C- characteristic breaker should be used.

The internal fuse must not be replaced by the user.

5.2. Output connection (Fig. 1 (2))

Use the "+" and "-" screw connections to establish the 24VDC connection. The output provides 24VDC. The output voltage can be adjusted from 24 to 28 VDC on the potentiometer. The green LED DC OK displays correct function of the output (Fig. 1 (4)). The device has a short circuit and overload protection and an overvoltage protection limited to 30-34.8 VDC.

5.3. Output characteristic curve

The device functions normal under operating line and load conditions. In the event of a short circuit or overload the output voltage and current collapses (I₀ = 110-150%). The secondary voltage is reduced and bounces until short circuit or overload on the secondary side has been removed.

5.4. Thermal behavior (Fig. 6)

- In the case of ambient temperatures:
 - At -10°C to -20°C [14°F to -4°F], the output capacity has to be reduced by 2% per degree Celsius increase in temperature.
 - Above +55°C [131°F], the output capacity has to be reduced by 3.33% per degree Celsius increase in temperature.

If the output capacity is not reduced when $T_{Amb} > 55^{\circ}C$ [131°F], the device will engage thermal protection by switching off, i.e., the output voltage will go into latch-off mode until the component temperature cools down and the AC power is recycled.

FOR TECHNICAL ASSISTANCE CALL 770-844-4200

RHINO PSV24-50S Power Supply

	Technical Specifications
Input (AC)	
Nominal input voltage / frequency	100-240 VAC / 50-60 Hz
Voltage range	85-264 VAC
Frequency	47-63 Hz
Nominal current	< 1.0 A @ 115VAC, < 0.6 A @ 230VAC
Inrush current limitation (+25°C, cold start)	< 35A @ 115VAC, < 60A @ 230VAC
Mains buffering at nominal load (typ.)	20ms typ. @ 115VAC (100% load) 90ms typ. @ 230VAC (100% load)
Turn-on time	< 3s @ 115VAC. < 1.5 s @ 230VAC (100% load)
Internal fuse	T 3.15 A / 250V (non-replaceable)
Becommended backup protection	20A B- or 13A C- characteristic circuit breaker
Leakage current	< 1mA @ 240VAC
Outnut (DC)	
Nominal output voltage U _N / tolerance	24VDC + 2 %
Voltage adjustment range	24-28 VDC (maximum power ≤ 50W)
Nominal current	21A
Derating	Refer to Fig. 6 -10°C to -20°C (2%/°C) > 55°C (3.33%/°C) in vertical orientation
Startup with capacitive loads	Max 3 000µF
Max power dissipation idling / nominal load approx	0.5 W / 7W
Efficiency at 100% load	86.0% tvn @ 115VAC 88.0% tvn @ 230VAC
PABD (20MHz) at +25°C 100% load	< 75 mVnn
Parallel operation	PSB60-REM20S / PSB60-REM40S or with OBing Diode
General Data	
Type of housing	Plastic (PC) enclosed
I ED signals	Green I ED DC OK
MTBE	> 350 000 hrs. as ner Telcordia
Dimensions (L x W x H)	75mm x 30mm x 89.5 mm [2.95 in x 1.18 in x 3.52 in] (See www.AutomationDirect.com for complete engineering drawings.)
Weight	0.18 kg [6.3 oz]
Connection method	Screw connection
Stripping length	4-5mm [0.16-0.20 in]
Operating temperature (surrounding air temperature)	-20°C to +70°C [-4°F to +158°F] (Refer to Fig. 6)
Storage temperature	-40°C to +85°C [-40°F to +185°F]
Humidity at +25°C, no condensation	5 to 95% RH
Vibration	Operating: IEC60068-2-6, Sine Wave: 10Hz to 500Hz @ 19.6m/s ² ; displacement of 0.35 mm, 60min per axis for all X, Y, Z directions Non-Operating: IEC60068-2-6, Random: 5Hz to 500Hz (2.09 Grms); 20 min. per axis for all X, Y, Z directions
Shock	Operating: IEC60068-2-27, Half Sine Wave: 10G for a duration of 11ms, shock for 1 direction (X axis) Non-Operating: IEC60068-2-27, Half Sine Wave: 50G for a duration of 11ms, 3 shocks for each 3 directions
Pollution degree	2
Altitude (operating)	2000m
Certification and Standards	1
Safety entry low voltage	SELV (EN60950)
Electrical safety (of information technology equipment)	UL/C-UL recognized to UL60950-1 and CSA C22.2 No. 60950-1 (File No. E198298), CB scheme to IEC60950-1, Limited Power Source (LPS)
Industrial control equipment	UL/C-UL listed to UL508 and CSA C22.2 No.107.1-01 (File No. E197592)
Class 2 power supply	UL/C-UL listed to UL508 and CSA C22.2 No.107.1-01 (File No. E197592)
CE	In conformance with EMC directive 2014/30/EU and Low Voltage Directive 2014/35/EU
Component power supply for general use	EN61204-3
Immunity	EN55024, EN61000-6-1, EN61000-6-2 (EN61000-4-2, 3, 4, 5, 6, 8, 11)
Emission	EN55032 EN55011 EN61000-3-3 EN61000-6-4
	SPET C LISTED Ind. Cont. Eq. LISTED Ind. Cont. Eq.
RoHS Compliant	Yes
Safety and Protection	
Surge voltage protection against internal surge voltages	No
Isolation voltage:	
Input / output Input / PF	3KVAC 3KVAC
Output / PE	0.5 kVAC
Protection degree	IP20
Safety class	Class I with PE connection

1-800-633-0405 For the latest prices, please check AutomationDirect.com. RHINO PSV24-100S Power Supply











Power Derating Curve for PSU in Vertical Mounting 110 100 90 80 Percentage of Max Load (%) 70 60 50 40 30 20 10 -20 -15 -10 -5 0 5 10 15 20 25 30 35 40 45 50 55 60 65 70 Surrounding Air Temperature (°C) -4 5 14 23 32 41 50 59 68 77 86 95 104 113 122 131 140 149 158 Surrounding Air Temperature (°F) Figure 6

READ INSTRUCTIONS BEFORE INSTALLING OR OPERATING THIS DEVICE. KEEP FOR FUTURE REFERENCE.

1. Safety instructions

- Switch main power off before connecting or disconnecting the device. Risk of explosion!
 To guarantee sufficient convection cooling, please keep a distance of >40mm above and >20mm
 - below the device as well as a lateral distance of >25mm to other cold source or heat source. Note that the enclosure of the device can become very hot depending on the ambient temperature and load of the power supply. Risk of burns!
- The main power must be turned off before connecting or disconnecting wires to the terminals!
- Do not introduce any objects into the unit!
- Dangerous voltage present for at least 5 minutes after disconnecting all sources of power.
- The power supplies are built-in units and must be installed in a cabinet or room (condensation free environment and indoor location) that is relatively free of conductive contaminants.
- The unit must be installed in an IP54 enclosure or cabinet in the final installation.
- CAUTION: FOR USE IN A CONTROLLED ENVIRONMENT.

2. Device description (Fig. 1)

- (1) Input terminal block connector
- (2) Output terminal block connector
- (3) DC voltage adjustment potentiometer
- (4) DC OK LED (green)
- (5) Universal mounting rail system

3. Mounting (Fig. 2)

The power supply unit can be mounted on 35mm DIN rails in accordance with EN60715. The device should be installed with input terminal block on the bottom.

Each device is delivered ready to install.

Snap on the DIN rail as shown in Fig. 2:

- 1. Tilt the unit slightly upwards and put it onto the DIN rail.
- 2. Push downwards until stopped.
- 3. Press against the bottom front side for locking.
- 4. Shake the unit slightly to ensure that it is secured.

4. Dismounting (Fig. 3)

To uninstall, use a flat screwdriver to pull or slide down the latch as shown in Fig. 3. Then slide the PSU in the opposite direction, release the latch and pull out the PSU from the rail.

5. Connection

The terminal block connectors allow easy and fast wiring.

You can use flexible (stranded wire) or solid cables with cross sections:

Electrical Connections and Wire Size					
Stranded / Solid Torque					
	mm ²	AWG	N∙m	lb∙in	
Input	0.32-3.3	22-12	0.51	4.5	
Output	0.52-3.3	20-12	0.51	4.5	

To secure reliable and shock proof connections, the stripping length should be 4-5mm (see Fig. 4 (1)). Please ensure that wires are fully inserted into the connecting terminals as shown in Fig. 4 (2).

In accordance to EN60950 / UL60950, flexible cables require ferrules.

Use appropriate copper cables that are designed to sustain operating temperature of at least $60^{\circ}C/75^{\circ}C$ for USA or at least $90^{\circ}C$ for Canada.

5.1. Input connection (Fig. 1, Fig. 5)

Use L, N and GND connections of input terminal connector (see Fig. 1 (1)) to establish the 100-240 VAC connection. Typical connection methods are shown in Figure 5.

The unit is protected with an internal fuse (not replaceable) at L pin and it has been tested and approved on 20A (UL) and 16A (IEC) branch circuits without additional protection device. An external protection device is only required if the supplying branch has an ampacity greater than above. Thus, if an external protective device is necessary, or utilized, a minimum value of 20A B- or 10A C- characteristic breaker should be used.



5.2. Output connection (Fig. 1 (2))

Use the "+" and "-" screw connections to establish the 24VDC connection. The output provides 24VDC. The output voltage can be adjusted from 22 to 24 VDC on the potentiometer. The green LED DC OK displays correct function of the output (Fig. 1 (4)). The device has a short circuit and overload protection and an overvoltage protection limited to 30-34.8 VDC.

5.3. Output characteristic curve

The device functions normal under operating line and load conditions. In the event of a short circuit or overload the output voltage and current collapses (I_O = 110-150%). The secondary voltage is reduced and bounces until short circuit or overload on the secondary side has been removed.

5.4. Thermal behavior (Fig. 6)

- In the case of ambient temperatures:
 - 1. At -10°C to -20°C [14°F to -4°F], the output capacity has to be reduced by 2% per degree Celsius increase in temperature.
 - Above +55°C [131°F], the output capacity has to be reduced by 3.33% per degree Celsius increase in temperature.

If the output capacity is not reduced when $T_{Amb} > 55^{\circ}C$ [131°F], the device will engage thermal protection by switching off, i.e., the output voltage will go into latch-off mode until the component temperature cools down and the AC power is recycled.

tPWR-127

RHINO PSV24-100S Power Supply

Technical Specifications				
Input (AC)				
Nominal input voltage / frequency	100-240 VAC / 50-60 Hz			
Voltage range	85-264 VAC			
Frequency	47-63 Hz			
Nominal current	< 1.2 A @ 115VAC, < 0.6 A @ 230VAC			
Inrush current limitation (+25°C, cold start)	< 35A @ 115VAC, < 60A @ 230VAC			
Mains huffering at nominal load (two.)	25ms typ. @ 115VAC (100% load)			
	50ms typ. @ 230VAC (100% load)			
Turn-on time	< 3s @ 115VAC, < 1.5 s @ 230VAC (100% load)			
Internal tuse	I 3.15 A / 250V (non-replaceable)			
Recommended backup protection	20A B- or 10A C- characteristic circuit breaker			
Leakage current	< 1mA @ 240VAC			
Output (DC)				
Nominal output voltage U _N / tolerance	24VDC ± 2 %			
Voltage adjustment range	22-24 VDC (maximum power ≤ 91.2 W)			
Nominal current	3.8 A			
Derating	-10°C to -20°C (2%/°C), > 55°C (3.33%/°C) in vertical orientation			
Startup with capacitive loads	Max. 3,000µF			
Max. power dissipation idling / nominal load approx.	0.4 W / 10W			
Efficiency at 100% load	87.0% typ. @ 115VAC, 89.0% typ. @ 230VAC			
PARD (20MHz) at +25°C, 100% load	< 75 mVpp			
Parallel operation	PSB60-REM20S / PSB60-REM40S or with ORing Diode			
General Data				
Type of housing	Plastic (PC), enclosed			
LED signals	Green LED DC OK			
MTBF	> 350,000 hrs. as per Telcordia			
Dimensions (L x W x H)	75mm x 45mm x 100mm [2.95 in x 1.77 in x 3.94 in] (See www.AutomationDirect.com for complete engineering drawings.)			
Weight	0.325 kg [11.5 oz]			
Connection method	Screw connection			
Stripping length	4-5mm [0.16-0.20 in]			
Operating temperature (surrounding air temperature)	-20°C to +70°C [-4°F to +158°F] (Refer to Fig. 6)			
Storage temperature	-40°C to +85°C [-40°F to +185°F]			
Humidity at +25°C, no condensation	5 to 95% RH			
Vibration	Operating: IEC60068-2-6, Sine Wave: 10Hz to 500Hz @ 19.6m/s ² ; displacement of 0.35 mm, 60min per axis for all X, Y, Z directions Non-Operating: IEC60068-2-6, Random: 5Hz to 500Hz (2.09 Grms); 20 min. per axis for all X, Y, Z directions			
Shock	Operating: IEC60068-2-27, Half Sine Wave: 10G for a duration of 11ms, shock for 1 direction (X axis) Non-Operating: IEC60068-2-27, Half Sine Wave: 50G for a duration of 11ms, 3 shocks for each 3 directions			
Pollution degree	2			
Altitude (operating)	2000m			
Certification and Standards				
Safety entry low voltage	SELV (EN60950)			
Electrical safety (of information technology equipment)	UL/C-UL recognized to UL60950-1 and CSA C22.2 No. 60950-1 (File No. E198298), CB scheme to IEC60950-1, Limited Power Source (LPS)			
Industrial control equipment	UL/C-UL listed to UL508 and CSA C22.2 No.107.1-01 (File No. E197592)			
Class 2 power supply	UL/C-UL listed to UL508 and CSA C22.2 No.107.1-01 (File No. E197592)			
CE	In conformance with EMC directive 2014/30/EU and Low Voltage Directive 2014/35/EU			
Component power supply for general use	EN61204-3			
Immunity	EN55024, EN61000-6-1, EN61000-6-2			
Emission	(EN01000-4-2, 3, 4, 3, 0, 0, 11) EN65022 EN65011 EN61000 2.3 EN61000 6.3 EN61000 6.4			
EITIISSIOIT	3PET (2) (2) (2) (2) (2) (2) (2) (2) (2) (2)			
Ce	C C C C S US LISTED E198298			
RoHS Compliant	Υρς			
Safety and Protection	100			
Surge voltage protection against internal surge voltages	Νο			
Isolation voltage:	NU			
Input / output	3kVAC			
Input / PE Output / PE	1.5 kVAC			
Protection degree				
Safety class	Class L with PF connection			
calley slace				

1-800-633-0405 For the latest prices, please check AutomationDirect.com. RHINO PSV24-120S Power Supply













READ INSTRUCTIONS BEFORE INSTALLING OR OPERATING THIS DEVICE. KEEP FOR FUTURE REFERENCE.

1. Safety instructions

- Switch main power off before connecting or disconnecting the device. Risk of explosion!
- If the unit is used in a manner not specified by the manufacturer, the protection provided by the equipment may be impaired.
- To guarantee sufficient convection cooling, please keep a distance of 50mm above and 18cm below the device as well as a lateral distance of 10mm to other units.
- Note that the enclosure of the device can become very hot depending on the ambient
 - temperature and load of the power supply. Risk of burns!
- The main power must be turned off before connecting or disconnecting wires to the terminals!
 Do not introduce any objects into the unit!
- Denot introduce any objects into the unit:
 Dangerous voltage present for at least 5 minutes after disconnecting all sources of power.
- The power supplies are built-in units and must be installed in a cabinet or room (condensation free environment and indoor location) that is relatively free of conductive contaminants.
- The unit must be installed in an IP54 enclosure or cabinet in the final installation.

• CAUTION: FOR USE IN A CONTROLLED ENVIRONMENT.

- 2. Device description (Fig. 1)
 - (1) Input terminal block connector
 - (2) Output terminal block connector
 - (3) DC voltage adjustment potentiometer
 - (4) DC OK LED (green)
 - (5) Universal mounting rail system

3. Mounting (Fig. 2)

The power supply unit can be mounted on 35mm DIN rails in accordance with EN60715. For vertical mounting, the device should be installed with input terminal block on the bottom.

Each device is delivered ready to install.

- Snap on the DIN rail as shown in Fig. 2:
 - 1. Tilt the unit slightly upwards and put it onto the DIN rail.
 - 2. Push downwards until stopped.
 - 3. Press against the bottom front side for locking.
 - 4. Shake the unit slightly to ensure that it is secured.
- 4. Dismounting (Fig. 3)

To uninstall, use a flat screwdriver to pull or slide down the latch as shown in Fig. 3. Then slide the PSU in the opposite direction, release the latch and pull out the PSU from the rail.

5. Connection

The terminal block connectors allow easy and fast wiring.

You can use flexible (stranded wire) or solid cables with cross sections:

Electrical Connections and Wire Size					
	Stranded / Solid Torque				
	mm²	AWG	N∙m	lb•in	
Input	0.823-8.365	18-8	1.01	9	
Output	0.20-3.3	24-12	0.68	6	

To secure reliable and shock proof connections, the stripping length should be 7mm (see Fig. 4 (1)). Please ensure that wires are fully inserted into the connecting terminals as shown in Fig. 4 (2). All wire strands must be fully inserted into the terminals with the screws securely fastened in order to ensure safety and maximum contact.

In accordance to EN60950 / UL60950, flexible cables require ferrules.

Use appropriate copper cables that are designed to sustain operating temperature of at least 60°C/75°C or more to fulfill UL requirements.

5.1. Input connection (Fig. 1, Fig. 5)

Use L, N and GND connections of input terminal connector (see Fig. 1 (1)) to establish the 100-240 VAC connection. Typical connection methods are shown in Figure 5.

The unit is protected with an internal fuse (not replaceable) at L pin and it has been tested and approved on 20A (UL) and 16A (IEC) branch circuits without additional protection device. An external protection device is only required if the supplying branch has an ampacity greater than above.

The internal fuse must not be replaced by the user.

5.2. Output connection (Fig. 1 (2))

Use the "+" and "-" screw connections to establish the 24VDC connection. The output provides 24VDC. The output voltage can be adjusted from 22 to 28 VDC on the potentiometer. The green LED DC OK displays correct function of the output (Fig. 1 (4)). The device has a short circuit and overload protection and an overvoltage protection limited to 28.8-35.2 VDC.

5.3. Output characteristic curve

The device functions normal under operating line and load conditions. In the event of an overload ($I_{o} = 105-150\%$) the output voltage will start to droop until overload has been removed.

5.4. Thermal behavior (Fig. 6)

In the case of ambient temperatures:

- At -10°C to -20°C [14°F to -4°F], the output capacity must be reduced by 2% per °C temperature increase.
 Above +40°C [104°F] (115VAC), the output capacity must be reduced by 1.67% per degree Celsius
- temperature increase. 3. Above +50°C [122°F] (230VAC), the output capacity must be reduced by 2.5% per degree Celsius
- temperature increase.

If the output capacity is not reduced when $T_{Amb} > 40^{\circ}C$ (115VAC) or $> 50^{\circ}C$ (230VAC), the device will engage thermal protection by switching off, i.e., the output voltage will go into latch-off mode until the component temperature cools down and the AC power is recycled.

FOR TECHNICAL ASSISTANCE CALL 770-844-4200

RHINO PSV24-120S Power Supply

Technical Specifications				
Input (AC)				
Nominal input voltage / frequency	100-240 VAC / 50-60 Hz			
Voltage range	85-264 VAC			
Frequency	47-63 Hz			
Nominal current	2.2.A.tvn @ 115VAC 1.2.A.tvn @ 230VAC			
Inrush current limitation (+25°C, cold start)	20A typ @ 115VAC, 40A typ @ 230VAC			
	20ms tvp. @ 115VAC (100% load)			
Mains buffering at nominal load (typ.)	90ms typ. @ 230VAC (100% load)			
Turn-on time	200ms typ. @ 115VAC & 230VAC (100% load)			
Internal fuse	T 4A / 250V (non-replaceable)			
Leakage current	< 0.25 mA @ 264VAC			
Output (DC)				
Nominal output voltage U _N / tolerance	24VDC ± 2 %			
Voltage adjustment range	22-28 VDC (maximum power ≤ 120W)			
Output current	5A			
Derating	Refer to Fig. 6 -10°C to -20°C (2%/°C), > 40°C (1.67%/°C) @ 115VAC -10°C to -20°C (2%/°C), > 50°C (2.5%/°C) @ 230VAC			
Startup with capacitive loads	Max. 8,000µF			
Max. power dissipation idling / nominal load approx.	0.65 W / 13.3 W			
Efficiency at 100% load	88.0% typ. @ 115VAC, 90.0% typ. @ 230VAC			
PARD (20MHz) at 100% load	< 120 mVpp			
Parallel operation	PSB60-REM20S / PSB60-REM40S or with ORing Diode			
General Data				
Type of housing	SGCC (Case Cover) / Aluminum (Case Chassis)			
LED signals	Green LED DC OK			
MTBF	> 700.000 hrs. as per Telcordia			
Dimensions (L x W x H)	123.6 mm x 40mm x 117.6 mm [4.87 in x 1.57 in x 4.63 in] (See www.AutomationDirect.com for complete engineering drawings.)			
Weight	0.54 kg [19 oz]			
Connection method	Screw connection			
Stripping length	7mm [0.28 in]			
Operating temperature (surrounding air temperature)	-20°C to ±70°C [-4°E to ±158°E] (Refer to Eig. 6)			
Storage temperature	-40°C to ±85°C [-40°E to ±185°F]			
Humidity at +25°C, no condensation	5 to 95% BH			
	Operating: IEC60068-2-6. Sine Wave: 10Hz to 500Hz @ 19.6m/s ² (2G peak): 10min per cycle. 60min for X direction			
	Non-Öperating: IEC60068-2-6, Random: 5Hz to 500Hz (2.09 Grms); 20 min. per axis for all X, Y, Z directions Operating: IEC60068-2-27, Half Sine Wave: 10G for a duration of 11ms, shock for 1 direction (X axis)			
Shock	Non-Operating: IEC60068-2-27, Half Sine Wave: 50G for a duration of 11ms, 3 shocks for each 3 directions			
Pollution degree	2			
Altitude (operating)	2000m for industrial application			
Cortification and Standarda	5000m for TLE application			
Cefety entry low voltage				
Salety entry tow voltage	SELV (EIV00930)			
	UL/G-UL Tecugritized to ULC0930-1 and CSA C22.2 No. 00330-1 (File No. E130230), CD Scheme to Ecologado-1			
	UL/U-UL IISteu to ULSU8 and USA UZZZ NU. 107. 1-01 (File NO. E 197592)			
	III contormance with ENIC directive 2014/30/EU and Low Voltage Directive 2014/35/EU			
Component power supply for general use	EN51204-3 EN55024 EN61000.6.1 EN61000.6.2			
Immunity	(EN61000-4-2, 3, 4, 5, 6, 8, 11, 12)			
Emission	EN55032, EN55011, EN61000-3-2 Class A, EN61000-3-3, EN61000-6-3, EN61000-6-4			
Voltage Sag Immunity	SEMI F47 – 0706 @ 200VAC			
Ce	4ZW4 c US LISTED Ind. Cont, Eq. LISTED			
RoHS Compliant	Yes			
Safety and Protection				
Transient surge voltage protection	Varistor			
Current limitation at short-circuits approx.	I _{surce} = 105-150% or Po _{max} typically			
Surge voltage protection against internal surge voltages	Yes			
Isolation voltage: Input / output	3kVAC			
Input / PE	2KVAC			
Protection degree	IP20			
Safaty class	Class L with DE connection			
Jaicly Ulass				

RHINO PSV24-240S Power Supply













READ INSTRUCTIONS BEFORE INSTALLING OR OPERATING THIS DEVICE. KEEP FOR FUTURE REFERENCE.

1. Safety instructions

- Switch main power off before connecting or disconnecting the device. Risk of explosion!
- If the unit is used in a manner not specified by the manufacturer, the protection provided by the
 equipment may be impaired.
- To guarantee sufficient convection cooling, please keep a distance of 50mm above and 18cm
- below the device as well as a lateral distance of 10mm to other units.Note that the enclosure of the device can become very hot depending on the ambient
- temperature and load of the power supply. Risk of burns!
- The main power must be turned off before connecting or disconnecting wires to the terminals!
 Do not introduce any objects into the unit!
- Dangerous voltage present for at least 5 minutes after disconnecting all sources of power.
- The power supplies are built-in units and must be installed in a cabinet or room (condensation
 - free environment and indoor location) that is relatively free of conductive contaminants.
- The unit must be installed in an IP54 enclosure or cabinet in the final installation.
 CAUTION: FOR USE IN A CONTROLLED ENVIRONMENT.

2. Device description (Fig. 1)

- (1) Input terminal block connector
- (2) Output terminal block connector
- (3) DC voltage adjustment potentiometer
- (4) DC OK LED (green)
- (5) Universal mounting rail system
- 3. Mounting (Fig. 2)

The power supply unit can be mounted on 35mm DIN rails in accordance with EN60715. For vertical mounting, the device should be installed with input terminal block on the bottom.

Each device is delivered ready to install.

- Snap on the DIN rail as shown in Fig. 2:
 - 1. Tilt the unit slightly upwards and put it onto the DIN rail.
 - 2. Push downwards until stopped.
 - 3. Press against the bottom front side for locking.
 - 4. Shake the unit slightly to ensure that it is secured.

4. Dismounting (Fig. 3)

To uninstall, use a flat screwdriver to pull or slide down the latch as shown in Fig. 3. Then slide the PSU in the opposite direction, release the latch and pull out the PSU from the rail.

5. Connection

The terminal block connectors allow easy and fast wiring.

You can use flexible (stranded wire) or solid cables with cross sections:

Electrical Connections and Wire Size				
	Stranded / Solid Torque			
	mm ² AV		N∙m	lb•in
Input	1.3-3.3	16-12	1.01	9
Output	1.3-3.3	16-12	0.68	6

To secure reliable and shock proof connections, the stripping length should be 7mm (see Fig. 4 (1)). Please ensure that wires are fully inserted into the connecting terminals as shown in Fig. 4 (2). All wire strands must be fully inserted into the terminals with the screws securely fastened in order to ensure safety and maximum contact.

In accordance to EN60950 / UL60950, flexible cables require ferrules.

Use appropriate copper cables that are designed to sustain operating temperature of at least 60° C/75 $^{\circ}$ C or more to fulfill UL requirements.

5.1. Input connection (Fig. 1, Fig. 5)

Use L, N and GND connections of input terminal connector (see Fig. 1 (1)) to establish the 100-240 VAC connection. Typical connection methods are shown in Figure 5.

The unit is protected with an internal fuse (not replaceable) at L pin and it has been tested and approved on 20A (UL) and 16A (IEC) branch circuits without additional protection device. An external protection device is only required if the supplying branch has an ampacity greater than above.

The internal fuse must not be replaced by the user.

5.2. Output connection (Fig. 1 (2))

Use the "+" and "-" screw connections to establish the 24VDC connection. The output provides 24VDC. The output voltage can be adjusted from 22 to 28 VDC on the potentiometer. The green LED DC OK displays correct function of the output (Fig. 1 (4)). The device has a short circuit and overload protection and an overvoltage protection limited to 28.8-35.2 VDC.

5.3. Output characteristic curve

The device functions normal under operating line and load conditions. In the event of an overload ($I_{O} = 105-150\%$) the output voltage will start to droop until overload has been removed.

5.4. Thermal behavior (Fig. 6)

- In the case of ambient temperatures:
 - Above +40°C [104°F] (115VAC), the output capacity has to be reduced by 1.67% per degree Celsius increase in temperature.
 - Above +50°C [122°F] (230VAC), the output capacity has to be reduced by 2.5% per degree Celsius increase in temperature.

If the output capacity is not reduced when $T_{Amb} > 40^{\circ}C$ [104°F] (115VAC) or $> 50^{\circ}C$ [122°F] (230VAC), the device will engage thermal protection by switching off, i.e., the output voltage will go into latch-off mode until the component temperature cools down and the AC power is recycled.

FOR TECHNICAL ASSISTANCE CALL 770-844-4200

www.automationdirect.com

Power Supplies

tPWR-131

RHINO PSV24-240S Power Supply

	Technical Specifications
Input (AC)	
Nominal input voltage / frequency	100-240 VAC / 50-60 Hz
Voltage range	85-264 VAC
Frequency	47-63 Hz
Nominal current	2.8 A typ. @ 115VAC, 1.4 A typ. @ 230VAC
Inrush current limitation (+25°C, cold start)	20A typ. @ 115VAC, 40A typ. @ 230VAC
Mains buffering at nominal load (typ.)	10ms typ. @ 115VAC (100% load)
	16ms typ. @ 230VAC (100% load)
Turn-on time	
Internal fuse	I 6.3 A / 25UV (NON-replaceable)
	< 1111A @ 204VAL
Nominal output voltage U _N / tolerance	24VUC ± 2 %
Voltage adjustment range	22-28 VDC (maximum power ≤ 240W)
	IUA Defer to Fig. 6
Derating	> 40°C (1.67%/°C) @ 115VAC (90-229 VAC)
	> 50°C (2.5%/°C) @ 230VAC (230-264 VAC)
Startup with capacitive loads	Max. 8,000µF
	4.62 W @ 115VAC (0% load)
Max. power dissipation idling / nominal load approx.	2.14 W @ 2007A0 (0.70 load)
a prostantina (3, 1, 1, 1, 1, 1, 1, 1, 1, 1, 1, 1, 1, 1,	31.53 W @ 115VAC (100% load)
F#isissay at 100% load	25.44 W @ 230VAC (100% load)
Efficiency at 100% load	
PARD (20MHz) at 100% load	< 12011/pp @ -10 C to +70 C < 240mVpp @ -20°C to -10°C
Parallel operation	PSB60-REM20S / PSB60-REM40S or with ORing Diode
General Data	
Type of housing	SGCC (Case Cover) / Aluminum (Case Chassis)
LED signals	Green LED DC OK
MTBF	> 700,000 hrs. as per Telcordia
Dimensions (L x W x H)	123.6 mm x 60mm x 117.6 mm [4.87 in x 2.36 in x 4.63 in] (See www.AutomationDirect.com for complete engineering drawings.)
Weight	0.80 kg [28 oz]
Connection method	Screw connection
Stripping length	7mm [0.28 in]
Operating temperature (surrounding air temperature)	-20°C to +70°C [-4°F to +158°F] (Refer to Fig. 6)
Storage temperature	-40°C to +85°C [-40°F to +185°F]
Humidity at +25°C, no condensation	5 to 95% RH
Vibration	Operating: IEC60068-2-6, Sine Wave: 10Hz to 500Hz @ 19.6m/s ² (2G peak); 10min per cycle, 60min for X direction
	Non-Operating: IEC60068-2-6, Random: 5Hz to 500Hz (2.09 Grms); 20 min. per axis for all X, Y, Z directions
Shock	Non-Operating: IEC60068-2-27, Half Sine Wave: 50G for a duration of 11ms, shock for Follection (A axis)
Pollution degree	2
Altitude (operating)	2000m for industrial application
	5000m for ITE application
Certification and Standards	
Safety entry low voltage	SELV (EN60950)
Electrical safety (of information technology equipment)	UL/C-UL recognized to UL60950-1 and CSA C22.2 No. 60950-1 (File No. E198298), CB scheme to IEC60950-1
	UL/C-UL IIsted to ULSU8 and USA C22.2 No. 107.1-01 (File No. E 197592)
	In conformance with EMU directive 2014/30/EU and Low Voltage Directive 2014/35/EU
Component power supply for general use	EN61204-3
Immunity	(EN61000-4-2, 3, 4, 5, 6, 8, 11, 12)
Emission	EN55032, EN55011, EN61000-3-2 Class A, EN61000-3-3, EN61000-6-3, EN61000-6-4
Voltage Sag Immunity	SEMI F47 – 0706 @ 200VAC
ſ	
	LISTED E198298
Dello Osmaliast	
Reference Protection	Yes
	The same
Current limitation at abort airquite sector	Varistor
Current imitation at snort-circuits approx.	Isurge = 100-100% OF PO _{max} typically
Surge voltage protection against internal surge voltages	Yes
Input / output	3kVAC
Input / PE	2kVAC
Output / PE	0.5 KVAC
Protection degree	IP20
Safety class	Class I with PE connection
IST Edition, 01/2019	

www.automationdirect.com

RHINO PSV24-480S Power Supply













READ INSTRUCTIONS BEFORE INSTALLING OR OPERATING THIS DEVICE. KEEP FOR FUTURE REFERENCE.

1. Safety instructions

- Switch main power off before connecting or disconnecting the device. Risk of explosion!
- If the unit is used in a manner not specified by the manufacturer, the protection provided by the
 equipment may be impaired.
- To guarantee sufficient convection cooling, please keep a distance of 50mm above and 18cm below the device as well as a lateral distance of 10mm to other units.
- Note that the enclosure of the device can become very hot depending on the ambient temperature and load of the power supply. Risk of burns!
- The main power must be turned off before connecting or disconnecting wires to the terminals!
 Do not introduce any objects into the unit!
- Dangerous voltage present for at least 5 minutes after disconnecting all sources of power.
- The power supplies are built-in units and must be installed in a cabinet or room (condensation
 - free environment and indoor location) that is relatively free of conductive contaminants.
- The unit must be installed in an IP54 enclosure or cabinet in the final installation.
- CAUTION: FOR USE IN A CONTROLLED ENVIRONMENT.
- 2. Device description (Fig. 1)
 - (1) Input terminal block connector
 - (2) Output terminal block connector
 - (3) DC voltage adjustment potentiometer
 - (4) DC OK LED (green)
 - (5) Universal mounting rail system

3. Mounting (Fig. 2)

The power supply unit can be mounted on 35mm DIN rails in accordance with EN60715. For vertical mounting, the device should be installed with input terminal block on the bottom.

Each device is delivered ready to install.

- Snap on the DIN rail as shown in Fig. 2:
 - 1. Tilt the unit slightly upwards and put it onto the DIN rail.
 - 2. Push downwards until stopped.
 - 3. Press against the bottom front side for locking.
 - 4. Shake the unit slightly to ensure that it is secured.

4. Dismounting (Fig. 3)

To uninstall, use a flat screwdriver to pull or slide down the latch as shown in Fig. 3. Then slide the PSU in the opposite direction, release the latch and pull out the PSU from the rail.

5. Connection

The terminal block connectors allow easy and fast wiring.

You can use flexible (stranded wire) or solid cables with cross sections:

Electrical Connections and Wire Size					
	Stranded / Solid Torque				
	mm²	AWG	N∙m	lb•in	
Input	1.3-3.3	16-12	1.01	9	
Output	1.3-3.3	16-12	0.68	6	

To secure reliable and shock proof connections, the stripping length should be 7mm (see Fig. 4 (1)). Please ensure that wires are fully inserted into the connecting terminals as shown in Fig. 4 (2). All wire strands must be fully inserted into the terminals with the screws securely fastened in order to ensure safety and maximum contact.

In accordance to EN60950 / UL60950, flexible cables require ferrules.

Use appropriate copper cables that are designed to sustain operating temperature of at least $60^{\circ}C/75^{\circ}C$ or more to fulfill UL requirements.

5.1. Input connection (Fig. 1, Fig. 5)

Use L, N and GND connections of input terminal connector (see Fig. 1 (1)) to establish the 100-240 VAC connection. Typical connection methods are shown in Figure 5.

The unit is protected with an internal fuse (not replaceable) at L pin and it has been tested and approved on 20A (UL) and 16A (IEC) branch circuits without additional protection device. An external protection device is only required if the supplying branch has an ampacity greater than above.

The internal fuse must not be replaced by the user.

5.2. Output connection (Fig. 1 (2))

Use the "+" and "-" screw connections to establish the 24VDC connection. The output provides 24VDC. The output voltage can be adjusted from 22 to 28 VDC on the potentiometer. The green LED DC OK displays correct function of the output (Fig. 1 (4)). The device has a short circuit and overload protection and an overvoltage protection limited to 28.8-35.2 VDC.

5.3. Output characteristic curve

The device functions normal under operating line and load conditions. In the event of an overload ($I_{\rm O}$ = 109-130%) the output voltage will start to droop until overload has been removed.

5.4. Thermal behavior (Fig. 6)

- In the case of ambient temperatures:
 - 1. Above +40°C [104°F] (115VAC), the output capacity has to be reduced by 1.67% per degree Celsius increase in temperature.
 - Above +50°C [122°F] (230VAC), the output capacity has to be reduced by 2.5% per degree Celsius increase in temperature.

If the output capacity is not reduced when $T_{Amb} > 40^{\circ}C [104^{\circ}F]$ (115VAC) or $> 50^{\circ}C [122^{\circ}F]$ (230VAC), the device will engage thermal protection by switching off, i.e., the output voltage will go into latch-off mode until the component temperature cools down and the AC power is recycled.

FOR TECHNICAL ASSISTANCE CALL 770-844-4200

RHINO PSV24-480S Power Supply

	Technical Specifications
Input (AC)	
Nominal input voltage / frequency	100-240 VAC / 50-60 Hz
Voltage range	85-264 VAC
Frequency	47-63 Hz
Nominal current	5.4 A typ. @ 115VAC, 2.7 A typ. @ 230VAC
Inrush current limitation (+25°C, cold start)	40A typ. @ 115VAC, 80A typ. @ 230VAC
Mains buffering at nominal load (typ.)	10ms typ. @ 115VAC (100% load)
	16ms typ. @ 230VAC (100% load)
Turn-on time	1000ms typ. @ 115VAC & 230VAC (100% load)
Internal fuse	FIU A / 25UV (non-replaceable)
Leakage current	< IMA @ 264VAC
Output (DC)	
Nominal output voltage U _N / tolerance	24VDC ± 2 %
Voltage adjustment range	22-28 VDC (maximum power ≤ 480W)
Output current	20A Defente Fin C
Derating	×60°C (1.67%/°C) @ 115VAC (90-229 VAC) > 50°C (2.5%/°C) @ 230VAC (230-264 VAC)
Startup with capacitive loads	Max. 8,000µF
	5W @ 115VAC (0% load)
Max nower dissipation idling / nominal load approx	4W @ 230VAC (0% load)
wax. power desipation raining / norminal road approx.	50W @ 115VAC (100% load)
Efficiency at 1000/ load	40W @ 230VAC (100% load)
Eniciency at 100% load	65.0% (y)D. @ 115VAL, 68.0% (y)D. @ 230VAL
PARD (20MHz) at 100% load	< 240mVpp @ -20°C to -10°C
Parallel operation	PSB60-REM40S or with ORing Diode
General Data	
Type of housing	SGCC (Case Cover) / Aluminum (Case Chassis)
I ED signals	Green LED DC OK
MTBF	> 700.000 hrs. as per Telcordia
Dimensions (L x W x H)	123.6 mm x 85.5 mm x 128.5 mm [4.87 in x 3.37 in x 5.06 in] (See www.AutomationDirect.com for complete engineering drawings.)
Weight	1.30 km [45.9 nz]
Connection method	Screw connection
Strinning length	7mm [0 28 in]
Operating temperature (surrounding air temperature)	-20°C to ±70°C [-4°E to ±158°F] (Befer to Fig. 6)
Storage temperature	40°C to 18°C [40°E to 19°C [
	5 to 05 00 PH
	Operation: IEC60068-2-6. Sine Wave: 10Hz to 500Hz @ 19 6m/s² (2G neak): 10min per cycle. 60min for X direction
Vibration	Non-Operating: IEC60068-2-6, Random: 5Hz to 500Hz (2.09 Grms); 20 min. per axis for all X, Y, Z directions Operating: IEC60068-2-27, Half Sine Wave: 10G for a duration of 11ms, shock for 1 direction (X axis)
	Non-Operating: IEC60068-2-27, Half Sine Wave: 50G for a duration of 11ms, 3 shocks for each 3 directions
Pollution degree	2
Altitude (operating)	2000m for industrial application
Certification and Standards	
Safety entry low voltage	SELV (EN60950)
Electrical safety (of information technology equipment)	UL/C-UL recognized to UL 60950-1 and CSA C22.2 No. 60950-1 (File No. E198298). CB scheme to IEC60950-1
Industrial control equipment	UL/C-UL listed to UL508 and CSA C22.2 No.107.1-01 (File No. F197592)
CE	In conformance with EMC directive 2014/30/EU and Low Voltage Directive 2014/35/EU
Component power supply for general use	EN61204-3
Immunity	EN55024, EN61000-6-1, EN61000-6-2
	(EN61000-4-2, 3, 4, 5, 6, 8, 11, 12)
Emission	EN55032, EN55011, EN61000-3-2 Class A, EN61000-3-3, EN61000-6-3, EN61000-6-4
Voltage Sag Immunity	SEMI F47 – 0706 @ 200VAC
C	E C LISTED Ind. Cont. Eq.
RoHS Compliant	Yes
Safety and Protection	
Transient surge voltage protection	Varistor
Current limitation at short-circuits approx.	I _{surge} = 109-130% or Po _{max} typically (continuous current)
Surge voltage protection against internal surge voltages	Yes
Isolation voltage: Input / output Input / PE Output / PE	3kVAC 2kVAC 05 kVAC
Output / PE	U.5 KVAU
Protection degree	1820 1872 - 1975 - 1975 - 1975 - 1975 - 1975 - 1975 - 1975 - 1975 - 1975 - 1975 - 1975 - 1975 - 1975 - 1975 - 1975 -
Safety class	Class I with PE connection

RHINO PSV48-120S Power Supply













READ INSTRUCTIONS BEFORE INSTALLING OR OPERATING THIS DEVICE. KEEP FOR FUTURE REFERENCE.

1. Safety instructions

- Switch main power off before connecting or disconnecting the device. Risk of explosion!
- If the unit is used in a manner not specified by the manufacturer, the protection provided by the
 equipment may be impaired.
- To guarantee sufficient convection cooling, please keep a distance of 50mm above and 18cm below the device as well as a lateral distance of 10mm to other units.
- Note that the enclosure of the device can become very hot depending on the ambient temperature and load of the power supply. Risk of burns!
- The main power must be turned off before connecting or disconnecting wires to the terminals!
 Do not introduce any objects into the unit!
- Dangerous voltage present for at least 5 minutes after disconnecting all sources of power.
- The power supplies are built-in units and must be installed in a cabinet or room (condensation
 - free environment and indoor location) that is relatively free of conductive contaminants.
- The unit must be installed in an IP54 enclosure or cabinet in the final installation.
- CAUTION: FOR USE IN A CONTROLLED ENVIRONMENT.

2. Device description (Fig. 1)

- (1) Input terminal block connector
- (2) Output terminal block connector
- (3) DC voltage adjustment potentiometer
- (4) DC OK LED (green)
- (5) Universal mounting rail system

3. Mounting (Fig. 2)

The power supply unit can be mounted on 35mm DIN rails in accordance with EN60715. For vertical mounting, the device should be installed with input terminal block on the bottom.

Each device is delivered ready to install.

- Snap on the DIN rail as shown in Fig. 2:
 - 1. Tilt the unit slightly upwards and put it onto the DIN rail.
 - 2. Push downwards until stopped.
 - 3. Press against the bottom front side for locking.
 - 4. Shake the unit slightly to ensure that it is secured.

4. Dismounting (Fig. 3)

To uninstall, use a flat screwdriver to pull or slide down the latch as shown in Fig. 3. Then slide the PSU in the opposite direction, release the latch and pull out the PSU from the rail.

5. Connection

The terminal block connectors allow easy and fast wiring.

You can use flexible (stranded wire) or solid cables with cross sections:

Electrical Connections and Wire Size					
	Stranded / Solid Torque				
	mm ²	AWG	N∙m	lb-in	
Input	0.823-8.365	18-8	1.01	9	
Output	0.20-3.3	24-12	0.68	6	

To secure reliable and shock proof connections, the stripping length should be 7mm (see Fig. 4 (1)). Please ensure that wires are fully inserted into the connecting terminals as shown in Fig. 4 (2). All wire strands must be fully inserted into the terminals with the screws securely fastened in order to ensure safety and maximum contact.

In accordance to EN60950 / UL60950, flexible cables require ferrules.

Use appropriate copper cables that are designed to sustain operating temperature of at least $60^{\circ}C/75^{\circ}C$ or more to fulfill UL requirements.

5.1. Input connection (Fig. 1, Fig. 5)

Use L, N and GND connections of input terminal connector (see Fig. 1 (1)) to establish the 100-240 VAC connection. Typical connection methods are shown in Figure 5.

The unit is protected with an internal fuse (not replaceable) at L pin and it has been tested and approved on 20A (UL) and 16A (IEC) branch circuits without additional protection device. An external protection device is only required if the supplying branch has an ampacity greater than above.

The internal fuse must not be replaced by the user.

5.2. Output connection (Fig. 1 (2))

Use the "+" and "-" screw connections to establish the 48 VDC connection. The output provides 48 VDC. The output voltage can be adjusted from 44 to 56 VDC on the potentiometer. The green LED DC OK displays correct function of the output (Fig. 1 (4)). The device has a short circuit and overload protection and an overvoltage protection limited to 56-67.2 VDC.

5.3. Output characteristic curve

The device functions normal under operating line and load conditions. In the event of an overload (I_{c} = 105-150%) the output voltage will start to droop until overload has been removed.

5.4. Thermal behavior (Fig. 6)

In the case of ambient temperatures:

- At -10°C to -20°C [14°F to -4°F], the output capacity has to be reduced by 2% per degree Celsius increase in temperature.
- Above +40°C [104°F] (115VAC), the output capacity has to be reduced by 1.67% per degree Celsius increase in temperature.
- Above +50°C [122°F] (230VAC), the output capacity has to be reduced by 2.5% per degree Celsius increase in temperature.

If the output capacity is not reduced when $T_{Amb} > 40^{\circ}C$ [104°F] (115VAC) or > 50°C [122°F] (230VAC), the device will engage thermal protection by switching off, i.e., the output voltage will go into latch-off mode until the component temperature cools down and the AC power is recycled.

FOR TECHNICAL ASSISTANCE CALL 770-844-4200

www.automationdirect.com



For the latest prices, please check AutomationDirect.com.

RHINO PSV48-120S Power Supply

Technical Specifications					
Input (AC)					
Nominal input voltage / frequency	100-240 VAC / 50-60 Hz				
Voltage range	85-264 VAC				
Frequency	47-63 Hz				
Nominal current	2.2 A typ. @ 115VAC, 1.2 A typ. @ 230VAC				
Inrush current limitation (+25°C, cold start)	20A typ. @ 115VAC, 40A typ. @ 230VAC				
Mains buffering at nominal load (typ.)	20ms typ. @ 115VAC (100% load)				
	901115 typ. @ 230VAC (100% 1040) 200me typ. @ 1151/AC & 2301/AC (100% 1040)				
	T 4Δ / 250V/ (non-renlaceable)				
	2.0.25 mA @ 264VAC				
Nominal output voltage LL. / tolerance	48VDC + 2 %				
Voltage adjustment range	44-56 VDC (maximum power < 120W)				
Output current	25 A				
	Refer to Fig. 6				
Derating	-10°C to -20°C (2%/°C), > 40°Č (1.67%/°C) @ 115VAC -10°C to -20°C (2%/°C) > 50°C (2.5%/°C) @ 230VAC				
Startup with capacitive loads	Max. 4.000uF				
Max, power dissipation idling / nominal load approx.	1.21 W / 13.3 W				
Efficiency at 100% load	89.0% typ. @ 115VAC. 90.0% typ. @ 230VAC				
PARD (20MHz) at 100% load	<150 mVpp				
Parallel operation	PSB60-REM20S / PSB60-REM40S or with ORing Diode				
General Data					
Type of housing	SGCC (Case Cover) / Aluminum (Case Chassis)				
LED signals	Green LED DC OK				
MTBF	> 700,000 hrs. as per Telcordia				
Dimensions (L x W x H)	123.6 mm x 40mm x 117.6 mm [4.87 in x 1.57 in x 4.63 in] (See www.AutomationDirect.com for complete engineering drawings.)				
Weight	0.54 kg [19 oz]				
Connection method	Screw connection				
Stripping length	7mm [0.28 in]				
Operating temperature (surrounding air temperature)	-20°C to +70°C [-4°F to +158°F] (Refer to Fig. 6)				
Storage temperature	-40°C to +85°C [-40°F to +185°F]				
Humidity at +25°C, no condensation	5 to 95% RH				
Vibration	Operating: IEC60068-2-6, Sine Wave: 10Hz to 500Hz @ 19.6m/s ² (2G peak); 10min per cycle, 60min for X direction Non-Operating: IEC60068-2-6, Random: 5Hz to 500Hz (2.09 Grms); 20 min. per axis for all X, Y, Z directions				
Shock	Operating: IEC60068-2-27, Half Sine Wave: 10G for a duration of 11ms, shock for 1 direction (X axis) Non-Operating: IEC60068-2-27, Half Sine Wave: 50G for a duration of 11ms, 3 shocks for each 3 directions				
Pollution degree	2				
Altitude (operating)	2000m for industrial application				
Certification and Standards					
Safety entry low voltage	SELV (EN60950)				
Electrical safety (of information technology equipment)	UL/C-UL recognized to UL60950-1 and CSA C22.2 No. 60950-1 (File No. E198298), CB scheme to IEC60950-1				
Industrial control equipment	UL/C-UL listed to UL508 and CSA C22.2 No.107.1-01 (File No. E197592)				
CE	In conformance with EMC directive 2014/30/EU and Low Voltage Directive 2014/35/EU				
Component power supply for general use	EN61204-3				
Immunity	EN55024, EN61000-6-1, EN61000-6-2				
Emission	(EN61000-4-2, 3, 4, 5, 6, 8, 11, 12)				
ETTIISSIOT	ENODU32, ENODUTT, ENOTUDU-3-2 CI3SS A, ENOTUDU-3-3, ENOTUDU-6-3, ENOTUDU-6-4				
Voltage Sag Initiality					
	Ind. Cont. Eq.				
RoHS Compliant	Yes				
Safety and Protection					
Transient surge voltage protection	Varistor				
Current limitation at short-circuits approx.	I _{surge} = 105-150% or Po _{max} typically				
Surge voltage protection against internal surge voltages	Yes				
Isolation voltage:					
Input / output Input / PE	3KVAU 2KVAC				
Output / PE	0.5 kVAC				
Protection degree	IP20				
Safety class	Class I with PE connection				

1-800-633-0405 **RHINO Battery Control Modules Overview**

A battery control module (BCM), in combination with an external sealed lead acid battery, can be added to a DC power supply to create a DC uninterruptible power supply (UPS) that will maintain power to a connected load upon loss of mains power.

The battery control module performs several key functions in the DC UPS system. Under normal conditions, it monitors the status of the DC input power, monitors and controls charging of the external lead acid battery, and provides status/alarm contacts to allow remote monitoring of the state of the UPS.

In the event that the DC power supply voltage drops out, the BCM monitors and supplies power to the load from the battery and monitors the battery during discharge.

Several battery control modules, with a range of features, are available for use with RHINO power supplies. Key differentiating features of the battery control modules are delineated in the following table.

Battery Control Module Selection Guide						
Part Number	<u>PSH-BCM360S</u>	PSB24-BCM960S	<u>PSL-24-BCM240</u>	PSM24-BCM360S		
Price	\$290.00	\$73.00	\$38.00	\$235.00		
Drawing Link	PDF	PDF	PDF	PDF		
Highlights	Most versatile	Highest power Lowest cost/watt Conformal coating	Lowest cost	Legacy		
Nominal Output Voltage	24/48 VDC 24 VDC 24 VDC 24 VDC 24		24 VDC			
Amperage Rating	15A at 24 VDC, 7.5 A at 48 VDC	40A	10A	15A		
Number of Power Inputs	Imber of Power Redundant inputs for two puts independent power supplies		One power supply	One power supply		
Battery Type	e 12V sealed lead acid 24V sealed lead acid 24V sealed lead acid 24V		24V sealed lead acid			
Protection Type	Over voltage, Over current, Deep discharge, Reverse polarity, Battery overcharge, Over temperature					
Battery Temperature Compensation	Yes	No	No	Yes		
Compatibility	Universal Universal Universal Requires RH		Requires RHINO PSM24 power supply			









RHINO BATTERY CONTROL MODULE PSH-BCM360S

Safety Instructions

- Read these instructions carefully and completely before installation.
- These instructions cannot account for every possible condition of installation, operation or maintenance. The equipment must be installed and put into service by qualified personnel only.
- Before any installation, maintenance or modification work ensure that the main switch is switched off and prevented from being switched on again. Non-observance, touching of any live components or improper handling of this power supply can result in death, severe personal injury or substantial property damage. Proper and safe operation is dependent on proper storage, handling, installation and operation.
- Compliance with the relevant national and local regulations must be ensured. Before operation is started the following conditions must be ensured:
 - When stranded wires are used, all strands must be fastened in the terminal blocks. (Potential danger of contact with the case.)
 - Power supply and mains cables must be sufficiently fused.
 - All output wires must be rated for the equipment output current and must be connected with the correct polarity.
 - Sufficient cooling must be ensured.
- *Never work on the equipment if power is supplied!* Risk of electric arcs and electrical shock, which can cause death, severe personal injury or substantial property damage.
- **Warning:** Hazardous voltages and components storing a very substantial amount of energy are present in this power supply during normal operating conditions. However, these are inaccessible. Improper handling may result in an electric shock or serious burns!
- Do not open the equipment.
- · Do not introduce any objects into the equipment.
- Adjustment potentiometer(s) may only be actuated using an insulated screwdriver.
- Keep away from fire and water.

Recycling

The unit contains elements that are suitable for recycling, and components that need special disposal. You are therefore requested to make sure that the power supply will be recycled in an environmentally friendly manner at the end of its service life.



Features

- Universal battery controller module for interruptible 24VDC and 48VDC bus voltage
- Redundant inputs for two independent sources
- Battery protection for over voltage, deep discharge, short circuit and reverse connection
- Alarm outputs for input, output and battery condition
- Remote On/Off for battery
- Controlled end of charge voltage by optional temperature sensor

General Description

The PSH-BCM360S module provides a professional battery management system to charge and monitor an external 12V leadacid battery with a capacity greater than 2.5 Ah. This module is a standalone unit and is designed to function with any 24VDC or 48VDC power supply output regulated to 1% or better. Together with one or a pair of 24VDC or 48VDC power supplies a perfect DC-UPS system can be configured.

The load voltage is configured through the means of a jumper on the unit with selectable 24VDC or 48VDC voltage levels. No other signals are required between the PSH-BCM360S and the connected power supplies for correct operation of the module.

The connected battery will be charged and held in charged mode by the power supply. In the event of a mains power failure the battery will supply output power without interruption.

A step up converter is used to maintain the selected output voltage level, Vnom – 6% (typical). To avoid overcharging the battery, an optional external temperature sensor can be used to adjust the battery voltage automatically to the required end-ofcharge voltage. This can extend the battery life.

The battery is protected against deep discharge. Mains power and battery status are monitored regularly and failures indicated by corresponding LEDs and alarm outputs.

The module also offers the unique feature of redundant inputs as well as the battery backup. Redundancy is achieved by two internal decoupling diodes which allow operation with two independent voltage sources in order to increase the reliability of the output even further.

FOR TECHNICAL ASSISTANCE CALL 770-844-4200

Mechanical Installation

This equipment is designed for professional indoor systems. In operation the equipment must not be accessible.

The correct mounting position for optimal cooling performance must be observed. Mount the equipment upright on horizontal DIN rail. Do not cover any ventilation holes. Leave a free space of minimum 80mm [3.15 in] above and below the power supply and on each side of the power supply leave a minimum space of 25mm [0.98 in] which allows air convection. Observe power derating.

To attach the module to the DIN rail, hook top part of clip on the DIN rail, then push down and inward until you hear a clicking sound. To remove the device, pull the latch of the clip using an insulated flathead screwdriver. When the clip has cleared the bottom of the DIN rail remove the screwdriver from recess. Lift the device off the DIN rail.

Electrical Installation

Only qualified personnel should carry out the installation. Following correct mounting of both the power supply and the BCM, the following steps must be followed to ensure correct connection and commissioning of the system.

- 1. Make sure the mains power is switched off, secured against switch on and not yet connected to the power supply.
- 2. Connect the power supply output to DC input of the BCM.
- 3. Ensure the blade fuse is correctly inserted into the BCM.
- 4. Configure the BCM module for your power supply voltage by choosing the jumper position J6 (see Figure 1).
- 5. Exercising caution, the AC power wires should now be connected to the power supply. Ensure that AC power is disabled by external isolation switch or circuit breaker.
- 6. When AC supply connection wires are connected and safe isolation is verified, AC power can now be switched on.
- 7. The potentiometer on the BCM is set by the factory to suit the recommended valve regulated lead acid battery from Panasonic and equivalent types and should not be adjusted by the user, unless lead acid batteries of different voltage temperature characteristics are connected. If a non recommended battery is used, the output voltage of the BCM module needs to be adjusted to the correct "End of Charge Voltage" obtained from battery manufacturer. Refer to the Battery Remote On/Off section to disconnect the battery, and set the required voltage using the potentiometer and a voltmeter.
- 8. If used, the temperature sensor should now be fixed to the battery and connected to the TS input on the BCM (Figure 2).
- 9. The battery wires should be connected on the BCM module; DO NOT connect to the battery first.
- 10. Then connect the battery wires on the battery.
- For proper operation, a new system should always start up with a fully charged battery. If a fully charged battery is not connected, the battery should be charged in full over night before any load is applied to the output of the BCM module.
- 12. To verify proper functionality, switch off the input AC power at the external circuit breaker and output power should be supplied from the battery if a fully charged battery has been connected.
- 13. The system is now fully operational and the output load can be connected.

Operation

Battery Backup for UPS Operation

The PSH-BCM360S module extends any 24VDC or 48VDC power supply to perform as an uninterruptible DC power supply. This is achieved by connecting a 12V lead-acid battery to the BATT_IN connector of the unit. During normal operation, the connected power supply provides energy to load with a voltage level of Vin -0.5 V (typical, 0.5 V loss due to internal decoupling diodes) as well as charging the connected battery. If the connected supply fails, the battery is then connected to the load (battery power mode), a step up converter is used to maintain the selected output voltage level, Vnom – 6% (typical).

Dual Inputs for Redundancy

The module provides two inputs to connect two power supplies to facilitate a redundant system. If one of the two connected sources fails then the second supply will provide energy to load maintaining the desired operation of the unit. The unit is designed to work with any type of fully stabilized 24V or 48V power supply.

Output Voltage Level and Efficiency

The PSH-BCM360S module functions with both 24VDC (15A) and 48VDC (7.5 A) supplies. The desired voltage is selectable by means of a jumper located on the side of the unit. It also offers very high efficiencies with up to 96% and 98% efficiency in normal mode for 24V and 48V modes respectively. In the battery power mode efficiencies are as high as 92% and 89% for 24V and 48V modes respectively.

Configuration Jumpers

One set of configuration jumpers (J6) are located on the top of the module (Figure 1).

	Configuration Jumper Settings				
Jumper	Parameter	Fitted	Not Fitted		
А	Battery test period	15 sec	10 min (default)		
В	Output voltage setting 24V (default)		48V		
С	Not in use (spare jumper fitted)	-			



Figure 1 – Configuration Jumpers (Top of Unit)

RHINO Battery Control Module PSH-BCM360S Operating Instructions 1st Edition, Rev. A 11/2018

Signals

The PSH-BCM360S module provides three signals to the user as an indication of the status of the unit; these signals are made available as LED indicators and corresponding isolated relay contacts (Figure 2) and are as follows.

	Status Signals			
Signal	Description			
DC-IN-OK	The DC-IN-OK LED will illuminate and relay will close if at least one of the inputs is present and has a voltage within $\pm 20\%$ / $\pm 3\%$ tolerance.			
BATT-OK	The BATT-OK LED will illuminate and relay will close if the battery is charged and has a low internal resistance. During battery discharge operation this signal monitors the output voltage and will switch off the LED and open the relay when the battery approaches the disconnection voltage.			
DC-OUT-OK	The DC-OUT-OK LED will illuminate and relay will close if the output voltage of the unit is higher than 85–90% of the nominal output voltage.			

Note: All Signal Relay contacts are rated for 30VDC/1A, 60VDC/0.5 A.

	Indicator LEDs – Status at a Glance			
DEAN	SIND BELOT SI DEC			
X	X	X	The BCM is operating normally.	
0	$\mathbf{\tilde{t}}$	$\mathbf{}$	Battery is supplying power to the load, and has sufficient charge.	
0	0	X	Battery is supplying power to the load, but the battery voltage has dropped to near its threshold level.	
0	0	0	NO power provided to the load. The battery is discharged below its operating threshold and no DC input power is present.	



riguro 2 olginar connocion rinout (Bottom or chi

Battery Remote On/Off

The PSH-BCM360S module provides a Battery Remote On/Off input (2 pins on signal connector) intended to facilitate using the potentiometer to set a new battery charge voltage level.

Battery Remote On/Off Input				
Battery State	Battery Remote On/Off Pins	Voltage		
Connected	Open Circuit	5V		
Disconnected	Short Circuit	<1V		

If this input is short circuited (switch closed in Figure 3) the battery will be disconnected from the unit by means of an internal relay. A voltage of 1V or less across the Battery Remote On/Off terminals will disconnect the battery from the unit. If the Battery Remote On/Off signal is set to off (short between pins) this will not affect the output of the unit in normal mode, however the battery will be disconnected, hence it will not charge. If the unit enters battery power mode while the Battery Remote On/Off signal is off, the battery will remain disconnected, hence no energy will be supplied to the load.



Battery

When the input DC voltage is present, the PSH-BCM360S unit will automatically charge the connected battery to a set end of battery charge voltage level, factory set for 25°C for leadacid batteries, using a constant current charging method of 1A (typical). As the battery voltage approaches the end of battery charge voltage level, the current will decrease proportionality; this characteristic is shown in Figure 4. If the battery specs differ from the 25°C default setting and the temperature sensor is not used, the user can adjust the set end of battery charge voltage level by means of the "Battery Voltage Adjust" potentiometer.



Note: For Cycle Use (repeated charging and discharging of battery), we recommend a charge current of 0.4 CA or smaller (C = battery capacity), therefore batteries with a capacity of 2.5 Ah or less should not be used with this module.

Temperature Sensor

The module also provides an input connector for an optional temperature compensation probe (part #PSM-TS). If this probe is connected, the unit will automatically compensate the end of battery charge voltage level depending on the measured temperature. The connection of the temperature probe also eliminates the need to change the potentiometer to compensate for a new temperature. The battery end voltage compensation curve is shown in Figure 5. (Applicable to factory setting of 13.6V/ 25°C)



RHINO Battery Control Module PSH-BCM360S Operating Instructions 1st Edition, Rev. A 11/2018

Battery Protection

The PSH-BCM360S module protects the connected battery against short circuit and overload by the means of a built in 40A fuse. This fuse is a standard 40A blade type fuse, which is accessible from the front panel of the unit for ease of replacement should the fuse be damaged during operation. The module also prevents deep discharge of the battery by disconnecting the battery from the load once the voltage level of battery has dropped below a defined threshold. An early warning of this disconnection is given to the user by the BATT-OK signal. The BATT-OK signal will switch off when the battery voltage is roughly 1V above the deep discharge threshold.

Ambient temperature and power rating

The PSH-BCM360S module operates at temperatures between -25°C and +70°C, with a minimum start-up temperature of -25°C. In normal mode the module can deliver full power up to 60°C. Refer to lead-acid battery spec sheet suggested operating temperature range and charge and discharge instructions below 0°C.

In Battery Power mode, a current derating of 2%/°C is required for 24V applications above 50°C. The boost current of 15A is available at ambient temperatures up to 40°C for a duration of 10 minutes as shown in Figure 6.

In Battery Power mode, a current derating of 2%/°C is required for 48V applications above 40°C. The boost current of 7.5 A is available at ambient temperatures up to 40°C for a duration of 3 minutes as shown in Figure 7.



Figure 6



Technical Specifications

Technical Specifications							
mput spec							
Inputs		2 x 360W, for any single or two identical 24VDC or 48VDC sources					
Input Voltage Range		24–28VDC or 48–56VDC (range selection with jumper)					
May Output		2004					
iviax. Output i	Power						
Output	Normal Mode	48VDC mode: Vin – (0.4–0.8 V); 15A max. 48VDC mode: Vin – (0.4–0.7 V); 7.5 A max.					
Voltage / Current	Battery Power Mode	24VDC mode: 22.2–22.9 V; 10A (15A in boost mode for 10 min) 48VDC mode: 44.6–45.3 V; 5A (7.5 A in boost mode for 3 min)					
Efficiency (load >50% of I _{out} max.)		Normal mode: 94–98% (battery charged) Battery power mode: 87–92%					
General S	pecifications						
Backup Battery		12V lead-acid battery with a capacity greater than 2.5 Ah (purchased separately)					
Battery Protection		Against over voltage, deep discharge, overcharge, short cir- cuit and reverse connection (built-in 40A user-replaceable blade fuse)					
Signals	Status	DC OK input, DC OK output, BAT OK all relay contact closed and LED on at status OK					
Jigilais	Contact Rating	30VDC / 1.0 A max. 60VDC / 0.5 A max.					
Battery Charging Current		0.8 – 1.2 A					
Nominal Battery Voltage (at 25°C)		13.6 VDC (factory setting)					
Battery Voltag	e Adjustment Range	13.2 - 14.4 VDC					
BCM Over-temperature Protection		100°C at back of BCM housing					
Battery Resistance Test		100m0hm min. (normal mode at 25°C)					
Battery Test Current		2.5A / 60ms typ. (normal mode at 25°C)					
Battery Test Interval (Jumper Setting)		15s or 10min					
Battery Warning		10.4 – 11.4 VDC (battery power mode only)					
Battery Disco	nnection	9.1 – 9.7 VDC (battery power mode only)					
Battery Remote Off		disconnects battery, prevents battery power mode					
Automatic Ba Compensatio	ttery Temperature n Range	-15°C to +50°C [+5°F to +122°F]					
Enclosure Ma	terial (Chassis/Cover)	Aluminum / Stainless Steel					
Weight		730g [25.8 oz]					
Mounting		DIN rail (EN 50022-35x15/7.5), snap-on self-locking spring					
0	Input, Output, Battery	Screw terminal (plug included)					
Connections	Signal, Control	Detachable screw terminals (plugs included)					
Safety / En	vironmental						
	Normal Mode	-25°C to +60°C [-13°F to +140°F] max. (without derating)					
Operating	Battery Power Mode, Nominal	24VDC mode: derating above +50°C: 2.0 %/K 48VDC mode: derating above +40°C: 2.0 %/K					
remperature	Battery Power Mode, Boost	24VDC mode: up to +40°C for 10 minutes max. 48VDC mode: up to +40°C for 3 minutes max.					
Storage Temp	erature	-25°C to +85°C [-13°F to +185°F] max.					
Temperature Coefficient		0.02 %/K					
Humidity		95% relative humidity max., non-condensing					
Maximum Altitude		2000m					
Safety Standards		IEC/EN 60950-1, UL 60950-1 (2nd) + Am1:2011, UL508 requirements					
MTBF (acc. to) IEC 61709 at 25°C)	> 1,500,000 hrs					
Protection Class							
Degree of Protection		IP20 (IEC/EN 60529)					
Electromagnetic compatibility (EMC)		Based on connected unit (no internal switching device)					
Vibration Acc. IEC 60068-2-6		3 axis, 1 g sine sweep, 10–55 Hz, 1 oct/min					
Shock Acc. IEC 60068-2-27		3 axis, 15 g half sine, 11ms					
Safety Approvals		CSA (tested to UL60950, UL508), File 229285					
All specificati	ions valid at nominal inp	or test certificate ieu ousou- i (SiQ TOF EN) nut voltage, full load and +25°C after warm-up time unless					

RHINO Battery Control Module PSH-BCM360S Operating Instructions 1st Edition, Rev. A 11/2018 www.automationdirect.com

For the latest prices, please check AutomationDirect.com.

Electrical Connections and Wire Size

Electrical Connections and Wire Size							
	24V	48V					
Input & Output*	14–7 AWG	17–7 AWG					
πιμαί α Ομίμαι	Max resistance $20m\Omega$	Max resistance $40m\Omega$					
Battery Input	11–7 AWG; Max resistance $10m\Omega$						
Status and Control Signals	32–12 AWG						
Tightoning Torquo	Input, Output, Battery: 1.76 N·m						
ngnening lorque	Status and Control Signals: 0.19 N·m						
Stripping Length	7.0 mm						

* Input cable (from power supply) and Output cable (to load) must be the same gauge wire.



1-800-633-0405 RHINO PSB24-BCM960S Battery Control **Module**



Overview

The PSB24-BCM960S battery control module is designed to support a 24V system with up to 40A output and 4.5 minutes back up time for 15AH battery capacity. It offers a wide input voltage from 24-28V and a wide operating temperature range from -20°C to 60°C. This product comes with dry contacts for battery management signals and LED indicator for battery status. The rugged compact aluminum case is shock and vibration resistant according to IEC 60068-2.

Features

- · Full corrosion resistant Aluminum chassis
- Suitable for 24V system up to 40A
- Built-in diagnostic monitoring for DC OK, Discharge and Battery Fail by relay contacts
- LED indicator for DC OK, Battery Fail, DC Input, Battery Reverse Polarity and Battery Discharge
- High MTBF > 500,000 hrs as per Telcordia SR-332
- Wide operation temperature range from -20 to 60°C
- Conformal coating on PCBA to protect against chemical and dust pollutants

Device description (Fig. 1)

Ind. Cont. Eq.



- 1. Input & Output/Battery terminal block connector
- 2. Signal terminal block connector
- 3. LED display status
- 4. Universal mounting rail system

1-800-633-0405 RHINO PSB24-BCM960S Battery Control Module Mounting Connection

The unit can be mounted on 35mm DIN rails in accordance with EN60715. For vertical mounting, the device should be installed with Input & Output/Battery terminal block on the bottom. For horizontal mounting, the device should be installed with Input & Output/Battery terminal block on the left side.

Each device is delivered ready to install.



Snap on the DIN rail as shown in Fig. 2:

1. Tilt the unit slightly upwards and put it onto the DIN rail.

2. Push downwards until stopped.

- 3. Press against the bottom front side for locking.
- 4. Shake the unit slightly to ensure that it is secured.

Dismounting



To uninstall, use a flat screwdriver to pull or slide down the latch as shown in Fig. 3. Then, slide the PSU in the opposite direction, release the latch and pull out the PSU from the rail.

Orientation

The terminal block connectors allow easy and fast wiring. The terminal block is IP20 compliant and thus provides the user safety and protection from electrical shock hazards.

You can use flexible (stranded wire) or solid cables as follows:

Electrical Connections and Wire Size								
	Stranded / Solid		Torque		Domorko			
	mm²	AWG	N∙m	lb∙in	Remarks			
Battery	3.3-13.3	12-6	1.52	13.5	Load: 0-20A			
DC In/Out	8.4-13.3	8-6	1.52	13.5	Load: 20-40A			
Signal	0.2-3.3	24-12	0.61	5.4	-			

Wires between the battery control module and battery must not be longer than 2m [6.5 ft]. For reliable and shockproof connections, the wire stripping length should be 10mm for Input & Output/Battery terminal block connector and 7mm for Signal terminal block connector (see Fig. 5 (1)). Please ensure that wires are fully inserted into the connecting terminals as shown in Fig. 5 (2).



In accordance with EN60950 / UL60950, flexible cables require ferrules.

Use appropriate copper cables that are designed to sustain operating temperature of at least 60°C/75°C for USA or at least 90°C for Canada.



Power Supplies
1-800-633-0405 RHINO <u>PSB24-BCM960S</u> Battery Control Module

Signal Wiring Diagram

Contact current: Imax = 1A Contact voltage: Vmax = 24VDC/VAC (Secondary circuit) No polarity requirement.



Status Indicators							
DCM Statua	Relay Ou	ıtput Conne	IED Disates Otatus				
BUM Status	Discharging	BAT Fail	DC OK	LED Display Status			
Battery Fully Charged	Open	Open	Closed	Green LED On			
Battery Charging	Open	Open	Closed	Green LED Flashing			
Battery Discharging* [Buffering Mode]	Closed*	Open	Closed	Orange LED Flashing			
No Battery Connected	Open	Closed	Open	Red LED On			
Output Shutdown	Open	Open	Open	No Light			

* With output current 3A to 40A.

Buffering Time								
Output Current	7.5 AH	12AH	15AH					
2.5 A	6,500s	14,500s	19,000s					
5A	3,000s	7,000s	9,000s					
10A	1,200s	2,400s	3,200s					
20A	400s	1,100s	1,500s					
30A	120s	450s	600s					
40A	25s	200s	280s					

Typical Application Notes



Power Derating



Buffering Time



1-800-633-0405 RHINO PSB24-BCM960S Battery Control Module

Technical Specifications						
Input (DC)						
Nominal input voltage	24VDC					
Voltage range	24-28VDC					
Maximum input voltage	30 ± 0.5 VDC					
Input current	Charging Mode: 2.0 ± 1.0 A [25°C], Discharging Mode: 40A Max.					
Maximum inrush current (cold start)	< 45A [25°C]					
Charging time	< 3 hr ± 1 hr [25°C]					
Efficiency	Charging Mode: > 70.0%, Discharging Mode: > 99.0%					
Output (DC)						
Nominal output voltage	24VDC typ. [depends on Vin]					
Discharging voltage	23-28 VDC					
Maximum output voltage	30 ± 0.5 VDC					
Output current	40A Max.					
Derating	Refer to Fig. 7					
Component derating	Vin = 28.0 VDC, Max. load					
Short circuit / Overload	No damage					
Batteries						
Recommended battery types	24V VRLA or 2 x 12V VRLA					
Recommended battery capacity	7.2-15.0 Ah					
Battery voltage range	23-28VDC [continuous operating], 30VDC Max [maximum voltage that will not cause damage to the unit] 14VDC Min [voltage level of battery to enable "BAT Fail" function]					
Battery fuse	Auto 50A / 80V, FK3 [Littelfuse] or similar in the battery path [protects the wires between the battery and the battery control module]					
General Data						
Type of housing	Aluminum					
LED signals	Green LED On = Unit is fully charged Green LED Flashing = Unit is charging Orange LED Flashing = Unit is discharging Red LED On = Battery fail (no battery is connected) Orange LED On = Battery 24 V or DC 24 V reverse polarity					
Signal relay contacts	DC OK = Contact is closed when battery is fully charged and the unit is ready to discharge/buffer. DISCHARGING = Contact is closed when the unit is discharging/buffering with output current of 3-40 A. BATTERY FAIL = Contact is closed when the battery fails to function.					
MTBF	> 500,000 hrs. as per Telcordia					
Weight	0.39 kg [14 oz]					
Connection method	Screw connection					
Stripping length	Input & Output/Battery terminal block connector: 10mm [0.39 in] Signal terminal block connector: 7mm [0.28 in]					
Operating temperature (surrounding air temperature)	-20 to 60°C [-4 to 140°F] [Refer to Fig. 7]					
Storage temperature	-25 to 85°C [-13 to 185°F]					
Humidity at +25°C, no condensation	< 95% RH					
Vibration (non-operating)	10Hz to 500Hz @ 30m/S² [3G peak]; displacement of 0.35mm; 60 min per axis for all X, Y, Z direction. Refer to IEC60068-2-6. Note: all figures quoted are amplitudes [peak values]					
Shock (in all directions)	30G [300m/S ²] in all directions according to IEC60068-2-27					
Pollution degree	2					
Altitude (operating)	3000m					

Continued on next page.

1-800-633-0405 RHINO PSB24-BCM960S Battery Control Module

	Technical Specifications (continued)						
Certification and St	andards						
Electrical equip	nent of machines	IEC60204-1					
Electronic equip power installatio	ment for use in electrical ons	EN50178 / IEC62103					
Safety entry low	voltage	PELV [EN60204], SELV [EN60950]					
Electrical safety (of information t	echnology equipment)	UL/C-UL recognized to UL60950-1 and CSA C22.2 No. 60950-1 File No. E198298, CB scheme to IEC60950-1					
Industrial contro	ol equipment	UL/C-UL listed to UL508 and CSA C22.2 No.107.1-01, CSA to CSA C22.2 No.107.1-01 File No. 249074					
Protection again	st electric shock	DIN57100-410					
CE		In conformance with EMC directive 2014/30/EU and Low Voltage Directive 2014/35/EU					
Component pow	er supply for general use	EN61204-3					
Immunity		EN55024, EN61000-6-2 [EN61000-4-2, 3, 4, 5, 6, 8]					
Emission		EN55032, EN55011					
Agency Approva	nls	C C C C C C C C C C C C C C C C C C C					
RoHS Compliant	t	Yes					
Safety and Protecti	ty and Protection						
Isolation voltage:	Input & Output / PE Signal / PE Input & Output / Signal	1kVAC 1kVAC 1kVAC					
Polarity protecti	on	Yes					
Protection degre	e	IP20					
Safety class		Class III					

1-800-633-0405 RHINO PSB24-BCM960S Battery Control **Module**

Block Diagram



RHINO PSL-24-BCM240 BATTERY CONTROL MODULE

READ INSTRUCTIONS BEFORE INSTALLING OR OPERATING THIS DEVICE. KEEP FOR FUTURE REFERENCE.

General Description

The PSL-24-BCM240 battery control module is designed to use in small cabinets where space is very critical. It requires less installation space due to its flat body with depth of only 55.6 mm, 71mm wide and 91mm tall. The tough plastic case is flame retardant, certified to UL 94V-0 specification. The module supports 24VDC systems with external battery up to 12AH capacity and comes with contacts for battery management signals and an LED indicator for battery status. The highly efficient convection cooled design is certified to major safety approvals including IEC/EN/UL 60950-1 for ITE and UL 508 for Industrial, which allows the module to be used reliably in most industrial applications.

IMPORTANT SAFETY INSTRUCTIONS

- Retain these instructions. This manual contains important safety instructions.
- When replacing batteries, only use the same type of batteries as described in the Specifications.
- Proper disposal of batteries is required. Refer to the relevant local codes for disposal requirements.
- Switch main power off before connecting or disconnecting the device. Danger of explosion!
- If the orange status LED is on steady, this indicates a failure in the installation. In this case, do not turn on power supply while the battery is connected. Danger of explosion!
- To guarantee sufficient convection cooling, keep a distance of 20mm above and below the device as well as a lateral distance of 5mm to other units. See Figure 4.
- Please note that the enclosure of the device can become very hot depending on the ambient temperature and load of the power supply. Risk of burns!
- The mains power must be turned off before connecting or disconnecting wires to the terminals!
- Do not introduce any objects into the unit!
- Dangerous voltage present for at least 5 minutes after disconnecting all sources of power.
- This is a built-in unit and must be installed in a cabinet or room (condensation free environment and indoor location) that is relatively free of conductive contaminants.

•CAUTION: FOR USE IN A CONTROLLED ENVIRONMENT.

Risk of electrical shock, fire, personal injury or death.

- 1. Turn power off before working on the device.
- 2. Make sure the wiring is correct by following all local and national codes.
- 3. Do not modify or repair the unit.
- 4. Use caution to prevent any foreign objects from entering into the housing.
- 5. Do not use in wet locations.
- 6. Do not use the unit in area where moisture or condensation can be expected.





Highlights & Features

- Suitable for 24V system up to 10A
- Zero switch over time from loss of DC input to battery operation
- Built-in diagnostic monitoring for DC OK, Discharge and Battery Fail by relay contacts
- \cdot Full power over entire operating temperature range from -20°C to +60°C
- LED indicators for DC OK, Battery Charging, Battery Discharging, Battery Fail and Battery Reverse Polarity
- High MTBF > 500,000 hrs. as per Telcordia SR-332
- Overvoltage, overcurrent, over temperature, short circuit protections
- Powered systems may include unbuffered loads

Device description (Fig. 1)



- (1) Input/Output/Battery terminal block connector
- (2) Signal terminal block connector
- (3) LED display status
- (4) Universal mounting rail system

FOR TECHNICAL ASSISTANCE CALL 770-844-4200

Mounting

The unit can be mounted on 35mm DIN rails in accordance with EN60715. For vertical mounting, the device should be installed with Input/Output/Battery terminal block on the bottom.

Each device is delivered ready to install.



Snap on the DIN rail as shown in Fig. 2:

- 1. Pull the unit's DIN rail latch DOWN.
- 2. Tilt the unit slightly upwards, hook the top end onto the DIN rail and push downwards until stopped.
- 3. Position the bottom front end against the DIN rail.
- 4. Push the unit's latch DIN rail UP to lock.

Dismounting



To uninstall:

- 1. Use a flat screwdriver to pull or slide down the latch as shown in Fig. 3.
- 2. Tilt the bottom part of the unit out.
- 3. Push the unit up and pull out from the DIN rail.

Orientation

To guarantee sufficient convection cooling, keep a distance of 20mm (0.79 inch) above and below the device as well as a lateral distance of 5mm (0.2 inch) to other units.



RHINO PSL-24-BCM240 Battery Control Module

Connection

The terminal block connectors allow easy and fast wiring. You can use flexible (stranded wire) or solid cables as follows:

Electrical Connections and Wire Size								
	Stranded	d / Solid	Τοι	rque				
	mm²	AWG	N·m	lb∙in				
In/Out/Battery	2.1-3.3	14-12	0.62	5.4				
Signal	0.21-3.3	24-12	0.62	5.4				

The wires between the battery control module and battery must not be longer than 2 x 2m (cord length 2m). For reliable and shock proof connections, the wire stripping length should be 7mm (see Fig. 5 (1)). Please ensure that wires are fully inserted into the connecting terminals as shown in Fig. 5 (2).



In accordance with EN60950 / UL60950, flexible cables require ferrules.

Use appropriate copper cables that are designed to sustain operating temperature of at least 60°C/75°C for USA or at least 90°C for Canada.

Power Derating



Signal wiring diagram

Contact relay rating: 1A/30VDC. No polarity requirement.



Status Indicators							
DOM Clature	Relay O	LED Display					
BUM Status	Discharging	BAT Fail	DC OK	Status			
Battery Fully Charged	Open	Open	Closed	Green LED On			
Battery Charging	Open	Open	Closed	Green LED Flashing			
Battery Discharging* (Buffering Mode)	Closed*	Open	Closed	Orange LED Flashing			
No Battery Connected	Open	Closed	Open	Red LED On			
Output Shutdown	Open	Open	Open	No Light			

* With output current 0.1 A to 10A.

Typical application notes



RHINO PSL-24-BCM240 Battery Control Module

Buffering Time



Buffering Time (minutes)							
Output Current	3.3 AH	7.5 AH	12AH				
0.5 A	400	900	1400				
1A	180	398	654				
2A	70	165	323				
4A	28	72	160				
6A	19	55	103				
8A	11	22	49				
10A	7	18	37				

1-800-633-0405

		Technical Specifications		
Input (DC)				
Nominal input voltage		24VDC		
Voltage range		24-28 VDC		
Maximum input voltage		< 33 VDC		
Input current		Charging Mode: 0.5 ± 0.1 A (25°C)		
Charaina time		Discharging Mode: 10A Max.		
Charging time		< 30 III ± 3 III (20°C) I0I Dallely 24V/ I2AH Charging Mode: > 80.0%		
Efficiency		Discharging Mode: > 99.0%		
Output (DC)				
Nominal output voltage		24VDC typ. (depends on Vin)		
Discharging voltage		22-28 VDC		
Maximum output voltage		< 33 VDC		
Output current		10A Max.		
Derating		Refer to Fig. 6		
Component derating		Vin = 28.0 VDC, Max. load		
Short circuit / Overload		Discharging Mode: Shutdown and no damage		
Recommended Batt	teries			
Battery types		24 V, VRLA		
Betten (conceity		2 x 12V, VRLA		
Ballery capacity		3.3-12.0 All 23-28VDC (continuous operation)		
Battery voltage range		33VDC Max (maximum voltage that will not cause damage to the unit) 20VDC Min (voltage level of battery to enable "BAT Fail" function)		
Battery fuse		Auto 15A / 58V, MINI (Littelfuse) or similar in the battery path (protects the wires between the battery and the battery control module)		
General Data				
Type of housing		Plastic (PC), enclosed		
		Green LED On = Unit is fully charged		
LED signals		Green LED Flashing = Unit is charging Orange LED Flashing = Unit is discharging Red LED On = Battery fail (no battery is connected)		
Signal relay contacts		DC OK = Contact is closed when battery is fully charged and the unit is ready to discharge/buffer. DISCHARGING = Contact is closed when the unit is discharging/buffering with output current of 5mA-10 A. BATTERY FAIL = Contact is closed when the battery fails to function.		
MTBF		> 500,000 hrs. as per Telcordia		
Dimensions (L x W x H)		91mm x 71mm x 55.6 mm [3.58 in x 2.80 in x 2.19 in] (See www.AutomationDirect.com for complete engineering drawings.)		
Weight		0.14 kg [4.9 oz]		
Connection method		Screw connection		
Stripping length		7mm [0.28 in]		
Operating temperature (surr	rounding air temperature)	-20°C to +60°C [-4°F to +140°F] (Refer to Fig. 7)		
Storage temperature		-25°C to +85°C [-13°F to +185°F]		
Humidity at +25°C, no cond	densation	5 to 95% RH		
Vibration Shock (in all directions)		Operating: IEC60068-2-6, Sine Wave: 10Hz to 500Hz @ 19.6 m/s ² (2G peak); 10 min per cycle, 60 min for all X, Y, Z directions Non-Operating: IEC60068-2-6, Random: 5Hz to 500Hz (2.09Grms); 20 min per axis for all X, Y, Z directions Operating: IEC60068-2-27, Half Sine Wave: 4G for a duration of 22ms, 3 shocks for each 3 directions Non-Operating: IEC60068-2-27, Half Sine Wave: 4G for a duration of 12ms, 3 shocks for each 3 directions		
Pollution degree				
Altitude (operating)		3000m		
Certification and St	andards			
Electrical equipment of mac	thines	IEC60204-1		
Electronic equipment for use	e in electrical power installations	EN62477-1 / IEC62103-1		
Safety entry low voltage		PELV (EN60204), SELV (EN 60950)		
Electrical safety (of informat	tion technoloav equipment)	UL/C-UL recognized to UL60950-1 and CSA C22.2 No. 60950-1 (File No. E198298), CB scheme to IEC60950-1		
Industrial control equipment	t	UL/C-UL listed to UL508 and CSA C22.2 No.107.1-01 (File No. E197592)		
CE		In conformance with EMC directive 2014/30/EU and Low Voltage Directive 2014/35/EU		
Component power supply fo	or general use	EN61204-3		
Immunity		EN55024, EN61000-6-2 (EN61000-4-2, 3, 4, 5, 6, 8)		
Emission		FN55032 FN55011		
	C	C C C US LISTED Ind. Cont. Eq.		
RoHS Compliant		Yes		
Safety and Protection	on			
Isolation voltage:	Input & Output / PE Signal / PE Input & Output / Signal	1kVAC 1kVAC 1kVAC		
Polarity protection		Yes		
Protection degree		IP20		
Safety class		Class III		

RHINO PSL-24-BCM240 Battery Control Module

Dimensions

mm [inches]









Block Diagram



RHINO PSL-24-BCM240 Battery Control Module

Troubleshooting

Troubleshooting							
Problem	Possible Cause	Suggestion					
Orange LED is ON Steady	Input connection or battery connection is reverse polarity.	Check polarity of input connection and battery connection and make corrections.					
BCM does not operate in charging mode after input is	Input wiring is open or no input voltage to the BCM is supplied.	Check wiring and voltage of input supply.					
appneu	Internal fuse is opened.	Replace the battery control module.					
	Battery wiring is not connected or is opened.	Check battery wiring and compare with Typical Application Notes in this BCM datasheet. Make corrections as needed.					
BCM does not operate in buffering mode after input voltage drops	Battery has not had enough time to be charged and it is still below the continuous operating voltage range.	Check battery voltage and compare with minimum required battery voltage provided in this BCM document.					
	Protection mode enabled.	Check for overvoltage, overcurrent, over temperature, or short circuit condition, and correct.					

1-800-633-0405 RHINO PSM24-BCM360S Battery Control Module

The battery control module, when combined with a PSM24 power supply, makes a perfect DC-UPS system by providing the means to charge and monitor an external lead acid battery. The power supply charges the connected battery and keeps it in a charged mode.

Consequently, the output voltage of the system is equivalent to the battery voltage. To avoid overcharging the battery, an external temperature sensor automatically adjusts the battery voltage to the required end of charge voltage. This configuration extends the battery life.



Battery Control Module							
Part Number	Price	Drawing Link	Input	Input Power Max	Output Voltage Nom	*Output Power Max	
PSM24-BCM360S <u>PSM24-BCM360S</u> (includes terminal plugs)	\$235.00	PDF	24VDC power supply and 24VDC battery	360W	24VDC	360W	

*reduce maximum output current by battery charging current.

General Specifications					
Operating Temperature	-25 to 70°C max [-13 to 158°F] 1.5%/K, derating above 40°C [104°F]				
Electromagnetic Compatibility	In correspondence to connected units [no internal switching device]				
Battery Protection	Over voltage, deep discharge, short-circuit and reverse connection [built-in fuse]				
Status Signals	DC-OK input, DC-OK output, BAT OK [all relay contacts closed at status OK]				
Rating per Relay Contact	30 VDC / 1.0 A max.				
Remote Link Wire 0.5m	One cable included with PSM24-BCM360S module				
Remote ON/OFF	By external contact: ON = J5.7 + J5.8 not shorted OFF = J5.7 + J5.8 shorted				

Battery Control Module Function Diagram



Battery Control Module Connector Positions



PIN	J1	J2	J3	J4	J5	J6
1	- Vin [DC In]	GND [-]	S+	15 sec test	DC-IN-OK Signal	PSM24-360S [factory setting]
2	+ Vin [DC In]	GND [-]	S-	Common	DC-IN-OK Relay contact	PSM24-180S
3	- Bat in	Vout [+]	—	10 min test	Bat-OK Signal	PSM24-090S
4	+ Bat in	Vout [+]	—	—	Bat-OK Relay Contact	_
5	_	_	—	—	DC-OUT-OK Signal	_
6	_	_	—	—	DC-OUT-OK Relay Contact	_
7	_	_	—	—	Remote ON/OFF	_
8	—	—	—	—	Remote ON/OFF	—
9	_	_	—	_	Temperature Sensing	_
10	_	_	_	_	Temperature Sensing	_

C

1-800-633-0405 For the latest prices, please check AutomationDirect.com. **RHINO DC to DC Converters PSP Series**

Overview

Both 25W and 60W DC-DC converters are available in the Rhino PSP DIN rail series. Wide input ranges of 9.5 to 18VDC and 18 to 75VDC allow these models to operate from all popular DC supply voltage systems. With tightly regulated output voltage these DC-DC converters provide a reliable power source for sensitive loads in industrial process controls, factory automation and other equipment exposed to a critical industrial environment. They can be used to isolate a specific load from the 24 volt bus voltage, and offer easy installation with snap-on DIN rail mounting and detachable screw terminal blocks.

Features

- Ultra-wide input voltage range
- Output voltage adjustable
- Overload and short circuit protection
- Low ripple and noise
- I/O-isolation 1500 VDC
- Compact, slim plastic case
- Reliable snap-on 35mm DIN rail mount
- Wall-mount bracket included
- 3-year warranty





PSP 25 Watt DC-DC Converters



PSP 60 Watt DC-DC Converters

DC-DC Converters								
Part Number	Price	Drawing Link	Input Voltage Range	Input Current Max. @ Vin, [lout = 0% / 100%]	Output Voltage [Adjustable]	Output Current Max	Output Power	Weight [lbs]
PSP24-DC12-1	\$120.00	PDF	9.5 - 18.0 VDC	80mA / 2.5 A @ 12VDC	24VDC	1A		0.31
PSP05-DC24-5	\$117.00	PDF		80mA / 1.3 A @ 24VDC	5VDC	5A	05147	0.31
PSP12-DC24-2	\$96.00	PDF			12VDC	2A	2500	0.31
PSP24-DC24-1	\$115.00	PDF			24VDC	1A		0.31
<u>PSP12-DC24-5</u>	\$136.00	<u>PDF</u>	18.0 - 75.0 VDC	31mA / 2.9 A @ 24VDC 19mA / 1.4 A @ 48VDC	12VDC	5A	6014	0.59
<u>PSP24-DC24-2</u>	\$140.00	PDF		45mA / 3.1 A @ 24VDC 25mA / 1.54 A @ 48VDC	24VDC	2.5 A	OUW	0.59

RHINO DC to DC Converters PSP Series

General Specifications			
Startup Voltage / Undervoltage Shut-down	17.2 VDC / 15.7 VDC [PSP24-DC12-1: 8.4 VDC / 7.6 VDC]		
Efficiency (Typical)	86%		
Output Voltage Adjustable Range	5VDC model: 5.0 - 5.25 VDC 12VDC models: 12.0 - 15.0 VDC 24VDC models: 24.0 - 28.0 VDC		
Overvoltage Protection, Trigger Point	5VDC model: <6.5 V 12VDC models: <24V 24VDC models: <42V		
Output Voltage Regulation*	0.5% max		
Ripple/Noise (20MHz bandwidth)	<50mV [pk-pk]		
<i>Temperature: Operating Storage (non-operating) Derating</i>	-25 to 70°C max [-13 to 158°F max] -25 to 85°C max, [-13 to 185°F max] 1.5%/K above 50°C [122°F] for 25W models, 2%/K above 40°C [104°F] for 60W models		
Humidity (Non-condensing)	95 % relative humidity max.		
Temperature Coefficient	0.02%/K		
Switching Frequency	55 – 180kHz depending on load [frequency modulation]		
Isolation Voltage (1 min.) – Input/Output	1500VDC		
Safety Standards	IEC 60950-1, EN 60950-1 [output SELV], UL 60950-1, EN 60204, CSA 22.2 60950-1-07, EN50178, UL 508		
Electromagnetic Compatibility (EMC)	Emissions: EN 61000-6-3; Immunity: EN 61000-6-2		
Parallel Operation	No parallel operation		
Safety Class	Degree of protection class 1		
Environmental Air	No corrosive gases permitted		
Enclosure Rating	IP 20 [IEC 60529]		
Enclosure Material	Plastic FR2010-110C [UL 94V-0 rated]		
Mounting	DIN rails per EN 50022-35x15/7.5 [snap-on with self-locking spring]; bracket for wall/chassis mount included		
Mounting Orientation	Vertical only		
Wiring	12-24 AWG [3.16-0.21 mm ²]		
Connections	Screw type plug-in connector [standard], Recommended tightening torque 0.5-0.7 Nm [4.5-6.2 in-lb]		
Short Circuit Protection	Current limited at 110% typical		
MTBF (IEC 61709 @ 25°C)	>2.5 million hours		
Agency Approvals**	UL/cUL 508 listed, File No. E197592; CSA File 229285; CE; Reach; RoHS		

* Input variation Vin min to Vin max and load variation 0 to 100%

**To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page at www.automationdirect.com

Note: All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.



The unit can be mounted on a chassis or wall using the included mounting bracket.

1-800-633-0405 **RHINO DC to DC Converters PSP Series**

Part Numbers: PSP24-DC12-1 PSP05-DC24-5 PSP12-DC24-2 PSP24-DC24-1

	Input		Output
1	Ground	1	+Vout
2	-Vin	2	-Vout
3	+Vin		



Part Numbers: PSP12-DC24-5 PSP24-DC24-2

	Input	Output		
1	Ground	1	+Vout	
2	-Vin	2	-Vout	
3	+Vin	NC	No Connect	



1-800-633-0405 For the latest prices, please check AutomationDirect.com. **RHINO DC to DC Converters PSE Series**

Overview

The Rhino PSE Series DC-DC converters offers a compact, reliable power source for industrial process controls, factory automation, and equipment in harsh environments. Ultra-wide input voltage ranges of 9.5-36 VDC and 18-75 VDC allow these models to operate from all popular DC supply voltage systems. With tightly regulated and highly accurate output voltage these DC-DC converters provide a reliable power source for sensitive loads where AC power is not accessible. Remote on/off control, input polarity protection, and overload protection make them extremely rugged and versatile. They offer easy installation with chassis or DIN rail mounting options.

Features

- Fully encapsulated low profile plastic case
- Ultra-wide input voltage range
- Reverse polarity, overload and short circuit protection
- I/O-isolation 2500VDC
- Operating temperature range: -40 to 85°C [-40 to 185°F]
- Chassis mount or 35mm DIN rail mount with optional adapter
- No minimum load required
- Remote On/Off
- DC on LED indicator
- 3-year warranty



DC-DC Converters									
Part Number	Price	Drawing Link	Input Voltage Range	Input Current Typ. @ Vin [No Load]	Output Voltage [VDC]	Output Current Max.	Output Power Max.	Efficiency	Weight [lb]
<u>PSE05-DC12-40</u>	\$92.00	<u>PDF</u>			5.1	8A		90%	
<u>PSE12-DC12-40</u>	\$92.00	PDF	9.5 - 36.0 VDC	90mA @ 24VDC	12	3.33 A		90%	
<u>PSE24-DC12-40</u>	\$92.00	PDF			24	1.67 A	40\0/	90%	0.49
PSE05-DC24-40	\$98.00	PDF			5.1	8A	40 1 1	89%	0.40
<u>PSE12-DC24-40</u>	\$98.00	PDF	18.0 - 75.0 VDC	55mA @ 48VDC	12	3.33 A		91%	
PSE24-DC24-40	\$98.00	PDF			24	1.67 A	_	92%	
PSE05-DC12-60	\$110.00	PDF		100mA @ 24VDC	5.1	12A		90%	
PSE12-DC12-60	\$110.00	PDF		100mA @ 24VDC	12	5A		91%	
PSE24-DC12-60	\$110.00	PDF	9.5 - 36.0 VDC	110mA @ 24VDC	24	2.5 A		91%	
PSE48-DC12-60	\$110.00	PDF		60mA @ 24VDC	48	1.25 A		91%	0.00
PSE05-DC24-60	\$115.00	PDF		40mA @ 48VDC	5.1	12A	0000	91%	0.00
PSE12-DC24-60	\$115.00	PDF		60mA @ 48VDC	12	5A]	92%	
PSE24-DC24-60	\$115.00	PDF	10.0 - 75.0 VDC	60mA @ 48VDC	24	2.5 A		91%	
PSE48-DC24-60	\$115.00	PDF		50mA @ 48VDC	48	1.25 A		91%	

Note: All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.

RHINO DC to DC Converters PSE Series

Input Specifications				
Series	40 Watt	60 Watt		
Surge Voltage (100 msec. max.)	PSExx-DC12 Models: 50V max. PSExx-DC24 Models: 100V max.			
Start-Up Time	30ms max.	50ms max.		
Conducted Noise (Input)	EN 55022 class A, FCC part 15 class A [without external components]			
Start-Up Voltage / Under Voltage Shut Down	PSExx-DC12 Models: 9VDC max. / 7.5 VDC typical PSExx-DC24 Models: 18VDC max. / 16VDC typical			
ESD (Electrostatic Discharge) EN 61000-4-2, air ±8kV, contact ±4KV, perf. criteria A		tact ±4KV, perf. criteria A		
Radiated Immunity	EN 61000-4-3, 10 V/m, perf. criteria A			
Fast Transient / Surge (With External Input Capacitor)	EN61000-4-4, ±2kV, perf. criteria A EN61000-4-5, ±2kV, perf. criteria A			
Conducted Immunity	EN61000-4-6, 10Vrms, perf. criteria A			

Note: All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.

Output Specifications			
Series	40 Watt	60 Watt	
Voltage Set Accuracy	±2.0% max.		
Regulation	Input variation [Vin min. to Vin max.]: 0.5% max. Load Variation 0 - 100%: 1.0% max.	Input variation [Vin min. to Vin max.]: 1.5% max. Load Variation 0 - 100%: 1.0% max.	
Minimum Load	Not re	quired	
Temperature Coefficient	±0.03	2 %/K	
Ripple and Noise (20MHz bandwidth)	5.1 VDC models:100 mVpk-pk. typical12 & 24VDC models:150 mVpk-pk. typical48VDC models:200 mVpk-pk. typical		
Transient Response	250µs typical [Alignment to 1% at load step change 75% to 100%]		
Over Voltage Protection	120% of Vout [Zener diode clamp]		
Output Current Limitation	At 150% of lout max.		
Short Circuit Protection	Hiccup mode, automatic recovery		
Capacitive Load	5.1 VDC models: 13,600μF max. 12VDC models: 2,400μF max. 24VDC models: 600μF max. 48VDC models: 150μF max.	5.1 VDC models: 20,000μF max. 12VDC models: 3,540μF max. 24VDC models: 890μF max. 48VDC models: 220μF max.	

Note: All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.

RHINO DC to DC Converters PSE Series

	General Specifications			
Series Specification		40 Watt	60 Watt	
	Operating Ambient with Natural Convection (20LFM)	-40 to 85°C [-40 to 1	85°F] [with derating]	
Tomporatura Banaa	IEC/EN/UL60950-1 Approved Ambient	+65°C max. [+149°F max] [without derating]	+60°C max. [+140°F max] [without derating]	
	Case Temperature	+95°C max. [+203°F max.]	
	Storage	-50 to +125°C	[-58 to +257°F]	
Load Derating (with Natur	ral Convection 20LFM)	4.5 %/K above +70°C [+158°F]	3.3 %/K above +70°C [+158°F]	
Thermal Impedance (with	Natural Convection 20LFM)	4.75 °C/W	3.5 °C/W	
Humidity (non condensin	g)	95% relative	humidity max	
Reliability, Calculated MT (MIL-HDBK-217F, @ +25°0	BF C, ground benign)	>644,290 hours	>242,029 hours	
Isolation Voltage (60 sec.,) Input/Output	2500VDC		
Isolation Capacitance Inp	ut/Output	2400pF max [100kHz, 1V]	3000pF [100kHz, 1V]	
Isolation Resistance Inpu	t/Output	>1000MΩ [500VDC]		
Switching Frequency		285kHz typical	210kHz typical	
	On	3.5 to 12VDC on terminal 1 reference to -Vin or open circuit		
Remote On/Off	Off	0 to +1.2 VDC on terminal 1 reference to -Vin		
	Off Idle Current	3mA typical		
Environmental Air		No corrosive gasses permitted		
Casing Material		Plastic resin [UL 94V-0 rated]		
Connections		Screw type connector (standard), Recommended tightening torque 0.5-0.6Nm [4.5-5.35 in-lb], wire stripping length 7-8mm		
Wiring		16-26 AWG [1.5-0.14 mm²]		
Soldering Temperature		Max. 260°C [500°F] / 10 seconds [1.5 mm from casing]		
Safety Standards		UL/cUL 60950-1 2nd edition, CSA C22.2 No. 60950-1-07, 2nd edition		
Agency Approvals		UR/cUR, File No. E198298; CE; Reach; RoHS		

Note: All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.

1-800-633-0405 For the latest prices, please check Aut RHINO DC to DC Converters PSE Series

PSE05-DC12-40,	PSE12-DC12-40,
PSE24-DC12-40,	PSE05-DC24-40
PSE12-DC24-40,	PSE24-DC24-40

Wiring Connection			
Pin	Signal		
1	Remote On/Off*		
2	-Vin (GND)		
3	+Vin (Vcc)		
4	+Vout		
5	NC		
6	-Vout		
7	NC		
8	NC		

* Refer to specifications for voltage requirements M3 x 0.5mm screw size, Typ

PSE05-DC12-60, PSE12-DC12-60, PSE24-DC12-60, PSE48-DC12-60, PSE05-DC24-40, PSE12-DC24-60, PSE24-DC24-60, PSE48-DC24-60

Wiring Connection			
Pin	Signal		
1	Remote On/Off*		
2	-Vin (GND)		
3	+Vin (Vcc)		
4	NC		
5	+Vout		
6	NC		
7	-Vout		
8	NC		

* Refer to specifications for voltage requirements M3 x 0.5mm screw size, Typ



⊕ 2 8	00000	\$
	45678	·
	123	
•	000	\$

For the latest prices, please check AutomationDirect.com. 1-800-633-0405 **RHINO DC to DC Converters PSE Series**

Mounting Bracket

35mm DIN Rail Mounting Bracket					
Part Number	Price	Drawing Link	Weight (lbs)	Description	
PSE-BRKT-2	\$13.00	<u>PDF</u>	0.2	DIN rail mounting bracket for 30W-60W PSE models	

Note: Kit contains interface plate, DIN rail clip and necessary screws.

Installation Example





PSE-BRKT-2

1-800-633-0405 **RHINO DC to DC Isolated Converter**

This isolated DC to DC power supply is used for eliminating ground loops or addressing isolation issues when interfacing to PLC analog I/O modules. The design features handle many types of configuration problems. The <u>FA-DCDC-1</u> is a DIN rail mount, \pm 10VDC, \pm 5VDC isolated power supply, with each output rated at 125mA. The input voltage range is 12-24V DC \pm 15% at approximately 6.7 Watts.



General Specifications					
Part Number'	FA-DCDC-1				
Price	\$116.00				
Drawing Link	PDF				
Input Voltage Range	12V to 24VDC ± 15%				
Input Power '	6.7 Watts, Vin 27.6V, 125mA load each channel				
Output Voltago ² (25°C)	+5V ±1%, 125mA load,-5V ±1% 125mA load				
	+10V ±1% typical, ±2% maximum; -10V ±1% typical, ±2% maximum				
Output Current	125mA [per output voltage]				
Output Ripple	±5V channels: <10mV peak to peak, Vin 10.2V 125mA load on both channels				
	±10V channels: <25mV peak to peak, Vin 10.2V, 125mA load on both channels				
Line Regulation '	±5V channels: <10mV, Vin 10.2V to 27.6V, 125mA load on both channels				
	±10V chamlels. <20mV, Vin 10.2V to 27.0V, 125mA load on both chamlels				
Load Regulation [°]	\pm 10V channels: <20mV, Vin 10.2V, 0 - 125mA load variation				
Isolation	Input to Output: 1500V; ±5V to ±10V: 1500V				
Inrush Current (50ms)	970mA, Vin 10.2V, 125mA load all channels				
Holdup Time (all channels)	30mS minimum, Vin 10V, 125mA load all channels				
Overshoot Protection	No overshoot - Turn on and turn off of Vin				
Input Protection (reverse DC input voltage)	Up to -50V reverse. ± Vin reverse polarity connection.				
Overload Protection	Auto shutdown. Short circuit. Cycle Vin post event				
Output Protection	Indefinite duration. ±5V tied to ±10V				
Peak Line Transient Voltage	100V for 10mS. Voltage spike on input				
Operating Temperature	0 to 60°C [32 to 140°F] full rated				
Storage Temperature	-20 to 70°C [-4 to 158°F]				
Enclosure	Clear Lexan 221-111 with UN5016 transparent blue colorant				
Mounting	35mm wide DIN rail: part # <u>DN-R35S1</u> or <u>DN-R35HS1</u> 1; surface mount				
Connection	3.5 mm screw terminal, 28-16 AWG, 1.7 lb-in torque				
Relative Humidity	5 to 90% [non-condensing]				
Environmental Air	No corrosive gases permitted				
Vibration	MIL STD 810C 514.2				
Shock	MIL STD 810C 516.2				
Noise Immunity	NEMA ICS3-304				
Agency Standards and Approvals	UL/cUL listed, UL File No. E200031, UL508/CSA - C22.2 No. 142-M1987 for ordinary				
- geney etandardo ana rippi or alo	Iocations. Class I, Division 2, Groups A, B, C, D Hazardous Locations				

Notes: ¹ All specifications are over the full operating temperature range [0°C to 60°C] unless stated otherwise.

² "Channel" means Output Voltage. For example: +5V is one channel and -10V is another.

³ All output voltage channels are independent of each other. Changing loading on one will have no effect on the other voltage outputs. ⁴ LINE Regulation: varying the Input Voltage over entire range [12V to 24V ± 15%] and the resultant change in the Output Voltage(s) under worst case load conditions [all output channels drawing 125mA].

⁵ LOAD Regulation: varying the output loads from no-load to a worst case 125mA load and measuring the resultant change in the Output Voltage(s) under a worst case minimum Input Voltage [10.2V] condition.







1-800-633-0405 **RHINO DC to DC Isolated Converter**

Applications





When using a linear potentiometer, the +10V connects to the high side of the potentiometer and the COM1 becomes the zero volt reference. The wiper connects to the analog input. The result is 0 to 10V at the analog module input. (Fig. 1)

Use in a solar/battery application where unregulated 12VDC is available and the analog module requires 24VDC for operation, connect the +10V to +24V module power, connect the -10V to the +5V and the COM2 to the 0V module power. (Fig. 2)





THIS EQUIPMENT IS SUITABLE FOR USE IN CLASS I, DIVISION 2/ZONE 2, GROUPS A, B, C AND D, OR NON-HAZARDOUS LOCATIONS ONLY. WARNING - EXPLOSION HAZARD - SUBSTITUTION OF COMPONENTS MAY IMPAIR SUITABILITY FOR CLASS I, DIVISION 2/ZONE 2. WARNING - EXPLOSION HAZARD - DO NOT CONNECT OR DISCONNECT CONNECTORS OR OPERATE SWITCHES WHILE CIRCUIT IS LIVE UNLESS THE AREA IS KNOWN TO BE NON HAZARDOUS.



Linear Power Supplies -Regulated

Overview

International Power IH series regulated open frame power supplies are designed to operate over a wide range of AC power sources.

Features

- VDE transformer construction
- 100/120/220/230-240 VAC input
- Overvoltage protection on 5V
- outputs
- +/- 0.05% regulation • Chassis notched for AC input
- 2-year warranty





IHB5-3-OVP

		Reg	ulated Linear Powe	r Supplies				
Power Supply		IHB5-3-OVP	IHCC512	IHBB15-1.5	<u>IHDD15-5</u>	IHB24-1.2		
Price		\$77.00	\$173.00	\$120.00	\$236.00	\$80.00		
Drawing		PDF	PDF	PDF	PDF	PDF		
VAC Input		100/120/220/240 VAC, +10 / - 13% Tolerance for 230VAC, Operation is +15 / -10% Frequency range: 47-63 Hz						
VDC Output	Output 1	5VDC @ 3A	5VDC @ 6A	± 12VDC @ 1.7 A	± 12VDC or ± 15VDC @ 5A	24VDC @ 1.2 A		
,	Output 2	-	12 to 15 VDC @ 2.5 A	± 15VDC @ 1.5 A	-	-		
Overvoltage Protect	ion	Provided, factory set @ 6.2 VDC, ± 0.4 VDC	Provided on the 5VDC output		Not provided			
Short Circuit Protect	tion			Automatic foldback				
Overload Protection			Automatic current limit					
Line Regulation		± 0.05% for a 10% line change						
Load Regulation	d Regulation +/- 0.05% for a 50% load change (Derate output current 10% for 50Hz operation.)							
Output Ripple 5.0 mV PK-PK max								
Transient Response	sient Response < 50 µsec per 50% load change							
Operating Temperature 0 to 50°C [32 to 122°F] full rated; derated linearly to 40% at 70°C [158°F]								
Storage Temperature	9		-40	to 85°C [-40 to 185°F]				
Temperature Coeffic	ient	Typical: 0.01% / Degree C; Maximum: 0.03% / Degree C						
Stability		+/- 0.3% for 24 hours after 1 hour warm-up						
Efficiency (typical)			45%			60%		
Vibration			MIL-STD-810G, M Random vibratio	ethod 514.6, Category 1, Pro n 10Hz - 2KHz, 6.15 grams (3	cedure1 3-axis)			
Shock			MIL-STD-81	0G, Method 514.6, Procedure Operating: 20GPK	e 3			
Remote Sensing Provided Provided - both outputs Provided								
EMI / RFI		Inherit low conducted and radiated noise levels EMI: FCC CFR Title 47 part 15 subpart B RFI: EN55022/CISPR22-Level B compatibility						
Humidity		95% relative humidity maximum						
Cooling Method	Doling Method High heat temperature environment, recommended forced air at 100W, 50CFM required at 250W or higher					igher		
Mounting		No restrictions						
Weight (lb [kg])		2 [0.90]	7 [3.17]	4 [1.81]	10 [4.53]	2 [0.90]		
Housing Material				Aluminum				
Connections			Input accepts 0.11	0 x 0.32 fast-ons or solder co	nnection			
Agency Approvals		UR (File # E133338), CE						

To obtain the most current agency approval information, see the Agency Compliance & Certifications Checklist section on the specific part number's web page. Continued on next page.





Linear Power Supplies -Regulated

Continued from previous page

	Regulated Linear Power Supplies							
Power Supply		<u>IHC24-2.4</u>	<u>IHD24-4.8</u>	<u>IHTAA-16W</u>	IHBAA-40W			
Price		\$103.00	\$168.00	\$117.00	\$139.00			
Drawing		PDF	PDF	PDF	PDF			
VAC Input			100/120/220/240 VAC, +10 / - 13% Tolerance for 230VAC, Operation is +15 / -10% Frequency range: 47-63 Hz					
Output 1		24VDC @ 2.4 A	24VDC @ 4.8 A	5VDC @ 2A	5VDC @ 3A			
VDC Output	Output 2	-	-	+12VDC or +15V @ 0.4 A	12VDC @ 1A or 15VDC @ 0.8			
	Output 3	-	-	-12 VDC or -15VDC @ 0.4 A or -5V @ 0.4 A	12VDC @ 1A, or 15VDC @ 0.8 A or 5V @ 0.4 A			
Overvoltage Protection		Not	provided	Provided on the	ne 5VDC output			
Short Circuit Protection			Au	tomatic foldback				
Overload Protection			Auto	omatic current limit				
Line Regulation			± 0.05%	for a 10% line change				
Load Regulation			+/- 0.05% for a 50% load change (Derate output current 10% for 50Hz operation.)					
Output Ripple		5.0 mV PK-PK max						
Transient Response		< 50 µsec per 50% load change						
Operating Temperature		0 to 50°C [32 to 122°F] full rated; derated linearly to 40% at 70°C [158°F]						
Storage Temperature		-40 to 85°C [-40 to 185°F]						
Temperature Coefficient		Typical: 0.01% / Degree C; Maximum: 0.03% / Degree C						
Stability		+/- 0.3% for 24 hours after 1 hour warm-up						
Efficiency (typical)		45% / 55% 60% 45%						
Vibration			MIL-STD-810G, Metr Random vibration ?	10d 514.6, Category 1, Procedure 1 10Hz - 2KHz, 6.15 grams (3-axis)				
Shock			MIL-STD-810G Oj	i, Method 514.6, Procedure 3 perating: 20GPK				
Remote Sensing				Provided				
EMI / RFI	EMI / RFI EMI / RFI EMI / RFI EMI = State of the state of							
Humidity		95% relative humidity maximum						
Cooling Method		High heat temperature environment, recommended forced air at 100W, 50CFM required at 250W or higher						
Mounting				No restrictions	1			
Weight (lb [kg])		4 [1.81] 7.5 [3.40] 2 [0.90] 5 [2.26]						
Housing Material		Aluminum						
Connections			Input accepts 0.110 x	0.32 fast-ons or solder connection	1			
Agency Approvals UL (File # E133338), CE								

To obtain the most current agency approval information, see the Agency Compliance & Certifications Checklist section on the specific part number's web page.



Linear Power Supplies -Regulated

Input Jumpering and Fusing Requirements

IHB5-3-OVP					
For use at	100VAC	120VAC	220VAC	230/240VAC	
Jumper	1&3, 2&4	1&3, 2&4	2&3	2&3	
Apply AC	1&5	4&1	1&5	4&1	
Max Current/Fuse Rating	0.5 A		0	.25 A	

<u>IHBB15-1.5</u>					
For use at	100VAC	120VAC	220VAC	230/240VAC	
Jumper	1&3, 2&4	1&3, 2&4	2&3	2&3	
Apply AC	1&5	1&4	1&5	1&4	
Max Current/Fuse Rating	1A 0.5 A		.5 A		

<u>IHB24-1.2</u>					
For use at	100VAC	120VAC	220VAC	230/240VAC	
Jumper	1&3, 2&4	1&3, 2&4	2&3	2&3	
Apply AC	1&5	4&1	1&5	1&4	
Max Current/Fuse Rating	0.75 A 0.375 A		375 A		

IHD24-4.8					
For use at 100VAC 120VAC 220VAC 230/240VA				230/240VAC	
Jumper	1&3, 2&4	1&3, 2&4	2&3	2&3	
Apply AC	1&5	1&4	1&5	1&4	
Max Current/Fuse Rating	2A		2A 1A		1A

IHBAA-40W					
For use at	100VAC	120VAC	220VAC	230/240VAC	
Jumper	1&3, 2&4	1&3, 2&4	2&3	2&3	
Apply AC	1&5	1&4	1&5	1&4	
Max Current/Fuse Rating	1.5 A 0.75 A		.75 A		

Negative output @ -5VDC @ 0.4 A, Jumper E1 and E2 & Reset R26. For \pm 15VDC, cut Jumpers VW1 and VW2

IHCC512					
For use at	100VAC	120VAC	220VAC	230/240VAC	
Jumper	1&3, 2&4	1&3, 2&4	2&3	2&3	
Apply AC	1&5	1&4	1&5	1&4	
Max Current/Fuse Rating	3A 1.5 A		.5 A		

<u>IHDD15-5</u>					
For use at	100VAC	120VAC	220VAC	230/240VAC	
Jumper	1&3, 2&4	1&3, 2&4	2&3	2&3	
Apply AC	1&5	1&4	1&5	1&4	
Max Current/Fuse Rating	3A 1.5 A		.5 A		

For +/-12VDC @ 5A, move wires at XFMR Pins B-B to A-A & adjust R26 & R29

<u>IHC24-2.4</u>					
For use at 100VAC 120VAC 220VAC 230/240VAC					
Jumper	1&3, 2&4	1&3, 2&4	2&3	2&3	
Apply AC	1&5	4&1	1&5	4&1	
Max Current/Fuse Rating	1.5 A 0.75 A		75 A		

IHTAA-16W									
For use at 100VAC 120VAC 220VAC 230/240VAC									
Jumper	1&3, 2&4	1&3, 2&4	2&3	2&3					
Apply AC	1&5 1&4 1&5			1&4					
Max Current/Fuse Rating	0.75 A		0.375 A						

Negative output @ -5VDC @ 0.4 A, Jumper E1 and E2 & Reset R25



Linear Power Supplies -Unregulated

Overview

International Power IP500U series unregulated power supplies are designed for low-cost, high-current applications when full regulation is not required. This rugged, highly reliable power supply line is ideal for applications such as powering solenoids, relays, DC motors, battery chargers, and DC to DC converters.

Features

- High surge current capabilities
- Isolated AC inputComputer-grade capacitors
- Floating output
- Full rated to 55°C [131°F]
- Open frame construction
- Secondary fuse protection
- 50A, 200V full bridge rectifier
- 2-year warranty





IP500U36



Unregulated Linear Power Supplies									
Power Supply	<u>IP500U36</u>	<u>IP500U48</u>	<u>IP500U75</u>						
Price	\$350.00	\$350.00	\$364.00						
Drawing	PDF	PDF	PDF						
VAC Input		100/240 VAC, +10%, (Primary taps provided) Frequency range: 47-63 Hz							
VDC Output @ nominal line	36.1 VDC @ 13.3 A full load 38.2 VDC @ half load 42.8 VDC @ 0A	48.8 VDC @ 13.3 A full load 52.8 VDC @ half load 56.6 VDC @ 0A	74.8 VDC @ 6.6 A full load 78.2 VDC @ half load 85.5 VDC @ 0A						
DC Connections	-Out (DC return	+Out 0.250 x 0.032 fast-on at fuse block n) 10-32 screw/solder terminal at minus side c	of the capacitor						
Efficiency (typical)		75% to 80% full load							
Short Circuit Protection	Output fused @ 15A								
Line Regulation	Equal to % line change								
Load Regulation @ nominal line	9% for a 50% to 100% load change (Derate output current for 10% for 58 Hz operation)								
Output Ripple	At full load 3% RMS max								
Operating Temperature	0 to 55°C [32 to 131°F] full rated; derated linearly to 40% at 70°C [158°F]								
Storage Temperature		-40 to 95°C [-40 to 203°F]							
EMI / RFI		Inherit low conducted and radiated noise levels EMI: FCC CFR Title 47 part 15 sub-part B RFI: EN55022/CISPR22-Level B compatibility							
Vibration	MIL-S Ra	STD-810G, Method 514.6, Category 1, Proced ndom vibration 10Hz - 2KHz, 6.15 grams (3-a:	lure 1 xis)						
Shock	MIL-STD-810G, Method 514.6, Procedure 3 Operating: 20GPK								
Humidity		95% relative humidity maximum							
Cooling Method	High heat temperature environ	ment, recommended forced air at 100W, 50C	FM required at 250W or higher						
Mounting		No restrictions							
Weight (lb [kg])		18 [8.16]							
Housing Material		Aluminum							
Agency Approvals		UR (File # E133338), CE							

To obtain the most current agency approval information, see the Agency Compliance & Certifications Checklist section on the specific part number's web page.

Input Jumpering and Fusing Requirements

<u>IP500U36, IP500U48, IP500U75</u>								
For use at 108VAC 120VAC 132VAC 216VAC 240VAC 26								
Jumper	1&5, 2&6	1&5, 3&7	1&5, 4&8	2&5	3&5	4&5		
Apply AC	1&2	1&3	1&4	1&6	1&7	1&8		
Max Current/Fuse Rating	8A	8A	8A	4A	4A	4A		

www.automationdirect.com

Power Supplies: Open Frame

The most economical choice for 24 VDC power

(94mm)

Â

2 5"

(63.5mm)

90 88



These power supplies are especially useful when an inexpensive external supply is required.

The <u>FA-24PS</u> compact switching power supply accepts 120/240VAC or 100-240VDC input and provides up to 1.25A (30 watts) output current at 24VDC.

The <u>FA-24PS-90</u> supplies 3.7 A (90 watts) at 24VDC and its input is jumper selectable between 120 or 240VAC.





	General Specifications								
Part Number	<u>FA-24PS</u>	FA-24PS-90							
Price	\$73.00	\$101.00							
Drawing Link	PDF	PDF							
Input Voltage Range	100-240VAC/DC	95-130VAC or 190-264VAC, jumper selectable							
Input Voltage Frequency	47 to 63Hz	47 to 63Hz							
Input Power	40VA	112VA							
Output Voltage	24VDC ±5%	24VDC ±5%							
Output Current	1.25 A maximum continuous	3.7 A maximum continuous, subject to derating							
Output Ripple	± 200mV maximum	± 200mV maximum							
Temperature Rating	0 to 60°C full rated	0 to 30°C full rated; derate current 1.1% per degree above 30°C; 60°C max							
Transient Response	Output stays within 1% for a load current change from 75% [0.9A] to either 50% [0.6A] or 100% [1.25A]	Output stays within 1% for a load current change from 75% [2.8A] to either 50% [1.8A] or 100% [3.7A]							
Mounting	DIN rail, 35mm wide; Models DN-R35S1 or DN-R35HS1	DIN rail, 35mm wide; Models <u>DN-R35S1</u> or <u>DN-R35HS1</u>							
Screw Terminals	Wire Size: 18-12AWG Rec. Screw Torque: 4.4 in•lb or 0.5 Nm	Wire Size: 18-12AWG Rec. Screw Torque: 4.4 in•lb or 0.5 Nm							
Insulation Resistance	10 MΩ at 500V minimum	10 MΩ at 500V minimum							
Dielectric Withstand Voltage	L or N Input to Output: 500 V min; Ground Input to Output: 250V min	L or N Input to Output: 500 V min; Ground Input to Output: 250V min							
Brown-out Protection	Provides temporary regulation down to 85VAC at full load	Provides temporary regulation at 95VAC at full load							
Input Protection	The power supply has an internal fuse for the AC input line, rated at 3.15 amps; not user replaceable; external input fusing required.	The power supply has an internal fuse for the AC input line, rated at 3.15 amps; not user replaceable; external input fusing required.							
Overload Protection	Protects power supply from overload and short circuit conditions. Includes automatic recovery upon removal of the overload condition	Protects power supply from overload and short circuit conditions. Includes automatic recovery upon removal of the overload condition							
Inrush Current (2mS)	115V <12.5 A / 230VAC <13.9 A	115VAC <79A / 230VAC <37A							
Overshoot Protection	No overshoot on turn-on or turn-off	No overshoot on turn-on or turn-off							
Agency Standards and Approvals	UL 508; Class I, Div 2, Groups A, B, C, D hazard	dous locations; CUL, UL Listed File No. E200031							



DC Terminals (24VDC)

DIN Rail

Brackets

3.5"

(89mm)

Power Supplies





787-2861-108-020

Single Channel Electronic Circuit Breakers

Features

- Space-saving ECB with one channel
- This model safely and reliably stops power in the event of an overload or if it short circuits on the secondary side
- The switch on capacity is >50,000 μF
- Minimizes wiring via two voltage outputs and maximizes commoning options in both input and output sides
- Switch the breaker on or off via remote input, or a local switch
- Prevents power supply overload due to total inrush current thanks to time delayed switching on during interconnected operation
- Bus up to 10 units together with the use of Jumper Bars

Single Channel Electronic Circuit Breaker									
Part Number	Price	Quantity Per Pack	Nominal Output Current	Mounting	Connection	Wiring	Drawing Link		
787-2861-100-000	\$59.00	1	1A [Fixed Setting]		Push-In CAGE CLAMP®	Diagram 1	PDF		
787-2861-200-000	\$59.00	1	2A [Fixed Setting]				PDF		
787-2861-400-000	\$59.00	1	4A [Fixed Setting]				PDF		
787-2861-600-000	\$59.00	1	6A [Fixed Setting]	35mm DIN rail			PDF		
787-2861-800-000	\$59.00	1	8A [Fixed Setting]				PDF		
787-2861-108-020	\$67.00	1	1 – 8A [Adjustable]				PDF		

Single Channel Electronic Circuit Breaker Accessories								
Part Number	Price	Description	Quantity Per Pack	Color	Nominal Current	Drawing Link		
<u>60432948</u>	\$12.00	10 Dele lumner Der	5	Blue	104	PDF		
60432947	\$12.00	10 Pole Jumper Bar	5	Red	IðA	PDF		





Single Channel Electronic Circuit Breakers

Single Channel ECB Specifications					
Nominal Input Voltage	24VDC				
Input Voltage Range	18 – 30VDC				
Total Number of Channels	1				
Nominal Output Voltage	24VDC				
Output Voltage Range	18 – 30VDC				
Voltage Drop	less than or equal to 50mV				
Nominal Output Current	See Selection Chart				
Trip Time	4ms to 100s [Load-Dependent]				
Switch-On Capacity	50,000uf per channel				
Switch-On Behavior	Time-delayed channel switching [Load-dependent, minimum]				
Active Current Limitation	No				
	1 x Status LED [green/yellow/red/blue]				
Signaling	1x Control input				
Operation Status Indicator	See LED Operation Table				
Remote Input	18 to 30VDC signal, switches on/off and resets the channel				
Fuse Protection	15A [Internal Fuse]				
Isolation Voltage	DC 0.5 kV				
Protection Type	IP20 [per EN 60529]				
Reverse Voltage Protection	No				
Transient Suppression	Suppressor diode [33V]				
Series/Parallel Operation of Single Channels	Not Permitted				
Tightening Torque	N/A				
Weight g [oz]	3.79 [0.0083]				
Connectors	Push-In CAGE CLAMP©, Solid Conductor 28-14 AWG, Stranded Conductor 22-14 AWG				
Agency Approvals	EN 61000-6-2; EN 61000-6-3; UL 61010-2-201; CE; RoHS				
Surrounding Air Temperature (Operation)	-25 to 70°C [-13 to 158°F]				
Surrounding Air Temperature (Storage)	-40 to 85°C [-40 to 185°F]				
Relative Humidity	10 to 95% [no condensation permissable]				
Derating	No derating				
Pollution Degree	2				

LED Operation							
Explanation	Status LED						
Initialization of the device(boot routine)	Off						
Channel switched ON	Green						
Channel switched ON Load current > 90% nominal current	Green flashing [1Hz]						
Channel switched ON Load current > 100% nominal current (overload)	Green flashing [5Hz]						
Channel switched OFF manually or through input S1	Red						
Channel tripped Wait for temperature to return to normal	Red flashing [1Hz]						
Channel tripped Temperature returned to normal. Channel can be switched ON again	Yellow flashing [1Hz]						
Channel tripped Undervoltage with simultaneous overcurrent	Blue flashing [1Hz]						
Channel tripped, undervoltage	Blue flickering [1Hz]						
Channel tripped,overvoltage	Red flickering [1Hz]						
Device error, wiring error, feedback voltage	Red/blue flashing [1Hz]						







Overview

WAGO's 24 VDC, single-channel ECBs improve operations and offer significant cost savings. The 787-3861 series has the ability to configure the S2 output on all variants and to report 7 different states including triggered or manually switched OFF along with early load warnings. All models have an easy to access reset button. Adjustable current models are easily programmed with discrete settings.

Single-Channel Electronic Circuit Breakers 787-3861 Series

Features

- Space-saving 6mm wide one-channel ECB
- This series reliably removes power in the event of an overload or short circuit on the secondary side
- Two voltage inputs and two voltage outputs maximize commoning options and reduce wiring
- Switch the breaker ON or OFF via remote input, or a local switch
- Time-delayed activation during interconnected operation prevents overloads due to inrush current



787-3861/004-020

S	Single-Channel Electronic Circuit Breakers 787-3861 Series Selection Chart									
Part Number	Price	Quantity Per Pack	Amperage Rating	Voltage	Voltage Drop	Trip Time	NEC Class 2	Wiring	Weight grams	Drawing Link
<u>787-3861/004-020</u>	\$35.00		Adjustable 0 5 44	0.5-4A 18-30 VDC	≤40mV (0.5A) ≤80mV (1A) ≤120mV (1.5A) ≤160mV (2A) ≤200mV (2.5A) ≤240mV (3A) ≤280mV (3.5A) ≤20mV (4A)	10ms to 90s	No	Diagram 1	55.7	<u>PDF</u>
<u>787-3861/004-1020</u>	\$36.00					(load-dependent)	Yes	Diagram 1	55.7	<u>PDF</u>
787-3861/050-000	\$32.00		0.54		<10m\/		No	Diagram 1	55.6	PDF
787-3861/050-1000	\$33.00		0.3A			4ms to 100s (load-dependent)	Yes	Diagram 1	55.6	PDF
<u>787-3861/100-000</u>	\$32.00		14		<90m1/		No	Diagram 1	55.6	PDF
<u>787-3861/100-1000</u>	\$33.00				<u>=00111</u>		Yes	Diagram 1	55.6	PDF
<u>787-3861/108-020</u>	\$35.00	1	Adjustable 1-8A		≤80mV (1A) ≤160mV (2A) ≤240mV (3A) ≤150mV (5A) ≤150mV (5A) ≤180mV (6A) ≤210mV (7A) ≤240mV (8A)	10ms to 90s (load-dependent)	No	Diagram 1	53.0	<u>PDF</u>
787-3861/200-000	\$32.00		24		<160m)/		No	Diagram 1	55.6	PDF
787-3861/200-1000	\$33.00		2A				Yes	Diagram 1	53.0	PDF
787-3861/400-000	\$32.00		4.0		<220m1/	4ms to 100s	No	Diagram 1	55.6	PDF
787-3861/400-1000	\$33.00		4A		≥s∠umv	(load-dependent)	Yes	Diagram 1	53.0	PDF
787-3861/600-000	\$32.00		6A		≤180mV		No	Diagram 1	55.6	PDF
787-3861/800-000	\$32.00		8A		≤ 240 mV		No	Diagram 1	55.6	PDF

Wiring Diagram

Diagram 1



www.automationdirect.com

1-800-633-0405



Single-Channel Electronic Circuit Breakers 787-3861 Series

Single-Channel Electronic Circui	t Breakers 787-3861 Series Specifications
Nominal Input Voltage	24 VDC
Input Voltage Range	18-30 VDC
Total Number of Channels	1
Nominal Output Voltage	24VDC
Output Voltage Range	18-30 VDC
Switch-On Behavior	Time-delayed channel switching (load dependent, min. 0 ms/max. 500ms)
Current Limitation	No
Signaling	1 x Status LED (green/yellow/red) 1 x Signal output (18- 30 VDC, max.0.015 A), Default setting: triggered
Operation Status Indicator	Green LED (channel OK) Red LED (channel switched OFF)
Remote Input	1 x Control input (15-30 VDC) (active high); 0-5 VDC (active low); max. 0.015 A)
Isolation Voltage	DC 0.5 kV
Protection Type	IP20 (per EN 60529)
Reverse Voltage Protection	No
Transient Suppression	Suppressor diode (33V)
Series/Parallel Operation of Single Channels	Not permitted
Tightening Torque	N/A
Connectors	Push-In CAGE CLAMP®, Solid Conductor 26-14 AWG [0.08-2.5 mm²], Stranded Conductor 22-14 AWG [0.34-2.5 mm²]
Mounting	35mm DIN rail
Surrounding Air Temperature (Operation)	-25 to 70°C [-13 to 158°F]
Surrounding Air Temperature (Storage)	-40 to 85°C [-40 to 185°F]
Relative Humidity	10 to 95% (no condensation permissable)
Derating	No derating
Pollution Degree	2
Agency Approvals	cULus File E175199,, CE, UKCA

To obtain the most current agency approval information, see the Agency Approval Compliance & Certifications Checklist section on the specific part number's web page.

LED Operation						
Explanation	Status LED					
Initialization of the device(boot routine)	Off					
Channel switched ON	Green					
Channel switched ON Load current > 90% nominal current	Green flashing (1Hz)					
Channel switched ON Load current > 100% nominal current (overload)	Green flashing (5Hz)					
Channel switched OFF manually or through input S1	Red					
Channel tripped - Wait for temperature to return to normal	Red flashing (1Hz)					
Channel tripped - Temperature returned to normal Channel can be switched ON again	Yellow flashing					
Channel tripped - Undervoltage	Red/Yellow flashing (1Hz)					
Channel tripped - Overvoltage	Red/Yellow flashing (5Hz)					
Device error, wiring error, feedback voltage	Red/Yellow/Green One after the other (1Hz)					

1-800-633-0405



Single-Channel Electronic Circuit Breakers 787-3861 Series

Overview

Distribution modules allow expansion of terminals from the 787-3861 series singlechannel electronic circuit breakers. Models available for Vout, GND, or both. Can be used with WAGO push-in jumpers for easy installation.



787-3861/000-1000

Potential Distribution Modules									
Part Number	Price	Quantity Per Pack	Amperage Rating	Channels	Operating Voltage	Mounting	Wiring	Weight grams	Drawing Link
787-3861/000-1000	\$11.00		20A	(8) 0 VDC	0 VDC		Diagram 1	55.7	PDF
787-3861/000-2000	\$11.00	1	20A	(8) 24 VDC	24 VDC	35mm DIN	Diagram 2	55.7	PDF
787-3861/000-3000	\$11.00		20A	(4) 0 VDC/(4) 24 VDC	0-24 VDC	- Tall	Diagram 3	55.7	PDF

Wiring Diagrams



Specifications					
Limiting Continuous Current	20A; 15A (UL)				
Protection Type	IP20 (per EN 60529)				
Tightening Torque	N/A				
Connectors	Push-In CAGE CLAMP®, Solid Conductor 26-14 AWG [0.08-2.5 mm ²], Stranded Conductor 22-14 AWG [0.34-2.5 mm ²]				
Mounting	35mm DIN rail				
Surrounding Air Temperature (Operation)	-25 to 70°C [-13 to 158°F]				
Surrounding Air Temperature (Storage)	-40 to 85°C [-40 to 185°F]				
Relative Humidity	10 to 95% (no condensation permissable)				
Pollution Degree	2				
Agency Approvals	cULus File E175199,, CE, UKCA				

To obtain the most current agency approval information, see the Agency Approval Compliance & Certifications Checklist section on the specific part number's web page.

1-800-633-0405 **Modular Circuit Protectors REX Series** 2010/ ENGINEERING TECHNOLOGY

Features

- Modular design using power supply, overcurrent protection, and power distribution modules
- No tools required for assembly
- Circuit protection via electronic trip curve
- Slim 12.5 mm module width
- 1 to 10A fixed and adjustable operating current
- Integral fail-safe element, adjusted to max. current rating
- Circuit protection rated for capacitive loads up to 20,000 μF
- Manual ON/OFF/reset switch
- LED status indication with auxiliary contact output
- Push-in terminal connections with release buttons



Modular Circuit Protectors											
Part Number	Price	Module Type	Number of Channels	Operating Current	Voltage Rating	Operating Voltage	Input Voltage	Output Voltage	Weight g [oz]	Drawing Link	Agency Approvals
Entrance Modules											
<u>EM-T01-001-24-40A</u> *	\$25.50	Mains supply	_	40A	24VDC	24VDC	24VDC	-	52 [1.83]	<u>PDF</u>	CE, UL Recognized E320024
<u>EM-T00-000-GND-40A</u>	\$11.00	Ground supply 0V	_	40A		0VDC	0VDC	-	40 [1.41]	PDF	CE, UL Recognized E335289
Potential Modules											
<u>PM-T01-00-LOAD-20A</u>	\$29.50	Load distribution	8	20A		24VDC	24VDC	24VDC	52 [1.83]	<u>PDF</u>	CE, UL Recognized E335289
<u>PM-T03-00-GND-20A</u>	\$27.00	Ground distribution	8	20A	24VDC	0VDC	0VDC	0VDC	52 [1.83]	PDF	
Circuit Protector Modules											
REXD-TE2-24-1A-10A	\$53.50	Overcurrent protection	2 independent	Adjustable 1-10A	24VDC	_	_	24VDC	62 [2.18]	PDF	CE, UL Recognized E320024, UL Listed E492388
<u>REX-TA1-24-10A</u>	\$41.00		1	10A		-	-		57 [2.01]	<u>PDF</u>	
<u>REX-TA1-24-8A</u>	\$41.00		1	8A		_	_		57 [2.01]	<u>PDF</u>	
<u>REX-TA2-24-6A</u>	\$45.50		2 independent	6A		_	-		58 [2.04]	PDF	
<u>REX-TA2-24-4A</u>	\$45.50		2 independent	4A		_	_		58 [2.04]	PDF	
<u>REX-TA2-24-3A-N</u>	\$57.00		2 independent	3A		-	_		58 [2.04]	PDF	CE, UL Recognized E320024 UL Listed E492388, NEC Class 2
<u>REX-TA2-24-2A</u>	\$45.50		2 independent	2A		_	_		58 [2.04]	PDF	

* 1 EM-T01-001-24-40A is required for each system.

Maximum 16 modules or 40Å max per system.



Application Example





1-800-633-0405 **Modular Circuit Protectors REX Series**

Basic Architecture





Full-Featured Architecture





⑧ 時承 REX Series Modular Circuit Protectors

Specifications

Specifications				
Housing Material	Wellamid			
Mounting	Symmetrical rail to EN 60715- 35 x 7.5, horizontal			
Ambient Temperature T _u	-25 to 60°C [-13 to 140°F] (Without condensation, cf. EN 60204-1)			
Storage Temperature	-40 to 70°C [-40 to 158°F]			
Operating Temperature	5 to 60°C [41 to 140°F]			
Humidity	96 hrs / 95% RH/40°C to IEC 60068-2-78-Cab climate class 3K3 to EN 60721			
Altitude	2,000m above sea level 3,000m above sea level up to +55 °C 4,000m above sea level up to +50 °C			
Operation Pressure	4 bar above atmospheric pressure			
Vibration	5g test to IEC 60068-2-6, test Fc			
Degree of Protection (IEC 60529, DIN VDE 0470)	IP20 EM and PM modules IP30 REX modules			
EMC Requirements (EMC Directive, CE logo)	Noise emission EN 61000-6-3 Susceptibility: EN 61000-6-2			
Insulation co-ordination (IEC 60934)	0.5 kV / pollution degree 2			
Dielectric Strength (max.)	30 VDC (load circuit)			
Insulation Resistance (OFF condition)	N/A, only electronic disconnection			
Agency Approvals	See selection chart table			

To obtain the most current agency approval information, see the Agency Compliance & Certifications Checklist section on the specific part number's web page.
BETAM Modular Circuit Protectors REX Series

EM-T01-001-24-40A Overview

A 24VDC switch-mode power supply powers the <u>EM-T01-001-24-40A</u> supply module, which distributes the power through the backplane to the circuit protection modules. The supply module also provides an auxiliary, dry contact status output to signal fault conditions to a connected device such as a PLC input protector, e.g. to the PLC input.

Specifications

EM-T01-001-24-40A Specifications								
Operating Voltage U _B	24VDC 18-30VDC							
Operating Current I _B (max)	40A							
Reverse Polarity Protection	Yes							
Signaling	Only <u>EM-T01-001-24-40A</u>							
Quiescent Current I _o	Typically 10mA							
Potential-free Auxiliary (max) (Change over contact)	30VDC / 0.5 A min., 10V / 1mA							
Group Signaling contact - (13) / (14)	Auxiliary contact, make contact							
Group Signaling Normal Conditions	Auxiliary contact closed based on all protection modules - when ON, load output connected - when OFF, load output disconnected							
Group Signaling Fault Conditions	Auxiliary contact open based on one or more protection modules - after overload or short circuit trip - after undervoltage release of operating voltage in ON condition with autoreset - at no operating voltage U _B in supply module							
Insulation Co-ordination	0.5 kV / pollution degree 2							
Power Failure Buffering Time	10ms max							
LINE + Push-in Terminal PT 10	0.5 to 10mm² flexible 24-8 AWG rigid stripping length 18mm							
0V / 13 / 14 Push-in Terminal PT 2.5	0.14 to 2.5 mm² flexible 24-24 AWG rigid stripping length 8 to 10mm							

(1) EM-T01-001-24-40A is required for each system.

Maximum 16 modules or 40A max per system.

Circuit protectors can be mounted side-by-side: REX-TA1-24-xx, REX-TA2-24-xx or REXD-TE2-24-1A-10A

Wiring Diagram

EM-T01-001-24-40A



For the latest prices, please check AutomationDirect.com.

1-800-633-0405

Modular Circuit Protectors REX Series

Specifications

Specifications										
Part Number	<u>PM-T01-00-LOAD-20A</u>	<u>PM-T03-00-GND-20A</u>								
Operating Voltage U _B OV	24VDC 0-30VDC									
Operating Current I _B (max)	40A	20A	20A							
Line Terminal	0V - GND	NA	0V - GND							
Insulation Co-ordination	NA	0.8 kV / pollution degree 2	NA							
LINE +	Push-in terminal PT 10 0.5 to 10 mm² flexible 24-8 AWG rigid stripping length 18mm	Push-in terminal PT 2.5 0.14 to 2.5 mm² flexible 24-14 AWG rigid stripping length 8 to 10mm	Push-in terminal PT 2.5 0.14 to 2.5 mm² flexible 24-14 AWG rigid stripping length 8 to 10mm							

Wiring Diagrams









REX Series Modular Circuit Protectors

Specifications

Specifications										
Part Number	<u>REXD-TE2-24-1A-10A</u>	REX-TA1-24-xx	REX-TA2-24-xx	<u>REX-TA2-24-3A-N</u>						
Operating Voltage U _B		24 VDC (18 to 30 VDC)								
Closed Circuit Current	1A-10A ON condition: typically 12mA	ON condition: typically 5mA	ON cc typica	ndition: Ily 8mA						
Reverse Polarity Protection		Yes								
Power Failure Buffering Time	Up to 10ms									
Rated Current	1A – 10A condition upon delivery max. current rating 8A, 10A 2 A/2A, 4A/4A, 6A/6A									
LED Status	Greer Re - after undervo OFF: Device switch	Green: Load circuit connect h/orange blinking: load current warning Orange: overload or short circuit until o ed: - after disconnection due to overload oltage release of operating voltage in C ned off by means of ON/OFF momental	ed limit reached 90 % lisconnection d or short circuit N condition with auto-reset y switch or no operating volt	age						
Load Output		Power MOSFET switching output (plu	s switching)							
Load Current Warning Limit (I _w Limit)		Typically 0.9 x I_N								
Hysteresis		Typically 5%								
Overload Current		$\begin{array}{c} \text{Disconnection } (I_{\text{UL}}) \\ \text{typically } I_{\text{OL}} : I_{\text{N}} \times 1.05 \ t_{\text{OL}} : 3, \\ \text{typically } I_{\text{OL}} : I_{\text{N}} \times 1.35 \ t_{\text{OL}} : 0, \\ \text{With trip times } (t_{\text{UL}}) \ \text{typically } I_{\text{OL}} : I_{\text{N}} \times 2, \\ \text{typically } I_{\text{OL}} : I_{\text{N}} \times 2.50 \ t_{\text{OL}} : 0.01 \\ \text{Short circuit} \\ \text{typically at short circuit} (I_{\text{SC}}) \ t_{\text{SC}} : 0 \end{array}$	s 5s 00 t _{ol} : 0.1s 2 s .002 s²)							
Voltage Drop I _N	1A typically 30mV, 70% typically 28mV 2A typically 39mV, 70% typically 34mV 3A typically 48mV, 70% typically 40mV 4A typically 57mV, 70% typically 46mV 5A typically 66mV, 70% typically 52mV 6A typically 74mV, 70% typically 55mV 7A typically 83mV, 70% typically 55mV 8A typically 92mV, 70% typically 71mV 9A typically 101mV, 70% typically 77mV 10A typically 110mV, 70% typically 83mV	2A (CL2) typ 3A (CL2) typ 4A typical 6A typicall 8A typicall 10A typical	ically 110mV, 70% typically 8 cally 130mV, 70% typically 9 y 115mV, 70% typically 80m / 170mV, 70% typically 110m / 160mV, 70% typically 105m y 180mV, 70% typically 120r	0mV 0mV V าV าV าV						
Fail-safe Element Integral Blade Fuse Adjusted to Related Current Rating I _N		8A fail-safe 8A 10A fail-safe 10A 2A/2A (CL2) fail-safe 2A/2 3A/3A (CL2) fail-safe 4A/4, 4A/4A fail-safe 4A/4A 6A/6A fail-safe 6.3 A / 6.3 / 1A-10A fail-safe 16A	A 4							
Operating Voltage Monitoring re Undervoltage		OFF at typically U _B < 16.0 ON at typically U _B > 19.0 hysteresis typically 2V with automatic OFF and ON swi	V / tching							
ON Delay With Power ON	Channel 1: typically 1,500ms Channel 2: typically 1,600ms	Cha Cha	annel 1: typically 100ms annel 2: typically 200ms							
ON Delay When Switching on With ON/OFF Switch		Channel 1: typically 5ms Channel 2: typically 100ms	8							
ON Delay After Undervoltage		Channel 1: typically 5ms Channel 2: typically 5ms								
Disconnection Of Load Current	Mar Afte	nually on the device with the ON/OFF r er an overload / short circuit disconnec (no automatic reset) Temporarily at undervoltag At no operating voltage	nomentary switch ion with storage e							

Continued on following page.

For the latest prices, please check AutomationDirect.com.



Continued from previous page

Specifications										
Part Number	REXD-TE2-24-1A-10A REX-TA1-24-xx REX-TA2-24-xx REX-TA2-24-xx									
Switch-on of Load Circuit		Momentary switch ON/OFF: Device can only be switched on when operating voltage is applied. Applying operating voltage: The device starts up with the condition last stored.								
Reset Function	A blocked load output	t (blocked by overload / short circuit)	can externally be reset by the ON/OF	FF momentary switch.						
Leakage Current in Load Circuit if OFF Condition		Typicall	y < 1mA							
Capacitive Loads	Depe	Up to 20 ending on cable attenuation, power su	l,000 μF: μpply used, load current and current r	rating						
Free-wheeling Diode		External free-wheeling circuit at indu	uctive load (rating according to load)							
Parallel Connection of Several Load Outputs		Not a	lowed							
Status Output SM		Status indicator	in REX system							
Electrical Data	Group	Minus switchin signaling is implemented in connection	g signal output on with <u>EM-T01-001-24-40A</u> supply n	nodule.						
Terminals LOAD+		Push-in terminal PT 2.5: 0 to 24-14 A Stripping leng	o 14mm² [2 to 5mm² flexible] WG rigid _t th 8 to 10mm							

Inquiry Mode <u>REXD-TE2-24-1A-10A</u>

Use Inquiry Mode to determine the current setting of the REXD-TE2-24-1A-10A module. Inquiry Mode is possible in all operating conditions (ON, OFF, UNDERVOLTAGE and TRIPPED).

- 1. Press and hold the button for 2 to 5 seconds to enter inquiry mode.
- 2. When the button is released, the LED will turn RED for 333ms to indicate that the module is in Inquiry Mode.
- 3. Then the LED will blink ORANGE at a pulse rate of 1Hz to indicate the current setting (number of pulses = current setting).
- 4. After the last pulse, the LED will turn RED for 333ms and flash the current setting again.
- 5. Press the button or wait for five indication cycles to exit Inquiry Mode.

Adjustment Mode <u>REXD-TE2-24-1A-10A</u>

Use Adjustment Mode to set the REXD-TE2-24-1A-10A module to the desired current setting. Adjustment Mode is possible in all operating conditions (ON, OFF, UNDERVOLTAGE and TRIPPED).

- 1. Press and hold the button for at least 5 seconds to enter Adjustment Mode.
- 2. When the button is released, the LED will turn RED for 333ms to indicate that the module is in Adjustment Mode.
- 3. The LED will blink GREEN at a pulse rate of 0.6 Hz for the desired current setting (number of pulses = current setting).
- 4. Once the maximum value is indicated, the LED will turn RED for 333ms and repeat the cycle.

5. To select a current setting, wait for the LED to flash the desired number of times, then press the button (for example, pressing the button after seven pulses will change the setting to 7A).

6. Adjustment Mode will be exited when a setting is selected or if no selection is made after five indication cycles.

1-800-633-0405 **Modular Circuit Protectors REX Series** 2이(~ ENGINEERING TECHNOLOGY

Typical Time/Current Characteristic

(T_{amb} = +23°C, UB - 24VDC)



Basic Trip Curve and Schematic Diagram REX-T



... times rated current trip curve REX-T

Temperature Factor / Continuous Duty

The time/current characteristic depends on the ambient temperature. To determine the maximum load current, please multiply the current rating with the temperature factor and consider the factor for side-by-side mounting.

Temperature Factor Table										
Ambient Temperature [°C]	0	10	23	40	50	60				
Temperature Factor	1	1	1	0.95	0.90	0.85				

Note:

When mounted side-by-side, the devices can carry a maximum of 80% of their rated load or a different rating must be selected.

With high temperatures, the load current warning threshold "warn limit typically 0.9 x IN" will be reduced in accordance with the temperature factor.

Selection of current rating of the circuit protector \leq rating of power supply.

1-800-633-0405 **Modular Circuit Protectors REX Series E-T-**A 2 ENGINEERING TECHNOLOGY

Mounting Diagram



Replacement Diagram



Gladiator Circuit Protectors GECP Series

Electronic Circuit Protectors Overview

The Gladiator electronic circuit protectors (ECP's), provide reliable load monitoring and protection in 24VDC control circuits. The <u>GECP-1CH-1-10A</u> features include adjustable trip current range (1-10A), patented adjustable characteristics fast, medium, slow 1, slow 2, and slow 3. All ECP's output alarm signal at 90% of the load setting, remote set/reset. In addition to factory floor applications, the ECP's serve well in remote locations and other hard to access applications. Narrow construction ensures compact design even with multi-channel configurations. No derating required as Gladiator ECP's function independently of ambient temperature.



Features

- LED status indicator at 90% of the overload ratio
- Output trip alarm
- LED status indicator on/off/alarm
- Remote Set/Reset
- Ideal for remote locations
- Independent of ambient temperature, no derating required
- 35mm DIN rail mounting
- 5-year warranty





GECP-1CH-1-10A

Single Channel Electronic Circuit Protectors											
Part Number	Price	Voltage Rating	Amperage Rating	Number Of Channels	Input Voltage	Output Voltage	Trip Curve	Connection	Mounting	Drawing Link	
<u>GECP-1CH-1-10A</u>	\$44.00	12/24 VDC	1-10A Adjustable	1	10-30 VDC	10-30 VDC	Selectable	Spring terminals	35mm DIN rail	PDF	
GECP-1CH-1A	\$29.50	12/24 VDC	1A	1	10-30 VDC	10-30 VDC	Slow 1 curve	Spring terminals	35mm DIN rail	PDF	
GECP-1CH-2A	\$29.50	12/24 VDC	2A	1	10-30 VDC	10-30 VDC	Slow 1 curve	Spring terminals	35mm DIN rail	PDF	
GECP-1CH-4A	\$29.50	12/24 VDC	4A	1	10-30 VDC	10-30 VDC	Slow 1 curve	Spring terminals	35mm DIN rail	PDF	
GECP-1CH-6A	\$29.50	12/24 VDC	6A	1	10-30 VDC	10-30 VDC	Slow 1 curve	Spring terminals	35mm DIN rail	PDF	
GECP-1CH-8A	\$29.50	12/24 VDC	8A	1	10-30 VDC	10-30 VDC	Slow 1 curve	Spring terminals	35mm DIN rail	PDF	

Max 40A per system when using with supply set GECP-24V-SS.

Gladiator Circuit Protectors GECP Series

Wiring Diagrams

GECP-1CH-1-10A



<u>GECP-1CH-1A</u>, <u>GECP-1CH-2A</u>, <u>GECP-1CH-4A</u>, <u>GECP-1CH-6A</u>, <u>GECP-1CH-8A</u>

DC 12/24V • 7		Load +
DC 12/24V • 6	<u>+ * +</u>	2 • Load +
0V <u>⊶</u> 5	C-Control	4 Status

1: + Output 2: + Output

2: + Output 3: Status output

4: + Output

5: 0V

6: + Supply (alternative)

7: + Supply

	LED Operation								
Status LED	Explanation								
LED Green, [ON]	Function is OK*								
LED Green, Flashing 1Hz [Overload]	Load about 90% of 1 nominal								
LED Green, Flashing 5Hz [Overload]	Load above 100% of 1 nominal								
LED Red, [OFF]	Module switched off or acknowledged*								
LED Red, Flashing 1Hz [Overload]	Output off due to overload/short circuit*								
LED Red, Flashing 5Hz [Error]	Wiring error - feedback (internal error)								
LED Red, Flashing Shortly [OFF]	Output off via remote set/reset								
LED Red/Green, Flashing 1Hz [ON]	Target settings via rotary switch deviate from actual settings: NOTICE: Switching off and on via pushbutton required.								
Button*** [ON/OFF]	Nominal operation: ON/OFF Load monitoring tripped: 1st push: acknowledge 2nd push: ON								
Rotary Switch (I) - Switch Position**	GECP-1CH-1-10A - current adjustment 1-10A								
Rotary Switch (C) - Switch Position**	Characteristic: 1: Fast, 2: Medium, 3: Slow-1, 4: Slow-2, 5: Slow-3								

* If the operating voltage is switched off, the last status is saved. (Default)

** Accept the setting - after switching on again via the button, not by Remote Set/Reset.

*** Master Function - switch off via pushbutton, can only be switched on again via pushbutton.

1-800-633-0405 For the latest prices, please check Automa **Gladiator** Circuit Protectors GECP Series

Characteristic Curves





Technical Data

NOTICE: Always refer to the respective current data sheet. This can be found on the product page of the product.

For the latest prices, please check AutomationDirect.com.

1-800-633-0405 For the latest prices, please check Automa **Gladiator** GECP Series Circuit Protectors

Supply Terminals

Overview

The <u>GECP-24V-SS</u> is used to supply 24V to the Electronic Circuit Protectors (ECP's) via 4- or 8-pin busbar, or by jumpering to the ECP's in the system.

The <u>GECP-0V-TERM</u> is used to bus together 0V signal to the ECP's in the system.

Features

- Single-channel design
- 40A maximum amperage rating
- 0VDC or 24VDC operating voltage
- 35mm DIN rail mounting



GECP-24V-SS



GECP-0V-TERM



Supply Terminals										
Part Number Price		Amperage Rating Operating Voltage		Mounting	Drawing Link					
GECP-24V-SS	\$20.00	40A	24VDC	25mm DIN roil	PDF					
GECP-0V-TERM	\$30.00	40A	0VDC	Somm Din Tai	PDF					

Note: End block included with GECP-24V-SS.

Wiring Diagrams

GECP-24V-SS



GECP-0V-TERM



Gladiator GECP Series Specifications

Specifications										
Part Number	<u>GECP-1CH-1-10A</u>	GECP-1CH-xA	GECP-0V-TERM	GECP-24V-SS						
Input										
Voltage Rating U _N	12/24 V	'DC	12/24 VDC	12/24/48 VDC						
Operation Voltage Range	10-30 V	/DC		_						
Total Number of Channels	1		_							
Rated Current I _N	DC 10	A	DC 10A 6 x max	DC 40A max						
Supply Current	DC 40A over Cu-ra	ails 10 x 3 mm		_						
Reverse Voltage Protection	Internal elec	ctronics		No						
Connection Type Input	Screwless co	ntact slide	_	Push-in 0.5 mm ² – 10mm ² UL Values/stranded 14-8 AWG						
Conductor Cross Section		_		Finely stranded: max. 10mm ² Finely stranded: max 10mm ² Finely stranded with AEH: max 6mm ²						
Control Input (Set/Reset)	1									
Signal Level	12/24 VDC according to EN 61131		—							
OFF	Pulse with falling edge > 100ms, < 800ms		_							
ON	Pulse with falling edge > 1s		—							
Output	1			1						
Voltage Rating U _n		—		12/24/48 VDC						
Switching Element	MOSF	ET		-						
Output Current	DC 10A	max	DC	C 40A max						
Voltage Drop	215 mV ma	x (10A)		—						
Status Display Output	LED green: operating volt LED red: error ir	age present - no error n load circuit		_						
Switch-on Capacity	10,000	μF								
Current Range	1 to 10A (Adjustable)	1 to 8A (see selection chart)		—						
Characteristic	Fast (1), Medium (2), slow 1	(3), slow 2 (4), slow 3 (5)								
Connection Type Output		—		Screwless Contact Slide						
Copper Bus Bar				5 X 1011111						
	12.24V/DC: executing valte	ao an atandhu na arrar								
Signal Level	0VDC: error, output switch	ed off or manual "OFF"		_						
Switching Element	Transistor, collector with	n pull-up resistance		_						
General	1	DA 0.0 // III. 0.4								
Housing Material		PA 6.6 (UL 94	V-0, NFF 12, F2)							
Housing Color		25mm DIN roll mo	viay							
Mounting Position										
Degree Of Protection		/ 	>20							
Connection Type		Push-In 0.25 – 2.5 mm² [24-14 AWG]		Push-In single wire/fine wire 0.50 – 10.0 mm ² [22-7 AWG] Fine stranded wire with ferrule, Finely stranded, ferrule with plastic collar 0.5 – 6mm ² [22-9 AWG] UL Values 14-8 AWG						
Weight	0.102 kg [0.22 lbs]	0.105 kg [0.23 lbs]	0.102 kg [0.22 lbs]	0.07 kg [0.15 lbs]						
Operating Temperature	-25 to 70°C [-13 to 158°F]		-25 to 50°C [-13 to 122°F]]						
Storage Temperature	-	-40 to 85°C	[-40 to 185°F]							
Relative Air Humidity		10 – 9	95% RH							
Vibration Resistance		4g according t	o EN 60068-2-6							
Shock resistance		15g according t	o EN 60068-2-27							
Certifications / Standards	CE, UKCA, UR (E530981), cULus (E191072), EN 61000-6-2, EN 61000-6-3, EN 61131-2 UL 60947-5-1	UR (E530981), cULus (E191072), EN60950-1, EN61131-1,2 EN61000, EN60947-4-1 EN55022	CE,UKCA, UR (E530981), cULus (E191072), EN 60947-1	CE, UKCA, UR (E530981), cULus (E191072) UL 60947-5-1						

Gladiator GECP Series Circuit Protectors

Busbar Features

- For busing power between 4 or 8 ECPs
- Copper with tin-plated surface
- 40A amperage rating
- 4- or 8-pin units available
- Must be used with 24V supply set part number <u>GECP-24V-SS</u>



	Busbars											
Part Number	Price	Amperage Rating	Number Of Pins	Material	Dimensions LxHxD mm [inch]	Operating And Storage Temperature	Weight	Drawing Link				
<u>GECP-BB-4</u>	\$4.00	40A	4	CU, Conner tin-plated	50.4 x 10.0 x 3.0 [1.98 x 0.39 x 0.11]	-40 to 80°C	0.013 kg [0.02 lbs]	<u>PDF</u>				
GECP-BB-8	\$5.00	40A	8	surface	82.8 x 10.0 x 3.0 [3.25 x 0.39 x 0.11]	[-40 to 176°F]	0.022 kg [0.04 lbs]	PDF				

Note: Cut to length permitted.

Jumper Comb Features

- For jumpering status outputs, 0V input, or for the set / reset terminals
- 6A amperage rating
- Push-in terminals
- 8-pole
- PVC material with FeZn contacts
- Blue normally used for 24V
- Red normally used for signal
- White normally used for 0V



Insulated Jumper Combs												
Part Number	Price	Quantity	Amperage Rating	Туре	Number Of Poles	Material	Operating Temperature	Storage Temperature	Weight	Color	Drawing Link	
<u>GECP-JC-8B</u>	\$5.00	1	6A	Push-in	8		-25 to 50°C [-13 to 122°F]	-40 to 85°C	0.003 kg [0.0006 lbs]	Blue	<u>PDF</u>	
<u>GECP-JC-8R</u>	\$5.00	1	6A	Push-in	8	PVC		[-40 to 185°F		Red	PDF	
<u>GECP-JC-8W</u>	\$5.00	1	6A	Push-in	8		-40 to [-40 to	o 85°C o 185°F		White	<u>PDF</u>	

Note: Cut to length permitted.

Gladiator GECP Series Circuit Protectors

Standalone System







Multi-Channel Electronic Circuit Breakers

Features

- Space saving ECB's with two, four, and eight channels
- Models range from 0.5-10A nominal current, adjustable for each channel via sealable selector switch
- One illuminated, three color button per channel simplifies switching (on/off), resetting, and on-site diagnostics
- Time-delayed switching of channels
- NEC Class 2 3.8 A fixed models available
- Remote input resets tripped channels or switches on/off any number of channels via pulse sequence.
- Easy to use Push-In CAGE CLAMP© terminals.

Applications

- 24VDC Circuit Protection
- PLC Input Power
- PLC I/O points
- Sensors
- Motor Controlled Circuits
- Control Instrumentation
- Relays
- Actuators
- Valves

Overview

The electronic circuit breaker distributes and monitors the load current over several circuits. They reliably recognize overloads and short circuits on an output. The circuit breakers' electronics permit brief current peaks and switch longer overloads off. The rated current for each output can be individually set with a current selector switch, which is accessible from the front. The outputs are time-delay and load-dependant activated to avoid overload current. If the rated current is exceeded for a set time, the output will be switched off automatically and can be switched on after a waiting time (thermal relaxation) using the pushbutton or the remote signal-input S1. The pushbutton can also be used to switch the output manually. The state of each output is also indicated with a multi-colored LED. Upon overload, the remaining circuits are separated from the defective current path without reverse feed, thanks to Active Current Limiting. A drop in voltage will not hinder the reliability of the respective circuit.

Multiple Channel Electronic Circuit Breaker										
Part Number	Price	Channel Units	Weight g [lbs]	Nominal Output Current (Per Channel)	Mounting	Output Voltage	Active Current Limitation	Connection	Wiring	Drawing Link
<u>787-1662-004-1000</u>	\$283.00	2	200 [0.44]	3.8 A			Yes, NEC Class 2		Diagram 2	<u>PDF</u>
<u>787-1662-006-1000</u>	\$254.00	2	170 [0.37]	0.5-6 A	35mm DIN rail 24VDC		Yes	Push-in CAGE CLAMP©	Diagram 1	<u>PDF</u>
787-1662-106-000	\$204.00	2	170 [0.37]	1-6 A I			No		Diagram 3	<u>PDF</u>
<u>787-1662</u>	\$204.00	2	200 [0.44]	2-10 A		24VDC	No		Diagram 4	<u>PDF</u>
<u>787-1664-004-1000</u>	\$397.00	4	205 [0.45]	3.8 A			Yes, NEC Class 2		Diagram 6	<u>PDF</u>
<u>787-1664-006-1000</u>	\$350.00	4	170 [0.37]	0.5-6 A			Yes		Diagram 5	<u>PDF</u>
<u>787-1664-106-000</u>	\$263.00	4	210 [0.46]	1-6 A			No		Diagram 7	<u>PDF</u>
<u>787-1664</u>	\$251.00	4	170 [0.37]	2-10 A			No		Diagram 8	<u>PDF</u>
787-1668-006-1000	\$598.00	8	440 [0.97]	0.5-6 A			Yes		Diagram 9	PDF
787-1668-106-000	\$421.00	8	490 [1.08]	1-6 A			No]	Diagram 10	PDF
787-1668	\$421.00	8	440 [0.97]	2-10 A			No		Diagram 11	PDF



For the latest prices, please check AutomationDirect.com.

Multi-Channel Electronic Circuit Breakers

Multiple Channel ECB Specifications						
Nominal Input Voltage	24VDC					
Input Voltage Range	18 – 30VDC					
Total Number of Channels	See Selection Chart					
Nominal Output Voltage	24VDC					
Output Voltage Range	18 – 30VDC					
Voltage Drop	See Product Insert					
Nominal Output Current	See Selection Chart					
Trip Time	16ms to 5s [Load-dependent]					
Switch-On Capacity	See Product Insert					
Switch-On Behavior	Time-delayed channel switching [Load-dependent, min. 50ms / max. 5s]					
Active Current Limitation	See Selection Chart					
Signaling	2,4, or 8 x Status LED [green/yellow/red] 1 x Control input 2 x active signal output [Ui max. 4 mA]					
Operation Status Indicator	See LED Operation Table Below					
Remote Input	18 – 30VDC signal, for 500ms switches on/off and resets the tripped channels					
Fuse Protection	15A [Internal Fuse]					
Isolation Voltage	DC 0.5 kV					
Protection Type	IP20 [per EN 60529]					
Reverse Voltage Protection	No					
Transient Suppression	Suppressor diode [33V]					
Series/Parallel Operation of Single Channels	Not Permitted					
Tightening Torque	N/A					
Weight	See Selection Chart					
Connectors	Push-In CAGE CLAMP [®] , Input [+] 20-8 AWG, Input [-], Output, Signaling 28-12 AWG					
Agency Approvals	EN 60950; EN 61000-6-2; EN 61000-6-3; UL 508; UL 2367; DNV GL; CE; RoHS					
Surrounding Air Temperature (Operation)	-25 to 70°C [-13 to 158°F]					
Surrounding Air Temperature (Storage)	-25 to 85°C [-13 to 185°F]					
Relative Humidity	5 to 96% [no condensation permissable]					
Derating	No derating Models ** <u>787-1664</u> & <u>787-1668</u> [greater than or equal to 50°C [122°F]; see instruction manual]					
Pollution Degree	2					

LED Operation					
State/Description	Output	LED			
Initialization	Off	Off			
Output on, function OK	On	Green			
Output Current > rated current	On	Green flashing			
Output was switched off manually or through signal input S1	Off	Red			
Output was switched off automatically (over current), thermal relaxation active	Off	Red flashing			
Output was switched off automatically (over current), thermal relaxation finished	Off	Orange flashing			
Output malfunction (internal fuse blown)	Off	Red flashing fast			



Multi-Channel Electronic Circuit Breakers

Wiring Diagrams



Diagram 2 S1 S2 S3 DC 24V(+) D

Diagram 3



Diagram 4



Diagram 5



Diagram 6





Multi-Channel Electronic Circuit Breakers

Wiring Diagrams

Diagram 7







Diagram 10



Diagram 11



1-800-633-0405 For the RHINO Accessories PSB Series

PSB Power Supply Accessories

Power Supply Accessories PSB Series					
Part Number Price Description					
<u>PSB-CVR</u>	\$6.00	Universal replacement terminal cover kit for all RHINO PSB series power supplies. Universal kit includes (9) terminal covers to replace all terminal covers on any PSB power supply model			



Gladiator DIN Rail Receptacles

Overview

Quad-receptacle DIN rail or panel mounted AC outlets are used for powering laptop computers and test equipment. GR-REC4 is a standard 125VAC, 15A quadreceptacle, and GR-REC4-GFCI is a 125VAC, 15A ground-fault circuit interrupter protected quad-receptacle.



GR-REC4-GFCI

Quad Straight Blade Receptacles									
Part Number	Price	Current Rating ¹	Voltage Rating	Circuit Protection	Number of Phases	Number of Poles	Number of Wires	Outlet Type	Drawing Link
<u>GR-REC4</u>	\$53.00	15A	125VAC	N/A	1	2	3	2X Standard Duplex Receptacle, Black, NEMA 5-15R	PDF
<u>GR-REC4-GFCI</u>	\$74.00	15A	125VAC	Ground-fault circuit interruption	1	2	3	1X Standard Duplex Receptacle ² , 1X GFCI Duplex Receptacle, Black, NEMA 5-15R	<u>PDF</u>

Note: 1 Combined current capacity of all four outlets.

Note: ² All receptacles are protected by a single GFCI circuit.

Specifications					
Wire Size Capacity	14-12 AWG [2.5 - 4.0 mm²]				
Wire Strip Length	0.20 - 0.31 in [5 - 8mm]				
Wire Type	Copper or Copper Clad				
Tightening Torque	4.5 lb-in [0.51 N•m]				
Operating Temperature ¹	32 to 140°F [0 to 60°C]				
Maximum Ambient Temperature ²	32 to 104°F [0 to 40°C]				
Housing Material	Polyamide 66, glass filled (FR370)				
Mounting	Panel mount or 35mm DIN rail				
Agency Approvals	cURus File E531313, RoHS				

¹ Maximum ambient temperature plus temperature rise of outlet wiring under load.

² Maximum ambient temperature rating per UL 508.

Wiring Instructions

- · Check the correct wiring termination below and make sure they match your electrical wiring.
- Make sure the terminal screws are properly tightened before powering the outlet on.



- "L" Symbol for LINE/BLACK connection
- Symbol for NEUTRAL/WHITE connection "N"
- Symbol for GROUND/GREEN connection



Gladiator DIN Rail Receptacles

Installation

- · Hold the device against the DIN rail, parallel to the mounting surface.
- Apply even pressure against the DIN rail until the device is secured to the rail. -1
- · You should hear a definite "click" to indicate that the device has locked onto the DIN rail. 0
- Apply pressure by pulling the device away from the mounting surfaced to ensure that the device is secure. - 3

Alternate Installation

- Tilt the device slightly to hang the upper clamp onto the DIN rail. - 4
- Apply pressure to the bottom end of the device to snap the bottom clamp onto the rail. - 6
- You should hear a definite "click" to indicate that the device has locked onto the DIN rail. 2
- Apply pressure by pulling the device away from the mounting surfaced to ensure that the device is secure. - 3

Removal

- Turn off power to the device and unplug any equipment left connected to the device.
- · Disconnect all power wiring.
- To remove the device from the DIN rail, apply upward pressure to the bottom of the device until the top clamp releases from the rail. -6
- Pull the top away from the mounting surface.
- The device can then be lowered from the rail and pulled away. -7







1-800-633-0405 DIN Rail Receptacles

Overview

The FA-REC3 is a triple straight blade AC receptacle, 15A, 125VAC used for powering laptop computers and test equipment. This unit can be mounted on 35mm, 32mm, or 15mm DIN rail.



DIN Rail Receptacles Specifications					
Part Number	FA-REC3				
Price	\$36.00				
Output Voltage	125VAC				
Outlet Type	NEMA 5-15R				
Output Current	15A maximum				
Total Current	Must not exceed 15A if all outlets are used				
GFCI	None				
Number of Phases	1				
Number of Poles	2				
Number of Wires	3				
Mounting	35mm, 32mm, or 15mm DIN rail				
Wire Capacity	14 to 12 AWG				
Screw Torque	0.5 N·m [4.4 lbf·in]				
Operating Temperature	0 to 60°C [32 to 140°F]				
Circuit Protection	None				
Housing Material	Plastic				
Agency Approval	cULus E139594				



Dimensions

inches [mm]





See our website: www.automationdirect.com for complete engineering drawings.

1-800-633-0405 **DIN Rail Receptacles**

Overview

Duplex straight blade AC receptacles are 35mm DIN Rail or panel mounted used for powering laptop computers and test equipment. The <u>FA-REC2</u> is a standard 125VAC, 15A receptacle and FA-GFCI is a 125VAC, 15A Ground-Fault Circuit Interrupter.





FA-GFCI

DIN Rail Receptacles Specifications							
Part Number	FA-REC2	<u>FA-GFCI</u>					
Price	\$43.50	\$62.00					
Output Voltage	125V	AC					
Output Type	NEMA	5-15					
Output Current	15A Max	imum					
Circuit Protection	No	Yes					
Mounting	Panel Mount or 35mm DIN Rail						
Number of Phases	1						
Number of Poles	2						
Number of Wires	3						
Wire Capacity	14–12 AWG (solid or stranded)						
Wire Strip Length	6–7 mm						
Tightening Torque	0.51 N·m [4.5 lbf·in]						
Operating Temperature	0 to 60°C [32 to 140°F]						
Circuit Protection	None	Ground-fault circuit interruption					
Wire Type	Copper or Copper Clad						
Housing Material	PA66/6, Nylon						
Weight	180g [6.35 oz] 230g [8.11 oz]						
Agency Approval	cULus E139594						

Dimensions

inches [mm]



FA-REC2

See our website: www.automationdirect.com for complete engineering drawings.