

DATA SHEET



Three Phase Induction Motor - Squirrel Cage

Customer :				
Product line		: Rolled Steel NEMA Premium Efficiency Three-Phase		Product code : 12675363
			Catalog # :	00318ET3E182TC-S
Frame	: 182/4TC	Cooling method	: IC411 - TEFC	
Insulation class	: F	Mounting	: F-1	
Duty cycle	: Cont.(S1)	Rotation ¹	: Both (CW and CCW)	
Ambient temperature	: -20°C to +40°C	Starting method	: Direct On Line	
Altitude	: 1000 m.a.s.l.	Approx. weight ²	: 87.7 lb	
Protection degree	: IP55	Moment of inertia (J)	: 0.4017 sq.ft.lb	
Design	: B			
Output [HP]	3	3	3	
Poles	4	4	4	
Frequency [Hz]	60	50	50	
Rated voltage [V]	230/460	190-220/380	415	
Rated current [A]	7.62/3.81	9.08-7.84/4.54	4.32	
L. R. Amperes [A]	67.1/33.5	60.8-52.5/30.4	34.6	
LRC [A]	8.8x(Code K)	6.7x(Code H)	8.0x(Code K)	
No load current [A]	4.00/2.00	3.95-3.41/1.97	2.23	
Rated speed [RPM]	1765	1455	1465	
Slip [%]	1.94	3.00	2.33	
Rated torque [ft.lb]	8.93	10.8	10.8	
Locked rotor torque [%]	220	170	220	
Breakdown torque [%]	300	260	320	
Service factor	1.15	1.15	1.15	
Temperature rise	80 K	80 K	80 K	
Locked rotor time	32s (cold) 18s (hot)	45s (cold) 25s (hot)	37s (cold) 21s (hot)	
Noise level ²	56.0 dB(A)	53.0 dB(A)	53.0 dB(A)	
Efficiency (%)	25%			
	50%	87.5	87.5	86.9
	75%	88.5	87.7	88.0
	100%	89.5	86.7	87.4
Power Factor	25%			
	50%	0.61	0.68	0.62
	75%	0.74	0.79	0.74
	100%	0.81	0.85	0.81
Bearing type	: <u>Drive end</u> 6206 ZZ <u>Non drive end</u> 6205 ZZ	Foundation loads		
Sealing	: V'Ring Without Bearing Seal	Max. traction	: 176 lb	
		Max. compression	: 264 lb	
Lubrication interval	: -			
Lubricant amount	: -			
Lubricant type	: Mobil Polyrex EM			
Notes USABLE @208V 8.43A SF 1.00 SFA 8.43A				
This revision replaces and cancel the previous one, which must be eliminated. (1) Looking the motor from the shaft end. (2) Measured at 1m and with tolerance of +3dB(A). (3) Approximate weight subject to changes after manufacturing process. (4) At 100% of full load.		These are average values based on tests with sinusoidal power supply, subject to the tolerances stipulated in NEMA MG-1.		
Rev.	Changes Summary		Performed	Checked
Performed by				
Checked by			Page	Revision
Date	27/10/2023		1 / 16	

TORQUE AND CURRENT VS SPEED CURVE

Three Phase Induction Motor - Squirrel Cage




Customer :

Product line : Rolled Steel NEMA Premium Efficiency
Three-Phase

Product code : 12675363

Catalog # : 00318ET3E182TC-S



Performance : 230/460 V 60 Hz 4P

Rated current	: 7.62/3.81 A	Moment of inertia (J)	: 0.4017 sq.ft.lb
LRC	: 8.8	Duty cycle	: Cont.(S1)
Rated torque	: 8.93 ft.lb	Insulation class	: F
Locked rotor torque	: 220 %	Service factor	: 1.15
Breakdown torque	: 300 %	Temperature rise	: 80 K
Rated speed	: 1765 rpm	Design	: B

Locked rotor time : 32s (cold) 18s (hot)

Rev.	Changes Summary	Performed	Checked	Date
Performed by			Page 2 / 16	Revision
Checked by				
Date	27/10/2023			

TORQUE AND CURRENT VS SPEED CURVE




Three Phase Induction Motor - Squirrel Cage

Customer :

Product line : Rolled Steel NEMA Premium Efficiency
Three-Phase

Product code : 12675363

Catalog # : 00318ET3E182TC-S



Performance : 190-220/380 V 50 Hz 4P

Rated current	: 9.08-7.84/4.54 A	Moment of inertia (J)	: 0.4017 sq.ft.lb
LRC	: 6.7	Duty cycle	: Cont.(S1)
Rated torque	: 10.8 ft.lb	Insulation class	: F
Locked rotor torque	: 170 %	Service factor	: 1.15
Breakdown torque	: 260 %	Temperature rise	: 80 K
Rated speed	: 1455 rpm	Design	: B

Locked rotor time : 45s (cold) 25s (hot)

Rev.	Changes Summary	Performed	Checked	Date
Performed by		Page		Revision
Checked by		3 / 16		
Date	27/10/2023			

TORQUE AND CURRENT VS SPEED CURVE




Three Phase Induction Motor - Squirrel Cage

Customer :

Product line : Rolled Steel NEMA Premium Efficiency
Three-Phase

Product code : 12675363

Catalog # : 00318ET3E182TC-S



Performance : 415 V 50 Hz 4P

Rated current	: 4.32 A	Moment of inertia (J)	: 0.4017 sq.ft.lb
LRC	: 8.0	Duty cycle	: Cont.(S1)
Rated torque	: 10.8 ft.lb	Insulation class	: F
Locked rotor torque	: 220 %	Service factor	: 1.15
Breakdown torque	: 320 %	Temperature rise	: 80 K
Rated speed	: 1465 rpm	Design	: B

Locked rotor time : 37s (cold) 21s (hot)

Rev.	Changes Summary	Performed	Checked	Date
Performed by			Page 4 / 16	Revision
Checked by				
Date	27/10/2023			

LOAD PERFORMANCE CURVE

Three Phase Induction Motor - Squirrel Cage




Customer :

Product line : Rolled Steel NEMA Premium Efficiency
Three-Phase

Product code : 12675363

Catalog # : 00318ET3E182TC-S



Performance : 230/460 V 60 Hz 4P

Rated current : 7.62/3.81 A
 LRC : 8.8
 Rated torque : 8.93 ft.lb
 Locked rotor torque : 220 %
 Breakdown torque : 300 %
 Rated speed : 1765 rpm

Moment of inertia (J) : 0.4017 sq.ft.lb
 Duty cycle : Cont.(S1)
 Insulation class : F
 Service factor : 1.15
 Temperature rise : 80 K
 Design : B

Rev.	Changes Summary	Performed	Checked	Date
Performed by			Page	Revision
Checked by				
Date				

LOAD PERFORMANCE CURVE

Three Phase Induction Motor - Squirrel Cage




Customer :

Product line : Rolled Steel NEMA Premium Efficiency Three-Phase

Product code : 12675363

Catalog # : 00318ET3E182TC-S



Performance : 190-220/380 V 50 Hz 4P

Rated current : 9.08-7.84/4.54 A
 LRC : 6.7
 Rated torque : 10.8 ft.lb
 Locked rotor torque : 170 %
 Breakdown torque : 260 %
 Rated speed : 1455 rpm

Moment of inertia (J) : 0.4017 sq.ft.lb
 Duty cycle : Cont.(S1)
 Insulation class : F
 Service factor : 1.15
 Temperature rise : 80 K
 Design : B

Rev.	Changes Summary	Performed	Checked	Date
Performed by			Page	Revision
Checked by			6 / 16	
Date	27/10/2023			

LOAD PERFORMANCE CURVE

Three Phase Induction Motor - Squirrel Cage




Customer :

Product line : Rolled Steel NEMA Premium Efficiency Three-Phase

Product code : 12675363

Catalog # : 00318ET3E182TC-S



Performance : 415 V 50 Hz 4P

Rated current : 4.32 A
 LRC : 8.0
 Rated torque : 10.8 ft.lb
 Locked rotor torque : 220 %
 Breakdown torque : 320 %
 Rated speed : 1465 rpm

Moment of inertia (J) : 0.4017 sq.ft.lb
 Duty cycle : Cont.(S1)
 Insulation class : F
 Service factor : 1.15
 Temperature rise : 80 K
 Design : B

Rev.	Changes Summary	Performed	Checked	Date
Performed by			Page	Revision
Checked by			7 / 16	
Date	27/10/2023			

THERMAL LIMIT CURVE



Three Phase Induction Motor - Squirrel Cage

Customer :

Product line : Rolled Steel NEMA Premium Efficiency
Three-Phase

Product code : 12675363

Catalog # : 00318ET3E182TC-S

Performance : 230/460 V 60 Hz 4P

Rated current : 7.62/3.81 A
LRC : 8.8
Rated torque : 8.93 ft.lb
Locked rotor torque : 220 %
Breakdown torque : 300 %
Rated speed : 1765 rpm

Moment of inertia (J) : 0.4017 sq.ft.lb
Duty cycle : Cont.(S1)
Insulation class : F
Service factor : 1.15
Temperature rise : 80 K
Design : B

Heating constant

Cooling constant


Rev.	Changes Summary	Performed	Checked	Date
Performed by				
Checked by			Page	Revision
Date	27/10/2023		8 / 16	

THERMAL LIMIT CURVE

Three Phase Induction Motor - Squirrel Cage



Customer : _____



Rev.	Changes Summary	Performed	Checked	Date
Performed by				
Checked by				
Date				
			Page	Revision
			9 / 16	

THERMAL LIMIT CURVE



Three Phase Induction Motor - Squirrel Cage

Customer :

Product line : Rolled Steel NEMA Premium Efficiency
Three-Phase

Product code : 12675363

Catalog # : 00318ET3E182TC-S

Performance : 190-220/380 V 50 Hz 4P

Rated current : 9.08-7.84/4.54 A
LRC : 6.7
Rated torque : 10.8 ft.lb
Locked rotor torque : 170 %
Breakdown torque : 260 %
Rated speed : 1455 rpm

Moment of inertia (J) : 0.4017 sq.ft.lb
Duty cycle : Cont.(S1)
Insulation class : F
Service factor : 1.15
Temperature rise : 80 K
Design : B

Heating constant

Cooling constant


Rev.	Changes Summary	Performed	Checked	Date
Performed by				
Checked by			Page	Revision
Date	27/10/2023		10 / 16	

THERMAL LIMIT CURVE

Three Phase Induction Motor - Squirrel Cage



Customer : _____



Rev.	Changes Summary	Performed	Checked	Date
Performed by		Page		Revision
Checked by		11 / 16		
Date		27/10/2023		

THERMAL LIMIT CURVE



Three Phase Induction Motor - Squirrel Cage

Customer :

Product line : Rolled Steel NEMA Premium Efficiency
Three-Phase

Product code : 12675363

Catalog # : 00318ET3E182TC-S

Performance : 415 V 50 Hz 4P

Rated current : 4.32 A
LRC : 8.0
Rated torque : 10.8 ft.lb
Locked rotor torque : 220 %
Breakdown torque : 320 %
Rated speed : 1465 rpm

Moment of inertia (J) : 0.4017 sq.ft.lb
Duty cycle : Cont.(S1)
Insulation class : F
Service factor : 1.15
Temperature rise : 80 K
Design : B

Heating constant

Cooling constant


Rev.	Changes Summary	Performed	Checked	Date
Performed by				
Checked by			Page	Revision
Date	27/10/2023		12 / 16	

THERMAL LIMIT CURVE

Three Phase Induction Motor - Squirrel Cage



Customer : _____



Rev.	Changes Summary	Performed	Checked	Date
Performed by		Page		Revision
Checked by		13 / 16		
Date		27/10/2023		

VFD OPERATION CURVE

Three Phase Induction Motor - Squirrel Cage




Customer :

Product line : Rolled Steel NEMA Premium Efficiency
Three-Phase

Product code : 12675363

Catalog # : 00318ET3E182TC-S



Performance : 230/460 V 60 Hz 4P

Rated current : 7.62/3.81 A
LRC : 8.8
Rated torque : 8.93 ft.lb
Locked rotor torque : 220 %
Breakdown torque : 300 %
Rated speed : 1765 rpm

Moment of inertia (J) : 0.4017 sq.ft.lb
Duty cycle : Cont.(S1)
Insulation class : F
Service factor : 1.15
Temperature rise : 80 K
Design : B

Rev.	Changes Summary	Performed	Checked	Date
Performed by			Page	Revision
Checked by				
Date				

VFD OPERATION CURVE

Three Phase Induction Motor - Squirrel Cage




Customer :

Product line : Rolled Steel NEMA Premium Efficiency
Three-Phase

Product code : 12675363

Catalog # : 00318ET3E182TC-S



Performance : 190-220/380 V 50 Hz 4P

Rated current : 9.08-7.84/4.54 A
 LRC : 6.7
 Rated torque : 10.8 ft.lb
 Locked rotor torque : 170 %
 Breakdown torque : 260 %
 Rated speed : 1455 rpm

Moment of inertia (J) : 0.4017 sq.ft.lb
 Duty cycle : Cont.(S1)
 Insulation class : F
 Service factor : 1.15
 Temperature rise : 80 K
 Design : B

Rev.	Changes Summary	Performed	Checked	Date
Performed by		Page		Revision
Checked by		15 / 16		
Date		27/10/2023		

VFD OPERATION CURVE

Three Phase Induction Motor - Squirrel Cage




Customer :

Product line : Rolled Steel NEMA Premium Efficiency
Three-Phase

Product code : 12675363

Catalog # : 00318ET3E182TC-S




Performance : 415 V 50 Hz 4P

Rated current : 4.32 A
LRC : 8.0
Rated torque : 10.8 ft.lb
Locked rotor torque : 220 %
Breakdown torque : 320 %
Rated speed : 1465 rpm



Moment of inertia (J) : 0.4017 sq.ft.lb
Duty cycle : Cont.(S1)
Insulation class : F
Service factor : 1.15
Temperature rise : 80 K
Design : B

Rev.	Changes Summary	Performed	Checked	Date
Performed by			Page 16 / 16	Revision
Checked by				
Date	27/10/2023			



A
B
C
D
E

Dimensions in inches XME A3

Color Munsell N 1 matte black										
Painting plan 207N										
Mounting F-1/B34R(D)										
					USERADMIN	00				
ECM	LOC	SUMMARY OF MODIFICATIONS			EXECUTED	CHECKED	RELEASED	DATE	VER	
EXECUTED	USERADMIN	 THREE PH. MOTOR ROLLED STEEL NEMA PREM. EFF. FRAME 182/4TC IP55 TEFC			PREVIEW WDD 00					
CHECKED					SHEET				1 / 1	
RELEASED										
REL. DATE		WMO	Jaragua do Sul	Product Engineering						

3 HP 04 Poles 60 Hz

A

**NEMA**
Premium3PT9
US LISTED
FOR SAFE AREA

Energy Verified

MADE IN MEXICO

MAT: 12675363 CC029A
W01.TE0IC0X0N
MODEL 00318ET3E182TC-S
18OCT2023 S/N:

For 60Hz: Class I, Zone 2, IIC
Class I, Div.2, Gr. A,B,C,D - T3
Div 2 Inverter Duty (SF1.00)
CT 2:1/VT 1000:1

PH 3	Hz 60	HP 3.0
FR 182/4TC		KW 2.2
DUTY CONT.		V 230/460
ALT 1000 m.a.s.l.		A 7.62/3.81
INS CL F AT 80K	IP55	SFA 8.76/4.38
AMB 40°C	DES B	SF 1.15
ENCL TEFC	CODE K	PF 0.81
		RPM 1765
		NEMA NOM. EFF 89.5%

ALTERNATE RATING: 3.0HP 50Hz 190-220/380-415V SF1.15
9.08-8.15/4.54-4.32A 1455RPM EFF 88.7% (IE3) IEC 60034-1

For safe area-inverter duty motor For 60Hz use on VPWM 1000:1 VT, 4:1 CT

DE 6206-ZZ ODE 6205-ZZ MOBIL POLYREX EM



T1-BLU T2-WHT
 T3-ORG T4-YEL
 T5-BLK T6-GRY
 T7-PNK T8-RED
 T9-RED BRK

INTERCHANGE ANY TWO LINE WIRES TO REVERSE THE ROTATION



WARNING: Motor must be grounded in accordance with local and national electrical codes to prevent serious electrical shocks. Disconnect power source before servicing unit.

AVERTISSEMENT: Le moteur doit être mis à la terre

conformément aux codes électriques locaux et nationaux afin d'éviter tout choc électrique grave. Déconnectez l'alimentation avant l'entretien de la machine.

