




IO-Link Interface Description

PQS612
PQS862

EN



Device variant

PQS612 Electronic pressure sensor, - 100000...1000000 Pa / -14.5...145.0 psi / NPT 1/8		
PQS862 Electronic pressure sensor, - 100000...1000000 Pa / -14.5...145.0 psi / G 1/8		

Vendor ID	310 / Bytes 1-54 (hex: 01-36)		
Device ID	1736 / Bytes 0-6-200 (hex: 00-06-C8)		
Bit rate	COM3		
Minimum cycle time	0,6 ms		
Process Data	4 Bytes (Input 4 Bytes / Output 0 Bytes)		
SIO mode supported	Yes		
Block parameterization	Yes		
Data storage	Yes		
Supported profiles	16	/ hex: 0x10	Smart Sensor - SSP 4.1.1
	48	/ hex: 0x30	BLOB transfer
	16384	/ hex: 0x4000	Identification and Diagnosis
	32788	/ hex: 0x8014	Function - Quantity detection
	33025	/ hex: 0x8101	Locator
	33026	/ hex: 0x8102	Product URI




NOTE:

If the Vendor ID and Device ID are specified in your PLC system, it is ensured that

- the correct device is connected,
- the IO-Link data storage is enabled,
- your application is still able to function, even if your device is replaced by a successor model at a later date



For the process value update rate, as well as further information regarding sensor performance, see data sheet.




Unit conversion



This list provides conversion formulas to convert the transmitted IO-Link raw data into physical units.

Pressure

Value in [psi]	= Transferred value	* 0.0145038
Value in [kgf/cm ²]	= Transferred value	* 0.00101972
Value in [mmHg]	= Transferred value	* 0.750064
Value in [inHg]	= Transferred value	* 0.02953
Value in [bar]	= Transferred value	* 0.001
Value in [MPa]	= Transferred value	* 0.0001



Process Data

Process Data

Process Data Input: 4 Bytes

Process Data Output: 0 Byte

Process Data Input

RecordT (32 Bit)

MDC Pressure

IntegerT (16 Bit)

Shows the current measurement value of the sensing element. (Pressure)

Value range [Pa] (-1000 to 10500) * 100
32764 (No measurement data) 0x7FFC
32760 (Out of range (+)) 0x7FF8

MDC - Scale

IntegerT (8 Bit)

Shows the multiplier for the measurement value of the sensor - 10exp(scale).

SSC.1 Pressure

BooleanT

Indicates the detection status of a switching signal channel depending on process data and SSC.1 Param and SSC.1 Config. (Pressure)

Value range false true (Low) (High)

SSC.2 Pressure

BooleanT

Indicates the detection status of a switching signal channel depending on process data and SSC.2 Param and SSC.2 Config. (Pressure)


Value range false true (Low) (High)

Device Status

UIntegerT (4 Bit)

Current device status, a copy of the parameter [Device Status, Index 36] in the process data channel

Value range 0 (Device is OK)
1 (Maintenance required)
2 (Out of specification)
3 (Functional check)
4 (Failure)



Data is transmitted in BigEndian format.

The position of the process data bytes is shown according to the device transmission sequence.

The content of your PLCs input buffer may vary according to your PLCs data format.


Please do not apply any byte swap feature.

Example function blocks incl. documentation are available on www.ifm.com --> Startup Packages




Parameter overview

Parameter	Index	Subindex	Type	Factory setting	Page
Device Access Locks	12		RecordT (16 Bit)	false (Unlocked)	12
Local Parameterizat...	12		BooleanT		
Vendor Name	16		StringT (64 Byte)	ifm electronic gmbh	11
Vendor Text	17		StringT (64 Byte)	www.ifm.com	11
Product Name	18		StringT (64 Byte)		11
Product ID	19		StringT (64 Byte)		11
Product Text	20		StringT (64 Byte)	Electronic pressure sensor	11
Serial Number	21		StringT (16 Byte)		11
Hardware Revision	22		StringT (64 Byte)		11
Firmware Revision	23		StringT (64 Byte)		11
Application-specific Tag	24		StringT (32 Byte)	***	11
Function Tag	25		StringT (32 Byte)	***	11
Location Tag	26		StringT (32 Byte)	***	11
Product URI	27		StringT (100 Byte)		11
Device Status	36		UIntegerT (8 Bit)		19
Detailed Device Status	37		OctetStringT (3 Byte) [11]		19
Process Data Input	40		RecordT (32 Bit)		4
MDC Pressure	40		IntegerT (16 Bit)		4
MDC - Scale	40		IntegerT (8 Bit)		4
SSC.1 Pressure	40		BooleanT		4
SSC.2 Pressure	40		BooleanT		4
Device Status	40		UIntegerT (4 Bit)		4
ID of the BLOB that is ...	49		IntegerT (16 Bit)		12
Teach Select	58		UIntegerT (8 Bit)	1 (SSC.1 Pressure)	12
Teach Result	59		RecordT (8 Bit)		12
State	59		UIntegerT (4 Bit)	0 (Idle)	12
SSC.1 Param Pressure	60		RecordT (64 Bit)		12
SP1	60	1	IntegerT (32 Bit)	2500	12
SP2	60	2	IntegerT (32 Bit)	2300	12
SSC.1 Config Pressure	61		RecordT (48 Bit)		13
Logic	61	1	UIntegerT (8 Bit)	0 (High active)	13
Mode	61	2	UIntegerT (8 Bit)	1 (Single point)	13
Hysteresis	61	3	IntegerT (32 Bit)	0 (Auto)	13
SSC.2 Param Pressure	62		RecordT (64 Bit)		13
SP1	62	1	IntegerT (32 Bit)	7500	13
SP2	62	2	IntegerT (32 Bit)	7300	13
SSC.2 Config Pressure	63		RecordT (48 Bit)		13
Logic	63	1	UIntegerT (8 Bit)	0 (High active)	13
Mode	63	2	UIntegerT (8 Bit)	1 (Single point)	13
Hysteresis	63	3	IntegerT (32 Bit)	0 (Auto)	14
SSC.1 Delay	320		RecordT (32 Bit)		14
Switching delay	320	1	UIntegerT (16 Bit)	0	14
Reset delay	320	2	UIntegerT (16 Bit)	0	14
SSC.2 Delay	321		RecordT (32 Bit)		14
Switching delay	321	1	UIntegerT (16 Bit)	0	14




Parameter overview

Parameter	Index	Subindex	Type	Factory setting	Page
Reset delay	321	2	UIntegerT (16 Bit)	0	14
SSC Counter	349		RecordT (64 Bit)		14
SSC.1	349	1	IntegerT (32 Bit)		14
SSC.2	349	2	IntegerT (32 Bit)		14
P-n	500		UIntegerT (8 Bit)	0 (PnP)	8
dAP.P	510		UIntegerT (16 Bit)	60	14
Media temperature	537		IntegerT (16 Bit)		20
Operating hours	542		IntegerT (32 Bit)		18
Internal temperature	543		IntegerT (16 Bit)		20
Active Events	545		RecordT (32 Bit)		18
Bit_31	545		BooleanT		18
Bit_30	545		BooleanT		18
Bit_16	545		BooleanT		18
Bit_15	545		BooleanT		18
Bit_14	545		BooleanT		18
Bit_9	545		BooleanT		18
Bit_8	545		BooleanT		18
Bit_4	545		BooleanT		18
Bit_2	545		BooleanT		18
Bit_1	545		BooleanT		18
Bit_0	545		BooleanT		18
Param configuration fault	546		UIntegerT (32 Bit) [10]	0 (OK)	19
Loc	550		UIntegerT (8 Bit)	1 (uLoc)	15
uni.P	551		UIntegerT (8 Bit)	2 (psi)	8
Hi.P	560		IntegerT (16 Bit)		15
Lo.P	561		IntegerT (16 Bit)		15
S.On	570		UIntegerT (8 Bit)	0 (OFF)	15
S.Tim	571		UIntegerT (8 Bit)	2 (3 min)	15
S.PRS	572		IntegerT (16 Bit)	5000	15
ou1	580		UIntegerT (8 Bit)	32 (SSC1.1 / SSC.1)	15
ou2	590		UIntegerT (8 Bit)	33 (SSC1.2 / SSC.2)	16
diS.U	800		UIntegerT (8 Bit)	1 (d2 / medium)	16
diS.R	801		UIntegerT (8 Bit)	0 (0 °)	16
diS.B	802		UIntegerT (8 Bit)	75 (75 %)	16
diS.L	803		UIntegerT (8 Bit)	0 (PV)	16
coL.P	810		UIntegerT (8 Bit)	16 (bk/wh / Value black and white)	16
uni.T	841		UIntegerT (8 Bit)	1 (°F)	8
LanG	923		UIntegerT (8 Bit)	0 (EN)	8
Bargraph start	936		IntegerT (32 Bit)	-1000	16
Bargraph end	937		IntegerT (32 Bit)	10000	17
coF	5001		IntegerT (16 Bit)	0	17
HIPS	5003		IntegerT (16 Bit)	10000	20
HIPC	5004		UIntegerT (32 Bit)	0	20
MDC Descriptor Pressure	16512		RecordT (88 Bit)		19
Lower Value	16512		IntegerT (32 Bit)	-1000	19



Parameter overview

Parameter	Index	Subindex	Type	Factory setting	Page
Upper Value	16512		IntegerT (32 Bit)	10000	19
Unit	16512		UIntegerT (16 Bit)	1130 (Pa)	20
Scale	16512		IntegerT (8 Bit)	2	20




Basic settings

P-n	Index 500	Subindex 0	UIntegerT (8 Bit)	ReadWrite
Output polarity for the switching outputs.				
Factory setting	0	(PnP)		
Value range	0	(PnP)		
	1	(nPn)		

uni.P	Index 551	Subindex 0	UIntegerT (8 Bit)	ReadWrite
Selection of pressure unit.				
Factory setting	2	(psi)		
Value range	0	(MPa)		
	1	(bar)		
	2	(psi)		
	3	(inHg)		
	4	(mmHg)		
	5	(kgf/cm ²)		

uni.T	Index 841	Subindex 0	UIntegerT (8 Bit)	ReadWrite
Selection of temperature unit.				
Factory setting	1	(°F)		
Value range	0	(°C)		
	1	(°F)		

Lang	Index 923	Subindex 0	UIntegerT (8 Bit)	ReadWrite
Select device menu language.				
Factory setting	0	(EN)		
Value range	0	(EN)		
	1	(DE)		
	2	(IT)		
	3	(FR)		
	4	(ES)		
	5	(PT)		
	6	(JA)		
	7	(KO)		
	9	(ZH)		



System Command




Command interface for applications. A positive acknowledge indicates the complete and correct finalization of the requested function.

System Command information:

- Address: Index 2, Subindex 0
- Datatype: UInteger (8 Bit)
- AccessRight: Write Only

#	Text	Description
1	Upload Start	Start block parameter upload
2	Upload End	End block parameter upload
3	Download Start	Start block parameter download
4	Download End	Stop block parameter download
5	Store	Finalize block parameterization and start Data Storage
6	Break	Cancel block parameterization
65	Teach SP1	Determine setpoint 1 in a single teach procedure.
66	Teach SP2	Determine setpoint 2 in a single teach procedure.
126	Locator Start	The visual indicators of the device are switched to the localization display pattern, which makes it easier to spot a device in an application.
127	Locator Stop	The localization indication pattern is stopped. The optical indicators of the device will show again the device specific states of operation.
129	Application Reset	The parameters of the technology-specific application are set to default values. Identification parameters remain unchanged. An upload to the data storage of the master will be executed, if activated in the port configuration of the master.
131	Back-to-box	The parameters of the device are set to factory default values and communication will be inhibited until the next power cycle. Note: Directly detach the device from the master port!
161	Reset [Hi.P] and [Lo.P] memory	
162	Reset [Lo.P] memory	
163	Reset [Hi.P] memory	
169	Reset overload counter [HIPC]	
175	BLOB-Reset / Event Log	



System Command

176 Start simulation

177 Stop simulation

194 Teach tcoF Teaches the zero-point offset. Command will be rejected, if current process data is out of range of parameter coF

228 Reset counter to zero

240 IO-Link 1.1 system test command 240,
Event 8DFE appears

241 IO-Link 1.1 system test command 241,
Event 8DFE disappears

242 IO-Link 1.1 system test command 242,
Event 8DFF appears

243 IO-Link 1.1 system test command 243,
Event 8DFF disappears



Identification

Vendor Name	Index 16	Subindex 0	StringT (64 Byte)	ReadOnly
The vendor name that is assigned to a Vendor ID.				
Factory setting	ifm electronic gmbh			
Vendor Text	Index 17	Subindex 0	StringT (64 Byte)	ReadOnly
Additional information about the vendor.				
Factory setting	www.ifm.com			
Product Name	Index 18	Subindex 0	StringT (64 Byte)	ReadOnly
Complete product name.				
Product ID	Index 19	Subindex 0	StringT (64 Byte)	ReadOnly
Vendor-specific product or type identification (e.g., item number or model number).				
Product Text	Index 20	Subindex 0	StringT (64 Byte)	ReadOnly
Additional product information for the device.				
Factory setting	Electronic pressure sensor			
Serial Number	Index 21	Subindex 0	StringT (16 Byte)	ReadOnly
Unique, vendor-specific identifier of the individual device.				
Hardware Revision	Index 22	Subindex 0	StringT (64 Byte)	ReadOnly
Unique, vendor-specific identifier of the hardware revision of the individual device.				
Firmware Revision	Index 23	Subindex 0	StringT (64 Byte)	ReadOnly
Unique, vendor-specific identifier of the firmware revision of the individual device.				
Application-specific Tag	Index 24	Subindex 0	StringT (32 Byte)	ReadWrite
Possibility to mark a device with user- or application-specific information.				
Factory setting	***			
Function Tag	Index 25	Subindex 0	StringT (32 Byte)	ReadWrite
Possibility to mark a device with function-specific information.				
Factory setting	***			
Location Tag	Index 26	Subindex 0	StringT (32 Byte)	ReadWrite
Possibility to mark a device with location-specific information.				
Factory setting	***			
Product URI	Index 27	Subindex 0	StringT (100 Byte)	ReadOnly
Provides a unique instance identification compliant to DIN-SPEC 91406.				



A base ten block diagram showing two tens rods and one unit cube. The first ten rod is empty. The second ten rod has one unit cube attached to its right end, representing the number 21.

Teach Select	Index 58	Subindex 0	UIntegerT (8 Bit)	ReadWrite
Selects the switching signal channel for which a teach procedure will be applied.				
Factory setting	1	(SSC.1 Pressure)		
Value range	1	(SSC.1 Pressure)		
	2	(SSC.2 Pressure)		

SSC.1 Param Pressure	Index 60	Subindex 0	RecordT (64 Bit)	ReadWrite
Defines the setpoint values for switching signal channel 1. (Pressure)				
SP1		Subindex 1	IntegerT (32 Bit)	
Defines the setpoint 1 value for the switching signal channel.				
Factory setting	2500			
Value range [Pa]	(-1000 to 10000) * 100			
SP2		Subindex 2	IntegerT (32 Bit)	
Defines the setpoint 2 value for the switching signal channel.				
Factory setting	2300			
Value range [Pa]	(-1000 to 10000) * 100			



Parameters

SSC.1 Config Pressure	Index 61	Subindex 0	RecordT (48 Bit)	ReadWrite
Defines the configuration parameter for switching signal channel 1. (Pressure)				
Logic		Subindex 1	UIntegerT (8 Bit)	
Defines the logical representation of the switching signal SSC in the process data.				
Factory setting	0	(High active)		
Value range	0 1	(High active) (Low active)		
Mode		Subindex 2	UIntegerT (8 Bit)	
Defines the evaluation mode for the switching signal SSC.				
Factory setting	1	(Single point)		
Value range	0 1 2 3	(Deactivated) (Single point) (Window) (Two point)		
Hysteresis		Subindex 3	IntegerT (32 Bit)	
Defines the hysteresis at the switchpoint. A higher hysteresis may help to increase stability in critical applications.				
Factory setting	0	(Auto)		
Value range [Pa]	(20 to 1000) * 100 0	(Auto)		

SSC.2 Param Pressure	Index 62	Subindex 0	RecordT (64 Bit)	ReadWrite
Defines the setpoint values for switching signal channel 2. (Pressure)				
SP1		Subindex 1	IntegerT (32 Bit)	
Defines the setpoint 1 value for the switching signal channel.				
Factory setting	7500			
Value range [Pa]	(-1000 to 10000) * 100			
SP2		Subindex 2	IntegerT (32 Bit)	
Defines the setpoint 2 value for the switching signal channel.				
Factory setting	7300			
Value range [Pa]	(-1000 to 10000) * 100			

SSC.2 Config Pressure	Index 63	Subindex 0	RecordT (48 Bit)	ReadWrite
Defines the configuration parameter for switching signal channel 2. (Pressure)				
Logic		Subindex 1	UIntegerT (8 Bit)	
Defines the logical representation of the switching signal SSC in the process data.				
Factory setting	0	(High active)		
Value range	0 1	(High active) (Low active)		
Mode		Subindex 2	UIntegerT (8 Bit)	
Defines the evaluation mode for the switching signal SSC.				
Factory setting	1	(Single point)		
Value range	0 1 2 3	(Deactivated) (Single point) (Window) (Two point)		



Parameters


SSC.2 Config Pressure	Index 63	Subindex 0	RecordT (48 Bit)	ReadWrite
Hysteresis		Subindex 3	IntegerT (32 Bit)	
Defines the hysteresis at the switchpoint. A higher hysteresis may help to increase stability in critical applications.				
Factory setting	0	(Auto)		
Value range [Pa]	(20 to 1000) * 100 0	(Auto)		

SSC.1 Delay	Index 320	Subindex 0	RecordT (32 Bit)	ReadWrite
Delays for the switching signal channel 1.1.				
Switching delay		Subindex 1	UIntegerT (16 Bit)	
Set delay time for the switching.				
Factory setting	0			
Value range [s]	(0 to 9999) * 0.01			
Reset delay		Subindex 2	UIntegerT (16 Bit)	
Set delay time for the reset.				
Factory setting	0			
Value range [s]	(0 to 9999) * 0.01			

SSC.2 Delay	Index 321	Subindex 0	RecordT (32 Bit)	ReadWrite
Delays for the switching signal channel 1.2.				
Switching delay		Subindex 1	UIntegerT (16 Bit)	
Set delay time for the switching.				
Factory setting	0			
Value range [s]	(0 to 9999) * 0.01			
Reset delay		Subindex 2	UIntegerT (16 Bit)	
Set delay time for the reset.				
Factory setting	0			
Value range [s]	(0 to 9999) * 0.01			

SSC Counter	Index 349	Subindex 0	RecordT (64 Bit)	ReadOnly
Available switching signal counters. Counts the SSC transitions from 0 to 1.				
SSC.1		Subindex 1	IntegerT (32 Bit)	
SSC.1 counter				
Value range	(0 to 2147482880) 2147483644	(NoData) 0x7FFFFFFC		
SSC.2		Subindex 2	IntegerT (32 Bit)	
SSC.2 counter				
Value range	(0 to 2147482880) 2147483644	(NoData) 0x7FFFFFFC		

dAP.P	Index 510	Subindex 0	UIntegerT (16 Bit)	ReadWrite
Damping of the pressure signal.				
Factory setting	60			
Value range [s]	(0 to 4000) * 0.001			



Parameters

Loc	Index 550	Subindex 0	UIntegerT (8 Bit)	ReadWrite
[Loc] locks the local user interface to prevent unintentional changes, [Loc] is resettable at the device.				
Factory setting	1	(uLoc)		
Value range	0 1	(Loc) (uLoc)		

Hi.P	Index 560	Subindex 0	IntegerT (16 Bit)	ReadOnly
Maximum memory value for pressure.				
Value range [Pa]	(-1000 to 10500) * 100 32760 32764	(OL - overload) 0x7FF8 (NoData) 0x7FFC		


Lo.P	Index 561	Subindex 0	IntegerT (16 Bit)	ReadOnly
Minimum memory value for pressure.				
Value range [Pa]	(-1000 to 10500) * 100 32760 32764	(OL - overload) 0x7FF8 (NoData) 0x7FFC		

S.On	Index 570	Subindex 0	UIntegerT (8 Bit)	ReadOnly
Simulation state.				
Factory setting	0	(OFF)		
Value range	0 1	(OFF) (On)		

S.Tim	Index 571	Subindex 0	UIntegerT (8 Bit)	ReadWrite
Simulation duration.				
Factory setting	2	(3 min)		
Value range	0 1 2 3 4 5 6 7 8 9 10	(1 min) (2 min) (3 min) (4 min) (5 min) (10 min) (15 min) (20 min) (30 min) (45 min) (60 min)		

S.PRS	Index 572	Subindex 0	IntegerT (16 Bit)	ReadWrite
Simulation of pressure.				
Factory setting	5000			
Value range [Pa]	(-1000 to 10500) * 100 32760 32764	(OL - overload) 0x7FF8 (Err) 0x7FFC		

ou1	Index 580	Subindex 0	UIntegerT (8 Bit)	ReadWrite
Output configuration [OUT 1].				
Factory setting	32	(SSC1.1 / SSC.1)		
Value range	32 16	(SSC1.1 / SSC.1) (OFF / Output Off)		



Parameters

ou2	Index 590	Subindex 0	UIntegerT (8 Bit)	ReadWrite
Output configuration [OUT 2].				
Factory setting	33	(SSC1.2 / SSC.2)		
Value range	33 16	(SSC1.2 / SSC.2) (OFF / Output Off)		

diS.U	Index 800	Subindex 0	UIntegerT (8 Bit)	ReadWrite
Current display update rate.				
Factory setting	1	(d2 / medium)		
Value range	0 1 2	(d1 / fast) (d2 / medium) (d3 / slow)		


diS.R	Index 801	Subindex 0	UIntegerT (8 Bit)	ReadWrite
Current display rotation clockwise.				
Factory setting	0	(0 °)		
Value range	0 1 2 3	(0 °) (90 °) (180 °) (270 °)		

diS.B	Index 802	Subindex 0	UIntegerT (8 Bit)	ReadWrite
Current display brightness.				
Factory setting	75	(75 %)		
Value range	25 50 75 100 0	(25 %) (50 %) (75 %) (100 %) (OFF)		

diS.L	Index 803	Subindex 0	UIntegerT (8 Bit)	ReadWrite
Current layout of the display.				
Factory setting	0	(PV)		
Value range	0 1 2 3 4 5 6 7	(PV) (App.Spec.Tag) (SSC.1-Param_SP1) (SSC.1-Param_SP2) (Bargraph SSC.1) (SSC Counter1) (Hi.P) (Lo.P)		

coL.P	Index 810	Subindex 0	UIntegerT (8 Bit)	ReadWrite
Colour configuration pressure.				
Factory setting	16	(bk/wh / Value black and white)		
Value range	16 4 5	(bk/wh / Value black and white) (r1ou / Value red when OUT1 switches) (G1ou / Value green when OUT1 switches)		


Bargraph start	Index 936	Subindex 0	IntegerT (32 Bit)	ReadWrite
Start of the bargraph scaling.				
Factory setting	-1000			
Value range [Pa]	(-1000 to 9980) * 100			



Parameters

Bargraph end	Index 937	Subindex 0	IntegerT (32 Bit)	ReadWrite
End of the bargraph scaling.				
Factory setting	10000			
Value range [Pa]	(-980 to 10000) * 100			


coF	Index 5001	Subindex 0	IntegerT (16 Bit)	ReadWrite
Zero-point calibration (Calibration offset).				
Factory setting	0			
Value range [%]	(-500 to 500) * 0.01			




Diagnosis

Operating hours	Index 542	Subindex 0	IntegerT (32 Bit)	ReadOnly
Counter of the operating hours since delivery.				
Value range [h]	(0 to 2147482880) * 1 2147483644	(NoData)	0x7FFFFFFC	

Active Events	Index 545	Subindex 0	RecordT (32 Bit)	ReadOnly
Bit mask for current pending events.				
Bit offset 31	(0x8DFF)	Test Event 2. Device Status = 1 (Maintenance required)		
Bit offset 30	(0x8DFE)	Test Event 1. Device Status = 1 (Maintenance required)		
Bit offset 16	(0x8C01)	Simulation active		
Bit offset 15	(0x4210)	Device temperature overrun		
Bit offset 14	(0x4220)	Device temperature underrun		
Bit offset 9	(0x8C30)	Process variable range underrun		
Bit offset 8	(0x8C10)	Process variable range overrun		
Bit offset 4	(0x4000)	Temperature fault		
Bit offset 2	(0x7710)	Short circuit		
Bit offset 1	(0x6320)	Parameter error		
Bit offset 0	(0x5000)	Device hardware fault		
Value range	true	Event active		
	false	Event inactive		






Diagnosis

Param configuration fault	Index 546	Subindex 0	UIntegerT (32 Bit) [10]	ReadOnly
Displays the incorrectly set parameters.				
Factory setting	0	(OK)		
Value range	0	(OK)		
	786432	(Device Access Locks, Index = 12)		
	38010880	(ou1, Index = 580)		
	36110336	(uni.P, Index = 551)		
	33423360	(dAP.P, Index = 510)		
	32768000	(P-n, Index = 500)		
	327745536	(coF, Index = 5001)		
	37486592	(S.PRS, Index = 572)		
	37421056	(S.Tim, Index = 571)		
	60489728	(LanG, Index = 923)		
	52494336	(diS.R, Index = 801)		
	52559872	(diS.B, Index = 802)		
	52625408	(diS.L, Index = 803)		
	61341696	(Bargraph start, Index = 936)		
	61407232	(Bargraph end, Index = 937)		
	53084160	(coL.P, Index = 810)		
	52428800	(diS.U, Index = 800)		
	38666240	(ou2, Index = 590)		
	327876608	(HIPS, Index = 5003)		
	36044800	(Loc, Index = 550)		
	3997696	(SSC.1 Config, Index = 61)		
	3997697	(SSC.1 Config, Index = 61, Subindex = 1)		
	3997698	(SSC.1 Config, Index = 61, Subindex = 2)		
	3997699	(SSC.1 Config, Index = 61, Subindex = 3)		
	20971520	(SSC.1 Delay, Index = 320)		
	20971521	(SSC.1 Delay, Index = 320, Subindex = 1)		
	20971522	(SSC.1 Delay, Index = 320, Subindex = 2)		
	3932160	(SSC.1 Param, Index = 60)		
	3932161	(SSC.1 Param, Index = 60, Subindex = 1)		
	3932162	(SSC.1 Param, Index = 60, Subindex = 2)		
	4128768	(SSC.2 Config, Index = 63)		
	4128769	(SSC.2 Config, Index = 63, Subindex = 1)		
	4128770	(SSC.2 Config, Index = 63, Subindex = 2)		
	4128771	(SSC.2 Config, Index = 63, Subindex = 3)		
	21037056	(SSC.2 Delay, Index = 321)		
	21037057	(SSC.2 Delay, Index = 321, Subindex = 1)		
	21037058	(SSC.2 Delay, Index = 321, Subindex = 2)		
	4063232	(SSC.2 Param, Index = 62)		
	4063233	(SSC.2 Param, Index = 62, Subindex = 1)		
	4063234	(SSC.2 Param, Index = 62, Subindex = 2)		
	3801088	(Teach Select, Index = 58)		
	55115776	(uni.T, Index = 841)		

Device Status	Index 36	Subindex 0	UIntegerT (8 Bit)	ReadOnly
Indicator for the current device condition and diagnosis state.				
Value range	0	(Device is OK)		
	1	(Maintenance required)		
	2	(Out of specification)		
	3	(Functional check)		
	4	(Failure)		

Detailed Device Status	Index 37	Subindex 0	OctetStringT (3 Byte) [11]	ReadOnly
List of all currently pending events in the device.				

MDC Descriptor Pressure	Index 16512	Subindex 0	RecordT (88 Bit)	ReadOnly
Descriptor for the characteristic of the measurement data channel (process data MV). (Pressure)				
Lower Value		Bit offset 56	IntegerT (32 Bit)	
Factory setting	-1000			
Shows the lower value of measurement range.				
Upper Value		Bit offset 24	IntegerT (32 Bit)	
Factory setting	10000			
Shows the upper value of measurement range.				



Diagnosis


MDC Descriptor Pressure	Index 16512	Subindex 0	RecordT (88 Bit)	ReadOnly
Unit		Bit offset 8	UIntegerT (16 Bit)	
Shows the physical unit.				
Factory setting	1130	(Pa)		
Value range	1130	(Pa)		
Scale		Bit offset 0	IntegerT (8 Bit)	
Shows the multiplier for measurement value - 10exp(scale).				
Factory setting	2			

HIPC	Index 5004	Subindex 0	UIntegerT (32 Bit)	ReadOnly
Pressure overload counter.				
Factory setting	0			
Value range	(0 to 4294967295) * 1			

HIPS	Index 5003	Subindex 0	IntegerT (16 Bit)	ReadWrite
Configuration of pressure overload counter switch point.				
Factory setting	10000			
Value range [Pa]	(-1000 to 10000) * 100			

Internal temperature	Index 543	Subindex 0	IntegerT (16 Bit)	ReadOnly
Current internal temperature of the device.				
Value range [°F]	(0 to 92) * 1.8 + 32 -32760 32760 32764	(UL - underload) 0x8008 (OL - overload) 0x7FF8 (NoData) 0x7FFC		

Media temperature	Index 537	Subindex 0	IntegerT (16 Bit)	ReadOnly
Current media temperature.				
Value range [°F]	(0 to 60) * 1.8 + 32 -32760 32760 32764	(UL - underload) 0x8008 (OL - overload) 0x7FF8 (NoData) 0x7FFC		




Events

Code	Device status	PQ *	Class	Name	Description
0x4000 16384d	3 (Functional check)	valid	Error	Temperature fault	Overload
0x4210 16912d	2 (Out of specification)	valid	Warning	Device temperature overrun	Clear source of heat
0x4220 16928d	2 (Out of specification)	valid	Warning	Device temperature underrun	Insulate device
0x5000 20480d	4 (Failure)	invalid	Error	Device hardware fault	Exchange device
0x6320 25376d	3 (Functional check)	invalid	Error	Parameter error	Check datasheet and values
0x7710 30480d	3 (Functional check)	valid	Error	Short circuit	Check installation
0x8C01 35841d	3 (Functional check)	valid	Warning	Simulation active	Check operating mode
0x8C10 35856d	2 (Out of specification)	valid	Warning	Process variable range overrun	Process data uncertain
0x8C30 35888d	2 (Out of specification)	valid	Warning	Process variable range underrun	Process data uncertain
0x8DFE 36350d	1 (Maintenance required)	valid	Warning	Test Event 1. Device Status = 1 (Maintenance required)	Event appears by setting index 2 to value 240, Event disappears by setting index 2 to value 241
0x8DFF 36351d	1 (Maintenance required)	valid	Warning	Test Event 2. Device Status = 1 (Maintenance required)	Event appears by setting index 2 to value 242, Event disappears by setting index 2 to value 243



Events are reported by the device itself to signal irregular device states.
PQ* = Process data quality.




Error types

Code	Name	Description
0x8000 32768d	Device application error - no details	Service was denied by the technology-specific application. No detailed root-cause information is available.
0x8011 32785d	Index not available	Read or write access attempt to a non-existing index.
0x8012 32786d	Subindex not available	Read or write access attempt to a non-existing subindex of an existing index.
0x8020 32800d	Service temporarily not available	Parameter not accessible due to the current state of the technology-specific application.
0x8021 32801d	Service temporarily unavailable - local control	Parameter not accessible. The device is currently in an ongoing, locally controlled operation.
0x8022 32802d	Service temporarily unavailable - device control	Parameter not accessible. The technology-specific application is currently in a remotely triggered operation.
0x8023 32803d	Access denied	Write access to a read-only parameter or read access to write-only parameter.
0x8030 32816d	Parameter value out of range	Written parameter value is outside of the permitted value range.
0x8031 32817d	Parameter value above limit	Written parameter value is above its specified value range.
0x8032 32818d	Parameter value below limit	Written parameter value is below its specified value range.
0x8033 32819d	Parameter length overrun	Written parameter is longer than specified.
0x8034 32820d	Parameter length underrun	Written parameter is shorter than specified.
0x8035 32821d	Function unavailable	Written command is not supported by the technology-specific application.
0x8036 32822d	Function temporarily unavailable	Written command is unavailable due to the current state of the technology-specific application.
0x8040 32832d	Invalid parameter set	Written single parameter value collides with other existing parameter settings.
0x8041 32833d	Inconsistent parameter set	Parameter set inconsistencies at the end of block parameter transfer. Device plausibility check failed.
0x8082 32898d	Application not ready	Read or write access denied. The technology-specific application is temporarily unavailable.



Error types are used for the ISDU response. Values unequal to '0' indicate the cause of a failed ISDU read or write procedure.



ErrorTypes



The table shows all IO-Link ISDU error codes.
The device does not need to support all listed error types.