



INSTRUCTION MANUAL

SAFETINEX

SAFETY LIGHT CURTAINS

SAFETY ACCESS CONTROL BARRIERS



ORIGINAL INSTRUCTIONS

EN - This manual is available to download from our website in many language versions, including **English**:

DE - Diese Bedienungsanleitung steht auf unserer Internetseite in vielen Sprachversionen, darunter **Deutsch**, zum Download bereit:

FR - Ce manuel est téléchargeable depuis notre site internet en plusieurs versions linguistiques, dont le **français**:

IT - Il presente manuale è disponibile sul nostro sito web anche in altre lingue:

ESP - Este manual está disponible para su descargar desde nuestro sitio web en varios idiomas, incluyendo el **español**:

PT - Este manual está disponível para descarregar a partir do nosso sítio *Web* em muitas línguas, incluindo o **português**:

http://www.contrinex.com/download/#anchor_manuals

INTRODUCTION 5

 Contrinex 5

 Safetinx safety systems 5

 Active optoelectronic protective devices (AOPD) 5

 Safeguarding function 6

 Hazardous area 6

 AOPD detection capability 6

 Advantages of AOPDs 7

 Operating principle 7

 Certification of Safetinx products 8

EUROPEAN SAFETY STANDARDS 8

 Types of safety standards applicable in the EU 8

 Examples of safety standards 9

 An approach to European standards 9

 The user side 10

 Machine manufacturer side 11

 Notified bodies 11

NORTH AMERICAN SAFETY STANDARDS 12

 A different approach 12

 OSHA Regulations and U.S. Consensus Standards 13

 North American Standards for safety issues: UL, ANSI and CSA 13

 American standard agencies 13

 Canadian standard agencies 14

 International standard agencies 14

RISK ASSESSMENT 15

 Definition of hazards and risk reduction strategy 15

 Risk assessment process 15

 Methods for determination of risk level 17

 Determination of risk level in North America 17

 Determination of required performance level (PL) 18

 Specific standards for safety distance calculation 19

INSTALLATION 20

 Installation rules 20

 Positioning the AOPD 20

 Minimum safety distance required 21

 Minimum safety distance calculation (EU) 22

 Minimum safety distance calculation (US & Canada) 23

OTHER COUNTRIES 24

ACRONYMS 25

TECHNICAL DOCUMENTATION	26
Safetinx YBB for finger protection	26
Safetinx YBB for hand protection	26
Safetinx YCA for access control	26
Advantages of the Safetinx range	26
Scope of this technical documentation	27
Operating principle	27
Self protected outputs	28
Resolution (R) of an AOPD	28
LED status indicators	29
Configurable functions	29
Transmission channel selection (YBB and YCA)	29
Test mode selection (YBB)	30
Operating range selection (YCA)	30
Installation	30
Minimum safety distance	30
Recommended beam heights for access control devices	31
Positioning the sender and receiver units	31
Distance from reflective surfaces	32
Installation of multiple systems	33
Mechanical installation	34
Connecting the protective device	36
Power supply	36
Electromagnetic compatibility (EMC)	36
Light radiation	36
Pin assignment	37
Safetinx safety relay YRB-4EML-31S	38
Response time from prot. field intrusion to switching of safety relay	38
Connection examples for YRB-4EML-31S safety relay	39
Alignment of sender and receiver unit	40
Test before the first commissioning	41
TESTING AND MAINTENANCE	42
Daily functional test	42
Finger & hand protective devices (YBB models)	42
Access control devices (YCA models)	42
Troubleshooting	43
Preventive periodic inspections	44
Cleaning	44
Daily testing log file	44
AVAILABLE MODELS	46
Beam resolution: 14 mm	46
Beam resolution: 30 mm	47
Beam gap: 300..500mm	48
Technical data	49
DISCLAIMER	50
EC DECLARATION OF CONFORMITY	52

CONTRINEX

Contrinex, a multinational company with headquarters in Switzerland, is specialized in the development, production and worldwide sales of position sensors, RFID and safety systems. Contrinex employs over 500 people, including 25 highly qualified R&D engineers, operates production units in Switzerland, Hungary, China and Brazil, has its own sales offices in all the major markets and is represented in over 60 countries. Contrinex applies stringent management and production principles, which are reflected in its ISO 14001:2004 and ISO 9001:2008 certifications. Additionally, Contrinex is subject to regular client-based audits. Identical quality controls and equipment as well as staff recruitment and training policies are implemented at the different production sites, thus guaranteeing consistent product quality.

SAFETINEX SAFETY SYSTEMS

The Safetinx product lines produced by Contrinex offer high quality safeguarding solutions for both personnel and machinery. Our specialists in sensor technology have developed high-performance electro-sensitive protective equipment. Our range of safety products comprises highly sensitive devices for finger and hand protection as well as access control, featuring various lengths and connection options. Safetinx products have been developed in compliance with the applicable international safety standards and have obtained the required product certification for use in the European Union, the United States of America and all other countries where the applicable IEC standards have been adopted.

ACTIVE OPTOELECTRONIC PROTECTIVE DEVICES (AOPD)

When looking to build a safety system around a danger zone, the first consideration is whether or not optical protection is suitable at all. For this to be the case, it must be possible for the machine control to be electrically influenced by means of the AOPD's semiconductor output. Moreover, it must also be possible to instantly terminate or exit the hazardous process in every operating phase. Further, there must be no danger of injury due to heat, radiation or from materials or components ejected by the machine. If such danger exists, then either the optical system is not suitable, or the danger must be otherwise excluded by applying additional safety measures.

The selection of a specific type of safeguard involves an evaluation of the hazard, in order to determine the applicable category or required performance level PL. The choice of an active optoelectronic protective device (AOPD), such as a safety light curtain, depends on:

- The relevant safety standards to be applied
- The definition of the safeguarding function
- The available space around the hazardous area



- The safety distance, as calculated by the appropriate formula and depending on the AOPD's resolution and position, as well as the response times of the light curtain or access control barrier, the safety relay and the machine stopping time
- Ergonomic factors (e.g. how often access is necessary)
- Commercial criteria

SAFEGUARDING FUNCTION

The AOPD resolution must be chosen according to the application and the required safeguarding function. It is defined as the minimum size of an object that can be reliably and safely detected at any position in the protective field. Basically, two approaches can be considered:

- Point of operation: detection of fingers or hands entering the defined hazardous area. The protective equipment immediately stops the machine or renders it harmless. The Safetinex YBB range is best suited for this type of application.
- Perimeter or entry-exit: once the entry of a person has been detected, the hazardous motion of the machine is stopped. The control device enabling the operator to restart the machine must be located outside the hazardous area. From there, the operator must have a full view of the hazardous area to verify that nobody is in it before restarting the machine. The Safetinex YCA range is best suited for this type of application.

In both cases, the primary function of the protective device is to stop the machine before the hazardous point is reached and to prevent unintentional machine start-up or restart. This function must comply with the category or performance level of the safety-related components of the machine's control system.

HAZARDOUS AREA

The hazardous area can be defined in terms of:

- The dimensions of the zone that requires protection
- The different access points to accessible hazards
- The risk of an undetected presence in the hazardous zone, or risk of bypassing the protective device

AOPD DETECTION CAPABILITY

The light curtain or barrier detection capability (or resolution) depends on the distance between the centerlines of each beam emitted by the sender. The choice for a specific resolution depends on the part of the body which needs protection (finger, hand, whole body).




FIG. 1: RESOLUTION OF THE ACCESS CONTROL BARRIER OR LIGHT CURTAIN

ADVANTAGES OF AOPDs

Safeguarding devices are used where risks cannot be eliminated by machine design. Rather than preventing access to a hazardous area, safety light curtains or access control barriers detect the entry of a person or part of a body and eliminate the hazard by triggering an immediate stop of the hazardous machine motion. They present several advantages over mechanical safeguarding devices:

- Access time to the machine is reduced, thereby increasing productivity
- Workplace ergonomics are greatly improved and less space is required
- The invisible infrared beams allow better visibility of the machine and operating process
- Protection applies to any approaching person

OPERATING PRINCIPLE

A light curtain or access control barrier comprises two units, namely a beam sender (or transmitter) and a receiver. The protective field is the area enclosed by these two components, the emitted light beams forming a permanent, though invisible, shield between the two units.




FIG. 2: OPERATING PRINCIPLE

The receiver unit is connected to a safety relay which transmits the signal to the machine control unit. When properly installed, the protective device detects any relevant entry into the hazardous area. As soon as such an entry is detected, the protective device immediately triggers the safety relay, which in turn causes the machine control system to bring the machine to a safe status and/or complete stop, thus eliminating the hazard.

The size of the protective field depends on the dimension of the AOPD and the distance between the sender and receiver units.

AOPDs are also commonly used as sensors to automate industrial operations where no critical human safety issue is involved. However, when directly linked to the safety of persons, their design and installation are strictly regulated.

CERTIFICATION OF SAFETINEX PRODUCTS

Safetinex products fully meet category 4, PL e according to EN/ISO 13849-1:2006 (former EN 954-1) and EN/IEC 61496-1/-2 type 4 requirements.

Before considering the use of Safetinex products in machine safety applications, it must be verified that the product certifications are valid in the country where the product is to be used.

The following chapters provide a brief introduction to the main standards and regulations applicable in the European Community and in North America. They are by no means a complete guide and only serve as a reminder of the most important issues. For detailed information, please refer to the original documents.

EUROPEAN SAFETY STANDARDS

This section is intended to provide help for designers and users of industrial machinery. It summarizes the basic principles of European directives, procedures and regulations in terms of protection against hazards in the work environment. It is by no means a complete guide and only serves as a reminder of the most important issues. For detailed information, please refer to the original documents.

TYPES OF SAFETY STANDARDS APPLICABLE IN THE EU

In the European Union, safety is legislated. The EU's Machinery Directive requires that all machines and safeguarding devices operating in EU countries meet essential safety standards. Harmonized European standards regarding machine safety policies are prepared by the CEN (European Committee for Standardization) or CENELEC (European Committee for Electrotechnical Standardization) and finalized by the EU Commission. Once ratified, these standards become European Standards (EN) that take precedence over national laws. Thus, EU countries must remove or modify any national standard that conflicts

with the European Standard. CENELEC and CEN cooperate closely with ISO and IEC, the main bodies for international standards.

Applicable standards usually have the prefix EN (“European Norm”), but most also have international – ISO/IEC – equivalents. There are different types of standards:

- A-type standards are basic safety standards applicable to all machinery, e.g. EN/ISO 14121
- B1-type standards set out special safety aspects and procedures, e.g. EN/ISO 13849-1
- B2-type standards set rules on safety equipment design, e.g. EN/IEC 61496-1, EN/TS/IEC 61496-2/-3
- C-type standards set safety requirements for a specific machine or type of machine

EXAMPLES OF SAFETY STANDARDS

In addition to the Machinery Directive 2006/42/EC and the Work Equipment Directive 89/655/EEC, there are standards that specifically focus on protective equipment, such as:

TYPE	SCOPE	EC STANDARDS	INTERNATIONAL STANDARDS
A - type standards	Safety of machinery Basic principles	EN 12100-1 EN 12100-2	ISO 12100-1 ISO 12100-2
	Risk assessment	EN 14121-1 EN 14121-2	ISO 14121-1 ISO 14121-2
B - type standards	Interlocking devices	EN 1088	ISO 14119
	Guards	EN 953	
	Safety related parts of control systems	EN 13849-1 EN 13849-2	ISO 13849-1 ISO 13849-2
	Safety of machines: Electro-sensitive protective equipment	EN 61496-1 CLC/TS 61496-2 CLC/TS 61496-3	IEC 61496-1 IEC 61496-2 IEC 61496-3
	Safety distance details	EN 13855	ISO 13855
	Positioning of protective equipment	EN 13855	ISO 13855

TABLE 1: EXAMPLES OF SOME APPLICABLE SAFETY STANDARDS

For additional information regarding European standards, please refer to www.cenorm.be, www.cenelec.be, www.din.de, www.iec.ch, www.iso.ch.

AN APPROACH TO EUROPEAN STANDARDS

The European Union has chosen to regulate the production, installation and use of old, modified and new machines within the European Union territory by approaching the parties concerned separately, i.e. one legal framework has been created for users and another for manufacturers.

The Work Equipment Directive sets out the rules applying to users of machines on production sites, while the Machinery Directive sets out those applying to machine constructors and safety equipment manufacturers. However, most subordinate standards apply to both parties, as shown in the following chart.




TABLE 2 : EUROPEAN MACHINE SAFETY OVERVIEW – USER AND MANUFACTURER SIDE.

THE USER SIDE

The user side is regulated by the Work Equipment Directive, which states that users of a machine are obliged to make sure that it complies with the legal requirements. Hence, if the user buys a machine which does not comply with the EU Machinery Directive, it is his responsibility to take the necessary actions to bring the machine up to the required quality and safety level.

Additionally, the Work Equipment Directive specifies what minimum regulations must be observed for safety purposes when work equipment is being used. The original text can be found on the relevant European Union website.

MACHINE MANUFACTURER SIDE

The manufacturer side is addressed by the Machinery Directive. This umbrella document refers to the specific requirements described in EN standards, and stipulates that each danger zone of a machine must be made safe. The method used to make different zones safe depends on the type of hazard.

The Machinery Directive requires that, before placing machinery on the market and/or putting it into service, the manufacturer ensures that a technical file is made available. This technical file shall comprise a construction file including, among others, “the documentation on risk assessment demonstrating the procedure followed, including:

- (i) a list of the essential health and safety requirements which apply to the machinery,
- (ii) the description of the protective measures implemented to eliminate identified hazards or to reduce risks and, when appropriate, the indication of the residual risks associated with the machinery.”
(Machinery Directive 2006/42/EC, Annex VII, A, 1, a)

Machines that are highly hazardous (as listed in Annex IV of the Machinery Directive) must conform to special procedures. The manufacturer is responsible for obtaining conformity through various procedures that may require examination of the machine by an EU notified body.

NOTIFIED BODIES

In order to have control over the execution of these directives, verification of certain steps by certifying bodies may be imposed by the directives. For example, all safety device concepts must be analyzed, checked and tested by such a third party organization. In many cases, this third party organization also audits the production process of a safety device manufacturer.

A notified (or certified) body is a certification, inspection or testing body designated by the notifying authority of an EU member state to issue attestations of conformity for products. Each EU member state has a list of notified bodies authorized to issue EU-type examination certificates. The lists include the identification number of each notified body, as well as the specific areas of activity and the tasks for which it has been designated.

European notified bodies responsible for carrying out conformity assessment procedures can be found through the NANDO (New Approach Notified and Designated Organizations) website, where accredited bodies can be searched for by country, product or directive. An official list of notified bodies responsible for assessing products in compliance with the Machinery Directive can also be found on the relevant European Union website.

NORTH AMERICAN SAFETY STANDARDS

This section is intended to provide help for designers and users of industrial machinery. It summarizes the basic principles of North American regulations and standards in terms of protection against hazards in the working environment. It is by no means a complete guide and only serves as a reminder of the important issues. For detailed information, please refer to appropriate agencies and documents.

A DIFFERENT APPROACH

Whereas European standards are mainly machine manufacturer oriented, North American standards are primarily directed towards users. Unlike in the EU, third party certification is not mandatory in the US or Canada. In terms of liability, it is the employer's responsibility to prove that he has done his utmost to ensure his employees' safety. However, certification has become a strong commercial asset in terms of market requirement. On users' request, national compliance agencies assess and grant the required certification.

Although the US and the EU have different methods for developing and applying standards, their purpose is the same, namely to ensure an appropriate level of safety in the workplace. Harmonized standards have the advantage of promoting world trade and reducing duplication of effort. Harmonized international standards allow manufacturers to access many markets with one product. Users profit from competitive products that meet uniform quality and functional requirements – wherever they were manufactured.

In the United States, standards are developed and enforced both by governmental agencies and industry groups. US employers, installers or OEMs are legally responsible for compliance with all applicable regulations, both national and international. In the US, the Occupational Safety and Health Administration (OSHA) is a federal agency that can enforce its regulations through penalties and fines.




FIG. 3: APPLICATION EXAMPLES OF YCA AND YBB DEVICES

OSHA REGULATIONS AND U.S. CONSENSUS STANDARDS

The Occupational Safety and Health Act passed on Dec. 29, 1970 established guidelines for safe and healthy working conditions.

Occupational and Health Standards in the U.S. are defined in Title 29 of the Code of Federal Regulations Part 1910. Subpart O of this document deals specifically with machinery and machine guarding, and defines the general requirements for all machines (1910.212) and for some specific types of machinery.

Encouraged and assisted by OSHA, more than half of the US states have developed their own safety and health programs and regulations which are then enforced by OSHA as “National Consensus Standards”. Information on both state plans and OSHA regulations may be obtained from their respective websites.

OSHA uses national consensus standards to further define machine protection requirements in addition to subpart O. In 1910.212, it states that *“The point of operation of machines whose operation exposes an employee to injury, shall be guarded. The guarding device shall be in conformity with any appropriate standards therefore, or, in the absence of applicable specific standards, shall be so designed and constructed as to prevent the operator from having any part of his body in the danger zone during the operating cycle.”*

“Any appropriate standards” refers to national consensus standards generally recognized in the industry. Bodies frequently referenced by OSHA include the American National Standards Institute (ANSI), the National Fire Protection Agency (NFPA), Underwriters Laboratories (UL) and the American Society of Mechanical Engineers (ASME).

As an example, ANSI B11.1 sets safety requirements for mechanical power presses, ANSI B11.15 specifies standards for pipe bending machines, ANSI B11 TR.1 gives ergonomic guidelines for the design, installation and use of machine tools, and ANSI/RIA R15.06 stipulates the safety requirements for industrial robots. Please consult national consensus standards bodies for complete listings.

NORTH AMERICAN STANDARDS FOR SAFETY ISSUES: UL, ANSI AND CSA

AMERICAN STANDARD AGENCIES

UL STANDARDS

Underwriters Laboratories Inc. is a testing organization established in 1894 and is authorized to conduct certification testing of any electrical device. Although UL certification is not mandatory, many companies strive to obtain its certification for products aimed at the U.S. market.

UL certification has two levels, namely listing certification, generally for final products, and recognition certification, for parts or components

built into a product. Once a product has obtained UL certification, additional on-site inspections are carried out on a quarterly basis to ensure that the production plant continues to manufacture products conforming to UL standards.

Since the purpose of UL standards is to eliminate the danger of fire or electric shock caused by electrical appliances, in principle only those appliances presenting such risks are subject to this certification.

For more details on the UL Standards, please consult the UL website.

ANSI STANDARDS

The American National Standards Institute was founded in 1918 to manage the standardization system in the US. It is not ANSI's task to create standards of its own, but rather to approve the standards set up by specialized organizations. Many UL standards have been converted into ANSI/UL standards.

For instance, ANSI standards include ANSI B 11.19: Standard for performance of safeguarding devices and ANSI/RIA R15.06: Standard for robot safety.

For more details on the ANSI Standards, please visit the ANSI website.

CANADIAN STANDARD AGENCIES

CSA STANDARDS

The Canadian Standards Association is an organization that administers and coordinates the standardization system in Canada. Cross-certification between the U.S. and Canada has been granted, based on the Mutual Recognition Agreement (MRA).

Electrical appliances connected to a public power source in Canada must conform to CSA Standards. Manufacturers of these products need to obtain C-UL or CSA certification, or the seller needs to apply for certification directly to the provincial authorities.

For more details on the CSA Standards, please visit the CSA website.

INTERNATIONAL STANDARD AGENCIES

International standards also play a significant role in North American machine safety. The two main international entities are the International Electrotechnical Committee (IEC) and the International Standards Organization (ISO). IEC is a recognized provider of standards in the electrotechnical field and is composed of national electrotechnical committees. ISO is an international federation of national standardization bodies. ISO and IEC influence international standards through formal relationships. In the US, ANSI coordinates with ISO and IEC through technical advisory groups (TAG).

DEFINITION OF HAZARDS AND RISK REDUCTION STRATEGY

EN/ISO 12100 serves as a basis for all subsequent standards. It describes every type of hazard that needs to be considered in terms of machine safety. Exposure to hazards includes numerous potential situations that must first be identified.

Mechanical hazards may result in crushing, shearing, cutting/severing, entanglement, drawing-in/trapping, impact, stabbing/puncture, friction/abrasion, injuries due to high pressure fluid ejection, etc. Machine hazards are also influenced by sharp edges, vibrations and unstable or moving objects. The list quotes electrical and thermal hazards, radiation, dust and hazardous substances (gas, vapors). In terms of ergonomics and the working environment, there are risks of falling, tripping or slipping. A combination of hazards may result in a specific new hazard.

EN/ISO 12100 subsequently gives general guidelines for eliminating or reducing hazards through prevention and protection. It is recommended to use technology that avoids most of the problems linked with the hazards listed above. Any decision that contributes to prevention against hazards is part of the security process and risk reduction strategy.

In this respect, taking ergonomic principles into consideration is important. A high level of automation will not only help operators, it will also increase productivity and reliability. Reducing unnecessary human movements and efforts can contribute to a safer working environment. Proper lighting of the work place will help to minimize hazards.

Operators must be able to stop machines at any time in case of an emergency. Starting and/or restarting the machine after an interruption must be carefully planned. When programmable electronic safety systems are used, the behavior of such systems in case of defect and the protection of the software requires particular attention.



RISK ASSESSMENT PROCESS

In essence, conducting a risk assessment involves identifying hazards, evaluating the potential severity of harm and identifying measures and solutions for eliminating or reducing such risks.

This requirement is stated in U.S. standards (Title 29 US Code of Federal Regulations, Part 1910, Subpart O).

For more details, please refer to the following documents:

- OSHA 3071, Job Hazard Analysis
- ANSI/RIA R15.06-1999, Safety Requirements for Industrial Robots and Robot Systems
- ANSI B11.TR3, Risk Assessment and Risk Reduction
- EN/ISO 14121, Principles of Risk Assessment. EN/ISO 14121 refers to additional standards, such as EN/ISO 13849-1 and EN/ISO 12100.

The following chart, based on EN/ISO 12100-1 and ANSI B11. TR3:2000, can be used to carry out risk analyses and ensure that all issues have been thoroughly considered. This iterative process must be carried out for every machine operating in the work place, as well as for all the potential hazards associated with each machine.




DIAGRAM 1: RISK ASSESSMENT PROCESS

This risk analysis and assessment process helps to take all the different aspects of potential machine hazards into consideration. It is important to document this procedure as evidence that the task has been fully carried out and to allow others to check it or use it for further improvements.



EN/ISO 14121 also describes procedures for identifying hazards and assessing risks, and provides guidance on the information required to achieve this goal. The process involves analyzing the risks in a systematic and documented way, in order to eliminate or reduce hazards. Qualitative and quantitative methods can be used.

All aspects of potential hazards must be taken into consideration:

- The phases of a machine's life
- The full range of foreseeable uses and misuses of a machine
- All persons possibly exposed to hazards when the machine is being used

Risk is defined as a function of the severity of possible harm and the probability that such harm occurs (frequency and duration of exposure, possibility of avoiding harm, etc.). One important piece of information is the history of accidents, if available.

Among the aspects to be considered when establishing elements of risk, the analysis should account for

- Different types of exposure depending on the type of work (setting, teaching, operating, cleaning, etc.)
- Human factors, such as applicability and ergonomic issues
- The reliability of safety functions, including their maintenance
- The possibility to defeat or circumvent safety measures

EN/ISO 14121-1:2007 gives a full list of hazards referenced by EN/ISO 12100.



In addition, the safety of any machine will diminish with time due to the deterioration of components, wear, loosening of parts, etc. It is therefore important to conduct regular inspections in order to detect defects that may lead to reduced safety, and to effect the necessary repairs before the level of risk exceeds the original assessment.

METHODS FOR DETERMINATION OF RISK LEVEL

The methods used for assessing the risks associated with a specific machine are addressed by several standards. Standards either impose or recommend corrective measures that will establish an adequate level of safety.

DETERMINATION OF RISK LEVEL IN NORTH AMERICA

In order to select the appropriate safety device adapted to the actual risks and dangers, it is important to assess the risk. ANSI B11.TR3-2000 provides a "Risk Estimation Matrix" in order to determine the level of risk depending on the cross-referenced factors of the probability of harm occurrence and harm severity:

PROBABILITY OF HARM OCCURRENCE	SEVERITY OF HARM			
	CATASTROPHIC	SERIOUS	MODERATE	MINOR
Very Likely	High	High	High	Medium
Likely	High	High	Medium	Low
Unlikely	Medium	Medium	Low	Negligible
Remote	Low	Low	Negligible	Negligible

TABLE 3: RISK ESTIMATION MATRIX AS PRESENTED BY ANSI B11.TR3-2000

The purpose of assessing the risk is to determine the appropriate level of safety. It is important that the protective device complies with the determined risk and is adapted to the machine control system. Risk assessment applies to each element that makes up the safety system, and not just the protective device itself. In particular, safety devices can only be used on machines that comply with control reliability as described in OSHA 29.1910.212 and ANSI B11.19-20.

Another important point to be considered is the life cycle of the machine and its protective devices. The safety of any machine will diminish with time due to the deterioration of components, wear, loosening of parts, etc. It is therefore important to conduct regular inspections in order to detect defects that may lead to reduced safety, and to effect the necessary repairs before the level of risk exceeds the original assessment.



EN/ISO 13849



DETERMINATION OF REQUIRED PERFORMANCE LEVEL (PL_r)


EN/ISO 13849-1 sets out a procedure for the selection and design of safety measures. The procedure contains the following 6 steps:

1. Identify the safety functions to be performed
2. Determine the required Performance Level
3. Design and technical realisation of the safety functions
4. Evaluate the achieved Performance Level
5. Verify the achieved Performance Level
6. Validate that all requirements are met

Based on risk identification, the required performance level of risk reduction is determined using the following graph sourced from EN/ISO 13849-1, Annex A.

The objective is to determine the required performance level PL_r that sets the requirements of the necessary safety system, depending on the risks involved in each case. As described below, three parameters are taken into consideration:

1. The potential severity of the harm
2. The frequency and/or duration of exposure to the hazard
3. The possibility of avoiding the hazard



- 1 starting point for evaluation of safety function contribution to risk reduction
- S severity of injury:
 - S1 slight (normally reversible injury)
 - S2 serious (normally irreversible injury or death)
- F frequency and/or exposure to hazard:
 - F1 seldom-to-less-often and/or exposure time is short
 - F2 frequent-to-continuous and/or exposure time is long
- P possibility of avoiding hazard or limiting harm:
 - P1 possible under specific conditions
 - P2 scarcely possible

DIAGRAM 2: REQUIRED PERFORMANCE LEVEL

In order to reduce the determined risk (PL_r) to an appropriate level, a safety system with performance level $PL \geq PL_r$ needs to be properly implemented. A corresponding average probability of dangerous failure per hour (PFH_b) can be associated with each performance level:

PERFORMANCE LEVEL (PL)	AVERAGE PROBABILITY OF DANGEROUS FAILURE PER HOUR
a	$10^{-5} \leq PFH_b < 10^{-4}$
b	$3 \times 10^{-6} \leq PFH_b < 10^{-5}$
c	$10^{-6} \leq PFH_b < 3 \times 10^{-6}$
d	$10^{-7} \leq PFH_b < 10^{-6}$
e	$10^{-8} \leq PFH_b < 10^{-7}$

TABLE 4: AVERAGE PROBABILITY OF DANGEROUS FAILURE PER HOUR

Safetinx Type 4 AOPDs meet all the requirements of Performance Level **e**. For details, please consult the product data sheet.



SPECIFIC STANDARDS FOR SAFETY DISTANCE CALCULATION

EN/ISO 13855 gives details concerning the positioning of safeguards with respect to the approach speeds of parts of the human body.

INSTALLATION

EN/ISO 13855

INSTALLATION RULES

All safety equipment has to be installed following the strict installation instructions given by the manufacturer and the applicable standards. Without proper installation, the safety device cannot fulfill its function and will give a false impression of safety to persons approaching a dangerous machine. EN/ISO 13855 defines the installation requirements for safety light curtains and access control barriers with respect to the approach speeds of parts of the human body. Below is a summary of the key concepts.

POSITIONING THE AOPD


The level of safety depends on the way the device is positioned. The risk assessment conclusions will help decide what position is best suited for preventing foreseeable hazards. In order to ensure proper safeguarding, special care must be taken to find the position that will not allow the protective device to be bypassed and such that any hazardous machine movement is safely stopped before potential harm occurs.

There are different classical ways to position safety light curtains:

- Vertically (“perpendicular approach”)
- Horizontally (“parallel approach”)
- In an L shape (vertically and horizontally combined)
- Inclined (“angular approach”).



FIG. 4: POSITIONING THE LIGHT CURTAIN



It must not be possible to pass over, below, around or go behind the protective field. When positioning access control barriers, it must not be possible to pass over the highest beam, below the lowest beam or between two beams. If this cannot be guaranteed, then additional protective devices must be used.

For practical details on L-shaped installations, please consult the relevant paragraph on page 34.

MINIMUM SAFETY DISTANCE REQUIRED

Since the principle of light curtains and access control barriers is to detect an intrusion early enough to intervene in the machine cycle before anyone has had time to reach the danger zone, positioning of protective equipment must respect the approach speed of parts of the human body, as well as the total response time of the installed safety system.

The following methodology, based on EN/ISO 13855, can be used to determine the proper minimum safety distance:




DIAGRAM 3: MINIMUM SAFETY DISTANCE EVALUATION PROCESS

MINIMUM SAFETY DISTANCE CALCULATION (EU)

In the following figures and formulas, the minimum safety distance (S) designates the distance between the beginning of the hazardous area and the protective screen, or the furthest protective beam in case of horizontal positioning of the AOPD.

According to EN/ISO 13855, the minimum safety distance depends on:

1. The approach speed of the body – or part thereof – to be detected
2. The total response time of the safety system:
 - a. Response time of the AOPD
 - b. Response time of the safety control unit
 - c. Machine stopping time (effective stopping of the machine's dangerous movement)
 - d. Any additional response delay
3. Resolution of the AOPD


EN/ISO 13855 defines a basic formula for calculating the minimum safety clearance between the protective device and the hazardous location:

$$S = K \times T + C$$

Parameters:

- S: Minimum safety distance between the AOPD sensing field and the hazardous area (mm). Cannot be less than 100 mm.
- K: Average approach speed at which a body or part of a body enters the detection zone (mm/s).
- T: Total response time (seconds), including
 - T_c : Response time of the protective device (in seconds, value provided on manufacturer's data sheet)
 - T_r : Response time of the safety relay (in seconds, value provided on manufacturer's data sheet)
 - T_m : Machine stopping time (in seconds, value provided by manufacturer or measured on request by specialists)

FIG. 5: MINIMUM SAFETY DISTANCE (EU)



C: Additional safety distance in mm, which depends on the resolution of the protective device. It cannot be less than zero.

R : Resolution of the protective device (mm)

C = $8 \times (R - 14 \text{ mm})$ where $R \leq 40 \text{ mm}$ (= 0 when the light curtain has a resolution of 14 mm)

C = 850 mm where $40 \text{ mm} < R \leq 70 \text{ mm}$

For a detection resolution $\leq 40 \text{ mm}$, the formula thus becomes:

$$S = K \times (T_c + T_r + T_m) + 8 \times (R - 14 \text{ mm})$$

For a detection resolution $40 \text{ mm} < R \leq 70 \text{ mm}$:

$$S = K \times (T_c + T_r + T_m) + 850 \text{ mm}$$

where

$$K = 2,000 \text{ mm/s}^*$$

The above calculation formula applies when the protective device is positioned vertically (perpendicular approach) or in case of an angular approach if the angle (β) between the protective field and the direction of entry exceeds 30° . S is then the distance from the hazardous point to the closest protective beam.

In the case of horizontal positioning of the protective device (parallel approach) or if the angle between the protective field and the direction of entry is less than 30° , the applicable formula is:

$$S = K \times (T_c + T_r + T_m) + (1,200 \text{ mm} - 0.4 \times H)$$

where

$$K = 1,600 \text{ mm/s}$$

H : Height of the lowest beam from the floor (max. 1000 mm).

Here, S is the distance from the hazardous point to the farthest protective beam.

The above calculation guidelines summarize the basic regulations and standards. For details, please refer to the applicable standard.

* if the calculated value of S is $> 500 \text{ mm}$, then recalculate S using

$$K = 1,600 \text{ mm/s.}$$

MINIMUM SAFETY DISTANCE CALCULATION (US & Canada)


The general safety distance calculation formula below is given in:

- ANSI B11.19-2003 Annex D Equation 7
- ANSI/RIA R15.06-1999
- CSA/CAN Z142-02
- Code of Federal Regulations (OSHA) Subpart O, Volume 29 Part 1910.217 (h) (9) (v) entitled "Machine Safeguarding"

$$D_s = K_s \times (T_s + T_c + T_r + T_{bm}) + D_{pf}$$

where

FIG. 6: MINIMUM SAFETY DISTANCE (US & Canada)



D_s The minimum safety distance in inches or mm from the hazardous zone to the detection point, plan or zone

K_s Approach speed of the body or parts of the body in inches/seconds or mm/second. ANSI standard B11.19-2003, ANSI/RIA R15.06-1999 and OSHA 1910.217(c) specify a recommended value of $K_s = 63$ inches/s (1,600 mm/s).

Components of the overall response time of the machine:

T_s Stop time of the machine tool measured at the final control element (seconds)

T_c Response time of the control system (seconds)

T_r Response time of the presence-sensing device and its interface (seconds)

T_{bm} Additional response time allowed for 'brake monitor' to compensate for wear. ANSI B11.19-2003 names it T_{spm} standing for "stopping performance monitor" (seconds).

Note: Any additional time delays must also be accounted for in this calculation.

D_{pf} Depth penetration factor, an additional distance added to the overall safety distance required. This value is based on the smallest detectable target size which depends on the protective device resolution (inches or mm).

When the AOPD is installed horizontally (parallel to direction of approach) or the angle (β) between the direction of approach and the sensing field is less than 30° , calculate D_s using the ANSI safety distance formula above, with $D_{pf} = 48$ inches. The safety distance is measured from the hazardous point to the sensing beam farthest away.

This calculation guideline summarizes the basic regulations and standards. For details, please refer to the applicable standards.

OTHER COUNTRIES

Every country is free to set its own rules and standards in terms of machine safety. Standards applicable in countries outside the European Union and the United States of America are determined by national law-making bodies.

For the correct use and installation of Safetinex products outside the European Union and the United States of America please consult the relevant national standards and directives.

ACRONYMS

ANSI	American National Standards Institute
AOPD	Active Optoelectronic Protective Device
BSI	British Standards Institution
CEN	European Committee for Standardisation
CENELEC	European Committee for Electrotechnical Standardisation
CLC	CENELEC (in document references)
CSA	Canadian Standards Association
DC _{avg}	Average Diagnostic Coverage
DIN	Deutsches Institut für Normung (German Institute for Standardization)
EC	European Community
EEC	European Economic Community
EN	European Norm
ESPE	Electro-Sensitive Protective Equipment
FMEA	Failure Mode and Effects Analysis
IEC	International Electrotechnical Commission
IEEE	Institute of Electrical & Electronics Engineers
ISO	International Organization for Standardization
MTTF _d	Mean Time To Dangerous Failure
NFPA	National Fire Protection Association
OEM	Original Equipment Manufacturer
OSHA	Occupational Safety and Health Administration
OSSD	Output Signal Switching Device
PES	Programmable Electronic Systems
PLC	Programmable Logic Controller
TS	Technical Specification
TÜV	Technischer Überwachungsverein
UL	Underwriters Laboratories Inc.



The Safetinx product range includes the following products:

SAFETINEX YBB FOR FINGER PROTECTION



- Safety light curtain with 14 mm resolution
- Protective height from 142 mm to 1690 mm
- Operating distance up to 3.5 m
- Cable version : 2, 5 and 10 m PUR-UL shielded cable
- M12 connector version
- Pigtail version (0.2 m PUR-UL shielded cable, M12 connector)

SAFETINEX YBB FOR HAND PROTECTION



- Safety light curtain with 30 mm resolution
- Protective height from 279 mm to 1827 mm
- Operating distance up to 12 m
- Cable version : 2, 5 and 10 m PUR-UL shielded cable
- M12 connector version
- Pigtail version (0.2 m PUR-UL shielded cable, M12 connector)

SAFETINEX YCA FOR ACCESS CONTROL



- Safety access control barriers with beam gap of 300, 400 or 500mm
- Protective height from 832 mm to 1532 mm
- Operating range: 1 ... 15 m / 10 ... 50 m (can be configured, for wiring information see table 8 on page 37)
- Cable version : 2, 5 and 10 m PUR-UL shielded cable
- M12 connector version
- Pigtail version (0.2 m PUR-UL shielded cable, M12 connector)

All Safetinx light curtains and access control barriers are Type 4 and Performance Level e compliant. Each component is housed in a rugged aluminum profile fitted with two lateral sliding grooves.

The Safetinx product range is complemented by a range of accessories. Please consult section "Available models" in this instruction manual or the Safetinx catalog for order information.

ADVANTAGES OF THE SAFETINEX RANGE

Safetinx safety devices offer the following advantages:

- Very short response time:
 - Finger protection 5.2 to 43.6 ms
 - Hand protection 5.2 to 24.4 ms
 - Access control 4.2 to 6.7 ms
- Up to 50 m operating distance
- 2-channel selection minimizing safety relevant cross-talk between neighboring AOPDs

- Fully compliant with industry standards and certified by internationally recognized organizations
- Certified Type 4 and Performance Level e devices
- Beam synchronized, no need for wired connection between sender and receiver
- Short-circuit protected outputs and voltage-reversal protection
- Low power consumption
- Built-in alignment system and easy adjustment of the units thanks to the high flexibility of the Safetinex bracket
- Various connector versions to fit any application
- Robust aluminum housing coated with resistant finish
- Compact design: 42 mm x 48 mm housing profile
- Competitive price

Furthermore, Safetinex light curtains and access control barriers have been designed to provide users with a comfortable work environment. Their use involves no additional unproductive movements and no waste of time. Users can freely access and move around the machine in complete safety.

SCOPE OF THIS TECHNICAL DOCUMENTATION

This section contains useful information for the selection, installation, operation and maintenance of Safetinex light curtains and access control barriers. It is intended for skilled personnel with a knowledge of safety issues and electronic equipment. For safety compliance of your installation, please refer to the relevant standards and directives.

OPERATING PRINCIPLE




FIG. 7: OPERATING PRINCIPLE

Safetinex light curtains and access control barriers are optoelectronic safety devices that include a sender and a receiver unit between which coded infrared beams are sequentially exchanged. The receiver unit is connected to a safety relay which transmits signals to the machine control system. Synchronization between the sender and receiver de-

VICES is performed optically, i.e. wired connection between the two units is not necessary.

Reception of all beams activates the two independently generated semiconductor outputs (OSSDs) of the receiver unit. The interruption of one or more beams deactivates the outputs within the response time of the AOPD. Any internal fault is detected by the device's permanent self-control function and has the same result as an intrusion into the protective field.

SELF PROTECTED OUTPUTS

Both OSSD1 and OSSD2 are self-protected and actively monitored PNP outputs. Both outputs are controlled by independent current-monitored high-side switches. Thanks to continuous monitoring, any short-circuit between an output and the power supply or ground is detected within the response time, leading to the deactivation of the other output. Similarly, a cross-circuit between the two outputs is also detected and both OSSDs are deactivated within the specified response time. The OSSD outputs are switched off and remain in that state as long as the fault remains.

RESOLUTION (R) OF AN AOPD

The resolution of an AOPD is the minimum diameter that an intruding object must have in order to interrupt, at any angle, at least one of the light beams. The resolution R of an AOPD is dependant on the beam gaps and diameter:

$$R = i + b$$

where i is the interval between the beam axes
and b is the effective infrared beam diameter



FIG. 8: RESOLUTION R OF AN AOPD

Safetinx YBB light curtains have resolutions of 14 mm and 30 mm, depending on the model, YCA access control devices have beam gaps from 300 mm to 500 mm. For details and order information, please consult section "Available models" in this instruction manual or the Safetinx catalog.

LED STATUS INDICATORS

Sender and receiver units consist of an optical part (lenses) and a LED indicator panel. The LEDs on the sender and receiver units indicate the operating status of the AOPD as shown below:




FIG. 9A: LED INDICATORS ON SENDER UNIT

SENDER

LED	FINGER & HAND PROTECTION (YBB)	ACCESS CONTROL (YCA)
Mode	yellow when test mode is active	OFF when max. sensing range = 15 m blue when max. sensing range = 50 m red or purple when wiring fault occurs
Channel	blue when channel 1 is selected purple when channel 2 is selected	
Alignment	steady orange when the screen is not fully aligned blinking orange when the first third of the screen is aligned OFF when screen is fully aligned	
Alignment	steady orange when the lowest beam is not aligned blinking orange when the lowest beam is aligned OFF when screen is fully aligned	

RECEIVER




FIG. 9B: LED INDICATORS ON RECEIVER UNIT

LED	FINGER & HAND PROTECTION (YBB) AND ACCESS CONTROL (YCA)
Power	green when power is ON
Channel	blue when channel 1 is selected purple when channel 2 is selected
Status	green when OSSD outputs are ON
Status	red when OSSD outputs are OFF

CONFIGURABLE FUNCTIONS

At wiring, YBB light curtains offer two user-controlled functions, namely "transmission channel selection" and "test mode selection".

YCA access control barriers offer "transmission channel selection" and "operating range selection".

TRANSMISSION CHANNEL SELECTION (YBB AND YCA)

Installing several light curtain pairs or access control barriers close to each other may lead to safety relevant optical crosstalking. Using different channels helps avoiding this problem. The transmission channel is selected through the polarity of the supply voltage on the sender and receiver unit. See tables 7 through to 8 on page 37 for the channel related pin connections. The "Installation of multiple systems" section below gives details on how to install the devices in opposite directions for L-shaped positioning.

TEST MODE SELECTION (YBB)

The sender unit is equipped with a test mode function controlled through the voltage supply on the test input. Enabling the test mode stops the light beams, simulating an intrusion into the protective field. Note that, as type 4 protective devices, YBBs are self-testing. However, the test input may be useful for system setup, to ensure that the machine control circuit operates properly or, to determine the actual response time of the overall safety setup. Table 5 below shows the test functions triggered by the pin connections on the sender unit.

TEST INPUT	FUNCTIONALITY
24 Volts	Test disabled
0 Volts or not connected	Test enabled, intrusion simulated

TABLE 5: TEST MODE SELECTION ON YBB DEVICES

For pin assignment information, please consult tables 7 and 8 on page 37.

OPERATING RANGE SELECTION (YCA)



Safety access control barriers (YCA) are equipped with an option to select an operating range of either 1...15m or 10...50m. For pin assignment information, please refer to tables 7 and 8 on p. 37. Please note that for safety reasons, the distance between the sender unit and the receiver unit must conform to the values of the selected operating range.

INSTALLATION

Depending on the working environment where the light curtain or access control barrier is to be installed, various factors must be taken into consideration, such as reflective surfaces neighboring the safety device or other safety devices that may potentially cause interference. Other basic safety installation rules include preventing access to the point of hazard through the correct positioning of the protective screen.

Installation of Safetinex protective devices involves the following steps:

- Calculation of the minimum safety distance
- Mounting the sender and receiver units
- Connecting the light curtain or access control barrier
- Aligning the units
- Performing tests before initial commissioning

MINIMUM SAFETY DISTANCE

The distance between the protective field and the hazardous area must be calculated with great care and in compliance with strict regulations.

Since these regulations differ slightly, depending on the country where the safety system is operated, please refer to the relevant preceding chapters and the applicable standards for details.

RECOMMENDED BEAM HEIGHTS FOR ACCESS CONTROL DEVICES

For vertical installation of multiple light beam devices, such as YCA products, EN/ISO 13855 recommends different combinations of the number of beams, height of the lowest beam above the reference plane and beam gap:

NUMBER OF BEAMS	BEAM HEIGHT ABOVE REFERENCE PLANE, E.G. FLOOR (mm)
4	300, 600, 900, 1200
3	300, 700, 1100
2	400, 900

TABLE 6: RECOMMENDED BEAM HEIGHTS FOR ACCESS CONTROL DEVICES



For any other combination, the user must perform the risk analysis described in the preceding chapters and the applicable standards, and make sure that the use of the access control device for his application cannot lead to any dangerous situation.

POSITIONING THE SENDER AND RECEIVER UNITS

Safety light curtains and access control barriers can be installed vertically to be used as a shield in front of, or around a hazardous zone. In cases where a larger surface around the hazardous machine needs to be safeguarded, a horizontally mounted AOPD may be appropriate.



Generally speaking, it must not be possible to pass over, around, below or go behind the protective field of the AOPD. When positioning access control barriers, it must not be possible to pass over the highest beam, below the lowest beam or between two beams. If this cannot be guaranteed, then additional protective devices must be used.



FIG. 10: POSITIONING THE LIGHT CURTAIN

If both vertical and horizontal accesses need to be secured, then two protective screens forming an "L" shape, one vertical and one horizontal, are necessary.




FIG. 11: L-SHAPED INSTALLATION OF THE LIGHT CURTAIN

For practical details on L-shaped installations, please consult the relevant paragraph on page 34.

DISTANCE FROM REFLECTIVE SURFACES

Reflective surfaces (such as mirrors, glass panes, polished metal parts, etc.) located near the light beams may cause undesired reflections of safety relevant light beams. This can result in a failure to detect opaque objects in the protection field. To avoid such problems, a minimum distance must be maintained between the protective field and any reflective surface, whether above, below or to the side.

The minimum distance (a) between the protective field and a reflective surface depends on the operating distance (d) between the sender and receiver units. The longer the operating distance, the further away reflective surfaces must be kept from the protective field.




FIG. 12: DISTANCE BETWEEN REFLECTIVE SURFACE AND PROTECTIVE FIELD IS TOO SHORT; A REFLECTED BEAM UNINTENTIONALLY REACHES THE RECEIVER




FIG. 13: DISTANCE BETWEEN REFLECTIVE SURFACE AND PROTECTIVE FIELD IS RESPECTED: NO UNDESIRABLE REFLECTIONS

The following diagram shall be used to determine the appropriate distance.




DIAGRAM 4: MINIMUM DISTANCE BETWEEN BEAMS AND REFLECTIVE SURFACE (A) IS DEPENDANT ON OPERATING DISTANCE (D)

INSTALLATION OF MULTIPLE SYSTEMS

Each receiver must only and exclusively receive beams from its matching sender. Installing several pairs of AOPDs close to each other may lead to optical crosstalk and result in failing to identify objects within the protective field (Fig. 14).




FIG. 14: INTERFERENCE BETWEEN TWO PAIRS OF PROTECTIVE DEVICES

To eliminate the possibility of optical crosstalk, units shall be separated by an opaque shield (Fig. 15).




FIG. 15: OPAQUE SHIELD SEPARATION BETWEEN TWO PAIRS OF PROTECTIVE DEVICES



When using an L-shaped installation, the units must be positioned in such a way that the beams run in opposite directions and the top of the units touch (Fig. 16). Furthermore, the two pairs of AOPDs must run on different transmission channels (Fig. 16).




FIG. 16: L-SHAPED INSTALLATION: OPPOSITE DIRECTION AND DIFFERENT TRANSMISSION CHANNELS

For details on wiring AOPDs in different transmission channels, please consult tables 7 and 8 on page 37.

MECHANICAL INSTALLATION

The sender and receiver units must be mounted with their optical panels accurately facing each other. The distance between the two optical faces must be within the specified operating range of the model.

The appropriate mounting devices must be used to fix the units. Depending on the application and the available space, two different mounting options are available:




FIG. 17: TOP AND BOTTOM MOUNTING BRACKET (REF. YXW-0001-000)

1. The mounting brackets for use at both ends of the units. These brackets can be fixed either in the same plane or at any angle. (Fig. 18) illustrates some mounting possibilities.




FIG. 18: DIFFERENT MOUNTING POSSIBILITIES WITH BRACKETS

2. The metal T-nuts, which can be slid into the side groove of the aluminum profile. These T-shaped M5 threaded nuts can be freely adjusted along the unit's side. To ensure firm alignment, the fixing points must be set in relation to the length of the device and as close as possible to the unit's ends.




FIG. 19: T-NUT (REF. YXW-0003-000)




FIG. 20: USING T-NUT WITH M5 SCREW

CONNECTING THE PROTECTIVE DEVICE

Please note that all electrical connections must be performed by experienced and qualified personnel.

Depending on the model, all electrical connections are made via cable, M12 connector. Connections are located at the bottom of both the sender and receiver units.



POWER SUPPLY

The power supply to both the sender and receiver units must be 24 V DC \pm 20% for YBB models and 24 V DC \pm 15% for YCA models. The power consumption of YBB and YCA protective devices depends on the model. Please refer to the data sheets for details.

The external supply voltage must be capable of buffering brief main voltage failures of 20 ms as specified in EN 60204-1.

Use a dedicated 24 V DC, Class 2 Safety Extra-low Voltage (SELV) or Protective Extra-low Voltage (PELV) power supply to supply each unit. These power supplies provide the necessary protection to ensure that under normal and single-fault conditions, the voltage between the different conductors, and between conductors and functional earth, does not exceed a safe value.

ELECTROMAGNETIC COMPATIBILITY (EMC)

In terms of immunity to electromagnetic fields, Safetinex protective devices fully comply with EN 55011/A2 and EN 61000-6-4 (electrostatic discharge, electrical and radio-frequency disturbances). Proximity to potential electromagnetic interference is acceptable within the limits of these standards.

In case of presence of strong electromagnetic fields, the use of shielded 5-pin cables is strongly recommended.

LIGHT RADIATION

Additional measures may be necessary to ensure that the AOPD does not fail to danger when other forms of light radiation are present in a particular application (for example, use of cableless control devices on cranes, radiation from weld spatter or effects from stroboscopic light).

PIN ASSIGNMENT

M12 CONNECTOR AND CABLE

Figure 21 and Tables 7/8 describe how the M12 connector pins or wires must be connected in order to achieve the selected functions.




FIG. 21: M12 PIN ASSIGNMENT

M12 PIN AND WIRE ASSIGNMENT ON FINGER & HAND PROTECTION DEVICES (YBB MODELS)					
PIN	WIRE COLOR	EMITTER		RECEIVER	
		ASSIGNMENT	FUNCTION	ASSIGNMENT	FUNCTION
1	brown	supply voltage	<ul style="list-style-type: none"> • 24 VDC for Channel 1 • 0 V for Channel 2 	supply voltage	<ul style="list-style-type: none"> • 24 VDC for Channel 1 • 0 V for Channel 2
2	white	-	reserved	output	OSSD1
3	blue	supply voltage	<ul style="list-style-type: none"> • 0 V for Channel 1 • 24 VDC for Channel 2 	supply voltage	<ul style="list-style-type: none"> • 0 V for Channel 1 • 24 VDC for Channel 2
4	black	test mode	<ul style="list-style-type: none"> • 0 V: test active • 24 V: test inactive 	output	OSSD2
FE	gray	functional Earth	shield	functional Earth	shield

TABLE 7: M12 PIN AND WIRE ASSIGNMENT AND FUNCTIONALITY ON YBB MODELS

M12 PIN AND WIRE ASSIGNMENT ON ACCESS CONTROL DEVICES (YCA MODELS)					
PIN	WIRE COLOR	EMITTER		RECEIVER	
		ASSIGNMENT	FUNCTION	ASSIGNMENT	FUNCTION
1	brown	supply voltage	<ul style="list-style-type: none"> • 24 VDC for Channel 1 • 0 V for Channel 2 	supply voltage	<ul style="list-style-type: none"> • 24 VDC for Channel 1 • 0 V for Channel 2
2	white	sensing range selection	<ul style="list-style-type: none"> • 0 V for 10... 50m • 24 V for 1... 15m 	output	OSSD1
3	blue	supply voltage	<ul style="list-style-type: none"> • 0 V for Channel 1 • 24 VDC for Channel 2 	supply voltage	<ul style="list-style-type: none"> • 0 V for Channel 1 • 24 VDC for Channel 2
4	black	sensing range selection	<ul style="list-style-type: none"> • 24 V for 10... 50m • 0 V for 1... 15m 	output	OSSD2
FE	gray	functional Earth	shield	functional Earth	shield

TABLE 8: M12 PIN AND WIRE ASSIGNMENT AND FUNCTIONALITY ON YCA MODELS

SAFETINEX SAFETY RELAY YRB-4EML-31S

As a part of the Safetinx product line, the safety relay YRB-4EML-31S can be used to connect YBB and YCA protective devices to the machine control system. The relay complies with the requirements of Category 4 / Performance Level e according to EN/ISO 13849-1. It can be used in applications up to Category 4 / Performance Level e according to EN/ISO 13849-1 and SIL 3 according to EN 62061. Its LEDs indicate the power supply as well as channel 1 and 2 activation.



FIG. 22: SAFETY RELAY YRB-4EML-31S




FIG. 23: BLOCK DIAGRAM

RESPONSE TIME FROM PROTECTIVE FIELD INTRUSION TO SWITCHING OF SAFETY RELAY

For proper calculation of the minimum safety distance, it is essential to understand that every element in the machine safety chain contributes to a delay in the so-called 'overall' or 'total response time' of the safety system.

To visualize this, please note that the figure below indicates the reaction time of an AOPD wired to YRB-4EML-31S safety relay. Additional machine control elements as well as the machine's own stopping time will increase the 'overall' or 'total response time' of the safety system as described in the chapters "MINIMUM SAFETY DISTANCE CALCULATION (EU)" and "MINIMUM SAFETY DISTANCE CALCULATION (US & CANADA)" above.





FIG. 24: SEQUENCE OF RELAY SWITCHING OPERATION

CONNECTION EXAMPLES FOR YRB-4EML-31S SAFETY RELAY

Below are two typical examples for connecting a Safetinx AOPD, using channel 1, to a Safetinx YRB-4EML-31S relay:

1 - For **Manual Restart** mode:



* Test button is only applicable for YBB models.


AOPD pin numbers refer to M12 connector.

FIG. 25: CONNECTION DIAGRAM FOR MANUAL RESTART MODE



Important notice: the restart button must always be located outside the hazardous area!

2 - For **Automatic Restart** mode:
 (YBB models only. Automatic restart is **not allowed** for YCA access control devices)



Light curtain pin numbers refer to M12 connector.

FIG. 26: CONNECTION DIAGRAM FOR AUTOMATIC RESTART MODE

ALIGNMENT OF SENDER AND RECEIVER UNITS

To complete the installation of the AOPD and to ensure proper functioning of the protective device, the sender and the receiver must be accurately aligned. Perfect alignment is achieved when each emitted light beam reaches its corresponding optical element on the receiver unit. This means positioning the two units so that the maximum amount of emitted light energy reaches the receiver element. The specified maximum optical aperture angle ($\pm 2.5^\circ$) requires accuracy in aligning the two units before they are firmly fixed in place.


During the alignment process, the OSSD output signals of the protective device must not have any effect on the machine. Make sure the machine remains switched off.

The alignment process is facilitated by two dedicated orange LED indicators on the sender unit. Figure 27 shows how the two LEDs behave during the alignment process.




Please make sure that the sender and the receiver units operate on the same transmission channel. For details on channel selection please refer to tables 7 to 8 on page 37.

Alignment process using the orange LED indicators on the **emitter** unit




Starting state: Both LEDs are on, meaning that

- AOPD is not aligned
- No emitted light beam hits the receiver




Step 1: Top LED is on, bottom LED is blinking, meaning that

- Only lowest beam hits the receiver
- The other light beams are not aligned at all



Step 2: Both LEDs are blinking, meaning that

- The first/lowest third of light beams hit the receiver
- The other light beams are not aligned yet



Step 3: Both LEDs are off, meaning that

- AOPD is correctly aligned
- All light beams hit the receiver

FIG. 27: ORANGE LEDS FOR ALIGNMENT

Alignment is achieved in three steps. During this process, please ensure that the green "Power" LED on the receiver remains on:

1. Mount one unit firmly and in its final position. Position the other unit so that the lower orange LED blinks. This confirms that the lowest beam (closest to the LED panel) is aligned.
2. Slightly rotate or tilt the loose unit until the upper orange LED blinks. When both orange LEDs are blinking, one third of the beams are properly aligned.
3. Adjust the loose unit again until both orange LEDs go off. All the beams of the AOPD are now properly aligned. Firmly fix position of both units.



TEST BEFORE THE FIRST COMMISSIONING

Before connecting OSSD1 and OSSD2 to the machine control, perform the "Daily functional test" as described in chapter "Testing and maintenance" below. This final test ensures that the protective device is operating properly.

DAILY FUNCTIONAL TEST

As operating conditions in the working environment may change from day to day, it is very important to perform the functional test daily, at change of shifts, and at each change of the machine operating mode. This will ensure the effectiveness of the protective device.

FINGER & HAND PROTECTION DEVICES (YBB MODELS)

The test must be performed with the supplied test rod. In case of multiple light curtains in the installation, make sure that the diameter of the test rod matches the resolution indicated on the light curtain units.

Do not use your fingers, hand or arm to check the protective field. Only use the appropriate rod.

Perform the test at three different locations within the protective field, from top to bottom, or from bottom to top.

- Close to the receiver unit
- Close to the sender unit
- In the middle between the receiver and the sender units

While moving the rod slowly* and perpendicularly to the protective field, keep an eye on the red LED on the receiver unit. As long as the rod is within the protective field, the red LED must remain on (note that the bottom green LED lights up when the red LED goes off and vice versa). If the red LED goes off even at just one point, the test has failed and the protected machine cannot be used until proper maintenance has solved the problem.

Use a daily testing log file as printed on page 45 of this manual to make sure the test is carried out on a daily basis.




FIG. 28: DAILY ROD TEST

* Please note that, according to IEC 61496-2, the maximum rod speed must not exceed 1.6 m/s.

ACCESS CONTROL DEVICES (YCA MODELS)

The test must be performed using an opaque object, with a size of at least 35mm x 35mm to completely cover each safety relevant light beam.

- Perform the test at three different locations within the protective screen:
- Close to the receiver unit
 - Close to the sender unit
 - In the middle between the receiver and the sender units

When covering each light beam, the red LED on the receiver unit must light up. If the red LED goes off even at just one point, the test has failed and the protected machine cannot be used until proper maintenance has solved the problem.

Use a daily testing log file as printed on page 45 of this manual to make sure the test is carried out on a daily basis.

TROUBLESHOOTING



In case of a malfunction, first make sure the machine is completely stopped and all potential dangers have been eliminated before proceeding any further.

The following chart will help quick troubleshooting in the case of a malfunction.

LED DISPLAY	POTENTIAL CAUSE	MEASURES TO CLEAR ERROR
Yellow 'Mode' LED (on YBB sender) is lit	Protective device is in Test Mode	Connect test input to 24 V in order to disable test mode (see tables 7-8 on page 37).
'Mode' LED (on YCA sender) is lit red or purple	Incorrect wiring	Check wiring (see tables 7-8 on page 37).
Sender Channel LED color does not match receiver Channel LED color	Sender and receiver units do not use the same transmission channel	Check the connectors wiring and match the sender and receiver transmission channels (see tables 7-8 on page 37).
Orange alignment LED (Sender) is on or blinking	Protective device alignment is poor	Follow instructions describing how to align the protective device (see figure 27 above).
Power LED (receiver) does not light up	No operating voltage or voltage is too low	Check the connection cables. Check the voltage supply.
Receiver red LED remains lit	Protective field is obstructed	Remove any object in the protective field.
	or alignment is poor	Realign the sender and receiver units (see figure 27 above).
	or fault detected	Switch the power supply off and on again on both units.
Receiver red LED is on Sender LEDs are off except channel LED	The last (highest) beam is obscured	Clear last beam.
	or non-matching channels	Match channels (see tables 7-8 on page 37).
	or OSSD short-circuit	Ensure that OSSDs are neither shorted together, nor connected to 0V or 24VDC.
	or device malfunction	Return unit for revision.

TABLE 9: TROUBLESHOOTING

PREVENTIVE PERIODIC INSPECTIONS

The EU directive on the use of machinery equipment stipulates the regular inspection of safety devices. Light curtains and access control barriers must be periodically tested by qualified and trained personnel. This allows early detection of new hazards and helps maintain the necessary level of safety. At the same time, it should be checked that the protective devices function in accordance with the current use of the machine. Periodic inspections give the opportunity to ensure that the type of protective device corresponds to the hazards actually encountered, that the user cannot bypass it and that nothing hinders its functionality.

Please use a form such as the one on page 45 of this manual. It will help keep track of periodic testing.

CLEANING

In order to keep the protective device in full operating condition and prevent potentially biased results, the active screens on the sender and receiver units must be regularly cleaned. The cleaning frequency depends on the ambient air pollution and the presence of dust and dirt on the screen. Use a mild and non-abrasive detergent to remove dirt from these surfaces, then dry the screen with a soft cloth. After cleaning, the daily functional test, as described above, must be performed in order to detect potential position changes of the protective devices.

DAILY TESTING LOG FILE


The following tests must be carried out every day the protective device is in operation.

The tests must be conducted by authorized and trained personnel, and entered in a log file as printed on page 45 of this manual.

- Check for signs of external damage, particularly to the front screen, the mounting or the electrical connections.
- Check that it is not possible to access the machine's danger zone from any unprotected area.
- Test the protective field: Perform the daily functional test as described above.

If any of the above tests have failed, block the machine immediately to prevent its use and notify the supervisor.


AVAILABLE MODELS



BEAM RESOLUTION: 14 MM

Part reference	Protective Height Hs [mm]	Housing Height Hb [mm]	Total Height Ht [mm]	Number of Beams	Current Consumption [mA]	Response Time [ms]	MTTF _d [years]	DC _{avg}
YBB-14x4-0150-G012	142	221	251	17	140	5.2	142	96%
YBB-14x4-0250-G012	271	350	380	33	145	8.4	114	96%
YBB-14x4-0400-G012	400	479	509	49	150	11.6	96	95%
YBB-14x4-0500-G012	529	608	638	65	160	14.8	83	95%
YBB-14x4-0700-G012	658	737	767	81	165	18	73	95%
YBB-14x4-0800-G012	787	866	896	97	170	21.2	65	94%
YBB-14x4-0900-G012	916	995	1025	113	175	24.4	59	94%
YBB-14x4-1000-G012	1045	1124	1154	129	180	27.6	53	94%
YBB-14x4-1200-G012	1174	1253	1283	145	190	30.8	49	94%
YBB-14x4-1300-G012	1303	1382	1412	161	195	34	45	94%
YBB-14x4-1400-G012	1432	1511	1541	177	200	37.2	42	94%
YBB-14x4-1600-G012	1561	1640	1670	193	205	40.4	39	94%
YBB-14x4-1700-G012	1690	1769	1799	209	210	43.6	37	94%


x = S for sender / R for receiver / K for kit (sender + receiver)



BEAM RESOLUTION: 30 MM

Part reference	Protective Height Hs [mm]	Housing Height Hb [mm]	Total Height Ht [mm]	Number of Beams	Current Consumption [mA]	Response Time [ms]	MTTF _d [years]	DC _{avg}
YBB-30x4-0250-G012	279	350	380	17	130	5.2	142	96%
YBB-30x4-0400-G012	408	479	509	25	130	6.8	126	96%
YBB-30x4-0500-G012	537	608	638	33	135	8.4	114	96%
YBB-30x4-0700-G012	666	737	767	41	140	10	104	95%
YBB-30x4-0800-G012	795	866	896	49	145	11.6	96	95%
YBB-30x4-0900-G012	924	995	1025	57	145	13.2	89	95%
YBB-30x4-1000-G012	1053	1124	1154	65	150	14.8	83	95%
YBB-30x4-1200-G012	1182	1253	1283	73	155	16.4	77	95%
YBB-30x4-1300-G012	1311	1382	1412	81	155	18	73	95%
YBB-30x4-1400-G012	1440	1511	1541	89	160	19.6	69	95%
YBB-30x4-1600-G012	1569	1640	1670	97	165	21.2	65	94%
YBB-30x4-1700-G012	1698	1769	1799	105	170	22.8	62	94%
YBB-30x4-1800-G012	1827	1898	1928	113	175	24.4	59	94%

x = S for sender / R for receiver / K for kit (sender + receiver)



BEAM GAP: 300 ... 500 MM											
Part reference	Numb. of Beams	Beam Gap Bg [mm]	Protective Height Hs [mm]	Height Extension He [mm]	Housing Height Hb [mm]	Total Height Ht [mm]	Current Consump. [mA]	Resp. Time [ms]	MTTF _d [years]	DC _{avg}	
YCA-50x4-4300-G012	4	300	932	121	1124	1154	110	5.0	100	96.9%	
YCA-50x4-5300-G012	5	300	1232	79	1382	1412	110	5.9	94	96.8%	
YCA-50x4-6300-G012	6	300	1532	37	1640	1670	110	6.7	88	96.8%	
YCA-50x4-3400-G012	3	400	832	92	995	1025	110	4.2	108	96.9%	
YCA-50x4-4400-G012	4	400	1232	79	1382	1412	110	5.0	100	96.9%	
YCA-50x4-3500-G012	3	500	1032	21	1124	1154	110	4.2	108	96.9%	

x = S for sender / R for receiver / K for kit (sender + receiver)

TECHNICAL DATA	
Dimensions	42 mm x 48 mm x Ht
Supply voltage	24 VDC \pm 20% (YBB) / \pm 15% (YCA)
Current consumption sender (TX)	50 mA max. / 1.5 W max. (YBB) 35 mA max. / 1.0 W max. (YCA)
Current consumption receiver (RX) (excl. load)	160 mA max. / 4.7 W max. (YBB) 75 mA max. / 2.2 W max. (YCA)
Outputs	2 PNP outputs short-circuit protected
Output current	Max. 0.2 A per output
Output voltage ON min.	-1.0 V of the operating voltage at T = 25 °C (77 °F)
Output voltage OFF max.	1.0 V
Leakage current	< 1 mA
Maximum load inductance	100 mH
Response time	See «Available Models» table above
Sender, wavelength	IR 950 nm for YBB-14 IR 850 nm for YBB-30 and YCA
Resolution (YBB)	14 mm for YBB-14 30 mm for YBB-30
Beam gap (YCA)	300 ... 500 mm
Operating range	0.25 ... 3.5 m for YBB-14 0.25 ... 12 m for YBB-30 1 ... 15 m / 10 ... 50 m for YCA
Safety level	Cat. 4, PL e (EN/ISO 13849-1) Type 4 (IEC 61496-1/-2) SIL 3 (IEC 62061)
Operating temperature	-35 ... +60°C (-31 ... +140°F)
Storage temperature	-40 ... +70°C (-40 ... +158°F)
Humidity	15 ... 95 % (non-condensing)
Protection class	Class III (IEC 61140)
Degree of protection (EN 60529) (depending on model)	IP 65 + IP 67
Ambient brightness	TS 61496-2
Reference standards	IEC 61496-1, IEC 61496-2
Housing material	Aluminum
Material of upper and lower cover	PA + 30% fiberglass
Material of optics	PMMA
Cable runs	100 m max (at 10 nF capacitive load)

DISCLAIMER

A safety light curtain or access control barrier is a safety device, designed to protect operators and other personnel working around a potentially dangerous machine. Before installing or using a safety light curtain or access control barrier the following requirements must be met:

- This instruction manual is part of the Safetinex light curtain or access control barrier. It must remain accessible during its whole life cycle for anybody in charge of installation, operation, maintenance, cleaning and safety control.
- Safetinex products are only safe protective devices if all the procedures in this instruction manual and in the related documents are carefully followed and fully complied with. If these instructions are not entirely followed, or the safety device is subject to manipulation, it may lead to serious injury or death. Contrinex AG declines any responsibility in case of faulty installation and/or manipulation of Safetinex devices.
- In any installation where the light curtain or access control barrier is used as a safety device, the employer is responsible for ensuring that all applicable governmental requirements are satisfied. The installer is also responsible for complying with all local laws and standards.
- The installation and inspection of the protective device must be performed by trained and qualified specialists, i.e. personnel technically experienced in operating the machinery and the specific protective device involved, and well aware of the applicable safety regulations and standards.
- The employer must ensure that all machine operators, maintenance personnel, supervisors, etc. are familiar with and understand all instructions regarding the proper use of the light curtain or access control barrier, the machinery on which it is installed and the appropriate safety regulations. Operators must be instructed and trained by qualified specialists.
- Optoelectronic protective devices cannot be used as stand-alone solutions if the operator is exposed to any risk of injury from flying or splashing (e.g. molten) materials. Light curtains or access control barriers do not offer protection against flying objects.
- The machine for which the safety light curtain or access control barrier is installed must be able to stop its motion at any point in its cycle.
- Light curtains or access control barriers cannot be used on any machinery that has an irregular stopping time or inadequate control devices or mechanisms.
- Light curtains or access control barriers cannot be used where the environment may weaken the efficiency of the protective device.
- If the light curtain or access control barrier cannot protect all accesses to the hazardous area, additional safeguards, such as mechanical guards, may be required.

- All brakes and other stopping mechanisms and controls must be inspected regularly to ensure they are in proper working order. If the stop mechanisms are not performing properly, the machine may not stop safely even though the light curtain or access control barrier is functioning properly.
- The test procedure described in this instruction manual must be performed during installation and after any maintenance, cleaning, adjustment, repair or modification to the light curtain or access control barrier, or the machine. In addition, the test procedure must be carried out every time the system is started, in general, once a day.
- The log file presented in this manual must be used to document the regular testing of Safetindex products. Contrinex AG declines any responsibility if the test procedure has not been carried out as prescribed in this instruction manual and fully documented in the log file. Testing ensures that the light curtain or access control barrier and the machine control system properly stop the machine.
- The device contains no parts that require maintenance. In case of failure, do not open the device, but send it to manufacturer for repair. Opening the device or implementing unauthorized changes voids any warranty.
- Contrinex AG declines any responsibility if the protective device is not used for its specific purpose, or if it has been modified, whether before, during or after installation.

The enforcement of these requirements is outside Contrinex's control. The employer is responsible for following the above provisions and any other procedures, conditions and requirements specific to the machinery.

EC DECLARATION
OF CONFORMITY



EG-Konformitätserklärung
Déclaration de conformité CE
EC-Declaration of Conformity

Nr. / no. / no. **2015_401**

Wir
Nous
We

CONTRINEX AG, route André Piller 50, CH-1762 Givisiez

(Name & Anschrift des Anbieters / nom & adresse du fournisseur / supplier's name & address)

erklären in alleiniger Verantwortung, dass die Produkte
déclarons sous notre propre responsabilité, que les produits
declare under our sole responsibility that the products

Sicherheits-Lichtvorhänge
Barrières de sécurité
Safety light curtains

YBB-###4-###-###

(Bezeichnung, Typ oder Modell) / Nom, type ou modèle / Name, type or model)

mit folgender(en) europäischen Richtlinie(n) übereinstimmen:
est (sont) conforme(s) avec la (les) directive(s) européenne(s) suivante(s):
conform(s) to the following European standard(s):

Low Voltage Directive 2006/95/EC
EMC Directive 2014/30/UE
European Directive on Safety of Machinery 2006/42/EC

Dies wird nachgewiesen durch die Einhaltung folgender Norm(en) (letztgültigen Fassung):
Ceci est démontré par la conformité à (aux) norme(s) suivante(s) (la version la plus récente s'applique):
This is documented in accordance with the following standard(s) (latest version applicable):

IEC 61496-1 (Type 4)
EN 61496-1
IEC 61496-2 (Type 4)
EN ISO 13849-1 (Cat. 4, PL e)
EN 61000-6-4

Notifizierte Stelle / Organisme notifié / Notified body:

TÜV SÜD Product Service GmbH, Ridlerstrasse 65, DE-80339 München

Givisiez, 07.07.2015

*(Ort und Datum der Ausstellung /
lieu et date de délivrance /
place and date of issue)*

(L. Genilloud)

*(Name und Unterschrift oder gleichwertige
Kennzeichen des (der) Befugten / Nom et signature
ou identification équivalente de (des) autorisé(s) / name
and signature or equivalent identification of authorized
person(s))*

Diese Konformitätserklärung entspricht der Europäischen Norm EN ISO/IEC 17050-1:2004-10 "Konformitätsbewertung - Konformitätserklärung von Anbietern - Teil 1: Allgemeine Anforderungen".
Cette déclaration de conformité est basée sur la norme européenne EN ISO/CEI 17050-1:2004-10 "Évaluation de la conformité - Déclaration de conformité du fournisseur - Partie 1: Exigences générales".
This declaration of conformity is in accordance with the European Standard EN ISO/IEC 17050-1:2004-10 "Conformity assessment - Supplier's declaration of conformity - Part 1: General requirements"

Certificats de conformité 2009.lnnd / rev. 5 / 07.07.15 / CB_MDM

CONTRINEX AG Industrial Electronics
route André Piller 50 - CH 1762 Givisiez - Switzerland - **Tel:** +41 26 460 46 46 - **Fax:** +41 26 460 46 40 - **Internet:** www.contrinex.com - **E-mail:** info@contrinex.com

**EG-Konformitätserklärung
Déclaration de conformité CE
EC-Declaration of Conformity**Nr. / no. / no. **2015_402**Wir
Nous
We**CONTRINEX AG, route André Piller 50, CH-1762 Givisiez***(Name & Anschrift des Anbieters / nom & adresse du fournisseur / supplier's name & address)*erklären in alleiniger Verantwortung, dass die Produkte
déclarons sous notre propre responsabilité, que les produits
declare under our sole responsibility that the products**Mehrstrahl-Sicherheits-Lichtschranken
Barrières périmétriques de sécurité
Safety access control barriers****YCA-###4-####-####***(Bezeichnung, Typ oder Modell / Nom, type ou modèle / Name, type or model)*mit folgender(en) europäischen Richtlinie(n) übereinstimmen:
est (sont) conforme(s) avec la (les) directive(s) européenne(s) suivante(s):
conform(s) to the following European standard(s):**Low Voltage Directive 2006/95/EC
EMC Directive 2014/30/UE
European Directive on Safety of Machinery 2006/42/EC**Dies wird nachgewiesen durch die Einhaltung folgender Norm(en) (letztgültigen Fassung):
Ceci est démontré par la conformité à (aux) norme(s) suivante(s) (la version la plus récente s'applique):
This is documented in accordance with the following standard(s) (latest version applicable):**IEC 61496-1 (Type 4)
EN 61496-1
IEC 61496-2 (Type 4)
ISO 13849-1 (Cat. 4, PL e)
EN ISO 13849-1 (Cat. 4, PL e)
EN 61000-6-4**

Notifizierte Stelle / Organisme notifié / Notified body:

TÜV SÜD Product Service GmbH, Ridlerstrasse 65, DE-80339 München**Givisiez, 07.07.2015***(Ort und Datum der Ausstellung /
lieu et date de délivrance /
place and date of issue)* **(L. Genilloud)***(Name und Unterschrift oder gleichwertige
Kennzeichen des (der) Befugten /
Nom et signature ou identification équivalente de
(des) autorisé(s) / name and signature or
equivalent identification of authorized person(s))*Diese Konformitätserklärung entspricht der Europäischen Norm EN ISO/IEC 17050-1:2004-10 "Konformitätsbewertung - Konformitätserklärung von Anbietern - Teil 1: Allgemeine Anforderungen".
Cette déclaration de conformité est basé sur la norme européenne EN ISO/CEI 17050-1:2004-10 "Évaluation de la conformité - Déclaration de conformité du fournisseur - Partie 1: Exigences générales".
This declaration of conformity is in accordance with the European Standard EN ISO/IEC 17050-1:2004-10 "Conformity assessment - Supplier's declaration of conformity - Part 1: General requirements"

Certificats de conformité 2009.indd / rev. 3 / 07.07.15 / MDM

**EG-Konformitätserklärung
Déclaration de conformité CE
EC-Declaration of Conformity**Nr. / no. / no. **2016_406**

Wir / Nous / We

CONTRINEX AG, route André Pillier 50, CH-1762 Givisiez*(Name & Anschrift des Anbieters / nom & adresse du fournisseur / supplier's name & address)*

erklären in alleiniger Verantwortung, dass die Produkte
déclarons sous notre propre responsabilité, que les produits
declare under our sole responsibility that the products

**Lichtschranken-Schaltgerät
Relais de sécurité
Safety relay****YRB-4EML-31S***(Bezeichnung, Typ oder Modell / Norm, type ou modèle / Name, type or model)*

mit folgender(en) europäischen Richtlinie(n) übereinstimmen:
est (sont) conforme(s) avec la (les) directive(s) européenne(s) suivante(s):
conform(s) to the following European standard(s):

**EMC Directive 2014/30/EU
European Directive on Safety of Machinery 2006/42/EG**

Dies wird nachgewiesen durch die Einhaltung folgender Norm(en):
Ceci est démontré par la conformité à (aux) norme(s) suivante(s):
This is documented in accordance with the following standard(s):

**EN 61000-6-4:2007+A1:2011* EN 61000-6-2:2005+AC:2005
EN ISO 13849-1:2008+AC:2009 EN 62061:2005+AC:2010+A1:2013**


Notifizierte Stelle / Organisme notifié / Notified body:

**TÜV Rheinland Industrie Service GmbH
Alboinstrasse 56, DE-12103 Berlin**

Für die Zusammenstellung der technischen Unterlagen ist bevollmächtigt:
Pour la composition des documents techniques est autorisé:
For the compilation of the technical documents is authorized:


Givisiez, 19.04.16 *(Ch, Datum / Issu, date / Place, date)*
D. Wittwer, International Product Manager - Contrinex AG, route André Pillier 50, CH-1762 Givisiez

Rechtsverbindliche Unterschrift / Signature légale / Legally binding signature:


Givisiez, 19.04.16 *(Ch, Datum / Issu, date / Place, date)*
L. Genilloud, Vice President R&D - Contrinex AG, route André Pillier 50, CH-1762 Givisiez

* Warnung: Dies ist ein Klasse A-Erzeugnis. In Wohngebieten kann es zu Störungen des Funkempfanges kommen. Der Betreiber soll entsprechende Schutzmassnahmen treffen.

* Warning: This is a Class A product. In a domestic environment it may cause radio interference, in which case the user may be required to take adequate measures.

Diese Erklärung bescheinigt die Übereinstimmung mit den genannten Richtlinien, beinhaltet jedoch keine Zusicherung von Eigenschaften. Die Sicherheitsmassnahmen der Produktdokumentation sind zu beachten.
Cette déclaration certifie la conformité des directives mentionnées, mais ne comprend aucune garantie des caractéristiques du produit. Les directives de sécurité de la documentation du produit sont à considérer.

This declaration confirms the conformity with the mentioned directives, but does not guarantee any product characteristics. The safety directives of the product documentation must be taken into account.

Diese Konformitätserklärung entspricht der Europäischen Norm EN ISO/IEC 17050-1:2004-10 "Konformitätsbewertung - Konformitätserklärung von Anbietern - Teil 1: Allgemeine Anforderungen".

Cette déclaration de conformité est basé sur la norme européenne EN ISO/CEI 17050-1:2004-10 "Évaluation de la conformité - Déclaration de conformité du fournisseur - Partie 1: Exigences générales".

This declaration of conformity is in accordance with the European Standard EN ISO/IEC 17050-1:2004-10 "Conformity assessment - Supplier's declaration of conformity - Part 1: General requirements"

Certificats de conformité 2016.indd / rev. 0 / 19.04.16 / IMDG



CONTRINEX

ALL OVER THE WORLD

EUROPE

Austria
Belgium*
Croatia
Czech Republic
Denmark
Estonia
Finland
France*
Germany*
Great Britain*
Greece
Hungary
Ireland
Italy*
Luxembourg
Netherlands
Norway
Poland
Portugal*
Romania
Russian Federation

Slovakia
Slovenia
Spain
Sweden
Switzerland*
Turkey
Ukraine

AFRICA

Morocco
South Africa

THE AMERICAS

Argentina
Brazil*
Canada
Chile
Mexico*
Peru
United States*
Venezuela

ASIA

China*
India*
Indonesia
Japan*
Korea
Malaysia
Pakistan
Philippines
Singapore*
Taiwan
Thailand
Vietnam

MIDDLE EAST

Israel
United Arab Emirates

AUSTRALASIA

Australia
New Zealand

* Contrinex subsidiary

Terms of delivery and right to change design reserved.
Please check our website for updates.

900 200 002 - 04.16

CONTRINEX HEADQUARTERS Industrial Electronics
route André Piller 50 - PO Box - CH 1762 Givisiez - Switzerland
Tel: +41 26 460 46 46 - **Fax:** +41 26 460 46 40
Internet: www.contrinex.com - **E-mail:** info@contrinex.com

www.contrinex.com