

GH15 Series IEC Motor Controls

The GH15 series of IEC contactors and thermal overload relays are manufactured by Europe's leading maritime contactor company. Contactors for ocean-going vessels are built to the most rigid specifications. This same design technology carries over to this line of industrial motor controls.

We offer individual components that

allow you to use the contactor alone or to assemble your motor starter using our thermal overload relays. You can also combine a manual motor starter/protector for all-in-one protection.

Use contactors wherever you need a heavy-duty switching device with up to three poles. Add up to 2 side-mounted auxiliary blocks (1 per side)

plus 1 top-mounted auxiliary contact block per contactor max. This will equal up to 8 possible auxiliary contact configurations. Or use the optional mechanical interlock to create an inexpensive reversing contactor.

Self-lifting pressure plate terminals make for quick wiring terminations.

Actuator coils, available in 110/120 V and 220/240 V, 60Hz models, accommodate most applications.

IEC sizes B through TT accommodate up to 250 hp motors @460 VAC.

Terminals are IP20 rated to protect fingers from electrical shock.

35mm DIN-rail mounting and panel mounting (larger size) provides fast and easy installation. Panel mounting holes are provided.

Top and side mounted auxiliary contacts offer versatility for space requirements.

Approvals

- cULus listed #E191059
- UL 60947-4-1A



See next page for detailed specifications.

GH15 Series Contactor Configurations

| Contactor Configurations | | | | | | | |
|--------------------------|---------------------|------------------------------|-------------------------|--------------------|--------------------------------|------|--------------------------------|
| IEC FRAME SIZE | Contactor Model* | Part Number | Price | Number of Contacts | | | Coil Voltage and Frequency |
| | | | | Main | Auxiliary Contacts Included | | |
| | | | | | N.O | N.C. | |
| 45 mm | GH15BN | GH15BN-3-10A | \$0dp _x : | 3 | 1 | — | 110-120 VAC 50-60 Hz |
| | | GH15BN-3-01A | \$0dp _u : | 3 | — | 1 | 110-120 VAC 50-60 Hz |
| | | GH15BN-3-10B | \$0dp _y : | 3 | 1 | — | 220-240 VAC 50-60 Hz |
| | GH15CN | GH15CN-3-10A | \$;0dp _l : | 3 | 1 | — | 110-120 VAC 50-60 Hz |
| | | GH15CN-3-01A | \$0dp _z : | 3 | — | 1 | 110-120 VAC 50-60 Hz |
| | | GH15CN-3-10B | \$0dp __ : | 3 | 1 | — | 220-240 VAC 50-60 Hz |
| | | GH15CN-3-01B | \$;0dp _j : | 3 | — | 1 | 220-240 VAC 50-60 Hz |
| | GH15DN | GH15DN-3-10A | \$0dp _? : | 3 | 1 | — | 110-120 VAC 50-60 Hz |
| | | GH15DN-3-01A | \$0dp _# : | 3 | — | 1 | 110-120 VAC 50-60 Hz |
| | | GH15DN-3-10B | \$;0dp _{,:} | 3 | 1 | — | 220-240 VAC 50-60 Hz |
| | | GH15DN-3-01B | \$;0dp _! : | 3 | — | 1 | 220-240 VAC 50-60 Hz |
| | GH15ET | GH15ET-3-00A | \$00dq ₀ : | 3 | — | — | 110-120 VAC 50-60 Hz |
| | | GH15ET-3-00B | \$00dq ₁ : | 3 | — | — | 220-240 VAC 50-60 Hz |
| | GH15FT | GH15FT-3-00A | \$00dq ₂ : | 3 | — | — | 110-120 VAC 50-60 Hz |
| | | GH15FT-3-00B | \$00dq ₃ : | 3 | — | — | 220-240 VAC 50-60 Hz |
| 60 mm | GH15GT | GH15GT-3-00A | \$00dq _h : | 3 | — | — | 120 VAC 60 Hz only |
| | | GH15GT-3-00B | \$-00dq _i : | 3 | — | — | 240 VAC 60 Hz / 212 VAC 50 Hz |
| | GH15HT | GH15HT-3-00A | \$-00dq _j : | 3 | — | — | 120 VAC 60 Hz only |
| | | GH15HT-3-00B | \$00dq _k : | 3 | — | — | 240 VAC 60 Hz / 212 VAC 50 Hz |
| | GH15JT | GH15JT-3-00A | \$-00dq _l : | 3 | — | — | 120 VAC 60 Hz only |
| | | GH15JT-3-00B | \$00dq _n : | 3 | — | — | 240 VAC 60 Hz / 212 VAC 50 Hz |
| 79 mm | GH15KT | GH15KT-3-00A | \$00dp _k : | 3 | — | — | 120 VAC 60 Hz only |
| | | GH15LT-3-00A | \$00dp _n : | 3 | — | — | 120 VAC 60 Hz only |
| | GH15MT | GH15LT-3-00B | \$00dp _o : | 3 | — | — | 240 VAC 60 Hz / 212 VAC 50 Hz |
| | | GH15MT-3-00A | \$00dp _p : | 3 | — | — | 110-120 VAC 50-60 Hz / 110 VDC |
| | | GH15MT-3-00B | \$00dp _q : | 3 | — | — | 220-240 VAC 50-60 Hz |
| 110 mm | GH15NT | GH15NT-3-00A | \$00dp ₇ : | 3 | — | — | 110-120 VAC 50-60 Hz / 110 VDC |
| | | GH15PT-3-00A | \$00dp ₉ : | 3 | — | — | 110-120 VAC 50-60 Hz / 110 VDC |
| | | GH15PT-3-00B | \$00dp _a : | 3 | — | — | 220-240 VAC 50-60 Hz / 220 VDC |
| 145 mm | GH15RT | GH15RT-3-00A | \$00dp _c : | 3 | — | — | 110-120 VAC 50-60 Hz / 110 VDC |
| | | GH15ST-3-00A | \$00dp _e : | 3 | — | — | 110-120 VAC 50-60 Hz / 110 VDC |
| | GH15TT | GH15TT-3-00A | \$;000dp _g : | 3 | — | — | 110-120 VAC 50-60 Hz / 110 VDC |
| | | GH15TT-3-00B | \$;000dp _h : | 3 | — | — | 220-240 VAC 50-60 Hz / 220 VDC |

* Up to 2 auxiliary contact blocks may be added to the contactor by utilizing the side mount and top mount contact block assemblies. Though referred to as a top mount assembly, the GH15T mounts to the front of the contactor.

Note: If using the [BM0H](#) or [BM3H-AD](#) mechanical interlock, the use of auxiliary contacts is prohibited on the side of each contactor where the interlock is mounted. This does not pertain to the auxiliary contact built into the GH15BN, GH15CN and GH15DN contactors.




GH15 Series 45mm Contactor Specifications

| 45mm Contactor Specifications | | | | | | | |
|--|--|------|---|--------|--------|--------------------|--------|
| Contactor Model | | | GH15BN | GH15CN | GH15DN | GH15ET | GH15FT |
| Insulation Voltage | AC | (V) | 600 Volts AC | | | | |
| Ampere Rating UL 508 | Max. UL Continuous Current | (A) | 11 | 14 | 19 | 32 | 32 |
| | Max. UL General Use Current note 2 | (A) | 20 | 20 | 25 | 40 | 45 |
| Maximum Power (hp) of Three-Phase Motors | 200V | (hp) | 2 | 3 | 3 | 7.5 | 7.5 |
| | 230/240V | (hp) | 3 | 3 | 5 | 7.5 | 10 |
| | 460/480V | (hp) | 5 | 7.5 | 10 | 15 | 20 |
| | 575V | (hp) | 7.5 | 10 | 15 | 20 | 25 |
| Maximum Power (hp) of Single-Phase Motors | 115V | (hp) | 0.5 | 0.5 | 1 | 2 | 2 |
| | 230/240V | (hp) | 1 | 2 | 3 | 3 | 5 |
| Insulation Voltage | AC | (V) | 690 Volts AC | | | | |
| Ampere Rating EN/IEC 60947 | AC-3 I _e (ambient Temp = 55°C @ 440V) | (A) | 9 | 12 | 16 | 25 | 32 |
| | AC-1 I _e (ambient Temp = 40°C @ 690V) | (A) | 30 | 30 | 30 | 45 | 50 |
| Maximum Power (kW) of Three-Phase Motors AC3 Category note 1 | 230/240V | (kW) | 2.2 | 3 | 4 | 6.5 | 7.5 |
| | 400V | (kW) | 4 | 5.5 | 7.5 | 11 | 15 |
| | 440/480V | (kW) | 4.7 | 6.4 | 9 | 12.5 | 16.5 |
| | 500V | (kW) | 5.5 | 7.5 | 10 | 11 | 15 |
| | 690V | (kW) | 5.5 | 7.5 | 7.5 | 11 | 15 |
| Max Short Circuit Protection Fuses Class RK5 UL Rated Fuses | Type 2 Coordination note 3 | (A) | 25 | 30 | 50 | 60 | 70 |
| SCCR Rating (kA) | | kA | 5 | 5 | 5 | 5 | 5 |
| Auxiliary Contacts Electrical Capacity | | | A600 note 4 | | | | |
| Coil Voltage Operating Limits | | | AC Pick-up 85-110% rated control voltage / AC Drop-out 20-75% rated control voltage | | | | |
| Average Coil Power Requirements / Coil current (A) = VA/Coil Voltage | | | AC Pick-Up (VA) 80-100 / AC Sealed (VA) 9-12 | | | | |
| Power Factor | | | Pick-up 0.65 / Sealed 0.35 | | | | |
| Coil Operating Time at Rated Coil Voltage | | | Pick-up (ms) 10-25 / Drop-out (ms) 6-18 | | | | |
| Maximum Operating Frequency (No-Load Operation) | | | 3000 operations / hour | | | | |
| Mechanical Durability | | | 10,000,000 operations | | | | |
| Operating Ambient Temperature | | | -25 to +70C (-13 to +158F) | | | | |
| Electrical Protection Degree | | | IP20 (IP10 for power entry cables) | | | | |
| Mounting | | | Screw (panel mount) or 35mm DIN rail | | | | |
| Main Circuit Connections | Wire Size | | 14-10 AWG Stranded | | | 14-8 AWG Stranded | |
| | Tightening Torque | | 1.4 N·m (12 lb·in) | | | 2.3 N·m (20 lb·in) | |
| Auxilliary Circuit Connections | Wire Size | | 16-12 AWG Stranded / 14-12 AWG Solid | | | | |
| | Tightening Torque | | 0.8 N·m (7 lb·in) | | | | |

Notes

1. AC3 type loads consist of squirrel cage three phase motors.
2. AC1 non-inductive or slightly inductive loads. Typically resistive loads (i.e. furnaces, ovens, etc.)
3. Type 2 coordination is a protection category for IEC 60947-4-1. Section 8.2.5.1 specifies that Type 2 coordination requires that, under short circuit conditions, the contactor or starter shall cause no danger to persons or installations, and shall be suitable for further use. The risk of minor contact welding is possible.

Contactor Diagram




GH15 Series 60mm Contactor Specifications

| 60mm Contactor Specifications | | | | | |
|--|---|------|--|--------|--------|
| Contactor Model | | | GH15GT | GH15HT | GH15JT |
| Insulation Voltage | AC | (V) | 600 Volts AC | | |
| Ampere Rating UL 508 | Max. UL Continuous Current | (A) | 42 | 52 | 65 |
| | Max. UL General Use Current note 2 | (A) | 60 | 70 | 80 |
| Maximum Power (hp) of Three-Phase Motors | 200V | (hp) | 10 | 15 | 15 |
| | 230/240V | (hp) | 10 | 15 | 20 |
| | 460/480V | (hp) | 25 | 30 | 40 |
| | 575V | (hp) | 30 | 40 | 50 |
| Maximum Power (hp) of Single-Phase Motors | 115V | (hp) | 3 | 3 | 5 |
| | 230/240V | (hp) | 5 | 7.5 | 10 |
| Insulation Voltage | AC | (V) | 690 Volts AC | | |
| Ampere Rating EN/IEC 60947 | AC-3 I _e (ambient Temp = 55°C @440V) | (A) | 40 | 50 | 63 |
| | AC-1 I _e (ambient Temp = 40°C @690V) | (A) | 63 | 80 | 100 |
| Maximum Power (kW) of Three-Phase Motors AC3 Category note 1 | 230/240V | (kW) | 11 | 12.5 | 18.5 |
| | 400V | (kW) | 18.5 | 22 | 30 |
| | 440/480V | (kW) | 21 | 25 | 33 |
| | 500V | (kW) | 18.5 | 22 | 30 |
| | 690V | (kW) | 18.5 | 22 | 30 |
| Max Short Circuit Protection Circuit Breaker UL Rated MCCB | Type 2 Coordination note 3 | (A) | 150 | 175 | 200 |
| SCCR Rating (kA) | | (kA) | 5 | 5 | 5 |
| Auxiliary Contacts Electrical Capacity | | | A600 note 4 | | |
| Coil Voltage Operating Limits | | | AC Pick-up 85-110% rated control voltage AC Drop-Out 20-75% rated control voltage | | |
| Average Coil Power Requirements / Coil current (A) = VA/Coil Voltage | | | AC Pick-up (VA) 250 / AC Sealed (VA) 18 | | |
| Power Factor | | | Pick-up 0.54 / Sealed 0.35 | | |
| Coil Operating Time at Rated Coil Voltage | | | Pick-up (ms) 12-30 / Drop-out (ms) 6-15 | | |
| Maximum Operating Frequency (No-Load Operation) | | | 3000 operations / hour | | |
| Mechanical Durability | | | 10,000,000 operations | | |
| Operating Ambient Temperature | | | -25 to +70C (-13 to +158F) | | |
| Electrical Protection Degree | | | IP20 (IP10 for power entry cables) | | |
| Mounting | | | Screw (panel mount) or 35mm DIN rail | | |
| Main Circuit Connections | Wire Size | | 12-3 AWG stranded | | |
| | Tightening Torque | | 5.0 N·m (45 lb·in) | | |
| Auxiliary Circuit Connections | Wire Size | | 16-12 AWG (stranded recommended) | | |
| | Tightening Torque | | 0.8 N·m (7 lb·in) | | |

Notes

1. AC3 type loads consist of squirrel cage three phase motors.
2. AC1 non-inductive or slightly inductive loads. Typically resistive loads (i.e. furnaces, ovens, etc.)
3. Type 2 coordination is a protection category for IEC 60947-4-1. Section 8.2.5.1 specifies that Type 2 coordination requires that, under short circuit conditions, the contactor or starter shall cause no danger to persons or installations, and shall be suitable for further use. The risk of minor contact welding is possible.
4. NEMA ICS 5-2000. For more information, refer to Control Circuit Contact Electrical Ratings.

Contactor Diagram




GH15 Series 79mm Contactor Specifications

| 79mm Contactor Specifications | | | | | |
|--|---|------|--|--------|---|
| Contactor Model | | | GH15KT | GH15LT | GH15MT |
| Insulation Voltage | AC | (V) | 600 Volts AC | | |
| Ampere Rating UL 508 | Max. UL Continuous Current | (A) | 90 | 90 | 120 |
| | Max. UL General Use Current note 2 | (A) | 90 | 100 | 120 |
| Maximum Power (hp) of Three-Phase Motors | 200V | (hp) | 20 | 25 | 30 |
| | 230/240V | (hp) | 25 | 30 | 40 |
| | 460/480V | (hp) | 50 | 60 | 75 |
| | 575V | (hp) | 60 | 75 | 100 |
| Maximum Power (hp) of Single-Phase Motors | 115V | (hp) | 5 | 7.5 | 10 |
| | 230/240V | (hp) | 15 | 15 | 20 |
| Insulation Voltage | AC | (V) | 1000 Volts AC | | |
| Ampere Rating EN/IEC 60947 | AC-3 I _e (ambient Temp = 55°C @440V) | (A) | 80 | 95 | 110 |
| | AC-1 I _e (ambient Temp = 40°C @690V) | (A) | 125 | 125 | 135 |
| Maximum Power (kW) of Three-Phase Motors AC3 Category note 1 | 230/240V | (kW) | 22 | 25 | 30 |
| | 400V | (kW) | 37 | 45 | 55 |
| | 440/480V | (kW) | 45 | 51 | 63 |
| | 500V | (kW) | 45 | 51 | 55 |
| | 690V | (kW) | 45 | 51 | 55 |
| Max Short Circuit Protection Fuses Class RK5 UL Rated Fuses | Type 2 Coordination note 3 | (A) | 250 | 250 | 225 |
| SCCR Rating (kA) | | (kA) | 10 | 10 | 10 |
| Auxiliary Contacts Electrical Capacity | | | A600 note 4 | | |
| Coil Voltage Operating Limits | | | AC/DC Pick-up 85-110% rated control voltage AC/DC Drop-Out 20-75% rated control voltage | | |
| Average Coil Power Requirements / Coil current (A) = VA/Coil Voltage | | | AC Pick-up (VA) 250 / AC Sealed (VA) 18 | | AC Pick-up (VA) 250 AC Sealed 24-125V (VA) 4 AC Sealed 220-600V (VA) 19 |
| Power Factor | | | Pick-up 0.54 / Sealed 0.35 | | Pick-up 0.98 Sealed 24-125V 0.98 Sealed 220-600V 0.2 |
| Coil Operating Time at Rated Coil Voltage | | | Pick-up (ms) 12-30 / Drop-out (ms) 6-15 | | Pick-up (ms) 15-50 Drop-out (ms) 30-80 |
| Maximum Operating Frequency (No-Load Operation) | | | 3000 operations / hour | | |
| Mechanical Durability | | | 10,000,000 operations | | |
| Operating Ambient Temperature | | | -25 to +70C (- 13 to +158F) | | |
| Electrical Protection Degree | | | IP20 (Front) | | |
| Mounting | | | Screw (panel mount) | | |
| Main Circuit Connections | Wire Size | | 10-2 AWG Stranded (1 or 2 wires) | | |
| | Tightening Torque | | 8.0 N·m (70 lb·in) | | |
| Auxilliary Circuit Connections | Wire Size | | 2 x 16-12 AWG Stranded / 2 x 14-12 AWG Solid | | |
| | Tightening Torque | | 0.8 N·m (7 lb·in) | | |

Notes

- AC3 type loads consist of squirrel cage three phase motors.
- AC1 non-inductive or slightly inductive loads. Typically resistive loads (i.e. furnaces, ovens, etc.)
- Type 2 coordination is a protection category for IEC 60947-4-1. Section 8.2.5.1 specifies that Type 2 coordination requires that, under short circuit conditions, the contactor or starter shall cause no danger to persons or installations, and shall be suitable for further use. The risk of minor contact welding is possible.
- NEMA ICS 5-2000. For more information, refer to Control Circuit Contact Electrical Ratings.

Contactor Diagram




GH15 Series 110mm Contactor Specifications

| 110mm Contactor Specifications | | | | |
|--|---|------|--|--------|
| Contactor Model | | | GH15NT | GH15PT |
| Insulation Voltage | AC | (V) | 600 Volts AC | |
| Ampere Rating UL 508 | Max. UL Continuous Current | (A) | 180 | 180 |
| | Max. UL General Use Current note 2 | (A) | 180 | 220 |
| Maximum Power (hp) of Three-Phase Motors | 200V | (hp) | 40 | 50 |
| | 230/240V | (hp) | 50 | 60 |
| | 460/480V | (hp) | 100 | 125 |
| | 575V | (hp) | 125 | 150 |
| Maximum Power (hp) of Single-Phase Motors | 115V | (hp) | 15 | 15 |
| | 230/240V | (hp) | 25 | 30 |
| Insulation Voltage | AC | (V) | 1000 Volts AC | |
| Ampere Rating EN/IEC 60947 | AC-3 I _e (ambient Temp = 55°C @440V) | (A) | 150 | 175 |
| | AC-1 I _e (ambient Temp = 40°C @690V) | (A) | 230 | 250 |
| Maximum Power (kW) of Three-Phase Motors AC3 Category note 1 | 230/240V | (kW) | 40 | 50 |
| | 400V | (kW) | 75 | 90 |
| | 440/480V | (kW) | 85 | 100 |
| | 500V | (kW) | 90 | 110 |
| | 690V | (kW) | 110 | 132 |
| Max Short Circuit Protection Fuses Class RK5 UL Rated Fuses | Type 2 Coordination note 3 | (A) | 300 | 350 |
| SCCR Rating (kA) | | (kA) | 10 | 10 |
| Auxiliary Contacts Electrical Capacity | | | A600 note 4 | |
| Coil Voltage Operating Limits | | | AC/DC Pick-up 85-110% rated control voltage AC/DC Drop-Out 20-75% rated control voltage | |
| Average Coil Power Requirements / Coil current (A) = VA/Coil Voltage | | | AC Pick-up (VA) 350 / AC Sealed (VA) 5 | |
| Power Factor | | | Pick-up 0.98 / Sealed 0.98 | |
| Coil Operating Time at Rated Coil Voltage | | | Pick-up (ms) 30-60 / Drop-out (ms) 30-80 | |
| Maximum Operating Frequency (No-Load Operation) | | | 1200 operations / hour | |
| Mechanical Durability | | | 10,000,000 operations | |
| Operating Ambient Temperature | | | -25 to +70°C (-13 to +158°F) | |
| Electrical Protection Degree | | | IP00 - IP20 | |
| Mounting | | | Screw (panel mount) | |
| Main Circuit Connections with Terminal Kit MR3-AD | Wire Size | | 2 x 4/0 AWG Stranded / 1 x 4/0 AWG Solid | |
| | Tightening Torque | | 17 N·m (150 lb·in) | |
| Auxiliary Circuit Connections | Wire Size | | 2 X 5-4/0 AWG Stranded | |
| | Tightening Torque | | 0.8 N·m (7 lb·in) | |

Notes

1. AC3 type loads consist of squirrel cage three phase motors.
2. AC1 non-inductive or slightly inductive loads. Typically resistive loads (i.e. furnaces, ovens, etc.)
3. Type 2 coordination is a protection category for IEC 60947-4-1. Section 8.2.5.1 specifies that Type 2 coordination requires that, under short circuit conditions, the contactor or starter shall cause no danger to persons or installations, and shall be suitable for further use. The risk of minor contact welding is possible.
4. NEMA ICS 5-2000. For more information, refer to Control Circuit Contact Electrical Ratings.

Contactor Diagram



GH15 Series 145mm Contactor Specifications


| 145mm Contactor Specifications | | | | | |
|--|--|------|--|--------|--------|
| Contactor Model | | | GH15RT | GH15ST | GH15TT |
| Insulation Voltage | AC | (V) | 600 Volts AC | | |
| Ampere Rating UL 508 | Max. UL Continuous Current | (A) | 250 | 300 | 360 |
| | Max. UL General Use Current note 2 | (A) | 250 | 300 | 360 |
| Maximum Power (hp) of Three-Phase Motors | 200V | (hp) | 60 | 75 | 100 |
| | 230/240V | (hp) | 75 | 100 | 125 |
| | 460/480V | (hp) | 150 | 200 | 250 |
| | 575V | (hp) | 200 | 250 | 300 |
| Maximum Power (hp) of Single-Phase Motors | 230/240V | (hp) | 40 | 50 | 50 |
| Insulation Voltage | AC | (V) | 1000 Volts AC | | |
| Ampere Rating EN/IEC 60947 | AC-3 I_e (ambient Temp = 55°C @440V) | (A) | 210 | 260 | 315 |
| | AC-1 I_e (ambient Temp = 40°C @690V) | (A) | 350 | 450 | 500 |
| Maximum Power (kW) of Three-Phase Motors AC3 Category note 1 | 230/240V | (kW) | 60 | 75 | 90 |
| | 400V | (kW) | 110 | 132 | 160 |
| | 440/480V | (kW) | 125 | 150 | 190 |
| | 500V | (kW) | 132 | 160 | 210 |
| | 690V | (kW) | 132 | 160 | 210 |
| Max Short Circuit Protection Fuses Class RK5 UL Rated Fuses | Type 2 Coordination note 3 | (A) | 400 | 450 | 500 |
| SCCR Rating (kA) | | (kA) | 18 | 18 | 18 |
| Auxiliary Contacts Electrical Capacity | | | A600 note 4 | | |
| Coil Voltage Operating Limits | | | AC/DC Pick-up 85-110% rated control voltage AC/DC Drop-Out 20-75% rated control voltage | | |
| Average Coil Power Requirements / Coil current (A) = VA/Coil Voltage | | | AC Pick-up (VA) 360 / AC Sealed (VA) 5 | | |
| Power Factor | | | Pick-up 0.98 / Sealed 0.98 | | |
| Coil Operating Time at Rated Coil Voltage | | | Pick-up (ms) 40-60 / Drop-out (ms) 40-60 | | |
| Maximum Operating Frequency (No-Load Operation) | | | 1200 operations / hour | | |
| Mechanical Durability | | | 8,000,000 operations | | |
| Operating Ambient Temperature | | | -25 to +70C (- 13 to +158F) | | |
| Electrical Protection Degree | | | IP20 (Front) | | |
| Mounting | | | Screw (panel mount) | | |
| Main Circuit Connections with Terminal Kit KAL-4 | Wire size | | 2 x 6-300 MCM (75° copper wire only) | | |
| | Tightening Torque | | 31 N·m (275 lb·in) | | |
| Auxiliary Circuit Connections | Wire Size | | 16-12 AWG Stranded / 14-12 AWG Solid | | |
| | Tightening Torque | | 0.8 N·m (7 lb·in) | | |

Notes

- AC3 type loads consist of squirrel cage three phase motors.
- AC1 non-inductive or slightly inductive loads. Typically resistive loads (i.e. furnaces, ovens, etc.)
- Type 2 coordination is a protection category for IEC 60947-4-1. Section 8.2.5.1 specifies that Type 2 coordination requires that, under short circuit conditions, the contactor or starter shall cause no danger to persons or installations, and shall be suitable for further use. The risk of minor contact welding is possible.
- NEMA ICS 5-2000. For more information, refer to Control Circuit Contact Electrical Ratings.

Contactor Diagram

GH15RT-3-00
GH15ST-3-00
GH15TT-3-00





GH15 Series Contactor

Electrical Durability of Main Contacts

Main contacts have a conductor material support, on which a silver alloy tip is welded. This tip makes, carries and breaks the load currents. The contact durability is represented by the average number of operations which the contact can carry out without maintenance and before the contact requires replacement. Every operation involves mechanical stresses

when the contactor closes and thermal stress during load current conduction. However, the main stress that affects contact durability is due to the electric arc between contacts during making and breaking operations. The electric arc causes the erosion of the contact active material; such erosion will increase according to the intensity of the current

and the arcing time. Therefore the contact durability is strictly dependent on the type of load, i.e. on the utilization category, rated operational current and rated voltage. The following diagrams give curves of contact durability for each contactor for use in category AC-1, AC-3 and AC-4.




Note: Average durability curves are at 400V. For higher operational voltages, reduce the durability according following table.

| Electrical Durability Curve Adjustment for Voltages Over 400V | | |
|---|-------------|------|
| | AC-1 / AC-4 | AC-3 |
| 400V | 0% | 0% |
| 440V | 10% | 5% |
| 500V | 20% | 10% |
| 690V | 40% | 20% |


GH15 Series Contactor Dimensions

| Dimensions mm [inches] | | | | | | | | | |
|------------------------|--------------|--------------|--------------|--------------|--------------|------------|--------------|-------------|---------------------------|
| Contactor Model | Wide | High | Deep | Mounting | | | | | Product Weight kg [lb] |
| | A | B | C | D | E | E1 | F | G | |
| GH15BN | 45.0 [1.77] | 80.0 [3.15] | 85.0 [3.35] | 35.0 [1.38] | 60.0 [2.36] | 7.5 [0.30] | 116.0 [4.57] | 12.0 [0.47] | 0.41 [0.90] |
| GH15CN | | | | | | | | | |
| GH15DN | | | | | | | | | |
| GH15ET | 45.0 [1.77] | 80.0 [3.15] | 91.0 [3.58] | 35.0 [1.38] | 60.0 [2.36] | 7.5 [0.30] | 122.0 [4.80] | 12.0 [0.47] | 0.47 [1.04] |
| GH15FT | | | | | | | | | |
| GH15GT | 60.0 [2.36] | 114.0 [4.49] | 109.0 [4.29] | 50.0 [1.97] | 100.0 [3.94] | — | 140.0 [5.51] | 12.0 [0.47] | 1.12 [2.47] |
| GH15HT | | | | | | | | | |
| GH15JT | | | | | | | | | |
| GH15KT | 79.0 [3.11] | 137.0 [5.39] | 130.0 [5.12] | 70.0 [2.76] | 100.0 [3.94] | — | 161.0 [6.34] | 12.0 [0.47] | 1.80 [3.97] |
| GH15LT | | | | | | | | | |
| GH15MT | 79.0 [3.11] | 162.0 [6.38] | 130.0 [5.12] | 70.0 [2.76] | 100.0 [3.94] | — | 161.0 [6.34] | 12.0 [0.47] | 2.20 [4.85] |
| GH15NT | 110.0 [4.33] | 170.0 [6.69] | 162.0 [6.38] | 100.0 [3.94] | 130.0 [5.12] | — | 193.0 [7.59] | 12.0 [0.47] | 4.00 [8.82] |
| GH15PT | | | | | | | | | |
| GH15RT | 145.0 [5.71] | 200.0 [7.87] | 208.0 [8.19] | 120.0 [4.72] | 160.0 [6.30] | — | 239.0 [9.41] | 12.0 [0.47] | 7.50 [16.53] |
| GH15ST | | | | | | | | | |
| GH15TT | | | | | | | | | |

GH15BN, GH15CN, GH15DN, GH15ET, GH15FT



GH15GT, GH15HT, GH15JT




GH15 Series Contactor Dimensions


Dimensions

mm [in]


GH15KT, GH15LT, GH15MT



GH15NT and GH15PT




GH15RT, GH15ST, GH15TT



GH15 Series Mounting Positions

The correct mounting position is with the base plate in the vertical plane. The device can be mounted up to 25° from the vertical position.



GH15 Series Contactor Accessories

Auxiliary contacts

Auxiliary contacts are designed for installation on all the GH15 series contactors. The snap-on design makes them quick and easy to install. The bifurcated contact blocks feature silver nickel alloy contacts.

Add up to 2 side-mounted auxiliary blocks (1 per side) plus 1 top-mounted auxiliary contact block per contactor max. This will equal up to 8 possible auxiliary contact configurations.


| Auxiliary Contacts | | | |
|-------------------------|----------|-------------|----------|
| Part Number | Price | Description | Mounting |
| GH15T11 | \$0dsh: | 1 NO 1 NC | Top |
| GH15T22 | \$-0dsi: | 2 NO 2 NC | Top |
| GH15T31 | \$-0dsj: | 3 NO 1 NC | Top |
| GH15T40 | \$0dsk: | 4 NO | Top |
| GH15S11 | \$0dsg: | 1 NO 1 NC | Side |

Contacts rated A600 per NEMA ICS 5-2000. For more info, refer to Control Circuit Contact Electrical Ratings.



Note: See contactor drawings page for dimensions

Auxiliary Contact Blocks




GH15 Series Contactor Accessories

Mechanical Interlock


Mechanical interlocks connect two contactors horizontally. When one contactor is energized, the other contactor is mechanically prohibited from making, even though it may be energized. The mechanical interlocks work with 45, 60, 79, 110 and 145 mm contactors.

| Mechanical Interlock | | | |
|-----------------------|----------|---|----------|
| Part Number | Price | Description | Mounting |
| <u>BM0H</u> | \$0dse: | Mechanical interlock, for use with GH15BN, GH15CN, GH15DN, GH15ET, GH15FT, GH15GT, GH15HT, GH15JT, GH15KT, GH15LT, or GH15MT series contactors. | Side |
| <u>BM3H-AD</u> | \$.0dsf: | Mechanical interlock, for use with GH15NT, GH15PT, GH15RT, GH15ST or GH15TT series contactors. | Side |


BM0H / BM3H-AD



BM0H



BM3H-AD



Terminal Screens

Terminal screens are for use with contactors and thermal overload relays to protect against accidental contact with live components.

| Terminal Screens* | | | | |
|-----------------------|----------|----------|---|----------------------------|
| Part Number | Price | Quantity | Description | Use With |
| <u>PR37-AD</u> | \$-0dsl: | 1 screen | Terminal screen, top or bottom, covers 3 poles. Use on line or load side. Mounting hardware included. | GH15NT GH15PT |
| <u>PRT3-AD</u> | \$0dsn: | 1 screen | Terminal screen, top or bottom, covers 3 poles. Use on line or load side. Mounting hardware included. | GH15RT GH15ST GH15TT |

* No additional protecting device is required for contactors up to IEC Size 79mm since the equipment by itself ensures IP20 frontal protection.
Note: Not for use with MR3-AD and KAL-4. See product insert for connections.

PRT3-AD



PR37-AD

| Terminal Lug | | | | |
|----------------------|----------|----------|--|--------------------------------------|
| Part Number | Price | Quantity | Description | Use With |
| <u>MR3-AD</u> | \$.054!: | 1 | Terminal lug, 1-pole, can hold (2) wires 5 AWG - 4/0 AWG. | GH15NT GH15PT RTD180 |
| <u>KAL-4</u> | \$054#: | 1 | Terminal lug, 1-pole, can hold (1) wire 6 AWG - 300 MCM. Mounting hardware included. | GH15RT GH15ST GH15TT RTD320 |

MR3-AD



KAL-4



Adjustable Overloads For GH15 Series Contactors

The RTD series adjustable motor overload relays are designed for use with the GH15 Series 45 mm, 60 mm, 79 mm, 110 mm, and 145 mm contactors.

By combining the contactor with an overload relay, you have a reliable motor starter solution.



RTD32 overload relays for 45mm contactors

- 16 sizes for motor currents from 0.4 to 32 amps
- Units come with (1) N.O. and (1) N.C. auxiliary contacts
- Mount directly to 45mm contactors
- Class 10A trip class
- cULus listed, CE

RTD65 overload relays for 60mm contactors

- Four sizes for motor currents from 20 to 65 amps
- Units come with (1) N.O. and (1) N.C. auxiliary contacts
- Mount directly to 60mm contactors
- Class 10A trip class
- cULus listed, CE

RTD180 overload relays for 79mm and 110mm contactors

- 3 sizes for motor currents from 60 to 180 amps
- Units come with (1) N.O. and (1) N.C. auxiliary contacts
- Mount directly to 110mm contactors with connection links (included)
- Hard-wire connection to 79 mm contactors (No connection links available)
- Class 10A trip class
- cULus listed, CE


RTD320 overload relays for 145mm contactors

- 2 sizes for motor currents from 144 to 320 amps
- Units come with (1) N.O. and (1) N.C. auxiliary contacts
- Mount directly to 145mm contactors with connection links (included)
- Class 10A trip class
- cULus listed, CE




GH15 Series Adjustable Overload Relay Features

RTD32
for 45 mm Contactors




Note: Scale is 1:1 on dial.

RTD180 for 79 mm and 110 mm Contactors



Note: The secondary current for the dial adjustment of the relay is 100x the dial current. For example, for a rated load current of 120A, the relay setting should be 1.2A.


RTD65
for 60 mm Contactors



Note: Scale is 1:1 on dial.

Note: Additional Black Loadside Terminal Block is available on RTD65-5200 and RTD65-6500 only.

RTD320
for 145 mm Contactors



Note: The secondary current for the dial adjustment of the relay is 80x the dial current. For example, for a rated load current of 216A, the relay setting should be 2.7A.

GH15 Series Overload Relay Selection Guide

Step 1 Determine the motor FLA and service factor listed on the motor name plate. Next, calculate the size overload protection required based on 2005 NEC 430.32. Select your motor's FLA (Full Load Amperage) from Column A. Tripping current occurs at 125% of FLA in column A.

Step 2 Follow across to Column B to find your contactor size. Check the maximum amperage rating for that contactor. Ranges overlap and you may have to go to the next larger size.

Step 3 After selecting your contactor, follow across to Column C to find your overload relay model number.


Step 4 Order the contactor and overload relay, any desired auxiliary contacts, then assemble and install your motor starter.

| Motor Contactor and Overload Relay Selection Guide (When Motor FLA is Known) | | | | |
|--|--------------------------------|------------------------------|----------|--------------------------|
| A | B | C | Price | IEC Contactor Frame Size |
| Current Range Motor FLA | Contactor Model | Overload Relay | | |
| 0.4 to 0.6A | GH15BN up to maximum FLA of 9A | RTD32-60 | \$0dqd: | 45mm |
| 0.6 to 0.9A | | RTD32-90 | \$0dqf: | |
| 0.8 to 1.2A | | RTD32-120 | \$0dq5: | |
| 1.2 to 1.8A | | RTD32-180 | \$0dq7: | |
| 1.8 to 2.7A | | RTD32-270 | \$0dqa: | |
| 2.7 to 4.0A | | RTD32-400 | \$0dq: | |
| 4.0 to 6.0A | | RTD32-600 | \$0dqe: | |
| 6.0 to 9.0A | | RTD32-900 | \$0dqg: | |
| 8.0 to 11.0A | GH15CN up to 12A FLA | RTD32-1100 | \$0dq4: | |
| 10.0 to 14.0A | | RTD32-1400 | \$0dq6: | |
| 10.0 to 14.0A | GH15DN up to 16A FLA | RTD32-1400 | \$0dq6: | |
| 13.0 to 18.0A | | RTD32-1800 | \$0dq8: | |
| 13.0 to 18.0A | GH15ET up to 25A FLA | RTD32-1800 | \$0dq8: | |
| 17.0 to 24.0A | | RTD32-2400 | \$0dq9: | |
| 22.0 to 32.0A | | RTD32-3200 | \$00dqb: | |
| 22.0 to 32.0A | GH15FT up to 32A FLA | RTD32-3200 | \$00dqb: | |
| 20.0 to 28.0A | GH15GT up to 40A FLA | RTD65-2800 | \$00dqo: | 60mm |
| 28.0 to 42.0A | | RTD65-4200 | \$00dqp: | |
| 28.0 to 42.0A | GH15HT up to 50A FLA | RTD65-4200 | \$00dqp: | |
| 40.0 to 52.0A | | RTD65-5200 | \$00dq: | |
| 40.0 to 52.0A | GH15JT up to 63A FLA | RTD65-5200 | \$00dq: | |
| 52.0 to 65.0A | | RTD65-6500 | \$00dqs: | |
| 60.0 to 90.0A | GH15KT up to 80A FLA | RTD180-9000 | \$00dpt: | 79mm |
| 60.0 to 90.0A | GH15LT up to 95A FLA | RTD180-9000 | \$00dpt: | |
| 80.0 to 120.0A | GH15MT up to 110A FLA | RTD180-12000 | \$00dps: | |
| 120.0 to 180.0A | GH15NT up to 150A FLA | RTD180-18000 | \$00dpb: | 110mm |
| 120.0 to 180.0A | GH15PT up to 175A FLA | RTD180-18000 | \$00dpb: | |
| 144.0 to 216.0A | GH15RT up to 210A FLA | RTD320-21600 | \$00dpi: | 145mm |
| 144.0 to 216.0A | GH15ST up to 260A FLA | RTD320-21600 | \$00dpi: | |
| 216.0 to 320.0A | | RTD320-32000 | \$00dpj: | |
| 144.0 to 216.0A | GH15TT up to 315A FLA | RTD320-21600 | \$00dpi: | |
| 216.0 to 320.0A | | RTD320-32000 | \$00dpj: | |

GH15 Series Contactors Overload Technical Characteristics

Typical Trip Curves


45mm and 60mm Overloads



Note: Curves show tripping time (average value) versus multiples of setting current I_r .

— Tripping starting from cold
— Tripping starting from hot

79mm, 110mm, and 145mm Overloads





GH15 Series Contactors Overload

Technical Characteristics

| Thermal Overload Relays Specifications | | | | | |
|--|-------------------------------|--|-------------------|------------------|------------------|
| | RTD32 | RTD65 | RTD180 | RTD180-18000 | RTD320 |
| Storage temperature | -40 to +70°C (-40°F to 158°F) | | | | |
| Operating temperature | -25 to +55°C (-13°F to 131°F) | | | | |
| Tripping class IEC 60947-4-1 | 10A | | | | |
| Phase loss sensitive | Yes | | | | |
| Connection to contactor | Built-in links | | Pass through wire | Links for direct | Links for direct |
| Frequency limits | 0-400 Hz | | 50-60 Hz | | |
| Power dissipation per phase | 2.3 Watts | 3.7 Watts (52-65 A) setting range: 4.5 W | 3 Watts | | 5 Watts |
| Short circuit current rating 600V | 5kA rms | | | | |
| Aux contacts wire range | 14-10 AWG | | | | |
| Aux contacts tightening torque | 8.1 lb-in | | | | |


| Overload Aux Contact Ratings | | | | | |
|---------------------------------|-----------------------------------|------------------------|--------------|--------------|--------------|
| Contact Rating Code Designation | Thermal Continuous Current (Amps) | Maximum Current (Amps) | | | |
| | | 120 Volt | 240 Volt | 480 Volt | 600 Volt |
| | | Make / Break | Make / Break | Make / Break | Make / Break |
| 95-96 (NC) B600 | 5 | 30 / 3 | 15 / 1.5 | 7.5 / 0.75 | 6 / 0.6 |
| 97-98 (NO) C600 | 2.5 | 15 / 1.5 | 7.5 / 0.75 | 3.75 / 0.375 | 3 / 0.3 |

IEC Terminal Designations




Wiring Diagrams

RTD32 / RTD65






RTD180 / RTD320



GH15 Series Overload Relay Dimensions

45mm Contactor and Overload Dimensions




GH15BN, -CN, -DN, -ET, -FT + RTD32


| Overload Dimensions mm [in] | | | | | | | | | | | | | | |
|-----------------------------|----------------|-----------------|--|-----------------|------------------|-----------------|-----------------|-----------------|-----------------|-----------------|----------------|----------------|----------------|----------------|
| Contactor Model | Overload Model | Width | Height | | | Depth | D | E | E1 | F | G | H | I | |
| | | A | B | B1 | B2 | C | | | | | | | | |
| GH15BN | RTD32 | 45.0 [1.77] | 146.0 [5.75] | — | — | 85.0 [3.35] | 35.0 [1.38] | 60.0 [2.36] | 7.5 [0.30] | — | — | — | — | |
| GH15CN | | | | | | | | | | | | | | |
| GH15DN | | | | | | | | | | | | | | |
| GH15ET | | | | | | | | | | | | | | |
| GH15FT | | | | | | | | | | | | | | |
| GH15GT | RTD65 | 68.5 [2.70] | 169.0 [6.65] | — | — | 109.0 [4.29] | 50.0 [1.97] | 100.0 [3.94] | — | — | — | — | — | |
| GH15HT | | | | | | | | | | | | | | |
| GH15JT | | | | | | | | | | | | | | |
| GH15KT | RTD180 | 128.0 [5.04] | contactor and overloads do not have a link connector | 137.0 [5.39] | 81.0 [3.19] | 130.0 [5.12] | 70.0 [2.76] | 100.0 [3.94] | — | — | 68.0 [2.68] | 40.0 [1.57] | — | |
| GH15LT | | | | 162.0 [6.38] | 81.0 [3.19] | | | | | | | | | |
| GH15MT | | | | RTD180-18000 | 290.0 [11.42] | — | — | 145.0 [5.71] | 100.0 [3.94] | 130.0 [5.12] | — | 42.5 [1.67] | 68.0 [2.68] | 40.0 [1.57] |
| GH15NT | | | | | | | | | | | | | | |
| GH15PT | | | | | | | | | | | | | | |
| GH15RT | RTD320 | 145.0 [5.71] | 361.0 [14.21] | — | | 208.0 [8.19] | 120.0 [4.72] | 160.0 [6.30] | — | 80.0 [3.15] | 68.0 [2.68] | 40.0 [1.57] | 96.0 [3.78] | |
| GH15ST | | | | | | | | | | | | | | |
| GH15TT | | | | | | | | | | | | | | |

GH15 Series Overload Relay Dimensions

60mm Contactor and Overload Dimensions




79mm Contactor and Overload Dimensions




Note: See our website www.automationdirect.com for complete engineering drawings

GH15 Series Overload Relay Dimensions

110mm Contactor and Overload Dimensions



145mm Contactor and Overload Dimensions



Note: See our website www.automationdirect.com for complete engineering drawings